

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331419-935

Luminaire Tested: **SA2XXDIP-C865D1080U935-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331419-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D1080U935-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6646.8 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331419-935
CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331419-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46
1	97	92	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44	38
2	88	81	75	69	81	74	69	65	62	58	55	51	48	46	40	39	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	33	31	27
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27	23
5	67	56	48	42	62	52	44	39	43	38	34	36	32	29	29	26	24	20
6	62	50	42	36	57	46	39	34	39	34	30	32	28	25	26	23	21	18
7	57	45	37	32	53	42	35	30	35	30	26	30	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17	14
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19184	19184	19184
5°	19258	18979	19091
10°	19143	18787	18882
15°	18907	18544	18524
20°	18570	18179	18158
25°	18235	17728	17728
30°	17807	17316	17167
35°	17406	16821	16575
40°	16904	16326	16012
45°	16408	15835	15445
50°	15870	15325	14780
55°	15308	14728	14184
60°	14683	14018	13504
65°	14013	13310	12699
70°	13161	12458	11863
75°	11971	11472	11185
80°	10628	10302	9772
85°	8670	8262	7410



TEST NUMBER: P331419-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.7	1.7
10°-20°	314.4	4.7
20°-30°	462.1	7.0
30°-40°	536.8	8.1
40°-50°	536.2	8.1
50°-60°	467.6	7.0
60°-70°	345.7	5.2
70°-80°	195.8	2.9
80°-90°	57.3	0.9
90°-100°	208.0	3.1
100°-110°	705.7	10.6
110°-120°	749.7	11.3
120°-130°	617.2	9.3
130°-140°	495.6	7.5
140°-150°	374.5	5.6
150°-160°	263.2	4.0
160°-170°	154.9	2.3
170°-180°	50.4	0.8
0°-30°	888.2	13.4
0°-40°	1425.0	21.4
0°-60°	2428.7	36.5
0°-90°	3027.6	45.5
90°-120°	1663.4	25.0
90°-150°	3150.7	47.4
90°-180°	3619.0	54.4
0°-180°	6646.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1188	1188	1188	1188	1188	
5°	1188	1183	1171	1180	1178	113
15°	1131	1124	1109	1113	1108	318
25°	1024	1014	995	997	995	471
35°	883	871	853	847	841	551
45°	719	710	694	681	676	554
55°	544	537	523	510	504	486
65°	367	360	348	338	332	363
75°	192	189	184	178	179	205
85°	47	46	45	41	40	54
90°	1	14	34	32	33	4
95°	35	86	392	148	114	37
105°	122	184	741	1325	1127	130
115°	215	272	620	1280	1483	213
125°	300	355	596	1037	1203	266
135°	352	420	589	871	997	272
145°	402	462	586	728	796	252
155°	457	494	569	644	669	210
165°	498	513	545	578	587	140
175°	519	520	524	531	529	49
180°	520	520	520	520	520	



TEST NUMBER: P331419-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2
2.5°	1193.7	1192.7	1191.6	1190.7	1189.6	1188.0	1185.8	1183.5	1181.3	1179.1	1181.1
5°	1188.2	1187.1	1186.2	1185.2	1184.1	1182.2	1179.5	1176.6	1173.9	1171.0	1173.1
7.5°	1177.7	1176.1	1174.6	1172.9	1171.4	1169.2	1166.3	1163.5	1160.6	1157.8	1159.9
10°	1167.6	1165.9	1164.1	1162.3	1160.5	1158.1	1155.0	1152.0	1149.0	1145.9	1148.0
12.5°	1153.9	1152.4	1150.8	1149.2	1147.6	1145.3	1142.3	1139.2	1136.2	1133.2	1134.5
15°	1131.1	1129.5	1128.0	1126.5	1125.0	1122.6	1119.3	1115.9	1112.7	1109.4	1110.3
17.5°	1101.8	1100.3	1098.8	1097.3	1095.7	1093.3	1089.9	1086.6	1083.2	1079.9	1081.1
20°	1080.8	1079.3	1077.8	1076.2	1074.7	1072.2	1068.6	1065.1	1061.5	1058.0	1058.7
22.5°	1059.8	1057.7	1055.5	1053.3	1051.3	1048.5	1045.2	1041.8	1038.5	1035.1	1035.3
25°	1023.6	1021.7	1019.6	1017.6	1015.5	1012.4	1008.1	1003.8	999.4	995.1	995.7
27.5°	982.6	980.8	978.9	977.1	975.3	972.6	969.2	965.8	962.4	959.0	958.3
30°	955.1	953.1	951.1	949.1	947.0	944.1	940.3	936.5	932.6	928.8	928.1
32.5°	925.9	924.3	922.6	921.0	919.4	916.5	912.6	908.5	904.6	900.5	899.1
35°	883.1	880.6	878.0	875.6	873.0	869.7	865.6	861.6	857.5	853.4	852.0
37.5°	834.9	832.7	830.4	828.2	826.0	822.9	818.8	814.8	810.6	806.6	804.7
40°	802.0	800.0	798.0	795.9	793.9	790.8	786.8	782.7	778.7	774.6	772.3
42.5°	770.1	768.0	765.9	764.0	761.9	758.9	754.8	750.8	746.7	742.6	740.1
45°	718.6	716.9	715.1	713.3	711.5	708.7	704.9	701.1	697.3	693.5	690.7
47.5°	667.4	665.8	664.1	662.5	660.7	657.9	653.9	650.0	646.0	642.0	639.1
50°	631.8	630.5	629.3	628.0	626.7	624.3	620.8	617.2	613.6	610.1	606.6
52.5°	597.1	595.4	593.7	592.0	590.4	587.9	584.5	581.2	577.8	574.5	571.5
55°	543.8	542.3	540.8	539.2	537.7	535.5	532.4	529.3	526.3	523.2	520.2
57.5°	490.3	489.1	487.9	486.7	485.5	483.2	479.8	476.5	473.1	469.8	466.8
60°	454.7	453.7	452.7	451.7	450.6	448.4	444.8	441.3	437.7	434.1	431.4
62.5°	420.0	418.4	416.7	415.1	413.5	411.3	408.5	405.8	403.0	400.4	397.8
65°	366.8	365.2	363.7	362.1	360.7	358.6	356.1	353.5	351.0	348.4	346.2
67.5°	312.6	311.3	310.1	308.9	307.7	306.0	303.7	301.4	299.1	296.8	295.1
70°	278.8	277.8	276.7	275.7	274.7	273.0	270.8	268.5	266.2	263.9	262.2
72.5°	244.0	243.1	242.0	241.0	240.0	238.8	237.3	235.8	234.3	232.8	231.1
75°	191.9	191.4	190.9	190.5	189.9	189.0	187.8	186.5	185.2	183.9	182.4
77.5°	145.3	144.5	143.6	142.8	141.9	141.2	140.7	140.2	139.7	139.1	138.4
80°	114.3	114.0	113.7	113.5	113.2	112.9	112.4	111.8	111.3	110.8	110.0
82.5°	85.0	85.0	84.9	84.8	84.8	84.6	84.3	84.0	83.7	83.4	82.4
85°	46.8	46.6	46.3	46.1	45.8	45.5	45.3	45.0	44.8	44.6	43.8
87.5°	16.6	16.9	17.2	17.2	17.2	17.4	18.0	19.0	19.8	19.6	18.8
90°	1.0	4.0	8.0	10.0	12.0	15.0	20.0	27.0	33.0	34.0	33.0
92.5°	12.2	17.6	24.8	29.2	36.0	45.4	68.0	99.8	128.2	130.0	109.9
95°	35.0	39.0	49.0	58.0	74.0	98.0	144.0	231.0	347.1	392.1	343.1
97.5°	57.0	62.4	73.0	86.6	105.0	132.2	190.0	311.3	504.1	669.3	702.1
100°	77.0	80.0	89.0	105.0	125.0	153.0	206.0	328.0	544.1	790.1	934.2
102.5°	95.4	97.6	106.6	122.6	143.4	171.4	220.4	328.9	528.9	794.2	1020.6
105°	122.0	126.1	133.0	148.0	170.0	198.0	245.0	334.1	499.1	741.1	1007.2
107.5°	150.8	154.0	160.8	174.6	196.5	224.6	270.3	347.8	484.3	684.3	919.4
110°	170.0	174.0	180.0	193.0	214.0	243.1	287.1	359.0	481.1	657.1	864.2



TEST NUMBER: P331419-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	187.6	191.7	198.5	210.6	230.8	260.6	303.1	371.1	481.9	639.6	825.8
115°	215.1	220.1	226.0	238.1	258.0	285.1	328.0	389.1	486.1	620.1	778.2
117.5°	243.5	247.5	253.5	264.1	283.3	311.3	351.0	408.3	493.3	610.7	748.1
120°	261.1	265.0	271.0	280.1	300.1	328.0	367.0	421.1	498.1	605.1	732.1
122.5°	277.8	281.0	287.1	296.9	316.8	345.7	382.3	432.3	503.7	601.9	718.5
125°	300.1	303.1	309.1	321.1	341.0	369.1	405.1	450.1	512.1	596.2	699.1
127.5°	317.6	321.7	330.1	343.3	362.5	391.2	426.3	466.7	520.7	592.7	681.1
130°	328.0	332.1	342.1	356.1	376.1	404.1	439.1	477.1	527.1	591.1	669.2
132.5°	337.7	342.5	353.3	368.1	388.9	416.9	450.3	487.5	533.5	590.3	659.5
135°	352.1	356.1	368.1	383.1	406.0	434.1	466.1	501.1	541.1	589.1	646.1
137.5°	365.7	370.5	382.5	398.5	421.3	447.3	478.9	511.5	547.9	588.9	636.7
140°	376.1	380.0	392.1	408.1	430.1	456.1	486.1	517.1	551.1	588.1	631.1
142.5°	386.5	389.7	400.9	416.9	438.1	462.5	491.7	521.9	553.5	588.1	625.5
145°	402.1	406.0	416.1	431.1	451.1	473.1	500.1	528.1	556.1	586.1	618.1
147.5°	418.9	421.9	431.4	445.3	461.9	481.5	506.9	531.5	556.9	582.6	610.5
150°	430.1	433.1	441.1	454.1	469.1	487.1	510.1	533.1	556.1	580.1	604.1
152.5°	441.3	442.7	450.6	462.1	476.3	492.7	513.3	533.9	554.5	576.1	598.5
155°	457.1	458.1	464.1	475.1	486.1	501.1	518.1	535.1	552.1	569.1	588.1
157.5°	470.3	471.3	476.1	485.7	494.5	507.1	521.5	535.1	547.5	561.9	578.3
160°	479.1	480.1	484.1	492.1	500.1	511.1	523.1	535.1	545.1	557.2	571.1
162.5°	487.9	487.3	491.3	497.7	504.9	513.5	523.9	534.3	542.7	553.1	564.7
165°	498.1	497.1	499.1	505.1	510.1	516.1	525.1	532.1	538.1	545.1	554.1
167.5°	506.5	505.3	507.1	510.9	514.5	518.3	524.9	530.7	533.5	538.1	543.7
170°	512.1	510.1	511.1	514.1	516.1	519.1	524.1	529.1	531.1	534.1	538.1
172.5°	515.3	514.1	513.5	516.5	517.7	519.9	523.3	526.7	527.9	529.3	532.5
175°	519.1	518.1	517.1	519.1	519.1	520.1	522.1	524.1	523.1	524.1	525.1
177.5°	520.9	519.3	518.5	520.1	520.1	520.1	520.9	522.5	520.9	520.1	520.9
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331419-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2
2.5°	1183.1	1185.2	1187.1	1188.0	1187.6	1187.1	1186.8	1186.4
5°	1175.1	1177.2	1179.2	1179.9	1179.5	1179.0	1178.5	1177.9
7.5°	1161.8	1163.9	1166.0	1166.7	1166.1	1165.5	1165.0	1164.4
10°	1150.0	1152.0	1154.1	1154.7	1153.9	1153.1	1152.4	1151.7
12.5°	1136.0	1137.4	1138.8	1139.3	1138.7	1138.2	1137.6	1137.0
15°	1111.4	1112.4	1113.4	1113.3	1112.1	1110.8	1109.5	1108.2
17.5°	1082.2	1083.4	1084.6	1084.5	1083.3	1082.1	1080.9	1079.7
20°	1059.5	1060.2	1061.0	1060.8	1059.9	1058.9	1057.8	1056.8
22.5°	1035.4	1035.5	1035.7	1035.5	1034.8	1034.2	1033.6	1033.0
25°	996.2	996.6	997.1	997.1	996.6	996.2	995.7	995.1
27.5°	957.5	956.7	956.0	955.0	953.7	952.5	951.3	950.1
30°	927.3	926.6	925.8	924.9	923.9	922.9	921.9	920.8
32.5°	897.8	896.4	895.0	893.8	892.9	891.8	890.8	889.8
35°	850.4	848.9	847.4	845.9	844.7	843.4	842.1	840.9
37.5°	802.9	801.0	799.1	797.5	796.3	795.1	793.9	792.6
40°	770.1	767.8	765.5	763.8	762.8	761.8	760.8	759.7
42.5°	737.6	735.1	732.7	730.7	729.3	727.9	726.4	725.0
45°	687.9	685.1	682.3	680.4	679.4	678.4	677.3	676.4
47.5°	636.2	633.3	630.3	628.1	626.6	625.2	623.7	622.2
50°	603.0	599.4	595.9	593.5	592.2	590.9	589.7	588.4
52.5°	568.5	565.6	562.7	560.3	558.7	557.0	555.3	553.6
55°	517.2	514.1	511.1	508.9	507.6	506.4	505.1	503.9
57.5°	463.8	460.8	457.8	455.8	454.9	453.9	453.0	451.9
60°	428.6	425.8	423.0	421.2	420.4	419.7	418.9	418.2
62.5°	395.1	392.5	389.9	388.2	387.2	386.2	385.3	384.4
65°	343.9	341.6	339.3	337.5	336.3	335.0	333.7	332.4
67.5°	293.3	291.4	289.7	288.3	287.3	286.3	285.2	284.2
70°	260.4	258.6	256.8	255.4	254.4	253.4	252.4	251.3
72.5°	229.3	227.5	225.8	224.5	223.6	222.8	222.0	221.2
75°	180.9	179.3	177.9	177.4	177.9	178.4	178.8	179.3
77.5°	137.7	136.9	136.1	135.3	134.7	134.0	133.3	132.5
80°	109.3	108.6	107.8	107.1	106.6	106.2	105.6	105.1
82.5°	81.5	80.5	79.6	79.0	78.9	78.8	78.7	78.6
85°	43.0	42.3	41.5	41.0	40.7	40.5	40.2	40.0
87.5°	18.0	17.0	16.8	16.5	16.4	16.2	15.9	15.8
90°	32.0	30.0	32.0	33.0	33.0	33.0	33.0	33.0
92.5°	87.2	74.8	66.4	60.2	59.4	56.2	57.0	55.4
95°	262.1	201.0	159.0	137.0	124.0	116.1	113.0	114.0
97.5°	611.5	500.3	392.1	319.9	272.1	247.5	232.8	224.5
100°	913.2	789.2	652.1	531.1	448.1	405.1	376.1	358.1
102.5°	1110.9	1082.8	982.6	854.4	764.1	690.8	654.5	630.2
105°	1215.2	1328.3	1341.3	1308.3	1246.2	1184.2	1141.3	1127.2
107.5°	1140.1	1310.3	1414.3	1462.7	1470.5	1467.1	1458.4	1439.9
110°	1075.2	1254.2	1382.2	1464.3	1507.3	1526.3	1535.3	1534.3



TEST NUMBER: P331419-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1016.0	1187.8	1324.6	1418.7	1478.5	1510.3	1527.3	1532.7
115°	943.2	1097.3	1228.2	1331.3	1402.3	1448.3	1474.3	1483.3
117.5°	888.4	1023.6	1142.5	1239.1	1311.5	1360.0	1387.5	1395.1
120°	861.2	985.2	1091.2	1182.2	1252.2	1299.2	1328.3	1338.3
122.5°	839.6	953.2	1053.6	1135.8	1198.6	1244.8	1270.7	1279.0
125°	808.1	911.2	999.2	1074.2	1132.2	1170.3	1195.2	1203.2
127.5°	777.1	870.4	953.4	1022.6	1073.2	1108.8	1130.4	1136.9
130°	757.2	843.2	922.2	988.2	1037.2	1071.3	1091.2	1099.2
132.5°	738.0	817.6	890.2	952.2	1000.4	1034.4	1052.8	1060.0
135°	711.1	777.1	843.2	899.1	942.2	975.2	993.2	997.2
137.5°	689.7	744.9	797.4	846.2	885.4	913.8	929.6	935.6
140°	676.1	724.2	770.2	814.2	846.2	872.2	887.2	893.2
142.5°	665.0	705.8	745.4	782.1	812.5	836.2	849.5	850.8
145°	649.1	682.2	713.2	742.2	766.1	783.2	793.2	796.2
147.5°	637.0	663.0	687.2	708.3	728.1	741.8	748.6	750.4
150°	628.1	650.1	671.1	689.1	704.1	716.2	722.1	723.2
152.5°	619.3	639.7	657.5	673.1	684.9	695.3	699.7	699.9
155°	607.1	623.1	638.1	649.1	660.1	667.1	671.1	669.2
157.5°	592.9	606.3	618.9	627.5	635.3	641.1	642.9	642.9
160°	584.1	595.1	606.1	613.1	620.1	625.1	626.1	626.1
162.5°	575.3	584.7	594.1	599.5	606.5	609.9	610.9	610.1
165°	562.1	569.1	576.1	580.1	584.1	588.1	588.1	587.1
167.5°	549.5	554.9	559.7	563.4	565.1	567.3	567.1	565.9
170°	543.1	546.1	550.1	552.1	553.1	556.1	555.1	553.1
172.5°	535.9	538.1	541.3	542.5	543.5	544.9	543.9	542.7
175°	528.1	529.1	530.1	531.1	531.1	532.1	531.1	529.1
177.5°	522.5	522.5	523.3	523.3	523.3	523.3	522.5	520.9
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1

(END OF REPORT)