

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331375-935

Luminaire Tested: **SA2XXDIP-C865D330U935-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331375-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C865D330U935-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4408.0 lumens  
Efficiency: N/A  
Efficacy: 101.3 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331375-935  
CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331375-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	79	79	79	74
1	104	100	96	93	99	95	92	89	86	84	81	78	76	74	71	69	68	64
2	95	88	82	77	90	84	79	74	76	72	69	69	66	63	63	60	58	55
3	87	78	71	65	83	75	68	63	68	63	59	62	58	54	56	53	50	47
4	80	70	62	56	76	67	60	54	61	55	51	56	51	47	51	47	44	41
5	74	63	55	49	70	60	53	47	55	49	44	51	46	42	46	42	39	36
6	69	57	49	43	65	54	47	42	50	44	39	46	41	37	42	38	35	32
7	64	52	44	38	61	50	42	37	46	40	35	42	37	33	39	34	31	29
8	60	47	39	34	57	45	38	33	42	36	31	39	34	30	36	31	28	26
9	56	43	36	31	53	42	35	30	39	33	28	36	31	27	33	29	26	24
10	52	40	33	28	50	39	32	27	36	30	26	33	28	25	31	27	23	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	24001	24001	24001	24001
5°	26909	24159	21409	24159
10°	30836	23961	18528	23961
15°	34111	23520	16368	23520
20°	33593	23048	14921	23048
25°	30289	22422	14004	22422
30°	25031	21420	13336	21420
35°	18242	20371	12861	20371
40°	14570	19134	12596	19134
45°	12732	17701	12237	17701
50°	11969	16317	11997	16317
55°	11032	14908	11674	14908
60°	10111	13411	11179	13411
65°	9211	12069	10693	12069
70°	8360	10763	9980	10763
75°	7411	9301	8840	9301
80°	6369	7699	7113	7699
85°	5706	5706	4224	5706



TEST NUMBER: P331375-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.6	3.2
10°-20°	411.6	9.3
20°-30°	597.3	13.6
30°-40°	630.3	14.3
40°-50°	558.1	12.7
50°-60°	445.4	10.1
60°-70°	302.7	6.9
70°-80°	155.2	3.5
80°-90°	38.4	0.9
90°-100°	12.8	0.3
100°-110°	47.1	1.1
110°-120°	125.8	2.9
120°-130°	207.7	4.7
130°-140°	220.8	5.0
140°-150°	205.3	4.7
150°-160°	165.0	3.7
160°-170°	106.3	2.4
170°-180°	36.6	0.8
0°-30°	1150.5	26.1
0°-40°	1780.8	40.4
0°-60°	2784.3	63.2
0°-90°	3280.6	74.4
90°-120°	185.7	4.2
90°-150°	819.5	18.6
90°-180°	1127.0	25.6
0°-180°	4408.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1486	1486	1486	1486	1486	
5°	1660	1491	1321	1491	1660	166
15°	2041	1407	979	1407	2041	563
25°	1700	1259	786	1259	1700	768
35°	926	1034	652	1034	926	602
45°	558	775	536	775	558	438
55°	392	530	415	530	392	351
65°	241	316	280	316	241	240
75°	119	149	142	149	119	127
85°	31	31	23	31	31	34
90°	8	0	8	0	8	5
95°	12	18	12	18	12	11
105°	21	85	21	85	21	22
115°	23	160	23	160	23	57
125°	238	226	238	226	238	206
135°	289	280	289	280	289	223
145°	330	325	330	325	330	206
155°	358	358	358	358	358	165
165°	376	377	376	377	376	106
175°	383	386	383	386	383	37
180°	385	385	385	385	385	



TEST NUMBER: P331375-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1555.1	1555.6	1556.5	1549.2	1548.3	1548.3	1541.9	1536.4	1530.0	1521.3	1522.2
5°	1660.3	1666.6	1668.8	1662.0	1651.7	1650.5	1640.8	1624.8	1610.0	1597.9	1589.4
7.5°	1785.7	1788.2	1782.6	1773.6	1765.9	1752.2	1734.1	1716.5	1691.7	1669.0	1652.0
10°	1880.8	1884.2	1874.5	1861.3	1850.5	1834.4	1808.2	1781.3	1748.8	1717.4	1692.2
12.5°	1953.0	1961.4	1949.0	1947.2	1928.6	1906.7	1875.4	1861.8	1816.0	1772.2	1745.2
15°	2040.7	2040.1	2041.3	2030.4	2016.7	2013.3	1980.2	1944.2	1879.6	1853.9	1809.4
17.5°	2015.3	2024.0	2028.1	2027.9	2027.6	2025.4	2014.8	1992.1	1959.7	1918.0	1866.6
20°	1955.1	1966.4	1968.2	1981.3	1988.7	1998.5	2002.4	1996.1	1976.2	1941.3	1896.8
22.5°	1861.8	1865.0	1870.4	1890.8	1906.9	1931.3	1944.0	1965.1	1957.4	1940.4	1903.2
25°	1700.2	1694.5	1714.5	1724.8	1762.0	1800.8	1828.8	1859.6	1887.1	1903.6	1892.7
27.5°	1506.2	1497.6	1527.6	1554.9	1585.0	1627.1	1670.8	1722.3	1765.1	1818.7	1837.1
30°	1342.6	1347.7	1376.3	1405.4	1451.1	1510.5	1559.7	1616.3	1677.4	1737.3	1779.1
32.5°	1166.1	1185.9	1204.0	1248.6	1288.9	1355.1	1427.1	1497.9	1574.1	1642.3	1706.8
35°	925.5	948.4	973.5	1006.1	1062.6	1128.3	1198.6	1294.0	1398.0	1491.2	1567.7
37.5°	779.0	775.4	789.8	813.3	859.1	912.1	993.1	1087.4	1209.7	1319.1	1427.1
40°	691.3	689.0	699.3	721.0	755.9	794.7	865.6	948.4	1062.0	1195.8	1324.3
42.5°	630.9	632.3	638.0	653.3	677.3	709.2	762.2	832.8	936.9	1062.7	1200.9
45°	557.6	561.6	567.9	575.3	589.0	615.3	645.0	695.3	777.6	882.7	1018.6
47.5°	504.8	504.9	511.3	517.8	526.0	540.8	565.0	596.6	654.6	740.2	857.1
50°	476.5	472.5	477.1	482.2	490.8	501.0	517.0	546.7	585.6	654.7	752.4
52.5°	441.8	441.9	446.0	447.9	455.6	465.9	480.4	501.0	536.2	590.3	670.6
55°	391.9	394.8	397.1	400.5	407.3	414.7	426.2	439.9	467.4	507.9	567.3
57.5°	345.1	345.9	348.3	354.8	359.1	366.0	376.9	389.3	407.1	437.1	481.8
60°	313.1	313.1	317.6	320.5	326.2	333.0	341.6	353.6	369.6	394.2	430.2
62.5°	283.9	283.4	285.2	289.9	294.2	300.7	309.2	319.3	334.4	356.3	385.9
65°	241.1	240.0	243.4	244.5	249.1	255.4	262.3	273.1	285.1	301.1	327.4
67.5°	199.9	201.3	203.2	205.3	207.8	214.5	219.0	226.7	236.9	250.1	267.9
70°	177.1	177.1	177.1	178.8	182.3	185.7	190.3	196.6	206.2	217.7	233.7
72.5°	151.5	153.3	155.2	154.1	158.5	160.6	166.0	169.5	178.8	186.1	200.3
75°	118.8	118.8	118.8	121.7	123.4	125.1	128.5	132.0	136.6	145.7	153.1
77.5°	88.7	88.4	89.0	89.7	91.5	93.6	94.6	97.7	101.9	106.2	112.4
80°	68.5	69.7	70.3	71.4	71.4	72.6	73.1	77.1	80.0	82.8	86.9
82.5°	53.0	53.2	53.4	53.6	54.1	54.8	56.2	57.5	58.5	60.9	64.0
85°	30.8	30.3	30.3	31.4	30.8	30.8	32.0	33.1	33.1	33.7	35.4
87.5°	13.3	13.3	13.8	13.3	13.3	13.7	13.6	13.1	13.5	13.9	14.3
90°	7.5	7.4	7.2	7.1	7.1	6.8	6.5	6.2	5.9	5.6	5.1
92.5°	7.5	7.4	7.4	7.3	7.2	7.1	7.0	6.8	6.6	6.5	6.2
95°	12.0	12.1	12.1	12.1	12.2	12.1	11.8	11.5	11.2	10.8	10.4
97.5°	16.0	15.9	15.8	15.8	15.7	15.5	15.2	15.1	14.8	14.6	13.5
100°	18.7	18.5	18.4	18.3	18.2	17.8	17.4	16.9	16.4	15.8	14.8
102.5°	20.0	19.8	19.6	19.5	19.3	18.9	18.3	17.6	17.0	16.3	25.1
105°	21.2	20.9	20.7	20.4	20.1	19.7	19.0	18.3	17.7	17.0	33.8
107.5°	21.8	21.5	21.3	21.0	20.8	21.0	21.7	22.4	23.1	23.8	44.0
110°	22.0	21.8	21.5	21.3	21.0	23.9	30.1	36.3	42.5	48.7	66.6



TEST NUMBER: P331375-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	22.2	22.0	21.8	21.6	21.4	32.6	55.2	77.7	100.3	122.9	127.3
115°	22.8	27.3	31.8	36.2	40.6	57.2	85.8	114.5	143.1	171.8	170.2
117.5°	93.2	107.9	122.5	137.2	151.8	162.6	169.4	176.4	183.3	190.3	189.2
120°	169.8	178.1	186.5	194.8	203.2	207.0	206.3	205.5	204.8	204.1	202.9
122.5°	211.9	213.5	215.2	216.8	218.3	219.0	218.5	218.1	217.7	217.2	216.0
125°	238.0	237.8	237.6	237.5	237.3	236.9	236.5	236.1	235.7	235.2	234.0
127.5°	254.5	254.4	254.4	254.4	254.3	254.0	253.4	252.8	252.1	251.5	250.6
130°	264.8	264.8	264.8	264.9	265.0	264.7	264.0	263.3	262.6	262.0	261.3
132.5°	274.7	274.8	274.9	274.9	275.0	274.7	274.1	273.6	273.0	272.4	271.7
135°	289.2	289.4	289.5	289.6	289.7	289.5	288.9	288.3	287.7	287.1	286.5
137.5°	302.5	302.6	302.9	303.1	303.2	303.1	302.5	301.9	301.3	300.7	300.1
140°	310.6	311.0	311.3	311.6	311.9	311.8	311.3	310.6	310.1	309.5	308.9
142.5°	318.7	319.0	319.3	319.6	319.9	319.9	319.3	318.8	318.3	317.8	317.0
145°	329.8	330.2	330.5	330.8	331.1	331.1	330.6	330.2	329.8	329.3	328.3
147.5°	339.8	340.0	340.3	340.5	340.8	340.8	340.4	340.1	339.8	339.5	338.5
150°	345.8	346.0	346.4	346.7	347.0	347.0	346.6	346.2	345.9	345.5	344.5
152.5°	350.9	351.3	351.7	352.1	352.5	352.5	352.1	351.8	351.4	351.0	350.1
155°	358.0	358.5	359.0	359.5	360.0	360.1	359.6	359.3	359.0	358.5	357.8
157.5°	364.5	365.0	365.5	365.9	366.4	366.4	366.1	365.7	365.2	364.8	364.3
160°	368.3	368.8	369.2	369.6	370.1	370.1	369.7	369.4	368.9	368.6	368.2
162.5°	371.4	372.0	372.5	373.0	373.6	373.6	373.2	372.7	372.4	372.0	371.6
165°	376.1	376.5	376.9	377.4	377.8	377.8	377.4	376.9	376.5	376.1	375.9
167.5°	379.0	379.6	380.1	380.7	381.3	381.3	380.9	380.5	380.0	379.6	379.4
170°	380.8	381.4	381.9	382.5	383.1	383.1	382.7	382.3	381.9	381.4	381.3
172.5°	382.2	382.7	383.3	383.8	384.4	384.4	384.0	383.6	383.1	382.7	382.6
175°	383.3	383.9	384.6	385.2	385.8	385.9	385.5	385.0	384.6	384.2	384.1
177.5°	384.1	384.5	385.0	385.4	385.8	385.9	385.6	385.2	384.9	384.5	384.4
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331375-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1525.4	1521.7	1519.5	1511.2	1503.9	1496.6	1494.4	1495.2	1485.2	1475.6	1471.4
5°	1584.8	1573.4	1562.5	1547.1	1528.9	1508.8	1498.6	1490.6	1470.6	1448.9	1436.3
7.5°	1638.1	1621.7	1600.9	1571.8	1545.2	1513.7	1493.7	1476.0	1446.8	1416.2	1397.4
10°	1670.5	1648.2	1621.3	1586.0	1553.4	1515.1	1488.2	1461.5	1427.1	1390.6	1367.7
12.5°	1698.4	1668.4	1641.9	1596.5	1558.0	1510.1	1478.3	1440.4	1404.3	1360.9	1338.5
15°	1764.8	1709.3	1659.1	1607.7	1560.2	1493.4	1458.0	1407.1	1359.7	1306.1	1280.3
17.5°	1816.1	1753.9	1674.6	1609.3	1553.9	1480.0	1428.0	1367.0	1311.0	1249.6	1214.6
20°	1845.4	1773.9	1688.8	1611.1	1544.8	1460.3	1403.7	1341.4	1275.7	1206.6	1168.9
22.5°	1862.7	1787.6	1703.4	1604.2	1526.6	1444.2	1373.1	1304.8	1238.3	1163.6	1124.1
25°	1868.2	1799.7	1710.5	1598.5	1503.7	1410.6	1324.9	1258.6	1178.0	1108.4	1050.7
27.5°	1841.0	1791.8	1706.2	1587.8	1477.3	1368.4	1272.9	1197.8	1112.8	1037.2	979.1
30°	1807.7	1779.1	1695.7	1576.8	1456.3	1339.2	1234.1	1148.9	1064.4	987.8	928.4
32.5°	1756.0	1749.8	1676.5	1561.3	1433.9	1302.2	1193.3	1107.3	1013.7	938.4	881.8
35°	1654.5	1682.0	1635.6	1526.6	1391.7	1249.5	1131.8	1033.5	936.4	864.4	811.2
37.5°	1518.5	1586.7	1574.5	1475.7	1334.8	1192.1	1062.2	959.5	866.9	794.3	742.1
40°	1424.9	1511.7	1524.2	1436.8	1294.6	1147.8	1010.1	907.8	817.5	751.3	698.7
42.5°	1324.3	1425.7	1460.3	1390.3	1250.7	1101.1	963.5	857.6	768.2	703.8	657.1
45°	1155.8	1290.0	1352.3	1312.3	1177.5	1024.3	882.7	775.2	694.1	633.6	597.6
47.5°	998.2	1144.9	1228.6	1214.5	1096.0	944.3	804.3	701.2	622.2	573.9	541.7
50°	886.7	1037.5	1138.6	1143.2	1037.5	887.3	746.7	649.6	577.0	531.9	505.6
52.5°	789.8	933.8	1044.0	1068.2	972.2	827.9	695.1	598.4	534.5	493.0	469.5
55°	663.3	785.0	907.2	951.8	874.7	737.5	614.8	529.6	469.6	441.1	420.5
57.5°	551.5	652.9	765.8	815.0	767.5	650.1	534.9	461.1	412.3	387.4	371.6
60°	492.5	572.5	673.0	731.8	690.7	586.2	485.6	415.3	375.4	353.1	338.2
62.5°	437.6	508.5	593.5	647.3	624.9	526.3	436.3	374.2	339.7	318.8	308.1
65°	361.1	417.1	482.8	532.4	517.6	442.7	369.1	315.9	288.5	271.9	263.4
67.5°	297.3	337.8	383.3	426.9	414.9	361.9	302.6	261.3	240.9	226.6	221.4
70°	257.1	287.9	328.5	363.3	353.6	310.2	263.4	228.0	210.3	198.3	193.1
72.5°	218.7	244.1	275.0	303.5	297.0	260.9	221.8	195.0	181.4	170.4	166.2
75°	165.1	184.5	203.4	222.2	220.5	192.5	169.7	149.1	138.3	129.7	127.9
77.5°	121.9	132.8	145.6	156.8	153.7	137.7	119.8	108.0	100.0	94.3	93.3
80°	93.2	99.4	108.6	116.6	112.5	105.7	91.4	82.8	77.1	71.4	69.1
82.5°	67.5	73.8	79.3	83.6	80.6	74.1	65.3	59.5	56.1	52.2	51.3
85°	35.4	38.8	41.2	42.3	41.2	37.1	33.1	30.8	28.0	26.3	25.7
87.5°	14.6	14.6	14.5	15.2	13.7	13.6	11.6	10.1	9.8	9.5	8.7
90°	4.6	4.0	3.6	3.0	2.3	1.6	0.9	0.3	0.9	1.6	2.3
92.5°	5.9	5.7	5.5	5.3	5.4	5.5	5.6	5.6	5.6	5.5	5.4
95°	10.0	9.6	9.1	9.9	12.0	14.0	16.0	18.1	16.0	14.0	12.0
97.5°	12.5	11.5	10.5	12.9	18.7	24.4	30.1	35.9	30.1	24.4	18.7
100°	13.8	12.7	11.6	15.4	23.8	32.3	40.8	49.2	40.8	32.3	23.8
102.5°	33.9	42.7	51.5	56.8	58.6	60.4	62.2	64.0	62.2	60.4	58.6
105°	50.8	67.7	84.6	92.0	90.2	88.3	86.4	84.6	86.4	88.3	90.2
107.5°	64.3	84.6	104.8	114.2	112.7	111.2	109.7	108.1	109.7	111.2	112.7
110°	84.5	102.4	120.2	128.5	127.3	126.0	124.6	123.3	124.6	126.0	127.3





TEST NUMBER: P331375-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	131.7	136.1	140.5	142.2	141.0	139.9	138.7	137.6	138.7	139.9	141.0
115°	168.7	167.1	165.6	164.3	163.2	162.2	161.1	160.1	161.1	162.2	163.2
117.5°	188.1	187.1	186.0	184.9	183.7	182.5	181.3	180.2	181.3	182.5	183.7
120°	201.8	200.7	199.6	198.5	197.7	196.7	195.8	194.8	195.8	196.7	197.7
122.5°	214.7	213.5	212.3	211.3	210.3	209.3	208.4	207.3	208.4	209.3	210.3
125°	232.9	231.7	230.6	229.5	228.8	227.9	227.1	226.4	227.1	227.9	228.8
127.5°	249.8	248.8	248.0	247.1	246.2	245.3	244.4	243.5	244.4	245.3	246.2
130°	260.6	259.9	259.2	258.4	257.4	256.4	255.5	254.4	255.5	256.4	257.4
132.5°	271.0	270.4	269.7	269.0	268.1	267.3	266.4	265.6	266.4	267.3	268.1
135°	285.9	285.3	284.8	284.0	283.0	282.1	281.0	280.1	281.0	282.1	283.0
137.5°	299.4	298.8	298.2	297.5	296.8	296.1	295.4	294.7	295.4	296.1	296.8
140°	308.2	307.5	306.9	306.3	305.7	305.2	304.8	304.3	304.8	305.2	305.7
142.5°	316.2	315.5	314.7	314.1	313.7	313.1	312.7	312.3	312.7	313.1	313.7
145°	327.3	326.1	325.1	324.6	324.7	324.8	324.9	324.9	324.9	324.8	324.7
147.5°	337.4	336.3	335.3	334.9	335.1	335.4	335.6	335.9	335.6	335.4	335.1
150°	343.5	342.5	341.6	341.2	341.6	342.1	342.5	342.9	342.5	342.1	341.6
152.5°	349.1	348.2	347.2	347.1	347.5	348.0	348.5	349.0	348.5	348.0	347.5
155°	357.1	356.4	355.6	355.5	356.0	356.6	357.1	357.7	357.1	356.6	356.0
157.5°	363.8	363.3	362.7	362.7	363.2	363.6	364.1	364.5	364.1	363.6	363.2
160°	367.8	367.5	367.1	367.1	367.5	367.8	368.2	368.6	368.2	367.8	367.5
162.5°	371.3	370.9	370.7	370.7	371.0	371.4	371.8	372.1	371.8	371.4	371.0
165°	375.7	375.6	375.4	375.5	375.8	376.2	376.6	376.9	376.6	376.2	375.8
167.5°	379.3	379.1	378.9	379.0	379.4	379.8	380.1	380.5	380.1	379.8	379.4
170°	381.2	381.0	380.9	381.0	381.4	381.8	382.1	382.5	382.1	381.8	381.4
172.5°	382.5	382.4	382.2	382.4	382.7	383.1	383.5	383.8	383.5	383.1	382.7
175°	383.9	383.8	383.7	383.8	384.3	384.7	385.1	385.6	385.1	384.7	384.3
177.5°	384.4	384.4	384.4	384.4	384.8	385.1	385.5	385.8	385.5	385.1	384.8
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331375-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1466.9	1464.1	1454.6	1449.6	1441.3	1433.6	1428.5	1430.8	1432.6	1431.7	1430.4
5°	1424.9	1414.0	1397.4	1383.1	1372.9	1354.0	1346.0	1342.0	1338.6	1334.6	1330.6
7.5°	1374.8	1357.7	1333.9	1313.5	1294.3	1270.9	1257.6	1249.6	1241.4	1232.3	1224.3
10°	1339.2	1315.2	1290.0	1261.5	1238.6	1217.5	1198.6	1186.0	1174.7	1163.7	1155.8
12.5°	1301.7	1274.0	1242.9	1203.9	1178.7	1148.5	1145.6	1123.4	1105.6	1098.9	1089.5
15°	1242.1	1203.2	1163.7	1117.5	1097.5	1070.1	1052.9	1035.8	1020.4	1009.5	1006.7
17.5°	1174.3	1124.0	1084.8	1051.5	1018.7	990.7	974.9	961.2	948.5	934.0	932.0
20°	1122.7	1079.2	1036.4	1007.2	973.5	944.9	925.5	911.8	901.0	892.4	884.9
22.5°	1073.8	1026.2	987.0	955.1	921.9	898.8	883.5	870.2	861.2	851.7	844.7
25°	995.2	958.1	915.2	879.3	851.8	837.0	824.4	813.0	807.3	801.0	793.0
27.5°	926.5	885.3	845.2	817.3	793.2	780.1	771.2	763.4	758.0	754.3	749.8
30°	878.1	836.4	804.9	777.6	757.6	744.4	738.7	734.2	727.9	725.6	723.3
32.5°	831.5	793.9	767.1	743.3	724.2	715.7	710.4	706.3	701.4	699.0	694.5
35°	765.6	734.2	707.8	694.7	679.3	671.8	667.9	662.2	657.5	655.3	654.7
37.5°	703.5	676.2	658.9	642.0	635.5	630.9	625.5	621.6	620.2	619.8	619.3
40°	663.3	641.0	625.6	611.9	609.0	602.2	597.6	594.2	594.2	594.8	594.2
42.5°	626.7	606.7	593.1	581.3	577.9	573.9	569.3	569.0	570.0	571.9	570.0
45°	571.3	557.1	547.3	541.6	535.3	531.3	530.7	532.4	533.0	533.6	535.3
47.5°	520.4	510.8	502.0	495.8	493.0	492.3	491.6	494.6	497.4	498.4	501.0
50°	490.2	479.3	471.9	467.9	465.6	464.5	465.6	469.1	471.3	474.2	475.9
52.5°	456.3	448.7	443.6	440.5	439.5	440.2	440.5	444.4	448.1	449.0	449.9
55°	409.7	403.9	402.8	397.6	399.9	399.3	402.2	404.5	407.9	411.4	411.9
57.5°	363.0	358.4	355.3	355.9	356.5	359.0	361.4	365.4	369.1	372.7	373.1
60°	331.9	329.7	328.0	328.0	329.1	332.5	335.4	339.3	341.6	344.0	345.6
62.5°	303.6	301.4	299.6	300.5	303.5	305.6	308.8	311.0	313.3	315.6	316.4
65°	258.8	257.7	259.4	260.5	261.1	264.0	267.9	269.7	271.9	273.1	277.1
67.5°	217.6	217.7	217.6	219.1	222.5	223.2	227.0	230.9	231.4	233.6	236.2
70°	189.7	190.8	192.0	193.1	196.0	197.1	199.9	201.6	204.0	205.7	207.4
72.5°	164.1	164.3	165.5	165.2	167.6	170.1	172.5	174.3	176.5	178.7	180.4
75°	126.2	126.2	127.4	127.9	130.9	133.7	133.1	134.2	136.6	138.8	140.0
77.5°	92.2	90.9	92.2	92.8	93.7	96.1	96.5	98.2	100.7	100.0	101.3
80°	70.3	68.5	70.3	70.9	70.9	73.7	73.7	74.8	76.5	74.8	76.5
82.5°	50.2	49.3	50.6	50.7	51.7	51.7	52.7	52.9	54.6	53.8	54.6
85°	25.1	24.5	25.1	24.5	25.1	25.7	25.7	25.1	25.1	26.3	24.5
87.5°	8.4	8.0	7.7	7.7	7.4	7.1	6.6	6.7	6.8	5.9	5.9
90°	3.0	3.6	4.0	4.6	5.1	5.6	5.9	6.2	6.5	6.8	7.1
92.5°	5.3	5.5	5.7	5.9	6.2	6.5	6.6	6.8	7.0	7.1	7.2
95°	9.9	9.1	9.6	10.0	10.4	10.8	11.2	11.5	11.8	12.1	12.2
97.5°	12.9	10.5	11.5	12.5	13.5	14.6	14.8	15.1	15.2	15.5	15.7
100°	15.4	11.6	12.7	13.8	14.8	15.8	16.4	16.9	17.4	17.8	18.2
102.5°	56.8	51.5	42.7	33.9	25.1	16.3	17.0	17.6	18.3	18.9	19.3
105°	92.0	84.6	67.7	50.8	33.8	17.0	17.7	18.3	19.0	19.7	20.1
107.5°	114.2	104.8	84.6	64.3	44.0	23.8	23.1	22.4	21.7	21.0	20.8
110°	128.5	120.2	102.4	84.5	66.6	48.7	42.5	36.3	30.1	23.9	21.0



TEST NUMBER: P331375-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	142.2	140.5	136.1	131.7	127.3	122.9	100.3	77.7	55.2	32.6	21.4
115°	164.3	165.6	167.1	168.7	170.2	171.8	143.1	114.5	85.8	57.2	40.6
117.5°	184.9	186.0	187.1	188.1	189.2	190.3	183.3	176.4	169.4	162.6	151.8
120°	198.5	199.6	200.7	201.8	202.9	204.1	204.8	205.5	206.3	207.0	203.2
122.5°	211.3	212.3	213.5	214.7	216.0	217.2	217.7	218.1	218.5	219.0	218.3
125°	229.5	230.6	231.7	232.9	234.0	235.2	235.7	236.1	236.5	236.9	237.3
127.5°	247.1	248.0	248.8	249.8	250.6	251.5	252.1	252.8	253.4	254.0	254.3
130°	258.4	259.2	259.9	260.6	261.3	262.0	262.6	263.3	264.0	264.7	265.0
132.5°	269.0	269.7	270.4	271.0	271.7	272.4	273.0	273.6	274.1	274.7	275.0
135°	284.0	284.8	285.3	285.9	286.5	287.1	287.7	288.3	288.9	289.5	289.7
137.5°	297.5	298.2	298.8	299.4	300.1	300.7	301.3	301.9	302.5	303.1	303.2
140°	306.3	306.9	307.5	308.2	308.9	309.5	310.1	310.6	311.3	311.8	311.9
142.5°	314.1	314.7	315.5	316.2	317.0	317.8	318.3	318.8	319.3	319.9	319.9
145°	324.6	325.1	326.1	327.3	328.3	329.3	329.8	330.2	330.6	331.1	331.1
147.5°	334.9	335.3	336.3	337.4	338.5	339.5	339.8	340.1	340.4	340.8	340.8
150°	341.2	341.6	342.5	343.5	344.5	345.5	345.9	346.2	346.6	347.0	347.0
152.5°	347.1	347.2	348.2	349.1	350.1	351.0	351.4	351.8	352.1	352.5	352.5
155°	355.5	355.6	356.4	357.1	357.8	358.5	359.0	359.3	359.6	360.1	360.0
157.5°	362.7	362.7	363.3	363.8	364.3	364.8	365.2	365.7	366.1	366.4	366.4
160°	367.1	367.1	367.5	367.8	368.2	368.6	368.9	369.4	369.7	370.1	370.1
162.5°	370.7	370.7	370.9	371.3	371.6	372.0	372.4	372.7	373.2	373.6	373.6
165°	375.5	375.4	375.6	375.7	375.9	376.1	376.5	376.9	377.4	377.8	377.8
167.5°	379.0	378.9	379.1	379.3	379.4	379.6	380.0	380.5	380.9	381.3	381.3
170°	381.0	380.9	381.0	381.2	381.3	381.4	381.9	382.3	382.7	383.1	383.1
172.5°	382.4	382.2	382.4	382.5	382.6	382.7	383.1	383.6	384.0	384.4	384.4
175°	383.8	383.7	383.8	383.9	384.1	384.2	384.6	385.0	385.5	385.9	385.8
177.5°	384.4	384.4	384.4	384.4	384.4	384.5	384.9	385.2	385.6	385.9	385.8
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331375-935  
 CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1425.7	1424.9	1424.9	1420.7	1424.9	1424.9	1425.7	1430.4	1431.7	1432.6	1430.8
5°	1322.6	1320.9	1318.0	1320.9	1318.0	1320.9	1322.6	1330.6	1334.6	1338.6	1342.0
7.5°	1220.6	1213.7	1212.6	1205.9	1212.6	1213.7	1220.6	1224.3	1232.3	1241.4	1249.6
10°	1146.1	1141.5	1140.9	1130.1	1140.9	1141.5	1146.1	1155.8	1163.7	1174.7	1186.0
12.5°	1089.4	1078.4	1080.6	1074.3	1080.6	1078.4	1089.4	1089.5	1098.9	1105.6	1123.4
15°	991.3	991.3	988.9	979.2	988.9	991.3	991.3	1006.7	1009.5	1020.4	1035.8
17.5°	920.8	919.5	914.1	916.9	914.1	919.5	920.8	932.0	934.0	948.5	961.2
20°	878.7	875.3	868.4	868.4	868.4	875.3	878.7	884.9	892.4	901.0	911.8
22.5°	839.0	838.7	831.4	833.6	831.4	838.7	839.0	844.7	851.7	861.2	870.2
25°	792.4	787.8	784.5	786.1	784.5	787.8	792.4	793.0	801.0	807.3	813.0
27.5°	748.3	745.8	745.5	740.9	745.5	745.8	748.3	749.8	754.3	758.0	763.4
30°	722.7	717.0	718.2	715.3	718.2	717.0	722.7	723.3	725.6	727.9	734.2
32.5°	693.4	691.4	690.3	687.9	690.3	691.4	693.4	694.5	699.0	701.4	706.3
35°	653.6	654.2	651.3	652.5	651.3	654.2	653.6	654.7	655.3	657.5	662.2
37.5°	618.7	620.5	619.2	619.6	619.2	620.5	618.7	619.3	619.8	620.2	621.6
40°	595.9	595.9	595.9	597.6	595.9	595.9	595.9	594.2	594.8	594.2	594.2
42.5°	573.9	573.0	572.1	572.0	572.1	573.0	573.9	570.0	571.9	570.0	569.0
45°	536.5	538.2	538.7	535.9	538.7	538.2	536.5	535.3	533.6	533.0	532.4
47.5°	502.6	502.7	502.6	505.1	502.6	502.7	502.6	501.0	498.4	497.4	494.6
50°	478.8	477.6	478.8	477.6	478.8	477.6	478.8	475.9	474.2	471.3	469.1
52.5°	453.7	453.8	453.1	453.0	453.1	453.8	453.7	449.9	449.0	448.1	444.4
55°	414.2	415.3	414.7	414.7	414.7	415.3	414.2	411.9	411.4	407.9	404.5
57.5°	373.4	374.4	375.2	372.7	375.2	374.4	373.4	373.1	372.7	369.1	365.4
60°	345.1	347.9	347.3	346.2	347.3	347.9	345.1	345.6	344.0	341.6	339.3
62.5°	319.0	320.0	319.9	319.7	319.9	320.0	319.0	316.4	315.6	313.3	311.0
65°	278.8	279.9	278.2	279.9	278.2	279.9	278.8	277.1	273.1	271.9	269.7
67.5°	235.5	235.8	237.1	237.9	237.1	235.8	235.5	236.2	233.6	231.4	230.9
70°	208.5	207.9	209.7	211.4	209.7	207.9	208.5	207.4	205.7	204.0	201.6
72.5°	180.2	181.4	180.9	182.1	180.9	181.4	180.2	180.4	178.7	176.5	174.3
75°	138.8	140.5	140.0	141.7	140.0	140.5	138.8	140.0	138.8	136.6	134.2
77.5°	100.3	100.6	100.3	101.3	100.3	100.6	100.3	101.3	100.0	100.7	98.2
80°	76.5	75.4	74.3	76.5	74.3	75.4	76.5	76.5	74.8	76.5	74.8
82.5°	53.2	53.9	52.8	52.8	52.8	53.9	53.2	54.6	53.8	54.6	52.9
85°	24.5	24.0	22.8	22.8	22.8	24.0	24.5	24.5	26.3	25.1	25.1
87.5°	6.0	5.6	5.6	5.2	5.6	5.6	6.0	5.9	5.9	6.8	6.7
90°	7.1	7.2	7.4	7.5	7.4	7.2	7.1	7.1	6.8	6.5	6.2
92.5°	7.3	7.4	7.4	7.5	7.4	7.4	7.3	7.2	7.1	7.0	6.8
95°	12.1	12.1	12.1	12.0	12.1	12.1	12.1	12.2	12.1	11.8	11.5
97.5°	15.8	15.8	15.9	16.0	15.9	15.8	15.8	15.7	15.5	15.2	15.1
100°	18.3	18.4	18.5	18.7	18.5	18.4	18.3	18.2	17.8	17.4	16.9
102.5°	19.5	19.6	19.8	20.0	19.8	19.6	19.5	19.3	18.9	18.3	17.6
105°	20.4	20.7	20.9	21.2	20.9	20.7	20.4	20.1	19.7	19.0	18.3
107.5°	21.0	21.3	21.5	21.8	21.5	21.3	21.0	20.8	21.0	21.7	22.4
110°	21.3	21.5	21.8	22.0	21.8	21.5	21.3	21.0	23.9	30.1	36.3



TEST NUMBER: P331375-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	21.6	21.8	22.0	22.2	22.0	21.8	21.6	21.4	32.6	55.2	77.7
115°	36.2	31.8	27.3	22.8	27.3	31.8	36.2	40.6	57.2	85.8	114.5
117.5°	137.2	122.5	107.9	93.2	107.9	122.5	137.2	151.8	162.6	169.4	176.4
120°	194.8	186.5	178.1	169.8	178.1	186.5	194.8	203.2	207.0	206.3	205.5
122.5°	216.8	215.2	213.5	211.9	213.5	215.2	216.8	218.3	219.0	218.5	218.1
125°	237.5	237.6	237.8	238.0	237.8	237.6	237.5	237.3	236.9	236.5	236.1
127.5°	254.4	254.4	254.4	254.5	254.4	254.4	254.4	254.3	254.0	253.4	252.8
130°	264.9	264.8	264.8	264.8	264.8	264.8	264.9	265.0	264.7	264.0	263.3
132.5°	274.9	274.9	274.8	274.7	274.8	274.9	274.9	275.0	274.7	274.1	273.6
135°	289.6	289.5	289.4	289.2	289.4	289.5	289.6	289.7	289.5	288.9	288.3
137.5°	303.1	302.9	302.6	302.5	302.6	302.9	303.1	303.2	303.1	302.5	301.9
140°	311.6	311.3	311.0	310.6	311.0	311.3	311.6	311.9	311.8	311.3	310.6
142.5°	319.6	319.3	319.0	318.7	319.0	319.3	319.6	319.9	319.9	319.3	318.8
145°	330.8	330.5	330.2	329.8	330.2	330.5	330.8	331.1	331.1	330.6	330.2
147.5°	340.5	340.3	340.0	339.8	340.0	340.3	340.5	340.8	340.8	340.4	340.1
150°	346.7	346.4	346.0	345.8	346.0	346.4	346.7	347.0	347.0	346.6	346.2
152.5°	352.1	351.7	351.3	350.9	351.3	351.7	352.1	352.5	352.5	352.1	351.8
155°	359.5	359.0	358.5	358.0	358.5	359.0	359.5	360.0	360.1	359.6	359.3
157.5°	365.9	365.5	365.0	364.5	365.0	365.5	365.9	366.4	366.4	366.1	365.7
160°	369.6	369.2	368.8	368.3	368.8	369.2	369.6	370.1	370.1	369.7	369.4
162.5°	373.0	372.5	372.0	371.4	372.0	372.5	373.0	373.6	373.6	373.2	372.7
165°	377.4	376.9	376.5	376.1	376.5	376.9	377.4	377.8	377.8	377.4	376.9
167.5°	380.7	380.1	379.6	379.0	379.6	380.1	380.7	381.3	381.3	380.9	380.5
170°	382.5	381.9	381.4	380.8	381.4	381.9	382.5	383.1	383.1	382.7	382.3
172.5°	383.8	383.3	382.7	382.2	382.7	383.3	383.8	384.4	384.4	384.0	383.6
175°	385.2	384.6	383.9	383.3	383.9	384.6	385.2	385.8	385.9	385.5	385.0
177.5°	385.4	385.0	384.5	384.1	384.5	385.0	385.4	385.8	385.9	385.6	385.2
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331375-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1428.5	1433.6	1441.3	1449.6	1454.6	1464.1	1466.9	1471.4	1475.6	1485.2	1495.2
5°	1346.0	1354.0	1372.9	1383.1	1397.4	1414.0	1424.9	1436.3	1448.9	1470.6	1490.6
7.5°	1257.6	1270.9	1294.3	1313.5	1333.9	1357.7	1374.8	1397.4	1416.2	1446.8	1476.0
10°	1198.6	1217.5	1238.6	1261.5	1290.0	1315.2	1339.2	1367.7	1390.6	1427.1	1461.5
12.5°	1145.6	1148.5	1178.7	1203.9	1242.9	1274.0	1301.7	1338.5	1360.9	1404.3	1440.4
15°	1052.9	1070.1	1097.5	1117.5	1163.7	1203.2	1242.1	1280.3	1306.1	1359.7	1407.1
17.5°	974.9	990.7	1018.7	1051.5	1084.8	1124.0	1174.3	1214.6	1249.6	1311.0	1367.0
20°	925.5	944.9	973.5	1007.2	1036.4	1079.2	1122.7	1168.9	1206.6	1275.7	1341.4
22.5°	883.5	898.8	921.9	955.1	987.0	1026.2	1073.8	1124.1	1163.6	1238.3	1304.8
25°	824.4	837.0	851.8	879.3	915.2	958.1	995.2	1050.7	1108.4	1178.0	1258.6
27.5°	771.2	780.1	793.2	817.3	845.2	885.3	926.5	979.1	1037.2	1112.8	1197.8
30°	738.7	744.4	757.6	777.6	804.9	836.4	878.1	928.4	987.8	1064.4	1148.9
32.5°	710.4	715.7	724.2	743.3	767.1	793.9	831.5	881.8	938.4	1013.7	1107.3
35°	667.9	671.8	679.3	694.7	707.8	734.2	765.6	811.2	864.4	936.4	1033.5
37.5°	625.5	630.9	635.5	642.0	658.9	676.2	703.5	742.1	794.3	866.9	959.5
40°	597.6	602.2	609.0	611.9	625.6	641.0	663.3	698.7	751.3	817.5	907.8
42.5°	569.3	573.9	577.9	581.3	593.1	606.7	626.7	657.1	703.8	768.2	857.6
45°	530.7	531.3	535.3	541.6	547.3	557.1	571.3	597.6	633.6	694.1	775.2
47.5°	491.6	492.3	493.0	495.8	502.0	510.8	520.4	541.7	573.9	622.2	701.2
50°	465.6	464.5	465.6	467.9	471.9	479.3	490.2	505.6	531.9	577.0	649.6
52.5°	440.5	440.2	439.5	440.5	443.6	448.7	456.3	469.5	493.0	534.5	598.4
55°	402.2	399.3	399.9	397.6	402.8	403.9	409.7	420.5	441.1	469.6	529.6
57.5°	361.4	359.0	356.5	355.9	355.3	358.4	363.0	371.6	387.4	412.3	461.1
60°	335.4	332.5	329.1	328.0	328.0	329.7	331.9	338.2	353.1	375.4	415.3
62.5°	308.8	305.6	303.5	300.5	299.6	301.4	303.6	308.1	318.8	339.7	374.2
65°	267.9	264.0	261.1	260.5	259.4	257.7	258.8	263.4	271.9	288.5	315.9
67.5°	227.0	223.2	222.5	219.1	217.6	217.7	217.6	221.4	226.6	240.9	261.3
70°	199.9	197.1	196.0	193.1	192.0	190.8	189.7	193.1	198.3	210.3	228.0
72.5°	172.5	170.1	167.6	165.2	165.5	164.3	164.1	166.2	170.4	181.4	195.0
75°	133.1	133.7	130.9	127.9	127.4	126.2	126.2	127.9	129.7	138.3	149.1
77.5°	96.5	96.1	93.7	92.8	92.2	90.9	92.2	93.3	94.3	100.0	108.0
80°	73.7	73.7	70.9	70.9	70.3	68.5	70.3	69.1	71.4	77.1	82.8
82.5°	52.7	51.7	51.7	50.7	50.6	49.3	50.2	51.3	52.2	56.1	59.5
85°	25.7	25.7	25.1	24.5	25.1	24.5	25.1	25.7	26.3	28.0	30.8
87.5°	6.6	7.1	7.4	7.7	7.7	8.0	8.4	8.7	9.5	9.8	10.1
90°	5.9	5.6	5.1	4.6	4.0	3.6	3.0	2.3	1.6	0.9	0.3
92.5°	6.6	6.5	6.2	5.9	5.7	5.5	5.3	5.4	5.5	5.6	5.6
95°	11.2	10.8	10.4	10.0	9.6	9.1	9.9	12.0	14.0	16.0	18.1
97.5°	14.8	14.6	13.5	12.5	11.5	10.5	12.9	18.7	24.4	30.1	35.9
100°	16.4	15.8	14.8	13.8	12.7	11.6	15.4	23.8	32.3	40.8	49.2
102.5°	17.0	16.3	25.1	33.9	42.7	51.5	56.8	58.6	60.4	62.2	64.0
105°	17.7	17.0	33.8	50.8	67.7	84.6	92.0	90.2	88.3	86.4	84.6
107.5°	23.1	23.8	44.0	64.3	84.6	104.8	114.2	112.7	111.2	109.7	108.1
110°	42.5	48.7	66.6	84.5	102.4	120.2	128.5	127.3	126.0	124.6	123.3



TEST NUMBER: P331375-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	100.3	122.9	127.3	131.7	136.1	140.5	142.2	141.0	139.9	138.7	137.6
115°	143.1	171.8	170.2	168.7	167.1	165.6	164.3	163.2	162.2	161.1	160.1
117.5°	183.3	190.3	189.2	188.1	187.1	186.0	184.9	183.7	182.5	181.3	180.2
120°	204.8	204.1	202.9	201.8	200.7	199.6	198.5	197.7	196.7	195.8	194.8
122.5°	217.7	217.2	216.0	214.7	213.5	212.3	211.3	210.3	209.3	208.4	207.3
125°	235.7	235.2	234.0	232.9	231.7	230.6	229.5	228.8	227.9	227.1	226.4
127.5°	252.1	251.5	250.6	249.8	248.8	248.0	247.1	246.2	245.3	244.4	243.5
130°	262.6	262.0	261.3	260.6	259.9	259.2	258.4	257.4	256.4	255.5	254.4
132.5°	273.0	272.4	271.7	271.0	270.4	269.7	269.0	268.1	267.3	266.4	265.6
135°	287.7	287.1	286.5	285.9	285.3	284.8	284.0	283.0	282.1	281.0	280.1
137.5°	301.3	300.7	300.1	299.4	298.8	298.2	297.5	296.8	296.1	295.4	294.7
140°	310.1	309.5	308.9	308.2	307.5	306.9	306.3	305.7	305.2	304.8	304.3
142.5°	318.3	317.8	317.0	316.2	315.5	314.7	314.1	313.7	313.1	312.7	312.3
145°	329.8	329.3	328.3	327.3	326.1	325.1	324.6	324.7	324.8	324.9	324.9
147.5°	339.8	339.5	338.5	337.4	336.3	335.3	334.9	335.1	335.4	335.6	335.9
150°	345.9	345.5	344.5	343.5	342.5	341.6	341.2	341.6	342.1	342.5	342.9
152.5°	351.4	351.0	350.1	349.1	348.2	347.2	347.1	347.5	348.0	348.5	349.0
155°	359.0	358.5	357.8	357.1	356.4	355.6	355.5	356.0	356.6	357.1	357.7
157.5°	365.2	364.8	364.3	363.8	363.3	362.7	362.7	363.2	363.6	364.1	364.5
160°	368.9	368.6	368.2	367.8	367.5	367.1	367.1	367.5	367.8	368.2	368.6
162.5°	372.4	372.0	371.6	371.3	370.9	370.7	370.7	371.0	371.4	371.8	372.1
165°	376.5	376.1	375.9	375.7	375.6	375.4	375.5	375.8	376.2	376.6	376.9
167.5°	380.0	379.6	379.4	379.3	379.1	378.9	379.0	379.4	379.8	380.1	380.5
170°	381.9	381.4	381.3	381.2	381.0	380.9	381.0	381.4	381.8	382.1	382.5
172.5°	383.1	382.7	382.6	382.5	382.4	382.2	382.4	382.7	383.1	383.5	383.8
175°	384.6	384.2	384.1	383.9	383.8	383.7	383.8	384.3	384.7	385.1	385.6
177.5°	384.9	384.5	384.4	384.4	384.4	384.4	384.4	384.8	385.1	385.5	385.8
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331375-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1494.4	1496.6	1503.9	1511.2	1519.5	1521.7	1525.4	1522.2	1521.3	1530.0	1536.4
5°	1498.6	1508.8	1528.9	1547.1	1562.5	1573.4	1584.8	1589.4	1597.9	1610.0	1624.8
7.5°	1493.7	1513.7	1545.2	1571.8	1600.9	1621.7	1638.1	1652.0	1669.0	1691.7	1716.5
10°	1488.2	1515.1	1553.4	1586.0	1621.3	1648.2	1670.5	1692.2	1717.4	1748.8	1781.3
12.5°	1478.3	1510.1	1558.0	1596.5	1641.9	1668.4	1698.4	1745.2	1772.2	1816.0	1861.8
15°	1458.0	1493.4	1560.2	1607.7	1659.1	1709.3	1764.8	1809.4	1853.9	1879.6	1944.2
17.5°	1428.0	1480.0	1553.9	1609.3	1674.6	1753.9	1816.1	1866.6	1918.0	1959.7	1992.1
20°	1403.7	1460.3	1544.8	1611.1	1688.8	1773.9	1845.4	1896.8	1941.3	1976.2	1996.1
22.5°	1373.1	1444.2	1526.6	1604.2	1703.4	1787.6	1862.7	1903.2	1940.4	1957.4	1965.1
25°	1324.9	1410.6	1503.7	1598.5	1710.5	1799.7	1868.2	1892.7	1903.6	1887.1	1859.6
27.5°	1272.9	1368.4	1477.3	1587.8	1706.2	1791.8	1841.0	1837.1	1818.7	1765.1	1722.3
30°	1234.1	1339.2	1456.3	1576.8	1695.7	1779.1	1807.7	1779.1	1737.3	1677.4	1616.3
32.5°	1193.3	1302.2	1433.9	1561.3	1676.5	1749.8	1756.0	1706.8	1642.3	1574.1	1497.9
35°	1131.8	1249.5	1391.7	1526.6	1635.6	1682.0	1654.5	1567.7	1491.2	1398.0	1294.0
37.5°	1062.2	1192.1	1334.8	1475.7	1574.5	1586.7	1518.5	1427.1	1319.1	1209.7	1087.4
40°	1010.1	1147.8	1294.6	1436.8	1524.2	1511.7	1424.9	1324.3	1195.8	1062.0	948.4
42.5°	963.5	1101.1	1250.7	1390.3	1460.3	1425.7	1324.3	1200.9	1062.7	936.9	832.8
45°	882.7	1024.3	1177.5	1312.3	1352.3	1290.0	1155.8	1018.6	882.7	777.6	695.3
47.5°	804.3	944.3	1096.0	1214.5	1228.6	1144.9	998.2	857.1	740.2	654.6	596.6
50°	746.7	887.3	1037.5	1143.2	1138.6	1037.5	886.7	752.4	654.7	585.6	546.7
52.5°	695.1	827.9	972.2	1068.2	1044.0	933.8	789.8	670.6	590.3	536.2	501.0
55°	614.8	737.5	874.7	951.8	907.2	785.0	663.3	567.3	507.9	467.4	439.9
57.5°	534.9	650.1	767.5	815.0	765.8	652.9	551.5	481.8	437.1	407.1	389.3
60°	485.6	586.2	690.7	731.8	673.0	572.5	492.5	430.2	394.2	369.6	353.6
62.5°	436.3	526.3	624.9	647.3	593.5	508.5	437.6	385.9	356.3	334.4	319.3
65°	369.1	442.7	517.6	532.4	482.8	417.1	361.1	327.4	301.1	285.1	273.1
67.5°	302.6	361.9	414.9	426.9	383.3	337.8	297.3	267.9	250.1	236.9	226.7
70°	263.4	310.2	353.6	363.3	328.5	287.9	257.1	233.7	217.7	206.2	196.6
72.5°	221.8	260.9	297.0	303.5	275.0	244.1	218.7	200.3	186.1	178.8	169.5
75°	169.7	192.5	220.5	222.2	203.4	184.5	165.1	153.1	145.7	136.6	132.0
77.5°	119.8	137.7	153.7	156.8	145.6	132.8	121.9	112.4	106.2	101.9	97.7
80°	91.4	105.7	112.5	116.6	108.6	99.4	93.2	86.9	82.8	80.0	77.1
82.5°	65.3	74.1	80.6	83.6	79.3	73.8	67.5	64.0	60.9	58.5	57.5
85°	33.1	37.1	41.2	42.3	41.2	38.8	35.4	35.4	33.7	33.1	33.1
87.5°	11.6	13.6	13.7	15.2	14.5	14.6	14.6	14.3	13.9	13.5	13.1
90°	0.9	1.6	2.3	3.0	3.6	4.0	4.6	5.1	5.6	5.9	6.2
92.5°	5.6	5.5	5.4	5.3	5.5	5.7	5.9	6.2	6.5	6.6	6.8
95°	16.0	14.0	12.0	9.9	9.1	9.6	10.0	10.4	10.8	11.2	11.5
97.5°	30.1	24.4	18.7	12.9	10.5	11.5	12.5	13.5	14.6	14.8	15.1
100°	40.8	32.3	23.8	15.4	11.6	12.7	13.8	14.8	15.8	16.4	16.9
102.5°	62.2	60.4	58.6	56.8	51.5	42.7	33.9	25.1	16.3	17.0	17.6
105°	86.4	88.3	90.2	92.0	84.6	67.7	50.8	33.8	17.0	17.7	18.3
107.5°	109.7	111.2	112.7	114.2	104.8	84.6	64.3	44.0	23.8	23.1	22.4
110°	124.6	126.0	127.3	128.5	120.2	102.4	84.5	66.6	48.7	42.5	36.3





TEST NUMBER: P331375-935  
 CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	138.7	139.9	141.0	142.2	140.5	136.1	131.7	127.3	122.9	100.3	77.7
115°	161.1	162.2	163.2	164.3	165.6	167.1	168.7	170.2	171.8	143.1	114.5
117.5°	181.3	182.5	183.7	184.9	186.0	187.1	188.1	189.2	190.3	183.3	176.4
120°	195.8	196.7	197.7	198.5	199.6	200.7	201.8	202.9	204.1	204.8	205.5
122.5°	208.4	209.3	210.3	211.3	212.3	213.5	214.7	216.0	217.2	217.7	218.1
125°	227.1	227.9	228.8	229.5	230.6	231.7	232.9	234.0	235.2	235.7	236.1
127.5°	244.4	245.3	246.2	247.1	248.0	248.8	249.8	250.6	251.5	252.1	252.8
130°	255.5	256.4	257.4	258.4	259.2	259.9	260.6	261.3	262.0	262.6	263.3
132.5°	266.4	267.3	268.1	269.0	269.7	270.4	271.0	271.7	272.4	273.0	273.6
135°	281.0	282.1	283.0	284.0	284.8	285.3	285.9	286.5	287.1	287.7	288.3
137.5°	295.4	296.1	296.8	297.5	298.2	298.8	299.4	300.1	300.7	301.3	301.9
140°	304.8	305.2	305.7	306.3	306.9	307.5	308.2	308.9	309.5	310.1	310.6
142.5°	312.7	313.1	313.7	314.1	314.7	315.5	316.2	317.0	317.8	318.3	318.8
145°	324.9	324.8	324.7	324.6	325.1	326.1	327.3	328.3	329.3	329.8	330.2
147.5°	335.6	335.4	335.1	334.9	335.3	336.3	337.4	338.5	339.5	339.8	340.1
150°	342.5	342.1	341.6	341.2	341.6	342.5	343.5	344.5	345.5	345.9	346.2
152.5°	348.5	348.0	347.5	347.1	347.2	348.2	349.1	350.1	351.0	351.4	351.8
155°	357.1	356.6	356.0	355.5	355.6	356.4	357.1	357.8	358.5	359.0	359.3
157.5°	364.1	363.6	363.2	362.7	362.7	363.3	363.8	364.3	364.8	365.2	365.7
160°	368.2	367.8	367.5	367.1	367.1	367.5	367.8	368.2	368.6	368.9	369.4
162.5°	371.8	371.4	371.0	370.7	370.7	370.9	371.3	371.6	372.0	372.4	372.7
165°	376.6	376.2	375.8	375.5	375.4	375.6	375.7	375.9	376.1	376.5	376.9
167.5°	380.1	379.8	379.4	379.0	378.9	379.1	379.3	379.4	379.6	380.0	380.5
170°	382.1	381.8	381.4	381.0	380.9	381.0	381.2	381.3	381.4	381.9	382.3
172.5°	383.5	383.1	382.7	382.4	382.2	382.4	382.5	382.6	382.7	383.1	383.6
175°	385.1	384.7	384.3	383.8	383.7	383.8	383.9	384.1	384.2	384.6	385.0
177.5°	385.5	385.1	384.8	384.4	384.4	384.4	384.4	384.4	384.5	384.9	385.2
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331375-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1541.9	1548.3	1548.3	1549.2	1556.5	1555.6	1555.1
5°	1640.8	1650.5	1651.7	1662.0	1668.8	1666.6	1660.3
7.5°	1734.1	1752.2	1765.9	1773.6	1782.6	1788.2	1785.7
10°	1808.2	1834.4	1850.5	1861.3	1874.5	1884.2	1880.8
12.5°	1875.4	1906.7	1928.6	1947.2	1949.0	1961.4	1953.0
15°	1980.2	2013.3	2016.7	2030.4	2041.3	2040.1	2040.7
17.5°	2014.8	2025.4	2027.6	2027.9	2028.1	2024.0	2015.3
20°	2002.4	1998.5	1988.7	1981.3	1968.2	1966.4	1955.1
22.5°	1944.0	1931.3	1906.9	1890.8	1870.4	1865.0	1861.8
25°	1828.8	1800.8	1762.0	1724.8	1714.5	1694.5	1700.2
27.5°	1670.8	1627.1	1585.0	1554.9	1527.6	1497.6	1506.2
30°	1559.7	1510.5	1451.1	1405.4	1376.3	1347.7	1342.6
32.5°	1427.1	1355.1	1288.9	1248.6	1204.0	1185.9	1166.1
35°	1198.6	1128.3	1062.6	1006.1	973.5	948.4	925.5
37.5°	993.1	912.1	859.1	813.3	789.8	775.4	779.0
40°	865.6	794.7	755.9	721.0	699.3	689.0	691.3
42.5°	762.2	709.2	677.3	653.3	638.0	632.3	630.9
45°	645.0	615.3	589.0	575.3	567.9	561.6	557.6
47.5°	565.0	540.8	526.0	517.8	511.3	504.9	504.8
50°	517.0	501.0	490.8	482.2	477.1	472.5	476.5
52.5°	480.4	465.9	455.6	447.9	446.0	441.9	441.8
55°	426.2	414.7	407.3	400.5	397.1	394.8	391.9
57.5°	376.9	366.0	359.1	354.8	348.3	345.9	345.1
60°	341.6	333.0	326.2	320.5	317.6	313.1	313.1
62.5°	309.2	300.7	294.2	289.9	285.2	283.4	283.9
65°	262.3	255.4	249.1	244.5	243.4	240.0	241.1
67.5°	219.0	214.5	207.8	205.3	203.2	201.3	199.9
70°	190.3	185.7	182.3	178.8	177.1	177.1	177.1
72.5°	166.0	160.6	158.5	154.1	155.2	153.3	151.5
75°	128.5	125.1	123.4	121.7	118.8	118.8	118.8
77.5°	94.6	93.6	91.5	89.7	89.0	88.4	88.7
80°	73.1	72.6	71.4	71.4	70.3	69.7	68.5
82.5°	56.2	54.8	54.1	53.6	53.4	53.2	53.0
85°	32.0	30.8	30.8	31.4	30.3	30.3	30.8
87.5°	13.6	13.7	13.3	13.3	13.8	13.3	13.3
90°	6.5	6.8	7.1	7.1	7.2	7.4	7.5
92.5°	7.0	7.1	7.2	7.3	7.4	7.4	7.5
95°	11.8	12.1	12.2	12.1	12.1	12.1	12.0
97.5°	15.2	15.5	15.7	15.8	15.8	15.9	16.0
100°	17.4	17.8	18.2	18.3	18.4	18.5	18.7
102.5°	18.3	18.9	19.3	19.5	19.6	19.8	20.0
105°	19.0	19.7	20.1	20.4	20.7	20.9	21.2
107.5°	21.7	21.0	20.8	21.0	21.3	21.5	21.8
110°	30.1	23.9	21.0	21.3	21.5	21.8	22.0



TEST NUMBER: P331375-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	55.2	32.6	21.4	21.6	21.8	22.0	22.2
115°	85.8	57.2	40.6	36.2	31.8	27.3	22.8
117.5°	169.4	162.6	151.8	137.2	122.5	107.9	93.2
120°	206.3	207.0	203.2	194.8	186.5	178.1	169.8
122.5°	218.5	219.0	218.3	216.8	215.2	213.5	211.9
125°	236.5	236.9	237.3	237.5	237.6	237.8	238.0
127.5°	253.4	254.0	254.3	254.4	254.4	254.4	254.5
130°	264.0	264.7	265.0	264.9	264.8	264.8	264.8
132.5°	274.1	274.7	275.0	274.9	274.9	274.8	274.7
135°	288.9	289.5	289.7	289.6	289.5	289.4	289.2
137.5°	302.5	303.1	303.2	303.1	302.9	302.6	302.5
140°	311.3	311.8	311.9	311.6	311.3	311.0	310.6
142.5°	319.3	319.9	319.9	319.6	319.3	319.0	318.7
145°	330.6	331.1	331.1	330.8	330.5	330.2	329.8
147.5°	340.4	340.8	340.8	340.5	340.3	340.0	339.8
150°	346.6	347.0	347.0	346.7	346.4	346.0	345.8
152.5°	352.1	352.5	352.5	352.1	351.7	351.3	350.9
155°	359.6	360.1	360.0	359.5	359.0	358.5	358.0
157.5°	366.1	366.4	366.4	365.9	365.5	365.0	364.5
160°	369.7	370.1	370.1	369.6	369.2	368.8	368.3
162.5°	373.2	373.6	373.6	373.0	372.5	372.0	371.4
165°	377.4	377.8	377.8	377.4	376.9	376.5	376.1
167.5°	380.9	381.3	381.3	380.7	380.1	379.6	379.0
170°	382.7	383.1	383.1	382.5	381.9	381.4	380.8
172.5°	384.0	384.4	384.4	383.8	383.3	382.7	382.2
175°	385.5	385.9	385.8	385.2	384.6	383.9	383.3
177.5°	385.6	385.9	385.8	385.4	385.0	384.5	384.1
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7

(END OF REPORT)