

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333835

Luminaire Tested: **SA2XXDP-C290D935-4F0-1E-UDD-F**

Issue Date: 10/11/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P333835  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-10)  
Test Lab: INNOVATIONS CENTER  
Issue Date: 10/11/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDP-C290D935-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT LED LUMINAIRE, FLUSH SATIN WHITE DIFFUSER  
PENDANT/SURFACE/WALL MOUNT, 290 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 994.7 lumens  
Efficiency: N/A  
Efficacy: 85.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333835  
CATALOG NUMBER: SA2XXDP-C290D935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333835

CATALOG NUMBER: SA2XXDP-C290D935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76	83	78	74	80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48	59	52	47	57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42	53	47	42	52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37	49	42	37	47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27	38	32	27	37	32	27	26

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6313	6313	6313
5°	6337	6245	6282
10°	6299	6183	6212
15°	6221	6101	6096
20°	6110	5981	5974
25°	6000	5833	5833
30°	5860	5697	5649
35°	5728	5535	5454
40°	5562	5373	5269
45°	5400	5211	5083
50°	5222	5041	4863
55°	5036	4847	4667
60°	4831	4614	4443
65°	4611	4382	4180
70°	4329	4098	3904
75°	3943	3774	3681
80°	3496	3394	3217
85°	2853	2723	2445



TEST NUMBER: P333835  
 CATALOG NUMBER: SA2XXDP-C290D935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	36.8	3.7
10°-20°	103.5	10.4
20°-30°	152.1	15.3
30°-40°	176.7	17.8
40°-50°	176.5	17.7
50°-60°	153.9	15.5
60°-70°	113.8	11.4
70°-80°	64.4	6.5
80°-90°	17.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	292.5	29.4
0°-40°	469.2	47.2
0°-60°	799.6	80.4
0°-90°	994.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	994.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	391	391	391	391	391	
5°	391	390	385	388	388	37
15°	372	370	365	366	365	105
25°	337	334	327	328	327	155
35°	291	287	281	279	277	181
45°	236	234	228	224	223	183
55°	179	177	172	168	166	160
65°	121	118	115	111	109	119
75°	63	62	60	58	59	67
85°	15	15	15	14	13	18
90°	0	0	0	0	0	



TEST NUMBER: P333835  
 CATALOG NUMBER: SA2XXDP-C290D935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	391.0	391.0	391.0	391.0	391.0
2.5°	393.2	391.3	387.2	391.0	390.2
5°	391.0	389.5	385.3	388.3	387.6
7.5°	388.3	386.1	381.9	385.0	384.2
10°	384.2	381.6	377.1	380.1	378.9
12.5°	378.6	376.3	371.8	373.7	372.9
15°	372.2	369.9	365.0	366.5	364.7
17.5°	364.3	362.0	357.1	359.0	357.1
20°	355.6	353.4	348.1	349.2	347.7
22.5°	347.0	343.6	338.7	338.7	338.0
25°	336.8	333.8	327.4	328.2	327.4
27.5°	325.6	322.9	318.0	316.9	315.0
30°	314.3	311.3	305.6	304.5	303.0
32.5°	302.3	300.0	294.0	291.7	290.2
35°	290.6	286.8	280.8	278.6	276.7
37.5°	277.4	274.1	268.0	265.4	263.5
40°	263.9	260.9	254.9	251.5	250.0
42.5°	250.7	247.7	241.7	238.0	235.7
45°	236.5	233.8	228.2	224.1	222.6
47.5°	222.6	219.9	213.9	209.8	207.5
50°	207.9	206.0	200.7	195.5	193.6
52.5°	193.6	191.0	186.1	182.0	179.3
55°	178.9	176.7	172.2	167.7	165.8
57.5°	164.3	162.4	157.5	153.0	151.5
60°	149.6	148.1	142.9	138.7	137.6
62.5°	135.3	132.7	128.9	125.2	123.7
65°	120.7	118.4	114.7	111.3	109.4
67.5°	105.6	103.8	100.4	97.7	96.2
70°	91.7	90.2	86.8	84.2	82.7
72.5°	77.4	75.9	74.1	71.4	70.3
75°	63.2	62.4	60.5	58.3	59.0
77.5°	50.4	48.9	48.1	47.0	45.9
80°	37.6	37.2	36.5	35.3	34.6
82.5°	25.6	25.6	25.2	23.7	23.7
85°	15.4	15.0	14.7	13.5	13.2
87.5°	6.8	6.0	5.3	4.1	3.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)