

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331381-935

Luminaire Tested: **SA2XXDIP-C865D330U935-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331381-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C865D330U935-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4151.3 lumens  
Efficiency: N/A  
Efficacy: 95.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331381-935  
CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331381-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	97	94	90	87	84	82	79	76	74	72	68	67	65	61
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55	51
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	44
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	50	44	52	46	41	47	42	38	43	39	35	32
6	67	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	29
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	38	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19184	19184	19184
5°	19258	18979	19091
10°	19143	18787	18882
15°	18907	18544	18524
20°	18570	18179	18158
25°	18235	17728	17728
30°	17807	17316	17167
35°	17406	16821	16575
40°	16904	16326	16012
45°	16408	15835	15445
50°	15870	15325	14780
55°	15308	14728	14184
60°	14683	14018	13504
65°	14013	13310	12699
70°	13161	12458	11863
75°	11971	11472	11185
80°	10628	10302	9772
85°	8670	8262	7410



TEST NUMBER: P331381-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.7	2.7
10°-20°	314.4	7.6
20°-30°	462.1	11.1
30°-40°	536.8	12.9
40°-50°	536.2	12.9
50°-60°	467.6	11.3
60°-70°	345.7	8.3
70°-80°	195.8	4.7
80°-90°	53.6	1.3
90°-100°	12.8	0.3
100°-110°	47.1	1.1
110°-120°	125.8	3.0
120°-130°	207.7	5.0
130°-140°	220.8	5.3
140°-150°	205.3	4.9
150°-160°	165.0	4.0
160°-170°	106.3	2.6
170°-180°	36.6	0.9
0°-30°	888.2	21.4
0°-40°	1425.0	34.3
0°-60°	2428.7	58.5
0°-90°	3023.9	72.8
90°-120°	185.7	4.5
90°-150°	819.5	19.7
90°-180°	1127.0	27.1
0°-180°	4151.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1188	1188	1188	1188	1188	
5°	1188	1183	1171	1180	1178	113
15°	1131	1124	1109	1113	1108	318
25°	1024	1014	995	997	995	471
35°	883	871	853	847	841	551
45°	719	710	694	681	676	554
55°	544	537	523	510	504	486
65°	367	360	348	338	332	363
75°	192	189	184	178	179	205
85°	47	46	45	41	40	54
90°	0	3	6	7	8	3
95°	18	10	11	12	12	22
105°	85	88	17	20	21	90
115°	160	165	172	49	23	158
125°	226	230	235	237	238	202
135°	280	284	287	290	289	216
145°	325	325	329	331	330	203
155°	358	356	358	360	358	165
165°	377	375	376	378	376	106
175°	386	384	384	386	383	37
180°	385	385	385	385	385	



TEST NUMBER: P331381-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2
2.5°	1193.7	1192.7	1191.6	1190.7	1189.6	1188.0	1185.8	1183.5	1181.3	1179.1	1181.1
5°	1188.2	1187.1	1186.2	1185.2	1184.1	1182.2	1179.5	1176.6	1173.9	1171.0	1173.1
7.5°	1177.7	1176.1	1174.6	1172.9	1171.4	1169.2	1166.3	1163.5	1160.6	1157.8	1159.9
10°	1167.6	1165.9	1164.1	1162.3	1160.5	1158.1	1155.0	1152.0	1149.0	1145.9	1148.0
12.5°	1153.9	1152.4	1150.8	1149.2	1147.6	1145.3	1142.3	1139.2	1136.2	1133.2	1134.5
15°	1131.1	1129.5	1128.0	1126.5	1125.0	1122.6	1119.3	1115.9	1112.7	1109.4	1110.3
17.5°	1101.8	1100.3	1098.8	1097.3	1095.7	1093.3	1089.9	1086.6	1083.2	1079.9	1081.1
20°	1080.8	1079.3	1077.8	1076.2	1074.7	1072.2	1068.6	1065.1	1061.5	1058.0	1058.7
22.5°	1059.8	1057.7	1055.5	1053.3	1051.3	1048.5	1045.2	1041.8	1038.5	1035.1	1035.3
25°	1023.6	1021.7	1019.6	1017.6	1015.5	1012.4	1008.1	1003.8	999.4	995.1	995.7
27.5°	982.6	980.8	978.9	977.1	975.3	972.6	969.2	965.8	962.4	959.0	958.3
30°	955.1	953.1	951.1	949.1	947.0	944.1	940.3	936.5	932.6	928.8	928.1
32.5°	925.9	924.3	922.6	921.0	919.4	916.5	912.6	908.5	904.6	900.5	899.1
35°	883.1	880.6	878.0	875.6	873.0	869.7	865.6	861.6	857.5	853.4	852.0
37.5°	834.9	832.7	830.4	828.2	826.0	822.9	818.8	814.8	810.6	806.6	804.7
40°	802.0	800.0	798.0	795.9	793.9	790.8	786.8	782.7	778.7	774.6	772.3
42.5°	770.1	768.0	765.9	764.0	761.9	758.9	754.8	750.8	746.7	742.6	740.1
45°	718.6	716.9	715.1	713.3	711.5	708.7	704.9	701.1	697.3	693.5	690.7
47.5°	667.4	665.8	664.1	662.5	660.7	657.9	653.9	650.0	646.0	642.0	639.1
50°	631.8	630.5	629.3	628.0	626.7	624.3	620.8	617.2	613.6	610.1	606.6
52.5°	597.1	595.4	593.7	592.0	590.4	587.9	584.5	581.2	577.8	574.5	571.5
55°	543.8	542.3	540.8	539.2	537.7	535.5	532.4	529.3	526.3	523.2	520.2
57.5°	490.3	489.1	487.9	486.7	485.5	483.2	479.8	476.5	473.1	469.8	466.8
60°	454.7	453.7	452.7	451.7	450.6	448.4	444.8	441.3	437.7	434.1	431.4
62.5°	420.0	418.4	416.7	415.1	413.5	411.3	408.5	405.8	403.0	400.4	397.8
65°	366.8	365.2	363.7	362.1	360.7	358.6	356.1	353.5	351.0	348.4	346.2
67.5°	312.6	311.3	310.1	308.9	307.7	306.0	303.7	301.4	299.1	296.8	295.1
70°	278.8	277.8	276.7	275.7	274.7	273.0	270.8	268.5	266.2	263.9	262.2
72.5°	244.0	243.1	242.0	241.0	240.0	238.8	237.3	235.8	234.3	232.8	231.1
75°	191.9	191.4	190.9	190.5	189.9	189.0	187.8	186.5	185.2	183.9	182.4
77.5°	145.3	144.5	143.6	142.8	141.9	141.2	140.7	140.2	139.7	139.1	138.4
80°	114.3	114.0	113.7	113.5	113.2	112.9	112.4	111.8	111.3	110.8	110.0
82.5°	85.0	85.0	84.9	84.8	84.8	84.6	84.3	84.0	83.7	83.4	82.4
85°	46.8	46.6	46.3	46.1	45.8	45.5	45.3	45.0	44.8	44.6	43.8
87.5°	16.5	16.3	15.9	15.7	15.4	15.2	14.8	14.6	14.2	13.9	13.3
90°	0.3	0.9	1.6	2.3	3.0	3.6	4.0	4.6	5.1	5.6	5.9
92.5°	5.6	5.6	5.5	5.4	5.3	5.5	5.7	5.9	6.2	6.5	6.6
95°	18.1	16.0	14.0	12.0	9.9	9.1	9.6	10.0	10.4	10.8	11.2
97.5°	35.9	30.1	24.4	18.7	12.9	10.5	11.5	12.5	13.5	14.6	14.8
100°	49.2	40.8	32.3	23.8	15.4	11.6	12.7	13.8	14.8	15.8	16.4
102.5°	64.0	62.2	60.4	58.6	56.8	51.5	42.7	33.9	25.1	16.3	17.0
105°	84.6	86.4	88.3	90.2	92.0	84.6	67.7	50.8	33.8	17.0	17.7
107.5°	108.1	109.7	111.2	112.7	114.2	104.8	84.6	64.3	44.0	23.8	23.1
110°	123.3	124.6	126.0	127.3	128.5	120.2	102.4	84.5	66.6	48.7	42.5



TEST NUMBER: P331381-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	137.6	138.7	139.9	141.0	142.2	140.5	136.1	131.7	127.3	122.9	100.3
115°	160.1	161.1	162.2	163.2	164.3	165.6	167.1	168.7	170.2	171.8	143.1
117.5°	180.2	181.3	182.5	183.7	184.9	186.0	187.1	188.1	189.2	190.3	183.3
120°	194.8	195.8	196.7	197.7	198.5	199.6	200.7	201.8	202.9	204.1	204.8
122.5°	207.3	208.4	209.3	210.3	211.3	212.3	213.5	214.7	216.0	217.2	217.7
125°	226.4	227.1	227.9	228.8	229.5	230.6	231.7	232.9	234.0	235.2	235.7
127.5°	243.5	244.4	245.3	246.2	247.1	248.0	248.8	249.8	250.6	251.5	252.1
130°	254.4	255.5	256.4	257.4	258.4	259.2	259.9	260.6	261.3	262.0	262.6
132.5°	265.6	266.4	267.3	268.1	269.0	269.7	270.4	271.0	271.7	272.4	273.0
135°	280.1	281.0	282.1	283.0	284.0	284.8	285.3	285.9	286.5	287.1	287.7
137.5°	294.7	295.4	296.1	296.8	297.5	298.2	298.8	299.4	300.1	300.7	301.3
140°	304.3	304.8	305.2	305.7	306.3	306.9	307.5	308.2	308.9	309.5	310.1
142.5°	312.3	312.7	313.1	313.7	314.1	314.7	315.5	316.2	317.0	317.8	318.3
145°	324.9	324.9	324.8	324.7	324.6	325.1	326.1	327.3	328.3	329.3	329.8
147.5°	335.9	335.6	335.4	335.1	334.9	335.3	336.3	337.4	338.5	339.5	339.8
150°	342.9	342.5	342.1	341.6	341.2	341.6	342.5	343.5	344.5	345.5	345.9
152.5°	349.0	348.5	348.0	347.5	347.1	347.2	348.2	349.1	350.1	351.0	351.4
155°	357.7	357.1	356.6	356.0	355.5	355.6	356.4	357.1	357.8	358.5	359.0
157.5°	364.5	364.1	363.6	363.2	362.7	362.7	363.3	363.8	364.3	364.8	365.2
160°	368.6	368.2	367.8	367.5	367.1	367.1	367.5	367.8	368.2	368.6	368.9
162.5°	372.1	371.8	371.4	371.0	370.7	370.7	370.9	371.3	371.6	372.0	372.4
165°	376.9	376.6	376.2	375.8	375.5	375.4	375.6	375.7	375.9	376.1	376.5
167.5°	380.5	380.1	379.8	379.4	379.0	378.9	379.1	379.3	379.4	379.6	380.0
170°	382.5	382.1	381.8	381.4	381.0	380.9	381.0	381.2	381.3	381.4	381.9
172.5°	383.8	383.5	383.1	382.7	382.4	382.2	382.4	382.5	382.6	382.7	383.1
175°	385.6	385.1	384.7	384.3	383.8	383.7	383.8	383.9	384.1	384.2	384.6
177.5°	385.8	385.5	385.1	384.8	384.4	384.4	384.4	384.4	384.4	384.5	384.9
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331381-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2
2.5°	1183.1	1185.2	1187.1	1188.0	1187.6	1187.1	1186.8	1186.4
5°	1175.1	1177.2	1179.2	1179.9	1179.5	1179.0	1178.5	1177.9
7.5°	1161.8	1163.9	1166.0	1166.7	1166.1	1165.5	1165.0	1164.4
10°	1150.0	1152.0	1154.1	1154.7	1153.9	1153.1	1152.4	1151.7
12.5°	1136.0	1137.4	1138.8	1139.3	1138.7	1138.2	1137.6	1137.0
15°	1111.4	1112.4	1113.4	1113.3	1112.1	1110.8	1109.5	1108.2
17.5°	1082.2	1083.4	1084.6	1084.5	1083.3	1082.1	1080.9	1079.7
20°	1059.5	1060.2	1061.0	1060.8	1059.9	1058.9	1057.8	1056.8
22.5°	1035.4	1035.5	1035.7	1035.5	1034.8	1034.2	1033.6	1033.0
25°	996.2	996.6	997.1	997.1	996.6	996.2	995.7	995.1
27.5°	957.5	956.7	956.0	955.0	953.7	952.5	951.3	950.1
30°	927.3	926.6	925.8	924.9	923.9	922.9	921.9	920.8
32.5°	897.8	896.4	895.0	893.8	892.9	891.8	890.8	889.8
35°	850.4	848.9	847.4	845.9	844.7	843.4	842.1	840.9
37.5°	802.9	801.0	799.1	797.5	796.3	795.1	793.9	792.6
40°	770.1	767.8	765.5	763.8	762.8	761.8	760.8	759.7
42.5°	737.6	735.1	732.7	730.7	729.3	727.9	726.4	725.0
45°	687.9	685.1	682.3	680.4	679.4	678.4	677.3	676.4
47.5°	636.2	633.3	630.3	628.1	626.6	625.2	623.7	622.2
50°	603.0	599.4	595.9	593.5	592.2	590.9	589.7	588.4
52.5°	568.5	565.6	562.7	560.3	558.7	557.0	555.3	553.6
55°	517.2	514.1	511.1	508.9	507.6	506.4	505.1	503.9
57.5°	463.8	460.8	457.8	455.8	454.9	453.9	453.0	451.9
60°	428.6	425.8	423.0	421.2	420.4	419.7	418.9	418.2
62.5°	395.1	392.5	389.9	388.2	387.2	386.2	385.3	384.4
65°	343.9	341.6	339.3	337.5	336.3	335.0	333.7	332.4
67.5°	293.3	291.4	289.7	288.3	287.3	286.3	285.2	284.2
70°	260.4	258.6	256.8	255.4	254.4	253.4	252.4	251.3
72.5°	229.3	227.5	225.8	224.5	223.6	222.8	222.0	221.2
75°	180.9	179.3	177.9	177.4	177.9	178.4	178.8	179.3
77.5°	137.7	136.9	136.1	135.3	134.7	134.0	133.3	132.5
80°	109.3	108.6	107.8	107.1	106.6	106.2	105.6	105.1
82.5°	81.5	80.5	79.6	79.0	78.9	78.8	78.7	78.6
85°	43.0	42.3	41.5	41.0	40.7	40.5	40.2	40.0
87.5°	12.8	12.2	11.7	11.4	11.2	11.0	10.8	10.7
90°	6.2	6.5	6.8	7.1	7.1	7.2	7.4	7.5
92.5°	6.8	7.0	7.1	7.2	7.3	7.4	7.4	7.5
95°	11.5	11.8	12.1	12.2	12.1	12.1	12.1	12.0
97.5°	15.1	15.2	15.5	15.7	15.8	15.8	15.9	16.0
100°	16.9	17.4	17.8	18.2	18.3	18.4	18.5	18.7
102.5°	17.6	18.3	18.9	19.3	19.5	19.6	19.8	20.0
105°	18.3	19.0	19.7	20.1	20.4	20.7	20.9	21.2
107.5°	22.4	21.7	21.0	20.8	21.0	21.3	21.5	21.8
110°	36.3	30.1	23.9	21.0	21.3	21.5	21.8	22.0





TEST NUMBER: P331381-935

CATALOG NUMBER: SA2XXDIP-C865D330U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	77.7	55.2	32.6	21.4	21.6	21.8	22.0	22.2
115°	114.5	85.8	57.2	40.6	36.2	31.8	27.3	22.8
117.5°	176.4	169.4	162.6	151.8	137.2	122.5	107.9	93.2
120°	205.5	206.3	207.0	203.2	194.8	186.5	178.1	169.8
122.5°	218.1	218.5	219.0	218.3	216.8	215.2	213.5	211.9
125°	236.1	236.5	236.9	237.3	237.5	237.6	237.8	238.0
127.5°	252.8	253.4	254.0	254.3	254.4	254.4	254.4	254.5
130°	263.3	264.0	264.7	265.0	264.9	264.8	264.8	264.8
132.5°	273.6	274.1	274.7	275.0	274.9	274.9	274.8	274.7
135°	288.3	288.9	289.5	289.7	289.6	289.5	289.4	289.2
137.5°	301.9	302.5	303.1	303.2	303.1	302.9	302.6	302.5
140°	310.6	311.3	311.8	311.9	311.6	311.3	311.0	310.6
142.5°	318.8	319.3	319.9	319.9	319.6	319.3	319.0	318.7
145°	330.2	330.6	331.1	331.1	330.8	330.5	330.2	329.8
147.5°	340.1	340.4	340.8	340.8	340.5	340.3	340.0	339.8
150°	346.2	346.6	347.0	347.0	346.7	346.4	346.0	345.8
152.5°	351.8	352.1	352.5	352.5	352.1	351.7	351.3	350.9
155°	359.3	359.6	360.1	360.0	359.5	359.0	358.5	358.0
157.5°	365.7	366.1	366.4	366.4	365.9	365.5	365.0	364.5
160°	369.4	369.7	370.1	370.1	369.6	369.2	368.8	368.3
162.5°	372.7	373.2	373.6	373.6	373.0	372.5	372.0	371.4
165°	376.9	377.4	377.8	377.8	377.4	376.9	376.5	376.1
167.5°	380.5	380.9	381.3	381.3	380.7	380.1	379.6	379.0
170°	382.3	382.7	383.1	383.1	382.5	381.9	381.4	380.8
172.5°	383.6	384.0	384.4	384.4	383.8	383.3	382.7	382.2
175°	385.0	385.5	385.9	385.8	385.2	384.6	383.9	383.3
177.5°	385.2	385.6	385.9	385.8	385.4	385.0	384.5	384.1
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7

(END OF REPORT)