

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331736-935

Luminaire Tested: **SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331736-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4291.0 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331736-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331736-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	80	80	80	77
1	105	101	97	94	100	96	93	90	88	85	83	80	78	77	73	72	70	67
2	97	90	84	79	92	86	81	76	79	74	71	72	69	66	66	63	61	58
3	89	80	73	67	85	77	70	65	71	65	61	65	61	57	60	56	54	51
4	82	72	64	58	78	69	62	57	64	58	54	59	54	50	54	50	47	45
5	76	65	57	51	73	63	55	50	58	52	47	54	49	45	50	46	42	40
6	71	59	51	46	67	57	50	44	53	47	42	49	44	40	46	41	38	36
7	66	54	46	41	63	52	45	40	49	42	38	45	40	36	42	38	34	32
8	62	50	42	37	59	48	41	36	45	39	35	42	37	33	39	35	31	29
9	58	46	38	34	55	44	38	33	42	36	31	39	34	30	36	32	29	27
10	54	43	35	31	52	41	35	30	39	33	29	36	31	28	34	30	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30658	30658	30658	30658
5°	34240	30851	27353	30851
10°	37990	30634	23710	30634
15°	39858	30186	18683	30186
20°	34553	29520	16167	29520
25°	22661	28609	14434	28609
30°	15252	27505	13064	27505
35°	12354	26112	11783	26112
40°	10985	24601	10903	24601
45°	9944	22825	9732	22825
50°	9048	21064	9018	21064
55°	8507	19111	8397	19111
60°	7114	17321	7030	17321
65°	5998	15729	6804	15729
70°	5542	14049	6420	14049
75°	5190	12227	5926	12227
80°	4788	10060	5272	10060
85°	4409	7947	4650	7947



TEST NUMBER: P331736-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.0	4.2
10°-20°	501.6	11.7
20°-30°	646.3	15.1
30°-40°	614.2	14.3
40°-50°	526.2	12.3
50°-60°	400.7	9.3
60°-70°	253.3	5.9
70°-80°	126.5	2.9
80°-90°	34.4	0.8
90°-100°	22.8	0.5
100°-110°	70.9	1.7
110°-120°	121.3	2.8
120°-130°	159.5	3.7
130°-140°	179.0	4.2
140°-150°	175.5	4.1
150°-160°	147.2	3.4
160°-170°	97.6	2.3
170°-180°	34.1	0.8
0°-30°	1327.9	30.9
0°-40°	1942.1	45.3
0°-60°	2869.0	66.9
0°-90°	3283.1	76.5
90°-120°	215.0	5.0
90°-150°	729.0	17.0
90°-180°	1008.0	23.5
0°-180°	4291.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1899	1899	1899	1899	1899	
5°	2113	1904	1688	1904	2113	209
15°	2384	1806	1118	1806	2384	643
25°	1272	1606	810	1606	1272	604
35°	627	1325	598	1325	627	401
45°	436	1000	426	1000	436	337
55°	302	679	298	679	302	265
65°	157	412	178	412	157	160
75°	83	196	95	196	83	88
85°	24	43	25	43	24	26
90°	10	0	10	0	10	6
95°	19	16	19	16	19	21
105°	68	65	68	65	68	71
115°	122	122	122	122	122	120
125°	178	177	178	177	178	158
135°	232	229	232	229	232	178
145°	281	278	281	278	281	176
155°	320	318	320	318	320	147
165°	346	346	346	346	346	98
175°	359	360	359	360	359	34
180°	360	360	360	360	360	



TEST NUMBER: P331736-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1975.9	1977.5	1979.1	1975.4	1975.4	1972.2	1965.4	1960.1	1945.3	1943.2	1943.2
5°	2112.6	2111.3	2113.9	2105.4	2093.5	2090.9	2078.4	2061.8	2044.7	2025.6	2021.6
7.5°	2248.6	2246.6	2241.3	2239.9	2230.8	2210.8	2190.6	2169.1	2140.6	2112.8	2098.8
10°	2317.2	2339.0	2325.7	2302.7	2307.3	2276.3	2259.8	2231.5	2207.7	2166.1	2156.9
12.5°	2384.7	2393.3	2389.1	2376.0	2370.1	2348.5	2326.2	2301.6	2257.8	2220.4	2188.0
15°	2384.5	2397.0	2400.3	2396.3	2399.7	2398.3	2386.4	2366.0	2327.7	2286.8	2251.2
17.5°	2208.5	2217.2	2238.8	2253.4	2271.9	2311.0	2330.2	2337.8	2332.1	2308.8	2283.6
20°	2011.0	1996.5	2057.2	2088.3	2114.6	2180.6	2237.3	2259.1	2294.0	2293.4	2286.8
22.5°	1731.3	1734.7	1792.3	1829.1	1906.2	1972.1	2036.8	2118.7	2186.4	2231.1	2257.3
25°	1272.0	1297.2	1354.5	1404.7	1490.5	1613.2	1724.7	1854.0	1976.1	2072.4	2164.1
27.5°	955.4	957.3	1002.7	1049.0	1100.0	1200.6	1340.9	1495.4	1669.4	1813.0	1978.1
30°	818.1	814.2	833.3	861.7	905.3	983.1	1088.6	1240.4	1413.9	1630.3	1823.0
32.5°	721.0	721.3	735.6	756.6	792.8	845.3	917.7	1040.9	1204.9	1417.6	1643.6
35°	626.8	626.1	636.7	651.9	667.0	700.7	750.2	814.9	927.6	1126.3	1357.2
37.5°	559.2	562.1	567.3	576.8	593.6	612.3	642.0	685.4	765.8	883.2	1077.3
40°	521.2	522.5	529.8	537.7	547.6	562.1	586.5	621.6	680.3	774.0	915.8
42.5°	486.4	487.8	492.8	500.2	508.1	522.5	542.8	573.0	620.6	693.7	810.7
45°	435.5	435.5	440.1	443.4	451.9	465.1	481.6	506.7	539.7	593.8	671.7
47.5°	387.7	387.8	390.9	396.6	401.9	412.2	428.4	448.9	472.9	514.8	581.3
50°	360.2	360.9	362.9	367.5	370.8	380.0	392.6	410.4	435.5	467.8	523.2
52.5°	338.1	337.7	340.2	342.2	344.4	351.0	360.4	376.1	398.5	426.6	472.5
55°	302.2	299.5	303.5	306.8	308.8	311.4	316.7	326.6	345.7	369.5	403.8
57.5°	257.4	256.2	259.1	262.1	268.3	275.4	279.9	286.2	296.1	313.1	347.2
60°	220.3	220.3	226.3	228.3	235.6	244.8	254.0	259.3	269.2	280.4	305.5
62.5°	187.6	188.2	191.0	193.0	197.0	208.4	221.3	232.9	242.3	253.0	269.6
65°	157.0	158.3	158.3	159.6	162.3	165.0	170.2	179.4	196.0	211.1	223.7
67.5°	133.3	133.7	134.1	135.3	136.0	139.0	141.0	145.2	149.0	163.3	178.9
70°	117.4	119.4	118.7	120.1	120.7	122.1	124.7	126.7	132.6	136.0	145.2
72.5°	102.6	104.1	104.0	104.8	106.5	106.8	108.8	110.8	114.7	117.4	122.4
75°	83.2	82.5	83.2	84.5	85.2	85.8	85.8	88.4	90.4	93.0	96.3
77.5°	64.1	64.8	64.7	64.8	64.9	66.1	66.0	67.2	69.1	70.4	72.1
80°	51.5	52.1	51.5	52.1	52.8	53.5	52.8	53.5	55.4	56.7	56.7
82.5°	39.9	40.0	40.4	40.6	40.6	40.8	41.7	41.8	43.3	43.0	43.6
85°	23.8	23.1	23.1	23.1	23.8	24.5	23.8	23.8	24.5	24.5	24.5
87.5°	10.5	11.0	11.0	11.0	11.0	11.0	11.0	11.5	11.1	11.6	10.8
90°	10.3	10.2	10.2	10.2	10.1	10.1	10.2	10.4	10.5	10.7	9.1
92.5°	9.8	9.8	9.8	9.8	9.8	9.8	9.7	9.7	9.7	9.6	9.3
95°	18.9	19.0	19.1	19.3	19.4	19.5	19.5	19.5	19.5	19.5	19.4
97.5°	32.6	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.5
100°	41.7	41.8	41.8	41.8	41.9	42.0	42.0	42.0	42.0	42.0	41.8
102.5°	51.9	52.0	52.0	52.1	52.2	52.2	52.1	52.1	52.0	51.9	51.7
105°	67.5	67.5	67.5	67.5	67.5	67.5	67.3	67.2	67.1	66.9	66.8
107.5°	82.2	82.6	82.9	83.2	83.5	83.6	83.6	83.5	83.4	83.4	83.4
110°	93.7	93.9	94.1	94.3	94.5	94.6	94.6	94.6	94.6	94.6	94.6



TEST NUMBER: P331736-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	104.6	104.8	105.0	105.1	105.2	105.4	105.6	105.7	105.9	106.1	106.1
115°	121.7	121.9	122.1	122.3	122.5	122.6	122.7	122.8	122.9	122.9	123.0
117.5°	137.9	138.1	138.4	138.5	138.7	138.9	139.1	139.2	139.4	139.6	139.9
120°	149.4	149.6	149.7	150.0	150.2	150.2	150.2	150.2	150.2	150.2	150.8
122.5°	160.6	160.7	160.8	161.0	161.2	161.3	161.4	161.6	161.8	162.0	162.3
125°	177.6	177.7	177.8	177.9	177.9	178.1	178.2	178.5	178.7	178.8	179.1
127.5°	193.2	193.5	193.6	193.9	194.1	194.3	194.6	194.8	195.0	195.3	195.5
130°	204.4	204.7	204.9	205.3	205.5	205.7	205.9	206.0	206.1	206.2	206.4
132.5°	215.2	215.3	215.6	215.8	216.0	216.3	216.5	216.8	217.1	217.4	217.4
135°	231.8	232.0	232.2	232.4	232.6	232.7	232.8	232.9	232.9	233.0	232.9
137.5°	246.8	247.2	247.5	247.7	248.0	248.1	248.1	248.2	248.3	248.3	248.1
140°	257.4	257.6	257.9	258.1	258.4	258.6	258.6	258.6	258.6	258.6	258.2
142.5°	266.8	267.1	267.3	267.7	267.9	268.0	267.9	267.9	267.9	267.8	267.6
145°	281.0	281.4	281.6	281.9	282.1	282.2	282.1	282.1	282.1	282.0	281.5
147.5°	293.8	294.0	294.3	294.5	294.8	294.9	294.7	294.5	294.5	294.3	294.0
150°	302.0	302.3	302.5	302.6	302.9	302.9	302.6	302.5	302.3	302.0	301.8
152.5°	309.9	310.1	310.4	310.6	310.9	310.9	310.6	310.4	310.1	309.9	309.5
155°	320.3	320.6	320.7	320.9	321.2	321.1	320.7	320.4	320.0	319.7	319.5
157.5°	329.3	329.7	329.9	330.3	330.6	330.5	330.1	329.6	329.2	328.7	328.6
160°	334.9	335.2	335.4	335.7	336.0	336.0	335.5	335.1	334.7	334.3	334.2
162.5°	339.8	340.1	340.4	340.8	341.0	341.0	340.5	340.1	339.7	339.1	339.1
165°	346.2	346.5	346.8	347.2	347.5	347.4	347.0	346.5	346.0	345.5	345.5
167.5°	351.4	351.7	352.1	352.5	352.8	352.8	352.2	351.8	351.3	350.9	350.9
170°	354.0	354.5	354.9	355.3	355.7	355.7	355.2	354.7	354.2	353.8	353.9
172.5°	356.3	356.7	357.1	357.5	357.9	357.8	357.4	356.9	356.5	355.9	356.0
175°	358.6	359.0	359.5	359.9	360.2	360.2	359.7	359.3	358.8	358.3	358.4
177.5°	359.7	360.1	360.4	360.7	361.0	361.0	360.7	360.4	360.1	359.7	359.8
180°	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5



TEST NUMBER: P331736-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1944.3	1940.0	1936.4	1926.8	1922.1	1911.5	1910.0	1909.4	1895.7	1882.5	1878.8
5°	2011.0	2000.4	1984.7	1966.2	1947.1	1927.3	1914.1	1903.5	1877.1	1852.0	1837.5
7.5°	2078.4	2055.6	2028.3	1993.4	1964.2	1931.5	1907.2	1885.4	1848.0	1812.1	1787.9
10°	2128.5	2091.5	2055.2	2007.1	1969.5	1932.5	1898.2	1868.5	1826.3	1778.8	1745.2
12.5°	2159.6	2119.0	2069.0	2021.9	1973.2	1926.2	1880.3	1842.1	1792.5	1743.4	1703.5
15°	2201.7	2158.2	2097.5	2030.2	1967.5	1906.2	1853.4	1805.9	1741.2	1682.5	1633.7
17.5°	2236.2	2176.3	2111.1	2033.3	1960.7	1882.7	1814.7	1754.0	1682.0	1611.2	1553.7
20°	2247.2	2187.9	2112.6	2034.8	1949.0	1857.3	1784.1	1718.1	1640.9	1563.7	1497.7
22.5°	2240.4	2194.2	2110.6	2017.4	1929.5	1833.6	1750.8	1674.3	1588.6	1509.8	1433.3
25°	2193.8	2178.0	2098.8	1997.2	1896.9	1785.4	1689.7	1605.9	1508.3	1423.8	1340.7
27.5°	2085.2	2119.4	2070.3	1962.0	1850.5	1731.0	1623.5	1528.1	1426.8	1331.7	1248.9
30°	1980.7	2059.2	2038.1	1937.8	1813.1	1695.7	1574.9	1475.3	1367.1	1269.5	1187.7
32.5°	1837.6	1967.4	1988.0	1904.0	1775.1	1646.1	1519.5	1420.4	1307.4	1204.5	1124.8
35°	1609.9	1803.9	1892.9	1839.5	1710.2	1571.0	1440.3	1324.8	1211.3	1109.7	1030.6
37.5°	1338.2	1602.4	1750.8	1754.6	1635.9	1491.2	1348.8	1234.2	1118.1	1018.3	932.7
40°	1161.9	1448.2	1641.6	1684.5	1584.2	1427.8	1283.9	1167.2	1053.7	956.1	857.7
42.5°	1003.6	1288.8	1526.5	1601.0	1521.4	1366.1	1221.7	1099.6	989.3	896.9	796.5
45°	811.6	1060.9	1322.8	1456.1	1412.0	1268.1	1115.7	999.6	896.0	816.1	719.8
47.5°	684.6	860.4	1113.9	1294.1	1293.3	1162.0	1012.1	900.9	804.8	730.0	652.0
50°	612.3	765.3	979.8	1184.3	1201.4	1091.3	948.7	838.6	748.9	670.4	607.7
52.5°	547.3	673.5	866.3	1062.4	1111.2	1015.8	877.5	775.8	688.7	616.5	562.8
55°	462.5	560.2	706.6	890.0	964.0	896.6	774.0	678.9	608.3	547.6	501.4
57.5°	391.2	464.5	582.0	729.7	815.8	773.4	672.2	595.0	534.6	479.7	443.2
60°	346.4	406.4	506.1	629.5	724.4	694.7	608.3	536.4	484.9	437.5	403.1
62.5°	304.2	355.8	441.2	541.3	628.4	616.1	545.5	485.2	440.1	396.8	367.7
65°	244.8	282.4	349.0	427.6	497.5	503.4	452.6	411.7	371.4	337.2	311.4
67.5°	194.9	219.5	266.4	332.5	385.0	403.6	372.6	341.4	309.4	282.9	260.6
70°	164.3	184.1	218.3	271.8	320.0	339.8	322.0	297.6	269.8	248.1	228.9
72.5°	133.1	152.4	177.7	217.0	258.2	279.7	273.5	255.9	233.4	215.3	197.3
75°	100.3	106.2	123.4	149.8	182.1	200.6	205.2	196.0	178.1	164.3	153.7
77.5°	74.1	77.7	85.9	99.8	120.9	137.3	144.1	143.0	130.8	122.7	112.8
80°	59.4	61.4	65.3	71.3	87.1	103.6	108.2	108.2	99.6	96.3	86.4
82.5°	45.1	46.6	49.0	52.3	59.7	74.0	79.2	80.2	74.8	70.4	62.7
85°	25.7	25.1	26.4	28.4	29.7	33.7	41.6	42.9	41.6	36.2	34.3
87.5°	10.5	10.8	10.4	9.6	10.1	10.4	12.9	15.3	13.4	12.0	11.1
90°	7.7	6.2	4.7	3.5	2.8	1.9	1.1	0.3	1.1	1.9	2.8
92.5°	9.0	8.6	8.3	7.8	7.2	6.6	6.0	5.4	6.0	6.6	7.2
95°	19.2	19.0	18.9	18.5	17.8	17.1	16.5	15.8	16.5	17.1	17.8
97.5°	32.2	31.9	31.7	31.3	30.7	30.0	29.5	28.9	29.5	30.0	30.7
100°	41.6	41.3	41.2	40.8	40.3	39.7	39.2	38.7	39.2	39.7	40.3
102.5°	51.4	51.1	51.0	50.5	50.1	49.7	49.2	48.8	49.2	49.7	50.1
105°	66.6	66.6	66.4	66.2	66.0	65.8	65.6	65.4	65.6	65.8	66.0
107.5°	83.4	83.4	83.4	83.3	83.0	82.7	82.4	82.1	82.4	82.7	83.0
110°	94.6	94.6	94.6	94.4	94.0	93.6	93.2	92.8	93.2	93.6	94.0



TEST NUMBER: P331736-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	106.2	106.2	106.2	106.1	105.6	105.3	104.9	104.4	104.9	105.3	105.6
115°	123.1	123.3	123.5	123.3	122.9	122.5	122.1	121.7	122.1	122.5	122.9
117.5°	140.3	140.7	141.1	141.0	140.4	139.9	139.4	138.8	139.4	139.9	140.4
120°	151.4	151.9	152.4	152.4	151.9	151.4	150.8	150.2	150.8	151.4	151.9
122.5°	162.7	163.1	163.5	163.3	162.6	162.0	161.4	160.7	161.4	162.0	162.6
125°	179.3	179.4	179.7	179.4	178.8	178.2	177.6	177.0	177.6	178.2	178.8
127.5°	195.8	196.0	196.2	196.0	195.2	194.5	193.7	193.0	193.7	194.5	195.2
130°	206.6	206.6	206.8	206.4	205.5	204.7	203.8	202.9	203.8	204.7	205.5
132.5°	217.4	217.3	217.3	217.0	216.2	215.5	214.8	214.1	214.8	215.5	216.2
135°	232.7	232.6	232.5	232.0	231.3	230.6	229.8	229.0	229.8	230.6	231.3
137.5°	248.0	247.8	247.6	247.3	246.7	246.0	245.4	244.8	245.4	246.0	246.7
140°	257.9	257.5	257.2	256.8	256.1	255.5	254.9	254.3	254.9	255.5	256.1
142.5°	267.3	267.1	266.9	266.5	265.9	265.3	264.7	264.1	264.7	265.3	265.9
145°	281.2	280.8	280.3	279.9	279.5	279.0	278.5	278.0	278.5	279.0	279.5
147.5°	293.8	293.4	293.2	292.7	292.2	291.6	291.1	290.5	291.1	291.6	292.2
150°	301.5	301.3	301.0	300.7	300.2	299.8	299.5	299.0	299.5	299.8	300.2
152.5°	309.2	308.8	308.6	308.2	307.8	307.4	306.9	306.6	306.9	307.4	307.8
155°	319.3	319.1	318.9	318.7	318.5	318.3	318.1	317.9	318.1	318.3	318.5
157.5°	328.5	328.4	328.2	328.1	328.0	327.8	327.7	327.5	327.7	327.8	328.0
160°	334.2	334.1	334.1	333.9	333.8	333.6	333.6	333.4	333.6	333.6	333.8
162.5°	339.1	339.0	338.9	338.9	338.8	338.8	338.8	338.7	338.8	338.8	338.8
165°	345.5	345.5	345.5	345.6	345.7	345.7	345.8	345.9	345.8	345.7	345.7
167.5°	350.9	350.9	350.9	351.0	351.2	351.5	351.6	351.8	351.6	351.5	351.2
170°	353.9	354.0	354.0	354.2	354.4	354.6	354.8	355.0	354.8	354.6	354.4
172.5°	356.1	356.2	356.2	356.4	356.5	356.8	357.0	357.1	357.0	356.8	356.5
175°	358.6	358.8	358.9	359.0	359.2	359.5	359.6	359.9	359.6	359.5	359.2
177.5°	360.0	360.1	360.2	360.3	360.5	360.6	360.8	360.9	360.8	360.6	360.5
180°	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5



TEST NUMBER: P331736-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1872.0	1868.3	1861.4	1850.8	1844.5	1833.4	1826.0	1830.2	1831.3	1830.2	1829.2
5°	1821.7	1807.8	1788.7	1770.2	1753.1	1734.6	1724.1	1719.4	1710.2	1704.9	1702.3
7.5°	1760.8	1737.0	1709.9	1677.7	1650.4	1621.8	1607.1	1599.8	1581.0	1570.7	1561.7
10°	1715.5	1677.8	1650.8	1608.6	1582.9	1545.2	1519.5	1520.2	1494.4	1479.9	1469.4
12.5°	1665.3	1624.0	1579.0	1541.0	1505.3	1475.1	1444.0	1431.5	1404.2	1390.2	1361.7
15°	1582.2	1534.0	1486.5	1435.0	1398.8	1351.9	1307.1	1252.3	1208.1	1169.8	1159.3
17.5°	1491.4	1431.8	1384.1	1323.7	1261.5	1182.8	1130.8	1099.0	1072.3	1052.1	1037.1
20°	1429.1	1368.4	1317.6	1226.6	1142.7	1089.3	1051.0	1026.7	998.9	977.1	965.3
22.5°	1363.7	1300.3	1231.1	1129.5	1064.1	1021.2	987.1	959.1	940.3	923.3	912.5
25°	1270.7	1201.4	1087.4	1017.4	964.6	919.7	896.0	878.8	859.0	835.9	825.4
27.5°	1172.6	1062.4	980.4	928.4	878.0	848.9	827.5	801.9	784.2	773.8	762.8
30°	1099.2	989.0	925.1	868.3	832.7	800.3	775.2	760.8	743.6	725.7	718.5
32.5°	1017.4	929.4	868.1	820.8	784.6	757.1	737.3	713.8	701.4	690.4	675.2
35°	915.8	849.1	793.1	754.8	720.5	698.1	674.9	661.1	638.7	629.5	623.5
37.5°	829.7	772.0	730.1	689.7	662.5	637.7	623.6	601.6	591.9	579.0	566.5
40°	781.2	724.4	684.2	651.2	620.9	602.4	584.5	566.8	552.2	546.3	531.2
42.5°	731.6	685.4	645.1	609.0	588.7	569.1	546.6	533.5	518.5	508.9	499.5
45°	663.1	622.2	587.9	558.2	535.7	515.3	500.8	479.0	470.5	451.3	443.4
47.5°	603.0	564.9	532.2	503.9	482.1	468.7	447.5	430.4	416.7	405.0	394.9
50°	560.2	528.5	496.8	471.7	451.9	432.8	411.0	402.4	381.3	375.4	369.5
52.5°	521.1	491.0	462.0	437.5	417.7	399.1	379.9	368.7	354.5	348.5	344.1
55°	466.5	437.5	409.7	388.0	368.2	349.0	337.2	323.3	316.7	312.1	306.8
57.5°	411.6	385.5	364.2	342.2	322.3	307.0	293.3	285.0	278.2	272.1	265.8
60°	376.8	351.6	332.5	312.1	291.6	279.1	268.5	258.6	250.7	241.5	238.8
62.5°	339.8	317.9	300.3	280.4	262.6	251.2	241.1	231.7	222.2	208.8	205.1
65°	289.0	271.8	253.4	236.9	221.0	209.8	195.3	184.8	180.8	179.4	178.8
67.5°	243.1	226.9	211.0	194.1	179.7	169.3	162.0	160.3	157.6	156.8	154.9
70°	212.5	197.3	181.4	165.6	151.8	149.8	147.1	144.5	141.2	139.9	138.5
72.5°	185.0	169.3	153.4	140.8	134.8	132.3	129.8	127.1	124.8	123.6	122.7
75°	141.9	127.3	116.8	112.2	108.8	106.9	102.9	100.9	99.6	97.6	96.9
77.5°	102.1	93.9	89.1	86.2	82.7	80.6	78.4	76.4	75.0	74.6	73.5
80°	77.8	73.9	70.6	66.6	65.3	62.7	62.0	60.0	60.7	58.7	58.7
82.5°	60.4	55.4	52.7	50.8	49.5	47.4	46.8	45.8	45.9	44.4	44.4
85°	31.0	29.7	28.4	27.0	27.0	25.1	25.7	25.1	25.1	23.8	23.1
87.5°	10.8	10.4	9.6	10.0	10.2	10.1	10.0	9.5	9.5	9.4	8.9
90°	3.5	4.7	6.2	7.7	9.1	10.7	10.5	10.4	10.2	10.1	10.1
92.5°	7.8	8.3	8.6	9.0	9.3	9.6	9.7	9.7	9.7	9.8	9.8
95°	18.5	18.9	19.0	19.2	19.4	19.5	19.5	19.5	19.5	19.5	19.4
97.5°	31.3	31.7	31.9	32.2	32.5	32.7	32.7	32.7	32.7	32.7	32.7
100°	40.8	41.2	41.3	41.6	41.8	42.0	42.0	42.0	42.0	42.0	41.9
102.5°	50.5	51.0	51.1	51.4	51.7	51.9	52.0	52.1	52.1	52.2	52.2
105°	66.2	66.4	66.6	66.6	66.8	66.9	67.1	67.2	67.3	67.5	67.5
107.5°	83.3	83.4	83.4	83.4	83.4	83.4	83.4	83.5	83.6	83.6	83.5
110°	94.4	94.6	94.6	94.6	94.6	94.6	94.6	94.6	94.6	94.6	94.5



TEST NUMBER: P331736-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	106.1	106.2	106.2	106.2	106.1	106.1	105.9	105.7	105.6	105.4	105.2
115°	123.3	123.5	123.3	123.1	123.0	122.9	122.9	122.8	122.7	122.6	122.5
117.5°	141.0	141.1	140.7	140.3	139.9	139.6	139.4	139.2	139.1	138.9	138.7
120°	152.4	152.4	151.9	151.4	150.8	150.2	150.2	150.2	150.2	150.2	150.2
122.5°	163.3	163.5	163.1	162.7	162.3	162.0	161.8	161.6	161.4	161.3	161.2
125°	179.4	179.7	179.4	179.3	179.1	178.8	178.7	178.5	178.2	178.1	177.9
127.5°	196.0	196.2	196.0	195.8	195.5	195.3	195.0	194.8	194.6	194.3	194.1
130°	206.4	206.8	206.6	206.6	206.4	206.2	206.1	206.0	205.9	205.7	205.5
132.5°	217.0	217.3	217.3	217.4	217.4	217.4	217.1	216.8	216.5	216.3	216.0
135°	232.0	232.5	232.6	232.7	232.9	233.0	232.9	232.9	232.8	232.7	232.6
137.5°	247.3	247.6	247.8	248.0	248.1	248.3	248.3	248.2	248.1	248.1	248.0
140°	256.8	257.2	257.5	257.9	258.2	258.6	258.6	258.6	258.6	258.6	258.4
142.5°	266.5	266.9	267.1	267.3	267.6	267.8	267.9	267.9	267.9	268.0	267.9
145°	279.9	280.3	280.8	281.2	281.5	282.0	282.1	282.1	282.1	282.2	282.1
147.5°	292.7	293.2	293.4	293.8	294.0	294.3	294.5	294.5	294.7	294.9	294.8
150°	300.7	301.0	301.3	301.5	301.8	302.0	302.3	302.5	302.6	302.9	302.9
152.5°	308.2	308.6	308.8	309.2	309.5	309.9	310.1	310.4	310.6	310.9	310.9
155°	318.7	318.9	319.1	319.3	319.5	319.7	320.0	320.4	320.7	321.1	321.2
157.5°	328.1	328.2	328.4	328.5	328.6	328.7	329.2	329.6	330.1	330.5	330.6
160°	333.9	334.1	334.1	334.2	334.2	334.3	334.7	335.1	335.5	336.0	336.0
162.5°	338.9	338.9	339.0	339.1	339.1	339.1	339.7	340.1	340.5	341.0	341.0
165°	345.6	345.5	345.5	345.5	345.5	345.5	346.0	346.5	347.0	347.4	347.5
167.5°	351.0	350.9	350.9	350.9	350.9	350.9	351.3	351.8	352.2	352.8	352.8
170°	354.2	354.0	354.0	353.9	353.9	353.8	354.2	354.7	355.2	355.7	355.7
172.5°	356.4	356.2	356.2	356.1	356.0	355.9	356.5	356.9	357.4	357.8	357.9
175°	359.0	358.9	358.8	358.6	358.4	358.3	358.8	359.3	359.7	360.2	360.2
177.5°	360.3	360.2	360.1	360.0	359.8	359.7	360.1	360.4	360.7	361.0	361.0
180°	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5



TEST NUMBER: P331736-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1823.4	1824.5	1822.9	1823.9	1822.9	1824.5	1823.4	1829.2	1830.2	1831.3	1830.2
5°	1698.9	1691.0	1689.7	1687.7	1689.7	1691.0	1698.9	1702.3	1704.9	1710.2	1719.4
7.5°	1550.4	1549.2	1545.9	1541.3	1545.9	1549.2	1550.4	1561.7	1570.7	1581.0	1599.8
10°	1454.8	1451.6	1450.9	1446.2	1450.9	1451.6	1454.8	1469.4	1479.9	1494.4	1520.2
12.5°	1342.9	1321.7	1319.5	1307.9	1319.5	1321.7	1342.9	1361.7	1390.2	1404.2	1431.5
15°	1143.4	1139.4	1126.3	1117.7	1126.3	1139.4	1143.4	1159.3	1169.8	1208.1	1252.3
17.5°	1029.4	1016.5	1012.4	1010.6	1012.4	1016.5	1029.4	1037.1	1052.1	1072.3	1099.0
20°	956.1	944.2	942.2	940.9	942.2	944.2	956.1	965.3	977.1	998.9	1026.7
22.5°	905.3	892.9	887.8	883.8	887.8	892.9	905.3	912.5	923.3	940.3	959.1
25°	818.8	814.2	811.6	810.2	811.6	814.2	818.8	825.4	835.9	859.0	878.8
27.5°	751.1	741.0	739.0	735.6	739.0	741.0	751.1	762.8	773.8	784.2	801.9
30°	712.6	709.3	704.6	700.7	704.6	709.3	712.6	718.5	725.7	743.6	760.8
32.5°	667.2	664.4	660.3	658.5	660.3	664.4	667.2	675.2	690.4	701.4	713.8
35°	616.9	607.7	603.7	597.8	603.7	607.7	616.9	623.5	629.5	638.7	661.1
37.5°	563.7	558.9	553.3	555.3	553.3	558.9	563.7	566.5	579.0	591.9	601.6
40°	522.5	519.3	518.0	517.3	518.0	519.3	522.5	531.2	546.3	552.2	566.8
42.5°	489.8	480.7	477.3	477.2	477.3	480.7	489.8	499.5	508.9	518.5	533.5
45°	440.1	431.5	425.6	426.2	425.6	431.5	440.1	443.4	451.3	470.5	479.0
47.5°	389.2	388.9	385.2	386.3	385.2	388.9	389.2	394.9	405.0	416.7	430.4
50°	364.9	360.9	358.3	359.0	358.3	360.9	364.9	369.5	375.4	381.3	402.4
52.5°	341.6	338.2	336.1	338.9	336.1	338.2	341.6	344.1	348.5	354.5	368.7
55°	303.5	299.5	298.9	298.3	298.9	299.5	303.5	306.8	312.1	316.7	323.3
57.5°	260.9	258.2	254.3	252.5	254.3	258.2	260.9	265.8	272.1	278.2	285.0
60°	230.2	225.0	218.3	217.7	218.3	225.0	230.2	238.8	241.5	250.7	258.6
62.5°	202.2	201.2	199.9	199.8	199.9	201.2	202.2	205.1	208.8	222.2	231.7
65°	177.5	176.8	177.5	178.1	177.5	176.8	177.5	178.8	179.4	180.8	184.8
67.5°	154.6	153.4	152.3	152.8	152.3	153.4	154.6	154.9	156.8	157.6	160.3
70°	137.2	136.6	136.0	136.0	136.0	136.6	137.2	138.5	139.9	141.2	144.5
72.5°	120.4	120.2	119.6	119.0	119.6	120.2	120.4	122.7	123.6	124.8	127.1
75°	96.3	95.0	95.0	95.0	95.0	95.0	96.3	96.9	97.6	99.6	100.9
77.5°	73.4	72.7	72.1	71.5	72.1	72.7	73.4	73.5	74.6	75.0	76.4
80°	58.0	57.4	56.7	56.7	56.7	57.4	58.0	58.7	58.7	60.7	60.0
82.5°	44.3	43.7	43.6	43.0	43.6	43.7	44.3	44.4	44.4	45.9	45.8
85°	23.8	24.5	23.8	25.1	23.8	24.5	23.8	23.1	23.8	25.1	25.1
87.5°	8.9	8.4	9.0	8.4	9.0	8.4	8.9	8.9	9.4	9.5	9.5
90°	10.2	10.2	10.2	10.3	10.2	10.2	10.2	10.1	10.1	10.2	10.4
92.5°	9.8	9.8	9.8	9.8	9.8	9.8	9.8	9.8	9.8	9.7	9.7
95°	19.3	19.1	19.0	18.9	19.0	19.1	19.3	19.4	19.5	19.5	19.5
97.5°	32.7	32.7	32.7	32.6	32.7	32.7	32.7	32.7	32.7	32.7	32.7
100°	41.8	41.8	41.8	41.7	41.8	41.8	41.8	41.9	42.0	42.0	42.0
102.5°	52.1	52.0	52.0	51.9	52.0	52.0	52.1	52.2	52.2	52.1	52.1
105°	67.5	67.5	67.5	67.5	67.5	67.5	67.5	67.5	67.5	67.3	67.2
107.5°	83.2	82.9	82.6	82.2	82.6	82.9	83.2	83.5	83.6	83.6	83.5
110°	94.3	94.1	93.9	93.7	93.9	94.1	94.3	94.5	94.6	94.6	94.6



TEST NUMBER: P331736-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	105.1	105.0	104.8	104.6	104.8	105.0	105.1	105.2	105.4	105.6	105.7
115°	122.3	122.1	121.9	121.7	121.9	122.1	122.3	122.5	122.6	122.7	122.8
117.5°	138.5	138.4	138.1	137.9	138.1	138.4	138.5	138.7	138.9	139.1	139.2
120°	150.0	149.7	149.6	149.4	149.6	149.7	150.0	150.2	150.2	150.2	150.2
122.5°	161.0	160.8	160.7	160.6	160.7	160.8	161.0	161.2	161.3	161.4	161.6
125°	177.9	177.8	177.7	177.6	177.7	177.8	177.9	177.9	178.1	178.2	178.5
127.5°	193.9	193.6	193.5	193.2	193.5	193.6	193.9	194.1	194.3	194.6	194.8
130°	205.3	204.9	204.7	204.4	204.7	204.9	205.3	205.5	205.7	205.9	206.0
132.5°	215.8	215.6	215.3	215.2	215.3	215.6	215.8	216.0	216.3	216.5	216.8
135°	232.4	232.2	232.0	231.8	232.0	232.2	232.4	232.6	232.7	232.8	232.9
137.5°	247.7	247.5	247.2	246.8	247.2	247.5	247.7	248.0	248.1	248.1	248.2
140°	258.1	257.9	257.6	257.4	257.6	257.9	258.1	258.4	258.6	258.6	258.6
142.5°	267.7	267.3	267.1	266.8	267.1	267.3	267.7	267.9	268.0	267.9	267.9
145°	281.9	281.6	281.4	281.0	281.4	281.6	281.9	282.1	282.2	282.1	282.1
147.5°	294.5	294.3	294.0	293.8	294.0	294.3	294.5	294.8	294.9	294.7	294.5
150°	302.6	302.5	302.3	302.0	302.3	302.5	302.6	302.9	302.9	302.6	302.5
152.5°	310.6	310.4	310.1	309.9	310.1	310.4	310.6	310.9	310.9	310.6	310.4
155°	320.9	320.7	320.6	320.3	320.6	320.7	320.9	321.2	321.1	320.7	320.4
157.5°	330.3	329.9	329.7	329.3	329.7	329.9	330.3	330.6	330.5	330.1	329.6
160°	335.7	335.4	335.2	334.9	335.2	335.4	335.7	336.0	336.0	335.5	335.1
162.5°	340.8	340.4	340.1	339.8	340.1	340.4	340.8	341.0	341.0	340.5	340.1
165°	347.2	346.8	346.5	346.2	346.5	346.8	347.2	347.5	347.4	347.0	346.5
167.5°	352.5	352.1	351.7	351.4	351.7	352.1	352.5	352.8	352.8	352.2	351.8
170°	355.3	354.9	354.5	354.0	354.5	354.9	355.3	355.7	355.7	355.2	354.7
172.5°	357.5	357.1	356.7	356.3	356.7	357.1	357.5	357.9	357.8	357.4	356.9
175°	359.9	359.5	359.0	358.6	359.0	359.5	359.9	360.2	360.2	359.7	359.3
177.5°	360.7	360.4	360.1	359.7	360.1	360.4	360.7	361.0	361.0	360.7	360.4
180°	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5



TEST NUMBER: P331736-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1826.0	1833.4	1844.5	1850.8	1861.4	1868.3	1872.0	1878.8	1882.5	1895.7	1909.4
5°	1724.1	1734.6	1753.1	1770.2	1788.7	1807.8	1821.7	1837.5	1852.0	1877.1	1903.5
7.5°	1607.1	1621.8	1650.4	1677.7	1709.9	1737.0	1760.8	1787.9	1812.1	1848.0	1885.4
10°	1519.5	1545.2	1582.9	1608.6	1650.8	1677.8	1715.5	1745.2	1778.8	1826.3	1868.5
12.5°	1444.0	1475.1	1505.3	1541.0	1579.0	1624.0	1665.3	1703.5	1743.4	1792.5	1842.1
15°	1307.1	1351.9	1398.8	1435.0	1486.5	1534.0	1582.2	1633.7	1682.5	1741.2	1805.9
17.5°	1130.8	1182.8	1261.5	1323.7	1384.1	1431.8	1491.4	1553.7	1611.2	1682.0	1754.0
20°	1051.0	1089.3	1142.7	1226.6	1317.6	1368.4	1429.1	1497.7	1563.7	1640.9	1718.1
22.5°	987.1	1021.2	1064.1	1129.5	1231.1	1300.3	1363.7	1433.3	1509.8	1588.6	1674.3
25°	896.0	919.7	964.6	1017.4	1087.4	1201.4	1270.7	1340.7	1423.8	1508.3	1605.9
27.5°	827.5	848.9	878.0	928.4	980.4	1062.4	1172.6	1248.9	1331.7	1426.8	1528.1
30°	775.2	800.3	832.7	868.3	925.1	989.0	1099.2	1187.7	1269.5	1367.1	1475.3
32.5°	737.3	757.1	784.6	820.8	868.1	929.4	1017.4	1124.8	1204.5	1307.4	1420.4
35°	674.9	698.1	720.5	754.8	793.1	849.1	915.8	1030.6	1109.7	1211.3	1324.8
37.5°	623.6	637.7	662.5	689.7	730.1	772.0	829.7	932.7	1018.3	1118.1	1234.2
40°	584.5	602.4	620.9	651.2	684.2	724.4	781.2	857.7	956.1	1053.7	1167.2
42.5°	546.6	569.1	588.7	609.0	645.1	685.4	731.6	796.5	896.9	989.3	1099.6
45°	500.8	515.3	535.7	558.2	587.9	622.2	663.1	719.8	816.1	896.0	999.6
47.5°	447.5	468.7	482.1	503.9	532.2	564.9	603.0	652.0	730.0	804.8	900.9
50°	411.0	432.8	451.9	471.7	496.8	528.5	560.2	607.7	670.4	748.9	838.6
52.5°	379.9	399.1	417.7	437.5	462.0	491.0	521.1	562.8	616.5	688.7	775.8
55°	337.2	349.0	368.2	388.0	409.7	437.5	466.5	501.4	547.6	608.3	678.9
57.5°	293.3	307.0	322.3	342.2	364.2	385.5	411.6	443.2	479.7	534.6	595.0
60°	268.5	279.1	291.6	312.1	332.5	351.6	376.8	403.1	437.5	484.9	536.4
62.5°	241.1	251.2	262.6	280.4	300.3	317.9	339.8	367.7	396.8	440.1	485.2
65°	195.3	209.8	221.0	236.9	253.4	271.8	289.0	311.4	337.2	371.4	411.7
67.5°	162.0	169.3	179.7	194.1	211.0	226.9	243.1	260.6	282.9	309.4	341.4
70°	147.1	149.8	151.8	165.6	181.4	197.3	212.5	228.9	248.1	269.8	297.6
72.5°	129.8	132.3	134.8	140.8	153.4	169.3	185.0	197.3	215.3	233.4	255.9
75°	102.9	106.9	108.8	112.2	116.8	127.3	141.9	153.7	164.3	178.1	196.0
77.5°	78.4	80.6	82.7	86.2	89.1	93.9	102.1	112.8	122.7	130.8	143.0
80°	62.0	62.7	65.3	66.6	70.6	73.9	77.8	86.4	96.3	99.6	108.2
82.5°	46.8	47.4	49.5	50.8	52.7	55.4	60.4	62.7	70.4	74.8	80.2
85°	25.7	25.1	27.0	27.0	28.4	29.7	31.0	34.3	36.2	41.6	42.9
87.5°	10.0	10.1	10.2	10.0	9.6	10.4	10.8	11.1	12.0	13.4	15.3
90°	10.5	10.7	9.1	7.7	6.2	4.7	3.5	2.8	1.9	1.1	0.3
92.5°	9.7	9.6	9.3	9.0	8.6	8.3	7.8	7.2	6.6	6.0	5.4
95°	19.5	19.5	19.4	19.2	19.0	18.9	18.5	17.8	17.1	16.5	15.8
97.5°	32.7	32.7	32.5	32.2	31.9	31.7	31.3	30.7	30.0	29.5	28.9
100°	42.0	42.0	41.8	41.6	41.3	41.2	40.8	40.3	39.7	39.2	38.7
102.5°	52.0	51.9	51.7	51.4	51.1	51.0	50.5	50.1	49.7	49.2	48.8
105°	67.1	66.9	66.8	66.6	66.6	66.4	66.2	66.0	65.8	65.6	65.4
107.5°	83.4	83.4	83.4	83.4	83.4	83.4	83.3	83.0	82.7	82.4	82.1
110°	94.6	94.6	94.6	94.6	94.6	94.6	94.4	94.0	93.6	93.2	92.8



TEST NUMBER: P331736-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	105.9	106.1	106.1	106.2	106.2	106.2	106.1	105.6	105.3	104.9	104.4
115°	122.9	122.9	123.0	123.1	123.3	123.5	123.3	122.9	122.5	122.1	121.7
117.5°	139.4	139.6	139.9	140.3	140.7	141.1	141.0	140.4	139.9	139.4	138.8
120°	150.2	150.2	150.8	151.4	151.9	152.4	152.4	151.9	151.4	150.8	150.2
122.5°	161.8	162.0	162.3	162.7	163.1	163.5	163.3	162.6	162.0	161.4	160.7
125°	178.7	178.8	179.1	179.3	179.4	179.7	179.4	178.8	178.2	177.6	177.0
127.5°	195.0	195.3	195.5	195.8	196.0	196.2	196.0	195.2	194.5	193.7	193.0
130°	206.1	206.2	206.4	206.6	206.6	206.8	206.4	205.5	204.7	203.8	202.9
132.5°	217.1	217.4	217.4	217.4	217.3	217.3	217.0	216.2	215.5	214.8	214.1
135°	232.9	233.0	232.9	232.7	232.6	232.5	232.0	231.3	230.6	229.8	229.0
137.5°	248.3	248.3	248.1	248.0	247.8	247.6	247.3	246.7	246.0	245.4	244.8
140°	258.6	258.6	258.2	257.9	257.5	257.2	256.8	256.1	255.5	254.9	254.3
142.5°	267.9	267.8	267.6	267.3	267.1	266.9	266.5	265.9	265.3	264.7	264.1
145°	282.1	282.0	281.5	281.2	280.8	280.3	279.9	279.5	279.0	278.5	278.0
147.5°	294.5	294.3	294.0	293.8	293.4	293.2	292.7	292.2	291.6	291.1	290.5
150°	302.3	302.0	301.8	301.5	301.3	301.0	300.7	300.2	299.8	299.5	299.0
152.5°	310.1	309.9	309.5	309.2	308.8	308.6	308.2	307.8	307.4	306.9	306.6
155°	320.0	319.7	319.5	319.3	319.1	318.9	318.7	318.5	318.3	318.1	317.9
157.5°	329.2	328.7	328.6	328.5	328.4	328.2	328.1	328.0	327.8	327.7	327.5
160°	334.7	334.3	334.2	334.2	334.1	334.1	333.9	333.8	333.6	333.6	333.4
162.5°	339.7	339.1	339.1	339.1	339.0	338.9	338.9	338.8	338.8	338.8	338.7
165°	346.0	345.5	345.5	345.5	345.5	345.5	345.6	345.7	345.7	345.8	345.9
167.5°	351.3	350.9	350.9	350.9	350.9	350.9	351.0	351.2	351.5	351.6	351.8
170°	354.2	353.8	353.9	353.9	354.0	354.0	354.2	354.4	354.6	354.8	355.0
172.5°	356.5	355.9	356.0	356.1	356.2	356.2	356.4	356.5	356.8	357.0	357.1
175°	358.8	358.3	358.4	358.6	358.8	358.9	359.0	359.2	359.5	359.6	359.9
177.5°	360.1	359.7	359.8	360.0	360.1	360.2	360.3	360.5	360.6	360.8	360.9
180°	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5



TEST NUMBER: P331736-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1910.0	1911.5	1922.1	1926.8	1936.4	1940.0	1944.3	1943.2	1943.2	1945.3	1960.1
5°	1914.1	1927.3	1947.1	1966.2	1984.7	2000.4	2011.0	2021.6	2025.6	2044.7	2061.8
7.5°	1907.2	1931.5	1964.2	1993.4	2028.3	2055.6	2078.4	2098.8	2112.8	2140.6	2169.1
10°	1898.2	1932.5	1969.5	2007.1	2055.2	2091.5	2128.5	2156.9	2166.1	2207.7	2231.5
12.5°	1880.3	1926.2	1973.2	2021.9	2069.0	2119.0	2159.6	2188.0	2220.4	2257.8	2301.6
15°	1853.4	1906.2	1967.5	2030.2	2097.5	2158.2	2201.7	2251.2	2286.8	2327.7	2366.0
17.5°	1814.7	1882.7	1960.7	2033.3	2111.1	2176.3	2236.2	2283.6	2308.8	2332.1	2337.8
20°	1784.1	1857.3	1949.0	2034.8	2112.6	2187.9	2247.2	2286.8	2293.4	2294.0	2259.1
22.5°	1750.8	1833.6	1929.5	2017.4	2110.6	2194.2	2240.4	2257.3	2231.1	2186.4	2118.7
25°	1689.7	1785.4	1896.9	1997.2	2098.8	2178.0	2193.8	2164.1	2072.4	1976.1	1854.0
27.5°	1623.5	1731.0	1850.5	1962.0	2070.3	2119.4	2085.2	1978.1	1813.0	1669.4	1495.4
30°	1574.9	1695.7	1813.1	1937.8	2038.1	2059.2	1980.7	1823.0	1630.3	1413.9	1240.4
32.5°	1519.5	1646.1	1775.1	1904.0	1988.0	1967.4	1837.6	1643.6	1417.6	1204.9	1040.9
35°	1440.3	1571.0	1710.2	1839.5	1892.9	1803.9	1609.9	1357.2	1126.3	927.6	814.9
37.5°	1348.8	1491.2	1635.9	1754.6	1750.8	1602.4	1338.2	1077.3	883.2	765.8	685.4
40°	1283.9	1427.8	1584.2	1684.5	1641.6	1448.2	1161.9	915.8	774.0	680.3	621.6
42.5°	1221.7	1366.1	1521.4	1601.0	1526.5	1288.8	1003.6	810.7	693.7	620.6	573.0
45°	1115.7	1268.1	1412.0	1456.1	1322.8	1060.9	811.6	671.7	593.8	539.7	506.7
47.5°	1012.1	1162.0	1293.3	1294.1	1113.9	860.4	684.6	581.3	514.8	472.9	448.9
50°	948.7	1091.3	1201.4	1184.3	979.8	765.3	612.3	523.2	467.8	435.5	410.4
52.5°	877.5	1015.8	1111.2	1062.4	866.3	673.5	547.3	472.5	426.6	398.5	376.1
55°	774.0	896.6	964.0	890.0	706.6	560.2	462.5	403.8	369.5	345.7	326.6
57.5°	672.2	773.4	815.8	729.7	582.0	464.5	391.2	347.2	313.1	296.1	286.2
60°	608.3	694.7	724.4	629.5	506.1	406.4	346.4	305.5	280.4	269.2	259.3
62.5°	545.5	616.1	628.4	541.3	441.2	355.8	304.2	269.6	253.0	242.3	232.9
65°	452.6	503.4	497.5	427.6	349.0	282.4	244.8	223.7	211.1	196.0	179.4
67.5°	372.6	403.6	385.0	332.5	266.4	219.5	194.9	178.9	163.3	149.0	145.2
70°	322.0	339.8	320.0	271.8	218.3	184.1	164.3	145.2	136.0	132.6	126.7
72.5°	273.5	279.7	258.2	217.0	177.7	152.4	133.1	122.4	117.4	114.7	110.8
75°	205.2	200.6	182.1	149.8	123.4	106.2	100.3	96.3	93.0	90.4	88.4
77.5°	144.1	137.3	120.9	99.8	85.9	77.7	74.1	72.1	70.4	69.1	67.2
80°	108.2	103.6	87.1	71.3	65.3	61.4	59.4	56.7	56.7	55.4	53.5
82.5°	79.2	74.0	59.7	52.3	49.0	46.6	45.1	43.6	43.0	43.3	41.8
85°	41.6	33.7	29.7	28.4	26.4	25.1	25.7	24.5	24.5	24.5	23.8
87.5°	12.9	10.4	10.1	9.6	10.4	10.8	10.5	10.8	11.6	11.1	11.5
90°	1.1	1.9	2.8	3.5	4.7	6.2	7.7	9.1	10.7	10.5	10.4
92.5°	6.0	6.6	7.2	7.8	8.3	8.6	9.0	9.3	9.6	9.7	9.7
95°	16.5	17.1	17.8	18.5	18.9	19.0	19.2	19.4	19.5	19.5	19.5
97.5°	29.5	30.0	30.7	31.3	31.7	31.9	32.2	32.5	32.7	32.7	32.7
100°	39.2	39.7	40.3	40.8	41.2	41.3	41.6	41.8	42.0	42.0	42.0
102.5°	49.2	49.7	50.1	50.5	51.0	51.1	51.4	51.7	51.9	52.0	52.1
105°	65.6	65.8	66.0	66.2	66.4	66.6	66.6	66.8	66.9	67.1	67.2
107.5°	82.4	82.7	83.0	83.3	83.4	83.4	83.4	83.4	83.4	83.4	83.5
110°	93.2	93.6	94.0	94.4	94.6	94.6	94.6	94.6	94.6	94.6	94.6



TEST NUMBER: P331736-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	104.9	105.3	105.6	106.1	106.2	106.2	106.2	106.1	106.1	105.9	105.7
115°	122.1	122.5	122.9	123.3	123.5	123.3	123.1	123.0	122.9	122.9	122.8
117.5°	139.4	139.9	140.4	141.0	141.1	140.7	140.3	139.9	139.6	139.4	139.2
120°	150.8	151.4	151.9	152.4	152.4	151.9	151.4	150.8	150.2	150.2	150.2
122.5°	161.4	162.0	162.6	163.3	163.5	163.1	162.7	162.3	162.0	161.8	161.6
125°	177.6	178.2	178.8	179.4	179.7	179.4	179.3	179.1	178.8	178.7	178.5
127.5°	193.7	194.5	195.2	196.0	196.2	196.0	195.8	195.5	195.3	195.0	194.8
130°	203.8	204.7	205.5	206.4	206.8	206.6	206.6	206.4	206.2	206.1	206.0
132.5°	214.8	215.5	216.2	217.0	217.3	217.3	217.4	217.4	217.4	217.1	216.8
135°	229.8	230.6	231.3	232.0	232.5	232.6	232.7	232.9	233.0	232.9	232.9
137.5°	245.4	246.0	246.7	247.3	247.6	247.8	248.0	248.1	248.3	248.3	248.2
140°	254.9	255.5	256.1	256.8	257.2	257.5	257.9	258.2	258.6	258.6	258.6
142.5°	264.7	265.3	265.9	266.5	266.9	267.1	267.3	267.6	267.8	267.9	267.9
145°	278.5	279.0	279.5	279.9	280.3	280.8	281.2	281.5	282.0	282.1	282.1
147.5°	291.1	291.6	292.2	292.7	293.2	293.4	293.8	294.0	294.3	294.5	294.5
150°	299.5	299.8	300.2	300.7	301.0	301.3	301.5	301.8	302.0	302.3	302.5
152.5°	306.9	307.4	307.8	308.2	308.6	308.8	309.2	309.5	309.9	310.1	310.4
155°	318.1	318.3	318.5	318.7	318.9	319.1	319.3	319.5	319.7	320.0	320.4
157.5°	327.7	327.8	328.0	328.1	328.2	328.4	328.5	328.6	328.7	329.2	329.6
160°	333.6	333.6	333.8	333.9	334.1	334.1	334.2	334.2	334.3	334.7	335.1
162.5°	338.8	338.8	338.8	338.9	338.9	339.0	339.1	339.1	339.1	339.7	340.1
165°	345.8	345.7	345.7	345.6	345.5	345.5	345.5	345.5	345.5	346.0	346.5
167.5°	351.6	351.5	351.2	351.0	350.9	350.9	350.9	350.9	350.9	351.3	351.8
170°	354.8	354.6	354.4	354.2	354.0	354.0	353.9	353.9	353.8	354.2	354.7
172.5°	357.0	356.8	356.5	356.4	356.2	356.2	356.1	356.0	355.9	356.5	356.9
175°	359.6	359.5	359.2	359.0	358.9	358.8	358.6	358.4	358.3	358.8	359.3
177.5°	360.8	360.6	360.5	360.3	360.2	360.1	360.0	359.8	359.7	360.1	360.4
180°	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5



TEST NUMBER: P331736-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1965.4	1972.2	1975.4	1975.4	1979.1	1977.5	1975.9
5°	2078.4	2090.9	2093.5	2105.4	2113.9	2111.3	2112.6
7.5°	2190.6	2210.8	2230.8	2239.9	2241.3	2246.6	2248.6
10°	2259.8	2276.3	2307.3	2302.7	2325.7	2339.0	2317.2
12.5°	2326.2	2348.5	2370.1	2376.0	2389.1	2393.3	2384.7
15°	2386.4	2398.3	2399.7	2396.3	2400.3	2397.0	2384.5
17.5°	2330.2	2311.0	2271.9	2253.4	2238.8	2217.2	2208.5
20°	2237.3	2180.6	2114.6	2088.3	2057.2	1996.5	2011.0
22.5°	2036.8	1972.1	1906.2	1829.1	1792.3	1734.7	1731.3
25°	1724.7	1613.2	1490.5	1404.7	1354.5	1297.2	1272.0
27.5°	1340.9	1200.6	1100.0	1049.0	1002.7	957.3	955.4
30°	1088.6	983.1	905.3	861.7	833.3	814.2	818.1
32.5°	917.7	845.3	792.8	756.6	735.6	721.3	721.0
35°	750.2	700.7	667.0	651.9	636.7	626.1	626.8
37.5°	642.0	612.3	593.6	576.8	567.3	562.1	559.2
40°	586.5	562.1	547.6	537.7	529.8	522.5	521.2
42.5°	542.8	522.5	508.1	500.2	492.8	487.8	486.4
45°	481.6	465.1	451.9	443.4	440.1	435.5	435.5
47.5°	428.4	412.2	401.9	396.6	390.9	387.8	387.7
50°	392.6	380.0	370.8	367.5	362.9	360.9	360.2
52.5°	360.4	351.0	344.4	342.2	340.2	337.7	338.1
55°	316.7	311.4	308.8	306.8	303.5	299.5	302.2
57.5°	279.9	275.4	268.3	262.1	259.1	256.2	257.4
60°	254.0	244.8	235.6	228.3	226.3	220.3	220.3
62.5°	221.3	208.4	197.0	193.0	191.0	188.2	187.6
65°	170.2	165.0	162.3	159.6	158.3	158.3	157.0
67.5°	141.0	139.0	136.0	135.3	134.1	133.7	133.3
70°	124.7	122.1	120.7	120.1	118.7	119.4	117.4
72.5°	108.8	106.8	106.5	104.8	104.0	104.1	102.6
75°	85.8	85.8	85.2	84.5	83.2	82.5	83.2
77.5°	66.0	66.1	64.9	64.8	64.7	64.8	64.1
80°	52.8	53.5	52.8	52.1	51.5	52.1	51.5
82.5°	41.7	40.8	40.6	40.6	40.4	40.0	39.9
85°	23.8	24.5	23.8	23.1	23.1	23.1	23.8
87.5°	11.0	11.0	11.0	11.0	11.0	11.0	10.5
90°	10.2	10.1	10.1	10.2	10.2	10.2	10.3
92.5°	9.7	9.8	9.8	9.8	9.8	9.8	9.8
95°	19.5	19.5	19.4	19.3	19.1	19.0	18.9
97.5°	32.7	32.7	32.7	32.7	32.7	32.7	32.6
100°	42.0	42.0	41.9	41.8	41.8	41.8	41.7
102.5°	52.1	52.2	52.2	52.1	52.0	52.0	51.9
105°	67.3	67.5	67.5	67.5	67.5	67.5	67.5
107.5°	83.6	83.6	83.5	83.2	82.9	82.6	82.2
110°	94.6	94.6	94.5	94.3	94.1	93.9	93.7



TEST NUMBER: P331736-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	105.6	105.4	105.2	105.1	105.0	104.8	104.6
115°	122.7	122.6	122.5	122.3	122.1	121.9	121.7
117.5°	139.1	138.9	138.7	138.5	138.4	138.1	137.9
120°	150.2	150.2	150.2	150.0	149.7	149.6	149.4
122.5°	161.4	161.3	161.2	161.0	160.8	160.7	160.6
125°	178.2	178.1	177.9	177.9	177.8	177.7	177.6
127.5°	194.6	194.3	194.1	193.9	193.6	193.5	193.2
130°	205.9	205.7	205.5	205.3	204.9	204.7	204.4
132.5°	216.5	216.3	216.0	215.8	215.6	215.3	215.2
135°	232.8	232.7	232.6	232.4	232.2	232.0	231.8
137.5°	248.1	248.1	248.0	247.7	247.5	247.2	246.8
140°	258.6	258.6	258.4	258.1	257.9	257.6	257.4
142.5°	267.9	268.0	267.9	267.7	267.3	267.1	266.8
145°	282.1	282.2	282.1	281.9	281.6	281.4	281.0
147.5°	294.7	294.9	294.8	294.5	294.3	294.0	293.8
150°	302.6	302.9	302.9	302.6	302.5	302.3	302.0
152.5°	310.6	310.9	310.9	310.6	310.4	310.1	309.9
155°	320.7	321.1	321.2	320.9	320.7	320.6	320.3
157.5°	330.1	330.5	330.6	330.3	329.9	329.7	329.3
160°	335.5	336.0	336.0	335.7	335.4	335.2	334.9
162.5°	340.5	341.0	341.0	340.8	340.4	340.1	339.8
165°	347.0	347.4	347.5	347.2	346.8	346.5	346.2
167.5°	352.2	352.8	352.8	352.5	352.1	351.7	351.4
170°	355.2	355.7	355.7	355.3	354.9	354.5	354.0
172.5°	357.4	357.8	357.9	357.5	357.1	356.7	356.3
175°	359.7	360.2	360.2	359.9	359.5	359.0	358.6
177.5°	360.7	361.0	361.0	360.7	360.4	360.1	359.7
180°	360.5	360.5	360.5	360.5	360.5	360.5	360.5

(END OF REPORT)