

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331737-935

Luminaire Tested: **SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331737-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4383.9 lumens  
Efficiency: N/A  
Efficacy: 88.0 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331737-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331737-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75				75
1	104	100	97	94	99	96	93	90	87	85	82	79	77	75	72	70	69				65	
2	96	89	83	79	91	85	80	76	78	74	70	71	68	65	65	62	60				57	
3	89	80	73	67	84	76	70	65	70	65	61	64	60	57	58	55	53				50	
4	82	72	64	58	78	69	62	56	63	57	53	58	53	50	53	50	47				44	
5	76	65	57	51	72	62	55	50	57	51	47	53	48	44	49	45	42				39	
6	70	59	51	45	67	57	49	44	52	46	42	48	43	40	45	41	37				35	
7	66	54	46	41	63	52	45	40	48	42	38	45	39	36	41	37	34				32	
8	61	49	42	37	59	48	41	36	44	38	34	41	36	32	38	34	31				29	
9	58	46	38	33	55	44	37	33	41	35	31	38	33	30	36	31	28				26	
10	54	42	35	30	52	41	34	30	38	32	29	36	31	27	33	29	26				24	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	30658	30658	30658	30658
5°	34240	30851	27353	30851
10°	37990	30634	23710	30634
15°	39858	30186	18683	30186
20°	34553	29520	16167	29520
25°	22661	28609	14434	28609
30°	15252	27505	13064	27505
35°	12354	26112	11783	26112
40°	10985	24601	10903	24601
45°	9944	22825	9732	22825
50°	9048	21064	9018	21064
55°	8507	19111	8397	19111
60°	7114	17321	7030	17321
65°	5998	15729	6804	15729
70°	5542	14049	6420	14049
75°	5190	12227	5926	12227
80°	4788	10060	5272	10060
85°	4409	7947	4650	7947



TEST NUMBER: P331737-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	180.0	4.1
10°-20°	501.6	11.4
20°-30°	646.3	14.7
30°-40°	614.2	14.0
40°-50°	526.2	12.0
50°-60°	400.7	9.1
60°-70°	253.3	5.8
70°-80°	126.5	2.9
80°-90°	34.4	0.8
90°-100°	63.3	1.4
100°-110°	214.7	4.9
110°-120°	228.0	5.2
120°-130°	187.7	4.3
130°-140°	150.7	3.4
140°-150°	113.9	2.6
150°-160°	80.1	1.8
160°-170°	47.1	1.1
170°-180°	15.3	0.3
0°-30°	1327.9	30.3
0°-40°	1942.1	44.3
0°-60°	2869.0	65.4
0°-90°	3283.1	74.9
90°-120°	505.9	11.5
90°-150°	958.3	21.9
90°-180°	1101.0	25.1
0°-180°	4383.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1899	1899	1899	1899	1899	
5°	2113	1904	1688	1904	2113	209
15°	2384	1806	1118	1806	2384	643
25°	1272	1606	810	1606	1272	604
35°	627	1325	598	1325	627	401
45°	436	1000	426	1000	436	337
55°	302	679	298	679	302	265
65°	157	412	178	412	157	160
75°	83	196	95	196	83	88
85°	24	43	25	43	24	26
90°	10	0	10	0	10	7
95°	35	11	35	11	35	45
105°	343	37	343	37	343	332
115°	451	65	451	65	451	442
125°	366	91	366	91	366	331
135°	303	107	303	107	303	236
145°	242	122	242	122	242	154
155°	204	139	204	139	204	95
165°	179	152	179	152	179	51
175°	161	158	161	158	161	16
180°	158	158	158	158	158	



TEST NUMBER: P331737-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1975.9	1977.5	1979.1	1975.4	1975.4	1972.2	1965.4	1960.1	1945.3	1943.2	1943.2
5°	2112.6	2111.3	2113.9	2105.4	2093.5	2090.9	2078.4	2061.8	2044.7	2025.6	2021.6
7.5°	2248.6	2246.6	2241.3	2239.9	2230.8	2210.8	2190.6	2169.1	2140.6	2112.8	2098.8
10°	2317.2	2339.0	2325.7	2302.7	2307.3	2276.3	2259.8	2231.5	2207.7	2166.1	2156.9
12.5°	2384.7	2393.3	2389.1	2376.0	2370.1	2348.5	2326.2	2301.6	2257.8	2220.4	2188.0
15°	2384.5	2397.0	2400.3	2396.3	2399.7	2398.3	2386.4	2366.0	2327.7	2286.8	2251.2
17.5°	2208.5	2217.2	2238.8	2253.4	2271.9	2311.0	2330.2	2337.8	2332.1	2308.8	2283.6
20°	2011.0	1996.5	2057.2	2088.3	2114.6	2180.6	2237.3	2259.1	2294.0	2293.4	2286.8
22.5°	1731.3	1734.7	1792.3	1829.1	1906.2	1972.1	2036.8	2118.7	2186.4	2231.1	2257.3
25°	1272.0	1297.2	1354.5	1404.7	1490.5	1613.2	1724.7	1854.0	1976.1	2072.4	2164.1
27.5°	955.4	957.3	1002.7	1049.0	1100.0	1200.6	1340.9	1495.4	1669.4	1813.0	1978.1
30°	818.1	814.2	833.3	861.7	905.3	983.1	1088.6	1240.4	1413.9	1630.3	1823.0
32.5°	721.0	721.3	735.6	756.6	792.8	845.3	917.7	1040.9	1204.9	1417.6	1643.6
35°	626.8	626.1	636.7	651.9	667.0	700.7	750.2	814.9	927.6	1126.3	1357.2
37.5°	559.2	562.1	567.3	576.8	593.6	612.3	642.0	685.4	765.8	883.2	1077.3
40°	521.2	522.5	529.8	537.7	547.6	562.1	586.5	621.6	680.3	774.0	915.8
42.5°	486.4	487.8	492.8	500.2	508.1	522.5	542.8	573.0	620.6	693.7	810.7
45°	435.5	435.5	440.1	443.4	451.9	465.1	481.6	506.7	539.7	593.8	671.7
47.5°	387.7	387.8	390.9	396.6	401.9	412.2	428.4	448.9	472.9	514.8	581.3
50°	360.2	360.9	362.9	367.5	370.8	380.0	392.6	410.4	435.5	467.8	523.2
52.5°	338.1	337.7	340.2	342.2	344.4	351.0	360.4	376.1	398.5	426.6	472.5
55°	302.2	299.5	303.5	306.8	308.8	311.4	316.7	326.6	345.7	369.5	403.8
57.5°	257.4	256.2	259.1	262.1	268.3	275.4	279.9	286.2	296.1	313.1	347.2
60°	220.3	220.3	226.3	228.3	235.6	244.8	254.0	259.3	269.2	280.4	305.5
62.5°	187.6	188.2	191.0	193.0	197.0	208.4	221.3	232.9	242.3	253.0	269.6
65°	157.0	158.3	158.3	159.6	162.3	165.0	170.2	179.4	196.0	211.1	223.7
67.5°	133.3	133.7	134.1	135.3	136.0	139.0	141.0	145.2	149.0	163.3	178.9
70°	117.4	119.4	118.7	120.1	120.7	122.1	124.7	126.7	132.6	136.0	145.2
72.5°	102.6	104.1	104.0	104.8	106.5	106.8	108.8	110.8	114.7	117.4	122.4
75°	83.2	82.5	83.2	84.5	85.2	85.8	85.8	88.4	90.4	93.0	96.3
77.5°	64.1	64.8	64.7	64.8	64.9	66.1	66.0	67.2	69.1	70.4	72.1
80°	51.5	52.1	51.5	52.1	52.8	53.5	52.8	53.5	55.4	56.7	56.7
82.5°	39.9	40.0	40.4	40.6	40.6	40.8	41.7	41.8	43.3	43.0	43.6
85°	23.8	23.1	23.1	23.1	23.8	24.5	23.8	23.8	24.5	24.5	24.5
87.5°	10.4	11.0	11.0	11.0	11.0	10.9	10.8	11.5	11.0	11.5	11.0
90°	10.1	10.1	10.1	10.1	10.1	9.7	9.1	9.7	10.1	10.3	10.1
92.5°	16.9	17.3	17.1	18.1	18.3	20.2	22.7	26.5	33.4	39.5	39.0
95°	34.7	34.4	35.3	37.7	41.7	48.4	61.1	79.7	104.4	119.2	105.6
97.5°	68.3	70.9	75.3	82.7	97.3	119.2	152.1	186.0	213.5	203.5	153.3
100°	108.9	114.4	123.2	136.3	161.5	198.4	240.0	277.8	284.1	240.3	165.5
102.5°	191.7	199.1	210.1	232.4	259.8	298.9	329.3	337.9	310.4	241.5	160.8
105°	342.9	347.1	360.2	379.0	398.0	407.9	404.0	369.6	306.3	225.4	151.8
107.5°	438.0	443.6	446.3	447.3	444.9	430.2	398.6	346.7	279.7	208.1	147.3
110°	466.7	467.0	464.3	458.5	445.4	420.4	381.5	327.0	262.9	199.8	146.4



TEST NUMBER: P331737-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	466.1	464.5	459.3	449.7	431.5	402.9	361.3	309.0	251.2	194.5	146.5
115°	451.2	448.4	440.5	426.5	404.9	373.6	333.7	286.9	236.7	188.6	147.8
117.5°	424.3	422.0	413.7	398.9	376.9	347.5	311.3	270.2	227.6	185.7	150.1
120°	407.1	404.0	395.2	380.9	359.6	331.9	299.6	261.9	222.7	184.1	151.5
122.5°	389.0	386.5	378.7	364.5	345.4	320.5	289.9	255.4	218.5	183.0	153.2
125°	366.0	363.5	355.9	344.4	326.7	303.9	277.2	245.8	212.7	181.3	155.8
127.5°	345.8	343.8	337.3	326.4	311.0	290.0	264.8	236.3	207.2	180.3	158.3
130°	334.3	331.9	325.8	315.5	300.6	280.5	256.5	230.3	203.5	179.8	160.3
132.5°	322.4	320.2	314.6	304.3	289.6	270.8	248.7	224.5	200.6	179.5	162.3
135°	303.3	302.1	296.6	286.5	273.5	256.5	236.3	216.3	196.5	179.2	164.6
137.5°	284.6	282.8	277.9	269.3	257.4	242.5	226.6	209.8	193.6	179.1	166.7
140°	271.6	269.8	265.3	257.4	247.6	234.3	220.2	205.6	191.9	178.9	167.6
142.5°	258.7	258.4	254.3	247.1	237.9	226.7	214.6	202.2	190.3	178.9	168.3
145°	242.1	241.3	238.2	233.0	225.8	216.9	207.5	197.4	188.0	178.2	169.1
147.5°	228.3	227.6	225.6	221.4	215.4	209.0	201.6	193.7	185.7	177.2	169.4
150°	220.0	219.6	217.8	214.1	209.6	204.1	197.8	191.1	183.7	176.4	169.1
152.5°	212.9	212.8	211.5	208.4	204.7	200.0	194.6	188.4	182.0	175.2	168.7
155°	203.5	204.1	202.9	200.8	197.4	194.1	189.5	184.7	178.9	173.1	167.9
157.5°	195.5	195.5	195.0	193.2	190.9	188.2	184.4	180.4	175.9	170.9	166.5
160°	190.5	190.5	190.1	188.6	186.5	184.3	181.0	177.6	173.7	169.4	165.8
162.5°	185.5	185.8	185.5	184.5	182.4	180.7	177.9	175.0	171.8	168.2	165.1
165°	178.6	178.9	178.9	177.6	176.4	175.2	173.1	171.0	168.5	165.8	163.7
167.5°	172.1	172.5	172.5	171.9	171.3	170.2	168.8	167.1	165.4	163.7	162.3
170°	168.2	168.8	169.1	168.2	167.9	167.3	166.1	165.2	163.7	162.5	161.5
172.5°	165.1	165.4	165.7	165.3	165.0	164.6	163.7	163.0	162.0	161.0	160.6
175°	160.9	161.5	161.9	161.5	161.5	161.3	160.9	160.7	159.7	159.4	159.1
177.5°	158.4	158.9	159.2	159.2	159.2	159.2	158.9	158.9	158.4	158.2	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331737-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1944.3	1940.0	1936.4	1926.8	1922.1	1911.5	1910.0	1909.4	1895.7	1882.5	1878.8
5°	2011.0	2000.4	1984.7	1966.2	1947.1	1927.3	1914.1	1903.5	1877.1	1852.0	1837.5
7.5°	2078.4	2055.6	2028.3	1993.4	1964.2	1931.5	1907.2	1885.4	1848.0	1812.1	1787.9
10°	2128.5	2091.5	2055.2	2007.1	1969.5	1932.5	1898.2	1868.5	1826.3	1778.8	1745.2
12.5°	2159.6	2119.0	2069.0	2021.9	1973.2	1926.2	1880.3	1842.1	1792.5	1743.4	1703.5
15°	2201.7	2158.2	2097.5	2030.2	1967.5	1906.2	1853.4	1805.9	1741.2	1682.5	1633.7
17.5°	2236.2	2176.3	2111.1	2033.3	1960.7	1882.7	1814.7	1754.0	1682.0	1611.2	1553.7
20°	2247.2	2187.9	2112.6	2034.8	1949.0	1857.3	1784.1	1718.1	1640.9	1563.7	1497.7
22.5°	2240.4	2194.2	2110.6	2017.4	1929.5	1833.6	1750.8	1674.3	1588.6	1509.8	1433.3
25°	2193.8	2178.0	2098.8	1997.2	1896.9	1785.4	1689.7	1605.9	1508.3	1423.8	1340.7
27.5°	2085.2	2119.4	2070.3	1962.0	1850.5	1731.0	1623.5	1528.1	1426.8	1331.7	1248.9
30°	1980.7	2059.2	2038.1	1937.8	1813.1	1695.7	1574.9	1475.3	1367.1	1269.5	1187.7
32.5°	1837.6	1967.4	1988.0	1904.0	1775.1	1646.1	1519.5	1420.4	1307.4	1204.5	1124.8
35°	1609.9	1803.9	1892.9	1839.5	1710.2	1571.0	1440.3	1324.8	1211.3	1109.7	1030.6
37.5°	1338.2	1602.4	1750.8	1754.6	1635.9	1491.2	1348.8	1234.2	1118.1	1018.3	932.7
40°	1161.9	1448.2	1641.6	1684.5	1584.2	1427.8	1283.9	1167.2	1053.7	956.1	857.7
42.5°	1003.6	1288.8	1526.5	1601.0	1521.4	1366.1	1221.7	1099.6	989.3	896.9	796.5
45°	811.6	1060.9	1322.8	1456.1	1412.0	1268.1	1115.7	999.6	896.0	816.1	719.8
47.5°	684.6	860.4	1113.9	1294.1	1293.3	1162.0	1012.1	900.9	804.8	730.0	652.0
50°	612.3	765.3	979.8	1184.3	1201.4	1091.3	948.7	838.6	748.9	670.4	607.7
52.5°	547.3	673.5	866.3	1062.4	1111.2	1015.8	877.5	775.8	688.7	616.5	562.8
55°	462.5	560.2	706.6	890.0	964.0	896.6	774.0	678.9	608.3	547.6	501.4
57.5°	391.2	464.5	582.0	729.7	815.8	773.4	672.2	595.0	534.6	479.7	443.2
60°	346.4	406.4	506.1	629.5	724.4	694.7	608.3	536.4	484.9	437.5	403.1
62.5°	304.2	355.8	441.2	541.3	628.4	616.1	545.5	485.2	440.1	396.8	367.7
65°	244.8	282.4	349.0	427.6	497.5	503.4	452.6	411.7	371.4	337.2	311.4
67.5°	194.9	219.5	266.4	332.5	385.0	403.6	372.6	341.4	309.4	282.9	260.6
70°	164.3	184.1	218.3	271.8	320.0	339.8	322.0	297.6	269.8	248.1	228.9
72.5°	133.1	152.4	177.7	217.0	258.2	279.7	273.5	255.9	233.4	215.3	197.3
75°	100.3	106.2	123.4	149.8	182.1	200.6	205.2	196.0	178.1	164.3	153.7
77.5°	74.1	77.7	85.9	99.8	120.9	137.3	144.1	143.0	130.8	122.7	112.8
80°	59.4	61.4	65.3	71.3	87.1	103.6	108.2	108.2	99.6	96.3	86.4
82.5°	45.1	46.6	49.0	52.3	59.7	74.0	79.2	80.2	74.8	70.4	62.7
85°	25.7	25.1	26.4	28.4	29.7	33.7	41.6	42.9	41.6	36.2	34.3
87.5°	10.6	10.7	10.4	9.7	10.1	10.5	12.9	15.3	13.4	12.1	11.2
90°	8.2	6.1	4.6	3.6	3.0	2.4	1.2	0.3	1.2	2.4	3.0
92.5°	30.4	20.7	13.8	10.9	8.9	7.6	5.3	3.7	5.3	7.6	8.9
95°	70.3	43.8	29.8	22.5	17.7	14.9	11.9	10.7	11.9	14.9	17.7
97.5°	94.7	57.8	40.2	31.9	26.3	22.2	18.9	17.3	18.9	22.2	26.3
100°	99.8	62.7	46.6	38.1	31.9	27.0	24.4	23.4	24.4	27.0	31.9
102.5°	100.0	67.1	52.2	43.7	37.3	32.5	29.7	29.0	29.7	32.5	37.3
105°	101.6	74.6	60.3	51.7	45.0	40.5	38.3	37.1	38.3	40.5	45.0
107.5°	105.8	82.2	68.4	59.8	53.1	48.9	46.8	45.9	46.8	48.9	53.1
110°	109.2	87.3	74.0	65.1	58.7	54.8	53.0	51.7	53.0	54.8	58.7





TEST NUMBER: P331737-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	112.9	92.2	79.3	70.2	64.1	60.4	58.3	57.1	58.3	60.4	64.1
115°	118.3	99.8	86.7	78.5	72.4	68.8	66.9	65.4	66.9	68.8	72.4
117.5°	124.2	106.8	94.7	86.2	80.3	77.1	75.3	74.0	75.3	77.1	80.3
120°	128.1	111.7	99.8	91.3	85.2	82.5	80.6	79.4	80.6	82.5	85.2
122.5°	131.5	116.2	105.1	96.3	90.3	87.3	85.5	84.6	85.5	87.3	90.3
125°	136.9	123.2	112.3	103.8	97.6	94.0	92.2	91.3	92.2	94.0	97.6
127.5°	142.0	129.7	119.0	110.2	104.4	100.4	97.8	96.6	97.8	100.4	104.4
130°	145.1	133.5	122.9	114.4	108.3	104.0	101.0	99.8	101.0	104.0	108.3
132.5°	148.3	137.0	126.8	118.3	111.9	107.5	104.2	102.7	104.2	107.5	111.9
135°	152.4	141.8	132.0	123.6	116.5	111.9	108.3	107.1	108.3	111.9	116.5
137.5°	155.6	145.7	136.0	128.1	121.2	116.3	112.7	111.2	112.7	116.3	121.2
140°	157.3	147.8	138.7	130.8	124.2	119.2	115.6	114.4	115.6	119.2	124.2
142.5°	158.8	149.6	140.7	133.3	126.8	121.9	118.6	117.5	118.6	121.9	126.8
145°	160.7	152.1	143.9	137.2	131.1	126.6	123.6	122.3	123.6	126.6	131.1
147.5°	161.7	154.2	146.5	140.5	135.4	131.2	128.3	127.4	128.3	131.2	135.4
150°	162.1	155.2	148.2	142.7	138.1	134.1	131.7	130.8	131.7	134.1	138.1
152.5°	162.4	156.1	149.8	144.9	140.5	137.1	134.7	134.2	134.7	137.1	140.5
155°	162.7	157.6	152.4	147.8	144.5	141.1	139.3	139.1	139.3	141.1	144.5
157.5°	162.7	158.6	154.2	150.4	147.7	144.8	143.4	143.0	143.4	144.8	147.7
160°	162.7	159.1	155.5	152.1	149.6	147.2	146.0	145.7	146.0	147.2	149.6
162.5°	162.5	159.4	156.2	153.6	151.4	149.5	148.2	148.4	148.2	149.5	151.4
165°	161.9	159.7	157.0	155.2	153.6	151.8	151.2	151.5	151.2	151.8	153.6
167.5°	161.4	159.6	157.6	156.5	155.4	154.2	153.7	154.0	153.7	154.2	155.4
170°	160.9	159.4	157.9	157.0	156.4	155.5	155.2	155.8	155.2	155.5	156.4
172.5°	160.2	159.2	158.2	157.5	157.1	156.2	156.4	156.7	156.4	156.2	157.1
175°	159.4	158.8	158.2	157.9	157.9	157.3	157.6	157.9	157.6	157.3	157.9
177.5°	158.9	158.4	158.2	158.2	158.2	157.7	157.9	158.4	157.9	157.7	158.2
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331737-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1872.0	1868.3	1861.4	1850.8	1844.5	1833.4	1826.0	1830.2	1831.3	1830.2	1829.2
5°	1821.7	1807.8	1788.7	1770.2	1753.1	1734.6	1724.1	1719.4	1710.2	1704.9	1702.3
7.5°	1760.8	1737.0	1709.9	1677.7	1650.4	1621.8	1607.1	1599.8	1581.0	1570.7	1561.7
10°	1715.5	1677.8	1650.8	1608.6	1582.9	1545.2	1519.5	1520.2	1494.4	1479.9	1469.4
12.5°	1665.3	1624.0	1579.0	1541.0	1505.3	1475.1	1444.0	1431.5	1404.2	1390.2	1361.7
15°	1582.2	1534.0	1486.5	1435.0	1398.8	1351.9	1307.1	1252.3	1208.1	1169.8	1159.3
17.5°	1491.4	1431.8	1384.1	1323.7	1261.5	1182.8	1130.8	1099.0	1072.3	1052.1	1037.1
20°	1429.1	1368.4	1317.6	1226.6	1142.7	1089.3	1051.0	1026.7	998.9	977.1	965.3
22.5°	1363.7	1300.3	1231.1	1129.5	1064.1	1021.2	987.1	959.1	940.3	923.3	912.5
25°	1270.7	1201.4	1087.4	1017.4	964.6	919.7	896.0	878.8	859.0	835.9	825.4
27.5°	1172.6	1062.4	980.4	928.4	878.0	848.9	827.5	801.9	784.2	773.8	762.8
30°	1099.2	989.0	925.1	868.3	832.7	800.3	775.2	760.8	743.6	725.7	718.5
32.5°	1017.4	929.4	868.1	820.8	784.6	757.1	737.3	713.8	701.4	690.4	675.2
35°	915.8	849.1	793.1	754.8	720.5	698.1	674.9	661.1	638.7	629.5	623.5
37.5°	829.7	772.0	730.1	689.7	662.5	637.7	623.6	601.6	591.9	579.0	566.5
40°	781.2	724.4	684.2	651.2	620.9	602.4	584.5	566.8	552.2	546.3	531.2
42.5°	731.6	685.4	645.1	609.0	588.7	569.1	546.6	533.5	518.5	508.9	499.5
45°	663.1	622.2	587.9	558.2	535.7	515.3	500.8	479.0	470.5	451.3	443.4
47.5°	603.0	564.9	532.2	503.9	482.1	468.7	447.5	430.4	416.7	405.0	394.9
50°	560.2	528.5	496.8	471.7	451.9	432.8	411.0	402.4	381.3	375.4	369.5
52.5°	521.1	491.0	462.0	437.5	417.7	399.1	379.9	368.7	354.5	348.5	344.1
55°	466.5	437.5	409.7	388.0	368.2	349.0	337.2	323.3	316.7	312.1	306.8
57.5°	411.6	385.5	364.2	342.2	322.3	307.0	293.3	285.0	278.2	272.1	265.8
60°	376.8	351.6	332.5	312.1	291.6	279.1	268.5	258.6	250.7	241.5	238.8
62.5°	339.8	317.9	300.3	280.4	262.6	251.2	241.1	231.7	222.2	208.8	205.1
65°	289.0	271.8	253.4	236.9	221.0	209.8	195.3	184.8	180.8	179.4	178.8
67.5°	243.1	226.9	211.0	194.1	179.7	169.3	162.0	160.3	157.6	156.8	154.9
70°	212.5	197.3	181.4	165.6	151.8	149.8	147.1	144.5	141.2	139.9	138.5
72.5°	185.0	169.3	153.4	140.8	134.8	132.3	129.8	127.1	124.8	123.6	122.7
75°	141.9	127.3	116.8	112.2	108.8	106.9	102.9	100.9	99.6	97.6	96.9
77.5°	102.1	93.9	89.1	86.2	82.7	80.6	78.4	76.4	75.0	74.6	73.5
80°	77.8	73.9	70.6	66.6	65.3	62.7	62.0	60.0	60.7	58.7	58.7
82.5°	60.4	55.4	52.7	50.8	49.5	47.4	46.8	45.8	45.9	44.4	44.4
85°	31.0	29.7	28.4	27.0	27.0	25.1	25.7	25.1	25.1	23.8	23.1
87.5°	10.8	10.4	9.6	10.1	10.4	10.0	9.9	9.3	9.2	9.3	8.9
90°	3.6	4.6	6.1	8.2	10.1	10.3	10.1	9.7	9.1	9.7	10.1
92.5°	10.9	13.8	20.7	30.4	39.0	39.5	33.4	26.5	22.7	20.2	18.3
95°	22.5	29.8	43.8	70.3	105.6	119.2	104.4	79.7	61.1	48.4	41.7
97.5°	31.9	40.2	57.8	94.7	153.3	203.5	213.5	186.0	152.1	119.2	97.3
100°	38.1	46.6	62.7	99.8	165.5	240.3	284.1	277.8	240.0	198.4	161.5
102.5°	43.7	52.2	67.1	100.0	160.8	241.5	310.4	337.9	329.3	298.9	259.8
105°	51.7	60.3	74.6	101.6	151.8	225.4	306.3	369.6	404.0	407.9	398.0
107.5°	59.8	68.4	82.2	105.8	147.3	208.1	279.7	346.7	398.6	430.2	444.9
110°	65.1	74.0	87.3	109.2	146.4	199.8	262.9	327.0	381.5	420.4	445.4



TEST NUMBER: P331737-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	70.2	79.3	92.2	112.9	146.5	194.5	251.2	309.0	361.3	402.9	431.5
115°	78.5	86.7	99.8	118.3	147.8	188.6	236.7	286.9	333.7	373.6	404.9
117.5°	86.2	94.7	106.8	124.2	150.1	185.7	227.6	270.2	311.3	347.5	376.9
120°	91.3	99.8	111.7	128.1	151.5	184.1	222.7	261.9	299.6	331.9	359.6
122.5°	96.3	105.1	116.2	131.5	153.2	183.0	218.5	255.4	289.9	320.5	345.4
125°	103.8	112.3	123.2	136.9	155.8	181.3	212.7	245.8	277.2	303.9	326.7
127.5°	110.2	119.0	129.7	142.0	158.3	180.3	207.2	236.3	264.8	290.0	311.0
130°	114.4	122.9	133.5	145.1	160.3	179.8	203.5	230.3	256.5	280.5	300.6
132.5°	118.3	126.8	137.0	148.3	162.3	179.5	200.6	224.5	248.7	270.8	289.6
135°	123.6	132.0	141.8	152.4	164.6	179.2	196.5	216.3	236.3	256.5	273.5
137.5°	128.1	136.0	145.7	155.6	166.7	179.1	193.6	209.8	226.6	242.5	257.4
140°	130.8	138.7	147.8	157.3	167.6	178.9	191.9	205.6	220.2	234.3	247.6
142.5°	133.3	140.7	149.6	158.8	168.3	178.9	190.3	202.2	214.6	226.7	237.9
145°	137.2	143.9	152.1	160.7	169.1	178.2	188.0	197.4	207.5	216.9	225.8
147.5°	140.5	146.5	154.2	161.7	169.4	177.2	185.7	193.7	201.6	209.0	215.4
150°	142.7	148.2	155.2	162.1	169.1	176.4	183.7	191.1	197.8	204.1	209.6
152.5°	144.9	149.8	156.1	162.4	168.7	175.2	182.0	188.4	194.6	200.0	204.7
155°	147.8	152.4	157.6	162.7	167.9	173.1	178.9	184.7	189.5	194.1	197.4
157.5°	150.4	154.2	158.6	162.7	166.5	170.9	175.9	180.4	184.4	188.2	190.9
160°	152.1	155.5	159.1	162.7	165.8	169.4	173.7	177.6	181.0	184.3	186.5
162.5°	153.6	156.2	159.4	162.5	165.1	168.2	171.8	175.0	177.9	180.7	182.4
165°	155.2	157.0	159.7	161.9	163.7	165.8	168.5	171.0	173.1	175.2	176.4
167.5°	156.5	157.6	159.6	161.4	162.3	163.7	165.4	167.1	168.8	170.2	171.3
170°	157.0	157.9	159.4	160.9	161.5	162.5	163.7	165.2	166.1	167.3	167.9
172.5°	157.5	158.2	159.2	160.2	160.6	161.0	162.0	163.0	163.7	164.6	165.0
175°	157.9	158.2	158.8	159.4	159.1	159.4	159.7	160.7	160.9	161.3	161.5
177.5°	158.2	158.2	158.4	158.9	158.4	158.2	158.4	158.9	158.9	159.2	159.2
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331737-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1823.4	1824.5	1822.9	1823.9	1822.9	1824.5	1823.4	1829.2	1830.2	1831.3	1830.2
5°	1698.9	1691.0	1689.7	1687.7	1689.7	1691.0	1698.9	1702.3	1704.9	1710.2	1719.4
7.5°	1550.4	1549.2	1545.9	1541.3	1545.9	1549.2	1550.4	1561.7	1570.7	1581.0	1599.8
10°	1454.8	1451.6	1450.9	1446.2	1450.9	1451.6	1454.8	1469.4	1479.9	1494.4	1520.2
12.5°	1342.9	1321.7	1319.5	1307.9	1319.5	1321.7	1342.9	1361.7	1390.2	1404.2	1431.5
15°	1143.4	1139.4	1126.3	1117.7	1126.3	1139.4	1143.4	1159.3	1169.8	1208.1	1252.3
17.5°	1029.4	1016.5	1012.4	1010.6	1012.4	1016.5	1029.4	1037.1	1052.1	1072.3	1099.0
20°	956.1	944.2	942.2	940.9	942.2	944.2	956.1	965.3	977.1	998.9	1026.7
22.5°	905.3	892.9	887.8	883.8	887.8	892.9	905.3	912.5	923.3	940.3	959.1
25°	818.8	814.2	811.6	810.2	811.6	814.2	818.8	825.4	835.9	859.0	878.8
27.5°	751.1	741.0	739.0	735.6	739.0	741.0	751.1	762.8	773.8	784.2	801.9
30°	712.6	709.3	704.6	700.7	704.6	709.3	712.6	718.5	725.7	743.6	760.8
32.5°	667.2	664.4	660.3	658.5	660.3	664.4	667.2	675.2	690.4	701.4	713.8
35°	616.9	607.7	603.7	597.8	603.7	607.7	616.9	623.5	629.5	638.7	661.1
37.5°	563.7	558.9	553.3	555.3	553.3	558.9	563.7	566.5	579.0	591.9	601.6
40°	522.5	519.3	518.0	517.3	518.0	519.3	522.5	531.2	546.3	552.2	566.8
42.5°	489.8	480.7	477.3	477.2	477.3	480.7	489.8	499.5	508.9	518.5	533.5
45°	440.1	431.5	425.6	426.2	425.6	431.5	440.1	443.4	451.3	470.5	479.0
47.5°	389.2	388.9	385.2	386.3	385.2	388.9	389.2	394.9	405.0	416.7	430.4
50°	364.9	360.9	358.3	359.0	358.3	360.9	364.9	369.5	375.4	381.3	402.4
52.5°	341.6	338.2	336.1	338.9	336.1	338.2	341.6	344.1	348.5	354.5	368.7
55°	303.5	299.5	298.9	298.3	298.9	299.5	303.5	306.8	312.1	316.7	323.3
57.5°	260.9	258.2	254.3	252.5	254.3	258.2	260.9	265.8	272.1	278.2	285.0
60°	230.2	225.0	218.3	217.7	218.3	225.0	230.2	238.8	241.5	250.7	258.6
62.5°	202.2	201.2	199.9	199.8	199.9	201.2	202.2	205.1	208.8	222.2	231.7
65°	177.5	176.8	177.5	178.1	177.5	176.8	177.5	178.8	179.4	180.8	184.8
67.5°	154.6	153.4	152.3	152.8	152.3	153.4	154.6	154.9	156.8	157.6	160.3
70°	137.2	136.6	136.0	136.0	136.0	136.6	137.2	138.5	139.9	141.2	144.5
72.5°	120.4	120.2	119.6	119.0	119.6	120.2	120.4	122.7	123.6	124.8	127.1
75°	96.3	95.0	95.0	95.0	95.0	95.0	96.3	96.9	97.6	99.6	100.9
77.5°	73.4	72.7	72.1	71.5	72.1	72.7	73.4	73.5	74.6	75.0	76.4
80°	58.0	57.4	56.7	56.7	56.7	57.4	58.0	58.7	58.7	60.7	60.0
82.5°	44.3	43.7	43.6	43.0	43.6	43.7	44.3	44.4	44.4	45.9	45.8
85°	23.8	24.5	23.8	25.1	23.8	24.5	23.8	23.1	23.8	25.1	25.1
87.5°	8.9	8.4	8.9	8.4	8.9	8.4	8.9	8.9	9.3	9.2	9.3
90°	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1	9.7	9.1	9.7
92.5°	18.1	17.1	17.3	16.9	17.3	17.1	18.1	18.3	20.2	22.7	26.5
95°	37.7	35.3	34.4	34.7	34.4	35.3	37.7	41.7	48.4	61.1	79.7
97.5°	82.7	75.3	70.9	68.3	70.9	75.3	82.7	97.3	119.2	152.1	186.0
100°	136.3	123.2	114.4	108.9	114.4	123.2	136.3	161.5	198.4	240.0	277.8
102.5°	232.4	210.1	199.1	191.7	199.1	210.1	232.4	259.8	298.9	329.3	337.9
105°	379.0	360.2	347.1	342.9	347.1	360.2	379.0	398.0	407.9	404.0	369.6
107.5°	447.3	446.3	443.6	438.0	443.6	446.3	447.3	444.9	430.2	398.6	346.7
110°	458.5	464.3	467.0	466.7	467.0	464.3	458.5	445.4	420.4	381.5	327.0



TEST NUMBER: P331737-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	449.7	459.3	464.5	466.1	464.5	459.3	449.7	431.5	402.9	361.3	309.0
115°	426.5	440.5	448.4	451.2	448.4	440.5	426.5	404.9	373.6	333.7	286.9
117.5°	398.9	413.7	422.0	424.3	422.0	413.7	398.9	376.9	347.5	311.3	270.2
120°	380.9	395.2	404.0	407.1	404.0	395.2	380.9	359.6	331.9	299.6	261.9
122.5°	364.5	378.7	386.5	389.0	386.5	378.7	364.5	345.4	320.5	289.9	255.4
125°	344.4	355.9	363.5	366.0	363.5	355.9	344.4	326.7	303.9	277.2	245.8
127.5°	326.4	337.3	343.8	345.8	343.8	337.3	326.4	311.0	290.0	264.8	236.3
130°	315.5	325.8	331.9	334.3	331.9	325.8	315.5	300.6	280.5	256.5	230.3
132.5°	304.3	314.6	320.2	322.4	320.2	314.6	304.3	289.6	270.8	248.7	224.5
135°	286.5	296.6	302.1	303.3	302.1	296.6	286.5	273.5	256.5	236.3	216.3
137.5°	269.3	277.9	282.8	284.6	282.8	277.9	269.3	257.4	242.5	226.6	209.8
140°	257.4	265.3	269.8	271.6	269.8	265.3	257.4	247.6	234.3	220.2	205.6
142.5°	247.1	254.3	258.4	258.7	258.4	254.3	247.1	237.9	226.7	214.6	202.2
145°	233.0	238.2	241.3	242.1	241.3	238.2	233.0	225.8	216.9	207.5	197.4
147.5°	221.4	225.6	227.6	228.3	227.6	225.6	221.4	215.4	209.0	201.6	193.7
150°	214.1	217.8	219.6	220.0	219.6	217.8	214.1	209.6	204.1	197.8	191.1
152.5°	208.4	211.5	212.8	212.9	212.8	211.5	208.4	204.7	200.0	194.6	188.4
155°	200.8	202.9	204.1	203.5	204.1	202.9	200.8	197.4	194.1	189.5	184.7
157.5°	193.2	195.0	195.5	195.5	195.5	195.0	193.2	190.9	188.2	184.4	180.4
160°	188.6	190.1	190.5	190.5	190.5	190.1	188.6	186.5	184.3	181.0	177.6
162.5°	184.5	185.5	185.8	185.5	185.8	185.5	184.5	182.4	180.7	177.9	175.0
165°	177.6	178.9	178.9	178.6	178.9	178.9	177.6	176.4	175.2	173.1	171.0
167.5°	171.9	172.5	172.5	172.1	172.5	172.5	171.9	171.3	170.2	168.8	167.1
170°	168.2	169.1	168.8	168.2	168.8	169.1	168.2	167.9	167.3	166.1	165.2
172.5°	165.3	165.7	165.4	165.1	165.4	165.7	165.3	165.0	164.6	163.7	163.0
175°	161.5	161.9	161.5	160.9	161.5	161.9	161.5	161.5	161.3	160.9	160.7
177.5°	159.2	159.2	158.9	158.4	158.9	159.2	159.2	159.2	159.2	158.9	158.9
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331737-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1826.0	1833.4	1844.5	1850.8	1861.4	1868.3	1872.0	1878.8	1882.5	1895.7	1909.4
5°	1724.1	1734.6	1753.1	1770.2	1788.7	1807.8	1821.7	1837.5	1852.0	1877.1	1903.5
7.5°	1607.1	1621.8	1650.4	1677.7	1709.9	1737.0	1760.8	1787.9	1812.1	1848.0	1885.4
10°	1519.5	1545.2	1582.9	1608.6	1650.8	1677.8	1715.5	1745.2	1778.8	1826.3	1868.5
12.5°	1444.0	1475.1	1505.3	1541.0	1579.0	1624.0	1665.3	1703.5	1743.4	1792.5	1842.1
15°	1307.1	1351.9	1398.8	1435.0	1486.5	1534.0	1582.2	1633.7	1682.5	1741.2	1805.9
17.5°	1130.8	1182.8	1261.5	1323.7	1384.1	1431.8	1491.4	1553.7	1611.2	1682.0	1754.0
20°	1051.0	1089.3	1142.7	1226.6	1317.6	1368.4	1429.1	1497.7	1563.7	1640.9	1718.1
22.5°	987.1	1021.2	1064.1	1129.5	1231.1	1300.3	1363.7	1433.3	1509.8	1588.6	1674.3
25°	896.0	919.7	964.6	1017.4	1087.4	1201.4	1270.7	1340.7	1423.8	1508.3	1605.9
27.5°	827.5	848.9	878.0	928.4	980.4	1062.4	1172.6	1248.9	1331.7	1426.8	1528.1
30°	775.2	800.3	832.7	868.3	925.1	989.0	1099.2	1187.7	1269.5	1367.1	1475.3
32.5°	737.3	757.1	784.6	820.8	868.1	929.4	1017.4	1124.8	1204.5	1307.4	1420.4
35°	674.9	698.1	720.5	754.8	793.1	849.1	915.8	1030.6	1109.7	1211.3	1324.8
37.5°	623.6	637.7	662.5	689.7	730.1	772.0	829.7	932.7	1018.3	1118.1	1234.2
40°	584.5	602.4	620.9	651.2	684.2	724.4	781.2	857.7	956.1	1053.7	1167.2
42.5°	546.6	569.1	588.7	609.0	645.1	685.4	731.6	796.5	896.9	989.3	1099.6
45°	500.8	515.3	535.7	558.2	587.9	622.2	663.1	719.8	816.1	896.0	999.6
47.5°	447.5	468.7	482.1	503.9	532.2	564.9	603.0	652.0	730.0	804.8	900.9
50°	411.0	432.8	451.9	471.7	496.8	528.5	560.2	607.7	670.4	748.9	838.6
52.5°	379.9	399.1	417.7	437.5	462.0	491.0	521.1	562.8	616.5	688.7	775.8
55°	337.2	349.0	368.2	388.0	409.7	437.5	466.5	501.4	547.6	608.3	678.9
57.5°	293.3	307.0	322.3	342.2	364.2	385.5	411.6	443.2	479.7	534.6	595.0
60°	268.5	279.1	291.6	312.1	332.5	351.6	376.8	403.1	437.5	484.9	536.4
62.5°	241.1	251.2	262.6	280.4	300.3	317.9	339.8	367.7	396.8	440.1	485.2
65°	195.3	209.8	221.0	236.9	253.4	271.8	289.0	311.4	337.2	371.4	411.7
67.5°	162.0	169.3	179.7	194.1	211.0	226.9	243.1	260.6	282.9	309.4	341.4
70°	147.1	149.8	151.8	165.6	181.4	197.3	212.5	228.9	248.1	269.8	297.6
72.5°	129.8	132.3	134.8	140.8	153.4	169.3	185.0	197.3	215.3	233.4	255.9
75°	102.9	106.9	108.8	112.2	116.8	127.3	141.9	153.7	164.3	178.1	196.0
77.5°	78.4	80.6	82.7	86.2	89.1	93.9	102.1	112.8	122.7	130.8	143.0
80°	62.0	62.7	65.3	66.6	70.6	73.9	77.8	86.4	96.3	99.6	108.2
82.5°	46.8	47.4	49.5	50.8	52.7	55.4	60.4	62.7	70.4	74.8	80.2
85°	25.7	25.1	27.0	27.0	28.4	29.7	31.0	34.3	36.2	41.6	42.9
87.5°	9.9	10.0	10.4	10.1	9.6	10.4	10.8	11.2	12.1	13.4	15.3
90°	10.1	10.3	10.1	8.2	6.1	4.6	3.6	3.0	2.4	1.2	0.3
92.5°	33.4	39.5	39.0	30.4	20.7	13.8	10.9	8.9	7.6	5.3	3.7
95°	104.4	119.2	105.6	70.3	43.8	29.8	22.5	17.7	14.9	11.9	10.7
97.5°	213.5	203.5	153.3	94.7	57.8	40.2	31.9	26.3	22.2	18.9	17.3
100°	284.1	240.3	165.5	99.8	62.7	46.6	38.1	31.9	27.0	24.4	23.4
102.5°	310.4	241.5	160.8	100.0	67.1	52.2	43.7	37.3	32.5	29.7	29.0
105°	306.3	225.4	151.8	101.6	74.6	60.3	51.7	45.0	40.5	38.3	37.1
107.5°	279.7	208.1	147.3	105.8	82.2	68.4	59.8	53.1	48.9	46.8	45.9
110°	262.9	199.8	146.4	109.2	87.3	74.0	65.1	58.7	54.8	53.0	51.7



TEST NUMBER: P331737-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	251.2	194.5	146.5	112.9	92.2	79.3	70.2	64.1	60.4	58.3	57.1
115°	236.7	188.6	147.8	118.3	99.8	86.7	78.5	72.4	68.8	66.9	65.4
117.5°	227.6	185.7	150.1	124.2	106.8	94.7	86.2	80.3	77.1	75.3	74.0
120°	222.7	184.1	151.5	128.1	111.7	99.8	91.3	85.2	82.5	80.6	79.4
122.5°	218.5	183.0	153.2	131.5	116.2	105.1	96.3	90.3	87.3	85.5	84.6
125°	212.7	181.3	155.8	136.9	123.2	112.3	103.8	97.6	94.0	92.2	91.3
127.5°	207.2	180.3	158.3	142.0	129.7	119.0	110.2	104.4	100.4	97.8	96.6
130°	203.5	179.8	160.3	145.1	133.5	122.9	114.4	108.3	104.0	101.0	99.8
132.5°	200.6	179.5	162.3	148.3	137.0	126.8	118.3	111.9	107.5	104.2	102.7
135°	196.5	179.2	164.6	152.4	141.8	132.0	123.6	116.5	111.9	108.3	107.1
137.5°	193.6	179.1	166.7	155.6	145.7	136.0	128.1	121.2	116.3	112.7	111.2
140°	191.9	178.9	167.6	157.3	147.8	138.7	130.8	124.2	119.2	115.6	114.4
142.5°	190.3	178.9	168.3	158.8	149.6	140.7	133.3	126.8	121.9	118.6	117.5
145°	188.0	178.2	169.1	160.7	152.1	143.9	137.2	131.1	126.6	123.6	122.3
147.5°	185.7	177.2	169.4	161.7	154.2	146.5	140.5	135.4	131.2	128.3	127.4
150°	183.7	176.4	169.1	162.1	155.2	148.2	142.7	138.1	134.1	131.7	130.8
152.5°	182.0	175.2	168.7	162.4	156.1	149.8	144.9	140.5	137.1	134.7	134.2
155°	178.9	173.1	167.9	162.7	157.6	152.4	147.8	144.5	141.1	139.3	139.1
157.5°	175.9	170.9	166.5	162.7	158.6	154.2	150.4	147.7	144.8	143.4	143.0
160°	173.7	169.4	165.8	162.7	159.1	155.5	152.1	149.6	147.2	146.0	145.7
162.5°	171.8	168.2	165.1	162.5	159.4	156.2	153.6	151.4	149.5	148.2	148.4
165°	168.5	165.8	163.7	161.9	159.7	157.0	155.2	153.6	151.8	151.2	151.5
167.5°	165.4	163.7	162.3	161.4	159.6	157.6	156.5	155.4	154.2	153.7	154.0
170°	163.7	162.5	161.5	160.9	159.4	157.9	157.0	156.4	155.5	155.2	155.8
172.5°	162.0	161.0	160.6	160.2	159.2	158.2	157.5	157.1	156.2	156.4	156.7
175°	159.7	159.4	159.1	159.4	158.8	158.2	157.9	157.9	157.3	157.6	157.9
177.5°	158.4	158.2	158.4	158.9	158.4	158.2	158.2	158.2	157.7	157.9	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331737-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1910.0	1911.5	1922.1	1926.8	1936.4	1940.0	1944.3	1943.2	1943.2	1945.3	1960.1
5°	1914.1	1927.3	1947.1	1966.2	1984.7	2000.4	2011.0	2021.6	2025.6	2044.7	2061.8
7.5°	1907.2	1931.5	1964.2	1993.4	2028.3	2055.6	2078.4	2098.8	2112.8	2140.6	2169.1
10°	1898.2	1932.5	1969.5	2007.1	2055.2	2091.5	2128.5	2156.9	2166.1	2207.7	2231.5
12.5°	1880.3	1926.2	1973.2	2021.9	2069.0	2119.0	2159.6	2188.0	2220.4	2257.8	2301.6
15°	1853.4	1906.2	1967.5	2030.2	2097.5	2158.2	2201.7	2251.2	2286.8	2327.7	2366.0
17.5°	1814.7	1882.7	1960.7	2033.3	2111.1	2176.3	2236.2	2283.6	2308.8	2332.1	2337.8
20°	1784.1	1857.3	1949.0	2034.8	2112.6	2187.9	2247.2	2286.8	2293.4	2294.0	2259.1
22.5°	1750.8	1833.6	1929.5	2017.4	2110.6	2194.2	2240.4	2257.3	2231.1	2186.4	2118.7
25°	1689.7	1785.4	1896.9	1997.2	2098.8	2178.0	2193.8	2164.1	2072.4	1976.1	1854.0
27.5°	1623.5	1731.0	1850.5	1962.0	2070.3	2119.4	2085.2	1978.1	1813.0	1669.4	1495.4
30°	1574.9	1695.7	1813.1	1937.8	2038.1	2059.2	1980.7	1823.0	1630.3	1413.9	1240.4
32.5°	1519.5	1646.1	1775.1	1904.0	1988.0	1967.4	1837.6	1643.6	1417.6	1204.9	1040.9
35°	1440.3	1571.0	1710.2	1839.5	1892.9	1803.9	1609.9	1357.2	1126.3	927.6	814.9
37.5°	1348.8	1491.2	1635.9	1754.6	1750.8	1602.4	1338.2	1077.3	883.2	765.8	685.4
40°	1283.9	1427.8	1584.2	1684.5	1641.6	1448.2	1161.9	915.8	774.0	680.3	621.6
42.5°	1221.7	1366.1	1521.4	1601.0	1526.5	1288.8	1003.6	810.7	693.7	620.6	573.0
45°	1115.7	1268.1	1412.0	1456.1	1322.8	1060.9	811.6	671.7	593.8	539.7	506.7
47.5°	1012.1	1162.0	1293.3	1294.1	1113.9	860.4	684.6	581.3	514.8	472.9	448.9
50°	948.7	1091.3	1201.4	1184.3	979.8	765.3	612.3	523.2	467.8	435.5	410.4
52.5°	877.5	1015.8	1111.2	1062.4	866.3	673.5	547.3	472.5	426.6	398.5	376.1
55°	774.0	896.6	964.0	890.0	706.6	560.2	462.5	403.8	369.5	345.7	326.6
57.5°	672.2	773.4	815.8	729.7	582.0	464.5	391.2	347.2	313.1	296.1	286.2
60°	608.3	694.7	724.4	629.5	506.1	406.4	346.4	305.5	280.4	269.2	259.3
62.5°	545.5	616.1	628.4	541.3	441.2	355.8	304.2	269.6	253.0	242.3	232.9
65°	452.6	503.4	497.5	427.6	349.0	282.4	244.8	223.7	211.1	196.0	179.4
67.5°	372.6	403.6	385.0	332.5	266.4	219.5	194.9	178.9	163.3	149.0	145.2
70°	322.0	339.8	320.0	271.8	218.3	184.1	164.3	145.2	136.0	132.6	126.7
72.5°	273.5	279.7	258.2	217.0	177.7	152.4	133.1	122.4	117.4	114.7	110.8
75°	205.2	200.6	182.1	149.8	123.4	106.2	100.3	96.3	93.0	90.4	88.4
77.5°	144.1	137.3	120.9	99.8	85.9	77.7	74.1	72.1	70.4	69.1	67.2
80°	108.2	103.6	87.1	71.3	65.3	61.4	59.4	56.7	56.7	55.4	53.5
82.5°	79.2	74.0	59.7	52.3	49.0	46.6	45.1	43.6	43.0	43.3	41.8
85°	41.6	33.7	29.7	28.4	26.4	25.1	25.7	24.5	24.5	24.5	23.8
87.5°	12.9	10.5	10.1	9.7	10.4	10.7	10.6	11.0	11.5	11.0	11.5
90°	1.2	2.4	3.0	3.6	4.6	6.1	8.2	10.1	10.3	10.1	9.7
92.5°	5.3	7.6	8.9	10.9	13.8	20.7	30.4	39.0	39.5	33.4	26.5
95°	11.9	14.9	17.7	22.5	29.8	43.8	70.3	105.6	119.2	104.4	79.7
97.5°	18.9	22.2	26.3	31.9	40.2	57.8	94.7	153.3	203.5	213.5	186.0
100°	24.4	27.0	31.9	38.1	46.6	62.7	99.8	165.5	240.3	284.1	277.8
102.5°	29.7	32.5	37.3	43.7	52.2	67.1	100.0	160.8	241.5	310.4	337.9
105°	38.3	40.5	45.0	51.7	60.3	74.6	101.6	151.8	225.4	306.3	369.6
107.5°	46.8	48.9	53.1	59.8	68.4	82.2	105.8	147.3	208.1	279.7	346.7
110°	53.0	54.8	58.7	65.1	74.0	87.3	109.2	146.4	199.8	262.9	327.0





TEST NUMBER: P331737-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	58.3	60.4	64.1	70.2	79.3	92.2	112.9	146.5	194.5	251.2	309.0
115°	66.9	68.8	72.4	78.5	86.7	99.8	118.3	147.8	188.6	236.7	286.9
117.5°	75.3	77.1	80.3	86.2	94.7	106.8	124.2	150.1	185.7	227.6	270.2
120°	80.6	82.5	85.2	91.3	99.8	111.7	128.1	151.5	184.1	222.7	261.9
122.5°	85.5	87.3	90.3	96.3	105.1	116.2	131.5	153.2	183.0	218.5	255.4
125°	92.2	94.0	97.6	103.8	112.3	123.2	136.9	155.8	181.3	212.7	245.8
127.5°	97.8	100.4	104.4	110.2	119.0	129.7	142.0	158.3	180.3	207.2	236.3
130°	101.0	104.0	108.3	114.4	122.9	133.5	145.1	160.3	179.8	203.5	230.3
132.5°	104.2	107.5	111.9	118.3	126.8	137.0	148.3	162.3	179.5	200.6	224.5
135°	108.3	111.9	116.5	123.6	132.0	141.8	152.4	164.6	179.2	196.5	216.3
137.5°	112.7	116.3	121.2	128.1	136.0	145.7	155.6	166.7	179.1	193.6	209.8
140°	115.6	119.2	124.2	130.8	138.7	147.8	157.3	167.6	178.9	191.9	205.6
142.5°	118.6	121.9	126.8	133.3	140.7	149.6	158.8	168.3	178.9	190.3	202.2
145°	123.6	126.6	131.1	137.2	143.9	152.1	160.7	169.1	178.2	188.0	197.4
147.5°	128.3	131.2	135.4	140.5	146.5	154.2	161.7	169.4	177.2	185.7	193.7
150°	131.7	134.1	138.1	142.7	148.2	155.2	162.1	169.1	176.4	183.7	191.1
152.5°	134.7	137.1	140.5	144.9	149.8	156.1	162.4	168.7	175.2	182.0	188.4
155°	139.3	141.1	144.5	147.8	152.4	157.6	162.7	167.9	173.1	178.9	184.7
157.5°	143.4	144.8	147.7	150.4	154.2	158.6	162.7	166.5	170.9	175.9	180.4
160°	146.0	147.2	149.6	152.1	155.5	159.1	162.7	165.8	169.4	173.7	177.6
162.5°	148.2	149.5	151.4	153.6	156.2	159.4	162.5	165.1	168.2	171.8	175.0
165°	151.2	151.8	153.6	155.2	157.0	159.7	161.9	163.7	165.8	168.5	171.0
167.5°	153.7	154.2	155.4	156.5	157.6	159.6	161.4	162.3	163.7	165.4	167.1
170°	155.2	155.5	156.4	157.0	157.9	159.4	160.9	161.5	162.5	163.7	165.2
172.5°	156.4	156.2	157.1	157.5	158.2	159.2	160.2	160.6	161.0	162.0	163.0
175°	157.6	157.3	157.9	157.9	158.2	158.8	159.4	159.1	159.4	159.7	160.7
177.5°	157.9	157.7	158.2	158.2	158.2	158.4	158.9	158.4	158.2	158.4	158.9
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331737-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1965.4	1972.2	1975.4	1975.4	1979.1	1977.5	1975.9
5°	2078.4	2090.9	2093.5	2105.4	2113.9	2111.3	2112.6
7.5°	2190.6	2210.8	2230.8	2239.9	2241.3	2246.6	2248.6
10°	2259.8	2276.3	2307.3	2302.7	2325.7	2339.0	2317.2
12.5°	2326.2	2348.5	2370.1	2376.0	2389.1	2393.3	2384.7
15°	2386.4	2398.3	2399.7	2396.3	2400.3	2397.0	2384.5
17.5°	2330.2	2311.0	2271.9	2253.4	2238.8	2217.2	2208.5
20°	2237.3	2180.6	2114.6	2088.3	2057.2	1996.5	2011.0
22.5°	2036.8	1972.1	1906.2	1829.1	1792.3	1734.7	1731.3
25°	1724.7	1613.2	1490.5	1404.7	1354.5	1297.2	1272.0
27.5°	1340.9	1200.6	1100.0	1049.0	1002.7	957.3	955.4
30°	1088.6	983.1	905.3	861.7	833.3	814.2	818.1
32.5°	917.7	845.3	792.8	756.6	735.6	721.3	721.0
35°	750.2	700.7	667.0	651.9	636.7	626.1	626.8
37.5°	642.0	612.3	593.6	576.8	567.3	562.1	559.2
40°	586.5	562.1	547.6	537.7	529.8	522.5	521.2
42.5°	542.8	522.5	508.1	500.2	492.8	487.8	486.4
45°	481.6	465.1	451.9	443.4	440.1	435.5	435.5
47.5°	428.4	412.2	401.9	396.6	390.9	387.8	387.7
50°	392.6	380.0	370.8	367.5	362.9	360.9	360.2
52.5°	360.4	351.0	344.4	342.2	340.2	337.7	338.1
55°	316.7	311.4	308.8	306.8	303.5	299.5	302.2
57.5°	279.9	275.4	268.3	262.1	259.1	256.2	257.4
60°	254.0	244.8	235.6	228.3	226.3	220.3	220.3
62.5°	221.3	208.4	197.0	193.0	191.0	188.2	187.6
65°	170.2	165.0	162.3	159.6	158.3	158.3	157.0
67.5°	141.0	139.0	136.0	135.3	134.1	133.7	133.3
70°	124.7	122.1	120.7	120.1	118.7	119.4	117.4
72.5°	108.8	106.8	106.5	104.8	104.0	104.1	102.6
75°	85.8	85.8	85.2	84.5	83.2	82.5	83.2
77.5°	66.0	66.1	64.9	64.8	64.7	64.8	64.1
80°	52.8	53.5	52.8	52.1	51.5	52.1	51.5
82.5°	41.7	40.8	40.6	40.6	40.4	40.0	39.9
85°	23.8	24.5	23.8	23.1	23.1	23.1	23.8
87.5°	10.8	10.9	11.0	11.0	11.0	11.0	10.4
90°	9.1	9.7	10.1	10.1	10.1	10.1	10.1
92.5°	22.7	20.2	18.3	18.1	17.1	17.3	16.9
95°	61.1	48.4	41.7	37.7	35.3	34.4	34.7
97.5°	152.1	119.2	97.3	82.7	75.3	70.9	68.3
100°	240.0	198.4	161.5	136.3	123.2	114.4	108.9
102.5°	329.3	298.9	259.8	232.4	210.1	199.1	191.7
105°	404.0	407.9	398.0	379.0	360.2	347.1	342.9
107.5°	398.6	430.2	444.9	447.3	446.3	443.6	438.0
110°	381.5	420.4	445.4	458.5	464.3	467.0	466.7



TEST NUMBER: P331737-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	361.3	402.9	431.5	449.7	459.3	464.5	466.1
115°	333.7	373.6	404.9	426.5	440.5	448.4	451.2
117.5°	311.3	347.5	376.9	398.9	413.7	422.0	424.3
120°	299.6	331.9	359.6	380.9	395.2	404.0	407.1
122.5°	289.9	320.5	345.4	364.5	378.7	386.5	389.0
125°	277.2	303.9	326.7	344.4	355.9	363.5	366.0
127.5°	264.8	290.0	311.0	326.4	337.3	343.8	345.8
130°	256.5	280.5	300.6	315.5	325.8	331.9	334.3
132.5°	248.7	270.8	289.6	304.3	314.6	320.2	322.4
135°	236.3	256.5	273.5	286.5	296.6	302.1	303.3
137.5°	226.6	242.5	257.4	269.3	277.9	282.8	284.6
140°	220.2	234.3	247.6	257.4	265.3	269.8	271.6
142.5°	214.6	226.7	237.9	247.1	254.3	258.4	258.7
145°	207.5	216.9	225.8	233.0	238.2	241.3	242.1
147.5°	201.6	209.0	215.4	221.4	225.6	227.6	228.3
150°	197.8	204.1	209.6	214.1	217.8	219.6	220.0
152.5°	194.6	200.0	204.7	208.4	211.5	212.8	212.9
155°	189.5	194.1	197.4	200.8	202.9	204.1	203.5
157.5°	184.4	188.2	190.9	193.2	195.0	195.5	195.5
160°	181.0	184.3	186.5	188.6	190.1	190.5	190.5
162.5°	177.9	180.7	182.4	184.5	185.5	185.8	185.5
165°	173.1	175.2	176.4	177.6	178.9	178.9	178.6
167.5°	168.8	170.2	171.3	171.9	172.5	172.5	172.1
170°	166.1	167.3	167.9	168.2	169.1	168.8	168.2
172.5°	163.7	164.6	165.0	165.3	165.7	165.4	165.1
175°	160.9	161.3	161.5	161.5	161.9	161.5	160.9
177.5°	158.9	159.2	159.2	159.2	159.2	158.9	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2

(END OF REPORT)