

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331743-935

Luminaire Tested: **SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331743-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5060.7 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331743-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331743-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	102	98	94	91	96	92	89	86	82	80	77	72	70	69	63	62	61	57
2	94	87	81	76	88	82	77	73	73	69	66	65	62	59	57	55	53	49
3	86	77	70	65	81	73	67	62	65	61	57	58	55	51	52	49	46	43
4	80	69	62	56	75	66	59	54	59	54	49	53	49	45	47	44	41	38
5	74	63	55	49	69	59	52	47	54	48	44	48	44	40	43	39	37	34
6	68	57	49	43	64	54	47	42	49	43	39	44	39	36	39	36	33	30
7	64	52	44	39	60	49	42	37	45	39	35	40	36	32	36	33	30	27
8	59	47	40	35	56	45	38	34	41	36	31	37	33	29	34	30	27	25
9	56	44	36	32	52	42	35	31	38	33	29	35	30	27	31	28	25	23
10	52	40	33	29	49	39	32	28	35	30	26	32	28	25	29	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30658	30658	30658	30658
5°	34240	30851	27353	30851
10°	37990	30634	23710	30634
15°	39858	30186	18683	30186
20°	34553	29520	16167	29520
25°	22661	28609	14434	28609
30°	15252	27505	13064	27505
35°	12354	26112	11783	26112
40°	10985	24601	10903	24601
45°	9944	22825	9732	22825
50°	9048	21064	9018	21064
55°	8507	19111	8397	19111
60°	7114	17321	7030	17321
65°	5998	15729	6804	15729
70°	5542	14049	6420	14049
75°	5190	12227	5926	12227
80°	4788	10060	5272	10060
85°	4409	7947	4650	7947



TEST NUMBER: P331743-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.0	3.6
10°-20°	501.6	9.9
20°-30°	646.3	12.8
30°-40°	614.2	12.1
40°-50°	526.2	10.4
50°-60°	400.7	7.9
60°-70°	253.3	5.0
70°-80°	126.5	2.5
80°-90°	35.2	0.7
90°-100°	102.1	2.0
100°-110°	346.4	6.8
110°-120°	368.0	7.3
120°-130°	303.0	6.0
130°-140°	243.3	4.8
140°-150°	183.9	3.6
150°-160°	129.2	2.6
160°-170°	76.1	1.5
170°-180°	24.8	0.5
0°-30°	1327.9	26.2
0°-40°	1942.1	38.4
0°-60°	2869.0	56.7
0°-90°	3284.0	64.9
90°-120°	816.6	16.1
90°-150°	1546.7	30.6
90°-180°	1777.0	35.1
0°-180°	5060.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1899	1899	1899	1899	1899	
5°	2113	1904	1688	1904	2113	209
15°	2384	1806	1118	1806	2384	643
25°	1272	1606	810	1606	1272	604
35°	627	1325	598	1325	627	401
45°	436	1000	426	1000	436	337
55°	302	679	298	679	302	265
65°	157	412	178	412	157	160
75°	83	196	95	196	83	88
85°	24	43	25	43	24	26
90°	16	0	16	0	16	10
95°	56	17	56	17	56	73
105°	553	60	553	60	553	535
115°	728	106	728	106	728	713
125°	591	147	591	147	591	534
135°	490	173	490	173	490	380
145°	391	197	391	197	391	248
155°	328	224	328	224	328	153
165°	288	244	288	244	288	82
175°	260	255	260	255	260	25
180°	255	255	255	255	255	



TEST NUMBER: P331743-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1975.9	1977.5	1979.1	1975.4	1975.4	1972.2	1965.4	1960.1	1945.3	1943.2	1943.2
5°	2112.6	2111.3	2113.9	2105.4	2093.5	2090.9	2078.4	2061.8	2044.7	2025.6	2021.6
7.5°	2248.6	2246.6	2241.3	2239.9	2230.8	2210.8	2190.6	2169.1	2140.6	2112.8	2098.8
10°	2317.2	2339.0	2325.7	2302.7	2307.3	2276.3	2259.8	2231.5	2207.7	2166.1	2156.9
12.5°	2384.7	2393.3	2389.1	2376.0	2370.1	2348.5	2326.2	2301.6	2257.8	2220.4	2188.0
15°	2384.5	2397.0	2400.3	2396.3	2399.7	2398.3	2386.4	2366.0	2327.7	2286.8	2251.2
17.5°	2208.5	2217.2	2238.8	2253.4	2271.9	2311.0	2330.2	2337.8	2332.1	2308.8	2283.6
20°	2011.0	1996.5	2057.2	2088.3	2114.6	2180.6	2237.3	2259.1	2294.0	2293.4	2286.8
22.5°	1731.3	1734.7	1792.3	1829.1	1906.2	1972.1	2036.8	2118.7	2186.4	2231.1	2257.3
25°	1272.0	1297.2	1354.5	1404.7	1490.5	1613.2	1724.7	1854.0	1976.1	2072.4	2164.1
27.5°	955.4	957.3	1002.7	1049.0	1100.0	1200.6	1340.9	1495.4	1669.4	1813.0	1978.1
30°	818.1	814.2	833.3	861.7	905.3	983.1	1088.6	1240.4	1413.9	1630.3	1823.0
32.5°	721.0	721.3	735.6	756.6	792.8	845.3	917.7	1040.9	1204.9	1417.6	1643.6
35°	626.8	626.1	636.7	651.9	667.0	700.7	750.2	814.9	927.6	1126.3	1357.2
37.5°	559.2	562.1	567.3	576.8	593.6	612.3	642.0	685.4	765.8	883.2	1077.3
40°	521.2	522.5	529.8	537.7	547.6	562.1	586.5	621.6	680.3	774.0	915.8
42.5°	486.4	487.8	492.8	500.2	508.1	522.5	542.8	573.0	620.6	693.7	810.7
45°	435.5	435.5	440.1	443.4	451.9	465.1	481.6	506.7	539.7	593.8	671.7
47.5°	387.7	387.8	390.9	396.6	401.9	412.2	428.4	448.9	472.9	514.8	581.3
50°	360.2	360.9	362.9	367.5	370.8	380.0	392.6	410.4	435.5	467.8	523.2
52.5°	338.1	337.7	340.2	342.2	344.4	351.0	360.4	376.1	398.5	426.6	472.5
55°	302.2	299.5	303.5	306.8	308.8	311.4	316.7	326.6	345.7	369.5	403.8
57.5°	257.4	256.2	259.1	262.1	268.3	275.4	279.9	286.2	296.1	313.1	347.2
60°	220.3	220.3	226.3	228.3	235.6	244.8	254.0	259.3	269.2	280.4	305.5
62.5°	187.6	188.2	191.0	193.0	197.0	208.4	221.3	232.9	242.3	253.0	269.6
65°	157.0	158.3	158.3	159.6	162.3	165.0	170.2	179.4	196.0	211.1	223.7
67.5°	133.3	133.7	134.1	135.3	136.0	139.0	141.0	145.2	149.0	163.3	178.9
70°	117.4	119.4	118.7	120.1	120.7	122.1	124.7	126.7	132.6	136.0	145.2
72.5°	102.6	104.1	104.0	104.8	106.5	106.8	108.8	110.8	114.7	117.4	122.4
75°	83.2	82.5	83.2	84.5	85.2	85.8	85.8	88.4	90.4	93.0	96.3
77.5°	64.1	64.8	64.7	64.8	64.9	66.1	66.0	67.2	69.1	70.4	72.1
80°	51.5	52.1	51.5	52.1	52.8	53.5	52.8	53.5	55.4	56.7	56.7
82.5°	39.9	40.0	40.4	40.6	40.6	40.8	41.7	41.8	43.3	43.0	43.6
85°	23.8	23.1	23.1	23.1	23.8	24.5	23.8	23.8	24.5	24.5	24.5
87.5°	11.7	12.2	12.2	12.2	12.2	12.1	11.9	12.7	12.2	12.8	12.2
90°	16.2	16.2	16.2	16.2	16.2	15.7	14.7	15.7	16.2	16.7	16.2
92.5°	27.2	28.0	27.6	29.2	29.5	32.6	36.8	42.8	53.9	63.8	62.9
95°	56.0	55.4	57.0	60.9	67.2	78.1	98.7	128.6	168.4	192.5	170.4
97.5°	110.2	114.3	121.5	133.5	157.0	192.5	245.6	300.2	344.7	328.6	247.5
100°	175.8	184.6	198.9	220.0	260.7	320.1	387.4	448.3	458.6	387.9	267.1
102.5°	309.4	321.3	339.1	375.1	419.4	482.4	531.6	545.4	501.0	389.9	259.7
105°	553.4	560.3	581.3	611.8	642.2	658.5	652.0	596.6	494.5	363.9	245.0
107.5°	706.9	716.0	720.2	721.9	718.1	694.3	643.3	559.6	451.3	336.0	237.7
110°	753.2	753.7	749.3	739.9	718.8	678.6	615.7	527.9	424.2	322.6	236.2



TEST NUMBER: P331743-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	752.4	749.8	741.4	725.8	696.5	650.3	583.2	498.8	405.4	313.9	236.6
115°	728.1	723.8	711.0	688.4	653.6	603.0	538.6	463.0	382.0	304.4	238.7
117.5°	684.8	681.1	667.7	643.9	608.3	560.9	502.5	436.1	367.3	299.8	242.2
120°	656.9	652.0	637.8	614.8	580.4	535.7	483.6	422.8	359.5	297.0	244.5
122.5°	627.9	623.8	611.1	588.4	557.6	517.2	468.0	412.2	352.8	295.5	247.3
125°	590.7	586.8	574.5	555.9	527.4	490.5	447.3	396.7	343.2	292.7	251.4
127.5°	558.1	554.9	544.3	526.8	502.0	468.0	427.3	381.5	334.4	291.0	255.6
130°	539.6	535.7	525.9	509.2	485.1	452.7	414.0	371.7	328.5	290.2	258.7
132.5°	520.4	516.9	507.8	491.1	467.4	437.0	401.4	362.3	323.7	289.8	261.9
135°	489.6	487.6	478.7	462.5	441.4	414.0	381.5	349.1	317.2	289.2	265.6
137.5°	459.3	456.3	448.6	434.6	415.4	391.4	365.8	338.6	312.5	289.1	269.0
140°	438.5	435.5	428.2	415.4	399.7	378.1	355.5	331.9	309.9	288.7	270.5
142.5°	417.7	417.1	410.5	398.9	384.0	365.9	346.5	326.4	307.1	288.7	271.7
145°	390.8	389.3	384.4	376.1	364.4	350.1	334.8	318.7	303.4	287.7	273.0
147.5°	368.3	367.5	364.1	357.5	347.8	337.3	325.5	312.7	299.7	285.9	273.4
150°	355.0	354.5	351.5	345.7	338.3	329.5	319.2	308.3	296.6	284.8	273.0
152.5°	343.6	343.5	341.4	336.2	330.5	322.8	314.1	304.0	293.9	282.8	272.2
155°	328.5	329.5	327.5	324.1	318.7	313.2	305.9	298.1	288.7	279.4	271.0
157.5°	315.6	315.6	314.8	311.9	308.1	303.8	297.6	291.1	283.9	275.9	268.8
160°	307.4	307.4	306.9	304.4	301.0	297.6	292.1	286.7	280.3	273.5	267.6
162.5°	299.5	299.9	299.5	297.7	294.3	291.7	287.1	282.4	277.2	271.6	266.4
165°	288.3	288.7	288.7	286.7	284.8	282.8	279.4	276.0	272.0	267.6	264.2
167.5°	277.8	278.4	278.5	277.4	276.6	274.7	272.4	269.8	266.9	264.2	261.9
170°	271.6	272.5	273.0	271.6	271.0	270.1	268.1	266.7	264.2	262.2	260.7
172.5°	266.4	267.0	267.5	266.8	266.3	265.7	264.2	263.1	261.4	259.8	259.2
175°	259.8	260.7	261.2	260.7	260.7	260.3	259.8	259.2	257.8	257.3	256.8
177.5°	255.7	256.5	256.9	256.9	256.9	256.9	256.5	256.5	255.7	255.3	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331743-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1944.3	1940.0	1936.4	1926.8	1922.1	1911.5	1910.0	1909.4	1895.7	1882.5	1878.8
5°	2011.0	2000.4	1984.7	1966.2	1947.1	1927.3	1914.1	1903.5	1877.1	1852.0	1837.5
7.5°	2078.4	2055.6	2028.3	1993.4	1964.2	1931.5	1907.2	1885.4	1848.0	1812.1	1787.9
10°	2128.5	2091.5	2055.2	2007.1	1969.5	1932.5	1898.2	1868.5	1826.3	1778.8	1745.2
12.5°	2159.6	2119.0	2069.0	2021.9	1973.2	1926.2	1880.3	1842.1	1792.5	1743.4	1703.5
15°	2201.7	2158.2	2097.5	2030.2	1967.5	1906.2	1853.4	1805.9	1741.2	1682.5	1633.7
17.5°	2236.2	2176.3	2111.1	2033.3	1960.7	1882.7	1814.7	1754.0	1682.0	1611.2	1553.7
20°	2247.2	2187.9	2112.6	2034.8	1949.0	1857.3	1784.1	1718.1	1640.9	1563.7	1497.7
22.5°	2240.4	2194.2	2110.6	2017.4	1929.5	1833.6	1750.8	1674.3	1588.6	1509.8	1433.3
25°	2193.8	2178.0	2098.8	1997.2	1896.9	1785.4	1689.7	1605.9	1508.3	1423.8	1340.7
27.5°	2085.2	2119.4	2070.3	1962.0	1850.5	1731.0	1623.5	1528.1	1426.8	1331.7	1248.9
30°	1980.7	2059.2	2038.1	1937.8	1813.1	1695.7	1574.9	1475.3	1367.1	1269.5	1187.7
32.5°	1837.6	1967.4	1988.0	1904.0	1775.1	1646.1	1519.5	1420.4	1307.4	1204.5	1124.8
35°	1609.9	1803.9	1892.9	1839.5	1710.2	1571.0	1440.3	1324.8	1211.3	1109.7	1030.6
37.5°	1338.2	1602.4	1750.8	1754.6	1635.9	1491.2	1348.8	1234.2	1118.1	1018.3	932.7
40°	1161.9	1448.2	1641.6	1684.5	1584.2	1427.8	1283.9	1167.2	1053.7	956.1	857.7
42.5°	1003.6	1288.8	1526.5	1601.0	1521.4	1366.1	1221.7	1099.6	989.3	896.9	796.5
45°	811.6	1060.9	1322.8	1456.1	1412.0	1268.1	1115.7	999.6	896.0	816.1	719.8
47.5°	684.6	860.4	1113.9	1294.1	1293.3	1162.0	1012.1	900.9	804.8	730.0	652.0
50°	612.3	765.3	979.8	1184.3	1201.4	1091.3	948.7	838.6	748.9	670.4	607.7
52.5°	547.3	673.5	866.3	1062.4	1111.2	1015.8	877.5	775.8	688.7	616.5	562.8
55°	462.5	560.2	706.6	890.0	964.0	896.6	774.0	678.9	608.3	547.6	501.4
57.5°	391.2	464.5	582.0	729.7	815.8	773.4	672.2	595.0	534.6	479.7	443.2
60°	346.4	406.4	506.1	629.5	724.4	694.7	608.3	536.4	484.9	437.5	403.1
62.5°	304.2	355.8	441.2	541.3	628.4	616.1	545.5	485.2	440.1	396.8	367.7
65°	244.8	282.4	349.0	427.6	497.5	503.4	452.6	411.7	371.4	337.2	311.4
67.5°	194.9	219.5	266.4	332.5	385.0	403.6	372.6	341.4	309.4	282.9	260.6
70°	164.3	184.1	218.3	271.8	320.0	339.8	322.0	297.6	269.8	248.1	228.9
72.5°	133.1	152.4	177.7	217.0	258.2	279.7	273.5	255.9	233.4	215.3	197.3
75°	100.3	106.2	123.4	149.8	182.1	200.6	205.2	196.0	178.1	164.3	153.7
77.5°	74.1	77.7	85.9	99.8	120.9	137.3	144.1	143.0	130.8	122.7	112.8
80°	59.4	61.4	65.3	71.3	87.1	103.6	108.2	108.2	99.6	96.3	86.4
82.5°	45.1	46.6	49.0	52.3	59.7	74.0	79.2	80.2	74.8	70.4	62.7
85°	25.7	25.1	26.4	28.4	29.7	33.7	41.6	42.9	41.6	36.2	34.3
87.5°	11.6	11.5	10.9	10.2	10.5	10.8	13.1	15.4	13.6	12.4	11.5
90°	13.3	9.8	7.4	5.9	4.9	4.0	2.0	0.5	2.0	4.0	4.9
92.5°	49.0	33.4	22.3	17.7	14.4	12.1	8.6	6.0	8.6	12.1	14.4
95°	113.4	70.7	48.1	36.3	28.5	24.0	19.1	17.2	19.1	24.0	28.5
97.5°	152.8	93.3	64.9	51.6	42.5	35.8	30.7	28.0	30.7	35.8	42.5
100°	161.1	101.2	75.2	61.4	51.6	43.7	39.3	37.8	39.3	43.7	51.6
102.5°	161.4	108.2	84.1	70.4	60.2	52.3	48.0	46.8	48.0	52.3	60.2
105°	164.0	120.3	97.2	83.4	72.7	65.3	61.9	59.9	61.9	65.3	72.7
107.5°	170.7	132.7	110.3	96.4	85.8	79.0	75.6	74.0	75.6	79.0	85.8
110°	176.2	140.9	119.3	105.0	94.8	88.4	85.4	83.4	85.4	88.4	94.8



TEST NUMBER: P331743-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	182.2	148.8	127.9	113.3	103.4	97.4	94.1	92.1	94.1	97.4	103.4
115°	191.0	161.1	139.9	126.7	116.8	111.0	108.1	105.6	108.1	111.0	116.8
117.5°	200.4	172.4	152.8	139.1	129.7	124.4	121.5	119.5	121.5	124.4	129.7
120°	206.7	180.2	161.1	147.3	137.5	133.0	130.1	128.1	130.1	133.0	137.5
122.5°	212.2	187.7	169.7	155.6	145.8	140.9	138.0	136.4	138.0	140.9	145.8
125°	220.9	198.9	181.2	167.5	157.6	151.7	148.8	147.3	148.8	151.7	157.6
127.5°	229.1	209.3	192.1	178.0	168.5	162.0	157.9	155.9	157.9	162.0	168.5
130°	234.2	215.6	198.4	184.6	174.8	167.9	163.0	161.1	163.0	167.9	174.8
132.5°	239.4	221.0	204.7	190.9	180.7	173.4	168.2	165.7	168.2	173.4	180.7
135°	246.0	228.9	213.1	199.3	188.0	180.7	174.8	172.8	174.8	180.7	188.0
137.5°	251.1	235.1	219.6	206.8	195.6	187.8	181.8	179.5	181.8	187.8	195.6
140°	253.8	238.7	223.9	211.1	200.4	192.5	186.6	184.6	186.6	192.5	200.4
142.5°	256.2	241.4	227.0	215.1	204.7	196.8	191.3	189.8	191.3	196.8	204.7
145°	259.2	245.5	232.2	221.4	211.6	204.2	199.3	197.4	199.3	204.2	211.6
147.5°	261.0	248.8	236.3	226.8	218.6	211.8	207.1	205.6	207.1	211.8	218.6
150°	261.7	250.4	239.1	230.3	222.9	216.5	212.6	211.1	212.6	216.5	222.9
152.5°	262.1	252.0	241.9	233.8	226.9	221.3	217.3	216.6	217.3	221.3	226.9
155°	262.7	254.3	246.0	238.7	233.2	227.8	224.9	224.4	224.9	227.8	233.2
157.5°	262.7	256.0	248.9	242.8	238.4	233.8	231.4	230.8	231.4	233.8	238.4
160°	262.7	256.8	250.9	245.5	241.6	237.6	235.7	235.2	235.7	237.6	241.6
162.5°	262.3	257.2	252.1	247.9	244.4	241.2	239.2	239.5	239.2	241.2	244.4
165°	261.2	257.8	253.4	250.4	248.0	245.0	244.0	244.5	244.0	245.0	248.0
167.5°	260.5	257.7	254.4	252.6	250.8	248.9	248.1	248.7	248.1	248.9	250.8
170°	259.8	257.3	254.9	253.4	252.4	250.9	250.4	251.4	250.4	250.9	252.4
172.5°	258.6	256.9	255.2	254.2	253.6	252.1	252.4	253.0	252.4	252.1	253.6
175°	257.3	256.3	255.3	254.9	254.9	253.8	254.3	254.9	254.3	253.8	254.9
177.5°	256.5	255.7	255.3	255.3	255.3	254.5	254.9	255.7	254.9	254.5	255.3
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331743-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1872.0	1868.3	1861.4	1850.8	1844.5	1833.4	1826.0	1830.2	1831.3	1830.2	1829.2
5°	1821.7	1807.8	1788.7	1770.2	1753.1	1734.6	1724.1	1719.4	1710.2	1704.9	1702.3
7.5°	1760.8	1737.0	1709.9	1677.7	1650.4	1621.8	1607.1	1599.8	1581.0	1570.7	1561.7
10°	1715.5	1677.8	1650.8	1608.6	1582.9	1545.2	1519.5	1520.2	1494.4	1479.9	1469.4
12.5°	1665.3	1624.0	1579.0	1541.0	1505.3	1475.1	1444.0	1431.5	1404.2	1390.2	1361.7
15°	1582.2	1534.0	1486.5	1435.0	1398.8	1351.9	1307.1	1252.3	1208.1	1169.8	1159.3
17.5°	1491.4	1431.8	1384.1	1323.7	1261.5	1182.8	1130.8	1099.0	1072.3	1052.1	1037.1
20°	1429.1	1368.4	1317.6	1226.6	1142.7	1089.3	1051.0	1026.7	998.9	977.1	965.3
22.5°	1363.7	1300.3	1231.1	1129.5	1064.1	1021.2	987.1	959.1	940.3	923.3	912.5
25°	1270.7	1201.4	1087.4	1017.4	964.6	919.7	896.0	878.8	859.0	835.9	825.4
27.5°	1172.6	1062.4	980.4	928.4	878.0	848.9	827.5	801.9	784.2	773.8	762.8
30°	1099.2	989.0	925.1	868.3	832.7	800.3	775.2	760.8	743.6	725.7	718.5
32.5°	1017.4	929.4	868.1	820.8	784.6	757.1	737.3	713.8	701.4	690.4	675.2
35°	915.8	849.1	793.1	754.8	720.5	698.1	674.9	661.1	638.7	629.5	623.5
37.5°	829.7	772.0	730.1	689.7	662.5	637.7	623.6	601.6	591.9	579.0	566.5
40°	781.2	724.4	684.2	651.2	620.9	602.4	584.5	566.8	552.2	546.3	531.2
42.5°	731.6	685.4	645.1	609.0	588.7	569.1	546.6	533.5	518.5	508.9	499.5
45°	663.1	622.2	587.9	558.2	535.7	515.3	500.8	479.0	470.5	451.3	443.4
47.5°	603.0	564.9	532.2	503.9	482.1	468.7	447.5	430.4	416.7	405.0	394.9
50°	560.2	528.5	496.8	471.7	451.9	432.8	411.0	402.4	381.3	375.4	369.5
52.5°	521.1	491.0	462.0	437.5	417.7	399.1	379.9	368.7	354.5	348.5	344.1
55°	466.5	437.5	409.7	388.0	368.2	349.0	337.2	323.3	316.7	312.1	306.8
57.5°	411.6	385.5	364.2	342.2	322.3	307.0	293.3	285.0	278.2	272.1	265.8
60°	376.8	351.6	332.5	312.1	291.6	279.1	268.5	258.6	250.7	241.5	238.8
62.5°	339.8	317.9	300.3	280.4	262.6	251.2	241.1	231.7	222.2	208.8	205.1
65°	289.0	271.8	253.4	236.9	221.0	209.8	195.3	184.8	180.8	179.4	178.8
67.5°	243.1	226.9	211.0	194.1	179.7	169.3	162.0	160.3	157.6	156.8	154.9
70°	212.5	197.3	181.4	165.6	151.8	149.8	147.1	144.5	141.2	139.9	138.5
72.5°	185.0	169.3	153.4	140.8	134.8	132.3	129.8	127.1	124.8	123.6	122.7
75°	141.9	127.3	116.8	112.2	108.8	106.9	102.9	100.9	99.6	97.6	96.9
77.5°	102.1	93.9	89.1	86.2	82.7	80.6	78.4	76.4	75.0	74.6	73.5
80°	77.8	73.9	70.6	66.6	65.3	62.7	62.0	60.0	60.7	58.7	58.7
82.5°	60.4	55.4	52.7	50.8	49.5	47.4	46.8	45.8	45.9	44.4	44.4
85°	31.0	29.7	28.4	27.0	27.0	25.1	25.7	25.1	25.1	23.8	23.1
87.5°	11.2	10.9	10.4	11.1	11.7	11.3	11.2	10.5	10.3	10.5	10.1
90°	5.9	7.4	9.8	13.3	16.2	16.7	16.2	15.7	14.7	15.7	16.2
92.5°	17.7	22.3	33.4	49.0	62.9	63.8	53.9	42.8	36.8	32.6	29.5
95°	36.3	48.1	70.7	113.4	170.4	192.5	168.4	128.6	98.7	78.1	67.2
97.5°	51.6	64.9	93.3	152.8	247.5	328.6	344.7	300.2	245.6	192.5	157.0
100°	61.4	75.2	101.2	161.1	267.1	387.9	458.6	448.3	387.4	320.1	260.7
102.5°	70.4	84.1	108.2	161.4	259.7	389.9	501.0	545.4	531.6	482.4	419.4
105°	83.4	97.2	120.3	164.0	245.0	363.9	494.5	596.6	652.0	658.5	642.2
107.5°	96.4	110.3	132.7	170.7	237.7	336.0	451.3	559.6	643.3	694.3	718.1
110°	105.0	119.3	140.9	176.2	236.2	322.6	424.2	527.9	615.7	678.6	718.8



TEST NUMBER: P331743-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	113.3	127.9	148.8	182.2	236.6	313.9	405.4	498.8	583.2	650.3	696.5
115°	126.7	139.9	161.1	191.0	238.7	304.4	382.0	463.0	538.6	603.0	653.6
117.5°	139.1	152.8	172.4	200.4	242.2	299.8	367.3	436.1	502.5	560.9	608.3
120°	147.3	161.1	180.2	206.7	244.5	297.0	359.5	422.8	483.6	535.7	580.4
122.5°	155.6	169.7	187.7	212.2	247.3	295.5	352.8	412.2	468.0	517.2	557.6
125°	167.5	181.2	198.9	220.9	251.4	292.7	343.2	396.7	447.3	490.5	527.4
127.5°	178.0	192.1	209.3	229.1	255.6	291.0	334.4	381.5	427.3	468.0	502.0
130°	184.6	198.4	215.6	234.2	258.7	290.2	328.5	371.7	414.0	452.7	485.1
132.5°	190.9	204.7	221.0	239.4	261.9	289.8	323.7	362.3	401.4	437.0	467.4
135°	199.3	213.1	228.9	246.0	265.6	289.2	317.2	349.1	381.5	414.0	441.4
137.5°	206.8	219.6	235.1	251.1	269.0	289.1	312.5	338.6	365.8	391.4	415.4
140°	211.1	223.9	238.7	253.8	270.5	288.7	309.9	331.9	355.5	378.1	399.7
142.5°	215.1	227.0	241.4	256.2	271.7	288.7	307.1	326.4	346.5	365.9	384.0
145°	221.4	232.2	245.5	259.2	273.0	287.7	303.4	318.7	334.8	350.1	364.4
147.5°	226.8	236.3	248.8	261.0	273.4	285.9	299.7	312.7	325.5	337.3	347.8
150°	230.3	239.1	250.4	261.7	273.0	284.8	296.6	308.3	319.2	329.5	338.3
152.5°	233.8	241.9	252.0	262.1	272.2	282.8	293.9	304.0	314.1	322.8	330.5
155°	238.7	246.0	254.3	262.7	271.0	279.4	288.7	298.1	305.9	313.2	318.7
157.5°	242.8	248.9	256.0	262.7	268.8	275.9	283.9	291.1	297.6	303.8	308.1
160°	245.5	250.9	256.8	262.7	267.6	273.5	280.3	286.7	292.1	297.6	301.0
162.5°	247.9	252.1	257.2	262.3	266.4	271.6	277.2	282.4	287.1	291.7	294.3
165°	250.4	253.4	257.8	261.2	264.2	267.6	272.0	276.0	279.4	282.8	284.8
167.5°	252.6	254.4	257.7	260.5	261.9	264.2	266.9	269.8	272.4	274.7	276.6
170°	253.4	254.9	257.3	259.8	260.7	262.2	264.2	266.7	268.1	270.1	271.0
172.5°	254.2	255.2	256.9	258.6	259.2	259.8	261.4	263.1	264.2	265.7	266.3
175°	254.9	255.3	256.3	257.3	256.8	257.3	257.8	259.2	259.8	260.3	260.7
177.5°	255.3	255.3	255.7	256.5	255.7	255.3	255.7	256.5	256.5	256.9	256.9
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331743-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1823.4	1824.5	1822.9	1823.9	1822.9	1824.5	1823.4	1829.2	1830.2	1831.3	1830.2
5°	1698.9	1691.0	1689.7	1687.7	1689.7	1691.0	1698.9	1702.3	1704.9	1710.2	1719.4
7.5°	1550.4	1549.2	1545.9	1541.3	1545.9	1549.2	1550.4	1561.7	1570.7	1581.0	1599.8
10°	1454.8	1451.6	1450.9	1446.2	1450.9	1451.6	1454.8	1469.4	1479.9	1494.4	1520.2
12.5°	1342.9	1321.7	1319.5	1307.9	1319.5	1321.7	1342.9	1361.7	1390.2	1404.2	1431.5
15°	1143.4	1139.4	1126.3	1117.7	1126.3	1139.4	1143.4	1159.3	1169.8	1208.1	1252.3
17.5°	1029.4	1016.5	1012.4	1010.6	1012.4	1016.5	1029.4	1037.1	1052.1	1072.3	1099.0
20°	956.1	944.2	942.2	940.9	942.2	944.2	956.1	965.3	977.1	998.9	1026.7
22.5°	905.3	892.9	887.8	883.8	887.8	892.9	905.3	912.5	923.3	940.3	959.1
25°	818.8	814.2	811.6	810.2	811.6	814.2	818.8	825.4	835.9	859.0	878.8
27.5°	751.1	741.0	739.0	735.6	739.0	741.0	751.1	762.8	773.8	784.2	801.9
30°	712.6	709.3	704.6	700.7	704.6	709.3	712.6	718.5	725.7	743.6	760.8
32.5°	667.2	664.4	660.3	658.5	660.3	664.4	667.2	675.2	690.4	701.4	713.8
35°	616.9	607.7	603.7	597.8	603.7	607.7	616.9	623.5	629.5	638.7	661.1
37.5°	563.7	558.9	553.3	555.3	553.3	558.9	563.7	566.5	579.0	591.9	601.6
40°	522.5	519.3	518.0	517.3	518.0	519.3	522.5	531.2	546.3	552.2	566.8
42.5°	489.8	480.7	477.3	477.2	477.3	480.7	489.8	499.5	508.9	518.5	533.5
45°	440.1	431.5	425.6	426.2	425.6	431.5	440.1	443.4	451.3	470.5	479.0
47.5°	389.2	388.9	385.2	386.3	385.2	388.9	389.2	394.9	405.0	416.7	430.4
50°	364.9	360.9	358.3	359.0	358.3	360.9	364.9	369.5	375.4	381.3	402.4
52.5°	341.6	338.2	336.1	338.9	336.1	338.2	341.6	344.1	348.5	354.5	368.7
55°	303.5	299.5	298.9	298.3	298.9	299.5	303.5	306.8	312.1	316.7	323.3
57.5°	260.9	258.2	254.3	252.5	254.3	258.2	260.9	265.8	272.1	278.2	285.0
60°	230.2	225.0	218.3	217.7	218.3	225.0	230.2	238.8	241.5	250.7	258.6
62.5°	202.2	201.2	199.9	199.8	199.9	201.2	202.2	205.1	208.8	222.2	231.7
65°	177.5	176.8	177.5	178.1	177.5	176.8	177.5	178.8	179.4	180.8	184.8
67.5°	154.6	153.4	152.3	152.8	152.3	153.4	154.6	154.9	156.8	157.6	160.3
70°	137.2	136.6	136.0	136.0	136.0	136.6	137.2	138.5	139.9	141.2	144.5
72.5°	120.4	120.2	119.6	119.0	119.6	120.2	120.4	122.7	123.6	124.8	127.1
75°	96.3	95.0	95.0	95.0	95.0	95.0	96.3	96.9	97.6	99.6	100.9
77.5°	73.4	72.7	72.1	71.5	72.1	72.7	73.4	73.5	74.6	75.0	76.4
80°	58.0	57.4	56.7	56.7	56.7	57.4	58.0	58.7	58.7	60.7	60.0
82.5°	44.3	43.7	43.6	43.0	43.6	43.7	44.3	44.4	44.4	45.9	45.8
85°	23.8	24.5	23.8	25.1	23.8	24.5	23.8	23.1	23.8	25.1	25.1
87.5°	10.1	9.6	10.1	9.6	10.1	9.6	10.1	10.1	10.5	10.3	10.5
90°	16.2	16.2	16.2	16.2	16.2	16.2	16.2	16.2	15.7	14.7	15.7
92.5°	29.2	27.6	28.0	27.2	28.0	27.6	29.2	29.5	32.6	36.8	42.8
95°	60.9	57.0	55.4	56.0	55.4	57.0	60.9	67.2	78.1	98.7	128.6
97.5°	133.5	121.5	114.3	110.2	114.3	121.5	133.5	157.0	192.5	245.6	300.2
100°	220.0	198.9	184.6	175.8	184.6	198.9	220.0	260.7	320.1	387.4	448.3
102.5°	375.1	339.1	321.3	309.4	321.3	339.1	375.1	419.4	482.4	531.6	545.4
105°	611.8	581.3	560.3	553.4	560.3	581.3	611.8	642.2	658.5	652.0	596.6
107.5°	721.9	720.2	716.0	706.9	716.0	720.2	721.9	718.1	694.3	643.3	559.6
110°	739.9	749.3	753.7	753.2	753.7	749.3	739.9	718.8	678.6	615.7	527.9



TEST NUMBER: P331743-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	725.8	741.4	749.8	752.4	749.8	741.4	725.8	696.5	650.3	583.2	498.8
115°	688.4	711.0	723.8	728.1	723.8	711.0	688.4	653.6	603.0	538.6	463.0
117.5°	643.9	667.7	681.1	684.8	681.1	667.7	643.9	608.3	560.9	502.5	436.1
120°	614.8	637.8	652.0	656.9	652.0	637.8	614.8	580.4	535.7	483.6	422.8
122.5°	588.4	611.1	623.8	627.9	623.8	611.1	588.4	557.6	517.2	468.0	412.2
125°	555.9	574.5	586.8	590.7	586.8	574.5	555.9	527.4	490.5	447.3	396.7
127.5°	526.8	544.3	554.9	558.1	554.9	544.3	526.8	502.0	468.0	427.3	381.5
130°	509.2	525.9	535.7	539.6	535.7	525.9	509.2	485.1	452.7	414.0	371.7
132.5°	491.1	507.8	516.9	520.4	516.9	507.8	491.1	467.4	437.0	401.4	362.3
135°	462.5	478.7	487.6	489.6	487.6	478.7	462.5	441.4	414.0	381.5	349.1
137.5°	434.6	448.6	456.3	459.3	456.3	448.6	434.6	415.4	391.4	365.8	338.6
140°	415.4	428.2	435.5	438.5	435.5	428.2	415.4	399.7	378.1	355.5	331.9
142.5°	398.9	410.5	417.1	417.7	417.1	410.5	398.9	384.0	365.9	346.5	326.4
145°	376.1	384.4	389.3	390.8	389.3	384.4	376.1	364.4	350.1	334.8	318.7
147.5°	357.5	364.1	367.5	368.3	367.5	364.1	357.5	347.8	337.3	325.5	312.7
150°	345.7	351.5	354.5	355.0	354.5	351.5	345.7	338.3	329.5	319.2	308.3
152.5°	336.2	341.4	343.5	343.6	343.5	341.4	336.2	330.5	322.8	314.1	304.0
155°	324.1	327.5	329.5	328.5	329.5	327.5	324.1	318.7	313.2	305.9	298.1
157.5°	311.9	314.8	315.6	315.6	315.6	314.8	311.9	308.1	303.8	297.6	291.1
160°	304.4	306.9	307.4	307.4	307.4	306.9	304.4	301.0	297.6	292.1	286.7
162.5°	297.7	299.5	299.9	299.5	299.9	299.5	297.7	294.3	291.7	287.1	282.4
165°	286.7	288.7	288.7	288.3	288.7	288.7	286.7	284.8	282.8	279.4	276.0
167.5°	277.4	278.5	278.4	277.8	278.4	278.5	277.4	276.6	274.7	272.4	269.8
170°	271.6	273.0	272.5	271.6	272.5	273.0	271.6	271.0	270.1	268.1	266.7
172.5°	266.8	267.5	267.0	266.4	267.0	267.5	266.8	266.3	265.7	264.2	263.1
175°	260.7	261.2	260.7	259.8	260.7	261.2	260.7	260.7	260.3	259.8	259.2
177.5°	256.9	256.9	256.5	255.7	256.5	256.9	256.9	256.9	256.9	256.5	256.5
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331743-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1826.0	1833.4	1844.5	1850.8	1861.4	1868.3	1872.0	1878.8	1882.5	1895.7	1909.4
5°	1724.1	1734.6	1753.1	1770.2	1788.7	1807.8	1821.7	1837.5	1852.0	1877.1	1903.5
7.5°	1607.1	1621.8	1650.4	1677.7	1709.9	1737.0	1760.8	1787.9	1812.1	1848.0	1885.4
10°	1519.5	1545.2	1582.9	1608.6	1650.8	1677.8	1715.5	1745.2	1778.8	1826.3	1868.5
12.5°	1444.0	1475.1	1505.3	1541.0	1579.0	1624.0	1665.3	1703.5	1743.4	1792.5	1842.1
15°	1307.1	1351.9	1398.8	1435.0	1486.5	1534.0	1582.2	1633.7	1682.5	1741.2	1805.9
17.5°	1130.8	1182.8	1261.5	1323.7	1384.1	1431.8	1491.4	1553.7	1611.2	1682.0	1754.0
20°	1051.0	1089.3	1142.7	1226.6	1317.6	1368.4	1429.1	1497.7	1563.7	1640.9	1718.1
22.5°	987.1	1021.2	1064.1	1129.5	1231.1	1300.3	1363.7	1433.3	1509.8	1588.6	1674.3
25°	896.0	919.7	964.6	1017.4	1087.4	1201.4	1270.7	1340.7	1423.8	1508.3	1605.9
27.5°	827.5	848.9	878.0	928.4	980.4	1062.4	1172.6	1248.9	1331.7	1426.8	1528.1
30°	775.2	800.3	832.7	868.3	925.1	989.0	1099.2	1187.7	1269.5	1367.1	1475.3
32.5°	737.3	757.1	784.6	820.8	868.1	929.4	1017.4	1124.8	1204.5	1307.4	1420.4
35°	674.9	698.1	720.5	754.8	793.1	849.1	915.8	1030.6	1109.7	1211.3	1324.8
37.5°	623.6	637.7	662.5	689.7	730.1	772.0	829.7	932.7	1018.3	1118.1	1234.2
40°	584.5	602.4	620.9	651.2	684.2	724.4	781.2	857.7	956.1	1053.7	1167.2
42.5°	546.6	569.1	588.7	609.0	645.1	685.4	731.6	796.5	896.9	989.3	1099.6
45°	500.8	515.3	535.7	558.2	587.9	622.2	663.1	719.8	816.1	896.0	999.6
47.5°	447.5	468.7	482.1	503.9	532.2	564.9	603.0	652.0	730.0	804.8	900.9
50°	411.0	432.8	451.9	471.7	496.8	528.5	560.2	607.7	670.4	748.9	838.6
52.5°	379.9	399.1	417.7	437.5	462.0	491.0	521.1	562.8	616.5	688.7	775.8
55°	337.2	349.0	368.2	388.0	409.7	437.5	466.5	501.4	547.6	608.3	678.9
57.5°	293.3	307.0	322.3	342.2	364.2	385.5	411.6	443.2	479.7	534.6	595.0
60°	268.5	279.1	291.6	312.1	332.5	351.6	376.8	403.1	437.5	484.9	536.4
62.5°	241.1	251.2	262.6	280.4	300.3	317.9	339.8	367.7	396.8	440.1	485.2
65°	195.3	209.8	221.0	236.9	253.4	271.8	289.0	311.4	337.2	371.4	411.7
67.5°	162.0	169.3	179.7	194.1	211.0	226.9	243.1	260.6	282.9	309.4	341.4
70°	147.1	149.8	151.8	165.6	181.4	197.3	212.5	228.9	248.1	269.8	297.6
72.5°	129.8	132.3	134.8	140.8	153.4	169.3	185.0	197.3	215.3	233.4	255.9
75°	102.9	106.9	108.8	112.2	116.8	127.3	141.9	153.7	164.3	178.1	196.0
77.5°	78.4	80.6	82.7	86.2	89.1	93.9	102.1	112.8	122.7	130.8	143.0
80°	62.0	62.7	65.3	66.6	70.6	73.9	77.8	86.4	96.3	99.6	108.2
82.5°	46.8	47.4	49.5	50.8	52.7	55.4	60.4	62.7	70.4	74.8	80.2
85°	25.7	25.1	27.0	27.0	28.4	29.7	31.0	34.3	36.2	41.6	42.9
87.5°	11.2	11.3	11.7	11.1	10.4	10.9	11.2	11.5	12.4	13.6	15.4
90°	16.2	16.7	16.2	13.3	9.8	7.4	5.9	4.9	4.0	2.0	0.5
92.5°	53.9	63.8	62.9	49.0	33.4	22.3	17.7	14.4	12.1	8.6	6.0
95°	168.4	192.5	170.4	113.4	70.7	48.1	36.3	28.5	24.0	19.1	17.2
97.5°	344.7	328.6	247.5	152.8	93.3	64.9	51.6	42.5	35.8	30.7	28.0
100°	458.6	387.9	267.1	161.1	101.2	75.2	61.4	51.6	43.7	39.3	37.8
102.5°	501.0	389.9	259.7	161.4	108.2	84.1	70.4	60.2	52.3	48.0	46.8
105°	494.5	363.9	245.0	164.0	120.3	97.2	83.4	72.7	65.3	61.9	59.9
107.5°	451.3	336.0	237.7	170.7	132.7	110.3	96.4	85.8	79.0	75.6	74.0
110°	424.2	322.6	236.2	176.2	140.9	119.3	105.0	94.8	88.4	85.4	83.4



TEST NUMBER: P331743-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	405.4	313.9	236.6	182.2	148.8	127.9	113.3	103.4	97.4	94.1	92.1
115°	382.0	304.4	238.7	191.0	161.1	139.9	126.7	116.8	111.0	108.1	105.6
117.5°	367.3	299.8	242.2	200.4	172.4	152.8	139.1	129.7	124.4	121.5	119.5
120°	359.5	297.0	244.5	206.7	180.2	161.1	147.3	137.5	133.0	130.1	128.1
122.5°	352.8	295.5	247.3	212.2	187.7	169.7	155.6	145.8	140.9	138.0	136.4
125°	343.2	292.7	251.4	220.9	198.9	181.2	167.5	157.6	151.7	148.8	147.3
127.5°	334.4	291.0	255.6	229.1	209.3	192.1	178.0	168.5	162.0	157.9	155.9
130°	328.5	290.2	258.7	234.2	215.6	198.4	184.6	174.8	167.9	163.0	161.1
132.5°	323.7	289.8	261.9	239.4	221.0	204.7	190.9	180.7	173.4	168.2	165.7
135°	317.2	289.2	265.6	246.0	228.9	213.1	199.3	188.0	180.7	174.8	172.8
137.5°	312.5	289.1	269.0	251.1	235.1	219.6	206.8	195.6	187.8	181.8	179.5
140°	309.9	288.7	270.5	253.8	238.7	223.9	211.1	200.4	192.5	186.6	184.6
142.5°	307.1	288.7	271.7	256.2	241.4	227.0	215.1	204.7	196.8	191.3	189.8
145°	303.4	287.7	273.0	259.2	245.5	232.2	221.4	211.6	204.2	199.3	197.4
147.5°	299.7	285.9	273.4	261.0	248.8	236.3	226.8	218.6	211.8	207.1	205.6
150°	296.6	284.8	273.0	261.7	250.4	239.1	230.3	222.9	216.5	212.6	211.1
152.5°	293.9	282.8	272.2	262.1	252.0	241.9	233.8	226.9	221.3	217.3	216.6
155°	288.7	279.4	271.0	262.7	254.3	246.0	238.7	233.2	227.8	224.9	224.4
157.5°	283.9	275.9	268.8	262.7	256.0	248.9	242.8	238.4	233.8	231.4	230.8
160°	280.3	273.5	267.6	262.7	256.8	250.9	245.5	241.6	237.6	235.7	235.2
162.5°	277.2	271.6	266.4	262.3	257.2	252.1	247.9	244.4	241.2	239.2	239.5
165°	272.0	267.6	264.2	261.2	257.8	253.4	250.4	248.0	245.0	244.0	244.5
167.5°	266.9	264.2	261.9	260.5	257.7	254.4	252.6	250.8	248.9	248.1	248.7
170°	264.2	262.2	260.7	259.8	257.3	254.9	253.4	252.4	250.9	250.4	251.4
172.5°	261.4	259.8	259.2	258.6	256.9	255.2	254.2	253.6	252.1	252.4	253.0
175°	257.8	257.3	256.8	257.3	256.3	255.3	254.9	254.9	253.8	254.3	254.9
177.5°	255.7	255.3	255.7	256.5	255.7	255.3	255.3	255.3	254.5	254.9	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331743-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1910.0	1911.5	1922.1	1926.8	1936.4	1940.0	1944.3	1943.2	1943.2	1945.3	1960.1
5°	1914.1	1927.3	1947.1	1966.2	1984.7	2000.4	2011.0	2021.6	2025.6	2044.7	2061.8
7.5°	1907.2	1931.5	1964.2	1993.4	2028.3	2055.6	2078.4	2098.8	2112.8	2140.6	2169.1
10°	1898.2	1932.5	1969.5	2007.1	2055.2	2091.5	2128.5	2156.9	2166.1	2207.7	2231.5
12.5°	1880.3	1926.2	1973.2	2021.9	2069.0	2119.0	2159.6	2188.0	2220.4	2257.8	2301.6
15°	1853.4	1906.2	1967.5	2030.2	2097.5	2158.2	2201.7	2251.2	2286.8	2327.7	2366.0
17.5°	1814.7	1882.7	1960.7	2033.3	2111.1	2176.3	2236.2	2283.6	2308.8	2332.1	2337.8
20°	1784.1	1857.3	1949.0	2034.8	2112.6	2187.9	2247.2	2286.8	2293.4	2294.0	2259.1
22.5°	1750.8	1833.6	1929.5	2017.4	2110.6	2194.2	2240.4	2257.3	2231.1	2186.4	2118.7
25°	1689.7	1785.4	1896.9	1997.2	2098.8	2178.0	2193.8	2164.1	2072.4	1976.1	1854.0
27.5°	1623.5	1731.0	1850.5	1962.0	2070.3	2119.4	2085.2	1978.1	1813.0	1669.4	1495.4
30°	1574.9	1695.7	1813.1	1937.8	2038.1	2059.2	1980.7	1823.0	1630.3	1413.9	1240.4
32.5°	1519.5	1646.1	1775.1	1904.0	1988.0	1967.4	1837.6	1643.6	1417.6	1204.9	1040.9
35°	1440.3	1571.0	1710.2	1839.5	1892.9	1803.9	1609.9	1357.2	1126.3	927.6	814.9
37.5°	1348.8	1491.2	1635.9	1754.6	1750.8	1602.4	1338.2	1077.3	883.2	765.8	685.4
40°	1283.9	1427.8	1584.2	1684.5	1641.6	1448.2	1161.9	915.8	774.0	680.3	621.6
42.5°	1221.7	1366.1	1521.4	1601.0	1526.5	1288.8	1003.6	810.7	693.7	620.6	573.0
45°	1115.7	1268.1	1412.0	1456.1	1322.8	1060.9	811.6	671.7	593.8	539.7	506.7
47.5°	1012.1	1162.0	1293.3	1294.1	1113.9	860.4	684.6	581.3	514.8	472.9	448.9
50°	948.7	1091.3	1201.4	1184.3	979.8	765.3	612.3	523.2	467.8	435.5	410.4
52.5°	877.5	1015.8	1111.2	1062.4	866.3	673.5	547.3	472.5	426.6	398.5	376.1
55°	774.0	896.6	964.0	890.0	706.6	560.2	462.5	403.8	369.5	345.7	326.6
57.5°	672.2	773.4	815.8	729.7	582.0	464.5	391.2	347.2	313.1	296.1	286.2
60°	608.3	694.7	724.4	629.5	506.1	406.4	346.4	305.5	280.4	269.2	259.3
62.5°	545.5	616.1	628.4	541.3	441.2	355.8	304.2	269.6	253.0	242.3	232.9
65°	452.6	503.4	497.5	427.6	349.0	282.4	244.8	223.7	211.1	196.0	179.4
67.5°	372.6	403.6	385.0	332.5	266.4	219.5	194.9	178.9	163.3	149.0	145.2
70°	322.0	339.8	320.0	271.8	218.3	184.1	164.3	145.2	136.0	132.6	126.7
72.5°	273.5	279.7	258.2	217.0	177.7	152.4	133.1	122.4	117.4	114.7	110.8
75°	205.2	200.6	182.1	149.8	123.4	106.2	100.3	96.3	93.0	90.4	88.4
77.5°	144.1	137.3	120.9	99.8	85.9	77.7	74.1	72.1	70.4	69.1	67.2
80°	108.2	103.6	87.1	71.3	65.3	61.4	59.4	56.7	56.7	55.4	53.5
82.5°	79.2	74.0	59.7	52.3	49.0	46.6	45.1	43.6	43.0	43.3	41.8
85°	41.6	33.7	29.7	28.4	26.4	25.1	25.7	24.5	24.5	24.5	23.8
87.5°	13.1	10.8	10.5	10.2	10.9	11.5	11.6	12.2	12.8	12.2	12.7
90°	2.0	4.0	4.9	5.9	7.4	9.8	13.3	16.2	16.7	16.2	15.7
92.5°	8.6	12.1	14.4	17.7	22.3	33.4	49.0	62.9	63.8	53.9	42.8
95°	19.1	24.0	28.5	36.3	48.1	70.7	113.4	170.4	192.5	168.4	128.6
97.5°	30.7	35.8	42.5	51.6	64.9	93.3	152.8	247.5	328.6	344.7	300.2
100°	39.3	43.7	51.6	61.4	75.2	101.2	161.1	267.1	387.9	458.6	448.3
102.5°	48.0	52.3	60.2	70.4	84.1	108.2	161.4	259.7	389.9	501.0	545.4
105°	61.9	65.3	72.7	83.4	97.2	120.3	164.0	245.0	363.9	494.5	596.6
107.5°	75.6	79.0	85.8	96.4	110.3	132.7	170.7	237.7	336.0	451.3	559.6
110°	85.4	88.4	94.8	105.0	119.3	140.9	176.2	236.2	322.6	424.2	527.9



TEST NUMBER: P331743-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	94.1	97.4	103.4	113.3	127.9	148.8	182.2	236.6	313.9	405.4	498.8
115°	108.1	111.0	116.8	126.7	139.9	161.1	191.0	238.7	304.4	382.0	463.0
117.5°	121.5	124.4	129.7	139.1	152.8	172.4	200.4	242.2	299.8	367.3	436.1
120°	130.1	133.0	137.5	147.3	161.1	180.2	206.7	244.5	297.0	359.5	422.8
122.5°	138.0	140.9	145.8	155.6	169.7	187.7	212.2	247.3	295.5	352.8	412.2
125°	148.8	151.7	157.6	167.5	181.2	198.9	220.9	251.4	292.7	343.2	396.7
127.5°	157.9	162.0	168.5	178.0	192.1	209.3	229.1	255.6	291.0	334.4	381.5
130°	163.0	167.9	174.8	184.6	198.4	215.6	234.2	258.7	290.2	328.5	371.7
132.5°	168.2	173.4	180.7	190.9	204.7	221.0	239.4	261.9	289.8	323.7	362.3
135°	174.8	180.7	188.0	199.3	213.1	228.9	246.0	265.6	289.2	317.2	349.1
137.5°	181.8	187.8	195.6	206.8	219.6	235.1	251.1	269.0	289.1	312.5	338.6
140°	186.6	192.5	200.4	211.1	223.9	238.7	253.8	270.5	288.7	309.9	331.9
142.5°	191.3	196.8	204.7	215.1	227.0	241.4	256.2	271.7	288.7	307.1	326.4
145°	199.3	204.2	211.6	221.4	232.2	245.5	259.2	273.0	287.7	303.4	318.7
147.5°	207.1	211.8	218.6	226.8	236.3	248.8	261.0	273.4	285.9	299.7	312.7
150°	212.6	216.5	222.9	230.3	239.1	250.4	261.7	273.0	284.8	296.6	308.3
152.5°	217.3	221.3	226.9	233.8	241.9	252.0	262.1	272.2	282.8	293.9	304.0
155°	224.9	227.8	233.2	238.7	246.0	254.3	262.7	271.0	279.4	288.7	298.1
157.5°	231.4	233.8	238.4	242.8	248.9	256.0	262.7	268.8	275.9	283.9	291.1
160°	235.7	237.6	241.6	245.5	250.9	256.8	262.7	267.6	273.5	280.3	286.7
162.5°	239.2	241.2	244.4	247.9	252.1	257.2	262.3	266.4	271.6	277.2	282.4
165°	244.0	245.0	248.0	250.4	253.4	257.8	261.2	264.2	267.6	272.0	276.0
167.5°	248.1	248.9	250.8	252.6	254.4	257.7	260.5	261.9	264.2	266.9	269.8
170°	250.4	250.9	252.4	253.4	254.9	257.3	259.8	260.7	262.2	264.2	266.7
172.5°	252.4	252.1	253.6	254.2	255.2	256.9	258.6	259.2	259.8	261.4	263.1
175°	254.3	253.8	254.9	254.9	255.3	256.3	257.3	256.8	257.3	257.8	259.2
177.5°	254.9	254.5	255.3	255.3	255.3	255.7	256.5	255.7	255.3	255.7	256.5
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331743-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1965.4	1972.2	1975.4	1975.4	1979.1	1977.5	1975.9
5°	2078.4	2090.9	2093.5	2105.4	2113.9	2111.3	2112.6
7.5°	2190.6	2210.8	2230.8	2239.9	2241.3	2246.6	2248.6
10°	2259.8	2276.3	2307.3	2302.7	2325.7	2339.0	2317.2
12.5°	2326.2	2348.5	2370.1	2376.0	2389.1	2393.3	2384.7
15°	2386.4	2398.3	2399.7	2396.3	2400.3	2397.0	2384.5
17.5°	2330.2	2311.0	2271.9	2253.4	2238.8	2217.2	2208.5
20°	2237.3	2180.6	2114.6	2088.3	2057.2	1996.5	2011.0
22.5°	2036.8	1972.1	1906.2	1829.1	1792.3	1734.7	1731.3
25°	1724.7	1613.2	1490.5	1404.7	1354.5	1297.2	1272.0
27.5°	1340.9	1200.6	1100.0	1049.0	1002.7	957.3	955.4
30°	1088.6	983.1	905.3	861.7	833.3	814.2	818.1
32.5°	917.7	845.3	792.8	756.6	735.6	721.3	721.0
35°	750.2	700.7	667.0	651.9	636.7	626.1	626.8
37.5°	642.0	612.3	593.6	576.8	567.3	562.1	559.2
40°	586.5	562.1	547.6	537.7	529.8	522.5	521.2
42.5°	542.8	522.5	508.1	500.2	492.8	487.8	486.4
45°	481.6	465.1	451.9	443.4	440.1	435.5	435.5
47.5°	428.4	412.2	401.9	396.6	390.9	387.8	387.7
50°	392.6	380.0	370.8	367.5	362.9	360.9	360.2
52.5°	360.4	351.0	344.4	342.2	340.2	337.7	338.1
55°	316.7	311.4	308.8	306.8	303.5	299.5	302.2
57.5°	279.9	275.4	268.3	262.1	259.1	256.2	257.4
60°	254.0	244.8	235.6	228.3	226.3	220.3	220.3
62.5°	221.3	208.4	197.0	193.0	191.0	188.2	187.6
65°	170.2	165.0	162.3	159.6	158.3	158.3	157.0
67.5°	141.0	139.0	136.0	135.3	134.1	133.7	133.3
70°	124.7	122.1	120.7	120.1	118.7	119.4	117.4
72.5°	108.8	106.8	106.5	104.8	104.0	104.1	102.6
75°	85.8	85.8	85.2	84.5	83.2	82.5	83.2
77.5°	66.0	66.1	64.9	64.8	64.7	64.8	64.1
80°	52.8	53.5	52.8	52.1	51.5	52.1	51.5
82.5°	41.7	40.8	40.6	40.6	40.4	40.0	39.9
85°	23.8	24.5	23.8	23.1	23.1	23.1	23.8
87.5°	11.9	12.1	12.2	12.2	12.2	12.2	11.7
90°	14.7	15.7	16.2	16.2	16.2	16.2	16.2
92.5°	36.8	32.6	29.5	29.2	27.6	28.0	27.2
95°	98.7	78.1	67.2	60.9	57.0	55.4	56.0
97.5°	245.6	192.5	157.0	133.5	121.5	114.3	110.2
100°	387.4	320.1	260.7	220.0	198.9	184.6	175.8
102.5°	531.6	482.4	419.4	375.1	339.1	321.3	309.4
105°	652.0	658.5	642.2	611.8	581.3	560.3	553.4
107.5°	643.3	694.3	718.1	721.9	720.2	716.0	706.9
110°	615.7	678.6	718.8	739.9	749.3	753.7	753.2



TEST NUMBER: P331743-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	583.2	650.3	696.5	725.8	741.4	749.8	752.4
115°	538.6	603.0	653.6	688.4	711.0	723.8	728.1
117.5°	502.5	560.9	608.3	643.9	667.7	681.1	684.8
120°	483.6	535.7	580.4	614.8	637.8	652.0	656.9
122.5°	468.0	517.2	557.6	588.4	611.1	623.8	627.9
125°	447.3	490.5	527.4	555.9	574.5	586.8	590.7
127.5°	427.3	468.0	502.0	526.8	544.3	554.9	558.1
130°	414.0	452.7	485.1	509.2	525.9	535.7	539.6
132.5°	401.4	437.0	467.4	491.1	507.8	516.9	520.4
135°	381.5	414.0	441.4	462.5	478.7	487.6	489.6
137.5°	365.8	391.4	415.4	434.6	448.6	456.3	459.3
140°	355.5	378.1	399.7	415.4	428.2	435.5	438.5
142.5°	346.5	365.9	384.0	398.9	410.5	417.1	417.7
145°	334.8	350.1	364.4	376.1	384.4	389.3	390.8
147.5°	325.5	337.3	347.8	357.5	364.1	367.5	368.3
150°	319.2	329.5	338.3	345.7	351.5	354.5	355.0
152.5°	314.1	322.8	330.5	336.2	341.4	343.5	343.6
155°	305.9	313.2	318.7	324.1	327.5	329.5	328.5
157.5°	297.6	303.8	308.1	311.9	314.8	315.6	315.6
160°	292.1	297.6	301.0	304.4	306.9	307.4	307.4
162.5°	287.1	291.7	294.3	297.7	299.5	299.9	299.5
165°	279.4	282.8	284.8	286.7	288.7	288.7	288.3
167.5°	272.4	274.7	276.6	277.4	278.5	278.4	277.8
170°	268.1	270.1	271.0	271.6	273.0	272.5	271.6
172.5°	264.2	265.7	266.3	266.8	267.5	267.0	266.4
175°	259.8	260.3	260.7	260.7	261.2	260.7	259.8
177.5°	256.5	256.9	256.9	256.9	256.9	256.5	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3

(END OF REPORT)