

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331642-935

Luminaire Tested: **SA2XXRDIP-C290D1080U935-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331642-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D1080U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4598.9 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331642-935
CATALOG NUMBER: SA2XXRDIP-C290D1080U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331642-935

CATALOG NUMBER: SA2XXRDIP-C290D1080U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	19				
1	91	87	83	80	80	77	74	71	58	56	54	41	40	39	25	24	24	17				
2	83	76	70	66	73	67	63	59	51	48	45	36	34	33	22	21	20	14				
3	76	67	60	55	67	59	54	49	45	41	38	32	30	28	20	19	18	12				
4	69	59	52	46	61	53	46	42	40	36	33	29	26	24	18	16	15	11				
5	64	53	45	39	56	47	40	36	36	31	28	26	23	21	16	15	13	9				
6	58	47	40	34	51	42	36	31	32	28	24	23	20	18	15	13	12	8				
7	54	42	35	30	47	38	31	27	29	25	21	21	18	16	13	12	10	7				
8	50	38	31	26	44	34	28	24	26	22	19	19	16	14	12	11	9	7				
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	11	10	9	6				
10	43	32	25	21	38	28	23	19	22	18	15	16	13	11	10	9	8	6				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6978	6978	6978
5°	7005	6891	6929
10°	6951	6779	6720
15°	6870	6578	6387
20°	6761	6290	5976
25°	6649	5964	5574
30°	6490	5630	5062
35°	6337	5267	4610
40°	6182	4890	4089
45°	6003	4464	3617
50°	5815	4037	3152
55°	5624	3578	2711
60°	5406	3094	2251
65°	5154	2598	2048
70°	4858	2143	1884
75°	4492	1953	1759
80°	3961	1748	1599
85°	3112	1371	1371



TEST NUMBER: P331642-935

CATALOG NUMBER: SA2XXRDIP-C290D1080U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.5	0.9
10°-20°	111.1	2.4
20°-30°	156.0	3.4
30°-40°	170.1	3.7
40°-50°	156.4	3.4
50°-60°	122.8	2.7
60°-70°	80.1	1.7
70°-80°	41.3	0.9
80°-90°	13.8	0.3
90°-100°	42.2	0.9
100°-110°	154.7	3.4
110°-120°	413.6	9.0
120°-130°	682.8	14.8
130°-140°	726.1	15.8
140°-150°	674.9	14.7
150°-160°	542.6	11.8
160°-170°	349.7	7.6
170°-180°	120.4	2.6
0°-30°	307.5	6.7
0°-40°	477.6	10.4
0°-60°	756.8	16.5
0°-90°	892.0	19.4
90°-120°	610.5	13.3
90°-150°	2694.3	58.6
90°-180°	3707.0	80.6
0°-180°	4598.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	432	432	432	432	432	
5°	432	430	425	428	428	41
15°	411	406	394	386	382	116
25°	373	360	335	319	313	172
35°	322	301	267	243	234	201
45°	263	236	196	169	158	203
55°	200	169	127	104	96	179
65°	135	103	68	55	54	134
75°	72	45	31	29	28	76
85°	17	9	7	7	7	20
90°	1	11	18	23	25	3
95°	60	31	36	40	39	73
105°	278	290	56	66	70	297
115°	526	542	565	161	75	518
125°	744	756	773	780	783	663
135°	921	935	944	952	951	711
145°	1068	1068	1083	1089	1085	668
155°	1176	1169	1179	1184	1177	542
165°	1239	1234	1237	1242	1237	350
175°	1268	1262	1263	1269	1260	121
180°	1265	1265	1265	1265	1265	



TEST NUMBER: P331642-935

CATALOG NUMBER: SA2XXRDIP-C290D1080U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2
2.5°	433.8	433.4	433.1	432.7	432.4	431.8	431.0	430.3	429.6	428.8	429.5
5°	432.2	431.8	431.4	430.9	430.5	429.6	428.5	427.4	426.3	425.2	425.9
7.5°	427.7	427.2	426.6	426.1	425.6	424.6	423.4	422.0	420.7	419.4	419.6
10°	424.0	423.4	422.8	422.1	421.5	420.3	418.6	416.9	415.2	413.5	413.2
12.5°	419.3	418.5	417.8	417.1	416.3	414.8	412.6	410.4	408.1	405.9	405.4
15°	411.0	410.1	409.1	408.2	407.3	405.3	402.3	399.4	396.4	393.5	391.8
17.5°	401.0	399.5	398.0	396.6	395.1	392.5	388.7	385.0	381.2	377.4	375.4
20°	393.5	391.8	390.0	388.2	386.5	383.5	379.1	374.8	370.5	366.1	363.9
22.5°	385.4	383.4	381.4	379.5	377.5	374.1	369.2	364.3	359.5	354.6	351.7
25°	373.2	370.3	367.6	364.8	362.1	357.7	352.0	346.3	340.5	334.8	331.2
27.5°	358.4	355.4	352.4	349.4	346.3	341.6	335.1	328.6	322.2	315.7	311.6
30°	348.1	344.8	341.5	338.2	334.9	329.8	322.8	315.9	308.9	302.0	297.6
32.5°	338.1	334.2	330.4	326.5	322.6	317.2	310.1	303.0	295.9	288.8	283.8
35°	321.5	317.1	312.6	308.2	303.8	297.7	290.1	282.4	274.8	267.2	261.7
37.5°	305.0	300.1	295.2	290.3	285.4	279.0	270.8	262.6	254.5	246.3	240.3
40°	293.3	288.2	282.9	277.7	272.5	265.7	257.3	248.8	240.4	232.0	225.8
42.5°	281.5	276.0	270.4	265.0	259.5	252.4	243.7	235.0	226.3	217.6	211.2
45°	262.9	257.0	251.2	245.4	239.5	232.0	222.9	213.8	204.7	195.5	189.4
47.5°	244.7	238.5	232.4	226.2	220.0	212.2	202.8	193.4	183.9	174.5	168.4
50°	231.5	225.4	219.2	213.0	206.9	199.0	189.4	179.9	170.3	160.7	154.7
52.5°	218.7	212.2	205.9	199.4	193.0	185.0	175.6	166.3	157.0	147.6	141.8
55°	199.8	193.1	186.3	179.5	172.7	164.7	155.2	145.9	136.5	127.1	121.9
57.5°	180.6	173.6	166.6	159.7	152.7	144.7	135.7	126.7	117.7	108.7	103.8
60°	167.4	160.5	153.5	146.5	139.6	131.6	122.7	113.7	104.8	95.8	91.4
62.5°	154.5	147.7	140.7	133.7	126.7	119.0	110.5	101.9	93.4	84.9	80.7
65°	134.9	127.9	120.9	113.8	106.8	99.4	91.5	83.7	75.9	68.0	65.1
67.5°	116.0	109.0	102.0	95.1	88.1	81.0	74.0	67.0	59.9	52.9	51.5
70°	102.9	96.1	89.3	82.6	75.8	69.4	63.4	57.3	51.4	45.4	44.5
72.5°	90.3	83.9	77.3	70.9	64.3	58.7	53.9	49.1	44.3	39.4	38.7
75°	72.0	65.9	59.8	53.7	47.6	43.1	40.1	37.2	34.3	31.3	30.7
77.5°	53.9	48.6	43.2	37.9	32.5	29.2	27.7	26.3	24.9	23.5	23.2
80°	42.6	38.2	33.8	29.4	24.9	22.2	21.4	20.5	19.6	18.8	18.4
82.5°	32.3	28.8	25.4	22.0	18.5	16.4	15.8	15.2	14.6	14.1	13.9
85°	16.8	15.0	13.2	11.4	9.6	8.4	8.2	7.9	7.7	7.4	7.4
87.5°	5.2	5.1	5.0	4.8	4.7	4.8	5.2	5.5	5.9	6.2	6.3
90°	0.9	3.2	5.4	7.7	9.9	11.8	13.4	15.1	16.7	18.3	19.3
92.5°	18.5	18.3	18.1	17.9	17.7	18.0	18.8	19.6	20.4	21.3	21.8
95°	59.5	52.8	46.1	39.3	32.6	30.0	31.4	32.9	34.3	35.7	36.7
97.5°	118.0	99.2	80.2	61.3	42.4	34.6	37.9	41.2	44.5	47.8	48.6
100°	162.0	134.1	106.2	78.4	50.5	38.3	41.8	45.3	48.7	52.2	53.8
102.5°	210.3	204.4	198.5	192.6	186.8	169.4	140.4	111.5	82.6	53.6	55.8
105°	278.3	284.4	290.4	296.5	302.6	277.9	222.4	166.9	111.3	55.8	58.0
107.5°	355.7	360.6	365.5	370.4	375.4	344.6	277.9	211.4	144.7	78.2	75.9
110°	405.4	409.7	414.1	418.3	422.6	395.3	336.5	277.8	219.0	160.1	139.8



TEST NUMBER: P331642-935

CATALOG NUMBER: SA2XXRDIP-C290D1080U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	452.4	456.2	459.9	463.6	467.4	462.1	447.5	433.1	418.5	404.0	329.8
115°	526.3	529.8	533.2	536.7	540.1	544.4	549.5	554.6	559.6	564.7	470.5
117.5°	592.4	596.2	600.1	604.0	607.9	611.5	615.0	618.5	622.0	625.5	602.7
120°	640.7	643.8	646.8	649.9	652.9	656.3	660.0	663.6	667.3	670.9	673.3
122.5°	681.7	684.9	688.1	691.4	694.6	698.2	702.1	706.1	710.2	714.1	715.6
125°	744.2	746.7	749.4	752.1	754.7	757.9	761.8	765.7	769.6	773.4	774.8
127.5°	800.7	803.7	806.6	809.5	812.4	815.3	818.2	821.0	824.0	826.9	829.0
130°	836.5	839.8	843.1	846.4	849.5	852.3	854.5	856.8	859.0	861.3	863.5
132.5°	873.1	876.0	878.7	881.5	884.2	886.7	889.0	891.2	893.5	895.7	897.6
135°	920.8	924.0	927.3	930.6	933.8	936.3	938.1	940.0	941.8	943.7	945.7
137.5°	968.9	971.2	973.4	975.8	978.0	980.2	982.3	984.4	986.4	988.5	990.5
140°	1000.4	1002.0	1003.7	1005.3	1006.9	1008.8	1011.1	1013.3	1015.5	1017.8	1019.6
142.5°	1026.7	1028.2	1029.7	1031.1	1032.6	1034.7	1037.2	1039.7	1042.3	1044.9	1046.5
145°	1068.2	1067.9	1067.7	1067.6	1067.3	1068.9	1072.4	1075.8	1079.3	1082.8	1084.2
147.5°	1104.2	1103.5	1102.7	1101.9	1101.1	1102.4	1105.9	1109.2	1112.7	1116.1	1117.1
150°	1127.7	1126.2	1124.8	1123.3	1122.0	1122.8	1126.1	1129.4	1132.6	1135.8	1137.1
152.5°	1147.4	1145.8	1144.2	1142.6	1141.1	1141.8	1144.9	1148.0	1151.1	1154.2	1155.4
155°	1176.1	1174.3	1172.5	1170.6	1168.8	1169.2	1171.6	1174.0	1176.5	1178.9	1180.1
157.5°	1198.7	1197.1	1195.6	1194.0	1192.5	1192.6	1194.3	1195.9	1197.7	1199.4	1200.8
160°	1211.9	1210.7	1209.4	1208.2	1206.9	1206.9	1208.2	1209.4	1210.7	1211.9	1213.1
162.5°	1223.6	1222.4	1221.1	1219.9	1218.7	1218.6	1219.6	1220.7	1221.8	1222.8	1224.2
165°	1239.3	1238.0	1236.8	1235.6	1234.4	1234.1	1234.7	1235.4	1236.0	1236.6	1237.9
167.5°	1251.0	1249.8	1248.5	1247.3	1246.1	1245.8	1246.4	1246.9	1247.5	1248.1	1249.5
170°	1257.6	1256.4	1255.2	1254.0	1252.8	1252.3	1252.8	1253.1	1253.5	1254.0	1255.3
172.5°	1262.0	1260.8	1259.6	1258.4	1257.1	1256.7	1257.1	1257.5	1257.9	1258.4	1259.7
175°	1267.7	1266.3	1264.8	1263.4	1262.0	1261.5	1261.9	1262.3	1262.7	1263.1	1264.6
177.5°	1268.6	1267.5	1266.3	1265.2	1264.0	1263.5	1263.7	1263.9	1264.0	1264.2	1265.3
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331642-935

CATALOG NUMBER: SA2XXRDIP-C290D1080U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2
2.5°	430.2	430.8	431.5	431.8	431.7	431.5	431.4	431.3
5°	426.7	427.5	428.3	428.5	428.3	428.0	427.7	427.5
7.5°	419.8	420.1	420.3	420.2	419.7	419.2	418.8	418.4
10°	412.9	412.7	412.4	412.0	411.5	411.0	410.4	409.9
12.5°	405.0	404.5	404.1	403.4	402.5	401.7	400.8	399.9
15°	390.2	388.5	386.8	385.6	384.8	383.8	383.0	382.1
17.5°	373.4	371.4	369.5	367.8	366.3	364.8	363.3	361.8
20°	361.8	359.6	357.4	355.3	353.4	351.5	349.7	347.8
22.5°	349.0	346.1	343.4	341.2	339.8	338.4	336.9	335.5
25°	327.7	324.1	320.6	318.1	316.8	315.5	314.2	312.9
27.5°	307.4	303.2	299.1	296.0	293.9	291.9	289.8	287.7
30°	293.1	288.7	284.2	280.9	278.4	276.1	273.8	271.5
32.5°	278.7	273.6	268.5	264.9	262.8	260.5	258.3	256.1
35°	256.2	250.7	245.2	241.5	239.6	237.7	235.8	233.9
37.5°	234.3	228.3	222.2	218.1	215.9	213.7	211.5	209.3
40°	219.6	213.4	207.2	203.0	200.8	198.5	196.2	194.0
42.5°	204.7	198.4	192.0	187.8	185.5	183.4	181.2	179.0
45°	183.2	177.0	170.9	166.8	164.7	162.6	160.5	158.4
47.5°	162.2	156.1	150.0	145.9	144.0	142.2	140.3	138.4
50°	148.8	142.8	136.7	132.9	131.0	129.2	127.3	125.5
52.5°	136.0	130.3	124.5	120.7	119.1	117.4	115.6	114.0
55°	116.7	111.5	106.2	102.8	101.2	99.5	97.9	96.3
57.5°	99.1	94.3	89.5	86.4	85.1	83.7	82.3	80.8
60°	87.0	82.6	78.1	75.2	73.8	72.4	71.0	69.7
62.5°	76.5	72.2	68.0	65.4	64.6	63.8	62.9	62.1
65°	62.2	59.2	56.2	54.6	54.3	54.1	53.8	53.6
67.5°	50.2	48.8	47.4	46.7	46.3	46.1	45.8	45.5
70°	43.7	42.8	41.9	41.3	40.9	40.6	40.2	39.9
72.5°	38.0	37.2	36.5	36.1	35.8	35.6	35.4	35.2
75°	30.0	29.4	28.8	28.5	28.4	28.3	28.2	28.2
77.5°	22.7	22.4	22.0	21.9	21.7	21.5	21.4	21.3
80°	18.1	17.7	17.4	17.2	17.2	17.2	17.2	17.2
82.5°	13.7	13.4	13.3	13.2	13.2	13.2	13.2	13.2
85°	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
87.5°	6.5	6.5	6.7	6.8	6.9	7.0	7.1	7.1
90°	20.3	21.4	22.4	23.1	23.5	23.9	24.3	24.7
92.5°	22.3	22.8	23.3	23.8	24.0	24.2	24.5	24.7
95°	37.7	38.7	39.8	40.2	40.0	39.8	39.5	39.3
97.5°	49.4	50.2	51.1	51.6	51.8	52.1	52.3	52.5
100°	55.4	57.1	58.7	59.7	60.1	60.5	61.0	61.3
102.5°	57.9	60.0	62.1	63.5	64.0	64.6	65.2	65.7
105°	60.3	62.5	64.7	66.3	67.2	67.9	68.7	69.6
107.5°	73.6	71.3	69.1	68.4	69.1	69.9	70.8	71.5
110°	119.5	99.2	78.8	69.1	69.8	70.7	71.5	72.3



TEST NUMBER: P331642-935

CATALOG NUMBER: SA2XXRDIP-C290D1080U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	255.6	181.4	107.2	70.4	71.1	71.7	72.4	73.0
115°	376.3	282.2	188.0	133.6	119.0	104.4	89.7	75.1
117.5°	580.0	557.2	534.4	498.9	450.8	402.7	354.6	306.4
120°	675.8	678.2	680.7	668.1	640.7	613.2	585.7	558.4
122.5°	717.0	718.5	720.0	718.0	712.7	707.4	702.1	696.7
125°	776.3	777.7	779.1	780.2	780.8	781.4	782.0	782.6
127.5°	831.0	833.1	835.2	836.3	836.4	836.5	836.6	836.7
130°	865.7	868.0	870.2	871.2	871.1	870.8	870.6	870.5
132.5°	899.5	901.5	903.4	904.2	904.0	903.8	903.6	903.4
135°	947.7	949.8	951.7	952.6	952.2	951.7	951.4	951.0
137.5°	992.5	994.5	996.4	997.1	996.4	995.7	995.1	994.4
140°	1021.5	1023.3	1025.1	1025.5	1024.5	1023.5	1022.4	1021.5
142.5°	1048.2	1049.9	1051.5	1051.9	1050.9	1049.8	1048.9	1047.8
145°	1085.6	1087.0	1088.5	1088.6	1087.7	1086.7	1085.6	1084.6
147.5°	1118.2	1119.3	1120.3	1120.4	1119.6	1118.7	1117.8	1117.0
150°	1138.3	1139.5	1140.7	1140.8	1139.8	1138.8	1137.8	1136.8
152.5°	1156.6	1157.9	1159.1	1159.0	1157.6	1156.3	1154.9	1153.7
155°	1181.3	1182.6	1183.8	1183.5	1181.9	1180.3	1178.7	1177.1
157.5°	1202.1	1203.5	1204.9	1204.8	1203.2	1201.6	1200.1	1198.4
160°	1214.3	1215.5	1216.7	1216.6	1215.2	1213.8	1212.4	1210.9
162.5°	1225.5	1226.9	1228.4	1228.1	1226.4	1224.7	1222.9	1221.2
165°	1239.4	1240.8	1242.3	1242.3	1240.8	1239.4	1237.9	1236.6
167.5°	1250.9	1252.3	1253.8	1253.5	1251.7	1249.9	1248.1	1246.2
170°	1256.8	1258.2	1259.6	1259.4	1257.6	1255.8	1254.0	1252.1
172.5°	1261.2	1262.6	1264.0	1263.9	1262.0	1260.2	1258.4	1256.5
175°	1265.9	1267.4	1268.8	1268.5	1266.4	1264.4	1262.4	1260.3
177.5°	1266.4	1267.6	1268.8	1268.6	1267.1	1265.7	1264.2	1262.7
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9

(END OF REPORT)