

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331627-935

Luminaire Tested: **SA2XXRDIP-C290D725U935-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331627-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3469.3 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331627-935
CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331627-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28																			
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	32	32	31	24																			
2	85	78	73	68	76	70	66	62	56	52	50	42	40	38	29	28	27	21																			
3	78	69	63	57	70	62	57	52	49	45	42	37	35	33	26	25	23	19																			
4	72	62	54	49	64	56	49	44	44	40	36	34	31	28	24	22	21	16																			
5	66	55	47	42	59	50	43	38	40	35	32	30	27	25	22	20	18	15																			
6	61	49	42	36	54	45	38	33	36	31	28	28	24	22	20	18	16	13																			
7	56	45	37	32	50	40	34	29	33	28	24	25	22	20	18	16	15	12																			
8	52	41	33	28	47	37	31	26	30	25	22	23	20	18	17	15	13	11																			
9	48	37	30	25	44	34	28	23	27	23	20	21	18	16	16	14	12	10																			
10	45	34	27	23	41	31	25	21	25	21	18	20	17	14	15	13	11	9																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9087	9087	9087	9087
5°	10149	9144	8109	9144
10°	11262	9081	7029	9081
15°	11814	8948	5538	8948
20°	10244	8751	4792	8751
25°	6716	8480	4277	8480
30°	4521	8153	3872	8153
35°	3662	7740	3493	7740
40°	3256	7290	3231	7290
45°	2948	6766	2884	6766
50°	2683	6244	2673	6244
55°	2519	5664	2488	5664
60°	2109	5134	2086	5134
65°	1780	4661	2017	4661
70°	1643	4164	1902	4164
75°	1535	3624	1759	3624
80°	1413	2985	1562	2985
85°	1315	2353	1371	2353



TEST NUMBER: P331627-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.4	1.5
10°-20°	148.7	4.3
20°-30°	191.6	5.5
30°-40°	182.1	5.2
40°-50°	156.0	4.5
50°-60°	118.8	3.4
60°-70°	75.1	2.2
70°-80°	37.5	1.1
80°-90°	11.9	0.3
90°-100°	28.4	0.8
100°-110°	104.1	3.0
110°-120°	278.3	8.0
120°-130°	459.4	13.2
130°-140°	488.6	14.1
140°-150°	454.1	13.1
150°-160°	365.1	10.5
160°-170°	235.3	6.8
170°-180°	81.0	2.3
0°-30°	393.6	11.3
0°-40°	575.7	16.6
0°-60°	850.4	24.5
0°-90°	974.9	28.1
90°-120°	410.8	11.8
90°-150°	1813.0	52.3
90°-180°	2494.0	71.9
0°-180°	3469.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	563	563	563	563	563	
5°	626	564	500	564	626	62
15°	707	535	331	535	707	191
25°	377	476	240	476	377	179
35°	186	393	177	393	186	119
45°	129	296	126	296	129	100
55°	90	201	88	201	90	79
65°	47	122	53	122	47	47
75°	25	58	28	58	25	26
85°	7	13	7	13	7	8
90°	17	1	17	1	17	8
95°	26	40	26	40	26	25
105°	47	187	47	187	47	49
115°	50	354	50	354	50	126
125°	527	501	527	501	527	456
135°	640	620	640	620	640	493
145°	730	719	730	719	730	456
155°	792	791	792	791	792	365
165°	832	834	832	834	832	235
175°	848	853	848	853	848	81
180°	851	851	851	851	851	



TEST NUMBER: P331627-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	585.7	586.2	586.7	585.6	585.6	584.6	582.6	581.0	576.6	576.0	576.0
5°	626.2	625.9	626.6	624.1	620.6	619.7	616.0	611.1	606.1	600.5	599.3
7.5°	666.5	665.9	664.3	663.9	661.2	655.3	649.4	643.0	634.6	626.3	622.2
10°	686.9	693.4	689.4	682.6	683.9	674.8	669.9	661.4	654.4	642.0	639.4
12.5°	706.9	709.5	708.2	704.3	702.6	696.2	689.6	682.3	669.3	658.2	648.6
15°	706.8	710.5	711.5	710.3	711.3	710.9	707.4	701.4	690.0	677.9	667.3
17.5°	654.6	657.2	663.7	668.0	673.5	685.0	690.8	692.9	691.3	684.3	676.9
20°	596.2	591.9	609.8	619.0	626.8	646.4	663.2	669.7	680.0	679.8	677.9
22.5°	513.2	514.2	531.2	542.2	565.0	584.6	603.7	628.0	648.1	661.3	669.1
25°	377.0	384.5	401.5	416.4	441.8	478.2	511.3	549.6	585.7	614.3	641.5
27.5°	283.2	283.8	297.2	311.0	326.1	355.9	397.5	443.2	494.8	537.4	586.3
30°	242.5	241.3	247.0	255.5	268.4	291.4	322.7	367.6	419.1	483.3	540.4
32.5°	213.7	213.8	218.1	224.3	235.0	250.6	272.0	308.6	357.1	420.3	487.2
35°	185.8	185.6	188.7	193.2	197.7	207.7	222.4	241.5	275.0	333.8	402.3
37.5°	165.7	166.6	168.2	171.0	175.9	181.5	190.3	203.2	227.0	261.8	319.3
40°	154.5	154.9	157.0	159.4	162.3	166.6	173.8	184.3	201.6	229.4	271.5
42.5°	144.2	144.6	146.1	148.3	150.6	154.9	160.9	169.9	184.0	205.6	240.3
45°	129.1	129.1	130.4	131.4	134.0	137.8	142.8	150.2	160.0	176.0	199.1
47.5°	114.9	114.9	115.9	117.5	119.2	122.2	127.0	133.1	140.2	152.6	172.3
50°	106.8	107.0	107.5	108.9	109.9	112.6	116.4	121.7	129.1	138.7	155.1
52.5°	100.2	100.1	100.8	101.4	102.1	104.0	106.9	111.5	118.1	126.5	140.1
55°	89.5	88.8	90.0	90.9	91.5	92.3	93.8	96.8	102.5	109.5	119.7
57.5°	76.3	75.9	76.8	77.7	79.6	81.6	83.0	84.8	87.7	92.8	102.9
60°	65.3	65.3	67.1	67.7	69.8	72.6	75.3	76.9	79.8	83.1	90.6
62.5°	55.6	55.8	56.6	57.2	58.4	61.7	65.6	69.1	71.8	75.0	79.9
65°	46.6	46.9	46.9	47.4	48.1	48.9	50.5	53.2	58.1	62.6	66.3
67.5°	39.5	39.6	39.8	40.1	40.3	41.2	41.8	43.0	44.2	48.4	53.0
70°	34.8	35.4	35.2	35.6	35.8	36.2	36.9	37.5	39.3	40.3	43.0
72.5°	30.4	30.8	30.8	31.1	31.6	31.7	32.3	32.9	34.0	34.8	36.3
75°	24.6	24.5	24.6	25.1	25.2	25.4	25.4	26.2	26.8	27.6	28.6
77.5°	19.0	19.2	19.2	19.2	19.3	19.6	19.5	19.9	20.5	20.9	21.4
80°	15.2	15.4	15.2	15.4	15.7	15.8	15.7	15.8	16.4	16.8	16.8
82.5°	11.8	11.9	12.0	12.0	12.1	12.1	12.4	12.4	12.8	12.7	12.9
85°	7.1	6.9	6.9	6.9	7.1	7.2	7.1	7.1	7.2	7.2	7.2
87.5°	5.9	5.9	5.9	5.9	5.8	5.7	5.5	5.6	5.3	5.3	4.9
90°	16.6	16.4	16.1	15.8	15.5	15.1	14.4	13.7	13.0	12.3	11.2
92.5°	16.6	16.4	16.3	16.1	16.0	15.7	15.3	15.0	14.6	14.3	13.8
95°	26.5	26.6	26.8	26.9	27.0	26.8	26.1	25.4	24.7	24.0	23.1
97.5°	35.4	35.2	35.0	34.9	34.7	34.4	33.8	33.2	32.7	32.1	30.0
100°	41.2	41.0	40.7	40.5	40.2	39.5	38.4	37.3	36.2	35.1	32.8
102.5°	44.3	43.8	43.5	43.0	42.7	41.8	40.4	38.9	37.5	36.1	55.5
105°	46.8	46.2	45.7	45.2	44.6	43.6	42.1	40.6	39.1	37.5	74.9
107.5°	48.1	47.6	47.1	46.5	46.0	46.5	48.0	49.5	51.1	52.6	97.4
110°	48.6	48.1	47.5	47.0	46.5	53.0	66.7	80.4	94.1	107.8	147.3



TEST NUMBER: P331627-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	49.2	48.7	48.3	47.9	47.4	72.2	122.1	172.0	222.0	271.8	281.6
115°	50.5	60.4	70.2	80.1	89.9	126.6	189.9	253.3	316.7	380.0	376.6
117.5°	206.2	238.6	271.0	303.3	335.7	359.6	374.9	390.3	405.6	420.9	418.5
120°	375.7	394.2	412.7	431.1	449.6	458.1	456.4	454.8	453.1	451.4	449.0
122.5°	468.8	472.4	476.0	479.6	483.2	484.5	483.5	482.5	481.5	480.5	477.9
125°	526.6	526.2	525.8	525.4	525.0	524.3	523.3	522.4	521.4	520.5	517.8
127.5°	563.1	563.0	562.9	562.8	562.7	562.0	560.6	559.2	557.8	556.4	554.5
130°	585.7	585.8	586.0	586.2	586.3	585.6	584.1	582.6	581.1	579.5	578.1
132.5°	607.9	608.0	608.2	608.3	608.5	607.9	606.6	605.3	604.0	602.7	601.2
135°	639.9	640.2	640.5	640.8	641.0	640.5	639.1	637.7	636.4	635.0	633.8
137.5°	669.1	669.6	670.0	670.5	671.0	670.5	669.2	667.9	666.5	665.2	663.7
140°	687.3	688.0	688.7	689.4	690.1	689.8	688.5	687.3	686.1	684.9	683.4
142.5°	705.1	705.8	706.5	707.1	707.8	707.6	706.5	705.3	704.2	703.1	701.4
145°	729.9	730.6	731.2	731.9	732.5	732.5	731.5	730.6	729.6	728.6	726.3
147.5°	751.7	752.3	752.8	753.4	754.0	753.9	753.2	752.4	751.7	751.1	748.7
150°	764.9	765.6	766.3	767.0	767.7	767.6	766.8	765.9	765.2	764.3	762.2
152.5°	776.3	777.2	778.1	779.0	779.9	780.0	779.1	778.3	777.5	776.6	774.6
155°	792.0	793.2	794.3	795.3	796.4	796.6	795.7	795.0	794.1	793.2	791.6
157.5°	806.5	807.5	808.6	809.7	810.7	810.8	809.9	808.9	808.0	807.1	805.9
160°	814.9	815.8	816.7	817.7	818.6	818.7	817.9	817.1	816.3	815.5	814.6
162.5°	821.7	822.9	824.1	825.3	826.5	826.6	825.6	824.7	823.8	822.9	822.2
165°	832.1	833.0	834.0	835.0	835.9	835.9	835.0	834.0	833.0	832.1	831.6
167.5°	838.6	839.8	841.1	842.3	843.5	843.7	842.7	841.8	840.8	839.8	839.5
170°	842.6	843.8	845.0	846.3	847.5	847.7	846.6	845.7	844.7	843.8	843.5
172.5°	845.5	846.7	848.0	849.2	850.4	850.6	849.6	848.7	847.7	846.7	846.4
175°	848.1	849.5	850.8	852.2	853.6	853.8	852.8	851.9	850.9	850.0	849.6
177.5°	849.7	850.7	851.7	852.6	853.7	853.8	853.0	852.2	851.4	850.7	850.6
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331627-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	576.4	575.1	573.9	571.2	569.7	566.6	566.2	566.0	562.0	558.0	556.9
5°	596.2	593.0	588.3	582.8	577.1	571.3	567.4	564.2	556.4	549.0	544.7
7.5°	616.0	609.3	601.2	590.9	582.2	572.6	565.3	558.9	547.8	537.1	529.9
10°	630.9	620.0	609.2	595.0	583.8	572.8	562.7	553.9	541.4	527.3	517.3
12.5°	640.2	628.1	613.3	599.3	584.9	570.9	557.3	546.0	531.3	516.8	505.0
15°	652.6	639.7	621.7	601.8	583.2	565.0	549.4	535.3	516.2	498.7	484.2
17.5°	662.9	645.1	625.8	602.7	581.2	558.1	538.0	520.0	498.6	477.6	460.5
20°	666.2	648.5	626.2	603.1	577.7	550.5	528.8	509.3	486.4	463.5	443.9
22.5°	664.1	650.4	625.6	598.0	572.0	543.5	519.0	496.3	470.9	447.5	424.9
25°	650.3	645.6	622.2	592.0	562.3	529.3	500.8	476.0	447.1	422.1	397.4
27.5°	618.1	628.3	613.7	581.6	548.5	513.2	481.2	453.0	422.9	394.8	370.2
30°	587.1	610.4	604.2	574.4	537.4	502.7	466.8	437.3	405.3	376.3	352.1
32.5°	544.8	583.2	589.3	564.4	526.2	487.9	450.4	421.0	387.5	357.1	333.4
35°	477.2	534.7	561.1	545.3	507.0	465.6	427.0	392.7	359.0	329.0	305.5
37.5°	396.7	475.0	519.0	520.1	484.9	442.0	399.8	365.8	331.4	301.9	276.5
40°	344.4	429.3	486.6	499.3	469.6	423.3	380.6	345.9	312.4	283.4	254.3
42.5°	297.5	382.0	452.5	474.6	451.0	404.9	362.1	326.0	293.3	265.9	236.1
45°	240.6	314.5	392.1	431.6	418.5	375.9	330.7	296.3	265.6	241.9	213.4
47.5°	202.9	255.0	330.2	383.6	383.4	344.5	300.0	267.1	238.6	216.4	193.3
50°	181.5	226.9	290.4	351.0	356.1	323.5	281.2	248.6	222.0	198.7	180.1
52.5°	162.2	199.7	256.8	315.0	329.4	301.1	260.1	230.0	204.1	182.7	166.9
55°	137.1	166.1	209.5	263.8	285.8	265.8	229.4	201.2	180.3	162.3	148.6
57.5°	116.0	137.7	172.5	216.3	241.8	229.3	199.2	176.3	158.4	142.2	131.4
60°	102.7	120.5	150.0	186.6	214.7	206.0	180.3	159.0	143.8	129.7	119.5
62.5°	90.1	105.5	130.8	160.5	186.2	182.6	161.7	143.8	130.4	117.6	109.0
65°	72.6	83.7	103.5	126.7	147.5	149.2	134.1	122.0	110.1	100.0	92.3
67.5°	57.8	65.1	79.0	98.6	114.1	119.7	110.5	101.2	91.7	83.9	77.2
70°	48.7	54.6	64.7	80.6	94.9	100.7	95.4	88.2	80.0	73.5	67.8
72.5°	39.4	45.2	52.7	64.3	76.5	82.9	81.0	75.9	69.2	63.8	58.5
75°	29.7	31.5	36.6	44.4	54.0	59.5	60.8	58.1	52.8	48.7	45.5
77.5°	22.0	23.1	25.5	29.5	35.8	40.7	42.7	42.4	38.7	36.4	33.4
80°	17.6	18.2	19.4	21.1	25.8	30.7	32.1	32.1	29.5	28.6	25.7
82.5°	13.3	13.8	14.6	15.5	17.7	22.0	23.5	23.8	22.2	20.9	18.6
85°	7.7	7.4	7.8	8.4	8.8	10.0	12.3	12.7	12.3	10.8	10.2
87.5°	4.6	4.6	4.4	4.0	3.9	3.7	4.2	4.6	4.3	4.1	4.1
90°	10.2	9.0	7.9	6.6	5.2	3.6	2.2	0.6	2.2	3.6	5.2
92.5°	13.2	12.7	12.1	11.9	12.1	12.1	12.3	12.4	12.3	12.1	12.1
95°	22.1	21.2	20.1	22.0	26.5	31.0	35.6	40.0	35.6	31.0	26.5
97.5°	27.7	25.5	23.2	28.5	41.2	54.0	66.7	79.5	66.7	54.0	41.2
100°	30.5	28.2	25.8	34.0	52.8	71.5	90.2	109.0	90.2	71.5	52.8
102.5°	75.0	94.5	113.9	125.6	129.7	133.6	137.6	141.5	137.6	133.6	129.7
105°	112.3	149.6	187.0	203.6	199.6	195.4	191.3	187.3	191.3	195.4	199.6
107.5°	142.2	187.0	231.9	252.6	249.3	246.0	242.6	239.4	242.6	246.0	249.3
110°	186.9	226.4	266.0	284.3	281.5	278.6	275.7	272.9	275.7	278.6	281.5



TEST NUMBER: P331627-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	291.4	301.2	310.9	314.5	312.0	309.4	306.9	304.4	306.9	309.4	312.0
115°	373.2	369.7	366.4	363.4	361.1	358.8	356.5	354.1	356.5	358.8	361.1
117.5°	416.2	413.9	411.5	409.0	406.4	403.8	401.2	398.6	401.2	403.8	406.4
120°	446.5	444.1	441.6	439.4	437.3	435.2	433.2	431.1	433.2	435.2	437.3
122.5°	475.2	472.5	469.8	467.4	465.2	463.0	460.9	458.7	460.9	463.0	465.2
125°	515.2	512.6	510.1	507.8	506.1	504.3	502.5	500.8	502.5	504.3	506.1
127.5°	552.5	550.6	548.6	546.6	544.7	542.8	540.8	538.8	540.8	542.8	544.7
130°	576.5	575.1	573.5	571.7	569.5	567.3	565.2	562.9	565.2	567.3	569.5
132.5°	599.7	598.2	596.7	595.0	593.1	591.3	589.4	587.5	589.4	591.3	593.1
135°	632.5	631.3	630.1	628.4	626.2	624.0	621.8	619.6	621.8	624.0	626.2
137.5°	662.4	661.0	659.6	658.1	656.6	655.0	653.5	652.0	653.5	655.0	656.6
140°	681.9	680.4	678.9	677.5	676.5	675.4	674.2	673.2	674.2	675.4	676.5
142.5°	699.6	697.9	696.2	694.8	693.9	692.9	691.9	691.0	691.9	692.9	693.9
145°	723.9	721.6	719.3	718.2	718.3	718.5	718.6	718.8	718.6	718.5	718.3
147.5°	746.4	744.2	741.8	741.0	741.5	742.0	742.5	743.0	742.5	742.0	741.5
150°	759.9	757.8	755.6	754.9	756.0	756.9	757.9	758.8	757.9	756.9	756.0
152.5°	772.5	770.4	768.4	767.8	768.9	770.0	771.0	772.1	771.0	770.0	768.9
155°	790.0	788.3	786.7	786.5	787.7	788.9	790.2	791.4	790.2	788.9	787.7
157.5°	804.8	803.7	802.5	802.5	803.5	804.5	805.6	806.6	805.6	804.5	803.5
160°	813.8	813.0	812.2	812.2	813.0	813.8	814.6	815.5	814.6	813.8	813.0
162.5°	821.4	820.7	820.0	820.0	820.9	821.7	822.5	823.4	822.5	821.7	820.9
165°	831.3	830.9	830.4	830.6	831.5	832.3	833.1	834.0	833.1	832.3	831.5
167.5°	839.0	838.7	838.3	838.5	839.4	840.2	841.0	841.8	841.0	840.2	839.4
170°	843.3	843.0	842.7	843.0	843.8	844.6	845.4	846.3	845.4	844.6	843.8
172.5°	846.2	845.9	845.7	845.9	846.7	847.6	848.3	849.2	848.3	847.6	846.7
175°	849.4	849.1	848.9	849.2	850.2	851.1	852.0	853.0	852.0	851.1	850.2
177.5°	850.5	850.3	850.2	850.6	851.4	852.1	852.9	853.7	852.9	852.1	851.4
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331627-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	554.9	553.8	551.7	548.6	546.7	543.5	541.3	542.5	542.9	542.5	542.3
5°	540.0	535.9	530.2	524.7	519.6	514.2	511.0	509.7	507.0	505.4	504.5
7.5°	521.9	514.9	506.9	497.3	489.2	480.7	476.4	474.2	468.6	465.6	463.0
10°	508.5	497.3	489.3	476.8	469.2	458.1	450.4	450.6	443.0	438.7	435.6
12.5°	493.6	481.4	468.0	456.8	446.2	437.2	428.0	424.3	416.2	412.1	403.6
15°	469.0	454.7	440.7	425.4	414.7	400.7	387.4	371.2	358.1	346.7	343.6
17.5°	442.1	424.4	410.3	392.4	373.9	350.6	335.2	325.7	317.9	311.9	307.4
20°	423.6	405.6	390.5	363.6	338.7	322.9	311.6	304.3	296.1	289.6	286.1
22.5°	404.2	385.5	364.9	334.8	315.4	302.7	292.7	284.3	278.7	273.7	270.4
25°	376.7	356.1	322.3	301.6	285.9	272.6	265.6	260.5	254.7	247.8	244.7
27.5°	347.6	315.0	290.6	275.2	260.3	251.7	245.3	237.7	232.5	229.4	226.1
30°	325.8	293.2	274.2	257.4	246.8	237.2	229.8	225.5	220.4	215.2	213.0
32.5°	301.6	275.5	257.3	243.3	232.6	224.4	218.5	211.5	207.9	204.7	200.2
35°	271.5	251.7	235.1	223.8	213.5	206.9	200.1	196.0	189.3	186.6	184.9
37.5°	246.0	228.9	216.5	204.5	196.4	189.1	184.9	178.3	175.5	171.6	167.9
40°	231.5	214.7	202.9	193.0	184.0	178.6	173.3	168.0	163.7	162.0	157.5
42.5°	216.9	203.2	191.2	180.6	174.5	168.7	162.0	158.2	153.7	150.8	148.1
45°	196.6	184.4	174.3	165.5	158.8	152.7	148.4	142.0	139.5	133.8	131.4
47.5°	178.7	167.5	157.7	149.4	142.9	139.0	132.7	127.6	123.6	120.0	117.0
50°	166.1	156.6	147.2	139.8	134.0	128.3	121.8	119.3	113.0	111.2	109.5
52.5°	154.5	145.5	137.0	129.7	123.8	118.3	112.6	109.3	105.0	103.3	102.0
55°	138.3	129.7	121.5	115.0	109.2	103.5	100.0	95.8	93.8	92.5	90.9
57.5°	122.0	114.3	108.0	101.4	95.5	91.0	87.0	84.5	82.5	80.7	78.8
60°	111.7	104.3	98.6	92.5	86.4	82.7	79.6	76.6	74.3	71.5	70.8
62.5°	100.7	94.2	89.0	83.1	77.8	74.5	71.5	68.7	65.9	61.9	60.8
65°	85.7	80.6	75.1	70.2	65.5	62.2	57.9	54.8	53.6	53.2	53.0
67.5°	72.1	67.2	62.5	57.5	53.3	50.2	48.0	47.5	46.7	46.5	45.9
70°	62.9	58.5	53.8	49.1	44.9	44.4	43.7	42.8	41.8	41.5	41.1
72.5°	54.8	50.2	45.5	41.8	40.0	39.3	38.5	37.6	37.0	36.6	36.4
75°	42.0	37.7	34.6	33.2	32.3	31.7	30.5	30.0	29.5	28.9	28.8
77.5°	30.3	27.8	26.4	25.6	24.5	23.9	23.2	22.6	22.2	22.1	21.8
80°	23.1	21.9	20.9	19.7	19.4	18.6	18.4	17.8	18.0	17.4	17.4
82.5°	17.9	16.4	15.6	15.1	14.6	14.0	13.9	13.6	13.6	13.2	13.2
85°	9.2	8.8	8.4	8.0	8.0	7.4	7.7	7.4	7.4	7.1	6.9
87.5°	4.3	4.4	4.3	4.6	4.7	4.8	4.9	4.9	5.1	5.2	5.2
90°	6.6	7.9	9.0	10.2	11.2	12.3	13.0	13.7	14.4	15.1	15.5
92.5°	11.9	12.1	12.7	13.2	13.8	14.3	14.6	15.0	15.3	15.7	16.0
95°	22.0	20.1	21.2	22.1	23.1	24.0	24.7	25.4	26.1	26.8	27.0
97.5°	28.5	23.2	25.5	27.7	30.0	32.1	32.7	33.2	33.8	34.4	34.7
100°	34.0	25.8	28.2	30.5	32.8	35.1	36.2	37.3	38.4	39.5	40.2
102.5°	125.6	113.9	94.5	75.0	55.5	36.1	37.5	38.9	40.4	41.8	42.7
105°	203.6	187.0	149.6	112.3	74.9	37.5	39.1	40.6	42.1	43.6	44.6
107.5°	252.6	231.9	187.0	142.2	97.4	52.6	51.1	49.5	48.0	46.5	46.0
110°	284.3	266.0	226.4	186.9	147.3	107.8	94.1	80.4	66.7	53.0	46.5



TEST NUMBER: P331627-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	314.5	310.9	301.2	291.4	281.6	271.8	222.0	172.0	122.1	72.2	47.4
115°	363.4	366.4	369.7	373.2	376.6	380.0	316.7	253.3	189.9	126.6	89.9
117.5°	409.0	411.5	413.9	416.2	418.5	420.9	405.6	390.3	374.9	359.6	335.7
120°	439.4	441.6	444.1	446.5	449.0	451.4	453.1	454.8	456.4	458.1	449.6
122.5°	467.4	469.8	472.5	475.2	477.9	480.5	481.5	482.5	483.5	484.5	483.2
125°	507.8	510.1	512.6	515.2	517.8	520.5	521.4	522.4	523.3	524.3	525.0
127.5°	546.6	548.6	550.6	552.5	554.5	556.4	557.8	559.2	560.6	562.0	562.7
130°	571.7	573.5	575.1	576.5	578.1	579.5	581.1	582.6	584.1	585.6	586.3
132.5°	595.0	596.7	598.2	599.7	601.2	602.7	604.0	605.3	606.6	607.9	608.5
135°	628.4	630.1	631.3	632.5	633.8	635.0	636.4	637.7	639.1	640.5	641.0
137.5°	658.1	659.6	661.0	662.4	663.7	665.2	666.5	667.9	669.2	670.5	671.0
140°	677.5	678.9	680.4	681.9	683.4	684.9	686.1	687.3	688.5	689.8	690.1
142.5°	694.8	696.2	697.9	699.6	701.4	703.1	704.2	705.3	706.5	707.6	707.8
145°	718.2	719.3	721.6	723.9	726.3	728.6	729.6	730.6	731.5	732.5	732.5
147.5°	741.0	741.8	744.2	746.4	748.7	751.1	751.7	752.4	753.2	753.9	754.0
150°	754.9	755.6	757.8	759.9	762.2	764.3	765.2	765.9	766.8	767.6	767.7
152.5°	767.8	768.4	770.4	772.5	774.6	776.6	777.5	778.3	779.1	780.0	779.9
155°	786.5	786.7	788.3	790.0	791.6	793.2	794.1	795.0	795.7	796.6	796.4
157.5°	802.5	802.5	803.7	804.8	805.9	807.1	808.0	808.9	809.9	810.8	810.7
160°	812.2	812.2	813.0	813.8	814.6	815.5	816.3	817.1	817.9	818.7	818.6
162.5°	820.0	820.0	820.7	821.4	822.2	822.9	823.8	824.7	825.6	826.6	826.5
165°	830.6	830.4	830.9	831.3	831.6	832.1	833.0	834.0	835.0	835.9	835.9
167.5°	838.5	838.3	838.7	839.0	839.5	839.8	840.8	841.8	842.7	843.7	843.5
170°	843.0	842.7	843.0	843.3	843.5	843.8	844.7	845.7	846.6	847.7	847.5
172.5°	845.9	845.7	845.9	846.2	846.4	846.7	847.7	848.7	849.6	850.6	850.4
175°	849.2	848.9	849.1	849.4	849.6	850.0	850.9	851.9	852.8	853.8	853.6
177.5°	850.6	850.2	850.3	850.5	850.6	850.7	851.4	852.2	853.0	853.8	853.7
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331627-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	540.5	540.8	540.4	540.6	540.4	540.8	540.5	542.3	542.5	542.9	542.5
5°	503.6	501.3	500.8	500.3	500.8	501.3	503.6	504.5	505.4	507.0	509.7
7.5°	459.6	459.3	458.2	456.8	458.2	459.3	459.6	463.0	465.6	468.6	474.2
10°	431.3	430.2	430.1	428.7	430.1	430.2	431.3	435.6	438.7	443.0	450.6
12.5°	398.0	391.8	391.2	387.7	391.2	391.8	398.0	403.6	412.1	416.2	424.3
15°	339.0	337.8	333.8	331.3	333.8	337.8	339.0	343.6	346.7	358.1	371.2
17.5°	305.1	301.3	300.1	299.5	300.1	301.3	305.1	307.4	311.9	317.9	325.7
20°	283.4	279.9	279.3	278.9	279.3	279.9	283.4	286.1	289.6	296.1	304.3
22.5°	268.4	264.7	263.2	262.0	263.2	264.7	268.4	270.4	273.7	278.7	284.3
25°	242.7	241.3	240.6	240.1	240.6	241.3	242.7	244.7	247.8	254.7	260.5
27.5°	222.7	219.6	219.0	218.0	219.0	219.6	222.7	226.1	229.4	232.5	237.7
30°	211.2	210.3	208.9	207.7	208.9	210.3	211.2	213.0	215.2	220.4	225.5
32.5°	197.8	196.9	195.7	195.2	195.7	196.9	197.8	200.2	204.7	207.9	211.5
35°	182.9	180.1	178.9	177.2	178.9	180.1	182.9	184.9	186.6	189.3	196.0
37.5°	167.1	165.7	164.0	164.6	164.0	165.7	167.1	167.9	171.6	175.5	178.3
40°	154.9	153.9	153.5	153.3	153.5	153.9	154.9	157.5	162.0	163.7	168.0
42.5°	145.2	142.5	141.5	141.5	141.5	142.5	145.2	148.1	150.8	153.7	158.2
45°	130.4	127.9	126.1	126.3	126.1	127.9	130.4	131.4	133.8	139.5	142.0
47.5°	115.4	115.3	114.2	114.5	114.2	115.3	115.4	117.0	120.0	123.6	127.6
50°	108.1	107.0	106.2	106.4	106.2	107.0	108.1	109.5	111.2	113.0	119.3
52.5°	101.3	100.2	99.6	100.5	99.6	100.2	101.3	102.0	103.3	105.0	109.3
55°	90.0	88.8	88.6	88.4	88.6	88.8	90.0	90.9	92.5	93.8	95.8
57.5°	77.3	76.5	75.3	74.9	75.3	76.5	77.3	78.8	80.7	82.5	84.5
60°	68.3	66.7	64.7	64.6	64.7	66.7	68.3	70.8	71.5	74.3	76.6
62.5°	59.9	59.7	59.2	59.2	59.2	59.7	59.9	60.8	61.9	65.9	68.7
65°	52.6	52.4	52.6	52.8	52.6	52.4	52.6	53.0	53.2	53.6	54.8
67.5°	45.8	45.5	45.1	45.3	45.1	45.5	45.8	45.9	46.5	46.7	47.5
70°	40.6	40.5	40.3	40.3	40.3	40.5	40.6	41.1	41.5	41.8	42.8
72.5°	35.6	35.6	35.5	35.3	35.5	35.6	35.6	36.4	36.6	37.0	37.6
75°	28.6	28.2	28.2	28.2	28.2	28.2	28.6	28.8	28.9	29.5	30.0
77.5°	21.8	21.5	21.4	21.2	21.4	21.5	21.8	21.8	22.1	22.2	22.6
80°	17.2	17.0	16.8	16.8	16.8	17.0	17.2	17.4	17.4	18.0	17.8
82.5°	13.2	12.9	12.9	12.7	12.9	12.9	13.2	13.2	13.2	13.6	13.6
85°	7.1	7.2	7.1	7.4	7.1	7.2	7.1	6.9	7.1	7.4	7.4
87.5°	5.2	5.1	5.3	5.2	5.3	5.1	5.2	5.2	5.2	5.1	4.9
90°	15.8	16.1	16.4	16.6	16.4	16.1	15.8	15.5	15.1	14.4	13.7
92.5°	16.1	16.3	16.4	16.6	16.4	16.3	16.1	16.0	15.7	15.3	15.0
95°	26.9	26.8	26.6	26.5	26.6	26.8	26.9	27.0	26.8	26.1	25.4
97.5°	34.9	35.0	35.2	35.4	35.2	35.0	34.9	34.7	34.4	33.8	33.2
100°	40.5	40.7	41.0	41.2	41.0	40.7	40.5	40.2	39.5	38.4	37.3
102.5°	43.0	43.5	43.8	44.3	43.8	43.5	43.0	42.7	41.8	40.4	38.9
105°	45.2	45.7	46.2	46.8	46.2	45.7	45.2	44.6	43.6	42.1	40.6
107.5°	46.5	47.1	47.6	48.1	47.6	47.1	46.5	46.0	46.5	48.0	49.5
110°	47.0	47.5	48.1	48.6	48.1	47.5	47.0	46.5	53.0	66.7	80.4



TEST NUMBER: P331627-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	47.9	48.3	48.7	49.2	48.7	48.3	47.9	47.4	72.2	122.1	172.0
115°	80.1	70.2	60.4	50.5	60.4	70.2	80.1	89.9	126.6	189.9	253.3
117.5°	303.3	271.0	238.6	206.2	238.6	271.0	303.3	335.7	359.6	374.9	390.3
120°	431.1	412.7	394.2	375.7	394.2	412.7	431.1	449.6	458.1	456.4	454.8
122.5°	479.6	476.0	472.4	468.8	472.4	476.0	479.6	483.2	484.5	483.5	482.5
125°	525.4	525.8	526.2	526.6	526.2	525.8	525.4	525.0	524.3	523.3	522.4
127.5°	562.8	562.9	563.0	563.1	563.0	562.9	562.8	562.7	562.0	560.6	559.2
130°	586.2	586.0	585.8	585.7	585.8	586.0	586.2	586.3	585.6	584.1	582.6
132.5°	608.3	608.2	608.0	607.9	608.0	608.2	608.3	608.5	607.9	606.6	605.3
135°	640.8	640.5	640.2	639.9	640.2	640.5	640.8	641.0	640.5	639.1	637.7
137.5°	670.5	670.0	669.6	669.1	669.6	670.0	670.5	671.0	670.5	669.2	667.9
140°	689.4	688.7	688.0	687.3	688.0	688.7	689.4	690.1	689.8	688.5	687.3
142.5°	707.1	706.5	705.8	705.1	705.8	706.5	707.1	707.8	707.6	706.5	705.3
145°	731.9	731.2	730.6	729.9	730.6	731.2	731.9	732.5	732.5	731.5	730.6
147.5°	753.4	752.8	752.3	751.7	752.3	752.8	753.4	754.0	753.9	753.2	752.4
150°	767.0	766.3	765.6	764.9	765.6	766.3	767.0	767.7	767.6	766.8	765.9
152.5°	779.0	778.1	777.2	776.3	777.2	778.1	779.0	779.9	780.0	779.1	778.3
155°	795.3	794.3	793.2	792.0	793.2	794.3	795.3	796.4	796.6	795.7	795.0
157.5°	809.7	808.6	807.5	806.5	807.5	808.6	809.7	810.7	810.8	809.9	808.9
160°	817.7	816.7	815.8	814.9	815.8	816.7	817.7	818.6	818.7	817.9	817.1
162.5°	825.3	824.1	822.9	821.7	822.9	824.1	825.3	826.5	826.6	825.6	824.7
165°	835.0	834.0	833.0	832.1	833.0	834.0	835.0	835.9	835.9	835.0	834.0
167.5°	842.3	841.1	839.8	838.6	839.8	841.1	842.3	843.5	843.7	842.7	841.8
170°	846.3	845.0	843.8	842.6	843.8	845.0	846.3	847.5	847.7	846.6	845.7
172.5°	849.2	848.0	846.7	845.5	846.7	848.0	849.2	850.4	850.6	849.6	848.7
175°	852.2	850.8	849.5	848.1	849.5	850.8	852.2	853.6	853.8	852.8	851.9
177.5°	852.6	851.7	850.7	849.7	850.7	851.7	852.6	853.7	853.8	853.0	852.2
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331627-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	541.3	543.5	546.7	548.6	551.7	553.8	554.9	556.9	558.0	562.0	566.0
5°	511.0	514.2	519.6	524.7	530.2	535.9	540.0	544.7	549.0	556.4	564.2
7.5°	476.4	480.7	489.2	497.3	506.9	514.9	521.9	529.9	537.1	547.8	558.9
10°	450.4	458.1	469.2	476.8	489.3	497.3	508.5	517.3	527.3	541.4	553.9
12.5°	428.0	437.2	446.2	456.8	468.0	481.4	493.6	505.0	516.8	531.3	546.0
15°	387.4	400.7	414.7	425.4	440.7	454.7	469.0	484.2	498.7	516.2	535.3
17.5°	335.2	350.6	373.9	392.4	410.3	424.4	442.1	460.5	477.6	498.6	520.0
20°	311.6	322.9	338.7	363.6	390.5	405.6	423.6	443.9	463.5	486.4	509.3
22.5°	292.7	302.7	315.4	334.8	364.9	385.5	404.2	424.9	447.5	470.9	496.3
25°	265.6	272.6	285.9	301.6	322.3	356.1	376.7	397.4	422.1	447.1	476.0
27.5°	245.3	251.7	260.3	275.2	290.6	315.0	347.6	370.2	394.8	422.9	453.0
30°	229.8	237.2	246.8	257.4	274.2	293.2	325.8	352.1	376.3	405.3	437.3
32.5°	218.5	224.4	232.6	243.3	257.3	275.5	301.6	333.4	357.1	387.5	421.0
35°	200.1	206.9	213.5	223.8	235.1	251.7	271.5	305.5	329.0	359.0	392.7
37.5°	184.9	189.1	196.4	204.5	216.5	228.9	246.0	276.5	301.9	331.4	365.8
40°	173.3	178.6	184.0	193.0	202.9	214.7	231.5	254.3	283.4	312.4	345.9
42.5°	162.0	168.7	174.5	180.6	191.2	203.2	216.9	236.1	265.9	293.3	326.0
45°	148.4	152.7	158.8	165.5	174.3	184.4	196.6	213.4	241.9	265.6	296.3
47.5°	132.7	139.0	142.9	149.4	157.7	167.5	178.7	193.3	216.4	238.6	267.1
50°	121.8	128.3	134.0	139.8	147.2	156.6	166.1	180.1	198.7	222.0	248.6
52.5°	112.6	118.3	123.8	129.7	137.0	145.5	154.5	166.9	182.7	204.1	230.0
55°	100.0	103.5	109.2	115.0	121.5	129.7	138.3	148.6	162.3	180.3	201.2
57.5°	87.0	91.0	95.5	101.4	108.0	114.3	122.0	131.4	142.2	158.4	176.3
60°	79.6	82.7	86.4	92.5	98.6	104.3	111.7	119.5	129.7	143.8	159.0
62.5°	71.5	74.5	77.8	83.1	89.0	94.2	100.7	109.0	117.6	130.4	143.8
65°	57.9	62.2	65.5	70.2	75.1	80.6	85.7	92.3	100.0	110.1	122.0
67.5°	48.0	50.2	53.3	57.5	62.5	67.2	72.1	77.2	83.9	91.7	101.2
70°	43.7	44.4	44.9	49.1	53.8	58.5	62.9	67.8	73.5	80.0	88.2
72.5°	38.5	39.3	40.0	41.8	45.5	50.2	54.8	58.5	63.8	69.2	75.9
75°	30.5	31.7	32.3	33.2	34.6	37.7	42.0	45.5	48.7	52.8	58.1
77.5°	23.2	23.9	24.5	25.6	26.4	27.8	30.3	33.4	36.4	38.7	42.4
80°	18.4	18.6	19.4	19.7	20.9	21.9	23.1	25.7	28.6	29.5	32.1
82.5°	13.9	14.0	14.6	15.1	15.6	16.4	17.9	18.6	20.9	22.2	23.8
85°	7.7	7.4	8.0	8.0	8.4	8.8	9.2	10.2	10.8	12.3	12.7
87.5°	4.9	4.8	4.7	4.6	4.3	4.4	4.3	4.1	4.1	4.3	4.6
90°	13.0	12.3	11.2	10.2	9.0	7.9	6.6	5.2	3.6	2.2	0.6
92.5°	14.6	14.3	13.8	13.2	12.7	12.1	11.9	12.1	12.1	12.3	12.4
95°	24.7	24.0	23.1	22.1	21.2	20.1	22.0	26.5	31.0	35.6	40.0
97.5°	32.7	32.1	30.0	27.7	25.5	23.2	28.5	41.2	54.0	66.7	79.5
100°	36.2	35.1	32.8	30.5	28.2	25.8	34.0	52.8	71.5	90.2	109.0
102.5°	37.5	36.1	55.5	75.0	94.5	113.9	125.6	129.7	133.6	137.6	141.5
105°	39.1	37.5	74.9	112.3	149.6	187.0	203.6	199.6	195.4	191.3	187.3
107.5°	51.1	52.6	97.4	142.2	187.0	231.9	252.6	249.3	246.0	242.6	239.4
110°	94.1	107.8	147.3	186.9	226.4	266.0	284.3	281.5	278.6	275.7	272.9



TEST NUMBER: P331627-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	222.0	271.8	281.6	291.4	301.2	310.9	314.5	312.0	309.4	306.9	304.4
115°	316.7	380.0	376.6	373.2	369.7	366.4	363.4	361.1	358.8	356.5	354.1
117.5°	405.6	420.9	418.5	416.2	413.9	411.5	409.0	406.4	403.8	401.2	398.6
120°	453.1	451.4	449.0	446.5	444.1	441.6	439.4	437.3	435.2	433.2	431.1
122.5°	481.5	480.5	477.9	475.2	472.5	469.8	467.4	465.2	463.0	460.9	458.7
125°	521.4	520.5	517.8	515.2	512.6	510.1	507.8	506.1	504.3	502.5	500.8
127.5°	557.8	556.4	554.5	552.5	550.6	548.6	546.6	544.7	542.8	540.8	538.8
130°	581.1	579.5	578.1	576.5	575.1	573.5	571.7	569.5	567.3	565.2	562.9
132.5°	604.0	602.7	601.2	599.7	598.2	596.7	595.0	593.1	591.3	589.4	587.5
135°	636.4	635.0	633.8	632.5	631.3	630.1	628.4	626.2	624.0	621.8	619.6
137.5°	666.5	665.2	663.7	662.4	661.0	659.6	658.1	656.6	655.0	653.5	652.0
140°	686.1	684.9	683.4	681.9	680.4	678.9	677.5	676.5	675.4	674.2	673.2
142.5°	704.2	703.1	701.4	699.6	697.9	696.2	694.8	693.9	692.9	691.9	691.0
145°	729.6	728.6	726.3	723.9	721.6	719.3	718.2	718.3	718.5	718.6	718.8
147.5°	751.7	751.1	748.7	746.4	744.2	741.8	741.0	741.5	742.0	742.5	743.0
150°	765.2	764.3	762.2	759.9	757.8	755.6	754.9	756.0	756.9	757.9	758.8
152.5°	777.5	776.6	774.6	772.5	770.4	768.4	767.8	768.9	770.0	771.0	772.1
155°	794.1	793.2	791.6	790.0	788.3	786.7	786.5	787.7	788.9	790.2	791.4
157.5°	808.0	807.1	805.9	804.8	803.7	802.5	802.5	803.5	804.5	805.6	806.6
160°	816.3	815.5	814.6	813.8	813.0	812.2	812.2	813.0	813.8	814.6	815.5
162.5°	823.8	822.9	822.2	821.4	820.7	820.0	820.0	820.9	821.7	822.5	823.4
165°	833.0	832.1	831.6	831.3	830.9	830.4	830.6	831.5	832.3	833.1	834.0
167.5°	840.8	839.8	839.5	839.0	838.7	838.3	838.5	839.4	840.2	841.0	841.8
170°	844.7	843.8	843.5	843.3	843.0	842.7	843.0	843.8	844.6	845.4	846.3
172.5°	847.7	846.7	846.4	846.2	845.9	845.7	845.9	846.7	847.6	848.3	849.2
175°	850.9	850.0	849.6	849.4	849.1	848.9	849.2	850.2	851.1	852.0	853.0
177.5°	851.4	850.7	850.6	850.5	850.3	850.2	850.6	851.4	852.1	852.9	853.7
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2

TEST NUMBER: P331627-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	566.2	566.6	569.7	571.2	573.9	575.1	576.4	576.0	576.0	576.6	581.0
5°	567.4	571.3	577.1	582.8	588.3	593.0	596.2	599.3	600.5	606.1	611.1
7.5°	565.3	572.6	582.2	590.9	601.2	609.3	616.0	622.2	626.3	634.6	643.0
10°	562.7	572.8	583.8	595.0	609.2	620.0	630.9	639.4	642.0	654.4	661.4
12.5°	557.3	570.9	584.9	599.3	613.3	628.1	640.2	648.6	658.2	669.3	682.3
15°	549.4	565.0	583.2	601.8	621.7	639.7	652.6	667.3	677.9	690.0	701.4
17.5°	538.0	558.1	581.2	602.7	625.8	645.1	662.9	676.9	684.3	691.3	692.9
20°	528.8	550.5	577.7	603.1	626.2	648.5	666.2	677.9	679.8	680.0	669.7
22.5°	519.0	543.5	572.0	598.0	625.6	650.4	664.1	669.1	661.3	648.1	628.0
25°	500.8	529.3	562.3	592.0	622.2	645.6	650.3	641.5	614.3	585.7	549.6
27.5°	481.2	513.2	548.5	581.6	613.7	628.3	618.1	586.3	537.4	494.8	443.2
30°	466.8	502.7	537.4	574.4	604.2	610.4	587.1	540.4	483.3	419.1	367.6
32.5°	450.4	487.9	526.2	564.4	589.3	583.2	544.8	487.2	420.3	357.1	308.6
35°	427.0	465.6	507.0	545.3	561.1	534.7	477.2	402.3	333.8	275.0	241.5
37.5°	399.8	442.0	484.9	520.1	519.0	475.0	396.7	319.3	261.8	227.0	203.2
40°	380.6	423.3	469.6	499.3	486.6	429.3	344.4	271.5	229.4	201.6	184.3
42.5°	362.1	404.9	451.0	474.6	452.5	382.0	297.5	240.3	205.6	184.0	169.9
45°	330.7	375.9	418.5	431.6	392.1	314.5	240.6	199.1	176.0	160.0	150.2
47.5°	300.0	344.5	383.4	383.6	330.2	255.0	202.9	172.3	152.6	140.2	133.1
50°	281.2	323.5	356.1	351.0	290.4	226.9	181.5	155.1	138.7	129.1	121.7
52.5°	260.1	301.1	329.4	315.0	256.8	199.7	162.2	140.1	126.5	118.1	111.5
55°	229.4	265.8	285.8	263.8	209.5	166.1	137.1	119.7	109.5	102.5	96.8
57.5°	199.2	229.3	241.8	216.3	172.5	137.7	116.0	102.9	92.8	87.7	84.8
60°	180.3	206.0	214.7	186.6	150.0	120.5	102.7	90.6	83.1	79.8	76.9
62.5°	161.7	182.6	186.2	160.5	130.8	105.5	90.1	79.9	75.0	71.8	69.1
65°	134.1	149.2	147.5	126.7	103.5	83.7	72.6	66.3	62.6	58.1	53.2
67.5°	110.5	119.7	114.1	98.6	79.0	65.1	57.8	53.0	48.4	44.2	43.0
70°	95.4	100.7	94.9	80.6	64.7	54.6	48.7	43.0	40.3	39.3	37.5
72.5°	81.0	82.9	76.5	64.3	52.7	45.2	39.4	36.3	34.8	34.0	32.9
75°	60.8	59.5	54.0	44.4	36.6	31.5	29.7	28.6	27.6	26.8	26.2
77.5°	42.7	40.7	35.8	29.5	25.5	23.1	22.0	21.4	20.9	20.5	19.9
80°	32.1	30.7	25.8	21.1	19.4	18.2	17.6	16.8	16.8	16.4	15.8
82.5°	23.5	22.0	17.7	15.5	14.6	13.8	13.3	12.9	12.7	12.8	12.4
85°	12.3	10.0	8.8	8.4	7.8	7.4	7.7	7.2	7.2	7.2	7.1
87.5°	4.2	3.7	3.9	4.0	4.4	4.6	4.6	4.9	5.3	5.3	5.6
90°	2.2	3.6	5.2	6.6	7.9	9.0	10.2	11.2	12.3	13.0	13.7
92.5°	12.3	12.1	12.1	11.9	12.1	12.7	13.2	13.8	14.3	14.6	15.0
95°	35.6	31.0	26.5	22.0	20.1	21.2	22.1	23.1	24.0	24.7	25.4
97.5°	66.7	54.0	41.2	28.5	23.2	25.5	27.7	30.0	32.1	32.7	33.2
100°	90.2	71.5	52.8	34.0	25.8	28.2	30.5	32.8	35.1	36.2	37.3
102.5°	137.6	133.6	129.7	125.6	113.9	94.5	75.0	55.5	36.1	37.5	38.9
105°	191.3	195.4	199.6	203.6	187.0	149.6	112.3	74.9	37.5	39.1	40.6
107.5°	242.6	246.0	249.3	252.6	231.9	187.0	142.2	97.4	52.6	51.1	49.5
110°	275.7	278.6	281.5	284.3	266.0	226.4	186.9	147.3	107.8	94.1	80.4



TEST NUMBER: P331627-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	306.9	309.4	312.0	314.5	310.9	301.2	291.4	281.6	271.8	222.0	172.0
115°	356.5	358.8	361.1	363.4	366.4	369.7	373.2	376.6	380.0	316.7	253.3
117.5°	401.2	403.8	406.4	409.0	411.5	413.9	416.2	418.5	420.9	405.6	390.3
120°	433.2	435.2	437.3	439.4	441.6	444.1	446.5	449.0	451.4	453.1	454.8
122.5°	460.9	463.0	465.2	467.4	469.8	472.5	475.2	477.9	480.5	481.5	482.5
125°	502.5	504.3	506.1	507.8	510.1	512.6	515.2	517.8	520.5	521.4	522.4
127.5°	540.8	542.8	544.7	546.6	548.6	550.6	552.5	554.5	556.4	557.8	559.2
130°	565.2	567.3	569.5	571.7	573.5	575.1	576.5	578.1	579.5	581.1	582.6
132.5°	589.4	591.3	593.1	595.0	596.7	598.2	599.7	601.2	602.7	604.0	605.3
135°	621.8	624.0	626.2	628.4	630.1	631.3	632.5	633.8	635.0	636.4	637.7
137.5°	653.5	655.0	656.6	658.1	659.6	661.0	662.4	663.7	665.2	666.5	667.9
140°	674.2	675.4	676.5	677.5	678.9	680.4	681.9	683.4	684.9	686.1	687.3
142.5°	691.9	692.9	693.9	694.8	696.2	697.9	699.6	701.4	703.1	704.2	705.3
145°	718.6	718.5	718.3	718.2	719.3	721.6	723.9	726.3	728.6	729.6	730.6
147.5°	742.5	742.0	741.5	741.0	741.8	744.2	746.4	748.7	751.1	751.7	752.4
150°	757.9	756.9	756.0	754.9	755.6	757.8	759.9	762.2	764.3	765.2	765.9
152.5°	771.0	770.0	768.9	767.8	768.4	770.4	772.5	774.6	776.6	777.5	778.3
155°	790.2	788.9	787.7	786.5	786.7	788.3	790.0	791.6	793.2	794.1	795.0
157.5°	805.6	804.5	803.5	802.5	802.5	803.7	804.8	805.9	807.1	808.0	808.9
160°	814.6	813.8	813.0	812.2	812.2	813.0	813.8	814.6	815.5	816.3	817.1
162.5°	822.5	821.7	820.9	820.0	820.0	820.7	821.4	822.2	822.9	823.8	824.7
165°	833.1	832.3	831.5	830.6	830.4	830.9	831.3	831.6	832.1	833.0	834.0
167.5°	841.0	840.2	839.4	838.5	838.3	838.7	839.0	839.5	839.8	840.8	841.8
170°	845.4	844.6	843.8	843.0	842.7	843.0	843.3	843.5	843.8	844.7	845.7
172.5°	848.3	847.6	846.7	845.9	845.7	845.9	846.2	846.4	846.7	847.7	848.7
175°	852.0	851.1	850.2	849.2	848.9	849.1	849.4	849.6	850.0	850.9	851.9
177.5°	852.9	852.1	851.4	850.6	850.2	850.3	850.5	850.6	850.7	851.4	852.2
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331627-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	582.6	584.6	585.6	585.6	586.7	586.2	585.7
5°	616.0	619.7	620.6	624.1	626.6	625.9	626.2
7.5°	649.4	655.3	661.2	663.9	664.3	665.9	666.5
10°	669.9	674.8	683.9	682.6	689.4	693.4	686.9
12.5°	689.6	696.2	702.6	704.3	708.2	709.5	706.9
15°	707.4	710.9	711.3	710.3	711.5	710.5	706.8
17.5°	690.8	685.0	673.5	668.0	663.7	657.2	654.6
20°	663.2	646.4	626.8	619.0	609.8	591.9	596.2
22.5°	603.7	584.6	565.0	542.2	531.2	514.2	513.2
25°	511.3	478.2	441.8	416.4	401.5	384.5	377.0
27.5°	397.5	355.9	326.1	311.0	297.2	283.8	283.2
30°	322.7	291.4	268.4	255.5	247.0	241.3	242.5
32.5°	272.0	250.6	235.0	224.3	218.1	213.8	213.7
35°	222.4	207.7	197.7	193.2	188.7	185.6	185.8
37.5°	190.3	181.5	175.9	171.0	168.2	166.6	165.7
40°	173.8	166.6	162.3	159.4	157.0	154.9	154.5
42.5°	160.9	154.9	150.6	148.3	146.1	144.6	144.2
45°	142.8	137.8	134.0	131.4	130.4	129.1	129.1
47.5°	127.0	122.2	119.2	117.5	115.9	114.9	114.9
50°	116.4	112.6	109.9	108.9	107.5	107.0	106.8
52.5°	106.9	104.0	102.1	101.4	100.8	100.1	100.2
55°	93.8	92.3	91.5	90.9	90.0	88.8	89.5
57.5°	83.0	81.6	79.6	77.7	76.8	75.9	76.3
60°	75.3	72.6	69.8	67.7	67.1	65.3	65.3
62.5°	65.6	61.7	58.4	57.2	56.6	55.8	55.6
65°	50.5	48.9	48.1	47.4	46.9	46.9	46.6
67.5°	41.8	41.2	40.3	40.1	39.8	39.6	39.5
70°	36.9	36.2	35.8	35.6	35.2	35.4	34.8
72.5°	32.3	31.7	31.6	31.1	30.8	30.8	30.4
75°	25.4	25.4	25.2	25.1	24.6	24.5	24.6
77.5°	19.5	19.6	19.3	19.2	19.2	19.2	19.0
80°	15.7	15.8	15.7	15.4	15.2	15.4	15.2
82.5°	12.4	12.1	12.1	12.0	12.0	11.9	11.8
85°	7.1	7.2	7.1	6.9	6.9	6.9	7.1
87.5°	5.5	5.7	5.8	5.9	5.9	5.9	5.9
90°	14.4	15.1	15.5	15.8	16.1	16.4	16.6
92.5°	15.3	15.7	16.0	16.1	16.3	16.4	16.6
95°	26.1	26.8	27.0	26.9	26.8	26.6	26.5
97.5°	33.8	34.4	34.7	34.9	35.0	35.2	35.4
100°	38.4	39.5	40.2	40.5	40.7	41.0	41.2
102.5°	40.4	41.8	42.7	43.0	43.5	43.8	44.3
105°	42.1	43.6	44.6	45.2	45.7	46.2	46.8
107.5°	48.0	46.5	46.0	46.5	47.1	47.6	48.1
110°	66.7	53.0	46.5	47.0	47.5	48.1	48.6



TEST NUMBER: P331627-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	122.1	72.2	47.4	47.9	48.3	48.7	49.2
115°	189.9	126.6	89.9	80.1	70.2	60.4	50.5
117.5°	374.9	359.6	335.7	303.3	271.0	238.6	206.2
120°	456.4	458.1	449.6	431.1	412.7	394.2	375.7
122.5°	483.5	484.5	483.2	479.6	476.0	472.4	468.8
125°	523.3	524.3	525.0	525.4	525.8	526.2	526.6
127.5°	560.6	562.0	562.7	562.8	562.9	563.0	563.1
130°	584.1	585.6	586.3	586.2	586.0	585.8	585.7
132.5°	606.6	607.9	608.5	608.3	608.2	608.0	607.9
135°	639.1	640.5	641.0	640.8	640.5	640.2	639.9
137.5°	669.2	670.5	671.0	670.5	670.0	669.6	669.1
140°	688.5	689.8	690.1	689.4	688.7	688.0	687.3
142.5°	706.5	707.6	707.8	707.1	706.5	705.8	705.1
145°	731.5	732.5	732.5	731.9	731.2	730.6	729.9
147.5°	753.2	753.9	754.0	753.4	752.8	752.3	751.7
150°	766.8	767.6	767.7	767.0	766.3	765.6	764.9
152.5°	779.1	780.0	779.9	779.0	778.1	777.2	776.3
155°	795.7	796.6	796.4	795.3	794.3	793.2	792.0
157.5°	809.9	810.8	810.7	809.7	808.6	807.5	806.5
160°	817.9	818.7	818.6	817.7	816.7	815.8	814.9
162.5°	825.6	826.6	826.5	825.3	824.1	822.9	821.7
165°	835.0	835.9	835.9	835.0	834.0	833.0	832.1
167.5°	842.7	843.7	843.5	842.3	841.1	839.8	838.6
170°	846.6	847.7	847.5	846.3	845.0	843.8	842.6
172.5°	849.6	850.6	850.4	849.2	848.0	846.7	845.5
175°	852.8	853.8	853.6	852.2	850.8	849.5	848.1
177.5°	853.0	853.8	853.7	852.6	851.7	850.7	849.7
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2

(END OF REPORT)