

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331633-935

Luminaire Tested: **SA2XXRDIP-C290D925U935-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331633-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4160.1 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331633-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331633-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32	23
1	92	88	85	81	82	79	76	73	60	59	57	44	43	42	29	28	27	20
2	84	77	72	67	75	69	64	60	53	50	48	39	37	35	26	25	24	18
3	77	68	62	56	68	61	55	51	47	44	40	35	32	30	23	22	21	15
4	71	61	53	48	63	54	48	43	42	38	35	31	28	26	21	19	18	14
5	65	54	46	41	57	48	42	37	38	33	30	28	25	23	19	17	16	12
6	60	48	41	36	53	44	37	32	34	30	26	25	22	20	17	16	14	11
7	55	44	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10
8	51	40	32	27	45	36	29	25	28	24	21	21	18	16	15	13	12	9
9	48	36	29	24	42	33	27	22	26	22	18	20	17	14	14	12	11	8
10	44	33	26	22	40	30	24	20	24	20	17	18	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9087	9087	9087	9087
5°	10149	9144	8109	9144
10°	11262	9081	7029	9081
15°	11814	8948	5538	8948
20°	10244	8751	4792	8751
25°	6716	8480	4277	8480
30°	4521	8153	3872	8153
35°	3662	7740	3493	7740
40°	3256	7290	3231	7290
45°	2948	6766	2884	6766
50°	2683	6244	2673	6244
55°	2519	5664	2488	5664
60°	2109	5134	2086	5134
65°	1780	4661	2017	4661
70°	1643	4164	1902	4164
75°	1535	3624	1759	3624
80°	1413	2985	1562	2985
85°	1315	2353	1371	2353



TEST NUMBER: P331633-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.4	1.3
10°-20°	148.7	3.6
20°-30°	191.6	4.6
30°-40°	182.1	4.4
40°-50°	156.0	3.7
50°-60°	118.8	2.9
60°-70°	75.1	1.8
70°-80°	37.5	0.9
80°-90°	12.4	0.3
90°-100°	36.2	0.9
100°-110°	132.9	3.2
110°-120°	355.3	8.5
120°-130°	586.6	14.1
130°-140°	623.8	15.0
140°-150°	579.8	13.9
150°-160°	466.2	11.2
160°-170°	300.4	7.2
170°-180°	103.4	2.5
0°-30°	393.6	9.5
0°-40°	575.7	13.8
0°-60°	850.4	20.4
0°-90°	975.4	23.4
90°-120°	524.5	12.6
90°-150°	2314.7	55.6
90°-180°	3185.0	76.6
0°-180°	4160.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	563	563	563	563	563	
5°	626	564	500	564	626	62
15°	707	535	331	535	707	191
25°	377	476	240	476	377	179
35°	186	393	177	393	186	119
45°	129	296	126	296	129	100
55°	90	201	88	201	90	79
65°	47	122	53	122	47	47
75°	25	58	28	58	25	26
85°	7	13	7	13	7	8
90°	21	1	21	1	21	10
95°	34	51	34	51	34	32
105°	60	239	60	239	60	62
115°	64	452	64	452	64	162
125°	672	639	672	639	672	582
135°	817	791	817	791	817	630
145°	932	918	932	918	932	583
155°	1011	1010	1011	1010	1011	467
165°	1062	1065	1062	1065	1062	300
175°	1083	1089	1083	1089	1083	103
180°	1087	1087	1087	1087	1087	



TEST NUMBER: P331633-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	585.7	586.2	586.7	585.6	585.6	584.6	582.6	581.0	576.6	576.0	576.0
5°	626.2	625.9	626.6	624.1	620.6	619.7	616.0	611.1	606.1	600.5	599.3
7.5°	666.5	665.9	664.3	663.9	661.2	655.3	649.4	643.0	634.6	626.3	622.2
10°	686.9	693.4	689.4	682.6	683.9	674.8	669.9	661.4	654.4	642.0	639.4
12.5°	706.9	709.5	708.2	704.3	702.6	696.2	689.6	682.3	669.3	658.2	648.6
15°	706.8	710.5	711.5	710.3	711.3	710.9	707.4	701.4	690.0	677.9	667.3
17.5°	654.6	657.2	663.7	668.0	673.5	685.0	690.8	692.9	691.3	684.3	676.9
20°	596.2	591.9	609.8	619.0	626.8	646.4	663.2	669.7	680.0	679.8	677.9
22.5°	513.2	514.2	531.2	542.2	565.0	584.6	603.7	628.0	648.1	661.3	669.1
25°	377.0	384.5	401.5	416.4	441.8	478.2	511.3	549.6	585.7	614.3	641.5
27.5°	283.2	283.8	297.2	311.0	326.1	355.9	397.5	443.2	494.8	537.4	586.3
30°	242.5	241.3	247.0	255.5	268.4	291.4	322.7	367.6	419.1	483.3	540.4
32.5°	213.7	213.8	218.1	224.3	235.0	250.6	272.0	308.6	357.1	420.3	487.2
35°	185.8	185.6	188.7	193.2	197.7	207.7	222.4	241.5	275.0	333.8	402.3
37.5°	165.7	166.6	168.2	171.0	175.9	181.5	190.3	203.2	227.0	261.8	319.3
40°	154.5	154.9	157.0	159.4	162.3	166.6	173.8	184.3	201.6	229.4	271.5
42.5°	144.2	144.6	146.1	148.3	150.6	154.9	160.9	169.9	184.0	205.6	240.3
45°	129.1	129.1	130.4	131.4	134.0	137.8	142.8	150.2	160.0	176.0	199.1
47.5°	114.9	114.9	115.9	117.5	119.2	122.2	127.0	133.1	140.2	152.6	172.3
50°	106.8	107.0	107.5	108.9	109.9	112.6	116.4	121.7	129.1	138.7	155.1
52.5°	100.2	100.1	100.8	101.4	102.1	104.0	106.9	111.5	118.1	126.5	140.1
55°	89.5	88.8	90.0	90.9	91.5	92.3	93.8	96.8	102.5	109.5	119.7
57.5°	76.3	75.9	76.8	77.7	79.6	81.6	83.0	84.8	87.7	92.8	102.9
60°	65.3	65.3	67.1	67.7	69.8	72.6	75.3	76.9	79.8	83.1	90.6
62.5°	55.6	55.8	56.6	57.2	58.4	61.7	65.6	69.1	71.8	75.0	79.9
65°	46.6	46.9	46.9	47.4	48.1	48.9	50.5	53.2	58.1	62.6	66.3
67.5°	39.5	39.6	39.8	40.1	40.3	41.2	41.8	43.0	44.2	48.4	53.0
70°	34.8	35.4	35.2	35.6	35.8	36.2	36.9	37.5	39.3	40.3	43.0
72.5°	30.4	30.8	30.8	31.1	31.6	31.7	32.3	32.9	34.0	34.8	36.3
75°	24.6	24.5	24.6	25.1	25.2	25.4	25.4	26.2	26.8	27.6	28.6
77.5°	19.0	19.2	19.2	19.2	19.3	19.6	19.5	19.9	20.5	20.9	21.4
80°	15.2	15.4	15.2	15.4	15.7	15.8	15.7	15.8	16.4	16.8	16.8
82.5°	11.8	11.9	12.0	12.0	12.1	12.1	12.4	12.4	12.8	12.7	12.9
85°	7.1	6.9	6.9	6.9	7.1	7.2	7.1	7.1	7.2	7.2	7.2
87.5°	6.7	6.8	6.8	6.7	6.6	6.5	6.4	6.3	5.9	5.9	5.5
90°	21.3	20.9	20.5	20.1	19.8	19.2	18.3	17.5	16.6	15.8	14.3
92.5°	21.3	21.0	20.8	20.6	20.4	20.1	19.6	19.1	18.7	18.3	17.6
95°	33.8	34.0	34.2	34.4	34.5	34.2	33.3	32.4	31.5	30.7	29.4
97.5°	45.1	44.9	44.7	44.5	44.3	43.8	43.1	42.4	41.8	41.1	38.2
100°	52.7	52.3	52.0	51.7	51.3	50.5	49.0	47.6	46.2	44.9	41.8
102.5°	56.5	56.0	55.4	55.0	54.5	53.4	51.6	49.7	47.9	46.1	40.9
105°	59.8	59.1	58.4	57.7	57.0	55.6	53.7	51.8	49.9	48.0	45.7
107.5°	61.5	60.8	60.1	59.4	58.7	59.3	61.3	63.2	65.2	67.2	70.3
110°	62.2	61.4	60.7	60.0	59.3	67.7	85.2	102.6	120.1	137.6	188.1



TEST NUMBER: P331633-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	62.8	62.2	61.6	61.0	60.5	92.1	155.8	219.6	283.4	347.1	359.6
115°	64.5	77.1	89.6	102.2	114.8	161.5	242.5	323.4	404.2	485.2	480.8
117.5°	263.3	304.6	345.9	387.3	428.6	459.1	478.7	498.3	517.8	537.4	534.4
120°	479.7	503.3	526.8	550.4	574.0	584.8	582.7	580.6	578.5	576.4	573.3
122.5°	598.6	603.1	607.7	612.3	616.9	618.5	617.3	616.0	614.8	613.5	610.1
125°	672.4	671.8	671.2	670.7	670.2	669.3	668.1	666.9	665.7	664.4	661.2
127.5°	718.8	718.8	718.7	718.6	718.4	717.6	715.7	713.9	712.1	710.4	707.9
130°	747.8	748.0	748.1	748.4	748.6	747.6	745.7	743.8	741.8	739.9	738.0
132.5°	776.1	776.3	776.4	776.6	776.8	776.1	774.5	772.8	771.2	769.5	767.6
135°	817.0	817.3	817.7	818.0	818.4	817.7	816.0	814.2	812.4	810.7	809.2
137.5°	854.3	854.9	855.5	856.1	856.7	856.1	854.4	852.6	850.9	849.3	847.5
140°	877.5	878.5	879.3	880.2	881.1	880.7	879.2	877.5	876.0	874.4	872.5
142.5°	900.2	901.1	902.0	902.8	903.7	903.4	902.0	900.5	899.1	897.7	895.5
145°	931.9	932.7	933.6	934.4	935.3	935.1	933.9	932.7	931.4	930.2	927.3
147.5°	959.7	960.4	961.1	961.8	962.6	962.5	961.6	960.7	959.8	958.9	956.0
150°	976.6	977.5	978.4	979.3	980.2	980.1	979.0	977.9	976.9	975.9	973.1
152.5°	991.1	992.3	993.4	994.5	995.7	995.7	994.7	993.7	992.6	991.6	988.9
155°	1011.2	1012.6	1014.0	1015.5	1016.8	1017.0	1016.0	1014.9	1013.8	1012.8	1010.7
157.5°	1029.7	1031.0	1032.3	1033.7	1035.1	1035.2	1034.0	1032.8	1031.7	1030.4	1029.0
160°	1040.3	1041.6	1042.8	1044.0	1045.3	1045.3	1044.3	1043.2	1042.2	1041.1	1040.1
162.5°	1049.1	1050.7	1052.1	1053.7	1055.2	1055.3	1054.1	1052.9	1051.7	1050.6	1049.6
165°	1062.4	1063.6	1064.8	1066.0	1067.2	1067.2	1066.0	1064.8	1063.6	1062.4	1061.9
167.5°	1070.7	1072.3	1073.8	1075.4	1076.9	1077.2	1075.9	1074.7	1073.5	1072.3	1071.8
170°	1075.7	1077.3	1078.8	1080.5	1082.0	1082.2	1081.0	1079.8	1078.5	1077.3	1076.9
172.5°	1079.5	1081.1	1082.6	1084.2	1085.8	1086.0	1084.8	1083.5	1082.3	1081.1	1080.7
175°	1082.8	1084.5	1086.3	1088.0	1089.8	1090.0	1088.8	1087.6	1086.4	1085.1	1084.8
177.5°	1084.9	1086.1	1087.4	1088.6	1089.9	1090.0	1089.1	1088.0	1087.1	1086.1	1086.0
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8



TEST NUMBER: P331633-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	576.4	575.1	573.9	571.2	569.7	566.6	566.2	566.0	562.0	558.0	556.9
5°	596.2	593.0	588.3	582.8	577.1	571.3	567.4	564.2	556.4	549.0	544.7
7.5°	616.0	609.3	601.2	590.9	582.2	572.6	565.3	558.9	547.8	537.1	529.9
10°	630.9	620.0	609.2	595.0	583.8	572.8	562.7	553.9	541.4	527.3	517.3
12.5°	640.2	628.1	613.3	599.3	584.9	570.9	557.3	546.0	531.3	516.8	505.0
15°	652.6	639.7	621.7	601.8	583.2	565.0	549.4	535.3	516.2	498.7	484.2
17.5°	662.9	645.1	625.8	602.7	581.2	558.1	538.0	520.0	498.6	477.6	460.5
20°	666.2	648.5	626.2	603.1	577.7	550.5	528.8	509.3	486.4	463.5	443.9
22.5°	664.1	650.4	625.6	598.0	572.0	543.5	519.0	496.3	470.9	447.5	424.9
25°	650.3	645.6	622.2	592.0	562.3	529.3	500.8	476.0	447.1	422.1	397.4
27.5°	618.1	628.3	613.7	581.6	548.5	513.2	481.2	453.0	422.9	394.8	370.2
30°	587.1	610.4	604.2	574.4	537.4	502.7	466.8	437.3	405.3	376.3	352.1
32.5°	544.8	583.2	589.3	564.4	526.2	487.9	450.4	421.0	387.5	357.1	333.4
35°	477.2	534.7	561.1	545.3	507.0	465.6	427.0	392.7	359.0	329.0	305.5
37.5°	396.7	475.0	519.0	520.1	484.9	442.0	399.8	365.8	331.4	301.9	276.5
40°	344.4	429.3	486.6	499.3	469.6	423.3	380.6	345.9	312.4	283.4	254.3
42.5°	297.5	382.0	452.5	474.6	451.0	404.9	362.1	326.0	293.3	265.9	236.1
45°	240.6	314.5	392.1	431.6	418.5	375.9	330.7	296.3	265.6	241.9	213.4
47.5°	202.9	255.0	330.2	383.6	383.4	344.5	300.0	267.1	238.6	216.4	193.3
50°	181.5	226.9	290.4	351.0	356.1	323.5	281.2	248.6	222.0	198.7	180.1
52.5°	162.2	199.7	256.8	315.0	329.4	301.1	260.1	230.0	204.1	182.7	166.9
55°	137.1	166.1	209.5	263.8	285.8	265.8	229.4	201.2	180.3	162.3	148.6
57.5°	116.0	137.7	172.5	216.3	241.8	229.3	199.2	176.3	158.4	142.2	131.4
60°	102.7	120.5	150.0	186.6	214.7	206.0	180.3	159.0	143.8	129.7	119.5
62.5°	90.1	105.5	130.8	160.5	186.2	182.6	161.7	143.8	130.4	117.6	109.0
65°	72.6	83.7	103.5	126.7	147.5	149.2	134.1	122.0	110.1	100.0	92.3
67.5°	57.8	65.1	79.0	98.6	114.1	119.7	110.5	101.2	91.7	83.9	77.2
70°	48.7	54.6	64.7	80.6	94.9	100.7	95.4	88.2	80.0	73.5	67.8
72.5°	39.4	45.2	52.7	64.3	76.5	82.9	81.0	75.9	69.2	63.8	58.5
75°	29.7	31.5	36.6	44.4	54.0	59.5	60.8	58.1	52.8	48.7	45.5
77.5°	22.0	23.1	25.5	29.5	35.8	40.7	42.7	42.4	38.7	36.4	33.4
80°	17.6	18.2	19.4	21.1	25.8	30.7	32.1	32.1	29.5	28.6	25.7
82.5°	13.3	13.8	14.6	15.5	17.7	22.0	23.5	23.8	22.2	20.9	18.6
85°	7.7	7.4	7.8	8.4	8.8	10.0	12.3	12.7	12.3	10.8	10.2
87.5°	5.3	5.1	4.8	4.4	4.1	3.9	4.3	4.7	4.5	4.4	4.5
90°	12.9	11.5	10.2	8.4	6.5	4.6	2.7	0.8	2.7	4.6	6.5
92.5°	16.9	16.2	15.4	15.2	15.3	15.5	15.7	15.8	15.7	15.5	15.3
95°	28.2	27.0	25.7	28.1	33.8	39.6	45.4	51.1	45.4	39.6	33.8
97.5°	35.4	32.5	29.7	36.4	52.7	69.0	85.2	101.4	85.2	69.0	52.7
100°	38.9	35.9	33.0	43.4	67.3	91.3	115.2	139.2	115.2	91.3	67.3
102.5°	95.7	120.6	145.5	160.4	165.5	170.6	175.6	180.7	175.6	170.6	165.5
105°	143.4	191.1	238.8	260.0	254.8	249.5	244.3	239.0	244.3	249.5	254.8
107.5°	181.6	238.8	296.0	322.5	318.2	314.0	309.8	305.6	309.8	314.0	318.2
110°	238.6	289.1	339.6	363.0	359.4	355.7	352.1	348.4	352.1	355.7	359.4



TEST NUMBER: P331633-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	372.0	384.5	397.0	401.6	398.4	395.1	391.8	388.6	391.8	395.1	398.4
115°	476.5	472.1	467.7	464.0	461.1	458.1	455.1	452.1	455.1	458.1	461.1
117.5°	531.4	528.4	525.4	522.2	518.9	515.6	512.2	508.9	512.2	515.6	518.9
120°	570.1	567.0	563.8	560.9	558.3	555.7	553.0	550.4	553.0	555.7	558.3
122.5°	606.7	603.2	599.8	596.7	593.9	591.2	588.4	585.7	588.4	591.2	593.9
125°	657.8	654.5	651.2	648.4	646.1	643.9	641.5	639.3	641.5	643.9	646.1
127.5°	705.4	702.9	700.4	697.9	695.4	692.9	690.4	687.9	690.4	692.9	695.4
130°	736.1	734.2	732.3	729.9	727.1	724.3	721.5	718.8	721.5	724.3	727.1
132.5°	765.7	763.8	761.8	759.7	757.3	754.9	752.5	750.2	752.5	754.9	757.3
135°	807.6	806.0	804.4	802.3	799.4	796.7	793.8	791.1	793.8	796.7	799.4
137.5°	845.7	843.9	842.1	840.2	838.3	836.4	834.4	832.4	834.4	836.4	838.3
140°	870.6	868.7	866.8	865.0	863.7	862.3	860.9	859.5	860.9	862.3	863.7
142.5°	893.3	891.0	888.9	887.2	885.9	884.7	883.4	882.1	883.4	884.7	885.9
145°	924.3	921.4	918.3	917.0	917.1	917.3	917.5	917.7	917.5	917.3	917.1
147.5°	953.0	950.0	947.1	946.0	946.7	947.4	948.0	948.6	948.0	947.4	946.7
150°	970.3	967.5	964.7	963.9	965.1	966.3	967.6	968.8	967.6	966.3	965.1
152.5°	986.3	983.6	980.9	980.3	981.7	983.0	984.4	985.8	984.4	983.0	981.7
155°	1008.7	1006.5	1004.4	1004.2	1005.7	1007.3	1008.9	1010.5	1008.9	1007.3	1005.7
157.5°	1027.5	1026.1	1024.6	1024.5	1025.8	1027.2	1028.5	1029.8	1028.5	1027.2	1025.8
160°	1039.1	1037.9	1036.9	1036.9	1037.9	1039.1	1040.1	1041.1	1040.1	1039.1	1037.9
162.5°	1048.7	1047.8	1046.9	1047.0	1048.0	1049.1	1050.2	1051.2	1050.2	1049.1	1048.0
165°	1061.3	1060.8	1060.2	1060.5	1061.5	1062.6	1063.7	1064.7	1063.7	1062.6	1061.5
167.5°	1071.3	1070.8	1070.3	1070.6	1071.6	1072.7	1073.8	1074.8	1073.8	1072.7	1071.6
170°	1076.6	1076.2	1075.9	1076.2	1077.3	1078.3	1079.3	1080.5	1079.3	1078.3	1077.3
172.5°	1080.4	1080.0	1079.7	1080.0	1081.1	1082.1	1083.1	1084.2	1083.1	1082.1	1081.1
175°	1084.4	1084.1	1083.7	1084.2	1085.4	1086.7	1087.9	1089.1	1087.9	1086.7	1085.4
177.5°	1085.8	1085.7	1085.5	1086.0	1086.9	1088.0	1088.9	1089.9	1088.9	1088.0	1086.9
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8



TEST NUMBER: P331633-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	554.9	553.8	551.7	548.6	546.7	543.5	541.3	542.5	542.9	542.5	542.3
5°	540.0	535.9	530.2	524.7	519.6	514.2	511.0	509.7	507.0	505.4	504.5
7.5°	521.9	514.9	506.9	497.3	489.2	480.7	476.4	474.2	468.6	465.6	463.0
10°	508.5	497.3	489.3	476.8	469.2	458.1	450.4	450.6	443.0	438.7	435.6
12.5°	493.6	481.4	468.0	456.8	446.2	437.2	428.0	424.3	416.2	412.1	403.6
15°	469.0	454.7	440.7	425.4	414.7	400.7	387.4	371.2	358.1	346.7	343.6
17.5°	442.1	424.4	410.3	392.4	373.9	350.6	335.2	325.7	317.9	311.9	307.4
20°	423.6	405.6	390.5	363.6	338.7	322.9	311.6	304.3	296.1	289.6	286.1
22.5°	404.2	385.5	364.9	334.8	315.4	302.7	292.7	284.3	278.7	273.7	270.4
25°	376.7	356.1	322.3	301.6	285.9	272.6	265.6	260.5	254.7	247.8	244.7
27.5°	347.6	315.0	290.6	275.2	260.3	251.7	245.3	237.7	232.5	229.4	226.1
30°	325.8	293.2	274.2	257.4	246.8	237.2	229.8	225.5	220.4	215.2	213.0
32.5°	301.6	275.5	257.3	243.3	232.6	224.4	218.5	211.5	207.9	204.7	200.2
35°	271.5	251.7	235.1	223.8	213.5	206.9	200.1	196.0	189.3	186.6	184.9
37.5°	246.0	228.9	216.5	204.5	196.4	189.1	184.9	178.3	175.5	171.6	167.9
40°	231.5	214.7	202.9	193.0	184.0	178.6	173.3	168.0	163.7	162.0	157.5
42.5°	216.9	203.2	191.2	180.6	174.5	168.7	162.0	158.2	153.7	150.8	148.1
45°	196.6	184.4	174.3	165.5	158.8	152.7	148.4	142.0	139.5	133.8	131.4
47.5°	178.7	167.5	157.7	149.4	142.9	139.0	132.7	127.6	123.6	120.0	117.0
50°	166.1	156.6	147.2	139.8	134.0	128.3	121.8	119.3	113.0	111.2	109.5
52.5°	154.5	145.5	137.0	129.7	123.8	118.3	112.6	109.3	105.0	103.3	102.0
55°	138.3	129.7	121.5	115.0	109.2	103.5	100.0	95.8	93.8	92.5	90.9
57.5°	122.0	114.3	108.0	101.4	95.5	91.0	87.0	84.5	82.5	80.7	78.8
60°	111.7	104.3	98.6	92.5	86.4	82.7	79.6	76.6	74.3	71.5	70.8
62.5°	100.7	94.2	89.0	83.1	77.8	74.5	71.5	68.7	65.9	61.9	60.8
65°	85.7	80.6	75.1	70.2	65.5	62.2	57.9	54.8	53.6	53.2	53.0
67.5°	72.1	67.2	62.5	57.5	53.3	50.2	48.0	47.5	46.7	46.5	45.9
70°	62.9	58.5	53.8	49.1	44.9	44.4	43.7	42.8	41.8	41.5	41.1
72.5°	54.8	50.2	45.5	41.8	40.0	39.3	38.5	37.6	37.0	36.6	36.4
75°	42.0	37.7	34.6	33.2	32.3	31.7	30.5	30.0	29.5	28.9	28.8
77.5°	30.3	27.8	26.4	25.6	24.5	23.9	23.2	22.6	22.2	22.1	21.8
80°	23.1	21.9	20.9	19.7	19.4	18.6	18.4	17.8	18.0	17.4	17.4
82.5°	17.9	16.4	15.6	15.1	14.6	14.0	13.9	13.6	13.6	13.2	13.2
85°	9.2	8.8	8.4	8.0	8.0	7.4	7.7	7.4	7.4	7.1	6.9
87.5°	4.6	4.8	4.8	5.1	5.3	5.5	5.7	5.7	5.9	6.0	6.0
90°	8.4	10.2	11.5	12.9	14.3	15.8	16.6	17.5	18.3	19.2	19.8
92.5°	15.2	15.4	16.2	16.9	17.6	18.3	18.7	19.1	19.6	20.1	20.4
95°	28.1	25.7	27.0	28.2	29.4	30.7	31.5	32.4	33.3	34.2	34.5
97.5°	36.4	29.7	32.5	35.4	38.2	41.1	41.8	42.4	43.1	43.8	44.3
100°	43.4	33.0	35.9	38.9	41.8	44.9	46.2	47.6	49.0	50.5	51.3
102.5°	160.4	145.5	120.6	95.7	70.9	46.1	47.9	49.7	51.6	53.4	54.5
105°	260.0	238.8	191.1	143.4	95.7	48.0	49.9	51.8	53.7	55.6	57.0
107.5°	322.5	296.0	238.8	181.6	124.3	67.2	65.2	63.2	61.3	59.3	58.7
110°	363.0	339.6	289.1	238.6	188.1	137.6	120.1	102.6	85.2	67.7	59.3



TEST NUMBER: P331633-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	401.6	397.0	384.5	372.0	359.6	347.1	283.4	219.6	155.8	92.1	60.5
115°	464.0	467.7	472.1	476.5	480.8	485.2	404.2	323.4	242.5	161.5	114.8
117.5°	522.2	525.4	528.4	531.4	534.4	537.4	517.8	498.3	478.7	459.1	428.6
120°	560.9	563.8	567.0	570.1	573.3	576.4	578.5	580.6	582.7	584.8	574.0
122.5°	596.7	599.8	603.2	606.7	610.1	613.5	614.8	616.0	617.3	618.5	616.9
125°	648.4	651.2	654.5	657.8	661.2	664.4	665.7	666.9	668.1	669.3	670.2
127.5°	697.9	700.4	702.9	705.4	707.9	710.4	712.1	713.9	715.7	717.6	718.4
130°	729.9	732.3	734.2	736.1	738.0	739.9	741.8	743.8	745.7	747.6	748.6
132.5°	759.7	761.8	763.8	765.7	767.6	769.5	771.2	772.8	774.5	776.1	776.8
135°	802.3	804.4	806.0	807.6	809.2	810.7	812.4	814.2	816.0	817.7	818.4
137.5°	840.2	842.1	843.9	845.7	847.5	849.3	850.9	852.6	854.4	856.1	856.7
140°	865.0	866.8	868.7	870.6	872.5	874.4	876.0	877.5	879.2	880.7	881.1
142.5°	887.2	888.9	891.0	893.3	895.5	897.7	899.1	900.5	902.0	903.4	903.7
145°	917.0	918.3	921.4	924.3	927.3	930.2	931.4	932.7	933.9	935.1	935.3
147.5°	946.0	947.1	950.0	953.0	956.0	958.9	959.8	960.7	961.6	962.5	962.6
150°	963.9	964.7	967.5	970.3	973.1	975.9	976.9	977.9	979.0	980.1	980.2
152.5°	980.3	980.9	983.6	986.3	988.9	991.6	992.6	993.7	994.7	995.7	995.7
155°	1004.2	1004.4	1006.5	1008.7	1010.7	1012.8	1013.8	1014.9	1016.0	1017.0	1016.8
157.5°	1024.5	1024.6	1026.1	1027.5	1029.0	1030.4	1031.7	1032.8	1034.0	1035.2	1035.1
160°	1036.9	1036.9	1037.9	1039.1	1040.1	1041.1	1042.2	1043.2	1044.3	1045.3	1045.3
162.5°	1047.0	1046.9	1047.8	1048.7	1049.6	1050.6	1051.7	1052.9	1054.1	1055.3	1055.2
165°	1060.5	1060.2	1060.8	1061.3	1061.9	1062.4	1063.6	1064.8	1066.0	1067.2	1067.2
167.5°	1070.6	1070.3	1070.8	1071.3	1071.8	1072.3	1073.5	1074.7	1075.9	1077.2	1076.9
170°	1076.2	1075.9	1076.2	1076.6	1076.9	1077.3	1078.5	1079.8	1081.0	1082.2	1082.0
172.5°	1080.0	1079.7	1080.0	1080.4	1080.7	1081.1	1082.3	1083.5	1084.8	1086.0	1085.8
175°	1084.2	1083.7	1084.1	1084.4	1084.8	1085.1	1086.4	1087.6	1088.8	1090.0	1089.8
177.5°	1086.0	1085.5	1085.7	1085.8	1086.0	1086.1	1087.1	1088.0	1089.1	1090.0	1089.9
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8



TEST NUMBER: P331633-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	540.5	540.8	540.4	540.6	540.4	540.8	540.5	542.3	542.5	542.9	542.5
5°	503.6	501.3	500.8	500.3	500.8	501.3	503.6	504.5	505.4	507.0	509.7
7.5°	459.6	459.3	458.2	456.8	458.2	459.3	459.6	463.0	465.6	468.6	474.2
10°	431.3	430.2	430.1	428.7	430.1	430.2	431.3	435.6	438.7	443.0	450.6
12.5°	398.0	391.8	391.2	387.7	391.2	391.8	398.0	403.6	412.1	416.2	424.3
15°	339.0	337.8	333.8	331.3	333.8	337.8	339.0	343.6	346.7	358.1	371.2
17.5°	305.1	301.3	300.1	299.5	300.1	301.3	305.1	307.4	311.9	317.9	325.7
20°	283.4	279.9	279.3	278.9	279.3	279.9	283.4	286.1	289.6	296.1	304.3
22.5°	268.4	264.7	263.2	262.0	263.2	264.7	268.4	270.4	273.7	278.7	284.3
25°	242.7	241.3	240.6	240.1	240.6	241.3	242.7	244.7	247.8	254.7	260.5
27.5°	222.7	219.6	219.0	218.0	219.0	219.6	222.7	226.1	229.4	232.5	237.7
30°	211.2	210.3	208.9	207.7	208.9	210.3	211.2	213.0	215.2	220.4	225.5
32.5°	197.8	196.9	195.7	195.2	195.7	196.9	197.8	200.2	204.7	207.9	211.5
35°	182.9	180.1	178.9	177.2	178.9	180.1	182.9	184.9	186.6	189.3	196.0
37.5°	167.1	165.7	164.0	164.6	164.0	165.7	167.1	167.9	171.6	175.5	178.3
40°	154.9	153.9	153.5	153.3	153.5	153.9	154.9	157.5	162.0	163.7	168.0
42.5°	145.2	142.5	141.5	141.5	141.5	142.5	145.2	148.1	150.8	153.7	158.2
45°	130.4	127.9	126.1	126.3	126.1	127.9	130.4	131.4	133.8	139.5	142.0
47.5°	115.4	115.3	114.2	114.5	114.2	115.3	115.4	117.0	120.0	123.6	127.6
50°	108.1	107.0	106.2	106.4	106.2	107.0	108.1	109.5	111.2	113.0	119.3
52.5°	101.3	100.2	99.6	100.5	99.6	100.2	101.3	102.0	103.3	105.0	109.3
55°	90.0	88.8	88.6	88.4	88.6	88.8	90.0	90.9	92.5	93.8	95.8
57.5°	77.3	76.5	75.3	74.9	75.3	76.5	77.3	78.8	80.7	82.5	84.5
60°	68.3	66.7	64.7	64.6	64.7	66.7	68.3	70.8	71.5	74.3	76.6
62.5°	59.9	59.7	59.2	59.2	59.2	59.7	59.9	60.8	61.9	65.9	68.7
65°	52.6	52.4	52.6	52.8	52.6	52.4	52.6	53.0	53.2	53.6	54.8
67.5°	45.8	45.5	45.1	45.3	45.1	45.5	45.8	45.9	46.5	46.7	47.5
70°	40.6	40.5	40.3	40.3	40.3	40.5	40.6	41.1	41.5	41.8	42.8
72.5°	35.6	35.6	35.5	35.3	35.5	35.6	35.6	36.4	36.6	37.0	37.6
75°	28.6	28.2	28.2	28.2	28.2	28.2	28.6	28.8	28.9	29.5	30.0
77.5°	21.8	21.5	21.4	21.2	21.4	21.5	21.8	21.8	22.1	22.2	22.6
80°	17.2	17.0	16.8	16.8	16.8	17.0	17.2	17.4	17.4	18.0	17.8
82.5°	13.2	12.9	12.9	12.7	12.9	12.9	13.2	13.2	13.2	13.6	13.6
85°	7.1	7.2	7.1	7.4	7.1	7.2	7.1	6.9	7.1	7.4	7.4
87.5°	6.1	6.0	6.2	6.1	6.2	6.0	6.1	6.0	6.0	5.9	5.7
90°	20.1	20.5	20.9	21.3	20.9	20.5	20.1	19.8	19.2	18.3	17.5
92.5°	20.6	20.8	21.0	21.3	21.0	20.8	20.6	20.4	20.1	19.6	19.1
95°	34.4	34.2	34.0	33.8	34.0	34.2	34.4	34.5	34.2	33.3	32.4
97.5°	44.5	44.7	44.9	45.1	44.9	44.7	44.5	44.3	43.8	43.1	42.4
100°	51.7	52.0	52.3	52.7	52.3	52.0	51.7	51.3	50.5	49.0	47.6
102.5°	55.0	55.4	56.0	56.5	56.0	55.4	55.0	54.5	53.4	51.6	49.7
105°	57.7	58.4	59.1	59.8	59.1	58.4	57.7	57.0	55.6	53.7	51.8
107.5°	59.4	60.1	60.8	61.5	60.8	60.1	59.4	58.7	59.3	61.3	63.2
110°	60.0	60.7	61.4	62.2	61.4	60.7	60.0	59.3	67.7	85.2	102.6



TEST NUMBER: P331633-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	61.0	61.6	62.2	62.8	62.2	61.6	61.0	60.5	92.1	155.8	219.6
115°	102.2	89.6	77.1	64.5	77.1	89.6	102.2	114.8	161.5	242.5	323.4
117.5°	387.3	345.9	304.6	263.3	304.6	345.9	387.3	428.6	459.1	478.7	498.3
120°	550.4	526.8	503.3	479.7	503.3	526.8	550.4	574.0	584.8	582.7	580.6
122.5°	612.3	607.7	603.1	598.6	603.1	607.7	612.3	616.9	618.5	617.3	616.0
125°	670.7	671.2	671.8	672.4	671.8	671.2	670.7	670.2	669.3	668.1	666.9
127.5°	718.6	718.7	718.8	718.8	718.8	718.7	718.6	718.4	717.6	715.7	713.9
130°	748.4	748.1	748.0	747.8	748.0	748.1	748.4	748.6	747.6	745.7	743.8
132.5°	776.6	776.4	776.3	776.1	776.3	776.4	776.6	776.8	776.1	774.5	772.8
135°	818.0	817.7	817.3	817.0	817.3	817.7	818.0	818.4	817.7	816.0	814.2
137.5°	856.1	855.5	854.9	854.3	854.9	855.5	856.1	856.7	856.1	854.4	852.6
140°	880.2	879.3	878.5	877.5	878.5	879.3	880.2	881.1	880.7	879.2	877.5
142.5°	902.8	902.0	901.1	900.2	901.1	902.0	902.8	903.7	903.4	902.0	900.5
145°	934.4	933.6	932.7	931.9	932.7	933.6	934.4	935.3	935.1	933.9	932.7
147.5°	961.8	961.1	960.4	959.7	960.4	961.1	961.8	962.6	962.5	961.6	960.7
150°	979.3	978.4	977.5	976.6	977.5	978.4	979.3	980.2	980.1	979.0	977.9
152.5°	994.5	993.4	992.3	991.1	992.3	993.4	994.5	995.7	995.7	994.7	993.7
155°	1015.5	1014.0	1012.6	1011.2	1012.6	1014.0	1015.5	1016.8	1017.0	1016.0	1014.9
157.5°	1033.7	1032.3	1031.0	1029.7	1031.0	1032.3	1033.7	1035.1	1035.2	1034.0	1032.8
160°	1044.0	1042.8	1041.6	1040.3	1041.6	1042.8	1044.0	1045.3	1045.3	1044.3	1043.2
162.5°	1053.7	1052.1	1050.7	1049.1	1050.7	1052.1	1053.7	1055.2	1055.3	1054.1	1052.9
165°	1066.0	1064.8	1063.6	1062.4	1063.6	1064.8	1066.0	1067.2	1067.2	1066.0	1064.8
167.5°	1075.4	1073.8	1072.3	1070.7	1072.3	1073.8	1075.4	1076.9	1077.2	1075.9	1074.7
170°	1080.5	1078.8	1077.3	1075.7	1077.3	1078.8	1080.5	1082.0	1082.2	1081.0	1079.8
172.5°	1084.2	1082.6	1081.1	1079.5	1081.1	1082.6	1084.2	1085.8	1086.0	1084.8	1083.5
175°	1088.0	1086.3	1084.5	1082.8	1084.5	1086.3	1088.0	1089.8	1090.0	1088.8	1087.6
177.5°	1088.6	1087.4	1086.1	1084.9	1086.1	1087.4	1088.6	1089.9	1090.0	1089.1	1088.0
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8



TEST NUMBER: P331633-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	541.3	543.5	546.7	548.6	551.7	553.8	554.9	556.9	558.0	562.0	566.0
5°	511.0	514.2	519.6	524.7	530.2	535.9	540.0	544.7	549.0	556.4	564.2
7.5°	476.4	480.7	489.2	497.3	506.9	514.9	521.9	529.9	537.1	547.8	558.9
10°	450.4	458.1	469.2	476.8	489.3	497.3	508.5	517.3	527.3	541.4	553.9
12.5°	428.0	437.2	446.2	456.8	468.0	481.4	493.6	505.0	516.8	531.3	546.0
15°	387.4	400.7	414.7	425.4	440.7	454.7	469.0	484.2	498.7	516.2	535.3
17.5°	335.2	350.6	373.9	392.4	410.3	424.4	442.1	460.5	477.6	498.6	520.0
20°	311.6	322.9	338.7	363.6	390.5	405.6	423.6	443.9	463.5	486.4	509.3
22.5°	292.7	302.7	315.4	334.8	364.9	385.5	404.2	424.9	447.5	470.9	496.3
25°	265.6	272.6	285.9	301.6	322.3	356.1	376.7	397.4	422.1	447.1	476.0
27.5°	245.3	251.7	260.3	275.2	290.6	315.0	347.6	370.2	394.8	422.9	453.0
30°	229.8	237.2	246.8	257.4	274.2	293.2	325.8	352.1	376.3	405.3	437.3
32.5°	218.5	224.4	232.6	243.3	257.3	275.5	301.6	333.4	357.1	387.5	421.0
35°	200.1	206.9	213.5	223.8	235.1	251.7	271.5	305.5	329.0	359.0	392.7
37.5°	184.9	189.1	196.4	204.5	216.5	228.9	246.0	276.5	301.9	331.4	365.8
40°	173.3	178.6	184.0	193.0	202.9	214.7	231.5	254.3	283.4	312.4	345.9
42.5°	162.0	168.7	174.5	180.6	191.2	203.2	216.9	236.1	265.9	293.3	326.0
45°	148.4	152.7	158.8	165.5	174.3	184.4	196.6	213.4	241.9	265.6	296.3
47.5°	132.7	139.0	142.9	149.4	157.7	167.5	178.7	193.3	216.4	238.6	267.1
50°	121.8	128.3	134.0	139.8	147.2	156.6	166.1	180.1	198.7	222.0	248.6
52.5°	112.6	118.3	123.8	129.7	137.0	145.5	154.5	166.9	182.7	204.1	230.0
55°	100.0	103.5	109.2	115.0	121.5	129.7	138.3	148.6	162.3	180.3	201.2
57.5°	87.0	91.0	95.5	101.4	108.0	114.3	122.0	131.4	142.2	158.4	176.3
60°	79.6	82.7	86.4	92.5	98.6	104.3	111.7	119.5	129.7	143.8	159.0
62.5°	71.5	74.5	77.8	83.1	89.0	94.2	100.7	109.0	117.6	130.4	143.8
65°	57.9	62.2	65.5	70.2	75.1	80.6	85.7	92.3	100.0	110.1	122.0
67.5°	48.0	50.2	53.3	57.5	62.5	67.2	72.1	77.2	83.9	91.7	101.2
70°	43.7	44.4	44.9	49.1	53.8	58.5	62.9	67.8	73.5	80.0	88.2
72.5°	38.5	39.3	40.0	41.8	45.5	50.2	54.8	58.5	63.8	69.2	75.9
75°	30.5	31.7	32.3	33.2	34.6	37.7	42.0	45.5	48.7	52.8	58.1
77.5°	23.2	23.9	24.5	25.6	26.4	27.8	30.3	33.4	36.4	38.7	42.4
80°	18.4	18.6	19.4	19.7	20.9	21.9	23.1	25.7	28.6	29.5	32.1
82.5°	13.9	14.0	14.6	15.1	15.6	16.4	17.9	18.6	20.9	22.2	23.8
85°	7.7	7.4	8.0	8.0	8.4	8.8	9.2	10.2	10.8	12.3	12.7
87.5°	5.7	5.5	5.3	5.1	4.8	4.8	4.6	4.5	4.4	4.5	4.7
90°	16.6	15.8	14.3	12.9	11.5	10.2	8.4	6.5	4.6	2.7	0.8
92.5°	18.7	18.3	17.6	16.9	16.2	15.4	15.2	15.3	15.5	15.7	15.8
95°	31.5	30.7	29.4	28.2	27.0	25.7	28.1	33.8	39.6	45.4	51.1
97.5°	41.8	41.1	38.2	35.4	32.5	29.7	36.4	52.7	69.0	85.2	101.4
100°	46.2	44.9	41.8	38.9	35.9	33.0	43.4	67.3	91.3	115.2	139.2
102.5°	47.9	46.1	70.9	95.7	120.6	145.5	160.4	165.5	170.6	175.6	180.7
105°	49.9	48.0	95.7	143.4	191.1	238.8	260.0	254.8	249.5	244.3	239.0
107.5°	65.2	67.2	124.3	181.6	238.8	296.0	322.5	318.2	314.0	309.8	305.6
110°	120.1	137.6	188.1	238.6	289.1	339.6	363.0	359.4	355.7	352.1	348.4



TEST NUMBER: P331633-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	283.4	347.1	359.6	372.0	384.5	397.0	401.6	398.4	395.1	391.8	388.6
115°	404.2	485.2	480.8	476.5	472.1	467.7	464.0	461.1	458.1	455.1	452.1
117.5°	517.8	537.4	534.4	531.4	528.4	525.4	522.2	518.9	515.6	512.2	508.9
120°	578.5	576.4	573.3	570.1	567.0	563.8	560.9	558.3	555.7	553.0	550.4
122.5°	614.8	613.5	610.1	606.7	603.2	599.8	596.7	593.9	591.2	588.4	585.7
125°	665.7	664.4	661.2	657.8	654.5	651.2	648.4	646.1	643.9	641.5	639.3
127.5°	712.1	710.4	707.9	705.4	702.9	700.4	697.9	695.4	692.9	690.4	687.9
130°	741.8	739.9	738.0	736.1	734.2	732.3	729.9	727.1	724.3	721.5	718.8
132.5°	771.2	769.5	767.6	765.7	763.8	761.8	759.7	757.3	754.9	752.5	750.2
135°	812.4	810.7	809.2	807.6	806.0	804.4	802.3	799.4	796.7	793.8	791.1
137.5°	850.9	849.3	847.5	845.7	843.9	842.1	840.2	838.3	836.4	834.4	832.4
140°	876.0	874.4	872.5	870.6	868.7	866.8	865.0	863.7	862.3	860.9	859.5
142.5°	899.1	897.7	895.5	893.3	891.0	888.9	887.2	885.9	884.7	883.4	882.1
145°	931.4	930.2	927.3	924.3	921.4	918.3	917.0	917.1	917.3	917.5	917.7
147.5°	959.8	958.9	956.0	953.0	950.0	947.1	946.0	946.7	947.4	948.0	948.6
150°	976.9	975.9	973.1	970.3	967.5	964.7	963.9	965.1	966.3	967.6	968.8
152.5°	992.6	991.6	988.9	986.3	983.6	980.9	980.3	981.7	983.0	984.4	985.8
155°	1013.8	1012.8	1010.7	1008.7	1006.5	1004.4	1004.2	1005.7	1007.3	1008.9	1010.5
157.5°	1031.7	1030.4	1029.0	1027.5	1026.1	1024.6	1024.5	1025.8	1027.2	1028.5	1029.8
160°	1042.2	1041.1	1040.1	1039.1	1037.9	1036.9	1036.9	1037.9	1039.1	1040.1	1041.1
162.5°	1051.7	1050.6	1049.6	1048.7	1047.8	1046.9	1047.0	1048.0	1049.1	1050.2	1051.2
165°	1063.6	1062.4	1061.9	1061.3	1060.8	1060.2	1060.5	1061.5	1062.6	1063.7	1064.7
167.5°	1073.5	1072.3	1071.8	1071.3	1070.8	1070.3	1070.6	1071.6	1072.7	1073.8	1074.8
170°	1078.5	1077.3	1076.9	1076.6	1076.2	1075.9	1076.2	1077.3	1078.3	1079.3	1080.5
172.5°	1082.3	1081.1	1080.7	1080.4	1080.0	1079.7	1080.0	1081.1	1082.1	1083.1	1084.2
175°	1086.4	1085.1	1084.8	1084.4	1084.1	1083.7	1084.2	1085.4	1086.7	1087.9	1089.1
177.5°	1087.1	1086.1	1086.0	1085.8	1085.7	1085.5	1086.0	1086.9	1088.0	1088.9	1089.9
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8



TEST NUMBER: P331633-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	566.2	566.6	569.7	571.2	573.9	575.1	576.4	576.0	576.0	576.6	581.0
5°	567.4	571.3	577.1	582.8	588.3	593.0	596.2	599.3	600.5	606.1	611.1
7.5°	565.3	572.6	582.2	590.9	601.2	609.3	616.0	622.2	626.3	634.6	643.0
10°	562.7	572.8	583.8	595.0	609.2	620.0	630.9	639.4	642.0	654.4	661.4
12.5°	557.3	570.9	584.9	599.3	613.3	628.1	640.2	648.6	658.2	669.3	682.3
15°	549.4	565.0	583.2	601.8	621.7	639.7	652.6	667.3	677.9	690.0	701.4
17.5°	538.0	558.1	581.2	602.7	625.8	645.1	662.9	676.9	684.3	691.3	692.9
20°	528.8	550.5	577.7	603.1	626.2	648.5	666.2	677.9	679.8	680.0	669.7
22.5°	519.0	543.5	572.0	598.0	625.6	650.4	664.1	669.1	661.3	648.1	628.0
25°	500.8	529.3	562.3	592.0	622.2	645.6	650.3	641.5	614.3	585.7	549.6
27.5°	481.2	513.2	548.5	581.6	613.7	628.3	618.1	586.3	537.4	494.8	443.2
30°	466.8	502.7	537.4	574.4	604.2	610.4	587.1	540.4	483.3	419.1	367.6
32.5°	450.4	487.9	526.2	564.4	589.3	583.2	544.8	487.2	420.3	357.1	308.6
35°	427.0	465.6	507.0	545.3	561.1	534.7	477.2	402.3	333.8	275.0	241.5
37.5°	399.8	442.0	484.9	520.1	519.0	475.0	396.7	319.3	261.8	227.0	203.2
40°	380.6	423.3	469.6	499.3	486.6	429.3	344.4	271.5	229.4	201.6	184.3
42.5°	362.1	404.9	451.0	474.6	452.5	382.0	297.5	240.3	205.6	184.0	169.9
45°	330.7	375.9	418.5	431.6	392.1	314.5	240.6	199.1	176.0	160.0	150.2
47.5°	300.0	344.5	383.4	383.6	330.2	255.0	202.9	172.3	152.6	140.2	133.1
50°	281.2	323.5	356.1	351.0	290.4	226.9	181.5	155.1	138.7	129.1	121.7
52.5°	260.1	301.1	329.4	315.0	256.8	199.7	162.2	140.1	126.5	118.1	111.5
55°	229.4	265.8	285.8	263.8	209.5	166.1	137.1	119.7	109.5	102.5	96.8
57.5°	199.2	229.3	241.8	216.3	172.5	137.7	116.0	102.9	92.8	87.7	84.8
60°	180.3	206.0	214.7	186.6	150.0	120.5	102.7	90.6	83.1	79.8	76.9
62.5°	161.7	182.6	186.2	160.5	130.8	105.5	90.1	79.9	75.0	71.8	69.1
65°	134.1	149.2	147.5	126.7	103.5	83.7	72.6	66.3	62.6	58.1	53.2
67.5°	110.5	119.7	114.1	98.6	79.0	65.1	57.8	53.0	48.4	44.2	43.0
70°	95.4	100.7	94.9	80.6	64.7	54.6	48.7	43.0	40.3	39.3	37.5
72.5°	81.0	82.9	76.5	64.3	52.7	45.2	39.4	36.3	34.8	34.0	32.9
75°	60.8	59.5	54.0	44.4	36.6	31.5	29.7	28.6	27.6	26.8	26.2
77.5°	42.7	40.7	35.8	29.5	25.5	23.1	22.0	21.4	20.9	20.5	19.9
80°	32.1	30.7	25.8	21.1	19.4	18.2	17.6	16.8	16.8	16.4	15.8
82.5°	23.5	22.0	17.7	15.5	14.6	13.8	13.3	12.9	12.7	12.8	12.4
85°	12.3	10.0	8.8	8.4	7.8	7.4	7.7	7.2	7.2	7.2	7.1
87.5°	4.3	3.9	4.1	4.4	4.8	5.1	5.3	5.5	5.9	5.9	6.3
90°	2.7	4.6	6.5	8.4	10.2	11.5	12.9	14.3	15.8	16.6	17.5
92.5°	15.7	15.5	15.3	15.2	15.4	16.2	16.9	17.6	18.3	18.7	19.1
95°	45.4	39.6	33.8	28.1	25.7	27.0	28.2	29.4	30.7	31.5	32.4
97.5°	85.2	69.0	52.7	36.4	29.7	32.5	35.4	38.2	41.1	41.8	42.4
100°	115.2	91.3	67.3	43.4	33.0	35.9	38.9	41.8	44.9	46.2	47.6
102.5°	175.6	170.6	165.5	160.4	145.5	120.6	95.7	70.9	46.1	47.9	49.7
105°	244.3	249.5	254.8	260.0	238.8	191.1	143.4	95.7	48.0	49.9	51.8
107.5°	309.8	314.0	318.2	322.5	296.0	238.8	181.6	124.3	67.2	65.2	63.2
110°	352.1	355.7	359.4	363.0	339.6	289.1	238.6	188.1	137.6	120.1	102.6



TEST NUMBER: P331633-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	391.8	395.1	398.4	401.6	397.0	384.5	372.0	359.6	347.1	283.4	219.6
115°	455.1	458.1	461.1	464.0	467.7	472.1	476.5	480.8	485.2	404.2	323.4
117.5°	512.2	515.6	518.9	522.2	525.4	528.4	531.4	534.4	537.4	517.8	498.3
120°	553.0	555.7	558.3	560.9	563.8	567.0	570.1	573.3	576.4	578.5	580.6
122.5°	588.4	591.2	593.9	596.7	599.8	603.2	606.7	610.1	613.5	614.8	616.0
125°	641.5	643.9	646.1	648.4	651.2	654.5	657.8	661.2	664.4	665.7	666.9
127.5°	690.4	692.9	695.4	697.9	700.4	702.9	705.4	707.9	710.4	712.1	713.9
130°	721.5	724.3	727.1	729.9	732.3	734.2	736.1	738.0	739.9	741.8	743.8
132.5°	752.5	754.9	757.3	759.7	761.8	763.8	765.7	767.6	769.5	771.2	772.8
135°	793.8	796.7	799.4	802.3	804.4	806.0	807.6	809.2	810.7	812.4	814.2
137.5°	834.4	836.4	838.3	840.2	842.1	843.9	845.7	847.5	849.3	850.9	852.6
140°	860.9	862.3	863.7	865.0	866.8	868.7	870.6	872.5	874.4	876.0	877.5
142.5°	883.4	884.7	885.9	887.2	888.9	891.0	893.3	895.5	897.7	899.1	900.5
145°	917.5	917.3	917.1	917.0	918.3	921.4	924.3	927.3	930.2	931.4	932.7
147.5°	948.0	947.4	946.7	946.0	947.1	950.0	953.0	956.0	958.9	959.8	960.7
150°	967.6	966.3	965.1	963.9	964.7	967.5	970.3	973.1	975.9	976.9	977.9
152.5°	984.4	983.0	981.7	980.3	980.9	983.6	986.3	988.9	991.6	992.6	993.7
155°	1008.9	1007.3	1005.7	1004.2	1004.4	1006.5	1008.7	1010.7	1012.8	1013.8	1014.9
157.5°	1028.5	1027.2	1025.8	1024.5	1024.6	1026.1	1027.5	1029.0	1030.4	1031.7	1032.8
160°	1040.1	1039.1	1037.9	1036.9	1036.9	1037.9	1039.1	1040.1	1041.1	1042.2	1043.2
162.5°	1050.2	1049.1	1048.0	1047.0	1046.9	1047.8	1048.7	1049.6	1050.6	1051.7	1052.9
165°	1063.7	1062.6	1061.5	1060.5	1060.2	1060.8	1061.3	1061.9	1062.4	1063.6	1064.8
167.5°	1073.8	1072.7	1071.6	1070.6	1070.3	1070.8	1071.3	1071.8	1072.3	1073.5	1074.7
170°	1079.3	1078.3	1077.3	1076.2	1075.9	1076.2	1076.6	1076.9	1077.3	1078.5	1079.8
172.5°	1083.1	1082.1	1081.1	1080.0	1079.7	1080.0	1080.4	1080.7	1081.1	1082.3	1083.5
175°	1087.9	1086.7	1085.4	1084.2	1083.7	1084.1	1084.4	1084.8	1085.1	1086.4	1087.6
177.5°	1088.9	1088.0	1086.9	1086.0	1085.5	1085.7	1085.8	1086.0	1086.1	1087.1	1088.0
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8



TEST NUMBER: P331633-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	582.6	584.6	585.6	585.6	586.7	586.2	585.7
5°	616.0	619.7	620.6	624.1	626.6	625.9	626.2
7.5°	649.4	655.3	661.2	663.9	664.3	665.9	666.5
10°	669.9	674.8	683.9	682.6	689.4	693.4	686.9
12.5°	689.6	696.2	702.6	704.3	708.2	709.5	706.9
15°	707.4	710.9	711.3	710.3	711.5	710.5	706.8
17.5°	690.8	685.0	673.5	668.0	663.7	657.2	654.6
20°	663.2	646.4	626.8	619.0	609.8	591.9	596.2
22.5°	603.7	584.6	565.0	542.2	531.2	514.2	513.2
25°	511.3	478.2	441.8	416.4	401.5	384.5	377.0
27.5°	397.5	355.9	326.1	311.0	297.2	283.8	283.2
30°	322.7	291.4	268.4	255.5	247.0	241.3	242.5
32.5°	272.0	250.6	235.0	224.3	218.1	213.8	213.7
35°	222.4	207.7	197.7	193.2	188.7	185.6	185.8
37.5°	190.3	181.5	175.9	171.0	168.2	166.6	165.7
40°	173.8	166.6	162.3	159.4	157.0	154.9	154.5
42.5°	160.9	154.9	150.6	148.3	146.1	144.6	144.2
45°	142.8	137.8	134.0	131.4	130.4	129.1	129.1
47.5°	127.0	122.2	119.2	117.5	115.9	114.9	114.9
50°	116.4	112.6	109.9	108.9	107.5	107.0	106.8
52.5°	106.9	104.0	102.1	101.4	100.8	100.1	100.2
55°	93.8	92.3	91.5	90.9	90.0	88.8	89.5
57.5°	83.0	81.6	79.6	77.7	76.8	75.9	76.3
60°	75.3	72.6	69.8	67.7	67.1	65.3	65.3
62.5°	65.6	61.7	58.4	57.2	56.6	55.8	55.6
65°	50.5	48.9	48.1	47.4	46.9	46.9	46.6
67.5°	41.8	41.2	40.3	40.1	39.8	39.6	39.5
70°	36.9	36.2	35.8	35.6	35.2	35.4	34.8
72.5°	32.3	31.7	31.6	31.1	30.8	30.8	30.4
75°	25.4	25.4	25.2	25.1	24.6	24.5	24.6
77.5°	19.5	19.6	19.3	19.2	19.2	19.2	19.0
80°	15.7	15.8	15.7	15.4	15.2	15.4	15.2
82.5°	12.4	12.1	12.1	12.0	12.0	11.9	11.8
85°	7.1	7.2	7.1	6.9	6.9	6.9	7.1
87.5°	6.4	6.5	6.6	6.7	6.8	6.8	6.7
90°	18.3	19.2	19.8	20.1	20.5	20.9	21.3
92.5°	19.6	20.1	20.4	20.6	20.8	21.0	21.3
95°	33.3	34.2	34.5	34.4	34.2	34.0	33.8
97.5°	43.1	43.8	44.3	44.5	44.7	44.9	45.1
100°	49.0	50.5	51.3	51.7	52.0	52.3	52.7
102.5°	51.6	53.4	54.5	55.0	55.4	56.0	56.5
105°	53.7	55.6	57.0	57.7	58.4	59.1	59.8
107.5°	61.3	59.3	58.7	59.4	60.1	60.8	61.5
110°	85.2	67.7	59.3	60.0	60.7	61.4	62.2



TEST NUMBER: P331633-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	155.8	92.1	60.5	61.0	61.6	62.2	62.8
115°	242.5	161.5	114.8	102.2	89.6	77.1	64.5
117.5°	478.7	459.1	428.6	387.3	345.9	304.6	263.3
120°	582.7	584.8	574.0	550.4	526.8	503.3	479.7
122.5°	617.3	618.5	616.9	612.3	607.7	603.1	598.6
125°	668.1	669.3	670.2	670.7	671.2	671.8	672.4
127.5°	715.7	717.6	718.4	718.6	718.7	718.8	718.8
130°	745.7	747.6	748.6	748.4	748.1	748.0	747.8
132.5°	774.5	776.1	776.8	776.6	776.4	776.3	776.1
135°	816.0	817.7	818.4	818.0	817.7	817.3	817.0
137.5°	854.4	856.1	856.7	856.1	855.5	854.9	854.3
140°	879.2	880.7	881.1	880.2	879.3	878.5	877.5
142.5°	902.0	903.4	903.7	902.8	902.0	901.1	900.2
145°	933.9	935.1	935.3	934.4	933.6	932.7	931.9
147.5°	961.6	962.5	962.6	961.8	961.1	960.4	959.7
150°	979.0	980.1	980.2	979.3	978.4	977.5	976.6
152.5°	994.7	995.7	995.7	994.5	993.4	992.3	991.1
155°	1016.0	1017.0	1016.8	1015.5	1014.0	1012.6	1011.2
157.5°	1034.0	1035.2	1035.1	1033.7	1032.3	1031.0	1029.7
160°	1044.3	1045.3	1045.3	1044.0	1042.8	1041.6	1040.3
162.5°	1054.1	1055.3	1055.2	1053.7	1052.1	1050.7	1049.1
165°	1066.0	1067.2	1067.2	1066.0	1064.8	1063.6	1062.4
167.5°	1075.9	1077.2	1076.9	1075.4	1073.8	1072.3	1070.7
170°	1081.0	1082.2	1082.0	1080.5	1078.8	1077.3	1075.7
172.5°	1084.8	1086.0	1085.8	1084.2	1082.6	1081.1	1079.5
175°	1088.8	1090.0	1089.8	1088.0	1086.3	1084.5	1082.8
177.5°	1089.1	1090.0	1089.9	1088.6	1087.4	1086.1	1084.9
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8

(END OF REPORT)