

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331634-935

Luminaire Tested: **SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1**

Issue Date: 10/7/2019


Test Information

Test Method: LM-79-08
Report Number: P331634-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3823.9 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331634-935
CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331634-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	93	89	85	82	82	79	76	74	61	60	58	45	44	43	30	30	29	22
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25	19
3	77	69	62	57	69	62	56	51	48	44	41	36	33	31	24	23	22	17
4	71	61	54	48	63	55	49	44	43	39	35	32	29	27	22	21	19	15
5	65	54	47	41	58	49	43	38	39	34	31	29	26	24	20	18	17	13
6	60	49	41	36	54	44	38	33	35	30	27	26	23	21	18	17	15	12
7	56	44	37	31	50	40	33	29	32	27	24	24	21	19	17	15	14	11
8	52	40	33	28	46	36	30	26	29	24	21	22	19	17	16	14	12	10
9	48	37	30	25	43	33	27	23	27	22	19	20	17	15	15	13	11	9
10	45	33	27	22	40	30	24	20	24	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9087	9087	9087	9087
5°	10149	9144	8109	9144
10°	11262	9081	7029	9081
15°	11814	8948	5538	8948
20°	10244	8751	4792	8751
25°	6716	8480	4277	8480
30°	4521	8153	3872	8153
35°	3662	7740	3493	7740
40°	3256	7290	3231	7290
45°	2948	6766	2884	6766
50°	2683	6244	2673	6244
55°	2519	5664	2488	5664
60°	2109	5134	2086	5134
65°	1780	4661	2017	4661
70°	1643	4164	1902	4164
75°	1535	3624	1759	3624
80°	1413	2985	1562	2985
85°	1315	2353	1371	2353



TEST NUMBER: P331634-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.4	1.4
10°-20°	148.7	3.9
20°-30°	191.6	5.0
30°-40°	182.1	4.8
40°-50°	156.0	4.1
50°-60°	118.8	3.1
60°-70°	75.1	2.0
70°-80°	37.5	1.0
80°-90°	13.8	0.4
90°-100°	64.5	1.7
100°-110°	200.4	5.2
110°-120°	342.5	9.0
120°-130°	450.4	11.8
130°-140°	505.6	13.2
140°-150°	495.7	13.0
150°-160°	415.8	10.9
160°-170°	275.8	7.2
170°-180°	96.4	2.5
0°-30°	393.6	10.3
0°-40°	575.7	15.1
0°-60°	850.4	22.2
0°-90°	976.8	25.5
90°-120°	607.4	15.9
90°-150°	2059.1	53.8
90°-180°	2847.0	74.5
0°-180°	3823.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	563	563	563	563	563	
5°	626	564	500	564	626	62
15°	707	535	331	535	707	191
25°	377	476	240	476	377	179
35°	186	393	177	393	186	119
45°	129	296	126	296	129	100
55°	90	201	88	201	90	79
65°	47	122	53	122	47	47
75°	25	58	28	58	25	26
85°	7	13	7	13	7	8
90°	29	1	29	1	29	13
95°	53	45	53	45	53	59
105°	191	185	191	185	191	201
115°	344	344	344	344	344	339
125°	502	500	502	500	502	447
135°	655	647	655	647	655	504
145°	794	785	794	785	794	496
155°	905	898	905	898	905	416
165°	978	977	978	977	978	276
175°	1013	1016	1013	1016	1013	96
180°	1018	1018	1018	1018	1018	



TEST NUMBER: P331634-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	585.7	586.2	586.7	585.6	585.6	584.6	582.6	581.0	576.6	576.0	576.0
5°	626.2	625.9	626.6	624.1	620.6	619.7	616.0	611.1	606.1	600.5	599.3
7.5°	666.5	665.9	664.3	663.9	661.2	655.3	649.4	643.0	634.6	626.3	622.2
10°	686.9	693.4	689.4	682.6	683.9	674.8	669.9	661.4	654.4	642.0	639.4
12.5°	706.9	709.5	708.2	704.3	702.6	696.2	689.6	682.3	669.3	658.2	648.6
15°	706.8	710.5	711.5	710.3	711.3	710.9	707.4	701.4	690.0	677.9	667.3
17.5°	654.6	657.2	663.7	668.0	673.5	685.0	690.8	692.9	691.3	684.3	676.9
20°	596.2	591.9	609.8	619.0	626.8	646.4	663.2	669.7	680.0	679.8	677.9
22.5°	513.2	514.2	531.2	542.2	565.0	584.6	603.7	628.0	648.1	661.3	669.1
25°	377.0	384.5	401.5	416.4	441.8	478.2	511.3	549.6	585.7	614.3	641.5
27.5°	283.2	283.8	297.2	311.0	326.1	355.9	397.5	443.2	494.8	537.4	586.3
30°	242.5	241.3	247.0	255.5	268.4	291.4	322.7	367.6	419.1	483.3	540.4
32.5°	213.7	213.8	218.1	224.3	235.0	250.6	272.0	308.6	357.1	420.3	487.2
35°	185.8	185.6	188.7	193.2	197.7	207.7	222.4	241.5	275.0	333.8	402.3
37.5°	165.7	166.6	168.2	171.0	175.9	181.5	190.3	203.2	227.0	261.8	319.3
40°	154.5	154.9	157.0	159.4	162.3	166.6	173.8	184.3	201.6	229.4	271.5
42.5°	144.2	144.6	146.1	148.3	150.6	154.9	160.9	169.9	184.0	205.6	240.3
45°	129.1	129.1	130.4	131.4	134.0	137.8	142.8	150.2	160.0	176.0	199.1
47.5°	114.9	114.9	115.9	117.5	119.2	122.2	127.0	133.1	140.2	152.6	172.3
50°	106.8	107.0	107.5	108.9	109.9	112.6	116.4	121.7	129.1	138.7	155.1
52.5°	100.2	100.1	100.8	101.4	102.1	104.0	106.9	111.5	118.1	126.5	140.1
55°	89.5	88.8	90.0	90.9	91.5	92.3	93.8	96.8	102.5	109.5	119.7
57.5°	76.3	75.9	76.8	77.7	79.6	81.6	83.0	84.8	87.7	92.8	102.9
60°	65.3	65.3	67.1	67.7	69.8	72.6	75.3	76.9	79.8	83.1	90.6
62.5°	55.6	55.8	56.6	57.2	58.4	61.7	65.6	69.1	71.8	75.0	79.9
65°	46.6	46.9	46.9	47.4	48.1	48.9	50.5	53.2	58.1	62.6	66.3
67.5°	39.5	39.6	39.8	40.1	40.3	41.2	41.8	43.0	44.2	48.4	53.0
70°	34.8	35.4	35.2	35.6	35.8	36.2	36.9	37.5	39.3	40.3	43.0
72.5°	30.4	30.8	30.8	31.1	31.6	31.7	32.3	32.9	34.0	34.8	36.3
75°	24.6	24.5	24.6	25.1	25.2	25.4	25.4	26.2	26.8	27.6	28.6
77.5°	19.0	19.2	19.2	19.2	19.3	19.6	19.5	19.9	20.5	20.9	21.4
80°	15.2	15.4	15.2	15.4	15.7	15.8	15.7	15.8	16.4	16.8	16.8
82.5°	11.8	11.9	12.0	12.0	12.1	12.1	12.4	12.4	12.8	12.7	12.9
85°	7.1	6.9	6.9	6.9	7.1	7.2	7.1	7.1	7.2	7.2	7.2
87.5°	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.7	8.6	8.9	7.8
90°	29.2	29.0	28.8	28.7	28.4	28.6	28.9	29.3	29.7	30.0	25.8
92.5°	27.8	27.8	27.7	27.7	27.7	27.6	27.6	27.5	27.4	27.3	26.3
95°	53.3	53.6	54.1	54.4	54.8	55.0	55.0	55.0	55.0	55.0	54.6
97.5°	92.3	92.3	92.4	92.4	92.5	92.5	92.5	92.5	92.5	92.5	91.7
100°	117.7	117.9	118.1	118.3	118.5	118.6	118.6	118.6	118.6	118.6	118.0
102.5°	146.6	146.8	147.0	147.1	147.3	147.4	147.2	147.1	146.9	146.8	146.0
105°	190.7	190.7	190.7	190.7	190.7	190.5	190.2	189.8	189.4	189.0	188.6
107.5°	232.3	233.2	234.1	235.0	235.8	236.2	236.1	235.9	235.7	235.6	235.6
110°	264.7	265.2	265.8	266.4	266.9	267.3	267.3	267.3	267.3	267.3	267.3



TEST NUMBER: P331634-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	295.6	296.0	296.4	296.9	297.2	297.7	298.2	298.6	299.1	299.5	299.7
115°	343.7	344.2	344.8	345.4	345.9	346.4	346.6	346.7	347.0	347.2	347.5
117.5°	389.6	390.1	390.7	391.3	391.8	392.4	392.9	393.3	393.7	394.3	395.3
120°	421.9	422.5	423.0	423.6	424.2	424.5	424.5	424.5	424.5	424.5	426.0
122.5°	453.5	453.9	454.3	454.8	455.2	455.6	456.1	456.5	457.0	457.4	458.6
125°	501.8	502.0	502.1	502.4	502.6	502.9	503.5	504.1	504.6	505.2	505.8
127.5°	545.8	546.4	547.0	547.6	548.2	548.9	549.6	550.3	551.0	551.6	552.3
130°	577.4	578.2	578.9	579.7	580.5	581.0	581.4	581.8	582.2	582.6	583.0
132.5°	607.7	608.3	608.9	609.5	610.1	610.8	611.7	612.5	613.4	614.2	614.1
135°	654.7	655.3	655.9	656.4	657.0	657.4	657.6	657.8	658.0	658.1	657.8
137.5°	697.3	698.1	698.9	699.6	700.4	700.9	701.0	701.2	701.4	701.5	701.0
140°	726.9	727.7	728.4	729.2	730.0	730.4	730.4	730.4	730.4	730.4	729.4
142.5°	753.7	754.5	755.3	756.0	756.8	757.1	756.9	756.8	756.6	756.5	755.8
145°	793.9	794.7	795.5	796.3	797.0	797.3	797.1	796.9	796.7	796.5	795.4
147.5°	829.8	830.6	831.3	832.1	832.8	832.9	832.5	832.1	831.6	831.2	830.4
150°	853.3	853.8	854.4	855.0	855.5	855.5	855.0	854.4	853.8	853.3	852.5
152.5°	875.2	876.0	876.7	877.4	878.1	878.1	877.4	876.7	876.0	875.2	874.3
155°	904.7	905.3	905.9	906.5	907.1	906.9	905.9	905.0	904.0	903.0	902.5
157.5°	930.2	931.1	932.0	933.0	933.8	933.7	932.4	931.1	929.8	928.5	928.2
160°	946.0	946.8	947.5	948.3	949.1	948.9	947.7	946.6	945.5	944.3	944.1
162.5°	959.8	960.7	961.6	962.5	963.5	963.2	961.9	960.6	959.3	958.0	957.9
165°	977.8	978.8	979.7	980.7	981.6	981.5	980.1	978.8	977.4	976.1	976.1
167.5°	992.6	993.6	994.5	995.6	996.5	996.3	995.1	993.7	992.4	991.0	991.1
170°	1000.1	1001.3	1002.5	1003.6	1004.7	1004.6	1003.3	1001.9	1000.7	999.3	999.4
172.5°	1006.3	1007.5	1008.7	1009.8	1010.9	1010.8	1009.5	1008.1	1006.9	1005.5	1005.6
175°	1013.1	1014.2	1015.3	1016.5	1017.6	1017.5	1016.2	1014.9	1013.5	1012.2	1012.5
177.5°	1016.2	1017.0	1018.0	1018.9	1019.8	1019.8	1018.9	1018.0	1017.0	1016.2	1016.4
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331634-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	576.4	575.1	573.9	571.2	569.7	566.6	566.2	566.0	562.0	558.0	556.9
5°	596.2	593.0	588.3	582.8	577.1	571.3	567.4	564.2	556.4	549.0	544.7
7.5°	616.0	609.3	601.2	590.9	582.2	572.6	565.3	558.9	547.8	537.1	529.9
10°	630.9	620.0	609.2	595.0	583.8	572.8	562.7	553.9	541.4	527.3	517.3
12.5°	640.2	628.1	613.3	599.3	584.9	570.9	557.3	546.0	531.3	516.8	505.0
15°	652.6	639.7	621.7	601.8	583.2	565.0	549.4	535.3	516.2	498.7	484.2
17.5°	662.9	645.1	625.8	602.7	581.2	558.1	538.0	520.0	498.6	477.6	460.5
20°	666.2	648.5	626.2	603.1	577.7	550.5	528.8	509.3	486.4	463.5	443.9
22.5°	664.1	650.4	625.6	598.0	572.0	543.5	519.0	496.3	470.9	447.5	424.9
25°	650.3	645.6	622.2	592.0	562.3	529.3	500.8	476.0	447.1	422.1	397.4
27.5°	618.1	628.3	613.7	581.6	548.5	513.2	481.2	453.0	422.9	394.8	370.2
30°	587.1	610.4	604.2	574.4	537.4	502.7	466.8	437.3	405.3	376.3	352.1
32.5°	544.8	583.2	589.3	564.4	526.2	487.9	450.4	421.0	387.5	357.1	333.4
35°	477.2	534.7	561.1	545.3	507.0	465.6	427.0	392.7	359.0	329.0	305.5
37.5°	396.7	475.0	519.0	520.1	484.9	442.0	399.8	365.8	331.4	301.9	276.5
40°	344.4	429.3	486.6	499.3	469.6	423.3	380.6	345.9	312.4	283.4	254.3
42.5°	297.5	382.0	452.5	474.6	451.0	404.9	362.1	326.0	293.3	265.9	236.1
45°	240.6	314.5	392.1	431.6	418.5	375.9	330.7	296.3	265.6	241.9	213.4
47.5°	202.9	255.0	330.2	383.6	383.4	344.5	300.0	267.1	238.6	216.4	193.3
50°	181.5	226.9	290.4	351.0	356.1	323.5	281.2	248.6	222.0	198.7	180.1
52.5°	162.2	199.7	256.8	315.0	329.4	301.1	260.1	230.0	204.1	182.7	166.9
55°	137.1	166.1	209.5	263.8	285.8	265.8	229.4	201.2	180.3	162.3	148.6
57.5°	116.0	137.7	172.5	216.3	241.8	229.3	199.2	176.3	158.4	142.2	131.4
60°	102.7	120.5	150.0	186.6	214.7	206.0	180.3	159.0	143.8	129.7	119.5
62.5°	90.1	105.5	130.8	160.5	186.2	182.6	161.7	143.8	130.4	117.6	109.0
65°	72.6	83.7	103.5	126.7	147.5	149.2	134.1	122.0	110.1	100.0	92.3
67.5°	57.8	65.1	79.0	98.6	114.1	119.7	110.5	101.2	91.7	83.9	77.2
70°	48.7	54.6	64.7	80.6	94.9	100.7	95.4	88.2	80.0	73.5	67.8
72.5°	39.4	45.2	52.7	64.3	76.5	82.9	81.0	75.9	69.2	63.8	58.5
75°	29.7	31.5	36.6	44.4	54.0	59.5	60.8	58.1	52.8	48.7	45.5
77.5°	22.0	23.1	25.5	29.5	35.8	40.7	42.7	42.4	38.7	36.4	33.4
80°	17.6	18.2	19.4	21.1	25.8	30.7	32.1	32.1	29.5	28.6	25.7
82.5°	13.3	13.8	14.6	15.5	17.7	22.0	23.5	23.8	22.2	20.9	18.6
85°	7.7	7.4	7.8	8.4	8.8	10.0	12.3	12.7	12.3	10.8	10.2
87.5°	7.0	6.3	5.5	4.6	4.4	4.0	4.4	4.7	4.6	4.6	4.6
90°	21.7	17.5	13.3	10.0	7.7	5.4	3.2	0.9	3.2	5.4	7.7
92.5°	25.3	24.4	23.3	22.0	20.3	18.7	17.0	15.3	17.0	18.7	20.3
95°	54.2	53.8	53.5	52.3	50.4	48.5	46.6	44.7	46.6	48.5	50.4
97.5°	91.0	90.3	89.5	88.3	86.7	85.0	83.3	81.6	83.3	85.0	86.7
100°	117.4	116.8	116.3	115.2	113.7	112.2	110.6	109.1	110.6	112.2	113.7
102.5°	145.3	144.6	143.9	142.8	141.6	140.4	139.2	138.0	139.2	140.4	141.6
105°	188.3	187.9	187.5	187.0	186.5	185.9	185.3	184.8	185.3	185.9	186.5
107.5°	235.6	235.6	235.6	235.2	234.4	233.5	232.6	231.8	232.6	233.5	234.4
110°	267.3	267.3	267.3	266.7	265.5	264.3	263.2	262.1	263.2	264.3	265.5



TEST NUMBER: P331634-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	299.8	300.0	300.1	299.6	298.5	297.4	296.2	295.1	296.2	297.4	298.5
115°	347.9	348.3	348.6	348.3	347.2	345.9	344.8	343.7	344.8	345.9	347.2
117.5°	396.3	397.4	398.5	398.3	396.7	395.2	393.6	392.2	393.6	395.2	396.7
120°	427.5	429.0	430.6	430.6	429.0	427.5	426.0	424.5	426.0	427.5	429.0
122.5°	459.6	460.6	461.8	461.3	459.5	457.7	455.8	454.0	455.8	457.7	459.5
125°	506.4	507.0	507.6	507.0	505.2	503.5	501.8	500.1	501.8	503.5	505.2
127.5°	553.0	553.7	554.4	553.6	551.5	549.3	547.1	544.9	547.1	549.3	551.5
130°	583.3	583.7	584.1	583.1	580.6	578.1	575.6	573.1	575.6	578.1	580.6
132.5°	614.1	614.0	613.9	612.9	610.8	608.8	606.7	604.8	606.7	608.8	610.8
135°	657.4	657.0	656.7	655.4	653.3	651.2	649.1	647.0	649.1	651.2	653.3
137.5°	700.5	700.0	699.5	698.4	696.6	694.9	693.2	691.6	693.2	694.9	696.6
140°	728.4	727.5	726.5	725.2	723.5	721.8	720.1	718.3	720.1	721.8	723.5
142.5°	755.2	754.5	753.9	752.7	751.0	749.2	747.5	745.8	747.5	749.2	751.0
145°	794.2	793.1	791.9	790.7	789.4	788.0	786.7	785.3	786.7	788.0	789.4
147.5°	829.7	829.0	828.2	827.0	825.4	823.8	822.2	820.5	822.2	823.8	825.4
150°	851.7	850.9	850.2	849.2	848.1	846.9	845.8	844.6	845.8	846.9	848.1
152.5°	873.4	872.5	871.6	870.6	869.4	868.2	867.1	865.9	867.1	868.2	869.4
155°	901.9	901.4	900.8	900.2	899.7	899.1	898.5	897.9	898.5	899.1	899.7
157.5°	927.8	927.5	927.1	926.8	926.3	926.0	925.6	925.2	925.6	926.0	926.3
160°	943.9	943.7	943.6	943.2	942.9	942.5	942.1	941.8	942.1	942.5	942.9
162.5°	957.7	957.5	957.3	957.2	957.1	957.0	956.9	956.8	956.9	957.0	957.1
165°	976.1	976.1	976.1	976.2	976.4	976.5	976.8	977.0	976.8	976.5	976.4
167.5°	991.1	991.2	991.2	991.5	992.0	992.6	993.2	993.8	993.2	992.6	992.0
170°	999.7	999.9	1000.1	1000.4	1001.0	1001.6	1002.1	1002.7	1002.1	1001.6	1001.0
172.5°	1005.8	1006.1	1006.3	1006.6	1007.2	1007.8	1008.3	1008.9	1008.3	1007.8	1007.2
175°	1013.0	1013.3	1013.7	1014.2	1014.8	1015.3	1015.9	1016.5	1015.9	1015.3	1014.8
177.5°	1016.8	1017.0	1017.4	1017.7	1018.2	1018.6	1019.1	1019.6	1019.1	1018.6	1018.2
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331634-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	554.9	553.8	551.7	548.6	546.7	543.5	541.3	542.5	542.9	542.5	542.3
5°	540.0	535.9	530.2	524.7	519.6	514.2	511.0	509.7	507.0	505.4	504.5
7.5°	521.9	514.9	506.9	497.3	489.2	480.7	476.4	474.2	468.6	465.6	463.0
10°	508.5	497.3	489.3	476.8	469.2	458.1	450.4	450.6	443.0	438.7	435.6
12.5°	493.6	481.4	468.0	456.8	446.2	437.2	428.0	424.3	416.2	412.1	403.6
15°	469.0	454.7	440.7	425.4	414.7	400.7	387.4	371.2	358.1	346.7	343.6
17.5°	442.1	424.4	410.3	392.4	373.9	350.6	335.2	325.7	317.9	311.9	307.4
20°	423.6	405.6	390.5	363.6	338.7	322.9	311.6	304.3	296.1	289.6	286.1
22.5°	404.2	385.5	364.9	334.8	315.4	302.7	292.7	284.3	278.7	273.7	270.4
25°	376.7	356.1	322.3	301.6	285.9	272.6	265.6	260.5	254.7	247.8	244.7
27.5°	347.6	315.0	290.6	275.2	260.3	251.7	245.3	237.7	232.5	229.4	226.1
30°	325.8	293.2	274.2	257.4	246.8	237.2	229.8	225.5	220.4	215.2	213.0
32.5°	301.6	275.5	257.3	243.3	232.6	224.4	218.5	211.5	207.9	204.7	200.2
35°	271.5	251.7	235.1	223.8	213.5	206.9	200.1	196.0	189.3	186.6	184.9
37.5°	246.0	228.9	216.5	204.5	196.4	189.1	184.9	178.3	175.5	171.6	167.9
40°	231.5	214.7	202.9	193.0	184.0	178.6	173.3	168.0	163.7	162.0	157.5
42.5°	216.9	203.2	191.2	180.6	174.5	168.7	162.0	158.2	153.7	150.8	148.1
45°	196.6	184.4	174.3	165.5	158.8	152.7	148.4	142.0	139.5	133.8	131.4
47.5°	178.7	167.5	157.7	149.4	142.9	139.0	132.7	127.6	123.6	120.0	117.0
50°	166.1	156.6	147.2	139.8	134.0	128.3	121.8	119.3	113.0	111.2	109.5
52.5°	154.5	145.5	137.0	129.7	123.8	118.3	112.6	109.3	105.0	103.3	102.0
55°	138.3	129.7	121.5	115.0	109.2	103.5	100.0	95.8	93.8	92.5	90.9
57.5°	122.0	114.3	108.0	101.4	95.5	91.0	87.0	84.5	82.5	80.7	78.8
60°	111.7	104.3	98.6	92.5	86.4	82.7	79.6	76.6	74.3	71.5	70.8
62.5°	100.7	94.2	89.0	83.1	77.8	74.5	71.5	68.7	65.9	61.9	60.8
65°	85.7	80.6	75.1	70.2	65.5	62.2	57.9	54.8	53.6	53.2	53.0
67.5°	72.1	67.2	62.5	57.5	53.3	50.2	48.0	47.5	46.7	46.5	45.9
70°	62.9	58.5	53.8	49.1	44.9	44.4	43.7	42.8	41.8	41.5	41.1
72.5°	54.8	50.2	45.5	41.8	40.0	39.3	38.5	37.6	37.0	36.6	36.4
75°	42.0	37.7	34.6	33.2	32.3	31.7	30.5	30.0	29.5	28.9	28.8
77.5°	30.3	27.8	26.4	25.6	24.5	23.9	23.2	22.6	22.2	22.1	21.8
80°	23.1	21.9	20.9	19.7	19.4	18.6	18.4	17.8	18.0	17.4	17.4
82.5°	17.9	16.4	15.6	15.1	14.6	14.0	13.9	13.6	13.6	13.2	13.2
85°	9.2	8.8	8.4	8.0	8.0	7.4	7.7	7.4	7.4	7.1	6.9
87.5°	5.0	5.5	6.0	6.8	7.7	8.4	8.3	8.1	8.0	7.9	7.7
90°	10.0	13.3	17.5	21.7	25.8	30.0	29.7	29.3	28.9	28.6	28.4
92.5°	22.0	23.3	24.4	25.3	26.3	27.3	27.4	27.5	27.6	27.6	27.7
95°	52.3	53.5	53.8	54.2	54.6	55.0	55.0	55.0	55.0	55.0	54.8
97.5°	88.3	89.5	90.3	91.0	91.7	92.5	92.5	92.5	92.5	92.5	92.5
100°	115.2	116.3	116.8	117.4	118.0	118.6	118.6	118.6	118.6	118.6	118.5
102.5°	142.8	143.9	144.6	145.3	146.0	146.8	146.9	147.1	147.2	147.4	147.3
105°	187.0	187.5	187.9	188.3	188.6	189.0	189.4	189.8	190.2	190.5	190.7
107.5°	235.2	235.6	235.6	235.6	235.6	235.6	235.7	235.9	236.1	236.2	235.8
110°	266.7	267.3	267.3	267.3	267.3	267.3	267.3	267.3	267.3	267.3	266.9



TEST NUMBER: P331634-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	299.6	300.1	300.0	299.8	299.7	299.5	299.1	298.6	298.2	297.7	297.2
115°	348.3	348.6	348.3	347.9	347.5	347.2	347.0	346.7	346.6	346.4	345.9
117.5°	398.3	398.5	397.4	396.3	395.3	394.3	393.7	393.3	392.9	392.4	391.8
120°	430.6	430.6	429.0	427.5	426.0	424.5	424.5	424.5	424.5	424.5	424.2
122.5°	461.3	461.8	460.6	459.6	458.6	457.4	457.0	456.5	456.1	455.6	455.2
125°	507.0	507.6	507.0	506.4	505.8	505.2	504.6	504.1	503.5	502.9	502.6
127.5°	553.6	554.4	553.7	553.0	552.3	551.6	551.0	550.3	549.6	548.9	548.2
130°	583.1	584.1	583.7	583.3	583.0	582.6	582.2	581.8	581.4	581.0	580.5
132.5°	612.9	613.9	614.0	614.1	614.1	614.2	613.4	612.5	611.7	610.8	610.1
135°	655.4	656.7	657.0	657.4	657.8	658.1	658.0	657.8	657.6	657.4	657.0
137.5°	698.4	699.5	700.0	700.5	701.0	701.5	701.4	701.2	701.0	700.9	700.4
140°	725.2	726.5	727.5	728.4	729.4	730.4	730.4	730.4	730.4	730.4	730.0
142.5°	752.7	753.9	754.5	755.2	755.8	756.5	756.6	756.8	756.9	757.1	756.8
145°	790.7	791.9	793.1	794.2	795.4	796.5	796.7	796.9	797.1	797.3	797.0
147.5°	827.0	828.2	829.0	829.7	830.4	831.2	831.6	832.1	832.5	832.9	832.8
150°	849.2	850.2	850.9	851.7	852.5	853.3	853.8	854.4	855.0	855.5	855.5
152.5°	870.6	871.6	872.5	873.4	874.3	875.2	876.0	876.7	877.4	878.1	878.1
155°	900.2	900.8	901.4	901.9	902.5	903.0	904.0	905.0	905.9	906.9	907.1
157.5°	926.8	927.1	927.5	927.8	928.2	928.5	929.8	931.1	932.4	933.7	933.8
160°	943.2	943.6	943.7	943.9	944.1	944.3	945.5	946.6	947.7	948.9	949.1
162.5°	957.2	957.3	957.5	957.7	957.9	958.0	959.3	960.6	961.9	963.2	963.5
165°	976.2	976.1	976.1	976.1	976.1	976.1	977.4	978.8	980.1	981.5	981.6
167.5°	991.5	991.2	991.2	991.1	991.1	991.0	992.4	993.7	995.1	996.3	996.5
170°	1000.4	1000.1	999.9	999.7	999.4	999.3	1000.7	1001.9	1003.3	1004.6	1004.7
172.5°	1006.6	1006.3	1006.1	1005.8	1005.6	1005.5	1006.9	1008.1	1009.5	1010.8	1010.9
175°	1014.2	1013.7	1013.3	1013.0	1012.5	1012.2	1013.5	1014.9	1016.2	1017.5	1017.6
177.5°	1017.7	1017.4	1017.0	1016.8	1016.4	1016.2	1017.0	1018.0	1018.9	1019.8	1019.8
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331634-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	540.5	540.8	540.4	540.6	540.4	540.8	540.5	542.3	542.5	542.9	542.5
5°	503.6	501.3	500.8	500.3	500.8	501.3	503.6	504.5	505.4	507.0	509.7
7.5°	459.6	459.3	458.2	456.8	458.2	459.3	459.6	463.0	465.6	468.6	474.2
10°	431.3	430.2	430.1	428.7	430.1	430.2	431.3	435.6	438.7	443.0	450.6
12.5°	398.0	391.8	391.2	387.7	391.2	391.8	398.0	403.6	412.1	416.2	424.3
15°	339.0	337.8	333.8	331.3	333.8	337.8	339.0	343.6	346.7	358.1	371.2
17.5°	305.1	301.3	300.1	299.5	300.1	301.3	305.1	307.4	311.9	317.9	325.7
20°	283.4	279.9	279.3	278.9	279.3	279.9	283.4	286.1	289.6	296.1	304.3
22.5°	268.4	264.7	263.2	262.0	263.2	264.7	268.4	270.4	273.7	278.7	284.3
25°	242.7	241.3	240.6	240.1	240.6	241.3	242.7	244.7	247.8	254.7	260.5
27.5°	222.7	219.6	219.0	218.0	219.0	219.6	222.7	226.1	229.4	232.5	237.7
30°	211.2	210.3	208.9	207.7	208.9	210.3	211.2	213.0	215.2	220.4	225.5
32.5°	197.8	196.9	195.7	195.2	195.7	196.9	197.8	200.2	204.7	207.9	211.5
35°	182.9	180.1	178.9	177.2	178.9	180.1	182.9	184.9	186.6	189.3	196.0
37.5°	167.1	165.7	164.0	164.6	164.0	165.7	167.1	167.9	171.6	175.5	178.3
40°	154.9	153.9	153.5	153.3	153.5	153.9	154.9	157.5	162.0	163.7	168.0
42.5°	145.2	142.5	141.5	141.5	141.5	142.5	145.2	148.1	150.8	153.7	158.2
45°	130.4	127.9	126.1	126.3	126.1	127.9	130.4	131.4	133.8	139.5	142.0
47.5°	115.4	115.3	114.2	114.5	114.2	115.3	115.4	117.0	120.0	123.6	127.6
50°	108.1	107.0	106.2	106.4	106.2	107.0	108.1	109.5	111.2	113.0	119.3
52.5°	101.3	100.2	99.6	100.5	99.6	100.2	101.3	102.0	103.3	105.0	109.3
55°	90.0	88.8	88.6	88.4	88.6	88.8	90.0	90.9	92.5	93.8	95.8
57.5°	77.3	76.5	75.3	74.9	75.3	76.5	77.3	78.8	80.7	82.5	84.5
60°	68.3	66.7	64.7	64.6	64.7	66.7	68.3	70.8	71.5	74.3	76.6
62.5°	59.9	59.7	59.2	59.2	59.2	59.7	59.9	60.8	61.9	65.9	68.7
65°	52.6	52.4	52.6	52.8	52.6	52.4	52.6	53.0	53.2	53.6	54.8
67.5°	45.8	45.5	45.1	45.3	45.1	45.5	45.8	45.9	46.5	46.7	47.5
70°	40.6	40.5	40.3	40.3	40.3	40.5	40.6	41.1	41.5	41.8	42.8
72.5°	35.6	35.6	35.5	35.3	35.5	35.6	35.6	36.4	36.6	37.0	37.6
75°	28.6	28.2	28.2	28.2	28.2	28.2	28.6	28.8	28.9	29.5	30.0
77.5°	21.8	21.5	21.4	21.2	21.4	21.5	21.8	21.8	22.1	22.2	22.6
80°	17.2	17.0	16.8	16.8	16.8	17.0	17.2	17.4	17.4	18.0	17.8
82.5°	13.2	12.9	12.9	12.7	12.9	12.9	13.2	13.2	13.2	13.6	13.6
85°	7.1	7.2	7.1	7.4	7.1	7.2	7.1	6.9	7.1	7.4	7.4
87.5°	7.7	7.7	7.8	7.7	7.8	7.7	7.7	7.7	7.9	8.0	8.1
90°	28.7	28.8	29.0	29.2	29.0	28.8	28.7	28.4	28.6	28.9	29.3
92.5°	27.7	27.7	27.8	27.8	27.8	27.7	27.7	27.7	27.6	27.6	27.5
95°	54.4	54.1	53.6	53.3	53.6	54.1	54.4	54.8	55.0	55.0	55.0
97.5°	92.4	92.4	92.3	92.3	92.3	92.4	92.4	92.5	92.5	92.5	92.5
100°	118.3	118.1	117.9	117.7	117.9	118.1	118.3	118.5	118.6	118.6	118.6
102.5°	147.1	147.0	146.8	146.6	146.8	147.0	147.1	147.3	147.4	147.2	147.1
105°	190.7	190.7	190.7	190.7	190.7	190.7	190.7	190.7	190.5	190.2	189.8
107.5°	235.0	234.1	233.2	232.3	233.2	234.1	235.0	235.8	236.2	236.1	235.9
110°	266.4	265.8	265.2	264.7	265.2	265.8	266.4	266.9	267.3	267.3	267.3



TEST NUMBER: P331634-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	296.9	296.4	296.0	295.6	296.0	296.4	296.9	297.2	297.7	298.2	298.6
115°	345.4	344.8	344.2	343.7	344.2	344.8	345.4	345.9	346.4	346.6	346.7
117.5°	391.3	390.7	390.1	389.6	390.1	390.7	391.3	391.8	392.4	392.9	393.3
120°	423.6	423.0	422.5	421.9	422.5	423.0	423.6	424.2	424.5	424.5	424.5
122.5°	454.8	454.3	453.9	453.5	453.9	454.3	454.8	455.2	455.6	456.1	456.5
125°	502.4	502.1	502.0	501.8	502.0	502.1	502.4	502.6	502.9	503.5	504.1
127.5°	547.6	547.0	546.4	545.8	546.4	547.0	547.6	548.2	548.9	549.6	550.3
130°	579.7	578.9	578.2	577.4	578.2	578.9	579.7	580.5	581.0	581.4	581.8
132.5°	609.5	608.9	608.3	607.7	608.3	608.9	609.5	610.1	610.8	611.7	612.5
135°	656.4	655.9	655.3	654.7	655.3	655.9	656.4	657.0	657.4	657.6	657.8
137.5°	699.6	698.9	698.1	697.3	698.1	698.9	699.6	700.4	700.9	701.0	701.2
140°	729.2	728.4	727.7	726.9	727.7	728.4	729.2	730.0	730.4	730.4	730.4
142.5°	756.0	755.3	754.5	753.7	754.5	755.3	756.0	756.8	757.1	756.9	756.8
145°	796.3	795.5	794.7	793.9	794.7	795.5	796.3	797.0	797.3	797.1	796.9
147.5°	832.1	831.3	830.6	829.8	830.6	831.3	832.1	832.8	832.9	832.5	832.1
150°	855.0	854.4	853.8	853.3	853.8	854.4	855.0	855.5	855.5	855.0	854.4
152.5°	877.4	876.7	876.0	875.2	876.0	876.7	877.4	878.1	878.1	877.4	876.7
155°	906.5	905.9	905.3	904.7	905.3	905.9	906.5	907.1	906.9	905.9	905.0
157.5°	933.0	932.0	931.1	930.2	931.1	932.0	933.0	933.8	933.7	932.4	931.1
160°	948.3	947.5	946.8	946.0	946.8	947.5	948.3	949.1	948.9	947.7	946.6
162.5°	962.5	961.6	960.7	959.8	960.7	961.6	962.5	963.5	963.2	961.9	960.6
165°	980.7	979.7	978.8	977.8	978.8	979.7	980.7	981.6	981.5	980.1	978.8
167.5°	995.6	994.5	993.6	992.6	993.6	994.5	995.6	996.5	996.3	995.1	993.7
170°	1003.6	1002.5	1001.3	1000.1	1001.3	1002.5	1003.6	1004.7	1004.6	1003.3	1001.9
172.5°	1009.8	1008.7	1007.5	1006.3	1007.5	1008.7	1009.8	1010.9	1010.8	1009.5	1008.1
175°	1016.5	1015.3	1014.2	1013.1	1014.2	1015.3	1016.5	1017.6	1017.5	1016.2	1014.9
177.5°	1018.9	1018.0	1017.0	1016.2	1017.0	1018.0	1018.9	1019.8	1019.8	1018.9	1018.0
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331634-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	541.3	543.5	546.7	548.6	551.7	553.8	554.9	556.9	558.0	562.0	566.0
5°	511.0	514.2	519.6	524.7	530.2	535.9	540.0	544.7	549.0	556.4	564.2
7.5°	476.4	480.7	489.2	497.3	506.9	514.9	521.9	529.9	537.1	547.8	558.9
10°	450.4	458.1	469.2	476.8	489.3	497.3	508.5	517.3	527.3	541.4	553.9
12.5°	428.0	437.2	446.2	456.8	468.0	481.4	493.6	505.0	516.8	531.3	546.0
15°	387.4	400.7	414.7	425.4	440.7	454.7	469.0	484.2	498.7	516.2	535.3
17.5°	335.2	350.6	373.9	392.4	410.3	424.4	442.1	460.5	477.6	498.6	520.0
20°	311.6	322.9	338.7	363.6	390.5	405.6	423.6	443.9	463.5	486.4	509.3
22.5°	292.7	302.7	315.4	334.8	364.9	385.5	404.2	424.9	447.5	470.9	496.3
25°	265.6	272.6	285.9	301.6	322.3	356.1	376.7	397.4	422.1	447.1	476.0
27.5°	245.3	251.7	260.3	275.2	290.6	315.0	347.6	370.2	394.8	422.9	453.0
30°	229.8	237.2	246.8	257.4	274.2	293.2	325.8	352.1	376.3	405.3	437.3
32.5°	218.5	224.4	232.6	243.3	257.3	275.5	301.6	333.4	357.1	387.5	421.0
35°	200.1	206.9	213.5	223.8	235.1	251.7	271.5	305.5	329.0	359.0	392.7
37.5°	184.9	189.1	196.4	204.5	216.5	228.9	246.0	276.5	301.9	331.4	365.8
40°	173.3	178.6	184.0	193.0	202.9	214.7	231.5	254.3	283.4	312.4	345.9
42.5°	162.0	168.7	174.5	180.6	191.2	203.2	216.9	236.1	265.9	293.3	326.0
45°	148.4	152.7	158.8	165.5	174.3	184.4	196.6	213.4	241.9	265.6	296.3
47.5°	132.7	139.0	142.9	149.4	157.7	167.5	178.7	193.3	216.4	238.6	267.1
50°	121.8	128.3	134.0	139.8	147.2	156.6	166.1	180.1	198.7	222.0	248.6
52.5°	112.6	118.3	123.8	129.7	137.0	145.5	154.5	166.9	182.7	204.1	230.0
55°	100.0	103.5	109.2	115.0	121.5	129.7	138.3	148.6	162.3	180.3	201.2
57.5°	87.0	91.0	95.5	101.4	108.0	114.3	122.0	131.4	142.2	158.4	176.3
60°	79.6	82.7	86.4	92.5	98.6	104.3	111.7	119.5	129.7	143.8	159.0
62.5°	71.5	74.5	77.8	83.1	89.0	94.2	100.7	109.0	117.6	130.4	143.8
65°	57.9	62.2	65.5	70.2	75.1	80.6	85.7	92.3	100.0	110.1	122.0
67.5°	48.0	50.2	53.3	57.5	62.5	67.2	72.1	77.2	83.9	91.7	101.2
70°	43.7	44.4	44.9	49.1	53.8	58.5	62.9	67.8	73.5	80.0	88.2
72.5°	38.5	39.3	40.0	41.8	45.5	50.2	54.8	58.5	63.8	69.2	75.9
75°	30.5	31.7	32.3	33.2	34.6	37.7	42.0	45.5	48.7	52.8	58.1
77.5°	23.2	23.9	24.5	25.6	26.4	27.8	30.3	33.4	36.4	38.7	42.4
80°	18.4	18.6	19.4	19.7	20.9	21.9	23.1	25.7	28.6	29.5	32.1
82.5°	13.9	14.0	14.6	15.1	15.6	16.4	17.9	18.6	20.9	22.2	23.8
85°	7.7	7.4	8.0	8.0	8.4	8.8	9.2	10.2	10.8	12.3	12.7
87.5°	8.3	8.4	7.7	6.8	6.0	5.5	5.0	4.6	4.6	4.6	4.7
90°	29.7	30.0	25.8	21.7	17.5	13.3	10.0	7.7	5.4	3.2	0.9
92.5°	27.4	27.3	26.3	25.3	24.4	23.3	22.0	20.3	18.7	17.0	15.3
95°	55.0	55.0	54.6	54.2	53.8	53.5	52.3	50.4	48.5	46.6	44.7
97.5°	92.5	92.5	91.7	91.0	90.3	89.5	88.3	86.7	85.0	83.3	81.6
100°	118.6	118.6	118.0	117.4	116.8	116.3	115.2	113.7	112.2	110.6	109.1
102.5°	146.9	146.8	146.0	145.3	144.6	143.9	142.8	141.6	140.4	139.2	138.0
105°	189.4	189.0	188.6	188.3	187.9	187.5	187.0	186.5	185.9	185.3	184.8
107.5°	235.7	235.6	235.6	235.6	235.6	235.6	235.2	234.4	233.5	232.6	231.8
110°	267.3	267.3	267.3	267.3	267.3	267.3	266.7	265.5	264.3	263.2	262.1



TEST NUMBER: P331634-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	299.1	299.5	299.7	299.8	300.0	300.1	299.6	298.5	297.4	296.2	295.1
115°	347.0	347.2	347.5	347.9	348.3	348.6	348.3	347.2	345.9	344.8	343.7
117.5°	393.7	394.3	395.3	396.3	397.4	398.5	398.3	396.7	395.2	393.6	392.2
120°	424.5	424.5	426.0	427.5	429.0	430.6	430.6	429.0	427.5	426.0	424.5
122.5°	457.0	457.4	458.6	459.6	460.6	461.8	461.3	459.5	457.7	455.8	454.0
125°	504.6	505.2	505.8	506.4	507.0	507.6	507.0	505.2	503.5	501.8	500.1
127.5°	551.0	551.6	552.3	553.0	553.7	554.4	553.6	551.5	549.3	547.1	544.9
130°	582.2	582.6	583.0	583.3	583.7	584.1	583.1	580.6	578.1	575.6	573.1
132.5°	613.4	614.2	614.1	614.1	614.0	613.9	612.9	610.8	608.8	606.7	604.8
135°	658.0	658.1	657.8	657.4	657.0	656.7	655.4	653.3	651.2	649.1	647.0
137.5°	701.4	701.5	701.0	700.5	700.0	699.5	698.4	696.6	694.9	693.2	691.6
140°	730.4	730.4	729.4	728.4	727.5	726.5	725.2	723.5	721.8	720.1	718.3
142.5°	756.6	756.5	755.8	755.2	754.5	753.9	752.7	751.0	749.2	747.5	745.8
145°	796.7	796.5	795.4	794.2	793.1	791.9	790.7	789.4	788.0	786.7	785.3
147.5°	831.6	831.2	830.4	829.7	829.0	828.2	827.0	825.4	823.8	822.2	820.5
150°	853.8	853.3	852.5	851.7	850.9	850.2	849.2	848.1	846.9	845.8	844.6
152.5°	876.0	875.2	874.3	873.4	872.5	871.6	870.6	869.4	868.2	867.1	865.9
155°	904.0	903.0	902.5	901.9	901.4	900.8	900.2	899.7	899.1	898.5	897.9
157.5°	929.8	928.5	928.2	927.8	927.5	927.1	926.8	926.3	926.0	925.6	925.2
160°	945.5	944.3	944.1	943.9	943.7	943.6	943.2	942.9	942.5	942.1	941.8
162.5°	959.3	958.0	957.9	957.7	957.5	957.3	957.2	957.1	957.0	956.9	956.8
165°	977.4	976.1	976.1	976.1	976.1	976.1	976.2	976.4	976.5	976.8	977.0
167.5°	992.4	991.0	991.1	991.1	991.2	991.2	991.5	992.0	992.6	993.2	993.8
170°	1000.7	999.3	999.4	999.7	999.9	1000.1	1000.4	1001.0	1001.6	1002.1	1002.7
172.5°	1006.9	1005.5	1005.6	1005.8	1006.1	1006.3	1006.6	1007.2	1007.8	1008.3	1008.9
175°	1013.5	1012.2	1012.5	1013.0	1013.3	1013.7	1014.2	1014.8	1015.3	1015.9	1016.5
177.5°	1017.0	1016.2	1016.4	1016.8	1017.0	1017.4	1017.7	1018.2	1018.6	1019.1	1019.6
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331634-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	566.2	566.6	569.7	571.2	573.9	575.1	576.4	576.0	576.0	576.6	581.0
5°	567.4	571.3	577.1	582.8	588.3	593.0	596.2	599.3	600.5	606.1	611.1
7.5°	565.3	572.6	582.2	590.9	601.2	609.3	616.0	622.2	626.3	634.6	643.0
10°	562.7	572.8	583.8	595.0	609.2	620.0	630.9	639.4	642.0	654.4	661.4
12.5°	557.3	570.9	584.9	599.3	613.3	628.1	640.2	648.6	658.2	669.3	682.3
15°	549.4	565.0	583.2	601.8	621.7	639.7	652.6	667.3	677.9	690.0	701.4
17.5°	538.0	558.1	581.2	602.7	625.8	645.1	662.9	676.9	684.3	691.3	692.9
20°	528.8	550.5	577.7	603.1	626.2	648.5	666.2	677.9	679.8	680.0	669.7
22.5°	519.0	543.5	572.0	598.0	625.6	650.4	664.1	669.1	661.3	648.1	628.0
25°	500.8	529.3	562.3	592.0	622.2	645.6	650.3	641.5	614.3	585.7	549.6
27.5°	481.2	513.2	548.5	581.6	613.7	628.3	618.1	586.3	537.4	494.8	443.2
30°	466.8	502.7	537.4	574.4	604.2	610.4	587.1	540.4	483.3	419.1	367.6
32.5°	450.4	487.9	526.2	564.4	589.3	583.2	544.8	487.2	420.3	357.1	308.6
35°	427.0	465.6	507.0	545.3	561.1	534.7	477.2	402.3	333.8	275.0	241.5
37.5°	399.8	442.0	484.9	520.1	519.0	475.0	396.7	319.3	261.8	227.0	203.2
40°	380.6	423.3	469.6	499.3	486.6	429.3	344.4	271.5	229.4	201.6	184.3
42.5°	362.1	404.9	451.0	474.6	452.5	382.0	297.5	240.3	205.6	184.0	169.9
45°	330.7	375.9	418.5	431.6	392.1	314.5	240.6	199.1	176.0	160.0	150.2
47.5°	300.0	344.5	383.4	383.6	330.2	255.0	202.9	172.3	152.6	140.2	133.1
50°	281.2	323.5	356.1	351.0	290.4	226.9	181.5	155.1	138.7	129.1	121.7
52.5°	260.1	301.1	329.4	315.0	256.8	199.7	162.2	140.1	126.5	118.1	111.5
55°	229.4	265.8	285.8	263.8	209.5	166.1	137.1	119.7	109.5	102.5	96.8
57.5°	199.2	229.3	241.8	216.3	172.5	137.7	116.0	102.9	92.8	87.7	84.8
60°	180.3	206.0	214.7	186.6	150.0	120.5	102.7	90.6	83.1	79.8	76.9
62.5°	161.7	182.6	186.2	160.5	130.8	105.5	90.1	79.9	75.0	71.8	69.1
65°	134.1	149.2	147.5	126.7	103.5	83.7	72.6	66.3	62.6	58.1	53.2
67.5°	110.5	119.7	114.1	98.6	79.0	65.1	57.8	53.0	48.4	44.2	43.0
70°	95.4	100.7	94.9	80.6	64.7	54.6	48.7	43.0	40.3	39.3	37.5
72.5°	81.0	82.9	76.5	64.3	52.7	45.2	39.4	36.3	34.8	34.0	32.9
75°	60.8	59.5	54.0	44.4	36.6	31.5	29.7	28.6	27.6	26.8	26.2
77.5°	42.7	40.7	35.8	29.5	25.5	23.1	22.0	21.4	20.9	20.5	19.9
80°	32.1	30.7	25.8	21.1	19.4	18.2	17.6	16.8	16.8	16.4	15.8
82.5°	23.5	22.0	17.7	15.5	14.6	13.8	13.3	12.9	12.7	12.8	12.4
85°	12.3	10.0	8.8	8.4	7.8	7.4	7.7	7.2	7.2	7.2	7.1
87.5°	4.4	4.0	4.4	4.6	5.5	6.3	7.0	7.8	8.9	8.6	8.7
90°	3.2	5.4	7.7	10.0	13.3	17.5	21.7	25.8	30.0	29.7	29.3
92.5°	17.0	18.7	20.3	22.0	23.3	24.4	25.3	26.3	27.3	27.4	27.5
95°	46.6	48.5	50.4	52.3	53.5	53.8	54.2	54.6	55.0	55.0	55.0
97.5°	83.3	85.0	86.7	88.3	89.5	90.3	91.0	91.7	92.5	92.5	92.5
100°	110.6	112.2	113.7	115.2	116.3	116.8	117.4	118.0	118.6	118.6	118.6
102.5°	139.2	140.4	141.6	142.8	143.9	144.6	145.3	146.0	146.8	146.9	147.1
105°	185.3	185.9	186.5	187.0	187.5	187.9	188.3	188.6	189.0	189.4	189.8
107.5°	232.6	233.5	234.4	235.2	235.6	235.6	235.6	235.6	235.6	235.7	235.9
110°	263.2	264.3	265.5	266.7	267.3	267.3	267.3	267.3	267.3	267.3	267.3



TEST NUMBER: P331634-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	296.2	297.4	298.5	299.6	300.1	300.0	299.8	299.7	299.5	299.1	298.6
115°	344.8	345.9	347.2	348.3	348.6	348.3	347.9	347.5	347.2	347.0	346.7
117.5°	393.6	395.2	396.7	398.3	398.5	397.4	396.3	395.3	394.3	393.7	393.3
120°	426.0	427.5	429.0	430.6	430.6	429.0	427.5	426.0	424.5	424.5	424.5
122.5°	455.8	457.7	459.5	461.3	461.8	460.6	459.6	458.6	457.4	457.0	456.5
125°	501.8	503.5	505.2	507.0	507.6	507.0	506.4	505.8	505.2	504.6	504.1
127.5°	547.1	549.3	551.5	553.6	554.4	553.7	553.0	552.3	551.6	551.0	550.3
130°	575.6	578.1	580.6	583.1	584.1	583.7	583.3	583.0	582.6	582.2	581.8
132.5°	606.7	608.8	610.8	612.9	613.9	614.0	614.1	614.1	614.2	613.4	612.5
135°	649.1	651.2	653.3	655.4	656.7	657.0	657.4	657.8	658.1	658.0	657.8
137.5°	693.2	694.9	696.6	698.4	699.5	700.0	700.5	701.0	701.5	701.4	701.2
140°	720.1	721.8	723.5	725.2	726.5	727.5	728.4	729.4	730.4	730.4	730.4
142.5°	747.5	749.2	751.0	752.7	753.9	754.5	755.2	755.8	756.5	756.6	756.8
145°	786.7	788.0	789.4	790.7	791.9	793.1	794.2	795.4	796.5	796.7	796.9
147.5°	822.2	823.8	825.4	827.0	828.2	829.0	829.7	830.4	831.2	831.6	832.1
150°	845.8	846.9	848.1	849.2	850.2	850.9	851.7	852.5	853.3	853.8	854.4
152.5°	867.1	868.2	869.4	870.6	871.6	872.5	873.4	874.3	875.2	876.0	876.7
155°	898.5	899.1	899.7	900.2	900.8	901.4	901.9	902.5	903.0	904.0	905.0
157.5°	925.6	926.0	926.3	926.8	927.1	927.5	927.8	928.2	928.5	929.8	931.1
160°	942.1	942.5	942.9	943.2	943.6	943.7	943.9	944.1	944.3	945.5	946.6
162.5°	956.9	957.0	957.1	957.2	957.3	957.5	957.7	957.9	958.0	959.3	960.6
165°	976.8	976.5	976.4	976.2	976.1	976.1	976.1	976.1	976.1	977.4	978.8
167.5°	993.2	992.6	992.0	991.5	991.2	991.2	991.1	991.1	991.0	992.4	993.7
170°	1002.1	1001.6	1001.0	1000.4	1000.1	999.9	999.7	999.4	999.3	1000.7	1001.9
172.5°	1008.3	1007.8	1007.2	1006.6	1006.3	1006.1	1005.8	1005.6	1005.5	1006.9	1008.1
175°	1015.9	1015.3	1014.8	1014.2	1013.7	1013.3	1013.0	1012.5	1012.2	1013.5	1014.9
177.5°	1019.1	1018.6	1018.2	1017.7	1017.4	1017.0	1016.8	1016.4	1016.2	1017.0	1018.0
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331634-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	582.6	584.6	585.6	585.6	586.7	586.2	585.7
5°	616.0	619.7	620.6	624.1	626.6	625.9	626.2
7.5°	649.4	655.3	661.2	663.9	664.3	665.9	666.5
10°	669.9	674.8	683.9	682.6	689.4	693.4	686.9
12.5°	689.6	696.2	702.6	704.3	708.2	709.5	706.9
15°	707.4	710.9	711.3	710.3	711.5	710.5	706.8
17.5°	690.8	685.0	673.5	668.0	663.7	657.2	654.6
20°	663.2	646.4	626.8	619.0	609.8	591.9	596.2
22.5°	603.7	584.6	565.0	542.2	531.2	514.2	513.2
25°	511.3	478.2	441.8	416.4	401.5	384.5	377.0
27.5°	397.5	355.9	326.1	311.0	297.2	283.8	283.2
30°	322.7	291.4	268.4	255.5	247.0	241.3	242.5
32.5°	272.0	250.6	235.0	224.3	218.1	213.8	213.7
35°	222.4	207.7	197.7	193.2	188.7	185.6	185.8
37.5°	190.3	181.5	175.9	171.0	168.2	166.6	165.7
40°	173.8	166.6	162.3	159.4	157.0	154.9	154.5
42.5°	160.9	154.9	150.6	148.3	146.1	144.6	144.2
45°	142.8	137.8	134.0	131.4	130.4	129.1	129.1
47.5°	127.0	122.2	119.2	117.5	115.9	114.9	114.9
50°	116.4	112.6	109.9	108.9	107.5	107.0	106.8
52.5°	106.9	104.0	102.1	101.4	100.8	100.1	100.2
55°	93.8	92.3	91.5	90.9	90.0	88.8	89.5
57.5°	83.0	81.6	79.6	77.7	76.8	75.9	76.3
60°	75.3	72.6	69.8	67.7	67.1	65.3	65.3
62.5°	65.6	61.7	58.4	57.2	56.6	55.8	55.6
65°	50.5	48.9	48.1	47.4	46.9	46.9	46.6
67.5°	41.8	41.2	40.3	40.1	39.8	39.6	39.5
70°	36.9	36.2	35.8	35.6	35.2	35.4	34.8
72.5°	32.3	31.7	31.6	31.1	30.8	30.8	30.4
75°	25.4	25.4	25.2	25.1	24.6	24.5	24.6
77.5°	19.5	19.6	19.3	19.2	19.2	19.2	19.0
80°	15.7	15.8	15.7	15.4	15.2	15.4	15.2
82.5°	12.4	12.1	12.1	12.0	12.0	11.9	11.8
85°	7.1	7.2	7.1	6.9	6.9	6.9	7.1
87.5°	8.4	8.4	8.4	8.4	8.4	8.4	8.4
90°	28.9	28.6	28.4	28.7	28.8	29.0	29.2
92.5°	27.6	27.6	27.7	27.7	27.7	27.8	27.8
95°	55.0	55.0	54.8	54.4	54.1	53.6	53.3
97.5°	92.5	92.5	92.5	92.4	92.4	92.3	92.3
100°	118.6	118.6	118.5	118.3	118.1	117.9	117.7
102.5°	147.2	147.4	147.3	147.1	147.0	146.8	146.6
105°	190.2	190.5	190.7	190.7	190.7	190.7	190.7
107.5°	236.1	236.2	235.8	235.0	234.1	233.2	232.3
110°	267.3	267.3	266.9	266.4	265.8	265.2	264.7



TEST NUMBER: P331634-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	298.2	297.7	297.2	296.9	296.4	296.0	295.6
115°	346.6	346.4	345.9	345.4	344.8	344.2	343.7
117.5°	392.9	392.4	391.8	391.3	390.7	390.1	389.6
120°	424.5	424.5	424.2	423.6	423.0	422.5	421.9
122.5°	456.1	455.6	455.2	454.8	454.3	453.9	453.5
125°	503.5	502.9	502.6	502.4	502.1	502.0	501.8
127.5°	549.6	548.9	548.2	547.6	547.0	546.4	545.8
130°	581.4	581.0	580.5	579.7	578.9	578.2	577.4
132.5°	611.7	610.8	610.1	609.5	608.9	608.3	607.7
135°	657.6	657.4	657.0	656.4	655.9	655.3	654.7
137.5°	701.0	700.9	700.4	699.6	698.9	698.1	697.3
140°	730.4	730.4	730.0	729.2	728.4	727.7	726.9
142.5°	756.9	757.1	756.8	756.0	755.3	754.5	753.7
145°	797.1	797.3	797.0	796.3	795.5	794.7	793.9
147.5°	832.5	832.9	832.8	832.1	831.3	830.6	829.8
150°	855.0	855.5	855.5	855.0	854.4	853.8	853.3
152.5°	877.4	878.1	878.1	877.4	876.7	876.0	875.2
155°	905.9	906.9	907.1	906.5	905.9	905.3	904.7
157.5°	932.4	933.7	933.8	933.0	932.0	931.1	930.2
160°	947.7	948.9	949.1	948.3	947.5	946.8	946.0
162.5°	961.9	963.2	963.5	962.5	961.6	960.7	959.8
165°	980.1	981.5	981.6	980.7	979.7	978.8	977.8
167.5°	995.1	996.3	996.5	995.6	994.5	993.6	992.6
170°	1003.3	1004.6	1004.7	1003.6	1002.5	1001.3	1000.1
172.5°	1009.5	1010.8	1010.9	1009.8	1008.7	1007.5	1006.3
175°	1016.2	1017.5	1017.6	1016.5	1015.3	1014.2	1013.1
177.5°	1018.9	1019.8	1019.8	1018.9	1018.0	1017.0	1016.2
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2

(END OF REPORT)