

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331669-935

Luminaire Tested: **SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331669-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5309.2 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331669-935
CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331669-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	33	33	26
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	29	28	23
3	79	70	63	58	70	63	57	53	50	46	43	39	36	34	28	26	25	20
4	72	62	55	49	65	56	50	45	45	41	37	35	32	29	25	23	22	18
5	66	55	48	42	59	50	44	39	40	36	32	31	28	26	23	21	19	16
6	61	50	42	37	55	45	39	34	37	32	28	28	25	23	21	19	17	14
7	57	45	38	32	51	41	34	30	33	29	25	26	23	20	19	17	16	13
8	52	41	34	29	47	37	31	27	30	26	22	24	21	18	18	16	14	12
9	49	37	30	26	44	34	28	24	28	23	20	22	19	16	17	14	13	11
10	46	34	27	23	41	31	25	21	26	21	18	20	17	15	15	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14941	14941	14941	14941
5°	16686	15034	13331	15034
10°	18513	14929	11555	14929
15°	19423	14710	9105	14710
20°	16838	14385	7878	14385
25°	11043	13942	7035	13942
30°	7433	13403	6367	13403
35°	6022	12727	5742	12727
40°	5354	11989	5313	11989
45°	4845	11125	4743	11125
50°	4411	10263	4393	10263
55°	4144	9315	4090	9315
60°	3468	8441	3426	8441
65°	2923	7664	3316	7664
70°	2705	6845	3125	6845
75°	2533	5958	2888	5958
80°	2334	4900	2566	4900
85°	2130	3872	2260	3872



TEST NUMBER: P331669-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	1.7
10°-20°	244.4	4.6
20°-30°	315.0	5.9
30°-40°	299.3	5.6
40°-50°	256.4	4.8
50°-60°	195.3	3.7
60°-70°	123.4	2.3
70°-80°	61.6	1.2
80°-90°	19.2	0.4
90°-100°	42.2	0.8
100°-110°	154.7	2.9
110°-120°	413.6	7.8
120°-130°	682.8	12.9
130°-140°	726.1	13.7
140°-150°	674.9	12.7
150°-160°	542.6	10.2
160°-170°	349.7	6.6
170°-180°	120.4	2.3
0°-30°	647.1	12.2
0°-40°	946.4	17.8
0°-60°	1398.1	26.3
0°-90°	1602.4	30.2
90°-120°	610.5	11.5
90°-150°	2694.3	50.7
90°-180°	3707.0	69.8
0°-180°	5309.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	925	925	925	925	925	
5°	1030	928	822	928	1030	102
15°	1162	880	545	880	1162	313
25°	620	783	395	783	620	294
35°	306	646	291	646	306	195
45°	212	487	208	487	212	164
55°	147	331	145	331	147	129
65°	76	201	87	201	76	78
75°	41	96	46	96	41	43
85°	12	21	12	21	12	13
90°	25	1	25	1	25	11
95°	39	60	39	60	39	37
105°	70	278	70	278	70	72
115°	75	526	75	526	75	188
125°	783	744	783	744	783	677
135°	951	921	951	921	951	733
145°	1085	1068	1085	1068	1085	678
155°	1177	1176	1177	1176	1177	543
165°	1237	1239	1237	1239	1237	349
175°	1260	1268	1260	1268	1260	120
180°	1265	1265	1265	1265	1265	



TEST NUMBER: P331669-935
 CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	962.9	963.7	964.5	962.7	962.7	961.1	957.8	955.2	948.0	946.9	946.9
5°	1029.5	1028.9	1030.2	1026.0	1020.2	1018.9	1012.8	1004.8	996.4	987.1	985.2
7.5°	1095.8	1094.8	1092.3	1091.5	1087.1	1077.4	1067.6	1057.0	1043.2	1029.6	1022.8
10°	1129.2	1139.8	1133.4	1122.1	1124.4	1109.3	1101.2	1087.4	1075.8	1055.6	1051.1
12.5°	1162.1	1166.3	1164.2	1157.9	1155.0	1144.5	1133.7	1121.6	1100.3	1082.1	1066.3
15°	1162.0	1168.1	1169.8	1167.8	1169.4	1168.7	1163.0	1153.0	1134.4	1114.4	1097.1
17.5°	1076.2	1080.5	1091.0	1098.1	1107.2	1126.2	1135.6	1139.3	1136.4	1125.1	1112.8
20°	980.0	972.9	1002.5	1017.6	1030.5	1062.6	1090.3	1100.9	1117.9	1117.7	1114.4
22.5°	843.7	845.3	873.4	891.3	928.9	961.0	992.6	1032.5	1065.5	1087.3	1100.0
25°	619.9	632.1	660.1	684.5	726.3	786.2	840.5	903.5	962.9	1010.0	1054.6
27.5°	465.5	466.5	488.6	511.3	536.1	585.0	653.5	728.8	813.6	883.5	964.0
30°	398.7	396.7	406.1	419.9	441.2	479.1	530.5	604.5	689.1	794.5	888.4
32.5°	351.4	351.5	358.5	368.8	386.3	411.9	447.2	507.2	587.2	690.9	800.9
35°	305.5	305.1	310.3	317.7	325.0	341.5	365.6	397.1	452.1	548.9	661.4
37.5°	272.5	274.0	276.5	281.1	289.2	298.3	312.9	334.0	373.2	430.4	525.0
40°	254.0	254.7	258.2	262.1	266.9	274.0	285.9	302.9	331.5	377.1	446.3
42.5°	237.0	237.6	240.2	243.7	247.5	254.7	264.5	279.2	302.5	338.0	395.1
45°	212.2	212.2	214.5	216.0	220.2	226.7	234.7	246.9	263.0	289.4	327.4
47.5°	188.9	189.0	190.5	193.2	195.9	200.9	208.8	218.8	230.5	250.9	283.3
50°	175.6	175.9	176.8	179.1	180.7	185.2	191.3	200.0	212.2	228.0	254.9
52.5°	164.7	164.5	165.7	166.8	167.8	171.1	175.6	183.3	194.2	207.9	230.3
55°	147.2	145.9	147.9	149.5	150.5	151.8	154.3	159.2	168.5	180.0	196.7
57.5°	125.4	124.8	126.2	127.7	130.7	134.2	136.4	139.5	144.3	152.6	169.2
60°	107.4	107.4	110.3	111.2	114.8	119.2	123.8	126.4	131.2	136.6	148.9
62.5°	91.4	91.7	93.1	94.0	96.0	101.5	107.9	113.5	118.0	123.3	131.4
65°	76.5	77.1	77.1	77.8	79.1	80.4	82.9	87.5	95.5	102.9	109.0
67.5°	64.9	65.2	65.3	66.0	66.3	67.7	68.7	70.8	72.6	79.6	87.2
70°	57.3	58.2	57.9	58.5	58.8	59.5	60.8	61.7	64.7	66.2	70.8
72.5°	50.0	50.7	50.7	51.1	51.9	52.0	53.0	54.0	55.9	57.3	59.7
75°	40.6	40.2	40.6	41.2	41.5	41.8	41.8	43.0	44.1	45.4	46.9
77.5°	31.3	31.6	31.5	31.6	31.6	32.2	32.1	32.7	33.7	34.4	35.1
80°	25.1	25.4	25.1	25.4	25.7	26.0	25.7	26.0	27.0	27.6	27.6
82.5°	19.5	19.5	19.7	19.7	19.8	19.9	20.3	20.4	21.1	20.9	21.2
85°	11.5	11.3	11.3	11.3	11.5	11.9	11.5	11.5	11.9	11.9	11.9
87.5°	9.0	9.2	9.1	9.0	9.0	8.9	8.6	8.7	8.3	8.3	7.7
90°	24.7	24.3	23.9	23.5	23.1	22.4	21.4	20.3	19.3	18.3	16.7
92.5°	24.7	24.5	24.2	24.0	23.8	23.3	22.8	22.3	21.8	21.3	20.4
95°	39.3	39.5	39.8	40.0	40.2	39.8	38.7	37.7	36.7	35.7	34.3
97.5°	52.5	52.3	52.1	51.8	51.6	51.1	50.2	49.4	48.6	47.8	44.5
100°	61.3	61.0	60.5	60.1	59.7	58.7	57.1	55.4	53.8	52.2	48.7
102.5°	65.7	65.2	64.6	64.0	63.5	62.1	60.0	57.9	55.8	53.6	48.6
105°	69.6	68.7	67.9	67.2	66.3	64.7	62.5	60.3	58.0	55.8	48.6
107.5°	71.5	70.8	69.9	69.1	68.4	69.1	71.3	73.6	75.9	78.2	144.7
110°	72.3	71.5	70.7	69.8	69.1	78.8	99.2	119.5	139.8	160.1	219.0



TEST NUMBER: P331669-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	73.0	72.4	71.7	71.1	70.4	107.2	181.4	255.6	329.8	404.0	418.5
115°	75.1	89.7	104.4	119.0	133.6	188.0	282.2	376.3	470.5	564.7	559.6
117.5°	306.4	354.6	402.7	450.8	498.9	534.4	557.2	580.0	602.7	625.5	622.0
120°	558.4	585.7	613.2	640.7	668.1	680.7	678.2	675.8	673.3	670.9	667.3
122.5°	696.7	702.1	707.4	712.7	718.0	720.0	718.5	717.0	715.6	714.1	710.2
125°	782.6	782.0	781.4	780.8	780.2	779.1	777.7	776.3	774.8	773.4	769.6
127.5°	836.7	836.6	836.5	836.4	836.3	835.2	833.1	831.0	829.0	826.9	824.0
130°	870.5	870.6	870.8	871.1	871.2	870.2	868.0	865.7	863.5	861.3	859.0
132.5°	903.4	903.6	903.8	904.0	904.2	903.4	901.5	899.5	897.6	895.7	893.5
135°	951.0	951.4	951.7	952.2	952.6	951.7	949.8	947.7	945.7	943.7	941.8
137.5°	994.4	995.1	995.7	996.4	997.1	996.4	994.5	992.5	990.5	988.5	986.4
140°	1021.5	1022.4	1023.5	1024.5	1025.5	1025.1	1023.3	1021.5	1019.6	1017.8	1015.5
142.5°	1047.8	1048.9	1049.8	1050.9	1051.9	1051.5	1049.9	1048.2	1046.5	1044.9	1042.3
145°	1084.6	1085.6	1086.7	1087.7	1088.6	1088.5	1087.0	1085.6	1084.2	1082.8	1079.3
147.5°	1117.0	1117.8	1118.7	1119.6	1120.4	1120.3	1119.3	1118.2	1117.1	1116.1	1112.7
150°	1136.8	1137.8	1138.8	1139.8	1140.8	1140.7	1139.5	1138.3	1137.1	1135.8	1132.6
152.5°	1153.7	1154.9	1156.3	1157.6	1159.0	1159.1	1157.9	1156.6	1155.4	1154.2	1151.1
155°	1177.1	1178.7	1180.3	1181.9	1183.5	1183.8	1182.6	1181.3	1180.1	1178.9	1176.5
157.5°	1198.4	1200.1	1201.6	1203.2	1204.8	1204.9	1203.5	1202.1	1200.8	1199.4	1197.7
160°	1210.9	1212.4	1213.8	1215.2	1216.6	1216.7	1215.5	1214.3	1213.1	1211.9	1210.7
162.5°	1221.2	1222.9	1224.7	1226.4	1228.1	1228.4	1226.9	1225.5	1224.2	1222.8	1221.8
165°	1236.6	1237.9	1239.4	1240.8	1242.3	1242.3	1240.8	1239.4	1237.9	1236.6	1236.0
167.5°	1246.2	1248.1	1249.9	1251.7	1253.5	1253.8	1252.3	1250.9	1249.5	1248.1	1247.5
170°	1252.1	1254.0	1255.8	1257.6	1259.4	1259.6	1258.2	1256.8	1255.3	1254.0	1253.5
172.5°	1256.5	1258.4	1260.2	1262.0	1263.9	1264.0	1262.6	1261.2	1259.7	1258.4	1257.9
175°	1260.3	1262.4	1264.4	1266.4	1268.5	1268.8	1267.4	1265.9	1264.6	1263.1	1262.7
177.5°	1262.7	1264.2	1265.7	1267.1	1268.6	1268.8	1267.6	1266.4	1265.3	1264.2	1264.0
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331669-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	947.4	945.5	943.7	939.0	936.7	931.5	930.7	930.5	923.9	917.4	915.6
5°	980.0	974.9	967.2	958.1	948.8	939.2	932.7	927.6	914.7	902.5	895.4
7.5°	1012.8	1001.8	988.4	971.4	957.2	941.2	929.4	918.8	900.5	883.0	871.2
10°	1037.2	1019.3	1001.6	978.1	959.8	941.8	925.1	910.6	890.0	866.9	850.4
12.5°	1052.4	1032.6	1008.2	985.3	961.6	938.7	916.3	897.7	873.6	849.6	830.1
15°	1073.0	1051.7	1022.2	989.4	958.8	928.9	903.2	880.0	848.5	819.9	796.1
17.5°	1089.8	1060.5	1028.7	990.8	955.5	917.5	884.3	854.7	819.7	785.1	757.2
20°	1095.1	1066.2	1029.5	991.6	949.8	905.1	869.4	837.2	799.6	762.0	729.9
22.5°	1091.7	1069.3	1028.5	983.1	940.3	893.5	853.3	815.9	774.2	735.8	698.5
25°	1069.1	1061.4	1022.8	973.3	924.4	870.0	823.5	782.6	735.0	693.9	653.3
27.5°	1016.2	1032.9	1008.9	956.1	901.8	843.5	791.2	744.7	695.3	648.9	608.6
30°	965.3	1003.5	993.2	944.3	883.6	826.3	767.5	718.9	666.2	618.6	578.8
32.5°	895.5	958.7	968.8	927.9	865.0	802.1	740.5	692.2	637.1	586.9	548.1
35°	784.5	879.1	922.5	896.4	833.4	765.6	701.9	645.7	590.3	540.8	502.2
37.5°	652.1	780.8	853.3	855.1	797.2	726.7	657.4	601.5	544.8	496.3	454.5
40°	566.2	705.8	800.0	820.9	772.0	695.8	625.7	568.8	513.5	465.9	418.0
42.5°	489.0	628.1	743.9	780.2	741.4	665.7	595.4	535.9	482.1	437.0	388.1
45°	395.5	517.0	644.6	709.6	688.1	617.9	543.7	487.2	436.6	397.7	350.8
47.5°	333.6	419.3	542.8	630.7	630.3	566.3	493.3	439.0	392.2	355.8	317.7
50°	298.3	373.0	477.5	577.1	585.5	531.8	462.4	408.6	365.0	326.7	296.1
52.5°	266.7	328.2	422.1	517.7	541.5	495.0	427.7	378.1	335.6	300.4	274.2
55°	225.4	272.9	344.4	433.8	469.8	437.0	377.1	330.9	296.4	266.9	244.4
57.5°	190.6	226.4	283.6	355.6	397.5	376.9	327.6	290.0	260.5	233.8	216.0
60°	168.8	198.0	246.6	306.8	353.0	338.5	296.4	261.4	236.3	213.2	196.5
62.5°	148.3	173.4	215.0	263.8	306.3	300.2	265.9	236.4	214.5	193.4	179.3
65°	119.2	137.6	170.0	208.4	242.5	245.3	220.6	200.6	181.0	164.3	151.8
67.5°	95.0	106.9	129.8	162.0	187.6	196.7	181.6	166.3	150.8	137.8	127.0
70°	80.1	89.7	106.4	132.5	155.9	165.6	156.9	145.0	131.5	120.9	111.6
72.5°	64.9	74.3	86.6	105.7	125.9	136.3	133.3	124.7	113.7	105.0	96.2
75°	48.9	51.7	60.1	73.0	88.8	97.7	100.0	95.5	86.8	80.1	74.9
77.5°	36.2	37.9	41.8	48.6	58.9	66.9	70.3	69.7	63.7	59.8	55.0
80°	28.9	29.9	31.9	34.7	42.4	50.5	52.7	52.7	48.6	46.9	42.1
82.5°	22.0	22.7	23.8	25.5	29.1	36.1	38.6	39.1	36.4	34.4	30.6
85°	12.6	12.2	12.8	13.9	14.5	16.4	20.2	20.9	20.2	17.7	16.7
87.5°	7.4	7.3	7.0	6.4	6.1	5.9	6.8	7.7	7.1	6.7	6.6
90°	15.1	13.4	11.8	9.9	7.7	5.4	3.2	0.9	3.2	5.4	7.7
92.5°	19.6	18.8	18.0	17.7	17.9	18.1	18.3	18.5	18.3	18.1	17.9
95°	32.9	31.4	30.0	32.6	39.3	46.1	52.8	59.5	52.8	46.1	39.3
97.5°	41.2	37.9	34.6	42.4	61.3	80.2	99.2	118.0	99.2	80.2	61.3
100°	45.3	41.8	38.3	50.5	78.4	106.2	134.1	162.0	134.1	106.2	78.4
102.5°	111.5	140.4	169.4	186.8	192.6	198.5	204.4	210.3	204.4	198.5	192.6
105°	166.9	222.4	277.9	302.6	296.5	290.4	284.4	278.3	284.4	290.4	296.5
107.5°	211.4	277.9	344.6	375.4	370.4	365.5	360.6	355.7	360.6	365.5	370.4
110°	277.8	336.5	395.3	422.6	418.3	414.1	409.7	405.4	409.7	414.1	418.3



TEST NUMBER: P331669-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	433.1	447.5	462.1	467.4	463.6	459.9	456.2	452.4	456.2	459.9	463.6
115°	554.6	549.5	544.4	540.1	536.7	533.2	529.8	526.3	529.8	533.2	536.7
117.5°	618.5	615.0	611.5	607.9	604.0	600.1	596.2	592.4	596.2	600.1	604.0
120°	663.6	660.0	656.3	652.9	649.9	646.8	643.8	640.7	643.8	646.8	649.9
122.5°	706.1	702.1	698.2	694.6	691.4	688.1	684.9	681.7	684.9	688.1	691.4
125°	765.7	761.8	757.9	754.7	752.1	749.4	746.7	744.2	746.7	749.4	752.1
127.5°	821.0	818.2	815.3	812.4	809.5	806.6	803.7	800.7	803.7	806.6	809.5
130°	856.8	854.5	852.3	849.5	846.4	843.1	839.8	836.5	839.8	843.1	846.4
132.5°	891.2	889.0	886.7	884.2	881.5	878.7	876.0	873.1	876.0	878.7	881.5
135°	940.0	938.1	936.3	933.8	930.6	927.3	924.0	920.8	924.0	927.3	930.6
137.5°	984.4	982.3	980.2	978.0	975.8	973.4	971.2	968.9	971.2	973.4	975.8
140°	1013.3	1011.1	1008.8	1006.9	1005.3	1003.7	1002.0	1000.4	1002.0	1003.7	1005.3
142.5°	1039.7	1037.2	1034.7	1032.6	1031.1	1029.7	1028.2	1026.7	1028.2	1029.7	1031.1
145°	1075.8	1072.4	1068.9	1067.3	1067.6	1067.7	1067.9	1068.2	1067.9	1067.7	1067.6
147.5°	1109.2	1105.9	1102.4	1101.1	1101.9	1102.7	1103.5	1104.2	1103.5	1102.7	1101.9
150°	1129.4	1126.1	1122.8	1122.0	1123.3	1124.8	1126.2	1127.7	1126.2	1124.8	1123.3
152.5°	1148.0	1144.9	1141.8	1141.1	1142.6	1144.2	1145.8	1147.4	1145.8	1144.2	1142.6
155°	1174.0	1171.6	1169.2	1168.8	1170.6	1172.5	1174.3	1176.1	1174.3	1172.5	1170.6
157.5°	1195.9	1194.3	1192.6	1192.5	1194.0	1195.6	1197.1	1198.7	1197.1	1195.6	1194.0
160°	1209.4	1208.2	1206.9	1206.9	1208.2	1209.4	1210.7	1211.9	1210.7	1209.4	1208.2
162.5°	1220.7	1219.6	1218.6	1218.7	1219.9	1221.1	1222.4	1223.6	1222.4	1221.1	1219.9
165°	1235.4	1234.7	1234.1	1234.4	1235.6	1236.8	1238.0	1239.3	1238.0	1236.8	1235.6
167.5°	1246.9	1246.4	1245.8	1246.1	1247.3	1248.5	1249.8	1251.0	1249.8	1248.5	1247.3
170°	1253.1	1252.8	1252.3	1252.8	1254.0	1255.2	1256.4	1257.6	1256.4	1255.2	1254.0
172.5°	1257.5	1257.1	1256.7	1257.1	1258.4	1259.6	1260.8	1262.0	1260.8	1259.6	1258.4
175°	1262.3	1261.9	1261.5	1262.0	1263.4	1264.8	1266.3	1267.7	1266.3	1264.8	1263.4
177.5°	1263.9	1263.7	1263.5	1264.0	1265.2	1266.3	1267.5	1268.6	1267.5	1266.3	1265.2
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331669-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	912.2	910.4	907.1	902.0	898.9	893.5	889.8	891.9	892.4	891.9	891.4
5°	887.8	881.0	871.7	862.6	854.3	845.3	840.2	837.9	833.4	830.9	829.6
7.5°	858.1	846.4	833.3	817.6	804.3	790.3	783.2	779.6	770.4	765.4	761.0
10°	835.9	817.6	804.4	783.9	771.4	753.0	740.5	740.8	728.2	721.2	716.0
12.5°	811.6	791.4	769.5	751.0	733.6	718.8	703.7	697.6	684.2	677.4	663.6
15°	771.0	747.5	724.4	699.3	681.7	658.8	637.0	610.3	588.8	570.1	564.9
17.5°	726.8	697.8	674.5	645.1	614.8	576.4	551.0	535.5	522.5	512.7	505.4
20°	696.5	666.8	642.1	597.7	556.9	530.8	512.2	500.3	486.8	476.2	470.4
22.5°	664.5	633.7	599.9	550.4	518.6	497.7	481.0	467.4	458.2	450.0	444.7
25°	619.2	585.5	529.9	495.8	470.1	448.2	436.6	428.3	418.6	407.3	402.3
27.5°	571.4	517.7	477.8	452.5	427.9	413.7	403.3	390.8	382.2	377.1	371.8
30°	535.6	482.0	450.8	423.1	405.8	390.0	377.8	370.7	362.4	353.7	350.2
32.5°	495.8	452.9	423.0	400.0	382.4	368.9	359.3	347.8	341.8	336.5	329.1
35°	446.3	413.8	386.5	367.8	351.1	340.2	328.9	322.2	311.3	306.8	303.8
37.5°	404.3	376.2	355.8	336.1	322.9	310.8	303.9	293.2	288.4	282.1	276.0
40°	380.6	353.0	333.5	317.4	302.6	293.5	284.9	276.2	269.1	266.2	258.8
42.5°	356.5	334.0	314.4	296.8	286.9	277.3	266.4	260.0	252.6	248.0	243.4
45°	323.1	303.2	286.5	272.0	261.1	251.2	244.0	233.4	229.3	219.9	216.0
47.5°	293.8	275.3	259.3	245.6	234.9	228.4	218.1	209.7	203.1	197.3	192.4
50°	272.9	257.5	242.1	229.9	220.2	210.9	200.4	196.1	185.8	183.0	180.0
52.5°	253.9	239.3	225.2	213.2	203.5	194.5	185.1	179.7	172.7	169.8	167.7
55°	227.3	213.2	199.7	189.1	179.4	170.0	164.3	157.6	154.3	152.1	149.5
57.5°	200.5	187.9	177.5	166.8	157.0	149.6	142.9	138.9	135.5	132.6	129.5
60°	183.6	171.3	162.0	152.1	142.2	136.0	130.9	126.1	122.2	117.7	116.4
62.5°	165.6	154.9	146.4	136.6	127.9	122.3	117.5	113.0	108.3	101.8	100.0
65°	140.9	132.5	123.5	115.5	107.7	102.3	95.1	90.1	88.1	87.5	87.1
67.5°	118.5	110.6	102.8	94.6	87.6	82.5	78.9	78.1	76.8	76.4	75.5
70°	103.5	96.2	88.4	80.7	74.0	73.0	71.7	70.4	68.8	68.2	67.5
72.5°	90.1	82.5	74.8	68.6	65.7	64.5	63.2	61.9	60.9	60.2	59.8
75°	69.1	62.1	56.9	54.7	53.0	52.1	50.2	49.2	48.6	47.6	47.3
77.5°	49.8	45.8	43.4	42.0	40.3	39.3	38.2	37.2	36.5	36.3	35.8
80°	38.0	36.0	34.4	32.5	31.9	30.6	30.2	29.3	29.6	28.6	28.6
82.5°	29.4	27.0	25.7	24.8	24.1	23.1	22.7	22.3	22.4	21.7	21.7
85°	15.2	14.5	13.9	13.2	13.2	12.2	12.6	12.2	12.2	11.5	11.3
87.5°	6.9	7.0	6.8	7.1	7.5	7.5	7.7	7.7	7.8	8.1	7.9
90°	9.9	11.8	13.4	15.1	16.7	18.3	19.3	20.3	21.4	22.4	23.1
92.5°	17.7	18.0	18.8	19.6	20.4	21.3	21.8	22.3	22.8	23.3	23.8
95°	32.6	30.0	31.4	32.9	34.3	35.7	36.7	37.7	38.7	39.8	40.2
97.5°	42.4	34.6	37.9	41.2	44.5	47.8	48.6	49.4	50.2	51.1	51.6
100°	50.5	38.3	41.8	45.3	48.7	52.2	53.8	55.4	57.1	58.7	59.7
102.5°	186.8	169.4	140.4	111.5	82.6	53.6	55.8	57.9	60.0	62.1	63.5
105°	302.6	277.9	222.4	166.9	111.3	55.8	58.0	60.3	62.5	64.7	66.3
107.5°	375.4	344.6	277.9	211.4	144.7	78.2	75.9	73.6	71.3	69.1	68.4
110°	422.6	395.3	336.5	277.8	219.0	160.1	139.8	119.5	99.2	78.8	69.1



TEST NUMBER: P331669-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	467.4	462.1	447.5	433.1	418.5	404.0	329.8	255.6	181.4	107.2	70.4
115°	540.1	544.4	549.5	554.6	559.6	564.7	470.5	376.3	282.2	188.0	133.6
117.5°	607.9	611.5	615.0	618.5	622.0	625.5	602.7	580.0	557.2	534.4	498.9
120°	652.9	656.3	660.0	663.6	667.3	670.9	673.3	675.8	678.2	680.7	668.1
122.5°	694.6	698.2	702.1	706.1	710.2	714.1	715.6	717.0	718.5	720.0	718.0
125°	754.7	757.9	761.8	765.7	769.6	773.4	774.8	776.3	777.7	779.1	780.2
127.5°	812.4	815.3	818.2	821.0	824.0	826.9	829.0	831.0	833.1	835.2	836.3
130°	849.5	852.3	854.5	856.8	859.0	861.3	863.5	865.7	868.0	870.2	871.2
132.5°	884.2	886.7	889.0	891.2	893.5	895.7	897.6	899.5	901.5	903.4	904.2
135°	933.8	936.3	938.1	940.0	941.8	943.7	945.7	947.7	949.8	951.7	952.6
137.5°	978.0	980.2	982.3	984.4	986.4	988.5	990.5	992.5	994.5	996.4	997.1
140°	1006.9	1008.8	1011.1	1013.3	1015.5	1017.8	1019.6	1021.5	1023.3	1025.1	1025.5
142.5°	1032.6	1034.7	1037.2	1039.7	1042.3	1044.9	1046.5	1048.2	1049.9	1051.5	1051.9
145°	1067.3	1068.9	1072.4	1075.8	1079.3	1082.8	1084.2	1085.6	1087.0	1088.5	1088.6
147.5°	1101.1	1102.4	1105.9	1109.2	1112.7	1116.1	1117.1	1118.2	1119.3	1120.3	1120.4
150°	1122.0	1122.8	1126.1	1129.4	1132.6	1135.8	1137.1	1138.3	1139.5	1140.7	1140.8
152.5°	1141.1	1141.8	1144.9	1148.0	1151.1	1154.2	1155.4	1156.6	1157.9	1159.1	1159.0
155°	1168.8	1169.2	1171.6	1174.0	1176.5	1178.9	1180.1	1181.3	1182.6	1183.8	1183.5
157.5°	1192.5	1192.6	1194.3	1195.9	1197.7	1199.4	1200.8	1202.1	1203.5	1204.9	1204.8
160°	1206.9	1206.9	1208.2	1209.4	1210.7	1211.9	1213.1	1214.3	1215.5	1216.7	1216.6
162.5°	1218.7	1218.6	1219.6	1220.7	1221.8	1222.8	1224.2	1225.5	1226.9	1228.4	1228.1
165°	1234.4	1234.1	1234.7	1235.4	1236.0	1236.6	1237.9	1239.4	1240.8	1242.3	1242.3
167.5°	1246.1	1245.8	1246.4	1246.9	1247.5	1248.1	1249.5	1250.9	1252.3	1253.8	1253.5
170°	1252.8	1252.3	1252.8	1253.1	1253.5	1254.0	1255.3	1256.8	1258.2	1259.6	1259.4
172.5°	1257.1	1256.7	1257.1	1257.5	1257.9	1258.4	1259.7	1261.2	1262.6	1264.0	1263.9
175°	1262.0	1261.5	1261.9	1262.3	1262.7	1263.1	1264.6	1265.9	1267.4	1268.8	1268.5
177.5°	1264.0	1263.5	1263.7	1263.9	1264.0	1264.2	1265.3	1266.4	1267.6	1268.8	1268.6
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331669-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	888.6	889.1	888.3	888.8	888.3	889.1	888.6	891.4	891.9	892.4	891.9
5°	827.9	824.1	823.5	822.5	823.5	824.1	827.9	829.6	830.9	833.4	837.9
7.5°	755.5	754.9	753.4	751.1	753.4	754.9	755.5	761.0	765.4	770.4	779.6
10°	708.9	707.4	707.1	704.8	707.1	707.4	708.9	716.0	721.2	728.2	740.8
12.5°	654.4	644.1	643.0	637.4	643.0	644.1	654.4	663.6	677.4	684.2	697.6
15°	557.2	555.3	548.9	544.7	548.9	555.3	557.2	564.9	570.1	588.8	610.3
17.5°	501.6	495.3	493.4	492.5	493.4	495.3	501.6	505.4	512.7	522.5	535.5
20°	465.9	460.1	459.2	458.5	459.2	460.1	465.9	470.4	476.2	486.8	500.3
22.5°	441.2	435.1	432.7	430.8	432.7	435.1	441.2	444.7	450.0	458.2	467.4
25°	399.0	396.7	395.5	394.9	395.5	396.7	399.0	402.3	407.3	418.6	428.3
27.5°	366.0	361.1	360.1	358.4	360.1	361.1	366.0	371.8	377.1	382.2	390.8
30°	347.2	345.6	343.4	341.5	343.4	345.6	347.2	350.2	353.7	362.4	370.7
32.5°	325.1	323.8	321.8	320.9	321.8	323.8	325.1	329.1	336.5	341.8	347.8
35°	300.7	296.1	294.2	291.3	294.2	296.1	300.7	303.8	306.8	311.3	322.2
37.5°	274.7	272.3	269.7	270.6	269.7	272.3	274.7	276.0	282.1	288.4	293.2
40°	254.7	253.0	252.4	252.1	252.4	253.0	254.7	258.8	266.2	269.1	276.2
42.5°	238.7	234.3	232.6	232.6	232.6	234.3	238.7	243.4	248.0	252.6	260.0
45°	214.5	210.3	207.4	207.7	207.4	210.3	214.5	216.0	219.9	229.3	233.4
47.5°	189.7	189.5	187.7	188.3	187.7	189.5	189.7	192.4	197.3	203.1	209.7
50°	177.8	175.9	174.6	174.9	174.6	175.9	177.8	180.0	183.0	185.8	196.1
52.5°	166.5	164.8	163.8	165.1	163.8	164.8	166.5	167.7	169.8	172.7	179.7
55°	147.9	145.9	145.7	145.3	145.7	145.9	147.9	149.5	152.1	154.3	157.6
57.5°	127.2	125.9	123.9	123.1	123.9	125.9	127.2	129.5	132.6	135.5	138.9
60°	112.2	109.6	106.4	106.1	106.4	109.6	112.2	116.4	117.7	122.2	126.1
62.5°	98.6	98.1	97.5	97.4	97.5	98.1	98.6	100.0	101.8	108.3	113.0
65°	86.5	86.2	86.5	86.8	86.5	86.2	86.5	87.1	87.5	88.1	90.1
67.5°	75.3	74.8	74.2	74.5	74.2	74.8	75.3	75.5	76.4	76.8	78.1
70°	66.9	66.6	66.2	66.2	66.2	66.6	66.9	67.5	68.2	68.8	70.4
72.5°	58.6	58.5	58.3	58.0	58.3	58.5	58.6	59.8	60.2	60.9	61.9
75°	46.9	46.3	46.3	46.3	46.3	46.3	46.9	47.3	47.6	48.6	49.2
77.5°	35.7	35.5	35.1	34.9	35.1	35.5	35.7	35.8	36.3	36.5	37.2
80°	28.3	28.0	27.6	27.6	27.6	28.0	28.3	28.6	28.6	29.6	29.3
82.5°	21.6	21.3	21.2	20.9	21.2	21.3	21.6	21.7	21.7	22.4	22.3
85°	11.5	11.9	11.5	12.2	11.5	11.9	11.5	11.3	11.5	12.2	12.2
87.5°	8.0	7.8	8.2	8.0	8.2	7.8	8.0	7.9	8.1	7.8	7.7
90°	23.5	23.9	24.3	24.7	24.3	23.9	23.5	23.1	22.4	21.4	20.3
92.5°	24.0	24.2	24.5	24.7	24.5	24.2	24.0	23.8	23.3	22.8	22.3
95°	40.0	39.8	39.5	39.3	39.5	39.8	40.0	40.2	39.8	38.7	37.7
97.5°	51.8	52.1	52.3	52.5	52.3	52.1	51.8	51.6	51.1	50.2	49.4
100°	60.1	60.5	61.0	61.3	61.0	60.5	60.1	59.7	58.7	57.1	55.4
102.5°	64.0	64.6	65.2	65.7	65.2	64.6	64.0	63.5	62.1	60.0	57.9
105°	67.2	67.9	68.7	69.6	68.7	67.9	67.2	66.3	64.7	62.5	60.3
107.5°	69.1	69.9	70.8	71.5	70.8	69.9	69.1	68.4	69.1	71.3	73.6
110°	69.8	70.7	71.5	72.3	71.5	70.7	69.8	69.1	78.8	99.2	119.5



TEST NUMBER: P331669-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	71.1	71.7	72.4	73.0	72.4	71.7	71.1	70.4	107.2	181.4	255.6
115°	119.0	104.4	89.7	75.1	89.7	104.4	119.0	133.6	188.0	282.2	376.3
117.5°	450.8	402.7	354.6	306.4	354.6	402.7	450.8	498.9	534.4	557.2	580.0
120°	640.7	613.2	585.7	558.4	585.7	613.2	640.7	668.1	680.7	678.2	675.8
122.5°	712.7	707.4	702.1	696.7	702.1	707.4	712.7	718.0	720.0	718.5	717.0
125°	780.8	781.4	782.0	782.6	782.0	781.4	780.8	780.2	779.1	777.7	776.3
127.5°	836.4	836.5	836.6	836.7	836.6	836.5	836.4	836.3	835.2	833.1	831.0
130°	871.1	870.8	870.6	870.5	870.6	870.8	871.1	871.2	870.2	868.0	865.7
132.5°	904.0	903.8	903.6	903.4	903.6	903.8	904.0	904.2	903.4	901.5	899.5
135°	952.2	951.7	951.4	951.0	951.4	951.7	952.2	952.6	951.7	949.8	947.7
137.5°	996.4	995.7	995.1	994.4	995.1	995.7	996.4	997.1	996.4	994.5	992.5
140°	1024.5	1023.5	1022.4	1021.5	1022.4	1023.5	1024.5	1025.5	1025.1	1023.3	1021.5
142.5°	1050.9	1049.8	1048.9	1047.8	1048.9	1049.8	1050.9	1051.9	1051.5	1049.9	1048.2
145°	1087.7	1086.7	1085.6	1084.6	1085.6	1086.7	1087.7	1088.6	1088.5	1087.0	1085.6
147.5°	1119.6	1118.7	1117.8	1117.0	1117.8	1118.7	1119.6	1120.4	1120.3	1119.3	1118.2
150°	1139.8	1138.8	1137.8	1136.8	1137.8	1138.8	1139.8	1140.8	1140.7	1139.5	1138.3
152.5°	1157.6	1156.3	1154.9	1153.7	1154.9	1156.3	1157.6	1159.0	1159.1	1157.9	1156.6
155°	1181.9	1180.3	1178.7	1177.1	1178.7	1180.3	1181.9	1183.5	1183.8	1182.6	1181.3
157.5°	1203.2	1201.6	1200.1	1198.4	1200.1	1201.6	1203.2	1204.8	1204.9	1203.5	1202.1
160°	1215.2	1213.8	1212.4	1210.9	1212.4	1213.8	1215.2	1216.6	1216.7	1215.5	1214.3
162.5°	1226.4	1224.7	1222.9	1221.2	1222.9	1224.7	1226.4	1228.1	1228.4	1226.9	1225.5
165°	1240.8	1239.4	1237.9	1236.6	1237.9	1239.4	1240.8	1242.3	1242.3	1240.8	1239.4
167.5°	1251.7	1249.9	1248.1	1246.2	1248.1	1249.9	1251.7	1253.5	1253.8	1252.3	1250.9
170°	1257.6	1255.8	1254.0	1252.1	1254.0	1255.8	1257.6	1259.4	1259.6	1258.2	1256.8
172.5°	1262.0	1260.2	1258.4	1256.5	1258.4	1260.2	1262.0	1263.9	1264.0	1262.6	1261.2
175°	1266.4	1264.4	1262.4	1260.3	1262.4	1264.4	1266.4	1268.5	1268.8	1267.4	1265.9
177.5°	1267.1	1265.7	1264.2	1262.7	1264.2	1265.7	1267.1	1268.6	1268.8	1267.6	1266.4
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331669-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	889.8	893.5	898.9	902.0	907.1	910.4	912.2	915.6	917.4	923.9	930.5
5°	840.2	845.3	854.3	862.6	871.7	881.0	887.8	895.4	902.5	914.7	927.6
7.5°	783.2	790.3	804.3	817.6	833.3	846.4	858.1	871.2	883.0	900.5	918.8
10°	740.5	753.0	771.4	783.9	804.4	817.6	835.9	850.4	866.9	890.0	910.6
12.5°	703.7	718.8	733.6	751.0	769.5	791.4	811.6	830.1	849.6	873.6	897.7
15°	637.0	658.8	681.7	699.3	724.4	747.5	771.0	796.1	819.9	848.5	880.0
17.5°	551.0	576.4	614.8	645.1	674.5	697.8	726.8	757.2	785.1	819.7	854.7
20°	512.2	530.8	556.9	597.7	642.1	666.8	696.5	729.9	762.0	799.6	837.2
22.5°	481.0	497.7	518.6	550.4	599.9	633.7	664.5	698.5	735.8	774.2	815.9
25°	436.6	448.2	470.1	495.8	529.9	585.5	619.2	653.3	693.9	735.0	782.6
27.5°	403.3	413.7	427.9	452.5	477.8	517.7	571.4	608.6	648.9	695.3	744.7
30°	377.8	390.0	405.8	423.1	450.8	482.0	535.6	578.8	618.6	666.2	718.9
32.5°	359.3	368.9	382.4	400.0	423.0	452.9	495.8	548.1	586.9	637.1	692.2
35°	328.9	340.2	351.1	367.8	386.5	413.8	446.3	502.2	540.8	590.3	645.7
37.5°	303.9	310.8	322.9	336.1	355.8	376.2	404.3	454.5	496.3	544.8	601.5
40°	284.9	293.5	302.6	317.4	333.5	353.0	380.6	418.0	465.9	513.5	568.8
42.5°	266.4	277.3	286.9	296.8	314.4	334.0	356.5	388.1	437.0	482.1	535.9
45°	244.0	251.2	261.1	272.0	286.5	303.2	323.1	350.8	397.7	436.6	487.2
47.5°	218.1	228.4	234.9	245.6	259.3	275.3	293.8	317.7	355.8	392.2	439.0
50°	200.4	210.9	220.2	229.9	242.1	257.5	272.9	296.1	326.7	365.0	408.6
52.5°	185.1	194.5	203.5	213.2	225.2	239.3	253.9	274.2	300.4	335.6	378.1
55°	164.3	170.0	179.4	189.1	199.7	213.2	227.3	244.4	266.9	296.4	330.9
57.5°	142.9	149.6	157.0	166.8	177.5	187.9	200.5	216.0	233.8	260.5	290.0
60°	130.9	136.0	142.2	152.1	162.0	171.3	183.6	196.5	213.2	236.3	261.4
62.5°	117.5	122.3	127.9	136.6	146.4	154.9	165.6	179.3	193.4	214.5	236.4
65°	95.1	102.3	107.7	115.5	123.5	132.5	140.9	151.8	164.3	181.0	200.6
67.5°	78.9	82.5	87.6	94.6	102.8	110.6	118.5	127.0	137.8	150.8	166.3
70°	71.7	73.0	74.0	80.7	88.4	96.2	103.5	111.6	120.9	131.5	145.0
72.5°	63.2	64.5	65.7	68.6	74.8	82.5	90.1	96.2	105.0	113.7	124.7
75°	50.2	52.1	53.0	54.7	56.9	62.1	69.1	74.9	80.1	86.8	95.5
77.5°	38.2	39.3	40.3	42.0	43.4	45.8	49.8	55.0	59.8	63.7	69.7
80°	30.2	30.6	31.9	32.5	34.4	36.0	38.0	42.1	46.9	48.6	52.7
82.5°	22.7	23.1	24.1	24.8	25.7	27.0	29.4	30.6	34.4	36.4	39.1
85°	12.6	12.2	13.2	13.2	13.9	14.5	15.2	16.7	17.7	20.2	20.9
87.5°	7.7	7.5	7.5	7.1	6.8	7.0	6.9	6.6	6.7	7.1	7.7
90°	19.3	18.3	16.7	15.1	13.4	11.8	9.9	7.7	5.4	3.2	0.9
92.5°	21.8	21.3	20.4	19.6	18.8	18.0	17.7	17.9	18.1	18.3	18.5
95°	36.7	35.7	34.3	32.9	31.4	30.0	32.6	39.3	46.1	52.8	59.5
97.5°	48.6	47.8	44.5	41.2	37.9	34.6	42.4	61.3	80.2	99.2	118.0
100°	53.8	52.2	48.7	45.3	41.8	38.3	50.5	78.4	106.2	134.1	162.0
102.5°	55.8	53.6	82.6	111.5	140.4	169.4	186.8	192.6	198.5	204.4	210.3
105°	58.0	55.8	111.3	166.9	222.4	277.9	302.6	296.5	290.4	284.4	278.3
107.5°	75.9	78.2	144.7	211.4	277.9	344.6	375.4	370.4	365.5	360.6	355.7
110°	139.8	160.1	219.0	277.8	336.5	395.3	422.6	418.3	414.1	409.7	405.4



TEST NUMBER: P331669-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	329.8	404.0	418.5	433.1	447.5	462.1	467.4	463.6	459.9	456.2	452.4
115°	470.5	564.7	559.6	554.6	549.5	544.4	540.1	536.7	533.2	529.8	526.3
117.5°	602.7	625.5	622.0	618.5	615.0	611.5	607.9	604.0	600.1	596.2	592.4
120°	673.3	670.9	667.3	663.6	660.0	656.3	652.9	649.9	646.8	643.8	640.7
122.5°	715.6	714.1	710.2	706.1	702.1	698.2	694.6	691.4	688.1	684.9	681.7
125°	774.8	773.4	769.6	765.7	761.8	757.9	754.7	752.1	749.4	746.7	744.2
127.5°	829.0	826.9	824.0	821.0	818.2	815.3	812.4	809.5	806.6	803.7	800.7
130°	863.5	861.3	859.0	856.8	854.5	852.3	849.5	846.4	843.1	839.8	836.5
132.5°	897.6	895.7	893.5	891.2	889.0	886.7	884.2	881.5	878.7	876.0	873.1
135°	945.7	943.7	941.8	940.0	938.1	936.3	933.8	930.6	927.3	924.0	920.8
137.5°	990.5	988.5	986.4	984.4	982.3	980.2	978.0	975.8	973.4	971.2	968.9
140°	1019.6	1017.8	1015.5	1013.3	1011.1	1008.8	1006.9	1005.3	1003.7	1002.0	1000.4
142.5°	1046.5	1044.9	1042.3	1039.7	1037.2	1034.7	1032.6	1031.1	1029.7	1028.2	1026.7
145°	1084.2	1082.8	1079.3	1075.8	1072.4	1068.9	1067.3	1067.6	1067.7	1067.9	1068.2
147.5°	1117.1	1116.1	1112.7	1109.2	1105.9	1102.4	1101.1	1101.9	1102.7	1103.5	1104.2
150°	1137.1	1135.8	1132.6	1129.4	1126.1	1122.8	1122.0	1123.3	1124.8	1126.2	1127.7
152.5°	1155.4	1154.2	1151.1	1148.0	1144.9	1141.8	1141.1	1142.6	1144.2	1145.8	1147.4
155°	1180.1	1178.9	1176.5	1174.0	1171.6	1169.2	1168.8	1170.6	1172.5	1174.3	1176.1
157.5°	1200.8	1199.4	1197.7	1195.9	1194.3	1192.6	1192.5	1194.0	1195.6	1197.1	1198.7
160°	1213.1	1211.9	1210.7	1209.4	1208.2	1206.9	1206.9	1208.2	1209.4	1210.7	1211.9
162.5°	1224.2	1222.8	1221.8	1220.7	1219.6	1218.6	1218.7	1219.9	1221.1	1222.4	1223.6
165°	1237.9	1236.6	1236.0	1235.4	1234.7	1234.1	1234.4	1235.6	1236.8	1238.0	1239.3
167.5°	1249.5	1248.1	1247.5	1246.9	1246.4	1245.8	1246.1	1247.3	1248.5	1249.8	1251.0
170°	1255.3	1254.0	1253.5	1253.1	1252.8	1252.3	1252.8	1254.0	1255.2	1256.4	1257.6
172.5°	1259.7	1258.4	1257.9	1257.5	1257.1	1256.7	1257.1	1258.4	1259.6	1260.8	1262.0
175°	1264.6	1263.1	1262.7	1262.3	1261.9	1261.5	1262.0	1263.4	1264.8	1266.3	1267.7
177.5°	1265.3	1264.2	1264.0	1263.9	1263.7	1263.5	1264.0	1265.2	1266.3	1267.5	1268.6
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331669-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	930.7	931.5	936.7	939.0	943.7	945.5	947.4	946.9	946.9	948.0	955.2
5°	932.7	939.2	948.8	958.1	967.2	974.9	980.0	985.2	987.1	996.4	1004.8
7.5°	929.4	941.2	957.2	971.4	988.4	1001.8	1012.8	1022.8	1029.6	1043.2	1057.0
10°	925.1	941.8	959.8	978.1	1001.6	1019.3	1037.2	1051.1	1055.6	1075.8	1087.4
12.5°	916.3	938.7	961.6	985.3	1008.2	1032.6	1052.4	1066.3	1082.1	1100.3	1121.6
15°	903.2	928.9	958.8	989.4	1022.2	1051.7	1073.0	1097.1	1114.4	1134.4	1153.0
17.5°	884.3	917.5	955.5	990.8	1028.7	1060.5	1089.8	1112.8	1125.1	1136.4	1139.3
20°	869.4	905.1	949.8	991.6	1029.5	1066.2	1095.1	1114.4	1117.7	1117.9	1100.9
22.5°	853.3	893.5	940.3	983.1	1028.5	1069.3	1091.7	1100.0	1087.3	1065.5	1032.5
25°	823.5	870.0	924.4	973.3	1022.8	1061.4	1069.1	1054.6	1010.0	962.9	903.5
27.5°	791.2	843.5	901.8	956.1	1008.9	1032.9	1016.2	964.0	883.5	813.6	728.8
30°	767.5	826.3	883.6	944.3	993.2	1003.5	965.3	888.4	794.5	689.1	604.5
32.5°	740.5	802.1	865.0	927.9	968.8	958.7	895.5	800.9	690.9	587.2	507.2
35°	701.9	765.6	833.4	896.4	922.5	879.1	784.5	661.4	548.9	452.1	397.1
37.5°	657.4	726.7	797.2	855.1	853.3	780.8	652.1	525.0	430.4	373.2	334.0
40°	625.7	695.8	772.0	820.9	800.0	705.8	566.2	446.3	377.1	331.5	302.9
42.5°	595.4	665.7	741.4	780.2	743.9	628.1	489.0	395.1	338.0	302.5	279.2
45°	543.7	617.9	688.1	709.6	644.6	517.0	395.5	327.4	289.4	263.0	246.9
47.5°	493.3	566.3	630.3	630.7	542.8	419.3	333.6	283.3	250.9	230.5	218.8
50°	462.4	531.8	585.5	577.1	477.5	373.0	298.3	254.9	228.0	212.2	200.0
52.5°	427.7	495.0	541.5	517.7	422.1	328.2	266.7	230.3	207.9	194.2	183.3
55°	377.1	437.0	469.8	433.8	344.4	272.9	225.4	196.7	180.0	168.5	159.2
57.5°	327.6	376.9	397.5	355.6	283.6	226.4	190.6	169.2	152.6	144.3	139.5
60°	296.4	338.5	353.0	306.8	246.6	198.0	168.8	148.9	136.6	131.2	126.4
62.5°	265.9	300.2	306.3	263.8	215.0	173.4	148.3	131.4	123.3	118.0	113.5
65°	220.6	245.3	242.5	208.4	170.0	137.6	119.2	109.0	102.9	95.5	87.5
67.5°	181.6	196.7	187.6	162.0	129.8	106.9	95.0	87.2	79.6	72.6	70.8
70°	156.9	165.6	155.9	132.5	106.4	89.7	80.1	70.8	66.2	64.7	61.7
72.5°	133.3	136.3	125.9	105.7	86.6	74.3	64.9	59.7	57.3	55.9	54.0
75°	100.0	97.7	88.8	73.0	60.1	51.7	48.9	46.9	45.4	44.1	43.0
77.5°	70.3	66.9	58.9	48.6	41.8	37.9	36.2	35.1	34.4	33.7	32.7
80°	52.7	50.5	42.4	34.7	31.9	29.9	28.9	27.6	27.6	27.0	26.0
82.5°	38.6	36.1	29.1	25.5	23.8	22.7	22.0	21.2	20.9	21.1	20.4
85°	20.2	16.4	14.5	13.9	12.8	12.2	12.6	11.9	11.9	11.9	11.5
87.5°	6.8	5.9	6.1	6.4	7.0	7.3	7.4	7.7	8.3	8.3	8.7
90°	3.2	5.4	7.7	9.9	11.8	13.4	15.1	16.7	18.3	19.3	20.3
92.5°	18.3	18.1	17.9	17.7	18.0	18.8	19.6	20.4	21.3	21.8	22.3
95°	52.8	46.1	39.3	32.6	30.0	31.4	32.9	34.3	35.7	36.7	37.7
97.5°	99.2	80.2	61.3	42.4	34.6	37.9	41.2	44.5	47.8	48.6	49.4
100°	134.1	106.2	78.4	50.5	38.3	41.8	45.3	48.7	52.2	53.8	55.4
102.5°	204.4	198.5	192.6	186.8	169.4	140.4	111.5	82.6	53.6	55.8	57.9
105°	284.4	290.4	296.5	302.6	277.9	222.4	166.9	111.3	55.8	58.0	60.3
107.5°	360.6	365.5	370.4	375.4	344.6	277.9	211.4	144.7	78.2	75.9	73.6
110°	409.7	414.1	418.3	422.6	395.3	336.5	277.8	219.0	160.1	139.8	119.5



TEST NUMBER: P331669-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	456.2	459.9	463.6	467.4	462.1	447.5	433.1	418.5	404.0	329.8	255.6
115°	529.8	533.2	536.7	540.1	544.4	549.5	554.6	559.6	564.7	470.5	376.3
117.5°	596.2	600.1	604.0	607.9	611.5	615.0	618.5	622.0	625.5	602.7	580.0
120°	643.8	646.8	649.9	652.9	656.3	660.0	663.6	667.3	670.9	673.3	675.8
122.5°	684.9	688.1	691.4	694.6	698.2	702.1	706.1	710.2	714.1	715.6	717.0
125°	746.7	749.4	752.1	754.7	757.9	761.8	765.7	769.6	773.4	774.8	776.3
127.5°	803.7	806.6	809.5	812.4	815.3	818.2	821.0	824.0	826.9	829.0	831.0
130°	839.8	843.1	846.4	849.5	852.3	854.5	856.8	859.0	861.3	863.5	865.7
132.5°	876.0	878.7	881.5	884.2	886.7	889.0	891.2	893.5	895.7	897.6	899.5
135°	924.0	927.3	930.6	933.8	936.3	938.1	940.0	941.8	943.7	945.7	947.7
137.5°	971.2	973.4	975.8	978.0	980.2	982.3	984.4	986.4	988.5	990.5	992.5
140°	1002.0	1003.7	1005.3	1006.9	1008.8	1011.1	1013.3	1015.5	1017.8	1019.6	1021.5
142.5°	1028.2	1029.7	1031.1	1032.6	1034.7	1037.2	1039.7	1042.3	1044.9	1046.5	1048.2
145°	1067.9	1067.7	1067.6	1067.3	1068.9	1072.4	1075.8	1079.3	1082.8	1084.2	1085.6
147.5°	1103.5	1102.7	1101.9	1101.1	1102.4	1105.9	1109.2	1112.7	1116.1	1117.1	1118.2
150°	1126.2	1124.8	1123.3	1122.0	1122.8	1126.1	1129.4	1132.6	1135.8	1137.1	1138.3
152.5°	1145.8	1144.2	1142.6	1141.1	1141.8	1144.9	1148.0	1151.1	1154.2	1155.4	1156.6
155°	1174.3	1172.5	1170.6	1168.8	1169.2	1171.6	1174.0	1176.5	1178.9	1180.1	1181.3
157.5°	1197.1	1195.6	1194.0	1192.5	1192.6	1194.3	1195.9	1197.7	1199.4	1200.8	1202.1
160°	1210.7	1209.4	1208.2	1206.9	1206.9	1208.2	1209.4	1210.7	1211.9	1213.1	1214.3
162.5°	1222.4	1221.1	1219.9	1218.7	1218.6	1219.6	1220.7	1221.8	1222.8	1224.2	1225.5
165°	1238.0	1236.8	1235.6	1234.4	1234.1	1234.7	1235.4	1236.0	1236.6	1237.9	1239.4
167.5°	1249.8	1248.5	1247.3	1246.1	1245.8	1246.4	1246.9	1247.5	1248.1	1249.5	1250.9
170°	1256.4	1255.2	1254.0	1252.8	1252.3	1252.8	1253.1	1253.5	1254.0	1255.3	1256.8
172.5°	1260.8	1259.6	1258.4	1257.1	1256.7	1257.1	1257.5	1257.9	1258.4	1259.7	1261.2
175°	1266.3	1264.8	1263.4	1262.0	1261.5	1261.9	1262.3	1262.7	1263.1	1264.6	1265.9
177.5°	1267.5	1266.3	1265.2	1264.0	1263.5	1263.7	1263.9	1264.0	1264.2	1265.3	1266.4
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331669-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	957.8	961.1	962.7	962.7	964.5	963.7	962.9
5°	1012.8	1018.9	1020.2	1026.0	1030.2	1028.9	1029.5
7.5°	1067.6	1077.4	1087.1	1091.5	1092.3	1094.8	1095.8
10°	1101.2	1109.3	1124.4	1122.1	1133.4	1139.8	1129.2
12.5°	1133.7	1144.5	1155.0	1157.9	1164.2	1166.3	1162.1
15°	1163.0	1168.7	1169.4	1167.8	1169.8	1168.1	1162.0
17.5°	1135.6	1126.2	1107.2	1098.1	1091.0	1080.5	1076.2
20°	1090.3	1062.6	1030.5	1017.6	1002.5	972.9	980.0
22.5°	992.6	961.0	928.9	891.3	873.4	845.3	843.7
25°	840.5	786.2	726.3	684.5	660.1	632.1	619.9
27.5°	653.5	585.0	536.1	511.3	488.6	466.5	465.5
30°	530.5	479.1	441.2	419.9	406.1	396.7	398.7
32.5°	447.2	411.9	386.3	368.8	358.5	351.5	351.4
35°	365.6	341.5	325.0	317.7	310.3	305.1	305.5
37.5°	312.9	298.3	289.2	281.1	276.5	274.0	272.5
40°	285.9	274.0	266.9	262.1	258.2	254.7	254.0
42.5°	264.5	254.7	247.5	243.7	240.2	237.6	237.0
45°	234.7	226.7	220.2	216.0	214.5	212.2	212.2
47.5°	208.8	200.9	195.9	193.2	190.5	189.0	188.9
50°	191.3	185.2	180.7	179.1	176.8	175.9	175.6
52.5°	175.6	171.1	167.8	166.8	165.7	164.5	164.7
55°	154.3	151.8	150.5	149.5	147.9	145.9	147.2
57.5°	136.4	134.2	130.7	127.7	126.2	124.8	125.4
60°	123.8	119.2	114.8	111.2	110.3	107.4	107.4
62.5°	107.9	101.5	96.0	94.0	93.1	91.7	91.4
65°	82.9	80.4	79.1	77.8	77.1	77.1	76.5
67.5°	68.7	67.7	66.3	66.0	65.3	65.2	64.9
70°	60.8	59.5	58.8	58.5	57.9	58.2	57.3
72.5°	53.0	52.0	51.9	51.1	50.7	50.7	50.0
75°	41.8	41.8	41.5	41.2	40.6	40.2	40.6
77.5°	32.1	32.2	31.6	31.6	31.5	31.6	31.3
80°	25.7	26.0	25.7	25.4	25.1	25.4	25.1
82.5°	20.3	19.9	19.8	19.7	19.7	19.5	19.5
85°	11.5	11.9	11.5	11.3	11.3	11.3	11.5
87.5°	8.6	8.9	9.0	9.0	9.1	9.2	9.0
90°	21.4	22.4	23.1	23.5	23.9	24.3	24.7
92.5°	22.8	23.3	23.8	24.0	24.2	24.5	24.7
95°	38.7	39.8	40.2	40.0	39.8	39.5	39.3
97.5°	50.2	51.1	51.6	51.8	52.1	52.3	52.5
100°	57.1	58.7	59.7	60.1	60.5	61.0	61.3
102.5°	60.0	62.1	63.5	64.0	64.6	65.2	65.7
105°	62.5	64.7	66.3	67.2	67.9	68.7	69.6
107.5°	71.3	69.1	68.4	69.1	69.9	70.8	71.5
110°	99.2	78.8	69.1	69.8	70.7	71.5	72.3



TEST NUMBER: P331669-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	181.4	107.2	70.4	71.1	71.7	72.4	73.0
115°	282.2	188.0	133.6	119.0	104.4	89.7	75.1
117.5°	557.2	534.4	498.9	450.8	402.7	354.6	306.4
120°	678.2	680.7	668.1	640.7	613.2	585.7	558.4
122.5°	718.5	720.0	718.0	712.7	707.4	702.1	696.7
125°	777.7	779.1	780.2	780.8	781.4	782.0	782.6
127.5°	833.1	835.2	836.3	836.4	836.5	836.6	836.7
130°	868.0	870.2	871.2	871.1	870.8	870.6	870.5
132.5°	901.5	903.4	904.2	904.0	903.8	903.6	903.4
135°	949.8	951.7	952.6	952.2	951.7	951.4	951.0
137.5°	994.5	996.4	997.1	996.4	995.7	995.1	994.4
140°	1023.3	1025.1	1025.5	1024.5	1023.5	1022.4	1021.5
142.5°	1049.9	1051.5	1051.9	1050.9	1049.8	1048.9	1047.8
145°	1087.0	1088.5	1088.6	1087.7	1086.7	1085.6	1084.6
147.5°	1119.3	1120.3	1120.4	1119.6	1118.7	1117.8	1117.0
150°	1139.5	1140.7	1140.8	1139.8	1138.8	1137.8	1136.8
152.5°	1157.9	1159.1	1159.0	1157.6	1156.3	1154.9	1153.7
155°	1182.6	1183.8	1183.5	1181.9	1180.3	1178.7	1177.1
157.5°	1203.5	1204.9	1204.8	1203.2	1201.6	1200.1	1198.4
160°	1215.5	1216.7	1216.6	1215.2	1213.8	1212.4	1210.9
162.5°	1226.9	1228.4	1228.1	1226.4	1224.7	1222.9	1221.2
165°	1240.8	1242.3	1242.3	1240.8	1239.4	1237.9	1236.6
167.5°	1252.3	1253.8	1253.5	1251.7	1249.9	1248.1	1246.2
170°	1258.2	1259.6	1259.4	1257.6	1255.8	1254.0	1252.1
172.5°	1262.6	1264.0	1263.9	1262.0	1260.2	1258.4	1256.5
175°	1267.4	1268.8	1268.5	1266.4	1264.4	1262.4	1260.3
177.5°	1267.6	1268.8	1268.6	1267.1	1265.7	1264.2	1262.7
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9

(END OF REPORT)