

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331670-935

Luminaire Tested: **SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331670-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4917.8 lumens  
Efficiency: N/A  
Efficacy: 99.6 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331670-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331670-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	36	35	35	28
2	86	79	74	69	78	72	67	63	58	54	52	45	42	41	32	31	30	25
3	79	70	63	58	71	64	58	53	51	47	44	40	37	35	29	28	26	22
4	73	63	55	50	65	57	50	46	46	41	38	36	33	30	27	25	23	19
5	67	56	48	43	60	51	44	39	41	37	33	32	29	27	24	22	21	17
6	62	50	43	37	55	46	39	34	37	33	29	30	26	24	22	20	18	15
7	57	45	38	33	51	42	35	30	34	29	26	27	24	21	20	18	17	14
8	53	41	34	29	48	38	31	27	31	26	23	25	21	19	19	17	15	13
9	49	38	31	26	45	35	28	24	29	24	21	23	20	17	18	15	14	11
10	46	35	28	23	42	32	26	22	26	22	19	21	18	16	16	14	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	14941	14941	14941	14941
5°	16686	15034	13331	15034
10°	18513	14929	11555	14929
15°	19423	14710	9105	14710
20°	16838	14385	7878	14385
25°	11043	13942	7035	13942
30°	7433	13403	6367	13403
35°	6022	12727	5742	12727
40°	5354	11989	5313	11989
45°	4845	11125	4743	11125
50°	4411	10263	4393	10263
55°	4144	9315	4090	9315
60°	3468	8441	3426	8441
65°	2923	7664	3316	7664
70°	2705	6845	3125	6845
75°	2533	5958	2888	5958
80°	2334	4900	2566	4900
85°	2130	3872	2260	3872



TEST NUMBER: P331670-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	87.7	1.8
10°-20°	244.4	5.0
20°-30°	315.0	6.4
30°-40°	299.3	6.1
40°-50°	256.4	5.2
50°-60°	195.3	4.0
60°-70°	123.4	2.5
70°-80°	61.6	1.3
80°-90°	20.8	0.4
90°-100°	75.1	1.5
100°-110°	233.2	4.7
110°-120°	398.7	8.1
120°-130°	524.3	10.7
130°-140°	588.5	12.0
140°-150°	577.0	11.7
150°-160°	484.0	9.8
160°-170°	321.0	6.5
170°-180°	112.2	2.3
0°-30°	647.1	13.2
0°-40°	946.4	19.2
0°-60°	1398.1	28.4
0°-90°	1604.0	32.6
90°-120°	707.0	14.4
90°-150°	2396.8	48.7
90°-180°	3314.0	67.4
0°-180°	4917.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	925	925	925	925	925	
5°	1030	928	822	928	1030	102
15°	1162	880	545	880	1162	313
25°	620	783	395	783	620	294
35°	306	646	291	646	306	195
45°	212	487	208	487	212	164
55°	147	331	145	331	147	129
65°	76	201	87	201	76	78
75°	41	96	46	96	41	43
85°	12	21	12	21	12	13
90°	34	1	34	1	34	15
95°	62	52	62	52	62	69
105°	222	215	222	215	222	234
115°	400	400	400	400	400	395
125°	584	582	584	582	584	521
135°	762	753	762	753	762	587
145°	924	914	924	914	924	577
155°	1053	1045	1053	1045	1053	485
165°	1138	1137	1138	1137	1138	321
175°	1179	1183	1179	1183	1179	112
180°	1185	1185	1185	1185	1185	



TEST NUMBER: P331670-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	962.9	963.7	964.5	962.7	962.7	961.1	957.8	955.2	948.0	946.9	946.9
5°	1029.5	1028.9	1030.2	1026.0	1020.2	1018.9	1012.8	1004.8	996.4	987.1	985.2
7.5°	1095.8	1094.8	1092.3	1091.5	1087.1	1077.4	1067.6	1057.0	1043.2	1029.6	1022.8
10°	1129.2	1139.8	1133.4	1122.1	1124.4	1109.3	1101.2	1087.4	1075.8	1055.6	1051.1
12.5°	1162.1	1166.3	1164.2	1157.9	1155.0	1144.5	1133.7	1121.6	1100.3	1082.1	1066.3
15°	1162.0	1168.1	1169.8	1167.8	1169.4	1168.7	1163.0	1153.0	1134.4	1114.4	1097.1
17.5°	1076.2	1080.5	1091.0	1098.1	1107.2	1126.2	1135.6	1139.3	1136.4	1125.1	1112.8
20°	980.0	972.9	1002.5	1017.6	1030.5	1062.6	1090.3	1100.9	1117.9	1117.7	1114.4
22.5°	843.7	845.3	873.4	891.3	928.9	961.0	992.6	1032.5	1065.5	1087.3	1100.0
25°	619.9	632.1	660.1	684.5	726.3	786.2	840.5	903.5	962.9	1010.0	1054.6
27.5°	465.5	466.5	488.6	511.3	536.1	585.0	653.5	728.8	813.6	883.5	964.0
30°	398.7	396.7	406.1	419.9	441.2	479.1	530.5	604.5	689.1	794.5	888.4
32.5°	351.4	351.5	358.5	368.8	386.3	411.9	447.2	507.2	587.2	690.9	800.9
35°	305.5	305.1	310.3	317.7	325.0	341.5	365.6	397.1	452.1	548.9	661.4
37.5°	272.5	274.0	276.5	281.1	289.2	298.3	312.9	334.0	373.2	430.4	525.0
40°	254.0	254.7	258.2	262.1	266.9	274.0	285.9	302.9	331.5	377.1	446.3
42.5°	237.0	237.6	240.2	243.7	247.5	254.7	264.5	279.2	302.5	338.0	395.1
45°	212.2	212.2	214.5	216.0	220.2	226.7	234.7	246.9	263.0	289.4	327.4
47.5°	188.9	189.0	190.5	193.2	195.9	200.9	208.8	218.8	230.5	250.9	283.3
50°	175.6	175.9	176.8	179.1	180.7	185.2	191.3	200.0	212.2	228.0	254.9
52.5°	164.7	164.5	165.7	166.8	167.8	171.1	175.6	183.3	194.2	207.9	230.3
55°	147.2	145.9	147.9	149.5	150.5	151.8	154.3	159.2	168.5	180.0	196.7
57.5°	125.4	124.8	126.2	127.7	130.7	134.2	136.4	139.5	144.3	152.6	169.2
60°	107.4	107.4	110.3	111.2	114.8	119.2	123.8	126.4	131.2	136.6	148.9
62.5°	91.4	91.7	93.1	94.0	96.0	101.5	107.9	113.5	118.0	123.3	131.4
65°	76.5	77.1	77.1	77.8	79.1	80.4	82.9	87.5	95.5	102.9	109.0
67.5°	64.9	65.2	65.3	66.0	66.3	67.7	68.7	70.8	72.6	79.6	87.2
70°	57.3	58.2	57.9	58.5	58.8	59.5	60.8	61.7	64.7	66.2	70.8
72.5°	50.0	50.7	50.7	51.1	51.9	52.0	53.0	54.0	55.9	57.3	59.7
75°	40.6	40.2	40.6	41.2	41.5	41.8	41.8	43.0	44.1	45.4	46.9
77.5°	31.3	31.6	31.5	31.6	31.6	32.2	32.1	32.7	33.7	34.4	35.1
80°	25.1	25.4	25.1	25.4	25.7	26.0	25.7	26.0	27.0	27.6	27.6
82.5°	19.5	19.5	19.7	19.7	19.8	19.9	20.3	20.4	21.1	20.9	21.2
85°	11.5	11.3	11.3	11.3	11.5	11.9	11.5	11.5	11.9	11.9	11.9
87.5°	10.9	11.1	11.1	11.0	11.0	11.0	11.1	11.5	11.3	11.6	10.4
90°	34.0	33.8	33.6	33.3	33.1	33.2	33.7	34.1	34.5	35.0	30.1
92.5°	32.4	32.4	32.3	32.3	32.2	32.2	32.0	31.9	31.9	31.8	30.7
95°	62.0	62.4	62.9	63.4	63.8	64.0	64.0	64.0	64.0	64.0	63.5
97.5°	107.5	107.5	107.5	107.5	107.6	107.6	107.6	107.6	107.6	107.6	106.8
100°	137.0	137.2	137.5	137.7	137.9	138.0	138.0	138.0	138.0	138.0	137.3
102.5°	170.7	170.8	171.1	171.3	171.5	171.5	171.3	171.2	171.0	170.8	170.0
105°	222.1	222.1	222.1	222.1	222.1	221.8	221.4	220.9	220.5	220.0	219.6
107.5°	270.4	271.5	272.5	273.5	274.5	274.9	274.7	274.6	274.4	274.2	274.2
110°	308.1	308.7	309.4	310.0	310.7	311.1	311.1	311.1	311.1	311.1	311.1



TEST NUMBER: P331670-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	344.1	344.6	345.0	345.5	346.0	346.6	347.1	347.6	348.1	348.6	348.8
115°	400.0	400.7	401.4	402.1	402.7	403.1	403.4	403.6	403.8	404.1	404.5
117.5°	453.5	454.1	454.8	455.5	456.2	456.8	457.3	457.8	458.3	458.8	460.1
120°	491.0	491.7	492.4	493.1	493.7	494.0	494.0	494.0	494.0	494.0	495.8
122.5°	527.9	528.4	528.8	529.3	529.9	530.3	530.9	531.4	531.9	532.4	533.7
125°	584.1	584.3	584.5	584.7	585.0	585.4	586.1	586.8	587.4	588.1	588.8
127.5°	635.2	636.0	636.7	637.4	638.1	638.9	639.6	640.5	641.3	642.0	642.9
130°	672.1	673.0	673.8	674.8	675.6	676.3	676.7	677.2	677.6	678.1	678.6
132.5°	707.3	708.0	708.7	709.5	710.2	711.0	712.0	712.9	713.9	714.9	714.8
135°	762.1	762.8	763.4	764.1	764.7	765.2	765.4	765.7	765.9	766.1	765.7
137.5°	811.7	812.6	813.5	814.3	815.3	815.8	816.0	816.1	816.3	816.5	815.9
140°	846.1	847.0	847.9	848.8	849.6	850.1	850.1	850.1	850.1	850.1	849.0
142.5°	877.3	878.2	879.1	879.9	880.9	881.2	881.1	880.9	880.7	880.5	879.8
145°	924.1	925.0	925.9	926.8	927.6	928.0	927.8	927.6	927.3	927.1	925.7
147.5°	966.0	966.7	967.6	968.5	969.3	969.5	969.0	968.5	968.0	967.5	966.6
150°	993.2	993.8	994.5	995.1	995.8	995.8	995.1	994.5	993.8	993.2	992.2
152.5°	1018.7	1019.6	1020.5	1021.2	1022.1	1022.1	1021.2	1020.5	1019.6	1018.7	1017.7
155°	1053.1	1053.8	1054.5	1055.2	1055.8	1055.6	1054.5	1053.3	1052.2	1051.1	1050.5
157.5°	1082.7	1083.8	1084.9	1085.9	1087.0	1086.8	1085.3	1083.7	1082.3	1080.7	1080.3
160°	1101.1	1102.0	1102.9	1103.8	1104.7	1104.5	1103.1	1101.8	1100.4	1099.2	1098.9
162.5°	1117.1	1118.2	1119.3	1120.3	1121.4	1121.2	1119.6	1118.2	1116.6	1115.2	1114.9
165°	1138.2	1139.3	1140.4	1141.5	1142.5	1142.4	1140.8	1139.3	1137.7	1136.2	1136.2
167.5°	1155.4	1156.5	1157.6	1158.8	1159.9	1159.8	1158.2	1156.7	1155.1	1153.6	1153.6
170°	1164.2	1165.4	1166.8	1168.1	1169.5	1169.3	1167.8	1166.2	1164.7	1163.1	1163.4
172.5°	1171.3	1172.7	1174.0	1175.4	1176.6	1176.6	1175.0	1173.5	1171.9	1170.4	1170.5
175°	1179.1	1180.5	1181.8	1183.2	1184.5	1184.4	1182.8	1181.3	1179.7	1178.1	1178.6
177.5°	1182.8	1183.8	1184.9	1185.9	1187.0	1187.0	1185.9	1184.9	1183.8	1182.8	1183.1
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331670-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	947.4	945.5	943.7	939.0	936.7	931.5	930.7	930.5	923.9	917.4	915.6
5°	980.0	974.9	967.2	958.1	948.8	939.2	932.7	927.6	914.7	902.5	895.4
7.5°	1012.8	1001.8	988.4	971.4	957.2	941.2	929.4	918.8	900.5	883.0	871.2
10°	1037.2	1019.3	1001.6	978.1	959.8	941.8	925.1	910.6	890.0	866.9	850.4
12.5°	1052.4	1032.6	1008.2	985.3	961.6	938.7	916.3	897.7	873.6	849.6	830.1
15°	1073.0	1051.7	1022.2	989.4	958.8	928.9	903.2	880.0	848.5	819.9	796.1
17.5°	1089.8	1060.5	1028.7	990.8	955.5	917.5	884.3	854.7	819.7	785.1	757.2
20°	1095.1	1066.2	1029.5	991.6	949.8	905.1	869.4	837.2	799.6	762.0	729.9
22.5°	1091.7	1069.3	1028.5	983.1	940.3	893.5	853.3	815.9	774.2	735.8	698.5
25°	1069.1	1061.4	1022.8	973.3	924.4	870.0	823.5	782.6	735.0	693.9	653.3
27.5°	1016.2	1032.9	1008.9	956.1	901.8	843.5	791.2	744.7	695.3	648.9	608.6
30°	965.3	1003.5	993.2	944.3	883.6	826.3	767.5	718.9	666.2	618.6	578.8
32.5°	895.5	958.7	968.8	927.9	865.0	802.1	740.5	692.2	637.1	586.9	548.1
35°	784.5	879.1	922.5	896.4	833.4	765.6	701.9	645.7	590.3	540.8	502.2
37.5°	652.1	780.8	853.3	855.1	797.2	726.7	657.4	601.5	544.8	496.3	454.5
40°	566.2	705.8	800.0	820.9	772.0	695.8	625.7	568.8	513.5	465.9	418.0
42.5°	489.0	628.1	743.9	780.2	741.4	665.7	595.4	535.9	482.1	437.0	388.1
45°	395.5	517.0	644.6	709.6	688.1	617.9	543.7	487.2	436.6	397.7	350.8
47.5°	333.6	419.3	542.8	630.7	630.3	566.3	493.3	439.0	392.2	355.8	317.7
50°	298.3	373.0	477.5	577.1	585.5	531.8	462.4	408.6	365.0	326.7	296.1
52.5°	266.7	328.2	422.1	517.7	541.5	495.0	427.7	378.1	335.6	300.4	274.2
55°	225.4	272.9	344.4	433.8	469.8	437.0	377.1	330.9	296.4	266.9	244.4
57.5°	190.6	226.4	283.6	355.6	397.5	376.9	327.6	290.0	260.5	233.8	216.0
60°	168.8	198.0	246.6	306.8	353.0	338.5	296.4	261.4	236.3	213.2	196.5
62.5°	148.3	173.4	215.0	263.8	306.3	300.2	265.9	236.4	214.5	193.4	179.3
65°	119.2	137.6	170.0	208.4	242.5	245.3	220.6	200.6	181.0	164.3	151.8
67.5°	95.0	106.9	129.8	162.0	187.6	196.7	181.6	166.3	150.8	137.8	127.0
70°	80.1	89.7	106.4	132.5	155.9	165.6	156.9	145.0	131.5	120.9	111.6
72.5°	64.9	74.3	86.6	105.7	125.9	136.3	133.3	124.7	113.7	105.0	96.2
75°	48.9	51.7	60.1	73.0	88.8	97.7	100.0	95.5	86.8	80.1	74.9
77.5°	36.2	37.9	41.8	48.6	58.9	66.9	70.3	69.7	63.7	59.8	55.0
80°	28.9	29.9	31.9	34.7	42.4	50.5	52.7	52.7	48.6	46.9	42.1
82.5°	22.0	22.7	23.8	25.5	29.1	36.1	38.6	39.1	36.4	34.4	30.6
85°	12.6	12.2	12.8	13.9	14.5	16.4	20.2	20.9	20.2	17.7	16.7
87.5°	9.4	8.7	7.7	6.7	6.5	6.1	6.9	7.7	7.1	6.9	7.0
90°	25.2	20.3	15.4	11.7	9.0	6.4	3.7	1.0	3.7	6.4	9.0
92.5°	29.5	28.3	27.2	25.7	23.7	21.7	19.7	17.8	19.7	21.7	23.7
95°	63.1	62.7	62.3	60.9	58.6	56.5	54.2	52.0	54.2	56.5	58.6
97.5°	105.9	105.0	104.3	102.8	100.9	98.9	96.9	95.1	96.9	98.9	100.9
100°	136.6	136.0	135.3	134.1	132.3	130.6	128.8	127.0	128.8	130.6	132.3
102.5°	169.1	168.3	167.5	166.3	164.9	163.5	162.0	160.7	162.0	163.5	164.9
105°	219.1	218.7	218.3	217.7	217.1	216.4	215.7	215.0	215.7	216.4	217.1
107.5°	274.2	274.2	274.2	273.7	272.8	271.8	270.8	269.8	270.8	271.8	272.8
110°	311.1	311.1	311.1	310.4	309.0	307.7	306.3	305.1	306.3	307.7	309.0





TEST NUMBER: P331670-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	349.0	349.1	349.4	348.8	347.4	346.1	344.7	343.5	344.7	346.1	347.4
115°	404.9	405.4	405.8	405.4	404.1	402.7	401.4	400.0	401.4	402.7	404.1
117.5°	461.3	462.6	463.8	463.6	461.8	460.0	458.2	456.4	458.2	460.0	461.8
120°	497.7	499.4	501.2	501.2	499.4	497.7	495.8	494.0	495.8	497.7	499.4
122.5°	534.9	536.2	537.4	537.0	534.9	532.7	530.6	528.5	530.6	532.7	534.9
125°	589.4	590.0	590.7	590.0	588.1	586.1	584.1	582.0	584.1	586.1	588.1
127.5°	643.7	644.5	645.3	644.4	641.9	639.4	636.8	634.3	636.8	639.4	641.9
130°	679.0	679.4	679.8	678.6	675.7	672.9	669.9	667.1	669.9	672.9	675.7
132.5°	714.7	714.6	714.5	713.3	710.9	708.6	706.3	703.9	706.3	708.6	710.9
135°	765.2	764.7	764.3	762.8	760.4	758.0	755.5	753.1	755.5	758.0	760.4
137.5°	815.4	814.8	814.2	812.9	810.9	808.9	806.9	804.9	806.9	808.9	810.9
140°	847.9	846.8	845.7	844.1	842.1	840.1	838.1	836.1	838.1	840.1	842.1
142.5°	879.0	878.2	877.4	876.1	874.1	872.1	870.1	868.1	870.1	872.1	874.1
145°	924.5	923.1	921.8	920.3	918.8	917.2	915.7	914.1	915.7	917.2	918.8
147.5°	965.8	964.8	964.0	962.6	960.7	958.8	957.0	955.1	957.0	958.8	960.7
150°	991.4	990.5	989.5	988.4	987.1	985.8	984.5	983.1	984.5	985.8	987.1
152.5°	1016.6	1015.5	1014.4	1013.2	1011.9	1010.6	1009.3	1007.9	1009.3	1010.6	1011.9
155°	1049.8	1049.1	1048.4	1047.8	1047.1	1046.5	1045.8	1045.2	1045.8	1046.5	1047.1
157.5°	1080.0	1079.5	1079.1	1078.7	1078.2	1077.8	1077.4	1076.9	1077.4	1077.8	1078.2
160°	1098.7	1098.5	1098.2	1097.9	1097.4	1097.0	1096.6	1096.1	1096.6	1097.0	1097.4
162.5°	1114.7	1114.5	1114.2	1114.1	1114.0	1113.9	1113.8	1113.7	1113.8	1113.9	1114.0
165°	1136.2	1136.2	1136.2	1136.3	1136.4	1136.7	1137.0	1137.1	1137.0	1136.7	1136.4
167.5°	1153.7	1153.7	1153.7	1154.1	1154.8	1155.4	1156.1	1156.8	1156.1	1155.4	1154.8
170°	1163.6	1163.8	1164.1	1164.5	1165.1	1165.8	1166.5	1167.2	1166.5	1165.8	1165.1
172.5°	1170.8	1171.0	1171.2	1171.6	1172.3	1173.0	1173.7	1174.3	1173.7	1173.0	1172.3
175°	1179.1	1179.5	1179.9	1180.5	1181.1	1181.8	1182.5	1183.2	1182.5	1181.8	1181.1
177.5°	1183.4	1183.8	1184.1	1184.6	1185.2	1185.7	1186.2	1186.7	1186.2	1185.7	1185.2
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331670-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	912.2	910.4	907.1	902.0	898.9	893.5	889.8	891.9	892.4	891.9	891.4
5°	887.8	881.0	871.7	862.6	854.3	845.3	840.2	837.9	833.4	830.9	829.6
7.5°	858.1	846.4	833.3	817.6	804.3	790.3	783.2	779.6	770.4	765.4	761.0
10°	835.9	817.6	804.4	783.9	771.4	753.0	740.5	740.8	728.2	721.2	716.0
12.5°	811.6	791.4	769.5	751.0	733.6	718.8	703.7	697.6	684.2	677.4	663.6
15°	771.0	747.5	724.4	699.3	681.7	658.8	637.0	610.3	588.8	570.1	564.9
17.5°	726.8	697.8	674.5	645.1	614.8	576.4	551.0	535.5	522.5	512.7	505.4
20°	696.5	666.8	642.1	597.7	556.9	530.8	512.2	500.3	486.8	476.2	470.4
22.5°	664.5	633.7	599.9	550.4	518.6	497.7	481.0	467.4	458.2	450.0	444.7
25°	619.2	585.5	529.9	495.8	470.1	448.2	436.6	428.3	418.6	407.3	402.3
27.5°	571.4	517.7	477.8	452.5	427.9	413.7	403.3	390.8	382.2	377.1	371.8
30°	535.6	482.0	450.8	423.1	405.8	390.0	377.8	370.7	362.4	353.7	350.2
32.5°	495.8	452.9	423.0	400.0	382.4	368.9	359.3	347.8	341.8	336.5	329.1
35°	446.3	413.8	386.5	367.8	351.1	340.2	328.9	322.2	311.3	306.8	303.8
37.5°	404.3	376.2	355.8	336.1	322.9	310.8	303.9	293.2	288.4	282.1	276.0
40°	380.6	353.0	333.5	317.4	302.6	293.5	284.9	276.2	269.1	266.2	258.8
42.5°	356.5	334.0	314.4	296.8	286.9	277.3	266.4	260.0	252.6	248.0	243.4
45°	323.1	303.2	286.5	272.0	261.1	251.2	244.0	233.4	229.3	219.9	216.0
47.5°	293.8	275.3	259.3	245.6	234.9	228.4	218.1	209.7	203.1	197.3	192.4
50°	272.9	257.5	242.1	229.9	220.2	210.9	200.4	196.1	185.8	183.0	180.0
52.5°	253.9	239.3	225.2	213.2	203.5	194.5	185.1	179.7	172.7	169.8	167.7
55°	227.3	213.2	199.7	189.1	179.4	170.0	164.3	157.6	154.3	152.1	149.5
57.5°	200.5	187.9	177.5	166.8	157.0	149.6	142.9	138.9	135.5	132.6	129.5
60°	183.6	171.3	162.0	152.1	142.2	136.0	130.9	126.1	122.2	117.7	116.4
62.5°	165.6	154.9	146.4	136.6	127.9	122.3	117.5	113.0	108.3	101.8	100.0
65°	140.9	132.5	123.5	115.5	107.7	102.3	95.1	90.1	88.1	87.5	87.1
67.5°	118.5	110.6	102.8	94.6	87.6	82.5	78.9	78.1	76.8	76.4	75.5
70°	103.5	96.2	88.4	80.7	74.0	73.0	71.7	70.4	68.8	68.2	67.5
72.5°	90.1	82.5	74.8	68.6	65.7	64.5	63.2	61.9	60.9	60.2	59.8
75°	69.1	62.1	56.9	54.7	53.0	52.1	50.2	49.2	48.6	47.6	47.3
77.5°	49.8	45.8	43.4	42.0	40.3	39.3	38.2	37.2	36.5	36.3	35.8
80°	38.0	36.0	34.4	32.5	31.9	30.6	30.2	29.3	29.6	28.6	28.6
82.5°	29.4	27.0	25.7	24.8	24.1	23.1	22.7	22.3	22.4	21.7	21.7
85°	15.2	14.5	13.9	13.2	13.2	12.2	12.6	12.2	12.2	11.5	11.3
87.5°	7.2	7.7	8.2	9.1	10.2	10.8	10.8	10.4	10.3	10.2	10.0
90°	11.7	15.4	20.3	25.2	30.1	35.0	34.5	34.1	33.7	33.2	33.1
92.5°	25.7	27.2	28.3	29.5	30.7	31.8	31.9	31.9	32.0	32.2	32.2
95°	60.9	62.3	62.7	63.1	63.5	64.0	64.0	64.0	64.0	64.0	63.8
97.5°	102.8	104.3	105.0	105.9	106.8	107.6	107.6	107.6	107.6	107.6	107.6
100°	134.1	135.3	136.0	136.6	137.3	138.0	138.0	138.0	138.0	138.0	137.9
102.5°	166.3	167.5	168.3	169.1	170.0	170.8	171.0	171.2	171.3	171.5	171.5
105°	217.7	218.3	218.7	219.1	219.6	220.0	220.5	220.9	221.4	221.8	222.1
107.5°	273.7	274.2	274.2	274.2	274.2	274.2	274.4	274.6	274.7	274.9	274.5
110°	310.4	311.1	311.1	311.1	311.1	311.1	311.1	311.1	311.1	311.1	310.7



TEST NUMBER: P331670-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	348.8	349.4	349.1	349.0	348.8	348.6	348.1	347.6	347.1	346.6	346.0
115°	405.4	405.8	405.4	404.9	404.5	404.1	403.8	403.6	403.4	403.1	402.7
117.5°	463.6	463.8	462.6	461.3	460.1	458.8	458.3	457.8	457.3	456.8	456.2
120°	501.2	501.2	499.4	497.7	495.8	494.0	494.0	494.0	494.0	494.0	493.7
122.5°	537.0	537.4	536.2	534.9	533.7	532.4	531.9	531.4	530.9	530.3	529.9
125°	590.0	590.7	590.0	589.4	588.8	588.1	587.4	586.8	586.1	585.4	585.0
127.5°	644.4	645.3	644.5	643.7	642.9	642.0	641.3	640.5	639.6	638.9	638.1
130°	678.6	679.8	679.4	679.0	678.6	678.1	677.6	677.2	676.7	676.3	675.6
132.5°	713.3	714.5	714.6	714.7	714.8	714.9	713.9	712.9	712.0	711.0	710.2
135°	762.8	764.3	764.7	765.2	765.7	766.1	765.9	765.7	765.4	765.2	764.7
137.5°	812.9	814.2	814.8	815.4	815.9	816.5	816.3	816.1	816.0	815.8	815.3
140°	844.1	845.7	846.8	847.9	849.0	850.1	850.1	850.1	850.1	850.1	849.6
142.5°	876.1	877.4	878.2	879.0	879.8	880.5	880.7	880.9	881.1	881.2	880.9
145°	920.3	921.8	923.1	924.5	925.7	927.1	927.3	927.6	927.8	928.0	927.6
147.5°	962.6	964.0	964.8	965.8	966.6	967.5	968.0	968.5	969.0	969.5	969.3
150°	988.4	989.5	990.5	991.4	992.2	993.2	993.8	994.5	995.1	995.8	995.8
152.5°	1013.2	1014.4	1015.5	1016.6	1017.7	1018.7	1019.6	1020.5	1021.2	1022.1	1022.1
155°	1047.8	1048.4	1049.1	1049.8	1050.5	1051.1	1052.2	1053.3	1054.5	1055.6	1055.8
157.5°	1078.7	1079.1	1079.5	1080.0	1080.3	1080.7	1082.3	1083.7	1085.3	1086.8	1087.0
160°	1097.9	1098.2	1098.5	1098.7	1098.9	1099.2	1100.4	1101.8	1103.1	1104.5	1104.7
162.5°	1114.1	1114.2	1114.5	1114.7	1114.9	1115.2	1116.6	1118.2	1119.6	1121.2	1121.4
165°	1136.3	1136.2	1136.2	1136.2	1136.2	1136.2	1137.7	1139.3	1140.8	1142.4	1142.5
167.5°	1154.1	1153.7	1153.7	1153.7	1153.6	1153.6	1155.1	1156.7	1158.2	1159.8	1159.9
170°	1164.5	1164.1	1163.8	1163.6	1163.4	1163.1	1164.7	1166.2	1167.8	1169.3	1169.5
172.5°	1171.6	1171.2	1171.0	1170.8	1170.5	1170.4	1171.9	1173.5	1175.0	1176.6	1176.6
175°	1180.5	1179.9	1179.5	1179.1	1178.6	1178.1	1179.7	1181.3	1182.8	1184.4	1184.5
177.5°	1184.6	1184.1	1183.8	1183.4	1183.1	1182.8	1183.8	1184.9	1185.9	1187.0	1187.0
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331670-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	888.6	889.1	888.3	888.8	888.3	889.1	888.6	891.4	891.9	892.4	891.9
5°	827.9	824.1	823.5	822.5	823.5	824.1	827.9	829.6	830.9	833.4	837.9
7.5°	755.5	754.9	753.4	751.1	753.4	754.9	755.5	761.0	765.4	770.4	779.6
10°	708.9	707.4	707.1	704.8	707.1	707.4	708.9	716.0	721.2	728.2	740.8
12.5°	654.4	644.1	643.0	637.4	643.0	644.1	654.4	663.6	677.4	684.2	697.6
15°	557.2	555.3	548.9	544.7	548.9	555.3	557.2	564.9	570.1	588.8	610.3
17.5°	501.6	495.3	493.4	492.5	493.4	495.3	501.6	505.4	512.7	522.5	535.5
20°	465.9	460.1	459.2	458.5	459.2	460.1	465.9	470.4	476.2	486.8	500.3
22.5°	441.2	435.1	432.7	430.8	432.7	435.1	441.2	444.7	450.0	458.2	467.4
25°	399.0	396.7	395.5	394.9	395.5	396.7	399.0	402.3	407.3	418.6	428.3
27.5°	366.0	361.1	360.1	358.4	360.1	361.1	366.0	371.8	377.1	382.2	390.8
30°	347.2	345.6	343.4	341.5	343.4	345.6	347.2	350.2	353.7	362.4	370.7
32.5°	325.1	323.8	321.8	320.9	321.8	323.8	325.1	329.1	336.5	341.8	347.8
35°	300.7	296.1	294.2	291.3	294.2	296.1	300.7	303.8	306.8	311.3	322.2
37.5°	274.7	272.3	269.7	270.6	269.7	272.3	274.7	276.0	282.1	288.4	293.2
40°	254.7	253.0	252.4	252.1	252.4	253.0	254.7	258.8	266.2	269.1	276.2
42.5°	238.7	234.3	232.6	232.6	232.6	234.3	238.7	243.4	248.0	252.6	260.0
45°	214.5	210.3	207.4	207.7	207.4	210.3	214.5	216.0	219.9	229.3	233.4
47.5°	189.7	189.5	187.7	188.3	187.7	189.5	189.7	192.4	197.3	203.1	209.7
50°	177.8	175.9	174.6	174.9	174.6	175.9	177.8	180.0	183.0	185.8	196.1
52.5°	166.5	164.8	163.8	165.1	163.8	164.8	166.5	167.7	169.8	172.7	179.7
55°	147.9	145.9	145.7	145.3	145.7	145.9	147.9	149.5	152.1	154.3	157.6
57.5°	127.2	125.9	123.9	123.1	123.9	125.9	127.2	129.5	132.6	135.5	138.9
60°	112.2	109.6	106.4	106.1	106.4	109.6	112.2	116.4	117.7	122.2	126.1
62.5°	98.6	98.1	97.5	97.4	97.5	98.1	98.6	100.0	101.8	108.3	113.0
65°	86.5	86.2	86.5	86.8	86.5	86.2	86.5	87.1	87.5	88.1	90.1
67.5°	75.3	74.8	74.2	74.5	74.2	74.8	75.3	75.5	76.4	76.8	78.1
70°	66.9	66.6	66.2	66.2	66.2	66.6	66.9	67.5	68.2	68.8	70.4
72.5°	58.6	58.5	58.3	58.0	58.3	58.5	58.6	59.8	60.2	60.9	61.9
75°	46.9	46.3	46.3	46.3	46.3	46.3	46.9	47.3	47.6	48.6	49.2
77.5°	35.7	35.5	35.1	34.9	35.1	35.5	35.7	35.8	36.3	36.5	37.2
80°	28.3	28.0	27.6	27.6	27.6	28.0	28.3	28.6	28.6	29.6	29.3
82.5°	21.6	21.3	21.2	20.9	21.2	21.3	21.6	21.7	21.7	22.4	22.3
85°	11.5	11.9	11.5	12.2	11.5	11.9	11.5	11.3	11.5	12.2	12.2
87.5°	10.0	9.8	10.1	9.9	10.1	9.8	10.0	10.0	10.2	10.3	10.4
90°	33.3	33.6	33.8	34.0	33.8	33.6	33.3	33.1	33.2	33.7	34.1
92.5°	32.3	32.3	32.4	32.4	32.4	32.3	32.3	32.2	32.2	32.0	31.9
95°	63.4	62.9	62.4	62.0	62.4	62.9	63.4	63.8	64.0	64.0	64.0
97.5°	107.5	107.5	107.5	107.5	107.5	107.5	107.5	107.6	107.6	107.6	107.6
100°	137.7	137.5	137.2	137.0	137.2	137.5	137.7	137.9	138.0	138.0	138.0
102.5°	171.3	171.1	170.8	170.7	170.8	171.1	171.3	171.5	171.5	171.3	171.2
105°	222.1	222.1	222.1	222.1	222.1	222.1	222.1	222.1	221.8	221.4	220.9
107.5°	273.5	272.5	271.5	270.4	271.5	272.5	273.5	274.5	274.9	274.7	274.6
110°	310.0	309.4	308.7	308.1	308.7	309.4	310.0	310.7	311.1	311.1	311.1



TEST NUMBER: P331670-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	345.5	345.0	344.6	344.1	344.6	345.0	345.5	346.0	346.6	347.1	347.6
115°	402.1	401.4	400.7	400.0	400.7	401.4	402.1	402.7	403.1	403.4	403.6
117.5°	455.5	454.8	454.1	453.5	454.1	454.8	455.5	456.2	456.8	457.3	457.8
120°	493.1	492.4	491.7	491.0	491.7	492.4	493.1	493.7	494.0	494.0	494.0
122.5°	529.3	528.8	528.4	527.9	528.4	528.8	529.3	529.9	530.3	530.9	531.4
125°	584.7	584.5	584.3	584.1	584.3	584.5	584.7	585.0	585.4	586.1	586.8
127.5°	637.4	636.7	636.0	635.2	636.0	636.7	637.4	638.1	638.9	639.6	640.5
130°	674.8	673.8	673.0	672.1	673.0	673.8	674.8	675.6	676.3	676.7	677.2
132.5°	709.5	708.7	708.0	707.3	708.0	708.7	709.5	710.2	711.0	712.0	712.9
135°	764.1	763.4	762.8	762.1	762.8	763.4	764.1	764.7	765.2	765.4	765.7
137.5°	814.3	813.5	812.6	811.7	812.6	813.5	814.3	815.3	815.8	816.0	816.1
140°	848.8	847.9	847.0	846.1	847.0	847.9	848.8	849.6	850.1	850.1	850.1
142.5°	879.9	879.1	878.2	877.3	878.2	879.1	879.9	880.9	881.2	881.1	880.9
145°	926.8	925.9	925.0	924.1	925.0	925.9	926.8	927.6	928.0	927.8	927.6
147.5°	968.5	967.6	966.7	966.0	966.7	967.6	968.5	969.3	969.5	969.0	968.5
150°	995.1	994.5	993.8	993.2	993.8	994.5	995.1	995.8	995.8	995.1	994.5
152.5°	1021.2	1020.5	1019.6	1018.7	1019.6	1020.5	1021.2	1022.1	1022.1	1021.2	1020.5
155°	1055.2	1054.5	1053.8	1053.1	1053.8	1054.5	1055.2	1055.8	1055.6	1054.5	1053.3
157.5°	1085.9	1084.9	1083.8	1082.7	1083.8	1084.9	1085.9	1087.0	1086.8	1085.3	1083.7
160°	1103.8	1102.9	1102.0	1101.1	1102.0	1102.9	1103.8	1104.7	1104.5	1103.1	1101.8
162.5°	1120.3	1119.3	1118.2	1117.1	1118.2	1119.3	1120.3	1121.4	1121.2	1119.6	1118.2
165°	1141.5	1140.4	1139.3	1138.2	1139.3	1140.4	1141.5	1142.5	1142.4	1140.8	1139.3
167.5°	1158.8	1157.6	1156.5	1155.4	1156.5	1157.6	1158.8	1159.9	1159.8	1158.2	1156.7
170°	1168.1	1166.8	1165.4	1164.2	1165.4	1166.8	1168.1	1169.5	1169.3	1167.8	1166.2
172.5°	1175.4	1174.0	1172.7	1171.3	1172.7	1174.0	1175.4	1176.6	1176.6	1175.0	1173.5
175°	1183.2	1181.8	1180.5	1179.1	1180.5	1181.8	1183.2	1184.5	1184.4	1182.8	1181.3
177.5°	1185.9	1184.9	1183.8	1182.8	1183.8	1184.9	1185.9	1187.0	1187.0	1185.9	1184.9
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331670-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	889.8	893.5	898.9	902.0	907.1	910.4	912.2	915.6	917.4	923.9	930.5
5°	840.2	845.3	854.3	862.6	871.7	881.0	887.8	895.4	902.5	914.7	927.6
7.5°	783.2	790.3	804.3	817.6	833.3	846.4	858.1	871.2	883.0	900.5	918.8
10°	740.5	753.0	771.4	783.9	804.4	817.6	835.9	850.4	866.9	890.0	910.6
12.5°	703.7	718.8	733.6	751.0	769.5	791.4	811.6	830.1	849.6	873.6	897.7
15°	637.0	658.8	681.7	699.3	724.4	747.5	771.0	796.1	819.9	848.5	880.0
17.5°	551.0	576.4	614.8	645.1	674.5	697.8	726.8	757.2	785.1	819.7	854.7
20°	512.2	530.8	556.9	597.7	642.1	666.8	696.5	729.9	762.0	799.6	837.2
22.5°	481.0	497.7	518.6	550.4	599.9	633.7	664.5	698.5	735.8	774.2	815.9
25°	436.6	448.2	470.1	495.8	529.9	585.5	619.2	653.3	693.9	735.0	782.6
27.5°	403.3	413.7	427.9	452.5	477.8	517.7	571.4	608.6	648.9	695.3	744.7
30°	377.8	390.0	405.8	423.1	450.8	482.0	535.6	578.8	618.6	666.2	718.9
32.5°	359.3	368.9	382.4	400.0	423.0	452.9	495.8	548.1	586.9	637.1	692.2
35°	328.9	340.2	351.1	367.8	386.5	413.8	446.3	502.2	540.8	590.3	645.7
37.5°	303.9	310.8	322.9	336.1	355.8	376.2	404.3	454.5	496.3	544.8	601.5
40°	284.9	293.5	302.6	317.4	333.5	353.0	380.6	418.0	465.9	513.5	568.8
42.5°	266.4	277.3	286.9	296.8	314.4	334.0	356.5	388.1	437.0	482.1	535.9
45°	244.0	251.2	261.1	272.0	286.5	303.2	323.1	350.8	397.7	436.6	487.2
47.5°	218.1	228.4	234.9	245.6	259.3	275.3	293.8	317.7	355.8	392.2	439.0
50°	200.4	210.9	220.2	229.9	242.1	257.5	272.9	296.1	326.7	365.0	408.6
52.5°	185.1	194.5	203.5	213.2	225.2	239.3	253.9	274.2	300.4	335.6	378.1
55°	164.3	170.0	179.4	189.1	199.7	213.2	227.3	244.4	266.9	296.4	330.9
57.5°	142.9	149.6	157.0	166.8	177.5	187.9	200.5	216.0	233.8	260.5	290.0
60°	130.9	136.0	142.2	152.1	162.0	171.3	183.6	196.5	213.2	236.3	261.4
62.5°	117.5	122.3	127.9	136.6	146.4	154.9	165.6	179.3	193.4	214.5	236.4
65°	95.1	102.3	107.7	115.5	123.5	132.5	140.9	151.8	164.3	181.0	200.6
67.5°	78.9	82.5	87.6	94.6	102.8	110.6	118.5	127.0	137.8	150.8	166.3
70°	71.7	73.0	74.0	80.7	88.4	96.2	103.5	111.6	120.9	131.5	145.0
72.5°	63.2	64.5	65.7	68.6	74.8	82.5	90.1	96.2	105.0	113.7	124.7
75°	50.2	52.1	53.0	54.7	56.9	62.1	69.1	74.9	80.1	86.8	95.5
77.5°	38.2	39.3	40.3	42.0	43.4	45.8	49.8	55.0	59.8	63.7	69.7
80°	30.2	30.6	31.9	32.5	34.4	36.0	38.0	42.1	46.9	48.6	52.7
82.5°	22.7	23.1	24.1	24.8	25.7	27.0	29.4	30.6	34.4	36.4	39.1
85°	12.6	12.2	13.2	13.2	13.9	14.5	15.2	16.7	17.7	20.2	20.9
87.5°	10.8	10.8	10.2	9.1	8.2	7.7	7.2	7.0	6.9	7.1	7.7
90°	34.5	35.0	30.1	25.2	20.3	15.4	11.7	9.0	6.4	3.7	1.0
92.5°	31.9	31.8	30.7	29.5	28.3	27.2	25.7	23.7	21.7	19.7	17.8
95°	64.0	64.0	63.5	63.1	62.7	62.3	60.9	58.6	56.5	54.2	52.0
97.5°	107.6	107.6	106.8	105.9	105.0	104.3	102.8	100.9	98.9	96.9	95.1
100°	138.0	138.0	137.3	136.6	136.0	135.3	134.1	132.3	130.6	128.8	127.0
102.5°	171.0	170.8	170.0	169.1	168.3	167.5	166.3	164.9	163.5	162.0	160.7
105°	220.5	220.0	219.6	219.1	218.7	218.3	217.7	217.1	216.4	215.7	215.0
107.5°	274.4	274.2	274.2	274.2	274.2	274.2	273.7	272.8	271.8	270.8	269.8
110°	311.1	311.1	311.1	311.1	311.1	311.1	310.4	309.0	307.7	306.3	305.1



TEST NUMBER: P331670-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	348.1	348.6	348.8	349.0	349.1	349.4	348.8	347.4	346.1	344.7	343.5
115°	403.8	404.1	404.5	404.9	405.4	405.8	405.4	404.1	402.7	401.4	400.0
117.5°	458.3	458.8	460.1	461.3	462.6	463.8	463.6	461.8	460.0	458.2	456.4
120°	494.0	494.0	495.8	497.7	499.4	501.2	501.2	499.4	497.7	495.8	494.0
122.5°	531.9	532.4	533.7	534.9	536.2	537.4	537.0	534.9	532.7	530.6	528.5
125°	587.4	588.1	588.8	589.4	590.0	590.7	590.0	588.1	586.1	584.1	582.0
127.5°	641.3	642.0	642.9	643.7	644.5	645.3	644.4	641.9	639.4	636.8	634.3
130°	677.6	678.1	678.6	679.0	679.4	679.8	678.6	675.7	672.9	669.9	667.1
132.5°	713.9	714.9	714.8	714.7	714.6	714.5	713.3	710.9	708.6	706.3	703.9
135°	765.9	766.1	765.7	765.2	764.7	764.3	762.8	760.4	758.0	755.5	753.1
137.5°	816.3	816.5	815.9	815.4	814.8	814.2	812.9	810.9	808.9	806.9	804.9
140°	850.1	850.1	849.0	847.9	846.8	845.7	844.1	842.1	840.1	838.1	836.1
142.5°	880.7	880.5	879.8	879.0	878.2	877.4	876.1	874.1	872.1	870.1	868.1
145°	927.3	927.1	925.7	924.5	923.1	921.8	920.3	918.8	917.2	915.7	914.1
147.5°	968.0	967.5	966.6	965.8	964.8	964.0	962.6	960.7	958.8	957.0	955.1
150°	993.8	993.2	992.2	991.4	990.5	989.5	988.4	987.1	985.8	984.5	983.1
152.5°	1019.6	1018.7	1017.7	1016.6	1015.5	1014.4	1013.2	1011.9	1010.6	1009.3	1007.9
155°	1052.2	1051.1	1050.5	1049.8	1049.1	1048.4	1047.8	1047.1	1046.5	1045.8	1045.2
157.5°	1082.3	1080.7	1080.3	1080.0	1079.5	1079.1	1078.7	1078.2	1077.8	1077.4	1076.9
160°	1100.4	1099.2	1098.9	1098.7	1098.5	1098.2	1097.9	1097.4	1097.0	1096.6	1096.1
162.5°	1116.6	1115.2	1114.9	1114.7	1114.5	1114.2	1114.1	1114.0	1113.9	1113.8	1113.7
165°	1137.7	1136.2	1136.2	1136.2	1136.2	1136.2	1136.3	1136.4	1136.7	1137.0	1137.1
167.5°	1155.1	1153.6	1153.6	1153.7	1153.7	1153.7	1154.1	1154.8	1155.4	1156.1	1156.8
170°	1164.7	1163.1	1163.4	1163.6	1163.8	1164.1	1164.5	1165.1	1165.8	1166.5	1167.2
172.5°	1171.9	1170.4	1170.5	1170.8	1171.0	1171.2	1171.6	1172.3	1173.0	1173.7	1174.3
175°	1179.7	1178.1	1178.6	1179.1	1179.5	1179.9	1180.5	1181.1	1181.8	1182.5	1183.2
177.5°	1183.8	1182.8	1183.1	1183.4	1183.8	1184.1	1184.6	1185.2	1185.7	1186.2	1186.7
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331670-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	930.7	931.5	936.7	939.0	943.7	945.5	947.4	946.9	946.9	948.0	955.2
5°	932.7	939.2	948.8	958.1	967.2	974.9	980.0	985.2	987.1	996.4	1004.8
7.5°	929.4	941.2	957.2	971.4	988.4	1001.8	1012.8	1022.8	1029.6	1043.2	1057.0
10°	925.1	941.8	959.8	978.1	1001.6	1019.3	1037.2	1051.1	1055.6	1075.8	1087.4
12.5°	916.3	938.7	961.6	985.3	1008.2	1032.6	1052.4	1066.3	1082.1	1100.3	1121.6
15°	903.2	928.9	958.8	989.4	1022.2	1051.7	1073.0	1097.1	1114.4	1134.4	1153.0
17.5°	884.3	917.5	955.5	990.8	1028.7	1060.5	1089.8	1112.8	1125.1	1136.4	1139.3
20°	869.4	905.1	949.8	991.6	1029.5	1066.2	1095.1	1114.4	1117.7	1117.9	1100.9
22.5°	853.3	893.5	940.3	983.1	1028.5	1069.3	1091.7	1100.0	1087.3	1065.5	1032.5
25°	823.5	870.0	924.4	973.3	1022.8	1061.4	1069.1	1054.6	1010.0	962.9	903.5
27.5°	791.2	843.5	901.8	956.1	1008.9	1032.9	1016.2	964.0	883.5	813.6	728.8
30°	767.5	826.3	883.6	944.3	993.2	1003.5	965.3	888.4	794.5	689.1	604.5
32.5°	740.5	802.1	865.0	927.9	968.8	958.7	895.5	800.9	690.9	587.2	507.2
35°	701.9	765.6	833.4	896.4	922.5	879.1	784.5	661.4	548.9	452.1	397.1
37.5°	657.4	726.7	797.2	855.1	853.3	780.8	652.1	525.0	430.4	373.2	334.0
40°	625.7	695.8	772.0	820.9	800.0	705.8	566.2	446.3	377.1	331.5	302.9
42.5°	595.4	665.7	741.4	780.2	743.9	628.1	489.0	395.1	338.0	302.5	279.2
45°	543.7	617.9	688.1	709.6	644.6	517.0	395.5	327.4	289.4	263.0	246.9
47.5°	493.3	566.3	630.3	630.7	542.8	419.3	333.6	283.3	250.9	230.5	218.8
50°	462.4	531.8	585.5	577.1	477.5	373.0	298.3	254.9	228.0	212.2	200.0
52.5°	427.7	495.0	541.5	517.7	422.1	328.2	266.7	230.3	207.9	194.2	183.3
55°	377.1	437.0	469.8	433.8	344.4	272.9	225.4	196.7	180.0	168.5	159.2
57.5°	327.6	376.9	397.5	355.6	283.6	226.4	190.6	169.2	152.6	144.3	139.5
60°	296.4	338.5	353.0	306.8	246.6	198.0	168.8	148.9	136.6	131.2	126.4
62.5°	265.9	300.2	306.3	263.8	215.0	173.4	148.3	131.4	123.3	118.0	113.5
65°	220.6	245.3	242.5	208.4	170.0	137.6	119.2	109.0	102.9	95.5	87.5
67.5°	181.6	196.7	187.6	162.0	129.8	106.9	95.0	87.2	79.6	72.6	70.8
70°	156.9	165.6	155.9	132.5	106.4	89.7	80.1	70.8	66.2	64.7	61.7
72.5°	133.3	136.3	125.9	105.7	86.6	74.3	64.9	59.7	57.3	55.9	54.0
75°	100.0	97.7	88.8	73.0	60.1	51.7	48.9	46.9	45.4	44.1	43.0
77.5°	70.3	66.9	58.9	48.6	41.8	37.9	36.2	35.1	34.4	33.7	32.7
80°	52.7	50.5	42.4	34.7	31.9	29.9	28.9	27.6	27.6	27.0	26.0
82.5°	38.6	36.1	29.1	25.5	23.8	22.7	22.0	21.2	20.9	21.1	20.4
85°	20.2	16.4	14.5	13.9	12.8	12.2	12.6	11.9	11.9	11.9	11.5
87.5°	6.9	6.1	6.5	6.7	7.7	8.7	9.4	10.4	11.6	11.3	11.5
90°	3.7	6.4	9.0	11.7	15.4	20.3	25.2	30.1	35.0	34.5	34.1
92.5°	19.7	21.7	23.7	25.7	27.2	28.3	29.5	30.7	31.8	31.9	31.9
95°	54.2	56.5	58.6	60.9	62.3	62.7	63.1	63.5	64.0	64.0	64.0
97.5°	96.9	98.9	100.9	102.8	104.3	105.0	105.9	106.8	107.6	107.6	107.6
100°	128.8	130.6	132.3	134.1	135.3	136.0	136.6	137.3	138.0	138.0	138.0
102.5°	162.0	163.5	164.9	166.3	167.5	168.3	169.1	170.0	170.8	171.0	171.2
105°	215.7	216.4	217.1	217.7	218.3	218.7	219.1	219.6	220.0	220.5	220.9
107.5°	270.8	271.8	272.8	273.7	274.2	274.2	274.2	274.2	274.2	274.4	274.6
110°	306.3	307.7	309.0	310.4	311.1	311.1	311.1	311.1	311.1	311.1	311.1





TEST NUMBER: P331670-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	344.7	346.1	347.4	348.8	349.4	349.1	349.0	348.8	348.6	348.1	347.6
115°	401.4	402.7	404.1	405.4	405.8	405.4	404.9	404.5	404.1	403.8	403.6
117.5°	458.2	460.0	461.8	463.6	463.8	462.6	461.3	460.1	458.8	458.3	457.8
120°	495.8	497.7	499.4	501.2	501.2	499.4	497.7	495.8	494.0	494.0	494.0
122.5°	530.6	532.7	534.9	537.0	537.4	536.2	534.9	533.7	532.4	531.9	531.4
125°	584.1	586.1	588.1	590.0	590.7	590.0	589.4	588.8	588.1	587.4	586.8
127.5°	636.8	639.4	641.9	644.4	645.3	644.5	643.7	642.9	642.0	641.3	640.5
130°	669.9	672.9	675.7	678.6	679.8	679.4	679.0	678.6	678.1	677.6	677.2
132.5°	706.3	708.6	710.9	713.3	714.5	714.6	714.7	714.8	714.9	713.9	712.9
135°	755.5	758.0	760.4	762.8	764.3	764.7	765.2	765.7	766.1	765.9	765.7
137.5°	806.9	808.9	810.9	812.9	814.2	814.8	815.4	815.9	816.5	816.3	816.1
140°	838.1	840.1	842.1	844.1	845.7	846.8	847.9	849.0	850.1	850.1	850.1
142.5°	870.1	872.1	874.1	876.1	877.4	878.2	879.0	879.8	880.5	880.7	880.9
145°	915.7	917.2	918.8	920.3	921.8	923.1	924.5	925.7	927.1	927.3	927.6
147.5°	957.0	958.8	960.7	962.6	964.0	964.8	965.8	966.6	967.5	968.0	968.5
150°	984.5	985.8	987.1	988.4	989.5	990.5	991.4	992.2	993.2	993.8	994.5
152.5°	1009.3	1010.6	1011.9	1013.2	1014.4	1015.5	1016.6	1017.7	1018.7	1019.6	1020.5
155°	1045.8	1046.5	1047.1	1047.8	1048.4	1049.1	1049.8	1050.5	1051.1	1052.2	1053.3
157.5°	1077.4	1077.8	1078.2	1078.7	1079.1	1079.5	1080.0	1080.3	1080.7	1082.3	1083.7
160°	1096.6	1097.0	1097.4	1097.9	1098.2	1098.5	1098.7	1098.9	1099.2	1100.4	1101.8
162.5°	1113.8	1113.9	1114.0	1114.1	1114.2	1114.5	1114.7	1114.9	1115.2	1116.6	1118.2
165°	1137.0	1136.7	1136.4	1136.3	1136.2	1136.2	1136.2	1136.2	1136.2	1137.7	1139.3
167.5°	1156.1	1155.4	1154.8	1154.1	1153.7	1153.7	1153.7	1153.6	1153.6	1155.1	1156.7
170°	1166.5	1165.8	1165.1	1164.5	1164.1	1163.8	1163.6	1163.4	1163.1	1164.7	1166.2
172.5°	1173.7	1173.0	1172.3	1171.6	1171.2	1171.0	1170.8	1170.5	1170.4	1171.9	1173.5
175°	1182.5	1181.8	1181.1	1180.5	1179.9	1179.5	1179.1	1178.6	1178.1	1179.7	1181.3
177.5°	1186.2	1185.7	1185.2	1184.6	1184.1	1183.8	1183.4	1183.1	1182.8	1183.8	1184.9
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331670-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	957.8	961.1	962.7	962.7	964.5	963.7	962.9
5°	1012.8	1018.9	1020.2	1026.0	1030.2	1028.9	1029.5
7.5°	1067.6	1077.4	1087.1	1091.5	1092.3	1094.8	1095.8
10°	1101.2	1109.3	1124.4	1122.1	1133.4	1139.8	1129.2
12.5°	1133.7	1144.5	1155.0	1157.9	1164.2	1166.3	1162.1
15°	1163.0	1168.7	1169.4	1167.8	1169.8	1168.1	1162.0
17.5°	1135.6	1126.2	1107.2	1098.1	1091.0	1080.5	1076.2
20°	1090.3	1062.6	1030.5	1017.6	1002.5	972.9	980.0
22.5°	992.6	961.0	928.9	891.3	873.4	845.3	843.7
25°	840.5	786.2	726.3	684.5	660.1	632.1	619.9
27.5°	653.5	585.0	536.1	511.3	488.6	466.5	465.5
30°	530.5	479.1	441.2	419.9	406.1	396.7	398.7
32.5°	447.2	411.9	386.3	368.8	358.5	351.5	351.4
35°	365.6	341.5	325.0	317.7	310.3	305.1	305.5
37.5°	312.9	298.3	289.2	281.1	276.5	274.0	272.5
40°	285.9	274.0	266.9	262.1	258.2	254.7	254.0
42.5°	264.5	254.7	247.5	243.7	240.2	237.6	237.0
45°	234.7	226.7	220.2	216.0	214.5	212.2	212.2
47.5°	208.8	200.9	195.9	193.2	190.5	189.0	188.9
50°	191.3	185.2	180.7	179.1	176.8	175.9	175.6
52.5°	175.6	171.1	167.8	166.8	165.7	164.5	164.7
55°	154.3	151.8	150.5	149.5	147.9	145.9	147.2
57.5°	136.4	134.2	130.7	127.7	126.2	124.8	125.4
60°	123.8	119.2	114.8	111.2	110.3	107.4	107.4
62.5°	107.9	101.5	96.0	94.0	93.1	91.7	91.4
65°	82.9	80.4	79.1	77.8	77.1	77.1	76.5
67.5°	68.7	67.7	66.3	66.0	65.3	65.2	64.9
70°	60.8	59.5	58.8	58.5	57.9	58.2	57.3
72.5°	53.0	52.0	51.9	51.1	50.7	50.7	50.0
75°	41.8	41.8	41.5	41.2	40.6	40.2	40.6
77.5°	32.1	32.2	31.6	31.6	31.5	31.6	31.3
80°	25.7	26.0	25.7	25.4	25.1	25.4	25.1
82.5°	20.3	19.9	19.8	19.7	19.7	19.5	19.5
85°	11.5	11.9	11.5	11.3	11.3	11.3	11.5
87.5°	11.1	11.0	11.0	11.0	11.1	11.1	10.9
90°	33.7	33.2	33.1	33.3	33.6	33.8	34.0
92.5°	32.0	32.2	32.2	32.3	32.3	32.4	32.4
95°	64.0	64.0	63.8	63.4	62.9	62.4	62.0
97.5°	107.6	107.6	107.6	107.5	107.5	107.5	107.5
100°	138.0	138.0	137.9	137.7	137.5	137.2	137.0
102.5°	171.3	171.5	171.5	171.3	171.1	170.8	170.7
105°	221.4	221.8	222.1	222.1	222.1	222.1	222.1
107.5°	274.7	274.9	274.5	273.5	272.5	271.5	270.4
110°	311.1	311.1	310.7	310.0	309.4	308.7	308.1



TEST NUMBER: P331670-935

CATALOG NUMBER: SA2XXRDIP-C485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	347.1	346.6	346.0	345.5	345.0	344.6	344.1
115°	403.4	403.1	402.7	402.1	401.4	400.7	400.0
117.5°	457.3	456.8	456.2	455.5	454.8	454.1	453.5
120°	494.0	494.0	493.7	493.1	492.4	491.7	491.0
122.5°	530.9	530.3	529.9	529.3	528.8	528.4	527.9
125°	586.1	585.4	585.0	584.7	584.5	584.3	584.1
127.5°	639.6	638.9	638.1	637.4	636.7	636.0	635.2
130°	676.7	676.3	675.6	674.8	673.8	673.0	672.1
132.5°	712.0	711.0	710.2	709.5	708.7	708.0	707.3
135°	765.4	765.2	764.7	764.1	763.4	762.8	762.1
137.5°	816.0	815.8	815.3	814.3	813.5	812.6	811.7
140°	850.1	850.1	849.6	848.8	847.9	847.0	846.1
142.5°	881.1	881.2	880.9	879.9	879.1	878.2	877.3
145°	927.8	928.0	927.6	926.8	925.9	925.0	924.1
147.5°	969.0	969.5	969.3	968.5	967.6	966.7	966.0
150°	995.1	995.8	995.8	995.1	994.5	993.8	993.2
152.5°	1021.2	1022.1	1022.1	1021.2	1020.5	1019.6	1018.7
155°	1054.5	1055.6	1055.8	1055.2	1054.5	1053.8	1053.1
157.5°	1085.3	1086.8	1087.0	1085.9	1084.9	1083.8	1082.7
160°	1103.1	1104.5	1104.7	1103.8	1102.9	1102.0	1101.1
162.5°	1119.6	1121.2	1121.4	1120.3	1119.3	1118.2	1117.1
165°	1140.8	1142.4	1142.5	1141.5	1140.4	1139.3	1138.2
167.5°	1158.2	1159.8	1159.9	1158.8	1157.6	1156.5	1155.4
170°	1167.8	1169.3	1169.5	1168.1	1166.8	1165.4	1164.2
172.5°	1175.0	1176.6	1176.6	1175.4	1174.0	1172.7	1171.3
175°	1182.8	1184.4	1184.5	1183.2	1181.8	1180.5	1179.1
177.5°	1185.9	1187.0	1187.0	1185.9	1184.9	1183.8	1182.8
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2

(END OF REPORT)