

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331704-935

Luminaire Tested: **SA2XXRDIP-C675D1080U935-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331704-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D1080U935-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5621.5 lumens  
Efficiency: N/A  
Efficacy: 98.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331704-935

CATALOG NUMBER: SA2XXRDIP-C675D1080U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331704-935

CATALOG NUMBER: SA2XXRDIP-C675D1080U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36				
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	38	37	31				
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32	26				
3	79	70	63	58	71	64	58	53	52	48	44	41	38	36	31	29	27	23				
4	73	62	55	49	65	57	50	45	46	42	38	37	33	31	28	25	24	20				
5	67	56	48	42	60	51	44	39	42	37	33	33	29	27	25	23	21	17				
6	61	50	42	37	56	46	39	34	37	32	29	30	26	24	23	20	19	15				
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	18	17	14				
8	53	41	33	28	48	38	31	26	31	26	23	25	21	19	19	17	15	12				
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	14	11				
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	17	14	12	10				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15681	15681	15681
5°	15741	15486	15571
10°	15621	15231	15101
15°	15442	14780	14355
20°	15192	14136	13426
25°	14938	13402	12527
30°	14585	12652	11373
35°	14241	11832	10360
40°	13894	10985	9187
45°	13486	10035	8127
50°	13069	9075	7086
55°	12645	8042	6086
60°	12148	6952	5050
65°	11584	5841	4604
70°	10914	4810	4230
75°	10087	4386	3949
80°	8908	3924	3598
85°	7003	3094	3094



TEST NUMBER: P331704-935

CATALOG NUMBER: SA2XXRDIP-C675D1080U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.9	1.6
10°-20°	249.6	4.4
20°-30°	350.5	6.2
30°-40°	382.2	6.8
40°-50°	351.5	6.3
50°-60°	276.0	4.9
60°-70°	180.0	3.2
70°-80°	92.8	1.7
80°-90°	28.7	0.5
90°-100°	208.0	3.7
100°-110°	705.7	12.6
110°-120°	749.7	13.3
120°-130°	617.2	11.0
130°-140°	495.6	8.8
140°-150°	374.5	6.7
150°-160°	263.2	4.7
160°-170°	154.9	2.8
170°-180°	50.4	0.9
0°-30°	691.1	12.3
0°-40°	1073.3	19.1
0°-60°	1700.8	30.3
0°-90°	2002.3	35.6
90°-120°	1663.4	29.6
90°-150°	3150.7	56.0
90°-180°	3619.0	64.4
0°-180°	5621.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	971	966	956	963	961	92
15°	924	913	884	868	859	260
25°	838	809	752	718	703	385
35°	722	676	600	547	526	452
45°	591	530	440	379	356	456
55°	449	379	286	235	216	401
65°	303	232	153	125	120	300
75°	162	102	70	64	63	171
85°	38	20	17	17	17	45
90°	1	14	34	32	33	4
95°	35	86	392	148	114	37
105°	122	184	741	1325	1127	130
115°	215	272	620	1280	1483	213
125°	300	355	596	1037	1203	266
135°	352	420	589	871	997	272
145°	402	462	586	728	796	252
155°	457	494	569	644	669	210
165°	498	513	545	578	587	140
175°	519	520	524	531	529	49
180°	520	520	520	520	520	



TEST NUMBER: P331704-935

CATALOG NUMBER: SA2XXRDIP-C675D1080U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2
2.5°	974.7	974.0	973.2	972.4	971.6	970.3	968.6	966.9	965.3	963.5	965.1
5°	971.2	970.3	969.3	968.3	967.3	965.6	963.0	960.5	957.9	955.5	957.2
7.5°	961.2	960.0	958.8	957.6	956.4	954.2	951.3	948.4	945.4	942.5	942.9
10°	952.8	951.4	950.0	948.6	947.3	944.7	940.7	936.9	933.0	929.0	928.5
12.5°	942.2	940.6	938.8	937.2	935.5	932.2	927.2	922.2	917.1	912.1	911.1
15°	923.8	921.6	919.5	917.3	915.2	910.8	904.1	897.5	890.9	884.2	880.5
17.5°	901.1	897.9	894.6	891.2	887.9	882.1	873.6	865.0	856.5	848.0	843.6
20°	884.2	880.3	876.4	872.5	868.6	861.8	852.0	842.2	832.5	822.7	817.8
22.5°	865.9	861.6	857.2	852.8	848.4	840.8	829.7	818.7	807.7	796.7	790.4
25°	838.5	832.2	826.0	819.8	813.6	803.9	791.1	778.2	765.3	752.3	744.3
27.5°	805.5	798.7	791.9	785.1	778.3	767.6	753.1	738.6	724.0	709.5	700.2
30°	782.3	774.8	767.4	760.0	752.6	741.1	725.4	709.8	694.1	678.6	668.6
32.5°	759.7	751.1	742.4	733.7	725.0	712.7	696.8	680.9	665.0	649.0	637.7
35°	722.5	712.6	702.6	692.6	682.7	669.1	651.9	634.7	617.5	600.3	588.0
37.5°	685.3	674.2	663.3	652.4	641.4	626.8	608.6	590.2	571.9	553.5	540.0
40°	659.2	647.5	635.8	624.1	612.3	597.0	578.1	559.1	540.2	521.2	507.4
42.5°	632.5	620.2	607.8	595.5	583.2	567.1	547.6	528.1	508.4	488.9	474.5
45°	590.6	577.6	564.5	551.4	538.3	521.5	501.0	480.5	459.9	439.5	425.6
47.5°	549.8	536.0	522.1	508.2	494.4	476.9	455.7	434.5	413.4	392.2	378.4
50°	520.3	506.4	492.6	478.7	464.9	447.2	425.7	404.2	382.7	361.3	347.8
52.5°	491.5	477.0	462.5	448.1	433.5	415.8	394.8	373.8	352.8	331.7	318.7
55°	449.2	433.9	418.7	403.5	388.2	370.1	349.0	327.9	306.8	285.7	274.0
57.5°	405.7	390.1	374.4	358.9	343.2	325.3	305.0	284.7	264.4	244.2	233.4
60°	376.2	360.6	344.9	329.3	313.7	295.8	275.7	255.5	235.5	215.3	205.3
62.5°	347.3	331.7	316.1	300.5	284.8	267.4	248.3	229.1	209.9	190.7	181.2
65°	303.2	287.4	271.6	255.8	240.0	223.3	205.7	188.1	170.5	152.9	146.3
67.5°	260.7	245.0	229.3	213.6	197.9	182.1	166.3	150.5	134.7	118.8	115.8
70°	231.2	215.9	200.7	185.5	170.2	155.8	142.4	128.9	115.5	101.9	100.0
72.5°	203.0	188.4	173.8	159.2	144.6	131.9	121.1	110.2	99.4	88.6	87.0
75°	161.7	148.1	134.4	120.7	107.0	96.9	90.2	83.6	77.0	70.3	69.0
77.5°	121.1	109.1	97.1	85.2	73.2	65.5	62.3	59.2	56.0	52.8	51.9
80°	95.8	85.8	75.9	66.0	56.0	50.0	48.0	46.1	44.2	42.2	41.4
82.5°	72.6	64.8	57.1	49.2	41.5	36.9	35.6	34.3	33.0	31.7	31.2
85°	37.8	33.7	29.6	25.5	21.4	19.0	18.4	17.9	17.3	16.7	16.7
87.5°	11.5	10.8	10.3	9.5	8.6	8.6	9.6	11.0	12.2	12.4	12.1
90°	1.0	4.0	8.0	10.0	12.0	15.0	20.0	27.0	33.0	34.0	33.0
92.5°	12.2	17.6	24.8	29.2	36.0	45.4	68.0	99.8	128.2	130.0	109.9
95°	35.0	39.0	49.0	58.0	74.0	98.0	144.0	231.0	347.1	392.1	343.1
97.5°	57.0	62.4	73.0	86.6	105.0	132.2	190.0	311.3	504.1	669.3	702.1
100°	77.0	80.0	89.0	105.0	125.0	153.0	206.0	328.0	544.1	790.1	934.2
102.5°	95.4	97.6	106.6	122.6	143.4	171.4	220.4	328.9	528.9	794.2	1020.6
105°	122.0	126.1	133.0	148.0	170.0	198.0	245.0	334.1	499.1	741.1	1007.2
107.5°	150.8	154.0	160.8	174.6	196.5	224.6	270.3	347.8	484.3	684.3	919.4
110°	170.0	174.0	180.0	193.0	214.0	243.1	287.1	359.0	481.1	657.1	864.2



TEST NUMBER: P331704-935

CATALOG NUMBER: SA2XXRDIP-C675D1080U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	187.6	191.7	198.5	210.6	230.8	260.6	303.1	371.1	481.9	639.6	825.8
115°	215.1	220.1	226.0	238.1	258.0	285.1	328.0	389.1	486.1	620.1	778.2
117.5°	243.5	247.5	253.5	264.1	283.3	311.3	351.0	408.3	493.3	610.7	748.1
120°	261.1	265.0	271.0	280.1	300.1	328.0	367.0	421.1	498.1	605.1	732.1
122.5°	277.8	281.0	287.1	296.9	316.8	345.7	382.3	432.3	503.7	601.9	718.5
125°	300.1	303.1	309.1	321.1	341.0	369.1	405.1	450.1	512.1	596.2	699.1
127.5°	317.6	321.7	330.1	343.3	362.5	391.2	426.3	466.7	520.7	592.7	681.1
130°	328.0	332.1	342.1	356.1	376.1	404.1	439.1	477.1	527.1	591.1	669.2
132.5°	337.7	342.5	353.3	368.1	388.9	416.9	450.3	487.5	533.5	590.3	659.5
135°	352.1	356.1	368.1	383.1	406.0	434.1	466.1	501.1	541.1	589.1	646.1
137.5°	365.7	370.5	382.5	398.5	421.3	447.3	478.9	511.5	547.9	588.9	636.7
140°	376.1	380.0	392.1	408.1	430.1	456.1	486.1	517.1	551.1	588.1	631.1
142.5°	386.5	389.7	400.9	416.9	438.1	462.5	491.7	521.9	553.5	588.1	625.5
145°	402.1	406.0	416.1	431.1	451.1	473.1	500.1	528.1	556.1	586.1	618.1
147.5°	418.9	421.9	431.4	445.3	461.9	481.5	506.9	531.5	556.9	582.6	610.5
150°	430.1	433.1	441.1	454.1	469.1	487.1	510.1	533.1	556.1	580.1	604.1
152.5°	441.3	442.7	450.6	462.1	476.3	492.7	513.3	533.9	554.5	576.1	598.5
155°	457.1	458.1	464.1	475.1	486.1	501.1	518.1	535.1	552.1	569.1	588.1
157.5°	470.3	471.3	476.1	485.7	494.5	507.1	521.5	535.1	547.5	561.9	578.3
160°	479.1	480.1	484.1	492.1	500.1	511.1	523.1	535.1	545.1	557.2	571.1
162.5°	487.9	487.3	491.3	497.7	504.9	513.5	523.9	534.3	542.7	553.1	564.7
165°	498.1	497.1	499.1	505.1	510.1	516.1	525.1	532.1	538.1	545.1	554.1
167.5°	506.5	505.3	507.1	510.9	514.5	518.3	524.9	530.7	533.5	538.1	543.7
170°	512.1	510.1	511.1	514.1	516.1	519.1	524.1	529.1	531.1	534.1	538.1
172.5°	515.3	514.1	513.5	516.5	517.7	519.9	523.3	526.7	527.9	529.3	532.5
175°	519.1	518.1	517.1	519.1	519.1	520.1	522.1	524.1	523.1	524.1	525.1
177.5°	520.9	519.3	518.5	520.1	520.1	520.1	520.9	522.5	520.9	520.1	520.9
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331704-935

CATALOG NUMBER: SA2XXRDIP-C675D1080U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2
2.5°	966.6	968.2	969.7	970.3	970.1	969.7	969.5	969.1
5°	958.9	960.7	962.4	963.0	962.4	961.8	961.3	960.7
7.5°	943.4	943.9	944.4	944.2	943.1	942.2	941.2	940.1
10°	927.9	927.3	926.7	925.8	924.6	923.5	922.3	921.1
12.5°	910.1	909.0	907.9	906.5	904.5	902.6	900.6	898.6
15°	876.8	873.1	869.4	866.5	864.6	862.6	860.7	858.8
17.5°	839.2	834.7	830.3	826.5	823.1	819.8	816.4	813.0
20°	813.0	808.0	803.1	798.6	794.3	790.0	785.7	781.4
22.5°	784.1	777.8	771.5	766.8	763.5	760.3	757.2	754.0
25°	736.3	728.3	720.3	714.9	712.0	709.0	706.1	703.2
27.5°	690.8	681.5	672.2	665.1	660.5	655.8	651.2	646.5
30°	658.7	648.7	638.7	631.1	625.8	620.5	615.3	610.0
32.5°	626.3	614.9	603.6	595.4	590.4	585.5	580.5	575.6
35°	575.8	563.4	551.1	542.8	538.5	534.2	529.9	525.6
37.5°	526.4	512.9	499.4	490.1	485.2	480.3	475.4	470.5
40°	493.4	479.6	465.7	456.2	451.2	446.1	441.0	435.9
42.5°	460.2	445.8	431.5	421.9	417.0	412.1	407.2	402.2
45°	411.7	397.9	384.0	374.7	370.1	365.3	360.7	355.9
47.5°	364.6	350.9	337.0	328.0	323.7	319.5	315.2	311.0
50°	334.3	320.8	307.4	298.5	294.5	290.3	286.3	282.1
52.5°	305.7	292.7	279.7	271.3	267.5	263.7	259.9	256.1
55°	262.3	250.5	238.8	231.1	227.4	223.6	219.9	216.2
57.5°	222.7	212.0	201.2	194.2	191.1	188.0	184.9	181.8
60°	195.4	185.5	175.5	168.9	165.8	162.7	159.5	156.4
62.5°	171.8	162.2	152.7	147.1	145.2	143.4	141.5	139.6
65°	139.7	133.0	126.4	122.8	122.2	121.6	121.0	120.5
67.5°	112.7	109.7	106.7	104.8	104.2	103.6	103.0	102.3
70°	98.1	96.1	94.1	92.8	92.0	91.2	90.4	89.6
72.5°	85.3	83.7	82.1	81.0	80.5	80.1	79.6	79.1
75°	67.6	66.2	64.8	64.1	63.9	63.7	63.5	63.3
77.5°	51.1	50.4	49.6	49.1	48.7	48.5	48.1	47.8
80°	40.6	39.9	39.1	38.7	38.7	38.7	38.7	38.7
82.5°	30.7	30.2	29.8	29.5	29.5	29.5	29.5	29.5
85°	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7
87.5°	11.7	11.2	11.4	11.5	11.5	11.5	11.5	11.5
90°	32.0	30.0	32.0	33.0	33.0	33.0	33.0	33.0
92.5°	87.2	74.8	66.4	60.2	59.4	56.2	57.0	55.4
95°	262.1	201.0	159.0	137.0	124.0	116.1	113.0	114.0
97.5°	611.5	500.3	392.1	319.9	272.1	247.5	232.8	224.5
100°	913.2	789.2	652.1	531.1	448.1	405.1	376.1	358.1
102.5°	1110.9	1082.8	982.6	854.4	764.1	690.8	654.5	630.2
105°	1215.2	1328.3	1341.3	1308.3	1246.2	1184.2	1141.3	1127.2
107.5°	1140.1	1310.3	1414.3	1462.7	1470.5	1467.1	1458.4	1439.9
110°	1075.2	1254.2	1382.2	1464.3	1507.3	1526.3	1535.3	1534.3





TEST NUMBER: P331704-935

CATALOG NUMBER: SA2XXRDIP-C675D1080U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1016.0	1187.8	1324.6	1418.7	1478.5	1510.3	1527.3	1532.7
115°	943.2	1097.3	1228.2	1331.3	1402.3	1448.3	1474.3	1483.3
117.5°	888.4	1023.6	1142.5	1239.1	1311.5	1360.0	1387.5	1395.1
120°	861.2	985.2	1091.2	1182.2	1252.2	1299.2	1328.3	1338.3
122.5°	839.6	953.2	1053.6	1135.8	1198.6	1244.8	1270.7	1279.0
125°	808.1	911.2	999.2	1074.2	1132.2	1170.3	1195.2	1203.2
127.5°	777.1	870.4	953.4	1022.6	1073.2	1108.8	1130.4	1136.9
130°	757.2	843.2	922.2	988.2	1037.2	1071.3	1091.2	1099.2
132.5°	738.0	817.6	890.2	952.2	1000.4	1034.4	1052.8	1060.0
135°	711.1	777.1	843.2	899.1	942.2	975.2	993.2	997.2
137.5°	689.7	744.9	797.4	846.2	885.4	913.8	929.6	935.6
140°	676.1	724.2	770.2	814.2	846.2	872.2	887.2	893.2
142.5°	665.0	705.8	745.4	782.1	812.5	836.2	849.5	850.8
145°	649.1	682.2	713.2	742.2	766.1	783.2	793.2	796.2
147.5°	637.0	663.0	687.2	708.3	728.1	741.8	748.6	750.4
150°	628.1	650.1	671.1	689.1	704.1	716.2	722.1	723.2
152.5°	619.3	639.7	657.5	673.1	684.9	695.3	699.7	699.9
155°	607.1	623.1	638.1	649.1	660.1	667.1	671.1	669.2
157.5°	592.9	606.3	618.9	627.5	635.3	641.1	642.9	642.9
160°	584.1	595.1	606.1	613.1	620.1	625.1	626.1	626.1
162.5°	575.3	584.7	594.1	599.5	606.5	609.9	610.9	610.1
165°	562.1	569.1	576.1	580.1	584.1	588.1	588.1	587.1
167.5°	549.5	554.9	559.7	563.4	565.1	567.3	567.1	565.9
170°	543.1	546.1	550.1	552.1	553.1	556.1	555.1	553.1
172.5°	535.9	538.1	541.3	542.5	543.5	544.9	543.9	542.7
175°	528.1	529.1	530.1	531.1	531.1	532.1	531.1	529.1
177.5°	522.5	522.5	523.3	523.3	523.3	523.3	522.5	520.9
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1

(END OF REPORT)