

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331680-935

Luminaire Tested: **SA2XXRDIP-C675D330U935-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331680-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D330U935-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3099.8 lumens  
Efficiency: N/A  
Efficacy: 88.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331680-935  
CATALOG NUMBER: SA2XXRDIP-C675D330U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331680-935

CATALOG NUMBER: SA2XXRDIP-C675D330U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64				
1	102	97	94	90	95	92	88	86	81	79	76	71	70	68	62	61	60	56				
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	56	53	51	48				
3	85	76	69	63	80	72	65	60	64	59	55	57	53	50	50	47	44	41				
4	78	68	60	54	74	64	57	52	57	52	47	51	47	43	45	42	39	36				
5	72	61	53	47	68	58	50	45	52	46	41	46	41	38	41	37	34	31				
6	67	55	47	41	63	52	45	40	47	41	36	42	37	33	37	33	31	28				
7	62	50	42	36	58	47	40	35	43	37	32	38	34	30	34	30	27	25				
8	58	46	38	33	54	43	36	31	39	33	29	35	30	27	32	28	25	23				
9	54	42	34	29	51	40	33	28	36	30	26	33	28	24	29	25	23	21				
10	51	39	31	26	48	37	30	26	33	28	24	30	26	22	27	23	21	19				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15681	15681	15681
5°	15741	15486	15571
10°	15621	15231	15101
15°	15442	14780	14355
20°	15192	14136	13426
25°	14938	13402	12527
30°	14585	12652	11373
35°	14241	11832	10360
40°	13894	10985	9187
45°	13486	10035	8127
50°	13069	9075	7086
55°	12645	8042	6086
60°	12148	6952	5050
65°	11584	5841	4604
70°	10914	4810	4230
75°	10087	4386	3949
80°	8908	3924	3598
85°	7003	3094	3094



TEST NUMBER: P331680-935

CATALOG NUMBER: SA2XXRDIP-C675D330U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.9	2.9
10°-20°	249.6	8.1
20°-30°	350.5	11.3
30°-40°	382.2	12.3
40°-50°	351.5	11.3
50°-60°	276.0	8.9
60°-70°	180.0	5.8
70°-80°	92.8	3.0
80°-90°	25.5	0.8
90°-100°	63.3	2.0
100°-110°	214.7	6.9
110°-120°	228.0	7.4
120°-130°	187.7	6.1
130°-140°	150.7	4.9
140°-150°	113.9	3.7
150°-160°	80.1	2.6
160°-170°	47.1	1.5
170°-180°	15.3	0.5
0°-30°	691.1	22.3
0°-40°	1073.3	34.6
0°-60°	1700.8	54.9
0°-90°	1999.0	64.5
90°-120°	505.9	16.3
90°-150°	958.3	30.9
90°-180°	1101.0	35.5
0°-180°	3099.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	971	966	956	963	961	92
15°	924	913	884	868	859	260
25°	838	809	752	718	703	385
35°	722	676	600	547	526	452
45°	591	530	440	379	356	456
55°	449	379	286	235	216	401
65°	303	232	153	125	120	300
75°	162	102	70	64	63	171
85°	38	20	17	17	17	45
90°	0	4	10	10	10	2
95°	11	26	119	45	35	11
105°	37	56	225	403	343	39
115°	65	83	189	389	451	65
125°	91	108	181	315	366	81
135°	107	128	179	265	303	83
145°	122	141	178	221	242	77
155°	139	150	173	196	204	64
165°	152	156	166	176	179	43
175°	158	158	159	161	161	15
180°	158	158	158	158	158	



TEST NUMBER: P331680-935

CATALOG NUMBER: SA2XXRDIP-C675D330U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2
2.5°	974.7	974.0	973.2	972.4	971.6	970.3	968.6	966.9	965.3	963.5	965.1
5°	971.2	970.3	969.3	968.3	967.3	965.6	963.0	960.5	957.9	955.5	957.2
7.5°	961.2	960.0	958.8	957.6	956.4	954.2	951.3	948.4	945.4	942.5	942.9
10°	952.8	951.4	950.0	948.6	947.3	944.7	940.7	936.9	933.0	929.0	928.5
12.5°	942.2	940.6	938.8	937.2	935.5	932.2	927.2	922.2	917.1	912.1	911.1
15°	923.8	921.6	919.5	917.3	915.2	910.8	904.1	897.5	890.9	884.2	880.5
17.5°	901.1	897.9	894.6	891.2	887.9	882.1	873.6	865.0	856.5	848.0	843.6
20°	884.2	880.3	876.4	872.5	868.6	861.8	852.0	842.2	832.5	822.7	817.8
22.5°	865.9	861.6	857.2	852.8	848.4	840.8	829.7	818.7	807.7	796.7	790.4
25°	838.5	832.2	826.0	819.8	813.6	803.9	791.1	778.2	765.3	752.3	744.3
27.5°	805.5	798.7	791.9	785.1	778.3	767.6	753.1	738.6	724.0	709.5	700.2
30°	782.3	774.8	767.4	760.0	752.6	741.1	725.4	709.8	694.1	678.6	668.6
32.5°	759.7	751.1	742.4	733.7	725.0	712.7	696.8	680.9	665.0	649.0	637.7
35°	722.5	712.6	702.6	692.6	682.7	669.1	651.9	634.7	617.5	600.3	588.0
37.5°	685.3	674.2	663.3	652.4	641.4	626.8	608.6	590.2	571.9	553.5	540.0
40°	659.2	647.5	635.8	624.1	612.3	597.0	578.1	559.1	540.2	521.2	507.4
42.5°	632.5	620.2	607.8	595.5	583.2	567.1	547.6	528.1	508.4	488.9	474.5
45°	590.6	577.6	564.5	551.4	538.3	521.5	501.0	480.5	459.9	439.5	425.6
47.5°	549.8	536.0	522.1	508.2	494.4	476.9	455.7	434.5	413.4	392.2	378.4
50°	520.3	506.4	492.6	478.7	464.9	447.2	425.7	404.2	382.7	361.3	347.8
52.5°	491.5	477.0	462.5	448.1	433.5	415.8	394.8	373.8	352.8	331.7	318.7
55°	449.2	433.9	418.7	403.5	388.2	370.1	349.0	327.9	306.8	285.7	274.0
57.5°	405.7	390.1	374.4	358.9	343.2	325.3	305.0	284.7	264.4	244.2	233.4
60°	376.2	360.6	344.9	329.3	313.7	295.8	275.7	255.5	235.5	215.3	205.3
62.5°	347.3	331.7	316.1	300.5	284.8	267.4	248.3	229.1	209.9	190.7	181.2
65°	303.2	287.4	271.6	255.8	240.0	223.3	205.7	188.1	170.5	152.9	146.3
67.5°	260.7	245.0	229.3	213.6	197.9	182.1	166.3	150.5	134.7	118.8	115.8
70°	231.2	215.9	200.7	185.5	170.2	155.8	142.4	128.9	115.5	101.9	100.0
72.5°	203.0	188.4	173.8	159.2	144.6	131.9	121.1	110.2	99.4	88.6	87.0
75°	161.7	148.1	134.4	120.7	107.0	96.9	90.2	83.6	77.0	70.3	69.0
77.5°	121.1	109.1	97.1	85.2	73.2	65.5	62.3	59.2	56.0	52.8	51.9
80°	95.8	85.8	75.9	66.0	56.0	50.0	48.0	46.1	44.2	42.2	41.4
82.5°	72.6	64.8	57.1	49.2	41.5	36.9	35.6	34.3	33.0	31.7	31.2
85°	37.8	33.7	29.6	25.5	21.4	19.0	18.4	17.9	17.3	16.7	16.7
87.5°	11.3	10.2	9.2	8.1	7.0	6.5	6.8	7.2	7.7	7.7	7.5
90°	0.3	1.2	2.4	3.0	3.6	4.6	6.1	8.2	10.1	10.3	10.1
92.5°	3.7	5.3	7.6	8.9	10.9	13.8	20.7	30.4	39.0	39.5	33.4
95°	10.7	11.9	14.9	17.7	22.5	29.8	43.8	70.3	105.6	119.2	104.4
97.5°	17.3	18.9	22.2	26.3	31.9	40.2	57.8	94.7	153.3	203.5	213.5
100°	23.4	24.4	27.0	31.9	38.1	46.6	62.7	99.8	165.5	240.3	284.1
102.5°	29.0	29.7	32.5	37.3	43.7	52.2	67.1	100.0	160.8	241.5	310.4
105°	37.1	38.3	40.5	45.0	51.7	60.3	74.6	101.6	151.8	225.4	306.3
107.5°	45.9	46.8	48.9	53.1	59.8	68.4	82.2	105.8	147.3	208.1	279.7
110°	51.7	53.0	54.8	58.7	65.1	74.0	87.3	109.2	146.4	199.8	262.9



TEST NUMBER: P331680-935

CATALOG NUMBER: SA2XXRDIP-C675D330U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	57.1	58.3	60.4	64.1	70.2	79.3	92.2	112.9	146.5	194.5	251.2
115°	65.4	66.9	68.8	72.4	78.5	86.7	99.8	118.3	147.8	188.6	236.7
117.5°	74.0	75.3	77.1	80.3	86.2	94.7	106.8	124.2	150.1	185.7	227.6
120°	79.4	80.6	82.5	85.2	91.3	99.8	111.7	128.1	151.5	184.1	222.7
122.5°	84.6	85.5	87.3	90.3	96.3	105.1	116.2	131.5	153.2	183.0	218.5
125°	91.3	92.2	94.0	97.6	103.8	112.3	123.2	136.9	155.8	181.3	212.7
127.5°	96.6	97.8	100.4	104.4	110.2	119.0	129.7	142.0	158.3	180.3	207.2
130°	99.8	101.0	104.0	108.3	114.4	122.9	133.5	145.1	160.3	179.8	203.5
132.5°	102.7	104.2	107.5	111.9	118.3	126.8	137.0	148.3	162.3	179.5	200.6
135°	107.1	108.3	111.9	116.5	123.6	132.0	141.8	152.4	164.6	179.2	196.5
137.5°	111.2	112.7	116.3	121.2	128.1	136.0	145.7	155.6	166.7	179.1	193.6
140°	114.4	115.6	119.2	124.2	130.8	138.7	147.8	157.3	167.6	178.9	191.9
142.5°	117.5	118.6	121.9	126.8	133.3	140.7	149.6	158.8	168.3	178.9	190.3
145°	122.3	123.6	126.6	131.1	137.2	143.9	152.1	160.7	169.1	178.2	188.0
147.5°	127.4	128.3	131.2	135.4	140.5	146.5	154.2	161.7	169.4	177.2	185.7
150°	130.8	131.7	134.1	138.1	142.7	148.2	155.2	162.1	169.1	176.4	183.7
152.5°	134.2	134.7	137.1	140.5	144.9	149.8	156.1	162.4	168.7	175.2	182.0
155°	139.1	139.3	141.1	144.5	147.8	152.4	157.6	162.7	167.9	173.1	178.9
157.5°	143.0	143.4	144.8	147.7	150.4	154.2	158.6	162.7	166.5	170.9	175.9
160°	145.7	146.0	147.2	149.6	152.1	155.5	159.1	162.7	165.8	169.4	173.7
162.5°	148.4	148.2	149.5	151.4	153.6	156.2	159.4	162.5	165.1	168.2	171.8
165°	151.5	151.2	151.8	153.6	155.2	157.0	159.7	161.9	163.7	165.8	168.5
167.5°	154.0	153.7	154.2	155.4	156.5	157.6	159.6	161.4	162.3	163.7	165.4
170°	155.8	155.2	155.5	156.4	157.0	157.9	159.4	160.9	161.5	162.5	163.7
172.5°	156.7	156.4	156.2	157.1	157.5	158.2	159.2	160.2	160.6	161.0	162.0
175°	157.9	157.6	157.3	157.9	157.9	158.2	158.8	159.4	159.1	159.4	159.7
177.5°	158.4	157.9	157.7	158.2	158.2	158.2	158.4	158.9	158.4	158.2	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331680-935

CATALOG NUMBER: SA2XXRDIP-C675D330U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2
2.5°	966.6	968.2	969.7	970.3	970.1	969.7	969.5	969.1
5°	958.9	960.7	962.4	963.0	962.4	961.8	961.3	960.7
7.5°	943.4	943.9	944.4	944.2	943.1	942.2	941.2	940.1
10°	927.9	927.3	926.7	925.8	924.6	923.5	922.3	921.1
12.5°	910.1	909.0	907.9	906.5	904.5	902.6	900.6	898.6
15°	876.8	873.1	869.4	866.5	864.6	862.6	860.7	858.8
17.5°	839.2	834.7	830.3	826.5	823.1	819.8	816.4	813.0
20°	813.0	808.0	803.1	798.6	794.3	790.0	785.7	781.4
22.5°	784.1	777.8	771.5	766.8	763.5	760.3	757.2	754.0
25°	736.3	728.3	720.3	714.9	712.0	709.0	706.1	703.2
27.5°	690.8	681.5	672.2	665.1	660.5	655.8	651.2	646.5
30°	658.7	648.7	638.7	631.1	625.8	620.5	615.3	610.0
32.5°	626.3	614.9	603.6	595.4	590.4	585.5	580.5	575.6
35°	575.8	563.4	551.1	542.8	538.5	534.2	529.9	525.6
37.5°	526.4	512.9	499.4	490.1	485.2	480.3	475.4	470.5
40°	493.4	479.6	465.7	456.2	451.2	446.1	441.0	435.9
42.5°	460.2	445.8	431.5	421.9	417.0	412.1	407.2	402.2
45°	411.7	397.9	384.0	374.7	370.1	365.3	360.7	355.9
47.5°	364.6	350.9	337.0	328.0	323.7	319.5	315.2	311.0
50°	334.3	320.8	307.4	298.5	294.5	290.3	286.3	282.1
52.5°	305.7	292.7	279.7	271.3	267.5	263.7	259.9	256.1
55°	262.3	250.5	238.8	231.1	227.4	223.6	219.9	216.2
57.5°	222.7	212.0	201.2	194.2	191.1	188.0	184.9	181.8
60°	195.4	185.5	175.5	168.9	165.8	162.7	159.5	156.4
62.5°	171.8	162.2	152.7	147.1	145.2	143.4	141.5	139.6
65°	139.7	133.0	126.4	122.8	122.2	121.6	121.0	120.5
67.5°	112.7	109.7	106.7	104.8	104.2	103.6	103.0	102.3
70°	98.1	96.1	94.1	92.8	92.0	91.2	90.4	89.6
72.5°	85.3	83.7	82.1	81.0	80.5	80.1	79.6	79.1
75°	67.6	66.2	64.8	64.1	63.9	63.7	63.5	63.3
77.5°	51.1	50.4	49.6	49.1	48.7	48.5	48.1	47.8
80°	40.6	39.9	39.1	38.7	38.7	38.7	38.7	38.7
82.5°	30.7	30.2	29.8	29.5	29.5	29.5	29.5	29.5
85°	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7
87.5°	7.2	7.0	7.0	6.9	6.9	6.9	6.9	6.9
90°	9.7	9.1	9.7	10.1	10.1	10.1	10.1	10.1
92.5°	26.5	22.7	20.2	18.3	18.1	17.1	17.3	16.9
95°	79.7	61.1	48.4	41.7	37.7	35.3	34.4	34.7
97.5°	186.0	152.1	119.2	97.3	82.7	75.3	70.9	68.3
100°	277.8	240.0	198.4	161.5	136.3	123.2	114.4	108.9
102.5°	337.9	329.3	298.9	259.8	232.4	210.1	199.1	191.7
105°	369.6	404.0	407.9	398.0	379.0	360.2	347.1	342.9
107.5°	346.7	398.6	430.2	444.9	447.3	446.3	443.6	438.0
110°	327.0	381.5	420.4	445.4	458.5	464.3	467.0	466.7





TEST NUMBER: P331680-935

CATALOG NUMBER: SA2XXRDIP-C675D330U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	309.0	361.3	402.9	431.5	449.7	459.3	464.5	466.1
115°	286.9	333.7	373.6	404.9	426.5	440.5	448.4	451.2
117.5°	270.2	311.3	347.5	376.9	398.9	413.7	422.0	424.3
120°	261.9	299.6	331.9	359.6	380.9	395.2	404.0	407.1
122.5°	255.4	289.9	320.5	345.4	364.5	378.7	386.5	389.0
125°	245.8	277.2	303.9	326.7	344.4	355.9	363.5	366.0
127.5°	236.3	264.8	290.0	311.0	326.4	337.3	343.8	345.8
130°	230.3	256.5	280.5	300.6	315.5	325.8	331.9	334.3
132.5°	224.5	248.7	270.8	289.6	304.3	314.6	320.2	322.4
135°	216.3	236.3	256.5	273.5	286.5	296.6	302.1	303.3
137.5°	209.8	226.6	242.5	257.4	269.3	277.9	282.8	284.6
140°	205.6	220.2	234.3	247.6	257.4	265.3	269.8	271.6
142.5°	202.2	214.6	226.7	237.9	247.1	254.3	258.4	258.7
145°	197.4	207.5	216.9	225.8	233.0	238.2	241.3	242.1
147.5°	193.7	201.6	209.0	215.4	221.4	225.6	227.6	228.3
150°	191.1	197.8	204.1	209.6	214.1	217.8	219.6	220.0
152.5°	188.4	194.6	200.0	204.7	208.4	211.5	212.8	212.9
155°	184.7	189.5	194.1	197.4	200.8	202.9	204.1	203.5
157.5°	180.4	184.4	188.2	190.9	193.2	195.0	195.5	195.5
160°	177.6	181.0	184.3	186.5	188.6	190.1	190.5	190.5
162.5°	175.0	177.9	180.7	182.4	184.5	185.5	185.8	185.5
165°	171.0	173.1	175.2	176.4	177.6	178.9	178.9	178.6
167.5°	167.1	168.8	170.2	171.3	171.9	172.5	172.5	172.1
170°	165.2	166.1	167.3	167.9	168.2	169.1	168.8	168.2
172.5°	163.0	163.7	164.6	165.0	165.3	165.7	165.4	165.1
175°	160.7	160.9	161.3	161.5	161.5	161.9	161.5	160.9
177.5°	158.9	158.9	159.2	159.2	159.2	159.2	158.9	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2

(END OF REPORT)