

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331715-935

Luminaire Tested: **SA2XXRDIP-C865D530U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331715-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D530U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4225.7 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331715-935
CATALOG NUMBER: SA2XXRDIP-C865D530U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331715-935

CATALOG NUMBER: SA2XXRDIP-C865D530U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62				
1	101	97	93	90	94	91	88	85	80	77	75	69	68	66	60	59	57	53				
2	92	85	79	74	86	80	75	70	70	66	63	62	59	56	53	51	49	45				
3	85	75	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43	39				
4	78	67	59	54	73	63	56	51	56	51	46	49	45	42	43	40	37	34				
5	72	60	52	46	67	57	50	44	51	45	40	45	40	37	39	36	33	30				
6	66	54	46	41	62	51	44	39	46	40	36	41	36	32	36	32	29	27				
7	62	49	41	36	58	47	40	35	42	36	32	37	32	29	33	29	26	24				
8	57	45	37	32	54	43	36	31	38	33	28	34	30	26	30	27	24	22				
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	24	22	20				
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	22	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20384	20384	20384
5°	20462	20128	20238
10°	20305	19799	19630
15°	20072	19211	18658
20°	19747	18374	17452
25°	19417	17423	16283
30°	18957	16444	14783
35°	18510	15380	13466
40°	18061	14280	11944
45°	17532	13045	10565
50°	16990	11796	9211
55°	16434	10452	7910
60°	15791	9038	6568
65°	15060	7595	5979
70°	14186	6255	5500
75°	13119	5702	5128
80°	11576	5095	4677
85°	9114	4020	4020



TEST NUMBER: P331715-935

CATALOG NUMBER: SA2XXRDIP-C865D530U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.2	2.8
10°-20°	324.5	7.7
20°-30°	455.6	10.8
30°-40°	496.8	11.8
40°-50°	456.8	10.8
50°-60°	358.8	8.5
60°-70°	233.9	5.5
70°-80°	120.6	2.9
80°-90°	33.6	0.8
90°-100°	36.9	0.9
100°-110°	114.5	2.7
110°-120°	195.7	4.6
120°-130°	257.4	6.1
130°-140°	288.9	6.8
140°-150°	283.3	6.7
150°-160°	237.6	5.6
160°-170°	157.6	3.7
170°-180°	55.1	1.3
0°-30°	898.3	21.3
0°-40°	1395.1	33.0
0°-60°	2210.7	52.3
0°-90°	2598.9	61.5
90°-120°	347.1	8.2
90°-150°	1176.6	27.8
90°-180°	1627.0	38.5
0°-180°	4225.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1262	1262	1262	1262	1262	
5°	1262	1256	1242	1251	1249	120
15°	1201	1187	1149	1128	1116	338
25°	1090	1051	978	933	914	501
35°	939	878	780	711	683	587
45°	768	689	571	493	463	593
55°	584	493	371	305	281	521
65°	394	301	199	162	156	391
75°	210	133	91	84	82	223
85°	49	26	22	22	22	58
90°	0	7	17	16	17	3
95°	26	30	31	31	30	29
105°	106	107	108	109	109	112
115°	196	199	198	198	196	194
125°	286	290	289	287	287	255
135°	370	375	376	376	374	285
145°	449	452	455	456	454	280
155°	513	515	516	518	517	236
165°	558	558	558	561	559	157
175°	581	579	578	581	579	55
180°	582	582	582	582	582	



TEST NUMBER: P331715-935

CATALOG NUMBER: SA2XXRDIP-C865D530U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5
2.5°	1267.0	1266.0	1265.0	1263.9	1263.0	1261.4	1259.1	1256.9	1254.6	1252.4	1254.5
5°	1262.5	1261.2	1259.9	1258.6	1257.4	1255.1	1251.8	1248.5	1245.2	1241.9	1244.1
7.5°	1249.4	1247.8	1246.3	1244.7	1243.1	1240.4	1236.6	1232.7	1228.8	1224.9	1225.6
10°	1238.5	1236.7	1234.9	1233.1	1231.3	1228.0	1222.9	1217.8	1212.7	1207.6	1206.9
12.5°	1224.8	1222.5	1220.4	1218.2	1216.0	1211.7	1205.1	1198.7	1192.1	1185.7	1184.3
15°	1200.8	1198.0	1195.2	1192.4	1189.6	1183.9	1175.3	1166.7	1158.0	1149.3	1144.5
17.5°	1171.3	1167.0	1162.8	1158.5	1154.3	1146.6	1135.5	1124.4	1113.4	1102.3	1096.6
20°	1149.3	1144.3	1139.2	1134.1	1129.0	1120.2	1107.4	1094.8	1082.1	1069.4	1063.0
22.5°	1125.6	1119.9	1114.2	1108.5	1102.9	1092.9	1078.5	1064.2	1049.9	1035.5	1027.3
25°	1089.9	1081.8	1073.7	1065.6	1057.5	1045.0	1028.2	1011.5	994.7	978.0	967.6
27.5°	1047.0	1038.1	1029.3	1020.5	1011.7	997.8	978.9	960.0	941.1	922.2	910.1
30°	1016.8	1007.2	997.6	987.9	978.3	963.3	943.0	922.6	902.3	882.0	869.1
32.5°	987.6	976.3	965.0	953.7	942.5	926.5	905.8	885.0	864.4	843.6	828.9
35°	939.1	926.2	913.3	900.3	887.3	869.7	847.3	825.0	802.7	780.3	764.3
37.5°	890.7	876.5	862.3	848.0	833.8	814.8	791.0	767.2	743.4	719.5	701.9
40°	856.9	841.6	826.4	811.1	795.9	776.0	751.4	726.8	702.1	677.5	659.4
42.5°	822.2	806.1	790.1	774.0	757.9	737.2	711.8	686.3	660.9	635.4	616.8
45°	767.8	750.7	733.7	716.7	699.7	677.9	651.3	624.6	597.9	571.3	553.2
47.5°	714.7	696.7	678.7	660.6	642.7	619.8	592.4	564.8	537.3	509.8	491.9
50°	676.4	658.3	640.3	622.2	604.2	581.3	553.4	525.4	497.5	469.6	452.0
52.5°	638.9	620.0	601.2	582.4	563.5	540.4	513.2	485.8	458.5	431.2	414.2
55°	583.8	564.0	544.2	524.4	504.6	481.0	453.6	426.1	398.7	371.3	356.1
57.5°	527.4	507.0	486.7	466.4	446.2	422.8	396.4	370.1	343.7	317.4	303.4
60°	489.0	468.6	448.4	428.1	407.8	384.5	358.3	332.2	306.1	279.9	267.0
62.5°	451.5	431.2	410.9	390.5	370.2	347.7	322.7	297.8	272.9	247.9	235.6
65°	394.2	373.6	353.0	332.4	311.9	290.2	267.3	244.5	221.6	198.8	190.2
67.5°	338.9	318.5	298.1	277.6	257.2	236.7	216.2	195.6	175.0	154.5	150.5
70°	300.5	280.7	260.9	241.1	221.3	202.6	185.1	167.6	150.1	132.5	130.0
72.5°	263.9	245.0	225.9	207.0	188.0	171.4	157.4	143.3	129.2	115.2	113.0
75°	210.3	192.4	174.7	156.9	139.1	126.0	117.3	108.7	100.0	91.4	89.6
77.5°	157.5	141.8	126.2	110.6	95.1	85.2	81.0	76.9	72.8	68.5	67.5
80°	124.5	111.6	98.7	85.7	72.8	65.0	62.4	59.9	57.3	54.8	53.8
82.5°	94.4	84.3	74.1	64.1	54.0	48.0	46.3	44.6	42.9	41.2	40.6
85°	49.2	43.8	38.5	33.1	27.8	24.8	24.0	23.2	22.5	21.7	21.7
87.5°	14.7	13.3	12.0	10.6	9.3	8.9	9.3	9.8	10.2	10.8	10.5
90°	0.5	1.8	3.1	4.4	5.8	7.6	10.0	12.4	14.8	17.2	17.0
92.5°	8.8	9.7	10.7	11.6	12.6	13.3	13.9	14.5	15.1	15.6	15.7
95°	25.6	26.6	27.7	28.8	29.9	30.6	30.7	31.0	31.2	31.4	31.4
97.5°	46.7	47.6	48.6	49.5	50.5	51.1	51.6	52.0	52.4	52.9	52.9
100°	62.3	63.2	64.1	65.0	65.9	66.5	66.8	67.1	67.4	67.8	67.8
102.5°	78.9	79.6	80.2	80.9	81.6	82.2	82.7	83.0	83.4	83.9	83.9
105°	105.6	105.9	106.2	106.5	106.9	107.1	107.4	107.5	107.8	108.1	108.2
107.5°	132.5	132.9	133.5	133.9	134.4	134.7	134.7	134.7	134.7	134.7	134.7
110°	149.7	150.4	151.0	151.7	152.4	152.7	152.7	152.7	152.7	152.7	152.7



TEST NUMBER: P331715-935

CATALOG NUMBER: SA2XXRDIP-C865D530U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	168.6	169.3	169.9	170.6	171.3	171.5	171.4	171.3	171.3	171.2	170.9
115°	196.4	197.1	197.7	198.4	199.0	199.2	199.0	198.8	198.5	198.4	198.3
117.5°	224.1	225.0	225.8	226.7	227.6	227.7	227.1	226.4	225.8	225.2	225.0
120°	242.5	243.4	244.3	245.1	246.1	246.1	245.1	244.3	243.4	242.5	242.5
122.5°	259.4	260.5	261.6	262.6	263.6	263.8	263.2	262.6	262.0	261.4	261.1
125°	285.8	286.7	287.7	288.7	289.6	290.0	289.6	289.4	289.0	288.7	288.3
127.5°	311.3	312.6	313.8	315.1	316.3	316.8	316.4	316.0	315.6	315.2	314.8
130°	327.5	328.9	330.3	331.7	333.1	333.7	333.6	333.3	333.1	332.9	332.7
132.5°	345.5	346.7	347.8	349.0	350.2	350.8	350.9	350.9	350.9	350.9	350.5
135°	369.7	370.9	372.1	373.3	374.5	375.2	375.4	375.7	375.9	376.1	376.0
137.5°	395.1	396.1	397.1	398.1	399.1	399.7	400.0	400.3	400.5	400.8	400.7
140°	410.4	411.5	412.4	413.4	414.4	415.2	415.7	416.2	416.8	417.3	417.3
142.5°	426.2	427.1	428.2	429.1	430.1	430.8	431.2	431.5	431.9	432.2	432.3
145°	448.8	449.5	450.3	451.1	451.9	452.5	453.1	453.8	454.5	455.1	455.2
147.5°	468.9	469.8	470.7	471.7	472.5	473.2	473.6	474.1	474.5	475.0	475.2
150°	482.7	483.3	484.0	484.6	485.3	485.8	486.2	486.6	487.1	487.6	487.8
152.5°	494.8	495.5	496.1	496.8	497.4	498.0	498.5	499.0	499.6	500.2	500.5
155°	513.1	513.4	513.8	514.0	514.4	514.7	515.1	515.4	515.7	516.0	516.6
157.5°	528.7	528.9	529.1	529.3	529.6	529.8	529.9	530.2	530.4	530.5	531.3
160°	538.1	538.3	538.6	538.7	539.0	539.2	539.2	539.3	539.5	539.6	540.3
162.5°	546.7	546.8	546.8	546.9	546.9	547.0	547.1	547.3	547.3	547.4	548.2
165°	558.3	558.1	558.0	557.9	557.8	557.8	557.8	557.8	557.8	557.8	558.5
167.5°	567.8	567.6	567.2	566.9	566.5	566.4	566.4	566.4	566.3	566.3	567.1
170°	573.0	572.7	572.3	572.0	571.7	571.4	571.4	571.2	571.1	571.0	571.8
172.5°	576.5	576.2	575.8	575.5	575.2	575.0	574.9	574.8	574.6	574.5	575.3
175°	580.8	580.5	580.1	579.9	579.5	579.3	579.0	578.9	578.6	578.3	579.1
177.5°	582.6	582.3	582.0	581.8	581.5	581.3	581.2	581.0	580.8	580.7	581.2
180°	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8



TEST NUMBER: P331715-935

CATALOG NUMBER: SA2XXRDIP-C865D530U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5
2.5°	1256.5	1258.5	1260.5	1261.4	1260.9	1260.5	1260.2	1259.7
5°	1246.5	1248.7	1251.0	1251.8	1251.0	1250.3	1249.5	1248.7
7.5°	1226.3	1226.9	1227.6	1227.3	1226.0	1224.7	1223.3	1222.0
10°	1206.1	1205.3	1204.5	1203.4	1201.9	1200.4	1198.9	1197.3
12.5°	1182.9	1181.6	1180.2	1178.3	1175.7	1173.2	1170.6	1168.1
15°	1139.7	1134.9	1130.1	1126.4	1123.9	1121.3	1118.8	1116.2
17.5°	1090.8	1085.0	1079.3	1074.3	1069.9	1065.6	1061.2	1056.8
20°	1056.7	1050.3	1044.0	1038.0	1032.4	1026.8	1021.2	1015.7
22.5°	1019.3	1011.1	1002.9	996.7	992.6	988.3	984.2	980.1
25°	957.2	946.8	936.3	929.2	925.4	921.6	917.8	914.0
27.5°	897.9	885.8	873.7	864.6	858.6	852.5	846.4	840.4
30°	856.1	843.2	830.2	820.3	813.5	806.6	799.8	792.9
32.5°	814.1	799.3	784.5	773.9	767.5	761.0	754.6	748.1
35°	748.3	732.4	716.4	705.6	700.0	694.4	688.8	683.2
37.5°	684.3	666.7	649.1	637.1	630.7	624.2	617.9	611.5
40°	641.4	623.5	605.4	593.1	586.5	579.9	573.3	566.7
42.5°	598.2	579.5	560.9	548.4	542.0	535.6	529.2	522.8
45°	535.2	517.2	499.1	487.1	481.0	474.9	468.8	462.7
47.5°	473.9	456.0	438.1	426.4	420.9	415.3	409.7	404.2
50°	434.5	417.0	399.5	388.1	382.7	377.4	372.0	366.7
52.5°	397.4	380.5	363.5	352.7	347.7	342.8	337.9	332.9
55°	340.9	325.6	310.4	300.3	295.5	290.7	285.9	281.0
57.5°	289.5	275.5	261.6	252.5	248.5	244.4	240.3	236.3
60°	254.0	241.1	228.1	219.6	215.5	211.5	207.4	203.4
62.5°	223.3	210.9	198.5	191.1	188.7	186.3	183.8	181.4
65°	181.5	172.9	164.3	159.5	158.8	158.1	157.3	156.5
67.5°	146.5	142.6	138.6	136.2	135.4	134.6	133.8	133.0
70°	127.4	124.9	122.3	120.6	119.6	118.6	117.5	116.5
72.5°	110.9	108.7	106.6	105.3	104.6	104.0	103.4	102.8
75°	87.8	86.1	84.3	83.3	83.0	82.7	82.5	82.2
77.5°	66.6	65.5	64.5	63.8	63.4	62.9	62.6	62.2
80°	52.8	51.8	50.8	50.3	50.3	50.3	50.3	50.3
82.5°	40.0	39.3	38.7	38.4	38.4	38.4	38.4	38.4
85°	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7
87.5°	10.2	10.0	9.7	9.6	9.6	9.7	9.7	9.7
90°	16.8	16.5	16.3	16.3	16.4	16.4	16.6	16.7
92.5°	15.7	15.8	15.8	15.8	15.8	15.8	15.9	15.9
95°	31.4	31.4	31.4	31.3	31.1	30.9	30.7	30.5
97.5°	52.9	52.9	52.9	52.8	52.8	52.8	52.8	52.7
100°	67.8	67.8	67.8	67.7	67.6	67.5	67.4	67.2
102.5°	84.0	84.1	84.2	84.2	84.1	83.9	83.9	83.8
105°	108.5	108.7	108.9	109.0	109.0	109.0	109.0	109.0
107.5°	134.8	134.9	135.0	134.7	134.2	133.8	133.3	132.8
110°	152.7	152.7	152.7	152.6	152.2	151.9	151.5	151.2



TEST NUMBER: P331715-935

CATALOG NUMBER: SA2XXRDIP-C865D530U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	170.7	170.4	170.1	169.9	169.6	169.4	169.1	168.9
115°	198.1	198.0	197.9	197.7	197.3	197.1	196.7	196.4
117.5°	224.7	224.5	224.2	223.9	223.6	223.3	222.9	222.6
120°	242.5	242.5	242.5	242.4	242.0	241.8	241.4	241.1
122.5°	260.9	260.6	260.4	260.1	259.8	259.6	259.4	259.2
125°	288.0	287.7	287.4	287.1	287.1	287.0	286.8	286.7
127.5°	314.4	314.0	313.7	313.2	312.9	312.5	312.2	311.9
130°	332.4	332.3	332.0	331.7	331.2	330.8	330.4	329.9
132.5°	350.0	349.5	349.0	348.6	348.3	347.9	347.6	347.2
135°	375.9	375.7	375.7	375.4	375.1	374.8	374.4	374.1
137.5°	400.6	400.5	400.5	400.2	399.8	399.3	398.9	398.5
140°	417.3	417.3	417.3	417.2	416.6	416.2	415.8	415.3
142.5°	432.4	432.5	432.6	432.4	432.0	431.5	431.1	430.7
145°	455.4	455.5	455.6	455.4	455.0	454.5	454.1	453.7
147.5°	475.4	475.7	476.0	475.9	475.4	475.0	474.6	474.2
150°	488.2	488.5	488.9	488.9	488.5	488.2	487.8	487.6
152.5°	500.9	501.4	501.8	501.8	501.4	500.9	500.5	500.2
155°	517.1	517.6	518.2	518.3	518.0	517.6	517.3	517.0
157.5°	532.0	532.8	533.6	533.6	533.1	532.6	532.1	531.5
160°	540.9	541.6	542.2	542.3	541.9	541.5	541.0	540.5
162.5°	548.9	549.7	550.4	550.5	550.0	549.5	549.0	548.5
165°	559.3	560.1	560.8	560.9	560.3	559.8	559.3	558.7
167.5°	567.8	568.6	569.4	569.5	568.9	568.3	567.7	567.1
170°	572.6	573.3	574.0	574.1	573.4	572.8	572.1	571.5
172.5°	576.1	576.9	577.6	577.6	577.0	576.4	575.7	575.1
175°	579.9	580.7	581.4	581.5	580.8	580.1	579.5	578.9
177.5°	581.7	582.2	582.7	582.7	582.2	581.7	581.2	580.7
180°	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8

(END OF REPORT)