

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331721-935

Luminaire Tested: **SA2XXRDIP-C865D725U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331721-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C865D725U935-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4829.7 lumens  
Efficiency: N/A  
Efficacy: 88.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331721-935  
CATALOG NUMBER: SA2XXRDIP-C865D725U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331721-935

CATALOG NUMBER: SA2XXRDIP-C865D725U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	67	61	77	69	63	58	60	55	51	51	47	44	43	40	38	34
4	76	66	58	52	71	61	55	49	53	48	44	46	42	38	39	36	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	29	26	23
7	60	48	40	35	56	45	38	33	40	34	30	34	30	27	29	26	23	21
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21	19
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20384	20384	20384
5°	20462	20128	20238
10°	20305	19799	19630
15°	20072	19211	18658
20°	19747	18374	17452
25°	19417	17423	16283
30°	18957	16444	14783
35°	18510	15380	13466
40°	18061	14280	11944
45°	17532	13045	10565
50°	16990	11796	9211
55°	16434	10452	7910
60°	15791	9038	6568
65°	15060	7595	5979
70°	14186	6255	5500
75°	13119	5702	5128
80°	11576	5095	4677
85°	9114	4020	4020



TEST NUMBER: P331721-935

CATALOG NUMBER: SA2XXRDIP-C865D725U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.2	2.4
10°-20°	324.5	6.7
20°-30°	455.6	9.4
30°-40°	496.8	10.3
40°-50°	456.8	9.5
50°-60°	358.8	7.4
60°-70°	233.9	4.8
70°-80°	120.6	2.5
80°-90°	34.5	0.7
90°-100°	50.5	1.0
100°-110°	157.0	3.2
110°-120°	268.3	5.6
120°-130°	352.8	7.3
130°-140°	396.0	8.2
140°-150°	388.3	8.0
150°-160°	325.7	6.7
160°-170°	216.0	4.5
170°-180°	75.5	1.6
0°-30°	898.3	18.6
0°-40°	1395.1	28.9
0°-60°	2210.7	45.8
0°-90°	2599.7	53.8
90°-120°	475.8	9.9
90°-150°	1612.8	33.4
90°-180°	2230.0	46.2
0°-180°	4829.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1262	1262	1262	1262	1262	
5°	1262	1256	1242	1251	1249	120
15°	1201	1187	1149	1128	1116	338
25°	1090	1051	978	933	914	501
35°	939	878	780	711	683	587
45°	768	689	571	493	463	593
55°	584	493	371	305	281	521
65°	394	301	199	162	156	391
75°	210	133	91	84	82	223
85°	49	26	22	22	22	58
90°	1	9	24	22	23	4
95°	35	41	43	43	42	40
105°	145	147	148	149	149	153
115°	269	273	272	271	269	266
125°	392	397	396	394	393	350
135°	507	514	516	515	513	391
145°	615	620	624	624	622	384
155°	703	705	707	710	709	324
165°	765	765	764	769	766	216
175°	796	794	793	797	794	76
180°	798	798	798	798	798	



TEST NUMBER: P331721-935

CATALOG NUMBER: SA2XXRDIP-C865D725U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5
2.5°	1267.0	1266.0	1265.0	1263.9	1263.0	1261.4	1259.1	1256.9	1254.6	1252.4	1254.5
5°	1262.5	1261.2	1259.9	1258.6	1257.4	1255.1	1251.8	1248.5	1245.2	1241.9	1244.1
7.5°	1249.4	1247.8	1246.3	1244.7	1243.1	1240.4	1236.6	1232.7	1228.8	1224.9	1225.6
10°	1238.5	1236.7	1234.9	1233.1	1231.3	1228.0	1222.9	1217.8	1212.7	1207.6	1206.9
12.5°	1224.8	1222.5	1220.4	1218.2	1216.0	1211.7	1205.1	1198.7	1192.1	1185.7	1184.3
15°	1200.8	1198.0	1195.2	1192.4	1189.6	1183.9	1175.3	1166.7	1158.0	1149.3	1144.5
17.5°	1171.3	1167.0	1162.8	1158.5	1154.3	1146.6	1135.5	1124.4	1113.4	1102.3	1096.6
20°	1149.3	1144.3	1139.2	1134.1	1129.0	1120.2	1107.4	1094.8	1082.1	1069.4	1063.0
22.5°	1125.6	1119.9	1114.2	1108.5	1102.9	1092.9	1078.5	1064.2	1049.9	1035.5	1027.3
25°	1089.9	1081.8	1073.7	1065.6	1057.5	1045.0	1028.2	1011.5	994.7	978.0	967.6
27.5°	1047.0	1038.1	1029.3	1020.5	1011.7	997.8	978.9	960.0	941.1	922.2	910.1
30°	1016.8	1007.2	997.6	987.9	978.3	963.3	943.0	922.6	902.3	882.0	869.1
32.5°	987.6	976.3	965.0	953.7	942.5	926.5	905.8	885.0	864.4	843.6	828.9
35°	939.1	926.2	913.3	900.3	887.3	869.7	847.3	825.0	802.7	780.3	764.3
37.5°	890.7	876.5	862.3	848.0	833.8	814.8	791.0	767.2	743.4	719.5	701.9
40°	856.9	841.6	826.4	811.1	795.9	776.0	751.4	726.8	702.1	677.5	659.4
42.5°	822.2	806.1	790.1	774.0	757.9	737.2	711.8	686.3	660.9	635.4	616.8
45°	767.8	750.7	733.7	716.7	699.7	677.9	651.3	624.6	597.9	571.3	553.2
47.5°	714.7	696.7	678.7	660.6	642.7	619.8	592.4	564.8	537.3	509.8	491.9
50°	676.4	658.3	640.3	622.2	604.2	581.3	553.4	525.4	497.5	469.6	452.0
52.5°	638.9	620.0	601.2	582.4	563.5	540.4	513.2	485.8	458.5	431.2	414.2
55°	583.8	564.0	544.2	524.4	504.6	481.0	453.6	426.1	398.7	371.3	356.1
57.5°	527.4	507.0	486.7	466.4	446.2	422.8	396.4	370.1	343.7	317.4	303.4
60°	489.0	468.6	448.4	428.1	407.8	384.5	358.3	332.2	306.1	279.9	267.0
62.5°	451.5	431.2	410.9	390.5	370.2	347.7	322.7	297.8	272.9	247.9	235.6
65°	394.2	373.6	353.0	332.4	311.9	290.2	267.3	244.5	221.6	198.8	190.2
67.5°	338.9	318.5	298.1	277.6	257.2	236.7	216.2	195.6	175.0	154.5	150.5
70°	300.5	280.7	260.9	241.1	221.3	202.6	185.1	167.6	150.1	132.5	130.0
72.5°	263.9	245.0	225.9	207.0	188.0	171.4	157.4	143.3	129.2	115.2	113.0
75°	210.3	192.4	174.7	156.9	139.1	126.0	117.3	108.7	100.0	91.4	89.6
77.5°	157.5	141.8	126.2	110.6	95.1	85.2	81.0	76.9	72.8	68.5	67.5
80°	124.5	111.6	98.7	85.7	72.8	65.0	62.4	59.9	57.3	54.8	53.8
82.5°	94.4	84.3	74.1	64.1	54.0	48.0	46.3	44.6	42.9	41.2	40.6
85°	49.2	43.8	38.5	33.1	27.8	24.8	24.0	23.2	22.5	21.7	21.7
87.5°	14.7	13.5	12.2	10.9	9.7	9.4	10.1	10.7	11.4	12.1	11.8
90°	0.7	2.5	4.3	6.0	7.8	10.4	13.7	17.0	20.2	23.6	23.2
92.5°	12.0	13.3	14.6	15.9	17.2	18.3	19.0	19.8	20.7	21.4	21.4
95°	35.0	36.5	38.0	39.5	41.0	41.8	42.2	42.4	42.8	43.0	43.0
97.5°	64.0	65.3	66.6	67.8	69.2	70.2	70.7	71.3	71.8	72.4	72.4
100°	85.5	86.7	87.8	89.0	90.2	91.1	91.5	92.0	92.4	92.9	92.9
102.5°	108.1	109.0	110.0	111.0	111.9	112.7	113.2	113.8	114.3	114.9	115.0
105°	144.7	145.2	145.6	146.0	146.5	146.9	147.1	147.5	147.7	148.1	148.4
107.5°	181.6	182.3	182.9	183.6	184.2	184.5	184.5	184.5	184.5	184.5	184.7
110°	205.3	206.1	207.1	207.9	208.9	209.3	209.3	209.3	209.3	209.3	209.3



TEST NUMBER: P331721-935

CATALOG NUMBER: SA2XXRDIP-C865D725U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	231.1	232.0	232.9	233.8	234.7	235.1	235.0	234.9	234.7	234.6	234.3
115°	269.2	270.1	271.0	271.9	272.8	273.1	272.8	272.5	272.2	271.9	271.7
117.5°	307.1	308.3	309.5	310.7	311.9	312.1	311.3	310.5	309.6	308.8	308.4
120°	332.4	333.6	334.8	336.0	337.3	337.3	336.0	334.8	333.6	332.4	332.4
122.5°	355.6	357.1	358.5	359.9	361.4	361.6	360.8	360.0	359.1	358.3	357.9
125°	391.7	393.0	394.3	395.7	397.1	397.5	397.1	396.6	396.1	395.7	395.3
127.5°	426.8	428.5	430.2	432.0	433.6	434.2	433.7	433.2	432.6	432.0	431.5
130°	448.9	450.8	452.8	454.7	456.7	457.4	457.2	456.8	456.6	456.3	456.0
132.5°	473.6	475.3	476.8	478.4	480.0	480.8	480.9	481.0	481.0	481.0	480.4
135°	506.8	508.4	510.1	511.7	513.3	514.3	514.6	514.9	515.2	515.5	515.4
137.5°	541.7	542.9	544.3	545.7	547.0	547.9	548.3	548.6	549.1	549.4	549.3
140°	562.7	564.0	565.3	566.6	568.0	569.0	569.8	570.6	571.3	572.0	572.0
142.5°	584.2	585.5	586.9	588.2	589.5	590.5	591.0	591.5	592.0	592.5	592.6
145°	615.1	616.1	617.3	618.3	619.3	620.3	621.2	622.1	622.9	623.9	624.1
147.5°	642.7	643.9	645.2	646.4	647.7	648.7	649.3	649.9	650.5	651.1	651.3
150°	661.6	662.5	663.3	664.3	665.1	665.9	666.5	667.1	667.7	668.3	668.7
152.5°	678.2	679.2	680.0	681.0	681.8	682.6	683.4	684.1	684.8	685.5	686.0
155°	703.3	703.7	704.2	704.6	705.1	705.5	705.9	706.5	706.9	707.3	708.1
157.5°	724.7	725.0	725.3	725.6	725.9	726.2	726.4	726.7	726.9	727.2	728.2
160°	737.6	737.9	738.2	738.5	738.8	739.0	739.2	739.3	739.5	739.6	740.5
162.5°	749.4	749.5	749.6	749.6	749.7	749.8	749.9	750.1	750.3	750.4	751.4
165°	765.2	765.1	764.9	764.7	764.6	764.5	764.5	764.5	764.5	764.5	765.6
167.5°	778.3	777.9	777.5	777.1	776.6	776.4	776.4	776.3	776.3	776.2	777.3
170°	785.4	785.0	784.5	784.0	783.6	783.3	783.2	783.0	782.8	782.6	783.8
172.5°	790.2	789.8	789.4	788.8	788.4	788.2	788.0	787.8	787.7	787.6	788.6
175°	796.2	795.7	795.2	794.8	794.4	794.0	793.7	793.4	793.1	792.8	793.8
177.5°	798.6	798.2	797.9	797.5	797.1	796.9	796.6	796.3	796.1	795.9	796.6
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331721-935

CATALOG NUMBER: SA2XXRDIP-C865D725U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5
2.5°	1256.5	1258.5	1260.5	1261.4	1260.9	1260.5	1260.2	1259.7
5°	1246.5	1248.7	1251.0	1251.8	1251.0	1250.3	1249.5	1248.7
7.5°	1226.3	1226.9	1227.6	1227.3	1226.0	1224.7	1223.3	1222.0
10°	1206.1	1205.3	1204.5	1203.4	1201.9	1200.4	1198.9	1197.3
12.5°	1182.9	1181.6	1180.2	1178.3	1175.7	1173.2	1170.6	1168.1
15°	1139.7	1134.9	1130.1	1126.4	1123.9	1121.3	1118.8	1116.2
17.5°	1090.8	1085.0	1079.3	1074.3	1069.9	1065.6	1061.2	1056.8
20°	1056.7	1050.3	1044.0	1038.0	1032.4	1026.8	1021.2	1015.7
22.5°	1019.3	1011.1	1002.9	996.7	992.6	988.3	984.2	980.1
25°	957.2	946.8	936.3	929.2	925.4	921.6	917.8	914.0
27.5°	897.9	885.8	873.7	864.6	858.6	852.5	846.4	840.4
30°	856.1	843.2	830.2	820.3	813.5	806.6	799.8	792.9
32.5°	814.1	799.3	784.5	773.9	767.5	761.0	754.6	748.1
35°	748.3	732.4	716.4	705.6	700.0	694.4	688.8	683.2
37.5°	684.3	666.7	649.1	637.1	630.7	624.2	617.9	611.5
40°	641.4	623.5	605.4	593.1	586.5	579.9	573.3	566.7
42.5°	598.2	579.5	560.9	548.4	542.0	535.6	529.2	522.8
45°	535.2	517.2	499.1	487.1	481.0	474.9	468.8	462.7
47.5°	473.9	456.0	438.1	426.4	420.9	415.3	409.7	404.2
50°	434.5	417.0	399.5	388.1	382.7	377.4	372.0	366.7
52.5°	397.4	380.5	363.5	352.7	347.7	342.8	337.9	332.9
55°	340.9	325.6	310.4	300.3	295.5	290.7	285.9	281.0
57.5°	289.5	275.5	261.6	252.5	248.5	244.4	240.3	236.3
60°	254.0	241.1	228.1	219.6	215.5	211.5	207.4	203.4
62.5°	223.3	210.9	198.5	191.1	188.7	186.3	183.8	181.4
65°	181.5	172.9	164.3	159.5	158.8	158.1	157.3	156.5
67.5°	146.5	142.6	138.6	136.2	135.4	134.6	133.8	133.0
70°	127.4	124.9	122.3	120.6	119.6	118.6	117.5	116.5
72.5°	110.9	108.7	106.6	105.3	104.6	104.0	103.4	102.8
75°	87.8	86.1	84.3	83.3	83.0	82.7	82.5	82.2
77.5°	66.6	65.5	64.5	63.8	63.4	62.9	62.6	62.2
80°	52.8	51.8	50.8	50.3	50.3	50.3	50.3	50.3
82.5°	40.0	39.3	38.7	38.4	38.4	38.4	38.4	38.4
85°	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7
87.5°	11.5	11.2	10.9	10.8	10.8	10.9	10.9	10.9
90°	23.0	22.6	22.4	22.3	22.5	22.6	22.7	22.9
92.5°	21.5	21.6	21.6	21.7	21.7	21.8	21.8	21.8
95°	43.0	43.0	43.0	43.0	42.6	42.4	42.0	41.8
97.5°	72.4	72.4	72.4	72.4	72.4	72.3	72.3	72.2
100°	92.9	92.9	92.9	92.8	92.6	92.5	92.4	92.2
102.5°	115.2	115.3	115.5	115.4	115.3	115.1	114.9	114.8
105°	148.7	149.0	149.3	149.4	149.4	149.4	149.4	149.4
107.5°	184.8	184.9	185.0	184.8	184.1	183.4	182.7	182.0
110°	209.3	209.3	209.3	209.1	208.6	208.2	207.8	207.2





TEST NUMBER: P331721-935

CATALOG NUMBER: SA2XXRDIP-C865D725U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	233.8	233.5	233.2	232.8	232.5	232.1	231.9	231.5
115°	271.6	271.5	271.3	271.0	270.5	270.1	269.7	269.2
117.5°	308.1	307.7	307.3	306.9	306.5	306.0	305.6	305.1
120°	332.4	332.4	332.4	332.3	331.7	331.3	330.9	330.5
122.5°	357.6	357.2	356.9	356.5	356.2	355.9	355.5	355.2
125°	394.9	394.3	393.9	393.6	393.5	393.3	393.2	393.0
127.5°	431.0	430.4	429.9	429.4	429.0	428.4	428.0	427.5
130°	455.7	455.4	455.1	454.6	454.0	453.5	452.9	452.3
132.5°	479.7	479.1	478.5	477.9	477.3	476.9	476.4	476.0
135°	515.2	515.1	514.9	514.6	514.2	513.8	513.2	512.8
137.5°	549.2	549.1	549.0	548.6	548.0	547.4	546.8	546.2
140°	572.0	572.0	572.0	571.7	571.2	570.6	570.0	569.4
142.5°	592.7	592.9	593.0	592.7	592.1	591.5	591.0	590.4
145°	624.1	624.3	624.5	624.2	623.6	623.0	622.4	621.8
147.5°	651.7	652.0	652.4	652.3	651.7	651.1	650.6	650.0
150°	669.2	669.6	670.1	670.1	669.6	669.2	668.7	668.3
152.5°	686.6	687.3	687.8	687.8	687.3	686.6	686.0	685.5
155°	708.8	709.6	710.3	710.5	710.0	709.6	709.1	708.7
157.5°	729.3	730.3	731.3	731.4	730.7	730.0	729.3	728.6
160°	741.4	742.4	743.2	743.4	742.8	742.2	741.6	741.0
162.5°	752.4	753.5	754.5	754.6	753.9	753.2	752.4	751.7
165°	766.6	767.7	768.7	768.9	768.1	767.3	766.6	765.9
167.5°	778.3	779.4	780.4	780.6	779.8	779.0	778.3	777.5
170°	784.8	785.8	786.9	787.0	786.1	785.1	784.3	783.3
172.5°	789.6	790.7	791.7	791.8	790.9	790.0	789.1	788.2
175°	794.9	795.9	796.9	797.0	796.2	795.2	794.4	793.5
177.5°	797.3	798.1	798.7	798.7	798.1	797.3	796.6	795.9
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5

(END OF REPORT)