

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331728-935

Luminaire Tested: **SA2XXRDIP-C865D925U935-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331728-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D925U935-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5710.0 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331728-935
CATALOG NUMBER: SA2XXRDIP-C865D925U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331728-935

CATALOG NUMBER: SA2XXRDIP-C865D925U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46
1	97	93	89	86	89	86	82	80	71	69	67	59	57	56	47	46	45	39
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	42	40	38	34
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29	25
5	69	57	50	44	63	53	46	41	45	40	36	37	34	31	30	28	25	22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	25	23	20	18
8	54	42	35	30	50	40	33	28	34	29	25	28	24	22	23	21	18	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17	14
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20384	20384	20384
5°	20462	20128	20238
10°	20305	19799	19630
15°	20072	19211	18658
20°	19747	18374	17452
25°	19417	17423	16283
30°	18957	16444	14783
35°	18510	15380	13466
40°	18061	14280	11944
45°	17532	13045	10565
50°	16990	11796	9211
55°	16434	10452	7910
60°	15791	9038	6568
65°	15060	7595	5979
70°	14186	6255	5500
75°	13119	5702	5128
80°	11576	5095	4677
85°	9114	4020	4020



TEST NUMBER: P331728-935

CATALOG NUMBER: SA2XXRDIP-C865D925U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.2	2.1
10°-20°	324.5	5.7
20°-30°	455.6	8.0
30°-40°	496.8	8.7
40°-50°	456.8	8.0
50°-60°	358.8	6.3
60°-70°	233.9	4.1
70°-80°	120.6	2.1
80°-90°	35.3	0.6
90°-100°	178.7	3.1
100°-110°	606.3	10.6
110°-120°	644.1	11.3
120°-130°	530.2	9.3
130°-140°	425.8	7.5
140°-150°	321.8	5.6
150°-160°	226.1	4.0
160°-170°	133.1	2.3
170°-180°	43.3	0.8
0°-30°	898.3	15.7
0°-40°	1395.1	24.4
0°-60°	2210.7	38.7
0°-90°	2600.6	45.5
90°-120°	1429.1	25.0
90°-150°	2706.8	47.4
90°-180°	3109.0	54.4
0°-180°	5710.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1262	1262	1262	1262	1262	
5°	1262	1256	1242	1251	1249	120
15°	1201	1187	1149	1128	1116	338
25°	1090	1051	978	933	914	501
35°	939	878	780	711	683	587
45°	768	689	571	493	463	593
55°	584	493	371	305	281	521
65°	394	301	199	162	156	391
75°	210	133	91	84	82	223
85°	49	26	22	22	22	58
90°	1	12	29	28	28	4
95°	30	74	337	127	98	32
105°	105	158	637	1138	968	111
115°	185	233	533	1100	1274	183
125°	258	305	512	891	1034	229
135°	302	361	506	748	857	234
145°	345	397	504	625	684	217
155°	393	424	489	553	575	181
165°	428	441	468	497	504	121
175°	446	446	450	456	455	42
180°	447	447	447	447	447	



TEST NUMBER: P331728-935

CATALOG NUMBER: SA2XXRDIP-C865D925U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5
2.5°	1267.0	1266.0	1265.0	1263.9	1263.0	1261.4	1259.1	1256.9	1254.6	1252.4	1254.5
5°	1262.5	1261.2	1259.9	1258.6	1257.4	1255.1	1251.8	1248.5	1245.2	1241.9	1244.1
7.5°	1249.4	1247.8	1246.3	1244.7	1243.1	1240.4	1236.6	1232.7	1228.8	1224.9	1225.6
10°	1238.5	1236.7	1234.9	1233.1	1231.3	1228.0	1222.9	1217.8	1212.7	1207.6	1206.9
12.5°	1224.8	1222.5	1220.4	1218.2	1216.0	1211.7	1205.1	1198.7	1192.1	1185.7	1184.3
15°	1200.8	1198.0	1195.2	1192.4	1189.6	1183.9	1175.3	1166.7	1158.0	1149.3	1144.5
17.5°	1171.3	1167.0	1162.8	1158.5	1154.3	1146.6	1135.5	1124.4	1113.4	1102.3	1096.6
20°	1149.3	1144.3	1139.2	1134.1	1129.0	1120.2	1107.4	1094.8	1082.1	1069.4	1063.0
22.5°	1125.6	1119.9	1114.2	1108.5	1102.9	1092.9	1078.5	1064.2	1049.9	1035.5	1027.3
25°	1089.9	1081.8	1073.7	1065.6	1057.5	1045.0	1028.2	1011.5	994.7	978.0	967.6
27.5°	1047.0	1038.1	1029.3	1020.5	1011.7	997.8	978.9	960.0	941.1	922.2	910.1
30°	1016.8	1007.2	997.6	987.9	978.3	963.3	943.0	922.6	902.3	882.0	869.1
32.5°	987.6	976.3	965.0	953.7	942.5	926.5	905.8	885.0	864.4	843.6	828.9
35°	939.1	926.2	913.3	900.3	887.3	869.7	847.3	825.0	802.7	780.3	764.3
37.5°	890.7	876.5	862.3	848.0	833.8	814.8	791.0	767.2	743.4	719.5	701.9
40°	856.9	841.6	826.4	811.1	795.9	776.0	751.4	726.8	702.1	677.5	659.4
42.5°	822.2	806.1	790.1	774.0	757.9	737.2	711.8	686.3	660.9	635.4	616.8
45°	767.8	750.7	733.7	716.7	699.7	677.9	651.3	624.6	597.9	571.3	553.2
47.5°	714.7	696.7	678.7	660.6	642.7	619.8	592.4	564.8	537.3	509.8	491.9
50°	676.4	658.3	640.3	622.2	604.2	581.3	553.4	525.4	497.5	469.6	452.0
52.5°	638.9	620.0	601.2	582.4	563.5	540.4	513.2	485.8	458.5	431.2	414.2
55°	583.8	564.0	544.2	524.4	504.6	481.0	453.6	426.1	398.7	371.3	356.1
57.5°	527.4	507.0	486.7	466.4	446.2	422.8	396.4	370.1	343.7	317.4	303.4
60°	489.0	468.6	448.4	428.1	407.8	384.5	358.3	332.2	306.1	279.9	267.0
62.5°	451.5	431.2	410.9	390.5	370.2	347.7	322.7	297.8	272.9	247.9	235.6
65°	394.2	373.6	353.0	332.4	311.9	290.2	267.3	244.5	221.6	198.8	190.2
67.5°	338.9	318.5	298.1	277.6	257.2	236.7	216.2	195.6	175.0	154.5	150.5
70°	300.5	280.7	260.9	241.1	221.3	202.6	185.1	167.6	150.1	132.5	130.0
72.5°	263.9	245.0	225.9	207.0	188.0	171.4	157.4	143.3	129.2	115.2	113.0
75°	210.3	192.4	174.7	156.9	139.1	126.0	117.3	108.7	100.0	91.4	89.6
77.5°	157.5	141.8	126.2	110.6	95.1	85.2	81.0	76.9	72.8	68.5	67.5
80°	124.5	111.6	98.7	85.7	72.8	65.0	62.4	59.9	57.3	54.8	53.8
82.5°	94.4	84.3	74.1	64.1	54.0	48.0	46.3	44.6	42.9	41.2	40.6
85°	49.2	43.8	38.5	33.1	27.8	24.8	24.0	23.2	22.5	21.7	21.7
87.5°	14.8	13.7	12.7	11.5	10.2	9.9	10.8	12.0	13.0	13.2	12.7
90°	0.9	3.4	6.9	8.6	10.3	12.9	17.2	23.2	28.3	29.2	28.3
92.5°	10.5	15.2	21.4	25.1	30.9	39.0	58.5	85.8	110.1	111.7	94.4
95°	30.0	33.5	42.1	49.9	63.6	84.2	123.7	198.5	298.2	336.8	294.7
97.5°	49.0	53.6	62.8	74.4	90.2	113.6	163.2	267.4	433.1	575.1	603.2
100°	66.1	68.7	76.5	90.2	107.5	131.5	177.0	281.9	467.4	678.8	802.6
102.5°	82.0	83.9	91.6	105.4	123.2	147.3	189.4	282.6	454.4	682.3	876.8
105°	104.9	108.3	114.3	127.2	146.1	170.1	210.5	287.0	428.8	636.7	865.3
107.5°	129.6	132.3	138.2	150.1	168.8	193.0	232.2	298.9	416.0	588.0	789.9
110°	146.1	149.6	154.6	165.8	183.9	208.8	246.6	308.5	413.4	564.6	742.4



TEST NUMBER: P331728-935

CATALOG NUMBER: SA2XXRDIP-C865D925U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	161.2	164.6	170.5	181.0	198.3	223.9	260.4	318.8	414.0	549.4	709.5
115°	184.8	189.1	194.2	204.5	221.7	244.9	281.9	334.2	417.6	532.8	668.6
117.5°	209.1	212.6	217.7	226.9	243.3	267.4	301.6	350.8	423.8	524.7	642.7
120°	224.3	227.7	232.9	240.6	257.8	281.9	315.4	361.8	427.9	519.9	629.0
122.5°	238.8	241.4	246.6	255.0	272.2	297.0	328.4	371.3	432.7	517.1	617.3
125°	257.8	260.4	265.5	275.9	293.0	317.1	348.0	386.7	440.0	512.1	600.6
127.5°	272.9	276.4	283.5	294.9	311.4	336.1	366.3	401.0	447.4	509.2	585.2
130°	281.9	285.2	293.9	305.9	323.1	347.2	377.2	409.9	452.9	507.8	574.9
132.5°	290.1	294.2	303.5	316.2	334.1	358.2	386.8	418.8	458.3	507.1	566.6
135°	302.5	305.9	316.2	329.1	348.9	372.9	400.5	430.5	464.9	506.1	555.1
137.5°	314.2	318.3	328.6	342.3	362.0	384.3	411.5	439.5	470.7	505.9	547.0
140°	323.1	326.6	336.8	350.6	369.5	391.8	417.6	444.3	473.5	505.2	542.3
142.5°	332.0	334.8	344.4	358.2	376.3	397.4	422.4	448.4	475.5	505.2	537.4
145°	345.4	348.9	357.5	370.4	387.5	406.5	429.6	453.7	477.8	503.5	531.1
147.5°	359.9	362.5	370.7	382.5	396.8	413.7	435.5	456.7	478.5	500.5	524.5
150°	369.5	372.0	378.9	390.1	403.0	418.4	438.2	458.0	477.8	498.4	519.0
152.5°	379.1	380.3	387.2	397.0	409.2	423.3	441.0	458.7	476.4	495.0	514.2
155°	392.7	393.6	398.7	408.2	417.6	430.5	445.1	459.7	474.3	489.0	505.2
157.5°	404.1	404.9	409.1	417.2	424.8	435.7	448.1	459.7	470.4	482.8	496.9
160°	411.6	412.5	415.9	422.8	429.6	439.1	449.4	459.7	468.3	478.6	490.7
162.5°	419.1	418.6	422.1	427.6	433.8	441.2	450.1	459.0	466.2	475.2	485.2
165°	427.9	427.1	428.8	433.9	438.2	443.4	451.2	457.2	462.3	468.3	476.0
167.5°	435.1	434.1	435.7	438.9	442.0	445.3	451.0	456.0	458.3	462.3	467.1
170°	440.0	438.2	439.1	441.7	443.4	446.0	450.3	454.6	456.3	458.8	462.3
172.5°	442.7	441.7	441.2	443.8	444.8	446.7	449.6	452.5	453.6	454.8	457.5
175°	446.0	445.1	444.3	446.0	446.0	446.9	448.6	450.3	449.4	450.3	451.2
177.5°	447.5	446.2	445.5	446.9	446.9	446.9	447.5	448.9	447.5	446.9	447.5
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331728-935

CATALOG NUMBER: SA2XXRDIP-C865D925U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5
2.5°	1256.5	1258.5	1260.5	1261.4	1260.9	1260.5	1260.2	1259.7
5°	1246.5	1248.7	1251.0	1251.8	1251.0	1250.3	1249.5	1248.7
7.5°	1226.3	1226.9	1227.6	1227.3	1226.0	1224.7	1223.3	1222.0
10°	1206.1	1205.3	1204.5	1203.4	1201.9	1200.4	1198.9	1197.3
12.5°	1182.9	1181.6	1180.2	1178.3	1175.7	1173.2	1170.6	1168.1
15°	1139.7	1134.9	1130.1	1126.4	1123.9	1121.3	1118.8	1116.2
17.5°	1090.8	1085.0	1079.3	1074.3	1069.9	1065.6	1061.2	1056.8
20°	1056.7	1050.3	1044.0	1038.0	1032.4	1026.8	1021.2	1015.7
22.5°	1019.3	1011.1	1002.9	996.7	992.6	988.3	984.2	980.1
25°	957.2	946.8	936.3	929.2	925.4	921.6	917.8	914.0
27.5°	897.9	885.8	873.7	864.6	858.6	852.5	846.4	840.4
30°	856.1	843.2	830.2	820.3	813.5	806.6	799.8	792.9
32.5°	814.1	799.3	784.5	773.9	767.5	761.0	754.6	748.1
35°	748.3	732.4	716.4	705.6	700.0	694.4	688.8	683.2
37.5°	684.3	666.7	649.1	637.1	630.7	624.2	617.9	611.5
40°	641.4	623.5	605.4	593.1	586.5	579.9	573.3	566.7
42.5°	598.2	579.5	560.9	548.4	542.0	535.6	529.2	522.8
45°	535.2	517.2	499.1	487.1	481.0	474.9	468.8	462.7
47.5°	473.9	456.0	438.1	426.4	420.9	415.3	409.7	404.2
50°	434.5	417.0	399.5	388.1	382.7	377.4	372.0	366.7
52.5°	397.4	380.5	363.5	352.7	347.7	342.8	337.9	332.9
55°	340.9	325.6	310.4	300.3	295.5	290.7	285.9	281.0
57.5°	289.5	275.5	261.6	252.5	248.5	244.4	240.3	236.3
60°	254.0	241.1	228.1	219.6	215.5	211.5	207.4	203.4
62.5°	223.3	210.9	198.5	191.1	188.7	186.3	183.8	181.4
65°	181.5	172.9	164.3	159.5	158.8	158.1	157.3	156.5
67.5°	146.5	142.6	138.6	136.2	135.4	134.6	133.8	133.0
70°	127.4	124.9	122.3	120.6	119.6	118.6	117.5	116.5
72.5°	110.9	108.7	106.6	105.3	104.6	104.0	103.4	102.8
75°	87.8	86.1	84.3	83.3	83.0	82.7	82.5	82.2
77.5°	66.6	65.5	64.5	63.8	63.4	62.9	62.6	62.2
80°	52.8	51.8	50.8	50.3	50.3	50.3	50.3	50.3
82.5°	40.0	39.3	38.7	38.4	38.4	38.4	38.4	38.4
85°	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7
87.5°	12.4	11.9	12.0	12.1	12.1	12.1	12.1	12.1
90°	27.5	25.7	27.5	28.3	28.3	28.3	28.3	28.3
92.5°	74.9	64.3	57.1	51.7	51.1	48.3	49.0	47.6
95°	225.2	172.7	136.6	117.7	106.6	99.7	97.1	98.0
97.5°	525.4	429.8	336.8	274.8	233.8	212.6	200.0	192.9
100°	784.5	678.0	560.3	456.3	385.0	348.0	323.1	307.6
102.5°	954.3	930.3	844.2	734.0	656.5	593.4	562.3	541.4
105°	1044.0	1141.2	1152.4	1123.9	1070.7	1017.4	980.4	968.5
107.5°	979.5	1125.7	1215.0	1256.6	1263.3	1260.4	1253.0	1237.1
110°	923.8	1077.5	1187.6	1258.0	1294.9	1311.3	1319.1	1318.2



TEST NUMBER: P331728-935

CATALOG NUMBER: SA2XXRDIP-C865D925U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	872.9	1020.5	1138.1	1218.8	1270.2	1297.5	1312.2	1316.8
115°	810.3	942.6	1055.2	1143.8	1204.7	1244.2	1266.6	1274.4
117.5°	763.2	879.4	981.5	1064.5	1126.7	1168.5	1192.1	1198.5
120°	739.9	846.4	937.5	1015.7	1075.8	1116.2	1141.2	1149.8
122.5°	721.3	818.9	905.2	975.9	1029.8	1069.4	1091.7	1098.9
125°	694.3	782.8	858.4	922.9	972.8	1005.4	1026.8	1033.7
127.5°	667.7	747.8	819.1	878.6	922.0	952.6	971.2	976.7
130°	650.5	724.4	792.3	849.0	891.1	920.3	937.5	944.3
132.5°	634.0	702.4	764.7	818.0	859.5	888.7	904.5	910.7
135°	611.0	667.7	724.4	772.5	809.4	837.8	853.3	856.7
137.5°	592.5	640.0	685.0	726.9	760.7	785.1	798.7	803.8
140°	580.9	622.2	661.7	699.5	726.9	749.3	762.2	767.3
142.5°	571.3	606.3	640.3	672.0	698.1	718.4	729.9	730.9
145°	557.7	586.1	612.7	637.6	658.2	672.9	681.4	684.0
147.5°	547.2	569.6	590.3	608.6	625.6	637.2	643.1	644.6
150°	539.7	558.5	576.6	592.0	604.9	615.3	620.4	621.3
152.5°	532.1	549.6	564.9	578.3	588.4	597.4	601.2	601.3
155°	521.6	535.4	548.2	557.7	567.1	573.2	576.6	574.9
157.5°	509.4	520.9	531.8	539.2	545.8	550.8	552.3	552.3
160°	501.8	511.3	520.7	526.8	532.8	537.1	538.0	538.0
162.5°	494.3	502.3	510.4	515.1	521.1	524.0	524.9	524.2
165°	482.9	489.0	495.0	498.4	501.8	505.2	505.2	504.4
167.5°	472.1	476.7	480.9	484.0	485.5	487.4	487.2	486.2
170°	466.6	469.2	472.6	474.3	475.2	477.8	476.9	475.2
172.5°	460.4	462.3	465.0	466.1	466.9	468.1	467.3	466.2
175°	453.7	454.6	455.5	456.3	456.3	457.2	456.3	454.6
177.5°	448.9	448.9	449.6	449.6	449.6	449.6	448.9	447.5
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9

(END OF REPORT)