

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331458-840

Luminaire Tested: **SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331458-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8693.1 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331458-840

CATALOG NUMBER: SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331458-840

CATALOG NUMBER: SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42	38
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	39	36	33
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	58	51	45	64	54	47	42	47	42	37	40	36	33	34	31	28	25
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	31	27	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	31	26	23	26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	32513	32513	32513	32513
5°	36451	32725	29000	32725
10°	41769	32455	25097	32455
15°	46208	31861	22173	31861
20°	45505	31223	20213	31223
25°	41031	30375	18971	30375
30°	33907	29015	18066	29015
35°	24711	27595	17420	27595
40°	19736	25918	17062	25918
45°	17249	23980	16575	23980
50°	16211	22102	16252	22102
55°	14945	20194	15817	20194
60°	13695	18167	15145	18167
65°	12478	16351	14487	16351
70°	11325	14578	13520	14578
75°	10044	12601	11977	12601
80°	8638	10432	9642	10432
85°	7744	7744	5743	7744



TEST NUMBER: P331458-840

CATALOG NUMBER: SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.8	2.2
10°-20°	557.5	6.4
20°-30°	809.1	9.3
30°-40°	853.9	9.8
40°-50°	756.0	8.7
50°-60°	603.3	6.9
60°-70°	410.1	4.7
70°-80°	210.2	2.4
80°-90°	56.2	0.6
90°-100°	243.9	2.8
100°-110°	827.7	9.5
110°-120°	879.3	10.1
120°-130°	723.9	8.3
130°-140°	581.3	6.7
140°-150°	439.3	5.1
150°-160°	308.7	3.6
160°-170°	181.7	2.1
170°-180°	59.1	0.7
0°-30°	1558.5	17.9
0°-40°	2412.3	27.7
0°-60°	3771.7	43.4
0°-90°	4448.1	51.2
90°-120°	1951.0	22.4
90°-150°	3695.4	42.5
90°-180°	4245.0	48.8
0°-180°	8693.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2014	2014	2014	2014	2014	
5°	2249	2019	1789	2019	2249	225
15°	2764	1906	1326	1906	2764	763
25°	2303	1705	1065	1705	2303	1041
35°	1254	1400	884	1400	1254	815
45°	755	1050	726	1050	755	594
55°	531	717	562	717	531	476
65°	327	428	379	428	327	325
75°	161	202	192	202	161	172
85°	42	42	31	42	42	47
90°	39	1	39	1	39	23
95°	134	41	134	41	134	174
105°	1322	143	1322	143	1322	1279
115°	1740	252	1740	252	1740	1704
125°	1411	352	1411	352	1411	1275
135°	1170	413	1170	413	1170	909
145°	934	472	934	472	934	593
155°	785	536	785	536	785	366
165°	689	584	689	584	689	197
175°	621	609	621	609	621	60
180°	610	610	610	610	610	



TEST NUMBER: P331458-840

CATALOG NUMBER: SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2106.6	2107.2	2108.4	2098.5	2097.3	2097.3	2088.6	2081.2	2072.5	2060.7	2062.0
5°	2249.0	2257.5	2260.6	2251.3	2237.4	2235.8	2222.7	2201.0	2180.9	2164.6	2153.0
7.5°	2418.9	2422.4	2414.8	2402.6	2392.2	2373.6	2349.1	2325.1	2291.6	2260.8	2237.9
10°	2547.7	2552.3	2539.2	2521.4	2506.7	2485.1	2449.4	2413.1	2368.9	2326.4	2292.3
12.5°	2645.5	2657.0	2640.1	2637.8	2612.6	2582.8	2540.4	2522.0	2459.9	2400.7	2364.2
15°	2764.4	2763.6	2765.2	2750.5	2731.9	2727.2	2682.4	2633.6	2546.2	2511.3	2450.9
17.5°	2730.1	2741.8	2747.2	2747.0	2746.6	2743.7	2729.3	2698.5	2654.6	2598.2	2528.5
20°	2648.4	2663.8	2666.1	2683.9	2694.0	2707.1	2712.6	2704.0	2677.0	2629.8	2569.4
22.5°	2522.0	2526.4	2533.7	2561.3	2583.1	2616.2	2633.3	2661.9	2651.6	2628.5	2578.1
25°	2303.2	2295.4	2322.5	2336.4	2386.7	2439.3	2477.3	2519.1	2556.3	2578.7	2563.9
27.5°	2040.3	2028.7	2069.3	2106.3	2147.2	2204.1	2263.2	2333.0	2391.1	2463.7	2488.6
30°	1818.7	1825.6	1864.3	1903.8	1965.7	2046.2	2112.7	2189.4	2272.2	2353.5	2409.9
32.5°	1579.7	1606.5	1630.9	1691.4	1746.0	1835.7	1933.2	2029.0	2132.3	2224.7	2312.2
35°	1253.7	1284.6	1318.8	1362.8	1439.5	1528.4	1623.7	1752.9	1893.8	2019.9	2123.6
37.5°	1055.3	1050.4	1069.9	1101.8	1163.8	1235.7	1345.2	1472.9	1638.7	1787.0	1933.2
40°	936.4	933.3	947.3	976.6	1023.9	1076.5	1172.5	1284.6	1438.7	1619.8	1793.9
42.5°	854.7	856.6	864.3	885.0	917.4	960.7	1032.6	1128.0	1269.1	1439.7	1626.8
45°	755.4	760.7	769.3	779.3	797.9	833.5	873.7	941.9	1053.3	1195.7	1379.9
47.5°	683.8	684.0	692.7	701.5	712.5	732.6	765.4	808.1	886.8	1002.7	1161.0
50°	645.4	640.1	646.2	653.2	664.8	678.7	700.3	740.6	793.2	886.9	1019.3
52.5°	598.3	598.5	604.1	606.7	617.1	631.1	650.9	678.7	726.4	799.6	908.4
55°	530.9	534.7	537.9	542.5	551.8	561.9	577.3	595.9	633.1	688.0	768.5
57.5°	467.5	468.7	471.8	480.6	486.5	495.7	510.5	527.4	551.5	592.2	652.7
60°	424.1	424.1	430.3	434.1	441.9	451.2	462.8	479.1	500.7	534.0	582.8
62.5°	384.5	383.8	386.4	392.6	398.6	407.3	418.8	432.6	453.0	482.6	522.7
65°	326.6	325.1	329.7	331.2	337.4	346.0	355.3	369.9	386.2	407.9	443.4
67.5°	270.8	272.8	275.2	278.1	281.6	290.5	296.7	307.1	320.8	338.8	362.9
70°	239.9	239.9	239.9	242.3	246.9	251.6	257.7	266.2	279.4	294.9	316.5
72.5°	205.2	207.7	210.2	208.8	214.7	217.4	224.9	229.7	242.3	252.2	271.4
75°	161.0	161.0	161.0	164.8	167.1	169.5	174.1	178.7	185.0	197.3	207.4
77.5°	120.1	119.8	120.6	121.5	124.0	126.7	128.2	132.3	138.0	143.8	152.3
80°	92.9	94.4	95.2	96.7	96.7	98.3	99.1	104.5	108.4	112.2	117.6
82.5°	71.8	72.1	72.3	72.6	73.2	74.1	76.1	77.9	79.3	82.5	86.6
85°	41.8	41.0	41.0	42.5	41.8	41.8	43.3	44.8	44.8	45.6	48.0
87.5°	23.8	23.8	24.4	23.8	23.8	24.2	23.7	23.6	24.4	25.3	25.7
90°	38.7	38.7	38.7	38.7	38.7	37.6	35.2	37.6	38.7	39.9	38.7
92.5°	65.0	66.9	65.9	69.7	70.6	77.9	87.8	102.3	128.9	152.5	150.4
95°	133.7	132.6	136.1	145.4	160.7	186.5	235.8	307.4	402.4	459.9	407.1
97.5°	263.3	273.1	290.2	319.1	375.2	459.9	586.8	717.2	823.5	785.1	591.3
100°	420.0	441.1	475.1	525.5	622.9	764.9	925.6	1071.1	1095.7	926.8	638.1
102.5°	739.1	767.7	810.2	896.3	1002.1	1152.5	1270.0	1302.9	1197.1	931.5	620.4
105°	1322.1	1338.6	1389.0	1461.7	1534.5	1573.2	1557.9	1425.3	1181.3	869.3	585.4
107.5°	1688.8	1710.6	1720.7	1724.7	1715.6	1658.8	1536.8	1337.2	1078.3	802.6	568.0
110°	1799.6	1800.8	1790.2	1767.9	1717.5	1621.2	1471.1	1261.1	1013.6	770.7	564.3



TEST NUMBER: P331458-840

CATALOG NUMBER: SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1797.7	1791.4	1771.4	1734.1	1664.0	1553.7	1393.2	1191.6	968.6	750.1	565.2
115°	1739.8	1729.2	1698.7	1644.8	1561.5	1440.6	1287.0	1106.3	912.7	727.3	570.2
117.5°	1636.3	1627.4	1595.2	1538.2	1453.3	1340.0	1200.6	1042.0	877.5	716.3	578.6
120°	1569.6	1557.9	1523.9	1468.7	1386.6	1279.9	1155.5	1010.1	858.7	709.7	584.2
122.5°	1500.2	1490.4	1460.1	1405.8	1332.2	1235.8	1118.0	984.7	842.7	706.0	590.8
125°	1411.3	1401.9	1372.6	1328.0	1259.9	1171.9	1068.7	947.9	820.0	699.2	600.7
127.5°	1333.4	1325.9	1300.5	1258.8	1199.4	1118.2	1020.9	911.5	798.9	695.2	610.8
130°	1289.3	1279.9	1256.5	1216.6	1159.0	1081.7	989.0	888.1	784.9	693.3	618.2
132.5°	1243.2	1234.9	1213.3	1173.4	1116.8	1044.1	959.0	865.6	773.6	692.4	625.7
135°	1169.6	1164.9	1143.8	1105.1	1054.6	989.0	911.5	834.0	757.8	690.9	634.7
137.5°	1097.3	1090.4	1071.8	1038.4	992.5	935.2	873.7	809.0	746.8	690.7	642.7
140°	1047.6	1040.6	1023.0	992.5	954.9	903.3	849.4	793.0	740.2	689.8	646.4
142.5°	997.8	996.4	980.8	953.0	917.4	874.2	827.8	779.9	733.7	689.8	649.2
145°	933.8	930.3	918.6	898.6	870.5	836.5	800.1	761.3	725.0	687.4	652.3
147.5°	880.1	878.0	870.0	854.0	830.8	806.0	777.6	747.1	716.1	683.3	653.2
150°	848.2	847.0	840.0	825.9	808.3	787.2	762.5	736.7	708.5	680.4	652.3
152.5°	820.9	820.7	815.6	803.3	789.5	771.2	750.3	726.4	702.0	675.7	650.4
155°	784.9	787.2	782.4	774.3	761.3	748.4	730.8	712.1	689.8	667.5	647.5
157.5°	754.1	754.1	751.9	745.2	736.0	725.9	711.1	695.4	678.3	659.0	642.2
160°	734.4	734.4	733.2	727.3	719.1	710.9	698.0	685.1	669.8	653.5	639.3
162.5°	715.6	716.5	715.4	711.3	703.2	696.8	685.8	674.8	662.4	648.7	636.5
165°	688.6	689.8	689.8	685.1	680.4	675.7	667.5	659.3	649.9	639.3	631.2
167.5°	663.8	665.2	665.4	662.8	660.8	656.5	650.9	644.5	637.7	631.2	625.7
170°	648.7	651.1	652.3	648.7	647.5	645.2	640.6	637.0	631.2	626.4	622.9
172.5°	636.5	637.9	639.1	637.5	636.3	634.9	631.2	628.5	624.6	620.9	619.1
175°	620.6	622.9	624.1	622.9	622.9	621.8	620.6	619.5	615.9	614.7	613.6
177.5°	611.0	612.9	613.8	613.8	613.8	613.8	612.9	612.9	611.0	610.1	611.0
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1



TEST NUMBER: P331458-840

CATALOG NUMBER: SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2066.4	2061.4	2058.3	2047.2	2037.2	2027.3	2024.3	2025.5	2011.9	1998.8	1993.3
5°	2146.9	2131.3	2116.7	2095.8	2071.0	2043.9	2029.9	2019.1	1992.1	1962.7	1945.6
7.5°	2219.0	2196.9	2168.5	2129.2	2093.1	2050.5	2023.5	1999.4	1959.8	1918.3	1893.0
10°	2262.9	2232.7	2196.4	2148.4	2104.3	2052.4	2016.0	1979.6	1933.2	1883.7	1852.7
12.5°	2300.7	2260.0	2224.2	2162.6	2110.4	2045.6	2002.5	1951.2	1902.3	1843.4	1813.1
15°	2390.7	2315.5	2247.5	2177.8	2113.5	2023.0	1975.0	1906.1	1841.9	1769.2	1734.3
17.5°	2460.1	2375.7	2268.5	2180.0	2105.1	2004.8	1934.3	1851.8	1775.8	1692.7	1645.4
20°	2499.7	2403.0	2287.6	2182.4	2092.6	1978.1	1901.5	1817.2	1728.2	1634.5	1583.5
22.5°	2523.2	2421.6	2307.5	2173.1	2067.9	1956.4	1860.0	1767.6	1677.4	1576.3	1522.8
25°	2530.7	2437.8	2317.1	2165.5	2036.9	1910.8	1794.7	1705.0	1595.8	1501.4	1423.2
27.5°	2493.9	2427.3	2311.2	2150.8	2001.1	1853.7	1724.2	1622.6	1507.4	1404.9	1326.4
30°	2448.6	2409.9	2296.9	2136.0	1972.7	1814.0	1671.6	1556.3	1441.8	1338.1	1257.6
32.5°	2378.7	2370.4	2271.0	2115.0	1942.4	1763.9	1616.6	1500.0	1373.1	1271.2	1194.5
35°	2241.3	2278.4	2215.7	2067.9	1885.2	1692.5	1533.1	1400.0	1268.5	1170.9	1098.9
37.5°	2057.1	2149.3	2132.9	1999.0	1808.2	1614.9	1438.9	1299.7	1174.4	1075.9	1005.3
40°	1930.2	2047.8	2064.8	1946.4	1753.7	1554.8	1368.3	1229.7	1107.4	1017.7	946.4
42.5°	1793.9	1931.4	1978.1	1883.2	1694.3	1491.7	1305.1	1161.6	1040.6	953.3	890.2
45°	1565.6	1747.5	1831.9	1777.7	1595.1	1387.7	1195.7	1050.2	940.3	858.3	809.5
47.5°	1352.2	1551.0	1664.4	1645.2	1484.7	1279.3	1089.5	949.9	842.9	777.5	733.9
50°	1201.1	1405.4	1542.4	1548.6	1405.4	1201.8	1011.5	879.9	781.6	720.5	684.9
52.5°	1069.9	1264.9	1414.2	1447.0	1316.9	1121.4	941.5	810.6	724.1	667.9	636.0
55°	898.5	1063.4	1229.0	1289.3	1184.9	999.2	832.7	717.4	636.1	597.4	569.6
57.5°	747.0	884.4	1037.3	1104.1	1039.7	880.7	724.7	624.5	558.7	524.7	503.3
60°	667.1	775.5	911.7	991.4	935.6	794.1	657.8	562.6	508.5	478.3	458.2
62.5°	592.8	688.8	804.0	876.9	846.5	713.0	591.0	507.0	460.2	431.8	417.3
65°	489.1	564.9	654.0	721.2	701.1	599.8	500.0	428.0	390.8	368.4	356.8
67.5°	402.7	457.6	519.3	578.2	562.0	490.2	410.0	354.0	326.3	306.9	299.9
70°	348.3	390.0	445.0	492.2	479.1	420.2	356.8	308.8	284.8	268.5	261.6
72.5°	296.3	330.6	372.5	411.1	402.2	353.4	300.4	264.2	245.8	230.8	225.1
75°	223.7	249.9	275.5	301.0	298.7	260.8	229.8	202.0	187.3	175.7	173.4
77.5°	165.1	179.9	197.2	212.4	208.1	186.5	162.2	146.2	135.4	127.6	126.4
80°	126.1	134.6	147.0	157.8	152.5	143.2	123.8	112.2	104.5	96.7	93.6
82.5°	91.5	100.0	107.4	113.3	109.2	100.5	88.6	80.7	76.0	70.7	69.5
85°	48.0	52.6	55.7	57.3	55.7	50.3	44.8	41.8	38.0	35.6	34.8
87.5°	24.9	23.2	22.1	22.6	20.3	19.8	16.5	13.8	13.9	14.2	13.5
90°	31.7	23.4	17.6	14.0	11.7	9.4	4.6	1.2	4.6	9.4	11.7
92.5°	117.0	79.8	53.2	42.2	34.2	29.1	20.6	14.3	20.6	29.1	34.2
95°	270.9	169.0	114.9	86.8	68.1	57.5	45.7	41.1	45.7	57.5	68.1
97.5°	365.1	222.9	155.1	123.2	101.6	85.6	73.2	66.9	73.2	85.6	101.6
100°	384.8	241.7	179.5	146.6	123.2	104.4	93.8	90.3	93.8	104.4	123.2
102.5°	385.8	258.5	201.1	168.2	143.8	125.0	114.5	111.9	114.5	125.0	143.8
105°	391.8	287.4	232.3	199.4	173.6	156.0	147.8	143.1	147.8	156.0	173.6
107.5°	408.0	317.0	263.5	230.5	204.8	188.6	180.7	176.9	180.7	188.6	204.8
110°	421.1	336.7	285.1	251.1	226.4	211.2	204.1	199.4	204.1	211.2	226.4



TEST NUMBER: P331458-840

CATALOG NUMBER: SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	435.3	355.5	305.7	270.7	247.0	232.8	224.8	220.0	224.8	232.8	247.0
115°	456.4	384.8	334.4	302.7	279.2	265.1	258.1	252.3	258.1	265.1	279.2
117.5°	478.9	411.7	365.1	332.2	309.7	297.3	290.2	285.6	290.2	297.3	309.7
120°	493.9	430.5	384.8	351.9	328.5	317.9	310.8	306.2	310.8	317.9	328.5
122.5°	507.1	448.4	405.5	371.6	348.2	336.7	329.6	325.9	329.6	336.7	348.2
125°	528.0	475.1	432.9	400.0	376.6	362.5	355.5	351.9	355.5	362.5	376.6
127.5°	547.3	500.0	458.9	425.2	402.6	387.2	377.3	372.5	377.3	387.2	402.6
130°	559.6	515.0	473.9	441.1	417.7	401.2	389.5	384.8	389.5	401.2	417.7
132.5°	571.8	528.2	489.0	456.2	431.7	414.3	401.7	396.1	401.7	414.3	431.7
135°	587.7	546.6	509.2	476.3	449.3	431.7	417.7	412.9	417.7	431.7	449.3
137.5°	600.0	561.7	524.6	494.1	467.4	448.6	434.5	428.9	434.5	448.6	467.4
140°	606.5	570.2	534.9	504.4	478.7	459.9	445.8	441.1	445.8	459.9	478.7
142.5°	612.2	576.7	542.5	513.8	489.0	470.2	457.1	453.3	457.1	470.2	489.0
145°	619.5	586.5	554.9	529.1	505.6	488.1	476.3	471.6	476.3	488.1	505.6
147.5°	623.4	594.5	564.7	541.8	522.3	506.0	494.8	491.3	494.8	506.0	522.3
150°	625.3	598.3	571.3	550.2	532.6	517.4	508.0	504.4	508.0	517.4	532.6
152.5°	626.2	602.1	577.8	558.7	542.0	528.6	519.3	517.6	519.3	528.6	542.0
155°	627.6	607.6	587.7	570.2	557.2	544.3	537.2	536.1	537.2	544.3	557.2
157.5°	627.6	611.7	594.8	580.0	569.7	558.5	552.8	551.6	552.8	558.5	569.7
160°	627.6	613.6	599.5	586.5	577.1	567.7	563.1	561.9	563.1	567.7	577.1
162.5°	626.7	614.5	602.3	592.2	583.7	576.2	571.6	572.3	571.6	576.2	583.7
165°	624.1	615.9	605.3	598.3	592.4	585.4	583.1	584.2	583.1	585.4	592.4
167.5°	622.5	615.6	607.9	603.5	599.3	594.8	592.7	594.1	592.7	594.8	599.3
170°	620.6	614.7	608.8	605.3	603.0	599.5	598.3	600.7	598.3	599.5	603.0
172.5°	617.7	613.8	609.8	607.2	605.8	602.3	603.0	604.4	603.0	602.3	605.8
175°	614.7	612.4	610.1	608.8	608.8	606.5	607.6	608.8	607.6	606.5	608.8
177.5°	612.9	611.0	610.1	610.1	610.1	608.1	609.0	611.0	609.0	608.1	610.1
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1



TEST NUMBER: P331458-840

CATALOG NUMBER: SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1987.1	1983.4	1970.3	1963.6	1952.5	1941.9	1935.1	1938.2	1940.7	1939.4	1937.5
5°	1930.2	1915.4	1893.0	1873.6	1859.7	1834.2	1823.3	1818.0	1813.3	1807.9	1802.4
7.5°	1862.3	1839.2	1807.0	1779.4	1753.3	1721.6	1703.5	1692.7	1681.5	1669.3	1658.5
10°	1814.0	1781.5	1747.5	1708.8	1677.9	1649.2	1623.7	1606.6	1591.1	1576.5	1565.6
12.5°	1763.3	1725.9	1683.7	1630.8	1596.7	1555.7	1551.9	1521.9	1497.6	1488.5	1475.8
15°	1682.4	1629.8	1576.5	1513.8	1486.7	1449.6	1426.3	1403.1	1382.2	1367.5	1363.6
17.5°	1590.7	1522.6	1469.5	1424.4	1380.1	1342.0	1320.6	1302.0	1284.9	1265.2	1262.5
20°	1520.8	1461.9	1403.9	1364.4	1318.8	1280.0	1253.7	1235.2	1220.4	1208.8	1198.8
22.5°	1454.5	1390.1	1337.0	1293.8	1248.8	1217.5	1196.8	1178.8	1166.6	1153.8	1144.3
25°	1348.2	1297.9	1239.8	1191.0	1153.9	1133.8	1116.7	1101.3	1093.6	1085.0	1074.2
27.5°	1255.2	1199.2	1144.9	1107.1	1074.5	1056.7	1044.6	1034.1	1026.8	1021.9	1015.7
30°	1189.5	1133.0	1090.5	1053.3	1026.2	1008.5	1000.7	994.5	985.9	982.9	979.8
32.5°	1126.3	1075.4	1039.1	1006.8	981.0	969.4	962.3	956.7	950.1	947.0	940.8
35°	1037.0	994.5	958.9	941.1	920.2	910.1	904.7	897.0	890.8	887.7	886.9
37.5°	953.0	916.0	892.6	869.7	860.9	854.7	847.3	842.0	840.2	839.7	838.9
40°	898.5	868.3	847.5	828.9	825.0	815.7	809.5	804.9	804.9	805.7	804.9
42.5°	849.0	821.9	803.4	787.4	782.8	777.3	771.1	770.8	772.0	774.7	772.0
45°	774.0	754.6	741.4	733.7	725.2	719.7	718.9	721.2	722.1	722.9	725.2
47.5°	704.9	692.1	680.1	671.6	667.9	666.9	666.0	670.0	673.8	675.2	678.7
50°	664.0	649.3	639.2	633.8	630.8	629.1	630.8	635.4	638.4	642.4	644.7
52.5°	618.2	607.8	600.9	596.7	595.4	596.4	596.7	602.0	606.9	608.3	609.4
55°	554.9	547.1	545.6	538.7	541.7	541.0	544.8	548.0	552.6	557.2	558.0
57.5°	491.7	485.5	481.4	482.0	482.9	486.4	489.6	495.0	500.0	504.9	505.3
60°	449.7	446.6	444.2	444.2	445.8	450.4	454.2	459.7	462.8	465.9	468.2
62.5°	411.2	408.2	405.9	407.1	411.1	413.8	418.4	421.3	424.4	427.5	428.6
65°	350.6	349.0	351.3	352.9	353.7	357.6	362.9	365.3	368.4	369.9	375.4
67.5°	294.7	295.0	294.7	296.9	301.3	302.3	307.4	312.9	313.5	316.4	319.9
70°	256.9	258.5	260.0	261.6	265.5	267.0	270.8	273.2	276.3	278.6	280.9
72.5°	222.3	222.6	224.1	223.8	227.0	230.5	233.7	236.0	239.1	242.1	244.4
75°	171.1	171.1	172.6	173.4	177.2	181.1	180.4	181.9	185.0	188.0	189.7
77.5°	124.9	123.2	124.9	125.7	126.9	130.2	130.8	133.0	136.5	135.4	137.1
80°	95.2	92.9	95.2	95.9	95.9	99.9	99.9	101.4	103.7	101.4	103.7
82.5°	68.0	66.9	68.6	68.8	70.0	70.1	71.4	71.7	74.0	72.9	74.0
85°	34.0	33.3	34.0	33.3	34.0	34.8	34.8	34.0	34.0	35.6	33.3
87.5°	13.3	13.4	13.9	15.7	16.5	16.1	15.1	14.9	14.4	13.7	13.9
90°	14.0	17.6	23.4	31.7	38.7	39.9	38.7	37.6	35.2	37.6	38.7
92.5°	42.2	53.2	79.8	117.0	150.4	152.5	128.9	102.3	87.8	77.9	70.6
95°	86.8	114.9	169.0	270.9	407.1	459.9	402.4	307.4	235.8	186.5	160.7
97.5°	123.2	155.1	222.9	365.1	591.3	785.1	823.5	717.2	586.8	459.9	375.2
100°	146.6	179.5	241.7	384.8	638.1	926.8	1095.7	1071.1	925.6	764.9	622.9
102.5°	168.2	201.1	258.5	385.8	620.4	931.5	1197.1	1302.9	1270.0	1152.5	1002.1
105°	199.4	232.3	287.4	391.8	585.4	869.3	1181.3	1425.3	1557.9	1573.2	1534.5
107.5°	230.5	263.5	317.0	408.0	568.0	802.6	1078.3	1337.2	1536.8	1658.8	1715.6
110°	251.1	285.1	336.7	421.1	564.3	770.7	1013.6	1261.1	1471.1	1621.2	1717.5



TEST NUMBER: P331458-840

CATALOG NUMBER: SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	270.7	305.7	355.5	435.3	565.2	750.1	968.6	1191.6	1393.2	1553.7	1664.0
115°	302.7	334.4	384.8	456.4	570.2	727.3	912.7	1106.3	1287.0	1440.6	1561.5
117.5°	332.2	365.1	411.7	478.9	578.6	716.3	877.5	1042.0	1200.6	1340.0	1453.3
120°	351.9	384.8	430.5	493.9	584.2	709.7	858.7	1010.1	1155.5	1279.9	1386.6
122.5°	371.6	405.5	448.4	507.1	590.8	706.0	842.7	984.7	1118.0	1235.8	1332.2
125°	400.0	432.9	475.1	528.0	600.7	699.2	820.0	947.9	1068.7	1171.9	1259.9
127.5°	425.2	458.9	500.0	547.3	610.8	695.2	798.9	911.5	1020.9	1118.2	1199.4
130°	441.1	473.9	515.0	559.6	618.2	693.3	784.9	888.1	989.0	1081.7	1159.0
132.5°	456.2	489.0	528.2	571.8	625.7	692.4	773.6	865.6	959.0	1044.1	1116.8
135°	476.3	509.2	546.6	587.7	634.7	690.9	757.8	834.0	911.5	989.0	1054.6
137.5°	494.1	524.6	561.7	600.0	642.7	690.7	746.8	809.0	873.7	935.2	992.5
140°	504.4	534.9	570.2	606.5	646.4	689.8	740.2	793.0	849.4	903.3	954.9
142.5°	513.8	542.5	576.7	612.2	649.2	689.8	733.7	779.9	827.8	874.2	917.4
145°	529.1	554.9	586.5	619.5	652.3	687.4	725.0	761.3	800.1	836.5	870.5
147.5°	541.8	564.7	594.5	623.4	653.2	683.3	716.1	747.1	777.6	806.0	830.8
150°	550.2	571.3	598.3	625.3	652.3	680.4	708.5	736.7	762.5	787.2	808.3
152.5°	558.7	577.8	602.1	626.2	650.4	675.7	702.0	726.4	750.3	771.2	789.5
155°	570.2	587.7	607.6	627.6	647.5	667.5	689.8	712.1	730.8	748.4	761.3
157.5°	580.0	594.8	611.7	627.6	642.2	659.0	678.3	695.4	711.1	725.9	736.0
160°	586.5	599.5	613.6	627.6	639.3	653.5	669.8	685.1	698.0	710.9	719.1
162.5°	592.2	602.3	614.5	626.7	636.5	648.7	662.4	674.8	685.8	696.8	703.2
165°	598.3	605.3	615.9	624.1	631.2	639.3	649.9	659.3	667.5	675.7	680.4
167.5°	603.5	607.9	615.6	622.5	625.7	631.2	637.7	644.5	650.9	656.5	660.8
170°	605.3	608.8	614.7	620.6	622.9	626.4	631.2	637.0	640.6	645.2	647.5
172.5°	607.2	609.8	613.8	617.7	619.1	620.9	624.6	628.5	631.2	634.9	636.3
175°	608.8	610.1	612.4	614.7	613.6	614.7	615.9	619.5	620.6	621.8	622.9
177.5°	610.1	610.1	611.0	612.9	611.0	610.1	611.0	612.9	612.9	613.8	613.8
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1



TEST NUMBER: P331458-840

CATALOG NUMBER: SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1931.4	1930.2	1930.2	1924.6	1930.2	1930.2	1931.4	1937.5	1939.4	1940.7	1938.2
5°	1791.6	1789.3	1785.4	1789.3	1785.4	1789.3	1791.6	1802.4	1807.9	1813.3	1818.0
7.5°	1653.4	1644.1	1642.7	1633.6	1642.7	1644.1	1653.4	1658.5	1669.3	1681.5	1692.7
10°	1552.5	1546.3	1545.5	1530.8	1545.5	1546.3	1552.5	1565.6	1576.5	1591.1	1606.6
12.5°	1475.7	1460.9	1463.8	1455.2	1463.8	1460.9	1475.7	1475.8	1488.5	1497.6	1521.9
15°	1342.7	1342.7	1339.7	1326.5	1339.7	1342.7	1342.7	1363.6	1367.5	1382.2	1403.1
17.5°	1247.3	1245.7	1238.3	1241.9	1238.3	1245.7	1247.3	1262.5	1265.2	1284.9	1302.0
20°	1190.2	1185.7	1176.4	1176.4	1176.4	1185.7	1190.2	1198.8	1208.8	1220.4	1235.2
22.5°	1136.4	1136.1	1126.2	1129.3	1126.2	1136.1	1136.4	1144.3	1153.8	1166.6	1178.8
25°	1073.4	1067.2	1062.6	1064.9	1062.6	1067.2	1073.4	1074.2	1085.0	1093.6	1101.3
27.5°	1013.7	1010.3	1010.0	1003.6	1010.0	1010.3	1013.7	1015.7	1021.9	1026.8	1034.1
30°	979.0	971.3	972.8	969.0	972.8	971.3	979.0	979.8	982.9	985.9	994.5
32.5°	939.4	936.5	935.0	931.8	935.0	936.5	939.4	940.8	947.0	950.1	956.7
35°	885.3	886.2	882.2	883.8	882.2	886.2	885.3	886.9	887.7	890.8	897.0
37.5°	838.2	840.6	838.8	839.2	838.8	840.6	838.2	838.9	839.7	840.2	842.0
40°	807.2	807.2	807.2	809.5	807.2	807.2	807.2	804.9	805.7	804.9	804.9
42.5°	777.5	776.3	775.0	774.9	775.0	776.3	777.5	772.0	774.7	772.0	770.8
45°	726.7	729.0	729.8	725.9	729.8	729.0	726.7	725.2	722.9	722.1	721.2
47.5°	680.8	681.1	680.8	684.2	680.8	681.1	680.8	678.7	675.2	673.8	670.0
50°	648.5	647.0	648.5	647.0	648.5	647.0	648.5	644.7	642.4	638.4	635.4
52.5°	614.5	614.8	613.9	613.6	613.9	614.8	614.5	609.4	608.3	606.9	602.0
55°	561.1	562.6	561.9	561.9	561.9	562.6	561.1	558.0	557.2	552.6	548.0
57.5°	505.8	507.3	508.3	504.9	508.3	507.3	505.8	505.3	504.9	500.0	495.0
60°	467.5	471.3	470.5	469.0	470.5	471.3	467.5	468.2	465.9	462.8	459.7
62.5°	432.1	433.5	433.4	433.1	433.4	433.5	432.1	428.6	427.5	424.4	421.3
65°	377.7	379.2	376.9	379.2	376.9	379.2	377.7	375.4	369.9	368.4	365.3
67.5°	319.0	319.5	321.1	322.2	321.1	319.5	319.0	319.9	316.4	313.5	312.9
70°	282.5	281.8	284.1	286.4	284.1	281.8	282.5	280.9	278.6	276.3	273.2
72.5°	244.1	245.8	245.0	246.7	245.0	245.8	244.1	244.4	242.1	239.1	236.0
75°	188.0	190.4	189.7	192.0	189.7	190.4	188.0	189.7	188.0	185.0	181.9
77.5°	135.9	136.2	135.9	137.1	135.9	136.2	135.9	137.1	135.4	136.5	133.0
80°	103.7	102.2	100.6	103.7	100.6	102.2	103.7	103.7	101.4	103.7	101.4
82.5°	72.1	73.0	71.5	71.5	71.5	73.0	72.1	74.0	72.9	74.0	71.7
85°	33.3	32.5	31.0	31.0	31.0	32.5	33.3	33.3	35.6	34.0	34.0
87.5°	13.9	13.3	13.3	12.7	13.3	13.3	13.9	13.9	13.7	14.4	14.9
90°	38.7	38.7	38.7	38.7	38.7	38.7	38.7	38.7	37.6	35.2	37.6
92.5°	69.7	65.9	66.9	65.0	66.9	65.9	69.7	70.6	77.9	87.8	102.3
95°	145.4	136.1	132.6	133.7	132.6	136.1	145.4	160.7	186.5	235.8	307.4
97.5°	319.1	290.2	273.1	263.3	273.1	290.2	319.1	375.2	459.9	586.8	717.2
100°	525.5	475.1	441.1	420.0	441.1	475.1	525.5	622.9	764.9	925.6	1071.1
102.5°	896.3	810.2	767.7	739.1	767.7	810.2	896.3	1002.1	1152.5	1270.0	1302.9
105°	1461.7	1389.0	1338.6	1322.1	1338.6	1389.0	1461.7	1534.5	1573.2	1557.9	1425.3
107.5°	1724.7	1720.7	1710.6	1688.8	1710.6	1720.7	1724.7	1715.6	1658.8	1536.8	1337.2
110°	1767.9	1790.2	1800.8	1799.6	1800.8	1790.2	1767.9	1717.5	1621.2	1471.1	1261.1



TEST NUMBER: P331458-840

CATALOG NUMBER: SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1734.1	1771.4	1791.4	1797.7	1791.4	1771.4	1734.1	1664.0	1553.7	1393.2	1191.6
115°	1644.8	1698.7	1729.2	1739.8	1729.2	1698.7	1644.8	1561.5	1440.6	1287.0	1106.3
117.5°	1538.2	1595.2	1627.4	1636.3	1627.4	1595.2	1538.2	1453.3	1340.0	1200.6	1042.0
120°	1468.7	1523.9	1557.9	1569.6	1557.9	1523.9	1468.7	1386.6	1279.9	1155.5	1010.1
122.5°	1405.8	1460.1	1490.4	1500.2	1490.4	1460.1	1405.8	1332.2	1235.8	1118.0	984.7
125°	1328.0	1372.6	1401.9	1411.3	1401.9	1372.6	1328.0	1259.9	1171.9	1068.7	947.9
127.5°	1258.8	1300.5	1325.9	1333.4	1325.9	1300.5	1258.8	1199.4	1118.2	1020.9	911.5
130°	1216.6	1256.5	1279.9	1289.3	1279.9	1256.5	1216.6	1159.0	1081.7	989.0	888.1
132.5°	1173.4	1213.3	1234.9	1243.2	1234.9	1213.3	1173.4	1116.8	1044.1	959.0	865.6
135°	1105.1	1143.8	1164.9	1169.6	1164.9	1143.8	1105.1	1054.6	989.0	911.5	834.0
137.5°	1038.4	1071.8	1090.4	1097.3	1090.4	1071.8	1038.4	992.5	935.2	873.7	809.0
140°	992.5	1023.0	1040.6	1047.6	1040.6	1023.0	992.5	954.9	903.3	849.4	793.0
142.5°	953.0	980.8	996.4	997.8	996.4	980.8	953.0	917.4	874.2	827.8	779.9
145°	898.6	918.6	930.3	933.8	930.3	918.6	898.6	870.5	836.5	800.1	761.3
147.5°	854.0	870.0	878.0	880.1	878.0	870.0	854.0	830.8	806.0	777.6	747.1
150°	825.9	840.0	847.0	848.2	847.0	840.0	825.9	808.3	787.2	762.5	736.7
152.5°	803.3	815.6	820.7	820.9	820.7	815.6	803.3	789.5	771.2	750.3	726.4
155°	774.3	782.4	787.2	784.9	787.2	782.4	774.3	761.3	748.4	730.8	712.1
157.5°	745.2	751.9	754.1	754.1	754.1	751.9	745.2	736.0	725.9	711.1	695.4
160°	727.3	733.2	734.4	734.4	734.4	733.2	727.3	719.1	710.9	698.0	685.1
162.5°	711.3	715.4	716.5	715.6	716.5	715.4	711.3	703.2	696.8	685.8	674.8
165°	685.1	689.8	689.8	688.6	689.8	689.8	685.1	680.4	675.7	667.5	659.3
167.5°	662.8	665.4	665.2	663.8	665.2	665.4	662.8	660.8	656.5	650.9	644.5
170°	648.7	652.3	651.1	648.7	651.1	652.3	648.7	647.5	645.2	640.6	637.0
172.5°	637.5	639.1	637.9	636.5	637.9	639.1	637.5	636.3	634.9	631.2	628.5
175°	622.9	624.1	622.9	620.6	622.9	624.1	622.9	622.9	621.8	620.6	619.5
177.5°	613.8	613.8	612.9	611.0	612.9	613.8	613.8	613.8	613.8	612.9	612.9
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1



TEST NUMBER: P331458-840

CATALOG NUMBER: SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1935.1	1941.9	1952.5	1963.6	1970.3	1983.4	1987.1	1993.3	1998.8	2011.9	2025.5
5°	1823.3	1834.2	1859.7	1873.6	1893.0	1915.4	1930.2	1945.6	1962.7	1992.1	2019.1
7.5°	1703.5	1721.6	1753.3	1779.4	1807.0	1839.2	1862.3	1893.0	1918.3	1959.8	1999.4
10°	1623.7	1649.2	1677.9	1708.8	1747.5	1781.5	1814.0	1852.7	1883.7	1933.2	1979.6
12.5°	1551.9	1555.7	1596.7	1630.8	1683.7	1725.9	1763.3	1813.1	1843.4	1902.3	1951.2
15°	1426.3	1449.6	1486.7	1513.8	1576.5	1629.8	1682.4	1734.3	1769.2	1841.9	1906.1
17.5°	1320.6	1342.0	1380.1	1424.4	1469.5	1522.6	1590.7	1645.4	1692.7	1775.8	1851.8
20°	1253.7	1280.0	1318.8	1364.4	1403.9	1461.9	1520.8	1583.5	1634.5	1728.2	1817.2
22.5°	1196.8	1217.5	1248.8	1293.8	1337.0	1390.1	1454.5	1522.8	1576.3	1677.4	1767.6
25°	1116.7	1133.8	1153.9	1191.0	1239.8	1297.9	1348.2	1423.2	1501.4	1595.8	1705.0
27.5°	1044.6	1056.7	1074.5	1107.1	1144.9	1199.2	1255.2	1326.4	1404.9	1507.4	1622.6
30°	1000.7	1008.5	1026.2	1053.3	1090.5	1133.0	1189.5	1257.6	1338.1	1441.8	1556.3
32.5°	962.3	969.4	981.0	1006.8	1039.1	1075.4	1126.3	1194.5	1271.2	1373.1	1500.0
35°	904.7	910.1	920.2	941.1	958.9	994.5	1037.0	1098.9	1170.9	1268.5	1400.0
37.5°	847.3	854.7	860.9	869.7	892.6	916.0	953.0	1005.3	1075.9	1174.4	1299.7
40°	809.5	815.7	825.0	828.9	847.5	868.3	898.5	946.4	1017.7	1107.4	1229.7
42.5°	771.1	777.3	782.8	787.4	803.4	821.9	849.0	890.2	953.3	1040.6	1161.6
45°	718.9	719.7	725.2	733.7	741.4	754.6	774.0	809.5	858.3	940.3	1050.2
47.5°	666.0	666.9	667.9	671.6	680.1	692.1	704.9	733.9	777.5	842.9	949.9
50°	630.8	629.1	630.8	633.8	639.2	649.3	664.0	684.9	720.5	781.6	879.9
52.5°	596.7	596.4	595.4	596.7	600.9	607.8	618.2	636.0	667.9	724.1	810.6
55°	544.8	541.0	541.7	538.7	545.6	547.1	554.9	569.6	597.4	636.1	717.4
57.5°	489.6	486.4	482.9	482.0	481.4	485.5	491.7	503.3	524.7	558.7	624.5
60°	454.2	450.4	445.8	444.2	444.2	446.6	449.7	458.2	478.3	508.5	562.6
62.5°	418.4	413.8	411.1	407.1	405.9	408.2	411.2	417.3	431.8	460.2	507.0
65°	362.9	357.6	353.7	352.9	351.3	349.0	350.6	356.8	368.4	390.8	428.0
67.5°	307.4	302.3	301.3	296.9	294.7	295.0	294.7	299.9	306.9	326.3	354.0
70°	270.8	267.0	265.5	261.6	260.0	258.5	256.9	261.6	268.5	284.8	308.8
72.5°	233.7	230.5	227.0	223.8	224.1	222.6	222.3	225.1	230.8	245.8	264.2
75°	180.4	181.1	177.2	173.4	172.6	171.1	171.1	173.4	175.7	187.3	202.0
77.5°	130.8	130.2	126.9	125.7	124.9	123.2	124.9	126.4	127.6	135.4	146.2
80°	99.9	99.9	95.9	95.9	95.2	92.9	95.2	93.6	96.7	104.5	112.2
82.5°	71.4	70.1	70.0	68.8	68.6	66.9	68.0	69.5	70.7	76.0	80.7
85°	34.8	34.8	34.0	33.3	34.0	33.3	34.0	34.8	35.6	38.0	41.8
87.5°	15.1	16.1	16.5	15.7	13.9	13.4	13.3	13.5	14.2	13.9	13.8
90°	38.7	39.9	38.7	31.7	23.4	17.6	14.0	11.7	9.4	4.6	1.2
92.5°	128.9	152.5	150.4	117.0	79.8	53.2	42.2	34.2	29.1	20.6	14.3
95°	402.4	459.9	407.1	270.9	169.0	114.9	86.8	68.1	57.5	45.7	41.1
97.5°	823.5	785.1	591.3	365.1	222.9	155.1	123.2	101.6	85.6	73.2	66.9
100°	1095.7	926.8	638.1	384.8	241.7	179.5	146.6	123.2	104.4	93.8	90.3
102.5°	1197.1	931.5	620.4	385.8	258.5	201.1	168.2	143.8	125.0	114.5	111.9
105°	1181.3	869.3	585.4	391.8	287.4	232.3	199.4	173.6	156.0	147.8	143.1
107.5°	1078.3	802.6	568.0	408.0	317.0	263.5	230.5	204.8	188.6	180.7	176.9
110°	1013.6	770.7	564.3	421.1	336.7	285.1	251.1	226.4	211.2	204.1	199.4



TEST NUMBER: P331458-840

CATALOG NUMBER: SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	968.6	750.1	565.2	435.3	355.5	305.7	270.7	247.0	232.8	224.8	220.0
115°	912.7	727.3	570.2	456.4	384.8	334.4	302.7	279.2	265.1	258.1	252.3
117.5°	877.5	716.3	578.6	478.9	411.7	365.1	332.2	309.7	297.3	290.2	285.6
120°	858.7	709.7	584.2	493.9	430.5	384.8	351.9	328.5	317.9	310.8	306.2
122.5°	842.7	706.0	590.8	507.1	448.4	405.5	371.6	348.2	336.7	329.6	325.9
125°	820.0	699.2	600.7	528.0	475.1	432.9	400.0	376.6	362.5	355.5	351.9
127.5°	798.9	695.2	610.8	547.3	500.0	458.9	425.2	402.6	387.2	377.3	372.5
130°	784.9	693.3	618.2	559.6	515.0	473.9	441.1	417.7	401.2	389.5	384.8
132.5°	773.6	692.4	625.7	571.8	528.2	489.0	456.2	431.7	414.3	401.7	396.1
135°	757.8	690.9	634.7	587.7	546.6	509.2	476.3	449.3	431.7	417.7	412.9
137.5°	746.8	690.7	642.7	600.0	561.7	524.6	494.1	467.4	448.6	434.5	428.9
140°	740.2	689.8	646.4	606.5	570.2	534.9	504.4	478.7	459.9	445.8	441.1
142.5°	733.7	689.8	649.2	612.2	576.7	542.5	513.8	489.0	470.2	457.1	453.3
145°	725.0	687.4	652.3	619.5	586.5	554.9	529.1	505.6	488.1	476.3	471.6
147.5°	716.1	683.3	653.2	623.4	594.5	564.7	541.8	522.3	506.0	494.8	491.3
150°	708.5	680.4	652.3	625.3	598.3	571.3	550.2	532.6	517.4	508.0	504.4
152.5°	702.0	675.7	650.4	626.2	602.1	577.8	558.7	542.0	528.6	519.3	517.6
155°	689.8	667.5	647.5	627.6	607.6	587.7	570.2	557.2	544.3	537.2	536.1
157.5°	678.3	659.0	642.2	627.6	611.7	594.8	580.0	569.7	558.5	552.8	551.6
160°	669.8	653.5	639.3	627.6	613.6	599.5	586.5	577.1	567.7	563.1	561.9
162.5°	662.4	648.7	636.5	626.7	614.5	602.3	592.2	583.7	576.2	571.6	572.3
165°	649.9	639.3	631.2	624.1	615.9	605.3	598.3	592.4	585.4	583.1	584.2
167.5°	637.7	631.2	625.7	622.5	615.6	607.9	603.5	599.3	594.8	592.7	594.1
170°	631.2	626.4	622.9	620.6	614.7	608.8	605.3	603.0	599.5	598.3	600.7
172.5°	624.6	620.9	619.1	617.7	613.8	609.8	607.2	605.8	602.3	603.0	604.4
175°	615.9	614.7	613.6	614.7	612.4	610.1	608.8	608.8	606.5	607.6	608.8
177.5°	611.0	610.1	611.0	612.9	611.0	610.1	610.1	610.1	608.1	609.0	611.0
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1



TEST NUMBER: P331458-840

CATALOG NUMBER: SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2024.3	2027.3	2037.2	2047.2	2058.3	2061.4	2066.4	2062.0	2060.7	2072.5	2081.2
5°	2029.9	2043.9	2071.0	2095.8	2116.7	2131.3	2146.9	2153.0	2164.6	2180.9	2201.0
7.5°	2023.5	2050.5	2093.1	2129.2	2168.5	2196.9	2219.0	2237.9	2260.8	2291.6	2325.1
10°	2016.0	2052.4	2104.3	2148.4	2196.4	2232.7	2262.9	2292.3	2326.4	2368.9	2413.1
12.5°	2002.5	2045.6	2110.4	2162.6	2224.2	2260.0	2300.7	2364.2	2400.7	2459.9	2522.0
15°	1975.0	2023.0	2113.5	2177.8	2247.5	2315.5	2390.7	2450.9	2511.3	2546.2	2633.6
17.5°	1934.3	2004.8	2105.1	2180.0	2268.5	2375.7	2460.1	2528.5	2598.2	2654.6	2698.5
20°	1901.5	1978.1	2092.6	2182.4	2287.6	2403.0	2499.7	2569.4	2629.8	2677.0	2704.0
22.5°	1860.0	1956.4	2067.9	2173.1	2307.5	2421.6	2523.2	2578.1	2628.5	2651.6	2661.9
25°	1794.7	1910.8	2036.9	2165.5	2317.1	2437.8	2530.7	2563.9	2578.7	2556.3	2519.1
27.5°	1724.2	1853.7	2001.1	2150.8	2311.2	2427.3	2493.9	2488.6	2463.7	2391.1	2333.0
30°	1671.6	1814.0	1972.7	2136.0	2296.9	2409.9	2448.6	2409.9	2353.5	2272.2	2189.4
32.5°	1616.6	1763.9	1942.4	2115.0	2271.0	2370.4	2378.7	2312.2	2224.7	2132.3	2029.0
35°	1533.1	1692.5	1885.2	2067.9	2215.7	2278.4	2241.3	2123.6	2019.9	1893.8	1752.9
37.5°	1438.9	1614.9	1808.2	1999.0	2132.9	2149.3	2057.1	1933.2	1787.0	1638.7	1472.9
40°	1368.3	1554.8	1753.7	1946.4	2064.8	2047.8	1930.2	1793.9	1619.8	1438.7	1284.6
42.5°	1305.1	1491.7	1694.3	1883.2	1978.1	1931.4	1793.9	1626.8	1439.7	1269.1	1128.0
45°	1195.7	1387.7	1595.1	1777.7	1831.9	1747.5	1565.6	1379.9	1195.7	1053.3	941.9
47.5°	1089.5	1279.3	1484.7	1645.2	1664.4	1551.0	1352.2	1161.0	1002.7	886.8	808.1
50°	1011.5	1201.8	1405.4	1548.6	1542.4	1405.4	1201.1	1019.3	886.9	793.2	740.6
52.5°	941.5	1121.4	1316.9	1447.0	1414.2	1264.9	1069.9	908.4	799.6	726.4	678.7
55°	832.7	999.2	1184.9	1289.3	1229.0	1063.4	898.5	768.5	688.0	633.1	595.9
57.5°	724.7	880.7	1039.7	1104.1	1037.3	884.4	747.0	652.7	592.2	551.5	527.4
60°	657.8	794.1	935.6	991.4	911.7	775.5	667.1	582.8	534.0	500.7	479.1
62.5°	591.0	713.0	846.5	876.9	804.0	688.8	592.8	522.7	482.6	453.0	432.6
65°	500.0	599.8	701.1	721.2	654.0	564.9	489.1	443.4	407.9	386.2	369.9
67.5°	410.0	490.2	562.0	578.2	519.3	457.6	402.7	362.9	338.8	320.8	307.1
70°	356.8	420.2	479.1	492.2	445.0	390.0	348.3	316.5	294.9	279.4	266.2
72.5°	300.4	353.4	402.2	411.1	372.5	330.6	296.3	271.4	252.2	242.3	229.7
75°	229.8	260.8	298.7	301.0	275.5	249.9	223.7	207.4	197.3	185.0	178.7
77.5°	162.2	186.5	208.1	212.4	197.2	179.9	165.1	152.3	143.8	138.0	132.3
80°	123.8	143.2	152.5	157.8	147.0	134.6	126.1	117.6	112.2	108.4	104.5
82.5°	88.6	100.5	109.2	113.3	107.4	100.0	91.5	86.6	82.5	79.3	77.9
85°	44.8	50.3	55.7	57.3	55.7	52.6	48.0	48.0	45.6	44.8	44.8
87.5°	16.5	19.8	20.3	22.6	22.1	23.2	24.9	25.7	25.3	24.4	23.6
90°	4.6	9.4	11.7	14.0	17.6	23.4	31.7	38.7	39.9	38.7	37.6
92.5°	20.6	29.1	34.2	42.2	53.2	79.8	117.0	150.4	152.5	128.9	102.3
95°	45.7	57.5	68.1	86.8	114.9	169.0	270.9	407.1	459.9	402.4	307.4
97.5°	73.2	85.6	101.6	123.2	155.1	222.9	365.1	591.3	785.1	823.5	717.2
100°	93.8	104.4	123.2	146.6	179.5	241.7	384.8	638.1	926.8	1095.7	1071.1
102.5°	114.5	125.0	143.8	168.2	201.1	258.5	385.8	620.4	931.5	1197.1	1302.9
105°	147.8	156.0	173.6	199.4	232.3	287.4	391.8	585.4	869.3	1181.3	1425.3
107.5°	180.7	188.6	204.8	230.5	263.5	317.0	408.0	568.0	802.6	1078.3	1337.2
110°	204.1	211.2	226.4	251.1	285.1	336.7	421.1	564.3	770.7	1013.6	1261.1



TEST NUMBER: P331458-840

CATALOG NUMBER: SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	224.8	232.8	247.0	270.7	305.7	355.5	435.3	565.2	750.1	968.6	1191.6
115°	258.1	265.1	279.2	302.7	334.4	384.8	456.4	570.2	727.3	912.7	1106.3
117.5°	290.2	297.3	309.7	332.2	365.1	411.7	478.9	578.6	716.3	877.5	1042.0
120°	310.8	317.9	328.5	351.9	384.8	430.5	493.9	584.2	709.7	858.7	1010.1
122.5°	329.6	336.7	348.2	371.6	405.5	448.4	507.1	590.8	706.0	842.7	984.7
125°	355.5	362.5	376.6	400.0	432.9	475.1	528.0	600.7	699.2	820.0	947.9
127.5°	377.3	387.2	402.6	425.2	458.9	500.0	547.3	610.8	695.2	798.9	911.5
130°	389.5	401.2	417.7	441.1	473.9	515.0	559.6	618.2	693.3	784.9	888.1
132.5°	401.7	414.3	431.7	456.2	489.0	528.2	571.8	625.7	692.4	773.6	865.6
135°	417.7	431.7	449.3	476.3	509.2	546.6	587.7	634.7	690.9	757.8	834.0
137.5°	434.5	448.6	467.4	494.1	524.6	561.7	600.0	642.7	690.7	746.8	809.0
140°	445.8	459.9	478.7	504.4	534.9	570.2	606.5	646.4	689.8	740.2	793.0
142.5°	457.1	470.2	489.0	513.8	542.5	576.7	612.2	649.2	689.8	733.7	779.9
145°	476.3	488.1	505.6	529.1	554.9	586.5	619.5	652.3	687.4	725.0	761.3
147.5°	494.8	506.0	522.3	541.8	564.7	594.5	623.4	653.2	683.3	716.1	747.1
150°	508.0	517.4	532.6	550.2	571.3	598.3	625.3	652.3	680.4	708.5	736.7
152.5°	519.3	528.6	542.0	558.7	577.8	602.1	626.2	650.4	675.7	702.0	726.4
155°	537.2	544.3	557.2	570.2	587.7	607.6	627.6	647.5	667.5	689.8	712.1
157.5°	552.8	558.5	569.7	580.0	594.8	611.7	627.6	642.2	659.0	678.3	695.4
160°	563.1	567.7	577.1	586.5	599.5	613.6	627.6	639.3	653.5	669.8	685.1
162.5°	571.6	576.2	583.7	592.2	602.3	614.5	626.7	636.5	648.7	662.4	674.8
165°	583.1	585.4	592.4	598.3	605.3	615.9	624.1	631.2	639.3	649.9	659.3
167.5°	592.7	594.8	599.3	603.5	607.9	615.6	622.5	625.7	631.2	637.7	644.5
170°	598.3	599.5	603.0	605.3	608.8	614.7	620.6	622.9	626.4	631.2	637.0
172.5°	603.0	602.3	605.8	607.2	609.8	613.8	617.7	619.1	620.9	624.6	628.5
175°	607.6	606.5	608.8	608.8	610.1	612.4	614.7	613.6	614.7	615.9	619.5
177.5°	609.0	608.1	610.1	610.1	610.1	611.0	612.9	611.0	610.1	611.0	612.9
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1



TEST NUMBER: P331458-840

CATALOG NUMBER: SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2088.6	2097.3	2097.3	2098.5	2108.4	2107.2	2106.6
5°	2222.7	2235.8	2237.4	2251.3	2260.6	2257.5	2249.0
7.5°	2349.1	2373.6	2392.2	2402.6	2414.8	2422.4	2418.9
10°	2449.4	2485.1	2506.7	2521.4	2539.2	2552.3	2547.7
12.5°	2540.4	2582.8	2612.6	2637.8	2640.1	2657.0	2645.5
15°	2682.4	2727.2	2731.9	2750.5	2765.2	2763.6	2764.4
17.5°	2729.3	2743.7	2746.6	2747.0	2747.2	2741.8	2730.1
20°	2712.6	2707.1	2694.0	2683.9	2666.1	2663.8	2648.4
22.5°	2633.3	2616.2	2583.1	2561.3	2533.7	2526.4	2522.0
25°	2477.3	2439.3	2386.7	2336.4	2322.5	2295.4	2303.2
27.5°	2263.2	2204.1	2147.2	2106.3	2069.3	2028.7	2040.3
30°	2112.7	2046.2	1965.7	1903.8	1864.3	1825.6	1818.7
32.5°	1933.2	1835.7	1746.0	1691.4	1630.9	1606.5	1579.7
35°	1623.7	1528.4	1439.5	1362.8	1318.8	1284.6	1253.7
37.5°	1345.2	1235.7	1163.8	1101.8	1069.9	1050.4	1055.3
40°	1172.5	1076.5	1023.9	976.6	947.3	933.3	936.4
42.5°	1032.6	960.7	917.4	885.0	864.3	856.6	854.7
45°	873.7	833.5	797.9	779.3	769.3	760.7	755.4
47.5°	765.4	732.6	712.5	701.5	692.7	684.0	683.8
50°	700.3	678.7	664.8	653.2	646.2	640.1	645.4
52.5°	650.9	631.1	617.1	606.7	604.1	598.5	598.3
55°	577.3	561.9	551.8	542.5	537.9	534.7	530.9
57.5°	510.5	495.7	486.5	480.6	471.8	468.7	467.5
60°	462.8	451.2	441.9	434.1	430.3	424.1	424.1
62.5°	418.8	407.3	398.6	392.6	386.4	383.8	384.5
65°	355.3	346.0	337.4	331.2	329.7	325.1	326.6
67.5°	296.7	290.5	281.6	278.1	275.2	272.8	270.8
70°	257.7	251.6	246.9	242.3	239.9	239.9	239.9
72.5°	224.9	217.4	214.7	208.8	210.2	207.7	205.2
75°	174.1	169.5	167.1	164.8	161.0	161.0	161.0
77.5°	128.2	126.7	124.0	121.5	120.6	119.8	120.1
80°	99.1	98.3	96.7	96.7	95.2	94.4	92.9
82.5°	76.1	74.1	73.2	72.6	72.3	72.1	71.8
85°	43.3	41.8	41.8	42.5	41.0	41.0	41.8
87.5°	23.7	24.2	23.8	23.8	24.4	23.8	23.8
90°	35.2	37.6	38.7	38.7	38.7	38.7	38.7
92.5°	87.8	77.9	70.6	69.7	65.9	66.9	65.0
95°	235.8	186.5	160.7	145.4	136.1	132.6	133.7
97.5°	586.8	459.9	375.2	319.1	290.2	273.1	263.3
100°	925.6	764.9	622.9	525.5	475.1	441.1	420.0
102.5°	1270.0	1152.5	1002.1	896.3	810.2	767.7	739.1
105°	1557.9	1573.2	1534.5	1461.7	1389.0	1338.6	1322.1
107.5°	1536.8	1658.8	1715.6	1724.7	1720.7	1710.6	1688.8
110°	1471.1	1621.2	1717.5	1767.9	1790.2	1800.8	1799.6



TEST NUMBER: P331458-840

CATALOG NUMBER: SA2XXDIP-C1005D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1393.2	1553.7	1664.0	1734.1	1771.4	1791.4	1797.7
115°	1287.0	1440.6	1561.5	1644.8	1698.7	1729.2	1739.8
117.5°	1200.6	1340.0	1453.3	1538.2	1595.2	1627.4	1636.3
120°	1155.5	1279.9	1386.6	1468.7	1523.9	1557.9	1569.6
122.5°	1118.0	1235.8	1332.2	1405.8	1460.1	1490.4	1500.2
125°	1068.7	1171.9	1259.9	1328.0	1372.6	1401.9	1411.3
127.5°	1020.9	1118.2	1199.4	1258.8	1300.5	1325.9	1333.4
130°	989.0	1081.7	1159.0	1216.6	1256.5	1279.9	1289.3
132.5°	959.0	1044.1	1116.8	1173.4	1213.3	1234.9	1243.2
135°	911.5	989.0	1054.6	1105.1	1143.8	1164.9	1169.6
137.5°	873.7	935.2	992.5	1038.4	1071.8	1090.4	1097.3
140°	849.4	903.3	954.9	992.5	1023.0	1040.6	1047.6
142.5°	827.8	874.2	917.4	953.0	980.8	996.4	997.8
145°	800.1	836.5	870.5	898.6	918.6	930.3	933.8
147.5°	777.6	806.0	830.8	854.0	870.0	878.0	880.1
150°	762.5	787.2	808.3	825.9	840.0	847.0	848.2
152.5°	750.3	771.2	789.5	803.3	815.6	820.7	820.9
155°	730.8	748.4	761.3	774.3	782.4	787.2	784.9
157.5°	711.1	725.9	736.0	745.2	751.9	754.1	754.1
160°	698.0	710.9	719.1	727.3	733.2	734.4	734.4
162.5°	685.8	696.8	703.2	711.3	715.4	716.5	715.6
165°	667.5	675.7	680.4	685.1	689.8	689.8	688.6
167.5°	650.9	656.5	660.8	662.8	665.4	665.2	663.8
170°	640.6	645.2	647.5	648.7	652.3	651.1	648.7
172.5°	631.2	634.9	636.3	637.5	639.1	637.9	636.5
175°	620.6	621.8	622.9	622.9	624.1	622.9	620.6
177.5°	612.9	613.8	613.8	613.8	613.8	612.9	611.0
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1

(END OF REPORT)