

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331426-840

Luminaire Tested: **SA2XXDIP-C1005D330U840-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331426-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D330U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5418.5 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331426-840
CATALOG NUMBER: SA2XXDIP-C1005D330U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331426-840

CATALOG NUMBER: SA2XXDIP-C1005D330U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	98	98	98	88	88	88	80	80	80	76
1	104	99	95	91	98	94	91	88	86	83	80	78	76	74	70	69	67	64
2	94	87	80	75	89	83	77	72	75	71	67	68	65	62	62	59	57	53
3	86	76	68	62	82	73	66	60	66	61	56	60	56	52	55	51	48	45
4	79	68	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42	39
5	73	60	52	46	69	58	50	44	53	47	42	49	43	39	44	40	36	34
6	67	54	46	40	64	52	44	39	48	41	36	44	38	34	40	36	32	30
7	62	49	41	35	59	47	40	34	44	37	32	40	35	30	37	32	29	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	24
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23	21
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25987	25987	25987
5°	26086	25710	25861
10°	25932	25450	25576
15°	25611	25120	25095
20°	25156	24624	24598
25°	24704	24015	24015
30°	24121	23457	23256
35°	23580	22787	22450
40°	22898	22118	21692
45°	22229	21450	20922
50°	21499	20760	20022
55°	20738	19952	19212
60°	19888	18991	18290
65°	18980	18032	17207
70°	17825	16877	16074
75°	16220	15540	15159
80°	14393	13966	13240
85°	11745	11189	10022



TEST NUMBER: P331426-840

CATALOG NUMBER: SA2XXDIP-C1005D330U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.3	2.8
10°-20°	425.9	7.9
20°-30°	626.0	11.6
30°-40°	727.1	13.4
40°-50°	726.3	13.4
50°-60°	633.4	11.7
60°-70°	468.3	8.6
70°-80°	265.3	4.9
80°-90°	72.4	1.3
90°-100°	15.1	0.3
100°-110°	55.2	1.0
110°-120°	147.6	2.7
120°-130°	243.6	4.5
130°-140°	259.0	4.8
140°-150°	240.8	4.4
150°-160°	193.6	3.6
160°-170°	124.7	2.3
170°-180°	42.9	0.8
0°-30°	1203.2	22.2
0°-40°	1930.3	35.6
0°-60°	3290.0	60.7
0°-90°	4096.1	75.6
90°-120°	217.8	4.0
90°-150°	961.2	17.7
90°-180°	1322.0	24.4
0°-180°	5418.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1610	1610	1610	1610	1610	
5°	1610	1603	1586	1598	1596	153
15°	1532	1522	1503	1508	1501	431
25°	1387	1374	1348	1351	1348	638
35°	1196	1180	1156	1147	1139	747
45°	974	962	939	923	916	751
55°	737	727	709	691	682	658
65°	497	487	472	458	450	491
75°	260	257	249	241	243	278
85°	63	62	60	56	54	73
90°	0	4	7	8	9	4
95°	21	11	13	14	14	26
105°	99	104	20	23	25	106
115°	188	193	202	57	27	185
125°	266	270	276	278	279	237
135°	328	334	337	340	339	254
145°	381	381	386	388	387	238
155°	420	417	420	422	420	193
165°	442	440	441	443	441	125
175°	452	450	451	453	450	43
180°	451	451	451	451	451	



TEST NUMBER: P331426-840

CATALOG NUMBER: SA2XXDIP-C1005D330U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5
2.5°	1617.0	1615.6	1614.3	1612.9	1611.4	1609.3	1606.3	1603.3	1600.2	1597.2	1599.9
5°	1609.5	1608.2	1606.8	1605.4	1604.1	1601.4	1597.7	1593.9	1590.1	1586.3	1589.1
7.5°	1595.3	1593.2	1591.0	1588.9	1586.8	1583.8	1579.9	1576.1	1572.3	1568.4	1571.1
10°	1581.7	1579.3	1576.9	1574.5	1572.1	1568.8	1564.7	1560.5	1556.4	1552.3	1555.1
12.5°	1563.2	1560.9	1558.8	1556.7	1554.6	1551.5	1547.3	1543.2	1539.1	1535.0	1536.9
15°	1532.2	1530.1	1528.0	1526.0	1523.9	1520.7	1516.2	1511.7	1507.2	1502.8	1504.2
17.5°	1492.6	1490.5	1488.4	1486.3	1484.3	1481.0	1476.4	1471.9	1467.3	1462.9	1464.4
20°	1464.1	1462.0	1460.0	1457.8	1455.8	1452.4	1447.5	1442.8	1437.9	1433.1	1434.1
22.5°	1435.6	1432.7	1429.9	1426.9	1424.0	1420.4	1415.8	1411.3	1406.7	1402.2	1402.4
25°	1386.7	1383.9	1381.2	1378.5	1375.7	1371.4	1365.5	1359.7	1353.8	1348.0	1348.7
27.5°	1331.0	1328.5	1326.1	1323.5	1321.1	1317.6	1312.9	1308.3	1303.7	1299.1	1298.1
30°	1293.8	1291.1	1288.3	1285.6	1282.8	1278.9	1273.7	1268.6	1263.4	1258.2	1257.2
32.5°	1254.3	1252.0	1249.8	1247.6	1245.4	1241.6	1236.2	1230.7	1225.3	1219.8	1218.0
35°	1196.3	1192.9	1189.4	1186.0	1182.6	1178.1	1172.6	1167.1	1161.6	1156.1	1154.1
37.5°	1131.0	1128.0	1125.0	1122.0	1118.9	1114.7	1109.1	1103.7	1098.1	1092.7	1090.0
40°	1086.4	1083.7	1081.0	1078.2	1075.4	1071.4	1065.8	1060.4	1054.8	1049.4	1046.2
42.5°	1043.1	1040.4	1037.6	1034.9	1032.1	1027.9	1022.5	1016.9	1011.5	1005.9	1002.6
45°	973.5	971.1	968.7	966.2	963.8	960.1	954.9	949.8	944.6	939.4	935.6
47.5°	904.1	901.9	899.6	897.4	895.0	891.2	885.9	880.5	875.1	869.8	865.8
50°	855.9	854.1	852.4	850.7	849.0	845.7	840.9	836.1	831.2	826.5	821.6
52.5°	808.8	806.6	804.3	802.0	799.7	796.3	791.7	787.2	782.7	778.2	774.2
55°	736.7	734.6	732.6	730.5	728.4	725.3	721.2	717.1	713.0	708.8	704.7
57.5°	664.3	662.6	661.0	659.3	657.6	654.6	650.1	645.5	641.0	636.4	632.4
60°	615.9	614.6	613.2	611.9	610.5	607.3	602.6	597.7	592.9	588.1	584.3
62.5°	569.0	566.7	564.5	562.3	560.1	557.1	553.4	549.8	546.0	542.3	538.8
65°	496.8	494.7	492.7	490.6	488.6	485.7	482.3	478.9	475.4	472.0	469.0
67.5°	423.4	421.8	420.1	418.5	416.9	414.4	411.3	408.3	405.2	402.1	399.7
70°	377.6	376.3	374.9	373.5	372.1	369.9	366.8	363.7	360.6	357.5	355.1
72.5°	330.5	329.2	327.8	326.5	325.1	323.4	321.4	319.4	317.4	315.4	313.0
75°	260.0	259.3	258.6	257.9	257.2	256.0	254.3	252.6	250.9	249.1	247.1
77.5°	196.8	195.7	194.5	193.4	192.2	191.3	190.6	189.9	189.1	188.5	187.4
80°	154.8	154.4	154.1	153.7	153.4	152.9	152.2	151.5	150.8	150.2	149.1
82.5°	115.1	115.1	115.0	114.9	114.8	114.6	114.2	113.8	113.4	113.0	111.7
85°	63.4	63.1	62.8	62.4	62.1	61.7	61.4	61.0	60.7	60.4	59.3
87.5°	22.3	21.9	21.6	21.2	20.8	20.4	19.9	19.5	19.1	18.7	17.9
90°	0.3	1.1	1.9	2.7	3.5	4.2	4.7	5.4	6.0	6.6	6.9
92.5°	6.6	6.6	6.5	6.4	6.3	6.5	6.7	7.0	7.3	7.6	7.8
95°	21.2	18.8	16.5	14.0	11.6	10.7	11.2	11.7	12.2	12.7	13.1
97.5°	42.1	35.3	28.6	21.9	15.1	12.3	13.5	14.6	15.9	17.1	17.4
100°	57.8	47.9	37.9	28.0	18.1	13.6	14.9	16.2	17.4	18.6	19.2
102.5°	75.0	72.9	70.8	68.8	66.7	60.4	50.1	39.8	29.5	19.1	19.9
105°	99.3	101.4	103.6	105.8	108.0	99.2	79.4	59.6	39.7	19.9	20.7
107.5°	126.8	128.7	130.4	132.2	133.9	122.9	99.2	75.4	51.6	27.9	27.1
110°	144.6	146.1	147.7	149.3	150.8	141.0	120.1	99.1	78.1	57.2	49.9



TEST NUMBER: P331426-840

CATALOG NUMBER: SA2XXDIP-C1005D330U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	161.4	162.7	164.1	165.4	166.7	164.8	159.7	154.5	149.3	144.1	117.6
115°	187.7	188.9	190.3	191.5	192.7	194.2	196.0	197.8	199.7	201.5	167.8
117.5°	211.4	212.7	214.1	215.5	216.8	218.1	219.4	220.7	221.9	223.2	215.0
120°	228.5	229.6	230.8	231.9	232.9	234.1	235.4	236.7	238.0	239.3	240.2
122.5°	243.2	244.4	245.5	246.6	247.8	249.0	250.4	251.9	253.4	254.8	255.3
125°	265.5	266.4	267.3	268.3	269.2	270.4	271.8	273.2	274.5	275.9	276.4
127.5°	285.6	286.7	287.7	288.8	289.8	290.8	291.9	293.0	294.0	295.0	295.7
130°	298.4	299.6	300.7	301.9	303.1	304.1	304.9	305.7	306.5	307.3	308.0
132.5°	311.5	312.5	313.5	314.5	315.5	316.3	317.1	317.9	318.7	319.5	320.2
135°	328.5	329.6	330.8	331.9	333.2	334.1	334.7	335.4	336.0	336.7	337.4
137.5°	345.7	346.5	347.3	348.1	348.9	349.7	350.4	351.1	351.9	352.6	353.4
140°	356.9	357.5	358.0	358.6	359.2	359.9	360.7	361.5	362.3	363.0	363.8
142.5°	366.3	366.8	367.3	367.9	368.4	369.1	370.0	370.9	371.8	372.7	373.3
145°	381.0	381.0	380.9	380.8	380.7	381.3	382.5	383.8	385.1	386.3	386.8
147.5°	393.9	393.6	393.3	393.0	392.8	393.2	394.5	395.8	397.0	398.2	398.5
150°	402.2	401.7	401.2	400.7	400.2	400.6	401.7	402.9	404.0	405.3	405.7
152.5°	409.3	408.8	408.2	407.6	407.1	407.3	408.4	409.5	410.6	411.7	412.1
155°	419.6	418.9	418.3	417.6	417.0	417.1	418.0	418.8	419.7	420.5	421.0
157.5°	427.6	427.1	426.5	426.0	425.4	425.5	426.1	426.7	427.3	427.9	428.4
160°	432.3	431.9	431.4	431.0	430.6	430.6	431.0	431.4	431.9	432.3	432.7
162.5°	436.5	436.1	435.7	435.2	434.7	434.7	435.0	435.5	435.9	436.3	436.8
165°	442.1	441.7	441.2	440.8	440.4	440.3	440.5	440.7	440.9	441.1	441.6
167.5°	446.3	445.9	445.5	444.9	444.5	444.4	444.6	444.8	445.0	445.2	445.8
170°	448.7	448.2	447.8	447.4	446.9	446.8	446.9	447.1	447.2	447.4	447.9
172.5°	450.2	449.8	449.3	448.9	448.5	448.3	448.5	448.6	448.8	448.9	449.4
175°	452.2	451.7	451.2	450.7	450.2	450.0	450.2	450.3	450.5	450.6	451.1
177.5°	452.5	452.1	451.7	451.3	450.9	450.8	450.8	450.9	450.9	451.0	451.4
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331426-840

CATALOG NUMBER: SA2XXDIP-C1005D330U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5
2.5°	1602.7	1605.4	1608.2	1609.3	1608.7	1608.2	1607.6	1607.1
5°	1591.9	1594.6	1597.3	1598.4	1597.7	1597.0	1596.3	1595.6
7.5°	1573.9	1576.6	1579.4	1580.4	1579.6	1578.9	1578.1	1577.4
10°	1557.8	1560.5	1563.3	1564.2	1563.2	1562.1	1561.0	1560.0
12.5°	1538.8	1540.8	1542.7	1543.3	1542.5	1541.8	1541.0	1540.2
15°	1505.5	1506.9	1508.2	1508.1	1506.4	1504.7	1503.0	1501.3
17.5°	1466.0	1467.6	1469.2	1469.2	1467.4	1465.8	1464.2	1462.5
20°	1435.2	1436.2	1437.2	1437.0	1435.7	1434.3	1433.0	1431.6
22.5°	1402.6	1402.8	1403.0	1402.7	1401.9	1401.1	1400.2	1399.4
25°	1349.4	1350.1	1350.8	1350.8	1350.1	1349.4	1348.7	1348.0
27.5°	1297.1	1296.0	1294.9	1293.6	1292.0	1290.3	1288.7	1287.1
30°	1256.2	1255.2	1254.2	1252.9	1251.5	1250.1	1248.8	1247.4
32.5°	1216.2	1214.3	1212.4	1210.8	1209.4	1208.1	1206.7	1205.3
35°	1152.0	1149.9	1147.8	1146.0	1144.3	1142.6	1140.7	1139.0
37.5°	1087.5	1085.0	1082.5	1080.4	1078.7	1077.0	1075.4	1073.8
40°	1043.1	1040.1	1036.9	1034.7	1033.3	1032.0	1030.6	1029.2
42.5°	999.3	995.8	992.5	989.9	988.0	986.0	984.1	982.1
45°	931.9	928.1	924.3	921.7	920.3	919.0	917.6	916.3
47.5°	861.8	857.8	853.8	850.8	848.8	846.9	844.9	842.8
50°	816.8	812.0	807.2	804.0	802.2	800.5	798.8	797.1
52.5°	770.2	766.2	762.2	759.1	756.8	754.6	752.2	750.0
55°	700.5	696.4	692.4	689.4	687.7	686.0	684.3	682.5
57.5°	628.2	624.2	620.2	617.4	616.2	614.9	613.6	612.3
60°	580.6	576.7	573.0	570.6	569.6	568.6	567.4	566.4
62.5°	535.3	531.8	528.3	525.8	524.5	523.2	521.9	520.6
65°	465.9	462.7	459.7	457.3	455.6	453.8	452.1	450.4
67.5°	397.3	394.9	392.4	390.5	389.2	387.8	386.5	385.1
70°	352.6	350.3	347.9	346.0	344.6	343.3	341.8	340.5
72.5°	310.6	308.2	305.8	304.1	303.0	301.8	300.7	299.6
75°	245.1	243.0	241.0	240.2	241.0	241.6	242.3	243.0
77.5°	186.4	185.4	184.4	183.4	182.4	181.5	180.5	179.6
80°	148.0	147.0	146.0	145.1	144.4	143.8	143.1	142.4
82.5°	110.4	109.1	107.8	107.0	106.8	106.7	106.6	106.4
85°	58.3	57.3	56.2	55.5	55.2	54.8	54.5	54.1
87.5°	17.2	16.4	15.7	15.1	14.8	14.6	14.3	14.1
90°	7.3	7.6	8.0	8.3	8.4	8.5	8.7	8.8
92.5°	8.0	8.2	8.3	8.5	8.6	8.7	8.7	8.8
95°	13.4	13.8	14.1	14.3	14.2	14.1	14.1	14.0
97.5°	17.7	17.9	18.2	18.4	18.5	18.6	18.7	18.8
100°	19.8	20.4	20.9	21.3	21.4	21.6	21.7	21.9
102.5°	20.6	21.4	22.1	22.6	22.8	23.0	23.2	23.4
105°	21.5	22.3	23.1	23.6	23.9	24.2	24.5	24.8
107.5°	26.3	25.4	24.6	24.3	24.6	24.9	25.2	25.5
110°	42.6	35.3	28.1	24.6	24.9	25.2	25.5	25.8



TEST NUMBER: P331426-840

CATALOG NUMBER: SA2XXDIP-C1005D330U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	91.2	64.7	38.3	25.1	25.3	25.5	25.9	26.1
115°	134.3	100.7	67.1	47.7	42.4	37.3	32.0	26.8
117.5°	206.9	198.7	190.7	178.0	160.9	143.7	126.5	109.4
120°	241.1	242.0	242.8	238.3	228.5	218.7	208.9	199.1
122.5°	255.8	256.3	256.8	256.1	254.3	252.4	250.4	248.5
125°	276.9	277.4	277.9	278.3	278.5	278.7	278.9	279.1
127.5°	296.5	297.2	297.9	298.3	298.4	298.4	298.4	298.5
130°	308.8	309.6	310.4	310.8	310.7	310.6	310.6	310.5
132.5°	320.9	321.5	322.2	322.6	322.4	322.4	322.3	322.2
135°	338.1	338.8	339.5	339.8	339.7	339.5	339.4	339.2
137.5°	354.1	354.8	355.5	355.7	355.5	355.3	355.0	354.8
140°	364.4	365.1	365.7	365.9	365.5	365.2	364.8	364.4
142.5°	374.0	374.6	375.2	375.3	374.9	374.6	374.2	373.8
145°	387.3	387.8	388.3	388.4	388.0	387.7	387.3	386.9
147.5°	398.9	399.3	399.7	399.7	399.4	399.1	398.8	398.5
150°	406.1	406.5	407.0	407.0	406.7	406.3	405.9	405.6
152.5°	412.6	413.0	413.4	413.4	412.9	412.5	412.0	411.5
155°	421.4	421.8	422.3	422.2	421.6	421.1	420.5	419.9
157.5°	428.9	429.4	429.8	429.8	429.2	428.7	428.1	427.6
160°	433.2	433.6	434.0	434.0	433.5	433.0	432.5	432.0
162.5°	437.2	437.7	438.2	438.2	437.5	436.9	436.3	435.7
165°	442.1	442.6	443.1	443.1	442.6	442.1	441.6	441.1
167.5°	446.3	446.8	447.3	447.2	446.6	445.9	445.2	444.5
170°	448.4	448.9	449.4	449.3	448.7	448.0	447.4	446.7
172.5°	449.9	450.4	450.9	450.9	450.2	449.6	448.9	448.3
175°	451.6	452.1	452.6	452.5	451.8	451.1	450.3	449.6
177.5°	451.8	452.2	452.6	452.5	452.0	451.5	451.0	450.5
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2

(END OF REPORT)