

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331427-840

Luminaire Tested: **SA2XXDIP-C1005D330U840-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331427-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D330U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5278.8 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331427-840
CATALOG NUMBER: SA2XXDIP-C1005D330U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331427-840

CATALOG NUMBER: SA2XXDIP-C1005D330U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	108	108	108	108	99	99	99	90	90	90	81	81	81	78				78
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69	65				65
2	95	87	80	75	90	83	77	72	76	71	67	69	66	63	63	61	58	55				55
3	86	76	69	63	82	73	66	61	67	61	57	61	57	53	56	53	49	46				46
4	79	68	60	53	75	65	57	52	60	53	49	55	50	46	50	46	43	40				40
5	73	61	52	46	69	58	50	45	54	47	42	49	44	40	45	41	37	35				35
6	67	55	46	40	64	52	45	39	48	42	37	45	39	35	41	37	33	30				30
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	38	33	29	27				27
8	58	45	37	31	55	43	36	31	40	34	29	37	32	28	35	30	26	24				24
9	54	41	33	28	52	40	33	28	37	31	26	34	29	25	32	27	24	22				22
10	51	38	31	25	48	37	30	25	34	28	24	32	27	23	30	25	22	20				20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25987	25987	25987
5°	26086	25710	25861
10°	25932	25450	25576
15°	25611	25120	25095
20°	25156	24624	24598
25°	24704	24015	24015
30°	24121	23457	23256
35°	23580	22787	22450
40°	22898	22118	21692
45°	22229	21450	20922
50°	21499	20760	20022
55°	20738	19952	19212
60°	19888	18991	18290
65°	18980	18032	17207
70°	17825	16877	16074
75°	16220	15540	15159
80°	14393	13966	13240
85°	11745	11189	10022



TEST NUMBER: P331427-840

CATALOG NUMBER: SA2XXDIP-C1005D330U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.3	2.9
10°-20°	425.9	8.1
20°-30°	626.0	11.9
30°-40°	727.1	13.8
40°-50°	726.3	13.8
50°-60°	633.4	12.0
60°-70°	468.3	8.9
70°-80°	265.3	5.0
80°-90°	73.0	1.4
90°-100°	26.8	0.5
100°-110°	83.2	1.6
110°-120°	142.2	2.7
120°-130°	187.0	3.5
130°-140°	209.9	4.0
140°-150°	205.8	3.9
150°-160°	172.7	3.3
160°-170°	114.5	2.2
170°-180°	40.0	0.8
0°-30°	1203.2	22.8
0°-40°	1930.3	36.6
0°-60°	3290.0	62.3
0°-90°	4096.6	77.6
90°-120°	252.2	4.8
90°-150°	855.0	16.2
90°-180°	1182.0	22.4
0°-180°	5278.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1610	1610	1610	1610	1610	
5°	1610	1603	1586	1598	1596	153
15°	1532	1522	1503	1508	1501	431
25°	1387	1374	1348	1351	1348	638
35°	1196	1180	1156	1147	1139	747
45°	974	962	939	923	916	751
55°	737	727	709	691	682	658
65°	497	487	472	458	450	491
75°	260	257	249	241	243	278
85°	63	62	60	56	54	73
90°	0	5	12	12	12	4
95°	19	22	23	23	22	21
105°	77	78	78	79	79	81
115°	143	145	144	144	143	141
125°	208	211	210	209	208	185
135°	269	272	273	273	272	207
145°	326	329	331	331	330	204
155°	373	374	375	377	376	172
165°	406	405	405	408	406	114
175°	422	421	420	422	421	40
180°	423	423	423	423	423	



TEST NUMBER: P331427-840

CATALOG NUMBER: SA2XXDIP-C1005D330U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5
2.5°	1617.0	1615.6	1614.3	1612.9	1611.4	1609.3	1606.3	1603.3	1600.2	1597.2	1599.9
5°	1609.5	1608.2	1606.8	1605.4	1604.1	1601.4	1597.7	1593.9	1590.1	1586.3	1589.1
7.5°	1595.3	1593.2	1591.0	1588.9	1586.8	1583.8	1579.9	1576.1	1572.3	1568.4	1571.1
10°	1581.7	1579.3	1576.9	1574.5	1572.1	1568.8	1564.7	1560.5	1556.4	1552.3	1555.1
12.5°	1563.2	1560.9	1558.8	1556.7	1554.6	1551.5	1547.3	1543.2	1539.1	1535.0	1536.9
15°	1532.2	1530.1	1528.0	1526.0	1523.9	1520.7	1516.2	1511.7	1507.2	1502.8	1504.2
17.5°	1492.6	1490.5	1488.4	1486.3	1484.3	1481.0	1476.4	1471.9	1467.3	1462.9	1464.4
20°	1464.1	1462.0	1460.0	1457.8	1455.8	1452.4	1447.5	1442.8	1437.9	1433.1	1434.1
22.5°	1435.6	1432.7	1429.9	1426.9	1424.0	1420.4	1415.8	1411.3	1406.7	1402.2	1402.4
25°	1386.7	1383.9	1381.2	1378.5	1375.7	1371.4	1365.5	1359.7	1353.8	1348.0	1348.7
27.5°	1331.0	1328.5	1326.1	1323.5	1321.1	1317.6	1312.9	1308.3	1303.7	1299.1	1298.1
30°	1293.8	1291.1	1288.3	1285.6	1282.8	1278.9	1273.7	1268.6	1263.4	1258.2	1257.2
32.5°	1254.3	1252.0	1249.8	1247.6	1245.4	1241.6	1236.2	1230.7	1225.3	1219.8	1218.0
35°	1196.3	1192.9	1189.4	1186.0	1182.6	1178.1	1172.6	1167.1	1161.6	1156.1	1154.1
37.5°	1131.0	1128.0	1125.0	1122.0	1118.9	1114.7	1109.1	1103.7	1098.1	1092.7	1090.0
40°	1086.4	1083.7	1081.0	1078.2	1075.4	1071.4	1065.8	1060.4	1054.8	1049.4	1046.2
42.5°	1043.1	1040.4	1037.6	1034.9	1032.1	1027.9	1022.5	1016.9	1011.5	1005.9	1002.6
45°	973.5	971.1	968.7	966.2	963.8	960.1	954.9	949.8	944.6	939.4	935.6
47.5°	904.1	901.9	899.6	897.4	895.0	891.2	885.9	880.5	875.1	869.8	865.8
50°	855.9	854.1	852.4	850.7	849.0	845.7	840.9	836.1	831.2	826.5	821.6
52.5°	808.8	806.6	804.3	802.0	799.7	796.3	791.7	787.2	782.7	778.2	774.2
55°	736.7	734.6	732.6	730.5	728.4	725.3	721.2	717.1	713.0	708.8	704.7
57.5°	664.3	662.6	661.0	659.3	657.6	654.6	650.1	645.5	641.0	636.4	632.4
60°	615.9	614.6	613.2	611.9	610.5	607.3	602.6	597.7	592.9	588.1	584.3
62.5°	569.0	566.7	564.5	562.3	560.1	557.1	553.4	549.8	546.0	542.3	538.8
65°	496.8	494.7	492.7	490.6	488.6	485.7	482.3	478.9	475.4	472.0	469.0
67.5°	423.4	421.8	420.1	418.5	416.9	414.4	411.3	408.3	405.2	402.1	399.7
70°	377.6	376.3	374.9	373.5	372.1	369.9	366.8	363.7	360.6	357.5	355.1
72.5°	330.5	329.2	327.8	326.5	325.1	323.4	321.4	319.4	317.4	315.4	313.0
75°	260.0	259.3	258.6	257.9	257.2	256.0	254.3	252.6	250.9	249.1	247.1
77.5°	196.8	195.7	194.5	193.4	192.2	191.3	190.6	189.9	189.1	188.5	187.4
80°	154.8	154.4	154.1	153.7	153.4	152.9	152.2	151.5	150.8	150.2	149.1
82.5°	115.1	115.1	115.0	114.9	114.8	114.6	114.2	113.8	113.4	113.0	111.7
85°	63.4	63.1	62.8	62.4	62.1	61.7	61.4	61.0	60.7	60.4	59.3
87.5°	22.3	22.0	21.6	21.3	20.9	20.6	20.4	20.2	20.0	19.8	19.0
90°	0.4	1.3	2.2	3.2	4.1	5.6	7.3	9.0	10.7	12.5	12.3
92.5°	6.4	7.1	7.8	8.5	9.2	9.7	10.1	10.5	10.9	11.3	11.4
95°	18.6	19.4	20.1	20.9	21.7	22.2	22.3	22.5	22.7	22.8	22.8
97.5°	33.9	34.6	35.2	36.0	36.7	37.2	37.5	37.8	38.1	38.4	38.4
100°	45.3	45.9	46.6	47.3	47.9	48.3	48.5	48.8	49.0	49.3	49.3
102.5°	57.3	57.8	58.3	58.8	59.3	59.8	60.0	60.3	60.6	60.9	61.0
105°	76.7	77.0	77.2	77.5	77.7	77.9	78.1	78.2	78.4	78.5	78.7
107.5°	96.2	96.6	96.9	97.4	97.7	97.9	97.9	97.9	97.9	97.9	97.9
110°	108.9	109.3	109.8	110.3	110.7	111.0	111.0	111.0	111.0	111.0	111.0



TEST NUMBER: P331427-840

CATALOG NUMBER: SA2XXDIP-C1005D330U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	122.5	123.0	123.5	123.9	124.4	124.6	124.5	124.5	124.4	124.4	124.2
115°	142.7	143.2	143.7	144.1	144.6	144.8	144.6	144.4	144.3	144.1	144.1
117.5°	162.8	163.5	164.1	164.7	165.4	165.5	165.0	164.6	164.1	163.7	163.5
120°	176.2	176.9	177.5	178.1	178.7	178.7	178.1	177.5	176.9	176.2	176.2
122.5°	188.5	189.2	190.1	190.8	191.6	191.8	191.3	190.9	190.4	190.0	189.8
125°	207.6	208.3	209.0	209.7	210.5	210.8	210.5	210.3	210.1	209.7	209.5
127.5°	226.3	227.2	228.1	228.9	229.8	230.1	229.9	229.6	229.3	229.0	228.7
130°	238.0	239.0	240.0	241.1	242.1	242.6	242.4	242.3	242.1	241.9	241.8
132.5°	251.2	252.0	252.8	253.6	254.5	254.9	254.9	255.0	255.0	255.0	254.7
135°	268.6	269.5	270.4	271.2	272.2	272.7	272.9	273.0	273.2	273.3	273.2
137.5°	287.1	287.8	288.5	289.3	290.0	290.4	290.6	290.8	291.0	291.2	291.2
140°	298.3	299.0	299.7	300.4	301.1	301.6	302.1	302.5	302.9	303.3	303.3
142.5°	309.7	310.4	311.1	311.8	312.6	313.1	313.3	313.6	313.9	314.1	314.2
145°	326.1	326.7	327.2	327.8	328.3	328.8	329.3	329.8	330.2	330.7	330.8
147.5°	340.7	341.4	342.0	342.7	343.4	343.9	344.2	344.6	344.9	345.2	345.4
150°	350.7	351.2	351.6	352.1	352.6	353.0	353.4	353.7	354.0	354.3	354.6
152.5°	359.6	360.0	360.5	361.0	361.4	361.9	362.2	362.6	363.0	363.5	363.8
155°	372.8	373.0	373.3	373.5	373.8	374.1	374.3	374.5	374.8	375.0	375.4
157.5°	384.2	384.4	384.5	384.7	384.9	385.0	385.2	385.3	385.4	385.6	386.1
160°	391.0	391.2	391.3	391.5	391.6	391.8	391.8	391.9	392.0	392.1	392.5
162.5°	397.3	397.4	397.4	397.4	397.5	397.5	397.6	397.7	397.8	397.8	398.4
165°	405.7	405.6	405.5	405.5	405.4	405.3	405.3	405.3	405.3	405.3	405.9
167.5°	412.6	412.4	412.2	411.9	411.7	411.6	411.5	411.5	411.5	411.5	412.0
170°	416.4	416.2	415.9	415.7	415.5	415.3	415.2	415.1	415.1	415.0	415.5
172.5°	418.9	418.7	418.5	418.2	418.0	417.8	417.8	417.7	417.6	417.5	418.1
175°	422.1	421.8	421.6	421.3	421.1	420.9	420.8	420.6	420.4	420.3	420.8
177.5°	423.3	423.1	422.9	422.8	422.6	422.4	422.3	422.2	422.0	421.9	422.3
180°	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8



TEST NUMBER: P331427-840

CATALOG NUMBER: SA2XXDIP-C1005D330U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5
2.5°	1602.7	1605.4	1608.2	1609.3	1608.7	1608.2	1607.6	1607.1
5°	1591.9	1594.6	1597.3	1598.4	1597.7	1597.0	1596.3	1595.6
7.5°	1573.9	1576.6	1579.4	1580.4	1579.6	1578.9	1578.1	1577.4
10°	1557.8	1560.5	1563.3	1564.2	1563.2	1562.1	1561.0	1560.0
12.5°	1538.8	1540.8	1542.7	1543.3	1542.5	1541.8	1541.0	1540.2
15°	1505.5	1506.9	1508.2	1508.1	1506.4	1504.7	1503.0	1501.3
17.5°	1466.0	1467.6	1469.2	1469.2	1467.4	1465.8	1464.2	1462.5
20°	1435.2	1436.2	1437.2	1437.0	1435.7	1434.3	1433.0	1431.6
22.5°	1402.6	1402.8	1403.0	1402.7	1401.9	1401.1	1400.2	1399.4
25°	1349.4	1350.1	1350.8	1350.8	1350.1	1349.4	1348.7	1348.0
27.5°	1297.1	1296.0	1294.9	1293.6	1292.0	1290.3	1288.7	1287.1
30°	1256.2	1255.2	1254.2	1252.9	1251.5	1250.1	1248.8	1247.4
32.5°	1216.2	1214.3	1212.4	1210.8	1209.4	1208.1	1206.7	1205.3
35°	1152.0	1149.9	1147.8	1146.0	1144.3	1142.6	1140.7	1139.0
37.5°	1087.5	1085.0	1082.5	1080.4	1078.7	1077.0	1075.4	1073.8
40°	1043.1	1040.1	1036.9	1034.7	1033.3	1032.0	1030.6	1029.2
42.5°	999.3	995.8	992.5	989.9	988.0	986.0	984.1	982.1
45°	931.9	928.1	924.3	921.7	920.3	919.0	917.6	916.3
47.5°	861.8	857.8	853.8	850.8	848.8	846.9	844.9	842.8
50°	816.8	812.0	807.2	804.0	802.2	800.5	798.8	797.1
52.5°	770.2	766.2	762.2	759.1	756.8	754.6	752.2	750.0
55°	700.5	696.4	692.4	689.4	687.7	686.0	684.3	682.5
57.5°	628.2	624.2	620.2	617.4	616.2	614.9	613.6	612.3
60°	580.6	576.7	573.0	570.6	569.6	568.6	567.4	566.4
62.5°	535.3	531.8	528.3	525.8	524.5	523.2	521.9	520.6
65°	465.9	462.7	459.7	457.3	455.6	453.8	452.1	450.4
67.5°	397.3	394.9	392.4	390.5	389.2	387.8	386.5	385.1
70°	352.6	350.3	347.9	346.0	344.6	343.3	341.8	340.5
72.5°	310.6	308.2	305.8	304.1	303.0	301.8	300.7	299.6
75°	245.1	243.0	241.0	240.2	241.0	241.6	242.3	243.0
77.5°	186.4	185.4	184.4	183.4	182.4	181.5	180.5	179.6
80°	148.0	147.0	146.0	145.1	144.4	143.8	143.1	142.4
82.5°	110.4	109.1	107.8	107.0	106.8	106.7	106.6	106.4
85°	58.3	57.3	56.2	55.5	55.2	54.8	54.5	54.1
87.5°	18.1	17.3	16.4	15.9	15.6	15.3	15.0	14.8
90°	12.2	12.0	11.8	11.8	11.9	12.0	12.0	12.1
92.5°	11.4	11.4	11.5	11.5	11.5	11.5	11.5	11.5
95°	22.8	22.8	22.8	22.7	22.6	22.4	22.3	22.1
97.5°	38.4	38.4	38.4	38.4	38.4	38.4	38.4	38.3
100°	49.3	49.3	49.3	49.2	49.1	49.1	49.0	48.9
102.5°	61.1	61.1	61.2	61.2	61.1	61.0	61.0	60.9
105°	78.8	79.0	79.2	79.2	79.2	79.2	79.2	79.2
107.5°	98.0	98.1	98.1	98.0	97.6	97.3	96.8	96.4
110°	111.0	111.0	111.0	110.9	110.6	110.4	110.2	109.9



TEST NUMBER: P331427-840

CATALOG NUMBER: SA2XXDIP-C1005D330U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	124.0	123.8	123.6	123.4	123.3	123.1	122.9	122.7
115°	144.0	143.9	143.8	143.7	143.4	143.2	143.0	142.7
117.5°	163.3	163.1	162.9	162.7	162.5	162.3	162.0	161.8
120°	176.2	176.2	176.2	176.1	175.9	175.6	175.4	175.2
122.5°	189.6	189.3	189.1	189.0	188.8	188.6	188.4	188.3
125°	209.3	209.0	208.8	208.6	208.6	208.5	208.4	208.3
127.5°	228.5	228.2	227.9	227.6	227.4	227.1	226.9	226.6
130°	241.6	241.5	241.3	241.1	240.8	240.3	240.0	239.7
132.5°	254.3	254.0	253.7	253.4	253.1	252.9	252.6	252.4
135°	273.2	273.1	273.0	272.9	272.6	272.4	272.2	271.9
137.5°	291.1	291.0	291.0	290.8	290.5	290.2	289.9	289.5
140°	303.3	303.3	303.3	303.1	302.8	302.5	302.2	301.8
142.5°	314.3	314.3	314.4	314.3	314.0	313.6	313.3	313.0
145°	330.9	330.9	331.0	330.9	330.6	330.3	330.0	329.6
147.5°	345.5	345.7	345.9	345.8	345.5	345.2	344.9	344.6
150°	354.8	355.0	355.3	355.3	355.0	354.8	354.6	354.3
152.5°	364.1	364.4	364.7	364.7	364.4	364.1	363.8	363.5
155°	375.8	376.2	376.6	376.7	376.4	376.2	376.0	375.7
157.5°	386.6	387.2	387.7	387.8	387.4	387.0	386.7	386.3
160°	393.0	393.5	394.0	394.0	393.7	393.4	393.1	392.8
162.5°	398.9	399.4	400.0	400.0	399.7	399.3	398.9	398.5
165°	406.4	407.0	407.5	407.6	407.2	406.8	406.4	406.1
167.5°	412.6	413.1	413.7	413.8	413.4	412.9	412.5	412.1
170°	416.1	416.6	417.2	417.2	416.8	416.3	415.8	415.3
172.5°	418.6	419.2	419.7	419.8	419.3	418.8	418.4	417.9
175°	421.4	421.9	422.5	422.5	422.1	421.6	421.1	420.6
177.5°	422.7	423.0	423.4	423.4	423.0	422.7	422.3	421.9
180°	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8

(END OF REPORT)