

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332615-927

Luminaire Tested: **SA4XXDIP-C795D1035U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332615-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C795D1035U927-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5628.4 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332615-927

CATALOG NUMBER: SA4XXDIP-C795D1035U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332615-927

CATALOG NUMBER: SA4XXDIP-C795D1035U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48	
1	97	93	89	86	89	86	82	79	72	70	67	59	58	56	48	47	46	40	40	40	40	
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38	34	34	34	34	
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33	29	29	29	29	
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28	25	25	25	25	
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25	21	21	21	21	
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19	19	19	19	
7	58	45	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19	17	17	17	17	
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15	15	15	15	
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	13	13	13	13	
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14	12	12	12	12	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8490	8490	8490
5°	8515	8413	8474
10°	8461	8344	8385
15°	8359	8226	8247
20°	8223	8079	8086
25°	8068	7911	7888
30°	7879	7713	7643
35°	7681	7508	7407
40°	7477	7273	7140
45°	7263	7042	6907
50°	7027	6836	6625
55°	6773	6570	6356
60°	6516	6273	6082
65°	6229	5989	5746
70°	5908	5611	5391
75°	5415	5153	5022
80°	4816	4621	4505
85°	4215	4057	3974



TEST NUMBER: P332615-927

CATALOG NUMBER: SA4XXDIP-C795D1035U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.0	1.8
10°-20°	279.0	5.0
20°-30°	410.7	7.3
30°-40°	477.4	8.5
40°-50°	477.5	8.5
50°-60°	417.6	7.4
60°-70°	310.2	5.5
70°-80°	176.2	3.1
80°-90°	53.1	0.9
90°-100°	290.8	5.2
100°-110°	605.1	10.8
110°-120°	542.0	9.6
120°-130°	455.9	8.1
130°-140°	380.1	6.8
140°-150°	290.4	5.2
150°-160°	204.1	3.6
160°-170°	120.1	2.1
170°-180°	39.1	0.7
0°-30°	788.7	14.0
0°-40°	1266.2	22.5
0°-60°	2161.3	38.4
0°-90°	2700.8	48.0
90°-120°	1437.9	25.5
90°-150°	2564.4	45.6
90°-180°	2928.0	52.0
0°-180°	5628.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1052	1052	1052	1052	1052	
5°	1051	1047	1038	1047	1046	100
15°	1000	996	984	989	987	282
25°	906	900	888	889	886	417
35°	779	773	762	756	752	487
45°	636	630	617	608	605	490
55°	481	478	467	457	452	431
65°	326	322	314	305	301	323
75°	174	169	165	162	161	184
85°	46	45	44	44	43	50
90°	1	6	14	16	17	4
95°	26	82	644	319	193	29
105°	92	134	519	1117	1113	99
115°	163	204	463	889	1068	162
125°	227	270	460	756	852	202
135°	270	321	456	671	762	208
145°	311	356	454	566	622	195
155°	354	382	441	500	521	163
165°	385	397	423	448	455	109
175°	402	402	406	411	410	38
180°	402	402	402	402	402	



TEST NUMBER: P332615-927

CATALOG NUMBER: SA4XXDIP-C795D1035U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6
2.5°	1054.3	1053.8	1053.4	1053.0	1052.5	1051.5	1049.8	1048.1	1046.5	1044.9	1046.3
5°	1050.8	1050.0	1049.2	1048.5	1047.7	1046.3	1044.3	1042.2	1040.1	1038.1	1040.1
7.5°	1041.0	1040.2	1039.5	1038.7	1038.0	1036.5	1034.2	1031.9	1029.6	1027.3	1029.0
10°	1032.2	1031.5	1030.7	1030.0	1029.2	1027.6	1025.2	1022.8	1020.3	1017.9	1019.4
12.5°	1020.7	1020.0	1019.2	1018.5	1017.8	1016.1	1013.5	1010.9	1008.4	1005.8	1007.4
15°	1000.2	999.4	998.7	997.9	997.2	995.5	992.6	989.8	987.0	984.2	985.3
17.5°	975.4	974.5	973.5	972.6	971.7	969.9	967.3	964.6	961.9	959.3	960.0
20°	957.2	956.2	955.4	954.4	953.5	951.6	948.8	945.9	943.2	940.4	941.0
22.5°	937.7	936.4	935.2	934.0	932.7	930.7	927.9	925.1	922.3	919.5	920.5
25°	905.8	904.5	903.2	901.9	900.6	898.6	896.0	893.3	890.7	888.1	888.3
27.5°	869.4	868.1	866.7	865.4	864.0	862.1	859.7	857.3	854.8	852.4	851.9
30°	845.2	843.7	842.2	840.7	839.2	837.2	834.7	832.3	829.9	827.4	826.7
32.5°	819.5	818.2	816.8	815.5	814.1	812.1	809.6	807.0	804.5	801.8	801.0
35°	779.4	778.1	776.8	775.5	774.2	772.2	769.6	767.0	764.4	761.8	760.4
37.5°	737.1	735.9	734.7	733.6	732.3	730.3	727.5	724.7	721.9	719.1	717.6
40°	709.5	708.0	706.5	705.0	703.5	701.3	698.5	695.7	692.9	690.1	688.2
42.5°	679.9	678.9	678.0	677.2	676.2	674.2	671.1	668.0	664.9	661.8	659.7
45°	636.2	634.9	633.6	632.2	631.0	628.8	625.8	622.8	619.8	616.8	614.7
47.5°	590.5	589.6	588.7	587.8	586.9	585.1	582.3	579.6	576.8	574.0	571.6
50°	559.5	558.7	558.0	557.2	556.5	554.8	552.2	549.6	546.9	544.3	541.7
52.5°	529.2	528.3	527.4	526.5	525.5	523.7	520.9	518.2	515.4	512.6	510.3
55°	481.2	480.5	480.0	479.4	478.9	477.3	474.7	472.1	469.4	466.8	464.5
57.5°	435.3	434.7	434.0	433.4	432.8	431.1	428.6	426.0	423.4	420.8	418.7
60°	403.6	402.7	401.7	400.8	399.9	398.2	395.8	393.3	390.9	388.5	386.7
62.5°	372.6	371.9	371.1	370.3	369.5	367.8	365.2	362.6	360.0	357.4	355.9
65°	326.1	325.2	324.2	323.3	322.3	320.9	319.1	317.2	315.3	313.5	311.6
67.5°	279.2	278.4	277.5	276.6	275.8	274.5	272.7	270.8	269.1	267.3	265.5
70°	250.3	249.0	247.6	246.3	245.0	243.6	242.1	240.6	239.1	237.7	236.1
72.5°	219.3	217.9	216.7	215.3	214.0	212.8	211.6	210.3	209.1	207.9	206.8
75°	173.6	172.6	171.7	170.8	169.8	168.9	167.9	167.0	166.1	165.2	164.4
77.5°	129.9	129.5	129.1	128.7	128.3	127.7	126.8	126.0	125.2	124.4	124.1
80°	103.6	103.1	102.5	102.0	101.4	100.9	100.5	100.2	99.8	99.4	99.0
82.5°	78.0	77.8	77.5	77.2	77.0	76.8	76.8	76.7	76.6	76.5	76.3
85°	45.5	45.5	45.5	45.5	45.5	45.3	44.9	44.6	44.2	43.8	43.8
87.5°	17.7	17.8	18.1	18.2	18.2	18.1	18.9	18.7	18.9	19.0	18.9
90°	0.8	2.4	4.8	5.5	6.3	6.3	11.1	11.1	12.7	14.3	13.5
92.5°	9.0	13.2	20.6	30.2	41.7	58.2	98.4	159.8	219.5	250.9	209.0
95°	26.1	28.4	36.4	46.7	65.7	98.9	167.6	297.4	486.4	644.5	662.7
97.5°	46.8	46.8	53.6	63.1	79.4	107.3	160.3	267.3	455.2	678.8	832.6
100°	60.1	60.1	65.7	75.1	90.2	115.5	162.2	251.5	412.8	635.8	838.3
102.5°	72.7	74.0	78.9	87.8	102.2	126.2	168.4	247.1	384.4	582.1	790.8
105°	92.5	94.9	98.9	108.4	122.6	145.5	183.5	249.1	359.8	518.8	704.6
107.5°	114.4	116.0	119.9	130.0	143.6	166.2	201.1	260.8	355.4	483.4	635.0
110°	128.9	130.5	134.4	143.9	158.2	179.5	214.3	269.7	356.6	471.3	600.2



TEST NUMBER: P332615-927

CATALOG NUMBER: SA4XXDIP-C795D1035U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	142.8	144.4	149.0	157.9	172.1	193.5	227.0	279.2	360.4	465.6	580.7
115°	163.0	165.2	170.8	178.7	193.8	215.1	246.8	294.2	367.7	462.6	562.3
117.5°	183.8	186.0	190.9	199.6	213.7	235.8	265.9	309.5	375.5	461.8	554.1
120°	197.7	199.3	204.9	213.5	227.0	249.1	279.2	320.3	381.2	461.8	549.6
122.5°	210.4	211.9	217.5	225.5	240.3	261.7	291.8	330.4	386.9	461.2	544.5
125°	227.0	230.1	234.9	243.6	258.6	280.7	309.2	345.6	395.5	460.3	536.2
127.5°	241.7	244.2	249.9	259.8	275.5	297.9	325.3	358.7	402.2	458.5	525.0
130°	249.9	253.1	259.4	271.2	286.3	309.2	336.1	366.9	407.3	457.9	518.0
132.5°	258.1	260.6	268.9	280.1	296.4	318.1	345.0	375.2	411.7	457.2	511.7
135°	269.7	272.8	280.7	294.2	310.8	331.4	357.4	386.0	418.4	456.3	502.2
137.5°	281.2	284.2	292.9	305.7	323.0	342.6	366.9	393.6	422.3	456.1	493.9
140°	289.5	291.8	300.6	313.9	330.6	349.6	373.3	398.5	425.5	455.5	489.6
142.5°	298.3	300.7	308.7	321.5	337.5	355.8	379.0	402.3	428.0	455.5	485.8
145°	310.8	313.1	321.1	332.2	347.2	364.6	385.2	406.5	429.4	453.9	479.3
147.5°	324.9	325.7	332.6	344.0	356.5	372.2	391.5	410.1	430.2	451.1	473.4
150°	333.7	334.5	340.9	350.4	362.2	377.2	394.7	412.0	430.2	449.2	469.0
152.5°	342.0	342.1	348.5	357.3	367.9	381.7	397.2	413.3	429.0	446.0	463.9
155°	353.5	354.3	359.0	366.9	375.7	387.5	400.9	414.4	427.1	441.3	456.3
157.5°	364.7	364.7	369.2	375.3	382.9	392.3	403.6	414.4	425.0	436.4	448.5
160°	371.7	371.7	374.9	380.4	386.7	395.5	404.9	414.4	423.1	432.6	442.9
162.5°	378.0	377.4	379.9	384.8	390.5	397.4	406.2	414.4	421.2	428.8	437.8
165°	385.2	385.2	386.7	390.7	394.7	399.3	406.5	412.8	417.6	423.1	429.4
167.5°	392.3	391.5	392.3	395.3	397.5	401.1	406.3	410.9	413.8	417.4	421.8
170°	395.5	394.7	395.5	397.8	399.3	401.7	405.7	409.6	411.2	413.6	416.8
172.5°	398.5	397.8	397.9	399.7	400.6	402.3	405.0	408.4	408.7	409.8	412.3
175°	401.7	400.9	400.9	401.7	402.5	402.5	404.1	406.5	405.7	405.7	407.3
177.5°	403.1	402.5	401.9	402.5	402.5	402.5	403.1	404.4	403.1	403.1	403.8
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332615-927

CATALOG NUMBER: SA4XXDIP-C795D1035U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6
2.5°	1047.8	1049.3	1050.8	1051.5	1051.4	1051.2	1051.1	1050.9
5°	1042.2	1044.3	1046.3	1047.2	1046.8	1046.5	1046.1	1045.7
7.5°	1030.6	1032.3	1033.9	1034.6	1034.4	1034.2	1034.0	1033.7
10°	1020.9	1022.4	1023.9	1024.5	1024.1	1023.7	1023.3	1022.9
12.5°	1009.1	1010.7	1012.3	1012.9	1012.4	1011.9	1011.3	1010.8
15°	986.4	987.5	988.6	989.0	988.4	987.9	987.3	986.7
17.5°	960.7	961.4	962.1	962.3	961.9	961.5	961.2	960.8
20°	941.5	942.1	942.6	942.7	942.3	942.0	941.6	941.2
22.5°	921.5	922.5	923.5	923.7	923.0	922.3	921.6	921.0
25°	888.5	888.7	888.9	888.6	887.9	887.1	886.4	885.6
27.5°	851.5	851.0	850.6	849.9	849.0	848.0	847.1	846.1
30°	825.9	825.2	824.4	823.6	822.7	821.7	820.8	819.9
32.5°	800.0	799.2	798.3	797.3	796.4	795.4	794.5	793.6
35°	759.1	757.8	756.5	755.3	754.4	753.5	752.6	751.6
37.5°	716.2	714.8	713.4	712.1	710.8	709.6	708.4	707.1
40°	686.3	684.5	682.6	681.2	680.2	679.4	678.4	677.5
42.5°	657.4	655.3	653.1	651.7	651.1	650.5	649.8	649.2
45°	612.7	610.6	608.6	607.3	606.7	606.1	605.5	605.0
47.5°	569.3	567.0	564.7	562.8	561.4	560.0	558.6	557.1
50°	539.1	536.5	533.9	532.0	530.8	529.7	528.6	527.5
52.5°	508.0	505.6	503.4	501.5	500.1	498.7	497.3	495.8
55°	462.3	460.1	457.8	456.1	455.0	453.9	452.7	451.6
57.5°	416.5	414.4	412.3	410.7	409.6	408.4	407.4	406.3
60°	385.1	383.4	381.7	380.4	379.5	378.5	377.6	376.7
62.5°	354.3	352.8	351.3	350.1	349.1	348.2	347.3	346.3
65°	309.7	307.8	305.9	304.6	303.6	302.7	301.7	300.8
67.5°	263.7	261.9	260.1	259.0	258.8	258.6	258.3	258.0
70°	234.6	233.1	231.6	230.6	230.0	229.5	228.9	228.4
72.5°	205.6	204.4	203.2	202.3	201.7	201.1	200.6	200.0
75°	163.7	162.9	162.2	161.7	161.5	161.3	161.1	161.0
77.5°	123.9	123.7	123.5	123.1	122.6	122.2	121.7	121.2
80°	98.7	98.3	97.9	97.7	97.4	97.3	97.1	96.9
82.5°	76.0	75.8	75.6	75.4	75.3	75.0	74.9	74.6
85°	43.8	43.8	43.8	43.7	43.6	43.3	43.2	42.9
87.5°	19.0	19.2	19.3	19.3	19.5	19.6	19.5	19.5
90°	14.3	15.1	15.8	15.8	16.6	17.4	16.6	16.6
92.5°	155.3	116.9	93.0	77.2	67.9	63.6	60.9	60.9
95°	586.0	463.4	357.4	280.7	242.0	217.5	203.3	193.0
97.5°	865.9	820.2	742.9	660.4	603.6	556.0	532.3	515.8
100°	953.8	969.6	930.8	872.3	803.5	755.3	731.5	725.2
102.5°	949.4	1027.8	1039.0	1014.6	972.4	937.5	912.5	907.4
105°	885.7	1022.5	1100.8	1133.3	1134.9	1128.5	1117.5	1112.7
107.5°	795.4	941.1	1051.4	1121.9	1160.9	1179.0	1186.9	1189.0
110°	741.0	877.8	992.5	1079.5	1135.7	1168.9	1183.1	1190.3



TEST NUMBER: P332615-927

CATALOG NUMBER: SA4XXDIP-C795D1035U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	701.2	822.1	930.5	1017.5	1081.2	1121.4	1141.4	1152.9
115°	661.2	758.4	851.0	926.9	989.4	1036.8	1062.1	1068.4
117.5°	641.5	722.1	794.8	859.2	912.5	952.4	977.9	982.9
120°	632.6	706.2	769.5	825.6	870.7	905.5	926.1	934.8
122.5°	625.1	696.1	753.7	802.9	841.0	870.7	888.1	896.8
125°	612.1	680.1	734.7	778.2	809.8	832.7	847.8	852.5
127.5°	596.3	661.3	715.7	757.0	788.8	809.2	821.8	826.6
130°	583.7	646.1	699.9	741.8	774.2	794.0	806.7	811.4
132.5°	570.4	629.1	681.5	723.5	755.3	777.5	789.6	794.3
135°	552.0	603.4	651.6	691.2	722.9	745.0	757.6	762.4
137.5°	535.4	578.9	619.6	655.3	684.8	706.7	717.2	722.9
140°	525.9	563.1	598.7	631.8	659.6	677.0	688.0	694.3
142.5°	517.1	549.8	580.4	609.1	633.6	649.7	659.6	664.0
145°	504.5	531.5	555.2	577.3	597.1	610.5	618.5	622.4
147.5°	494.2	515.6	534.6	552.0	566.6	578.1	584.2	585.5
150°	488.0	506.1	522.0	536.2	548.8	559.1	563.9	564.7
152.5°	481.0	496.6	511.2	522.9	533.7	542.0	544.9	545.7
155°	470.6	483.2	495.0	504.5	512.5	518.8	521.2	521.2
157.5°	459.3	469.9	479.9	487.5	493.5	498.2	499.6	499.6
160°	452.3	461.1	469.8	476.1	480.9	485.6	486.4	486.4
162.5°	445.4	452.8	459.6	465.3	468.8	473.6	474.4	473.7
165°	435.8	440.5	446.0	450.0	453.1	456.3	455.5	454.7
167.5°	426.4	430.1	434.5	436.9	438.5	440.5	440.4	439.7
170°	420.7	423.1	426.3	428.6	430.2	431.0	430.2	430.2
172.5°	415.7	417.4	419.3	421.0	422.0	422.8	422.0	420.7
175°	408.8	409.6	411.2	411.2	411.2	412.8	411.2	409.6
177.5°	404.4	405.0	405.0	405.7	405.0	405.7	404.4	403.1
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5

(END OF REPORT)