

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331449-840

Luminaire Tested: **SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331449-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8094.4 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331449-840
CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331449-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55				
1	99	95	92	88	92	89	85	83	76	74	72	65	63	62	54	53	52	47				
2	91	84	78	73	84	78	73	69	67	64	60	58	55	52	49	47	45	40				
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	39	35				
4	77	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34	30				
5	70	59	51	45	65	55	48	43	48	43	39	42	37	34	36	32	30	27				
6	65	53	45	40	60	50	43	38	44	38	34	38	34	30	33	29	27	24				
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	26	24	21				
8	56	44	36	31	52	41	35	30	37	31	27	32	27	24	28	24	22	19				
9	52	40	33	28	49	38	31	27	34	28	24	29	25	22	26	22	20	17				
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	24	20	18	16				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	32513	32513	32513	32513
5°	36451	32725	29000	32725
10°	41769	32455	25097	32455
15°	46208	31861	22173	31861
20°	45505	31223	20213	31223
25°	41031	30375	18971	30375
30°	33907	29015	18066	29015
35°	24711	27595	17420	27595
40°	19736	25918	17062	25918
45°	17249	23980	16575	23980
50°	16211	22102	16252	22102
55°	14945	20194	15817	20194
60°	13695	18167	15145	18167
65°	12478	16351	14487	16351
70°	11325	14578	13520	14578
75°	10044	12601	11977	12601
80°	8638	10432	9642	10432
85°	7744	7744	5743	7744



TEST NUMBER: P331449-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.8	2.4
10°-20°	557.5	6.9
20°-30°	809.1	10.0
30°-40°	853.9	10.5
40°-50°	756.0	9.3
50°-60°	603.3	7.5
60°-70°	410.1	5.1
70°-80°	210.2	2.6
80°-90°	55.4	0.7
90°-100°	209.6	2.6
100°-110°	711.1	8.8
110°-120°	755.5	9.3
120°-130°	621.9	7.7
130°-140°	499.4	6.2
140°-150°	377.4	4.7
150°-160°	265.2	3.3
160°-170°	156.1	1.9
170°-180°	50.8	0.6
0°-30°	1558.5	19.3
0°-40°	2412.3	29.8
0°-60°	3771.7	46.6
0°-90°	4447.4	54.9
90°-120°	1676.1	20.7
90°-150°	3174.8	39.2
90°-180°	3647.0	45.1
0°-180°	8094.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2014	2014	2014	2014	2014	
5°	2249	2019	1789	2019	2249	225
15°	2764	1906	1326	1906	2764	763
25°	2303	1705	1065	1705	2303	1041
35°	1254	1400	884	1400	1254	815
45°	755	1050	726	1050	755	594
55°	531	717	562	717	531	476
65°	327	428	379	428	327	325
75°	161	202	192	202	161	172
85°	42	42	31	42	42	47
90°	33	1	33	1	33	20
95°	115	35	115	35	115	149
105°	1136	123	1136	123	1136	1099
115°	1495	217	1495	217	1495	1464
125°	1212	302	1212	302	1212	1096
135°	1005	355	1005	355	1005	781
145°	802	405	802	405	802	510
155°	674	461	674	461	674	315
165°	592	502	592	502	592	169
175°	533	523	533	523	533	52
180°	524	524	524	524	524	



TEST NUMBER: P331449-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2106.6	2107.2	2108.4	2098.5	2097.3	2097.3	2088.6	2081.2	2072.5	2060.7	2062.0
5°	2249.0	2257.5	2260.6	2251.3	2237.4	2235.8	2222.7	2201.0	2180.9	2164.6	2153.0
7.5°	2418.9	2422.4	2414.8	2402.6	2392.2	2373.6	2349.1	2325.1	2291.6	2260.8	2237.9
10°	2547.7	2552.3	2539.2	2521.4	2506.7	2485.1	2449.4	2413.1	2368.9	2326.4	2292.3
12.5°	2645.5	2657.0	2640.1	2637.8	2612.6	2582.8	2540.4	2522.0	2459.9	2400.7	2364.2
15°	2764.4	2763.6	2765.2	2750.5	2731.9	2727.2	2682.4	2633.6	2546.2	2511.3	2450.9
17.5°	2730.1	2741.8	2747.2	2747.0	2746.6	2743.7	2729.3	2698.5	2654.6	2598.2	2528.5
20°	2648.4	2663.8	2666.1	2683.9	2694.0	2707.1	2712.6	2704.0	2677.0	2629.8	2569.4
22.5°	2522.0	2526.4	2533.7	2561.3	2583.1	2616.2	2633.3	2661.9	2651.6	2628.5	2578.1
25°	2303.2	2295.4	2322.5	2336.4	2386.7	2439.3	2477.3	2519.1	2556.3	2578.7	2563.9
27.5°	2040.3	2028.7	2069.3	2106.3	2147.2	2204.1	2263.2	2333.0	2391.1	2463.7	2488.6
30°	1818.7	1825.6	1864.3	1903.8	1965.7	2046.2	2112.7	2189.4	2272.2	2353.5	2409.9
32.5°	1579.7	1606.5	1630.9	1691.4	1746.0	1835.7	1933.2	2029.0	2132.3	2224.7	2312.2
35°	1253.7	1284.6	1318.8	1362.8	1439.5	1528.4	1623.7	1752.9	1893.8	2019.9	2123.6
37.5°	1055.3	1050.4	1069.9	1101.8	1163.8	1235.7	1345.2	1472.9	1638.7	1787.0	1933.2
40°	936.4	933.3	947.3	976.6	1023.9	1076.5	1172.5	1284.6	1438.7	1619.8	1793.9
42.5°	854.7	856.6	864.3	885.0	917.4	960.7	1032.6	1128.0	1269.1	1439.7	1626.8
45°	755.4	760.7	769.3	779.3	797.9	833.5	873.7	941.9	1053.3	1195.7	1379.9
47.5°	683.8	684.0	692.7	701.5	712.5	732.6	765.4	808.1	886.8	1002.7	1161.0
50°	645.4	640.1	646.2	653.2	664.8	678.7	700.3	740.6	793.2	886.9	1019.3
52.5°	598.3	598.5	604.1	606.7	617.1	631.1	650.9	678.7	726.4	799.6	908.4
55°	530.9	534.7	537.9	542.5	551.8	561.9	577.3	595.9	633.1	688.0	768.5
57.5°	467.5	468.7	471.8	480.6	486.5	495.7	510.5	527.4	551.5	592.2	652.7
60°	424.1	424.1	430.3	434.1	441.9	451.2	462.8	479.1	500.7	534.0	582.8
62.5°	384.5	383.8	386.4	392.6	398.6	407.3	418.8	432.6	453.0	482.6	522.7
65°	326.6	325.1	329.7	331.2	337.4	346.0	355.3	369.9	386.2	407.9	443.4
67.5°	270.8	272.8	275.2	278.1	281.6	290.5	296.7	307.1	320.8	338.8	362.9
70°	239.9	239.9	239.9	242.3	246.9	251.6	257.7	266.2	279.4	294.9	316.5
72.5°	205.2	207.7	210.2	208.8	214.7	217.4	224.9	229.7	242.3	252.2	271.4
75°	161.0	161.0	161.0	164.8	167.1	169.5	174.1	178.7	185.0	197.3	207.4
77.5°	120.1	119.8	120.6	121.5	124.0	126.7	128.2	132.3	138.0	143.8	152.3
80°	92.9	94.4	95.2	96.7	96.7	98.3	99.1	104.5	108.4	112.2	117.6
82.5°	71.8	72.1	72.3	72.6	73.2	74.1	76.1	77.9	79.3	82.5	86.6
85°	41.8	41.0	41.0	42.5	41.8	41.8	43.3	44.8	44.8	45.6	48.0
87.5°	22.7	22.7	23.3	22.7	22.7	23.1	22.7	22.5	23.3	24.2	24.6
90°	33.2	33.2	33.2	33.2	33.2	32.2	30.2	32.2	33.2	34.2	33.2
92.5°	55.8	57.5	56.7	59.9	60.7	67.0	75.4	87.9	110.7	131.0	129.2
95°	114.9	113.9	116.9	125.0	138.0	160.3	202.6	264.1	345.7	395.1	349.7
97.5°	226.2	234.6	249.3	274.2	322.3	395.1	504.1	616.2	707.5	674.5	508.0
100°	360.8	379.0	408.2	451.5	535.2	657.1	795.2	920.2	941.4	796.2	548.3
102.5°	635.0	659.5	696.0	770.0	860.9	990.2	1091.2	1119.3	1028.4	800.2	533.0
105°	1135.9	1149.9	1193.4	1255.8	1318.3	1351.6	1338.5	1224.6	1014.9	746.8	502.9
107.5°	1451.0	1469.7	1478.3	1481.8	1473.9	1425.1	1320.3	1148.8	926.5	689.6	488.0
110°	1546.1	1547.1	1538.0	1518.8	1475.5	1392.9	1263.8	1083.5	870.8	662.2	484.8



TEST NUMBER: P331449-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1544.5	1539.0	1521.9	1489.9	1429.6	1334.8	1197.0	1023.8	832.1	644.4	485.5
115°	1494.7	1485.6	1459.4	1413.0	1341.5	1237.7	1105.6	950.4	784.2	624.9	489.8
117.5°	1405.7	1398.2	1370.5	1321.5	1248.6	1151.1	1031.5	895.1	753.9	615.4	497.1
120°	1348.6	1338.5	1309.2	1261.8	1191.3	1099.5	992.8	867.8	737.8	609.8	501.9
122.5°	1288.9	1280.4	1254.4	1207.8	1144.6	1061.7	960.5	846.0	724.1	606.5	507.6
125°	1212.4	1204.4	1179.2	1140.9	1082.5	1006.8	918.2	814.4	704.5	600.7	516.0
127.5°	1145.6	1139.1	1117.3	1081.5	1030.5	960.7	877.1	783.2	686.4	597.2	524.7
130°	1107.6	1099.5	1079.4	1045.2	995.8	929.3	849.6	763.0	674.3	595.6	531.2
132.5°	1068.1	1060.9	1042.4	1008.0	959.5	897.0	823.8	743.6	664.6	594.8	537.6
135°	1004.8	1000.8	982.7	949.4	906.1	849.6	783.2	716.6	651.1	593.6	545.2
137.5°	942.8	936.8	920.8	892.2	852.6	803.4	750.6	695.0	641.6	593.4	552.1
140°	900.0	894.0	878.9	852.6	820.4	776.1	729.7	681.4	636.0	592.6	555.3
142.5°	857.3	856.1	842.6	818.8	788.2	751.0	711.1	670.0	630.4	592.6	557.7
145°	802.2	799.2	789.2	772.0	747.8	718.6	687.4	654.1	622.9	590.6	560.4
147.5°	756.1	754.3	747.4	733.8	713.8	692.4	668.0	641.8	615.2	587.0	561.2
150°	728.7	727.7	721.6	709.5	694.4	676.3	655.1	633.0	608.7	584.6	560.4
152.5°	705.3	705.1	700.6	690.1	678.3	662.6	644.6	624.1	603.1	580.6	558.8
155°	674.3	676.3	672.3	665.2	654.1	643.0	627.9	611.8	592.6	573.5	556.3
157.5°	647.8	647.8	646.0	640.2	632.4	623.7	611.0	597.4	582.8	566.2	551.7
160°	631.0	631.0	630.0	624.9	617.8	610.8	599.7	588.5	575.5	561.4	549.3
162.5°	614.8	615.6	614.6	611.2	604.1	598.6	589.2	579.8	569.1	557.3	546.8
165°	591.6	592.6	592.6	588.5	584.6	580.6	573.5	566.4	558.4	549.3	542.2
167.5°	570.3	571.5	571.7	569.5	567.6	564.0	559.2	553.7	547.9	542.2	537.6
170°	557.3	559.4	560.4	557.3	556.3	554.3	550.3	547.2	542.2	538.2	535.2
172.5°	546.8	548.1	549.1	547.6	546.6	545.4	542.2	540.0	536.6	533.4	532.0
175°	533.2	535.2	536.2	535.2	535.2	534.2	533.2	532.2	529.2	528.2	527.1
177.5°	524.9	526.5	527.4	527.4	527.4	527.4	526.5	526.5	524.9	524.1	524.9
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331449-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2066.4	2061.4	2058.3	2047.2	2037.2	2027.3	2024.3	2025.5	2011.9	1998.8	1993.3
5°	2146.9	2131.3	2116.7	2095.8	2071.0	2043.9	2029.9	2019.1	1992.1	1962.7	1945.6
7.5°	2219.0	2196.9	2168.5	2129.2	2093.1	2050.5	2023.5	1999.4	1959.8	1918.3	1893.0
10°	2262.9	2232.7	2196.4	2148.4	2104.3	2052.4	2016.0	1979.6	1933.2	1883.7	1852.7
12.5°	2300.7	2260.0	2224.2	2162.6	2110.4	2045.6	2002.5	1951.2	1902.3	1843.4	1813.1
15°	2390.7	2315.5	2247.5	2177.8	2113.5	2023.0	1975.0	1906.1	1841.9	1769.2	1734.3
17.5°	2460.1	2375.7	2268.5	2180.0	2105.1	2004.8	1934.3	1851.8	1775.8	1692.7	1645.4
20°	2499.7	2403.0	2287.6	2182.4	2092.6	1978.1	1901.5	1817.2	1728.2	1634.5	1583.5
22.5°	2523.2	2421.6	2307.5	2173.1	2067.9	1956.4	1860.0	1767.6	1677.4	1576.3	1522.8
25°	2530.7	2437.8	2317.1	2165.5	2036.9	1910.8	1794.7	1705.0	1595.8	1501.4	1423.2
27.5°	2493.9	2427.3	2311.2	2150.8	2001.1	1853.7	1724.2	1622.6	1507.4	1404.9	1326.4
30°	2448.6	2409.9	2296.9	2136.0	1972.7	1814.0	1671.6	1556.3	1441.8	1338.1	1257.6
32.5°	2378.7	2370.4	2271.0	2115.0	1942.4	1763.9	1616.6	1500.0	1373.1	1271.2	1194.5
35°	2241.3	2278.4	2215.7	2067.9	1885.2	1692.5	1533.1	1400.0	1268.5	1170.9	1098.9
37.5°	2057.1	2149.3	2132.9	1999.0	1808.2	1614.9	1438.9	1299.7	1174.4	1075.9	1005.3
40°	1930.2	2047.8	2064.8	1946.4	1753.7	1554.8	1368.3	1229.7	1107.4	1017.7	946.4
42.5°	1793.9	1931.4	1978.1	1883.2	1694.3	1491.7	1305.1	1161.6	1040.6	953.3	890.2
45°	1565.6	1747.5	1831.9	1777.7	1595.1	1387.7	1195.7	1050.2	940.3	858.3	809.5
47.5°	1352.2	1551.0	1664.4	1645.2	1484.7	1279.3	1089.5	949.9	842.9	777.5	733.9
50°	1201.1	1405.4	1542.4	1548.6	1405.4	1201.8	1011.5	879.9	781.6	720.5	684.9
52.5°	1069.9	1264.9	1414.2	1447.0	1316.9	1121.4	941.5	810.6	724.1	667.9	636.0
55°	898.5	1063.4	1229.0	1289.3	1184.9	999.2	832.7	717.4	636.1	597.4	569.6
57.5°	747.0	884.4	1037.3	1104.1	1039.7	880.7	724.7	624.5	558.7	524.7	503.3
60°	667.1	775.5	911.7	991.4	935.6	794.1	657.8	562.6	508.5	478.3	458.2
62.5°	592.8	688.8	804.0	876.9	846.5	713.0	591.0	507.0	460.2	431.8	417.3
65°	489.1	564.9	654.0	721.2	701.1	599.8	500.0	428.0	390.8	368.4	356.8
67.5°	402.7	457.6	519.3	578.2	562.0	490.2	410.0	354.0	326.3	306.9	299.9
70°	348.3	390.0	445.0	492.2	479.1	420.2	356.8	308.8	284.8	268.5	261.6
72.5°	296.3	330.6	372.5	411.1	402.2	353.4	300.4	264.2	245.8	230.8	225.1
75°	223.7	249.9	275.5	301.0	298.7	260.8	229.8	202.0	187.3	175.7	173.4
77.5°	165.1	179.9	197.2	212.4	208.1	186.5	162.2	146.2	135.4	127.6	126.4
80°	126.1	134.6	147.0	157.8	152.5	143.2	123.8	112.2	104.5	96.7	93.6
82.5°	91.5	100.0	107.4	113.3	109.2	100.5	88.6	80.7	76.0	70.7	69.5
85°	48.0	52.6	55.7	57.3	55.7	50.3	44.8	41.8	38.0	35.6	34.8
87.5°	24.0	22.6	21.6	22.2	20.0	19.6	16.3	13.8	13.8	14.0	13.1
90°	27.2	20.2	15.1	12.1	10.1	8.1	4.0	1.0	4.0	8.1	10.1
92.5°	100.6	68.6	45.7	36.3	29.4	25.0	17.8	12.3	17.8	25.0	29.4
95°	232.8	145.1	98.8	74.6	58.5	49.4	39.3	35.2	39.3	49.4	58.5
97.5°	313.7	191.5	133.2	105.8	87.3	73.6	62.9	57.5	62.9	73.6	87.3
100°	330.6	207.6	154.2	126.0	105.8	89.7	80.6	77.6	80.6	89.7	105.8
102.5°	331.4	222.2	172.8	144.5	123.6	107.4	98.4	96.1	98.4	107.4	123.6
105°	336.6	246.9	199.5	171.4	149.2	134.0	127.0	123.0	127.0	134.0	149.2
107.5°	350.5	272.4	226.4	197.9	176.0	162.1	155.2	152.0	155.2	162.1	176.0
110°	361.8	289.2	244.9	215.7	194.5	181.4	175.4	171.4	175.4	181.4	194.5



TEST NUMBER: P331449-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	374.0	305.4	262.7	232.6	212.3	200.0	193.1	189.0	193.1	200.0	212.3
115°	392.0	330.6	287.2	260.0	239.8	227.8	221.8	216.7	221.8	227.8	239.8
117.5°	411.4	353.8	313.7	285.4	266.1	255.4	249.3	245.3	249.3	255.4	266.1
120°	424.3	369.9	330.6	302.4	282.2	273.2	267.1	263.1	267.1	273.2	282.2
122.5°	435.6	385.2	348.3	319.3	299.1	289.2	283.2	280.0	283.2	289.2	299.1
125°	453.5	408.2	371.9	343.7	323.6	311.4	305.4	302.4	305.4	311.4	323.6
127.5°	470.3	429.6	394.3	365.3	345.9	332.5	324.2	320.1	324.2	332.5	345.9
130°	480.8	442.4	407.2	379.0	358.8	344.7	334.6	330.6	334.6	344.7	358.8
132.5°	491.2	453.7	420.1	391.8	370.9	356.0	345.1	340.2	345.1	356.0	370.9
135°	504.9	469.7	437.4	409.2	386.0	370.9	358.8	354.8	358.8	370.9	386.0
137.5°	515.4	482.6	450.7	424.5	401.5	385.4	373.3	368.5	373.3	385.4	401.5
140°	521.1	489.8	459.6	433.4	411.2	395.1	383.0	379.0	383.0	395.1	411.2
142.5°	525.9	495.4	466.1	441.4	420.1	403.9	392.6	389.4	392.6	403.9	420.1
145°	532.2	503.9	476.8	454.5	434.4	419.3	409.2	405.2	409.2	419.3	434.4
147.5°	535.6	510.8	485.2	465.4	448.7	434.7	425.2	422.1	425.2	434.7	448.7
150°	537.1	514.0	490.8	472.7	457.6	444.4	436.4	433.4	436.4	444.4	457.6
152.5°	538.0	517.3	496.4	480.0	465.6	454.1	446.1	444.6	446.1	454.1	465.6
155°	539.2	522.1	504.9	489.8	478.8	467.7	461.6	460.6	461.6	467.7	478.8
157.5°	539.2	525.5	511.0	498.3	489.4	479.8	474.9	473.9	474.9	479.8	489.4
160°	539.2	527.1	515.0	503.9	495.8	487.8	483.8	482.8	483.8	487.8	495.8
162.5°	538.4	528.0	517.5	508.8	501.5	495.0	491.0	491.6	491.0	495.0	501.5
165°	536.2	529.2	520.1	514.0	509.0	502.9	500.9	501.9	500.9	502.9	509.0
167.5°	534.8	529.0	522.3	518.5	514.8	511.0	509.2	510.4	509.2	511.0	514.8
170°	533.2	528.2	523.1	520.1	518.1	515.0	514.0	516.0	514.0	515.0	518.1
172.5°	530.8	527.4	523.9	521.7	520.5	517.5	518.1	519.3	518.1	517.5	520.5
175°	528.2	526.1	524.1	523.1	523.1	521.1	522.1	523.1	522.1	521.1	523.1
177.5°	526.5	524.9	524.1	524.1	524.1	522.5	523.3	524.9	523.3	522.5	524.1
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331449-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1987.1	1983.4	1970.3	1963.6	1952.5	1941.9	1935.1	1938.2	1940.7	1939.4	1937.5
5°	1930.2	1915.4	1893.0	1873.6	1859.7	1834.2	1823.3	1818.0	1813.3	1807.9	1802.4
7.5°	1862.3	1839.2	1807.0	1779.4	1753.3	1721.6	1703.5	1692.7	1681.5	1669.3	1658.5
10°	1814.0	1781.5	1747.5	1708.8	1677.9	1649.2	1623.7	1606.6	1591.1	1576.5	1565.6
12.5°	1763.3	1725.9	1683.7	1630.8	1596.7	1555.7	1551.9	1521.9	1497.6	1488.5	1475.8
15°	1682.4	1629.8	1576.5	1513.8	1486.7	1449.6	1426.3	1403.1	1382.2	1367.5	1363.6
17.5°	1590.7	1522.6	1469.5	1424.4	1380.1	1342.0	1320.6	1302.0	1284.9	1265.2	1262.5
20°	1520.8	1461.9	1403.9	1364.4	1318.8	1280.0	1253.7	1235.2	1220.4	1208.8	1198.8
22.5°	1454.5	1390.1	1337.0	1293.8	1248.8	1217.5	1196.8	1178.8	1166.6	1153.8	1144.3
25°	1348.2	1297.9	1239.8	1191.0	1153.9	1133.8	1116.7	1101.3	1093.6	1085.0	1074.2
27.5°	1255.2	1199.2	1144.9	1107.1	1074.5	1056.7	1044.6	1034.1	1026.8	1021.9	1015.7
30°	1189.5	1133.0	1090.5	1053.3	1026.2	1008.5	1000.7	994.5	985.9	982.9	979.8
32.5°	1126.3	1075.4	1039.1	1006.8	981.0	969.4	962.3	956.7	950.1	947.0	940.8
35°	1037.0	994.5	958.9	941.1	920.2	910.1	904.7	897.0	890.8	887.7	886.9
37.5°	953.0	916.0	892.6	869.7	860.9	854.7	847.3	842.0	840.2	839.7	838.9
40°	898.5	868.3	847.5	828.9	825.0	815.7	809.5	804.9	804.9	805.7	804.9
42.5°	849.0	821.9	803.4	787.4	782.8	777.3	771.1	770.8	772.0	774.7	772.0
45°	774.0	754.6	741.4	733.7	725.2	719.7	718.9	721.2	722.1	722.9	725.2
47.5°	704.9	692.1	680.1	671.6	667.9	666.9	666.0	670.0	673.8	675.2	678.7
50°	664.0	649.3	639.2	633.8	630.8	629.1	630.8	635.4	638.4	642.4	644.7
52.5°	618.2	607.8	600.9	596.7	595.4	596.4	596.7	602.0	606.9	608.3	609.4
55°	554.9	547.1	545.6	538.7	541.7	541.0	544.8	548.0	552.6	557.2	558.0
57.5°	491.7	485.5	481.4	482.0	482.9	486.4	489.6	495.0	500.0	504.9	505.3
60°	449.7	446.6	444.2	444.2	445.8	450.4	454.2	459.7	462.8	465.9	468.2
62.5°	411.2	408.2	405.9	407.1	411.1	413.8	418.4	421.3	424.4	427.5	428.6
65°	350.6	349.0	351.3	352.9	353.7	357.6	362.9	365.3	368.4	369.9	375.4
67.5°	294.7	295.0	294.7	296.9	301.3	302.3	307.4	312.9	313.5	316.4	319.9
70°	256.9	258.5	260.0	261.6	265.5	267.0	270.8	273.2	276.3	278.6	280.9
72.5°	222.3	222.6	224.1	223.8	227.0	230.5	233.7	236.0	239.1	242.1	244.4
75°	171.1	171.1	172.6	173.4	177.2	181.1	180.4	181.9	185.0	188.0	189.7
77.5°	124.9	123.2	124.9	125.7	126.9	130.2	130.8	133.0	136.5	135.4	137.1
80°	95.2	92.9	95.2	95.9	95.9	99.9	99.9	101.4	103.7	101.4	103.7
82.5°	68.0	66.9	68.6	68.8	70.0	70.1	71.4	71.7	74.0	72.9	74.0
85°	34.0	33.3	34.0	33.3	34.0	34.8	34.8	34.0	34.0	35.6	33.3
87.5°	12.9	12.9	13.3	14.7	15.3	14.9	14.0	13.8	13.4	12.6	12.8
90°	12.1	15.1	20.2	27.2	33.2	34.2	33.2	32.2	30.2	32.2	33.2
92.5°	36.3	45.7	68.6	100.6	129.2	131.0	110.7	87.9	75.4	67.0	60.7
95°	74.6	98.8	145.1	232.8	349.7	395.1	345.7	264.1	202.6	160.3	138.0
97.5°	105.8	133.2	191.5	313.7	508.0	674.5	707.5	616.2	504.1	395.1	322.3
100°	126.0	154.2	207.6	330.6	548.3	796.2	941.4	920.2	795.2	657.1	535.2
102.5°	144.5	172.8	222.2	331.4	533.0	800.2	1028.4	1119.3	1091.2	990.2	860.9
105°	171.4	199.5	246.9	336.6	502.9	746.8	1014.9	1224.6	1338.5	1351.6	1318.3
107.5°	197.9	226.4	272.4	350.5	488.0	689.6	926.5	1148.8	1320.3	1425.1	1473.9
110°	215.7	244.9	289.2	361.8	484.8	662.2	870.8	1083.5	1263.8	1392.9	1475.5



TEST NUMBER: P331449-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	232.6	262.7	305.4	374.0	485.5	644.4	832.1	1023.8	1197.0	1334.8	1429.6
115°	260.0	287.2	330.6	392.0	489.8	624.9	784.2	950.4	1105.6	1237.7	1341.5
117.5°	285.4	313.7	353.8	411.4	497.1	615.4	753.9	895.1	1031.5	1151.1	1248.6
120°	302.4	330.6	369.9	424.3	501.9	609.8	737.8	867.8	992.8	1099.5	1191.3
122.5°	319.3	348.3	385.2	435.6	507.6	606.5	724.1	846.0	960.5	1061.7	1144.6
125°	343.7	371.9	408.2	453.5	516.0	600.7	704.5	814.4	918.2	1006.8	1082.5
127.5°	365.3	394.3	429.6	470.3	524.7	597.2	686.4	783.2	877.1	960.7	1030.5
130°	379.0	407.2	442.4	480.8	531.2	595.6	674.3	763.0	849.6	929.3	995.8
132.5°	391.8	420.1	453.7	491.2	537.6	594.8	664.6	743.6	823.8	897.0	959.5
135°	409.2	437.4	469.7	504.9	545.2	593.6	651.1	716.6	783.2	849.6	906.1
137.5°	424.5	450.7	482.6	515.4	552.1	593.4	641.6	695.0	750.6	803.4	852.6
140°	433.4	459.6	489.8	521.1	555.3	592.6	636.0	681.4	729.7	776.1	820.4
142.5°	441.4	466.1	495.4	525.9	557.7	592.6	630.4	670.0	711.1	751.0	788.2
145°	454.5	476.8	503.9	532.2	560.4	590.6	622.9	654.1	687.4	718.6	747.8
147.5°	465.4	485.2	510.8	535.6	561.2	587.0	615.2	641.8	668.0	692.4	713.8
150°	472.7	490.8	514.0	537.1	560.4	584.6	608.7	633.0	655.1	676.3	694.4
152.5°	480.0	496.4	517.3	538.0	558.8	580.6	603.1	624.1	644.6	662.6	678.3
155°	489.8	504.9	522.1	539.2	556.3	573.5	592.6	611.8	627.9	643.0	654.1
157.5°	498.3	511.0	525.5	539.2	551.7	566.2	582.8	597.4	611.0	623.7	632.4
160°	503.9	515.0	527.1	539.2	549.3	561.4	575.5	588.5	599.7	610.8	617.8
162.5°	508.8	517.5	528.0	538.4	546.8	557.3	569.1	579.8	589.2	598.6	604.1
165°	514.0	520.1	529.2	536.2	542.2	549.3	558.4	566.4	573.5	580.6	584.6
167.5°	518.5	522.3	529.0	534.8	537.6	542.2	547.9	553.7	559.2	564.0	567.6
170°	520.1	523.1	528.2	533.2	535.2	538.2	542.2	547.2	550.3	554.3	556.3
172.5°	521.7	523.9	527.4	530.8	532.0	533.4	536.6	540.0	542.2	545.4	546.6
175°	523.1	524.1	526.1	528.2	527.1	528.2	529.2	532.2	533.2	534.2	535.2
177.5°	524.1	524.1	524.9	526.5	524.9	524.1	524.9	526.5	526.5	527.4	527.4
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331449-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1931.4	1930.2	1930.2	1924.6	1930.2	1930.2	1931.4	1937.5	1939.4	1940.7	1938.2
5°	1791.6	1789.3	1785.4	1789.3	1785.4	1789.3	1791.6	1802.4	1807.9	1813.3	1818.0
7.5°	1653.4	1644.1	1642.7	1633.6	1642.7	1644.1	1653.4	1658.5	1669.3	1681.5	1692.7
10°	1552.5	1546.3	1545.5	1530.8	1545.5	1546.3	1552.5	1565.6	1576.5	1591.1	1606.6
12.5°	1475.7	1460.9	1463.8	1455.2	1463.8	1460.9	1475.7	1475.8	1488.5	1497.6	1521.9
15°	1342.7	1342.7	1339.7	1326.5	1339.7	1342.7	1342.7	1363.6	1367.5	1382.2	1403.1
17.5°	1247.3	1245.7	1238.3	1241.9	1238.3	1245.7	1247.3	1262.5	1265.2	1284.9	1302.0
20°	1190.2	1185.7	1176.4	1176.4	1176.4	1185.7	1190.2	1198.8	1208.8	1220.4	1235.2
22.5°	1136.4	1136.1	1126.2	1129.3	1126.2	1136.1	1136.4	1144.3	1153.8	1166.6	1178.8
25°	1073.4	1067.2	1062.6	1064.9	1062.6	1067.2	1073.4	1074.2	1085.0	1093.6	1101.3
27.5°	1013.7	1010.3	1010.0	1003.6	1010.0	1010.3	1013.7	1015.7	1021.9	1026.8	1034.1
30°	979.0	971.3	972.8	969.0	972.8	971.3	979.0	979.8	982.9	985.9	994.5
32.5°	939.4	936.5	935.0	931.8	935.0	936.5	939.4	940.8	947.0	950.1	956.7
35°	885.3	886.2	882.2	883.8	882.2	886.2	885.3	886.9	887.7	890.8	897.0
37.5°	838.2	840.6	838.8	839.2	838.8	840.6	838.2	838.9	839.7	840.2	842.0
40°	807.2	807.2	807.2	809.5	807.2	807.2	807.2	804.9	805.7	804.9	804.9
42.5°	777.5	776.3	775.0	774.9	775.0	776.3	777.5	772.0	774.7	772.0	770.8
45°	726.7	729.0	729.8	725.9	729.8	729.0	726.7	725.2	722.9	722.1	721.2
47.5°	680.8	681.1	680.8	684.2	680.8	681.1	680.8	678.7	675.2	673.8	670.0
50°	648.5	647.0	648.5	647.0	648.5	647.0	648.5	644.7	642.4	638.4	635.4
52.5°	614.5	614.8	613.9	613.6	613.9	614.8	614.5	609.4	608.3	606.9	602.0
55°	561.1	562.6	561.9	561.9	561.9	562.6	561.1	558.0	557.2	552.6	548.0
57.5°	505.8	507.3	508.3	504.9	508.3	507.3	505.8	505.3	504.9	500.0	495.0
60°	467.5	471.3	470.5	469.0	470.5	471.3	467.5	468.2	465.9	462.8	459.7
62.5°	432.1	433.5	433.4	433.1	433.4	433.5	432.1	428.6	427.5	424.4	421.3
65°	377.7	379.2	376.9	379.2	376.9	379.2	377.7	375.4	369.9	368.4	365.3
67.5°	319.0	319.5	321.1	322.2	321.1	319.5	319.0	319.9	316.4	313.5	312.9
70°	282.5	281.8	284.1	286.4	284.1	281.8	282.5	280.9	278.6	276.3	273.2
72.5°	244.1	245.8	245.0	246.7	245.0	245.8	244.1	244.4	242.1	239.1	236.0
75°	188.0	190.4	189.7	192.0	189.7	190.4	188.0	189.7	188.0	185.0	181.9
77.5°	135.9	136.2	135.9	137.1	135.9	136.2	135.9	137.1	135.4	136.5	133.0
80°	103.7	102.2	100.6	103.7	100.6	102.2	103.7	103.7	101.4	103.7	101.4
82.5°	72.1	73.0	71.5	71.5	71.5	73.0	72.1	74.0	72.9	74.0	71.7
85°	33.3	32.5	31.0	31.0	31.0	32.5	33.3	33.3	35.6	34.0	34.0
87.5°	12.8	12.2	12.2	11.6	12.2	12.2	12.8	12.8	12.6	13.4	13.8
90°	33.2	33.2	33.2	33.2	33.2	33.2	33.2	33.2	32.2	30.2	32.2
92.5°	59.9	56.7	57.5	55.8	57.5	56.7	59.9	60.7	67.0	75.4	87.9
95°	125.0	116.9	113.9	114.9	113.9	116.9	125.0	138.0	160.3	202.6	264.1
97.5°	274.2	249.3	234.6	226.2	234.6	249.3	274.2	322.3	395.1	504.1	616.2
100°	451.5	408.2	379.0	360.8	379.0	408.2	451.5	535.2	657.1	795.2	920.2
102.5°	770.0	696.0	659.5	635.0	659.5	696.0	770.0	860.9	990.2	1091.2	1119.3
105°	1255.8	1193.4	1149.9	1135.9	1149.9	1193.4	1255.8	1318.3	1351.6	1338.5	1224.6
107.5°	1481.8	1478.3	1469.7	1451.0	1469.7	1478.3	1481.8	1473.9	1425.1	1320.3	1148.8
110°	1518.8	1538.0	1547.1	1546.1	1547.1	1538.0	1518.8	1475.5	1392.9	1263.8	1083.5



TEST NUMBER: P331449-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1489.9	1521.9	1539.0	1544.5	1539.0	1521.9	1489.9	1429.6	1334.8	1197.0	1023.8
115°	1413.0	1459.4	1485.6	1494.7	1485.6	1459.4	1413.0	1341.5	1237.7	1105.6	950.4
117.5°	1321.5	1370.5	1398.2	1405.7	1398.2	1370.5	1321.5	1248.6	1151.1	1031.5	895.1
120°	1261.8	1309.2	1338.5	1348.6	1338.5	1309.2	1261.8	1191.3	1099.5	992.8	867.8
122.5°	1207.8	1254.4	1280.4	1288.9	1280.4	1254.4	1207.8	1144.6	1061.7	960.5	846.0
125°	1140.9	1179.2	1204.4	1212.4	1204.4	1179.2	1140.9	1082.5	1006.8	918.2	814.4
127.5°	1081.5	1117.3	1139.1	1145.6	1139.1	1117.3	1081.5	1030.5	960.7	877.1	783.2
130°	1045.2	1079.4	1099.5	1107.6	1099.5	1079.4	1045.2	995.8	929.3	849.6	763.0
132.5°	1008.0	1042.4	1060.9	1068.1	1060.9	1042.4	1008.0	959.5	897.0	823.8	743.6
135°	949.4	982.7	1000.8	1004.8	1000.8	982.7	949.4	906.1	849.6	783.2	716.6
137.5°	892.2	920.8	936.8	942.8	936.8	920.8	892.2	852.6	803.4	750.6	695.0
140°	852.6	878.9	894.0	900.0	894.0	878.9	852.6	820.4	776.1	729.7	681.4
142.5°	818.8	842.6	856.1	857.3	856.1	842.6	818.8	788.2	751.0	711.1	670.0
145°	772.0	789.2	799.2	802.2	799.2	789.2	772.0	747.8	718.6	687.4	654.1
147.5°	733.8	747.4	754.3	756.1	754.3	747.4	733.8	713.8	692.4	668.0	641.8
150°	709.5	721.6	727.7	728.7	727.7	721.6	709.5	694.4	676.3	655.1	633.0
152.5°	690.1	700.6	705.1	705.3	705.1	700.6	690.1	678.3	662.6	644.6	624.1
155°	665.2	672.3	676.3	674.3	676.3	672.3	665.2	654.1	643.0	627.9	611.8
157.5°	640.2	646.0	647.8	647.8	647.8	646.0	640.2	632.4	623.7	611.0	597.4
160°	624.9	630.0	631.0	631.0	631.0	630.0	624.9	617.8	610.8	599.7	588.5
162.5°	611.2	614.6	615.6	614.8	615.6	614.6	611.2	604.1	598.6	589.2	579.8
165°	588.5	592.6	592.6	591.6	592.6	592.6	588.5	584.6	580.6	573.5	566.4
167.5°	569.5	571.7	571.5	570.3	571.5	571.7	569.5	567.6	564.0	559.2	553.7
170°	557.3	560.4	559.4	557.3	559.4	560.4	557.3	556.3	554.3	550.3	547.2
172.5°	547.6	549.1	548.1	546.8	548.1	549.1	547.6	546.6	545.4	542.2	540.0
175°	535.2	536.2	535.2	533.2	535.2	536.2	535.2	535.2	534.2	533.2	532.2
177.5°	527.4	527.4	526.5	524.9	526.5	527.4	527.4	527.4	527.4	526.5	526.5
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331449-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1935.1	1941.9	1952.5	1963.6	1970.3	1983.4	1987.1	1993.3	1998.8	2011.9	2025.5
5°	1823.3	1834.2	1859.7	1873.6	1893.0	1915.4	1930.2	1945.6	1962.7	1992.1	2019.1
7.5°	1703.5	1721.6	1753.3	1779.4	1807.0	1839.2	1862.3	1893.0	1918.3	1959.8	1999.4
10°	1623.7	1649.2	1677.9	1708.8	1747.5	1781.5	1814.0	1852.7	1883.7	1933.2	1979.6
12.5°	1551.9	1555.7	1596.7	1630.8	1683.7	1725.9	1763.3	1813.1	1843.4	1902.3	1951.2
15°	1426.3	1449.6	1486.7	1513.8	1576.5	1629.8	1682.4	1734.3	1769.2	1841.9	1906.1
17.5°	1320.6	1342.0	1380.1	1424.4	1469.5	1522.6	1590.7	1645.4	1692.7	1775.8	1851.8
20°	1253.7	1280.0	1318.8	1364.4	1403.9	1461.9	1520.8	1583.5	1634.5	1728.2	1817.2
22.5°	1196.8	1217.5	1248.8	1293.8	1337.0	1390.1	1454.5	1522.8	1576.3	1677.4	1767.6
25°	1116.7	1133.8	1153.9	1191.0	1239.8	1297.9	1348.2	1423.2	1501.4	1595.8	1705.0
27.5°	1044.6	1056.7	1074.5	1107.1	1144.9	1199.2	1255.2	1326.4	1404.9	1507.4	1622.6
30°	1000.7	1008.5	1026.2	1053.3	1090.5	1133.0	1189.5	1257.6	1338.1	1441.8	1556.3
32.5°	962.3	969.4	981.0	1006.8	1039.1	1075.4	1126.3	1194.5	1271.2	1373.1	1500.0
35°	904.7	910.1	920.2	941.1	958.9	994.5	1037.0	1098.9	1170.9	1268.5	1400.0
37.5°	847.3	854.7	860.9	869.7	892.6	916.0	953.0	1005.3	1075.9	1174.4	1299.7
40°	809.5	815.7	825.0	828.9	847.5	868.3	898.5	946.4	1017.7	1107.4	1229.7
42.5°	771.1	777.3	782.8	787.4	803.4	821.9	849.0	890.2	953.3	1040.6	1161.6
45°	718.9	719.7	725.2	733.7	741.4	754.6	774.0	809.5	858.3	940.3	1050.2
47.5°	666.0	666.9	667.9	671.6	680.1	692.1	704.9	733.9	777.5	842.9	949.9
50°	630.8	629.1	630.8	633.8	639.2	649.3	664.0	684.9	720.5	781.6	879.9
52.5°	596.7	596.4	595.4	596.7	600.9	607.8	618.2	636.0	667.9	724.1	810.6
55°	544.8	541.0	541.7	538.7	545.6	547.1	554.9	569.6	597.4	636.1	717.4
57.5°	489.6	486.4	482.9	482.0	481.4	485.5	491.7	503.3	524.7	558.7	624.5
60°	454.2	450.4	445.8	444.2	444.2	446.6	449.7	458.2	478.3	508.5	562.6
62.5°	418.4	413.8	411.1	407.1	405.9	408.2	411.2	417.3	431.8	460.2	507.0
65°	362.9	357.6	353.7	352.9	351.3	349.0	350.6	356.8	368.4	390.8	428.0
67.5°	307.4	302.3	301.3	296.9	294.7	295.0	294.7	299.9	306.9	326.3	354.0
70°	270.8	267.0	265.5	261.6	260.0	258.5	256.9	261.6	268.5	284.8	308.8
72.5°	233.7	230.5	227.0	223.8	224.1	222.6	222.3	225.1	230.8	245.8	264.2
75°	180.4	181.1	177.2	173.4	172.6	171.1	171.1	173.4	175.7	187.3	202.0
77.5°	130.8	130.2	126.9	125.7	124.9	123.2	124.9	126.4	127.6	135.4	146.2
80°	99.9	99.9	95.9	95.9	95.2	92.9	95.2	93.6	96.7	104.5	112.2
82.5°	71.4	70.1	70.0	68.8	68.6	66.9	68.0	69.5	70.7	76.0	80.7
85°	34.8	34.8	34.0	33.3	34.0	33.3	34.0	34.8	35.6	38.0	41.8
87.5°	14.0	14.9	15.3	14.7	13.3	12.9	12.9	13.1	14.0	13.8	13.8
90°	33.2	34.2	33.2	27.2	20.2	15.1	12.1	10.1	8.1	4.0	1.0
92.5°	110.7	131.0	129.2	100.6	68.6	45.7	36.3	29.4	25.0	17.8	12.3
95°	345.7	395.1	349.7	232.8	145.1	98.8	74.6	58.5	49.4	39.3	35.2
97.5°	707.5	674.5	508.0	313.7	191.5	133.2	105.8	87.3	73.6	62.9	57.5
100°	941.4	796.2	548.3	330.6	207.6	154.2	126.0	105.8	89.7	80.6	77.6
102.5°	1028.4	800.2	533.0	331.4	222.2	172.8	144.5	123.6	107.4	98.4	96.1
105°	1014.9	746.8	502.9	336.6	246.9	199.5	171.4	149.2	134.0	127.0	123.0
107.5°	926.5	689.6	488.0	350.5	272.4	226.4	197.9	176.0	162.1	155.2	152.0
110°	870.8	662.2	484.8	361.8	289.2	244.9	215.7	194.5	181.4	175.4	171.4



TEST NUMBER: P331449-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	832.1	644.4	485.5	374.0	305.4	262.7	232.6	212.3	200.0	193.1	189.0
115°	784.2	624.9	489.8	392.0	330.6	287.2	260.0	239.8	227.8	221.8	216.7
117.5°	753.9	615.4	497.1	411.4	353.8	313.7	285.4	266.1	255.4	249.3	245.3
120°	737.8	609.8	501.9	424.3	369.9	330.6	302.4	282.2	273.2	267.1	263.1
122.5°	724.1	606.5	507.6	435.6	385.2	348.3	319.3	299.1	289.2	283.2	280.0
125°	704.5	600.7	516.0	453.5	408.2	371.9	343.7	323.6	311.4	305.4	302.4
127.5°	686.4	597.2	524.7	470.3	429.6	394.3	365.3	345.9	332.5	324.2	320.1
130°	674.3	595.6	531.2	480.8	442.4	407.2	379.0	358.8	344.7	334.6	330.6
132.5°	664.6	594.8	537.6	491.2	453.7	420.1	391.8	370.9	356.0	345.1	340.2
135°	651.1	593.6	545.2	504.9	469.7	437.4	409.2	386.0	370.9	358.8	354.8
137.5°	641.6	593.4	552.1	515.4	482.6	450.7	424.5	401.5	385.4	373.3	368.5
140°	636.0	592.6	555.3	521.1	489.8	459.6	433.4	411.2	395.1	383.0	379.0
142.5°	630.4	592.6	557.7	525.9	495.4	466.1	441.4	420.1	403.9	392.6	389.4
145°	622.9	590.6	560.4	532.2	503.9	476.8	454.5	434.4	419.3	409.2	405.2
147.5°	615.2	587.0	561.2	535.6	510.8	485.2	465.4	448.7	434.7	425.2	422.1
150°	608.7	584.6	560.4	537.1	514.0	490.8	472.7	457.6	444.4	436.4	433.4
152.5°	603.1	580.6	558.8	538.0	517.3	496.4	480.0	465.6	454.1	446.1	444.6
155°	592.6	573.5	556.3	539.2	522.1	504.9	489.8	478.8	467.7	461.6	460.6
157.5°	582.8	566.2	551.7	539.2	525.5	511.0	498.3	489.4	479.8	474.9	473.9
160°	575.5	561.4	549.3	539.2	527.1	515.0	503.9	495.8	487.8	483.8	482.8
162.5°	569.1	557.3	546.8	538.4	528.0	517.5	508.8	501.5	495.0	491.0	491.6
165°	558.4	549.3	542.2	536.2	529.2	520.1	514.0	509.0	502.9	500.9	501.9
167.5°	547.9	542.2	537.6	534.8	529.0	522.3	518.5	514.8	511.0	509.2	510.4
170°	542.2	538.2	535.2	533.2	528.2	523.1	520.1	518.1	515.0	514.0	516.0
172.5°	536.6	533.4	532.0	530.8	527.4	523.9	521.7	520.5	517.5	518.1	519.3
175°	529.2	528.2	527.1	528.2	526.1	524.1	523.1	523.1	521.1	522.1	523.1
177.5°	524.9	524.1	524.9	526.5	524.9	524.1	524.1	524.1	522.5	523.3	524.9
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331449-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2024.3	2027.3	2037.2	2047.2	2058.3	2061.4	2066.4	2062.0	2060.7	2072.5	2081.2
5°	2029.9	2043.9	2071.0	2095.8	2116.7	2131.3	2146.9	2153.0	2164.6	2180.9	2201.0
7.5°	2023.5	2050.5	2093.1	2129.2	2168.5	2196.9	2219.0	2237.9	2260.8	2291.6	2325.1
10°	2016.0	2052.4	2104.3	2148.4	2196.4	2232.7	2262.9	2292.3	2326.4	2368.9	2413.1
12.5°	2002.5	2045.6	2110.4	2162.6	2224.2	2260.0	2300.7	2364.2	2400.7	2459.9	2522.0
15°	1975.0	2023.0	2113.5	2177.8	2247.5	2315.5	2390.7	2450.9	2511.3	2546.2	2633.6
17.5°	1934.3	2004.8	2105.1	2180.0	2268.5	2375.7	2460.1	2528.5	2598.2	2654.6	2698.5
20°	1901.5	1978.1	2092.6	2182.4	2287.6	2403.0	2499.7	2569.4	2629.8	2677.0	2704.0
22.5°	1860.0	1956.4	2067.9	2173.1	2307.5	2421.6	2523.2	2578.1	2628.5	2651.6	2661.9
25°	1794.7	1910.8	2036.9	2165.5	2317.1	2437.8	2530.7	2563.9	2578.7	2556.3	2519.1
27.5°	1724.2	1853.7	2001.1	2150.8	2311.2	2427.3	2493.9	2488.6	2463.7	2391.1	2333.0
30°	1671.6	1814.0	1972.7	2136.0	2296.9	2409.9	2448.6	2409.9	2353.5	2272.2	2189.4
32.5°	1616.6	1763.9	1942.4	2115.0	2271.0	2370.4	2378.7	2312.2	2224.7	2132.3	2029.0
35°	1533.1	1692.5	1885.2	2067.9	2215.7	2278.4	2241.3	2123.6	2019.9	1893.8	1752.9
37.5°	1438.9	1614.9	1808.2	1999.0	2132.9	2149.3	2057.1	1933.2	1787.0	1638.7	1472.9
40°	1368.3	1554.8	1753.7	1946.4	2064.8	2047.8	1930.2	1793.9	1619.8	1438.7	1284.6
42.5°	1305.1	1491.7	1694.3	1883.2	1978.1	1931.4	1793.9	1626.8	1439.7	1269.1	1128.0
45°	1195.7	1387.7	1595.1	1777.7	1831.9	1747.5	1565.6	1379.9	1195.7	1053.3	941.9
47.5°	1089.5	1279.3	1484.7	1645.2	1664.4	1551.0	1352.2	1161.0	1002.7	886.8	808.1
50°	1011.5	1201.8	1405.4	1548.6	1542.4	1405.4	1201.1	1019.3	886.9	793.2	740.6
52.5°	941.5	1121.4	1316.9	1447.0	1414.2	1264.9	1069.9	908.4	799.6	726.4	678.7
55°	832.7	999.2	1184.9	1289.3	1229.0	1063.4	898.5	768.5	688.0	633.1	595.9
57.5°	724.7	880.7	1039.7	1104.1	1037.3	884.4	747.0	652.7	592.2	551.5	527.4
60°	657.8	794.1	935.6	991.4	911.7	775.5	667.1	582.8	534.0	500.7	479.1
62.5°	591.0	713.0	846.5	876.9	804.0	688.8	592.8	522.7	482.6	453.0	432.6
65°	500.0	599.8	701.1	721.2	654.0	564.9	489.1	443.4	407.9	386.2	369.9
67.5°	410.0	490.2	562.0	578.2	519.3	457.6	402.7	362.9	338.8	320.8	307.1
70°	356.8	420.2	479.1	492.2	445.0	390.0	348.3	316.5	294.9	279.4	266.2
72.5°	300.4	353.4	402.2	411.1	372.5	330.6	296.3	271.4	252.2	242.3	229.7
75°	229.8	260.8	298.7	301.0	275.5	249.9	223.7	207.4	197.3	185.0	178.7
77.5°	162.2	186.5	208.1	212.4	197.2	179.9	165.1	152.3	143.8	138.0	132.3
80°	123.8	143.2	152.5	157.8	147.0	134.6	126.1	117.6	112.2	108.4	104.5
82.5°	88.6	100.5	109.2	113.3	107.4	100.0	91.5	86.6	82.5	79.3	77.9
85°	44.8	50.3	55.7	57.3	55.7	52.6	48.0	48.0	45.6	44.8	44.8
87.5°	16.3	19.6	20.0	22.2	21.6	22.6	24.0	24.6	24.2	23.3	22.5
90°	4.0	8.1	10.1	12.1	15.1	20.2	27.2	33.2	34.2	33.2	32.2
92.5°	17.8	25.0	29.4	36.3	45.7	68.6	100.6	129.2	131.0	110.7	87.9
95°	39.3	49.4	58.5	74.6	98.8	145.1	232.8	349.7	395.1	345.7	264.1
97.5°	62.9	73.6	87.3	105.8	133.2	191.5	313.7	508.0	674.5	707.5	616.2
100°	80.6	89.7	105.8	126.0	154.2	207.6	330.6	548.3	796.2	941.4	920.2
102.5°	98.4	107.4	123.6	144.5	172.8	222.2	331.4	533.0	800.2	1028.4	1119.3
105°	127.0	134.0	149.2	171.4	199.5	246.9	336.6	502.9	746.8	1014.9	1224.6
107.5°	155.2	162.1	176.0	197.9	226.4	272.4	350.5	488.0	689.6	926.5	1148.8
110°	175.4	181.4	194.5	215.7	244.9	289.2	361.8	484.8	662.2	870.8	1083.5



TEST NUMBER: P331449-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	193.1	200.0	212.3	232.6	262.7	305.4	374.0	485.5	644.4	832.1	1023.8
115°	221.8	227.8	239.8	260.0	287.2	330.6	392.0	489.8	624.9	784.2	950.4
117.5°	249.3	255.4	266.1	285.4	313.7	353.8	411.4	497.1	615.4	753.9	895.1
120°	267.1	273.2	282.2	302.4	330.6	369.9	424.3	501.9	609.8	737.8	867.8
122.5°	283.2	289.2	299.1	319.3	348.3	385.2	435.6	507.6	606.5	724.1	846.0
125°	305.4	311.4	323.6	343.7	371.9	408.2	453.5	516.0	600.7	704.5	814.4
127.5°	324.2	332.5	345.9	365.3	394.3	429.6	470.3	524.7	597.2	686.4	783.2
130°	334.6	344.7	358.8	379.0	407.2	442.4	480.8	531.2	595.6	674.3	763.0
132.5°	345.1	356.0	370.9	391.8	420.1	453.7	491.2	537.6	594.8	664.6	743.6
135°	358.8	370.9	386.0	409.2	437.4	469.7	504.9	545.2	593.6	651.1	716.6
137.5°	373.3	385.4	401.5	424.5	450.7	482.6	515.4	552.1	593.4	641.6	695.0
140°	383.0	395.1	411.2	433.4	459.6	489.8	521.1	555.3	592.6	636.0	681.4
142.5°	392.6	403.9	420.1	441.4	466.1	495.4	525.9	557.7	592.6	630.4	670.0
145°	409.2	419.3	434.4	454.5	476.8	503.9	532.2	560.4	590.6	622.9	654.1
147.5°	425.2	434.7	448.7	465.4	485.2	510.8	535.6	561.2	587.0	615.2	641.8
150°	436.4	444.4	457.6	472.7	490.8	514.0	537.1	560.4	584.6	608.7	633.0
152.5°	446.1	454.1	465.6	480.0	496.4	517.3	538.0	558.8	580.6	603.1	624.1
155°	461.6	467.7	478.8	489.8	504.9	522.1	539.2	556.3	573.5	592.6	611.8
157.5°	474.9	479.8	489.4	498.3	511.0	525.5	539.2	551.7	566.2	582.8	597.4
160°	483.8	487.8	495.8	503.9	515.0	527.1	539.2	549.3	561.4	575.5	588.5
162.5°	491.0	495.0	501.5	508.8	517.5	528.0	538.4	546.8	557.3	569.1	579.8
165°	500.9	502.9	509.0	514.0	520.1	529.2	536.2	542.2	549.3	558.4	566.4
167.5°	509.2	511.0	514.8	518.5	522.3	529.0	534.8	537.6	542.2	547.9	553.7
170°	514.0	515.0	518.1	520.1	523.1	528.2	533.2	535.2	538.2	542.2	547.2
172.5°	518.1	517.5	520.5	521.7	523.9	527.4	530.8	532.0	533.4	536.6	540.0
175°	522.1	521.1	523.1	523.1	524.1	526.1	528.2	527.1	528.2	529.2	532.2
177.5°	523.3	522.5	524.1	524.1	524.1	524.9	526.5	524.9	524.1	524.9	526.5
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331449-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2088.6	2097.3	2097.3	2098.5	2108.4	2107.2	2106.6
5°	2222.7	2235.8	2237.4	2251.3	2260.6	2257.5	2249.0
7.5°	2349.1	2373.6	2392.2	2402.6	2414.8	2422.4	2418.9
10°	2449.4	2485.1	2506.7	2521.4	2539.2	2552.3	2547.7
12.5°	2540.4	2582.8	2612.6	2637.8	2640.1	2657.0	2645.5
15°	2682.4	2727.2	2731.9	2750.5	2765.2	2763.6	2764.4
17.5°	2729.3	2743.7	2746.6	2747.0	2747.2	2741.8	2730.1
20°	2712.6	2707.1	2694.0	2683.9	2666.1	2663.8	2648.4
22.5°	2633.3	2616.2	2583.1	2561.3	2533.7	2526.4	2522.0
25°	2477.3	2439.3	2386.7	2336.4	2322.5	2295.4	2303.2
27.5°	2263.2	2204.1	2147.2	2106.3	2069.3	2028.7	2040.3
30°	2112.7	2046.2	1965.7	1903.8	1864.3	1825.6	1818.7
32.5°	1933.2	1835.7	1746.0	1691.4	1630.9	1606.5	1579.7
35°	1623.7	1528.4	1439.5	1362.8	1318.8	1284.6	1253.7
37.5°	1345.2	1235.7	1163.8	1101.8	1069.9	1050.4	1055.3
40°	1172.5	1076.5	1023.9	976.6	947.3	933.3	936.4
42.5°	1032.6	960.7	917.4	885.0	864.3	856.6	854.7
45°	873.7	833.5	797.9	779.3	769.3	760.7	755.4
47.5°	765.4	732.6	712.5	701.5	692.7	684.0	683.8
50°	700.3	678.7	664.8	653.2	646.2	640.1	645.4
52.5°	650.9	631.1	617.1	606.7	604.1	598.5	598.3
55°	577.3	561.9	551.8	542.5	537.9	534.7	530.9
57.5°	510.5	495.7	486.5	480.6	471.8	468.7	467.5
60°	462.8	451.2	441.9	434.1	430.3	424.1	424.1
62.5°	418.8	407.3	398.6	392.6	386.4	383.8	384.5
65°	355.3	346.0	337.4	331.2	329.7	325.1	326.6
67.5°	296.7	290.5	281.6	278.1	275.2	272.8	270.8
70°	257.7	251.6	246.9	242.3	239.9	239.9	239.9
72.5°	224.9	217.4	214.7	208.8	210.2	207.7	205.2
75°	174.1	169.5	167.1	164.8	161.0	161.0	161.0
77.5°	128.2	126.7	124.0	121.5	120.6	119.8	120.1
80°	99.1	98.3	96.7	96.7	95.2	94.4	92.9
82.5°	76.1	74.1	73.2	72.6	72.3	72.1	71.8
85°	43.3	41.8	41.8	42.5	41.0	41.0	41.8
87.5°	22.7	23.1	22.7	22.7	23.3	22.7	22.7
90°	30.2	32.2	33.2	33.2	33.2	33.2	33.2
92.5°	75.4	67.0	60.7	59.9	56.7	57.5	55.8
95°	202.6	160.3	138.0	125.0	116.9	113.9	114.9
97.5°	504.1	395.1	322.3	274.2	249.3	234.6	226.2
100°	795.2	657.1	535.2	451.5	408.2	379.0	360.8
102.5°	1091.2	990.2	860.9	770.0	696.0	659.5	635.0
105°	1338.5	1351.6	1318.3	1255.8	1193.4	1149.9	1135.9
107.5°	1320.3	1425.1	1473.9	1481.8	1478.3	1469.7	1451.0
110°	1263.8	1392.9	1475.5	1518.8	1538.0	1547.1	1546.1



TEST NUMBER: P331449-840
 CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1197.0	1334.8	1429.6	1489.9	1521.9	1539.0	1544.5
115°	1105.6	1237.7	1341.5	1413.0	1459.4	1485.6	1494.7
117.5°	1031.5	1151.1	1248.6	1321.5	1370.5	1398.2	1405.7
120°	992.8	1099.5	1191.3	1261.8	1309.2	1338.5	1348.6
122.5°	960.5	1061.7	1144.6	1207.8	1254.4	1280.4	1288.9
125°	918.2	1006.8	1082.5	1140.9	1179.2	1204.4	1212.4
127.5°	877.1	960.7	1030.5	1081.5	1117.3	1139.1	1145.6
130°	849.6	929.3	995.8	1045.2	1079.4	1099.5	1107.6
132.5°	823.8	897.0	959.5	1008.0	1042.4	1060.9	1068.1
135°	783.2	849.6	906.1	949.4	982.7	1000.8	1004.8
137.5°	750.6	803.4	852.6	892.2	920.8	936.8	942.8
140°	729.7	776.1	820.4	852.6	878.9	894.0	900.0
142.5°	711.1	751.0	788.2	818.8	842.6	856.1	857.3
145°	687.4	718.6	747.8	772.0	789.2	799.2	802.2
147.5°	668.0	692.4	713.8	733.8	747.4	754.3	756.1
150°	655.1	676.3	694.4	709.5	721.6	727.7	728.7
152.5°	644.6	662.6	678.3	690.1	700.6	705.1	705.3
155°	627.9	643.0	654.1	665.2	672.3	676.3	674.3
157.5°	611.0	623.7	632.4	640.2	646.0	647.8	647.8
160°	599.7	610.8	617.8	624.9	630.0	631.0	631.0
162.5°	589.2	598.6	604.1	611.2	614.6	615.6	614.8
165°	573.5	580.6	584.6	588.5	592.6	592.6	591.6
167.5°	559.2	564.0	567.6	569.5	571.7	571.5	570.3
170°	550.3	554.3	556.3	557.3	560.4	559.4	557.3
172.5°	542.2	545.4	546.6	547.6	549.1	548.1	546.8
175°	533.2	534.2	535.2	535.2	536.2	535.2	533.2
177.5°	526.5	527.4	527.4	527.4	527.4	526.5	524.9
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1

(END OF REPORT)