

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332597-927

Luminaire Tested: **SA4XXDIP-C795D590U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332597-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C795D590U927-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4372.7 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332597-927

CATALOG NUMBER: SA4XXDIP-C795D590U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332597-927

CATALOG NUMBER: SA4XXDIP-C795D590U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	67	67	67	62																
1	100	96	92	88	94	90	86	83	79	76	74	69	67	65	59	58	56	56	56	56	52																
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	50	48	48	48	48	43																
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40	40	40	40	37																
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	38	35	35	35	35	32																
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	33	30	30	30	30	27																
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	27	27	27	24																
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	24	24	24	21																
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	21	21	21	19																
9	52	39	32	27	48	37	30	25	33	27	23	30	25	21	26	22	19	19	19	19	17																
10	48	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18	18	18	18	16																

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8490	8490	8490
5°	8515	8413	8474
10°	8461	8344	8385
15°	8359	8226	8247
20°	8223	8079	8086
25°	8068	7911	7888
30°	7879	7713	7643
35°	7681	7508	7407
40°	7477	7273	7140
45°	7263	7042	6907
50°	7027	6836	6625
55°	6773	6570	6356
60°	6516	6273	6082
65°	6229	5989	5746
70°	5908	5611	5391
75°	5415	5153	5022
80°	4816	4621	4505
85°	4215	4057	3974



TEST NUMBER: P332597-927

CATALOG NUMBER: SA4XXDIP-C795D590U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.0	2.3
10°-20°	279.0	6.4
20°-30°	410.7	9.4
30°-40°	477.4	10.9
40°-50°	477.5	10.9
50°-60°	417.6	9.6
60°-70°	310.2	7.1
70°-80°	176.2	4.0
80°-90°	52.1	1.2
90°-100°	166.1	3.8
100°-110°	345.8	7.9
110°-120°	309.7	7.1
120°-130°	260.5	6.0
130°-140°	217.2	5.0
140°-150°	166.0	3.8
150°-160°	116.6	2.7
160°-170°	68.6	1.6
170°-180°	22.3	0.5
0°-30°	788.7	18.0
0°-40°	1266.2	29.0
0°-60°	2161.3	49.4
0°-90°	2699.8	61.7
90°-120°	821.6	18.8
90°-150°	1465.3	33.5
90°-180°	1673.0	38.3
0°-180°	4372.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1052	1052	1052	1052	1052	
5°	1051	1047	1038	1047	1046	100
15°	1000	996	984	989	987	282
25°	906	900	888	889	886	417
35°	779	773	762	756	752	487
45°	636	630	617	608	605	490
55°	481	478	467	457	452	431
65°	326	322	314	305	301	323
75°	174	169	165	162	161	184
85°	46	45	44	44	43	50
90°	0	4	8	9	10	3
95°	15	47	368	182	110	17
105°	53	77	296	638	636	56
115°	93	117	264	508	610	92
125°	130	154	263	432	487	115
135°	154	183	261	384	436	119
145°	178	203	259	324	356	111
155°	202	218	252	286	298	93
165°	220	227	242	256	260	62
175°	230	230	232	235	234	22
180°	230	230	230	230	230	



TEST NUMBER: P332597-927

CATALOG NUMBER: SA4XXDIP-C795D590U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6
2.5°	1054.3	1053.8	1053.4	1053.0	1052.5	1051.5	1049.8	1048.1	1046.5	1044.9	1046.3
5°	1050.8	1050.0	1049.2	1048.5	1047.7	1046.3	1044.3	1042.2	1040.1	1038.1	1040.1
7.5°	1041.0	1040.2	1039.5	1038.7	1038.0	1036.5	1034.2	1031.9	1029.6	1027.3	1029.0
10°	1032.2	1031.5	1030.7	1030.0	1029.2	1027.6	1025.2	1022.8	1020.3	1017.9	1019.4
12.5°	1020.7	1020.0	1019.2	1018.5	1017.8	1016.1	1013.5	1010.9	1008.4	1005.8	1007.4
15°	1000.2	999.4	998.7	997.9	997.2	995.5	992.6	989.8	987.0	984.2	985.3
17.5°	975.4	974.5	973.5	972.6	971.7	969.9	967.3	964.6	961.9	959.3	960.0
20°	957.2	956.2	955.4	954.4	953.5	951.6	948.8	945.9	943.2	940.4	941.0
22.5°	937.7	936.4	935.2	934.0	932.7	930.7	927.9	925.1	922.3	919.5	920.5
25°	905.8	904.5	903.2	901.9	900.6	898.6	896.0	893.3	890.7	888.1	888.3
27.5°	869.4	868.1	866.7	865.4	864.0	862.1	859.7	857.3	854.8	852.4	851.9
30°	845.2	843.7	842.2	840.7	839.2	837.2	834.7	832.3	829.9	827.4	826.7
32.5°	819.5	818.2	816.8	815.5	814.1	812.1	809.6	807.0	804.5	801.8	801.0
35°	779.4	778.1	776.8	775.5	774.2	772.2	769.6	767.0	764.4	761.8	760.4
37.5°	737.1	735.9	734.7	733.6	732.3	730.3	727.5	724.7	721.9	719.1	717.6
40°	709.5	708.0	706.5	705.0	703.5	701.3	698.5	695.7	692.9	690.1	688.2
42.5°	679.9	678.9	678.0	677.2	676.2	674.2	671.1	668.0	664.9	661.8	659.7
45°	636.2	634.9	633.6	632.2	631.0	628.8	625.8	622.8	619.8	616.8	614.7
47.5°	590.5	589.6	588.7	587.8	586.9	585.1	582.3	579.6	576.8	574.0	571.6
50°	559.5	558.7	558.0	557.2	556.5	554.8	552.2	549.6	546.9	544.3	541.7
52.5°	529.2	528.3	527.4	526.5	525.5	523.7	520.9	518.2	515.4	512.6	510.3
55°	481.2	480.5	480.0	479.4	478.9	477.3	474.7	472.1	469.4	466.8	464.5
57.5°	435.3	434.7	434.0	433.4	432.8	431.1	428.6	426.0	423.4	420.8	418.7
60°	403.6	402.7	401.7	400.8	399.9	398.2	395.8	393.3	390.9	388.5	386.7
62.5°	372.6	371.9	371.1	370.3	369.5	367.8	365.2	362.6	360.0	357.4	355.9
65°	326.1	325.2	324.2	323.3	322.3	320.9	319.1	317.2	315.3	313.5	311.6
67.5°	279.2	278.4	277.5	276.6	275.8	274.5	272.7	270.8	269.1	267.3	265.5
70°	250.3	249.0	247.6	246.3	245.0	243.6	242.1	240.6	239.1	237.7	236.1
72.5°	219.3	217.9	216.7	215.3	214.0	212.8	211.6	210.3	209.1	207.9	206.8
75°	173.6	172.6	171.7	170.8	169.8	168.9	167.9	167.0	166.1	165.2	164.4
77.5°	129.9	129.5	129.1	128.7	128.3	127.7	126.8	126.0	125.2	124.4	124.1
80°	103.6	103.1	102.5	102.0	101.4	100.9	100.5	100.2	99.8	99.4	99.0
82.5°	78.0	77.8	77.5	77.2	77.0	76.8	76.8	76.7	76.6	76.5	76.3
85°	45.5	45.5	45.5	45.5	45.5	45.3	44.9	44.6	44.2	43.8	43.8
87.5°	17.6	17.7	17.7	17.7	17.7	17.5	17.9	17.7	17.7	17.8	17.7
90°	0.5	1.3	2.7	3.2	3.6	3.6	6.3	6.3	7.2	8.2	7.7
92.5°	5.1	7.5	11.7	17.3	23.8	33.3	56.2	91.3	125.5	143.3	119.4
95°	14.9	16.2	20.8	26.7	37.5	56.5	95.8	169.9	277.9	368.3	378.7
97.5°	26.8	26.8	30.7	36.0	45.4	61.3	91.6	152.7	260.2	387.9	475.8
100°	34.4	34.4	37.5	42.9	51.5	66.0	92.6	143.7	235.9	363.3	479.0
102.5°	41.6	42.3	45.1	50.1	58.4	72.1	96.3	141.2	219.6	332.6	451.9
105°	52.8	54.3	56.5	61.9	70.0	83.2	104.8	142.4	205.7	296.4	402.7
107.5°	65.4	66.2	68.5	74.3	82.1	95.0	114.9	149.0	203.1	276.2	362.9
110°	73.7	74.5	76.8	82.2	90.4	102.6	122.5	154.1	203.8	269.3	343.0



TEST NUMBER: P332597-927

CATALOG NUMBER: SA4XXDIP-C795D590U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	81.6	82.5	85.2	90.2	98.3	110.5	129.7	159.5	206.0	266.1	331.8
115°	93.1	94.4	97.6	102.1	110.7	122.9	141.0	168.1	210.2	264.4	321.3
117.5°	105.0	106.3	109.1	114.1	122.1	134.8	151.9	176.9	214.5	263.9	316.6
120°	113.0	113.9	117.0	122.0	129.7	142.4	159.5	183.0	217.9	263.9	314.1
122.5°	120.2	121.1	124.3	128.9	137.3	149.6	166.8	188.8	221.1	263.6	311.2
125°	129.7	131.5	134.2	139.2	147.7	160.4	176.7	197.5	225.9	263.0	306.4
127.5°	138.1	139.6	142.8	148.5	157.4	170.2	185.9	205.0	229.8	262.0	300.0
130°	142.8	144.6	148.2	155.0	163.6	176.7	192.0	209.7	232.7	261.7	296.0
132.5°	147.5	148.9	153.7	160.1	169.4	181.7	197.1	214.4	235.3	261.3	292.4
135°	154.1	155.9	160.4	168.1	177.6	189.3	204.2	220.5	239.1	260.7	286.9
137.5°	160.7	162.4	167.4	174.7	184.6	195.7	209.7	224.9	241.3	260.6	282.3
140°	165.4	166.8	171.7	179.4	188.9	199.7	213.3	227.8	243.1	260.3	279.7
142.5°	170.5	171.8	176.4	183.7	192.9	203.4	216.6	229.9	244.5	260.3	277.6
145°	177.6	179.0	183.5	189.8	198.4	208.3	220.1	232.3	245.4	259.4	273.9
147.5°	185.6	186.1	190.0	196.5	203.7	212.7	223.7	234.3	245.8	257.8	270.5
150°	190.7	191.2	194.8	200.2	207.0	215.6	225.5	235.4	245.8	256.7	268.0
152.5°	195.4	195.5	199.1	204.1	210.2	218.1	227.0	236.1	245.1	254.8	265.1
155°	202.0	202.5	205.2	209.7	214.7	221.4	229.1	236.8	244.0	252.2	260.7
157.5°	208.4	208.4	211.0	214.4	218.8	224.1	230.7	236.8	242.9	249.4	256.4
160°	212.4	212.4	214.2	217.4	220.9	225.9	231.4	236.8	241.8	247.2	253.1
162.5°	216.0	215.6	217.1	219.9	223.2	227.0	232.1	236.8	240.7	245.0	250.2
165°	220.1	220.1	220.9	223.2	225.5	228.2	232.3	235.9	238.6	241.8	245.4
167.5°	224.1	223.7	224.1	225.9	227.1	229.2	232.2	234.8	236.5	238.5	241.1
170°	225.9	225.5	225.9	227.3	228.2	229.6	231.8	234.1	235.0	236.3	238.1
172.5°	227.8	227.3	227.4	228.4	228.9	229.9	231.5	233.4	233.5	234.2	235.6
175°	229.6	229.1	229.1	229.6	230.0	230.0	230.9	232.3	231.8	231.8	232.7
177.5°	230.4	230.0	229.7	230.0	230.0	230.0	230.4	231.1	230.4	230.4	230.8
180°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0



TEST NUMBER: P332597-927

CATALOG NUMBER: SA4XXDIP-C795D590U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6
2.5°	1047.8	1049.3	1050.8	1051.5	1051.4	1051.2	1051.1	1050.9
5°	1042.2	1044.3	1046.3	1047.2	1046.8	1046.5	1046.1	1045.7
7.5°	1030.6	1032.3	1033.9	1034.6	1034.4	1034.2	1034.0	1033.7
10°	1020.9	1022.4	1023.9	1024.5	1024.1	1023.7	1023.3	1022.9
12.5°	1009.1	1010.7	1012.3	1012.9	1012.4	1011.9	1011.3	1010.8
15°	986.4	987.5	988.6	989.0	988.4	987.9	987.3	986.7
17.5°	960.7	961.4	962.1	962.3	961.9	961.5	961.2	960.8
20°	941.5	942.1	942.6	942.7	942.3	942.0	941.6	941.2
22.5°	921.5	922.5	923.5	923.7	923.0	922.3	921.6	921.0
25°	888.5	888.7	888.9	888.6	887.9	887.1	886.4	885.6
27.5°	851.5	851.0	850.6	849.9	849.0	848.0	847.1	846.1
30°	825.9	825.2	824.4	823.6	822.7	821.7	820.8	819.9
32.5°	800.0	799.2	798.3	797.3	796.4	795.4	794.5	793.6
35°	759.1	757.8	756.5	755.3	754.4	753.5	752.6	751.6
37.5°	716.2	714.8	713.4	712.1	710.8	709.6	708.4	707.1
40°	686.3	684.5	682.6	681.2	680.2	679.4	678.4	677.5
42.5°	657.4	655.3	653.1	651.7	651.1	650.5	649.8	649.2
45°	612.7	610.6	608.6	607.3	606.7	606.1	605.5	605.0
47.5°	569.3	567.0	564.7	562.8	561.4	560.0	558.6	557.1
50°	539.1	536.5	533.9	532.0	530.8	529.7	528.6	527.5
52.5°	508.0	505.6	503.4	501.5	500.1	498.7	497.3	495.8
55°	462.3	460.1	457.8	456.1	455.0	453.9	452.7	451.6
57.5°	416.5	414.4	412.3	410.7	409.6	408.4	407.4	406.3
60°	385.1	383.4	381.7	380.4	379.5	378.5	377.6	376.7
62.5°	354.3	352.8	351.3	350.1	349.1	348.2	347.3	346.3
65°	309.7	307.8	305.9	304.6	303.6	302.7	301.7	300.8
67.5°	263.7	261.9	260.1	259.0	258.8	258.6	258.3	258.0
70°	234.6	233.1	231.6	230.6	230.0	229.5	228.9	228.4
72.5°	205.6	204.4	203.2	202.3	201.7	201.1	200.6	200.0
75°	163.7	162.9	162.2	161.7	161.5	161.3	161.1	161.0
77.5°	123.9	123.7	123.5	123.1	122.6	122.2	121.7	121.2
80°	98.7	98.3	97.9	97.7	97.4	97.3	97.1	96.9
82.5°	76.0	75.8	75.6	75.4	75.3	75.0	74.9	74.6
85°	43.8	43.8	43.8	43.7	43.6	43.3	43.2	42.9
87.5°	17.8	17.9	18.0	18.0	18.1	18.1	18.1	18.1
90°	8.2	8.6	9.0	9.0	9.5	9.9	9.5	9.5
92.5°	88.7	66.8	53.2	44.1	38.7	36.4	34.8	34.8
95°	334.9	264.8	204.2	160.4	138.3	124.3	116.1	110.3
97.5°	494.7	468.7	424.5	377.3	344.9	317.7	304.1	294.7
100°	545.0	554.1	531.9	498.4	459.1	431.6	418.0	414.4
102.5°	542.5	587.3	593.7	579.8	555.6	535.7	521.4	518.5
105°	506.1	584.3	629.1	647.6	648.5	644.8	638.5	635.8
107.5°	454.6	537.7	600.8	641.0	663.4	673.7	678.2	679.4
110°	423.4	501.6	567.1	616.9	649.0	667.9	676.0	680.1



TEST NUMBER: P332597-927

CATALOG NUMBER: SA4XXDIP-C795D590U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	400.7	469.8	531.7	581.4	617.8	640.8	652.2	658.8
115°	377.8	433.4	486.2	529.7	565.3	592.5	606.9	610.5
117.5°	366.5	412.6	454.2	490.9	521.4	544.2	558.8	561.7
120°	361.6	403.5	439.7	471.7	497.6	517.5	529.2	534.2
122.5°	357.2	397.8	430.6	458.8	480.5	497.6	507.5	512.5
125°	349.7	388.6	419.8	444.7	462.7	475.9	484.4	487.1
127.5°	340.7	377.9	409.0	432.5	450.8	462.4	469.6	472.3
130°	333.5	369.2	399.9	423.9	442.4	453.7	461.0	463.7
132.5°	325.9	359.4	389.4	413.4	431.6	444.3	451.1	453.9
135°	315.4	344.8	372.3	395.0	413.0	425.7	432.9	435.6
137.5°	305.9	330.8	354.0	374.5	391.3	403.9	409.8	413.0
140°	300.5	321.8	342.1	361.1	376.9	386.8	393.2	396.8
142.5°	295.5	314.2	331.6	348.1	362.0	371.3	376.9	379.4
145°	288.3	303.6	317.3	329.9	341.2	348.9	353.4	355.6
147.5°	282.4	294.6	305.5	315.4	323.8	330.3	333.7	334.6
150°	278.8	289.2	298.3	306.4	313.6	319.5	322.2	322.7
152.5°	274.8	283.8	292.1	298.8	304.9	309.7	311.3	311.8
155°	268.9	276.1	282.9	288.3	292.9	296.4	297.8	297.8
157.5°	262.4	268.5	274.2	278.5	282.0	284.7	285.5	285.5
160°	258.5	263.5	268.4	272.0	274.7	277.5	277.9	277.9
162.5°	254.5	258.7	262.6	265.9	267.9	270.6	271.1	270.7
165°	249.0	251.7	254.8	257.1	259.0	260.7	260.3	259.8
167.5°	243.7	245.7	248.3	249.6	250.6	251.7	251.6	251.3
170°	240.4	241.8	243.6	244.9	245.8	246.3	245.8	245.8
172.5°	237.5	238.5	239.6	240.6	241.1	241.6	241.1	240.4
175°	233.6	234.1	235.0	235.0	235.0	235.9	235.0	234.1
177.5°	231.1	231.5	231.5	231.8	231.5	231.8	231.1	230.4
180°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0

(END OF REPORT)