

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332605-927

Luminaire Tested: **SA4XXDIP-C795D810U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332605-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C795D810U927-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4922.7 lumens  
Efficiency: N/A  
Efficacy: 107.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332605-927

CATALOG NUMBER: SA4XXDIP-C795D810U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332605-927

CATALOG NUMBER: SA4XXDIP-C795D810U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55				
1	99	94	90	87	92	88	84	81	75	73	71	64	62	61	53	52	51	46				
2	90	82	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43	39				
3	82	72	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33				
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28				
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	27	24				
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24	21				
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	19				
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19	17				
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15				
10	48	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8490	8490	8490
5°	8515	8413	8474
10°	8461	8344	8385
15°	8359	8226	8247
20°	8223	8079	8086
25°	8068	7911	7888
30°	7879	7713	7643
35°	7681	7508	7407
40°	7477	7273	7140
45°	7263	7042	6907
50°	7027	6836	6625
55°	6773	6570	6356
60°	6516	6273	6082
65°	6229	5989	5746
70°	5908	5611	5391
75°	5415	5153	5022
80°	4816	4621	4505
85°	4215	4057	3974



TEST NUMBER: P332605-927

CATALOG NUMBER: SA4XXDIP-C795D810U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.0	2.0
10°-20°	279.0	5.7
20°-30°	410.7	8.3
30°-40°	477.4	9.7
40°-50°	477.5	9.7
50°-60°	417.6	8.5
60°-70°	310.2	6.3
70°-80°	176.2	3.6
80°-90°	53.2	1.1
90°-100°	52.8	1.1
100°-110°	156.5	3.2
110°-120°	265.6	5.4
120°-130°	350.2	7.1
130°-140°	393.3	8.0
140°-150°	386.4	7.9
150°-160°	325.0	6.6
160°-170°	216.2	4.4
170°-180°	75.7	1.5
0°-30°	788.7	16.0
0°-40°	1266.2	25.7
0°-60°	2161.3	43.9
0°-90°	2700.9	54.9
90°-120°	474.9	9.6
90°-150°	1604.7	32.6
90°-180°	2222.0	45.1
0°-180°	4922.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1052	1052	1052	1052	1052	
5°	1051	1047	1038	1047	1046	100
15°	1000	996	984	989	987	282
25°	906	900	888	889	886	417
35°	779	773	762	756	752	487
45°	636	630	617	608	605	490
55°	481	478	467	457	452	431
65°	326	322	314	305	301	323
75°	174	169	165	162	161	184
85°	46	45	44	44	43	50
90°	2	9	14	17	19	5
95°	37	43	47	49	49	41
105°	144	145	147	149	151	153
115°	270	270	269	268	268	266
125°	393	393	393	391	390	350
135°	507	511	511	510	508	392
145°	616	619	619	619	617	386
155°	706	706	705	708	705	325
165°	769	767	766	769	767	217
175°	800	797	796	800	796	76
180°	801	801	801	801	801	



TEST NUMBER: P332605-927

CATALOG NUMBER: SA4XXDIP-C795D810U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6
2.5°	1054.3	1053.8	1053.4	1053.0	1052.5	1051.5	1049.8	1048.1	1046.5	1044.9	1046.3
5°	1050.8	1050.0	1049.2	1048.5	1047.7	1046.3	1044.3	1042.2	1040.1	1038.1	1040.1
7.5°	1041.0	1040.2	1039.5	1038.7	1038.0	1036.5	1034.2	1031.9	1029.6	1027.3	1029.0
10°	1032.2	1031.5	1030.7	1030.0	1029.2	1027.6	1025.2	1022.8	1020.3	1017.9	1019.4
12.5°	1020.7	1020.0	1019.2	1018.5	1017.8	1016.1	1013.5	1010.9	1008.4	1005.8	1007.4
15°	1000.2	999.4	998.7	997.9	997.2	995.5	992.6	989.8	987.0	984.2	985.3
17.5°	975.4	974.5	973.5	972.6	971.7	969.9	967.3	964.6	961.9	959.3	960.0
20°	957.2	956.2	955.4	954.4	953.5	951.6	948.8	945.9	943.2	940.4	941.0
22.5°	937.7	936.4	935.2	934.0	932.7	930.7	927.9	925.1	922.3	919.5	920.5
25°	905.8	904.5	903.2	901.9	900.6	898.6	896.0	893.3	890.7	888.1	888.3
27.5°	869.4	868.1	866.7	865.4	864.0	862.1	859.7	857.3	854.8	852.4	851.9
30°	845.2	843.7	842.2	840.7	839.2	837.2	834.7	832.3	829.9	827.4	826.7
32.5°	819.5	818.2	816.8	815.5	814.1	812.1	809.6	807.0	804.5	801.8	801.0
35°	779.4	778.1	776.8	775.5	774.2	772.2	769.6	767.0	764.4	761.8	760.4
37.5°	737.1	735.9	734.7	733.6	732.3	730.3	727.5	724.7	721.9	719.1	717.6
40°	709.5	708.0	706.5	705.0	703.5	701.3	698.5	695.7	692.9	690.1	688.2
42.5°	679.9	678.9	678.0	677.2	676.2	674.2	671.1	668.0	664.9	661.8	659.7
45°	636.2	634.9	633.6	632.2	631.0	628.8	625.8	622.8	619.8	616.8	614.7
47.5°	590.5	589.6	588.7	587.8	586.9	585.1	582.3	579.6	576.8	574.0	571.6
50°	559.5	558.7	558.0	557.2	556.5	554.8	552.2	549.6	546.9	544.3	541.7
52.5°	529.2	528.3	527.4	526.5	525.5	523.7	520.9	518.2	515.4	512.6	510.3
55°	481.2	480.5	480.0	479.4	478.9	477.3	474.7	472.1	469.4	466.8	464.5
57.5°	435.3	434.7	434.0	433.4	432.8	431.1	428.6	426.0	423.4	420.8	418.7
60°	403.6	402.7	401.7	400.8	399.9	398.2	395.8	393.3	390.9	388.5	386.7
62.5°	372.6	371.9	371.1	370.3	369.5	367.8	365.2	362.6	360.0	357.4	355.9
65°	326.1	325.2	324.2	323.3	322.3	320.9	319.1	317.2	315.3	313.5	311.6
67.5°	279.2	278.4	277.5	276.6	275.8	274.5	272.7	270.8	269.1	267.3	265.5
70°	250.3	249.0	247.6	246.3	245.0	243.6	242.1	240.6	239.1	237.7	236.1
72.5°	219.3	217.9	216.7	215.3	214.0	212.8	211.6	210.3	209.1	207.9	206.8
75°	173.6	172.6	171.7	170.8	169.8	168.9	167.9	167.0	166.1	165.2	164.4
77.5°	129.9	129.5	129.1	128.7	128.3	127.7	126.8	126.0	125.2	124.4	124.1
80°	103.6	103.1	102.5	102.0	101.4	100.9	100.5	100.2	99.8	99.4	99.0
82.5°	78.0	77.8	77.5	77.2	77.0	76.8	76.8	76.7	76.6	76.5	76.3
85°	45.5	45.5	45.5	45.5	45.5	45.3	44.9	44.6	44.2	43.8	43.8
87.5°	17.9	18.1	18.2	18.4	18.5	18.6	18.7	18.8	18.9	18.9	19.1
90°	1.8	3.4	4.9	6.4	7.9	9.2	10.3	11.4	12.5	13.6	14.4
92.5°	13.2	15.0	16.7	18.5	20.2	21.5	22.2	23.0	23.8	24.6	25.0
95°	37.2	38.4	39.6	40.9	42.1	43.3	44.2	45.2	46.1	47.1	47.5
97.5°	64.9	65.9	66.9	67.9	68.8	69.9	71.1	72.2	73.3	74.5	74.9
100°	86.7	87.2	87.8	88.3	88.9	89.8	91.0	92.3	93.5	94.7	95.1
102.5°	109.5	109.7	110.0	110.2	110.4	111.1	112.2	113.3	114.5	115.6	116.0
105°	144.3	144.4	144.6	144.7	144.9	145.2	145.8	146.3	146.9	147.4	147.8
107.5°	180.9	181.0	181.2	181.3	181.5	181.6	181.7	181.8	181.9	182.0	182.4
110°	205.7	205.9	206.1	206.4	206.7	206.8	206.7	206.5	206.4	206.2	206.0



TEST NUMBER: P332605-927

CATALOG NUMBER: SA4XXDIP-C795D810U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	231.4	231.4	231.5	231.6	231.6	231.5	231.2	231.0	230.8	230.5	230.4
115°	270.1	270.1	270.1	270.1	270.1	269.9	269.6	269.3	269.0	268.8	268.6
117.5°	306.4	306.6	306.7	306.7	306.9	306.8	306.7	306.4	306.3	306.1	305.6
120°	330.7	331.3	331.8	332.4	333.0	333.0	332.6	332.2	331.8	331.4	330.7
122.5°	356.0	356.2	356.4	356.6	356.9	356.9	356.7	356.5	356.3	356.1	355.6
125°	393.2	393.2	393.2	393.2	393.2	393.2	393.1	392.9	392.8	392.7	392.4
127.5°	427.1	427.5	427.9	428.3	428.7	428.8	428.6	428.4	428.2	427.9	427.7
130°	450.8	451.3	451.7	452.1	452.5	452.7	452.7	452.7	452.7	452.7	452.4
132.5°	475.2	475.5	475.8	476.0	476.3	476.4	476.3	476.3	476.1	476.0	475.7
135°	507.2	508.0	508.9	509.7	510.6	511.0	511.0	511.0	511.0	511.0	510.6
137.5°	542.2	542.6	542.9	543.3	543.7	544.0	544.2	544.5	544.6	544.9	544.5
140°	565.5	565.7	566.0	566.3	566.6	566.6	566.6	566.6	566.6	566.6	566.6
142.5°	586.8	587.0	587.3	587.6	587.9	588.0	587.8	587.7	587.6	587.5	587.5
145°	616.2	616.8	617.3	617.9	618.5	618.8	618.9	619.0	619.2	619.3	619.2
147.5°	645.5	646.1	646.7	647.5	648.1	648.4	648.2	648.2	648.0	647.9	647.8
150°	663.3	663.8	664.4	665.0	665.5	665.7	665.7	665.7	665.7	665.7	665.7
152.5°	680.2	680.5	680.8	681.1	681.4	681.7	681.8	681.9	682.0	682.1	682.5
155°	706.0	706.0	706.0	706.0	706.0	705.9	705.8	705.7	705.5	705.4	705.9
157.5°	727.9	727.5	727.3	727.1	726.8	726.7	726.7	726.7	726.6	726.6	727.0
160°	740.7	740.5	740.5	740.3	740.1	740.0	739.9	739.7	739.6	739.5	739.9
162.5°	752.6	752.3	751.9	751.5	751.1	750.9	750.8	750.7	750.5	750.4	751.1
165°	768.6	768.2	767.8	767.3	766.9	766.6	766.3	766.0	765.7	765.5	766.3
167.5°	780.9	780.2	779.7	779.1	778.6	778.2	778.2	778.3	778.3	778.3	779.2
170°	787.7	787.1	786.4	785.7	785.1	784.7	784.9	785.1	785.1	785.3	786.1
172.5°	792.7	792.2	791.5	791.0	790.4	790.1	790.2	790.2	790.2	790.3	791.2
175°	799.5	798.8	798.1	797.5	796.8	796.4	796.2	796.1	796.0	795.8	796.8
177.5°	801.8	801.2	800.7	800.1	799.5	799.3	799.3	799.3	799.3	799.3	800.0
180°	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7



TEST NUMBER: P332605-927

CATALOG NUMBER: SA4XXDIP-C795D810U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6
2.5°	1047.8	1049.3	1050.8	1051.5	1051.4	1051.2	1051.1	1050.9
5°	1042.2	1044.3	1046.3	1047.2	1046.8	1046.5	1046.1	1045.7
7.5°	1030.6	1032.3	1033.9	1034.6	1034.4	1034.2	1034.0	1033.7
10°	1020.9	1022.4	1023.9	1024.5	1024.1	1023.7	1023.3	1022.9
12.5°	1009.1	1010.7	1012.3	1012.9	1012.4	1011.9	1011.3	1010.8
15°	986.4	987.5	988.6	989.0	988.4	987.9	987.3	986.7
17.5°	960.7	961.4	962.1	962.3	961.9	961.5	961.2	960.8
20°	941.5	942.1	942.6	942.7	942.3	942.0	941.6	941.2
22.5°	921.5	922.5	923.5	923.7	923.0	922.3	921.6	921.0
25°	888.5	888.7	888.9	888.6	887.9	887.1	886.4	885.6
27.5°	851.5	851.0	850.6	849.9	849.0	848.0	847.1	846.1
30°	825.9	825.2	824.4	823.6	822.7	821.7	820.8	819.9
32.5°	800.0	799.2	798.3	797.3	796.4	795.4	794.5	793.6
35°	759.1	757.8	756.5	755.3	754.4	753.5	752.6	751.6
37.5°	716.2	714.8	713.4	712.1	710.8	709.6	708.4	707.1
40°	686.3	684.5	682.6	681.2	680.2	679.4	678.4	677.5
42.5°	657.4	655.3	653.1	651.7	651.1	650.5	649.8	649.2
45°	612.7	610.6	608.6	607.3	606.7	606.1	605.5	605.0
47.5°	569.3	567.0	564.7	562.8	561.4	560.0	558.6	557.1
50°	539.1	536.5	533.9	532.0	530.8	529.7	528.6	527.5
52.5°	508.0	505.6	503.4	501.5	500.1	498.7	497.3	495.8
55°	462.3	460.1	457.8	456.1	455.0	453.9	452.7	451.6
57.5°	416.5	414.4	412.3	410.7	409.6	408.4	407.4	406.3
60°	385.1	383.4	381.7	380.4	379.5	378.5	377.6	376.7
62.5°	354.3	352.8	351.3	350.1	349.1	348.2	347.3	346.3
65°	309.7	307.8	305.9	304.6	303.6	302.7	301.7	300.8
67.5°	263.7	261.9	260.1	259.0	258.8	258.6	258.3	258.0
70°	234.6	233.1	231.6	230.6	230.0	229.5	228.9	228.4
72.5°	205.6	204.4	203.2	202.3	201.7	201.1	200.6	200.0
75°	163.7	162.9	162.2	161.7	161.5	161.3	161.1	161.0
77.5°	123.9	123.7	123.5	123.1	122.6	122.2	121.7	121.2
80°	98.7	98.3	97.9	97.7	97.4	97.3	97.1	96.9
82.5°	76.0	75.8	75.6	75.4	75.3	75.0	74.9	74.6
85°	43.8	43.8	43.8	43.7	43.6	43.3	43.2	42.9
87.5°	19.3	19.4	19.6	19.6	19.7	19.8	19.8	19.9
90°	15.3	16.1	17.0	17.5	17.7	18.1	18.3	18.6
92.5°	25.5	26.0	26.5	26.9	27.0	27.2	27.3	27.5
95°	47.9	48.3	48.7	49.0	49.0	49.0	49.0	49.0
97.5°	75.4	75.9	76.4	76.7	76.7	76.7	76.7	76.7
100°	95.3	95.6	95.9	96.0	96.0	96.0	96.0	96.0
102.5°	116.4	116.7	117.1	117.3	117.5	117.6	117.7	117.8
105°	148.2	148.6	149.0	149.5	149.9	150.3	150.7	151.1
107.5°	182.8	183.1	183.5	183.7	183.6	183.6	183.6	183.5
110°	205.7	205.4	205.1	205.2	205.7	206.0	206.4	206.8





TEST NUMBER: P332605-927

CATALOG NUMBER: SA4XXDIP-C795D810U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	230.4	230.4	230.3	230.3	230.4	230.4	230.5	230.6
115°	268.5	268.4	268.2	268.1	268.0	267.8	267.7	267.5
117.5°	305.1	304.7	304.2	303.8	303.6	303.2	303.0	302.7
120°	329.9	329.2	328.6	328.4	328.7	328.9	329.2	329.5
122.5°	355.1	354.7	354.3	353.8	353.2	352.8	352.3	351.8
125°	392.1	391.8	391.6	391.3	391.0	390.7	390.5	390.1
127.5°	427.4	427.1	426.8	426.6	426.4	426.2	426.0	425.7
130°	452.2	451.9	451.6	451.2	450.7	450.1	449.6	449.0
132.5°	475.5	475.2	474.9	474.7	474.4	474.2	474.0	473.8
135°	510.4	510.1	509.8	509.5	509.1	508.7	508.3	507.9
137.5°	544.2	543.8	543.4	543.3	543.4	543.4	543.5	543.7
140°	566.4	566.3	566.1	566.0	565.9	565.7	565.5	565.5
142.5°	587.4	587.4	587.4	587.3	587.3	587.3	587.2	587.2
145°	619.0	618.9	618.8	618.5	618.1	617.7	617.3	616.9
147.5°	647.7	647.6	647.5	647.4	647.2	647.1	647.0	646.8
150°	665.7	665.7	665.7	665.7	665.6	665.4	665.3	665.1
152.5°	682.8	683.1	683.4	683.4	683.1	682.7	682.4	682.0
155°	706.5	707.0	707.6	707.6	707.0	706.5	705.9	705.4
157.5°	727.4	727.9	728.3	728.2	727.8	727.3	726.8	726.4
160°	740.3	740.7	741.1	741.0	740.3	739.6	738.9	738.2
162.5°	751.9	752.6	753.4	753.4	752.7	752.0	751.3	750.6
165°	767.1	767.9	768.8	768.9	768.3	767.8	767.2	766.8
167.5°	780.0	780.9	781.6	781.6	780.8	779.9	779.1	778.2
170°	787.0	787.7	788.6	788.5	787.6	786.6	785.6	784.7
172.5°	792.1	793.1	794.0	794.0	793.1	792.0	791.1	790.1
175°	797.7	798.7	799.7	799.7	798.7	797.7	796.8	795.8
177.5°	800.8	801.6	802.4	802.3	801.5	800.6	799.7	798.8
180°	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7

(END OF REPORT)