

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331268-840

Luminaire Tested: **SA2XXDIP-C290D925U840-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331268-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C290D925U840-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4661.0 lumens  
Efficiency: N/A  
Efficacy: 125.0 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331268-840  
CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331268-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28				
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31	24				
2	85	78	72	67	76	70	65	61	55	52	49	41	39	38	29	28	27	21				
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23	18				
4	71	61	53	48	63	55	49	44	44	39	36	33	30	28	23	21	20	16				
5	65	54	47	41	58	49	42	37	39	34	31	30	26	24	21	19	17	14				
6	60	49	41	35	54	44	37	33	35	30	27	27	24	21	19	17	16	12				
7	56	44	36	31	50	40	33	29	32	27	24	24	21	19	17	15	14	11				
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12	10				
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9				
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9637	9637	9637	9637
5°	10804	9700	8596	9700
10°	12381	9621	7438	9621
15°	13697	9444	6572	9444
20°	13490	9256	5991	9256
25°	12162	9002	5624	9002
30°	10051	8600	5354	8600
35°	7324	8180	5164	8180
40°	5851	7685	5056	7685
45°	5112	7108	4914	7108
50°	4808	6551	4818	6551
55°	4428	5987	4687	5987
60°	4059	5383	4492	5383
65°	3698	4844	4294	4844
70°	3356	4319	4008	4319
75°	2982	3737	3550	3737
80°	2566	3087	2854	3087
85°	2297	2297	1704	2297



TEST NUMBER: P331268-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.8	1.2
10°-20°	165.3	3.5
20°-30°	239.9	5.1
30°-40°	253.1	5.4
40°-50°	224.1	4.8
50°-60°	178.8	3.8
60°-70°	121.6	2.6
70°-80°	62.3	1.3
80°-90°	19.8	0.4
90°-100°	75.7	1.6
100°-110°	235.0	5.0
110°-120°	401.8	8.6
120°-130°	528.3	11.3
130°-140°	593.0	12.7
140°-150°	581.4	12.5
150°-160°	487.7	10.5
160°-170°	323.5	6.9
170°-180°	113.0	2.4
0°-30°	462.0	9.9
0°-40°	715.1	15.3
0°-60°	1118.0	24.0
0°-90°	1321.7	28.4
90°-120°	712.5	15.3
90°-150°	2415.2	51.8
90°-180°	3339.0	71.6
0°-180°	4661.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	597	597	597	597	597	
5°	667	598	530	598	667	67
15°	819	565	393	565	819	226
25°	683	505	316	505	683	309
35°	372	415	262	415	372	242
45°	224	311	215	311	224	176
55°	157	213	166	213	157	141
65°	97	127	112	127	97	96
75°	48	60	57	60	48	51
85°	12	12	9	12	12	14
90°	34	1	34	1	34	15
95°	62	52	62	52	62	70
105°	224	217	224	217	224	235
115°	403	403	403	403	403	398
125°	588	586	588	586	588	525
135°	768	759	768	759	768	591
145°	931	921	931	921	931	582
155°	1061	1053	1061	1053	1061	488
165°	1147	1146	1147	1146	1147	323
175°	1188	1192	1188	1192	1188	113
180°	1194	1194	1194	1194	1194	



TEST NUMBER: P331268-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	624.4	624.6	625.0	622.1	621.7	621.7	619.1	616.9	614.3	610.9	611.3
5°	666.6	669.1	670.0	667.3	663.2	662.8	658.8	652.5	646.4	641.7	638.2
7.5°	717.0	718.0	715.8	712.2	709.1	703.6	696.3	689.2	679.2	670.1	663.4
10°	755.2	756.6	752.7	747.4	743.1	736.6	726.1	715.3	702.3	689.6	679.5
12.5°	784.2	787.6	782.5	781.9	774.5	765.6	753.1	747.6	729.2	711.7	700.7
15°	819.4	819.2	819.7	815.3	809.8	808.4	795.2	780.6	754.8	744.4	726.5
17.5°	809.2	812.7	814.4	814.3	814.2	813.2	809.0	799.9	786.9	770.1	749.5
20°	785.1	789.6	790.3	795.6	798.6	802.4	804.1	801.5	793.6	779.5	761.6
22.5°	747.6	748.9	751.0	759.2	765.7	775.5	780.5	789.1	786.0	779.1	764.2
25°	682.7	680.4	688.4	692.6	707.5	723.1	734.4	746.7	757.7	764.4	760.0
27.5°	604.8	601.4	613.4	624.4	636.4	653.4	670.9	691.6	708.7	730.3	737.7
30°	539.1	541.2	552.6	564.3	582.7	606.5	626.3	648.9	673.6	697.6	714.4
32.5°	468.3	476.2	483.4	501.4	517.6	544.1	573.1	601.5	632.1	659.4	685.4
35°	371.6	380.8	390.9	403.9	426.7	453.0	481.3	519.6	561.4	598.7	629.4
37.5°	312.9	311.3	317.1	326.6	345.0	366.3	398.8	436.6	485.7	529.7	573.1
40°	277.6	276.7	280.7	289.5	303.5	319.1	347.6	380.8	426.5	480.2	531.8
42.5°	253.4	253.9	256.2	262.4	272.0	284.8	306.1	334.4	376.2	426.8	482.2
45°	223.9	225.5	228.0	231.1	236.5	247.1	259.0	279.2	312.3	354.5	409.0
47.5°	202.7	202.8	205.3	207.9	211.2	217.1	226.9	239.5	262.9	297.2	344.2
50°	191.4	189.8	191.6	193.6	197.0	201.2	207.6	219.5	235.1	262.9	302.2
52.5°	177.3	177.4	179.0	179.9	182.9	187.0	192.9	201.2	215.3	237.0	269.2
55°	157.3	158.5	159.5	160.8	163.6	166.5	171.2	176.6	187.6	203.9	227.8
57.5°	138.6	139.0	139.9	142.5	144.2	146.9	151.3	156.3	163.5	175.5	193.5
60°	125.7	125.7	127.5	128.7	131.0	133.7	137.1	142.0	148.5	158.2	172.8
62.5°	114.0	113.8	114.5	116.4	118.2	120.7	124.1	128.3	134.3	143.1	154.9
65°	96.8	96.3	97.8	98.2	100.0	102.5	105.3	109.7	114.5	120.9	131.5
67.5°	80.3	80.9	81.6	82.4	83.4	86.1	88.0	91.0	95.1	100.5	107.6
70°	71.1	71.1	71.1	71.8	73.2	74.5	76.3	78.9	82.8	87.4	93.8
72.5°	60.8	61.6	62.3	61.9	63.6	64.4	66.7	68.1	71.8	74.7	80.4
75°	47.8	47.8	47.8	48.9	49.6	50.2	51.6	53.0	54.8	58.5	61.5
77.5°	35.6	35.5	35.7	36.1	36.8	37.6	38.0	39.2	40.9	42.6	45.1
80°	27.6	28.0	28.2	28.7	28.7	29.1	29.4	31.0	32.1	33.2	34.8
82.5°	21.3	21.4	21.4	21.5	21.7	22.0	22.6	23.1	23.5	24.4	25.7
85°	12.4	12.1	12.1	12.6	12.4	12.4	12.8	13.3	13.3	13.5	14.2
87.5°	11.6	11.6	11.7	11.5	11.4	11.6	11.7	11.6	11.9	12.2	11.4
90°	34.2	34.0	33.8	33.6	33.3	33.5	33.9	34.3	34.8	35.2	30.3
92.5°	32.6	32.6	32.5	32.5	32.5	32.4	32.3	32.2	32.1	32.0	30.9
95°	62.5	62.9	63.4	63.8	64.2	64.5	64.5	64.5	64.5	64.5	64.0
97.5°	108.3	108.3	108.4	108.4	108.5	108.5	108.5	108.5	108.5	108.5	107.6
100°	138.0	138.3	138.6	138.8	139.0	139.1	139.1	139.1	139.1	139.1	138.5
102.5°	172.0	172.2	172.4	172.6	172.8	172.9	172.7	172.5	172.3	172.2	171.3
105°	223.7	223.7	223.7	223.7	223.7	223.5	223.1	222.6	222.2	221.7	221.3
107.5°	272.5	273.6	274.6	275.6	276.6	277.0	276.9	276.7	276.5	276.3	276.3
110°	310.4	311.0	311.7	312.5	313.1	313.5	313.5	313.5	313.5	313.5	313.5



TEST NUMBER: P331268-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	346.7	347.2	347.7	348.2	348.6	349.2	349.7	350.2	350.8	351.3	351.5
115°	403.1	403.7	404.5	405.2	405.8	406.3	406.5	406.7	407.0	407.2	407.6
117.5°	457.0	457.6	458.3	459.0	459.6	460.2	460.8	461.3	461.8	462.4	463.6
120°	494.8	495.5	496.1	496.9	497.6	497.9	497.9	497.9	497.9	497.9	499.7
122.5°	531.9	532.4	532.9	533.4	533.9	534.4	534.9	535.4	536.0	536.5	537.9
125°	588.5	588.8	589.0	589.3	589.5	589.9	590.6	591.3	591.9	592.6	593.3
127.5°	640.2	640.9	641.6	642.3	643.0	643.8	644.6	645.4	646.2	647.0	647.8
130°	677.2	678.1	679.0	679.9	680.9	681.5	682.0	682.4	682.9	683.3	683.8
132.5°	712.8	713.5	714.2	714.9	715.6	716.4	717.4	718.4	719.4	720.3	720.2
135°	767.9	768.6	769.3	769.9	770.6	771.0	771.3	771.5	771.7	771.9	771.5
137.5°	817.9	818.8	819.7	820.6	821.5	822.0	822.2	822.4	822.6	822.7	822.2
140°	852.6	853.5	854.3	855.3	856.2	856.7	856.7	856.7	856.7	856.7	855.6
142.5°	884.0	884.9	885.9	886.8	887.7	888.0	887.8	887.7	887.5	887.3	886.5
145°	931.2	932.1	933.0	933.9	934.8	935.1	934.9	934.6	934.4	934.2	932.9
147.5°	973.3	974.2	975.0	975.9	976.7	976.9	976.4	975.9	975.4	974.9	974.0
150°	1000.8	1001.4	1002.1	1002.8	1003.4	1003.4	1002.8	1002.1	1001.4	1000.8	999.9
152.5°	1026.5	1027.4	1028.2	1029.1	1030.0	1030.0	1029.1	1028.2	1027.4	1026.5	1025.4
155°	1061.2	1061.9	1062.6	1063.2	1063.9	1063.7	1062.6	1061.5	1060.4	1059.1	1058.5
157.5°	1091.1	1092.1	1093.2	1094.3	1095.3	1095.1	1093.6	1092.1	1090.6	1089.0	1088.6
160°	1109.5	1110.4	1111.4	1112.3	1113.2	1113.0	1111.6	1110.2	1108.9	1107.5	1107.3
162.5°	1125.7	1126.8	1127.8	1128.9	1130.0	1129.7	1128.2	1126.7	1125.2	1123.7	1123.5
165°	1146.9	1148.0	1149.1	1150.2	1151.3	1151.1	1149.5	1148.0	1146.4	1144.9	1144.9
167.5°	1164.2	1165.4	1166.5	1167.7	1168.8	1168.6	1167.1	1165.5	1164.0	1162.4	1162.5
170°	1173.1	1174.4	1175.8	1177.1	1178.4	1178.3	1176.8	1175.2	1173.7	1172.0	1172.3
172.5°	1180.3	1181.6	1183.1	1184.4	1185.7	1185.6	1184.1	1182.5	1180.9	1179.3	1179.5
175°	1188.2	1189.5	1190.8	1192.2	1193.6	1193.5	1191.8	1190.3	1188.7	1187.2	1187.6
177.5°	1191.8	1192.9	1194.0	1195.1	1196.1	1196.1	1195.1	1194.0	1192.9	1191.8	1192.1
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331268-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	612.5	611.1	610.2	606.8	603.9	601.0	600.1	600.4	596.3	592.5	590.9
5°	636.4	631.8	627.4	621.3	613.9	605.8	601.8	598.5	590.5	581.8	576.7
7.5°	657.7	651.2	642.8	631.2	620.5	607.8	599.8	592.7	581.0	568.7	561.1
10°	670.8	661.9	651.1	636.8	623.8	608.3	597.6	586.8	573.1	558.4	549.2
12.5°	682.0	669.9	659.3	641.1	625.6	606.3	593.6	578.3	563.9	546.4	537.5
15°	708.6	686.4	666.2	645.5	626.5	599.7	585.4	565.0	546.0	524.4	514.1
17.5°	729.2	704.2	672.5	646.2	624.0	594.2	573.4	549.0	526.4	501.8	487.8
20°	740.9	712.3	678.1	646.9	620.4	586.3	563.6	538.7	512.3	484.5	469.4
22.5°	747.9	717.8	684.0	644.2	613.0	580.0	551.4	523.9	497.3	467.3	451.4
25°	750.1	722.7	686.8	641.9	603.8	566.4	532.0	505.3	473.0	445.0	421.9
27.5°	739.2	719.5	685.1	637.5	593.2	549.5	511.1	481.0	446.9	416.5	393.1
30°	725.8	714.4	680.9	633.2	584.7	537.8	495.5	461.3	427.4	396.7	372.7
32.5°	705.1	702.7	673.2	626.9	575.7	522.9	479.2	444.6	407.0	376.8	354.1
35°	664.4	675.4	656.8	613.0	558.9	501.7	454.4	415.0	376.0	347.1	325.8
37.5°	609.8	637.1	632.3	592.6	535.9	478.7	426.5	385.3	348.1	318.9	298.0
40°	572.1	607.0	612.1	576.9	519.9	460.9	405.6	364.6	328.3	301.6	280.5
42.5°	531.8	572.5	586.3	558.3	502.2	442.1	386.9	344.4	308.4	282.6	263.9
45°	464.1	518.0	543.0	526.9	472.8	411.3	354.5	311.3	278.7	254.4	239.9
47.5°	400.8	459.7	493.3	487.7	440.1	379.2	323.0	281.6	249.8	230.5	217.5
50°	356.1	416.6	457.2	459.1	416.6	356.3	299.8	260.8	231.7	213.6	203.0
52.5°	317.1	375.0	419.2	429.0	390.3	332.4	279.1	240.2	214.6	197.9	188.5
55°	266.3	315.2	364.3	382.2	351.2	296.2	246.8	212.7	188.5	177.1	168.8
57.5°	221.5	262.2	307.5	327.3	308.2	261.1	214.8	185.1	165.6	155.5	149.2
60°	197.7	229.8	270.2	293.9	277.3	235.4	195.0	166.7	150.7	141.8	135.8
62.5°	175.7	204.2	238.3	259.9	251.0	211.4	175.2	150.3	136.4	128.1	123.7
65°	145.0	167.4	193.9	213.8	207.8	177.8	148.1	126.8	115.8	109.2	105.7
67.5°	119.4	135.6	153.9	171.4	166.6	145.3	121.6	104.9	96.7	91.0	88.9
70°	103.2	115.6	131.9	145.9	142.0	124.6	105.7	91.5	84.4	79.6	77.6
72.5°	87.9	98.0	110.5	121.9	119.3	104.7	89.1	78.4	72.8	68.4	66.8
75°	66.3	74.1	81.7	89.3	88.6	77.4	68.2	59.9	55.5	52.1	51.4
77.5°	49.0	53.3	58.5	62.9	61.7	55.2	48.1	43.3	40.2	37.9	37.5
80°	37.4	39.9	43.6	46.8	45.2	42.4	36.7	33.2	31.0	28.7	27.8
82.5°	27.2	29.6	31.8	33.6	32.3	29.8	26.3	23.9	22.5	21.0	20.6
85°	14.2	15.6	16.6	17.0	16.6	14.9	13.3	12.4	11.2	10.5	10.3
87.5°	10.6	9.6	8.6	8.2	7.2	6.6	5.4	4.2	4.5	4.9	5.2
90°	25.4	20.5	15.6	11.7	9.1	6.4	3.7	1.0	3.7	6.4	9.1
92.5°	29.7	28.6	27.4	25.9	23.8	21.9	19.9	18.0	19.9	21.9	23.8
95°	63.6	63.1	62.7	61.4	59.1	56.9	54.6	52.4	54.6	56.9	59.1
97.5°	106.7	105.9	105.0	103.6	101.7	99.7	97.8	95.7	97.8	99.7	101.7
100°	137.7	137.0	136.4	135.1	133.4	131.6	129.8	127.9	129.8	131.6	133.4
102.5°	170.5	169.6	168.7	167.5	166.1	164.7	163.3	161.9	163.3	164.7	166.1
105°	220.9	220.4	219.9	219.3	218.7	218.0	217.3	216.7	217.3	218.0	218.7
107.5°	276.3	276.3	276.3	275.9	274.9	273.9	272.9	271.9	272.9	273.9	274.9
110°	313.5	313.5	313.5	312.8	311.4	310.0	308.7	307.4	308.7	310.0	311.4





TEST NUMBER: P331268-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	351.6	351.8	352.0	351.4	350.1	348.8	347.4	346.1	347.4	348.8	350.1
115°	408.1	408.5	408.9	408.5	407.2	405.8	404.5	403.1	404.5	405.8	407.2
117.5°	464.8	466.2	467.4	467.2	465.3	463.5	461.7	460.0	461.7	463.5	465.3
120°	501.4	503.2	505.0	505.0	503.2	501.4	499.7	497.9	499.7	501.4	503.2
122.5°	539.1	540.3	541.6	541.1	539.0	536.8	534.6	532.5	534.6	536.8	539.0
125°	593.9	594.6	595.3	594.6	592.6	590.6	588.5	586.5	588.5	590.6	592.6
127.5°	648.6	649.4	650.3	649.3	646.8	644.3	641.7	639.1	641.7	644.3	646.8
130°	684.2	684.6	685.1	683.9	681.0	678.0	675.1	672.2	675.1	678.0	681.0
132.5°	720.2	720.1	720.0	718.8	716.4	714.1	711.7	709.3	711.7	714.1	716.4
135°	771.0	770.6	770.2	768.7	766.3	763.8	761.3	758.9	761.3	763.8	766.3
137.5°	821.6	821.0	820.4	819.1	817.1	815.1	813.0	811.1	813.0	815.1	817.1
140°	854.3	853.2	852.1	850.6	848.6	846.6	844.6	842.5	844.6	846.6	848.6
142.5°	885.8	884.9	884.2	882.8	880.8	878.8	876.8	874.7	876.8	878.8	880.8
145°	931.5	930.2	928.9	927.4	925.8	924.2	922.7	921.1	922.7	924.2	925.8
147.5°	973.1	972.3	971.4	970.0	968.1	966.2	964.3	962.4	964.3	966.2	968.1
150°	999.0	998.0	997.1	996.0	994.7	993.3	992.0	990.7	992.0	993.3	994.7
152.5°	1024.4	1023.3	1022.3	1021.1	1019.7	1018.3	1017.0	1015.6	1017.0	1018.3	1019.7
155°	1057.8	1057.2	1056.5	1055.8	1055.2	1054.5	1053.8	1053.2	1053.8	1054.5	1055.2
157.5°	1088.2	1087.8	1087.4	1087.0	1086.5	1086.1	1085.6	1085.2	1085.6	1086.1	1086.5
160°	1107.1	1106.9	1106.7	1106.3	1105.9	1105.4	1105.0	1104.6	1105.0	1105.4	1105.9
162.5°	1123.3	1123.1	1122.8	1122.7	1122.6	1122.5	1122.4	1122.3	1122.4	1122.5	1122.6
165°	1144.9	1144.9	1144.9	1145.0	1145.2	1145.4	1145.7	1145.9	1145.7	1145.4	1145.2
167.5°	1162.5	1162.6	1162.6	1163.0	1163.6	1164.3	1165.0	1165.6	1165.0	1164.3	1163.6
170°	1172.6	1172.8	1173.0	1173.4	1174.1	1174.8	1175.4	1176.1	1175.4	1174.8	1174.1
172.5°	1179.7	1180.0	1180.2	1180.6	1181.3	1182.0	1182.7	1183.4	1182.7	1182.0	1181.3
175°	1188.1	1188.5	1189.0	1189.5	1190.2	1190.8	1191.5	1192.2	1191.5	1190.8	1190.2
177.5°	1192.5	1192.9	1193.3	1193.7	1194.3	1194.8	1195.3	1195.9	1195.3	1194.8	1194.3
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331268-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	589.1	587.9	584.1	582.1	578.8	575.6	573.6	574.5	575.2	574.9	574.3
5°	572.1	567.7	561.1	555.4	551.3	543.7	540.5	538.9	537.5	535.9	534.3
7.5°	552.0	545.1	535.6	527.5	519.8	510.3	504.9	501.8	498.5	494.8	491.6
10°	537.8	528.1	518.0	506.5	497.4	488.9	481.3	476.3	471.6	467.3	464.1
12.5°	522.7	511.6	499.1	483.4	473.3	461.1	460.0	451.1	443.9	441.2	437.5
15°	498.8	483.1	467.3	448.7	440.7	429.7	422.8	415.9	409.7	405.4	404.2
17.5°	471.5	451.3	435.6	422.2	409.1	397.8	391.4	386.0	380.8	375.1	374.3
20°	450.8	433.3	416.2	404.5	390.9	379.4	371.6	366.2	361.7	358.3	355.4
22.5°	431.1	412.0	396.3	383.5	370.2	360.9	354.8	349.4	345.8	342.0	339.2
25°	399.6	384.8	367.5	353.0	342.0	336.1	331.0	326.5	324.2	321.6	318.4
27.5°	372.0	355.5	339.4	328.2	318.5	313.3	309.6	306.5	304.4	302.9	301.0
30°	352.6	335.9	323.3	312.3	304.2	298.9	296.6	294.8	292.3	291.3	290.4
32.5°	333.9	318.8	308.0	298.4	290.8	287.3	285.3	283.6	281.7	280.7	278.8
35°	307.4	294.8	284.3	278.9	272.8	269.7	268.2	265.9	264.1	263.2	262.9
37.5°	282.5	271.6	264.6	257.8	255.2	253.4	251.2	249.6	249.0	248.9	248.6
40°	266.3	257.4	251.2	245.7	244.6	241.8	239.9	238.6	238.6	238.8	238.6
42.5°	251.7	243.6	238.1	233.4	232.1	230.5	228.5	228.5	228.8	229.6	228.8
45°	229.4	223.7	219.7	217.5	215.0	213.4	213.1	213.8	214.0	214.3	215.0
47.5°	208.9	205.1	201.6	199.0	197.9	197.7	197.4	198.6	199.8	200.2	201.2
50°	196.8	192.5	189.5	187.8	186.9	186.5	186.9	188.3	189.2	190.4	191.1
52.5°	183.3	180.2	178.1	176.8	176.5	176.8	176.8	178.4	179.9	180.4	180.7
55°	164.5	162.2	161.8	159.7	160.6	160.4	161.5	162.4	163.8	165.2	165.4
57.5°	145.7	143.9	142.7	142.9	143.2	144.2	145.1	146.7	148.1	149.7	149.8
60°	133.3	132.4	131.7	131.7	132.1	133.5	134.6	136.2	137.1	138.1	138.8
62.5°	121.9	121.0	120.3	120.7	121.9	122.7	124.0	124.9	125.8	126.7	127.0
65°	103.9	103.5	104.1	104.6	104.8	105.9	107.6	108.3	109.2	109.7	111.3
67.5°	87.4	87.5	87.4	88.0	89.4	89.6	91.1	92.7	92.9	93.8	94.8
70°	76.1	76.6	77.1	77.6	78.7	79.2	80.3	81.0	81.9	82.6	83.3
72.5°	65.8	65.9	66.4	66.3	67.4	68.3	69.3	70.0	70.9	71.8	72.4
75°	50.7	50.7	51.2	51.4	52.5	53.7	53.4	53.9	54.8	55.7	56.2
77.5°	37.1	36.6	37.1	37.3	37.7	38.6	38.8	39.4	40.5	40.2	40.7
80°	28.2	27.6	28.2	28.5	28.5	29.6	29.6	30.1	30.7	30.1	30.7
82.5°	20.1	19.8	20.3	20.4	20.7	20.8	21.1	21.2	21.9	21.6	21.9
85°	10.1	9.9	10.1	9.9	10.1	10.3	10.3	10.1	10.1	10.5	9.9
87.5°	5.5	6.1	6.9	7.9	8.7	9.4	9.2	9.1	9.0	8.5	8.5
90°	11.7	15.6	20.5	25.4	30.3	35.2	34.8	34.3	33.9	33.5	33.3
92.5°	25.9	27.4	28.6	29.7	30.9	32.0	32.1	32.2	32.3	32.4	32.5
95°	61.4	62.7	63.1	63.6	64.0	64.5	64.5	64.5	64.5	64.5	64.2
97.5°	103.6	105.0	105.9	106.7	107.6	108.5	108.5	108.5	108.5	108.5	108.5
100°	135.1	136.4	137.0	137.7	138.5	139.1	139.1	139.1	139.1	139.1	139.0
102.5°	167.5	168.7	169.6	170.5	171.3	172.2	172.3	172.5	172.7	172.9	172.8
105°	219.3	219.9	220.4	220.9	221.3	221.7	222.2	222.6	223.1	223.5	223.7
107.5°	275.9	276.3	276.3	276.3	276.3	276.3	276.5	276.7	276.9	277.0	276.6
110°	312.8	313.5	313.5	313.5	313.5	313.5	313.5	313.5	313.5	313.5	313.1



TEST NUMBER: P331268-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	351.4	352.0	351.8	351.6	351.5	351.3	350.8	350.2	349.7	349.2	348.6
115°	408.5	408.9	408.5	408.1	407.6	407.2	407.0	406.7	406.5	406.3	405.8
117.5°	467.2	467.4	466.2	464.8	463.6	462.4	461.8	461.3	460.8	460.2	459.6
120°	505.0	505.0	503.2	501.4	499.7	497.9	497.9	497.9	497.9	497.9	497.6
122.5°	541.1	541.6	540.3	539.1	537.9	536.5	536.0	535.4	534.9	534.4	533.9
125°	594.6	595.3	594.6	593.9	593.3	592.6	591.9	591.3	590.6	589.9	589.5
127.5°	649.3	650.3	649.4	648.6	647.8	647.0	646.2	645.4	644.6	643.8	643.0
130°	683.9	685.1	684.6	684.2	683.8	683.3	682.9	682.4	682.0	681.5	680.9
132.5°	718.8	720.0	720.1	720.2	720.2	720.3	719.4	718.4	717.4	716.4	715.6
135°	768.7	770.2	770.6	771.0	771.5	771.9	771.7	771.5	771.3	771.0	770.6
137.5°	819.1	820.4	821.0	821.6	822.2	822.7	822.6	822.4	822.2	822.0	821.5
140°	850.6	852.1	853.2	854.3	855.6	856.7	856.7	856.7	856.7	856.7	856.2
142.5°	882.8	884.2	884.9	885.8	886.5	887.3	887.5	887.7	887.8	888.0	887.7
145°	927.4	928.9	930.2	931.5	932.9	934.2	934.4	934.6	934.9	935.1	934.8
147.5°	970.0	971.4	972.3	973.1	974.0	974.9	975.4	975.9	976.4	976.9	976.7
150°	996.0	997.1	998.0	999.0	999.9	1000.8	1001.4	1002.1	1002.8	1003.4	1003.4
152.5°	1021.1	1022.3	1023.3	1024.4	1025.4	1026.5	1027.4	1028.2	1029.1	1030.0	1030.0
155°	1055.8	1056.5	1057.2	1057.8	1058.5	1059.1	1060.4	1061.5	1062.6	1063.7	1063.9
157.5°	1087.0	1087.4	1087.8	1088.2	1088.6	1089.0	1090.6	1092.1	1093.6	1095.1	1095.3
160°	1106.3	1106.7	1106.9	1107.1	1107.3	1107.5	1108.9	1110.2	1111.6	1113.0	1113.2
162.5°	1122.7	1122.8	1123.1	1123.3	1123.5	1123.7	1125.2	1126.7	1128.2	1129.7	1130.0
165°	1145.0	1144.9	1144.9	1144.9	1144.9	1144.9	1146.4	1148.0	1149.5	1151.1	1151.3
167.5°	1163.0	1162.6	1162.6	1162.5	1162.5	1162.4	1164.0	1165.5	1167.1	1168.6	1168.8
170°	1173.4	1173.0	1172.8	1172.6	1172.3	1172.0	1173.7	1175.2	1176.8	1178.3	1178.4
172.5°	1180.6	1180.2	1180.0	1179.7	1179.5	1179.3	1180.9	1182.5	1184.1	1185.6	1185.7
175°	1189.5	1189.0	1188.5	1188.1	1187.6	1187.2	1188.7	1190.3	1191.8	1193.5	1193.6
177.5°	1193.7	1193.3	1192.9	1192.5	1192.1	1191.8	1192.9	1194.0	1195.1	1196.1	1196.1
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331268-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	572.5	572.1	572.1	570.5	572.1	572.1	572.5	574.3	574.9	575.2	574.5
5°	531.1	530.4	529.3	530.4	529.3	530.4	531.1	534.3	535.9	537.5	538.9
7.5°	490.1	487.4	487.0	484.2	487.0	487.4	490.1	491.6	494.8	498.5	501.8
10°	460.2	458.4	458.1	453.7	458.1	458.4	460.2	464.1	467.3	471.6	476.3
12.5°	437.5	433.0	433.9	431.4	433.9	433.0	437.5	437.5	441.2	443.9	451.1
15°	398.0	398.0	397.1	393.2	397.1	398.0	398.0	404.2	405.4	409.7	415.9
17.5°	369.7	369.2	367.1	368.2	367.1	369.2	369.7	374.3	375.1	380.8	386.0
20°	352.8	351.4	348.7	348.7	348.7	351.4	352.8	355.4	358.3	361.7	366.2
22.5°	336.9	336.8	333.9	334.8	333.9	336.8	336.9	339.2	342.0	345.8	349.4
25°	318.2	316.4	315.0	315.7	315.0	316.4	318.2	318.4	321.6	324.2	326.5
27.5°	300.4	299.4	299.3	297.5	299.3	299.4	300.4	301.0	302.9	304.4	306.5
30°	290.2	287.9	288.3	287.2	288.3	287.9	290.2	290.4	291.3	292.3	294.8
32.5°	278.4	277.6	277.2	276.2	277.2	277.6	278.4	278.8	280.7	281.7	283.6
35°	262.5	262.7	261.6	262.0	261.6	262.7	262.5	262.9	263.2	264.1	265.9
37.5°	248.4	249.1	248.6	248.7	248.6	249.1	248.4	248.6	248.9	249.0	249.6
40°	239.2	239.2	239.2	239.9	239.2	239.2	239.2	238.6	238.8	238.6	238.6
42.5°	230.5	230.0	229.7	229.6	229.7	230.0	230.5	228.8	229.6	228.8	228.5
45°	215.4	216.1	216.3	215.2	216.3	216.1	215.4	215.0	214.3	214.0	213.8
47.5°	201.8	201.9	201.8	202.8	201.8	201.9	201.8	201.2	200.2	199.8	198.6
50°	192.3	191.8	192.3	191.8	192.3	191.8	192.3	191.1	190.4	189.2	188.3
52.5°	182.2	182.3	182.0	181.9	182.0	182.3	182.2	180.7	180.4	179.9	178.4
55°	166.3	166.7	166.5	166.5	166.5	166.7	166.3	165.4	165.2	163.8	162.4
57.5°	150.0	150.4	150.7	149.7	150.7	150.4	150.0	149.8	149.7	148.1	146.7
60°	138.6	139.7	139.5	139.1	139.5	139.7	138.6	138.8	138.1	137.1	136.2
62.5°	128.1	128.6	128.5	128.4	128.5	128.6	128.1	127.0	126.7	125.8	124.9
65°	112.0	112.4	111.7	112.4	111.7	112.4	112.0	111.3	109.7	109.2	108.3
67.5°	94.5	94.7	95.2	95.5	95.2	94.7	94.5	94.8	93.8	92.9	92.7
70°	83.7	83.5	84.2	84.9	84.2	83.5	83.7	83.3	82.6	81.9	81.0
72.5°	72.3	72.8	72.6	73.1	72.6	72.8	72.3	72.4	71.8	70.9	70.0
75°	55.7	56.5	56.2	56.9	56.2	56.5	55.7	56.2	55.7	54.8	53.9
77.5°	40.3	40.4	40.3	40.7	40.3	40.4	40.3	40.7	40.2	40.5	39.4
80°	30.7	30.3	29.8	30.7	29.8	30.3	30.7	30.7	30.1	30.7	30.1
82.5°	21.4	21.6	21.2	21.2	21.2	21.6	21.4	21.9	21.6	21.9	21.2
85°	9.9	9.6	9.2	9.2	9.2	9.6	9.9	9.9	10.5	10.1	10.1
87.5°	8.6	8.4	8.5	8.3	8.5	8.4	8.6	8.5	8.5	9.0	9.1
90°	33.6	33.8	34.0	34.2	34.0	33.8	33.6	33.3	33.5	33.9	34.3
92.5°	32.5	32.5	32.6	32.6	32.6	32.5	32.5	32.5	32.4	32.3	32.2
95°	63.8	63.4	62.9	62.5	62.9	63.4	63.8	64.2	64.5	64.5	64.5
97.5°	108.4	108.4	108.3	108.3	108.3	108.4	108.4	108.5	108.5	108.5	108.5
100°	138.8	138.6	138.3	138.0	138.3	138.6	138.8	139.0	139.1	139.1	139.1
102.5°	172.6	172.4	172.2	172.0	172.2	172.4	172.6	172.8	172.9	172.7	172.5
105°	223.7	223.7	223.7	223.7	223.7	223.7	223.7	223.7	223.5	223.1	222.6
107.5°	275.6	274.6	273.6	272.5	273.6	274.6	275.6	276.6	277.0	276.9	276.7
110°	312.5	311.7	311.0	310.4	311.0	311.7	312.5	313.1	313.5	313.5	313.5



TEST NUMBER: P331268-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	348.2	347.7	347.2	346.7	347.2	347.7	348.2	348.6	349.2	349.7	350.2
115°	405.2	404.5	403.7	403.1	403.7	404.5	405.2	405.8	406.3	406.5	406.7
117.5°	459.0	458.3	457.6	457.0	457.6	458.3	459.0	459.6	460.2	460.8	461.3
120°	496.9	496.1	495.5	494.8	495.5	496.1	496.9	497.6	497.9	497.9	497.9
122.5°	533.4	532.9	532.4	531.9	532.4	532.9	533.4	533.9	534.4	534.9	535.4
125°	589.3	589.0	588.8	588.5	588.8	589.0	589.3	589.5	589.9	590.6	591.3
127.5°	642.3	641.6	640.9	640.2	640.9	641.6	642.3	643.0	643.8	644.6	645.4
130°	679.9	679.0	678.1	677.2	678.1	679.0	679.9	680.9	681.5	682.0	682.4
132.5°	714.9	714.2	713.5	712.8	713.5	714.2	714.9	715.6	716.4	717.4	718.4
135°	769.9	769.3	768.6	767.9	768.6	769.3	769.9	770.6	771.0	771.3	771.5
137.5°	820.6	819.7	818.8	817.9	818.8	819.7	820.6	821.5	822.0	822.2	822.4
140°	855.3	854.3	853.5	852.6	853.5	854.3	855.3	856.2	856.7	856.7	856.7
142.5°	886.8	885.9	884.9	884.0	884.9	885.9	886.8	887.7	888.0	887.8	887.7
145°	933.9	933.0	932.1	931.2	932.1	933.0	933.9	934.8	935.1	934.9	934.6
147.5°	975.9	975.0	974.2	973.3	974.2	975.0	975.9	976.7	976.9	976.4	975.9
150°	1002.8	1002.1	1001.4	1000.8	1001.4	1002.1	1002.8	1003.4	1003.4	1002.8	1002.1
152.5°	1029.1	1028.2	1027.4	1026.5	1027.4	1028.2	1029.1	1030.0	1030.0	1029.1	1028.2
155°	1063.2	1062.6	1061.9	1061.2	1061.9	1062.6	1063.2	1063.9	1063.7	1062.6	1061.5
157.5°	1094.3	1093.2	1092.1	1091.1	1092.1	1093.2	1094.3	1095.3	1095.1	1093.6	1092.1
160°	1112.3	1111.4	1110.4	1109.5	1110.4	1111.4	1112.3	1113.2	1113.0	1111.6	1110.2
162.5°	1128.9	1127.8	1126.8	1125.7	1126.8	1127.8	1128.9	1130.0	1129.7	1128.2	1126.7
165°	1150.2	1149.1	1148.0	1146.9	1148.0	1149.1	1150.2	1151.3	1151.1	1149.5	1148.0
167.5°	1167.7	1166.5	1165.4	1164.2	1165.4	1166.5	1167.7	1168.8	1168.6	1167.1	1165.5
170°	1177.1	1175.8	1174.4	1173.1	1174.4	1175.8	1177.1	1178.4	1178.3	1176.8	1175.2
172.5°	1184.4	1183.1	1181.6	1180.3	1181.6	1183.1	1184.4	1185.7	1185.6	1184.1	1182.5
175°	1192.2	1190.8	1189.5	1188.2	1189.5	1190.8	1192.2	1193.6	1193.5	1191.8	1190.3
177.5°	1195.1	1194.0	1192.9	1191.8	1192.9	1194.0	1195.1	1196.1	1196.1	1195.1	1194.0
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331268-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	573.6	575.6	578.8	582.1	584.1	587.9	589.1	590.9	592.5	596.3	600.4
5°	540.5	543.7	551.3	555.4	561.1	567.7	572.1	576.7	581.8	590.5	598.5
7.5°	504.9	510.3	519.8	527.5	535.6	545.1	552.0	561.1	568.7	581.0	592.7
10°	481.3	488.9	497.4	506.5	518.0	528.1	537.8	549.2	558.4	573.1	586.8
12.5°	460.0	461.1	473.3	483.4	499.1	511.6	522.7	537.5	546.4	563.9	578.3
15°	422.8	429.7	440.7	448.7	467.3	483.1	498.8	514.1	524.4	546.0	565.0
17.5°	391.4	397.8	409.1	422.2	435.6	451.3	471.5	487.8	501.8	526.4	549.0
20°	371.6	379.4	390.9	404.5	416.2	433.3	450.8	469.4	484.5	512.3	538.7
22.5°	354.8	360.9	370.2	383.5	396.3	412.0	431.1	451.4	467.3	497.3	523.9
25°	331.0	336.1	342.0	353.0	367.5	384.8	399.6	421.9	445.0	473.0	505.3
27.5°	309.6	313.3	318.5	328.2	339.4	355.5	372.0	393.1	416.5	446.9	481.0
30°	296.6	298.9	304.2	312.3	323.3	335.9	352.6	372.7	396.7	427.4	461.3
32.5°	285.3	287.3	290.8	298.4	308.0	318.8	333.9	354.1	376.8	407.0	444.6
35°	268.2	269.7	272.8	278.9	284.3	294.8	307.4	325.8	347.1	376.0	415.0
37.5°	251.2	253.4	255.2	257.8	264.6	271.6	282.5	298.0	318.9	348.1	385.3
40°	239.9	241.8	244.6	245.7	251.2	257.4	266.3	280.5	301.6	328.3	364.6
42.5°	228.5	230.5	232.1	233.4	238.1	243.6	251.7	263.9	282.6	308.4	344.4
45°	213.1	213.4	215.0	217.5	219.7	223.7	229.4	239.9	254.4	278.7	311.3
47.5°	197.4	197.7	197.9	199.0	201.6	205.1	208.9	217.5	230.5	249.8	281.6
50°	186.9	186.5	186.9	187.8	189.5	192.5	196.8	203.0	213.6	231.7	260.8
52.5°	176.8	176.8	176.5	176.8	178.1	180.2	183.3	188.5	197.9	214.6	240.2
55°	161.5	160.4	160.6	159.7	161.8	162.2	164.5	168.8	177.1	188.5	212.7
57.5°	145.1	144.2	143.2	142.9	142.7	143.9	145.7	149.2	155.5	165.6	185.1
60°	134.6	133.5	132.1	131.7	131.7	132.4	133.3	135.8	141.8	150.7	166.7
62.5°	124.0	122.7	121.9	120.7	120.3	121.0	121.9	123.7	128.1	136.4	150.3
65°	107.6	105.9	104.8	104.6	104.1	103.5	103.9	105.7	109.2	115.8	126.8
67.5°	91.1	89.6	89.4	88.0	87.4	87.5	87.4	88.9	91.0	96.7	104.9
70°	80.3	79.2	78.7	77.6	77.1	76.6	76.1	77.6	79.6	84.4	91.5
72.5°	69.3	68.3	67.4	66.3	66.4	65.9	65.8	66.8	68.4	72.8	78.4
75°	53.4	53.7	52.5	51.4	51.2	50.7	50.7	51.4	52.1	55.5	59.9
77.5°	38.8	38.6	37.7	37.3	37.1	36.6	37.1	37.5	37.9	40.2	43.3
80°	29.6	29.6	28.5	28.5	28.2	27.6	28.2	27.8	28.7	31.0	33.2
82.5°	21.1	20.8	20.7	20.4	20.3	19.8	20.1	20.6	21.0	22.5	23.9
85°	10.3	10.3	10.1	9.9	10.1	9.9	10.1	10.3	10.5	11.2	12.4
87.5°	9.2	9.4	8.7	7.9	6.9	6.1	5.5	5.2	4.9	4.5	4.2
90°	34.8	35.2	30.3	25.4	20.5	15.6	11.7	9.1	6.4	3.7	1.0
92.5°	32.1	32.0	30.9	29.7	28.6	27.4	25.9	23.8	21.9	19.9	18.0
95°	64.5	64.5	64.0	63.6	63.1	62.7	61.4	59.1	56.9	54.6	52.4
97.5°	108.5	108.5	107.6	106.7	105.9	105.0	103.6	101.7	99.7	97.8	95.7
100°	139.1	139.1	138.5	137.7	137.0	136.4	135.1	133.4	131.6	129.8	127.9
102.5°	172.3	172.2	171.3	170.5	169.6	168.7	167.5	166.1	164.7	163.3	161.9
105°	222.2	221.7	221.3	220.9	220.4	219.9	219.3	218.7	218.0	217.3	216.7
107.5°	276.5	276.3	276.3	276.3	276.3	276.3	275.9	274.9	273.9	272.9	271.9
110°	313.5	313.5	313.5	313.5	313.5	313.5	312.8	311.4	310.0	308.7	307.4



TEST NUMBER: P331268-840  
 CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	350.8	351.3	351.5	351.6	351.8	352.0	351.4	350.1	348.8	347.4	346.1
115°	407.0	407.2	407.6	408.1	408.5	408.9	408.5	407.2	405.8	404.5	403.1
117.5°	461.8	462.4	463.6	464.8	466.2	467.4	467.2	465.3	463.5	461.7	460.0
120°	497.9	497.9	499.7	501.4	503.2	505.0	505.0	503.2	501.4	499.7	497.9
122.5°	536.0	536.5	537.9	539.1	540.3	541.6	541.1	539.0	536.8	534.6	532.5
125°	591.9	592.6	593.3	593.9	594.6	595.3	594.6	592.6	590.6	588.5	586.5
127.5°	646.2	647.0	647.8	648.6	649.4	650.3	649.3	646.8	644.3	641.7	639.1
130°	682.9	683.3	683.8	684.2	684.6	685.1	683.9	681.0	678.0	675.1	672.2
132.5°	719.4	720.3	720.2	720.2	720.1	720.0	718.8	716.4	714.1	711.7	709.3
135°	771.7	771.9	771.5	771.0	770.6	770.2	768.7	766.3	763.8	761.3	758.9
137.5°	822.6	822.7	822.2	821.6	821.0	820.4	819.1	817.1	815.1	813.0	811.1
140°	856.7	856.7	855.6	854.3	853.2	852.1	850.6	848.6	846.6	844.6	842.5
142.5°	887.5	887.3	886.5	885.8	884.9	884.2	882.8	880.8	878.8	876.8	874.7
145°	934.4	934.2	932.9	931.5	930.2	928.9	927.4	925.8	924.2	922.7	921.1
147.5°	975.4	974.9	974.0	973.1	972.3	971.4	970.0	968.1	966.2	964.3	962.4
150°	1001.4	1000.8	999.9	999.0	998.0	997.1	996.0	994.7	993.3	992.0	990.7
152.5°	1027.4	1026.5	1025.4	1024.4	1023.3	1022.3	1021.1	1019.7	1018.3	1017.0	1015.6
155°	1060.4	1059.1	1058.5	1057.8	1057.2	1056.5	1055.8	1055.2	1054.5	1053.8	1053.2
157.5°	1090.6	1089.0	1088.6	1088.2	1087.8	1087.4	1087.0	1086.5	1086.1	1085.6	1085.2
160°	1108.9	1107.5	1107.3	1107.1	1106.9	1106.7	1106.3	1105.9	1105.4	1105.0	1104.6
162.5°	1125.2	1123.7	1123.5	1123.3	1123.1	1122.8	1122.7	1122.6	1122.5	1122.4	1122.3
165°	1146.4	1144.9	1144.9	1144.9	1144.9	1144.9	1145.0	1145.2	1145.4	1145.7	1145.9
167.5°	1164.0	1162.4	1162.5	1162.5	1162.6	1162.6	1163.0	1163.6	1164.3	1165.0	1165.6
170°	1173.7	1172.0	1172.3	1172.6	1172.8	1173.0	1173.4	1174.1	1174.8	1175.4	1176.1
172.5°	1180.9	1179.3	1179.5	1179.7	1180.0	1180.2	1180.6	1181.3	1182.0	1182.7	1183.4
175°	1188.7	1187.2	1187.6	1188.1	1188.5	1189.0	1189.5	1190.2	1190.8	1191.5	1192.2
177.5°	1192.9	1191.8	1192.1	1192.5	1192.9	1193.3	1193.7	1194.3	1194.8	1195.3	1195.9
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331268-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	600.1	601.0	603.9	606.8	610.2	611.1	612.5	611.3	610.9	614.3	616.9
5°	601.8	605.8	613.9	621.3	627.4	631.8	636.4	638.2	641.7	646.4	652.5
7.5°	599.8	607.8	620.5	631.2	642.8	651.2	657.7	663.4	670.1	679.2	689.2
10°	597.6	608.3	623.8	636.8	651.1	661.9	670.8	679.5	689.6	702.3	715.3
12.5°	593.6	606.3	625.6	641.1	659.3	669.9	682.0	700.7	711.7	729.2	747.6
15°	585.4	599.7	626.5	645.5	666.2	686.4	708.6	726.5	744.4	754.8	780.6
17.5°	573.4	594.2	624.0	646.2	672.5	704.2	729.2	749.5	770.1	786.9	799.9
20°	563.6	586.3	620.4	646.9	678.1	712.3	740.9	761.6	779.5	793.6	801.5
22.5°	551.4	580.0	613.0	644.2	684.0	717.8	747.9	764.2	779.1	786.0	789.1
25°	532.0	566.4	603.8	641.9	686.8	722.7	750.1	760.0	764.4	757.7	746.7
27.5°	511.1	549.5	593.2	637.5	685.1	719.5	739.2	737.7	730.3	708.7	691.6
30°	495.5	537.8	584.7	633.2	680.9	714.4	725.8	714.4	697.6	673.6	648.9
32.5°	479.2	522.9	575.7	626.9	673.2	702.7	705.1	685.4	659.4	632.1	601.5
35°	454.4	501.7	558.9	613.0	656.8	675.4	664.4	629.4	598.7	561.4	519.6
37.5°	426.5	478.7	535.9	592.6	632.3	637.1	609.8	573.1	529.7	485.7	436.6
40°	405.6	460.9	519.9	576.9	612.1	607.0	572.1	531.8	480.2	426.5	380.8
42.5°	386.9	442.1	502.2	558.3	586.3	572.5	531.8	482.2	426.8	376.2	334.4
45°	354.5	411.3	472.8	526.9	543.0	518.0	464.1	409.0	354.5	312.3	279.2
47.5°	323.0	379.2	440.1	487.7	493.3	459.7	400.8	344.2	297.2	262.9	239.5
50°	299.8	356.3	416.6	459.1	457.2	416.6	356.1	302.2	262.9	235.1	219.5
52.5°	279.1	332.4	390.3	429.0	419.2	375.0	317.1	269.2	237.0	215.3	201.2
55°	246.8	296.2	351.2	382.2	364.3	315.2	266.3	227.8	203.9	187.6	176.6
57.5°	214.8	261.1	308.2	327.3	307.5	262.2	221.5	193.5	175.5	163.5	156.3
60°	195.0	235.4	277.3	293.9	270.2	229.8	197.7	172.8	158.2	148.5	142.0
62.5°	175.2	211.4	251.0	259.9	238.3	204.2	175.7	154.9	143.1	134.3	128.3
65°	148.1	177.8	207.8	213.8	193.9	167.4	145.0	131.5	120.9	114.5	109.7
67.5°	121.6	145.3	166.6	171.4	153.9	135.6	119.4	107.6	100.5	95.1	91.0
70°	105.7	124.6	142.0	145.9	131.9	115.6	103.2	93.8	87.4	82.8	78.9
72.5°	89.1	104.7	119.3	121.9	110.5	98.0	87.9	80.4	74.7	71.8	68.1
75°	68.2	77.4	88.6	89.3	81.7	74.1	66.3	61.5	58.5	54.8	53.0
77.5°	48.1	55.2	61.7	62.9	58.5	53.3	49.0	45.1	42.6	40.9	39.2
80°	36.7	42.4	45.2	46.8	43.6	39.9	37.4	34.8	33.2	32.1	31.0
82.5°	26.3	29.8	32.3	33.6	31.8	29.6	27.2	25.7	24.4	23.5	23.1
85°	13.3	14.9	16.6	17.0	16.6	15.6	14.2	14.2	13.5	13.3	13.3
87.5°	5.4	6.6	7.2	8.2	8.6	9.6	10.6	11.4	12.2	11.9	11.6
90°	3.7	6.4	9.1	11.7	15.6	20.5	25.4	30.3	35.2	34.8	34.3
92.5°	19.9	21.9	23.8	25.9	27.4	28.6	29.7	30.9	32.0	32.1	32.2
95°	54.6	56.9	59.1	61.4	62.7	63.1	63.6	64.0	64.5	64.5	64.5
97.5°	97.8	99.7	101.7	103.6	105.0	105.9	106.7	107.6	108.5	108.5	108.5
100°	129.8	131.6	133.4	135.1	136.4	137.0	137.7	138.5	139.1	139.1	139.1
102.5°	163.3	164.7	166.1	167.5	168.7	169.6	170.5	171.3	172.2	172.3	172.5
105°	217.3	218.0	218.7	219.3	219.9	220.4	220.9	221.3	221.7	222.2	222.6
107.5°	272.9	273.9	274.9	275.9	276.3	276.3	276.3	276.3	276.3	276.5	276.7
110°	308.7	310.0	311.4	312.8	313.5	313.5	313.5	313.5	313.5	313.5	313.5





TEST NUMBER: P331268-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	347.4	348.8	350.1	351.4	352.0	351.8	351.6	351.5	351.3	350.8	350.2
115°	404.5	405.8	407.2	408.5	408.9	408.5	408.1	407.6	407.2	407.0	406.7
117.5°	461.7	463.5	465.3	467.2	467.4	466.2	464.8	463.6	462.4	461.8	461.3
120°	499.7	501.4	503.2	505.0	505.0	503.2	501.4	499.7	497.9	497.9	497.9
122.5°	534.6	536.8	539.0	541.1	541.6	540.3	539.1	537.9	536.5	536.0	535.4
125°	588.5	590.6	592.6	594.6	595.3	594.6	593.9	593.3	592.6	591.9	591.3
127.5°	641.7	644.3	646.8	649.3	650.3	649.4	648.6	647.8	647.0	646.2	645.4
130°	675.1	678.0	681.0	683.9	685.1	684.6	684.2	683.8	683.3	682.9	682.4
132.5°	711.7	714.1	716.4	718.8	720.0	720.1	720.2	720.2	720.3	719.4	718.4
135°	761.3	763.8	766.3	768.7	770.2	770.6	771.0	771.5	771.9	771.7	771.5
137.5°	813.0	815.1	817.1	819.1	820.4	821.0	821.6	822.2	822.7	822.6	822.4
140°	844.6	846.6	848.6	850.6	852.1	853.2	854.3	855.6	856.7	856.7	856.7
142.5°	876.8	878.8	880.8	882.8	884.2	884.9	885.8	886.5	887.3	887.5	887.7
145°	922.7	924.2	925.8	927.4	928.9	930.2	931.5	932.9	934.2	934.4	934.6
147.5°	964.3	966.2	968.1	970.0	971.4	972.3	973.1	974.0	974.9	975.4	975.9
150°	992.0	993.3	994.7	996.0	997.1	998.0	999.0	999.9	1000.8	1001.4	1002.1
152.5°	1017.0	1018.3	1019.7	1021.1	1022.3	1023.3	1024.4	1025.4	1026.5	1027.4	1028.2
155°	1053.8	1054.5	1055.2	1055.8	1056.5	1057.2	1057.8	1058.5	1059.1	1060.4	1061.5
157.5°	1085.6	1086.1	1086.5	1087.0	1087.4	1087.8	1088.2	1088.6	1089.0	1090.6	1092.1
160°	1105.0	1105.4	1105.9	1106.3	1106.7	1106.9	1107.1	1107.3	1107.5	1108.9	1110.2
162.5°	1122.4	1122.5	1122.6	1122.7	1122.8	1123.1	1123.3	1123.5	1123.7	1125.2	1126.7
165°	1145.7	1145.4	1145.2	1145.0	1144.9	1144.9	1144.9	1144.9	1144.9	1146.4	1148.0
167.5°	1165.0	1164.3	1163.6	1163.0	1162.6	1162.6	1162.5	1162.5	1162.4	1164.0	1165.5
170°	1175.4	1174.8	1174.1	1173.4	1173.0	1172.8	1172.6	1172.3	1172.0	1173.7	1175.2
172.5°	1182.7	1182.0	1181.3	1180.6	1180.2	1180.0	1179.7	1179.5	1179.3	1180.9	1182.5
175°	1191.5	1190.8	1190.2	1189.5	1189.0	1188.5	1188.1	1187.6	1187.2	1188.7	1190.3
177.5°	1195.3	1194.8	1194.3	1193.7	1193.3	1192.9	1192.5	1192.1	1191.8	1192.9	1194.0
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331268-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	619.1	621.7	621.7	622.1	625.0	624.6	624.4
5°	658.8	662.8	663.2	667.3	670.0	669.1	666.6
7.5°	696.3	703.6	709.1	712.2	715.8	718.0	717.0
10°	726.1	736.6	743.1	747.4	752.7	756.6	755.2
12.5°	753.1	765.6	774.5	781.9	782.5	787.6	784.2
15°	795.2	808.4	809.8	815.3	819.7	819.2	819.4
17.5°	809.0	813.2	814.2	814.3	814.4	812.7	809.2
20°	804.1	802.4	798.6	795.6	790.3	789.6	785.1
22.5°	780.5	775.5	765.7	759.2	751.0	748.9	747.6
25°	734.4	723.1	707.5	692.6	688.4	680.4	682.7
27.5°	670.9	653.4	636.4	624.4	613.4	601.4	604.8
30°	626.3	606.5	582.7	564.3	552.6	541.2	539.1
32.5°	573.1	544.1	517.6	501.4	483.4	476.2	468.3
35°	481.3	453.0	426.7	403.9	390.9	380.8	371.6
37.5°	398.8	366.3	345.0	326.6	317.1	311.3	312.9
40°	347.6	319.1	303.5	289.5	280.7	276.7	277.6
42.5°	306.1	284.8	272.0	262.4	256.2	253.9	253.4
45°	259.0	247.1	236.5	231.1	228.0	225.5	223.9
47.5°	226.9	217.1	211.2	207.9	205.3	202.8	202.7
50°	207.6	201.2	197.0	193.6	191.6	189.8	191.4
52.5°	192.9	187.0	182.9	179.9	179.0	177.4	177.3
55°	171.2	166.5	163.6	160.8	159.5	158.5	157.3
57.5°	151.3	146.9	144.2	142.5	139.9	139.0	138.6
60°	137.1	133.7	131.0	128.7	127.5	125.7	125.7
62.5°	124.1	120.7	118.2	116.4	114.5	113.8	114.0
65°	105.3	102.5	100.0	98.2	97.8	96.3	96.8
67.5°	88.0	86.1	83.4	82.4	81.6	80.9	80.3
70°	76.3	74.5	73.2	71.8	71.1	71.1	71.1
72.5°	66.7	64.4	63.6	61.9	62.3	61.6	60.8
75°	51.6	50.2	49.6	48.9	47.8	47.8	47.8
77.5°	38.0	37.6	36.8	36.1	35.7	35.5	35.6
80°	29.4	29.1	28.7	28.7	28.2	28.0	27.6
82.5°	22.6	22.0	21.7	21.5	21.4	21.4	21.3
85°	12.8	12.4	12.4	12.6	12.1	12.1	12.4
87.5°	11.7	11.6	11.4	11.5	11.7	11.6	11.6
90°	33.9	33.5	33.3	33.6	33.8	34.0	34.2
92.5°	32.3	32.4	32.5	32.5	32.5	32.6	32.6
95°	64.5	64.5	64.2	63.8	63.4	62.9	62.5
97.5°	108.5	108.5	108.5	108.4	108.4	108.3	108.3
100°	139.1	139.1	139.0	138.8	138.6	138.3	138.0
102.5°	172.7	172.9	172.8	172.6	172.4	172.2	172.0
105°	223.1	223.5	223.7	223.7	223.7	223.7	223.7
107.5°	276.9	277.0	276.6	275.6	274.6	273.6	272.5
110°	313.5	313.5	313.1	312.5	311.7	311.0	310.4



TEST NUMBER: P331268-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	349.7	349.2	348.6	348.2	347.7	347.2	346.7
115°	406.5	406.3	405.8	405.2	404.5	403.7	403.1
117.5°	460.8	460.2	459.6	459.0	458.3	457.6	457.0
120°	497.9	497.9	497.6	496.9	496.1	495.5	494.8
122.5°	534.9	534.4	533.9	533.4	532.9	532.4	531.9
125°	590.6	589.9	589.5	589.3	589.0	588.8	588.5
127.5°	644.6	643.8	643.0	642.3	641.6	640.9	640.2
130°	682.0	681.5	680.9	679.9	679.0	678.1	677.2
132.5°	717.4	716.4	715.6	714.9	714.2	713.5	712.8
135°	771.3	771.0	770.6	769.9	769.3	768.6	767.9
137.5°	822.2	822.0	821.5	820.6	819.7	818.8	817.9
140°	856.7	856.7	856.2	855.3	854.3	853.5	852.6
142.5°	887.8	888.0	887.7	886.8	885.9	884.9	884.0
145°	934.9	935.1	934.8	933.9	933.0	932.1	931.2
147.5°	976.4	976.9	976.7	975.9	975.0	974.2	973.3
150°	1002.8	1003.4	1003.4	1002.8	1002.1	1001.4	1000.8
152.5°	1029.1	1030.0	1030.0	1029.1	1028.2	1027.4	1026.5
155°	1062.6	1063.7	1063.9	1063.2	1062.6	1061.9	1061.2
157.5°	1093.6	1095.1	1095.3	1094.3	1093.2	1092.1	1091.1
160°	1111.6	1113.0	1113.2	1112.3	1111.4	1110.4	1109.5
162.5°	1128.2	1129.7	1130.0	1128.9	1127.8	1126.8	1125.7
165°	1149.5	1151.1	1151.3	1150.2	1149.1	1148.0	1146.9
167.5°	1167.1	1168.6	1168.8	1167.7	1166.5	1165.4	1164.2
170°	1176.8	1178.3	1178.4	1177.1	1175.8	1174.4	1173.1
172.5°	1184.1	1185.6	1185.7	1184.4	1183.1	1181.6	1180.3
175°	1191.8	1193.5	1193.6	1192.2	1190.8	1189.5	1188.2
177.5°	1195.1	1196.1	1196.1	1195.1	1194.0	1192.9	1191.8
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3

(END OF REPORT)