

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332974-927

Luminaire Tested: **SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332974-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6275.4 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332974-927
CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332974-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	54	53	52	47
2	91	84	78	73	84	78	73	68	67	63	60	57	55	52	48	46	45	40
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	39	35
4	76	66	58	52	71	62	55	49	53	48	44	46	42	39	39	36	34	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	30	26
6	65	53	45	39	60	50	43	37	43	38	34	38	33	30	32	29	26	23
7	60	48	40	35	56	45	38	33	40	34	30	34	30	27	29	26	23	21
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	24	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	21	25	22	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10973	10973	10973	10973
5°	12729	11006	9728	11006
10°	15057	10958	8682	10958
15°	17393	10857	7460	10857
20°	19365	10717	6747	10717
25°	19991	10580	6263	10580
30°	17500	10414	5972	10414
35°	13623	10168	5797	10168
40°	10215	9886	5702	9886
45°	8066	9435	5651	9435
50°	6810	8913	5488	8913
55°	5935	8341	5195	8341
60°	5339	7745	4598	7745
65°	4707	7104	3954	7104
70°	4239	6437	3567	6437
75°	3553	5705	3041	5705
80°	3003	4863	2850	4863
85°	2538	3798	2538	3798



TEST NUMBER: P332974-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.7	2.1
10°-20°	397.3	6.3
20°-30°	621.4	9.9
30°-40°	690.7	11.0
40°-50°	612.9	9.8
50°-60°	477.6	7.6
60°-70°	312.7	5.0
70°-80°	153.8	2.5
80°-90°	41.0	0.7
90°-100°	67.4	1.1
100°-110°	199.8	3.2
110°-120°	339.1	5.4
120°-130°	447.1	7.1
130°-140°	502.1	8.0
140°-150°	493.4	7.9
150°-160°	415.0	6.6
160°-170°	276.1	4.4
170°-180°	96.7	1.5
0°-30°	1150.3	18.3
0°-40°	1841.1	29.3
0°-60°	2931.5	46.7
0°-90°	3438.9	54.8
90°-120°	606.3	9.7
90°-150°	2048.8	32.6
90°-180°	2837.0	45.2
0°-180°	6275.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1359	1359	1359	1359	1359	
5°	1571	1358	1200	1358	1571	159
15°	2081	1299	893	1299	2081	592
25°	2244	1188	703	1188	2244	996
35°	1382	1032	588	1032	1382	866
45°	706	826	495	826	706	560
55°	422	593	369	593	422	384
65°	246	372	207	372	246	248
75°	114	183	98	183	114	125
85°	27	41	27	41	27	31
90°	24	2	24	2	24	13
95°	62	48	62	48	62	65
105°	193	184	193	184	193	203
115°	342	345	342	345	342	338
125°	498	502	498	502	498	444
135°	648	648	648	648	648	501
145°	788	787	788	787	788	493
155°	901	901	901	901	901	415
165°	979	981	979	981	979	276
175°	1016	1021	1016	1021	1016	96
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P332974-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2
2.5°	1433.7	1437.7	1433.7	1433.3	1428.9	1427.6	1425.8	1420.1	1409.6	1403.5	1404.8
5°	1570.7	1584.3	1576.7	1575.6	1563.5	1551.5	1543.8	1526.3	1507.7	1495.1	1484.6
7.5°	1729.0	1736.9	1732.1	1724.4	1704.9	1693.8	1676.1	1653.0	1619.6	1594.0	1570.7
10°	1836.8	1843.3	1841.2	1826.9	1812.7	1783.7	1767.2	1735.0	1692.7	1659.4	1628.1
12.5°	1942.8	1949.8	1930.5	1931.2	1904.2	1881.4	1855.3	1814.7	1765.9	1722.8	1683.8
15°	2081.1	2072.3	2072.3	2061.3	2031.2	1999.5	1972.6	1929.9	1868.5	1817.0	1762.8
17.5°	2189.3	2192.3	2187.8	2161.9	2138.3	2105.5	2056.3	2006.4	1949.5	1880.4	1825.0
20°	2254.1	2254.1	2249.2	2231.7	2201.0	2165.9	2112.8	2058.6	1986.3	1916.8	1854.3
22.5°	2280.4	2282.1	2276.3	2261.8	2234.3	2200.0	2154.8	2099.8	2025.3	1946.9	1869.6
25°	2244.3	2254.6	2255.7	2251.9	2243.7	2222.9	2184.0	2127.6	2060.8	1975.9	1892.6
27.5°	2060.5	2073.6	2085.1	2104.0	2129.2	2142.4	2144.1	2115.4	2057.1	1975.5	1891.7
30°	1877.3	1888.2	1923.9	1970.4	2006.5	2039.4	2067.9	2075.5	2042.7	1969.3	1881.1
32.5°	1674.0	1688.9	1724.5	1774.6	1834.8	1890.5	1954.4	1987.0	1986.2	1942.1	1860.5
35°	1382.3	1393.2	1426.1	1478.6	1550.9	1633.6	1735.0	1813.8	1867.4	1863.6	1813.8
37.5°	1114.8	1127.1	1160.3	1204.0	1274.1	1376.4	1474.5	1583.1	1682.4	1738.1	1721.4
40°	969.3	969.9	1002.2	1047.1	1112.8	1202.1	1308.8	1429.3	1539.9	1630.3	1647.8
42.5°	854.5	854.6	876.0	924.4	971.8	1055.7	1157.7	1277.3	1406.8	1511.2	1557.6
45°	706.5	711.4	728.9	758.0	795.2	866.3	947.9	1059.1	1204.3	1328.0	1405.3
47.5°	598.3	605.5	616.6	640.3	669.9	717.4	784.9	884.8	1002.8	1139.0	1248.9
50°	542.2	543.3	557.5	570.6	596.4	634.1	693.3	776.6	884.9	1015.9	1138.0
52.5°	494.0	493.8	502.3	519.0	539.9	569.3	617.1	692.8	789.0	906.3	1032.4
55°	421.7	424.5	431.0	444.1	460.0	480.9	518.6	575.6	651.2	751.4	865.9
57.5°	366.7	368.1	373.3	378.8	393.4	408.5	436.9	476.4	540.2	622.3	728.9
60°	330.7	331.3	333.0	341.2	352.7	366.9	386.1	419.5	473.2	548.2	632.6
62.5°	295.7	296.7	299.2	305.2	314.1	324.0	344.0	370.9	415.3	479.4	555.4
65°	246.4	247.0	250.8	253.0	260.2	268.9	283.7	301.7	332.4	386.1	443.6
67.5°	205.9	205.9	206.1	209.1	214.0	219.8	228.7	243.1	266.3	299.2	349.9
70°	179.6	179.6	180.7	182.4	185.1	190.0	195.0	205.9	222.9	249.7	288.6
72.5°	155.1	155.5	156.6	156.9	158.4	162.4	166.0	173.1	185.7	205.9	237.3
75°	113.9	115.6	118.3	120.5	123.2	122.7	126.5	130.9	134.8	146.8	164.9
77.5°	84.8	83.9	84.2	86.1	86.4	87.0	89.7	93.1	95.9	101.6	108.1
80°	64.6	64.6	66.2	66.8	66.2	66.8	69.6	71.2	72.3	74.5	80.5
82.5°	48.9	49.7	49.2	49.7	50.1	50.6	52.9	53.2	54.3	55.2	57.8
85°	27.4	28.0	28.4	27.4	27.4	27.4	28.4	29.0	30.1	29.5	30.7
87.5°	14.4	13.9	14.3	14.2	14.6	13.9	14.2	14.9	13.8	14.0	13.7
90°	23.7	23.4	23.1	22.7	22.3	21.6	20.6	19.5	18.5	17.4	16.0
92.5°	35.1	34.9	34.7	34.5	34.3	33.8	33.2	32.6	31.9	31.3	30.3
95°	62.5	62.5	62.5	62.5	62.5	62.2	61.7	61.2	60.6	60.1	58.9
97.5°	97.9	97.9	97.9	97.9	97.9	97.6	97.0	96.3	95.7	95.1	93.6
100°	122.6	122.6	122.6	122.6	122.6	122.4	122.0	121.7	121.4	121.0	119.4
102.5°	150.4	150.3	150.1	150.0	149.8	149.5	149.0	148.5	148.1	147.6	146.1
105°	192.9	192.4	191.9	191.3	190.8	190.3	189.8	189.3	188.7	188.2	187.5
107.5°	234.3	234.4	234.4	234.5	234.5	234.2	233.8	233.3	232.8	232.3	232.2
110°	264.1	263.6	263.0	262.5	262.0	261.9	262.2	262.6	262.9	263.3	263.5



TEST NUMBER: P332974-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	294.5	294.4	294.2	294.1	294.1	294.1	294.1	294.1	294.2	294.3	294.6
115°	341.6	341.7	341.9	342.1	342.3	342.5	342.6	342.8	343.0	343.2	343.5
117.5°	386.5	386.8	387.2	387.5	387.9	388.4	389.0	389.6	390.1	390.8	391.0
120°	420.6	420.3	419.9	419.6	419.2	419.5	420.4	421.3	422.2	423.0	423.6
122.5°	449.1	449.7	450.4	451.0	451.6	452.3	452.9	453.4	454.1	454.6	454.9
125°	498.1	498.5	498.8	499.2	499.6	499.9	500.3	500.6	501.0	501.3	501.5
127.5°	543.5	543.8	544.1	544.4	544.6	544.9	545.3	545.7	546.1	546.4	546.7
130°	573.2	573.9	574.6	575.4	576.1	576.6	576.9	577.3	577.7	578.0	578.0
132.5°	604.9	605.1	605.5	605.7	606.0	606.3	606.7	607.0	607.4	607.8	607.8
135°	648.4	648.9	649.4	650.0	650.5	650.9	651.3	651.6	652.0	652.4	652.4
137.5°	694.1	694.0	693.9	693.8	693.6	693.9	694.3	694.7	695.2	695.7	695.4
140°	721.9	722.1	722.2	722.5	722.6	722.8	722.9	723.2	723.3	723.5	723.5
142.5°	749.7	749.8	749.8	749.9	749.9	750.0	750.0	750.0	750.0	750.0	750.2
145°	787.5	788.1	788.6	789.1	789.6	790.0	790.2	790.4	790.5	790.7	790.5
147.5°	825.9	826.0	826.2	826.3	826.5	826.6	826.8	827.0	827.1	827.3	827.4
150°	849.2	849.4	849.5	849.8	849.9	850.0	850.0	850.0	850.0	850.0	850.0
152.5°	870.7	871.2	871.6	872.1	872.6	872.6	872.1	871.7	871.3	870.8	870.8
155°	900.6	901.3	902.1	902.7	903.4	903.4	902.7	902.1	901.3	900.6	900.8
157.5°	927.3	928.0	928.5	929.2	929.7	929.8	929.2	928.7	928.2	927.6	927.7
160°	942.5	943.4	944.3	945.2	946.0	946.2	945.7	945.2	944.6	944.1	944.3
162.5°	958.3	959.3	960.1	961.0	961.9	961.8	960.8	959.9	958.9	958.0	958.2
165°	978.9	979.6	980.3	981.0	981.7	981.5	980.5	979.5	978.3	977.3	977.6
167.5°	993.6	994.7	995.8	996.9	998.0	998.0	997.0	995.9	994.8	993.8	993.7
170°	1001.8	1003.1	1004.2	1005.5	1006.7	1006.9	1005.8	1004.7	1003.7	1002.6	1002.4
172.5°	1008.8	1010.0	1011.2	1012.5	1013.7	1013.8	1012.5	1011.3	1010.1	1008.9	1008.9
175°	1016.1	1017.3	1018.5	1019.8	1021.0	1021.0	1019.8	1018.5	1017.3	1016.1	1016.2
177.5°	1019.9	1021.0	1022.1	1023.3	1024.4	1024.5	1023.4	1022.5	1021.4	1020.5	1020.5
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4



TEST NUMBER: P332974-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2
2.5°	1400.4	1394.3	1391.2	1384.2	1375.9	1371.5	1367.5	1361.8	1354.4	1346.6	1340.8
5°	1471.5	1458.3	1441.9	1422.2	1404.7	1387.7	1372.9	1358.1	1341.2	1323.7	1306.2
7.5°	1544.4	1518.6	1490.6	1458.3	1427.0	1398.4	1372.1	1346.9	1318.3	1292.8	1269.6
10°	1595.3	1560.2	1521.3	1480.3	1439.2	1403.6	1368.6	1336.8	1301.7	1270.5	1244.2
12.5°	1636.5	1595.3	1548.5	1497.4	1448.0	1404.9	1364.6	1323.2	1283.3	1249.5	1214.4
15°	1704.8	1648.4	1585.4	1524.1	1460.0	1401.4	1347.2	1299.0	1253.5	1205.9	1172.5
17.5°	1751.8	1684.9	1608.3	1534.6	1458.9	1389.8	1327.2	1269.9	1217.4	1168.8	1129.0
20°	1779.8	1705.9	1621.0	1537.2	1452.3	1378.4	1311.1	1247.5	1193.3	1140.7	1099.6
22.5°	1795.6	1713.8	1621.0	1533.3	1445.3	1365.2	1291.3	1225.2	1166.2	1113.6	1068.1
25°	1800.6	1713.0	1618.3	1517.5	1421.1	1336.3	1259.6	1187.8	1122.1	1069.5	1021.4
27.5°	1793.7	1690.4	1593.4	1490.0	1390.6	1301.1	1220.6	1145.3	1079.4	1023.0	973.6
30°	1783.1	1672.5	1568.4	1461.1	1360.3	1274.4	1189.5	1117.2	1048.7	990.1	940.3
32.5°	1760.3	1650.6	1538.7	1428.7	1326.6	1238.0	1157.5	1084.7	1017.6	957.7	904.8
35°	1715.2	1604.0	1482.5	1369.7	1269.4	1177.4	1101.8	1031.7	967.7	903.6	847.7
37.5°	1655.7	1542.1	1421.3	1297.7	1197.4	1110.5	1041.2	975.3	912.8	854.3	792.4
40°	1599.7	1496.1	1371.3	1248.6	1145.7	1061.8	997.8	938.1	875.1	817.1	755.2
42.5°	1531.8	1443.6	1317.4	1194.3	1092.7	1011.9	952.2	893.8	836.5	780.3	715.7
45°	1418.4	1351.5	1233.3	1115.0	1012.6	932.6	877.9	826.4	776.0	722.3	661.6
47.5°	1288.5	1243.3	1141.1	1020.0	925.3	853.3	800.4	758.4	715.7	662.1	608.8
50°	1198.3	1169.2	1070.6	960.0	869.7	803.4	749.2	709.7	674.1	622.7	575.0
52.5°	1101.8	1086.4	1003.1	897.4	810.1	745.1	698.8	663.3	627.2	584.6	540.0
55°	955.1	963.3	892.6	801.2	719.1	664.3	622.1	592.6	561.9	525.8	491.2
57.5°	805.0	835.0	787.6	707.3	630.3	579.7	548.0	523.1	497.3	467.4	437.9
60°	715.2	740.4	713.6	642.9	575.6	528.5	498.9	479.7	454.0	426.6	404.2
62.5°	627.6	654.5	638.7	581.6	519.0	478.6	452.5	434.6	415.4	391.6	368.2
65°	517.5	535.0	527.4	488.0	443.6	409.1	385.0	371.9	354.3	336.8	316.0
67.5°	396.4	430.2	425.7	404.8	366.5	339.5	323.8	312.1	296.2	283.1	269.0
70°	325.8	357.0	356.5	339.5	318.7	293.5	282.6	272.7	258.5	245.9	234.4
72.5°	266.7	295.3	299.5	286.5	272.3	253.3	242.7	235.9	222.1	213.5	204.1
75°	186.7	207.6	213.0	213.0	206.4	196.6	187.3	182.9	173.1	165.4	159.9
77.5°	122.5	135.6	144.2	146.1	147.1	143.8	136.2	133.1	125.5	122.8	117.6
80°	86.5	95.3	105.1	108.4	111.1	110.1	106.8	104.6	97.5	94.7	92.5
82.5°	59.8	64.6	72.7	79.9	79.2	82.1	79.2	77.5	72.1	71.1	68.9
85°	31.2	31.8	32.9	37.8	40.6	41.6	42.1	41.0	39.5	39.5	35.6
87.5°	13.5	12.7	13.3	13.0	13.0	14.4	15.3	15.4	14.4	13.5	12.6
90°	14.6	13.2	11.8	10.1	8.2	6.3	4.3	2.4	4.3	6.3	8.2
92.5°	29.3	28.4	27.4	25.7	23.5	21.3	19.2	17.0	19.2	21.3	23.5
95°	57.7	56.4	55.1	53.8	52.2	50.6	49.0	47.5	49.0	50.6	52.2
97.5°	92.1	90.7	89.3	87.9	86.7	85.4	84.1	82.9	84.1	85.4	86.7
100°	117.8	116.2	114.6	113.5	112.8	112.1	111.4	110.7	111.4	112.1	112.8
102.5°	144.7	143.2	141.8	140.9	140.6	140.4	140.1	139.8	140.1	140.4	140.6
105°	186.8	186.1	185.4	185.0	184.7	184.6	184.4	184.3	184.4	184.6	184.7
107.5°	232.1	232.0	231.9	231.7	231.6	231.3	231.1	230.9	231.1	231.3	231.6
110°	263.6	263.8	264.0	264.0	263.6	263.2	262.8	262.5	262.8	263.2	263.6



TEST NUMBER: P332974-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	294.9	295.2	295.6	295.7	295.6	295.6	295.5	295.4	295.5	295.6	295.6
115°	343.9	344.2	344.6	344.8	344.8	344.8	344.8	344.8	344.8	344.8	344.8
117.5°	391.3	391.5	391.7	391.8	391.7	391.5	391.4	391.3	391.4	391.5	391.7
120°	424.1	424.6	425.2	425.1	424.4	423.7	422.9	422.2	422.9	423.7	424.4
122.5°	455.1	455.4	455.7	455.6	455.3	455.0	454.8	454.5	454.8	455.0	455.3
125°	501.7	501.8	502.0	502.1	502.1	502.1	502.1	502.1	502.1	502.1	502.1
127.5°	546.9	547.2	547.5	547.4	546.8	546.3	545.8	545.3	545.8	546.3	546.8
130°	578.0	578.0	578.0	577.7	577.2	576.7	576.2	575.6	576.2	576.7	577.2
132.5°	608.0	608.2	608.3	608.2	607.8	607.4	607.0	606.7	607.0	607.4	607.8
135°	652.4	652.4	652.4	651.8	650.8	649.7	648.6	647.6	648.6	649.7	650.8
137.5°	695.1	694.8	694.5	694.2	693.6	693.2	692.7	692.2	692.7	693.2	693.6
140°	723.5	723.5	723.5	723.3	722.9	722.6	722.2	721.9	722.2	722.6	722.9
142.5°	750.4	750.5	750.6	750.5	750.2	749.8	749.5	749.1	749.5	749.8	750.2
145°	790.4	790.2	790.0	789.6	788.9	788.1	787.4	786.7	787.4	788.1	788.9
147.5°	827.5	827.7	827.8	827.4	826.6	825.8	824.9	824.1	824.9	825.8	826.6
150°	850.0	850.0	850.0	849.7	849.0	848.3	847.6	846.8	847.6	848.3	849.0
152.5°	870.6	870.4	870.3	870.1	869.7	869.2	868.8	868.4	868.8	869.2	869.7
155°	900.9	901.1	901.3	901.4	901.4	901.4	901.4	901.4	901.4	901.4	901.4
157.5°	927.7	927.7	927.8	928.0	928.3	928.6	928.9	929.2	928.9	928.6	928.3
160°	944.4	944.6	944.8	945.0	945.2	945.3	945.5	945.7	945.5	945.3	945.2
162.5°	958.4	958.5	958.7	959.0	959.5	960.0	960.4	960.8	960.4	960.0	959.5
165°	978.0	978.3	978.7	979.1	979.7	980.2	980.7	981.3	980.7	980.2	979.7
167.5°	993.7	993.6	993.6	994.0	994.7	995.5	996.2	997.0	996.2	995.5	994.7
170°	1002.3	1002.1	1001.9	1002.3	1003.1	1004.0	1004.9	1005.8	1004.9	1004.0	1003.1
172.5°	1008.8	1008.8	1008.8	1009.2	1009.9	1010.7	1011.4	1012.1	1011.4	1010.7	1009.9
175°	1016.4	1016.6	1016.8	1017.3	1018.2	1019.1	1019.9	1020.8	1019.9	1019.1	1018.2
177.5°	1020.5	1020.5	1020.5	1020.8	1021.5	1022.2	1022.9	1023.7	1022.9	1022.2	1021.5
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4



TEST NUMBER: P332974-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2
2.5°	1334.7	1330.3	1324.6	1318.0	1310.2	1303.1	1300.1	1302.7	1304.0	1300.5	1300.1
5°	1294.1	1280.4	1269.4	1253.0	1239.8	1228.9	1221.2	1218.0	1219.0	1210.3	1208.1
7.5°	1248.4	1232.2	1214.3	1194.7	1176.5	1160.5	1152.0	1147.4	1138.1	1134.2	1127.5
10°	1219.0	1197.1	1179.6	1156.6	1135.8	1116.7	1107.3	1099.6	1090.4	1086.0	1076.7
12.5°	1188.8	1163.4	1144.1	1120.2	1099.0	1075.9	1067.0	1052.8	1038.2	1029.0	1017.1
15°	1146.2	1115.6	1092.0	1063.5	1038.3	1012.0	988.5	962.2	952.4	931.5	919.5
17.5°	1096.4	1065.2	1036.1	997.9	959.0	926.4	901.3	876.1	861.0	847.7	841.6
20°	1063.5	1035.1	994.5	950.1	906.9	870.8	850.5	834.1	817.6	808.3	801.8
22.5°	1032.4	996.0	949.0	901.1	857.9	829.6	812.4	795.5	782.1	773.2	764.5
25°	980.2	932.6	882.8	828.1	798.4	773.8	755.2	741.5	733.3	721.8	717.4
27.5°	926.7	869.0	814.0	777.2	746.4	723.9	707.7	697.4	687.0	679.6	673.9
30°	885.5	827.0	777.7	742.6	711.4	692.8	679.6	667.6	659.3	653.3	649.0
32.5°	844.8	786.2	744.8	707.1	682.5	664.3	650.3	641.3	634.9	627.0	624.4
35°	785.8	733.8	697.7	663.8	638.6	622.1	611.2	601.8	596.4	594.2	592.6
37.5°	729.2	686.7	647.8	620.0	597.5	584.6	571.6	567.0	563.3	559.4	561.1
40°	693.3	653.3	618.9	589.2	571.2	557.0	549.3	543.8	540.5	540.5	540.5
42.5°	662.2	623.1	589.5	563.0	544.9	532.8	524.3	519.7	518.6	518.2	520.8
45°	613.9	577.7	543.8	521.9	506.6	494.5	489.6	485.8	485.8	488.0	488.5
47.5°	566.0	532.2	504.9	480.4	466.4	458.8	454.6	452.6	452.8	455.0	457.5
50°	536.7	503.3	476.4	454.6	441.4	434.3	430.5	429.4	430.5	430.5	434.3
52.5°	504.7	474.8	448.4	430.0	415.1	408.4	406.3	404.8	405.4	407.3	408.8
55°	457.8	431.0	405.8	388.2	377.3	373.0	368.0	368.5	367.5	368.5	368.5
57.5°	410.8	386.7	363.3	349.4	339.8	333.4	328.0	329.5	328.0	327.7	326.9
60°	380.6	354.3	335.7	323.1	312.1	306.7	301.7	302.9	301.2	300.1	297.9
62.5°	347.8	325.8	308.1	296.0	287.2	280.8	275.9	274.8	271.0	267.3	262.4
65°	300.1	282.0	266.2	254.7	246.4	241.5	237.7	234.4	226.2	217.4	213.0
67.5°	253.8	240.7	225.9	216.2	209.5	203.0	195.7	190.1	182.4	177.7	174.9
70°	223.9	211.4	198.8	189.5	182.4	176.3	168.1	164.3	158.8	156.6	153.9
72.5°	195.5	183.8	172.1	163.7	156.1	151.4	144.9	141.1	138.6	137.8	135.1
75°	152.3	142.9	134.2	126.5	120.5	117.2	114.5	111.7	110.6	105.7	103.0
77.5°	111.1	105.0	99.4	94.0	89.7	87.5	82.2	79.1	77.2	74.9	74.4
80°	86.5	82.1	76.7	73.4	67.3	65.2	63.0	62.4	61.9	61.3	60.8
82.5°	65.0	60.7	55.2	53.2	51.6	50.3	49.0	48.4	47.8	48.2	48.1
85°	32.9	30.7	30.7	30.1	29.5	29.0	28.4	28.4	28.0	28.4	28.0
87.5°	13.0	12.8	13.2	12.5	13.3	13.5	13.3	13.5	14.2	13.5	13.6
90°	10.1	11.8	13.2	14.6	16.0	17.4	18.5	19.5	20.6	21.6	22.3
92.5°	25.7	27.4	28.4	29.3	30.3	31.3	31.9	32.6	33.2	33.8	34.3
95°	53.8	55.1	56.4	57.7	58.9	60.1	60.6	61.2	61.7	62.2	62.5
97.5°	87.9	89.3	90.7	92.1	93.6	95.1	95.7	96.3	97.0	97.6	97.9
100°	113.5	114.6	116.2	117.8	119.4	121.0	121.4	121.7	122.0	122.4	122.6
102.5°	140.9	141.8	143.2	144.7	146.1	147.6	148.1	148.5	149.0	149.5	149.8
105°	185.0	185.4	186.1	186.8	187.5	188.2	188.7	189.3	189.8	190.3	190.8
107.5°	231.7	231.9	232.0	232.1	232.2	232.3	232.8	233.3	233.8	234.2	234.5
110°	264.0	264.0	263.8	263.6	263.5	263.3	262.9	262.6	262.2	261.9	262.0



TEST NUMBER: P332974-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	295.7	295.6	295.2	294.9	294.6	294.3	294.2	294.1	294.1	294.1	294.1
115°	344.8	344.6	344.2	343.9	343.5	343.2	343.0	342.8	342.6	342.5	342.3
117.5°	391.8	391.7	391.5	391.3	391.0	390.8	390.1	389.6	389.0	388.4	387.9
120°	425.1	425.2	424.6	424.1	423.6	423.0	422.2	421.3	420.4	419.5	419.2
122.5°	455.6	455.7	455.4	455.1	454.9	454.6	454.1	453.4	452.9	452.3	451.6
125°	502.1	502.0	501.8	501.7	501.5	501.3	501.0	500.6	500.3	499.9	499.6
127.5°	547.4	547.5	547.2	546.9	546.7	546.4	546.1	545.7	545.3	544.9	544.6
130°	577.7	578.0	578.0	578.0	578.0	578.0	577.7	577.3	576.9	576.6	576.1
132.5°	608.2	608.3	608.2	608.0	607.8	607.8	607.4	607.0	606.7	606.3	606.0
135°	651.8	652.4	652.4	652.4	652.4	652.4	652.0	651.6	651.3	650.9	650.5
137.5°	694.2	694.5	694.8	695.1	695.4	695.7	695.2	694.7	694.3	693.9	693.6
140°	723.3	723.5	723.5	723.5	723.5	723.5	723.3	723.2	722.9	722.8	722.6
142.5°	750.5	750.6	750.5	750.4	750.2	750.0	750.0	750.0	750.0	750.0	749.9
145°	789.6	790.0	790.2	790.4	790.5	790.7	790.5	790.4	790.2	790.0	789.6
147.5°	827.4	827.8	827.7	827.5	827.4	827.3	827.1	827.0	826.8	826.6	826.5
150°	849.7	850.0	850.0	850.0	850.0	850.0	850.0	850.0	850.0	850.0	849.9
152.5°	870.1	870.3	870.4	870.6	870.8	870.8	871.3	871.7	872.1	872.6	872.6
155°	901.4	901.3	901.1	900.9	900.8	900.6	901.3	902.1	902.7	903.4	903.4
157.5°	928.0	927.8	927.7	927.7	927.7	927.6	928.2	928.7	929.2	929.8	929.7
160°	945.0	944.8	944.6	944.4	944.3	944.1	944.6	945.2	945.7	946.2	946.0
162.5°	959.0	958.7	958.5	958.4	958.2	958.0	958.9	959.9	960.8	961.8	961.9
165°	979.1	978.7	978.3	978.0	977.6	977.3	978.3	979.5	980.5	981.5	981.7
167.5°	994.0	993.6	993.6	993.7	993.7	993.8	994.8	995.9	997.0	998.0	998.0
170°	1002.3	1001.9	1002.1	1002.3	1002.4	1002.6	1003.7	1004.7	1005.8	1006.9	1006.7
172.5°	1009.2	1008.8	1008.8	1008.8	1008.9	1008.9	1010.1	1011.3	1012.5	1013.8	1013.7
175°	1017.3	1016.8	1016.6	1016.4	1016.2	1016.1	1017.3	1018.5	1019.8	1021.0	1021.0
177.5°	1020.8	1020.5	1020.5	1020.5	1020.5	1020.5	1021.4	1022.5	1023.4	1024.5	1024.4
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4



TEST NUMBER: P332974-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2
2.5°	1297.4	1298.3	1295.3	1294.4	1295.3	1298.3	1297.4	1300.1	1300.5	1304.0	1302.7
5°	1203.7	1202.6	1199.8	1200.4	1199.8	1202.6	1203.7	1208.1	1210.3	1219.0	1218.0
7.5°	1123.6	1119.3	1120.5	1116.1	1120.5	1119.3	1123.6	1127.5	1134.2	1138.1	1147.4
10°	1074.4	1068.4	1063.5	1059.1	1063.5	1068.4	1074.4	1076.7	1086.0	1090.4	1099.6
12.5°	1007.4	1002.3	995.6	997.0	995.6	1002.3	1007.4	1017.1	1029.0	1038.2	1052.8
15°	912.4	904.1	891.0	892.6	891.0	904.1	912.4	919.5	931.5	952.4	962.2
17.5°	831.9	831.9	825.9	827.4	825.9	831.9	831.9	841.6	847.7	861.0	876.1
20°	790.3	786.4	787.0	785.3	787.0	786.4	790.3	801.8	808.3	817.6	834.1
22.5°	761.4	756.6	752.8	749.4	752.8	756.6	761.4	764.5	773.2	782.1	795.5
25°	712.5	709.2	704.3	703.1	704.3	709.2	712.5	717.4	721.8	733.3	741.5
27.5°	669.6	668.9	666.9	664.4	666.9	668.9	669.6	673.9	679.6	687.0	697.4
30°	644.6	643.5	642.4	640.7	642.4	643.5	644.6	649.0	653.3	659.3	667.6
32.5°	622.3	621.5	620.4	620.6	620.4	621.5	622.3	624.4	627.0	634.9	641.3
35°	590.3	589.8	588.7	588.2	588.7	589.8	590.3	592.6	594.2	596.4	601.8
37.5°	560.5	562.0	561.3	561.2	561.3	562.0	560.5	561.1	559.4	563.3	567.0
40°	540.0	540.5	541.6	541.1	541.6	540.5	540.0	540.5	540.5	540.5	543.8
42.5°	522.9	523.0	524.5	522.7	524.5	523.0	522.9	520.8	518.2	518.6	519.7
45°	492.3	495.6	495.0	495.0	495.0	495.6	492.3	488.5	488.0	485.8	485.8
47.5°	458.9	461.8	462.6	462.4	462.6	461.8	458.9	457.5	455.0	452.8	452.6
50°	437.0	435.9	437.6	437.0	437.6	435.9	437.0	434.3	430.5	430.5	429.4
52.5°	410.3	410.5	410.4	409.9	410.4	410.5	410.3	408.8	407.3	405.4	404.8
55°	369.1	369.6	368.5	369.1	368.5	369.6	369.1	368.5	368.5	367.5	368.5
57.5°	324.4	321.8	322.9	321.5	322.9	321.8	324.4	326.9	327.7	328.0	329.5
60°	292.5	288.0	286.9	284.8	286.9	288.0	292.5	297.9	300.1	301.2	302.9
62.5°	256.5	253.4	249.7	251.4	249.7	253.4	256.5	262.4	267.3	271.0	274.8
65°	208.7	206.4	204.8	207.0	204.8	206.4	208.7	213.0	217.4	226.2	234.4
67.5°	172.7	171.5	171.5	170.4	171.5	171.5	172.7	174.9	177.7	182.4	190.1
70°	153.9	152.3	152.3	151.1	152.3	152.3	153.9	153.9	156.6	158.8	164.3
72.5°	134.6	132.9	133.4	132.8	133.4	132.9	134.6	135.1	137.8	138.6	141.1
75°	99.7	97.0	97.0	97.5	97.0	97.0	99.7	103.0	105.7	110.6	111.7
77.5°	74.4	73.8	74.6	73.6	74.6	73.8	74.4	74.4	74.9	77.2	79.1
80°	60.8	60.2	59.7	61.3	59.7	60.2	60.8	60.8	61.3	61.9	62.4
82.5°	47.2	47.1	47.0	49.0	47.0	47.1	47.2	48.1	48.2	47.8	48.4
85°	28.4	27.4	28.4	27.4	28.4	27.4	28.4	28.0	28.4	28.0	28.4
87.5°	14.6	14.3	13.9	14.4	13.9	14.3	14.6	13.6	13.5	14.2	13.5
90°	22.7	23.1	23.4	23.7	23.4	23.1	22.7	22.3	21.6	20.6	19.5
92.5°	34.5	34.7	34.9	35.1	34.9	34.7	34.5	34.3	33.8	33.2	32.6
95°	62.5	62.5	62.5	62.5	62.5	62.5	62.5	62.5	62.2	61.7	61.2
97.5°	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.6	97.0	96.3
100°	122.6	122.6	122.6	122.6	122.6	122.6	122.6	122.6	122.4	122.0	121.7
102.5°	150.0	150.1	150.3	150.4	150.3	150.1	150.0	149.8	149.5	149.0	148.5
105°	191.3	191.9	192.4	192.9	192.4	191.9	191.3	190.8	190.3	189.8	189.3
107.5°	234.5	234.4	234.4	234.3	234.4	234.4	234.5	234.5	234.2	233.8	233.3
110°	262.5	263.0	263.6	264.1	263.6	263.0	262.5	262.0	261.9	262.2	262.6



TEST NUMBER: P332974-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	294.1	294.2	294.4	294.5	294.4	294.2	294.1	294.1	294.1	294.1	294.1
115°	342.1	341.9	341.7	341.6	341.7	341.9	342.1	342.3	342.5	342.6	342.8
117.5°	387.5	387.2	386.8	386.5	386.8	387.2	387.5	387.9	388.4	389.0	389.6
120°	419.6	419.9	420.3	420.6	420.3	419.9	419.6	419.2	419.5	420.4	421.3
122.5°	451.0	450.4	449.7	449.1	449.7	450.4	451.0	451.6	452.3	452.9	453.4
125°	499.2	498.8	498.5	498.1	498.5	498.8	499.2	499.6	499.9	500.3	500.6
127.5°	544.4	544.1	543.8	543.5	543.8	544.1	544.4	544.6	544.9	545.3	545.7
130°	575.4	574.6	573.9	573.2	573.9	574.6	575.4	576.1	576.6	576.9	577.3
132.5°	605.7	605.5	605.1	604.9	605.1	605.5	605.7	606.0	606.3	606.7	607.0
135°	650.0	649.4	648.9	648.4	648.9	649.4	650.0	650.5	650.9	651.3	651.6
137.5°	693.8	693.9	694.0	694.1	694.0	693.9	693.8	693.6	693.9	694.3	694.7
140°	722.5	722.2	722.1	721.9	722.1	722.2	722.5	722.6	722.8	722.9	723.2
142.5°	749.9	749.8	749.8	749.7	749.8	749.8	749.9	749.9	750.0	750.0	750.0
145°	789.1	788.6	788.1	787.5	788.1	788.6	789.1	789.6	790.0	790.2	790.4
147.5°	826.3	826.2	826.0	825.9	826.0	826.2	826.3	826.5	826.6	826.8	827.0
150°	849.8	849.5	849.4	849.2	849.4	849.5	849.8	849.9	850.0	850.0	850.0
152.5°	872.1	871.6	871.2	870.7	871.2	871.6	872.1	872.6	872.6	872.1	871.7
155°	902.7	902.1	901.3	900.6	901.3	902.1	902.7	903.4	903.4	902.7	902.1
157.5°	929.2	928.5	928.0	927.3	928.0	928.5	929.2	929.7	929.8	929.2	928.7
160°	945.2	944.3	943.4	942.5	943.4	944.3	945.2	946.0	946.2	945.7	945.2
162.5°	961.0	960.1	959.3	958.3	959.3	960.1	961.0	961.9	961.8	960.8	959.9
165°	981.0	980.3	979.6	978.9	979.6	980.3	981.0	981.7	981.5	980.5	979.5
167.5°	996.9	995.8	994.7	993.6	994.7	995.8	996.9	998.0	998.0	997.0	995.9
170°	1005.5	1004.2	1003.1	1001.8	1003.1	1004.2	1005.5	1006.7	1006.9	1005.8	1004.7
172.5°	1012.5	1011.2	1010.0	1008.8	1010.0	1011.2	1012.5	1013.7	1013.8	1012.5	1011.3
175°	1019.8	1018.5	1017.3	1016.1	1017.3	1018.5	1019.8	1021.0	1021.0	1019.8	1018.5
177.5°	1023.3	1022.1	1021.0	1019.9	1021.0	1022.1	1023.3	1024.4	1024.5	1023.4	1022.5
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4



TEST NUMBER: P332974-927
 CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2
2.5°	1300.1	1303.1	1310.2	1318.0	1324.6	1330.3	1334.7	1340.8	1346.6	1354.4	1361.8
5°	1221.2	1228.9	1239.8	1253.0	1269.4	1280.4	1294.1	1306.2	1323.7	1341.2	1358.1
7.5°	1152.0	1160.5	1176.5	1194.7	1214.3	1232.2	1248.4	1269.6	1292.8	1318.3	1346.9
10°	1107.3	1116.7	1135.8	1156.6	1179.6	1197.1	1219.0	1244.2	1270.5	1301.7	1336.8
12.5°	1067.0	1075.9	1099.0	1120.2	1144.1	1163.4	1188.8	1214.4	1249.5	1283.3	1323.2
15°	988.5	1012.0	1038.3	1063.5	1092.0	1115.6	1146.2	1172.5	1205.9	1253.5	1299.0
17.5°	901.3	926.4	959.0	997.9	1036.1	1065.2	1096.4	1129.0	1168.8	1217.4	1269.9
20°	850.5	870.8	906.9	950.1	994.5	1035.1	1063.5	1099.6	1140.7	1193.3	1247.5
22.5°	812.4	829.6	857.9	901.1	949.0	996.0	1032.4	1068.1	1113.6	1166.2	1225.2
25°	755.2	773.8	798.4	828.1	882.8	932.6	980.2	1021.4	1069.5	1122.1	1187.8
27.5°	707.7	723.9	746.4	777.2	814.0	869.0	926.7	973.6	1023.0	1079.4	1145.3
30°	679.6	692.8	711.4	742.6	777.7	827.0	885.5	940.3	990.1	1048.7	1117.2
32.5°	650.3	664.3	682.5	707.1	744.8	786.2	844.8	904.8	957.7	1017.6	1084.7
35°	611.2	622.1	638.6	663.8	697.7	733.8	785.8	847.7	903.6	967.7	1031.7
37.5°	571.6	584.6	597.5	620.0	647.8	686.7	729.2	792.4	854.3	912.8	975.3
40°	549.3	557.0	571.2	589.2	618.9	653.3	693.3	755.2	817.1	875.1	938.1
42.5°	524.3	532.8	544.9	563.0	589.5	623.1	662.2	715.7	780.3	836.5	893.8
45°	489.6	494.5	506.6	521.9	543.8	577.7	613.9	661.6	722.3	776.0	826.4
47.5°	454.6	458.8	466.4	480.4	504.9	532.2	566.0	608.8	662.1	715.7	758.4
50°	430.5	434.3	441.4	454.6	476.4	503.3	536.7	575.0	622.7	674.1	709.7
52.5°	406.3	408.4	415.1	430.0	448.4	474.8	504.7	540.0	584.6	627.2	663.3
55°	368.0	373.0	377.3	388.2	405.8	431.0	457.8	491.2	525.8	561.9	592.6
57.5°	328.0	333.4	339.8	349.4	363.3	386.7	410.8	437.9	467.4	497.3	523.1
60°	301.7	306.7	312.1	323.1	335.7	354.3	380.6	404.2	426.6	454.0	479.7
62.5°	275.9	280.8	287.2	296.0	308.1	325.8	347.8	368.2	391.6	415.4	434.6
65°	237.7	241.5	246.4	254.7	266.2	282.0	300.1	316.0	336.8	354.3	371.9
67.5°	195.7	203.0	209.5	216.2	225.9	240.7	253.8	269.0	283.1	296.2	312.1
70°	168.1	176.3	182.4	189.5	198.8	211.4	223.9	234.4	245.9	258.5	272.7
72.5°	144.9	151.4	156.1	163.7	172.1	183.8	195.5	204.1	213.5	222.1	235.9
75°	114.5	117.2	120.5	126.5	134.2	142.9	152.3	159.9	165.4	173.1	182.9
77.5°	82.2	87.5	89.7	94.0	99.4	105.0	111.1	117.6	122.8	125.5	133.1
80°	63.0	65.2	67.3	73.4	76.7	82.1	86.5	92.5	94.7	97.5	104.6
82.5°	49.0	50.3	51.6	53.2	55.2	60.7	65.0	68.9	71.1	72.1	77.5
85°	28.4	29.0	29.5	30.1	30.7	30.7	32.9	35.6	39.5	39.5	41.0
87.5°	13.3	13.5	13.3	12.5	13.2	12.8	13.0	12.6	13.5	14.4	15.4
90°	18.5	17.4	16.0	14.6	13.2	11.8	10.1	8.2	6.3	4.3	2.4
92.5°	31.9	31.3	30.3	29.3	28.4	27.4	25.7	23.5	21.3	19.2	17.0
95°	60.6	60.1	58.9	57.7	56.4	55.1	53.8	52.2	50.6	49.0	47.5
97.5°	95.7	95.1	93.6	92.1	90.7	89.3	87.9	86.7	85.4	84.1	82.9
100°	121.4	121.0	119.4	117.8	116.2	114.6	113.5	112.8	112.1	111.4	110.7
102.5°	148.1	147.6	146.1	144.7	143.2	141.8	140.9	140.6	140.4	140.1	139.8
105°	188.7	188.2	187.5	186.8	186.1	185.4	185.0	184.7	184.6	184.4	184.3
107.5°	232.8	232.3	232.2	232.1	232.0	231.9	231.7	231.6	231.3	231.1	230.9
110°	262.9	263.3	263.5	263.6	263.8	264.0	264.0	263.6	263.2	262.8	262.5



TEST NUMBER: P332974-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	294.2	294.3	294.6	294.9	295.2	295.6	295.7	295.6	295.6	295.5	295.4
115°	343.0	343.2	343.5	343.9	344.2	344.6	344.8	344.8	344.8	344.8	344.8
117.5°	390.1	390.8	391.0	391.3	391.5	391.7	391.8	391.7	391.5	391.4	391.3
120°	422.2	423.0	423.6	424.1	424.6	425.2	425.1	424.4	423.7	422.9	422.2
122.5°	454.1	454.6	454.9	455.1	455.4	455.7	455.6	455.3	455.0	454.8	454.5
125°	501.0	501.3	501.5	501.7	501.8	502.0	502.1	502.1	502.1	502.1	502.1
127.5°	546.1	546.4	546.7	546.9	547.2	547.5	547.4	546.8	546.3	545.8	545.3
130°	577.7	578.0	578.0	578.0	578.0	578.0	577.7	577.2	576.7	576.2	575.6
132.5°	607.4	607.8	607.8	608.0	608.2	608.3	608.2	607.8	607.4	607.0	606.7
135°	652.0	652.4	652.4	652.4	652.4	652.4	651.8	650.8	649.7	648.6	647.6
137.5°	695.2	695.7	695.4	695.1	694.8	694.5	694.2	693.6	693.2	692.7	692.2
140°	723.3	723.5	723.5	723.5	723.5	723.5	723.3	722.9	722.6	722.2	721.9
142.5°	750.0	750.0	750.2	750.4	750.5	750.6	750.5	750.2	749.8	749.5	749.1
145°	790.5	790.7	790.5	790.4	790.2	790.0	789.6	788.9	788.1	787.4	786.7
147.5°	827.1	827.3	827.4	827.5	827.7	827.8	827.4	826.6	825.8	824.9	824.1
150°	850.0	850.0	850.0	850.0	850.0	850.0	849.7	849.0	848.3	847.6	846.8
152.5°	871.3	870.8	870.8	870.6	870.4	870.3	870.1	869.7	869.2	868.8	868.4
155°	901.3	900.6	900.8	900.9	901.1	901.3	901.4	901.4	901.4	901.4	901.4
157.5°	928.2	927.6	927.7	927.7	927.7	927.8	928.0	928.3	928.6	928.9	929.2
160°	944.6	944.1	944.3	944.4	944.6	944.8	945.0	945.2	945.3	945.5	945.7
162.5°	958.9	958.0	958.2	958.4	958.5	958.7	959.0	959.5	960.0	960.4	960.8
165°	978.3	977.3	977.6	978.0	978.3	978.7	979.1	979.7	980.2	980.7	981.3
167.5°	994.8	993.8	993.7	993.7	993.6	993.6	994.0	994.7	995.5	996.2	997.0
170°	1003.7	1002.6	1002.4	1002.3	1002.1	1001.9	1002.3	1003.1	1004.0	1004.9	1005.8
172.5°	1010.1	1008.9	1008.9	1008.8	1008.8	1008.8	1009.2	1009.9	1010.7	1011.4	1012.1
175°	1017.3	1016.1	1016.2	1016.4	1016.6	1016.8	1017.3	1018.2	1019.1	1019.9	1020.8
177.5°	1021.4	1020.5	1020.5	1020.5	1020.5	1020.5	1020.8	1021.5	1022.2	1022.9	1023.7
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4



TEST NUMBER: P332974-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2
2.5°	1367.5	1371.5	1375.9	1384.2	1391.2	1394.3	1400.4	1404.8	1403.5	1409.6	1420.1
5°	1372.9	1387.7	1404.7	1422.2	1441.9	1458.3	1471.5	1484.6	1495.1	1507.7	1526.3
7.5°	1372.1	1398.4	1427.0	1458.3	1490.6	1518.6	1544.4	1570.7	1594.0	1619.6	1653.0
10°	1368.6	1403.6	1439.2	1480.3	1521.3	1560.2	1595.3	1628.1	1659.4	1692.7	1735.0
12.5°	1364.6	1404.9	1448.0	1497.4	1548.5	1595.3	1636.5	1683.8	1722.8	1765.9	1814.7
15°	1347.2	1401.4	1460.0	1524.1	1585.4	1648.4	1704.8	1762.8	1817.0	1868.5	1929.9
17.5°	1327.2	1389.8	1458.9	1534.6	1608.3	1684.9	1751.8	1825.0	1880.4	1949.5	2006.4
20°	1311.1	1378.4	1452.3	1537.2	1621.0	1705.9	1779.8	1854.3	1916.8	1986.3	2058.6
22.5°	1291.3	1365.2	1445.3	1533.3	1621.0	1713.8	1795.6	1869.6	1946.9	2025.3	2099.8
25°	1259.6	1336.3	1421.1	1517.5	1618.3	1713.0	1800.6	1892.6	1975.9	2060.8	2127.6
27.5°	1220.6	1301.1	1390.6	1490.0	1593.4	1690.4	1793.7	1891.7	1975.5	2057.1	2115.4
30°	1189.5	1274.4	1360.3	1461.1	1568.4	1672.5	1783.1	1881.1	1969.3	2042.7	2075.5
32.5°	1157.5	1238.0	1326.6	1428.7	1538.7	1650.6	1760.3	1860.5	1942.1	1986.2	1987.0
35°	1101.8	1177.4	1269.4	1369.7	1482.5	1604.0	1715.2	1813.8	1863.6	1867.4	1813.8
37.5°	1041.2	1110.5	1197.4	1297.7	1421.3	1542.1	1655.7	1721.4	1738.1	1682.4	1583.1
40°	997.8	1061.8	1145.7	1248.6	1371.3	1496.1	1599.7	1647.8	1630.3	1539.9	1429.3
42.5°	952.2	1011.9	1092.7	1194.3	1317.4	1443.6	1531.8	1557.6	1511.2	1406.8	1277.3
45°	877.9	932.6	1012.6	1115.0	1233.3	1351.5	1418.4	1405.3	1328.0	1204.3	1059.1
47.5°	800.4	853.3	925.3	1020.0	1141.1	1243.3	1288.5	1248.9	1139.0	1002.8	884.8
50°	749.2	803.4	869.7	960.0	1070.6	1169.2	1198.3	1138.0	1015.9	884.9	776.6
52.5°	698.8	745.1	810.1	897.4	1003.1	1086.4	1101.8	1032.4	906.3	789.0	692.8
55°	622.1	664.3	719.1	801.2	892.6	963.3	955.1	865.9	751.4	651.2	575.6
57.5°	548.0	579.7	630.3	707.3	787.6	835.0	805.0	728.9	622.3	540.2	476.4
60°	498.9	528.5	575.6	642.9	713.6	740.4	715.2	632.6	548.2	473.2	419.5
62.5°	452.5	478.6	519.0	581.6	638.7	654.5	627.6	555.4	479.4	415.3	370.9
65°	385.0	409.1	443.6	488.0	527.4	535.0	517.5	443.6	386.1	332.4	301.7
67.5°	323.8	339.5	366.5	404.8	425.7	430.2	396.4	349.9	299.2	266.3	243.1
70°	282.6	293.5	318.7	339.5	356.5	357.0	325.8	288.6	249.7	222.9	205.9
72.5°	242.7	253.3	272.3	286.5	299.5	295.3	266.7	237.3	205.9	185.7	173.1
75°	187.3	196.6	206.4	213.0	213.0	207.6	186.7	164.9	146.8	134.8	130.9
77.5°	136.2	143.8	147.1	146.1	144.2	135.6	122.5	108.1	101.6	95.9	93.1
80°	106.8	110.1	111.1	108.4	105.1	95.3	86.5	80.5	74.5	72.3	71.2
82.5°	79.2	82.1	79.2	79.9	72.7	64.6	59.8	57.8	55.2	54.3	53.2
85°	42.1	41.6	40.6	37.8	32.9	31.8	31.2	30.7	29.5	30.1	29.0
87.5°	15.3	14.4	13.0	13.0	13.3	12.7	13.5	13.7	14.0	13.8	14.9
90°	4.3	6.3	8.2	10.1	11.8	13.2	14.6	16.0	17.4	18.5	19.5
92.5°	19.2	21.3	23.5	25.7	27.4	28.4	29.3	30.3	31.3	31.9	32.6
95°	49.0	50.6	52.2	53.8	55.1	56.4	57.7	58.9	60.1	60.6	61.2
97.5°	84.1	85.4	86.7	87.9	89.3	90.7	92.1	93.6	95.1	95.7	96.3
100°	111.4	112.1	112.8	113.5	114.6	116.2	117.8	119.4	121.0	121.4	121.7
102.5°	140.1	140.4	140.6	140.9	141.8	143.2	144.7	146.1	147.6	148.1	148.5
105°	184.4	184.6	184.7	185.0	185.4	186.1	186.8	187.5	188.2	188.7	189.3
107.5°	231.1	231.3	231.6	231.7	231.9	232.0	232.1	232.2	232.3	232.8	233.3
110°	262.8	263.2	263.6	264.0	264.0	263.8	263.6	263.5	263.3	262.9	262.6



TEST NUMBER: P332974-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	295.5	295.6	295.6	295.7	295.6	295.2	294.9	294.6	294.3	294.2	294.1
115°	344.8	344.8	344.8	344.8	344.6	344.2	343.9	343.5	343.2	343.0	342.8
117.5°	391.4	391.5	391.7	391.8	391.7	391.5	391.3	391.0	390.8	390.1	389.6
120°	422.9	423.7	424.4	425.1	425.2	424.6	424.1	423.6	423.0	422.2	421.3
122.5°	454.8	455.0	455.3	455.6	455.7	455.4	455.1	454.9	454.6	454.1	453.4
125°	502.1	502.1	502.1	502.1	502.0	501.8	501.7	501.5	501.3	501.0	500.6
127.5°	545.8	546.3	546.8	547.4	547.5	547.2	546.9	546.7	546.4	546.1	545.7
130°	576.2	576.7	577.2	577.7	578.0	578.0	578.0	578.0	578.0	577.7	577.3
132.5°	607.0	607.4	607.8	608.2	608.3	608.2	608.0	607.8	607.8	607.4	607.0
135°	648.6	649.7	650.8	651.8	652.4	652.4	652.4	652.4	652.4	652.0	651.6
137.5°	692.7	693.2	693.6	694.2	694.5	694.8	695.1	695.4	695.7	695.2	694.7
140°	722.2	722.6	722.9	723.3	723.5	723.5	723.5	723.5	723.5	723.3	723.2
142.5°	749.5	749.8	750.2	750.5	750.6	750.5	750.4	750.2	750.0	750.0	750.0
145°	787.4	788.1	788.9	789.6	790.0	790.2	790.4	790.5	790.7	790.5	790.4
147.5°	824.9	825.8	826.6	827.4	827.8	827.7	827.5	827.4	827.3	827.1	827.0
150°	847.6	848.3	849.0	849.7	850.0	850.0	850.0	850.0	850.0	850.0	850.0
152.5°	868.8	869.2	869.7	870.1	870.3	870.4	870.6	870.8	870.8	871.3	871.7
155°	901.4	901.4	901.4	901.4	901.3	901.1	900.9	900.8	900.6	901.3	902.1
157.5°	928.9	928.6	928.3	928.0	927.8	927.7	927.7	927.7	927.6	928.2	928.7
160°	945.5	945.3	945.2	945.0	944.8	944.6	944.4	944.3	944.1	944.6	945.2
162.5°	960.4	960.0	959.5	959.0	958.7	958.5	958.4	958.2	958.0	958.9	959.9
165°	980.7	980.2	979.7	979.1	978.7	978.3	978.0	977.6	977.3	978.3	979.5
167.5°	996.2	995.5	994.7	994.0	993.6	993.6	993.7	993.7	993.8	994.8	995.9
170°	1004.9	1004.0	1003.1	1002.3	1001.9	1002.1	1002.3	1002.4	1002.6	1003.7	1004.7
172.5°	1011.4	1010.7	1009.9	1009.2	1008.8	1008.8	1008.8	1008.9	1008.9	1010.1	1011.3
175°	1019.9	1019.1	1018.2	1017.3	1016.8	1016.6	1016.4	1016.2	1016.1	1017.3	1018.5
177.5°	1022.9	1022.2	1021.5	1020.8	1020.5	1020.5	1020.5	1020.5	1020.5	1021.4	1022.5
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4



TEST NUMBER: P332974-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2
2.5°	1425.8	1427.6	1428.9	1433.3	1433.7	1437.7	1433.7
5°	1543.8	1551.5	1563.5	1575.6	1576.7	1584.3	1570.7
7.5°	1676.1	1693.8	1704.9	1724.4	1732.1	1736.9	1729.0
10°	1767.2	1783.7	1812.7	1826.9	1841.2	1843.3	1836.8
12.5°	1855.3	1881.4	1904.2	1931.2	1930.5	1949.8	1942.8
15°	1972.6	1999.5	2031.2	2061.3	2072.3	2072.3	2081.1
17.5°	2056.3	2105.5	2138.3	2161.9	2187.8	2192.3	2189.3
20°	2112.8	2165.9	2201.0	2231.7	2249.2	2254.1	2254.1
22.5°	2154.8	2200.0	2234.3	2261.8	2276.3	2282.1	2280.4
25°	2184.0	2222.9	2243.7	2251.9	2255.7	2254.6	2244.3
27.5°	2144.1	2142.4	2129.2	2104.0	2085.1	2073.6	2060.5
30°	2067.9	2039.4	2006.5	1970.4	1923.9	1888.2	1877.3
32.5°	1954.4	1890.5	1834.8	1774.6	1724.5	1688.9	1674.0
35°	1735.0	1633.6	1550.9	1478.6	1426.1	1393.2	1382.3
37.5°	1474.5	1376.4	1274.1	1204.0	1160.3	1127.1	1114.8
40°	1308.8	1202.1	1112.8	1047.1	1002.2	969.9	969.3
42.5°	1157.7	1055.7	971.8	924.4	876.0	854.6	854.5
45°	947.9	866.3	795.2	758.0	728.9	711.4	706.5
47.5°	784.9	717.4	669.9	640.3	616.6	605.5	598.3
50°	693.3	634.1	596.4	570.6	557.5	543.3	542.2
52.5°	617.1	569.3	539.9	519.0	502.3	493.8	494.0
55°	518.6	480.9	460.0	444.1	431.0	424.5	421.7
57.5°	436.9	408.5	393.4	378.8	373.3	368.1	366.7
60°	386.1	366.9	352.7	341.2	333.0	331.3	330.7
62.5°	344.0	324.0	314.1	305.2	299.2	296.7	295.7
65°	283.7	268.9	260.2	253.0	250.8	247.0	246.4
67.5°	228.7	219.8	214.0	209.1	206.1	205.9	205.9
70°	195.0	190.0	185.1	182.4	180.7	179.6	179.6
72.5°	166.0	162.4	158.4	156.9	156.6	155.5	155.1
75°	126.5	122.7	123.2	120.5	118.3	115.6	113.9
77.5°	89.7	87.0	86.4	86.1	84.2	83.9	84.8
80°	69.6	66.8	66.2	66.8	66.2	64.6	64.6
82.5°	52.9	50.6	50.1	49.7	49.2	49.7	48.9
85°	28.4	27.4	27.4	27.4	28.4	28.0	27.4
87.5°	14.2	13.9	14.6	14.2	14.3	13.9	14.4
90°	20.6	21.6	22.3	22.7	23.1	23.4	23.7
92.5°	33.2	33.8	34.3	34.5	34.7	34.9	35.1
95°	61.7	62.2	62.5	62.5	62.5	62.5	62.5
97.5°	97.0	97.6	97.9	97.9	97.9	97.9	97.9
100°	122.0	122.4	122.6	122.6	122.6	122.6	122.6
102.5°	149.0	149.5	149.8	150.0	150.1	150.3	150.4
105°	189.8	190.3	190.8	191.3	191.9	192.4	192.9
107.5°	233.8	234.2	234.5	234.5	234.4	234.4	234.3
110°	262.2	261.9	262.0	262.5	263.0	263.6	264.1



TEST NUMBER: P332974-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	294.1	294.1	294.1	294.1	294.2	294.4	294.5
115°	342.6	342.5	342.3	342.1	341.9	341.7	341.6
117.5°	389.0	388.4	387.9	387.5	387.2	386.8	386.5
120°	420.4	419.5	419.2	419.6	419.9	420.3	420.6
122.5°	452.9	452.3	451.6	451.0	450.4	449.7	449.1
125°	500.3	499.9	499.6	499.2	498.8	498.5	498.1
127.5°	545.3	544.9	544.6	544.4	544.1	543.8	543.5
130°	576.9	576.6	576.1	575.4	574.6	573.9	573.2
132.5°	606.7	606.3	606.0	605.7	605.5	605.1	604.9
135°	651.3	650.9	650.5	650.0	649.4	648.9	648.4
137.5°	694.3	693.9	693.6	693.8	693.9	694.0	694.1
140°	722.9	722.8	722.6	722.5	722.2	722.1	721.9
142.5°	750.0	750.0	749.9	749.9	749.8	749.8	749.7
145°	790.2	790.0	789.6	789.1	788.6	788.1	787.5
147.5°	826.8	826.6	826.5	826.3	826.2	826.0	825.9
150°	850.0	850.0	849.9	849.8	849.5	849.4	849.2
152.5°	872.1	872.6	872.6	872.1	871.6	871.2	870.7
155°	902.7	903.4	903.4	902.7	902.1	901.3	900.6
157.5°	929.2	929.8	929.7	929.2	928.5	928.0	927.3
160°	945.7	946.2	946.0	945.2	944.3	943.4	942.5
162.5°	960.8	961.8	961.9	961.0	960.1	959.3	958.3
165°	980.5	981.5	981.7	981.0	980.3	979.6	978.9
167.5°	997.0	998.0	998.0	996.9	995.8	994.7	993.6
170°	1005.8	1006.9	1006.7	1005.5	1004.2	1003.1	1001.8
172.5°	1012.5	1013.8	1013.7	1012.5	1011.2	1010.0	1008.8
175°	1019.8	1021.0	1021.0	1019.8	1018.5	1017.3	1016.1
177.5°	1023.4	1024.5	1024.4	1023.3	1022.1	1021.0	1019.9
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4

(END OF REPORT)