

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331322-840

Luminaire Tested: **SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331322-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6057.4 lumens
Efficiency: N/A
Efficacy: 122.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331322-840
CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331322-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	59	59	59	43	43	43	36
1	95	91	87	84	86	82	79	76	67	64	62	52	51	49	39	38	37	31
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32	26
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	27	23
4	73	62	55	49	66	57	50	45	46	42	38	37	33	31	28	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17
6	62	50	42	37	56	46	39	34	38	33	29	30	26	24	23	20	19	15
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	19	17	14
8	53	41	34	28	48	38	31	26	31	26	23	25	21	19	19	17	15	13
9	49	37	30	25	45	34	28	24	29	24	20	23	19	17	18	15	14	11
10	46	34	27	23	42	32	25	21	26	22	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15844	15844	15844	15844
5°	17763	15948	14131	15948
10°	20354	15816	12231	15816
15°	22519	15527	10805	15527
20°	22175	15216	9850	15216
25°	19996	14801	9246	14801
30°	16524	14139	8804	14139
35°	12043	13448	8489	13448
40°	9619	12631	8315	12631
45°	8405	11686	8079	11686
50°	7902	10771	7920	10771
55°	7282	9841	7707	9841
60°	6675	8854	7379	8854
65°	6082	7966	7060	7966
70°	5519	7105	6590	7105
75°	4897	6145	5833	6145
80°	4203	5086	4695	5086
85°	3779	3779	2779	3779



TEST NUMBER: P331322-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	1.5
10°-20°	271.7	4.5
20°-30°	394.3	6.5
30°-40°	416.1	6.9
40°-50°	368.4	6.1
50°-60°	294.0	4.9
60°-70°	199.8	3.3
70°-80°	102.5	1.7
80°-90°	30.3	0.5
90°-100°	88.1	1.5
100°-110°	273.6	4.5
110°-120°	467.6	7.7
120°-130°	614.9	10.2
130°-140°	690.2	11.4
140°-150°	676.7	11.2
150°-160°	567.6	9.4
160°-170°	376.5	6.2
170°-180°	131.6	2.2
0°-30°	759.5	12.5
0°-40°	1175.6	19.4
0°-60°	1838.0	30.3
0°-90°	2170.6	35.8
90°-120°	829.3	13.7
90°-150°	2811.1	46.4
90°-180°	3887.0	64.2
0°-180°	6057.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	981	981	981	981	981	
5°	1096	984	872	984	1096	109
15°	1347	929	646	929	1347	372
25°	1122	831	519	831	1122	507
35°	611	682	431	682	611	397
45°	368	512	354	512	368	289
55°	259	350	274	350	259	232
65°	159	208	185	208	159	158
75°	78	98	94	98	78	84
85°	20	20	15	20	20	23
90°	40	1	40	1	40	18
95°	73	61	73	61	73	81
105°	260	252	260	252	260	274
115°	469	469	469	469	469	463
125°	685	683	685	683	685	611
135°	894	883	894	883	894	688
145°	1084	1072	1084	1072	1084	677
155°	1235	1226	1235	1226	1235	568
165°	1335	1334	1335	1334	1335	376
175°	1383	1388	1383	1388	1383	131
180°	1390	1390	1390	1390	1390	



TEST NUMBER: P331322-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1026.6	1026.9	1027.4	1022.7	1022.1	1022.1	1017.8	1014.2	1010.0	1004.2	1004.8
5°	1096.0	1100.1	1101.7	1097.1	1090.4	1089.5	1083.2	1072.6	1062.8	1054.9	1049.2
7.5°	1178.8	1180.4	1176.8	1170.8	1165.8	1156.7	1144.8	1133.1	1116.7	1101.7	1090.6
10°	1241.5	1243.9	1237.4	1228.7	1221.5	1211.0	1193.7	1175.9	1154.5	1133.7	1117.1
12.5°	1289.2	1294.8	1286.6	1285.5	1273.1	1258.7	1238.0	1229.0	1198.8	1169.9	1152.1
15°	1347.2	1346.8	1347.6	1340.4	1331.3	1329.1	1307.2	1283.4	1240.8	1223.9	1194.4
17.5°	1330.4	1336.2	1338.8	1338.7	1338.5	1337.1	1330.0	1315.0	1293.6	1266.2	1232.2
20°	1290.6	1298.1	1299.3	1308.0	1312.8	1319.3	1321.9	1317.8	1304.5	1281.5	1252.1
22.5°	1229.0	1231.1	1234.7	1248.2	1258.8	1274.9	1283.2	1297.2	1292.1	1280.9	1256.4
25°	1122.4	1118.6	1131.8	1138.6	1163.1	1188.7	1207.2	1227.6	1245.7	1256.7	1249.5
27.5°	994.3	988.7	1008.5	1026.4	1046.3	1074.1	1102.9	1136.9	1165.2	1200.6	1212.7
30°	886.3	889.7	908.6	927.8	958.0	997.1	1029.6	1066.9	1107.3	1146.9	1174.4
32.5°	769.8	782.8	794.8	824.3	850.8	894.5	942.1	988.8	1039.2	1084.1	1126.7
35°	611.0	626.0	642.7	664.2	701.5	744.9	791.2	854.2	922.9	984.3	1034.9
37.5°	514.2	511.9	521.4	536.9	567.1	602.2	655.5	717.8	798.6	870.8	942.1
40°	456.4	454.8	461.6	475.9	499.0	524.6	571.4	626.0	701.1	789.3	874.2
42.5°	416.5	417.4	421.2	431.3	447.1	468.2	503.2	549.8	618.4	701.6	792.7
45°	368.1	370.7	374.9	379.8	388.8	406.2	425.8	459.0	513.3	582.7	672.5
47.5°	333.3	333.4	337.5	341.8	347.2	357.0	373.0	393.8	432.1	488.7	565.8
50°	314.6	311.8	314.9	318.3	324.0	330.7	341.3	360.9	386.6	432.2	496.7
52.5°	291.6	291.6	294.4	295.7	300.7	307.5	317.2	330.7	354.0	389.7	442.7
55°	258.7	260.6	262.2	264.4	268.9	273.8	281.3	290.4	308.5	335.3	374.5
57.5°	227.8	228.4	229.9	234.2	237.1	241.6	248.7	257.0	268.7	288.6	318.1
60°	206.7	206.7	209.6	211.6	215.3	219.8	225.5	233.5	244.0	260.2	284.0
62.5°	187.3	187.0	188.2	191.4	194.2	198.4	204.1	210.9	220.8	235.2	254.7
65°	159.2	158.4	160.7	161.4	164.4	168.5	173.1	180.3	188.2	198.7	216.1
67.5°	132.0	132.9	134.1	135.5	137.2	141.6	144.6	149.7	156.3	165.1	176.9
70°	116.9	116.9	116.9	118.1	120.3	122.6	125.6	129.8	136.1	143.7	154.2
72.5°	100.0	101.2	102.4	101.8	104.6	105.9	109.6	111.9	118.1	122.9	132.2
75°	78.5	78.5	78.5	80.3	81.5	82.6	84.8	87.2	90.2	96.1	101.1
77.5°	58.6	58.4	58.8	59.2	60.4	61.8	62.4	64.5	67.3	70.1	74.2
80°	45.2	46.0	46.4	47.2	47.2	47.9	48.3	50.9	52.8	54.7	57.4
82.5°	35.0	35.1	35.2	35.3	35.6	36.2	37.1	38.0	38.6	40.2	42.2
85°	20.4	20.0	20.0	20.7	20.4	20.4	21.1	21.9	21.9	22.2	23.4
87.5°	15.9	15.8	16.1	15.7	15.7	16.0	16.1	15.9	16.3	16.7	15.9
90°	39.9	39.6	39.4	39.1	38.9	39.0	39.5	40.0	40.5	41.1	35.3
92.5°	38.0	38.0	37.9	37.9	37.8	37.8	37.6	37.5	37.4	37.3	36.0
95°	72.7	73.2	73.8	74.3	74.8	75.0	75.0	75.0	75.0	75.0	74.5
97.5°	126.0	126.0	126.1	126.1	126.2	126.2	126.2	126.2	126.2	126.2	125.2
100°	160.7	161.0	161.3	161.5	161.8	161.9	161.9	161.9	161.9	161.9	161.1
102.5°	200.2	200.4	200.7	200.9	201.2	201.2	201.0	200.8	200.6	200.4	199.3
105°	260.4	260.4	260.4	260.4	260.4	260.1	259.6	259.1	258.6	258.0	257.5
107.5°	317.2	318.4	319.6	320.8	321.9	322.4	322.2	322.0	321.8	321.6	321.6
110°	361.3	362.0	362.8	363.7	364.5	364.9	364.9	364.9	364.9	364.9	364.9



TEST NUMBER: P331322-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	403.5	404.1	404.7	405.3	405.9	406.5	407.1	407.7	408.3	408.9	409.1
115°	469.2	470.0	470.8	471.6	472.3	472.8	473.1	473.4	473.6	473.9	474.4
117.5°	531.9	532.6	533.4	534.2	535.0	535.7	536.3	536.9	537.6	538.2	539.7
120°	575.9	576.7	577.5	578.3	579.1	579.5	579.5	579.5	579.5	579.5	581.6
122.5°	619.1	619.8	620.3	620.9	621.5	622.0	622.7	623.3	623.9	624.5	626.0
125°	685.1	685.3	685.6	685.8	686.1	686.6	687.4	688.2	688.9	689.7	690.5
127.5°	745.1	746.0	746.8	747.6	748.4	749.3	750.2	751.2	752.1	753.1	754.1
130°	788.3	789.3	790.3	791.4	792.4	793.2	793.8	794.3	794.8	795.4	795.9
132.5°	829.6	830.4	831.2	832.1	832.9	833.9	835.1	836.2	837.4	838.5	838.4
135°	893.8	894.6	895.4	896.2	897.0	897.5	897.8	898.1	898.3	898.6	898.1
137.5°	952.0	953.1	954.1	955.1	956.2	956.8	957.0	957.3	957.5	957.7	956.9
140°	992.4	993.4	994.5	995.5	996.5	997.0	997.0	997.0	997.0	997.0	995.8
142.5°	1029.0	1030.1	1031.1	1032.1	1033.2	1033.6	1033.4	1033.2	1033.0	1032.8	1031.9
145°	1083.9	1084.9	1086.0	1087.0	1088.0	1088.4	1088.2	1087.9	1087.6	1087.4	1085.8
147.5°	1133.0	1133.9	1134.9	1135.9	1136.9	1137.1	1136.5	1136.0	1135.4	1134.8	1133.8
150°	1164.9	1165.6	1166.4	1167.2	1168.0	1168.0	1167.2	1166.4	1165.6	1164.9	1163.8
152.5°	1194.9	1195.9	1196.9	1197.8	1198.8	1198.8	1197.8	1196.9	1195.9	1194.9	1193.7
155°	1235.2	1236.0	1236.8	1237.6	1238.3	1238.1	1236.8	1235.5	1234.2	1232.8	1232.1
157.5°	1269.9	1271.2	1272.4	1273.6	1275.0	1274.7	1272.9	1271.1	1269.4	1267.6	1267.1
160°	1291.5	1292.5	1293.6	1294.6	1295.7	1295.5	1293.8	1292.3	1290.7	1289.2	1288.9
162.5°	1310.3	1311.5	1312.8	1314.0	1315.2	1315.0	1313.2	1311.5	1309.7	1308.0	1307.7
165°	1334.9	1336.3	1337.6	1338.9	1340.1	1339.9	1338.1	1336.3	1334.4	1332.6	1332.6
167.5°	1355.1	1356.5	1357.8	1359.2	1360.5	1360.3	1358.5	1356.7	1354.8	1353.0	1353.0
170°	1365.4	1367.0	1368.6	1370.1	1371.7	1371.5	1369.7	1367.9	1366.0	1364.2	1364.5
172.5°	1373.8	1375.4	1377.0	1378.6	1380.1	1380.0	1378.2	1376.3	1374.5	1372.7	1372.9
175°	1383.0	1384.6	1386.1	1387.8	1389.3	1389.2	1387.4	1385.5	1383.7	1381.8	1382.4
177.5°	1387.3	1388.5	1389.8	1391.0	1392.2	1392.2	1391.0	1389.8	1388.5	1387.3	1387.7
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1



TEST NUMBER: P331322-840
 CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1006.9	1004.5	1003.0	997.6	992.8	988.0	986.4	987.0	980.4	974.1	971.4
5°	1046.2	1038.6	1031.5	1021.3	1009.3	996.0	989.3	984.0	970.8	956.4	948.2
7.5°	1081.4	1070.6	1056.7	1037.6	1020.1	999.3	986.0	974.4	955.0	934.8	922.5
10°	1102.8	1088.0	1070.4	1046.9	1025.4	1000.2	982.5	964.7	942.1	918.0	902.9
12.5°	1121.2	1101.4	1083.9	1053.9	1028.4	996.8	975.8	950.9	927.1	898.4	883.5
15°	1165.0	1128.4	1095.2	1061.3	1030.0	985.8	962.5	928.9	897.6	862.1	845.2
17.5°	1198.8	1157.7	1105.5	1062.4	1025.8	976.9	942.6	902.4	865.4	824.9	801.8
20°	1218.2	1171.0	1114.8	1063.6	1019.8	964.0	926.7	885.6	842.1	796.5	771.6
22.5°	1229.6	1180.1	1124.5	1059.0	1007.7	953.4	906.5	861.4	817.4	768.2	742.0
25°	1233.2	1188.0	1129.1	1055.2	992.6	931.2	874.5	830.8	777.7	731.6	693.6
27.5°	1215.3	1182.9	1126.3	1048.1	975.2	903.3	840.3	790.7	734.6	684.7	646.3
30°	1193.3	1174.4	1119.3	1040.9	961.3	884.0	814.7	758.4	702.7	652.1	612.9
32.5°	1159.2	1155.1	1106.7	1030.7	946.5	859.6	787.8	730.9	669.1	619.5	582.1
35°	1092.2	1110.3	1079.7	1007.7	918.7	824.9	747.1	682.3	618.1	570.6	535.5
37.5°	1002.5	1047.4	1039.5	974.1	881.1	787.0	701.1	633.4	572.3	524.3	489.9
40°	940.6	997.9	1006.2	948.5	854.6	757.7	666.8	599.3	539.7	495.9	461.2
42.5°	874.2	941.2	964.0	917.8	825.7	726.9	636.0	566.1	507.2	464.5	433.8
45°	763.0	851.6	892.7	866.3	777.3	676.2	582.7	511.8	458.3	418.3	394.5
47.5°	658.9	755.8	811.1	801.7	723.5	623.4	531.0	462.9	410.8	378.9	357.6
50°	585.3	684.9	751.6	754.7	684.9	585.7	492.9	428.8	380.9	351.1	333.8
52.5°	521.4	616.4	689.2	705.2	641.8	546.4	458.8	395.1	352.8	325.5	309.9
55°	437.9	518.2	599.0	628.3	577.4	486.9	405.8	349.6	310.0	291.1	277.6
57.5°	364.1	431.0	505.5	538.1	506.6	429.2	353.1	304.4	272.3	255.7	245.3
60°	325.1	377.9	444.2	483.1	456.0	387.0	320.5	274.2	247.8	233.1	223.3
62.5°	288.9	335.7	391.7	427.3	412.5	347.4	288.0	247.0	224.3	210.5	203.4
65°	238.3	275.3	318.7	351.5	341.7	292.3	243.7	208.5	190.5	179.6	173.9
67.5°	196.2	223.0	253.1	281.8	273.9	238.8	199.9	172.5	159.0	149.6	146.2
70°	169.8	190.1	216.8	239.8	233.5	204.8	173.9	150.5	138.8	130.9	127.4
72.5°	144.4	161.1	181.6	200.4	196.0	172.2	146.4	128.8	119.8	112.5	109.7
75°	109.0	121.8	134.3	146.7	145.6	127.1	112.0	98.5	91.3	85.6	84.5
77.5°	80.5	87.7	96.1	103.5	101.5	90.9	79.1	71.3	66.0	62.2	61.6
80°	61.5	65.6	71.7	77.0	74.3	69.8	60.4	54.7	50.9	47.2	45.6
82.5°	44.5	48.8	52.3	55.2	53.2	49.0	43.1	39.3	37.1	34.4	33.8
85°	23.4	25.7	27.2	27.9	27.2	24.5	21.9	20.4	18.5	17.4	17.0
87.5°	14.9	13.8	12.7	12.4	10.9	10.2	8.4	6.9	7.2	7.5	7.6
90°	29.6	23.8	18.1	13.7	10.6	7.5	4.3	1.2	4.3	7.5	10.6
92.5°	34.6	33.2	31.9	30.1	27.8	25.4	23.1	20.9	23.1	25.4	27.8
95°	74.0	73.5	73.0	71.4	68.8	66.2	63.6	61.0	63.6	66.2	68.8
97.5°	124.2	123.2	122.3	120.6	118.4	116.0	113.7	111.5	113.7	116.0	118.4
100°	160.3	159.6	158.8	157.3	155.2	153.2	151.1	149.0	151.1	153.2	155.2
102.5°	198.3	197.4	196.4	195.1	193.4	191.8	190.1	188.4	190.1	191.8	193.4
105°	257.0	256.5	256.0	255.3	254.6	253.8	253.0	252.2	253.0	253.8	254.6
107.5°	321.6	321.6	321.6	321.0	319.9	318.8	317.6	316.5	317.6	318.8	319.9
110°	364.9	364.9	364.9	364.1	362.4	360.9	359.3	357.8	359.3	360.9	362.4



TEST NUMBER: P331322-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	409.3	409.5	409.8	409.1	407.5	406.0	404.3	402.8	404.3	406.0	407.5
115°	474.9	475.4	475.9	475.4	473.9	472.3	470.8	469.2	470.8	472.3	473.9
117.5°	541.1	542.6	544.0	543.7	541.6	539.6	537.5	535.3	537.5	539.6	541.6
120°	583.7	585.7	587.8	587.8	585.7	583.7	581.6	579.5	581.6	583.7	585.7
122.5°	627.4	628.9	630.4	629.9	627.3	624.8	622.4	619.9	622.4	624.8	627.3
125°	691.4	692.1	692.9	692.1	689.7	687.4	685.1	682.7	685.1	687.4	689.7
127.5°	755.0	755.9	756.9	755.8	752.9	749.9	746.9	744.0	746.9	749.9	752.9
130°	796.4	796.9	797.4	796.0	792.5	789.2	785.8	782.4	785.8	789.2	792.5
132.5°	838.3	838.2	838.1	836.7	833.8	831.1	828.4	825.6	828.4	831.1	833.8
135°	897.5	897.0	896.5	894.7	891.9	889.1	886.2	883.3	886.2	889.1	891.9
137.5°	956.3	955.6	954.9	953.4	951.1	948.8	946.4	944.0	946.4	948.8	951.1
140°	994.5	993.2	991.9	990.1	987.7	985.3	983.0	980.7	983.0	985.3	987.7
142.5°	1031.0	1030.1	1029.2	1027.5	1025.2	1022.9	1020.6	1018.2	1020.6	1022.9	1025.2
145°	1084.3	1082.7	1081.2	1079.4	1077.6	1075.8	1074.0	1072.2	1074.0	1075.8	1077.6
147.5°	1132.8	1131.7	1130.6	1129.0	1126.8	1124.6	1122.5	1120.2	1122.5	1124.6	1126.8
150°	1162.8	1161.7	1160.6	1159.3	1157.8	1156.2	1154.7	1153.1	1154.7	1156.2	1157.8
152.5°	1192.3	1191.1	1189.8	1188.4	1186.9	1185.3	1183.8	1182.1	1183.8	1185.3	1186.9
155°	1231.3	1230.5	1229.7	1229.0	1228.2	1227.4	1226.6	1225.9	1226.6	1227.4	1228.2
157.5°	1266.7	1266.2	1265.7	1265.3	1264.7	1264.1	1263.6	1263.1	1263.6	1264.1	1264.7
160°	1288.7	1288.4	1288.1	1287.8	1287.2	1286.7	1286.2	1285.7	1286.2	1286.7	1287.2
162.5°	1307.4	1307.2	1306.9	1306.8	1306.6	1306.5	1306.4	1306.3	1306.4	1306.5	1306.6
165°	1332.6	1332.6	1332.6	1332.7	1332.9	1333.2	1333.5	1333.7	1333.5	1333.2	1332.9
167.5°	1353.1	1353.1	1353.2	1353.6	1354.4	1355.1	1355.9	1356.8	1355.9	1355.1	1354.4
170°	1364.7	1365.0	1365.3	1365.8	1366.5	1367.4	1368.2	1369.0	1368.2	1367.4	1366.5
172.5°	1373.2	1373.5	1373.7	1374.2	1375.0	1375.8	1376.6	1377.4	1376.6	1375.8	1375.0
175°	1382.9	1383.4	1383.9	1384.6	1385.3	1386.1	1386.9	1387.8	1386.9	1386.1	1385.3
177.5°	1388.1	1388.5	1388.9	1389.5	1390.1	1390.7	1391.3	1391.9	1391.3	1390.7	1390.1
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1



TEST NUMBER: P331322-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	968.4	966.5	960.2	956.8	951.5	946.3	943.0	944.5	945.7	945.1	944.2
5°	940.6	933.4	922.5	913.0	906.3	893.8	888.6	886.0	883.6	881.0	878.4
7.5°	907.6	896.3	880.6	867.2	854.4	839.0	830.2	824.9	819.4	813.4	808.2
10°	884.0	868.2	851.6	832.7	817.7	803.7	791.2	782.9	775.4	768.2	763.0
12.5°	859.3	841.0	820.5	794.8	778.1	758.1	756.3	741.6	729.8	725.4	719.2
15°	819.9	794.3	768.2	737.7	724.5	706.4	695.1	683.8	673.6	666.4	664.5
17.5°	775.2	741.9	716.1	694.2	672.6	654.0	643.6	634.5	626.1	616.5	615.3
20°	741.0	712.5	684.2	664.9	642.7	623.8	611.0	601.9	594.7	589.1	584.2
22.5°	708.8	677.4	651.6	630.5	608.5	593.3	583.2	574.5	568.6	562.3	557.6
25°	657.0	632.5	604.2	580.5	562.3	552.5	544.2	536.6	532.9	528.8	523.5
27.5°	611.7	584.4	558.0	539.6	523.6	514.9	509.1	503.9	500.4	498.0	494.9
30°	579.7	552.1	531.4	513.3	500.1	491.4	487.7	484.6	480.5	479.0	477.5
32.5°	548.9	524.1	506.3	490.7	478.1	472.4	469.0	466.3	463.0	461.5	458.5
35°	505.3	484.6	467.3	458.6	448.4	443.5	440.9	437.1	434.1	432.6	432.2
37.5°	464.4	446.4	434.9	423.8	419.5	416.5	412.9	410.3	409.4	409.2	408.8
40°	437.9	423.1	412.9	403.9	402.0	397.5	394.5	392.2	392.2	392.6	392.2
42.5°	413.7	400.5	391.5	383.7	381.5	378.8	375.8	375.7	376.3	377.5	376.3
45°	377.2	367.7	361.3	357.5	353.4	350.7	350.3	351.5	351.8	352.2	353.4
47.5°	343.5	337.2	331.4	327.3	325.5	325.0	324.6	326.5	328.3	329.0	330.7
50°	323.6	316.4	311.5	308.9	307.4	306.6	307.4	309.6	311.1	313.1	314.2
52.5°	301.2	296.2	292.9	290.7	290.1	290.6	290.7	293.4	295.8	296.4	297.0
55°	270.4	266.6	265.9	262.5	264.0	263.6	265.5	267.0	269.2	271.6	272.0
57.5°	239.6	236.6	234.6	234.9	235.3	237.0	238.5	241.3	243.7	246.0	246.3
60°	219.1	217.6	216.5	216.5	217.2	219.5	221.4	224.0	225.5	227.0	228.1
62.5°	200.5	198.9	197.7	198.3	200.4	201.7	203.9	205.3	206.8	208.3	208.8
65°	170.9	170.1	171.3	172.0	172.4	174.2	176.9	178.0	179.6	180.3	182.9
67.5°	143.6	143.8	143.6	144.7	146.8	147.3	149.8	152.5	152.8	154.2	155.9
70°	125.2	125.9	126.7	127.4	129.4	130.1	132.0	133.1	134.6	135.7	136.9
72.5°	108.4	108.5	109.3	109.1	110.7	112.3	113.9	115.0	116.5	118.0	119.1
75°	83.3	83.3	84.1	84.5	86.3	88.3	87.9	88.7	90.2	91.7	92.4
77.5°	60.9	60.1	60.9	61.2	61.8	63.4	63.7	64.8	66.6	66.0	66.9
80°	46.4	45.2	46.4	46.8	46.8	48.7	48.7	49.4	50.5	49.4	50.5
82.5°	33.1	32.6	33.4	33.5	34.1	34.1	34.7	34.9	36.1	35.5	36.1
85°	16.6	16.3	16.6	16.3	16.6	17.0	17.0	16.6	16.6	17.4	16.3
87.5°	7.9	8.5	9.3	10.4	11.3	12.1	11.7	11.6	11.5	10.8	10.8
90°	13.7	18.1	23.8	29.6	35.3	41.1	40.5	40.0	39.5	39.0	38.9
92.5°	30.1	31.9	33.2	34.6	36.0	37.3	37.4	37.5	37.6	37.8	37.8
95°	71.4	73.0	73.5	74.0	74.5	75.0	75.0	75.0	75.0	75.0	74.8
97.5°	120.6	122.3	123.2	124.2	125.2	126.2	126.2	126.2	126.2	126.2	126.2
100°	157.3	158.8	159.6	160.3	161.1	161.9	161.9	161.9	161.9	161.9	161.8
102.5°	195.1	196.4	197.4	198.3	199.3	200.4	200.6	200.8	201.0	201.2	201.2
105°	255.3	256.0	256.5	257.0	257.5	258.0	258.6	259.1	259.6	260.1	260.4
107.5°	321.0	321.6	321.6	321.6	321.6	321.6	321.8	322.0	322.2	322.4	321.9
110°	364.1	364.9	364.9	364.9	364.9	364.9	364.9	364.9	364.9	364.9	364.5



TEST NUMBER: P331322-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	409.1	409.8	409.5	409.3	409.1	408.9	408.3	407.7	407.1	406.5	405.9
115°	475.4	475.9	475.4	474.9	474.4	473.9	473.6	473.4	473.1	472.8	472.3
117.5°	543.7	544.0	542.6	541.1	539.7	538.2	537.6	536.9	536.3	535.7	535.0
120°	587.8	587.8	585.7	583.7	581.6	579.5	579.5	579.5	579.5	579.5	579.1
122.5°	629.9	630.4	628.9	627.4	626.0	624.5	623.9	623.3	622.7	622.0	621.5
125°	692.1	692.9	692.1	691.4	690.5	689.7	688.9	688.2	687.4	686.6	686.1
127.5°	755.8	756.9	755.9	755.0	754.1	753.1	752.1	751.2	750.2	749.3	748.4
130°	796.0	797.4	796.9	796.4	795.9	795.4	794.8	794.3	793.8	793.2	792.4
132.5°	836.7	838.1	838.2	838.3	838.4	838.5	837.4	836.2	835.1	833.9	832.9
135°	894.7	896.5	897.0	897.5	898.1	898.6	898.3	898.1	897.8	897.5	897.0
137.5°	953.4	954.9	955.6	956.3	956.9	957.7	957.5	957.3	957.0	956.8	956.2
140°	990.1	991.9	993.2	994.5	995.8	997.0	997.0	997.0	997.0	997.0	996.5
142.5°	1027.5	1029.2	1030.1	1031.0	1031.9	1032.8	1033.0	1033.2	1033.4	1033.6	1033.2
145°	1079.4	1081.2	1082.7	1084.3	1085.8	1087.4	1087.6	1087.9	1088.2	1088.4	1088.0
147.5°	1129.0	1130.6	1131.7	1132.8	1133.8	1134.8	1135.4	1136.0	1136.5	1137.1	1136.9
150°	1159.3	1160.6	1161.7	1162.8	1163.8	1164.9	1165.6	1166.4	1167.2	1168.0	1168.0
152.5°	1188.4	1189.8	1191.1	1192.3	1193.7	1194.9	1195.9	1196.9	1197.8	1198.8	1198.8
155°	1229.0	1229.7	1230.5	1231.3	1232.1	1232.8	1234.2	1235.5	1236.8	1238.1	1238.3
157.5°	1265.3	1265.7	1266.2	1266.7	1267.1	1267.6	1269.4	1271.1	1272.9	1274.7	1275.0
160°	1287.8	1288.1	1288.4	1288.7	1288.9	1289.2	1290.7	1292.3	1293.8	1295.5	1295.7
162.5°	1306.8	1306.9	1307.2	1307.4	1307.7	1308.0	1309.7	1311.5	1313.2	1315.0	1315.2
165°	1332.7	1332.6	1332.6	1332.6	1332.6	1332.6	1334.4	1336.3	1338.1	1339.9	1340.1
167.5°	1353.6	1353.2	1353.1	1353.1	1353.0	1353.0	1354.8	1356.7	1358.5	1360.3	1360.5
170°	1365.8	1365.3	1365.0	1364.7	1364.5	1364.2	1366.0	1367.9	1369.7	1371.5	1371.7
172.5°	1374.2	1373.7	1373.5	1373.2	1372.9	1372.7	1374.5	1376.3	1378.2	1380.0	1380.1
175°	1384.6	1383.9	1383.4	1382.9	1382.4	1381.8	1383.7	1385.5	1387.4	1389.2	1389.3
177.5°	1389.5	1388.9	1388.5	1388.1	1387.7	1387.3	1388.5	1389.8	1391.0	1392.2	1392.2
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1



TEST NUMBER: P331322-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	941.2	940.6	940.6	937.9	940.6	940.6	941.2	944.2	945.1	945.7	944.5
5°	873.1	871.9	870.1	871.9	870.1	871.9	873.1	878.4	881.0	883.6	886.0
7.5°	805.8	801.2	800.5	796.1	800.5	801.2	805.8	808.2	813.4	819.4	824.9
10°	756.6	753.6	753.2	746.0	753.2	753.6	756.6	763.0	768.2	775.4	782.9
12.5°	719.1	711.9	713.4	709.2	713.4	711.9	719.1	719.2	725.4	729.8	741.6
15°	654.3	654.3	652.9	646.4	652.9	654.3	654.3	664.5	666.4	673.6	683.8
17.5°	607.8	607.0	603.4	605.2	603.4	607.0	607.8	615.3	616.5	626.1	634.5
20°	580.1	577.7	573.3	573.3	573.3	577.7	580.1	584.2	589.1	594.7	601.9
22.5°	553.8	553.6	548.9	550.4	548.9	553.6	553.8	557.6	562.3	568.6	574.5
25°	523.1	520.1	517.9	519.0	517.9	520.1	523.1	523.5	528.8	532.9	536.6
27.5°	494.0	492.3	492.2	489.1	492.2	492.3	494.0	494.9	498.0	500.4	503.9
30°	477.1	473.3	474.0	472.2	474.0	473.3	477.1	477.5	479.0	480.5	484.6
32.5°	457.8	456.5	455.7	454.0	455.7	456.5	457.8	458.5	461.5	463.0	466.3
35°	431.4	431.8	429.9	430.7	429.9	431.8	431.4	432.2	432.6	434.1	437.1
37.5°	408.5	409.7	408.8	409.0	408.8	409.7	408.5	408.8	409.2	409.4	410.3
40°	393.3	393.3	393.3	394.5	393.3	393.3	393.3	392.2	392.6	392.2	392.2
42.5°	378.9	378.3	377.7	377.6	377.7	378.3	378.9	376.3	377.5	376.3	375.7
45°	354.2	355.3	355.7	353.8	355.7	355.3	354.2	353.4	352.2	351.8	351.5
47.5°	331.7	331.8	331.7	333.4	331.7	331.8	331.7	330.7	329.0	328.3	326.5
50°	316.1	315.3	316.1	315.3	316.1	315.3	316.1	314.2	313.1	311.1	309.6
52.5°	299.4	299.6	299.1	299.0	299.1	299.6	299.4	297.0	296.4	295.8	293.4
55°	273.5	274.2	273.8	273.8	273.8	274.2	273.5	272.0	271.6	269.2	267.0
57.5°	246.5	247.2	247.7	246.0	247.7	247.2	246.5	246.3	246.0	243.7	241.3
60°	227.8	229.6	229.3	228.5	229.3	229.6	227.8	228.1	227.0	225.5	224.0
62.5°	210.6	211.3	211.2	211.1	211.2	211.3	210.6	208.8	208.3	206.8	205.3
65°	184.0	184.8	183.7	184.8	183.7	184.8	184.0	182.9	180.3	179.6	178.0
67.5°	155.4	155.7	156.5	157.0	156.5	155.7	155.4	155.9	154.2	152.8	152.5
70°	137.6	137.2	138.5	139.6	138.5	137.2	137.6	136.9	135.7	134.6	133.1
72.5°	119.0	119.8	119.4	120.3	119.4	119.8	119.0	119.1	118.0	116.5	115.0
75°	91.7	92.8	92.4	93.5	92.4	92.8	91.7	92.4	91.7	90.2	88.7
77.5°	66.2	66.3	66.2	66.9	66.2	66.3	66.2	66.9	66.0	66.6	64.8
80°	50.5	49.8	49.0	50.5	49.0	49.8	50.5	50.5	49.4	50.5	49.4
82.5°	35.1	35.6	34.8	34.8	34.8	35.6	35.1	36.1	35.5	36.1	34.9
85°	16.3	15.9	15.0	15.0	15.0	15.9	16.3	16.3	17.4	16.6	16.6
87.5°	10.8	10.6	10.6	10.4	10.6	10.6	10.8	10.8	10.8	11.5	11.6
90°	39.1	39.4	39.6	39.9	39.6	39.4	39.1	38.9	39.0	39.5	40.0
92.5°	37.9	37.9	38.0	38.0	38.0	37.9	37.9	37.8	37.8	37.6	37.5
95°	74.3	73.8	73.2	72.7	73.2	73.8	74.3	74.8	75.0	75.0	75.0
97.5°	126.1	126.1	126.0	126.0	126.0	126.1	126.1	126.2	126.2	126.2	126.2
100°	161.5	161.3	161.0	160.7	161.0	161.3	161.5	161.8	161.9	161.9	161.9
102.5°	200.9	200.7	200.4	200.2	200.4	200.7	200.9	201.2	201.2	201.0	200.8
105°	260.4	260.4	260.4	260.4	260.4	260.4	260.4	260.4	260.1	259.6	259.1
107.5°	320.8	319.6	318.4	317.2	318.4	319.6	320.8	321.9	322.4	322.2	322.0
110°	363.7	362.8	362.0	361.3	362.0	362.8	363.7	364.5	364.9	364.9	364.9



TEST NUMBER: P331322-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	405.3	404.7	404.1	403.5	404.1	404.7	405.3	405.9	406.5	407.1	407.7
115°	471.6	470.8	470.0	469.2	470.0	470.8	471.6	472.3	472.8	473.1	473.4
117.5°	534.2	533.4	532.6	531.9	532.6	533.4	534.2	535.0	535.7	536.3	536.9
120°	578.3	577.5	576.7	575.9	576.7	577.5	578.3	579.1	579.5	579.5	579.5
122.5°	620.9	620.3	619.8	619.1	619.8	620.3	620.9	621.5	622.0	622.7	623.3
125°	685.8	685.6	685.3	685.1	685.3	685.6	685.8	686.1	686.6	687.4	688.2
127.5°	747.6	746.8	746.0	745.1	746.0	746.8	747.6	748.4	749.3	750.2	751.2
130°	791.4	790.3	789.3	788.3	789.3	790.3	791.4	792.4	793.2	793.8	794.3
132.5°	832.1	831.2	830.4	829.6	830.4	831.2	832.1	832.9	833.9	835.1	836.2
135°	896.2	895.4	894.6	893.8	894.6	895.4	896.2	897.0	897.5	897.8	898.1
137.5°	955.1	954.1	953.1	952.0	953.1	954.1	955.1	956.2	956.8	957.0	957.3
140°	995.5	994.5	993.4	992.4	993.4	994.5	995.5	996.5	997.0	997.0	997.0
142.5°	1032.1	1031.1	1030.1	1029.0	1030.1	1031.1	1032.1	1033.2	1033.6	1033.4	1033.2
145°	1087.0	1086.0	1084.9	1083.9	1084.9	1086.0	1087.0	1088.0	1088.4	1088.2	1087.9
147.5°	1135.9	1134.9	1133.9	1133.0	1133.9	1134.9	1135.9	1136.9	1137.1	1136.5	1136.0
150°	1167.2	1166.4	1165.6	1164.9	1165.6	1166.4	1167.2	1168.0	1168.0	1167.2	1166.4
152.5°	1197.8	1196.9	1195.9	1194.9	1195.9	1196.9	1197.8	1198.8	1198.8	1197.8	1196.9
155°	1237.6	1236.8	1236.0	1235.2	1236.0	1236.8	1237.6	1238.3	1238.1	1236.8	1235.5
157.5°	1273.6	1272.4	1271.2	1269.9	1271.2	1272.4	1273.6	1275.0	1274.7	1272.9	1271.1
160°	1294.6	1293.6	1292.5	1291.5	1292.5	1293.6	1294.6	1295.7	1295.5	1293.8	1292.3
162.5°	1314.0	1312.8	1311.5	1310.3	1311.5	1312.8	1314.0	1315.2	1315.0	1313.2	1311.5
165°	1338.9	1337.6	1336.3	1334.9	1336.3	1337.6	1338.9	1340.1	1339.9	1338.1	1336.3
167.5°	1359.2	1357.8	1356.5	1355.1	1356.5	1357.8	1359.2	1360.5	1360.3	1358.5	1356.7
170°	1370.1	1368.6	1367.0	1365.4	1367.0	1368.6	1370.1	1371.7	1371.5	1369.7	1367.9
172.5°	1378.6	1377.0	1375.4	1373.8	1375.4	1377.0	1378.6	1380.1	1380.0	1378.2	1376.3
175°	1387.8	1386.1	1384.6	1383.0	1384.6	1386.1	1387.8	1389.3	1389.2	1387.4	1385.5
177.5°	1391.0	1389.8	1388.5	1387.3	1388.5	1389.8	1391.0	1392.2	1392.2	1391.0	1389.8
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1



TEST NUMBER: P331322-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	943.0	946.3	951.5	956.8	960.2	966.5	968.4	971.4	974.1	980.4	987.0
5°	888.6	893.8	906.3	913.0	922.5	933.4	940.6	948.2	956.4	970.8	984.0
7.5°	830.2	839.0	854.4	867.2	880.6	896.3	907.6	922.5	934.8	955.0	974.4
10°	791.2	803.7	817.7	832.7	851.6	868.2	884.0	902.9	918.0	942.1	964.7
12.5°	756.3	758.1	778.1	794.8	820.5	841.0	859.3	883.5	898.4	927.1	950.9
15°	695.1	706.4	724.5	737.7	768.2	794.3	819.9	845.2	862.1	897.6	928.9
17.5°	643.6	654.0	672.6	694.2	716.1	741.9	775.2	801.8	824.9	865.4	902.4
20°	611.0	623.8	642.7	664.9	684.2	712.5	741.0	771.6	796.5	842.1	885.6
22.5°	583.2	593.3	608.5	630.5	651.6	677.4	708.8	742.0	768.2	817.4	861.4
25°	544.2	552.5	562.3	580.5	604.2	632.5	657.0	693.6	731.6	777.7	830.8
27.5°	509.1	514.9	523.6	539.6	558.0	584.4	611.7	646.3	684.7	734.6	790.7
30°	487.7	491.4	500.1	513.3	531.4	552.1	579.7	612.9	652.1	702.7	758.4
32.5°	469.0	472.4	478.1	490.7	506.3	524.1	548.9	582.1	619.5	669.1	730.9
35°	440.9	443.5	448.4	458.6	467.3	484.6	505.3	535.5	570.6	618.1	682.3
37.5°	412.9	416.5	419.5	423.8	434.9	446.4	464.4	489.9	524.3	572.3	633.4
40°	394.5	397.5	402.0	403.9	412.9	423.1	437.9	461.2	495.9	539.7	599.3
42.5°	375.8	378.8	381.5	383.7	391.5	400.5	413.7	433.8	464.5	507.2	566.1
45°	350.3	350.7	353.4	357.5	361.3	367.7	377.2	394.5	418.3	458.3	511.8
47.5°	324.6	325.0	325.5	327.3	331.4	337.2	343.5	357.6	378.9	410.8	462.9
50°	307.4	306.6	307.4	308.9	311.5	316.4	323.6	333.8	351.1	380.9	428.8
52.5°	290.7	290.6	290.1	290.7	292.9	296.2	301.2	309.9	325.5	352.8	395.1
55°	265.5	263.6	264.0	262.5	265.9	266.6	270.4	277.6	291.1	310.0	349.6
57.5°	238.5	237.0	235.3	234.9	234.6	236.6	239.6	245.3	255.7	272.3	304.4
60°	221.4	219.5	217.2	216.5	216.5	217.6	219.1	223.3	233.1	247.8	274.2
62.5°	203.9	201.7	200.4	198.3	197.7	198.9	200.5	203.4	210.5	224.3	247.0
65°	176.9	174.2	172.4	172.0	171.3	170.1	170.9	173.9	179.6	190.5	208.5
67.5°	149.8	147.3	146.8	144.7	143.6	143.8	143.6	146.2	149.6	159.0	172.5
70°	132.0	130.1	129.4	127.4	126.7	125.9	125.2	127.4	130.9	138.8	150.5
72.5°	113.9	112.3	110.7	109.1	109.3	108.5	108.4	109.7	112.5	119.8	128.8
75°	87.9	88.3	86.3	84.5	84.1	83.3	83.3	84.5	85.6	91.3	98.5
77.5°	63.7	63.4	61.8	61.2	60.9	60.1	60.9	61.6	62.2	66.0	71.3
80°	48.7	48.7	46.8	46.8	46.4	45.2	46.4	45.6	47.2	50.9	54.7
82.5°	34.7	34.1	34.1	33.5	33.4	32.6	33.1	33.8	34.4	37.1	39.3
85°	17.0	17.0	16.6	16.3	16.6	16.3	16.6	17.0	17.4	18.5	20.4
87.5°	11.7	12.1	11.3	10.4	9.3	8.5	7.9	7.6	7.5	7.2	6.9
90°	40.5	41.1	35.3	29.6	23.8	18.1	13.7	10.6	7.5	4.3	1.2
92.5°	37.4	37.3	36.0	34.6	33.2	31.9	30.1	27.8	25.4	23.1	20.9
95°	75.0	75.0	74.5	74.0	73.5	73.0	71.4	68.8	66.2	63.6	61.0
97.5°	126.2	126.2	125.2	124.2	123.2	122.3	120.6	118.4	116.0	113.7	111.5
100°	161.9	161.9	161.1	160.3	159.6	158.8	157.3	155.2	153.2	151.1	149.0
102.5°	200.6	200.4	199.3	198.3	197.4	196.4	195.1	193.4	191.8	190.1	188.4
105°	258.6	258.0	257.5	257.0	256.5	256.0	255.3	254.6	253.8	253.0	252.2
107.5°	321.8	321.6	321.6	321.6	321.6	321.6	321.0	319.9	318.8	317.6	316.5
110°	364.9	364.9	364.9	364.9	364.9	364.9	364.1	362.4	360.9	359.3	357.8



TEST NUMBER: P331322-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	408.3	408.9	409.1	409.3	409.5	409.8	409.1	407.5	406.0	404.3	402.8
115°	473.6	473.9	474.4	474.9	475.4	475.9	475.4	473.9	472.3	470.8	469.2
117.5°	537.6	538.2	539.7	541.1	542.6	544.0	543.7	541.6	539.6	537.5	535.3
120°	579.5	579.5	581.6	583.7	585.7	587.8	587.8	585.7	583.7	581.6	579.5
122.5°	623.9	624.5	626.0	627.4	628.9	630.4	629.9	627.3	624.8	622.4	619.9
125°	688.9	689.7	690.5	691.4	692.1	692.9	692.1	689.7	687.4	685.1	682.7
127.5°	752.1	753.1	754.1	755.0	755.9	756.9	755.8	752.9	749.9	746.9	744.0
130°	794.8	795.4	795.9	796.4	796.9	797.4	796.0	792.5	789.2	785.8	782.4
132.5°	837.4	838.5	838.4	838.3	838.2	838.1	836.7	833.8	831.1	828.4	825.6
135°	898.3	898.6	898.1	897.5	897.0	896.5	894.7	891.9	889.1	886.2	883.3
137.5°	957.5	957.7	956.9	956.3	955.6	954.9	953.4	951.1	948.8	946.4	944.0
140°	997.0	997.0	995.8	994.5	993.2	991.9	990.1	987.7	985.3	983.0	980.7
142.5°	1033.0	1032.8	1031.9	1031.0	1030.1	1029.2	1027.5	1025.2	1022.9	1020.6	1018.2
145°	1087.6	1087.4	1085.8	1084.3	1082.7	1081.2	1079.4	1077.6	1075.8	1074.0	1072.2
147.5°	1135.4	1134.8	1133.8	1132.8	1131.7	1130.6	1129.0	1126.8	1124.6	1122.5	1120.2
150°	1165.6	1164.9	1163.8	1162.8	1161.7	1160.6	1159.3	1157.8	1156.2	1154.7	1153.1
152.5°	1195.9	1194.9	1193.7	1192.3	1191.1	1189.8	1188.4	1186.9	1185.3	1183.8	1182.1
155°	1234.2	1232.8	1232.1	1231.3	1230.5	1229.7	1229.0	1228.2	1227.4	1226.6	1225.9
157.5°	1269.4	1267.6	1267.1	1266.7	1266.2	1265.7	1265.3	1264.7	1264.1	1263.6	1263.1
160°	1290.7	1289.2	1288.9	1288.7	1288.4	1288.1	1287.8	1287.2	1286.7	1286.2	1285.7
162.5°	1309.7	1308.0	1307.7	1307.4	1307.2	1306.9	1306.8	1306.6	1306.5	1306.4	1306.3
165°	1334.4	1332.6	1332.6	1332.6	1332.6	1332.6	1332.7	1332.9	1333.2	1333.5	1333.7
167.5°	1354.8	1353.0	1353.0	1353.1	1353.1	1353.2	1353.6	1354.4	1355.1	1355.9	1356.8
170°	1366.0	1364.2	1364.5	1364.7	1365.0	1365.3	1365.8	1366.5	1367.4	1368.2	1369.0
172.5°	1374.5	1372.7	1372.9	1373.2	1373.5	1373.7	1374.2	1375.0	1375.8	1376.6	1377.4
175°	1383.7	1381.8	1382.4	1382.9	1383.4	1383.9	1384.6	1385.3	1386.1	1386.9	1387.8
177.5°	1388.5	1387.3	1387.7	1388.1	1388.5	1388.9	1389.5	1390.1	1390.7	1391.3	1391.9
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1



TEST NUMBER: P331322-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	986.4	988.0	992.8	997.6	1003.0	1004.5	1006.9	1004.8	1004.2	1010.0	1014.2
5°	989.3	996.0	1009.3	1021.3	1031.5	1038.6	1046.2	1049.2	1054.9	1062.8	1072.6
7.5°	986.0	999.3	1020.1	1037.6	1056.7	1070.6	1081.4	1090.6	1101.7	1116.7	1133.1
10°	982.5	1000.2	1025.4	1046.9	1070.4	1088.0	1102.8	1117.1	1133.7	1154.5	1175.9
12.5°	975.8	996.8	1028.4	1053.9	1083.9	1101.4	1121.2	1152.1	1169.9	1198.8	1229.0
15°	962.5	985.8	1030.0	1061.3	1095.2	1128.4	1165.0	1194.4	1223.9	1240.8	1283.4
17.5°	942.6	976.9	1025.8	1062.4	1105.5	1157.7	1198.8	1232.2	1266.2	1293.6	1315.0
20°	926.7	964.0	1019.8	1063.6	1114.8	1171.0	1218.2	1252.1	1281.5	1304.5	1317.8
22.5°	906.5	953.4	1007.7	1059.0	1124.5	1180.1	1229.6	1256.4	1280.9	1292.1	1297.2
25°	874.5	931.2	992.6	1055.2	1129.1	1188.0	1233.2	1249.5	1256.7	1245.7	1227.6
27.5°	840.3	903.3	975.2	1048.1	1126.3	1182.9	1215.3	1212.7	1200.6	1165.2	1136.9
30°	814.7	884.0	961.3	1040.9	1119.3	1174.4	1193.3	1174.4	1146.9	1107.3	1066.9
32.5°	787.8	859.6	946.5	1030.7	1106.7	1155.1	1159.2	1126.7	1084.1	1039.2	988.8
35°	747.1	824.9	918.7	1007.7	1079.7	1110.3	1092.2	1034.9	984.3	922.9	854.2
37.5°	701.1	787.0	881.1	974.1	1039.5	1047.4	1002.5	942.1	870.8	798.6	717.8
40°	666.8	757.7	854.6	948.5	1006.2	997.9	940.6	874.2	789.3	701.1	626.0
42.5°	636.0	726.9	825.7	917.8	964.0	941.2	874.2	792.7	701.6	618.4	549.8
45°	582.7	676.2	777.3	866.3	892.7	851.6	763.0	672.5	582.7	513.3	459.0
47.5°	531.0	623.4	723.5	801.7	811.1	755.8	658.9	565.8	488.7	432.1	393.8
50°	492.9	585.7	684.9	754.7	751.6	684.9	585.3	496.7	432.2	386.6	360.9
52.5°	458.8	546.4	641.8	705.2	689.2	616.4	521.4	442.7	389.7	354.0	330.7
55°	405.8	486.9	577.4	628.3	599.0	518.2	437.9	374.5	335.3	308.5	290.4
57.5°	353.1	429.2	506.6	538.1	505.5	431.0	364.1	318.1	288.6	268.7	257.0
60°	320.5	387.0	456.0	483.1	444.2	377.9	325.1	284.0	260.2	244.0	233.5
62.5°	288.0	347.4	412.5	427.3	391.7	335.7	288.9	254.7	235.2	220.8	210.9
65°	243.7	292.3	341.7	351.5	318.7	275.3	238.3	216.1	198.7	188.2	180.3
67.5°	199.9	238.8	273.9	281.8	253.1	223.0	196.2	176.9	165.1	156.3	149.7
70°	173.9	204.8	233.5	239.8	216.8	190.1	169.8	154.2	143.7	136.1	129.8
72.5°	146.4	172.2	196.0	200.4	181.6	161.1	144.4	132.2	122.9	118.1	111.9
75°	112.0	127.1	145.6	146.7	134.3	121.8	109.0	101.1	96.1	90.2	87.2
77.5°	79.1	90.9	101.5	103.5	96.1	87.7	80.5	74.2	70.1	67.3	64.5
80°	60.4	69.8	74.3	77.0	71.7	65.6	61.5	57.4	54.7	52.8	50.9
82.5°	43.1	49.0	53.2	55.2	52.3	48.8	44.5	42.2	40.2	38.6	38.0
85°	21.9	24.5	27.2	27.9	27.2	25.7	23.4	23.4	22.2	21.9	21.9
87.5°	8.4	10.2	10.9	12.4	12.7	13.8	14.9	15.9	16.7	16.3	15.9
90°	4.3	7.5	10.6	13.7	18.1	23.8	29.6	35.3	41.1	40.5	40.0
92.5°	23.1	25.4	27.8	30.1	31.9	33.2	34.6	36.0	37.3	37.4	37.5
95°	63.6	66.2	68.8	71.4	73.0	73.5	74.0	74.5	75.0	75.0	75.0
97.5°	113.7	116.0	118.4	120.6	122.3	123.2	124.2	125.2	126.2	126.2	126.2
100°	151.1	153.2	155.2	157.3	158.8	159.6	160.3	161.1	161.9	161.9	161.9
102.5°	190.1	191.8	193.4	195.1	196.4	197.4	198.3	199.3	200.4	200.6	200.8
105°	253.0	253.8	254.6	255.3	256.0	256.5	257.0	257.5	258.0	258.6	259.1
107.5°	317.6	318.8	319.9	321.0	321.6	321.6	321.6	321.6	321.6	321.8	322.0
110°	359.3	360.9	362.4	364.1	364.9	364.9	364.9	364.9	364.9	364.9	364.9



TEST NUMBER: P331322-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	404.3	406.0	407.5	409.1	409.8	409.5	409.3	409.1	408.9	408.3	407.7
115°	470.8	472.3	473.9	475.4	475.9	475.4	474.9	474.4	473.9	473.6	473.4
117.5°	537.5	539.6	541.6	543.7	544.0	542.6	541.1	539.7	538.2	537.6	536.9
120°	581.6	583.7	585.7	587.8	587.8	585.7	583.7	581.6	579.5	579.5	579.5
122.5°	622.4	624.8	627.3	629.9	630.4	628.9	627.4	626.0	624.5	623.9	623.3
125°	685.1	687.4	689.7	692.1	692.9	692.1	691.4	690.5	689.7	688.9	688.2
127.5°	746.9	749.9	752.9	755.8	756.9	755.9	755.0	754.1	753.1	752.1	751.2
130°	785.8	789.2	792.5	796.0	797.4	796.9	796.4	795.9	795.4	794.8	794.3
132.5°	828.4	831.1	833.8	836.7	838.1	838.2	838.3	838.4	838.5	837.4	836.2
135°	886.2	889.1	891.9	894.7	896.5	897.0	897.5	898.1	898.6	898.3	898.1
137.5°	946.4	948.8	951.1	953.4	954.9	955.6	956.3	956.9	957.7	957.5	957.3
140°	983.0	985.3	987.7	990.1	991.9	993.2	994.5	995.8	997.0	997.0	997.0
142.5°	1020.6	1022.9	1025.2	1027.5	1029.2	1030.1	1031.0	1031.9	1032.8	1033.0	1033.2
145°	1074.0	1075.8	1077.6	1079.4	1081.2	1082.7	1084.3	1085.8	1087.4	1087.6	1087.9
147.5°	1122.5	1124.6	1126.8	1129.0	1130.6	1131.7	1132.8	1133.8	1134.8	1135.4	1136.0
150°	1154.7	1156.2	1157.8	1159.3	1160.6	1161.7	1162.8	1163.8	1164.9	1165.6	1166.4
152.5°	1183.8	1185.3	1186.9	1188.4	1189.8	1191.1	1192.3	1193.7	1194.9	1195.9	1196.9
155°	1226.6	1227.4	1228.2	1229.0	1229.7	1230.5	1231.3	1232.1	1232.8	1234.2	1235.5
157.5°	1263.6	1264.1	1264.7	1265.3	1265.7	1266.2	1266.7	1267.1	1267.6	1269.4	1271.1
160°	1286.2	1286.7	1287.2	1287.8	1288.1	1288.4	1288.7	1288.9	1289.2	1290.7	1292.3
162.5°	1306.4	1306.5	1306.6	1306.8	1306.9	1307.2	1307.4	1307.7	1308.0	1309.7	1311.5
165°	1333.5	1333.2	1332.9	1332.7	1332.6	1332.6	1332.6	1332.6	1332.6	1334.4	1336.3
167.5°	1355.9	1355.1	1354.4	1353.6	1353.2	1353.1	1353.1	1353.0	1353.0	1354.8	1356.7
170°	1368.2	1367.4	1366.5	1365.8	1365.3	1365.0	1364.7	1364.5	1364.2	1366.0	1367.9
172.5°	1376.6	1375.8	1375.0	1374.2	1373.7	1373.5	1373.2	1372.9	1372.7	1374.5	1376.3
175°	1386.9	1386.1	1385.3	1384.6	1383.9	1383.4	1382.9	1382.4	1381.8	1383.7	1385.5
177.5°	1391.3	1390.7	1390.1	1389.5	1388.9	1388.5	1388.1	1387.7	1387.3	1388.5	1389.8
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1



TEST NUMBER: P331322-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1017.8	1022.1	1022.1	1022.7	1027.4	1026.9	1026.6
5°	1083.2	1089.5	1090.4	1097.1	1101.7	1100.1	1096.0
7.5°	1144.8	1156.7	1165.8	1170.8	1176.8	1180.4	1178.8
10°	1193.7	1211.0	1221.5	1228.7	1237.4	1243.9	1241.5
12.5°	1238.0	1258.7	1273.1	1285.5	1286.6	1294.8	1289.2
15°	1307.2	1329.1	1331.3	1340.4	1347.6	1346.8	1347.2
17.5°	1330.0	1337.1	1338.5	1338.7	1338.8	1336.2	1330.4
20°	1321.9	1319.3	1312.8	1308.0	1299.3	1298.1	1290.6
22.5°	1283.2	1274.9	1258.8	1248.2	1234.7	1231.1	1229.0
25°	1207.2	1188.7	1163.1	1138.6	1131.8	1118.6	1122.4
27.5°	1102.9	1074.1	1046.3	1026.4	1008.5	988.7	994.3
30°	1029.6	997.1	958.0	927.8	908.6	889.7	886.3
32.5°	942.1	894.5	850.8	824.3	794.8	782.8	769.8
35°	791.2	744.9	701.5	664.2	642.7	626.0	611.0
37.5°	655.5	602.2	567.1	536.9	521.4	511.9	514.2
40°	571.4	524.6	499.0	475.9	461.6	454.8	456.4
42.5°	503.2	468.2	447.1	431.3	421.2	417.4	416.5
45°	425.8	406.2	388.8	379.8	374.9	370.7	368.1
47.5°	373.0	357.0	347.2	341.8	337.5	333.4	333.3
50°	341.3	330.7	324.0	318.3	314.9	311.8	314.6
52.5°	317.2	307.5	300.7	295.7	294.4	291.6	291.6
55°	281.3	273.8	268.9	264.4	262.2	260.6	258.7
57.5°	248.7	241.6	237.1	234.2	229.9	228.4	227.8
60°	225.5	219.8	215.3	211.6	209.6	206.7	206.7
62.5°	204.1	198.4	194.2	191.4	188.2	187.0	187.3
65°	173.1	168.5	164.4	161.4	160.7	158.4	159.2
67.5°	144.6	141.6	137.2	135.5	134.1	132.9	132.0
70°	125.6	122.6	120.3	118.1	116.9	116.9	116.9
72.5°	109.6	105.9	104.6	101.8	102.4	101.2	100.0
75°	84.8	82.6	81.5	80.3	78.5	78.5	78.5
77.5°	62.4	61.8	60.4	59.2	58.8	58.4	58.6
80°	48.3	47.9	47.2	47.2	46.4	46.0	45.2
82.5°	37.1	36.2	35.6	35.3	35.2	35.1	35.0
85°	21.1	20.4	20.4	20.7	20.0	20.0	20.4
87.5°	16.1	16.0	15.7	15.7	16.1	15.8	15.9
90°	39.5	39.0	38.9	39.1	39.4	39.6	39.9
92.5°	37.6	37.8	37.8	37.9	37.9	38.0	38.0
95°	75.0	75.0	74.8	74.3	73.8	73.2	72.7
97.5°	126.2	126.2	126.2	126.1	126.1	126.0	126.0
100°	161.9	161.9	161.8	161.5	161.3	161.0	160.7
102.5°	201.0	201.2	201.2	200.9	200.7	200.4	200.2
105°	259.6	260.1	260.4	260.4	260.4	260.4	260.4
107.5°	322.2	322.4	321.9	320.8	319.6	318.4	317.2
110°	364.9	364.9	364.5	363.7	362.8	362.0	361.3



TEST NUMBER: P331322-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	407.1	406.5	405.9	405.3	404.7	404.1	403.5
115°	473.1	472.8	472.3	471.6	470.8	470.0	469.2
117.5°	536.3	535.7	535.0	534.2	533.4	532.6	531.9
120°	579.5	579.5	579.1	578.3	577.5	576.7	575.9
122.5°	622.7	622.0	621.5	620.9	620.3	619.8	619.1
125°	687.4	686.6	686.1	685.8	685.6	685.3	685.1
127.5°	750.2	749.3	748.4	747.6	746.8	746.0	745.1
130°	793.8	793.2	792.4	791.4	790.3	789.3	788.3
132.5°	835.1	833.9	832.9	832.1	831.2	830.4	829.6
135°	897.8	897.5	897.0	896.2	895.4	894.6	893.8
137.5°	957.0	956.8	956.2	955.1	954.1	953.1	952.0
140°	997.0	997.0	996.5	995.5	994.5	993.4	992.4
142.5°	1033.4	1033.6	1033.2	1032.1	1031.1	1030.1	1029.0
145°	1088.2	1088.4	1088.0	1087.0	1086.0	1084.9	1083.9
147.5°	1136.5	1137.1	1136.9	1135.9	1134.9	1133.9	1133.0
150°	1167.2	1168.0	1168.0	1167.2	1166.4	1165.6	1164.9
152.5°	1197.8	1198.8	1198.8	1197.8	1196.9	1195.9	1194.9
155°	1236.8	1238.1	1238.3	1237.6	1236.8	1236.0	1235.2
157.5°	1272.9	1274.7	1275.0	1273.6	1272.4	1271.2	1269.9
160°	1293.8	1295.5	1295.7	1294.6	1293.6	1292.5	1291.5
162.5°	1313.2	1315.0	1315.2	1314.0	1312.8	1311.5	1310.3
165°	1338.1	1339.9	1340.1	1338.9	1337.6	1336.3	1334.9
167.5°	1358.5	1360.3	1360.5	1359.2	1357.8	1356.5	1355.1
170°	1369.7	1371.5	1371.7	1370.1	1368.6	1367.0	1365.4
172.5°	1378.2	1380.0	1380.1	1378.6	1377.0	1375.4	1373.8
175°	1387.4	1389.2	1389.3	1387.8	1386.1	1384.6	1383.0
177.5°	1391.0	1392.2	1392.2	1391.0	1389.8	1388.5	1387.3
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1

(END OF REPORT)