

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331285-840

Luminaire Tested: **SA2XXDIP-C485D330U840-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331285-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D330U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3488.5 lumens
Efficiency: N/A
Efficacy: 126.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331285-840
CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331285-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62				
1	101	97	93	90	95	91	88	85	80	77	75	70	68	66	60	59	58	53				
2	93	85	79	74	87	80	75	71	71	67	63	62	59	56	54	52	50	46				
3	85	76	68	63	79	71	65	60	63	58	54	55	52	48	48	45	43	39				
4	78	67	60	54	73	64	57	51	56	51	47	50	45	42	44	40	38	34				
5	72	60	52	46	67	57	50	45	51	45	41	45	40	37	40	36	33	30				
6	66	55	47	41	62	52	44	39	46	40	36	41	36	33	36	32	30	27				
7	62	49	42	36	58	47	40	35	42	36	32	37	33	29	33	29	27	24				
8	57	45	37	32	54	43	36	31	39	33	29	34	30	26	31	27	24	22				
9	54	41	34	29	50	39	33	28	35	30	26	32	27	24	28	25	22	20				
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	26	23	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15844	15844	15844	15844
5°	17763	15948	14131	15948
10°	20354	15816	12231	15816
15°	22519	15527	10805	15527
20°	22175	15216	9850	15216
25°	19996	14801	9246	14801
30°	16524	14139	8804	14139
35°	12043	13448	8489	13448
40°	9619	12631	8315	12631
45°	8405	11686	8079	11686
50°	7902	10771	7920	10771
55°	7282	9841	7707	9841
60°	6675	8854	7379	8854
65°	6082	7966	7060	7966
70°	5519	7105	6590	7105
75°	4897	6145	5833	6145
80°	4203	5086	4695	5086
85°	3779	3779	2779	3779



TEST NUMBER: P331285-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	2.7
10°-20°	271.7	7.8
20°-30°	394.3	11.3
30°-40°	416.1	11.9
40°-50°	368.4	10.6
50°-60°	294.0	8.4
60°-70°	199.8	5.7
70°-80°	102.5	2.9
80°-90°	25.8	0.7
90°-100°	15.1	0.4
100°-110°	55.2	1.6
110°-120°	147.6	4.2
120°-130°	243.6	7.0
130°-140°	259.0	7.4
140°-150°	240.8	6.9
150°-160°	193.6	5.5
160°-170°	124.7	3.6
170°-180°	42.9	1.2
0°-30°	759.5	21.8
0°-40°	1175.6	33.7
0°-60°	1838.0	52.7
0°-90°	2166.1	62.1
90°-120°	217.8	6.2
90°-150°	961.2	27.6
90°-180°	1322.0	37.9
0°-180°	3488.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	981	981	981	981	981	
5°	1096	984	872	984	1096	109
15°	1347	929	646	929	1347	372
25°	1122	831	519	831	1122	507
35°	611	682	431	682	611	397
45°	368	512	354	512	368	289
55°	259	350	274	350	259	232
65°	159	208	185	208	159	158
75°	78	98	94	98	78	84
85°	20	20	15	20	20	23
90°	9	0	9	0	9	5
95°	14	21	14	21	14	13
105°	25	99	25	99	25	26
115°	27	188	27	188	27	67
125°	279	266	279	266	279	242
135°	339	328	339	328	339	261
145°	387	381	387	381	387	242
155°	420	420	420	420	420	194
165°	441	442	441	442	441	125
175°	450	452	450	452	450	43
180°	451	451	451	451	451	



TEST NUMBER: P331285-840
 CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1026.6	1026.9	1027.4	1022.7	1022.1	1022.1	1017.8	1014.2	1010.0	1004.2	1004.8
5°	1096.0	1100.1	1101.7	1097.1	1090.4	1089.5	1083.2	1072.6	1062.8	1054.9	1049.2
7.5°	1178.8	1180.4	1176.8	1170.8	1165.8	1156.7	1144.8	1133.1	1116.7	1101.7	1090.6
10°	1241.5	1243.9	1237.4	1228.7	1221.5	1211.0	1193.7	1175.9	1154.5	1133.7	1117.1
12.5°	1289.2	1294.8	1286.6	1285.5	1273.1	1258.7	1238.0	1229.0	1198.8	1169.9	1152.1
15°	1347.2	1346.8	1347.6	1340.4	1331.3	1329.1	1307.2	1283.4	1240.8	1223.9	1194.4
17.5°	1330.4	1336.2	1338.8	1338.7	1338.5	1337.1	1330.0	1315.0	1293.6	1266.2	1232.2
20°	1290.6	1298.1	1299.3	1308.0	1312.8	1319.3	1321.9	1317.8	1304.5	1281.5	1252.1
22.5°	1229.0	1231.1	1234.7	1248.2	1258.8	1274.9	1283.2	1297.2	1292.1	1280.9	1256.4
25°	1122.4	1118.6	1131.8	1138.6	1163.1	1188.7	1207.2	1227.6	1245.7	1256.7	1249.5
27.5°	994.3	988.7	1008.5	1026.4	1046.3	1074.1	1102.9	1136.9	1165.2	1200.6	1212.7
30°	886.3	889.7	908.6	927.8	958.0	997.1	1029.6	1066.9	1107.3	1146.9	1174.4
32.5°	769.8	782.8	794.8	824.3	850.8	894.5	942.1	988.8	1039.2	1084.1	1126.7
35°	611.0	626.0	642.7	664.2	701.5	744.9	791.2	854.2	922.9	984.3	1034.9
37.5°	514.2	511.9	521.4	536.9	567.1	602.2	655.5	717.8	798.6	870.8	942.1
40°	456.4	454.8	461.6	475.9	499.0	524.6	571.4	626.0	701.1	789.3	874.2
42.5°	416.5	417.4	421.2	431.3	447.1	468.2	503.2	549.8	618.4	701.6	792.7
45°	368.1	370.7	374.9	379.8	388.8	406.2	425.8	459.0	513.3	582.7	672.5
47.5°	333.3	333.4	337.5	341.8	347.2	357.0	373.0	393.8	432.1	488.7	565.8
50°	314.6	311.8	314.9	318.3	324.0	330.7	341.3	360.9	386.6	432.2	496.7
52.5°	291.6	291.6	294.4	295.7	300.7	307.5	317.2	330.7	354.0	389.7	442.7
55°	258.7	260.6	262.2	264.4	268.9	273.8	281.3	290.4	308.5	335.3	374.5
57.5°	227.8	228.4	229.9	234.2	237.1	241.6	248.7	257.0	268.7	288.6	318.1
60°	206.7	206.7	209.6	211.6	215.3	219.8	225.5	233.5	244.0	260.2	284.0
62.5°	187.3	187.0	188.2	191.4	194.2	198.4	204.1	210.9	220.8	235.2	254.7
65°	159.2	158.4	160.7	161.4	164.4	168.5	173.1	180.3	188.2	198.7	216.1
67.5°	132.0	132.9	134.1	135.5	137.2	141.6	144.6	149.7	156.3	165.1	176.9
70°	116.9	116.9	116.9	118.1	120.3	122.6	125.6	129.8	136.1	143.7	154.2
72.5°	100.0	101.2	102.4	101.8	104.6	105.9	109.6	111.9	118.1	122.9	132.2
75°	78.5	78.5	78.5	80.3	81.5	82.6	84.8	87.2	90.2	96.1	101.1
77.5°	58.6	58.4	58.8	59.2	60.4	61.8	62.4	64.5	67.3	70.1	74.2
80°	45.2	46.0	46.4	47.2	47.2	47.9	48.3	50.9	52.8	54.7	57.4
82.5°	35.0	35.1	35.2	35.3	35.6	36.2	37.1	38.0	38.6	40.2	42.2
85°	20.4	20.0	20.0	20.7	20.4	20.4	21.1	21.9	21.9	22.2	23.4
87.5°	9.6	9.6	9.9	9.5	9.5	9.7	9.7	9.3	9.5	9.8	9.9
90°	8.8	8.7	8.5	8.4	8.3	8.0	7.6	7.3	6.9	6.6	6.0
92.5°	8.8	8.7	8.7	8.6	8.5	8.3	8.2	8.0	7.8	7.6	7.3
95°	14.0	14.1	14.1	14.2	14.3	14.1	13.8	13.4	13.1	12.7	12.2
97.5°	18.8	18.7	18.6	18.5	18.4	18.2	17.9	17.7	17.4	17.1	15.9
100°	21.9	21.7	21.6	21.4	21.3	20.9	20.4	19.8	19.2	18.6	17.4
102.5°	23.4	23.2	23.0	22.8	22.6	22.1	21.4	20.6	19.9	19.1	29.5
105°	24.8	24.5	24.2	23.9	23.6	23.1	22.3	21.5	20.7	19.9	39.7
107.5°	25.5	25.2	24.9	24.6	24.3	24.6	25.4	26.3	27.1	27.9	51.6
110°	25.8	25.5	25.2	24.9	24.6	28.1	35.3	42.6	49.9	57.2	78.1



TEST NUMBER: P331285-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	26.1	25.9	25.5	25.3	25.1	38.3	64.7	91.2	117.6	144.1	149.3
115°	26.8	32.0	37.3	42.4	47.7	67.1	100.7	134.3	167.8	201.5	199.7
117.5°	109.4	126.5	143.7	160.9	178.0	190.7	198.7	206.9	215.0	223.2	221.9
120°	199.1	208.9	218.7	228.5	238.3	242.8	242.0	241.1	240.2	239.3	238.0
122.5°	248.5	250.4	252.4	254.3	256.1	256.8	256.3	255.8	255.3	254.8	253.4
125°	279.1	278.9	278.7	278.5	278.3	277.9	277.4	276.9	276.4	275.9	274.5
127.5°	298.5	298.4	298.4	298.4	298.3	297.9	297.2	296.5	295.7	295.0	294.0
130°	310.5	310.6	310.6	310.7	310.8	310.4	309.6	308.8	308.0	307.3	306.5
132.5°	322.2	322.3	322.4	322.4	322.6	322.2	321.5	320.9	320.2	319.5	318.7
135°	339.2	339.4	339.5	339.7	339.8	339.5	338.8	338.1	337.4	336.7	336.0
137.5°	354.8	355.0	355.3	355.5	355.7	355.5	354.8	354.1	353.4	352.6	351.9
140°	364.4	364.8	365.2	365.5	365.9	365.7	365.1	364.4	363.8	363.0	362.3
142.5°	373.8	374.2	374.6	374.9	375.3	375.2	374.6	374.0	373.3	372.7	371.8
145°	386.9	387.3	387.7	388.0	388.4	388.3	387.8	387.3	386.8	386.3	385.1
147.5°	398.5	398.8	399.1	399.4	399.7	399.7	399.3	398.9	398.5	398.2	397.0
150°	405.6	405.9	406.3	406.7	407.0	407.0	406.5	406.1	405.7	405.3	404.0
152.5°	411.5	412.0	412.5	412.9	413.4	413.4	413.0	412.6	412.1	411.7	410.6
155°	419.9	420.5	421.1	421.6	422.2	422.3	421.8	421.4	421.0	420.5	419.7
157.5°	427.6	428.1	428.7	429.2	429.8	429.8	429.4	428.9	428.4	427.9	427.3
160°	432.0	432.5	433.0	433.5	434.0	434.0	433.6	433.2	432.7	432.3	431.9
162.5°	435.7	436.3	436.9	437.5	438.2	438.2	437.7	437.2	436.8	436.3	435.9
165°	441.1	441.6	442.1	442.6	443.1	443.1	442.6	442.1	441.6	441.1	440.9
167.5°	444.5	445.2	445.9	446.6	447.2	447.3	446.8	446.3	445.8	445.2	445.0
170°	446.7	447.4	448.0	448.7	449.3	449.4	448.9	448.4	447.9	447.4	447.2
172.5°	448.3	448.9	449.6	450.2	450.9	450.9	450.4	449.9	449.4	448.9	448.8
175°	449.6	450.3	451.1	451.8	452.5	452.6	452.1	451.6	451.1	450.6	450.5
177.5°	450.5	451.0	451.5	452.0	452.5	452.6	452.2	451.8	451.4	451.0	450.9
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331285-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1006.9	1004.5	1003.0	997.6	992.8	988.0	986.4	987.0	980.4	974.1	971.4
5°	1046.2	1038.6	1031.5	1021.3	1009.3	996.0	989.3	984.0	970.8	956.4	948.2
7.5°	1081.4	1070.6	1056.7	1037.6	1020.1	999.3	986.0	974.4	955.0	934.8	922.5
10°	1102.8	1088.0	1070.4	1046.9	1025.4	1000.2	982.5	964.7	942.1	918.0	902.9
12.5°	1121.2	1101.4	1083.9	1053.9	1028.4	996.8	975.8	950.9	927.1	898.4	883.5
15°	1165.0	1128.4	1095.2	1061.3	1030.0	985.8	962.5	928.9	897.6	862.1	845.2
17.5°	1198.8	1157.7	1105.5	1062.4	1025.8	976.9	942.6	902.4	865.4	824.9	801.8
20°	1218.2	1171.0	1114.8	1063.6	1019.8	964.0	926.7	885.6	842.1	796.5	771.6
22.5°	1229.6	1180.1	1124.5	1059.0	1007.7	953.4	906.5	861.4	817.4	768.2	742.0
25°	1233.2	1188.0	1129.1	1055.2	992.6	931.2	874.5	830.8	777.7	731.6	693.6
27.5°	1215.3	1182.9	1126.3	1048.1	975.2	903.3	840.3	790.7	734.6	684.7	646.3
30°	1193.3	1174.4	1119.3	1040.9	961.3	884.0	814.7	758.4	702.7	652.1	612.9
32.5°	1159.2	1155.1	1106.7	1030.7	946.5	859.6	787.8	730.9	669.1	619.5	582.1
35°	1092.2	1110.3	1079.7	1007.7	918.7	824.9	747.1	682.3	618.1	570.6	535.5
37.5°	1002.5	1047.4	1039.5	974.1	881.1	787.0	701.1	633.4	572.3	524.3	489.9
40°	940.6	997.9	1006.2	948.5	854.6	757.7	666.8	599.3	539.7	495.9	461.2
42.5°	874.2	941.2	964.0	917.8	825.7	726.9	636.0	566.1	507.2	464.5	433.8
45°	763.0	851.6	892.7	866.3	777.3	676.2	582.7	511.8	458.3	418.3	394.5
47.5°	658.9	755.8	811.1	801.7	723.5	623.4	531.0	462.9	410.8	378.9	357.6
50°	585.3	684.9	751.6	754.7	684.9	585.7	492.9	428.8	380.9	351.1	333.8
52.5°	521.4	616.4	689.2	705.2	641.8	546.4	458.8	395.1	352.8	325.5	309.9
55°	437.9	518.2	599.0	628.3	577.4	486.9	405.8	349.6	310.0	291.1	277.6
57.5°	364.1	431.0	505.5	538.1	506.6	429.2	353.1	304.4	272.3	255.7	245.3
60°	325.1	377.9	444.2	483.1	456.0	387.0	320.5	274.2	247.8	233.1	223.3
62.5°	288.9	335.7	391.7	427.3	412.5	347.4	288.0	247.0	224.3	210.5	203.4
65°	238.3	275.3	318.7	351.5	341.7	292.3	243.7	208.5	190.5	179.6	173.9
67.5°	196.2	223.0	253.1	281.8	273.9	238.8	199.9	172.5	159.0	149.6	146.2
70°	169.8	190.1	216.8	239.8	233.5	204.8	173.9	150.5	138.8	130.9	127.4
72.5°	144.4	161.1	181.6	200.4	196.0	172.2	146.4	128.8	119.8	112.5	109.7
75°	109.0	121.8	134.3	146.7	145.6	127.1	112.0	98.5	91.3	85.6	84.5
77.5°	80.5	87.7	96.1	103.5	101.5	90.9	79.1	71.3	66.0	62.2	61.6
80°	61.5	65.6	71.7	77.0	74.3	69.8	60.4	54.7	50.9	47.2	45.6
82.5°	44.5	48.8	52.3	55.2	53.2	49.0	43.1	39.3	37.1	34.4	33.8
85°	23.4	25.7	27.2	27.9	27.2	24.5	21.9	20.4	18.5	17.4	17.0
87.5°	10.1	10.0	9.9	10.4	9.3	9.1	7.8	6.7	6.6	6.5	6.0
90°	5.4	4.7	4.2	3.5	2.7	1.9	1.1	0.3	1.1	1.9	2.7
92.5°	7.0	6.7	6.5	6.3	6.4	6.5	6.6	6.6	6.6	6.5	6.4
95°	11.7	11.2	10.7	11.6	14.0	16.5	18.8	21.2	18.8	16.5	14.0
97.5°	14.6	13.5	12.3	15.1	21.9	28.6	35.3	42.1	35.3	28.6	21.9
100°	16.2	14.9	13.6	18.1	28.0	37.9	47.9	57.8	47.9	37.9	28.0
102.5°	39.8	50.1	60.4	66.7	68.8	70.8	72.9	75.0	72.9	70.8	68.8
105°	59.6	79.4	99.2	108.0	105.8	103.6	101.4	99.3	101.4	103.6	105.8
107.5°	75.4	99.2	122.9	133.9	132.2	130.4	128.7	126.8	128.7	130.4	132.2
110°	99.1	120.1	141.0	150.8	149.3	147.7	146.1	144.6	146.1	147.7	149.3



TEST NUMBER: P331285-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	154.5	159.7	164.8	166.7	165.4	164.1	162.7	161.4	162.7	164.1	165.4
115°	197.8	196.0	194.2	192.7	191.5	190.3	188.9	187.7	188.9	190.3	191.5
117.5°	220.7	219.4	218.1	216.8	215.5	214.1	212.7	211.4	212.7	214.1	215.5
120°	236.7	235.4	234.1	232.9	231.9	230.8	229.6	228.5	229.6	230.8	231.9
122.5°	251.9	250.4	249.0	247.8	246.6	245.5	244.4	243.2	244.4	245.5	246.6
125°	273.2	271.8	270.4	269.2	268.3	267.3	266.4	265.5	266.4	267.3	268.3
127.5°	293.0	291.9	290.8	289.8	288.8	287.7	286.7	285.6	286.7	287.7	288.8
130°	305.7	304.9	304.1	303.1	301.9	300.7	299.6	298.4	299.6	300.7	301.9
132.5°	317.9	317.1	316.3	315.5	314.5	313.5	312.5	311.5	312.5	313.5	314.5
135°	335.4	334.7	334.1	333.2	331.9	330.8	329.6	328.5	329.6	330.8	331.9
137.5°	351.1	350.4	349.7	348.9	348.1	347.3	346.5	345.7	346.5	347.3	348.1
140°	361.5	360.7	359.9	359.2	358.6	358.0	357.5	356.9	357.5	358.0	358.6
142.5°	370.9	370.0	369.1	368.4	367.9	367.3	366.8	366.3	366.8	367.3	367.9
145°	383.8	382.5	381.3	380.7	380.8	380.9	381.0	381.0	381.0	380.9	380.8
147.5°	395.8	394.5	393.2	392.8	393.0	393.3	393.6	393.9	393.6	393.3	393.0
150°	402.9	401.7	400.6	400.2	400.7	401.2	401.7	402.2	401.7	401.2	400.7
152.5°	409.5	408.4	407.3	407.1	407.6	408.2	408.8	409.3	408.8	408.2	407.6
155°	418.8	418.0	417.1	417.0	417.6	418.3	418.9	419.6	418.9	418.3	417.6
157.5°	426.7	426.1	425.5	425.4	426.0	426.5	427.1	427.6	427.1	426.5	426.0
160°	431.4	431.0	430.6	430.6	431.0	431.4	431.9	432.3	431.9	431.4	431.0
162.5°	435.5	435.0	434.7	434.7	435.2	435.7	436.1	436.5	436.1	435.7	435.2
165°	440.7	440.5	440.3	440.4	440.8	441.2	441.7	442.1	441.7	441.2	440.8
167.5°	444.8	444.6	444.4	444.5	444.9	445.5	445.9	446.3	445.9	445.5	444.9
170°	447.1	446.9	446.8	446.9	447.4	447.8	448.2	448.7	448.2	447.8	447.4
172.5°	448.6	448.5	448.3	448.5	448.9	449.3	449.8	450.2	449.8	449.3	448.9
175°	450.3	450.2	450.0	450.2	450.7	451.2	451.7	452.2	451.7	451.2	450.7
177.5°	450.9	450.8	450.8	450.9	451.3	451.7	452.1	452.5	452.1	451.7	451.3
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331285-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	968.4	966.5	960.2	956.8	951.5	946.3	943.0	944.5	945.7	945.1	944.2
5°	940.6	933.4	922.5	913.0	906.3	893.8	888.6	886.0	883.6	881.0	878.4
7.5°	907.6	896.3	880.6	867.2	854.4	839.0	830.2	824.9	819.4	813.4	808.2
10°	884.0	868.2	851.6	832.7	817.7	803.7	791.2	782.9	775.4	768.2	763.0
12.5°	859.3	841.0	820.5	794.8	778.1	758.1	756.3	741.6	729.8	725.4	719.2
15°	819.9	794.3	768.2	737.7	724.5	706.4	695.1	683.8	673.6	666.4	664.5
17.5°	775.2	741.9	716.1	694.2	672.6	654.0	643.6	634.5	626.1	616.5	615.3
20°	741.0	712.5	684.2	664.9	642.7	623.8	611.0	601.9	594.7	589.1	584.2
22.5°	708.8	677.4	651.6	630.5	608.5	593.3	583.2	574.5	568.6	562.3	557.6
25°	657.0	632.5	604.2	580.5	562.3	552.5	544.2	536.6	532.9	528.8	523.5
27.5°	611.7	584.4	558.0	539.6	523.6	514.9	509.1	503.9	500.4	498.0	494.9
30°	579.7	552.1	531.4	513.3	500.1	491.4	487.7	484.6	480.5	479.0	477.5
32.5°	548.9	524.1	506.3	490.7	478.1	472.4	469.0	466.3	463.0	461.5	458.5
35°	505.3	484.6	467.3	458.6	448.4	443.5	440.9	437.1	434.1	432.6	432.2
37.5°	464.4	446.4	434.9	423.8	419.5	416.5	412.9	410.3	409.4	409.2	408.8
40°	437.9	423.1	412.9	403.9	402.0	397.5	394.5	392.2	392.2	392.6	392.2
42.5°	413.7	400.5	391.5	383.7	381.5	378.8	375.8	375.7	376.3	377.5	376.3
45°	377.2	367.7	361.3	357.5	353.4	350.7	350.3	351.5	351.8	352.2	353.4
47.5°	343.5	337.2	331.4	327.3	325.5	325.0	324.6	326.5	328.3	329.0	330.7
50°	323.6	316.4	311.5	308.9	307.4	306.6	307.4	309.6	311.1	313.1	314.2
52.5°	301.2	296.2	292.9	290.7	290.1	290.6	290.7	293.4	295.8	296.4	297.0
55°	270.4	266.6	265.9	262.5	264.0	263.6	265.5	267.0	269.2	271.6	272.0
57.5°	239.6	236.6	234.6	234.9	235.3	237.0	238.5	241.3	243.7	246.0	246.3
60°	219.1	217.6	216.5	216.5	217.2	219.5	221.4	224.0	225.5	227.0	228.1
62.5°	200.5	198.9	197.7	198.3	200.4	201.7	203.9	205.3	206.8	208.3	208.8
65°	170.9	170.1	171.3	172.0	172.4	174.2	176.9	178.0	179.6	180.3	182.9
67.5°	143.6	143.8	143.6	144.7	146.8	147.3	149.8	152.5	152.8	154.2	155.9
70°	125.2	125.9	126.7	127.4	129.4	130.1	132.0	133.1	134.6	135.7	136.9
72.5°	108.4	108.5	109.3	109.1	110.7	112.3	113.9	115.0	116.5	118.0	119.1
75°	83.3	83.3	84.1	84.5	86.3	88.3	87.9	88.7	90.2	91.7	92.4
77.5°	60.9	60.1	60.9	61.2	61.8	63.4	63.7	64.8	66.6	66.0	66.9
80°	46.4	45.2	46.4	46.8	46.8	48.7	48.7	49.4	50.5	49.4	50.5
82.5°	33.1	32.6	33.4	33.5	34.1	34.1	34.7	34.9	36.1	35.5	36.1
85°	16.6	16.3	16.6	16.3	16.6	17.0	17.0	16.6	16.6	17.4	16.3
87.5°	5.9	5.7	5.5	5.6	5.5	5.3	5.0	5.0	5.2	4.6	4.6
90°	3.5	4.2	4.7	5.4	6.0	6.6	6.9	7.3	7.6	8.0	8.3
92.5°	6.3	6.5	6.7	7.0	7.3	7.6	7.8	8.0	8.2	8.3	8.5
95°	11.6	10.7	11.2	11.7	12.2	12.7	13.1	13.4	13.8	14.1	14.3
97.5°	15.1	12.3	13.5	14.6	15.9	17.1	17.4	17.7	17.9	18.2	18.4
100°	18.1	13.6	14.9	16.2	17.4	18.6	19.2	19.8	20.4	20.9	21.3
102.5°	66.7	60.4	50.1	39.8	29.5	19.1	19.9	20.6	21.4	22.1	22.6
105°	108.0	99.2	79.4	59.6	39.7	19.9	20.7	21.5	22.3	23.1	23.6
107.5°	133.9	122.9	99.2	75.4	51.6	27.9	27.1	26.3	25.4	24.6	24.3
110°	150.8	141.0	120.1	99.1	78.1	57.2	49.9	42.6	35.3	28.1	24.6



TEST NUMBER: P331285-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	166.7	164.8	159.7	154.5	149.3	144.1	117.6	91.2	64.7	38.3	25.1
115°	192.7	194.2	196.0	197.8	199.7	201.5	167.8	134.3	100.7	67.1	47.7
117.5°	216.8	218.1	219.4	220.7	221.9	223.2	215.0	206.9	198.7	190.7	178.0
120°	232.9	234.1	235.4	236.7	238.0	239.3	240.2	241.1	242.0	242.8	238.3
122.5°	247.8	249.0	250.4	251.9	253.4	254.8	255.3	255.8	256.3	256.8	256.1
125°	269.2	270.4	271.8	273.2	274.5	275.9	276.4	276.9	277.4	277.9	278.3
127.5°	289.8	290.8	291.9	293.0	294.0	295.0	295.7	296.5	297.2	297.9	298.3
130°	303.1	304.1	304.9	305.7	306.5	307.3	308.0	308.8	309.6	310.4	310.8
132.5°	315.5	316.3	317.1	317.9	318.7	319.5	320.2	320.9	321.5	322.2	322.6
135°	333.2	334.1	334.7	335.4	336.0	336.7	337.4	338.1	338.8	339.5	339.8
137.5°	348.9	349.7	350.4	351.1	351.9	352.6	353.4	354.1	354.8	355.5	355.7
140°	359.2	359.9	360.7	361.5	362.3	363.0	363.8	364.4	365.1	365.7	365.9
142.5°	368.4	369.1	370.0	370.9	371.8	372.7	373.3	374.0	374.6	375.2	375.3
145°	380.7	381.3	382.5	383.8	385.1	386.3	386.8	387.3	387.8	388.3	388.4
147.5°	392.8	393.2	394.5	395.8	397.0	398.2	398.5	398.9	399.3	399.7	399.7
150°	400.2	400.6	401.7	402.9	404.0	405.3	405.7	406.1	406.5	407.0	407.0
152.5°	407.1	407.3	408.4	409.5	410.6	411.7	412.1	412.6	413.0	413.4	413.4
155°	417.0	417.1	418.0	418.8	419.7	420.5	421.0	421.4	421.8	422.3	422.2
157.5°	425.4	425.5	426.1	426.7	427.3	427.9	428.4	428.9	429.4	429.8	429.8
160°	430.6	430.6	431.0	431.4	431.9	432.3	432.7	433.2	433.6	434.0	434.0
162.5°	434.7	434.7	435.0	435.5	435.9	436.3	436.8	437.2	437.7	438.2	438.2
165°	440.4	440.3	440.5	440.7	440.9	441.1	441.6	442.1	442.6	443.1	443.1
167.5°	444.5	444.4	444.6	444.8	445.0	445.2	445.8	446.3	446.8	447.3	447.2
170°	446.9	446.8	446.9	447.1	447.2	447.4	447.9	448.4	448.9	449.4	449.3
172.5°	448.5	448.3	448.5	448.6	448.8	448.9	449.4	449.9	450.4	450.9	450.9
175°	450.2	450.0	450.2	450.3	450.5	450.6	451.1	451.6	452.1	452.6	452.5
177.5°	450.9	450.8	450.8	450.9	450.9	451.0	451.4	451.8	452.2	452.6	452.5
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331285-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	941.2	940.6	940.6	937.9	940.6	940.6	941.2	944.2	945.1	945.7	944.5
5°	873.1	871.9	870.1	871.9	870.1	871.9	873.1	878.4	881.0	883.6	886.0
7.5°	805.8	801.2	800.5	796.1	800.5	801.2	805.8	808.2	813.4	819.4	824.9
10°	756.6	753.6	753.2	746.0	753.2	753.6	756.6	763.0	768.2	775.4	782.9
12.5°	719.1	711.9	713.4	709.2	713.4	711.9	719.1	719.2	725.4	729.8	741.6
15°	654.3	654.3	652.9	646.4	652.9	654.3	654.3	664.5	666.4	673.6	683.8
17.5°	607.8	607.0	603.4	605.2	603.4	607.0	607.8	615.3	616.5	626.1	634.5
20°	580.1	577.7	573.3	573.3	573.3	577.7	580.1	584.2	589.1	594.7	601.9
22.5°	553.8	553.6	548.9	550.4	548.9	553.6	553.8	557.6	562.3	568.6	574.5
25°	523.1	520.1	517.9	519.0	517.9	520.1	523.1	523.5	528.8	532.9	536.6
27.5°	494.0	492.3	492.2	489.1	492.2	492.3	494.0	494.9	498.0	500.4	503.9
30°	477.1	473.3	474.0	472.2	474.0	473.3	477.1	477.5	479.0	480.5	484.6
32.5°	457.8	456.5	455.7	454.0	455.7	456.5	457.8	458.5	461.5	463.0	466.3
35°	431.4	431.8	429.9	430.7	429.9	431.8	431.4	432.2	432.6	434.1	437.1
37.5°	408.5	409.7	408.8	409.0	408.8	409.7	408.5	408.8	409.2	409.4	410.3
40°	393.3	393.3	393.3	394.5	393.3	393.3	393.3	392.2	392.6	392.2	392.2
42.5°	378.9	378.3	377.7	377.6	377.7	378.3	378.9	376.3	377.5	376.3	375.7
45°	354.2	355.3	355.7	353.8	355.7	355.3	354.2	353.4	352.2	351.8	351.5
47.5°	331.7	331.8	331.7	333.4	331.7	331.8	331.7	330.7	329.0	328.3	326.5
50°	316.1	315.3	316.1	315.3	316.1	315.3	316.1	314.2	313.1	311.1	309.6
52.5°	299.4	299.6	299.1	299.0	299.1	299.6	299.4	297.0	296.4	295.8	293.4
55°	273.5	274.2	273.8	273.8	273.8	274.2	273.5	272.0	271.6	269.2	267.0
57.5°	246.5	247.2	247.7	246.0	247.7	247.2	246.5	246.3	246.0	243.7	241.3
60°	227.8	229.6	229.3	228.5	229.3	229.6	227.8	228.1	227.0	225.5	224.0
62.5°	210.6	211.3	211.2	211.1	211.2	211.3	210.6	208.8	208.3	206.8	205.3
65°	184.0	184.8	183.7	184.8	183.7	184.8	184.0	182.9	180.3	179.6	178.0
67.5°	155.4	155.7	156.5	157.0	156.5	155.7	155.4	155.9	154.2	152.8	152.5
70°	137.6	137.2	138.5	139.6	138.5	137.2	137.6	136.9	135.7	134.6	133.1
72.5°	119.0	119.8	119.4	120.3	119.4	119.8	119.0	119.1	118.0	116.5	115.0
75°	91.7	92.8	92.4	93.5	92.4	92.8	91.7	92.4	91.7	90.2	88.7
77.5°	66.2	66.3	66.2	66.9	66.2	66.3	66.2	66.9	66.0	66.6	64.8
80°	50.5	49.8	49.0	50.5	49.0	49.8	50.5	50.5	49.4	50.5	49.4
82.5°	35.1	35.6	34.8	34.8	34.8	35.6	35.1	36.1	35.5	36.1	34.9
85°	16.3	15.9	15.0	15.0	15.0	15.9	16.3	16.3	17.4	16.6	16.6
87.5°	4.6	4.4	4.4	4.1	4.4	4.4	4.6	4.6	4.6	5.2	5.0
90°	8.4	8.5	8.7	8.8	8.7	8.5	8.4	8.3	8.0	7.6	7.3
92.5°	8.6	8.7	8.7	8.8	8.7	8.7	8.6	8.5	8.3	8.2	8.0
95°	14.2	14.1	14.1	14.0	14.1	14.1	14.2	14.3	14.1	13.8	13.4
97.5°	18.5	18.6	18.7	18.8	18.7	18.6	18.5	18.4	18.2	17.9	17.7
100°	21.4	21.6	21.7	21.9	21.7	21.6	21.4	21.3	20.9	20.4	19.8
102.5°	22.8	23.0	23.2	23.4	23.2	23.0	22.8	22.6	22.1	21.4	20.6
105°	23.9	24.2	24.5	24.8	24.5	24.2	23.9	23.6	23.1	22.3	21.5
107.5°	24.6	24.9	25.2	25.5	25.2	24.9	24.6	24.3	24.6	25.4	26.3
110°	24.9	25.2	25.5	25.8	25.5	25.2	24.9	24.6	28.1	35.3	42.6



TEST NUMBER: P331285-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	25.3	25.5	25.9	26.1	25.9	25.5	25.3	25.1	38.3	64.7	91.2
115°	42.4	37.3	32.0	26.8	32.0	37.3	42.4	47.7	67.1	100.7	134.3
117.5°	160.9	143.7	126.5	109.4	126.5	143.7	160.9	178.0	190.7	198.7	206.9
120°	228.5	218.7	208.9	199.1	208.9	218.7	228.5	238.3	242.8	242.0	241.1
122.5°	254.3	252.4	250.4	248.5	250.4	252.4	254.3	256.1	256.8	256.3	255.8
125°	278.5	278.7	278.9	279.1	278.9	278.7	278.5	278.3	277.9	277.4	276.9
127.5°	298.4	298.4	298.4	298.5	298.4	298.4	298.4	298.3	297.9	297.2	296.5
130°	310.7	310.6	310.6	310.5	310.6	310.6	310.7	310.8	310.4	309.6	308.8
132.5°	322.4	322.4	322.3	322.2	322.3	322.4	322.4	322.6	322.2	321.5	320.9
135°	339.7	339.5	339.4	339.2	339.4	339.5	339.7	339.8	339.5	338.8	338.1
137.5°	355.5	355.3	355.0	354.8	355.0	355.3	355.5	355.7	355.5	354.8	354.1
140°	365.5	365.2	364.8	364.4	364.8	365.2	365.5	365.9	365.7	365.1	364.4
142.5°	374.9	374.6	374.2	373.8	374.2	374.6	374.9	375.3	375.2	374.6	374.0
145°	388.0	387.7	387.3	386.9	387.3	387.7	388.0	388.4	388.3	387.8	387.3
147.5°	399.4	399.1	398.8	398.5	398.8	399.1	399.4	399.7	399.7	399.3	398.9
150°	406.7	406.3	405.9	405.6	405.9	406.3	406.7	407.0	407.0	406.5	406.1
152.5°	412.9	412.5	412.0	411.5	412.0	412.5	412.9	413.4	413.4	413.0	412.6
155°	421.6	421.1	420.5	419.9	420.5	421.1	421.6	422.2	422.3	421.8	421.4
157.5°	429.2	428.7	428.1	427.6	428.1	428.7	429.2	429.8	429.8	429.4	428.9
160°	433.5	433.0	432.5	432.0	432.5	433.0	433.5	434.0	434.0	433.6	433.2
162.5°	437.5	436.9	436.3	435.7	436.3	436.9	437.5	438.2	438.2	437.7	437.2
165°	442.6	442.1	441.6	441.1	441.6	442.1	442.6	443.1	443.1	442.6	442.1
167.5°	446.6	445.9	445.2	444.5	445.2	445.9	446.6	447.2	447.3	446.8	446.3
170°	448.7	448.0	447.4	446.7	447.4	448.0	448.7	449.3	449.4	448.9	448.4
172.5°	450.2	449.6	448.9	448.3	448.9	449.6	450.2	450.9	450.9	450.4	449.9
175°	451.8	451.1	450.3	449.6	450.3	451.1	451.8	452.5	452.6	452.1	451.6
177.5°	452.0	451.5	451.0	450.5	451.0	451.5	452.0	452.5	452.6	452.2	451.8
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331285-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	943.0	946.3	951.5	956.8	960.2	966.5	968.4	971.4	974.1	980.4	987.0
5°	888.6	893.8	906.3	913.0	922.5	933.4	940.6	948.2	956.4	970.8	984.0
7.5°	830.2	839.0	854.4	867.2	880.6	896.3	907.6	922.5	934.8	955.0	974.4
10°	791.2	803.7	817.7	832.7	851.6	868.2	884.0	902.9	918.0	942.1	964.7
12.5°	756.3	758.1	778.1	794.8	820.5	841.0	859.3	883.5	898.4	927.1	950.9
15°	695.1	706.4	724.5	737.7	768.2	794.3	819.9	845.2	862.1	897.6	928.9
17.5°	643.6	654.0	672.6	694.2	716.1	741.9	775.2	801.8	824.9	865.4	902.4
20°	611.0	623.8	642.7	664.9	684.2	712.5	741.0	771.6	796.5	842.1	885.6
22.5°	583.2	593.3	608.5	630.5	651.6	677.4	708.8	742.0	768.2	817.4	861.4
25°	544.2	552.5	562.3	580.5	604.2	632.5	657.0	693.6	731.6	777.7	830.8
27.5°	509.1	514.9	523.6	539.6	558.0	584.4	611.7	646.3	684.7	734.6	790.7
30°	487.7	491.4	500.1	513.3	531.4	552.1	579.7	612.9	652.1	702.7	758.4
32.5°	469.0	472.4	478.1	490.7	506.3	524.1	548.9	582.1	619.5	669.1	730.9
35°	440.9	443.5	448.4	458.6	467.3	484.6	505.3	535.5	570.6	618.1	682.3
37.5°	412.9	416.5	419.5	423.8	434.9	446.4	464.4	489.9	524.3	572.3	633.4
40°	394.5	397.5	402.0	403.9	412.9	423.1	437.9	461.2	495.9	539.7	599.3
42.5°	375.8	378.8	381.5	383.7	391.5	400.5	413.7	433.8	464.5	507.2	566.1
45°	350.3	350.7	353.4	357.5	361.3	367.7	377.2	394.5	418.3	458.3	511.8
47.5°	324.6	325.0	325.5	327.3	331.4	337.2	343.5	357.6	378.9	410.8	462.9
50°	307.4	306.6	307.4	308.9	311.5	316.4	323.6	333.8	351.1	380.9	428.8
52.5°	290.7	290.6	290.1	290.7	292.9	296.2	301.2	309.9	325.5	352.8	395.1
55°	265.5	263.6	264.0	262.5	265.9	266.6	270.4	277.6	291.1	310.0	349.6
57.5°	238.5	237.0	235.3	234.9	234.6	236.6	239.6	245.3	255.7	272.3	304.4
60°	221.4	219.5	217.2	216.5	216.5	217.6	219.1	223.3	233.1	247.8	274.2
62.5°	203.9	201.7	200.4	198.3	197.7	198.9	200.5	203.4	210.5	224.3	247.0
65°	176.9	174.2	172.4	172.0	171.3	170.1	170.9	173.9	179.6	190.5	208.5
67.5°	149.8	147.3	146.8	144.7	143.6	143.8	143.6	146.2	149.6	159.0	172.5
70°	132.0	130.1	129.4	127.4	126.7	125.9	125.2	127.4	130.9	138.8	150.5
72.5°	113.9	112.3	110.7	109.1	109.3	108.5	108.4	109.7	112.5	119.8	128.8
75°	87.9	88.3	86.3	84.5	84.1	83.3	83.3	84.5	85.6	91.3	98.5
77.5°	63.7	63.4	61.8	61.2	60.9	60.1	60.9	61.6	62.2	66.0	71.3
80°	48.7	48.7	46.8	46.8	46.4	45.2	46.4	45.6	47.2	50.9	54.7
82.5°	34.7	34.1	34.1	33.5	33.4	32.6	33.1	33.8	34.4	37.1	39.3
85°	17.0	17.0	16.6	16.3	16.6	16.3	16.6	17.0	17.4	18.5	20.4
87.5°	5.0	5.3	5.5	5.6	5.5	5.7	5.9	6.0	6.5	6.6	6.7
90°	6.9	6.6	6.0	5.4	4.7	4.2	3.5	2.7	1.9	1.1	0.3
92.5°	7.8	7.6	7.3	7.0	6.7	6.5	6.3	6.4	6.5	6.6	6.6
95°	13.1	12.7	12.2	11.7	11.2	10.7	11.6	14.0	16.5	18.8	21.2
97.5°	17.4	17.1	15.9	14.6	13.5	12.3	15.1	21.9	28.6	35.3	42.1
100°	19.2	18.6	17.4	16.2	14.9	13.6	18.1	28.0	37.9	47.9	57.8
102.5°	19.9	19.1	29.5	39.8	50.1	60.4	66.7	68.8	70.8	72.9	75.0
105°	20.7	19.9	39.7	59.6	79.4	99.2	108.0	105.8	103.6	101.4	99.3
107.5°	27.1	27.9	51.6	75.4	99.2	122.9	133.9	132.2	130.4	128.7	126.8
110°	49.9	57.2	78.1	99.1	120.1	141.0	150.8	149.3	147.7	146.1	144.6



TEST NUMBER: P331285-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	117.6	144.1	149.3	154.5	159.7	164.8	166.7	165.4	164.1	162.7	161.4
115°	167.8	201.5	199.7	197.8	196.0	194.2	192.7	191.5	190.3	188.9	187.7
117.5°	215.0	223.2	221.9	220.7	219.4	218.1	216.8	215.5	214.1	212.7	211.4
120°	240.2	239.3	238.0	236.7	235.4	234.1	232.9	231.9	230.8	229.6	228.5
122.5°	255.3	254.8	253.4	251.9	250.4	249.0	247.8	246.6	245.5	244.4	243.2
125°	276.4	275.9	274.5	273.2	271.8	270.4	269.2	268.3	267.3	266.4	265.5
127.5°	295.7	295.0	294.0	293.0	291.9	290.8	289.8	288.8	287.7	286.7	285.6
130°	308.0	307.3	306.5	305.7	304.9	304.1	303.1	301.9	300.7	299.6	298.4
132.5°	320.2	319.5	318.7	317.9	317.1	316.3	315.5	314.5	313.5	312.5	311.5
135°	337.4	336.7	336.0	335.4	334.7	334.1	333.2	331.9	330.8	329.6	328.5
137.5°	353.4	352.6	351.9	351.1	350.4	349.7	348.9	348.1	347.3	346.5	345.7
140°	363.8	363.0	362.3	361.5	360.7	359.9	359.2	358.6	358.0	357.5	356.9
142.5°	373.3	372.7	371.8	370.9	370.0	369.1	368.4	367.9	367.3	366.8	366.3
145°	386.8	386.3	385.1	383.8	382.5	381.3	380.7	380.8	380.9	381.0	381.0
147.5°	398.5	398.2	397.0	395.8	394.5	393.2	392.8	393.0	393.3	393.6	393.9
150°	405.7	405.3	404.0	402.9	401.7	400.6	400.2	400.7	401.2	401.7	402.2
152.5°	412.1	411.7	410.6	409.5	408.4	407.3	407.1	407.6	408.2	408.8	409.3
155°	421.0	420.5	419.7	418.8	418.0	417.1	417.0	417.6	418.3	418.9	419.6
157.5°	428.4	427.9	427.3	426.7	426.1	425.5	425.4	426.0	426.5	427.1	427.6
160°	432.7	432.3	431.9	431.4	431.0	430.6	430.6	431.0	431.4	431.9	432.3
162.5°	436.8	436.3	435.9	435.5	435.0	434.7	434.7	435.2	435.7	436.1	436.5
165°	441.6	441.1	440.9	440.7	440.5	440.3	440.4	440.8	441.2	441.7	442.1
167.5°	445.8	445.2	445.0	444.8	444.6	444.4	444.5	444.9	445.5	445.9	446.3
170°	447.9	447.4	447.2	447.1	446.9	446.8	446.9	447.4	447.8	448.2	448.7
172.5°	449.4	448.9	448.8	448.6	448.5	448.3	448.5	448.9	449.3	449.8	450.2
175°	451.1	450.6	450.5	450.3	450.2	450.0	450.2	450.7	451.2	451.7	452.2
177.5°	451.4	451.0	450.9	450.9	450.8	450.8	450.9	451.3	451.7	452.1	452.5
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331285-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	986.4	988.0	992.8	997.6	1003.0	1004.5	1006.9	1004.8	1004.2	1010.0	1014.2
5°	989.3	996.0	1009.3	1021.3	1031.5	1038.6	1046.2	1049.2	1054.9	1062.8	1072.6
7.5°	986.0	999.3	1020.1	1037.6	1056.7	1070.6	1081.4	1090.6	1101.7	1116.7	1133.1
10°	982.5	1000.2	1025.4	1046.9	1070.4	1088.0	1102.8	1117.1	1133.7	1154.5	1175.9
12.5°	975.8	996.8	1028.4	1053.9	1083.9	1101.4	1121.2	1152.1	1169.9	1198.8	1229.0
15°	962.5	985.8	1030.0	1061.3	1095.2	1128.4	1165.0	1194.4	1223.9	1240.8	1283.4
17.5°	942.6	976.9	1025.8	1062.4	1105.5	1157.7	1198.8	1232.2	1266.2	1293.6	1315.0
20°	926.7	964.0	1019.8	1063.6	1114.8	1171.0	1218.2	1252.1	1281.5	1304.5	1317.8
22.5°	906.5	953.4	1007.7	1059.0	1124.5	1180.1	1229.6	1256.4	1280.9	1292.1	1297.2
25°	874.5	931.2	992.6	1055.2	1129.1	1188.0	1233.2	1249.5	1256.7	1245.7	1227.6
27.5°	840.3	903.3	975.2	1048.1	1126.3	1182.9	1215.3	1212.7	1200.6	1165.2	1136.9
30°	814.7	884.0	961.3	1040.9	1119.3	1174.4	1193.3	1174.4	1146.9	1107.3	1066.9
32.5°	787.8	859.6	946.5	1030.7	1106.7	1155.1	1159.2	1126.7	1084.1	1039.2	988.8
35°	747.1	824.9	918.7	1007.7	1079.7	1110.3	1092.2	1034.9	984.3	922.9	854.2
37.5°	701.1	787.0	881.1	974.1	1039.5	1047.4	1002.5	942.1	870.8	798.6	717.8
40°	666.8	757.7	854.6	948.5	1006.2	997.9	940.6	874.2	789.3	701.1	626.0
42.5°	636.0	726.9	825.7	917.8	964.0	941.2	874.2	792.7	701.6	618.4	549.8
45°	582.7	676.2	777.3	866.3	892.7	851.6	763.0	672.5	582.7	513.3	459.0
47.5°	531.0	623.4	723.5	801.7	811.1	755.8	658.9	565.8	488.7	432.1	393.8
50°	492.9	585.7	684.9	754.7	751.6	684.9	585.3	496.7	432.2	386.6	360.9
52.5°	458.8	546.4	641.8	705.2	689.2	616.4	521.4	442.7	389.7	354.0	330.7
55°	405.8	486.9	577.4	628.3	599.0	518.2	437.9	374.5	335.3	308.5	290.4
57.5°	353.1	429.2	506.6	538.1	505.5	431.0	364.1	318.1	288.6	268.7	257.0
60°	320.5	387.0	456.0	483.1	444.2	377.9	325.1	284.0	260.2	244.0	233.5
62.5°	288.0	347.4	412.5	427.3	391.7	335.7	288.9	254.7	235.2	220.8	210.9
65°	243.7	292.3	341.7	351.5	318.7	275.3	238.3	216.1	198.7	188.2	180.3
67.5°	199.9	238.8	273.9	281.8	253.1	223.0	196.2	176.9	165.1	156.3	149.7
70°	173.9	204.8	233.5	239.8	216.8	190.1	169.8	154.2	143.7	136.1	129.8
72.5°	146.4	172.2	196.0	200.4	181.6	161.1	144.4	132.2	122.9	118.1	111.9
75°	112.0	127.1	145.6	146.7	134.3	121.8	109.0	101.1	96.1	90.2	87.2
77.5°	79.1	90.9	101.5	103.5	96.1	87.7	80.5	74.2	70.1	67.3	64.5
80°	60.4	69.8	74.3	77.0	71.7	65.6	61.5	57.4	54.7	52.8	50.9
82.5°	43.1	49.0	53.2	55.2	52.3	48.8	44.5	42.2	40.2	38.6	38.0
85°	21.9	24.5	27.2	27.9	27.2	25.7	23.4	23.4	22.2	21.9	21.9
87.5°	7.8	9.1	9.3	10.4	9.9	10.0	10.1	9.9	9.8	9.5	9.3
90°	1.1	1.9	2.7	3.5	4.2	4.7	5.4	6.0	6.6	6.9	7.3
92.5°	6.6	6.5	6.4	6.3	6.5	6.7	7.0	7.3	7.6	7.8	8.0
95°	18.8	16.5	14.0	11.6	10.7	11.2	11.7	12.2	12.7	13.1	13.4
97.5°	35.3	28.6	21.9	15.1	12.3	13.5	14.6	15.9	17.1	17.4	17.7
100°	47.9	37.9	28.0	18.1	13.6	14.9	16.2	17.4	18.6	19.2	19.8
102.5°	72.9	70.8	68.8	66.7	60.4	50.1	39.8	29.5	19.1	19.9	20.6
105°	101.4	103.6	105.8	108.0	99.2	79.4	59.6	39.7	19.9	20.7	21.5
107.5°	128.7	130.4	132.2	133.9	122.9	99.2	75.4	51.6	27.9	27.1	26.3
110°	146.1	147.7	149.3	150.8	141.0	120.1	99.1	78.1	57.2	49.9	42.6



TEST NUMBER: P331285-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	162.7	164.1	165.4	166.7	164.8	159.7	154.5	149.3	144.1	117.6	91.2
115°	188.9	190.3	191.5	192.7	194.2	196.0	197.8	199.7	201.5	167.8	134.3
117.5°	212.7	214.1	215.5	216.8	218.1	219.4	220.7	221.9	223.2	215.0	206.9
120°	229.6	230.8	231.9	232.9	234.1	235.4	236.7	238.0	239.3	240.2	241.1
122.5°	244.4	245.5	246.6	247.8	249.0	250.4	251.9	253.4	254.8	255.3	255.8
125°	266.4	267.3	268.3	269.2	270.4	271.8	273.2	274.5	275.9	276.4	276.9
127.5°	286.7	287.7	288.8	289.8	290.8	291.9	293.0	294.0	295.0	295.7	296.5
130°	299.6	300.7	301.9	303.1	304.1	304.9	305.7	306.5	307.3	308.0	308.8
132.5°	312.5	313.5	314.5	315.5	316.3	317.1	317.9	318.7	319.5	320.2	320.9
135°	329.6	330.8	331.9	333.2	334.1	334.7	335.4	336.0	336.7	337.4	338.1
137.5°	346.5	347.3	348.1	348.9	349.7	350.4	351.1	351.9	352.6	353.4	354.1
140°	357.5	358.0	358.6	359.2	359.9	360.7	361.5	362.3	363.0	363.8	364.4
142.5°	366.8	367.3	367.9	368.4	369.1	370.0	370.9	371.8	372.7	373.3	374.0
145°	381.0	380.9	380.8	380.7	381.3	382.5	383.8	385.1	386.3	386.8	387.3
147.5°	393.6	393.3	393.0	392.8	393.2	394.5	395.8	397.0	398.2	398.5	398.9
150°	401.7	401.2	400.7	400.2	400.6	401.7	402.9	404.0	405.3	405.7	406.1
152.5°	408.8	408.2	407.6	407.1	407.3	408.4	409.5	410.6	411.7	412.1	412.6
155°	418.9	418.3	417.6	417.0	417.1	418.0	418.8	419.7	420.5	421.0	421.4
157.5°	427.1	426.5	426.0	425.4	425.5	426.1	426.7	427.3	427.9	428.4	428.9
160°	431.9	431.4	431.0	430.6	430.6	431.0	431.4	431.9	432.3	432.7	433.2
162.5°	436.1	435.7	435.2	434.7	434.7	435.0	435.5	435.9	436.3	436.8	437.2
165°	441.7	441.2	440.8	440.4	440.3	440.5	440.7	440.9	441.1	441.6	442.1
167.5°	445.9	445.5	444.9	444.5	444.4	444.6	444.8	445.0	445.2	445.8	446.3
170°	448.2	447.8	447.4	446.9	446.8	446.9	447.1	447.2	447.4	447.9	448.4
172.5°	449.8	449.3	448.9	448.5	448.3	448.5	448.6	448.8	448.9	449.4	449.9
175°	451.7	451.2	450.7	450.2	450.0	450.2	450.3	450.5	450.6	451.1	451.6
177.5°	452.1	451.7	451.3	450.9	450.8	450.8	450.9	450.9	451.0	451.4	451.8
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331285-840
 CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1017.8	1022.1	1022.1	1022.7	1027.4	1026.9	1026.6
5°	1083.2	1089.5	1090.4	1097.1	1101.7	1100.1	1096.0
7.5°	1144.8	1156.7	1165.8	1170.8	1176.8	1180.4	1178.8
10°	1193.7	1211.0	1221.5	1228.7	1237.4	1243.9	1241.5
12.5°	1238.0	1258.7	1273.1	1285.5	1286.6	1294.8	1289.2
15°	1307.2	1329.1	1331.3	1340.4	1347.6	1346.8	1347.2
17.5°	1330.0	1337.1	1338.5	1338.7	1338.8	1336.2	1330.4
20°	1321.9	1319.3	1312.8	1308.0	1299.3	1298.1	1290.6
22.5°	1283.2	1274.9	1258.8	1248.2	1234.7	1231.1	1229.0
25°	1207.2	1188.7	1163.1	1138.6	1131.8	1118.6	1122.4
27.5°	1102.9	1074.1	1046.3	1026.4	1008.5	988.7	994.3
30°	1029.6	997.1	958.0	927.8	908.6	889.7	886.3
32.5°	942.1	894.5	850.8	824.3	794.8	782.8	769.8
35°	791.2	744.9	701.5	664.2	642.7	626.0	611.0
37.5°	655.5	602.2	567.1	536.9	521.4	511.9	514.2
40°	571.4	524.6	499.0	475.9	461.6	454.8	456.4
42.5°	503.2	468.2	447.1	431.3	421.2	417.4	416.5
45°	425.8	406.2	388.8	379.8	374.9	370.7	368.1
47.5°	373.0	357.0	347.2	341.8	337.5	333.4	333.3
50°	341.3	330.7	324.0	318.3	314.9	311.8	314.6
52.5°	317.2	307.5	300.7	295.7	294.4	291.6	291.6
55°	281.3	273.8	268.9	264.4	262.2	260.6	258.7
57.5°	248.7	241.6	237.1	234.2	229.9	228.4	227.8
60°	225.5	219.8	215.3	211.6	209.6	206.7	206.7
62.5°	204.1	198.4	194.2	191.4	188.2	187.0	187.3
65°	173.1	168.5	164.4	161.4	160.7	158.4	159.2
67.5°	144.6	141.6	137.2	135.5	134.1	132.9	132.0
70°	125.6	122.6	120.3	118.1	116.9	116.9	116.9
72.5°	109.6	105.9	104.6	101.8	102.4	101.2	100.0
75°	84.8	82.6	81.5	80.3	78.5	78.5	78.5
77.5°	62.4	61.8	60.4	59.2	58.8	58.4	58.6
80°	48.3	47.9	47.2	47.2	46.4	46.0	45.2
82.5°	37.1	36.2	35.6	35.3	35.2	35.1	35.0
85°	21.1	20.4	20.4	20.7	20.0	20.0	20.4
87.5°	9.7	9.7	9.5	9.5	9.9	9.6	9.6
90°	7.6	8.0	8.3	8.4	8.5	8.7	8.8
92.5°	8.2	8.3	8.5	8.6	8.7	8.7	8.8
95°	13.8	14.1	14.3	14.2	14.1	14.1	14.0
97.5°	17.9	18.2	18.4	18.5	18.6	18.7	18.8
100°	20.4	20.9	21.3	21.4	21.6	21.7	21.9
102.5°	21.4	22.1	22.6	22.8	23.0	23.2	23.4
105°	22.3	23.1	23.6	23.9	24.2	24.5	24.8
107.5°	25.4	24.6	24.3	24.6	24.9	25.2	25.5
110°	35.3	28.1	24.6	24.9	25.2	25.5	25.8



TEST NUMBER: P331285-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	64.7	38.3	25.1	25.3	25.5	25.9	26.1
115°	100.7	67.1	47.7	42.4	37.3	32.0	26.8
117.5°	198.7	190.7	178.0	160.9	143.7	126.5	109.4
120°	242.0	242.8	238.3	228.5	218.7	208.9	199.1
122.5°	256.3	256.8	256.1	254.3	252.4	250.4	248.5
125°	277.4	277.9	278.3	278.5	278.7	278.9	279.1
127.5°	297.2	297.9	298.3	298.4	298.4	298.4	298.5
130°	309.6	310.4	310.8	310.7	310.6	310.6	310.5
132.5°	321.5	322.2	322.6	322.4	322.4	322.3	322.2
135°	338.8	339.5	339.8	339.7	339.5	339.4	339.2
137.5°	354.8	355.5	355.7	355.5	355.3	355.0	354.8
140°	365.1	365.7	365.9	365.5	365.2	364.8	364.4
142.5°	374.6	375.2	375.3	374.9	374.6	374.2	373.8
145°	387.8	388.3	388.4	388.0	387.7	387.3	386.9
147.5°	399.3	399.7	399.7	399.4	399.1	398.8	398.5
150°	406.5	407.0	407.0	406.7	406.3	405.9	405.6
152.5°	413.0	413.4	413.4	412.9	412.5	412.0	411.5
155°	421.8	422.3	422.2	421.6	421.1	420.5	419.9
157.5°	429.4	429.8	429.8	429.2	428.7	428.1	427.6
160°	433.6	434.0	434.0	433.5	433.0	432.5	432.0
162.5°	437.7	438.2	438.2	437.5	436.9	436.3	435.7
165°	442.6	443.1	443.1	442.6	442.1	441.6	441.1
167.5°	446.8	447.3	447.2	446.6	445.9	445.2	444.5
170°	448.9	449.4	449.3	448.7	448.0	447.4	446.7
172.5°	450.4	450.9	450.9	450.2	449.6	448.9	448.3
175°	452.1	452.6	452.5	451.8	451.1	450.3	449.6
177.5°	452.2	452.6	452.5	452.0	451.5	451.0	450.5
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2

(END OF REPORT)