

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332984-927

Luminaire Tested: **SA4XXRDIP-C1020D1205U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332984-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C1020D1205U927-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6715.1 lumens  
Efficiency: N/A  
Efficacy: 102.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332984-927  
CATALOG NUMBER: SA4XXRDIP-C1020D1205U927-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332984-927

CATALOG NUMBER: SA4XXRDIP-C1020D1205U927-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49				
1	98	94	90	86	90	87	83	80	73	71	69	61	59	58	49	48	47	42				
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40	36				
3	82	72	65	59	75	67	61	56	57	52	48	48	44	41	39	37	35	30				
4	75	64	56	50	69	60	53	47	51	46	41	43	39	36	35	32	30	26				
5	69	57	49	43	63	53	46	41	46	40	36	38	34	31	32	29	26	23				
6	63	51	43	38	58	48	41	36	41	36	31	35	30	27	29	26	23	20				
7	59	47	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18				
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16				
9	51	39	31	26	47	36	29	25	31	26	22	27	23	19	22	19	17	15				
10	47	35	28	24	44	33	27	22	29	24	20	25	21	18	21	18	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11548	11548	11548
5°	11574	11432	11503
10°	11501	11294	11294
15°	11369	11058	10975
20°	11188	10746	10548
25°	10956	10381	10117
30°	10730	9996	9577
35°	10481	9596	9034
40°	10181	9141	8450
45°	9903	8691	7854
50°	9588	8171	7222
55°	9250	7631	6536
60°	8879	7038	5837
65°	8537	6298	5146
70°	8039	5481	4369
75°	7414	4545	3553
80°	6467	3464	3259
85°	5483	3149	2946



TEST NUMBER: P332984-927

CATALOG NUMBER: SA4XXRDIP-C1020D1205U927-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.4	2.0
10°-20°	374.7	5.6
20°-30°	541.1	8.1
30°-40°	613.3	9.1
40°-50°	592.3	8.8
50°-60°	492.5	7.3
60°-70°	340.1	5.1
70°-80°	172.4	2.6
80°-90°	46.8	0.7
90°-100°	338.4	5.0
100°-110°	704.3	10.5
110°-120°	630.9	9.4
120°-130°	530.7	7.9
130°-140°	442.5	6.6
140°-150°	338.0	5.0
150°-160°	237.6	3.5
160°-170°	139.8	2.1
170°-180°	45.5	0.7
0°-30°	1050.1	15.6
0°-40°	1663.5	24.8
0°-60°	2748.2	40.9
0°-90°	3307.5	49.3
90°-120°	1673.6	24.9
90°-150°	2984.8	44.4
90°-180°	3408.0	50.8
0°-180°	6715.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1430	1430	1430	1430	1430	
5°	1428	1423	1411	1421	1420	135
15°	1360	1349	1323	1321	1313	383
25°	1230	1209	1165	1147	1136	566
35°	1064	1027	974	937	917	664
45°	867	826	761	709	688	669
55°	657	612	542	487	464	588
65°	447	398	330	284	269	441
75°	238	197	146	122	114	251
85°	59	38	34	32	32	67
90°	1	7	17	18	19	5
95°	30	96	750	371	225	34
105°	108	156	604	1300	1295	115
115°	190	238	538	1035	1244	188
125°	264	314	536	880	992	235
135°	314	374	531	782	887	243
145°	362	414	528	659	724	227
155°	412	444	514	582	607	190
165°	448	462	492	522	529	127
175°	468	469	472	479	477	44
180°	469	469	469	469	469	



TEST NUMBER: P332984-927

CATALOG NUMBER: SA4XXRDIP-C1020D1205U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4
2.5°	1433.9	1433.1	1432.3	1431.6	1430.8	1429.3	1427.2	1425.1	1422.9	1420.8	1422.9
5°	1428.2	1427.3	1426.3	1425.3	1424.3	1422.4	1419.5	1416.6	1413.6	1410.7	1413.2
7.5°	1415.3	1414.3	1413.3	1412.2	1411.2	1408.8	1405.0	1401.2	1397.4	1393.6	1395.2
10°	1403.0	1401.8	1400.6	1399.4	1398.2	1395.3	1391.0	1386.6	1382.2	1377.8	1378.8
12.5°	1387.3	1385.8	1384.4	1383.1	1381.6	1378.3	1373.2	1368.0	1362.9	1357.7	1358.3
15°	1360.3	1358.1	1356.0	1353.8	1351.5	1347.4	1341.3	1335.2	1329.2	1323.1	1322.6
17.5°	1327.7	1324.5	1321.4	1318.2	1315.0	1309.8	1302.5	1295.2	1287.9	1280.6	1279.2
20°	1302.3	1299.1	1295.9	1292.8	1289.6	1283.9	1275.7	1267.3	1259.1	1250.8	1248.9
22.5°	1274.2	1270.7	1267.1	1263.6	1260.0	1253.8	1245.0	1236.1	1227.2	1218.4	1215.4
25°	1230.0	1225.6	1221.2	1216.9	1212.4	1205.3	1195.3	1185.3	1175.4	1165.4	1161.3
27.5°	1183.5	1178.1	1172.6	1167.0	1161.6	1153.5	1142.8	1132.2	1121.5	1110.8	1105.7
30°	1151.1	1145.0	1139.0	1132.9	1126.8	1118.0	1106.6	1095.1	1083.7	1072.3	1066.2
32.5°	1117.0	1110.1	1103.2	1096.4	1089.5	1080.1	1068.3	1056.5	1044.7	1032.8	1025.8
35°	1063.5	1055.7	1047.9	1040.1	1032.4	1022.4	1010.2	998.1	985.9	973.7	965.4
37.5°	1006.3	998.3	990.3	982.2	974.2	963.5	950.0	936.5	923.0	909.5	900.2
40°	966.1	958.0	950.0	941.9	933.9	923.0	909.1	895.2	881.3	867.4	857.2
42.5°	927.5	919.1	910.6	902.2	893.8	882.3	867.9	853.4	839.0	824.5	814.1
45°	867.4	858.5	849.5	840.4	831.4	819.6	805.0	790.4	775.8	761.2	749.3
47.5°	805.5	796.1	786.9	777.6	768.3	756.1	740.8	725.6	710.4	695.3	682.9
50°	763.4	753.9	744.4	734.9	725.4	712.9	697.4	681.8	666.1	650.6	638.4
52.5°	720.5	711.1	701.9	692.6	683.3	670.7	654.7	638.7	622.7	606.8	594.5
55°	657.2	647.5	637.7	628.0	618.2	605.5	589.6	573.8	558.0	542.2	529.5
57.5°	594.5	584.4	574.3	564.1	554.1	541.1	525.6	510.0	494.4	478.9	466.0
60°	549.9	540.1	530.4	520.6	510.9	498.2	482.7	467.1	451.5	435.9	423.3
62.5°	509.5	499.4	489.3	479.1	469.1	456.0	440.0	424.1	408.1	392.1	380.4
65°	446.9	436.4	426.0	415.5	405.0	392.0	376.4	360.8	345.2	329.7	319.2
67.5°	381.8	371.8	361.8	351.7	341.7	329.5	315.0	300.6	286.1	271.6	262.6
70°	340.6	330.4	320.2	310.0	299.8	287.7	273.9	259.9	246.1	232.2	224.2
72.5°	296.8	287.6	278.3	269.1	259.8	248.7	235.6	222.4	209.4	196.3	189.4
75°	237.7	228.7	219.7	210.6	201.7	191.4	180.0	168.6	157.1	145.7	140.1
77.5°	177.7	170.0	162.4	154.7	147.1	138.6	129.4	120.2	110.9	101.6	98.4
80°	139.1	132.1	125.0	118.0	110.9	103.7	96.4	89.1	81.8	74.5	73.8
82.5°	105.8	99.3	92.8	86.3	79.9	74.5	70.4	66.2	62.0	57.8	57.3
85°	59.2	54.3	49.4	44.5	39.7	36.8	36.1	35.4	34.7	34.0	33.4
87.5°	20.4	19.2	18.1	16.8	15.4	14.5	15.4	15.2	15.4	15.6	15.2
90°	1.0	2.8	5.5	6.4	7.4	7.4	12.9	12.9	14.7	16.6	15.7
92.5°	10.5	15.3	23.9	35.2	48.6	67.7	114.5	185.9	255.6	292.0	243.2
95°	30.3	33.1	42.4	54.3	76.4	115.1	195.1	346.1	566.1	750.2	771.4
97.5°	54.5	54.5	62.4	73.4	92.4	124.8	186.5	311.2	529.8	790.2	969.2
100°	69.9	69.9	76.4	87.5	105.0	134.4	188.7	292.7	480.5	740.1	975.7
102.5°	84.7	86.2	91.9	102.2	118.9	146.9	196.1	287.6	447.3	677.5	920.5
105°	107.7	110.4	115.1	126.1	142.7	169.4	213.6	289.9	418.8	603.9	820.1
107.5°	133.1	134.9	139.6	151.3	167.2	193.5	234.0	303.6	413.7	562.6	739.2
110°	150.0	151.9	156.5	167.5	184.1	209.0	249.5	313.9	415.2	548.7	698.7



TEST NUMBER: P332984-927

CATALOG NUMBER: SA4XXRDIP-C1020D1205U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	166.3	168.1	173.4	183.7	200.3	225.1	264.2	325.0	419.5	542.0	675.8
115°	189.6	192.4	198.8	208.0	225.5	250.4	287.2	342.5	428.0	538.5	654.5
117.5°	213.9	216.5	222.2	232.3	248.7	274.5	309.5	360.3	437.0	537.6	644.9
120°	230.1	232.0	238.4	248.5	264.2	289.9	325.0	372.8	443.7	537.6	639.8
122.5°	244.9	246.7	253.2	262.5	279.6	304.7	339.7	384.6	450.4	536.9	633.9
125°	264.2	267.8	273.4	283.5	301.0	326.8	359.9	402.3	460.3	535.8	624.1
127.5°	281.3	284.2	290.9	302.5	320.7	346.7	378.7	417.6	468.2	533.7	611.0
130°	290.9	294.5	301.9	315.8	333.2	359.9	391.3	427.1	474.0	533.0	602.9
132.5°	300.5	303.4	313.0	326.1	345.0	370.3	401.6	436.7	479.2	532.3	595.6
135°	313.9	317.6	326.8	342.5	361.8	385.7	416.1	449.2	487.0	531.2	584.6
137.5°	327.3	330.8	341.0	355.8	376.0	398.8	427.1	458.0	491.5	530.9	575.0
140°	336.9	339.7	349.8	365.4	384.8	406.9	434.5	463.9	495.3	530.2	569.8
142.5°	347.2	350.0	359.3	374.3	392.8	414.2	441.1	468.3	498.2	530.2	565.4
145°	361.8	364.6	373.8	386.6	404.1	424.4	448.3	473.2	499.9	528.4	557.9
147.5°	378.1	379.1	387.1	400.4	414.9	433.2	455.7	477.4	500.7	525.1	551.0
150°	388.5	389.4	396.7	407.8	421.6	439.1	459.3	479.6	500.7	522.8	545.9
152.5°	398.0	398.2	405.6	415.9	428.3	444.3	462.3	481.1	499.3	519.2	540.0
155°	411.5	412.4	417.9	427.1	437.3	451.1	466.7	482.4	497.1	513.7	531.2
157.5°	424.5	424.5	429.7	436.9	445.7	456.6	469.8	482.4	494.7	507.9	522.1
160°	432.6	432.6	436.3	442.8	450.1	460.3	471.3	482.4	492.5	503.5	515.5
162.5°	440.0	439.3	442.2	447.9	454.6	462.5	472.8	482.4	490.3	499.1	509.6
165°	448.3	448.3	450.1	454.7	459.3	464.9	473.2	480.5	486.0	492.5	499.9
167.5°	456.6	455.7	456.6	460.1	462.6	466.9	472.9	478.3	481.6	485.8	491.0
170°	460.3	459.3	460.3	463.0	464.9	467.6	472.2	476.8	478.6	481.4	485.1
172.5°	463.9	463.0	463.2	465.2	466.4	468.3	471.5	475.4	475.7	477.0	480.0
175°	467.6	466.7	466.7	467.6	468.6	468.6	470.4	473.2	472.2	472.2	474.0
177.5°	469.3	468.6	467.8	468.6	468.6	468.6	469.3	470.7	469.3	469.3	470.0
180°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6



TEST NUMBER: P332984-927

CATALOG NUMBER: SA4XXRDIP-C1020D1205U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4
2.5°	1425.1	1427.2	1429.3	1430.4	1430.1	1430.0	1429.7	1429.6
5°	1415.6	1418.0	1420.5	1421.4	1420.9	1420.5	1420.0	1419.5
7.5°	1396.8	1398.3	1399.9	1400.3	1399.5	1398.7	1397.9	1397.1
10°	1379.8	1380.8	1381.7	1381.7	1380.8	1379.8	1378.8	1377.8
12.5°	1358.8	1359.5	1360.0	1359.6	1358.3	1356.9	1355.6	1354.2
15°	1322.2	1321.6	1321.1	1320.0	1318.3	1316.6	1314.9	1313.2
17.5°	1277.9	1276.5	1275.2	1273.2	1270.6	1268.0	1265.4	1262.8
20°	1246.9	1245.0	1243.0	1240.5	1237.3	1234.1	1231.0	1227.8
22.5°	1212.5	1209.6	1206.7	1204.0	1201.3	1198.8	1196.2	1193.7
25°	1157.1	1152.9	1148.8	1145.5	1143.1	1140.7	1138.2	1135.8
27.5°	1100.6	1095.5	1090.4	1086.1	1082.6	1079.0	1075.5	1072.1
30°	1060.1	1054.0	1047.9	1042.9	1039.0	1035.1	1031.3	1027.4
32.5°	1018.7	1011.7	1004.6	999.3	995.5	991.8	988.2	984.4
35°	957.1	948.9	940.6	934.3	929.9	925.5	921.1	916.7
37.5°	891.0	881.8	872.5	865.7	861.3	856.9	852.5	848.2
40°	847.0	836.8	826.6	819.3	814.9	810.5	806.1	801.8
42.5°	803.7	793.3	782.8	775.4	770.8	766.2	761.6	757.1
45°	737.4	725.4	713.5	705.4	701.0	696.6	692.2	687.9
47.5°	670.6	658.2	645.8	637.2	632.4	627.6	622.7	618.0
50°	626.2	614.1	601.9	593.5	588.9	584.2	579.6	575.0
52.5°	582.0	569.7	557.3	548.7	543.9	539.1	534.2	529.5
55°	516.8	504.2	491.5	482.9	478.2	473.6	469.1	464.4
57.5°	453.1	440.3	427.5	419.3	415.7	412.3	408.8	405.3
60°	410.6	397.9	385.3	377.0	373.1	369.2	365.4	361.5
62.5°	368.8	357.0	345.4	337.9	334.9	331.8	328.6	325.5
65°	308.7	298.3	287.8	281.1	278.2	275.3	272.4	269.4
67.5°	253.6	244.6	235.6	229.5	226.2	223.1	219.8	216.7
70°	216.1	208.1	200.1	194.8	192.4	190.0	187.5	185.1
72.5°	182.5	175.7	168.8	164.3	162.0	159.8	157.6	155.3
75°	134.5	128.9	123.3	119.8	118.3	116.8	115.3	113.9
77.5°	95.1	91.9	88.6	86.7	86.3	85.9	85.4	85.0
80°	73.0	72.3	71.5	71.1	70.8	70.6	70.3	70.1
82.5°	56.7	56.2	55.7	55.3	55.1	54.8	54.6	54.3
85°	33.0	32.5	32.0	31.8	31.8	31.8	31.8	31.8
87.5°	15.2	15.2	15.1	15.1	15.5	15.9	15.9	16.2
90°	16.6	17.5	18.4	18.4	19.3	20.3	19.3	19.3
92.5°	180.8	136.0	108.3	89.8	79.0	74.0	70.9	70.9
95°	682.1	539.4	416.1	326.8	281.7	253.2	236.5	224.6
97.5°	1007.8	954.7	864.7	768.7	702.5	647.1	619.5	600.4
100°	1110.2	1128.5	1083.5	1015.3	935.3	879.1	851.5	844.1
102.5°	1105.0	1196.3	1209.3	1181.0	1131.9	1091.2	1062.1	1056.2
105°	1030.9	1190.3	1281.4	1319.1	1321.0	1313.6	1300.7	1295.1
107.5°	925.8	1095.4	1223.8	1305.8	1351.3	1372.3	1381.5	1383.9
110°	862.5	1021.8	1155.2	1256.5	1321.8	1360.5	1377.1	1385.4





TEST NUMBER: P332984-927

CATALOG NUMBER: SA4XXRDIP-C1020D1205U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	816.1	957.0	1083.1	1184.3	1258.5	1305.3	1328.5	1342.0
115°	769.5	882.8	990.5	1078.9	1151.6	1206.8	1236.3	1243.6
117.5°	746.7	840.4	925.1	1000.1	1062.1	1108.5	1138.3	1144.0
120°	736.4	822.0	895.6	961.0	1013.5	1054.0	1077.9	1088.1
122.5°	727.5	810.2	877.3	934.5	978.9	1013.5	1033.7	1043.9
125°	712.5	791.6	855.2	905.8	942.6	969.3	986.8	992.3
127.5°	694.0	769.8	833.1	881.1	918.1	941.9	956.6	962.1
130°	679.4	752.1	814.7	863.5	901.2	924.2	938.9	944.4
132.5°	663.8	732.2	793.3	842.1	879.1	905.1	919.0	924.6
135°	642.5	702.3	758.5	804.5	841.4	867.1	881.9	887.4
137.5°	623.2	673.8	721.1	762.7	797.2	822.6	834.7	841.4
140°	612.1	655.4	696.8	735.5	767.7	788.0	800.8	808.2
142.5°	601.8	639.9	675.5	709.0	737.5	756.3	767.7	772.9
145°	587.3	618.6	646.2	672.0	695.0	710.7	719.9	724.5
147.5°	575.4	600.2	622.3	642.5	659.5	672.9	679.9	681.5
150°	568.0	589.1	607.5	624.1	638.8	650.8	656.3	657.3
152.5°	559.8	578.1	595.0	608.6	621.2	630.9	634.2	635.2
155°	547.7	562.4	576.2	587.3	596.5	603.9	606.7	606.7
157.5°	534.6	547.0	558.6	567.4	574.4	580.0	581.6	581.6
160°	526.6	536.6	546.8	554.1	559.7	565.2	566.1	566.1
162.5°	518.4	527.1	535.0	541.6	545.7	551.2	552.2	551.4
165°	507.2	512.7	519.2	523.8	527.4	531.2	530.2	529.3
167.5°	496.4	500.6	505.7	508.5	510.3	512.7	512.5	511.8
170°	489.7	492.5	496.1	498.9	500.7	501.7	500.7	500.7
172.5°	483.8	485.8	488.1	490.0	491.2	492.1	491.2	489.7
175°	475.9	476.8	478.6	478.6	478.6	480.5	478.6	476.8
177.5°	470.7	471.5	471.5	472.2	471.5	472.2	470.7	469.3
180°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6

(END OF REPORT)