

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333008-927

Luminaire Tested: **SA4XXRDIP-C1195D1035U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P333008-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D1035U927-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6746.8 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333008-927
CATALOG NUMBER: SA4XXRDIP-C1195D1035U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333008-927

CATALOG NUMBER: SA4XXRDIP-C1195D1035U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	95	92	88	93	89	86	83	77	74	72	66	64	62	55	54	53	48
2	91	84	78	72	84	78	73	68	68	64	60	58	55	53	49	47	45	41
3	83	74	66	61	77	69	63	57	60	55	51	52	48	45	44	41	39	35
4	76	65	58	52	71	61	54	49	53	48	44	46	42	39	39	36	34	30
5	70	58	50	44	65	55	48	42	48	42	38	42	37	34	36	32	30	26
6	65	53	45	39	60	49	42	37	43	38	33	38	33	30	32	29	26	23
7	60	48	40	34	56	45	38	33	39	34	29	34	30	26	30	26	23	21
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	27	24	21	19
9	52	40	32	27	48	37	31	26	33	27	24	29	25	21	25	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13337	13337	13337
5°	13367	13203	13285
10°	13283	13045	13045
15°	13131	12771	12676
20°	12921	12411	12182
25°	12653	11989	11685
30°	12393	11544	11060
35°	12105	11083	10435
40°	11758	10559	9759
45°	11439	10038	9070
50°	11074	9437	8341
55°	10683	8812	7548
60°	10253	8128	6739
65°	9859	7272	5945
70°	9286	6331	5046
75°	8562	5250	4105
80°	7471	3998	3766
85°	6326	3631	3399



TEST NUMBER: P333008-927

CATALOG NUMBER: SA4XXRDIP-C1195D1035U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.2	2.3
10°-20°	432.8	6.4
20°-30°	624.9	9.3
30°-40°	708.3	10.5
40°-50°	684.0	10.1
50°-60°	568.8	8.4
60°-70°	392.8	5.8
70°-80°	199.1	3.0
80°-90°	53.3	0.8
90°-100°	290.8	4.3
100°-110°	605.1	9.0
110°-120°	542.0	8.0
120°-130°	455.9	6.8
130°-140°	380.1	5.6
140°-150°	290.4	4.3
150°-160°	204.1	3.0
160°-170°	120.1	1.8
170°-180°	39.1	0.6
0°-30°	1212.9	18.0
0°-40°	1921.2	28.5
0°-60°	3174.0	47.0
0°-90°	3819.1	56.6
90°-120°	1437.9	21.3
90°-150°	2564.4	38.0
90°-180°	2928.0	43.4
0°-180°	6746.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1652	1652	1652	1652	1652	
5°	1650	1644	1629	1641	1639	156
15°	1571	1559	1528	1525	1517	442
25°	1420	1396	1346	1325	1312	654
35°	1228	1186	1125	1083	1059	767
45°	1002	953	879	819	794	772
55°	759	707	626	563	536	679
65°	516	460	381	328	311	509
75°	274	227	168	140	132	290
85°	68	44	39	37	37	77
90°	1	6	14	16	17	5
95°	26	82	644	319	193	29
105°	92	134	519	1117	1113	99
115°	163	204	463	889	1068	162
125°	227	270	460	756	852	202
135°	270	321	456	671	762	208
145°	311	356	454	566	622	195
155°	354	382	441	500	521	163
165°	385	397	423	448	455	109
175°	402	402	406	411	410	38
180°	402	402	402	402	402	



TEST NUMBER: P333008-927

CATALOG NUMBER: SA4XXRDIP-C1195D1035U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0
2.5°	1656.1	1655.2	1654.3	1653.4	1652.5	1650.8	1648.4	1645.8	1643.4	1640.9	1643.4
5°	1649.5	1648.4	1647.3	1646.2	1645.0	1642.7	1639.4	1636.0	1632.7	1629.3	1632.1
7.5°	1634.6	1633.4	1632.2	1631.0	1629.8	1627.1	1622.7	1618.3	1613.9	1609.6	1611.4
10°	1620.4	1619.0	1617.6	1616.2	1614.8	1611.5	1606.5	1601.5	1596.4	1591.3	1592.4
12.5°	1602.2	1600.6	1598.9	1597.3	1595.7	1591.9	1585.9	1580.0	1574.0	1568.0	1568.8
15°	1571.1	1568.5	1566.1	1563.5	1561.0	1556.2	1549.2	1542.1	1535.1	1528.0	1527.5
17.5°	1533.4	1529.7	1526.1	1522.4	1518.8	1512.8	1504.3	1495.9	1487.4	1479.0	1477.4
20°	1504.0	1500.4	1496.7	1493.1	1489.5	1482.8	1473.3	1463.7	1454.1	1444.6	1442.3
22.5°	1471.6	1467.6	1463.5	1459.4	1455.2	1448.1	1437.8	1427.6	1417.4	1407.2	1403.7
25°	1420.5	1415.5	1410.4	1405.4	1400.3	1392.0	1380.5	1369.0	1357.5	1345.9	1341.2
27.5°	1366.9	1360.6	1354.2	1347.9	1341.5	1332.2	1319.9	1307.6	1295.2	1282.9	1277.0
30°	1329.5	1322.5	1315.4	1308.4	1301.4	1291.3	1278.0	1264.8	1251.6	1238.4	1231.4
32.5°	1290.0	1282.1	1274.1	1266.2	1258.3	1247.5	1233.8	1220.2	1206.5	1192.9	1184.7
35°	1228.3	1219.2	1210.3	1201.3	1192.3	1180.7	1166.7	1152.7	1138.6	1124.6	1115.0
37.5°	1162.3	1152.9	1143.7	1134.4	1125.1	1112.7	1097.2	1081.6	1066.0	1050.4	1039.7
40°	1115.7	1106.4	1097.2	1087.9	1078.6	1066.0	1050.0	1033.9	1017.9	1001.9	990.1
42.5°	1071.2	1061.4	1051.7	1042.0	1032.3	1019.1	1002.3	985.6	969.0	952.3	940.2
45°	1001.9	991.4	981.0	970.7	960.3	946.6	929.8	912.9	896.0	879.2	865.4
47.5°	930.3	919.5	908.8	898.0	887.3	873.1	855.6	838.0	820.5	803.0	788.7
50°	881.7	870.7	859.8	848.8	837.8	823.3	805.3	787.3	769.4	751.4	737.4
52.5°	832.1	821.3	810.6	799.9	789.2	774.5	756.1	737.7	719.2	700.8	686.5
55°	759.0	747.7	736.5	725.2	714.0	699.3	681.0	662.7	644.4	626.1	611.6
57.5°	686.6	674.9	663.2	651.6	639.8	625.0	607.0	589.0	571.0	553.0	538.2
60°	635.0	623.8	612.5	601.3	590.0	575.4	557.5	539.5	521.4	503.4	488.9
62.5°	588.4	576.8	565.1	553.4	541.7	526.6	508.2	489.7	471.3	452.9	439.3
65°	516.1	504.0	491.9	479.8	467.8	452.7	434.7	416.8	398.8	380.7	368.7
67.5°	440.9	429.4	417.8	406.2	394.7	380.5	363.8	347.1	330.4	313.7	303.3
70°	393.4	381.6	369.8	358.0	346.2	332.2	316.2	300.2	284.2	268.2	258.9
72.5°	342.8	332.2	321.5	310.8	300.1	287.2	272.0	256.9	241.8	226.6	218.7
75°	274.5	264.1	253.7	243.3	232.9	221.1	207.9	194.6	181.5	168.3	161.8
77.5°	205.2	196.4	187.5	178.7	169.8	160.1	149.4	138.8	128.1	117.4	113.6
80°	160.7	152.5	144.3	136.2	128.0	119.8	111.3	102.9	94.4	86.0	85.2
82.5°	122.2	114.7	107.3	99.7	92.3	86.1	81.3	76.4	71.6	66.8	66.1
85°	68.3	62.7	57.0	51.4	45.8	42.6	41.7	40.9	40.1	39.2	38.7
87.5°	23.4	21.9	20.6	19.0	17.3	16.3	17.0	16.8	17.0	17.0	16.6
90°	0.8	2.4	4.8	5.5	6.3	6.3	11.1	11.1	12.7	14.3	13.5
92.5°	9.0	13.2	20.6	30.2	41.7	58.2	98.4	159.8	219.5	250.9	209.0
95°	26.1	28.4	36.4	46.7	65.7	98.9	167.6	297.4	486.4	644.5	662.7
97.5°	46.8	46.8	53.6	63.1	79.4	107.3	160.3	267.3	455.2	678.8	832.6
100°	60.1	60.1	65.7	75.1	90.2	115.5	162.2	251.5	412.8	635.8	838.3
102.5°	72.7	74.0	78.9	87.8	102.2	126.2	168.4	247.1	384.4	582.1	790.8
105°	92.5	94.9	98.9	108.4	122.6	145.5	183.5	249.1	359.8	518.8	704.6
107.5°	114.4	116.0	119.9	130.0	143.6	166.2	201.1	260.8	355.4	483.4	635.0
110°	128.9	130.5	134.4	143.9	158.2	179.5	214.3	269.7	356.6	471.3	600.2



TEST NUMBER: P333008-927

CATALOG NUMBER: SA4XXRDIP-C1195D1035U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	142.8	144.4	149.0	157.9	172.1	193.5	227.0	279.2	360.4	465.6	580.7
115°	163.0	165.2	170.8	178.7	193.8	215.1	246.8	294.2	367.7	462.6	562.3
117.5°	183.8	186.0	190.9	199.6	213.7	235.8	265.9	309.5	375.5	461.8	554.1
120°	197.7	199.3	204.9	213.5	227.0	249.1	279.2	320.3	381.2	461.8	549.6
122.5°	210.4	211.9	217.5	225.5	240.3	261.7	291.8	330.4	386.9	461.2	544.5
125°	227.0	230.1	234.9	243.6	258.6	280.7	309.2	345.6	395.5	460.3	536.2
127.5°	241.7	244.2	249.9	259.8	275.5	297.9	325.3	358.7	402.2	458.5	525.0
130°	249.9	253.1	259.4	271.2	286.3	309.2	336.1	366.9	407.3	457.9	518.0
132.5°	258.1	260.6	268.9	280.1	296.4	318.1	345.0	375.2	411.7	457.2	511.7
135°	269.7	272.8	280.7	294.2	310.8	331.4	357.4	386.0	418.4	456.3	502.2
137.5°	281.2	284.2	292.9	305.7	323.0	342.6	366.9	393.6	422.3	456.1	493.9
140°	289.5	291.8	300.6	313.9	330.6	349.6	373.3	398.5	425.5	455.5	489.6
142.5°	298.3	300.7	308.7	321.5	337.5	355.8	379.0	402.3	428.0	455.5	485.8
145°	310.8	313.1	321.1	332.2	347.2	364.6	385.2	406.5	429.4	453.9	479.3
147.5°	324.9	325.7	332.6	344.0	356.5	372.2	391.5	410.1	430.2	451.1	473.4
150°	333.7	334.5	340.9	350.4	362.2	377.2	394.7	412.0	430.2	449.2	469.0
152.5°	342.0	342.1	348.5	357.3	367.9	381.7	397.2	413.3	429.0	446.0	463.9
155°	353.5	354.3	359.0	366.9	375.7	387.5	400.9	414.4	427.1	441.3	456.3
157.5°	364.7	364.7	369.2	375.3	382.9	392.3	403.6	414.4	425.0	436.4	448.5
160°	371.7	371.7	374.9	380.4	386.7	395.5	404.9	414.4	423.1	432.6	442.9
162.5°	378.0	377.4	379.9	384.8	390.5	397.4	406.2	414.4	421.2	428.8	437.8
165°	385.2	385.2	386.7	390.7	394.7	399.3	406.5	412.8	417.6	423.1	429.4
167.5°	392.3	391.5	392.3	395.3	397.5	401.1	406.3	410.9	413.8	417.4	421.8
170°	395.5	394.7	395.5	397.8	399.3	401.7	405.7	409.6	411.2	413.6	416.8
172.5°	398.5	397.8	397.9	399.7	400.6	402.3	405.0	408.4	408.7	409.8	412.3
175°	401.7	400.9	400.9	401.7	402.5	402.5	404.1	406.5	405.7	405.7	407.3
177.5°	403.1	402.5	401.9	402.5	402.5	402.5	403.1	404.4	403.1	403.1	403.8
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P333008-927

CATALOG NUMBER: SA4XXRDIP-C1195D1035U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0
2.5°	1645.8	1648.4	1650.8	1651.9	1651.7	1651.5	1651.2	1651.1
5°	1634.9	1637.7	1640.5	1641.6	1641.1	1640.5	1640.0	1639.4
7.5°	1613.1	1614.9	1616.8	1617.2	1616.3	1615.4	1614.5	1613.6
10°	1593.6	1594.7	1595.9	1595.9	1594.7	1593.6	1592.4	1591.3
12.5°	1569.4	1570.1	1570.7	1570.3	1568.8	1567.2	1565.6	1564.0
15°	1526.9	1526.4	1525.8	1524.6	1522.6	1520.6	1518.7	1516.7
17.5°	1475.8	1474.3	1472.7	1470.4	1467.4	1464.4	1461.5	1458.5
20°	1440.1	1437.8	1435.6	1432.7	1429.0	1425.4	1421.7	1418.0
22.5°	1400.4	1397.0	1393.7	1390.5	1387.5	1384.5	1381.6	1378.6
25°	1336.3	1331.6	1326.8	1323.0	1320.2	1317.4	1314.5	1311.8
27.5°	1271.1	1265.2	1259.3	1254.3	1250.3	1246.3	1242.2	1238.2
30°	1224.3	1217.3	1210.3	1204.5	1200.0	1195.6	1191.0	1186.5
32.5°	1176.5	1168.4	1160.2	1154.1	1149.8	1145.5	1141.2	1136.9
35°	1105.4	1095.9	1086.3	1079.0	1074.0	1068.9	1063.8	1058.8
37.5°	1029.0	1018.4	1007.7	999.8	994.7	989.7	984.7	979.6
40°	978.3	966.5	954.7	946.2	941.1	936.0	931.1	926.0
42.5°	928.2	916.2	904.1	895.5	890.2	884.9	879.6	874.3
45°	851.6	837.8	824.0	814.6	809.6	804.5	799.5	794.4
47.5°	774.4	760.2	745.9	735.9	730.4	724.8	719.2	713.7
50°	723.3	709.2	695.1	685.5	680.2	674.8	669.5	664.1
52.5°	672.2	658.0	643.6	633.7	628.2	622.7	617.0	611.5
55°	596.9	582.3	567.7	557.7	552.4	547.0	541.7	536.3
57.5°	523.4	508.5	493.7	484.3	480.2	476.1	472.1	468.0
60°	474.2	459.6	445.0	435.5	430.9	426.4	421.9	417.4
62.5°	425.9	412.4	398.9	390.3	386.7	383.2	379.5	376.0
65°	356.6	344.5	332.4	324.6	321.3	317.9	314.6	311.2
67.5°	292.9	282.5	272.1	265.1	261.3	257.6	253.9	250.2
70°	249.6	240.3	231.1	225.1	222.2	219.4	216.6	213.8
72.5°	210.8	202.9	195.0	189.7	187.1	184.6	182.0	179.4
75°	155.3	148.9	142.4	138.3	136.7	134.9	133.2	131.6
77.5°	109.9	106.1	102.3	100.2	99.7	99.2	98.7	98.2
80°	84.4	83.5	82.6	82.1	81.8	81.5	81.3	81.0
82.5°	65.6	65.0	64.3	63.8	63.6	63.3	63.1	62.7
85°	38.1	37.5	37.0	36.7	36.7	36.7	36.7	36.7
87.5°	16.6	16.5	16.4	16.4	16.8	17.2	17.3	17.5
90°	14.3	15.1	15.8	15.8	16.6	17.4	16.6	16.6
92.5°	155.3	116.9	93.0	77.2	67.9	63.6	60.9	60.9
95°	586.0	463.4	357.4	280.7	242.0	217.5	203.3	193.0
97.5°	865.9	820.2	742.9	660.4	603.6	556.0	532.3	515.8
100°	953.8	969.6	930.8	872.3	803.5	755.3	731.5	725.2
102.5°	949.4	1027.8	1039.0	1014.6	972.4	937.5	912.5	907.4
105°	885.7	1022.5	1100.8	1133.3	1134.9	1128.5	1117.5	1112.7
107.5°	795.4	941.1	1051.4	1121.9	1160.9	1179.0	1186.9	1189.0
110°	741.0	877.8	992.5	1079.5	1135.7	1168.9	1183.1	1190.3



TEST NUMBER: P333008-927

CATALOG NUMBER: SA4XXRDIP-C1195D1035U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	701.2	822.1	930.5	1017.5	1081.2	1121.4	1141.4	1152.9
115°	661.2	758.4	851.0	926.9	989.4	1036.8	1062.1	1068.4
117.5°	641.5	722.1	794.8	859.2	912.5	952.4	977.9	982.9
120°	632.6	706.2	769.5	825.6	870.7	905.5	926.1	934.8
122.5°	625.1	696.1	753.7	802.9	841.0	870.7	888.1	896.8
125°	612.1	680.1	734.7	778.2	809.8	832.7	847.8	852.5
127.5°	596.3	661.3	715.7	757.0	788.8	809.2	821.8	826.6
130°	583.7	646.1	699.9	741.8	774.2	794.0	806.7	811.4
132.5°	570.4	629.1	681.5	723.5	755.3	777.5	789.6	794.3
135°	552.0	603.4	651.6	691.2	722.9	745.0	757.6	762.4
137.5°	535.4	578.9	619.6	655.3	684.8	706.7	717.2	722.9
140°	525.9	563.1	598.7	631.8	659.6	677.0	688.0	694.3
142.5°	517.1	549.8	580.4	609.1	633.6	649.7	659.6	664.0
145°	504.5	531.5	555.2	577.3	597.1	610.5	618.5	622.4
147.5°	494.2	515.6	534.6	552.0	566.6	578.1	584.2	585.5
150°	488.0	506.1	522.0	536.2	548.8	559.1	563.9	564.7
152.5°	481.0	496.6	511.2	522.9	533.7	542.0	544.9	545.7
155°	470.6	483.2	495.0	504.5	512.5	518.8	521.2	521.2
157.5°	459.3	469.9	479.9	487.5	493.5	498.2	499.6	499.6
160°	452.3	461.1	469.8	476.1	480.9	485.6	486.4	486.4
162.5°	445.4	452.8	459.6	465.3	468.8	473.6	474.4	473.7
165°	435.8	440.5	446.0	450.0	453.1	456.3	455.5	454.7
167.5°	426.4	430.1	434.5	436.9	438.5	440.5	440.4	439.7
170°	420.7	423.1	426.3	428.6	430.2	431.0	430.2	430.2
172.5°	415.7	417.4	419.3	421.0	422.0	422.8	422.0	420.7
175°	408.8	409.6	411.2	411.2	411.2	412.8	411.2	409.6
177.5°	404.4	405.0	405.0	405.7	405.0	405.7	404.4	403.1
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5

(END OF REPORT)