

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333009-927

Luminaire Tested: **SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P333009-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7778.6 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333009-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333009-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44				
2	90	83	77	72	83	77	72	67	66	62	59	55	53	50	46	44	42	38				
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32				
4	76	65	57	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28				
5	70	58	50	44	64	54	47	42	47	41	37	40	36	32	33	30	28	25				
6	64	52	44	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22				
7	59	47	40	34	55	44	37	32	38	33	29	33	29	25	28	25	22	19				
8	55	43	35	30	51	40	33	29	35	30	26	30	26	23	26	22	20	18				
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	20	18	16				
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12674	12674	12674	12674
5°	14699	12712	11235	12712
10°	17390	12656	10027	12656
15°	20088	12538	8616	12538
20°	22365	12378	7792	12378
25°	23087	12219	7234	12219
30°	20211	12028	6898	12028
35°	15733	11744	6695	11744
40°	11798	11418	6585	11418
45°	9315	10896	6528	10896
50°	7863	10295	6339	10295
55°	6854	9633	6000	9633
60°	6168	8946	5310	8946
65°	5436	8202	4567	8202
70°	4898	7435	4121	7435
75°	4105	6591	3512	6591
80°	3468	5616	3292	5616
85°	2927	4400	2927	4400



TEST NUMBER: P333009-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.1	2.0
10°-20°	458.8	5.9
20°-30°	717.6	9.2
30°-40°	797.8	10.3
40°-50°	707.8	9.1
50°-60°	551.5	7.1
60°-70°	361.1	4.6
70°-80°	177.6	2.3
80°-90°	47.4	0.6
90°-100°	42.1	0.5
100°-110°	268.4	3.5
110°-120°	513.4	6.6
120°-130°	651.7	8.4
130°-140°	697.3	9.0
140°-150°	652.1	8.4
150°-160°	525.8	6.8
160°-170°	339.2	4.4
170°-180°	116.9	1.5
0°-30°	1328.5	17.1
0°-40°	2126.3	27.3
0°-60°	3385.7	43.5
0°-90°	3971.7	51.1
90°-120°	823.9	10.6
90°-150°	2825.0	36.3
90°-180°	3807.0	48.9
0°-180°	7778.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1570	1570	1570	1570	1570	
5°	1814	1569	1386	1569	1814	183
15°	2404	1500	1031	1500	2404	683
25°	2592	1372	812	1372	2592	1150
35°	1596	1192	679	1192	1596	1001
45°	816	954	572	954	816	646
55°	487	684	426	684	487	443
65°	285	429	239	429	285	286
75°	132	211	113	211	132	145
85°	32	48	32	48	32	36
90°	28	3	28	3	28	13
95°	27	51	27	51	27	21
105°	262	277	262	277	262	229
115°	521	517	521	517	521	516
125°	733	727	733	727	733	653
135°	908	902	908	902	908	699
145°	1046	1040	1046	1040	1046	653
155°	1140	1140	1140	1140	1140	525
165°	1198	1203	1198	1203	1198	338
175°	1223	1231	1223	1231	1223	116
180°	1231	1231	1231	1231	1231	



TEST NUMBER: P333009-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1655.8	1660.4	1655.8	1655.3	1650.3	1648.8	1646.7	1640.1	1628.0	1621.0	1622.5
5°	1813.9	1829.8	1820.9	1819.6	1805.8	1791.8	1783.0	1762.8	1741.2	1726.7	1714.7
7.5°	1996.9	2006.0	2000.4	1991.5	1969.0	1956.3	1935.8	1909.1	1870.5	1841.0	1814.1
10°	2121.4	2128.9	2126.5	2110.0	2093.5	2060.0	2041.1	2003.7	1955.0	1916.4	1880.4
12.5°	2243.8	2251.9	2229.7	2230.4	2199.3	2172.9	2142.8	2095.8	2039.6	1989.8	1944.6
15°	2403.5	2393.3	2393.3	2380.7	2345.9	2309.2	2278.2	2228.9	2158.1	2098.6	2036.0
17.5°	2528.4	2532.0	2526.7	2497.0	2469.6	2431.7	2374.9	2317.3	2251.5	2171.7	2107.7
20°	2603.3	2603.3	2597.6	2577.4	2542.0	2501.5	2440.2	2377.5	2294.0	2213.7	2141.6
22.5°	2633.7	2635.7	2629.0	2612.3	2580.5	2540.9	2488.7	2425.1	2339.1	2248.6	2159.3
25°	2591.9	2604.0	2605.2	2600.8	2591.3	2567.2	2522.4	2457.2	2380.0	2282.0	2185.9
27.5°	2379.6	2394.8	2408.2	2430.0	2459.1	2474.3	2476.3	2443.2	2375.8	2281.5	2184.8
30°	2168.1	2180.8	2221.9	2275.7	2317.5	2355.4	2388.3	2397.1	2359.2	2274.4	2172.6
32.5°	1933.4	1950.6	1991.7	2049.5	2119.1	2183.3	2257.2	2294.9	2293.9	2243.1	2148.8
35°	1596.4	1609.1	1647.0	1707.7	1791.2	1886.7	2003.7	2094.8	2156.8	2152.4	2094.8
37.5°	1287.5	1301.8	1340.1	1390.4	1471.4	1589.7	1702.9	1828.4	1943.0	2007.4	1988.1
40°	1119.5	1120.1	1157.5	1209.3	1285.2	1388.3	1511.6	1650.7	1778.5	1882.9	1903.1
42.5°	986.9	987.1	1011.7	1067.6	1122.3	1219.3	1337.0	1475.2	1624.8	1745.3	1798.9
45°	815.9	821.6	841.9	875.4	918.4	1000.6	1094.8	1223.2	1390.8	1533.7	1622.9
47.5°	690.9	699.3	712.2	739.5	773.8	828.5	906.5	1021.8	1158.2	1315.4	1442.3
50°	626.1	627.4	643.9	659.0	688.8	732.5	800.7	896.8	1022.1	1173.2	1314.3
52.5°	570.5	570.2	580.1	599.4	623.5	657.5	712.6	800.2	911.2	1046.8	1192.4
55°	487.0	490.2	497.7	512.9	531.3	555.3	599.0	664.7	752.0	867.8	1000.0
57.5°	423.5	425.2	431.1	437.5	454.4	471.8	504.6	550.2	623.9	718.7	841.9
60°	382.0	382.6	384.5	394.0	407.3	423.7	445.9	484.5	546.4	633.1	730.6
62.5°	341.5	342.7	345.6	352.5	362.8	374.1	397.4	428.3	479.7	553.7	641.4
65°	284.6	285.3	289.7	292.2	300.4	310.5	327.6	348.5	383.9	445.9	512.3
67.5°	237.8	237.8	238.1	241.5	247.2	253.9	264.1	280.8	307.5	345.6	404.2
70°	207.5	207.5	208.7	210.6	213.8	219.4	225.1	237.8	257.5	288.4	333.4
72.5°	179.1	179.6	180.9	181.3	182.9	187.6	191.8	199.9	214.4	237.8	274.1
75°	131.6	133.5	136.7	139.2	142.3	141.6	146.1	151.1	155.6	169.5	190.4
77.5°	97.9	96.9	97.3	99.4	99.8	100.4	103.6	107.5	110.8	117.4	124.8
80°	74.6	74.6	76.5	77.2	76.5	77.2	80.3	82.2	83.5	86.0	93.0
82.5°	56.4	57.4	56.8	57.4	57.8	58.5	61.1	61.5	62.7	63.8	66.7
85°	31.6	32.2	32.9	31.6	31.6	31.6	32.9	33.5	34.8	34.1	35.4
87.5°	16.6	16.1	16.5	16.4	16.8	16.2	16.4	17.2	15.9	16.2	15.8
90°	27.6	27.2	26.8	26.4	26.0	25.2	23.9	22.7	21.5	20.3	18.6
92.5°	25.4	25.3	25.3	25.2	25.1	24.4	23.2	21.9	20.8	19.5	17.9
95°	26.7	26.5	26.3	26.1	25.9	25.2	23.9	22.7	21.5	20.3	20.0
97.5°	25.7	25.6	25.3	25.2	25.0	24.8	24.6	24.6	24.4	24.3	47.1
100°	25.7	25.6	25.3	25.2	25.0	26.6	30.1	33.5	37.0	40.5	68.8
102.5°	26.5	26.5	26.5	26.4	26.4	45.1	82.6	120.1	157.6	195.1	198.8
105°	262.4	269.7	277.0	284.4	291.8	294.5	292.7	290.9	289.1	287.2	286.1
107.5°	365.6	364.8	364.1	363.3	362.5	361.6	360.8	359.9	358.9	358.1	356.6
110°	410.5	410.0	409.3	408.7	408.1	407.6	407.2	406.8	406.3	405.9	404.7



TEST NUMBER: P333009-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	455.4	454.7	453.9	453.1	452.3	452.0	452.1	452.2	452.3	452.3	451.8
115°	521.0	521.0	521.0	521.0	521.0	520.8	520.4	520.0	519.6	519.1	519.4
117.5°	587.6	587.7	587.8	587.9	588.0	588.0	588.1	588.2	588.3	588.4	588.0
120°	629.6	630.0	630.4	630.8	631.2	631.2	630.8	630.4	630.0	629.6	629.8
122.5°	670.8	671.2	671.7	672.1	672.5	672.6	672.3	672.1	671.8	671.6	671.3
125°	732.7	732.5	732.3	732.1	731.9	731.5	730.9	730.2	729.6	729.0	729.4
127.5°	787.0	787.2	787.3	787.5	787.7	787.8	787.9	788.1	788.1	788.3	787.3
130°	823.8	823.8	823.8	823.8	823.8	823.7	823.6	823.3	823.1	822.9	822.3
132.5°	857.7	857.9	858.0	858.2	858.3	858.3	858.2	857.9	857.7	857.5	856.7
135°	908.5	908.1	907.7	907.3	906.9	906.5	906.0	905.6	905.2	904.8	904.0
137.5°	952.0	952.0	952.2	952.4	952.4	952.3	951.8	951.4	950.9	950.5	949.6
140°	982.1	981.9	981.8	981.5	981.4	981.0	980.3	979.7	979.1	978.5	978.0
142.5°	1007.2	1007.2	1007.1	1007.1	1007.0	1006.8	1006.3	1005.9	1005.4	1005.0	1004.7
145°	1045.7	1045.3	1044.8	1044.4	1044.0	1043.7	1043.5	1043.3	1043.1	1042.9	1042.9
147.5°	1077.5	1077.3	1077.1	1076.9	1076.7	1076.5	1076.3	1076.2	1076.0	1075.9	1076.0
150°	1098.1	1098.0	1097.7	1097.5	1097.3	1097.2	1097.2	1097.2	1097.2	1097.2	1097.4
152.5°	1115.8	1115.9	1116.0	1116.2	1116.3	1116.2	1115.9	1115.6	1115.2	1114.9	1115.2
155°	1139.6	1140.2	1140.7	1141.4	1142.0	1141.9	1141.1	1140.3	1139.5	1138.6	1139.2
157.5°	1159.4	1160.5	1161.6	1162.6	1163.7	1163.7	1162.6	1161.6	1160.5	1159.4	1160.2
160°	1172.7	1173.9	1175.1	1176.4	1177.6	1177.6	1176.4	1175.1	1173.9	1172.7	1172.9
162.5°	1183.0	1184.4	1185.8	1187.2	1188.6	1188.7	1187.4	1186.2	1184.9	1183.8	1183.9
165°	1197.5	1199.4	1201.2	1203.1	1204.9	1205.0	1203.4	1201.7	1200.1	1198.5	1198.5
167.5°	1208.4	1210.5	1212.5	1214.6	1216.6	1216.7	1214.9	1213.1	1211.3	1209.5	1209.7
170°	1215.0	1217.1	1219.1	1221.1	1223.2	1223.4	1221.8	1220.1	1218.5	1216.9	1216.6
172.5°	1218.7	1220.9	1223.1	1225.3	1227.6	1227.8	1226.2	1224.6	1222.9	1221.3	1221.1
175°	1223.3	1225.7	1228.2	1230.7	1233.1	1233.4	1231.6	1229.8	1227.9	1226.1	1225.9
177.5°	1226.3	1228.2	1230.2	1232.2	1234.1	1234.5	1233.1	1231.8	1230.5	1229.2	1228.9
180°	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7



TEST NUMBER: P333009-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1617.4	1610.3	1606.8	1598.7	1589.0	1584.0	1579.5	1572.9	1564.2	1555.1	1548.6
5°	1699.5	1684.3	1665.3	1642.6	1622.3	1602.7	1585.6	1568.6	1549.0	1528.8	1508.5
7.5°	1783.8	1753.9	1721.6	1684.3	1648.0	1615.0	1584.6	1555.5	1522.7	1493.2	1466.3
10°	1842.5	1802.0	1757.1	1709.6	1662.2	1621.0	1580.6	1543.9	1503.4	1467.4	1437.0
12.5°	1890.0	1842.5	1788.4	1729.3	1672.3	1622.5	1576.0	1528.2	1482.2	1443.1	1402.6
15°	1968.9	1903.8	1831.1	1760.2	1686.2	1618.5	1555.9	1500.2	1447.8	1392.7	1354.2
17.5°	2023.2	1945.9	1857.5	1772.3	1685.0	1605.1	1532.9	1466.6	1406.0	1349.9	1303.9
20°	2055.6	1970.2	1872.2	1775.4	1677.4	1592.0	1514.2	1440.8	1378.2	1317.5	1270.0
22.5°	2073.8	1979.3	1872.2	1770.8	1669.3	1576.8	1491.4	1415.0	1346.8	1286.1	1233.6
25°	2079.6	1978.4	1869.0	1752.6	1641.3	1543.3	1454.7	1371.8	1295.9	1235.2	1179.6
27.5°	2071.6	1952.3	1840.3	1720.9	1606.0	1502.7	1409.7	1322.6	1246.7	1181.5	1124.4
30°	2059.4	1931.6	1811.4	1687.5	1571.1	1471.8	1373.7	1290.3	1211.2	1143.5	1086.0
32.5°	2033.1	1906.3	1777.0	1650.0	1532.2	1429.8	1336.8	1252.8	1175.3	1106.1	1045.0
35°	1980.9	1852.5	1712.1	1581.8	1466.1	1359.9	1272.6	1191.6	1117.6	1043.6	979.1
37.5°	1912.2	1781.1	1641.4	1498.7	1382.8	1282.5	1202.5	1126.5	1054.2	986.7	915.2
40°	1847.5	1728.0	1583.7	1442.1	1323.2	1226.4	1152.4	1083.5	1010.7	943.6	872.2
42.5°	1769.1	1667.2	1521.5	1379.3	1261.9	1168.7	1099.8	1032.4	966.2	901.2	826.6
45°	1638.2	1561.0	1424.3	1287.8	1169.5	1077.1	1013.9	954.4	896.2	834.2	764.1
47.5°	1488.1	1435.8	1318.0	1178.1	1068.7	985.6	924.5	875.8	826.6	764.7	703.1
50°	1383.9	1350.4	1236.5	1108.7	1004.4	927.9	865.2	819.7	778.6	719.1	664.1
52.5°	1272.6	1254.7	1158.6	1036.4	935.6	860.5	807.1	766.0	724.5	675.1	623.6
55°	1103.0	1112.5	1030.9	925.3	830.4	767.2	718.5	684.4	649.0	607.2	567.4
57.5°	929.8	964.4	909.7	816.9	728.0	669.6	632.9	604.1	574.4	539.8	505.7
60°	826.0	855.1	824.1	742.5	664.7	610.4	576.2	554.1	524.3	492.7	466.8
62.5°	724.8	756.0	737.6	671.7	599.4	552.7	522.5	501.9	479.8	452.3	425.3
65°	597.7	617.9	609.1	563.6	512.3	472.5	444.7	429.4	409.2	389.0	365.0
67.5°	457.8	496.9	491.7	467.5	423.3	392.1	373.9	360.5	342.1	327.0	310.7
70°	376.4	412.4	411.8	392.1	368.1	339.0	326.4	315.0	298.5	284.0	270.7
72.5°	308.0	341.0	345.9	330.9	314.5	292.5	280.4	272.5	256.5	246.5	235.8
75°	215.7	239.7	246.1	246.1	238.4	227.0	216.3	211.3	199.9	191.0	184.7
77.5°	141.4	156.6	166.4	168.7	169.9	166.1	157.2	153.7	145.0	141.8	135.7
80°	99.9	110.0	121.4	125.2	128.4	127.1	123.3	120.8	112.6	109.4	106.9
82.5°	69.1	74.6	84.0	92.4	91.4	94.7	91.4	89.4	83.3	82.1	79.5
85°	36.0	36.7	37.9	43.6	46.8	48.1	48.7	47.5	45.6	45.6	41.1
87.5°	15.5	14.7	15.4	15.0	15.1	16.6	17.7	17.7	16.7	15.6	14.6
90°	17.0	15.4	13.7	11.7	9.5	7.3	5.0	2.8	5.0	7.3	9.5
92.5°	16.2	14.6	13.0	12.1	12.0	11.9	11.7	11.6	11.7	11.9	12.0
95°	19.8	19.6	19.4	22.8	29.8	36.7	43.6	50.6	43.6	36.7	29.8
97.5°	69.9	92.8	115.6	124.8	120.5	116.2	111.9	107.5	111.9	116.2	120.5
100°	97.0	125.2	153.4	165.7	162.0	158.4	154.6	151.0	154.6	158.4	162.0
102.5°	202.5	206.2	209.8	210.3	207.6	204.9	202.2	199.6	202.2	204.9	207.6
105°	285.1	284.2	283.1	281.9	280.7	279.5	278.3	277.0	278.3	279.5	280.7
107.5°	355.3	353.9	352.5	351.5	350.9	350.3	349.7	349.0	349.7	350.3	350.9
110°	403.5	402.3	401.0	400.1	399.5	398.9	398.2	397.7	398.2	398.9	399.5



TEST NUMBER: P333009-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	451.1	450.6	450.0	449.2	448.1	446.9	445.9	444.8	445.9	446.9	448.1
115°	519.6	519.8	520.0	519.8	519.1	518.6	517.9	517.3	517.9	518.6	519.1
117.5°	587.5	587.0	586.5	585.9	585.1	584.3	583.4	582.7	583.4	584.3	585.1
120°	630.0	630.3	630.4	630.1	629.3	628.5	627.6	626.9	627.6	628.5	629.3
122.5°	671.0	670.7	670.4	670.0	669.6	669.1	668.6	668.0	668.6	669.1	669.6
125°	729.8	730.2	730.6	730.5	729.6	728.8	728.0	727.1	728.0	728.8	729.6
127.5°	786.4	785.4	784.5	783.9	783.8	783.5	783.3	783.2	783.3	783.5	783.8
130°	821.7	821.1	820.5	820.1	819.8	819.7	819.4	819.2	819.4	819.7	819.8
132.5°	856.0	855.2	854.4	853.8	853.5	853.1	852.7	852.4	852.7	853.1	853.5
135°	903.2	902.4	901.6	901.3	901.4	901.7	901.9	902.1	901.9	901.7	901.4
137.5°	948.7	947.8	946.9	946.4	946.3	946.3	946.2	946.1	946.2	946.3	946.3
140°	977.6	977.2	976.8	976.4	976.0	975.6	975.2	974.8	975.2	975.6	976.0
142.5°	1004.5	1004.2	1004.0	1003.5	1002.7	1002.0	1001.3	1000.5	1001.3	1002.0	1002.7
145°	1042.9	1042.9	1042.9	1042.6	1042.0	1041.4	1040.8	1040.1	1040.8	1041.4	1042.0
147.5°	1076.3	1076.5	1076.7	1076.2	1075.1	1073.9	1072.8	1071.6	1072.8	1073.9	1075.1
150°	1097.6	1097.8	1098.0	1097.7	1096.9	1096.1	1095.3	1094.5	1095.3	1096.1	1096.9
152.5°	1115.6	1116.0	1116.3	1116.2	1115.6	1114.9	1114.3	1113.6	1114.3	1114.9	1115.6
155°	1139.9	1140.5	1141.1	1141.3	1141.1	1140.9	1140.7	1140.5	1140.7	1140.9	1141.1
157.5°	1160.9	1161.5	1162.2	1162.6	1162.8	1162.8	1163.0	1163.1	1163.0	1162.8	1162.8
160°	1173.1	1173.3	1173.5	1173.9	1174.6	1175.1	1175.8	1176.4	1175.8	1175.1	1174.6
162.5°	1184.2	1184.3	1184.6	1185.0	1185.8	1186.6	1187.4	1188.1	1187.4	1186.6	1185.8
165°	1198.5	1198.5	1198.5	1199.0	1200.0	1201.0	1202.1	1203.1	1202.1	1201.0	1200.0
167.5°	1209.7	1209.9	1210.0	1210.6	1211.6	1212.8	1213.8	1214.8	1213.8	1212.8	1211.6
170°	1216.5	1216.2	1216.1	1216.6	1217.8	1219.0	1220.3	1221.5	1220.3	1219.0	1217.8
172.5°	1220.9	1220.7	1220.4	1221.0	1222.2	1223.4	1224.6	1225.9	1224.6	1223.4	1222.2
175°	1225.7	1225.4	1225.3	1225.7	1227.0	1228.2	1229.5	1230.7	1229.5	1228.2	1227.0
177.5°	1228.5	1228.2	1227.9	1228.3	1229.5	1230.6	1231.8	1232.9	1231.8	1230.6	1229.5
180°	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7



TEST NUMBER: P333009-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1541.5	1536.4	1529.9	1522.3	1513.1	1505.1	1501.5	1504.6	1506.1	1502.1	1501.5
5°	1494.5	1478.8	1466.1	1447.2	1431.9	1419.3	1410.5	1406.7	1407.9	1397.8	1395.3
7.5°	1441.9	1423.1	1402.3	1379.8	1358.8	1340.2	1330.5	1325.2	1314.5	1309.9	1302.2
10°	1407.9	1382.6	1362.4	1335.8	1311.8	1289.7	1278.9	1270.0	1259.3	1254.2	1243.5
12.5°	1373.0	1343.6	1321.4	1293.8	1269.2	1242.6	1232.3	1215.9	1199.0	1188.4	1174.6
15°	1323.8	1288.4	1261.2	1228.3	1199.2	1168.9	1141.6	1111.3	1099.9	1075.9	1061.9
17.5°	1266.2	1230.3	1196.7	1152.5	1107.6	1069.9	1040.9	1011.9	994.4	979.1	972.0
20°	1228.3	1195.4	1148.6	1097.3	1047.4	1005.7	982.2	963.3	944.3	933.6	926.0
22.5°	1192.4	1150.3	1096.0	1040.7	990.7	958.1	938.3	918.8	903.3	893.1	883.0
25°	1132.2	1077.1	1019.5	956.3	922.2	893.7	872.2	856.3	846.9	833.6	828.5
27.5°	1070.3	1003.6	940.2	897.6	862.1	836.0	817.3	805.4	793.4	784.9	778.3
30°	1022.7	955.1	898.1	857.6	821.6	800.1	784.9	771.0	761.5	754.6	749.5
32.5°	975.7	908.0	860.2	816.7	788.2	767.2	751.0	740.6	733.2	724.2	721.1
35°	907.6	847.6	805.8	766.6	737.4	718.5	705.8	695.1	688.8	686.3	684.4
37.5°	842.2	793.0	748.1	716.0	690.1	675.1	660.2	654.9	650.5	646.0	648.1
40°	800.7	754.6	714.7	680.6	659.7	643.3	634.4	628.0	624.2	624.2	624.2
42.5°	764.8	719.6	680.8	650.2	629.3	615.4	605.5	600.2	599.0	598.5	601.5
45°	709.0	667.3	628.0	602.8	585.0	571.2	565.5	561.0	561.0	563.6	564.2
47.5°	653.7	614.7	583.1	554.8	538.6	529.9	525.0	522.7	522.9	525.5	528.4
50°	619.8	581.2	550.2	525.0	509.8	501.5	497.1	495.9	497.1	497.1	501.5
52.5°	582.9	548.3	517.8	496.6	479.4	471.7	469.3	467.5	468.3	470.3	472.2
55°	528.8	497.7	468.7	448.5	435.8	430.7	425.0	425.6	424.4	425.6	425.6
57.5°	474.5	446.6	419.6	403.5	392.4	385.1	378.8	380.6	378.7	378.5	377.5
60°	439.6	409.2	387.7	373.2	360.5	354.2	348.5	349.7	347.8	346.6	344.0
62.5°	401.6	376.4	355.8	341.8	331.7	324.3	318.6	317.3	313.0	308.6	303.1
65°	346.6	325.7	307.4	294.1	284.6	278.9	274.5	270.7	261.2	251.1	246.1
67.5°	293.1	278.1	260.9	249.7	242.0	234.6	226.1	219.6	210.7	205.2	202.0
70°	258.6	244.2	229.6	218.8	210.6	203.7	194.2	189.7	183.4	180.9	177.8
72.5°	225.8	212.2	198.8	189.0	180.2	174.8	167.4	163.0	160.2	159.1	156.0
75°	175.9	165.1	155.0	146.1	139.2	135.4	132.2	129.0	127.8	122.1	118.9
77.5°	128.3	121.2	114.9	108.5	103.6	101.1	95.0	91.3	89.2	86.5	85.9
80°	99.9	94.9	88.6	84.8	77.8	75.3	72.7	72.1	71.5	70.8	70.2
82.5°	75.2	70.1	63.8	61.5	59.6	58.1	56.6	55.9	55.3	55.7	55.5
85°	37.9	35.4	35.4	34.8	34.1	33.5	32.9	32.9	32.2	32.9	32.2
87.5°	15.0	14.9	15.2	14.5	15.4	15.7	15.4	15.7	16.4	15.7	15.8
90°	11.7	13.7	15.4	17.0	18.6	20.3	21.5	22.7	23.9	25.2	26.0
92.5°	12.1	13.0	14.6	16.2	17.9	19.5	20.8	21.9	23.2	24.4	25.1
95°	22.8	19.4	19.6	19.8	20.0	20.3	21.5	22.7	23.9	25.2	25.9
97.5°	124.8	115.6	92.8	69.9	47.1	24.3	24.4	24.6	24.6	24.8	25.0
100°	165.7	153.4	125.2	97.0	68.8	40.5	37.0	33.5	30.1	26.6	25.0
102.5°	210.3	209.8	206.2	202.5	198.8	195.1	157.6	120.1	82.6	45.1	26.4
105°	281.9	283.1	284.2	285.1	286.1	287.2	289.1	290.9	292.7	294.5	291.8
107.5°	351.5	352.5	353.9	355.3	356.6	358.1	358.9	359.9	360.8	361.6	362.5
110°	400.1	401.0	402.3	403.5	404.7	405.9	406.3	406.8	407.2	407.6	408.1



TEST NUMBER: P333009-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	449.2	450.0	450.6	451.1	451.8	452.3	452.3	452.2	452.1	452.0	452.3
115°	519.8	520.0	519.8	519.6	519.4	519.1	519.6	520.0	520.4	520.8	521.0
117.5°	585.9	586.5	587.0	587.5	588.0	588.4	588.3	588.2	588.1	588.0	588.0
120°	630.1	630.4	630.3	630.0	629.8	629.6	630.0	630.4	630.8	631.2	631.2
122.5°	670.0	670.4	670.7	671.0	671.3	671.6	671.8	672.1	672.3	672.6	672.5
125°	730.5	730.6	730.2	729.8	729.4	729.0	729.6	730.2	730.9	731.5	731.9
127.5°	783.9	784.5	785.4	786.4	787.3	788.3	788.1	788.1	787.9	787.8	787.7
130°	820.1	820.5	821.1	821.7	822.3	822.9	823.1	823.3	823.6	823.7	823.8
132.5°	853.8	854.4	855.2	856.0	856.7	857.5	857.7	857.9	858.2	858.3	858.3
135°	901.3	901.6	902.4	903.2	904.0	904.8	905.2	905.6	906.0	906.5	906.9
137.5°	946.4	946.9	947.8	948.7	949.6	950.5	950.9	951.4	951.8	952.3	952.4
140°	976.4	976.8	977.2	977.6	978.0	978.5	979.1	979.7	980.3	981.0	981.4
142.5°	1003.5	1004.0	1004.2	1004.5	1004.7	1005.0	1005.4	1005.9	1006.3	1006.8	1007.0
145°	1042.6	1042.9	1042.9	1042.9	1042.9	1042.9	1043.1	1043.3	1043.5	1043.7	1044.0
147.5°	1076.2	1076.7	1076.5	1076.3	1076.0	1075.9	1076.0	1076.2	1076.3	1076.5	1076.7
150°	1097.7	1098.0	1097.8	1097.6	1097.4	1097.2	1097.2	1097.2	1097.2	1097.2	1097.3
152.5°	1116.2	1116.3	1116.0	1115.6	1115.2	1114.9	1115.2	1115.6	1115.9	1116.2	1116.3
155°	1141.3	1141.1	1140.5	1139.9	1139.2	1138.6	1139.5	1140.3	1141.1	1141.9	1142.0
157.5°	1162.6	1162.2	1161.5	1160.9	1160.2	1159.4	1160.5	1161.6	1162.6	1163.7	1163.7
160°	1173.9	1173.5	1173.3	1173.1	1172.9	1172.7	1173.9	1175.1	1176.4	1177.6	1177.6
162.5°	1185.0	1184.6	1184.3	1184.2	1183.9	1183.8	1184.9	1186.2	1187.4	1188.7	1188.6
165°	1199.0	1198.5	1198.5	1198.5	1198.5	1198.5	1200.1	1201.7	1203.4	1205.0	1204.9
167.5°	1210.6	1210.0	1209.9	1209.7	1209.7	1209.5	1211.3	1213.1	1214.9	1216.7	1216.6
170°	1216.6	1216.1	1216.2	1216.5	1216.6	1216.9	1218.5	1220.1	1221.8	1223.4	1223.2
172.5°	1221.0	1220.4	1220.7	1220.9	1221.1	1221.3	1222.9	1224.6	1226.2	1227.8	1227.6
175°	1225.7	1225.3	1225.4	1225.7	1225.9	1226.1	1227.9	1229.8	1231.6	1233.4	1233.1
177.5°	1228.3	1227.9	1228.2	1228.5	1228.9	1229.2	1230.5	1231.8	1233.1	1234.5	1234.1
180°	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7



TEST NUMBER: P333009-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1498.5	1499.5	1496.0	1494.9	1496.0	1499.5	1498.5	1501.5	1502.1	1506.1	1504.6
5°	1390.2	1388.9	1385.8	1386.4	1385.8	1388.9	1390.2	1395.3	1397.8	1407.9	1406.7
7.5°	1297.6	1292.7	1294.0	1289.0	1294.0	1292.7	1297.6	1302.2	1309.9	1314.5	1325.2
10°	1241.0	1234.0	1228.3	1223.2	1228.3	1234.0	1241.0	1243.5	1254.2	1259.3	1270.0
12.5°	1163.6	1157.5	1149.9	1151.4	1149.9	1157.5	1163.6	1174.6	1188.4	1199.0	1215.9
15°	1053.7	1044.3	1029.0	1030.9	1029.0	1044.3	1053.7	1061.9	1075.9	1099.9	1111.3
17.5°	960.8	960.8	953.9	955.5	953.9	960.8	960.8	972.0	979.1	994.4	1011.9
20°	912.7	908.2	908.9	907.0	908.9	908.2	912.7	926.0	933.6	944.3	963.3
22.5°	879.2	873.9	869.4	865.5	869.4	873.9	879.2	883.0	893.1	903.3	918.8
25°	822.8	819.0	813.4	812.1	813.4	819.0	822.8	828.5	833.6	846.9	856.3
27.5°	773.2	772.5	770.2	767.3	770.2	772.5	773.2	778.3	784.9	793.4	805.4
30°	744.4	743.1	741.9	740.0	741.9	743.1	744.4	749.5	754.6	761.5	771.0
32.5°	718.7	717.9	716.6	716.8	716.6	717.9	718.7	721.1	724.2	733.2	740.6
35°	681.8	681.2	679.9	679.3	679.9	681.2	681.8	684.4	686.3	688.8	695.1
37.5°	647.5	649.0	648.3	648.2	648.3	649.0	647.5	648.1	646.0	650.5	654.9
40°	623.6	624.2	625.5	624.9	625.5	624.2	623.6	624.2	624.2	624.2	628.0
42.5°	603.9	604.0	605.8	603.6	605.8	604.0	603.9	601.5	598.5	599.0	600.2
45°	568.6	572.4	571.8	571.8	571.8	572.4	568.6	564.2	563.6	561.0	561.0
47.5°	530.0	533.3	534.2	534.1	534.2	533.3	530.0	528.4	525.5	522.9	522.7
50°	504.7	503.4	505.3	504.7	505.3	503.4	504.7	501.5	497.1	497.1	495.9
52.5°	473.9	474.1	474.0	473.3	474.0	474.1	473.9	472.2	470.3	468.3	467.5
55°	426.3	426.9	425.6	426.3	425.6	426.9	426.3	425.6	425.6	424.4	425.6
57.5°	374.7	371.6	372.9	371.4	372.9	371.6	374.7	377.5	378.5	378.7	380.6
60°	337.8	332.7	331.4	328.9	331.4	332.7	337.8	344.0	346.6	347.8	349.7
62.5°	296.3	292.7	288.4	290.4	288.4	292.7	296.3	303.1	308.6	313.0	317.3
65°	241.0	238.4	236.5	239.1	236.5	238.4	241.0	246.1	251.1	261.2	270.7
67.5°	199.5	198.1	198.1	196.9	198.1	198.1	199.5	202.0	205.2	210.7	219.6
70°	177.8	175.9	175.9	174.6	175.9	175.9	177.8	177.8	180.9	183.4	189.7
72.5°	155.4	153.6	154.1	153.3	154.1	153.6	155.4	156.0	159.1	160.2	163.0
75°	115.1	111.9	111.9	112.6	111.9	111.9	115.1	118.9	122.1	127.8	129.0
77.5°	85.9	85.2	86.1	85.0	86.1	85.2	85.9	85.9	86.5	89.2	91.3
80°	70.2	69.6	68.9	70.8	68.9	69.6	70.2	70.2	70.8	71.5	72.1
82.5°	54.5	54.4	54.3	56.6	54.3	54.4	54.5	55.5	55.7	55.3	55.9
85°	32.9	31.6	32.9	31.6	32.9	31.6	32.9	32.2	32.9	32.2	32.9
87.5°	17.0	16.5	16.1	16.6	16.1	16.5	17.0	15.8	15.7	16.4	15.7
90°	26.4	26.8	27.2	27.6	27.2	26.8	26.4	26.0	25.2	23.9	22.7
92.5°	25.2	25.3	25.3	25.4	25.3	25.3	25.2	25.1	24.4	23.2	21.9
95°	26.1	26.3	26.5	26.7	26.5	26.3	26.1	25.9	25.2	23.9	22.7
97.5°	25.2	25.3	25.6	25.7	25.6	25.3	25.2	25.0	24.8	24.6	24.6
100°	25.2	25.3	25.6	25.7	25.6	25.3	25.2	25.0	26.6	30.1	33.5
102.5°	26.4	26.5	26.5	26.5	26.5	26.5	26.4	26.4	45.1	82.6	120.1
105°	284.4	277.0	269.7	262.4	269.7	277.0	284.4	291.8	294.5	292.7	290.9
107.5°	363.3	364.1	364.8	365.6	364.8	364.1	363.3	362.5	361.6	360.8	359.9
110°	408.7	409.3	410.0	410.5	410.0	409.3	408.7	408.1	407.6	407.2	406.8



TEST NUMBER: P333009-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	453.1	453.9	454.7	455.4	454.7	453.9	453.1	452.3	452.0	452.1	452.2
115°	521.0	521.0	521.0	521.0	521.0	521.0	521.0	521.0	520.8	520.4	520.0
117.5°	587.9	587.8	587.7	587.6	587.7	587.8	587.9	588.0	588.0	588.1	588.2
120°	630.8	630.4	630.0	629.6	630.0	630.4	630.8	631.2	631.2	630.8	630.4
122.5°	672.1	671.7	671.2	670.8	671.2	671.7	672.1	672.5	672.6	672.3	672.1
125°	732.1	732.3	732.5	732.7	732.5	732.3	732.1	731.9	731.5	730.9	730.2
127.5°	787.5	787.3	787.2	787.0	787.2	787.3	787.5	787.7	787.8	787.9	788.1
130°	823.8	823.8	823.8	823.8	823.8	823.8	823.8	823.8	823.7	823.6	823.3
132.5°	858.2	858.0	857.9	857.7	857.9	858.0	858.2	858.3	858.3	858.2	857.9
135°	907.3	907.7	908.1	908.5	908.1	907.7	907.3	906.9	906.5	906.0	905.6
137.5°	952.4	952.2	952.0	952.0	952.0	952.2	952.4	952.4	952.3	951.8	951.4
140°	981.5	981.8	981.9	982.1	981.9	981.8	981.5	981.4	981.0	980.3	979.7
142.5°	1007.1	1007.1	1007.2	1007.2	1007.2	1007.1	1007.1	1007.0	1006.8	1006.3	1005.9
145°	1044.4	1044.8	1045.3	1045.7	1045.3	1044.8	1044.4	1044.0	1043.7	1043.5	1043.3
147.5°	1076.9	1077.1	1077.3	1077.5	1077.3	1077.1	1076.9	1076.7	1076.5	1076.3	1076.2
150°	1097.5	1097.7	1098.0	1098.1	1098.0	1097.7	1097.5	1097.3	1097.2	1097.2	1097.2
152.5°	1116.2	1116.0	1115.9	1115.8	1115.9	1116.0	1116.2	1116.3	1116.2	1115.9	1115.6
155°	1141.4	1140.7	1140.2	1139.6	1140.2	1140.7	1141.4	1142.0	1141.9	1141.1	1140.3
157.5°	1162.6	1161.6	1160.5	1159.4	1160.5	1161.6	1162.6	1163.7	1163.7	1162.6	1161.6
160°	1176.4	1175.1	1173.9	1172.7	1173.9	1175.1	1176.4	1177.6	1177.6	1176.4	1175.1
162.5°	1187.2	1185.8	1184.4	1183.0	1184.4	1185.8	1187.2	1188.6	1188.7	1187.4	1186.2
165°	1203.1	1201.2	1199.4	1197.5	1199.4	1201.2	1203.1	1204.9	1205.0	1203.4	1201.7
167.5°	1214.6	1212.5	1210.5	1208.4	1210.5	1212.5	1214.6	1216.6	1216.7	1214.9	1213.1
170°	1221.1	1219.1	1217.1	1215.0	1217.1	1219.1	1221.1	1223.2	1223.4	1221.8	1220.1
172.5°	1225.3	1223.1	1220.9	1218.7	1220.9	1223.1	1225.3	1227.6	1227.8	1226.2	1224.6
175°	1230.7	1228.2	1225.7	1223.3	1225.7	1228.2	1230.7	1233.1	1233.4	1231.6	1229.8
177.5°	1232.2	1230.2	1228.2	1226.3	1228.2	1230.2	1232.2	1234.1	1234.5	1233.1	1231.8
180°	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7



TEST NUMBER: P333009-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1501.5	1505.1	1513.1	1522.3	1529.9	1536.4	1541.5	1548.6	1555.1	1564.2	1572.9
5°	1410.5	1419.3	1431.9	1447.2	1466.1	1478.8	1494.5	1508.5	1528.8	1549.0	1568.6
7.5°	1330.5	1340.2	1358.8	1379.8	1402.3	1423.1	1441.9	1466.3	1493.2	1522.7	1555.5
10°	1278.9	1289.7	1311.8	1335.8	1362.4	1382.6	1407.9	1437.0	1467.4	1503.4	1543.9
12.5°	1232.3	1242.6	1269.2	1293.8	1321.4	1343.6	1373.0	1402.6	1443.1	1482.2	1528.2
15°	1141.6	1168.9	1199.2	1228.3	1261.2	1288.4	1323.8	1354.2	1392.7	1447.8	1500.2
17.5°	1040.9	1069.9	1107.6	1152.5	1196.7	1230.3	1266.2	1303.9	1349.9	1406.0	1466.6
20°	982.2	1005.7	1047.4	1097.3	1148.6	1195.4	1228.3	1270.0	1317.5	1378.2	1440.8
22.5°	938.3	958.1	990.7	1040.7	1096.0	1150.3	1192.4	1233.6	1286.1	1346.8	1415.0
25°	872.2	893.7	922.2	956.3	1019.5	1077.1	1132.2	1179.6	1235.2	1295.9	1371.8
27.5°	817.3	836.0	862.1	897.6	940.2	1003.6	1070.3	1124.4	1181.5	1246.7	1322.6
30°	784.9	800.1	821.6	857.6	898.1	955.1	1022.7	1086.0	1143.5	1211.2	1290.3
32.5°	751.0	767.2	788.2	816.7	860.2	908.0	975.7	1045.0	1106.1	1175.3	1252.8
35°	705.8	718.5	737.4	766.6	805.8	847.6	907.6	979.1	1043.6	1117.6	1191.6
37.5°	660.2	675.1	690.1	716.0	748.1	793.0	842.2	915.2	986.7	1054.2	1126.5
40°	634.4	643.3	659.7	680.6	714.7	754.6	800.7	872.2	943.6	1010.7	1083.5
42.5°	605.5	615.4	629.3	650.2	680.8	719.6	764.8	826.6	901.2	966.2	1032.4
45°	565.5	571.2	585.0	602.8	628.0	667.3	709.0	764.1	834.2	896.2	954.4
47.5°	525.0	529.9	538.6	554.8	583.1	614.7	653.7	703.1	764.7	826.6	875.8
50°	497.1	501.5	509.8	525.0	550.2	581.2	619.8	664.1	719.1	778.6	819.7
52.5°	469.3	471.7	479.4	496.6	517.8	548.3	582.9	623.6	675.1	724.5	766.0
55°	425.0	430.7	435.8	448.5	468.7	497.7	528.8	567.4	607.2	649.0	684.4
57.5°	378.8	385.1	392.4	403.5	419.6	446.6	474.5	505.7	539.8	574.4	604.1
60°	348.5	354.2	360.5	373.2	387.7	409.2	439.6	466.8	492.7	524.3	554.1
62.5°	318.6	324.3	331.7	341.8	355.8	376.4	401.6	425.3	452.3	479.8	501.9
65°	274.5	278.9	284.6	294.1	307.4	325.7	346.6	365.0	389.0	409.2	429.4
67.5°	226.1	234.6	242.0	249.7	260.9	278.1	293.1	310.7	327.0	342.1	360.5
70°	194.2	203.7	210.6	218.8	229.6	244.2	258.6	270.7	284.0	298.5	315.0
72.5°	167.4	174.8	180.2	189.0	198.8	212.2	225.8	235.8	246.5	256.5	272.5
75°	132.2	135.4	139.2	146.1	155.0	165.1	175.9	184.7	191.0	199.9	211.3
77.5°	95.0	101.1	103.6	108.5	114.9	121.2	128.3	135.7	141.8	145.0	153.7
80°	72.7	75.3	77.8	84.8	88.6	94.9	99.9	106.9	109.4	112.6	120.8
82.5°	56.6	58.1	59.6	61.5	63.8	70.1	75.2	79.5	82.1	83.3	89.4
85°	32.9	33.5	34.1	34.8	35.4	35.4	37.9	41.1	45.6	45.6	47.5
87.5°	15.4	15.7	15.4	14.5	15.2	14.9	15.0	14.6	15.6	16.7	17.7
90°	21.5	20.3	18.6	17.0	15.4	13.7	11.7	9.5	7.3	5.0	2.8
92.5°	20.8	19.5	17.9	16.2	14.6	13.0	12.1	12.0	11.9	11.7	11.6
95°	21.5	20.3	20.0	19.8	19.6	19.4	22.8	29.8	36.7	43.6	50.6
97.5°	24.4	24.3	47.1	69.9	92.8	115.6	124.8	120.5	116.2	111.9	107.5
100°	37.0	40.5	68.8	97.0	125.2	153.4	165.7	162.0	158.4	154.6	151.0
102.5°	157.6	195.1	198.8	202.5	206.2	209.8	210.3	207.6	204.9	202.2	199.6
105°	289.1	287.2	286.1	285.1	284.2	283.1	281.9	280.7	279.5	278.3	277.0
107.5°	358.9	358.1	356.6	355.3	353.9	352.5	351.5	350.9	350.3	349.7	349.0
110°	406.3	405.9	404.7	403.5	402.3	401.0	400.1	399.5	398.9	398.2	397.7



TEST NUMBER: P333009-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	452.3	452.3	451.8	451.1	450.6	450.0	449.2	448.1	446.9	445.9	444.8
115°	519.6	519.1	519.4	519.6	519.8	520.0	519.8	519.1	518.6	517.9	517.3
117.5°	588.3	588.4	588.0	587.5	587.0	586.5	585.9	585.1	584.3	583.4	582.7
120°	630.0	629.6	629.8	630.0	630.3	630.4	630.1	629.3	628.5	627.6	626.9
122.5°	671.8	671.6	671.3	671.0	670.7	670.4	670.0	669.6	669.1	668.6	668.0
125°	729.6	729.0	729.4	729.8	730.2	730.6	730.5	729.6	728.8	728.0	727.1
127.5°	788.1	788.3	787.3	786.4	785.4	784.5	783.9	783.8	783.5	783.3	783.2
130°	823.1	822.9	822.3	821.7	821.1	820.5	820.1	819.8	819.7	819.4	819.2
132.5°	857.7	857.5	856.7	856.0	855.2	854.4	853.8	853.5	853.1	852.7	852.4
135°	905.2	904.8	904.0	903.2	902.4	901.6	901.3	901.4	901.7	901.9	902.1
137.5°	950.9	950.5	949.6	948.7	947.8	946.9	946.4	946.3	946.3	946.2	946.1
140°	979.1	978.5	978.0	977.6	977.2	976.8	976.4	976.0	975.6	975.2	974.8
142.5°	1005.4	1005.0	1004.7	1004.5	1004.2	1004.0	1003.5	1002.7	1002.0	1001.3	1000.5
145°	1043.1	1042.9	1042.9	1042.9	1042.9	1042.9	1042.6	1042.0	1041.4	1040.8	1040.1
147.5°	1076.0	1075.9	1076.0	1076.3	1076.5	1076.7	1076.2	1075.1	1073.9	1072.8	1071.6
150°	1097.2	1097.2	1097.4	1097.6	1097.8	1098.0	1097.7	1096.9	1096.1	1095.3	1094.5
152.5°	1115.2	1114.9	1115.2	1115.6	1116.0	1116.3	1116.2	1115.6	1114.9	1114.3	1113.6
155°	1139.5	1138.6	1139.2	1139.9	1140.5	1141.1	1141.3	1141.1	1140.9	1140.7	1140.5
157.5°	1160.5	1159.4	1160.2	1160.9	1161.5	1162.2	1162.6	1162.8	1162.8	1163.0	1163.1
160°	1173.9	1172.7	1172.9	1173.1	1173.3	1173.5	1173.9	1174.6	1175.1	1175.8	1176.4
162.5°	1184.9	1183.8	1183.9	1184.2	1184.3	1184.6	1185.0	1185.8	1186.6	1187.4	1188.1
165°	1200.1	1198.5	1198.5	1198.5	1198.5	1198.5	1199.0	1200.0	1201.0	1202.1	1203.1
167.5°	1211.3	1209.5	1209.7	1209.7	1209.9	1210.0	1210.6	1211.6	1212.8	1213.8	1214.8
170°	1218.5	1216.9	1216.6	1216.5	1216.2	1216.1	1216.6	1217.8	1219.0	1220.3	1221.5
172.5°	1222.9	1221.3	1221.1	1220.9	1220.7	1220.4	1221.0	1222.2	1223.4	1224.6	1225.9
175°	1227.9	1226.1	1225.9	1225.7	1225.4	1225.3	1225.7	1227.0	1228.2	1229.5	1230.7
177.5°	1230.5	1229.2	1228.9	1228.5	1228.2	1227.9	1228.3	1229.5	1230.6	1231.8	1232.9
180°	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7



TEST NUMBER: P333009-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1579.5	1584.0	1589.0	1598.7	1606.8	1610.3	1617.4	1622.5	1621.0	1628.0	1640.1
5°	1585.6	1602.7	1622.3	1642.6	1665.3	1684.3	1699.5	1714.7	1726.7	1741.2	1762.8
7.5°	1584.6	1615.0	1648.0	1684.3	1721.6	1753.9	1783.8	1814.1	1841.0	1870.5	1909.1
10°	1580.6	1621.0	1662.2	1709.6	1757.1	1802.0	1842.5	1880.4	1916.4	1955.0	2003.7
12.5°	1576.0	1622.5	1672.3	1729.3	1788.4	1842.5	1890.0	1944.6	1989.8	2039.6	2095.8
15°	1555.9	1618.5	1686.2	1760.2	1831.1	1903.8	1968.9	2036.0	2098.6	2158.1	2228.9
17.5°	1532.9	1605.1	1685.0	1772.3	1857.5	1945.9	2023.2	2107.7	2171.7	2251.5	2317.3
20°	1514.2	1592.0	1677.4	1775.4	1872.2	1970.2	2055.6	2141.6	2213.7	2294.0	2377.5
22.5°	1491.4	1576.8	1669.3	1770.8	1872.2	1979.3	2073.8	2159.3	2248.6	2339.1	2425.1
25°	1454.7	1543.3	1641.3	1752.6	1869.0	1978.4	2079.6	2185.9	2282.0	2380.0	2457.2
27.5°	1409.7	1502.7	1606.0	1720.9	1840.3	1952.3	2071.6	2184.8	2281.5	2375.8	2443.2
30°	1373.7	1471.8	1571.1	1687.5	1811.4	1931.6	2059.4	2172.6	2274.4	2359.2	2397.1
32.5°	1336.8	1429.8	1532.2	1650.0	1777.0	1906.3	2033.1	2148.8	2243.1	2293.9	2294.9
35°	1272.6	1359.9	1466.1	1581.8	1712.1	1852.5	1980.9	2094.8	2152.4	2156.8	2094.8
37.5°	1202.5	1282.5	1382.8	1498.7	1641.4	1781.1	1912.2	1988.1	2007.4	1943.0	1828.4
40°	1152.4	1226.4	1323.2	1442.1	1583.7	1728.0	1847.5	1903.1	1882.9	1778.5	1650.7
42.5°	1099.8	1168.7	1261.9	1379.3	1521.5	1667.2	1769.1	1798.9	1745.3	1624.8	1475.2
45°	1013.9	1077.1	1169.5	1287.8	1424.3	1561.0	1638.2	1622.9	1533.7	1390.8	1223.2
47.5°	924.5	985.6	1068.7	1178.1	1318.0	1435.8	1488.1	1442.3	1315.4	1158.2	1021.8
50°	865.2	927.9	1004.4	1108.7	1236.5	1350.4	1383.9	1314.3	1173.2	1022.1	896.8
52.5°	807.1	860.5	935.6	1036.4	1158.6	1254.7	1272.6	1192.4	1046.8	911.2	800.2
55°	718.5	767.2	830.4	925.3	1030.9	1112.5	1103.0	1000.0	867.8	752.0	664.7
57.5°	632.9	669.6	728.0	816.9	909.7	964.4	929.8	841.9	718.7	623.9	550.2
60°	576.2	610.4	664.7	742.5	824.1	855.1	826.0	730.6	633.1	546.4	484.5
62.5°	522.5	552.7	599.4	671.7	737.6	756.0	724.8	641.4	553.7	479.7	428.3
65°	444.7	472.5	512.3	563.6	609.1	617.9	597.7	512.3	445.9	383.9	348.5
67.5°	373.9	392.1	423.3	467.5	491.7	496.9	457.8	404.2	345.6	307.5	280.8
70°	326.4	339.0	368.1	392.1	411.8	412.4	376.4	333.4	288.4	257.5	237.8
72.5°	280.4	292.5	314.5	330.9	345.9	341.0	308.0	274.1	237.8	214.4	199.9
75°	216.3	227.0	238.4	246.1	246.1	239.7	215.7	190.4	169.5	155.6	151.1
77.5°	157.2	166.1	169.9	168.7	166.4	156.6	141.4	124.8	117.4	110.8	107.5
80°	123.3	127.1	128.4	125.2	121.4	110.0	99.9	93.0	86.0	83.5	82.2
82.5°	91.4	94.7	91.4	92.4	84.0	74.6	69.1	66.7	63.8	62.7	61.5
85°	48.7	48.1	46.8	43.6	37.9	36.7	36.0	35.4	34.1	34.8	33.5
87.5°	17.7	16.6	15.1	15.0	15.4	14.7	15.5	15.8	16.2	15.9	17.2
90°	5.0	7.3	9.5	11.7	13.7	15.4	17.0	18.6	20.3	21.5	22.7
92.5°	11.7	11.9	12.0	12.1	13.0	14.6	16.2	17.9	19.5	20.8	21.9
95°	43.6	36.7	29.8	22.8	19.4	19.6	19.8	20.0	20.3	21.5	22.7
97.5°	111.9	116.2	120.5	124.8	115.6	92.8	69.9	47.1	24.3	24.4	24.6
100°	154.6	158.4	162.0	165.7	153.4	125.2	97.0	68.8	40.5	37.0	33.5
102.5°	202.2	204.9	207.6	210.3	209.8	206.2	202.5	198.8	195.1	157.6	120.1
105°	278.3	279.5	280.7	281.9	283.1	284.2	285.1	286.1	287.2	289.1	290.9
107.5°	349.7	350.3	350.9	351.5	352.5	353.9	355.3	356.6	358.1	358.9	359.9
110°	398.2	398.9	399.5	400.1	401.0	402.3	403.5	404.7	405.9	406.3	406.8



TEST NUMBER: P333009-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	445.9	446.9	448.1	449.2	450.0	450.6	451.1	451.8	452.3	452.3	452.2
115°	517.9	518.6	519.1	519.8	520.0	519.8	519.6	519.4	519.1	519.6	520.0
117.5°	583.4	584.3	585.1	585.9	586.5	587.0	587.5	588.0	588.4	588.3	588.2
120°	627.6	628.5	629.3	630.1	630.4	630.3	630.0	629.8	629.6	630.0	630.4
122.5°	668.6	669.1	669.6	670.0	670.4	670.7	671.0	671.3	671.6	671.8	672.1
125°	728.0	728.8	729.6	730.5	730.6	730.2	729.8	729.4	729.0	729.6	730.2
127.5°	783.3	783.5	783.8	783.9	784.5	785.4	786.4	787.3	788.3	788.1	788.1
130°	819.4	819.7	819.8	820.1	820.5	821.1	821.7	822.3	822.9	823.1	823.3
132.5°	852.7	853.1	853.5	853.8	854.4	855.2	856.0	856.7	857.5	857.7	857.9
135°	901.9	901.7	901.4	901.3	901.6	902.4	903.2	904.0	904.8	905.2	905.6
137.5°	946.2	946.3	946.3	946.4	946.9	947.8	948.7	949.6	950.5	950.9	951.4
140°	975.2	975.6	976.0	976.4	976.8	977.2	977.6	978.0	978.5	979.1	979.7
142.5°	1001.3	1002.0	1002.7	1003.5	1004.0	1004.2	1004.5	1004.7	1005.0	1005.4	1005.9
145°	1040.8	1041.4	1042.0	1042.6	1042.9	1042.9	1042.9	1042.9	1042.9	1043.1	1043.3
147.5°	1072.8	1073.9	1075.1	1076.2	1076.7	1076.5	1076.3	1076.0	1075.9	1076.0	1076.2
150°	1095.3	1096.1	1096.9	1097.7	1098.0	1097.8	1097.6	1097.4	1097.2	1097.2	1097.2
152.5°	1114.3	1114.9	1115.6	1116.2	1116.3	1116.0	1115.6	1115.2	1114.9	1115.2	1115.6
155°	1140.7	1140.9	1141.1	1141.3	1141.1	1140.5	1139.9	1139.2	1138.6	1139.5	1140.3
157.5°	1163.0	1162.8	1162.8	1162.6	1162.2	1161.5	1160.9	1160.2	1159.4	1160.5	1161.6
160°	1175.8	1175.1	1174.6	1173.9	1173.5	1173.3	1173.1	1172.9	1172.7	1173.9	1175.1
162.5°	1187.4	1186.6	1185.8	1185.0	1184.6	1184.3	1184.2	1183.9	1183.8	1184.9	1186.2
165°	1202.1	1201.0	1200.0	1199.0	1198.5	1198.5	1198.5	1198.5	1198.5	1200.1	1201.7
167.5°	1213.8	1212.8	1211.6	1210.6	1210.0	1209.9	1209.7	1209.7	1209.5	1211.3	1213.1
170°	1220.3	1219.0	1217.8	1216.6	1216.1	1216.2	1216.5	1216.6	1216.9	1218.5	1220.1
172.5°	1224.6	1223.4	1222.2	1221.0	1220.4	1220.7	1220.9	1221.1	1221.3	1222.9	1224.6
175°	1229.5	1228.2	1227.0	1225.7	1225.3	1225.4	1225.7	1225.9	1226.1	1227.9	1229.8
177.5°	1231.8	1230.6	1229.5	1228.3	1227.9	1228.2	1228.5	1228.9	1229.2	1230.5	1231.8
180°	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7



TEST NUMBER: P333009-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1646.7	1648.8	1650.3	1655.3	1655.8	1660.4	1655.8
5°	1783.0	1791.8	1805.8	1819.6	1820.9	1829.8	1813.9
7.5°	1935.8	1956.3	1969.0	1991.5	2000.4	2006.0	1996.9
10°	2041.1	2060.0	2093.5	2110.0	2126.5	2128.9	2121.4
12.5°	2142.8	2172.9	2199.3	2230.4	2229.7	2251.9	2243.8
15°	2278.2	2309.2	2345.9	2380.7	2393.3	2393.3	2403.5
17.5°	2374.9	2431.7	2469.6	2497.0	2526.7	2532.0	2528.4
20°	2440.2	2501.5	2542.0	2577.4	2597.6	2603.3	2603.3
22.5°	2488.7	2540.9	2580.5	2612.3	2629.0	2635.7	2633.7
25°	2522.4	2567.2	2591.3	2600.8	2605.2	2604.0	2591.9
27.5°	2476.3	2474.3	2459.1	2430.0	2408.2	2394.8	2379.6
30°	2388.3	2355.4	2317.5	2275.7	2221.9	2180.8	2168.1
32.5°	2257.2	2183.3	2119.1	2049.5	1991.7	1950.6	1933.4
35°	2003.7	1886.7	1791.2	1707.7	1647.0	1609.1	1596.4
37.5°	1702.9	1589.7	1471.4	1390.4	1340.1	1301.8	1287.5
40°	1511.6	1388.3	1285.2	1209.3	1157.5	1120.1	1119.5
42.5°	1337.0	1219.3	1122.3	1067.6	1011.7	987.1	986.9
45°	1094.8	1000.6	918.4	875.4	841.9	821.6	815.9
47.5°	906.5	828.5	773.8	739.5	712.2	699.3	690.9
50°	800.7	732.5	688.8	659.0	643.9	627.4	626.1
52.5°	712.6	657.5	623.5	599.4	580.1	570.2	570.5
55°	599.0	555.3	531.3	512.9	497.7	490.2	487.0
57.5°	504.6	471.8	454.4	437.5	431.1	425.2	423.5
60°	445.9	423.7	407.3	394.0	384.5	382.6	382.0
62.5°	397.4	374.1	362.8	352.5	345.6	342.7	341.5
65°	327.6	310.5	300.4	292.2	289.7	285.3	284.6
67.5°	264.1	253.9	247.2	241.5	238.1	237.8	237.8
70°	225.1	219.4	213.8	210.6	208.7	207.5	207.5
72.5°	191.8	187.6	182.9	181.3	180.9	179.6	179.1
75°	146.1	141.6	142.3	139.2	136.7	133.5	131.6
77.5°	103.6	100.4	99.8	99.4	97.3	96.9	97.9
80°	80.3	77.2	76.5	77.2	76.5	74.6	74.6
82.5°	61.1	58.5	57.8	57.4	56.8	57.4	56.4
85°	32.9	31.6	31.6	31.6	32.9	32.2	31.6
87.5°	16.4	16.2	16.8	16.4	16.5	16.1	16.6
90°	23.9	25.2	26.0	26.4	26.8	27.2	27.6
92.5°	23.2	24.4	25.1	25.2	25.3	25.3	25.4
95°	23.9	25.2	25.9	26.1	26.3	26.5	26.7
97.5°	24.6	24.8	25.0	25.2	25.3	25.6	25.7
100°	30.1	26.6	25.0	25.2	25.3	25.6	25.7
102.5°	82.6	45.1	26.4	26.4	26.5	26.5	26.5
105°	292.7	294.5	291.8	284.4	277.0	269.7	262.4
107.5°	360.8	361.6	362.5	363.3	364.1	364.8	365.6
110°	407.2	407.6	408.1	408.7	409.3	410.0	410.5



TEST NUMBER: P333009-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	452.1	452.0	452.3	453.1	453.9	454.7	455.4
115°	520.4	520.8	521.0	521.0	521.0	521.0	521.0
117.5°	588.1	588.0	588.0	587.9	587.8	587.7	587.6
120°	630.8	631.2	631.2	630.8	630.4	630.0	629.6
122.5°	672.3	672.6	672.5	672.1	671.7	671.2	670.8
125°	730.9	731.5	731.9	732.1	732.3	732.5	732.7
127.5°	787.9	787.8	787.7	787.5	787.3	787.2	787.0
130°	823.6	823.7	823.8	823.8	823.8	823.8	823.8
132.5°	858.2	858.3	858.3	858.2	858.0	857.9	857.7
135°	906.0	906.5	906.9	907.3	907.7	908.1	908.5
137.5°	951.8	952.3	952.4	952.4	952.2	952.0	952.0
140°	980.3	981.0	981.4	981.5	981.8	981.9	982.1
142.5°	1006.3	1006.8	1007.0	1007.1	1007.1	1007.2	1007.2
145°	1043.5	1043.7	1044.0	1044.4	1044.8	1045.3	1045.7
147.5°	1076.3	1076.5	1076.7	1076.9	1077.1	1077.3	1077.5
150°	1097.2	1097.2	1097.3	1097.5	1097.7	1098.0	1098.1
152.5°	1115.9	1116.2	1116.3	1116.2	1116.0	1115.9	1115.8
155°	1141.1	1141.9	1142.0	1141.4	1140.7	1140.2	1139.6
157.5°	1162.6	1163.7	1163.7	1162.6	1161.6	1160.5	1159.4
160°	1176.4	1177.6	1177.6	1176.4	1175.1	1173.9	1172.7
162.5°	1187.4	1188.7	1188.6	1187.2	1185.8	1184.4	1183.0
165°	1203.4	1205.0	1204.9	1203.1	1201.2	1199.4	1197.5
167.5°	1214.9	1216.7	1216.6	1214.6	1212.5	1210.5	1208.4
170°	1221.8	1223.4	1223.2	1221.1	1219.1	1217.1	1215.0
172.5°	1226.2	1227.8	1227.6	1225.3	1223.1	1220.9	1218.7
175°	1231.6	1233.4	1233.1	1230.7	1228.2	1225.7	1223.3
177.5°	1233.1	1234.5	1234.1	1232.2	1230.2	1228.2	1226.3
180°	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7

(END OF REPORT)