

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331291-840

Luminaire Tested: **SA2XXDIP-C485D330U840-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331291-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C485D330U840-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3319.0 lumens  
Efficiency: N/A  
Efficacy: 120.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331291-840  
CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331291-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	96	92	88	93	90	86	83	78	76	73	68	66	64	58	57	55	51
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47	42
3	83	73	66	60	77	69	62	57	60	55	51	52	49	45	45	42	40	36
4	76	65	57	51	71	61	54	48	54	48	44	47	42	39	40	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26	24
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21
8	55	43	35	30	52	41	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12665	12665	12665
5°	12713	12530	12603
10°	12637	12403	12463
15°	12481	12242	12227
20°	12259	12000	11986
25°	12039	11703	11703
30°	11757	11432	11332
35°	11491	11105	10941
40°	11160	10779	10570
45°	10832	10453	10195
50°	10477	10115	9756
55°	10106	9723	9362
60°	9691	9255	8913
65°	9249	8787	8382
70°	8686	8224	7832
75°	7904	7573	7392
80°	7011	6797	6453
85°	5724	5446	4891



TEST NUMBER: P331291-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.8	2.2
10°-20°	207.5	6.3
20°-30°	305.0	9.2
30°-40°	354.3	10.7
40°-50°	354.0	10.7
50°-60°	308.7	9.3
60°-70°	228.2	6.9
70°-80°	129.3	3.9
80°-90°	35.9	1.1
90°-100°	15.1	0.5
100°-110°	55.2	1.7
110°-120°	147.6	4.4
120°-130°	243.6	7.3
130°-140°	259.0	7.8
140°-150°	240.8	7.3
150°-160°	193.6	5.8
160°-170°	124.7	3.8
170°-180°	42.9	1.3
0°-30°	586.3	17.7
0°-40°	940.7	28.3
0°-60°	1603.3	48.3
0°-90°	1996.6	60.2
90°-120°	217.8	6.6
90°-150°	961.2	29.0
90°-180°	1322.0	39.8
0°-180°	3319.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	784	784	784	784	784	
5°	784	781	773	779	778	74
15°	747	742	732	735	732	210
25°	676	669	657	658	657	311
35°	583	575	563	559	555	364
45°	474	469	458	450	446	366
55°	359	354	345	337	333	321
65°	242	237	230	223	219	239
75°	127	125	121	117	118	135
85°	31	30	29	27	26	35
90°	0	4	7	8	9	2
95°	21	11	13	14	14	26
105°	99	104	20	23	25	106
115°	188	193	202	57	27	185
125°	266	270	276	278	279	237
135°	328	334	337	340	339	254
145°	381	381	386	388	387	238
155°	420	417	420	422	420	193
165°	442	440	441	443	441	125
175°	452	450	451	453	450	43
180°	451	451	451	451	451	



TEST NUMBER: P331291-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	788.0	787.3	786.7	786.0	785.3	784.3	782.7	781.3	779.8	778.3	779.7
5°	784.4	783.7	783.0	782.3	781.7	780.4	778.6	776.8	774.9	773.1	774.4
7.5°	777.4	776.4	775.4	774.3	773.3	771.8	769.9	768.1	766.2	764.3	765.7
10°	770.8	769.6	768.4	767.3	766.1	764.5	762.4	760.5	758.5	756.5	757.8
12.5°	761.7	760.7	759.6	758.6	757.6	756.1	754.1	752.0	750.0	748.0	748.9
15°	746.7	745.7	744.7	743.7	742.7	741.0	738.8	736.7	734.5	732.4	733.0
17.5°	727.3	726.4	725.4	724.4	723.4	721.8	719.5	717.3	715.1	712.9	713.7
20°	713.5	712.5	711.4	710.4	709.4	707.8	705.4	703.1	700.7	698.4	698.9
22.5°	699.6	698.2	696.8	695.4	694.0	692.2	689.9	687.7	685.5	683.3	683.4
25°	675.8	674.4	673.1	671.8	670.4	668.3	665.5	662.6	659.7	656.9	657.2
27.5°	648.6	647.4	646.2	645.0	643.8	642.1	639.9	637.5	635.3	633.1	632.6
30°	630.6	629.1	627.8	626.5	625.1	623.2	620.7	618.2	615.7	613.2	612.7
32.5°	611.2	610.2	609.0	607.9	606.9	605.0	602.4	599.8	597.1	594.5	593.6
35°	583.0	581.3	579.7	577.9	576.3	574.1	571.5	568.8	566.0	563.4	562.4
37.5°	551.2	549.7	548.3	546.7	545.2	543.2	540.5	537.9	535.1	532.5	531.2
40°	529.5	528.1	526.7	525.4	524.1	522.1	519.4	516.7	514.0	511.4	509.9
42.5°	508.4	507.0	505.6	504.3	503.0	501.0	498.3	495.6	492.9	490.2	488.6
45°	474.4	473.2	472.0	470.9	469.7	467.9	465.3	462.8	460.3	457.8	456.0
47.5°	440.6	439.5	438.4	437.3	436.2	434.3	431.7	429.1	426.5	423.8	421.9
50°	417.1	416.3	415.4	414.5	413.7	412.1	409.8	407.5	405.1	402.7	400.4
52.5°	394.2	393.0	391.9	390.8	389.7	388.1	385.9	383.6	381.4	379.2	377.3
55°	359.0	358.0	357.0	356.0	355.0	353.5	351.4	349.4	347.4	345.4	343.5
57.5°	323.7	322.9	322.0	321.3	320.5	319.0	316.8	314.6	312.4	310.1	308.1
60°	300.1	299.5	298.8	298.1	297.5	296.0	293.7	291.2	288.9	286.6	284.8
62.5°	277.2	276.2	275.1	274.0	273.0	271.6	269.7	267.9	266.1	264.3	262.6
65°	242.1	241.1	240.0	239.0	238.1	236.7	235.1	233.4	231.7	230.0	228.5
67.5°	206.3	205.5	204.7	203.9	203.1	202.0	200.5	198.9	197.4	195.9	194.8
70°	184.0	183.4	182.7	182.0	181.4	180.3	178.7	177.2	175.7	174.2	173.1
72.5°	161.1	160.5	159.8	159.1	158.4	157.6	156.6	155.6	154.7	153.7	152.5
75°	126.7	126.3	126.0	125.7	125.3	124.8	123.9	123.1	122.3	121.4	120.4
77.5°	95.9	95.3	94.8	94.2	93.6	93.2	92.9	92.5	92.2	91.9	91.4
80°	75.4	75.2	75.1	74.9	74.7	74.5	74.1	73.8	73.5	73.1	72.6
82.5°	56.1	56.0	56.0	56.0	55.9	55.8	55.6	55.4	55.2	55.0	54.4
85°	30.9	30.8	30.6	30.4	30.3	30.1	29.9	29.8	29.6	29.4	28.9
87.5°	10.9	10.8	10.7	10.6	10.5	10.4	10.2	10.1	9.9	9.8	9.4
90°	0.3	1.1	1.9	2.7	3.5	4.2	4.7	5.4	6.0	6.6	6.9
92.5°	6.6	6.6	6.5	6.4	6.3	6.5	6.7	7.0	7.3	7.6	7.8
95°	21.2	18.8	16.5	14.0	11.6	10.7	11.2	11.7	12.2	12.7	13.1
97.5°	42.1	35.3	28.6	21.9	15.1	12.3	13.5	14.6	15.9	17.1	17.4
100°	57.8	47.9	37.9	28.0	18.1	13.6	14.9	16.2	17.4	18.6	19.2
102.5°	75.0	72.9	70.8	68.8	66.7	60.4	50.1	39.8	29.5	19.1	19.9
105°	99.3	101.4	103.6	105.8	108.0	99.2	79.4	59.6	39.7	19.9	20.7
107.5°	126.8	128.7	130.4	132.2	133.9	122.9	99.2	75.4	51.6	27.9	27.1
110°	144.6	146.1	147.7	149.3	150.8	141.0	120.1	99.1	78.1	57.2	49.9



TEST NUMBER: P331291-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	161.4	162.7	164.1	165.4	166.7	164.8	159.7	154.5	149.3	144.1	117.6
115°	187.7	188.9	190.3	191.5	192.7	194.2	196.0	197.8	199.7	201.5	167.8
117.5°	211.4	212.7	214.1	215.5	216.8	218.1	219.4	220.7	221.9	223.2	215.0
120°	228.5	229.6	230.8	231.9	232.9	234.1	235.4	236.7	238.0	239.3	240.2
122.5°	243.2	244.4	245.5	246.6	247.8	249.0	250.4	251.9	253.4	254.8	255.3
125°	265.5	266.4	267.3	268.3	269.2	270.4	271.8	273.2	274.5	275.9	276.4
127.5°	285.6	286.7	287.7	288.8	289.8	290.8	291.9	293.0	294.0	295.0	295.7
130°	298.4	299.6	300.7	301.9	303.1	304.1	304.9	305.7	306.5	307.3	308.0
132.5°	311.5	312.5	313.5	314.5	315.5	316.3	317.1	317.9	318.7	319.5	320.2
135°	328.5	329.6	330.8	331.9	333.2	334.1	334.7	335.4	336.0	336.7	337.4
137.5°	345.7	346.5	347.3	348.1	348.9	349.7	350.4	351.1	351.9	352.6	353.4
140°	356.9	357.5	358.0	358.6	359.2	359.9	360.7	361.5	362.3	363.0	363.8
142.5°	366.3	366.8	367.3	367.9	368.4	369.1	370.0	370.9	371.8	372.7	373.3
145°	381.0	381.0	380.9	380.8	380.7	381.3	382.5	383.8	385.1	386.3	386.8
147.5°	393.9	393.6	393.3	393.0	392.8	393.2	394.5	395.8	397.0	398.2	398.5
150°	402.2	401.7	401.2	400.7	400.2	400.6	401.7	402.9	404.0	405.3	405.7
152.5°	409.3	408.8	408.2	407.6	407.1	407.3	408.4	409.5	410.6	411.7	412.1
155°	419.6	418.9	418.3	417.6	417.0	417.1	418.0	418.8	419.7	420.5	421.0
157.5°	427.6	427.1	426.5	426.0	425.4	425.5	426.1	426.7	427.3	427.9	428.4
160°	432.3	431.9	431.4	431.0	430.6	430.6	431.0	431.4	431.9	432.3	432.7
162.5°	436.5	436.1	435.7	435.2	434.7	434.7	435.0	435.5	435.9	436.3	436.8
165°	442.1	441.7	441.2	440.8	440.4	440.3	440.5	440.7	440.9	441.1	441.6
167.5°	446.3	445.9	445.5	444.9	444.5	444.4	444.6	444.8	445.0	445.2	445.8
170°	448.7	448.2	447.8	447.4	446.9	446.8	446.9	447.1	447.2	447.4	447.9
172.5°	450.2	449.8	449.3	448.9	448.5	448.3	448.5	448.6	448.8	448.9	449.4
175°	452.2	451.7	451.2	450.7	450.2	450.0	450.2	450.3	450.5	450.6	451.1
177.5°	452.5	452.1	451.7	451.3	450.9	450.8	450.8	450.9	450.9	451.0	451.4
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331291-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	781.0	782.3	783.7	784.3	784.0	783.7	783.5	783.2
5°	775.8	777.1	778.4	778.9	778.6	778.2	777.9	777.6
7.5°	767.0	768.3	769.7	770.1	769.8	769.4	769.0	768.7
10°	759.1	760.5	761.8	762.2	761.7	761.2	760.7	760.2
12.5°	749.9	750.8	751.7	752.0	751.6	751.3	750.9	750.5
15°	733.7	734.4	735.0	734.9	734.1	733.3	732.5	731.5
17.5°	714.4	715.2	716.0	715.9	715.1	714.4	713.6	712.8
20°	699.4	699.9	700.4	700.3	699.6	698.9	698.3	697.6
22.5°	683.5	683.6	683.7	683.6	683.2	682.8	682.4	682.0
25°	657.6	657.9	658.2	658.2	657.9	657.6	657.2	656.9
27.5°	632.1	631.6	631.1	630.5	629.7	628.8	628.0	627.2
30°	612.2	611.7	611.2	610.6	609.9	609.3	608.5	607.8
32.5°	592.7	591.8	590.9	590.1	589.4	588.8	588.0	587.3
35°	561.4	560.4	559.4	558.5	557.6	556.7	555.9	555.1
37.5°	530.0	528.8	527.6	526.4	525.6	524.8	524.0	523.3
40°	508.4	506.9	505.3	504.2	503.5	502.9	502.2	501.5
42.5°	487.0	485.3	483.6	482.4	481.4	480.5	479.6	478.6
45°	454.1	452.3	450.4	449.2	448.5	447.9	447.2	446.5
47.5°	420.0	418.0	416.1	414.7	413.6	412.7	411.7	410.7
50°	398.1	395.7	393.3	391.7	390.9	390.1	389.2	388.4
52.5°	375.4	373.3	371.4	369.9	368.8	367.7	366.6	365.5
55°	341.4	339.4	337.4	336.0	335.1	334.3	333.5	332.6
57.5°	306.2	304.2	302.3	300.9	300.2	299.6	299.0	298.3
60°	282.9	281.0	279.2	278.0	277.5	277.0	276.5	276.0
62.5°	260.8	259.1	257.4	256.3	255.6	255.0	254.4	253.7
65°	227.0	225.5	224.0	222.8	222.0	221.2	220.4	219.4
67.5°	193.6	192.4	191.3	190.4	189.7	188.9	188.3	187.6
70°	171.9	170.7	169.6	168.6	167.9	167.2	166.6	165.9
72.5°	151.4	150.2	149.1	148.1	147.6	147.0	146.5	146.0
75°	119.4	118.5	117.4	117.0	117.4	117.8	118.1	118.5
77.5°	90.9	90.4	89.9	89.4	88.9	88.5	88.0	87.5
80°	72.1	71.6	71.2	70.7	70.4	70.1	69.7	69.4
82.5°	53.8	53.1	52.5	52.1	52.1	52.0	51.9	51.9
85°	28.4	27.9	27.4	27.1	26.9	26.8	26.6	26.4
87.5°	9.1	8.8	8.5	8.2	8.1	8.0	7.9	7.8
90°	7.3	7.6	8.0	8.3	8.4	8.5	8.7	8.8
92.5°	8.0	8.2	8.3	8.5	8.6	8.7	8.7	8.8
95°	13.4	13.8	14.1	14.3	14.2	14.1	14.1	14.0
97.5°	17.7	17.9	18.2	18.4	18.5	18.6	18.7	18.8
100°	19.8	20.4	20.9	21.3	21.4	21.6	21.7	21.9
102.5°	20.6	21.4	22.1	22.6	22.8	23.0	23.2	23.4
105°	21.5	22.3	23.1	23.6	23.9	24.2	24.5	24.8
107.5°	26.3	25.4	24.6	24.3	24.6	24.9	25.2	25.5
110°	42.6	35.3	28.1	24.6	24.9	25.2	25.5	25.8





TEST NUMBER: P331291-840

CATALOG NUMBER: SA2XXDIP-C485D330U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	91.2	64.7	38.3	25.1	25.3	25.5	25.9	26.1
115°	134.3	100.7	67.1	47.7	42.4	37.3	32.0	26.8
117.5°	206.9	198.7	190.7	178.0	160.9	143.7	126.5	109.4
120°	241.1	242.0	242.8	238.3	228.5	218.7	208.9	199.1
122.5°	255.8	256.3	256.8	256.1	254.3	252.4	250.4	248.5
125°	276.9	277.4	277.9	278.3	278.5	278.7	278.9	279.1
127.5°	296.5	297.2	297.9	298.3	298.4	298.4	298.4	298.5
130°	308.8	309.6	310.4	310.8	310.7	310.6	310.6	310.5
132.5°	320.9	321.5	322.2	322.6	322.4	322.4	322.3	322.2
135°	338.1	338.8	339.5	339.8	339.7	339.5	339.4	339.2
137.5°	354.1	354.8	355.5	355.7	355.5	355.3	355.0	354.8
140°	364.4	365.1	365.7	365.9	365.5	365.2	364.8	364.4
142.5°	374.0	374.6	375.2	375.3	374.9	374.6	374.2	373.8
145°	387.3	387.8	388.3	388.4	388.0	387.7	387.3	386.9
147.5°	398.9	399.3	399.7	399.7	399.4	399.1	398.8	398.5
150°	406.1	406.5	407.0	407.0	406.7	406.3	405.9	405.6
152.5°	412.6	413.0	413.4	413.4	412.9	412.5	412.0	411.5
155°	421.4	421.8	422.3	422.2	421.6	421.1	420.5	419.9
157.5°	428.9	429.4	429.8	429.8	429.2	428.7	428.1	427.6
160°	433.2	433.6	434.0	434.0	433.5	433.0	432.5	432.0
162.5°	437.2	437.7	438.2	438.2	437.5	436.9	436.3	435.7
165°	442.1	442.6	443.1	443.1	442.6	442.1	441.6	441.1
167.5°	446.3	446.8	447.3	447.2	446.6	445.9	445.2	444.5
170°	448.4	448.9	449.4	449.3	448.7	448.0	447.4	446.7
172.5°	449.9	450.4	450.9	450.9	450.2	449.6	448.9	448.3
175°	451.6	452.1	452.6	452.5	451.8	451.1	450.3	449.6
177.5°	451.8	452.2	452.6	452.5	452.0	451.5	451.0	450.5
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2

(END OF REPORT)