

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331294-840

Luminaire Tested: **SA2XXDIP-C485D530U840-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331294-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D530U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4301.2 lumens
Efficiency: N/A
Efficacy: 131.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331294-840
CATALOG NUMBER: SA2XXDIP-C485D530U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331294-840

CATALOG NUMBER: SA2XXDIP-C485D530U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	50				
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49	43				
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	37				
3	82	73	66	61	76	68	62	57	58	53	50	49	46	43	40	38	36	32				
4	76	65	57	52	70	61	54	49	52	47	43	44	40	37	36	34	31	28				
5	70	58	50	45	64	54	47	42	47	41	37	40	36	32	33	30	28	25				
6	64	52	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22				
7	60	48	40	34	55	44	37	33	38	33	29	33	29	26	28	25	22	20				
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	22	20	18				
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	21	18	16				
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	17	15				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15844	15844	15844	15844
5°	17763	15948	14131	15948
10°	20354	15816	12231	15816
15°	22519	15527	10805	15527
20°	22175	15216	9850	15216
25°	19996	14801	9246	14801
30°	16524	14139	8804	14139
35°	12043	13448	8489	13448
40°	9619	12631	8315	12631
45°	8405	11686	8079	11686
50°	7902	10771	7920	10771
55°	7282	9841	7707	9841
60°	6675	8854	7379	8854
65°	6082	7966	7060	7966
70°	5519	7105	6590	7105
75°	4897	6145	5833	6145
80°	4203	5086	4695	5086
85°	3779	3779	2779	3779



TEST NUMBER: P331294-840

CATALOG NUMBER: SA2XXDIP-C485D530U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	2.2
10°-20°	271.7	6.3
20°-30°	394.3	9.2
30°-40°	416.1	9.7
40°-50°	368.4	8.6
50°-60°	294.0	6.8
60°-70°	199.8	4.6
70°-80°	102.5	2.4
80°-90°	26.5	0.6
90°-100°	24.3	0.6
100°-110°	89.1	2.1
110°-120°	238.2	5.5
120°-130°	393.1	9.1
130°-140°	418.1	9.7
140°-150°	388.6	9.0
150°-160°	312.4	7.3
160°-170°	201.3	4.7
170°-180°	69.3	1.6
0°-30°	759.5	17.7
0°-40°	1175.6	27.3
0°-60°	1838.0	42.7
0°-90°	2166.8	50.4
90°-120°	351.5	8.2
90°-150°	1551.4	36.1
90°-180°	2134.0	49.6
0°-180°	4301.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	981	981	981	981	981	
5°	1096	984	872	984	1096	109
15°	1347	929	646	929	1347	372
25°	1122	831	519	831	1122	507
35°	611	682	431	682	611	397
45°	368	512	354	512	368	289
55°	259	350	274	350	259	232
65°	159	208	185	208	159	158
75°	78	98	94	98	78	84
85°	20	20	15	20	20	23
90°	14	0	14	0	14	7
95°	23	34	23	34	23	21
105°	40	160	40	160	40	42
115°	43	303	43	303	43	108
125°	451	428	451	428	451	390
135°	548	530	548	530	548	422
145°	624	615	624	615	624	391
155°	678	677	678	677	678	313
165°	712	714	712	714	712	201
175°	726	730	726	730	726	69
180°	728	728	728	728	728	



TEST NUMBER: P331294-840

CATALOG NUMBER: SA2XXDIP-C485D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1026.6	1026.9	1027.4	1022.7	1022.1	1022.1	1017.8	1014.2	1010.0	1004.2	1004.8
5°	1096.0	1100.1	1101.7	1097.1	1090.4	1089.5	1083.2	1072.6	1062.8	1054.9	1049.2
7.5°	1178.8	1180.4	1176.8	1170.8	1165.8	1156.7	1144.8	1133.1	1116.7	1101.7	1090.6
10°	1241.5	1243.9	1237.4	1228.7	1221.5	1211.0	1193.7	1175.9	1154.5	1133.7	1117.1
12.5°	1289.2	1294.8	1286.6	1285.5	1273.1	1258.7	1238.0	1229.0	1198.8	1169.9	1152.1
15°	1347.2	1346.8	1347.6	1340.4	1331.3	1329.1	1307.2	1283.4	1240.8	1223.9	1194.4
17.5°	1330.4	1336.2	1338.8	1338.7	1338.5	1337.1	1330.0	1315.0	1293.6	1266.2	1232.2
20°	1290.6	1298.1	1299.3	1308.0	1312.8	1319.3	1321.9	1317.8	1304.5	1281.5	1252.1
22.5°	1229.0	1231.1	1234.7	1248.2	1258.8	1274.9	1283.2	1297.2	1292.1	1280.9	1256.4
25°	1122.4	1118.6	1131.8	1138.6	1163.1	1188.7	1207.2	1227.6	1245.7	1256.7	1249.5
27.5°	994.3	988.7	1008.5	1026.4	1046.3	1074.1	1102.9	1136.9	1165.2	1200.6	1212.7
30°	886.3	889.7	908.6	927.8	958.0	997.1	1029.6	1066.9	1107.3	1146.9	1174.4
32.5°	769.8	782.8	794.8	824.3	850.8	894.5	942.1	988.8	1039.2	1084.1	1126.7
35°	611.0	626.0	642.7	664.2	701.5	744.9	791.2	854.2	922.9	984.3	1034.9
37.5°	514.2	511.9	521.4	536.9	567.1	602.2	655.5	717.8	798.6	870.8	942.1
40°	456.4	454.8	461.6	475.9	499.0	524.6	571.4	626.0	701.1	789.3	874.2
42.5°	416.5	417.4	421.2	431.3	447.1	468.2	503.2	549.8	618.4	701.6	792.7
45°	368.1	370.7	374.9	379.8	388.8	406.2	425.8	459.0	513.3	582.7	672.5
47.5°	333.3	333.4	337.5	341.8	347.2	357.0	373.0	393.8	432.1	488.7	565.8
50°	314.6	311.8	314.9	318.3	324.0	330.7	341.3	360.9	386.6	432.2	496.7
52.5°	291.6	291.6	294.4	295.7	300.7	307.5	317.2	330.7	354.0	389.7	442.7
55°	258.7	260.6	262.2	264.4	268.9	273.8	281.3	290.4	308.5	335.3	374.5
57.5°	227.8	228.4	229.9	234.2	237.1	241.6	248.7	257.0	268.7	288.6	318.1
60°	206.7	206.7	209.6	211.6	215.3	219.8	225.5	233.5	244.0	260.2	284.0
62.5°	187.3	187.0	188.2	191.4	194.2	198.4	204.1	210.9	220.8	235.2	254.7
65°	159.2	158.4	160.7	161.4	164.4	168.5	173.1	180.3	188.2	198.7	216.1
67.5°	132.0	132.9	134.1	135.5	137.2	141.6	144.6	149.7	156.3	165.1	176.9
70°	116.9	116.9	116.9	118.1	120.3	122.6	125.6	129.8	136.1	143.7	154.2
72.5°	100.0	101.2	102.4	101.8	104.6	105.9	109.6	111.9	118.1	122.9	132.2
75°	78.5	78.5	78.5	80.3	81.5	82.6	84.8	87.2	90.2	96.1	101.1
77.5°	58.6	58.4	58.8	59.2	60.4	61.8	62.4	64.5	67.3	70.1	74.2
80°	45.2	46.0	46.4	47.2	47.2	47.9	48.3	50.9	52.8	54.7	57.4
82.5°	35.0	35.1	35.2	35.3	35.6	36.2	37.1	38.0	38.6	40.2	42.2
85°	20.4	20.0	20.0	20.7	20.4	20.4	21.1	21.9	21.9	22.2	23.4
87.5°	10.7	10.6	10.9	10.5	10.5	10.7	10.6	10.2	10.4	10.6	10.7
90°	14.2	14.0	13.7	13.5	13.3	12.9	12.3	11.7	11.1	10.5	9.6
92.5°	14.2	14.1	13.9	13.8	13.6	13.4	13.1	12.8	12.5	12.2	11.7
95°	22.6	22.8	22.9	23.0	23.1	22.9	22.3	21.7	21.1	20.6	19.7
97.5°	30.3	30.1	30.0	29.8	29.7	29.4	28.9	28.5	28.0	27.5	25.7
100°	35.3	35.0	34.8	34.6	34.3	33.8	32.8	31.9	31.0	30.0	28.1
102.5°	37.9	37.5	37.2	36.9	36.6	35.7	34.5	33.3	32.1	30.9	47.6
105°	40.1	39.6	39.1	38.7	38.2	37.3	36.1	34.7	33.4	32.1	64.1
107.5°	41.2	40.7	40.3	39.8	39.4	39.8	41.1	42.4	43.7	45.0	83.3
110°	41.6	41.2	40.7	40.2	39.8	45.3	57.1	68.8	80.5	92.2	126.0



TEST NUMBER: P331294-840

CATALOG NUMBER: SA2XXDIP-C485D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	42.0	41.7	41.3	40.9	40.6	61.7	104.4	147.1	189.9	232.7	241.0
115°	43.2	51.6	60.1	68.5	77.0	108.3	162.5	216.7	270.9	325.2	322.2
117.5°	176.4	204.2	231.9	259.5	287.3	307.7	320.8	334.0	347.1	360.1	358.2
120°	321.4	337.3	353.1	368.9	384.8	391.9	390.5	389.1	387.7	386.3	384.2
122.5°	401.1	404.2	407.3	410.4	413.4	414.5	413.7	412.8	412.0	411.2	408.9
125°	450.6	450.3	449.9	449.6	449.2	448.6	447.8	447.0	446.2	445.4	443.1
127.5°	481.8	481.7	481.7	481.6	481.5	480.9	479.7	478.5	477.3	476.2	474.4
130°	501.2	501.3	501.4	501.5	501.7	501.1	499.8	498.5	497.3	495.9	494.6
132.5°	520.2	520.3	520.4	520.5	520.6	520.2	519.1	518.0	516.8	515.7	514.4
135°	547.5	547.9	548.1	548.3	548.6	548.1	546.8	545.7	544.5	543.3	542.3
137.5°	572.6	573.0	573.3	573.7	574.1	573.8	572.6	571.5	570.4	569.2	567.9
140°	588.1	588.8	589.4	589.9	590.5	590.3	589.2	588.1	587.1	586.0	584.7
142.5°	603.3	603.9	604.5	605.1	605.7	605.5	604.5	603.6	602.6	601.7	600.2
145°	624.5	625.1	625.7	626.3	626.8	626.7	625.9	625.1	624.3	623.5	621.5
147.5°	643.2	643.7	644.2	644.7	645.1	645.1	644.5	643.9	643.3	642.7	640.7
150°	654.6	655.1	655.7	656.3	656.9	656.8	656.1	655.4	654.7	654.0	652.2
152.5°	664.3	665.0	665.8	666.6	667.3	667.4	666.7	666.0	665.3	664.6	662.8
155°	677.7	678.7	679.6	680.5	681.5	681.7	681.0	680.2	679.5	678.8	677.4
157.5°	690.0	690.9	691.9	692.8	693.8	693.8	693.0	692.2	691.4	690.6	689.6
160°	697.2	698.0	698.9	699.7	700.5	700.5	699.8	699.1	698.5	697.8	697.1
162.5°	703.2	704.2	705.2	706.2	707.2	707.3	706.5	705.7	704.9	704.1	703.5
165°	712.0	712.9	713.7	714.5	715.3	715.3	714.5	713.7	712.9	712.0	711.7
167.5°	717.6	718.6	719.7	720.7	721.9	722.0	721.1	720.2	719.4	718.6	718.3
170°	720.9	722.1	723.1	724.1	725.2	725.3	724.5	723.7	722.9	722.1	721.8
172.5°	723.5	724.6	725.6	726.7	727.7	727.8	727.0	726.2	725.4	724.6	724.3
175°	725.7	726.9	728.0	729.2	730.4	730.5	729.7	728.9	728.1	727.3	727.0
177.5°	727.1	727.9	728.7	729.6	730.4	730.5	729.9	729.2	728.6	727.9	727.8
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331294-840

CATALOG NUMBER: SA2XXDIP-C485D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1006.9	1004.5	1003.0	997.6	992.8	988.0	986.4	987.0	980.4	974.1	971.4
5°	1046.2	1038.6	1031.5	1021.3	1009.3	996.0	989.3	984.0	970.8	956.4	948.2
7.5°	1081.4	1070.6	1056.7	1037.6	1020.1	999.3	986.0	974.4	955.0	934.8	922.5
10°	1102.8	1088.0	1070.4	1046.9	1025.4	1000.2	982.5	964.7	942.1	918.0	902.9
12.5°	1121.2	1101.4	1083.9	1053.9	1028.4	996.8	975.8	950.9	927.1	898.4	883.5
15°	1165.0	1128.4	1095.2	1061.3	1030.0	985.8	962.5	928.9	897.6	862.1	845.2
17.5°	1198.8	1157.7	1105.5	1062.4	1025.8	976.9	942.6	902.4	865.4	824.9	801.8
20°	1218.2	1171.0	1114.8	1063.6	1019.8	964.0	926.7	885.6	842.1	796.5	771.6
22.5°	1229.6	1180.1	1124.5	1059.0	1007.7	953.4	906.5	861.4	817.4	768.2	742.0
25°	1233.2	1188.0	1129.1	1055.2	992.6	931.2	874.5	830.8	777.7	731.6	693.6
27.5°	1215.3	1182.9	1126.3	1048.1	975.2	903.3	840.3	790.7	734.6	684.7	646.3
30°	1193.3	1174.4	1119.3	1040.9	961.3	884.0	814.7	758.4	702.7	652.1	612.9
32.5°	1159.2	1155.1	1106.7	1030.7	946.5	859.6	787.8	730.9	669.1	619.5	582.1
35°	1092.2	1110.3	1079.7	1007.7	918.7	824.9	747.1	682.3	618.1	570.6	535.5
37.5°	1002.5	1047.4	1039.5	974.1	881.1	787.0	701.1	633.4	572.3	524.3	489.9
40°	940.6	997.9	1006.2	948.5	854.6	757.7	666.8	599.3	539.7	495.9	461.2
42.5°	874.2	941.2	964.0	917.8	825.7	726.9	636.0	566.1	507.2	464.5	433.8
45°	763.0	851.6	892.7	866.3	777.3	676.2	582.7	511.8	458.3	418.3	394.5
47.5°	658.9	755.8	811.1	801.7	723.5	623.4	531.0	462.9	410.8	378.9	357.6
50°	585.3	684.9	751.6	754.7	684.9	585.7	492.9	428.8	380.9	351.1	333.8
52.5°	521.4	616.4	689.2	705.2	641.8	546.4	458.8	395.1	352.8	325.5	309.9
55°	437.9	518.2	599.0	628.3	577.4	486.9	405.8	349.6	310.0	291.1	277.6
57.5°	364.1	431.0	505.5	538.1	506.6	429.2	353.1	304.4	272.3	255.7	245.3
60°	325.1	377.9	444.2	483.1	456.0	387.0	320.5	274.2	247.8	233.1	223.3
62.5°	288.9	335.7	391.7	427.3	412.5	347.4	288.0	247.0	224.3	210.5	203.4
65°	238.3	275.3	318.7	351.5	341.7	292.3	243.7	208.5	190.5	179.6	173.9
67.5°	196.2	223.0	253.1	281.8	273.9	238.8	199.9	172.5	159.0	149.6	146.2
70°	169.8	190.1	216.8	239.8	233.5	204.8	173.9	150.5	138.8	130.9	127.4
72.5°	144.4	161.1	181.6	200.4	196.0	172.2	146.4	128.8	119.8	112.5	109.7
75°	109.0	121.8	134.3	146.7	145.6	127.1	112.0	98.5	91.3	85.6	84.5
77.5°	80.5	87.7	96.1	103.5	101.5	90.9	79.1	71.3	66.0	62.2	61.6
80°	61.5	65.6	71.7	77.0	74.3	69.8	60.4	54.7	50.9	47.2	45.6
82.5°	44.5	48.8	52.3	55.2	53.2	49.0	43.1	39.3	37.1	34.4	33.8
85°	23.4	25.7	27.2	27.9	27.2	24.5	21.9	20.4	18.5	17.4	17.0
87.5°	10.8	10.6	10.4	10.8	9.6	9.4	7.9	6.8	6.7	6.7	6.3
90°	8.7	7.8	6.8	5.7	4.3	3.1	1.8	0.5	1.8	3.1	4.3
92.5°	11.3	10.8	10.4	10.2	10.3	10.4	10.5	10.6	10.5	10.4	10.3
95°	18.9	18.1	17.3	18.8	22.6	26.6	30.4	34.2	30.4	26.6	22.6
97.5°	23.7	21.8	19.9	24.4	35.3	46.3	57.1	68.0	57.1	46.3	35.3
100°	26.1	24.0	22.1	29.1	45.1	61.2	77.3	93.3	77.3	61.2	45.1
102.5°	64.2	80.9	97.5	107.6	110.9	114.3	117.8	121.1	117.8	114.3	110.9
105°	96.1	128.1	160.1	174.3	170.8	167.2	163.7	160.2	163.7	167.2	170.8
107.5°	121.7	160.1	198.3	216.1	213.3	210.5	207.6	204.8	207.6	210.5	213.3
110°	160.0	193.8	227.6	243.3	240.9	238.4	235.9	233.5	235.9	238.4	240.9



TEST NUMBER: P331294-840
 CATALOG NUMBER: SA2XXDIP-C485D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	249.3	257.7	266.1	269.1	267.0	264.8	262.7	260.4	262.7	264.8	267.0
115°	319.3	316.4	313.5	311.0	309.0	307.0	305.0	303.1	305.0	307.0	309.0
117.5°	356.2	354.2	352.1	350.0	347.8	345.6	343.4	341.1	343.4	345.6	347.8
120°	382.1	380.0	377.9	376.0	374.2	372.4	370.6	368.9	370.6	372.4	374.2
122.5°	406.6	404.2	402.0	399.9	398.1	396.3	394.4	392.5	394.4	396.3	398.1
125°	440.9	438.7	436.5	434.5	433.0	431.5	430.0	428.5	430.0	431.5	433.0
127.5°	472.8	471.1	469.5	467.8	466.1	464.4	462.7	461.0	462.7	464.4	466.1
130°	493.3	492.1	490.8	489.2	487.4	485.4	483.5	481.7	483.5	485.4	487.4
132.5°	513.2	511.9	510.6	509.2	507.6	505.9	504.3	502.8	504.3	505.9	507.6
135°	541.3	540.2	539.2	537.7	535.8	533.9	532.1	530.2	532.1	533.9	535.8
137.5°	566.8	565.6	564.4	563.1	561.8	560.5	559.2	558.0	559.2	560.5	561.8
140°	583.5	582.2	580.9	579.8	578.9	577.9	576.9	576.0	576.9	577.9	578.9
142.5°	598.6	597.2	595.7	594.6	593.7	592.9	592.1	591.2	592.1	592.9	593.7
145°	619.5	617.5	615.5	614.6	614.7	614.8	614.9	615.0	614.9	614.8	614.7
147.5°	638.7	636.7	634.8	634.0	634.5	634.9	635.3	635.8	635.3	634.9	634.5
150°	650.3	648.4	646.5	646.0	646.8	647.6	648.4	649.2	648.4	647.6	646.8
152.5°	661.1	659.2	657.4	657.0	657.9	658.8	659.7	660.7	659.7	658.8	657.9
155°	676.0	674.6	673.2	673.0	674.1	675.1	676.2	677.2	676.2	675.1	674.1
157.5°	688.6	687.6	686.7	686.6	687.5	688.4	689.3	690.1	689.3	688.4	687.5
160°	696.4	695.7	695.0	695.0	695.7	696.4	697.1	697.8	697.1	696.4	695.7
162.5°	702.9	702.3	701.7	701.8	702.4	703.1	703.8	704.5	703.8	703.1	702.4
165°	711.2	710.9	710.6	710.7	711.4	712.2	712.9	713.6	712.9	712.2	711.4
167.5°	718.0	717.6	717.3	717.5	718.2	718.9	719.6	720.3	719.6	718.9	718.2
170°	721.5	721.3	721.0	721.3	722.1	722.8	723.5	724.1	723.5	722.8	722.1
172.5°	724.1	723.9	723.6	723.9	724.6	725.3	726.0	726.7	726.0	725.3	724.6
175°	726.8	726.6	726.4	726.6	727.5	728.3	729.1	729.9	729.1	728.3	727.5
177.5°	727.7	727.6	727.5	727.8	728.5	729.1	729.8	730.4	729.8	729.1	728.5
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331294-840

CATALOG NUMBER: SA2XXDIP-C485D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	968.4	966.5	960.2	956.8	951.5	946.3	943.0	944.5	945.7	945.1	944.2
5°	940.6	933.4	922.5	913.0	906.3	893.8	888.6	886.0	883.6	881.0	878.4
7.5°	907.6	896.3	880.6	867.2	854.4	839.0	830.2	824.9	819.4	813.4	808.2
10°	884.0	868.2	851.6	832.7	817.7	803.7	791.2	782.9	775.4	768.2	763.0
12.5°	859.3	841.0	820.5	794.8	778.1	758.1	756.3	741.6	729.8	725.4	719.2
15°	819.9	794.3	768.2	737.7	724.5	706.4	695.1	683.8	673.6	666.4	664.5
17.5°	775.2	741.9	716.1	694.2	672.6	654.0	643.6	634.5	626.1	616.5	615.3
20°	741.0	712.5	684.2	664.9	642.7	623.8	611.0	601.9	594.7	589.1	584.2
22.5°	708.8	677.4	651.6	630.5	608.5	593.3	583.2	574.5	568.6	562.3	557.6
25°	657.0	632.5	604.2	580.5	562.3	552.5	544.2	536.6	532.9	528.8	523.5
27.5°	611.7	584.4	558.0	539.6	523.6	514.9	509.1	503.9	500.4	498.0	494.9
30°	579.7	552.1	531.4	513.3	500.1	491.4	487.7	484.6	480.5	479.0	477.5
32.5°	548.9	524.1	506.3	490.7	478.1	472.4	469.0	466.3	463.0	461.5	458.5
35°	505.3	484.6	467.3	458.6	448.4	443.5	440.9	437.1	434.1	432.6	432.2
37.5°	464.4	446.4	434.9	423.8	419.5	416.5	412.9	410.3	409.4	409.2	408.8
40°	437.9	423.1	412.9	403.9	402.0	397.5	394.5	392.2	392.2	392.6	392.2
42.5°	413.7	400.5	391.5	383.7	381.5	378.8	375.8	375.7	376.3	377.5	376.3
45°	377.2	367.7	361.3	357.5	353.4	350.7	350.3	351.5	351.8	352.2	353.4
47.5°	343.5	337.2	331.4	327.3	325.5	325.0	324.6	326.5	328.3	329.0	330.7
50°	323.6	316.4	311.5	308.9	307.4	306.6	307.4	309.6	311.1	313.1	314.2
52.5°	301.2	296.2	292.9	290.7	290.1	290.6	290.7	293.4	295.8	296.4	297.0
55°	270.4	266.6	265.9	262.5	264.0	263.6	265.5	267.0	269.2	271.6	272.0
57.5°	239.6	236.6	234.6	234.9	235.3	237.0	238.5	241.3	243.7	246.0	246.3
60°	219.1	217.6	216.5	216.5	217.2	219.5	221.4	224.0	225.5	227.0	228.1
62.5°	200.5	198.9	197.7	198.3	200.4	201.7	203.9	205.3	206.8	208.3	208.8
65°	170.9	170.1	171.3	172.0	172.4	174.2	176.9	178.0	179.6	180.3	182.9
67.5°	143.6	143.8	143.6	144.7	146.8	147.3	149.8	152.5	152.8	154.2	155.9
70°	125.2	125.9	126.7	127.4	129.4	130.1	132.0	133.1	134.6	135.7	136.9
72.5°	108.4	108.5	109.3	109.1	110.7	112.3	113.9	115.0	116.5	118.0	119.1
75°	83.3	83.3	84.1	84.5	86.3	88.3	87.9	88.7	90.2	91.7	92.4
77.5°	60.9	60.1	60.9	61.2	61.8	63.4	63.7	64.8	66.6	66.0	66.9
80°	46.4	45.2	46.4	46.8	46.8	48.7	48.7	49.4	50.5	49.4	50.5
82.5°	33.1	32.6	33.4	33.5	34.1	34.1	34.7	34.9	36.1	35.5	36.1
85°	16.6	16.3	16.6	16.3	16.6	17.0	17.0	16.6	16.6	17.4	16.3
87.5°	6.3	6.2	6.1	6.3	6.2	6.1	5.9	6.0	6.1	5.6	5.7
90°	5.7	6.8	7.8	8.7	9.6	10.5	11.1	11.7	12.3	12.9	13.3
92.5°	10.2	10.4	10.8	11.3	11.7	12.2	12.5	12.8	13.1	13.4	13.6
95°	18.8	17.3	18.1	18.9	19.7	20.6	21.1	21.7	22.3	22.9	23.1
97.5°	24.4	19.9	21.8	23.7	25.7	27.5	28.0	28.5	28.9	29.4	29.7
100°	29.1	22.1	24.0	26.1	28.1	30.0	31.0	31.9	32.8	33.8	34.3
102.5°	107.6	97.5	80.9	64.2	47.6	30.9	32.1	33.3	34.5	35.7	36.6
105°	174.3	160.1	128.1	96.1	64.1	32.1	33.4	34.7	36.1	37.3	38.2
107.5°	216.1	198.3	160.1	121.7	83.3	45.0	43.7	42.4	41.1	39.8	39.4
110°	243.3	227.6	193.8	160.0	126.0	92.2	80.5	68.8	57.1	45.3	39.8



TEST NUMBER: P331294-840

CATALOG NUMBER: SA2XXDIP-C485D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	269.1	266.1	257.7	249.3	241.0	232.7	189.9	147.1	104.4	61.7	40.6
115°	311.0	313.5	316.4	319.3	322.2	325.2	270.9	216.7	162.5	108.3	77.0
117.5°	350.0	352.1	354.2	356.2	358.2	360.1	347.1	334.0	320.8	307.7	287.3
120°	376.0	377.9	380.0	382.1	384.2	386.3	387.7	389.1	390.5	391.9	384.8
122.5°	399.9	402.0	404.2	406.6	408.9	411.2	412.0	412.8	413.7	414.5	413.4
125°	434.5	436.5	438.7	440.9	443.1	445.4	446.2	447.0	447.8	448.6	449.2
127.5°	467.8	469.5	471.1	472.8	474.4	476.2	477.3	478.5	479.7	480.9	481.5
130°	489.2	490.8	492.1	493.3	494.6	495.9	497.3	498.5	499.8	501.1	501.7
132.5°	509.2	510.6	511.9	513.2	514.4	515.7	516.8	518.0	519.1	520.2	520.6
135°	537.7	539.2	540.2	541.3	542.3	543.3	544.5	545.7	546.8	548.1	548.6
137.5°	563.1	564.4	565.6	566.8	567.9	569.2	570.4	571.5	572.6	573.8	574.1
140°	579.8	580.9	582.2	583.5	584.7	586.0	587.1	588.1	589.2	590.3	590.5
142.5°	594.6	595.7	597.2	598.6	600.2	601.7	602.6	603.6	604.5	605.5	605.7
145°	614.6	615.5	617.5	619.5	621.5	623.5	624.3	625.1	625.9	626.7	626.8
147.5°	634.0	634.8	636.7	638.7	640.7	642.7	643.3	643.9	644.5	645.1	645.1
150°	646.0	646.5	648.4	650.3	652.2	654.0	654.7	655.4	656.1	656.8	656.9
152.5°	657.0	657.4	659.2	661.1	662.8	664.6	665.3	666.0	666.7	667.4	667.3
155°	673.0	673.2	674.6	676.0	677.4	678.8	679.5	680.2	681.0	681.7	681.5
157.5°	686.6	686.7	687.6	688.6	689.6	690.6	691.4	692.2	693.0	693.8	693.8
160°	695.0	695.0	695.7	696.4	697.1	697.8	698.5	699.1	699.8	700.5	700.5
162.5°	701.8	701.7	702.3	702.9	703.5	704.1	704.9	705.7	706.5	707.3	707.2
165°	710.7	710.6	710.9	711.2	711.7	712.0	712.9	713.7	714.5	715.3	715.3
167.5°	717.5	717.3	717.6	718.0	718.3	718.6	719.4	720.2	721.1	722.0	721.9
170°	721.3	721.0	721.3	721.5	721.8	722.1	722.9	723.7	724.5	725.3	725.2
172.5°	723.9	723.6	723.9	724.1	724.3	724.6	725.4	726.2	727.0	727.8	727.7
175°	726.6	726.4	726.6	726.8	727.0	727.3	728.1	728.9	729.7	730.5	730.4
177.5°	727.8	727.5	727.6	727.7	727.8	727.9	728.6	729.2	729.9	730.5	730.4
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331294-840

CATALOG NUMBER: SA2XXDIP-C485D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	941.2	940.6	940.6	937.9	940.6	940.6	941.2	944.2	945.1	945.7	944.5
5°	873.1	871.9	870.1	871.9	870.1	871.9	873.1	878.4	881.0	883.6	886.0
7.5°	805.8	801.2	800.5	796.1	800.5	801.2	805.8	808.2	813.4	819.4	824.9
10°	756.6	753.6	753.2	746.0	753.2	753.6	756.6	763.0	768.2	775.4	782.9
12.5°	719.1	711.9	713.4	709.2	713.4	711.9	719.1	719.2	725.4	729.8	741.6
15°	654.3	654.3	652.9	646.4	652.9	654.3	654.3	664.5	666.4	673.6	683.8
17.5°	607.8	607.0	603.4	605.2	603.4	607.0	607.8	615.3	616.5	626.1	634.5
20°	580.1	577.7	573.3	573.3	573.3	577.7	580.1	584.2	589.1	594.7	601.9
22.5°	553.8	553.6	548.9	550.4	548.9	553.6	553.8	557.6	562.3	568.6	574.5
25°	523.1	520.1	517.9	519.0	517.9	520.1	523.1	523.5	528.8	532.9	536.6
27.5°	494.0	492.3	492.2	489.1	492.2	492.3	494.0	494.9	498.0	500.4	503.9
30°	477.1	473.3	474.0	472.2	474.0	473.3	477.1	477.5	479.0	480.5	484.6
32.5°	457.8	456.5	455.7	454.0	455.7	456.5	457.8	458.5	461.5	463.0	466.3
35°	431.4	431.8	429.9	430.7	429.9	431.8	431.4	432.2	432.6	434.1	437.1
37.5°	408.5	409.7	408.8	409.0	408.8	409.7	408.5	408.8	409.2	409.4	410.3
40°	393.3	393.3	393.3	394.5	393.3	393.3	393.3	392.2	392.6	392.2	392.2
42.5°	378.9	378.3	377.7	377.6	377.7	378.3	378.9	376.3	377.5	376.3	375.7
45°	354.2	355.3	355.7	353.8	355.7	355.3	354.2	353.4	352.2	351.8	351.5
47.5°	331.7	331.8	331.7	333.4	331.7	331.8	331.7	330.7	329.0	328.3	326.5
50°	316.1	315.3	316.1	315.3	316.1	315.3	316.1	314.2	313.1	311.1	309.6
52.5°	299.4	299.6	299.1	299.0	299.1	299.6	299.4	297.0	296.4	295.8	293.4
55°	273.5	274.2	273.8	273.8	273.8	274.2	273.5	272.0	271.6	269.2	267.0
57.5°	246.5	247.2	247.7	246.0	247.7	247.2	246.5	246.3	246.0	243.7	241.3
60°	227.8	229.6	229.3	228.5	229.3	229.6	227.8	228.1	227.0	225.5	224.0
62.5°	210.6	211.3	211.2	211.1	211.2	211.3	210.6	208.8	208.3	206.8	205.3
65°	184.0	184.8	183.7	184.8	183.7	184.8	184.0	182.9	180.3	179.6	178.0
67.5°	155.4	155.7	156.5	157.0	156.5	155.7	155.4	155.9	154.2	152.8	152.5
70°	137.6	137.2	138.5	139.6	138.5	137.2	137.6	136.9	135.7	134.6	133.1
72.5°	119.0	119.8	119.4	120.3	119.4	119.8	119.0	119.1	118.0	116.5	115.0
75°	91.7	92.8	92.4	93.5	92.4	92.8	91.7	92.4	91.7	90.2	88.7
77.5°	66.2	66.3	66.2	66.9	66.2	66.3	66.2	66.9	66.0	66.6	64.8
80°	50.5	49.8	49.0	50.5	49.0	49.8	50.5	50.5	49.4	50.5	49.4
82.5°	35.1	35.6	34.8	34.8	34.8	35.6	35.1	36.1	35.5	36.1	34.9
85°	16.3	15.9	15.0	15.0	15.0	15.9	16.3	16.3	17.4	16.6	16.6
87.5°	5.8	5.5	5.6	5.3	5.6	5.5	5.8	5.7	5.6	6.1	6.0
90°	13.5	13.7	14.0	14.2	14.0	13.7	13.5	13.3	12.9	12.3	11.7
92.5°	13.8	13.9	14.1	14.2	14.1	13.9	13.8	13.6	13.4	13.1	12.8
95°	23.0	22.9	22.8	22.6	22.8	22.9	23.0	23.1	22.9	22.3	21.7
97.5°	29.8	30.0	30.1	30.3	30.1	30.0	29.8	29.7	29.4	28.9	28.5
100°	34.6	34.8	35.0	35.3	35.0	34.8	34.6	34.3	33.8	32.8	31.9
102.5°	36.9	37.2	37.5	37.9	37.5	37.2	36.9	36.6	35.7	34.5	33.3
105°	38.7	39.1	39.6	40.1	39.6	39.1	38.7	38.2	37.3	36.1	34.7
107.5°	39.8	40.3	40.7	41.2	40.7	40.3	39.8	39.4	39.8	41.1	42.4
110°	40.2	40.7	41.2	41.6	41.2	40.7	40.2	39.8	45.3	57.1	68.8



TEST NUMBER: P331294-840

CATALOG NUMBER: SA2XXDIP-C485D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	40.9	41.3	41.7	42.0	41.7	41.3	40.9	40.6	61.7	104.4	147.1
115°	68.5	60.1	51.6	43.2	51.6	60.1	68.5	77.0	108.3	162.5	216.7
117.5°	259.5	231.9	204.2	176.4	204.2	231.9	259.5	287.3	307.7	320.8	334.0
120°	368.9	353.1	337.3	321.4	337.3	353.1	368.9	384.8	391.9	390.5	389.1
122.5°	410.4	407.3	404.2	401.1	404.2	407.3	410.4	413.4	414.5	413.7	412.8
125°	449.6	449.9	450.3	450.6	450.3	449.9	449.6	449.2	448.6	447.8	447.0
127.5°	481.6	481.7	481.7	481.8	481.7	481.7	481.6	481.5	480.9	479.7	478.5
130°	501.5	501.4	501.3	501.2	501.3	501.4	501.5	501.7	501.1	499.8	498.5
132.5°	520.5	520.4	520.3	520.2	520.3	520.4	520.5	520.6	520.2	519.1	518.0
135°	548.3	548.1	547.9	547.5	547.9	548.1	548.3	548.6	548.1	546.8	545.7
137.5°	573.7	573.3	573.0	572.6	573.0	573.3	573.7	574.1	573.8	572.6	571.5
140°	589.9	589.4	588.8	588.1	588.8	589.4	589.9	590.5	590.3	589.2	588.1
142.5°	605.1	604.5	603.9	603.3	603.9	604.5	605.1	605.7	605.5	604.5	603.6
145°	626.3	625.7	625.1	624.5	625.1	625.7	626.3	626.8	626.7	625.9	625.1
147.5°	644.7	644.2	643.7	643.2	643.7	644.2	644.7	645.1	645.1	644.5	643.9
150°	656.3	655.7	655.1	654.6	655.1	655.7	656.3	656.9	656.8	656.1	655.4
152.5°	666.6	665.8	665.0	664.3	665.0	665.8	666.6	667.3	667.4	666.7	666.0
155°	680.5	679.6	678.7	677.7	678.7	679.6	680.5	681.5	681.7	681.0	680.2
157.5°	692.8	691.9	690.9	690.0	690.9	691.9	692.8	693.8	693.8	693.0	692.2
160°	699.7	698.9	698.0	697.2	698.0	698.9	699.7	700.5	700.5	699.8	699.1
162.5°	706.2	705.2	704.2	703.2	704.2	705.2	706.2	707.2	707.3	706.5	705.7
165°	714.5	713.7	712.9	712.0	712.9	713.7	714.5	715.3	715.3	714.5	713.7
167.5°	720.7	719.7	718.6	717.6	718.6	719.7	720.7	721.9	722.0	721.1	720.2
170°	724.1	723.1	722.1	720.9	722.1	723.1	724.1	725.2	725.3	724.5	723.7
172.5°	726.7	725.6	724.6	723.5	724.6	725.6	726.7	727.7	727.8	727.0	726.2
175°	729.2	728.0	726.9	725.7	726.9	728.0	729.2	730.4	730.5	729.7	728.9
177.5°	729.6	728.7	727.9	727.1	727.9	728.7	729.6	730.4	730.5	729.9	729.2
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331294-840

CATALOG NUMBER: SA2XXDIP-C485D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	943.0	946.3	951.5	956.8	960.2	966.5	968.4	971.4	974.1	980.4	987.0
5°	888.6	893.8	906.3	913.0	922.5	933.4	940.6	948.2	956.4	970.8	984.0
7.5°	830.2	839.0	854.4	867.2	880.6	896.3	907.6	922.5	934.8	955.0	974.4
10°	791.2	803.7	817.7	832.7	851.6	868.2	884.0	902.9	918.0	942.1	964.7
12.5°	756.3	758.1	778.1	794.8	820.5	841.0	859.3	883.5	898.4	927.1	950.9
15°	695.1	706.4	724.5	737.7	768.2	794.3	819.9	845.2	862.1	897.6	928.9
17.5°	643.6	654.0	672.6	694.2	716.1	741.9	775.2	801.8	824.9	865.4	902.4
20°	611.0	623.8	642.7	664.9	684.2	712.5	741.0	771.6	796.5	842.1	885.6
22.5°	583.2	593.3	608.5	630.5	651.6	677.4	708.8	742.0	768.2	817.4	861.4
25°	544.2	552.5	562.3	580.5	604.2	632.5	657.0	693.6	731.6	777.7	830.8
27.5°	509.1	514.9	523.6	539.6	558.0	584.4	611.7	646.3	684.7	734.6	790.7
30°	487.7	491.4	500.1	513.3	531.4	552.1	579.7	612.9	652.1	702.7	758.4
32.5°	469.0	472.4	478.1	490.7	506.3	524.1	548.9	582.1	619.5	669.1	730.9
35°	440.9	443.5	448.4	458.6	467.3	484.6	505.3	535.5	570.6	618.1	682.3
37.5°	412.9	416.5	419.5	423.8	434.9	446.4	464.4	489.9	524.3	572.3	633.4
40°	394.5	397.5	402.0	403.9	412.9	423.1	437.9	461.2	495.9	539.7	599.3
42.5°	375.8	378.8	381.5	383.7	391.5	400.5	413.7	433.8	464.5	507.2	566.1
45°	350.3	350.7	353.4	357.5	361.3	367.7	377.2	394.5	418.3	458.3	511.8
47.5°	324.6	325.0	325.5	327.3	331.4	337.2	343.5	357.6	378.9	410.8	462.9
50°	307.4	306.6	307.4	308.9	311.5	316.4	323.6	333.8	351.1	380.9	428.8
52.5°	290.7	290.6	290.1	290.7	292.9	296.2	301.2	309.9	325.5	352.8	395.1
55°	265.5	263.6	264.0	262.5	265.9	266.6	270.4	277.6	291.1	310.0	349.6
57.5°	238.5	237.0	235.3	234.9	234.6	236.6	239.6	245.3	255.7	272.3	304.4
60°	221.4	219.5	217.2	216.5	216.5	217.6	219.1	223.3	233.1	247.8	274.2
62.5°	203.9	201.7	200.4	198.3	197.7	198.9	200.5	203.4	210.5	224.3	247.0
65°	176.9	174.2	172.4	172.0	171.3	170.1	170.9	173.9	179.6	190.5	208.5
67.5°	149.8	147.3	146.8	144.7	143.6	143.8	143.6	146.2	149.6	159.0	172.5
70°	132.0	130.1	129.4	127.4	126.7	125.9	125.2	127.4	130.9	138.8	150.5
72.5°	113.9	112.3	110.7	109.1	109.3	108.5	108.4	109.7	112.5	119.8	128.8
75°	87.9	88.3	86.3	84.5	84.1	83.3	83.3	84.5	85.6	91.3	98.5
77.5°	63.7	63.4	61.8	61.2	60.9	60.1	60.9	61.6	62.2	66.0	71.3
80°	48.7	48.7	46.8	46.8	46.4	45.2	46.4	45.6	47.2	50.9	54.7
82.5°	34.7	34.1	34.1	33.5	33.4	32.6	33.1	33.8	34.4	37.1	39.3
85°	17.0	17.0	16.6	16.3	16.6	16.3	16.6	17.0	17.4	18.5	20.4
87.5°	5.9	6.1	6.2	6.3	6.1	6.2	6.3	6.3	6.7	6.7	6.8
90°	11.1	10.5	9.6	8.7	7.8	6.8	5.7	4.3	3.1	1.8	0.5
92.5°	12.5	12.2	11.7	11.3	10.8	10.4	10.2	10.3	10.4	10.5	10.6
95°	21.1	20.6	19.7	18.9	18.1	17.3	18.8	22.6	26.6	30.4	34.2
97.5°	28.0	27.5	25.7	23.7	21.8	19.9	24.4	35.3	46.3	57.1	68.0
100°	31.0	30.0	28.1	26.1	24.0	22.1	29.1	45.1	61.2	77.3	93.3
102.5°	32.1	30.9	47.6	64.2	80.9	97.5	107.6	110.9	114.3	117.8	121.1
105°	33.4	32.1	64.1	96.1	128.1	160.1	174.3	170.8	167.2	163.7	160.2
107.5°	43.7	45.0	83.3	121.7	160.1	198.3	216.1	213.3	210.5	207.6	204.8
110°	80.5	92.2	126.0	160.0	193.8	227.6	243.3	240.9	238.4	235.9	233.5



TEST NUMBER: P331294-840

CATALOG NUMBER: SA2XXDIP-C485D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	189.9	232.7	241.0	249.3	257.7	266.1	269.1	267.0	264.8	262.7	260.4
115°	270.9	325.2	322.2	319.3	316.4	313.5	311.0	309.0	307.0	305.0	303.1
117.5°	347.1	360.1	358.2	356.2	354.2	352.1	350.0	347.8	345.6	343.4	341.1
120°	387.7	386.3	384.2	382.1	380.0	377.9	376.0	374.2	372.4	370.6	368.9
122.5°	412.0	411.2	408.9	406.6	404.2	402.0	399.9	398.1	396.3	394.4	392.5
125°	446.2	445.4	443.1	440.9	438.7	436.5	434.5	433.0	431.5	430.0	428.5
127.5°	477.3	476.2	474.4	472.8	471.1	469.5	467.8	466.1	464.4	462.7	461.0
130°	497.3	495.9	494.6	493.3	492.1	490.8	489.2	487.4	485.4	483.5	481.7
132.5°	516.8	515.7	514.4	513.2	511.9	510.6	509.2	507.6	505.9	504.3	502.8
135°	544.5	543.3	542.3	541.3	540.2	539.2	537.7	535.8	533.9	532.1	530.2
137.5°	570.4	569.2	567.9	566.8	565.6	564.4	563.1	561.8	560.5	559.2	558.0
140°	587.1	586.0	584.7	583.5	582.2	580.9	579.8	578.9	577.9	576.9	576.0
142.5°	602.6	601.7	600.2	598.6	597.2	595.7	594.6	593.7	592.9	592.1	591.2
145°	624.3	623.5	621.5	619.5	617.5	615.5	614.6	614.7	614.8	614.9	615.0
147.5°	643.3	642.7	640.7	638.7	636.7	634.8	634.0	634.5	634.9	635.3	635.8
150°	654.7	654.0	652.2	650.3	648.4	646.5	646.0	646.8	647.6	648.4	649.2
152.5°	665.3	664.6	662.8	661.1	659.2	657.4	657.0	657.9	658.8	659.7	660.7
155°	679.5	678.8	677.4	676.0	674.6	673.2	673.0	674.1	675.1	676.2	677.2
157.5°	691.4	690.6	689.6	688.6	687.6	686.7	686.6	687.5	688.4	689.3	690.1
160°	698.5	697.8	697.1	696.4	695.7	695.0	695.0	695.7	696.4	697.1	697.8
162.5°	704.9	704.1	703.5	702.9	702.3	701.7	701.8	702.4	703.1	703.8	704.5
165°	712.9	712.0	711.7	711.2	710.9	710.6	710.7	711.4	712.2	712.9	713.6
167.5°	719.4	718.6	718.3	718.0	717.6	717.3	717.5	718.2	718.9	719.6	720.3
170°	722.9	722.1	721.8	721.5	721.3	721.0	721.3	722.1	722.8	723.5	724.1
172.5°	725.4	724.6	724.3	724.1	723.9	723.6	723.9	724.6	725.3	726.0	726.7
175°	728.1	727.3	727.0	726.8	726.6	726.4	726.6	727.5	728.3	729.1	729.9
177.5°	728.6	727.9	727.8	727.7	727.6	727.5	727.8	728.5	729.1	729.8	730.4
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331294-840
 CATALOG NUMBER: SA2XXDIP-C485D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	986.4	988.0	992.8	997.6	1003.0	1004.5	1006.9	1004.8	1004.2	1010.0	1014.2
5°	989.3	996.0	1009.3	1021.3	1031.5	1038.6	1046.2	1049.2	1054.9	1062.8	1072.6
7.5°	986.0	999.3	1020.1	1037.6	1056.7	1070.6	1081.4	1090.6	1101.7	1116.7	1133.1
10°	982.5	1000.2	1025.4	1046.9	1070.4	1088.0	1102.8	1117.1	1133.7	1154.5	1175.9
12.5°	975.8	996.8	1028.4	1053.9	1083.9	1101.4	1121.2	1152.1	1169.9	1198.8	1229.0
15°	962.5	985.8	1030.0	1061.3	1095.2	1128.4	1165.0	1194.4	1223.9	1240.8	1283.4
17.5°	942.6	976.9	1025.8	1062.4	1105.5	1157.7	1198.8	1232.2	1266.2	1293.6	1315.0
20°	926.7	964.0	1019.8	1063.6	1114.8	1171.0	1218.2	1252.1	1281.5	1304.5	1317.8
22.5°	906.5	953.4	1007.7	1059.0	1124.5	1180.1	1229.6	1256.4	1280.9	1292.1	1297.2
25°	874.5	931.2	992.6	1055.2	1129.1	1188.0	1233.2	1249.5	1256.7	1245.7	1227.6
27.5°	840.3	903.3	975.2	1048.1	1126.3	1182.9	1215.3	1212.7	1200.6	1165.2	1136.9
30°	814.7	884.0	961.3	1040.9	1119.3	1174.4	1193.3	1174.4	1146.9	1107.3	1066.9
32.5°	787.8	859.6	946.5	1030.7	1106.7	1155.1	1159.2	1126.7	1084.1	1039.2	988.8
35°	747.1	824.9	918.7	1007.7	1079.7	1110.3	1092.2	1034.9	984.3	922.9	854.2
37.5°	701.1	787.0	881.1	974.1	1039.5	1047.4	1002.5	942.1	870.8	798.6	717.8
40°	666.8	757.7	854.6	948.5	1006.2	997.9	940.6	874.2	789.3	701.1	626.0
42.5°	636.0	726.9	825.7	917.8	964.0	941.2	874.2	792.7	701.6	618.4	549.8
45°	582.7	676.2	777.3	866.3	892.7	851.6	763.0	672.5	582.7	513.3	459.0
47.5°	531.0	623.4	723.5	801.7	811.1	755.8	658.9	565.8	488.7	432.1	393.8
50°	492.9	585.7	684.9	754.7	751.6	684.9	585.3	496.7	432.2	386.6	360.9
52.5°	458.8	546.4	641.8	705.2	689.2	616.4	521.4	442.7	389.7	354.0	330.7
55°	405.8	486.9	577.4	628.3	599.0	518.2	437.9	374.5	335.3	308.5	290.4
57.5°	353.1	429.2	506.6	538.1	505.5	431.0	364.1	318.1	288.6	268.7	257.0
60°	320.5	387.0	456.0	483.1	444.2	377.9	325.1	284.0	260.2	244.0	233.5
62.5°	288.0	347.4	412.5	427.3	391.7	335.7	288.9	254.7	235.2	220.8	210.9
65°	243.7	292.3	341.7	351.5	318.7	275.3	238.3	216.1	198.7	188.2	180.3
67.5°	199.9	238.8	273.9	281.8	253.1	223.0	196.2	176.9	165.1	156.3	149.7
70°	173.9	204.8	233.5	239.8	216.8	190.1	169.8	154.2	143.7	136.1	129.8
72.5°	146.4	172.2	196.0	200.4	181.6	161.1	144.4	132.2	122.9	118.1	111.9
75°	112.0	127.1	145.6	146.7	134.3	121.8	109.0	101.1	96.1	90.2	87.2
77.5°	79.1	90.9	101.5	103.5	96.1	87.7	80.5	74.2	70.1	67.3	64.5
80°	60.4	69.8	74.3	77.0	71.7	65.6	61.5	57.4	54.7	52.8	50.9
82.5°	43.1	49.0	53.2	55.2	52.3	48.8	44.5	42.2	40.2	38.6	38.0
85°	21.9	24.5	27.2	27.9	27.2	25.7	23.4	23.4	22.2	21.9	21.9
87.5°	7.9	9.4	9.6	10.8	10.4	10.6	10.8	10.7	10.6	10.4	10.2
90°	1.8	3.1	4.3	5.7	6.8	7.8	8.7	9.6	10.5	11.1	11.7
92.5°	10.5	10.4	10.3	10.2	10.4	10.8	11.3	11.7	12.2	12.5	12.8
95°	30.4	26.6	22.6	18.8	17.3	18.1	18.9	19.7	20.6	21.1	21.7
97.5°	57.1	46.3	35.3	24.4	19.9	21.8	23.7	25.7	27.5	28.0	28.5
100°	77.3	61.2	45.1	29.1	22.1	24.0	26.1	28.1	30.0	31.0	31.9
102.5°	117.8	114.3	110.9	107.6	97.5	80.9	64.2	47.6	30.9	32.1	33.3
105°	163.7	167.2	170.8	174.3	160.1	128.1	96.1	64.1	32.1	33.4	34.7
107.5°	207.6	210.5	213.3	216.1	198.3	160.1	121.7	83.3	45.0	43.7	42.4
110°	235.9	238.4	240.9	243.3	227.6	193.8	160.0	126.0	92.2	80.5	68.8



TEST NUMBER: P331294-840

CATALOG NUMBER: SA2XXDIP-C485D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	262.7	264.8	267.0	269.1	266.1	257.7	249.3	241.0	232.7	189.9	147.1
115°	305.0	307.0	309.0	311.0	313.5	316.4	319.3	322.2	325.2	270.9	216.7
117.5°	343.4	345.6	347.8	350.0	352.1	354.2	356.2	358.2	360.1	347.1	334.0
120°	370.6	372.4	374.2	376.0	377.9	380.0	382.1	384.2	386.3	387.7	389.1
122.5°	394.4	396.3	398.1	399.9	402.0	404.2	406.6	408.9	411.2	412.0	412.8
125°	430.0	431.5	433.0	434.5	436.5	438.7	440.9	443.1	445.4	446.2	447.0
127.5°	462.7	464.4	466.1	467.8	469.5	471.1	472.8	474.4	476.2	477.3	478.5
130°	483.5	485.4	487.4	489.2	490.8	492.1	493.3	494.6	495.9	497.3	498.5
132.5°	504.3	505.9	507.6	509.2	510.6	511.9	513.2	514.4	515.7	516.8	518.0
135°	532.1	533.9	535.8	537.7	539.2	540.2	541.3	542.3	543.3	544.5	545.7
137.5°	559.2	560.5	561.8	563.1	564.4	565.6	566.8	567.9	569.2	570.4	571.5
140°	576.9	577.9	578.9	579.8	580.9	582.2	583.5	584.7	586.0	587.1	588.1
142.5°	592.1	592.9	593.7	594.6	595.7	597.2	598.6	600.2	601.7	602.6	603.6
145°	614.9	614.8	614.7	614.6	615.5	617.5	619.5	621.5	623.5	624.3	625.1
147.5°	635.3	634.9	634.5	634.0	634.8	636.7	638.7	640.7	642.7	643.3	643.9
150°	648.4	647.6	646.8	646.0	646.5	648.4	650.3	652.2	654.0	654.7	655.4
152.5°	659.7	658.8	657.9	657.0	657.4	659.2	661.1	662.8	664.6	665.3	666.0
155°	676.2	675.1	674.1	673.0	673.2	674.6	676.0	677.4	678.8	679.5	680.2
157.5°	689.3	688.4	687.5	686.6	686.7	687.6	688.6	689.6	690.6	691.4	692.2
160°	697.1	696.4	695.7	695.0	695.0	695.7	696.4	697.1	697.8	698.5	699.1
162.5°	703.8	703.1	702.4	701.8	701.7	702.3	702.9	703.5	704.1	704.9	705.7
165°	712.9	712.2	711.4	710.7	710.6	710.9	711.2	711.7	712.0	712.9	713.7
167.5°	719.6	718.9	718.2	717.5	717.3	717.6	718.0	718.3	718.6	719.4	720.2
170°	723.5	722.8	722.1	721.3	721.0	721.3	721.5	721.8	722.1	722.9	723.7
172.5°	726.0	725.3	724.6	723.9	723.6	723.9	724.1	724.3	724.6	725.4	726.2
175°	729.1	728.3	727.5	726.6	726.4	726.6	726.8	727.0	727.3	728.1	728.9
177.5°	729.8	729.1	728.5	727.8	727.5	727.6	727.7	727.8	727.9	728.6	729.2
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331294-840
 CATALOG NUMBER: SA2XXDIP-C485D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1017.8	1022.1	1022.1	1022.7	1027.4	1026.9	1026.6
5°	1083.2	1089.5	1090.4	1097.1	1101.7	1100.1	1096.0
7.5°	1144.8	1156.7	1165.8	1170.8	1176.8	1180.4	1178.8
10°	1193.7	1211.0	1221.5	1228.7	1237.4	1243.9	1241.5
12.5°	1238.0	1258.7	1273.1	1285.5	1286.6	1294.8	1289.2
15°	1307.2	1329.1	1331.3	1340.4	1347.6	1346.8	1347.2
17.5°	1330.0	1337.1	1338.5	1338.7	1338.8	1336.2	1330.4
20°	1321.9	1319.3	1312.8	1308.0	1299.3	1298.1	1290.6
22.5°	1283.2	1274.9	1258.8	1248.2	1234.7	1231.1	1229.0
25°	1207.2	1188.7	1163.1	1138.6	1131.8	1118.6	1122.4
27.5°	1102.9	1074.1	1046.3	1026.4	1008.5	988.7	994.3
30°	1029.6	997.1	958.0	927.8	908.6	889.7	886.3
32.5°	942.1	894.5	850.8	824.3	794.8	782.8	769.8
35°	791.2	744.9	701.5	664.2	642.7	626.0	611.0
37.5°	655.5	602.2	567.1	536.9	521.4	511.9	514.2
40°	571.4	524.6	499.0	475.9	461.6	454.8	456.4
42.5°	503.2	468.2	447.1	431.3	421.2	417.4	416.5
45°	425.8	406.2	388.8	379.8	374.9	370.7	368.1
47.5°	373.0	357.0	347.2	341.8	337.5	333.4	333.3
50°	341.3	330.7	324.0	318.3	314.9	311.8	314.6
52.5°	317.2	307.5	300.7	295.7	294.4	291.6	291.6
55°	281.3	273.8	268.9	264.4	262.2	260.6	258.7
57.5°	248.7	241.6	237.1	234.2	229.9	228.4	227.8
60°	225.5	219.8	215.3	211.6	209.6	206.7	206.7
62.5°	204.1	198.4	194.2	191.4	188.2	187.0	187.3
65°	173.1	168.5	164.4	161.4	160.7	158.4	159.2
67.5°	144.6	141.6	137.2	135.5	134.1	132.9	132.0
70°	125.6	122.6	120.3	118.1	116.9	116.9	116.9
72.5°	109.6	105.9	104.6	101.8	102.4	101.2	100.0
75°	84.8	82.6	81.5	80.3	78.5	78.5	78.5
77.5°	62.4	61.8	60.4	59.2	58.8	58.4	58.6
80°	48.3	47.9	47.2	47.2	46.4	46.0	45.2
82.5°	37.1	36.2	35.6	35.3	35.2	35.1	35.0
85°	21.1	20.4	20.4	20.7	20.0	20.0	20.4
87.5°	10.6	10.7	10.5	10.5	10.9	10.6	10.7
90°	12.3	12.9	13.3	13.5	13.7	14.0	14.2
92.5°	13.1	13.4	13.6	13.8	13.9	14.1	14.2
95°	22.3	22.9	23.1	23.0	22.9	22.8	22.6
97.5°	28.9	29.4	29.7	29.8	30.0	30.1	30.3
100°	32.8	33.8	34.3	34.6	34.8	35.0	35.3
102.5°	34.5	35.7	36.6	36.9	37.2	37.5	37.9
105°	36.1	37.3	38.2	38.7	39.1	39.6	40.1
107.5°	41.1	39.8	39.4	39.8	40.3	40.7	41.2
110°	57.1	45.3	39.8	40.2	40.7	41.2	41.6



TEST NUMBER: P331294-840

CATALOG NUMBER: SA2XXDIP-C485D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	104.4	61.7	40.6	40.9	41.3	41.7	42.0
115°	162.5	108.3	77.0	68.5	60.1	51.6	43.2
117.5°	320.8	307.7	287.3	259.5	231.9	204.2	176.4
120°	390.5	391.9	384.8	368.9	353.1	337.3	321.4
122.5°	413.7	414.5	413.4	410.4	407.3	404.2	401.1
125°	447.8	448.6	449.2	449.6	449.9	450.3	450.6
127.5°	479.7	480.9	481.5	481.6	481.7	481.7	481.8
130°	499.8	501.1	501.7	501.5	501.4	501.3	501.2
132.5°	519.1	520.2	520.6	520.5	520.4	520.3	520.2
135°	546.8	548.1	548.6	548.3	548.1	547.9	547.5
137.5°	572.6	573.8	574.1	573.7	573.3	573.0	572.6
140°	589.2	590.3	590.5	589.9	589.4	588.8	588.1
142.5°	604.5	605.5	605.7	605.1	604.5	603.9	603.3
145°	625.9	626.7	626.8	626.3	625.7	625.1	624.5
147.5°	644.5	645.1	645.1	644.7	644.2	643.7	643.2
150°	656.1	656.8	656.9	656.3	655.7	655.1	654.6
152.5°	666.7	667.4	667.3	666.6	665.8	665.0	664.3
155°	681.0	681.7	681.5	680.5	679.6	678.7	677.7
157.5°	693.0	693.8	693.8	692.8	691.9	690.9	690.0
160°	699.8	700.5	700.5	699.7	698.9	698.0	697.2
162.5°	706.5	707.3	707.2	706.2	705.2	704.2	703.2
165°	714.5	715.3	715.3	714.5	713.7	712.9	712.0
167.5°	721.1	722.0	721.9	720.7	719.7	718.6	717.6
170°	724.5	725.3	725.2	724.1	723.1	722.1	720.9
172.5°	727.0	727.8	727.7	726.7	725.6	724.6	723.5
175°	729.7	730.5	730.4	729.2	728.0	726.9	725.7
177.5°	729.9	730.5	730.4	729.6	728.7	727.9	727.1
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3

(END OF REPORT)