

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333010-927

Luminaire Tested: **SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P333010-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7273.3 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333010-927
CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333010-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55				
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	54	53	52	47				
2	91	84	78	73	84	78	73	68	67	63	60	57	55	52	48	46	45	40				
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	38	35				
4	76	66	58	52	71	61	55	49	53	48	44	46	42	39	39	36	33	30				
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26				
6	65	53	45	39	60	50	43	37	43	38	34	38	33	30	32	29	26	23				
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21				
8	56	44	36	31	52	41	34	29	36	30	27	31	27	24	27	24	21	19				
9	52	40	32	27	48	38	31	26	33	28	24	29	25	21	25	22	19	17				
10	49	37	30	25	45	35	28	24	31	25	22	27	22	19	23	20	17	15				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12674	12674	12674	12674
5°	14699	12712	11235	12712
10°	17390	12656	10027	12656
15°	20088	12538	8616	12538
20°	22365	12378	7792	12378
25°	23087	12219	7234	12219
30°	20211	12028	6898	12028
35°	15733	11744	6695	11744
40°	11798	11418	6585	11418
45°	9315	10896	6528	10896
50°	7863	10295	6339	10295
55°	6854	9633	6000	9633
60°	6168	8946	5310	8946
65°	5436	8202	4567	8202
70°	4898	7435	4121	7435
75°	4105	6591	3512	6591
80°	3468	5616	3292	5616
85°	2927	4400	2927	4400



TEST NUMBER: P333010-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.1	2.1
10°-20°	458.8	6.3
20°-30°	717.6	9.9
30°-40°	797.8	11.0
40°-50°	707.8	9.7
50°-60°	551.5	7.6
60°-70°	361.1	5.0
70°-80°	177.6	2.4
80°-90°	47.4	0.7
90°-100°	78.5	1.1
100°-110°	232.5	3.2
110°-120°	394.6	5.4
120°-130°	520.4	7.2
130°-140°	584.4	8.0
140°-150°	574.3	7.9
150°-160°	483.0	6.6
160°-170°	321.4	4.4
170°-180°	112.5	1.5
0°-30°	1328.5	18.3
0°-40°	2126.3	29.2
0°-60°	3385.7	46.5
0°-90°	3971.7	54.6
90°-120°	705.6	9.7
90°-150°	2384.7	32.8
90°-180°	3302.0	45.4
0°-180°	7273.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1570	1570	1570	1570	1570	
5°	1814	1569	1386	1569	1814	183
15°	2404	1500	1031	1500	2404	683
25°	2592	1372	812	1372	2592	1150
35°	1596	1192	679	1192	1596	1001
45°	816	954	572	954	816	646
55°	487	684	426	684	487	443
65°	285	429	239	429	285	286
75°	132	211	113	211	132	145
85°	32	48	32	48	32	36
90°	28	3	28	3	28	15
95°	73	55	73	55	73	76
105°	225	214	225	214	225	237
115°	398	401	398	401	398	393
125°	580	584	580	584	580	517
135°	755	754	755	754	755	583
145°	917	916	917	916	917	574
155°	1048	1049	1048	1049	1048	483
165°	1139	1142	1139	1142	1139	321
175°	1183	1188	1183	1188	1183	112
180°	1190	1190	1190	1190	1190	



TEST NUMBER: P333010-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1655.8	1660.4	1655.8	1655.3	1650.3	1648.8	1646.7	1640.1	1628.0	1621.0	1622.5
5°	1813.9	1829.8	1820.9	1819.6	1805.8	1791.8	1783.0	1762.8	1741.2	1726.7	1714.7
7.5°	1996.9	2006.0	2000.4	1991.5	1969.0	1956.3	1935.8	1909.1	1870.5	1841.0	1814.1
10°	2121.4	2128.9	2126.5	2110.0	2093.5	2060.0	2041.1	2003.7	1955.0	1916.4	1880.4
12.5°	2243.8	2251.9	2229.7	2230.4	2199.3	2172.9	2142.8	2095.8	2039.6	1989.8	1944.6
15°	2403.5	2393.3	2393.3	2380.7	2345.9	2309.2	2278.2	2228.9	2158.1	2098.6	2036.0
17.5°	2528.4	2532.0	2526.7	2497.0	2469.6	2431.7	2374.9	2317.3	2251.5	2171.7	2107.7
20°	2603.3	2603.3	2597.6	2577.4	2542.0	2501.5	2440.2	2377.5	2294.0	2213.7	2141.6
22.5°	2633.7	2635.7	2629.0	2612.3	2580.5	2540.9	2488.7	2425.1	2339.1	2248.6	2159.3
25°	2591.9	2604.0	2605.2	2600.8	2591.3	2567.2	2522.4	2457.2	2380.0	2282.0	2185.9
27.5°	2379.6	2394.8	2408.2	2430.0	2459.1	2474.3	2476.3	2443.2	2375.8	2281.5	2184.8
30°	2168.1	2180.8	2221.9	2275.7	2317.5	2355.4	2388.3	2397.1	2359.2	2274.4	2172.6
32.5°	1933.4	1950.6	1991.7	2049.5	2119.1	2183.3	2257.2	2294.9	2293.9	2243.1	2148.8
35°	1596.4	1609.1	1647.0	1707.7	1791.2	1886.7	2003.7	2094.8	2156.8	2152.4	2094.8
37.5°	1287.5	1301.8	1340.1	1390.4	1471.4	1589.7	1702.9	1828.4	1943.0	2007.4	1988.1
40°	1119.5	1120.1	1157.5	1209.3	1285.2	1388.3	1511.6	1650.7	1778.5	1882.9	1903.1
42.5°	986.9	987.1	1011.7	1067.6	1122.3	1219.3	1337.0	1475.2	1624.8	1745.3	1798.9
45°	815.9	821.6	841.9	875.4	918.4	1000.6	1094.8	1223.2	1390.8	1533.7	1622.9
47.5°	690.9	699.3	712.2	739.5	773.8	828.5	906.5	1021.8	1158.2	1315.4	1442.3
50°	626.1	627.4	643.9	659.0	688.8	732.5	800.7	896.8	1022.1	1173.2	1314.3
52.5°	570.5	570.2	580.1	599.4	623.5	657.5	712.6	800.2	911.2	1046.8	1192.4
55°	487.0	490.2	497.7	512.9	531.3	555.3	599.0	664.7	752.0	867.8	1000.0
57.5°	423.5	425.2	431.1	437.5	454.4	471.8	504.6	550.2	623.9	718.7	841.9
60°	382.0	382.6	384.5	394.0	407.3	423.7	445.9	484.5	546.4	633.1	730.6
62.5°	341.5	342.7	345.6	352.5	362.8	374.1	397.4	428.3	479.7	553.7	641.4
65°	284.6	285.3	289.7	292.2	300.4	310.5	327.6	348.5	383.9	445.9	512.3
67.5°	237.8	237.8	238.1	241.5	247.2	253.9	264.1	280.8	307.5	345.6	404.2
70°	207.5	207.5	208.7	210.6	213.8	219.4	225.1	237.8	257.5	288.4	333.4
72.5°	179.1	179.6	180.9	181.3	182.9	187.6	191.8	199.9	214.4	237.8	274.1
75°	131.6	133.5	136.7	139.2	142.3	141.6	146.1	151.1	155.6	169.5	190.4
77.5°	97.9	96.9	97.3	99.4	99.8	100.4	103.6	107.5	110.8	117.4	124.8
80°	74.6	74.6	76.5	77.2	76.5	77.2	80.3	82.2	83.5	86.0	93.0
82.5°	56.4	57.4	56.8	57.4	57.8	58.5	61.1	61.5	62.7	63.8	66.7
85°	31.6	32.2	32.9	31.6	31.6	31.6	32.9	33.5	34.8	34.1	35.4
87.5°	16.6	16.1	16.5	16.4	16.8	16.2	16.4	17.2	15.9	16.2	15.8
90°	27.6	27.2	26.8	26.4	26.0	25.2	23.9	22.7	21.5	20.3	18.6
92.5°	40.9	40.6	40.4	40.2	39.8	39.4	38.7	37.9	37.2	36.4	35.3
95°	72.7	72.7	72.7	72.7	72.7	72.4	71.8	71.1	70.6	69.9	68.5
97.5°	113.9	113.9	113.9	113.9	113.9	113.6	112.8	112.1	111.4	110.6	108.9
100°	142.7	142.7	142.7	142.7	142.7	142.4	142.0	141.6	141.2	140.9	138.9
102.5°	175.1	174.9	174.8	174.6	174.4	174.0	173.5	172.9	172.3	171.7	170.1
105°	224.6	223.9	223.3	222.8	222.1	221.5	220.9	220.3	219.7	219.0	218.2
107.5°	272.8	272.8	272.9	272.9	273.0	272.7	272.1	271.6	271.0	270.4	270.3
110°	307.4	306.8	306.2	305.5	304.9	304.8	305.2	305.6	306.1	306.5	306.7



TEST NUMBER: P333010-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	342.8	342.6	342.5	342.4	342.2	342.2	342.3	342.4	342.5	342.5	342.9
115°	397.6	397.8	398.0	398.2	398.4	398.6	398.8	399.0	399.3	399.4	399.8
117.5°	449.9	450.3	450.7	451.1	451.5	452.0	452.7	453.4	454.2	454.9	455.1
120°	489.6	489.3	488.8	488.4	488.0	488.3	489.3	490.4	491.4	492.4	493.0
122.5°	522.8	523.5	524.3	525.0	525.7	526.4	527.1	527.8	528.5	529.2	529.5
125°	579.8	580.2	580.7	581.1	581.5	581.9	582.3	582.7	583.1	583.5	583.7
127.5°	632.6	633.0	633.3	633.7	634.0	634.3	634.8	635.2	635.6	636.0	636.3
130°	667.3	668.0	668.9	669.7	670.5	671.1	671.5	671.9	672.4	672.8	672.8
132.5°	704.1	704.4	704.7	705.0	705.4	705.8	706.2	706.5	706.9	707.4	707.6
135°	754.7	755.3	755.9	756.5	757.2	757.6	758.0	758.5	758.9	759.3	759.3
137.5°	807.9	807.8	807.6	807.6	807.4	807.6	808.1	808.7	809.2	809.7	809.4
140°	840.3	840.5	840.7	840.9	841.1	841.3	841.5	841.7	841.9	842.1	842.1
142.5°	872.7	872.7	872.7	872.8	872.8	872.9	872.9	873.0	873.0	873.1	873.2
145°	916.7	917.3	917.9	918.5	919.1	919.6	919.7	920.0	920.1	920.4	920.1
147.5°	961.2	961.4	961.6	961.9	962.0	962.2	962.4	962.6	962.7	962.9	963.1
150°	988.5	988.6	988.9	989.0	989.3	989.4	989.4	989.4	989.4	989.4	989.4
152.5°	1013.5	1014.0	1014.5	1015.1	1015.7	1015.7	1015.2	1014.6	1014.2	1013.7	1013.5
155°	1048.3	1049.1	1050.0	1050.8	1051.5	1051.5	1050.8	1050.0	1049.1	1048.3	1048.5
157.5°	1079.4	1080.1	1080.8	1081.5	1082.2	1082.2	1081.6	1081.0	1080.4	1079.7	1079.8
160°	1097.1	1098.1	1099.1	1100.1	1101.1	1101.4	1100.7	1100.1	1099.5	1098.9	1099.1
162.5°	1115.5	1116.5	1117.5	1118.6	1119.6	1119.5	1118.4	1117.3	1116.2	1115.1	1115.3
165°	1139.4	1140.2	1141.1	1141.9	1142.6	1142.5	1141.2	1140.0	1138.8	1137.6	1138.0
167.5°	1156.5	1157.8	1159.0	1160.3	1161.6	1161.6	1160.4	1159.1	1157.9	1156.7	1156.7
170°	1166.1	1167.5	1168.9	1170.4	1171.8	1172.0	1170.7	1169.5	1168.2	1167.0	1166.8
172.5°	1174.2	1175.6	1177.0	1178.5	1180.0	1180.0	1178.5	1177.2	1175.8	1174.4	1174.3
175°	1182.6	1184.1	1185.5	1186.9	1188.4	1188.4	1186.9	1185.5	1184.1	1182.6	1182.9
177.5°	1187.1	1188.4	1189.7	1191.0	1192.3	1192.4	1191.3	1190.1	1189.0	1187.8	1187.8
180°	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0



TEST NUMBER: P333010-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1617.4	1610.3	1606.8	1598.7	1589.0	1584.0	1579.5	1572.9	1564.2	1555.1	1548.6
5°	1699.5	1684.3	1665.3	1642.6	1622.3	1602.7	1585.6	1568.6	1549.0	1528.8	1508.5
7.5°	1783.8	1753.9	1721.6	1684.3	1648.0	1615.0	1584.6	1555.5	1522.7	1493.2	1466.3
10°	1842.5	1802.0	1757.1	1709.6	1662.2	1621.0	1580.6	1543.9	1503.4	1467.4	1437.0
12.5°	1890.0	1842.5	1788.4	1729.3	1672.3	1622.5	1576.0	1528.2	1482.2	1443.1	1402.6
15°	1968.9	1903.8	1831.1	1760.2	1686.2	1618.5	1555.9	1500.2	1447.8	1392.7	1354.2
17.5°	2023.2	1945.9	1857.5	1772.3	1685.0	1605.1	1532.9	1466.6	1406.0	1349.9	1303.9
20°	2055.6	1970.2	1872.2	1775.4	1677.4	1592.0	1514.2	1440.8	1378.2	1317.5	1270.0
22.5°	2073.8	1979.3	1872.2	1770.8	1669.3	1576.8	1491.4	1415.0	1346.8	1286.1	1233.6
25°	2079.6	1978.4	1869.0	1752.6	1641.3	1543.3	1454.7	1371.8	1295.9	1235.2	1179.6
27.5°	2071.6	1952.3	1840.3	1720.9	1606.0	1502.7	1409.7	1322.6	1246.7	1181.5	1124.4
30°	2059.4	1931.6	1811.4	1687.5	1571.1	1471.8	1373.7	1290.3	1211.2	1143.5	1086.0
32.5°	2033.1	1906.3	1777.0	1650.0	1532.2	1429.8	1336.8	1252.8	1175.3	1106.1	1045.0
35°	1980.9	1852.5	1712.1	1581.8	1466.1	1359.9	1272.6	1191.6	1117.6	1043.6	979.1
37.5°	1912.2	1781.1	1641.4	1498.7	1382.8	1282.5	1202.5	1126.5	1054.2	986.7	915.2
40°	1847.5	1728.0	1583.7	1442.1	1323.2	1226.4	1152.4	1083.5	1010.7	943.6	872.2
42.5°	1769.1	1667.2	1521.5	1379.3	1261.9	1168.7	1099.8	1032.4	966.2	901.2	826.6
45°	1638.2	1561.0	1424.3	1287.8	1169.5	1077.1	1013.9	954.4	896.2	834.2	764.1
47.5°	1488.1	1435.8	1318.0	1178.1	1068.7	985.6	924.5	875.8	826.6	764.7	703.1
50°	1383.9	1350.4	1236.5	1108.7	1004.4	927.9	865.2	819.7	778.6	719.1	664.1
52.5°	1272.6	1254.7	1158.6	1036.4	935.6	860.5	807.1	766.0	724.5	675.1	623.6
55°	1103.0	1112.5	1030.9	925.3	830.4	767.2	718.5	684.4	649.0	607.2	567.4
57.5°	929.8	964.4	909.7	816.9	728.0	669.6	632.9	604.1	574.4	539.8	505.7
60°	826.0	855.1	824.1	742.5	664.7	610.4	576.2	554.1	524.3	492.7	466.8
62.5°	724.8	756.0	737.6	671.7	599.4	552.7	522.5	501.9	479.8	452.3	425.3
65°	597.7	617.9	609.1	563.6	512.3	472.5	444.7	429.4	409.2	389.0	365.0
67.5°	457.8	496.9	491.7	467.5	423.3	392.1	373.9	360.5	342.1	327.0	310.7
70°	376.4	412.4	411.8	392.1	368.1	339.0	326.4	315.0	298.5	284.0	270.7
72.5°	308.0	341.0	345.9	330.9	314.5	292.5	280.4	272.5	256.5	246.5	235.8
75°	215.7	239.7	246.1	246.1	238.4	227.0	216.3	211.3	199.9	191.0	184.7
77.5°	141.4	156.6	166.4	168.7	169.9	166.1	157.2	153.7	145.0	141.8	135.7
80°	99.9	110.0	121.4	125.2	128.4	127.1	123.3	120.8	112.6	109.4	106.9
82.5°	69.1	74.6	84.0	92.4	91.4	94.7	91.4	89.4	83.3	82.1	79.5
85°	36.0	36.7	37.9	43.6	46.8	48.1	48.7	47.5	45.6	45.6	41.1
87.5°	15.5	14.7	15.4	15.0	15.1	16.6	17.7	17.7	16.7	15.6	14.6
90°	17.0	15.4	13.7	11.7	9.5	7.3	5.0	2.8	5.0	7.3	9.5
92.5°	34.1	33.0	31.8	30.0	27.4	24.9	22.3	19.7	22.3	24.9	27.4
95°	67.1	65.7	64.2	62.6	60.8	58.9	57.0	55.2	57.0	58.9	60.8
97.5°	107.3	105.6	103.9	102.3	100.8	99.4	97.9	96.5	97.9	99.4	100.8
100°	137.1	135.3	133.5	132.1	131.3	130.5	129.7	128.9	129.7	130.5	131.3
102.5°	168.4	166.7	165.0	164.1	163.7	163.3	163.0	162.7	163.0	163.3	163.7
105°	217.4	216.6	215.8	215.2	215.1	214.8	214.7	214.4	214.7	214.8	215.1
107.5°	270.1	270.1	269.9	269.7	269.5	269.3	269.0	268.7	269.0	269.3	269.5
110°	306.9	307.1	307.3	307.2	306.8	306.3	305.9	305.5	305.9	306.3	306.8



TEST NUMBER: P333010-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	343.3	343.6	344.0	344.2	344.1	344.0	344.0	343.8	344.0	344.0	344.1
115°	400.3	400.7	401.1	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2
117.5°	455.4	455.7	456.0	456.1	455.9	455.7	455.6	455.4	455.6	455.7	455.9
120°	493.6	494.2	494.9	494.7	493.9	493.1	492.3	491.5	492.3	493.1	493.9
122.5°	529.8	530.0	530.4	530.4	530.0	529.7	529.3	529.0	529.3	529.7	530.0
125°	583.9	584.2	584.3	584.4	584.4	584.4	584.4	584.4	584.4	584.4	584.4
127.5°	636.6	636.9	637.3	637.2	636.5	635.9	635.3	634.7	635.3	635.9	636.5
130°	672.8	672.8	672.8	672.5	671.8	671.2	670.7	670.0	670.7	671.2	671.8
132.5°	707.7	707.9	708.1	707.9	707.4	707.0	706.5	706.1	706.5	707.0	707.4
135°	759.3	759.3	759.3	758.7	757.5	756.2	755.0	753.8	755.0	756.2	757.5
137.5°	809.1	808.7	808.4	807.9	807.4	806.8	806.3	805.6	806.3	806.8	807.4
140°	842.1	842.1	842.1	841.9	841.5	841.1	840.7	840.3	840.7	841.1	841.5
142.5°	873.4	873.5	873.7	873.6	873.1	872.7	872.4	872.0	872.4	872.7	873.1
145°	920.0	919.7	919.6	919.0	918.2	917.4	916.6	915.8	916.6	917.4	918.2
147.5°	963.2	963.4	963.5	963.1	962.1	961.2	960.2	959.2	960.2	961.2	962.1
150°	989.4	989.4	989.4	989.0	988.2	987.4	986.5	985.7	986.5	987.4	988.2
152.5°	1013.4	1013.2	1013.0	1012.7	1012.2	1011.7	1011.2	1010.7	1011.2	1011.7	1012.2
155°	1048.7	1048.9	1049.1	1049.2	1049.2	1049.2	1049.2	1049.2	1049.2	1049.2	1049.2
157.5°	1079.8	1079.9	1079.9	1080.1	1080.5	1080.9	1081.2	1081.6	1081.2	1080.9	1080.5
160°	1099.3	1099.5	1099.7	1099.9	1100.1	1100.3	1100.6	1100.7	1100.6	1100.3	1100.1
162.5°	1115.6	1115.7	1115.9	1116.3	1116.8	1117.4	1117.8	1118.4	1117.8	1117.4	1116.8
165°	1138.4	1138.8	1139.2	1139.7	1140.3	1140.9	1141.5	1142.2	1141.5	1140.9	1140.3
167.5°	1156.6	1156.6	1156.5	1157.0	1157.8	1158.6	1159.5	1160.4	1159.5	1158.6	1157.8
170°	1166.6	1166.4	1166.2	1166.6	1167.6	1168.6	1169.7	1170.7	1169.7	1168.6	1167.6
172.5°	1174.3	1174.3	1174.2	1174.6	1175.4	1176.3	1177.2	1178.1	1177.2	1176.3	1175.4
175°	1183.0	1183.3	1183.4	1184.1	1185.1	1186.1	1187.2	1188.2	1187.2	1186.1	1185.1
177.5°	1187.8	1187.8	1187.8	1188.2	1189.1	1189.9	1190.6	1191.5	1190.6	1189.9	1189.1
180°	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0



TEST NUMBER: P333010-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1541.5	1536.4	1529.9	1522.3	1513.1	1505.1	1501.5	1504.6	1506.1	1502.1	1501.5
5°	1494.5	1478.8	1466.1	1447.2	1431.9	1419.3	1410.5	1406.7	1407.9	1397.8	1395.3
7.5°	1441.9	1423.1	1402.3	1379.8	1358.8	1340.2	1330.5	1325.2	1314.5	1309.9	1302.2
10°	1407.9	1382.6	1362.4	1335.8	1311.8	1289.7	1278.9	1270.0	1259.3	1254.2	1243.5
12.5°	1373.0	1343.6	1321.4	1293.8	1269.2	1242.6	1232.3	1215.9	1199.0	1188.4	1174.6
15°	1323.8	1288.4	1261.2	1228.3	1199.2	1168.9	1141.6	1111.3	1099.9	1075.9	1061.9
17.5°	1266.2	1230.3	1196.7	1152.5	1107.6	1069.9	1040.9	1011.9	994.4	979.1	972.0
20°	1228.3	1195.4	1148.6	1097.3	1047.4	1005.7	982.2	963.3	944.3	933.6	926.0
22.5°	1192.4	1150.3	1096.0	1040.7	990.7	958.1	938.3	918.8	903.3	893.1	883.0
25°	1132.2	1077.1	1019.5	956.3	922.2	893.7	872.2	856.3	846.9	833.6	828.5
27.5°	1070.3	1003.6	940.2	897.6	862.1	836.0	817.3	805.4	793.4	784.9	778.3
30°	1022.7	955.1	898.1	857.6	821.6	800.1	784.9	771.0	761.5	754.6	749.5
32.5°	975.7	908.0	860.2	816.7	788.2	767.2	751.0	740.6	733.2	724.2	721.1
35°	907.6	847.6	805.8	766.6	737.4	718.5	705.8	695.1	688.8	686.3	684.4
37.5°	842.2	793.0	748.1	716.0	690.1	675.1	660.2	654.9	650.5	646.0	648.1
40°	800.7	754.6	714.7	680.6	659.7	643.3	634.4	628.0	624.2	624.2	624.2
42.5°	764.8	719.6	680.8	650.2	629.3	615.4	605.5	600.2	599.0	598.5	601.5
45°	709.0	667.3	628.0	602.8	585.0	571.2	565.5	561.0	561.0	563.6	564.2
47.5°	653.7	614.7	583.1	554.8	538.6	529.9	525.0	522.7	522.9	525.5	528.4
50°	619.8	581.2	550.2	525.0	509.8	501.5	497.1	495.9	497.1	497.1	501.5
52.5°	582.9	548.3	517.8	496.6	479.4	471.7	469.3	467.5	468.3	470.3	472.2
55°	528.8	497.7	468.7	448.5	435.8	430.7	425.0	425.6	424.4	425.6	425.6
57.5°	474.5	446.6	419.6	403.5	392.4	385.1	378.8	380.6	378.7	378.5	377.5
60°	439.6	409.2	387.7	373.2	360.5	354.2	348.5	349.7	347.8	346.6	344.0
62.5°	401.6	376.4	355.8	341.8	331.7	324.3	318.6	317.3	313.0	308.6	303.1
65°	346.6	325.7	307.4	294.1	284.6	278.9	274.5	270.7	261.2	251.1	246.1
67.5°	293.1	278.1	260.9	249.7	242.0	234.6	226.1	219.6	210.7	205.2	202.0
70°	258.6	244.2	229.6	218.8	210.6	203.7	194.2	189.7	183.4	180.9	177.8
72.5°	225.8	212.2	198.8	189.0	180.2	174.8	167.4	163.0	160.2	159.1	156.0
75°	175.9	165.1	155.0	146.1	139.2	135.4	132.2	129.0	127.8	122.1	118.9
77.5°	128.3	121.2	114.9	108.5	103.6	101.1	95.0	91.3	89.2	86.5	85.9
80°	99.9	94.9	88.6	84.8	77.8	75.3	72.7	72.1	71.5	70.8	70.2
82.5°	75.2	70.1	63.8	61.5	59.6	58.1	56.6	55.9	55.3	55.7	55.5
85°	37.9	35.4	35.4	34.8	34.1	33.5	32.9	32.9	32.2	32.9	32.2
87.5°	15.0	14.9	15.2	14.5	15.4	15.7	15.4	15.7	16.4	15.7	15.8
90°	11.7	13.7	15.4	17.0	18.6	20.3	21.5	22.7	23.9	25.2	26.0
92.5°	30.0	31.8	33.0	34.1	35.3	36.4	37.2	37.9	38.7	39.4	39.8
95°	62.6	64.2	65.7	67.1	68.5	69.9	70.6	71.1	71.8	72.4	72.7
97.5°	102.3	103.9	105.6	107.3	108.9	110.6	111.4	112.1	112.8	113.6	113.9
100°	132.1	133.5	135.3	137.1	138.9	140.9	141.2	141.6	142.0	142.4	142.7
102.5°	164.1	165.0	166.7	168.4	170.1	171.7	172.3	172.9	173.5	174.0	174.4
105°	215.2	215.8	216.6	217.4	218.2	219.0	219.7	220.3	220.9	221.5	222.1
107.5°	269.7	269.9	270.1	270.1	270.3	270.4	271.0	271.6	272.1	272.7	273.0
110°	307.2	307.3	307.1	306.9	306.7	306.5	306.1	305.6	305.2	304.8	304.9



TEST NUMBER: P333010-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	344.2	344.0	343.6	343.3	342.9	342.5	342.5	342.4	342.3	342.2	342.2
115°	401.2	401.1	400.7	400.3	399.8	399.4	399.3	399.0	398.8	398.6	398.4
117.5°	456.1	456.0	455.7	455.4	455.1	454.9	454.2	453.4	452.7	452.0	451.5
120°	494.7	494.9	494.2	493.6	493.0	492.4	491.4	490.4	489.3	488.3	488.0
122.5°	530.4	530.4	530.0	529.8	529.5	529.2	528.5	527.8	527.1	526.4	525.7
125°	584.4	584.3	584.2	583.9	583.7	583.5	583.1	582.7	582.3	581.9	581.5
127.5°	637.2	637.3	636.9	636.6	636.3	636.0	635.6	635.2	634.8	634.3	634.0
130°	672.5	672.8	672.8	672.8	672.8	672.8	672.4	671.9	671.5	671.1	670.5
132.5°	707.9	708.1	707.9	707.7	707.6	707.4	706.9	706.5	706.2	705.8	705.4
135°	758.7	759.3	759.3	759.3	759.3	759.3	758.9	758.5	758.0	757.6	757.2
137.5°	807.9	808.4	808.7	809.1	809.4	809.7	809.2	808.7	808.1	807.6	807.4
140°	841.9	842.1	842.1	842.1	842.1	842.1	841.9	841.7	841.5	841.3	841.1
142.5°	873.6	873.7	873.5	873.4	873.2	873.1	873.0	873.0	872.9	872.9	872.8
145°	919.0	919.6	919.7	920.0	920.1	920.4	920.1	920.0	919.7	919.6	919.1
147.5°	963.1	963.5	963.4	963.2	963.1	962.9	962.7	962.6	962.4	962.2	962.0
150°	989.0	989.4	989.4	989.4	989.4	989.4	989.4	989.4	989.4	989.4	989.3
152.5°	1012.7	1013.0	1013.2	1013.4	1013.5	1013.7	1014.2	1014.6	1015.2	1015.7	1015.7
155°	1049.2	1049.1	1048.9	1048.7	1048.5	1048.3	1049.1	1050.0	1050.8	1051.5	1051.5
157.5°	1080.1	1079.9	1079.9	1079.8	1079.8	1079.7	1080.4	1081.0	1081.6	1082.2	1082.2
160°	1099.9	1099.7	1099.5	1099.3	1099.1	1098.9	1099.5	1100.1	1100.7	1101.4	1101.1
162.5°	1116.3	1115.9	1115.7	1115.6	1115.3	1115.1	1116.2	1117.3	1118.4	1119.5	1119.6
165°	1139.7	1139.2	1138.8	1138.4	1138.0	1137.6	1138.8	1140.0	1141.2	1142.5	1142.6
167.5°	1157.0	1156.5	1156.6	1156.6	1156.7	1156.7	1157.9	1159.1	1160.4	1161.6	1161.6
170°	1166.6	1166.2	1166.4	1166.6	1166.8	1167.0	1168.2	1169.5	1170.7	1172.0	1171.8
172.5°	1174.6	1174.2	1174.3	1174.3	1174.3	1174.4	1175.8	1177.2	1178.5	1180.0	1180.0
175°	1184.1	1183.4	1183.3	1183.0	1182.9	1182.6	1184.1	1185.5	1186.9	1188.4	1188.4
177.5°	1188.2	1187.8	1187.8	1187.8	1187.8	1187.8	1189.0	1190.1	1191.3	1192.4	1192.3
180°	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0



TEST NUMBER: P333010-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1498.5	1499.5	1496.0	1494.9	1496.0	1499.5	1498.5	1501.5	1502.1	1506.1	1504.6
5°	1390.2	1388.9	1385.8	1386.4	1385.8	1388.9	1390.2	1395.3	1397.8	1407.9	1406.7
7.5°	1297.6	1292.7	1294.0	1289.0	1294.0	1292.7	1297.6	1302.2	1309.9	1314.5	1325.2
10°	1241.0	1234.0	1228.3	1223.2	1228.3	1234.0	1241.0	1243.5	1254.2	1259.3	1270.0
12.5°	1163.6	1157.5	1149.9	1151.4	1149.9	1157.5	1163.6	1174.6	1188.4	1199.0	1215.9
15°	1053.7	1044.3	1029.0	1030.9	1029.0	1044.3	1053.7	1061.9	1075.9	1099.9	1111.3
17.5°	960.8	960.8	953.9	955.5	953.9	960.8	960.8	972.0	979.1	994.4	1011.9
20°	912.7	908.2	908.9	907.0	908.9	908.2	912.7	926.0	933.6	944.3	963.3
22.5°	879.2	873.9	869.4	865.5	869.4	873.9	879.2	883.0	893.1	903.3	918.8
25°	822.8	819.0	813.4	812.1	813.4	819.0	822.8	828.5	833.6	846.9	856.3
27.5°	773.2	772.5	770.2	767.3	770.2	772.5	773.2	778.3	784.9	793.4	805.4
30°	744.4	743.1	741.9	740.0	741.9	743.1	744.4	749.5	754.6	761.5	771.0
32.5°	718.7	717.9	716.6	716.8	716.6	717.9	718.7	721.1	724.2	733.2	740.6
35°	681.8	681.2	679.9	679.3	679.9	681.2	681.8	684.4	686.3	688.8	695.1
37.5°	647.5	649.0	648.3	648.2	648.3	649.0	647.5	648.1	646.0	650.5	654.9
40°	623.6	624.2	625.5	624.9	625.5	624.2	623.6	624.2	624.2	624.2	628.0
42.5°	603.9	604.0	605.8	603.6	605.8	604.0	603.9	601.5	598.5	599.0	600.2
45°	568.6	572.4	571.8	571.8	571.8	572.4	568.6	564.2	563.6	561.0	561.0
47.5°	530.0	533.3	534.2	534.1	534.2	533.3	530.0	528.4	525.5	522.9	522.7
50°	504.7	503.4	505.3	504.7	505.3	503.4	504.7	501.5	497.1	497.1	495.9
52.5°	473.9	474.1	474.0	473.3	474.0	474.1	473.9	472.2	470.3	468.3	467.5
55°	426.3	426.9	425.6	426.3	425.6	426.9	426.3	425.6	425.6	424.4	425.6
57.5°	374.7	371.6	372.9	371.4	372.9	371.6	374.7	377.5	378.5	378.7	380.6
60°	337.8	332.7	331.4	328.9	331.4	332.7	337.8	344.0	346.6	347.8	349.7
62.5°	296.3	292.7	288.4	290.4	288.4	292.7	296.3	303.1	308.6	313.0	317.3
65°	241.0	238.4	236.5	239.1	236.5	238.4	241.0	246.1	251.1	261.2	270.7
67.5°	199.5	198.1	198.1	196.9	198.1	198.1	199.5	202.0	205.2	210.7	219.6
70°	177.8	175.9	175.9	174.6	175.9	175.9	177.8	177.8	180.9	183.4	189.7
72.5°	155.4	153.6	154.1	153.3	154.1	153.6	155.4	156.0	159.1	160.2	163.0
75°	115.1	111.9	111.9	112.6	111.9	111.9	115.1	118.9	122.1	127.8	129.0
77.5°	85.9	85.2	86.1	85.0	86.1	85.2	85.9	85.9	86.5	89.2	91.3
80°	70.2	69.6	68.9	70.8	68.9	69.6	70.2	70.2	70.8	71.5	72.1
82.5°	54.5	54.4	54.3	56.6	54.3	54.4	54.5	55.5	55.7	55.3	55.9
85°	32.9	31.6	32.9	31.6	32.9	31.6	32.9	32.2	32.9	32.2	32.9
87.5°	17.0	16.5	16.1	16.6	16.1	16.5	17.0	15.8	15.7	16.4	15.7
90°	26.4	26.8	27.2	27.6	27.2	26.8	26.4	26.0	25.2	23.9	22.7
92.5°	40.2	40.4	40.6	40.9	40.6	40.4	40.2	39.8	39.4	38.7	37.9
95°	72.7	72.7	72.7	72.7	72.7	72.7	72.7	72.7	72.4	71.8	71.1
97.5°	113.9	113.9	113.9	113.9	113.9	113.9	113.9	113.9	113.6	112.8	112.1
100°	142.7	142.7	142.7	142.7	142.7	142.7	142.7	142.7	142.4	142.0	141.6
102.5°	174.6	174.8	174.9	175.1	174.9	174.8	174.6	174.4	174.0	173.5	172.9
105°	222.8	223.3	223.9	224.6	223.9	223.3	222.8	222.1	221.5	220.9	220.3
107.5°	272.9	272.9	272.8	272.8	272.8	272.9	272.9	273.0	272.7	272.1	271.6
110°	305.5	306.2	306.8	307.4	306.8	306.2	305.5	304.9	304.8	305.2	305.6



TEST NUMBER: P333010-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	342.4	342.5	342.6	342.8	342.6	342.5	342.4	342.2	342.2	342.3	342.4
115°	398.2	398.0	397.8	397.6	397.8	398.0	398.2	398.4	398.6	398.8	399.0
117.5°	451.1	450.7	450.3	449.9	450.3	450.7	451.1	451.5	452.0	452.7	453.4
120°	488.4	488.8	489.3	489.6	489.3	488.8	488.4	488.0	488.3	489.3	490.4
122.5°	525.0	524.3	523.5	522.8	523.5	524.3	525.0	525.7	526.4	527.1	527.8
125°	581.1	580.7	580.2	579.8	580.2	580.7	581.1	581.5	581.9	582.3	582.7
127.5°	633.7	633.3	633.0	632.6	633.0	633.3	633.7	634.0	634.3	634.8	635.2
130°	669.7	668.9	668.0	667.3	668.0	668.9	669.7	670.5	671.1	671.5	671.9
132.5°	705.0	704.7	704.4	704.1	704.4	704.7	705.0	705.4	705.8	706.2	706.5
135°	756.5	755.9	755.3	754.7	755.3	755.9	756.5	757.2	757.6	758.0	758.5
137.5°	807.6	807.6	807.8	807.9	807.8	807.6	807.6	807.4	807.6	808.1	808.7
140°	840.9	840.7	840.5	840.3	840.5	840.7	840.9	841.1	841.3	841.5	841.7
142.5°	872.8	872.7	872.7	872.7	872.7	872.7	872.8	872.8	872.9	872.9	873.0
145°	918.5	917.9	917.3	916.7	917.3	917.9	918.5	919.1	919.6	919.7	920.0
147.5°	961.9	961.6	961.4	961.2	961.4	961.6	961.9	962.0	962.2	962.4	962.6
150°	989.0	988.9	988.6	988.5	988.6	988.9	989.0	989.3	989.4	989.4	989.4
152.5°	1015.1	1014.5	1014.0	1013.5	1014.0	1014.5	1015.1	1015.7	1015.7	1015.2	1014.6
155°	1050.8	1050.0	1049.1	1048.3	1049.1	1050.0	1050.8	1051.5	1051.5	1050.8	1050.0
157.5°	1081.5	1080.8	1080.1	1079.4	1080.1	1080.8	1081.5	1082.2	1082.2	1081.6	1081.0
160°	1100.1	1099.1	1098.1	1097.1	1098.1	1099.1	1100.1	1101.1	1101.4	1100.7	1100.1
162.5°	1118.6	1117.5	1116.5	1115.5	1116.5	1117.5	1118.6	1119.6	1119.5	1118.4	1117.3
165°	1141.9	1141.1	1140.2	1139.4	1140.2	1141.1	1141.9	1142.6	1142.5	1141.2	1140.0
167.5°	1160.3	1159.0	1157.8	1156.5	1157.8	1159.0	1160.3	1161.6	1161.6	1160.4	1159.1
170°	1170.4	1168.9	1167.5	1166.1	1167.5	1168.9	1170.4	1171.8	1172.0	1170.7	1169.5
172.5°	1178.5	1177.0	1175.6	1174.2	1175.6	1177.0	1178.5	1180.0	1180.0	1178.5	1177.2
175°	1186.9	1185.5	1184.1	1182.6	1184.1	1185.5	1186.9	1188.4	1188.4	1186.9	1185.5
177.5°	1191.0	1189.7	1188.4	1187.1	1188.4	1189.7	1191.0	1192.3	1192.4	1191.3	1190.1
180°	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0



TEST NUMBER: P333010-927
 CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1501.5	1505.1	1513.1	1522.3	1529.9	1536.4	1541.5	1548.6	1555.1	1564.2	1572.9
5°	1410.5	1419.3	1431.9	1447.2	1466.1	1478.8	1494.5	1508.5	1528.8	1549.0	1568.6
7.5°	1330.5	1340.2	1358.8	1379.8	1402.3	1423.1	1441.9	1466.3	1493.2	1522.7	1555.5
10°	1278.9	1289.7	1311.8	1335.8	1362.4	1382.6	1407.9	1437.0	1467.4	1503.4	1543.9
12.5°	1232.3	1242.6	1269.2	1293.8	1321.4	1343.6	1373.0	1402.6	1443.1	1482.2	1528.2
15°	1141.6	1168.9	1199.2	1228.3	1261.2	1288.4	1323.8	1354.2	1392.7	1447.8	1500.2
17.5°	1040.9	1069.9	1107.6	1152.5	1196.7	1230.3	1266.2	1303.9	1349.9	1406.0	1466.6
20°	982.2	1005.7	1047.4	1097.3	1148.6	1195.4	1228.3	1270.0	1317.5	1378.2	1440.8
22.5°	938.3	958.1	990.7	1040.7	1096.0	1150.3	1192.4	1233.6	1286.1	1346.8	1415.0
25°	872.2	893.7	922.2	956.3	1019.5	1077.1	1132.2	1179.6	1235.2	1295.9	1371.8
27.5°	817.3	836.0	862.1	897.6	940.2	1003.6	1070.3	1124.4	1181.5	1246.7	1322.6
30°	784.9	800.1	821.6	857.6	898.1	955.1	1022.7	1086.0	1143.5	1211.2	1290.3
32.5°	751.0	767.2	788.2	816.7	860.2	908.0	975.7	1045.0	1106.1	1175.3	1252.8
35°	705.8	718.5	737.4	766.6	805.8	847.6	907.6	979.1	1043.6	1117.6	1191.6
37.5°	660.2	675.1	690.1	716.0	748.1	793.0	842.2	915.2	986.7	1054.2	1126.5
40°	634.4	643.3	659.7	680.6	714.7	754.6	800.7	872.2	943.6	1010.7	1083.5
42.5°	605.5	615.4	629.3	650.2	680.8	719.6	764.8	826.6	901.2	966.2	1032.4
45°	565.5	571.2	585.0	602.8	628.0	667.3	709.0	764.1	834.2	896.2	954.4
47.5°	525.0	529.9	538.6	554.8	583.1	614.7	653.7	703.1	764.7	826.6	875.8
50°	497.1	501.5	509.8	525.0	550.2	581.2	619.8	664.1	719.1	778.6	819.7
52.5°	469.3	471.7	479.4	496.6	517.8	548.3	582.9	623.6	675.1	724.5	766.0
55°	425.0	430.7	435.8	448.5	468.7	497.7	528.8	567.4	607.2	649.0	684.4
57.5°	378.8	385.1	392.4	403.5	419.6	446.6	474.5	505.7	539.8	574.4	604.1
60°	348.5	354.2	360.5	373.2	387.7	409.2	439.6	466.8	492.7	524.3	554.1
62.5°	318.6	324.3	331.7	341.8	355.8	376.4	401.6	425.3	452.3	479.8	501.9
65°	274.5	278.9	284.6	294.1	307.4	325.7	346.6	365.0	389.0	409.2	429.4
67.5°	226.1	234.6	242.0	249.7	260.9	278.1	293.1	310.7	327.0	342.1	360.5
70°	194.2	203.7	210.6	218.8	229.6	244.2	258.6	270.7	284.0	298.5	315.0
72.5°	167.4	174.8	180.2	189.0	198.8	212.2	225.8	235.8	246.5	256.5	272.5
75°	132.2	135.4	139.2	146.1	155.0	165.1	175.9	184.7	191.0	199.9	211.3
77.5°	95.0	101.1	103.6	108.5	114.9	121.2	128.3	135.7	141.8	145.0	153.7
80°	72.7	75.3	77.8	84.8	88.6	94.9	99.9	106.9	109.4	112.6	120.8
82.5°	56.6	58.1	59.6	61.5	63.8	70.1	75.2	79.5	82.1	83.3	89.4
85°	32.9	33.5	34.1	34.8	35.4	35.4	37.9	41.1	45.6	45.6	47.5
87.5°	15.4	15.7	15.4	14.5	15.2	14.9	15.0	14.6	15.6	16.7	17.7
90°	21.5	20.3	18.6	17.0	15.4	13.7	11.7	9.5	7.3	5.0	2.8
92.5°	37.2	36.4	35.3	34.1	33.0	31.8	30.0	27.4	24.9	22.3	19.7
95°	70.6	69.9	68.5	67.1	65.7	64.2	62.6	60.8	58.9	57.0	55.2
97.5°	111.4	110.6	108.9	107.3	105.6	103.9	102.3	100.8	99.4	97.9	96.5
100°	141.2	140.9	138.9	137.1	135.3	133.5	132.1	131.3	130.5	129.7	128.9
102.5°	172.3	171.7	170.1	168.4	166.7	165.0	164.1	163.7	163.3	163.0	162.7
105°	219.7	219.0	218.2	217.4	216.6	215.8	215.2	215.1	214.8	214.7	214.4
107.5°	271.0	270.4	270.3	270.1	270.1	269.9	269.7	269.5	269.3	269.0	268.7
110°	306.1	306.5	306.7	306.9	307.1	307.3	307.2	306.8	306.3	305.9	305.5



TEST NUMBER: P333010-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	342.5	342.5	342.9	343.3	343.6	344.0	344.2	344.1	344.0	344.0	343.8
115°	399.3	399.4	399.8	400.3	400.7	401.1	401.2	401.2	401.2	401.2	401.2
117.5°	454.2	454.9	455.1	455.4	455.7	456.0	456.1	455.9	455.7	455.6	455.4
120°	491.4	492.4	493.0	493.6	494.2	494.9	494.7	493.9	493.1	492.3	491.5
122.5°	528.5	529.2	529.5	529.8	530.0	530.4	530.4	530.0	529.7	529.3	529.0
125°	583.1	583.5	583.7	583.9	584.2	584.3	584.4	584.4	584.4	584.4	584.4
127.5°	635.6	636.0	636.3	636.6	636.9	637.3	637.2	636.5	635.9	635.3	634.7
130°	672.4	672.8	672.8	672.8	672.8	672.8	672.5	671.8	671.2	670.7	670.0
132.5°	706.9	707.4	707.6	707.7	707.9	708.1	707.9	707.4	707.0	706.5	706.1
135°	758.9	759.3	759.3	759.3	759.3	759.3	758.7	757.5	756.2	755.0	753.8
137.5°	809.2	809.7	809.4	809.1	808.7	808.4	807.9	807.4	806.8	806.3	805.6
140°	841.9	842.1	842.1	842.1	842.1	842.1	841.9	841.5	841.1	840.7	840.3
142.5°	873.0	873.1	873.2	873.4	873.5	873.7	873.6	873.1	872.7	872.4	872.0
145°	920.1	920.4	920.1	920.0	919.7	919.6	919.0	918.2	917.4	916.6	915.8
147.5°	962.7	962.9	963.1	963.2	963.4	963.5	963.1	962.1	961.2	960.2	959.2
150°	989.4	989.4	989.4	989.4	989.4	989.4	989.0	988.2	987.4	986.5	985.7
152.5°	1014.2	1013.7	1013.5	1013.4	1013.2	1013.0	1012.7	1012.2	1011.7	1011.2	1010.7
155°	1049.1	1048.3	1048.5	1048.7	1048.9	1049.1	1049.2	1049.2	1049.2	1049.2	1049.2
157.5°	1080.4	1079.7	1079.8	1079.8	1079.9	1079.9	1080.1	1080.5	1080.9	1081.2	1081.6
160°	1099.5	1098.9	1099.1	1099.3	1099.5	1099.7	1099.9	1100.1	1100.3	1100.6	1100.7
162.5°	1116.2	1115.1	1115.3	1115.6	1115.7	1115.9	1116.3	1116.8	1117.4	1117.8	1118.4
165°	1138.8	1137.6	1138.0	1138.4	1138.8	1139.2	1139.7	1140.3	1140.9	1141.5	1142.2
167.5°	1157.9	1156.7	1156.7	1156.6	1156.6	1156.5	1157.0	1157.8	1158.6	1159.5	1160.4
170°	1168.2	1167.0	1166.8	1166.6	1166.4	1166.2	1166.6	1167.6	1168.6	1169.7	1170.7
172.5°	1175.8	1174.4	1174.3	1174.3	1174.3	1174.2	1174.6	1175.4	1176.3	1177.2	1178.1
175°	1184.1	1182.6	1182.9	1183.0	1183.3	1183.4	1184.1	1185.1	1186.1	1187.2	1188.2
177.5°	1189.0	1187.8	1187.8	1187.8	1187.8	1187.8	1188.2	1189.1	1189.9	1190.6	1191.5
180°	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0



TEST NUMBER: P333010-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1579.5	1584.0	1589.0	1598.7	1606.8	1610.3	1617.4	1622.5	1621.0	1628.0	1640.1
5°	1585.6	1602.7	1622.3	1642.6	1665.3	1684.3	1699.5	1714.7	1726.7	1741.2	1762.8
7.5°	1584.6	1615.0	1648.0	1684.3	1721.6	1753.9	1783.8	1814.1	1841.0	1870.5	1909.1
10°	1580.6	1621.0	1662.2	1709.6	1757.1	1802.0	1842.5	1880.4	1916.4	1955.0	2003.7
12.5°	1576.0	1622.5	1672.3	1729.3	1788.4	1842.5	1890.0	1944.6	1989.8	2039.6	2095.8
15°	1555.9	1618.5	1686.2	1760.2	1831.1	1903.8	1968.9	2036.0	2098.6	2158.1	2228.9
17.5°	1532.9	1605.1	1685.0	1772.3	1857.5	1945.9	2023.2	2107.7	2171.7	2251.5	2317.3
20°	1514.2	1592.0	1677.4	1775.4	1872.2	1970.2	2055.6	2141.6	2213.7	2294.0	2377.5
22.5°	1491.4	1576.8	1669.3	1770.8	1872.2	1979.3	2073.8	2159.3	2248.6	2339.1	2425.1
25°	1454.7	1543.3	1641.3	1752.6	1869.0	1978.4	2079.6	2185.9	2282.0	2380.0	2457.2
27.5°	1409.7	1502.7	1606.0	1720.9	1840.3	1952.3	2071.6	2184.8	2281.5	2375.8	2443.2
30°	1373.7	1471.8	1571.1	1687.5	1811.4	1931.6	2059.4	2172.6	2274.4	2359.2	2397.1
32.5°	1336.8	1429.8	1532.2	1650.0	1777.0	1906.3	2033.1	2148.8	2243.1	2293.9	2294.9
35°	1272.6	1359.9	1466.1	1581.8	1712.1	1852.5	1980.9	2094.8	2152.4	2156.8	2094.8
37.5°	1202.5	1282.5	1382.8	1498.7	1641.4	1781.1	1912.2	1988.1	2007.4	1943.0	1828.4
40°	1152.4	1226.4	1323.2	1442.1	1583.7	1728.0	1847.5	1903.1	1882.9	1778.5	1650.7
42.5°	1099.8	1168.7	1261.9	1379.3	1521.5	1667.2	1769.1	1798.9	1745.3	1624.8	1475.2
45°	1013.9	1077.1	1169.5	1287.8	1424.3	1561.0	1638.2	1622.9	1533.7	1390.8	1223.2
47.5°	924.5	985.6	1068.7	1178.1	1318.0	1435.8	1488.1	1442.3	1315.4	1158.2	1021.8
50°	865.2	927.9	1004.4	1108.7	1236.5	1350.4	1383.9	1314.3	1173.2	1022.1	896.8
52.5°	807.1	860.5	935.6	1036.4	1158.6	1254.7	1272.6	1192.4	1046.8	911.2	800.2
55°	718.5	767.2	830.4	925.3	1030.9	1112.5	1103.0	1000.0	867.8	752.0	664.7
57.5°	632.9	669.6	728.0	816.9	909.7	964.4	929.8	841.9	718.7	623.9	550.2
60°	576.2	610.4	664.7	742.5	824.1	855.1	826.0	730.6	633.1	546.4	484.5
62.5°	522.5	552.7	599.4	671.7	737.6	756.0	724.8	641.4	553.7	479.7	428.3
65°	444.7	472.5	512.3	563.6	609.1	617.9	597.7	512.3	445.9	383.9	348.5
67.5°	373.9	392.1	423.3	467.5	491.7	496.9	457.8	404.2	345.6	307.5	280.8
70°	326.4	339.0	368.1	392.1	411.8	412.4	376.4	333.4	288.4	257.5	237.8
72.5°	280.4	292.5	314.5	330.9	345.9	341.0	308.0	274.1	237.8	214.4	199.9
75°	216.3	227.0	238.4	246.1	246.1	239.7	215.7	190.4	169.5	155.6	151.1
77.5°	157.2	166.1	169.9	168.7	166.4	156.6	141.4	124.8	117.4	110.8	107.5
80°	123.3	127.1	128.4	125.2	121.4	110.0	99.9	93.0	86.0	83.5	82.2
82.5°	91.4	94.7	91.4	92.4	84.0	74.6	69.1	66.7	63.8	62.7	61.5
85°	48.7	48.1	46.8	43.6	37.9	36.7	36.0	35.4	34.1	34.8	33.5
87.5°	17.7	16.6	15.1	15.0	15.4	14.7	15.5	15.8	16.2	15.9	17.2
90°	5.0	7.3	9.5	11.7	13.7	15.4	17.0	18.6	20.3	21.5	22.7
92.5°	22.3	24.9	27.4	30.0	31.8	33.0	34.1	35.3	36.4	37.2	37.9
95°	57.0	58.9	60.8	62.6	64.2	65.7	67.1	68.5	69.9	70.6	71.1
97.5°	97.9	99.4	100.8	102.3	103.9	105.6	107.3	108.9	110.6	111.4	112.1
100°	129.7	130.5	131.3	132.1	133.5	135.3	137.1	138.9	140.9	141.2	141.6
102.5°	163.0	163.3	163.7	164.1	165.0	166.7	168.4	170.1	171.7	172.3	172.9
105°	214.7	214.8	215.1	215.2	215.8	216.6	217.4	218.2	219.0	219.7	220.3
107.5°	269.0	269.3	269.5	269.7	269.9	270.1	270.1	270.3	270.4	271.0	271.6
110°	305.9	306.3	306.8	307.2	307.3	307.1	306.9	306.7	306.5	306.1	305.6



TEST NUMBER: P333010-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	344.0	344.0	344.1	344.2	344.0	343.6	343.3	342.9	342.5	342.5	342.4
115°	401.2	401.2	401.2	401.2	401.1	400.7	400.3	399.8	399.4	399.3	399.0
117.5°	455.6	455.7	455.9	456.1	456.0	455.7	455.4	455.1	454.9	454.2	453.4
120°	492.3	493.1	493.9	494.7	494.9	494.2	493.6	493.0	492.4	491.4	490.4
122.5°	529.3	529.7	530.0	530.4	530.4	530.0	529.8	529.5	529.2	528.5	527.8
125°	584.4	584.4	584.4	584.4	584.3	584.2	583.9	583.7	583.5	583.1	582.7
127.5°	635.3	635.9	636.5	637.2	637.3	636.9	636.6	636.3	636.0	635.6	635.2
130°	670.7	671.2	671.8	672.5	672.8	672.8	672.8	672.8	672.8	672.4	671.9
132.5°	706.5	707.0	707.4	707.9	708.1	707.9	707.7	707.6	707.4	706.9	706.5
135°	755.0	756.2	757.5	758.7	759.3	759.3	759.3	759.3	759.3	758.9	758.5
137.5°	806.3	806.8	807.4	807.9	808.4	808.7	809.1	809.4	809.7	809.2	808.7
140°	840.7	841.1	841.5	841.9	842.1	842.1	842.1	842.1	842.1	841.9	841.7
142.5°	872.4	872.7	873.1	873.6	873.7	873.5	873.4	873.2	873.1	873.0	873.0
145°	916.6	917.4	918.2	919.0	919.6	919.7	920.0	920.1	920.4	920.1	920.0
147.5°	960.2	961.2	962.1	963.1	963.5	963.4	963.2	963.1	962.9	962.7	962.6
150°	986.5	987.4	988.2	989.0	989.4	989.4	989.4	989.4	989.4	989.4	989.4
152.5°	1011.2	1011.7	1012.2	1012.7	1013.0	1013.2	1013.4	1013.5	1013.7	1014.2	1014.6
155°	1049.2	1049.2	1049.2	1049.2	1049.1	1048.9	1048.7	1048.5	1048.3	1049.1	1050.0
157.5°	1081.2	1080.9	1080.5	1080.1	1079.9	1079.9	1079.8	1079.8	1079.7	1080.4	1081.0
160°	1100.6	1100.3	1100.1	1099.9	1099.7	1099.5	1099.3	1099.1	1098.9	1099.5	1100.1
162.5°	1117.8	1117.4	1116.8	1116.3	1115.9	1115.7	1115.6	1115.3	1115.1	1116.2	1117.3
165°	1141.5	1140.9	1140.3	1139.7	1139.2	1138.8	1138.4	1138.0	1137.6	1138.8	1140.0
167.5°	1159.5	1158.6	1157.8	1157.0	1156.5	1156.6	1156.6	1156.7	1156.7	1157.9	1159.1
170°	1169.7	1168.6	1167.6	1166.6	1166.2	1166.4	1166.6	1166.8	1167.0	1168.2	1169.5
172.5°	1177.2	1176.3	1175.4	1174.6	1174.2	1174.3	1174.3	1174.3	1174.4	1175.8	1177.2
175°	1187.2	1186.1	1185.1	1184.1	1183.4	1183.3	1183.0	1182.9	1182.6	1184.1	1185.5
177.5°	1190.6	1189.9	1189.1	1188.2	1187.8	1187.8	1187.8	1187.8	1187.8	1189.0	1190.1
180°	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0



TEST NUMBER: P333010-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1646.7	1648.8	1650.3	1655.3	1655.8	1660.4	1655.8
5°	1783.0	1791.8	1805.8	1819.6	1820.9	1829.8	1813.9
7.5°	1935.8	1956.3	1969.0	1991.5	2000.4	2006.0	1996.9
10°	2041.1	2060.0	2093.5	2110.0	2126.5	2128.9	2121.4
12.5°	2142.8	2172.9	2199.3	2230.4	2229.7	2251.9	2243.8
15°	2278.2	2309.2	2345.9	2380.7	2393.3	2393.3	2403.5
17.5°	2374.9	2431.7	2469.6	2497.0	2526.7	2532.0	2528.4
20°	2440.2	2501.5	2542.0	2577.4	2597.6	2603.3	2603.3
22.5°	2488.7	2540.9	2580.5	2612.3	2629.0	2635.7	2633.7
25°	2522.4	2567.2	2591.3	2600.8	2605.2	2604.0	2591.9
27.5°	2476.3	2474.3	2459.1	2430.0	2408.2	2394.8	2379.6
30°	2388.3	2355.4	2317.5	2275.7	2221.9	2180.8	2168.1
32.5°	2257.2	2183.3	2119.1	2049.5	1991.7	1950.6	1933.4
35°	2003.7	1886.7	1791.2	1707.7	1647.0	1609.1	1596.4
37.5°	1702.9	1589.7	1471.4	1390.4	1340.1	1301.8	1287.5
40°	1511.6	1388.3	1285.2	1209.3	1157.5	1120.1	1119.5
42.5°	1337.0	1219.3	1122.3	1067.6	1011.7	987.1	986.9
45°	1094.8	1000.6	918.4	875.4	841.9	821.6	815.9
47.5°	906.5	828.5	773.8	739.5	712.2	699.3	690.9
50°	800.7	732.5	688.8	659.0	643.9	627.4	626.1
52.5°	712.6	657.5	623.5	599.4	580.1	570.2	570.5
55°	599.0	555.3	531.3	512.9	497.7	490.2	487.0
57.5°	504.6	471.8	454.4	437.5	431.1	425.2	423.5
60°	445.9	423.7	407.3	394.0	384.5	382.6	382.0
62.5°	397.4	374.1	362.8	352.5	345.6	342.7	341.5
65°	327.6	310.5	300.4	292.2	289.7	285.3	284.6
67.5°	264.1	253.9	247.2	241.5	238.1	237.8	237.8
70°	225.1	219.4	213.8	210.6	208.7	207.5	207.5
72.5°	191.8	187.6	182.9	181.3	180.9	179.6	179.1
75°	146.1	141.6	142.3	139.2	136.7	133.5	131.6
77.5°	103.6	100.4	99.8	99.4	97.3	96.9	97.9
80°	80.3	77.2	76.5	77.2	76.5	74.6	74.6
82.5°	61.1	58.5	57.8	57.4	56.8	57.4	56.4
85°	32.9	31.6	31.6	31.6	32.9	32.2	31.6
87.5°	16.4	16.2	16.8	16.4	16.5	16.1	16.6
90°	23.9	25.2	26.0	26.4	26.8	27.2	27.6
92.5°	38.7	39.4	39.8	40.2	40.4	40.6	40.9
95°	71.8	72.4	72.7	72.7	72.7	72.7	72.7
97.5°	112.8	113.6	113.9	113.9	113.9	113.9	113.9
100°	142.0	142.4	142.7	142.7	142.7	142.7	142.7
102.5°	173.5	174.0	174.4	174.6	174.8	174.9	175.1
105°	220.9	221.5	222.1	222.8	223.3	223.9	224.6
107.5°	272.1	272.7	273.0	272.9	272.9	272.8	272.8
110°	305.2	304.8	304.9	305.5	306.2	306.8	307.4



TEST NUMBER: P333010-927

CATALOG NUMBER: SA4XXRDIP-C1195D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	342.3	342.2	342.2	342.4	342.5	342.6	342.8
115°	398.8	398.6	398.4	398.2	398.0	397.8	397.6
117.5°	452.7	452.0	451.5	451.1	450.7	450.3	449.9
120°	489.3	488.3	488.0	488.4	488.8	489.3	489.6
122.5°	527.1	526.4	525.7	525.0	524.3	523.5	522.8
125°	582.3	581.9	581.5	581.1	580.7	580.2	579.8
127.5°	634.8	634.3	634.0	633.7	633.3	633.0	632.6
130°	671.5	671.1	670.5	669.7	668.9	668.0	667.3
132.5°	706.2	705.8	705.4	705.0	704.7	704.4	704.1
135°	758.0	757.6	757.2	756.5	755.9	755.3	754.7
137.5°	808.1	807.6	807.4	807.6	807.6	807.8	807.9
140°	841.5	841.3	841.1	840.9	840.7	840.5	840.3
142.5°	872.9	872.9	872.8	872.8	872.7	872.7	872.7
145°	919.7	919.6	919.1	918.5	917.9	917.3	916.7
147.5°	962.4	962.2	962.0	961.9	961.6	961.4	961.2
150°	989.4	989.4	989.3	989.0	988.9	988.6	988.5
152.5°	1015.2	1015.7	1015.7	1015.1	1014.5	1014.0	1013.5
155°	1050.8	1051.5	1051.5	1050.8	1050.0	1049.1	1048.3
157.5°	1081.6	1082.2	1082.2	1081.5	1080.8	1080.1	1079.4
160°	1100.7	1101.4	1101.1	1100.1	1099.1	1098.1	1097.1
162.5°	1118.4	1119.5	1119.6	1118.6	1117.5	1116.5	1115.5
165°	1141.2	1142.5	1142.6	1141.9	1141.1	1140.2	1139.4
167.5°	1160.4	1161.6	1161.6	1160.3	1159.0	1157.8	1156.5
170°	1170.7	1172.0	1171.8	1170.4	1168.9	1167.5	1166.1
172.5°	1178.5	1180.0	1180.0	1178.5	1177.0	1175.6	1174.2
175°	1186.9	1188.4	1188.4	1186.9	1185.5	1184.1	1182.6
177.5°	1191.3	1192.4	1192.3	1191.0	1189.7	1188.4	1187.1
180°	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0

(END OF REPORT)