

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332996-927

Luminaire Tested: **SA4XXRDIP-C1195D590U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332996-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D590U927-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5491.1 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332996-927

CATALOG NUMBER: SA4XXRDIP-C1195D590U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332996-927

CATALOG NUMBER: SA4XXRDIP-C1195D590U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74	70	
1	103	98	94	91	97	93	90	87	83	81	78	74	72	71	66	65	63	63	63	63	59	
2	94	86	80	75	88	82	76	72	73	69	65	66	62	60	59	56	54	54	54	54	50	
3	86	76	69	63	81	72	66	60	65	60	56	58	54	51	52	49	46	46	46	46	43	
4	79	68	60	54	74	64	57	52	58	52	48	52	48	44	47	43	40	40	40	40	37	
5	72	61	52	46	68	58	50	45	52	46	41	47	42	38	42	38	35	35	35	35	32	
6	67	55	46	40	63	52	45	39	47	41	36	43	38	34	39	34	31	31	31	31	29	
7	62	50	41	36	59	47	40	35	43	37	32	39	34	30	35	31	28	28	28	28	26	
8	58	45	37	32	55	43	36	31	39	33	29	36	31	27	33	28	25	25	25	25	23	
9	54	41	34	29	51	40	33	28	36	30	26	33	28	24	30	26	23	23	23	23	21	
10	50	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	21	21	21	19	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13337	13337	13337
5°	13367	13203	13285
10°	13283	13045	13045
15°	13131	12771	12676
20°	12921	12411	12182
25°	12653	11989	11685
30°	12393	11544	11060
35°	12105	11083	10435
40°	11758	10559	9759
45°	11439	10038	9070
50°	11074	9437	8341
55°	10683	8812	7548
60°	10253	8128	6739
65°	9859	7272	5945
70°	9286	6331	5046
75°	8562	5250	4105
80°	7471	3998	3766
85°	6326	3631	3399



TEST NUMBER: P332996-927

CATALOG NUMBER: SA4XXRDIP-C1195D590U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.2	2.8
10°-20°	432.8	7.9
20°-30°	624.9	11.4
30°-40°	708.3	12.9
40°-50°	684.0	12.5
50°-60°	568.8	10.4
60°-70°	392.8	7.2
70°-80°	199.1	3.6
80°-90°	52.3	1.0
90°-100°	166.1	3.0
100°-110°	345.8	6.3
110°-120°	309.7	5.6
120°-130°	260.5	4.7
130°-140°	217.2	4.0
140°-150°	166.0	3.0
150°-160°	116.6	2.1
160°-170°	68.6	1.2
170°-180°	22.3	0.4
0°-30°	1212.9	22.1
0°-40°	1921.2	35.0
0°-60°	3174.0	57.8
0°-90°	3818.2	69.5
90°-120°	821.6	15.0
90°-150°	1465.3	26.7
90°-180°	1673.0	30.5
0°-180°	5491.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1652	1652	1652	1652	1652	
5°	1650	1644	1629	1641	1639	156
15°	1571	1559	1528	1525	1517	442
25°	1420	1396	1346	1325	1312	654
35°	1228	1186	1125	1083	1059	767
45°	1002	953	879	819	794	772
55°	759	707	626	563	536	679
65°	516	460	381	328	311	509
75°	274	227	168	140	132	290
85°	68	44	39	37	37	77
90°	0	4	8	9	10	4
95°	15	47	368	182	110	17
105°	53	77	296	638	636	56
115°	93	117	264	508	610	92
125°	130	154	263	432	487	115
135°	154	183	261	384	436	119
145°	178	203	259	324	356	111
155°	202	218	252	286	298	93
165°	220	227	242	256	260	62
175°	230	230	232	235	234	22
180°	230	230	230	230	230	



TEST NUMBER: P332996-927

CATALOG NUMBER: SA4XXRDIP-C1195D590U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0
2.5°	1656.1	1655.2	1654.3	1653.4	1652.5	1650.8	1648.4	1645.8	1643.4	1640.9	1643.4
5°	1649.5	1648.4	1647.3	1646.2	1645.0	1642.7	1639.4	1636.0	1632.7	1629.3	1632.1
7.5°	1634.6	1633.4	1632.2	1631.0	1629.8	1627.1	1622.7	1618.3	1613.9	1609.6	1611.4
10°	1620.4	1619.0	1617.6	1616.2	1614.8	1611.5	1606.5	1601.5	1596.4	1591.3	1592.4
12.5°	1602.2	1600.6	1598.9	1597.3	1595.7	1591.9	1585.9	1580.0	1574.0	1568.0	1568.8
15°	1571.1	1568.5	1566.1	1563.5	1561.0	1556.2	1549.2	1542.1	1535.1	1528.0	1527.5
17.5°	1533.4	1529.7	1526.1	1522.4	1518.8	1512.8	1504.3	1495.9	1487.4	1479.0	1477.4
20°	1504.0	1500.4	1496.7	1493.1	1489.5	1482.8	1473.3	1463.7	1454.1	1444.6	1442.3
22.5°	1471.6	1467.6	1463.5	1459.4	1455.2	1448.1	1437.8	1427.6	1417.4	1407.2	1403.7
25°	1420.5	1415.5	1410.4	1405.4	1400.3	1392.0	1380.5	1369.0	1357.5	1345.9	1341.2
27.5°	1366.9	1360.6	1354.2	1347.9	1341.5	1332.2	1319.9	1307.6	1295.2	1282.9	1277.0
30°	1329.5	1322.5	1315.4	1308.4	1301.4	1291.3	1278.0	1264.8	1251.6	1238.4	1231.4
32.5°	1290.0	1282.1	1274.1	1266.2	1258.3	1247.5	1233.8	1220.2	1206.5	1192.9	1184.7
35°	1228.3	1219.2	1210.3	1201.3	1192.3	1180.7	1166.7	1152.7	1138.6	1124.6	1115.0
37.5°	1162.3	1152.9	1143.7	1134.4	1125.1	1112.7	1097.2	1081.6	1066.0	1050.4	1039.7
40°	1115.7	1106.4	1097.2	1087.9	1078.6	1066.0	1050.0	1033.9	1017.9	1001.9	990.1
42.5°	1071.2	1061.4	1051.7	1042.0	1032.3	1019.1	1002.3	985.6	969.0	952.3	940.2
45°	1001.9	991.4	981.0	970.7	960.3	946.6	929.8	912.9	896.0	879.2	865.4
47.5°	930.3	919.5	908.8	898.0	887.3	873.1	855.6	838.0	820.5	803.0	788.7
50°	881.7	870.7	859.8	848.8	837.8	823.3	805.3	787.3	769.4	751.4	737.4
52.5°	832.1	821.3	810.6	799.9	789.2	774.5	756.1	737.7	719.2	700.8	686.5
55°	759.0	747.7	736.5	725.2	714.0	699.3	681.0	662.7	644.4	626.1	611.6
57.5°	686.6	674.9	663.2	651.6	639.8	625.0	607.0	589.0	571.0	553.0	538.2
60°	635.0	623.8	612.5	601.3	590.0	575.4	557.5	539.5	521.4	503.4	488.9
62.5°	588.4	576.8	565.1	553.4	541.7	526.6	508.2	489.7	471.3	452.9	439.3
65°	516.1	504.0	491.9	479.8	467.8	452.7	434.7	416.8	398.8	380.7	368.7
67.5°	440.9	429.4	417.8	406.2	394.7	380.5	363.8	347.1	330.4	313.7	303.3
70°	393.4	381.6	369.8	358.0	346.2	332.2	316.2	300.2	284.2	268.2	258.9
72.5°	342.8	332.2	321.5	310.8	300.1	287.2	272.0	256.9	241.8	226.6	218.7
75°	274.5	264.1	253.7	243.3	232.9	221.1	207.9	194.6	181.5	168.3	161.8
77.5°	205.2	196.4	187.5	178.7	169.8	160.1	149.4	138.8	128.1	117.4	113.6
80°	160.7	152.5	144.3	136.2	128.0	119.8	111.3	102.9	94.4	86.0	85.2
82.5°	122.2	114.7	107.3	99.7	92.3	86.1	81.3	76.4	71.6	66.8	66.1
85°	68.3	62.7	57.0	51.4	45.8	42.6	41.7	40.9	40.1	39.2	38.7
87.5°	23.4	21.8	20.2	18.5	16.8	15.8	16.1	15.8	15.8	15.8	15.4
90°	0.5	1.3	2.7	3.2	3.6	3.6	6.3	6.3	7.2	8.2	7.7
92.5°	5.1	7.5	11.7	17.3	23.8	33.3	56.2	91.3	125.5	143.3	119.4
95°	14.9	16.2	20.8	26.7	37.5	56.5	95.8	169.9	277.9	368.3	378.7
97.5°	26.8	26.8	30.7	36.0	45.4	61.3	91.6	152.7	260.2	387.9	475.8
100°	34.4	34.4	37.5	42.9	51.5	66.0	92.6	143.7	235.9	363.3	479.0
102.5°	41.6	42.3	45.1	50.1	58.4	72.1	96.3	141.2	219.6	332.6	451.9
105°	52.8	54.3	56.5	61.9	70.0	83.2	104.8	142.4	205.7	296.4	402.7
107.5°	65.4	66.2	68.5	74.3	82.1	95.0	114.9	149.0	203.1	276.2	362.9
110°	73.7	74.5	76.8	82.2	90.4	102.6	122.5	154.1	203.8	269.3	343.0



TEST NUMBER: P332996-927

CATALOG NUMBER: SA4XXRDIP-C1195D590U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	81.6	82.5	85.2	90.2	98.3	110.5	129.7	159.5	206.0	266.1	331.8
115°	93.1	94.4	97.6	102.1	110.7	122.9	141.0	168.1	210.2	264.4	321.3
117.5°	105.0	106.3	109.1	114.1	122.1	134.8	151.9	176.9	214.5	263.9	316.6
120°	113.0	113.9	117.0	122.0	129.7	142.4	159.5	183.0	217.9	263.9	314.1
122.5°	120.2	121.1	124.3	128.9	137.3	149.6	166.8	188.8	221.1	263.6	311.2
125°	129.7	131.5	134.2	139.2	147.7	160.4	176.7	197.5	225.9	263.0	306.4
127.5°	138.1	139.6	142.8	148.5	157.4	170.2	185.9	205.0	229.8	262.0	300.0
130°	142.8	144.6	148.2	155.0	163.6	176.7	192.0	209.7	232.7	261.7	296.0
132.5°	147.5	148.9	153.7	160.1	169.4	181.7	197.1	214.4	235.3	261.3	292.4
135°	154.1	155.9	160.4	168.1	177.6	189.3	204.2	220.5	239.1	260.7	286.9
137.5°	160.7	162.4	167.4	174.7	184.6	195.7	209.7	224.9	241.3	260.6	282.3
140°	165.4	166.8	171.7	179.4	188.9	199.7	213.3	227.8	243.1	260.3	279.7
142.5°	170.5	171.8	176.4	183.7	192.9	203.4	216.6	229.9	244.5	260.3	277.6
145°	177.6	179.0	183.5	189.8	198.4	208.3	220.1	232.3	245.4	259.4	273.9
147.5°	185.6	186.1	190.0	196.5	203.7	212.7	223.7	234.3	245.8	257.8	270.5
150°	190.7	191.2	194.8	200.2	207.0	215.6	225.5	235.4	245.8	256.7	268.0
152.5°	195.4	195.5	199.1	204.1	210.2	218.1	227.0	236.1	245.1	254.8	265.1
155°	202.0	202.5	205.2	209.7	214.7	221.4	229.1	236.8	244.0	252.2	260.7
157.5°	208.4	208.4	211.0	214.4	218.8	224.1	230.7	236.8	242.9	249.4	256.4
160°	212.4	212.4	214.2	217.4	220.9	225.9	231.4	236.8	241.8	247.2	253.1
162.5°	216.0	215.6	217.1	219.9	223.2	227.0	232.1	236.8	240.7	245.0	250.2
165°	220.1	220.1	220.9	223.2	225.5	228.2	232.3	235.9	238.6	241.8	245.4
167.5°	224.1	223.7	224.1	225.9	227.1	229.2	232.2	234.8	236.5	238.5	241.1
170°	225.9	225.5	225.9	227.3	228.2	229.6	231.8	234.1	235.0	236.3	238.1
172.5°	227.8	227.3	227.4	228.4	228.9	229.9	231.5	233.4	233.5	234.2	235.6
175°	229.6	229.1	229.1	229.6	230.0	230.0	230.9	232.3	231.8	231.8	232.7
177.5°	230.4	230.0	229.7	230.0	230.0	230.0	230.4	231.1	230.4	230.4	230.8
180°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0



TEST NUMBER: P332996-927

CATALOG NUMBER: SA4XXRDIP-C1195D590U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0
2.5°	1645.8	1648.4	1650.8	1651.9	1651.7	1651.5	1651.2	1651.1
5°	1634.9	1637.7	1640.5	1641.6	1641.1	1640.5	1640.0	1639.4
7.5°	1613.1	1614.9	1616.8	1617.2	1616.3	1615.4	1614.5	1613.6
10°	1593.6	1594.7	1595.9	1595.9	1594.7	1593.6	1592.4	1591.3
12.5°	1569.4	1570.1	1570.7	1570.3	1568.8	1567.2	1565.6	1564.0
15°	1526.9	1526.4	1525.8	1524.6	1522.6	1520.6	1518.7	1516.7
17.5°	1475.8	1474.3	1472.7	1470.4	1467.4	1464.4	1461.5	1458.5
20°	1440.1	1437.8	1435.6	1432.7	1429.0	1425.4	1421.7	1418.0
22.5°	1400.4	1397.0	1393.7	1390.5	1387.5	1384.5	1381.6	1378.6
25°	1336.3	1331.6	1326.8	1323.0	1320.2	1317.4	1314.5	1311.8
27.5°	1271.1	1265.2	1259.3	1254.3	1250.3	1246.3	1242.2	1238.2
30°	1224.3	1217.3	1210.3	1204.5	1200.0	1195.6	1191.0	1186.5
32.5°	1176.5	1168.4	1160.2	1154.1	1149.8	1145.5	1141.2	1136.9
35°	1105.4	1095.9	1086.3	1079.0	1074.0	1068.9	1063.8	1058.8
37.5°	1029.0	1018.4	1007.7	999.8	994.7	989.7	984.7	979.6
40°	978.3	966.5	954.7	946.2	941.1	936.0	931.1	926.0
42.5°	928.2	916.2	904.1	895.5	890.2	884.9	879.6	874.3
45°	851.6	837.8	824.0	814.6	809.6	804.5	799.5	794.4
47.5°	774.4	760.2	745.9	735.9	730.4	724.8	719.2	713.7
50°	723.3	709.2	695.1	685.5	680.2	674.8	669.5	664.1
52.5°	672.2	658.0	643.6	633.7	628.2	622.7	617.0	611.5
55°	596.9	582.3	567.7	557.7	552.4	547.0	541.7	536.3
57.5°	523.4	508.5	493.7	484.3	480.2	476.1	472.1	468.0
60°	474.2	459.6	445.0	435.5	430.9	426.4	421.9	417.4
62.5°	425.9	412.4	398.9	390.3	386.7	383.2	379.5	376.0
65°	356.6	344.5	332.4	324.6	321.3	317.9	314.6	311.2
67.5°	292.9	282.5	272.1	265.1	261.3	257.6	253.9	250.2
70°	249.6	240.3	231.1	225.1	222.2	219.4	216.6	213.8
72.5°	210.8	202.9	195.0	189.7	187.1	184.6	182.0	179.4
75°	155.3	148.9	142.4	138.3	136.7	134.9	133.2	131.6
77.5°	109.9	106.1	102.3	100.2	99.7	99.2	98.7	98.2
80°	84.4	83.5	82.6	82.1	81.8	81.5	81.3	81.0
82.5°	65.6	65.0	64.3	63.8	63.6	63.3	63.1	62.7
85°	38.1	37.5	37.0	36.7	36.7	36.7	36.7	36.7
87.5°	15.4	15.2	15.1	15.1	15.4	15.7	15.8	16.1
90°	8.2	8.6	9.0	9.0	9.5	9.9	9.5	9.5
92.5°	88.7	66.8	53.2	44.1	38.7	36.4	34.8	34.8
95°	334.9	264.8	204.2	160.4	138.3	124.3	116.1	110.3
97.5°	494.7	468.7	424.5	377.3	344.9	317.7	304.1	294.7
100°	545.0	554.1	531.9	498.4	459.1	431.6	418.0	414.4
102.5°	542.5	587.3	593.7	579.8	555.6	535.7	521.4	518.5
105°	506.1	584.3	629.1	647.6	648.5	644.8	638.5	635.8
107.5°	454.6	537.7	600.8	641.0	663.4	673.7	678.2	679.4
110°	423.4	501.6	567.1	616.9	649.0	667.9	676.0	680.1



TEST NUMBER: P332996-927

CATALOG NUMBER: SA4XXRDIP-C1195D590U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	400.7	469.8	531.7	581.4	617.8	640.8	652.2	658.8
115°	377.8	433.4	486.2	529.7	565.3	592.5	606.9	610.5
117.5°	366.5	412.6	454.2	490.9	521.4	544.2	558.8	561.7
120°	361.6	403.5	439.7	471.7	497.6	517.5	529.2	534.2
122.5°	357.2	397.8	430.6	458.8	480.5	497.6	507.5	512.5
125°	349.7	388.6	419.8	444.7	462.7	475.9	484.4	487.1
127.5°	340.7	377.9	409.0	432.5	450.8	462.4	469.6	472.3
130°	333.5	369.2	399.9	423.9	442.4	453.7	461.0	463.7
132.5°	325.9	359.4	389.4	413.4	431.6	444.3	451.1	453.9
135°	315.4	344.8	372.3	395.0	413.0	425.7	432.9	435.6
137.5°	305.9	330.8	354.0	374.5	391.3	403.9	409.8	413.0
140°	300.5	321.8	342.1	361.1	376.9	386.8	393.2	396.8
142.5°	295.5	314.2	331.6	348.1	362.0	371.3	376.9	379.4
145°	288.3	303.6	317.3	329.9	341.2	348.9	353.4	355.6
147.5°	282.4	294.6	305.5	315.4	323.8	330.3	333.7	334.6
150°	278.8	289.2	298.3	306.4	313.6	319.5	322.2	322.7
152.5°	274.8	283.8	292.1	298.8	304.9	309.7	311.3	311.8
155°	268.9	276.1	282.9	288.3	292.9	296.4	297.8	297.8
157.5°	262.4	268.5	274.2	278.5	282.0	284.7	285.5	285.5
160°	258.5	263.5	268.4	272.0	274.7	277.5	277.9	277.9
162.5°	254.5	258.7	262.6	265.9	267.9	270.6	271.1	270.7
165°	249.0	251.7	254.8	257.1	259.0	260.7	260.3	259.8
167.5°	243.7	245.7	248.3	249.6	250.6	251.7	251.6	251.3
170°	240.4	241.8	243.6	244.9	245.8	246.3	245.8	245.8
172.5°	237.5	238.5	239.6	240.6	241.1	241.6	241.1	240.4
175°	233.6	234.1	235.0	235.0	235.0	235.9	235.0	234.1
177.5°	231.1	231.5	231.5	231.8	231.5	231.8	231.1	230.4
180°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0

(END OF REPORT)