

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331311-840

Luminaire Tested: **SA2XXDIP-C485D725U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331311-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D725U840-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4855.7 lumens
Efficiency: N/A
Efficacy: 126.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331311-840
CATALOG NUMBER: SA2XXDIP-C485D725U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331311-840

CATALOG NUMBER: SA2XXDIP-C485D725U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	92	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	50	42	36	56	45	38	33	38	33	29	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	27	23	29	23	20	23	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12665	12665	12665
5°	12713	12530	12603
10°	12637	12403	12463
15°	12481	12242	12227
20°	12259	12000	11986
25°	12039	11703	11703
30°	11757	11432	11332
35°	11491	11105	10941
40°	11160	10779	10570
45°	10832	10453	10195
50°	10477	10115	9756
55°	10106	9723	9362
60°	9691	9255	8913
65°	9249	8787	8382
70°	8686	8224	7832
75°	7904	7573	7392
80°	7011	6797	6453
85°	5724	5446	4891



TEST NUMBER: P331311-840

CATALOG NUMBER: SA2XXDIP-C485D725U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.8	1.5
10°-20°	207.5	4.3
20°-30°	305.0	6.3
30°-40°	354.3	7.3
40°-50°	354.0	7.3
50°-60°	308.7	6.4
60°-70°	228.2	4.7
70°-80°	129.3	2.7
80°-90°	38.4	0.8
90°-100°	164.1	3.4
100°-110°	557.0	11.5
110°-120°	591.7	12.2
120°-130°	487.1	10.0
130°-140°	391.2	8.1
140°-150°	295.6	6.1
150°-160°	207.7	4.3
160°-170°	122.3	2.5
170°-180°	39.8	0.8
0°-30°	586.3	12.1
0°-40°	940.7	19.4
0°-60°	1603.3	33.0
0°-90°	1999.2	41.2
90°-120°	1312.8	27.0
90°-150°	2486.7	51.2
90°-180°	2856.0	58.8
0°-180°	4855.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	784	784	784	784	784	
5°	784	781	773	779	778	74
15°	747	742	732	735	732	210
25°	676	669	657	658	657	311
35°	583	575	563	559	555	364
45°	474	469	458	450	446	366
55°	359	354	345	337	333	321
65°	242	237	230	223	219	239
75°	127	125	121	117	118	135
85°	31	30	29	27	26	35
90°	1	11	27	26	26	3
95°	28	68	309	117	90	29
105°	96	145	585	1046	890	102
115°	170	214	490	1010	1171	168
125°	237	280	470	818	950	210
135°	278	332	465	688	787	215
145°	317	365	463	574	628	199
155°	361	390	449	508	528	166
165°	393	405	430	456	463	111
175°	410	410	414	419	418	39
180°	410	410	410	410	410	



TEST NUMBER: P331311-840

CATALOG NUMBER: SA2XXDIP-C485D725U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	788.0	787.3	786.7	786.0	785.3	784.3	782.7	781.3	779.8	778.3	779.7
5°	784.4	783.7	783.0	782.3	781.7	780.4	778.6	776.8	774.9	773.1	774.4
7.5°	777.4	776.4	775.4	774.3	773.3	771.8	769.9	768.1	766.2	764.3	765.7
10°	770.8	769.6	768.4	767.3	766.1	764.5	762.4	760.5	758.5	756.5	757.8
12.5°	761.7	760.7	759.6	758.6	757.6	756.1	754.1	752.0	750.0	748.0	748.9
15°	746.7	745.7	744.7	743.7	742.7	741.0	738.8	736.7	734.5	732.4	733.0
17.5°	727.3	726.4	725.4	724.4	723.4	721.8	719.5	717.3	715.1	712.9	713.7
20°	713.5	712.5	711.4	710.4	709.4	707.8	705.4	703.1	700.7	698.4	698.9
22.5°	699.6	698.2	696.8	695.4	694.0	692.2	689.9	687.7	685.5	683.3	683.4
25°	675.8	674.4	673.1	671.8	670.4	668.3	665.5	662.6	659.7	656.9	657.2
27.5°	648.6	647.4	646.2	645.0	643.8	642.1	639.9	637.5	635.3	633.1	632.6
30°	630.6	629.1	627.8	626.5	625.1	623.2	620.7	618.2	615.7	613.2	612.7
32.5°	611.2	610.2	609.0	607.9	606.9	605.0	602.4	599.8	597.1	594.5	593.6
35°	583.0	581.3	579.7	577.9	576.3	574.1	571.5	568.8	566.0	563.4	562.4
37.5°	551.2	549.7	548.3	546.7	545.2	543.2	540.5	537.9	535.1	532.5	531.2
40°	529.5	528.1	526.7	525.4	524.1	522.1	519.4	516.7	514.0	511.4	509.9
42.5°	508.4	507.0	505.6	504.3	503.0	501.0	498.3	495.6	492.9	490.2	488.6
45°	474.4	473.2	472.0	470.9	469.7	467.9	465.3	462.8	460.3	457.8	456.0
47.5°	440.6	439.5	438.4	437.3	436.2	434.3	431.7	429.1	426.5	423.8	421.9
50°	417.1	416.3	415.4	414.5	413.7	412.1	409.8	407.5	405.1	402.7	400.4
52.5°	394.2	393.0	391.9	390.8	389.7	388.1	385.9	383.6	381.4	379.2	377.3
55°	359.0	358.0	357.0	356.0	355.0	353.5	351.4	349.4	347.4	345.4	343.5
57.5°	323.7	322.9	322.0	321.3	320.5	319.0	316.8	314.6	312.4	310.1	308.1
60°	300.1	299.5	298.8	298.1	297.5	296.0	293.7	291.2	288.9	286.6	284.8
62.5°	277.2	276.2	275.1	274.0	273.0	271.6	269.7	267.9	266.1	264.3	262.6
65°	242.1	241.1	240.0	239.0	238.1	236.7	235.1	233.4	231.7	230.0	228.5
67.5°	206.3	205.5	204.7	203.9	203.1	202.0	200.5	198.9	197.4	195.9	194.8
70°	184.0	183.4	182.7	182.0	181.4	180.3	178.7	177.2	175.7	174.2	173.1
72.5°	161.1	160.5	159.8	159.1	158.4	157.6	156.6	155.6	154.7	153.7	152.5
75°	126.7	126.3	126.0	125.7	125.3	124.8	123.9	123.1	122.3	121.4	120.4
77.5°	95.9	95.3	94.8	94.2	93.6	93.2	92.9	92.5	92.2	91.9	91.4
80°	75.4	75.2	75.1	74.9	74.7	74.5	74.1	73.8	73.5	73.1	72.6
82.5°	56.1	56.0	56.0	56.0	55.9	55.8	55.6	55.4	55.2	55.0	54.4
85°	30.9	30.8	30.6	30.4	30.3	30.1	29.9	29.8	29.6	29.4	28.9
87.5°	11.0	11.2	11.6	11.6	11.7	11.9	12.4	13.2	13.9	13.8	13.2
90°	0.8	3.1	6.4	7.9	9.5	11.8	15.8	21.3	26.1	26.9	26.1
92.5°	9.6	13.9	19.6	23.0	28.4	35.9	53.7	78.8	101.2	102.6	86.6
95°	27.7	30.8	38.7	45.7	58.4	77.4	113.7	182.4	274.0	309.4	270.7
97.5°	45.0	49.3	57.7	68.4	82.9	104.3	150.0	245.7	397.9	528.3	554.2
100°	60.8	63.1	70.3	82.9	98.7	120.8	162.6	258.9	429.4	623.6	737.3
102.5°	75.3	77.1	84.1	96.7	113.2	135.3	174.0	259.5	417.5	626.8	805.5
105°	96.3	99.5	105.0	116.8	134.2	156.3	193.4	263.7	393.9	584.9	795.0
107.5°	119.1	121.6	126.9	137.8	155.0	177.3	213.3	274.6	382.2	540.1	725.6
110°	134.2	137.3	142.1	152.4	169.0	191.9	226.5	283.4	379.7	518.7	682.1



TEST NUMBER: P331311-840

CATALOG NUMBER: SA2XXDIP-C485D725U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	148.0	151.3	156.6	166.2	182.2	205.7	239.2	292.9	380.3	504.7	651.8
115°	169.8	173.7	178.4	187.8	203.7	225.0	258.9	307.1	383.6	489.5	614.2
117.5°	192.2	195.3	200.1	208.4	223.6	245.7	277.1	322.2	389.3	482.0	590.5
120°	206.0	209.2	213.9	221.1	236.8	258.9	289.7	332.3	393.1	477.6	577.8
122.5°	219.3	221.9	226.5	234.3	250.0	272.9	301.7	341.2	397.6	475.0	567.1
125°	236.8	239.2	243.9	253.4	269.2	291.2	319.7	355.3	404.1	470.5	551.8
127.5°	250.7	253.9	260.5	270.9	286.1	308.8	336.5	368.3	411.0	467.8	537.6
130°	258.9	262.1	269.9	281.0	296.8	318.9	346.6	376.6	416.1	466.6	528.2
132.5°	266.5	270.3	278.8	290.5	306.9	329.0	355.4	384.8	421.1	466.0	520.6
135°	277.9	281.0	290.5	302.4	320.5	342.6	367.9	395.5	427.1	464.9	510.0
137.5°	288.6	292.4	301.8	314.5	332.5	353.0	378.0	403.7	432.4	464.8	502.5
140°	296.8	299.9	309.4	322.0	339.4	360.0	383.6	408.1	434.9	464.1	498.2
142.5°	305.0	307.6	316.4	329.0	345.8	365.1	388.1	411.9	436.9	464.1	493.7
145°	317.3	320.5	328.4	340.2	356.0	373.3	394.8	416.8	438.9	462.6	487.9
147.5°	330.6	333.0	340.5	351.4	364.6	380.0	400.1	419.5	439.6	459.8	481.9
150°	339.4	341.8	348.1	358.4	370.2	384.5	402.6	420.7	438.9	457.9	476.8
152.5°	348.3	349.4	355.7	364.7	375.9	388.9	405.2	421.4	437.7	454.7	472.4
155°	360.7	361.5	366.3	375.0	383.6	395.5	408.9	422.3	435.8	449.2	464.1
157.5°	371.2	371.9	375.8	383.3	390.3	400.2	411.6	422.3	432.1	443.5	456.5
160°	378.1	378.9	382.0	388.4	394.8	403.3	412.8	422.3	430.2	439.7	450.8
162.5°	385.1	384.6	387.8	392.8	398.5	405.3	413.5	421.7	428.4	436.6	445.7
165°	393.1	392.3	393.9	398.7	402.6	407.4	414.4	420.0	424.7	430.2	437.4
167.5°	399.8	398.8	400.2	403.2	406.1	409.1	414.2	418.9	421.1	424.7	429.1
170°	404.1	402.6	403.3	405.8	407.4	409.7	413.6	417.6	419.2	421.5	424.7
172.5°	406.7	405.8	405.3	407.7	408.6	410.3	413.0	415.7	416.7	417.8	420.3
175°	409.7	408.9	408.1	409.7	409.7	410.5	412.0	413.6	412.8	413.6	414.4
177.5°	411.1	409.9	409.2	410.5	410.5	410.5	411.1	412.4	411.1	410.5	411.1
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331311-840

CATALOG NUMBER: SA2XXDIP-C485D725U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	781.0	782.3	783.7	784.3	784.0	783.7	783.5	783.2
5°	775.8	777.1	778.4	778.9	778.6	778.2	777.9	777.6
7.5°	767.0	768.3	769.7	770.1	769.8	769.4	769.0	768.7
10°	759.1	760.5	761.8	762.2	761.7	761.2	760.7	760.2
12.5°	749.9	750.8	751.7	752.0	751.6	751.3	750.9	750.5
15°	733.7	734.4	735.0	734.9	734.1	733.3	732.5	731.5
17.5°	714.4	715.2	716.0	715.9	715.1	714.4	713.6	712.8
20°	699.4	699.9	700.4	700.3	699.6	698.9	698.3	697.6
22.5°	683.5	683.6	683.7	683.6	683.2	682.8	682.4	682.0
25°	657.6	657.9	658.2	658.2	657.9	657.6	657.2	656.9
27.5°	632.1	631.6	631.1	630.5	629.7	628.8	628.0	627.2
30°	612.2	611.7	611.2	610.6	609.9	609.3	608.5	607.8
32.5°	592.7	591.8	590.9	590.1	589.4	588.8	588.0	587.3
35°	561.4	560.4	559.4	558.5	557.6	556.7	555.9	555.1
37.5°	530.0	528.8	527.6	526.4	525.6	524.8	524.0	523.3
40°	508.4	506.9	505.3	504.2	503.5	502.9	502.2	501.5
42.5°	487.0	485.3	483.6	482.4	481.4	480.5	479.6	478.6
45°	454.1	452.3	450.4	449.2	448.5	447.9	447.2	446.5
47.5°	420.0	418.0	416.1	414.7	413.6	412.7	411.7	410.7
50°	398.1	395.7	393.3	391.7	390.9	390.1	389.2	388.4
52.5°	375.4	373.3	371.4	369.9	368.8	367.7	366.6	365.5
55°	341.4	339.4	337.4	336.0	335.1	334.3	333.5	332.6
57.5°	306.2	304.2	302.3	300.9	300.2	299.6	299.0	298.3
60°	282.9	281.0	279.2	278.0	277.5	277.0	276.5	276.0
62.5°	260.8	259.1	257.4	256.3	255.6	255.0	254.4	253.7
65°	227.0	225.5	224.0	222.8	222.0	221.2	220.4	219.4
67.5°	193.6	192.4	191.3	190.4	189.7	188.9	188.3	187.6
70°	171.9	170.7	169.6	168.6	167.9	167.2	166.6	165.9
72.5°	151.4	150.2	149.1	148.1	147.6	147.0	146.5	146.0
75°	119.4	118.5	117.4	117.0	117.4	117.8	118.1	118.5
77.5°	90.9	90.4	89.9	89.4	88.9	88.5	88.0	87.5
80°	72.1	71.6	71.2	70.7	70.4	70.1	69.7	69.4
82.5°	53.8	53.1	52.5	52.1	52.1	52.0	51.9	51.9
85°	28.4	27.9	27.4	27.1	26.9	26.8	26.6	26.4
87.5°	12.7	12.0	11.9	11.8	11.6	11.5	11.4	11.2
90°	25.2	23.7	25.2	26.1	26.1	26.1	26.1	26.1
92.5°	68.9	59.1	52.4	47.6	46.9	44.3	45.0	43.7
95°	206.8	158.6	125.5	108.2	97.9	91.6	89.2	90.0
97.5°	482.6	394.9	309.4	252.5	214.7	195.3	183.8	177.1
100°	720.7	622.9	514.7	419.2	353.7	319.7	296.8	282.6
102.5°	876.8	854.6	775.5	674.3	603.1	545.1	516.5	497.4
105°	959.2	1048.3	1058.6	1032.6	983.6	934.6	900.7	889.7
107.5°	899.8	1034.1	1116.2	1154.5	1160.6	1157.9	1151.1	1136.4
110°	848.6	990.0	1091.0	1155.7	1189.6	1204.7	1211.7	1210.9



TEST NUMBER: P331311-840

CATALOG NUMBER: SA2XXDIP-C485D725U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	801.9	937.5	1045.5	1119.7	1166.9	1192.0	1205.5	1209.7
115°	744.4	866.0	969.4	1050.7	1106.7	1143.1	1163.6	1170.7
117.5°	701.1	807.9	901.7	978.0	1035.1	1073.5	1095.1	1101.1
120°	679.6	777.6	861.2	933.1	988.4	1025.4	1048.3	1056.2
122.5°	662.7	752.3	831.5	896.5	946.0	982.5	1002.9	1009.5
125°	637.8	719.1	788.6	847.8	893.6	923.6	943.3	949.7
127.5°	613.4	686.9	752.5	807.1	847.1	875.1	892.2	897.3
130°	597.5	665.5	727.8	779.9	818.6	845.5	861.2	867.6
132.5°	582.4	645.3	702.6	751.5	789.6	816.4	830.9	836.6
135°	561.3	613.4	665.5	709.6	743.7	769.7	783.9	787.1
137.5°	544.4	587.9	629.3	667.8	698.8	721.2	733.7	738.4
140°	533.6	571.6	607.8	642.6	667.8	688.3	700.2	705.0
142.5°	524.8	557.0	588.2	617.3	641.4	659.9	670.6	671.5
145°	512.3	538.4	562.9	585.7	604.7	618.1	626.0	628.3
147.5°	502.7	523.2	542.3	559.1	574.7	585.4	590.8	592.2
150°	495.7	513.1	529.7	543.9	555.7	565.2	570.0	570.8
152.5°	488.8	504.9	519.0	531.3	540.6	548.8	552.3	552.4
155°	479.2	491.8	503.6	512.3	521.0	526.5	529.7	528.2
157.5°	468.0	478.6	488.5	495.2	501.4	506.0	507.5	507.5
160°	461.0	469.7	478.4	483.9	489.5	493.4	494.1	494.1
162.5°	454.0	461.5	468.9	473.2	478.7	481.4	482.2	481.5
165°	443.6	449.2	454.7	457.9	461.0	464.1	464.1	463.4
167.5°	433.7	438.0	441.7	444.6	446.1	447.8	447.6	446.7
170°	428.7	431.0	434.1	435.8	436.6	438.9	438.1	436.6
172.5°	422.9	424.7	427.3	428.2	429.0	430.1	429.3	428.4
175°	416.8	417.6	418.4	419.2	419.2	420.0	419.2	417.6
177.5°	412.4	412.4	413.0	413.0	413.0	413.0	412.4	411.1
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5

(END OF REPORT)