

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331367-840

Luminaire Tested: **SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331367-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6851.7 lumens
Efficiency: N/A
Efficacy: 120.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331367-840
CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331367-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43	43	43	43
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43	37	37	37	37
2	88	81	75	70	81	75	70	65	62	58	55	51	48	46	40	38	37	32	32	32	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	27	27	27	27
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24	24	24	24
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	27	24	21	21	21	21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19	19	19	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17	17	17	17
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	23	20	18	15	15	15	15
9	50	39	31	26	46	36	29	25	30	25	22	26	22	19	21	18	16	14	14	14	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13	13	13	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21658	21658	21658	21658
5°	24280	21797	19316	21797
10°	27824	21620	16718	21620
15°	30780	21224	14770	21224
20°	30311	20797	13464	20797
25°	27332	20232	12636	20232
30°	22585	19328	12033	19328
35°	16462	18382	11606	18382
40°	13148	17266	11367	17266
45°	11488	15972	11040	15972
50°	10798	14722	10826	14722
55°	9956	13453	10536	13453
60°	9122	12103	10091	12103
65°	8309	10892	9650	10892
70°	7544	9711	9007	9711
75°	6687	8390	7973	8390
80°	5755	6946	6425	6946
85°	5169	5169	3816	5169



TEST NUMBER: P331367-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.7	1.9
10°-20°	371.4	5.4
20°-30°	539.0	7.9
30°-40°	568.8	8.3
40°-50°	503.6	7.3
50°-60°	401.9	5.9
60°-70°	273.2	4.0
70°-80°	140.0	2.0
80°-90°	39.3	0.6
90°-100°	88.1	1.3
100°-110°	273.6	4.0
110°-120°	467.6	6.8
120°-130°	614.9	9.0
130°-140°	690.2	10.1
140°-150°	676.7	9.9
150°-160°	567.6	8.3
160°-170°	376.5	5.5
170°-180°	131.6	1.9
0°-30°	1038.1	15.2
0°-40°	1606.9	23.5
0°-60°	2512.4	36.7
0°-90°	2964.9	43.3
90°-120°	829.3	12.1
90°-150°	2811.1	41.0
90°-180°	3887.0	56.7
0°-180°	6851.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1341	1341	1341	1341	1341	
5°	1498	1345	1192	1345	1498	150
15°	1841	1270	884	1270	1841	508
25°	1534	1136	709	1136	1534	693
35°	835	933	589	933	835	543
45°	503	700	484	700	503	396
55°	354	478	374	478	354	317
65°	218	285	253	285	218	216
75°	107	134	128	134	107	115
85°	28	28	21	28	28	32
90°	40	1	40	1	40	19
95°	73	61	73	61	73	81
105°	260	252	260	252	260	274
115°	469	469	469	469	469	463
125°	685	683	685	683	685	611
135°	894	883	894	883	894	688
145°	1084	1072	1084	1072	1084	677
155°	1235	1226	1235	1226	1235	568
165°	1335	1334	1335	1334	1335	376
175°	1383	1388	1383	1388	1383	131
180°	1390	1390	1390	1390	1390	



TEST NUMBER: P331367-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1403.2	1403.6	1404.5	1397.9	1397.0	1397.0	1391.3	1386.3	1380.6	1372.7	1373.5
5°	1498.1	1503.8	1505.8	1499.6	1490.4	1489.3	1480.6	1466.1	1452.7	1441.9	1434.2
7.5°	1611.3	1613.6	1608.5	1600.3	1593.5	1581.1	1564.8	1548.8	1526.4	1505.9	1490.7
10°	1697.1	1700.2	1691.4	1679.6	1669.8	1655.4	1631.6	1607.4	1578.0	1549.6	1526.9
12.5°	1762.2	1769.9	1758.7	1757.1	1740.3	1720.5	1692.2	1680.0	1638.6	1599.1	1574.8
15°	1841.4	1840.9	1842.0	1832.2	1819.8	1816.6	1786.8	1754.3	1696.1	1672.8	1632.6
17.5°	1818.6	1826.3	1830.0	1829.9	1829.6	1827.7	1818.1	1797.6	1768.4	1730.7	1684.3
20°	1764.1	1774.4	1775.9	1787.9	1794.5	1803.3	1806.9	1801.2	1783.2	1751.7	1711.5
22.5°	1680.0	1682.8	1687.7	1706.2	1720.7	1742.6	1754.1	1773.2	1766.3	1750.9	1717.3
25°	1534.2	1529.0	1547.1	1556.3	1589.8	1624.9	1650.2	1678.0	1702.7	1717.7	1707.9
27.5°	1359.1	1351.4	1378.4	1403.0	1430.3	1468.2	1507.6	1554.1	1592.8	1641.1	1657.7
30°	1211.4	1216.1	1241.9	1268.2	1309.4	1363.0	1407.3	1458.4	1513.6	1567.7	1605.3
32.5°	1052.3	1070.2	1086.4	1126.7	1163.0	1222.8	1287.8	1351.6	1420.4	1481.9	1540.1
35°	835.2	855.8	878.5	907.9	958.9	1018.1	1081.6	1167.6	1261.5	1345.5	1414.6
37.5°	703.0	699.6	712.7	733.9	775.3	823.0	896.1	981.2	1091.6	1190.3	1287.8
40°	623.8	621.7	631.0	650.6	682.1	717.1	781.0	855.8	958.4	1078.9	1195.0
42.5°	569.4	570.6	575.7	589.6	611.1	640.0	687.8	751.4	845.4	959.0	1083.6
45°	503.1	506.8	512.4	519.2	531.5	555.2	582.0	627.4	701.7	796.5	919.2
47.5°	455.6	455.7	461.4	467.3	474.6	488.0	509.9	538.3	590.7	667.9	773.4
50°	429.9	426.4	430.5	435.0	442.8	452.1	466.6	493.3	528.4	590.8	678.9
52.5°	398.6	398.7	402.4	404.1	411.1	420.3	433.5	452.1	483.8	532.6	605.1
55°	353.7	356.2	358.3	361.3	367.6	374.3	384.6	397.0	421.7	458.3	511.9
57.5°	311.3	312.1	314.3	320.1	324.1	330.2	340.0	351.2	367.4	394.5	434.7
60°	282.5	282.5	286.6	289.2	294.4	300.5	308.3	319.1	333.6	355.7	388.2
62.5°	256.1	255.7	257.3	261.6	265.5	271.2	279.0	288.2	301.7	321.4	348.2
65°	217.5	216.5	219.6	220.7	224.8	230.5	236.6	246.4	257.2	271.7	295.4
67.5°	180.5	181.7	183.3	185.3	187.5	193.5	197.6	204.6	213.7	225.7	241.8
70°	159.8	159.8	159.8	161.4	164.4	167.5	171.7	177.3	186.1	196.4	210.9
72.5°	136.7	138.4	140.0	139.1	143.0	144.8	149.8	153.0	161.4	167.9	180.8
75°	107.2	107.2	107.2	109.8	111.4	112.9	116.0	119.1	123.2	131.5	138.1
77.5°	80.0	79.8	80.3	80.9	82.6	84.4	85.3	88.2	92.0	95.7	101.5
80°	61.9	62.9	63.4	64.4	64.4	65.4	65.9	69.6	72.2	74.7	78.4
82.5°	47.9	48.1	48.2	48.4	48.8	49.4	50.7	51.9	52.8	54.9	57.8
85°	27.9	27.4	27.4	28.4	27.9	27.9	28.9	29.9	29.9	30.4	31.9
87.5°	18.7	18.7	19.0	18.6	18.5	18.9	19.0	18.7	19.3	19.8	19.0
90°	39.9	39.6	39.4	39.1	38.9	39.0	39.5	40.0	40.5	41.1	35.3
92.5°	38.0	38.0	37.9	37.9	37.8	37.8	37.6	37.5	37.4	37.3	36.0
95°	72.7	73.2	73.8	74.3	74.8	75.0	75.0	75.0	75.0	75.0	74.5
97.5°	126.0	126.0	126.1	126.1	126.2	126.2	126.2	126.2	126.2	126.2	125.2
100°	160.7	161.0	161.3	161.5	161.8	161.9	161.9	161.9	161.9	161.9	161.1
102.5°	200.2	200.4	200.7	200.9	201.2	201.2	201.0	200.8	200.6	200.4	199.3
105°	260.4	260.4	260.4	260.4	260.4	260.1	259.6	259.1	258.6	258.0	257.5
107.5°	317.2	318.4	319.6	320.8	321.9	322.4	322.2	322.0	321.8	321.6	321.6
110°	361.3	362.0	362.8	363.7	364.5	364.9	364.9	364.9	364.9	364.9	364.9



TEST NUMBER: P331367-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	403.5	404.1	404.7	405.3	405.9	406.5	407.1	407.7	408.3	408.9	409.1
115°	469.2	470.0	470.8	471.6	472.3	472.8	473.1	473.4	473.6	473.9	474.4
117.5°	531.9	532.6	533.4	534.2	535.0	535.7	536.3	536.9	537.6	538.2	539.7
120°	575.9	576.7	577.5	578.3	579.1	579.5	579.5	579.5	579.5	579.5	581.6
122.5°	619.1	619.8	620.3	620.9	621.5	622.0	622.7	623.3	623.9	624.5	626.0
125°	685.1	685.3	685.6	685.8	686.1	686.6	687.4	688.2	688.9	689.7	690.5
127.5°	745.1	746.0	746.8	747.6	748.4	749.3	750.2	751.2	752.1	753.1	754.1
130°	788.3	789.3	790.3	791.4	792.4	793.2	793.8	794.3	794.8	795.4	795.9
132.5°	829.6	830.4	831.2	832.1	832.9	833.9	835.1	836.2	837.4	838.5	838.4
135°	893.8	894.6	895.4	896.2	897.0	897.5	897.8	898.1	898.3	898.6	898.1
137.5°	952.0	953.1	954.1	955.1	956.2	956.8	957.0	957.3	957.5	957.7	956.9
140°	992.4	993.4	994.5	995.5	996.5	997.0	997.0	997.0	997.0	997.0	995.8
142.5°	1029.0	1030.1	1031.1	1032.1	1033.2	1033.6	1033.4	1033.2	1033.0	1032.8	1031.9
145°	1083.9	1084.9	1086.0	1087.0	1088.0	1088.4	1088.2	1087.9	1087.6	1087.4	1085.8
147.5°	1133.0	1133.9	1134.9	1135.9	1136.9	1137.1	1136.5	1136.0	1135.4	1134.8	1133.8
150°	1164.9	1165.6	1166.4	1167.2	1168.0	1168.0	1167.2	1166.4	1165.6	1164.9	1163.8
152.5°	1194.9	1195.9	1196.9	1197.8	1198.8	1198.8	1197.8	1196.9	1195.9	1194.9	1193.7
155°	1235.2	1236.0	1236.8	1237.6	1238.3	1238.1	1236.8	1235.5	1234.2	1232.8	1232.1
157.5°	1269.9	1271.2	1272.4	1273.6	1275.0	1274.7	1272.9	1271.1	1269.4	1267.6	1267.1
160°	1291.5	1292.5	1293.6	1294.6	1295.7	1295.5	1293.8	1292.3	1290.7	1289.2	1288.9
162.5°	1310.3	1311.5	1312.8	1314.0	1315.2	1315.0	1313.2	1311.5	1309.7	1308.0	1307.7
165°	1334.9	1336.3	1337.6	1338.9	1340.1	1339.9	1338.1	1336.3	1334.4	1332.6	1332.6
167.5°	1355.1	1356.5	1357.8	1359.2	1360.5	1360.3	1358.5	1356.7	1354.8	1353.0	1353.0
170°	1365.4	1367.0	1368.6	1370.1	1371.7	1371.5	1369.7	1367.9	1366.0	1364.2	1364.5
172.5°	1373.8	1375.4	1377.0	1378.6	1380.1	1380.0	1378.2	1376.3	1374.5	1372.7	1372.9
175°	1383.0	1384.6	1386.1	1387.8	1389.3	1389.2	1387.4	1385.5	1383.7	1381.8	1382.4
177.5°	1387.3	1388.5	1389.8	1391.0	1392.2	1392.2	1391.0	1389.8	1388.5	1387.3	1387.7
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1



TEST NUMBER: P331367-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1376.4	1373.1	1371.1	1363.6	1357.1	1350.5	1348.4	1349.2	1340.2	1331.5	1327.8
5°	1430.1	1419.8	1410.0	1396.0	1379.6	1361.5	1352.2	1344.9	1327.0	1307.4	1296.1
7.5°	1478.1	1463.4	1444.5	1418.3	1394.3	1365.9	1347.9	1331.9	1305.5	1277.9	1260.9
10°	1507.4	1487.2	1463.0	1431.1	1401.7	1367.2	1342.9	1318.7	1287.8	1254.8	1234.2
12.5°	1532.6	1505.4	1481.6	1440.6	1405.8	1362.6	1333.8	1299.7	1267.2	1228.0	1207.8
15°	1592.5	1542.5	1497.0	1450.7	1407.9	1347.6	1315.7	1269.7	1226.9	1178.5	1155.3
17.5°	1638.7	1582.6	1511.1	1452.1	1402.2	1335.4	1288.5	1233.6	1183.0	1127.5	1096.0
20°	1665.2	1600.6	1523.9	1453.8	1393.9	1317.7	1266.7	1210.4	1151.1	1088.7	1054.7
22.5°	1680.8	1613.1	1537.1	1447.5	1377.5	1303.2	1239.0	1177.4	1117.3	1050.1	1014.3
25°	1685.8	1623.9	1543.5	1442.4	1356.9	1272.8	1195.5	1135.7	1063.0	1000.1	948.1
27.5°	1661.2	1616.9	1539.5	1432.7	1333.0	1234.8	1148.6	1080.9	1004.1	935.8	883.5
30°	1631.1	1605.3	1530.0	1422.8	1314.0	1208.4	1113.5	1036.7	960.4	891.3	837.7
32.5°	1584.5	1578.9	1512.8	1408.8	1293.8	1175.0	1076.8	999.2	914.6	846.8	795.7
35°	1493.0	1517.7	1475.9	1377.5	1255.8	1127.4	1021.3	932.6	845.0	780.0	732.1
37.5°	1370.3	1431.7	1420.8	1331.6	1204.5	1075.7	958.5	865.8	782.2	716.7	669.6
40°	1285.7	1364.0	1375.4	1296.6	1168.2	1035.7	911.4	819.2	737.7	677.9	630.5
42.5°	1195.0	1286.6	1317.7	1254.5	1128.5	993.6	869.4	773.8	693.2	635.0	593.0
45°	1042.9	1164.1	1220.2	1184.2	1062.5	924.3	796.5	699.5	626.3	571.7	539.3
47.5°	900.7	1033.1	1108.6	1095.9	989.0	852.1	725.8	632.8	561.5	517.9	488.8
50°	800.1	936.1	1027.4	1031.6	936.1	800.6	673.8	586.1	520.7	480.0	456.3
52.5°	712.7	842.5	942.1	963.9	877.2	747.0	627.2	540.0	482.3	444.8	423.6
55°	598.5	708.3	818.6	858.9	789.2	665.5	554.7	477.9	423.7	398.0	379.4
57.5°	497.6	589.2	691.1	735.5	692.6	586.6	482.7	416.1	372.1	349.5	335.3
60°	444.3	516.5	607.2	660.4	623.3	529.0	438.2	374.8	338.7	318.6	305.2
62.5°	394.9	458.8	535.5	584.1	563.9	474.9	393.6	337.7	306.5	287.6	278.0
65°	325.8	376.4	435.7	480.5	467.1	399.5	333.1	285.1	260.3	245.4	237.6
67.5°	268.3	304.8	345.9	385.2	374.4	326.5	273.2	235.8	217.3	204.5	199.9
70°	232.0	259.8	296.4	327.9	319.1	279.9	237.6	205.7	189.8	178.8	174.2
72.5°	197.3	220.3	248.1	273.9	267.9	235.4	200.2	176.0	163.7	153.7	149.9
75°	149.0	166.5	183.5	200.6	198.9	173.7	153.1	134.5	124.7	117.0	115.4
77.5°	110.0	119.8	131.4	141.5	138.7	124.2	108.1	97.5	90.2	85.0	84.2
80°	84.0	89.7	98.0	105.1	101.6	95.3	82.5	74.7	69.6	64.4	62.4
82.5°	60.9	66.7	71.6	75.4	72.7	67.0	59.0	53.7	50.6	47.2	46.3
85°	31.9	35.0	37.2	38.2	37.2	33.5	29.9	27.9	25.2	23.7	23.2
87.5°	18.3	17.2	16.0	16.0	14.0	13.4	11.2	9.3	9.5	9.7	9.5
90°	29.6	23.8	18.1	13.7	10.6	7.5	4.3	1.2	4.3	7.5	10.6
92.5°	34.6	33.2	31.9	30.1	27.8	25.4	23.1	20.9	23.1	25.4	27.8
95°	74.0	73.5	73.0	71.4	68.8	66.2	63.6	61.0	63.6	66.2	68.8
97.5°	124.2	123.2	122.3	120.6	118.4	116.0	113.7	111.5	113.7	116.0	118.4
100°	160.3	159.6	158.8	157.3	155.2	153.2	151.1	149.0	151.1	153.2	155.2
102.5°	198.3	197.4	196.4	195.1	193.4	191.8	190.1	188.4	190.1	191.8	193.4
105°	257.0	256.5	256.0	255.3	254.6	253.8	253.0	252.2	253.0	253.8	254.6
107.5°	321.6	321.6	321.6	321.0	319.9	318.8	317.6	316.5	317.6	318.8	319.9
110°	364.9	364.9	364.9	364.1	362.4	360.9	359.3	357.8	359.3	360.9	362.4



TEST NUMBER: P331367-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	409.3	409.5	409.8	409.1	407.5	406.0	404.3	402.8	404.3	406.0	407.5
115°	474.9	475.4	475.9	475.4	473.9	472.3	470.8	469.2	470.8	472.3	473.9
117.5°	541.1	542.6	544.0	543.7	541.6	539.6	537.5	535.3	537.5	539.6	541.6
120°	583.7	585.7	587.8	587.8	585.7	583.7	581.6	579.5	581.6	583.7	585.7
122.5°	627.4	628.9	630.4	629.9	627.3	624.8	622.4	619.9	622.4	624.8	627.3
125°	691.4	692.1	692.9	692.1	689.7	687.4	685.1	682.7	685.1	687.4	689.7
127.5°	755.0	755.9	756.9	755.8	752.9	749.9	746.9	744.0	746.9	749.9	752.9
130°	796.4	796.9	797.4	796.0	792.5	789.2	785.8	782.4	785.8	789.2	792.5
132.5°	838.3	838.2	838.1	836.7	833.8	831.1	828.4	825.6	828.4	831.1	833.8
135°	897.5	897.0	896.5	894.7	891.9	889.1	886.2	883.3	886.2	889.1	891.9
137.5°	956.3	955.6	954.9	953.4	951.1	948.8	946.4	944.0	946.4	948.8	951.1
140°	994.5	993.2	991.9	990.1	987.7	985.3	983.0	980.7	983.0	985.3	987.7
142.5°	1031.0	1030.1	1029.2	1027.5	1025.2	1022.9	1020.6	1018.2	1020.6	1022.9	1025.2
145°	1084.3	1082.7	1081.2	1079.4	1077.6	1075.8	1074.0	1072.2	1074.0	1075.8	1077.6
147.5°	1132.8	1131.7	1130.6	1129.0	1126.8	1124.6	1122.5	1120.2	1122.5	1124.6	1126.8
150°	1162.8	1161.7	1160.6	1159.3	1157.8	1156.2	1154.7	1153.1	1154.7	1156.2	1157.8
152.5°	1192.3	1191.1	1189.8	1188.4	1186.9	1185.3	1183.8	1182.1	1183.8	1185.3	1186.9
155°	1231.3	1230.5	1229.7	1229.0	1228.2	1227.4	1226.6	1225.9	1226.6	1227.4	1228.2
157.5°	1266.7	1266.2	1265.7	1265.3	1264.7	1264.1	1263.6	1263.1	1263.6	1264.1	1264.7
160°	1288.7	1288.4	1288.1	1287.8	1287.2	1286.7	1286.2	1285.7	1286.2	1286.7	1287.2
162.5°	1307.4	1307.2	1306.9	1306.8	1306.6	1306.5	1306.4	1306.3	1306.4	1306.5	1306.6
165°	1332.6	1332.6	1332.6	1332.7	1332.9	1333.2	1333.5	1333.7	1333.5	1333.2	1332.9
167.5°	1353.1	1353.1	1353.2	1353.6	1354.4	1355.1	1355.9	1356.8	1355.9	1355.1	1354.4
170°	1364.7	1365.0	1365.3	1365.8	1366.5	1367.4	1368.2	1369.0	1368.2	1367.4	1366.5
172.5°	1373.2	1373.5	1373.7	1374.2	1375.0	1375.8	1376.6	1377.4	1376.6	1375.8	1375.0
175°	1382.9	1383.4	1383.9	1384.6	1385.3	1386.1	1386.9	1387.8	1386.9	1386.1	1385.3
177.5°	1388.1	1388.5	1388.9	1389.5	1390.1	1390.7	1391.3	1391.9	1391.3	1390.7	1390.1
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1



TEST NUMBER: P331367-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1323.6	1321.2	1312.5	1308.0	1300.5	1293.5	1289.0	1291.1	1292.7	1291.9	1290.6
5°	1285.7	1275.9	1260.9	1248.1	1238.8	1221.7	1214.6	1210.9	1207.9	1204.3	1200.6
7.5°	1240.5	1225.1	1203.7	1185.3	1167.9	1146.8	1134.8	1127.5	1120.1	1112.0	1104.8
10°	1208.4	1186.7	1164.1	1138.2	1117.6	1098.5	1081.6	1070.3	1060.0	1050.2	1042.9
12.5°	1174.6	1149.6	1121.6	1086.3	1063.6	1036.3	1033.7	1013.7	997.6	991.6	983.1
15°	1120.7	1085.7	1050.2	1008.4	990.3	965.5	950.1	934.6	920.7	910.9	908.4
17.5°	1059.6	1014.2	978.9	948.9	919.3	893.9	879.7	867.3	855.9	842.7	841.0
20°	1013.0	973.8	935.1	908.9	878.5	852.6	835.2	822.7	812.9	805.3	798.5
22.5°	968.9	925.9	890.6	861.8	831.8	811.0	797.2	785.3	777.1	768.5	762.2
25°	898.1	864.5	825.9	793.3	768.6	755.3	743.9	733.6	728.4	722.8	715.6
27.5°	836.1	798.8	762.7	737.5	715.8	703.9	695.8	688.8	684.0	680.6	676.6
30°	792.3	754.7	726.4	701.7	683.6	671.8	666.6	662.5	656.8	654.7	652.7
32.5°	750.3	716.4	692.2	670.7	653.5	645.7	641.0	637.3	632.9	630.8	626.6
35°	690.7	662.5	638.7	626.8	613.0	606.2	602.7	597.4	593.4	591.3	590.8
37.5°	634.8	610.2	594.6	579.4	573.5	569.4	564.4	560.9	559.7	559.4	558.9
40°	598.5	578.5	564.5	552.1	549.6	543.3	539.3	536.1	536.1	536.6	536.1
42.5°	565.5	547.4	535.2	524.5	521.5	517.8	513.6	513.4	514.3	516.0	514.3
45°	515.5	502.6	493.8	488.7	483.0	479.4	478.9	480.5	481.0	481.5	483.0
47.5°	469.5	461.0	453.0	447.4	444.8	444.2	443.6	446.4	448.8	449.7	452.1
50°	442.3	432.5	425.9	422.2	420.1	419.1	420.1	423.2	425.3	427.9	429.4
52.5°	411.8	404.9	400.2	397.5	396.7	397.3	397.5	401.0	404.2	405.2	406.0
55°	369.6	364.5	363.5	358.8	360.8	360.3	362.9	365.0	368.1	371.1	371.7
57.5°	327.6	323.5	320.6	321.0	321.6	324.0	326.1	329.7	333.1	336.3	336.6
60°	299.5	297.4	295.9	295.9	296.9	300.0	302.7	306.2	308.3	310.3	311.8
62.5°	274.0	271.9	270.3	271.1	273.9	275.7	278.7	280.6	282.7	284.8	285.5
65°	233.5	232.5	234.1	235.1	235.6	238.1	241.8	243.3	245.4	246.4	250.0
67.5°	196.3	196.5	196.3	197.7	200.8	201.4	204.8	208.3	208.7	210.8	213.1
70°	171.2	172.2	173.2	174.2	176.8	177.8	180.5	182.0	184.0	185.6	187.1
72.5°	148.0	148.2	149.3	149.1	151.3	153.5	155.7	157.2	159.3	161.3	162.8
75°	113.9	113.9	114.9	115.4	118.1	120.7	120.1	121.2	123.2	125.2	126.3
77.5°	83.2	82.1	83.2	83.7	84.5	86.7	87.2	88.6	90.9	90.2	91.4
80°	63.4	61.9	63.4	63.9	63.9	66.6	66.6	67.6	69.1	67.6	69.1
82.5°	45.2	44.5	45.6	45.7	46.6	46.7	47.6	47.8	49.3	48.6	49.3
85°	22.7	22.2	22.7	22.2	22.7	23.2	23.2	22.7	22.7	23.7	22.2
87.5°	9.8	10.2	10.9	12.1	12.8	13.5	13.0	12.9	12.8	11.9	11.9
90°	13.7	18.1	23.8	29.6	35.3	41.1	40.5	40.0	39.5	39.0	38.9
92.5°	30.1	31.9	33.2	34.6	36.0	37.3	37.4	37.5	37.6	37.8	37.8
95°	71.4	73.0	73.5	74.0	74.5	75.0	75.0	75.0	75.0	75.0	74.8
97.5°	120.6	122.3	123.2	124.2	125.2	126.2	126.2	126.2	126.2	126.2	126.2
100°	157.3	158.8	159.6	160.3	161.1	161.9	161.9	161.9	161.9	161.9	161.8
102.5°	195.1	196.4	197.4	198.3	199.3	200.4	200.6	200.8	201.0	201.2	201.2
105°	255.3	256.0	256.5	257.0	257.5	258.0	258.6	259.1	259.6	260.1	260.4
107.5°	321.0	321.6	321.6	321.6	321.6	321.6	321.8	322.0	322.2	322.4	321.9
110°	364.1	364.9	364.9	364.9	364.9	364.9	364.9	364.9	364.9	364.9	364.5



TEST NUMBER: P331367-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	409.1	409.8	409.5	409.3	409.1	408.9	408.3	407.7	407.1	406.5	405.9
115°	475.4	475.9	475.4	474.9	474.4	473.9	473.6	473.4	473.1	472.8	472.3
117.5°	543.7	544.0	542.6	541.1	539.7	538.2	537.6	536.9	536.3	535.7	535.0
120°	587.8	587.8	585.7	583.7	581.6	579.5	579.5	579.5	579.5	579.5	579.1
122.5°	629.9	630.4	628.9	627.4	626.0	624.5	623.9	623.3	622.7	622.0	621.5
125°	692.1	692.9	692.1	691.4	690.5	689.7	688.9	688.2	687.4	686.6	686.1
127.5°	755.8	756.9	755.9	755.0	754.1	753.1	752.1	751.2	750.2	749.3	748.4
130°	796.0	797.4	796.9	796.4	795.9	795.4	794.8	794.3	793.8	793.2	792.4
132.5°	836.7	838.1	838.2	838.3	838.4	838.5	837.4	836.2	835.1	833.9	832.9
135°	894.7	896.5	897.0	897.5	898.1	898.6	898.3	898.1	897.8	897.5	897.0
137.5°	953.4	954.9	955.6	956.3	956.9	957.7	957.5	957.3	957.0	956.8	956.2
140°	990.1	991.9	993.2	994.5	995.8	997.0	997.0	997.0	997.0	997.0	996.5
142.5°	1027.5	1029.2	1030.1	1031.0	1031.9	1032.8	1033.0	1033.2	1033.4	1033.6	1033.2
145°	1079.4	1081.2	1082.7	1084.3	1085.8	1087.4	1087.6	1087.9	1088.2	1088.4	1088.0
147.5°	1129.0	1130.6	1131.7	1132.8	1133.8	1134.8	1135.4	1136.0	1136.5	1137.1	1136.9
150°	1159.3	1160.6	1161.7	1162.8	1163.8	1164.9	1165.6	1166.4	1167.2	1168.0	1168.0
152.5°	1188.4	1189.8	1191.1	1192.3	1193.7	1194.9	1195.9	1196.9	1197.8	1198.8	1198.8
155°	1229.0	1229.7	1230.5	1231.3	1232.1	1232.8	1234.2	1235.5	1236.8	1238.1	1238.3
157.5°	1265.3	1265.7	1266.2	1266.7	1267.1	1267.6	1269.4	1271.1	1272.9	1274.7	1275.0
160°	1287.8	1288.1	1288.4	1288.7	1288.9	1289.2	1290.7	1292.3	1293.8	1295.5	1295.7
162.5°	1306.8	1306.9	1307.2	1307.4	1307.7	1308.0	1309.7	1311.5	1313.2	1315.0	1315.2
165°	1332.7	1332.6	1332.6	1332.6	1332.6	1332.6	1334.4	1336.3	1338.1	1339.9	1340.1
167.5°	1353.6	1353.2	1353.1	1353.1	1353.0	1353.0	1354.8	1356.7	1358.5	1360.3	1360.5
170°	1365.8	1365.3	1365.0	1364.7	1364.5	1364.2	1366.0	1367.9	1369.7	1371.5	1371.7
172.5°	1374.2	1373.7	1373.5	1373.2	1372.9	1372.7	1374.5	1376.3	1378.2	1380.0	1380.1
175°	1384.6	1383.9	1383.4	1382.9	1382.4	1381.8	1383.7	1385.5	1387.4	1389.2	1389.3
177.5°	1389.5	1388.9	1388.5	1388.1	1387.7	1387.3	1388.5	1389.8	1391.0	1392.2	1392.2
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1



TEST NUMBER: P331367-840
 CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1286.6	1285.7	1285.7	1282.0	1285.7	1285.7	1286.6	1290.6	1291.9	1292.7	1291.1
5°	1193.5	1191.8	1189.3	1191.8	1189.3	1191.8	1193.5	1200.6	1204.3	1207.9	1210.9
7.5°	1101.4	1095.2	1094.3	1088.1	1094.3	1095.2	1101.4	1104.8	1112.0	1120.1	1127.5
10°	1034.1	1030.0	1029.5	1019.7	1029.5	1030.0	1034.1	1042.9	1050.2	1060.0	1070.3
12.5°	983.0	973.1	975.0	969.4	975.0	973.1	983.0	983.1	991.6	997.6	1013.7
15°	894.4	894.4	892.3	883.6	892.3	894.4	894.4	908.4	910.9	920.7	934.6
17.5°	830.8	829.8	824.9	827.3	824.9	829.8	830.8	841.0	842.7	855.9	867.3
20°	792.8	789.8	783.6	783.6	783.6	789.8	792.8	798.5	805.3	812.9	822.7
22.5°	757.0	756.8	750.2	752.2	750.2	756.8	757.0	762.2	768.5	777.1	785.3
25°	715.0	710.9	707.8	709.3	707.8	710.9	715.0	715.6	722.8	728.4	733.6
27.5°	675.2	673.0	672.8	668.5	672.8	673.0	675.2	676.6	680.6	684.0	688.8
30°	652.2	647.0	648.0	645.4	648.0	647.0	652.2	652.7	654.7	656.8	662.5
32.5°	625.7	623.9	622.9	620.7	622.9	623.9	625.7	626.6	630.8	632.9	637.3
35°	589.8	590.3	587.7	588.8	587.7	590.3	589.8	590.8	591.3	593.4	597.4
37.5°	558.4	560.0	558.8	559.1	558.8	560.0	558.4	558.9	559.4	559.7	560.9
40°	537.7	537.7	537.7	539.3	537.7	537.7	537.7	536.1	536.6	536.1	536.1
42.5°	517.9	517.1	516.2	516.1	516.2	517.1	517.9	514.3	516.0	514.3	513.4
45°	484.0	485.6	486.1	483.5	486.1	485.6	484.0	483.0	481.5	481.0	480.5
47.5°	453.4	453.6	453.4	455.8	453.4	453.6	453.4	452.1	449.7	448.8	446.4
50°	432.0	431.0	432.0	431.0	432.0	431.0	432.0	429.4	427.9	425.3	423.2
52.5°	409.3	409.5	408.9	408.7	408.9	409.5	409.3	406.0	405.2	404.2	401.0
55°	373.8	374.8	374.3	374.3	374.3	374.8	373.8	371.7	371.1	368.1	365.0
57.5°	337.0	337.9	338.6	336.3	338.6	337.9	337.0	336.6	336.3	333.1	329.7
60°	311.3	314.0	313.5	312.5	313.5	314.0	311.3	311.8	310.3	308.3	306.2
62.5°	287.9	288.8	288.7	288.5	288.7	288.8	287.9	285.5	284.8	282.7	280.6
65°	251.6	252.6	251.1	252.6	251.1	252.6	251.6	250.0	246.4	245.4	243.3
67.5°	212.5	212.8	214.0	214.7	214.0	212.8	212.5	213.1	210.8	208.7	208.3
70°	188.1	187.6	189.1	190.8	189.1	187.6	188.1	187.1	185.6	184.0	182.0
72.5°	162.6	163.7	163.2	164.3	163.2	163.7	162.6	162.8	161.3	159.3	157.2
75°	125.2	126.8	126.3	127.8	126.3	126.8	125.2	126.3	125.2	123.2	121.2
77.5°	90.5	90.7	90.5	91.4	90.5	90.7	90.5	91.4	90.2	90.9	88.6
80°	69.1	68.1	67.1	69.1	67.1	68.1	69.1	69.1	67.6	69.1	67.6
82.5°	48.1	48.7	47.7	47.7	47.7	48.7	48.1	49.3	48.6	49.3	47.8
85°	22.2	21.6	20.6	20.6	20.6	21.6	22.2	22.2	23.7	22.7	22.7
87.5°	11.9	11.6	11.6	11.3	11.6	11.6	11.9	11.9	11.9	12.8	12.9
90°	39.1	39.4	39.6	39.9	39.6	39.4	39.1	38.9	39.0	39.5	40.0
92.5°	37.9	37.9	38.0	38.0	38.0	37.9	37.9	37.8	37.8	37.6	37.5
95°	74.3	73.8	73.2	72.7	73.2	73.8	74.3	74.8	75.0	75.0	75.0
97.5°	126.1	126.1	126.0	126.0	126.0	126.1	126.1	126.2	126.2	126.2	126.2
100°	161.5	161.3	161.0	160.7	161.0	161.3	161.5	161.8	161.9	161.9	161.9
102.5°	200.9	200.7	200.4	200.2	200.4	200.7	200.9	201.2	201.2	201.0	200.8
105°	260.4	260.4	260.4	260.4	260.4	260.4	260.4	260.4	260.1	259.6	259.1
107.5°	320.8	319.6	318.4	317.2	318.4	319.6	320.8	321.9	322.4	322.2	322.0
110°	363.7	362.8	362.0	361.3	362.0	362.8	363.7	364.5	364.9	364.9	364.9



TEST NUMBER: P331367-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	405.3	404.7	404.1	403.5	404.1	404.7	405.3	405.9	406.5	407.1	407.7
115°	471.6	470.8	470.0	469.2	470.0	470.8	471.6	472.3	472.8	473.1	473.4
117.5°	534.2	533.4	532.6	531.9	532.6	533.4	534.2	535.0	535.7	536.3	536.9
120°	578.3	577.5	576.7	575.9	576.7	577.5	578.3	579.1	579.5	579.5	579.5
122.5°	620.9	620.3	619.8	619.1	619.8	620.3	620.9	621.5	622.0	622.7	623.3
125°	685.8	685.6	685.3	685.1	685.3	685.6	685.8	686.1	686.6	687.4	688.2
127.5°	747.6	746.8	746.0	745.1	746.0	746.8	747.6	748.4	749.3	750.2	751.2
130°	791.4	790.3	789.3	788.3	789.3	790.3	791.4	792.4	793.2	793.8	794.3
132.5°	832.1	831.2	830.4	829.6	830.4	831.2	832.1	832.9	833.9	835.1	836.2
135°	896.2	895.4	894.6	893.8	894.6	895.4	896.2	897.0	897.5	897.8	898.1
137.5°	955.1	954.1	953.1	952.0	953.1	954.1	955.1	956.2	956.8	957.0	957.3
140°	995.5	994.5	993.4	992.4	993.4	994.5	995.5	996.5	997.0	997.0	997.0
142.5°	1032.1	1031.1	1030.1	1029.0	1030.1	1031.1	1032.1	1033.2	1033.6	1033.4	1033.2
145°	1087.0	1086.0	1084.9	1083.9	1084.9	1086.0	1087.0	1088.0	1088.4	1088.2	1087.9
147.5°	1135.9	1134.9	1133.9	1133.0	1133.9	1134.9	1135.9	1136.9	1137.1	1136.5	1136.0
150°	1167.2	1166.4	1165.6	1164.9	1165.6	1166.4	1167.2	1168.0	1168.0	1167.2	1166.4
152.5°	1197.8	1196.9	1195.9	1194.9	1195.9	1196.9	1197.8	1198.8	1198.8	1197.8	1196.9
155°	1237.6	1236.8	1236.0	1235.2	1236.0	1236.8	1237.6	1238.3	1238.1	1236.8	1235.5
157.5°	1273.6	1272.4	1271.2	1269.9	1271.2	1272.4	1273.6	1275.0	1274.7	1272.9	1271.1
160°	1294.6	1293.6	1292.5	1291.5	1292.5	1293.6	1294.6	1295.7	1295.5	1293.8	1292.3
162.5°	1314.0	1312.8	1311.5	1310.3	1311.5	1312.8	1314.0	1315.2	1315.0	1313.2	1311.5
165°	1338.9	1337.6	1336.3	1334.9	1336.3	1337.6	1338.9	1340.1	1339.9	1338.1	1336.3
167.5°	1359.2	1357.8	1356.5	1355.1	1356.5	1357.8	1359.2	1360.5	1360.3	1358.5	1356.7
170°	1370.1	1368.6	1367.0	1365.4	1367.0	1368.6	1370.1	1371.7	1371.5	1369.7	1367.9
172.5°	1378.6	1377.0	1375.4	1373.8	1375.4	1377.0	1378.6	1380.1	1380.0	1378.2	1376.3
175°	1387.8	1386.1	1384.6	1383.0	1384.6	1386.1	1387.8	1389.3	1389.2	1387.4	1385.5
177.5°	1391.0	1389.8	1388.5	1387.3	1388.5	1389.8	1391.0	1392.2	1392.2	1391.0	1389.8
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1



TEST NUMBER: P331367-840
 CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1289.0	1293.5	1300.5	1308.0	1312.5	1321.2	1323.6	1327.8	1331.5	1340.2	1349.2
5°	1214.6	1221.7	1238.8	1248.1	1260.9	1275.9	1285.7	1296.1	1307.4	1327.0	1344.9
7.5°	1134.8	1146.8	1167.9	1185.3	1203.7	1225.1	1240.5	1260.9	1277.9	1305.5	1331.9
10°	1081.6	1098.5	1117.6	1138.2	1164.1	1186.7	1208.4	1234.2	1254.8	1287.8	1318.7
12.5°	1033.7	1036.3	1063.6	1086.3	1121.6	1149.6	1174.6	1207.8	1228.0	1267.2	1299.7
15°	950.1	965.5	990.3	1008.4	1050.2	1085.7	1120.7	1155.3	1178.5	1226.9	1269.7
17.5°	879.7	893.9	919.3	948.9	978.9	1014.2	1059.6	1096.0	1127.5	1183.0	1233.6
20°	835.2	852.6	878.5	908.9	935.1	973.8	1013.0	1054.7	1088.7	1151.1	1210.4
22.5°	797.2	811.0	831.8	861.8	890.6	925.9	968.9	1014.3	1050.1	1117.3	1177.4
25°	743.9	755.3	768.6	793.3	825.9	864.5	898.1	948.1	1000.1	1063.0	1135.7
27.5°	695.8	703.9	715.8	737.5	762.7	798.8	836.1	883.5	935.8	1004.1	1080.9
30°	666.6	671.8	683.6	701.7	726.4	754.7	792.3	837.7	891.3	960.4	1036.7
32.5°	641.0	645.7	653.5	670.7	692.2	716.4	750.3	795.7	846.8	914.6	999.2
35°	602.7	606.2	613.0	626.8	638.7	662.5	690.7	732.1	780.0	845.0	932.6
37.5°	564.4	569.4	573.5	579.4	594.6	610.2	634.8	669.6	716.7	782.2	865.8
40°	539.3	543.3	549.6	552.1	564.5	578.5	598.5	630.5	677.9	737.7	819.2
42.5°	513.6	517.8	521.5	524.5	535.2	547.4	565.5	593.0	635.0	693.2	773.8
45°	478.9	479.4	483.0	488.7	493.8	502.6	515.5	539.3	571.7	626.3	699.5
47.5°	443.6	444.2	444.8	447.4	453.0	461.0	469.5	488.8	517.9	561.5	632.8
50°	420.1	419.1	420.1	422.2	425.9	432.5	442.3	456.3	480.0	520.7	586.1
52.5°	397.5	397.3	396.7	397.5	400.2	404.9	411.8	423.6	444.8	482.3	540.0
55°	362.9	360.3	360.8	358.8	363.5	364.5	369.6	379.4	398.0	423.7	477.9
57.5°	326.1	324.0	321.6	321.0	320.6	323.5	327.6	335.3	349.5	372.1	416.1
60°	302.7	300.0	296.9	295.9	295.9	297.4	299.5	305.2	318.6	338.7	374.8
62.5°	278.7	275.7	273.9	271.1	270.3	271.9	274.0	278.0	287.6	306.5	337.7
65°	241.8	238.1	235.6	235.1	234.1	232.5	233.5	237.6	245.4	260.3	285.1
67.5°	204.8	201.4	200.8	197.7	196.3	196.5	196.3	199.9	204.5	217.3	235.8
70°	180.5	177.8	176.8	174.2	173.2	172.2	171.2	174.2	178.8	189.8	205.7
72.5°	155.7	153.5	151.3	149.1	149.3	148.2	148.0	149.9	153.7	163.7	176.0
75°	120.1	120.7	118.1	115.4	114.9	113.9	113.9	115.4	117.0	124.7	134.5
77.5°	87.2	86.7	84.5	83.7	83.2	82.1	83.2	84.2	85.0	90.2	97.5
80°	66.6	66.6	63.9	63.9	63.4	61.9	63.4	62.4	64.4	69.6	74.7
82.5°	47.6	46.7	46.6	45.7	45.6	44.5	45.2	46.3	47.2	50.6	53.7
85°	23.2	23.2	22.7	22.2	22.7	22.2	22.7	23.2	23.7	25.2	27.9
87.5°	13.0	13.5	12.8	12.1	10.9	10.2	9.8	9.5	9.7	9.5	9.3
90°	40.5	41.1	35.3	29.6	23.8	18.1	13.7	10.6	7.5	4.3	1.2
92.5°	37.4	37.3	36.0	34.6	33.2	31.9	30.1	27.8	25.4	23.1	20.9
95°	75.0	75.0	74.5	74.0	73.5	73.0	71.4	68.8	66.2	63.6	61.0
97.5°	126.2	126.2	125.2	124.2	123.2	122.3	120.6	118.4	116.0	113.7	111.5
100°	161.9	161.9	161.1	160.3	159.6	158.8	157.3	155.2	153.2	151.1	149.0
102.5°	200.6	200.4	199.3	198.3	197.4	196.4	195.1	193.4	191.8	190.1	188.4
105°	258.6	258.0	257.5	257.0	256.5	256.0	255.3	254.6	253.8	253.0	252.2
107.5°	321.8	321.6	321.6	321.6	321.6	321.6	321.0	319.9	318.8	317.6	316.5
110°	364.9	364.9	364.9	364.9	364.9	364.9	364.1	362.4	360.9	359.3	357.8



TEST NUMBER: P331367-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	408.3	408.9	409.1	409.3	409.5	409.8	409.1	407.5	406.0	404.3	402.8
115°	473.6	473.9	474.4	474.9	475.4	475.9	475.4	473.9	472.3	470.8	469.2
117.5°	537.6	538.2	539.7	541.1	542.6	544.0	543.7	541.6	539.6	537.5	535.3
120°	579.5	579.5	581.6	583.7	585.7	587.8	587.8	585.7	583.7	581.6	579.5
122.5°	623.9	624.5	626.0	627.4	628.9	630.4	629.9	627.3	624.8	622.4	619.9
125°	688.9	689.7	690.5	691.4	692.1	692.9	692.1	689.7	687.4	685.1	682.7
127.5°	752.1	753.1	754.1	755.0	755.9	756.9	755.8	752.9	749.9	746.9	744.0
130°	794.8	795.4	795.9	796.4	796.9	797.4	796.0	792.5	789.2	785.8	782.4
132.5°	837.4	838.5	838.4	838.3	838.2	838.1	836.7	833.8	831.1	828.4	825.6
135°	898.3	898.6	898.1	897.5	897.0	896.5	894.7	891.9	889.1	886.2	883.3
137.5°	957.5	957.7	956.9	956.3	955.6	954.9	953.4	951.1	948.8	946.4	944.0
140°	997.0	997.0	995.8	994.5	993.2	991.9	990.1	987.7	985.3	983.0	980.7
142.5°	1033.0	1032.8	1031.9	1031.0	1030.1	1029.2	1027.5	1025.2	1022.9	1020.6	1018.2
145°	1087.6	1087.4	1085.8	1084.3	1082.7	1081.2	1079.4	1077.6	1075.8	1074.0	1072.2
147.5°	1135.4	1134.8	1133.8	1132.8	1131.7	1130.6	1129.0	1126.8	1124.6	1122.5	1120.2
150°	1165.6	1164.9	1163.8	1162.8	1161.7	1160.6	1159.3	1157.8	1156.2	1154.7	1153.1
152.5°	1195.9	1194.9	1193.7	1192.3	1191.1	1189.8	1188.4	1186.9	1185.3	1183.8	1182.1
155°	1234.2	1232.8	1232.1	1231.3	1230.5	1229.7	1229.0	1228.2	1227.4	1226.6	1225.9
157.5°	1269.4	1267.6	1267.1	1266.7	1266.2	1265.7	1265.3	1264.7	1264.1	1263.6	1263.1
160°	1290.7	1289.2	1288.9	1288.7	1288.4	1288.1	1287.8	1287.2	1286.7	1286.2	1285.7
162.5°	1309.7	1308.0	1307.7	1307.4	1307.2	1306.9	1306.8	1306.6	1306.5	1306.4	1306.3
165°	1334.4	1332.6	1332.6	1332.6	1332.6	1332.6	1332.7	1332.9	1333.2	1333.5	1333.7
167.5°	1354.8	1353.0	1353.0	1353.1	1353.1	1353.2	1353.6	1354.4	1355.1	1355.9	1356.8
170°	1366.0	1364.2	1364.5	1364.7	1365.0	1365.3	1365.8	1366.5	1367.4	1368.2	1369.0
172.5°	1374.5	1372.7	1372.9	1373.2	1373.5	1373.7	1374.2	1375.0	1375.8	1376.6	1377.4
175°	1383.7	1381.8	1382.4	1382.9	1383.4	1383.9	1384.6	1385.3	1386.1	1386.9	1387.8
177.5°	1388.5	1387.3	1387.7	1388.1	1388.5	1388.9	1389.5	1390.1	1390.7	1391.3	1391.9
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1



TEST NUMBER: P331367-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1348.4	1350.5	1357.1	1363.6	1371.1	1373.1	1376.4	1373.5	1372.7	1380.6	1386.3
5°	1352.2	1361.5	1379.6	1396.0	1410.0	1419.8	1430.1	1434.2	1441.9	1452.7	1466.1
7.5°	1347.9	1365.9	1394.3	1418.3	1444.5	1463.4	1478.1	1490.7	1505.9	1526.4	1548.8
10°	1342.9	1367.2	1401.7	1431.1	1463.0	1487.2	1507.4	1526.9	1549.6	1578.0	1607.4
12.5°	1333.8	1362.6	1405.8	1440.6	1481.6	1505.4	1532.6	1574.8	1599.1	1638.6	1680.0
15°	1315.7	1347.6	1407.9	1450.7	1497.0	1542.5	1592.5	1632.6	1672.8	1696.1	1754.3
17.5°	1288.5	1335.4	1402.2	1452.1	1511.1	1582.6	1638.7	1684.3	1730.7	1768.4	1797.6
20°	1266.7	1317.7	1393.9	1453.8	1523.9	1600.6	1665.2	1711.5	1751.7	1783.2	1801.2
22.5°	1239.0	1303.2	1377.5	1447.5	1537.1	1613.1	1680.8	1717.3	1750.9	1766.3	1773.2
25°	1195.5	1272.8	1356.9	1442.4	1543.5	1623.9	1685.8	1707.9	1717.7	1702.7	1678.0
27.5°	1148.6	1234.8	1333.0	1432.7	1539.5	1616.9	1661.2	1657.7	1641.1	1592.8	1554.1
30°	1113.5	1208.4	1314.0	1422.8	1530.0	1605.3	1631.1	1605.3	1567.7	1513.6	1458.4
32.5°	1076.8	1175.0	1293.8	1408.8	1512.8	1578.9	1584.5	1540.1	1481.9	1420.4	1351.6
35°	1021.3	1127.4	1255.8	1377.5	1475.9	1517.7	1493.0	1414.6	1345.5	1261.5	1167.6
37.5°	958.5	1075.7	1204.5	1331.6	1420.8	1431.7	1370.3	1287.8	1190.3	1091.6	981.2
40°	911.4	1035.7	1168.2	1296.6	1375.4	1364.0	1285.7	1195.0	1078.9	958.4	855.8
42.5°	869.4	993.6	1128.5	1254.5	1317.7	1286.6	1195.0	1083.6	959.0	845.4	751.4
45°	796.5	924.3	1062.5	1184.2	1220.2	1164.1	1042.9	919.2	796.5	701.7	627.4
47.5°	725.8	852.1	989.0	1095.9	1108.6	1033.1	900.7	773.4	667.9	590.7	538.3
50°	673.8	800.6	936.1	1031.6	1027.4	936.1	800.1	678.9	590.8	528.4	493.3
52.5°	627.2	747.0	877.2	963.9	942.1	842.5	712.7	605.1	532.6	483.8	452.1
55°	554.7	665.5	789.2	858.9	818.6	708.3	598.5	511.9	458.3	421.7	397.0
57.5°	482.7	586.6	692.6	735.5	691.1	589.2	497.6	434.7	394.5	367.4	351.2
60°	438.2	529.0	623.3	660.4	607.2	516.5	444.3	388.2	355.7	333.6	319.1
62.5°	393.6	474.9	563.9	584.1	535.5	458.8	394.9	348.2	321.4	301.7	288.2
65°	333.1	399.5	467.1	480.5	435.7	376.4	325.8	295.4	271.7	257.2	246.4
67.5°	273.2	326.5	374.4	385.2	345.9	304.8	268.3	241.8	225.7	213.7	204.6
70°	237.6	279.9	319.1	327.9	296.4	259.8	232.0	210.9	196.4	186.1	177.3
72.5°	200.2	235.4	267.9	273.9	248.1	220.3	197.3	180.8	167.9	161.4	153.0
75°	153.1	173.7	198.9	200.6	183.5	166.5	149.0	138.1	131.5	123.2	119.1
77.5°	108.1	124.2	138.7	141.5	131.4	119.8	110.0	101.5	95.7	92.0	88.2
80°	82.5	95.3	101.6	105.1	98.0	89.7	84.0	78.4	74.7	72.2	69.6
82.5°	59.0	67.0	72.7	75.4	71.6	66.7	60.9	57.8	54.9	52.8	51.9
85°	29.9	33.5	37.2	38.2	37.2	35.0	31.9	31.9	30.4	29.9	29.9
87.5°	11.2	13.4	14.0	16.0	16.0	17.2	18.3	19.0	19.8	19.3	18.7
90°	4.3	7.5	10.6	13.7	18.1	23.8	29.6	35.3	41.1	40.5	40.0
92.5°	23.1	25.4	27.8	30.1	31.9	33.2	34.6	36.0	37.3	37.4	37.5
95°	63.6	66.2	68.8	71.4	73.0	73.5	74.0	74.5	75.0	75.0	75.0
97.5°	113.7	116.0	118.4	120.6	122.3	123.2	124.2	125.2	126.2	126.2	126.2
100°	151.1	153.2	155.2	157.3	158.8	159.6	160.3	161.1	161.9	161.9	161.9
102.5°	190.1	191.8	193.4	195.1	196.4	197.4	198.3	199.3	200.4	200.6	200.8
105°	253.0	253.8	254.6	255.3	256.0	256.5	257.0	257.5	258.0	258.6	259.1
107.5°	317.6	318.8	319.9	321.0	321.6	321.6	321.6	321.6	321.6	321.8	322.0
110°	359.3	360.9	362.4	364.1	364.9	364.9	364.9	364.9	364.9	364.9	364.9



TEST NUMBER: P331367-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	404.3	406.0	407.5	409.1	409.8	409.5	409.3	409.1	408.9	408.3	407.7
115°	470.8	472.3	473.9	475.4	475.9	475.4	474.9	474.4	473.9	473.6	473.4
117.5°	537.5	539.6	541.6	543.7	544.0	542.6	541.1	539.7	538.2	537.6	536.9
120°	581.6	583.7	585.7	587.8	587.8	585.7	583.7	581.6	579.5	579.5	579.5
122.5°	622.4	624.8	627.3	629.9	630.4	628.9	627.4	626.0	624.5	623.9	623.3
125°	685.1	687.4	689.7	692.1	692.9	692.1	691.4	690.5	689.7	688.9	688.2
127.5°	746.9	749.9	752.9	755.8	756.9	755.9	755.0	754.1	753.1	752.1	751.2
130°	785.8	789.2	792.5	796.0	797.4	796.9	796.4	795.9	795.4	794.8	794.3
132.5°	828.4	831.1	833.8	836.7	838.1	838.2	838.3	838.4	838.5	837.4	836.2
135°	886.2	889.1	891.9	894.7	896.5	897.0	897.5	898.1	898.6	898.3	898.1
137.5°	946.4	948.8	951.1	953.4	954.9	955.6	956.3	956.9	957.7	957.5	957.3
140°	983.0	985.3	987.7	990.1	991.9	993.2	994.5	995.8	997.0	997.0	997.0
142.5°	1020.6	1022.9	1025.2	1027.5	1029.2	1030.1	1031.0	1031.9	1032.8	1033.0	1033.2
145°	1074.0	1075.8	1077.6	1079.4	1081.2	1082.7	1084.3	1085.8	1087.4	1087.6	1087.9
147.5°	1122.5	1124.6	1126.8	1129.0	1130.6	1131.7	1132.8	1133.8	1134.8	1135.4	1136.0
150°	1154.7	1156.2	1157.8	1159.3	1160.6	1161.7	1162.8	1163.8	1164.9	1165.6	1166.4
152.5°	1183.8	1185.3	1186.9	1188.4	1189.8	1191.1	1192.3	1193.7	1194.9	1195.9	1196.9
155°	1226.6	1227.4	1228.2	1229.0	1229.7	1230.5	1231.3	1232.1	1232.8	1234.2	1235.5
157.5°	1263.6	1264.1	1264.7	1265.3	1265.7	1266.2	1266.7	1267.1	1267.6	1269.4	1271.1
160°	1286.2	1286.7	1287.2	1287.8	1288.1	1288.4	1288.7	1288.9	1289.2	1290.7	1292.3
162.5°	1306.4	1306.5	1306.6	1306.8	1306.9	1307.2	1307.4	1307.7	1308.0	1309.7	1311.5
165°	1333.5	1333.2	1332.9	1332.7	1332.6	1332.6	1332.6	1332.6	1332.6	1334.4	1336.3
167.5°	1355.9	1355.1	1354.4	1353.6	1353.2	1353.1	1353.1	1353.0	1353.0	1354.8	1356.7
170°	1368.2	1367.4	1366.5	1365.8	1365.3	1365.0	1364.7	1364.5	1364.2	1366.0	1367.9
172.5°	1376.6	1375.8	1375.0	1374.2	1373.7	1373.5	1373.2	1372.9	1372.7	1374.5	1376.3
175°	1386.9	1386.1	1385.3	1384.6	1383.9	1383.4	1382.9	1382.4	1381.8	1383.7	1385.5
177.5°	1391.3	1390.7	1390.1	1389.5	1388.9	1388.5	1388.1	1387.7	1387.3	1388.5	1389.8
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1



TEST NUMBER: P331367-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1391.3	1397.0	1397.0	1397.9	1404.5	1403.6	1403.2
5°	1480.6	1489.3	1490.4	1499.6	1505.8	1503.8	1498.1
7.5°	1564.8	1581.1	1593.5	1600.3	1608.5	1613.6	1611.3
10°	1631.6	1655.4	1669.8	1679.6	1691.4	1700.2	1697.1
12.5°	1692.2	1720.5	1740.3	1757.1	1758.7	1769.9	1762.2
15°	1786.8	1816.6	1819.8	1832.2	1842.0	1840.9	1841.4
17.5°	1818.1	1827.7	1829.6	1829.9	1830.0	1826.3	1818.6
20°	1806.9	1803.3	1794.5	1787.9	1775.9	1774.4	1764.1
22.5°	1754.1	1742.6	1720.7	1706.2	1687.7	1682.8	1680.0
25°	1650.2	1624.9	1589.8	1556.3	1547.1	1529.0	1534.2
27.5°	1507.6	1468.2	1430.3	1403.0	1378.4	1351.4	1359.1
30°	1407.3	1363.0	1309.4	1268.2	1241.9	1216.1	1211.4
32.5°	1287.8	1222.8	1163.0	1126.7	1086.4	1070.2	1052.3
35°	1081.6	1018.1	958.9	907.9	878.5	855.8	835.2
37.5°	896.1	823.0	775.3	733.9	712.7	699.6	703.0
40°	781.0	717.1	682.1	650.6	631.0	621.7	623.8
42.5°	687.8	640.0	611.1	589.6	575.7	570.6	569.4
45°	582.0	555.2	531.5	519.2	512.4	506.8	503.1
47.5°	509.9	488.0	474.6	467.3	461.4	455.7	455.6
50°	466.6	452.1	442.8	435.0	430.5	426.4	429.9
52.5°	433.5	420.3	411.1	404.1	402.4	398.7	398.6
55°	384.6	374.3	367.6	361.3	358.3	356.2	353.7
57.5°	340.0	330.2	324.1	320.1	314.3	312.1	311.3
60°	308.3	300.5	294.4	289.2	286.6	282.5	282.5
62.5°	279.0	271.2	265.5	261.6	257.3	255.7	256.1
65°	236.6	230.5	224.8	220.7	219.6	216.5	217.5
67.5°	197.6	193.5	187.5	185.3	183.3	181.7	180.5
70°	171.7	167.5	164.4	161.4	159.8	159.8	159.8
72.5°	149.8	144.8	143.0	139.1	140.0	138.4	136.7
75°	116.0	112.9	111.4	109.8	107.2	107.2	107.2
77.5°	85.3	84.4	82.6	80.9	80.3	79.8	80.0
80°	65.9	65.4	64.4	64.4	63.4	62.9	61.9
82.5°	50.7	49.4	48.8	48.4	48.2	48.1	47.9
85°	28.9	27.9	27.9	28.4	27.4	27.4	27.9
87.5°	19.0	18.9	18.5	18.6	19.0	18.7	18.7
90°	39.5	39.0	38.9	39.1	39.4	39.6	39.9
92.5°	37.6	37.8	37.8	37.9	37.9	38.0	38.0
95°	75.0	75.0	74.8	74.3	73.8	73.2	72.7
97.5°	126.2	126.2	126.2	126.1	126.1	126.0	126.0
100°	161.9	161.9	161.8	161.5	161.3	161.0	160.7
102.5°	201.0	201.2	201.2	200.9	200.7	200.4	200.2
105°	259.6	260.1	260.4	260.4	260.4	260.4	260.4
107.5°	322.2	322.4	321.9	320.8	319.6	318.4	317.2
110°	364.9	364.9	364.5	363.7	362.8	362.0	361.3



TEST NUMBER: P331367-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	407.1	406.5	405.9	405.3	404.7	404.1	403.5
115°	473.1	472.8	472.3	471.6	470.8	470.0	469.2
117.5°	536.3	535.7	535.0	534.2	533.4	532.6	531.9
120°	579.5	579.5	579.1	578.3	577.5	576.7	575.9
122.5°	622.7	622.0	621.5	620.9	620.3	619.8	619.1
125°	687.4	686.6	686.1	685.8	685.6	685.3	685.1
127.5°	750.2	749.3	748.4	747.6	746.8	746.0	745.1
130°	793.8	793.2	792.4	791.4	790.3	789.3	788.3
132.5°	835.1	833.9	832.9	832.1	831.2	830.4	829.6
135°	897.8	897.5	897.0	896.2	895.4	894.6	893.8
137.5°	957.0	956.8	956.2	955.1	954.1	953.1	952.0
140°	997.0	997.0	996.5	995.5	994.5	993.4	992.4
142.5°	1033.4	1033.6	1033.2	1032.1	1031.1	1030.1	1029.0
145°	1088.2	1088.4	1088.0	1087.0	1086.0	1084.9	1083.9
147.5°	1136.5	1137.1	1136.9	1135.9	1134.9	1133.9	1133.0
150°	1167.2	1168.0	1168.0	1167.2	1166.4	1165.6	1164.9
152.5°	1197.8	1198.8	1198.8	1197.8	1196.9	1195.9	1194.9
155°	1236.8	1238.1	1238.3	1237.6	1236.8	1236.0	1235.2
157.5°	1272.9	1274.7	1275.0	1273.6	1272.4	1271.2	1269.9
160°	1293.8	1295.5	1295.7	1294.6	1293.6	1292.5	1291.5
162.5°	1313.2	1315.0	1315.2	1314.0	1312.8	1311.5	1310.3
165°	1338.1	1339.9	1340.1	1338.9	1337.6	1336.3	1334.9
167.5°	1358.5	1360.3	1360.5	1359.2	1357.8	1356.5	1355.1
170°	1369.7	1371.5	1371.7	1370.1	1368.6	1367.0	1365.4
172.5°	1378.2	1380.0	1380.1	1378.6	1377.0	1375.4	1373.8
175°	1387.4	1389.2	1389.3	1387.8	1386.1	1384.6	1383.0
177.5°	1391.0	1392.2	1392.2	1391.0	1389.8	1388.5	1387.3
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1

(END OF REPORT)