

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331369-840

Luminaire Tested: **SA2XXDIP-C675D1080U840-4F0-1E-UDD-D**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331369-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D1080U840-4F0-1E-UDD-D
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7065.3 lumens
Efficiency: N/A
Efficacy: 124.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: Semi-Indirect

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331369-840
CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-D

Luminous Intensity Polar Plot





TEST NUMBER: P331369-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42	34
1	93	89	84	81	84	80	76	73	64	61	59	49	47	46	35	34	33	27
2	84	77	70	65	76	69	64	59	55	51	48	42	40	37	30	29	27	22
3	77	67	60	54	69	61	54	49	48	44	40	37	34	31	26	24	23	18
4	70	59	51	45	63	53	46	41	43	38	34	33	29	26	23	21	19	15
5	64	52	44	38	57	47	40	35	38	33	29	29	25	22	21	18	16	13
6	59	47	39	33	53	42	35	30	34	29	25	26	22	19	19	16	14	11
7	54	42	34	28	49	38	31	26	31	25	22	24	20	17	17	15	13	10
8	50	38	30	25	45	34	28	23	28	23	19	22	18	15	16	13	11	9
9	47	35	27	22	42	31	25	20	25	20	17	20	16	13	15	12	10	8
10	43	32	24	20	39	29	22	18	23	18	15	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11485	11485	11485
5°	11541	11055	11013
10°	11469	10729	10608
15°	11310	10384	10181
20°	11112	10013	9772
25°	10913	9655	9399
30°	10635	9288	9023
35°	10355	8933	8760
40°	10057	8630	8496
45°	9777	8361	8270
50°	9476	8116	8048
55°	9160	7855	7822
60°	8770	7583	7583
65°	8367	7262	7299
70°	7917	6920	6990
75°	7339	6581	6708
80°	6436	6238	6424
85°	5566	5939	6199



TEST NUMBER: P331369-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.4	1.0
10°-20°	193.3	2.7
20°-30°	292.9	4.1
30°-40°	356.7	5.0
40°-50°	383.8	5.4
50°-60°	372.7	5.3
60°-70°	325.4	4.6
70°-80°	250.5	3.5
80°-90°	171.8	2.4
90°-100°	165.3	2.3
100°-110°	266.1	3.8
110°-120°	541.0	7.7
120°-130°	832.0	11.8
130°-140°	864.7	12.2
140°-150°	793.8	11.2
150°-160°	636.4	9.0
160°-170°	410.1	5.8
170°-180°	141.2	2.0
0°-30°	553.6	7.8
0°-40°	910.3	12.9
0°-60°	1666.8	23.6
0°-90°	2414.6	34.2
90°-120°	972.4	13.8
90°-150°	3462.9	49.0
90°-180°	4651.0	65.8
0°-180°	7065.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	711	711	711	711	711	
5°	713	710	704	710	709	68
15°	680	682	682	691	691	192
25°	618	626	635	647	651	284
35°	533	551	570	592	600	333
45°	437	465	501	532	543	337
55°	335	373	426	462	476	299
65°	229	280	340	381	396	227
75°	127	185	250	293	308	134
85°	37	101	167	209	225	40
90°	11	83	158	202	219	10
95°	78	94	160	203	216	92
105°	332	377	154	200	218	355
115°	621	653	724	280	192	611
125°	875	891	942	976	990	780
135°	1081	1098	1118	1149	1157	835
145°	1253	1253	1270	1283	1283	784
155°	1380	1371	1383	1388	1381	635
165°	1454	1448	1450	1457	1450	410
175°	1487	1480	1482	1488	1478	141
180°	1484	1484	1484	1484	1484	



TEST NUMBER: P331369-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-D

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	711.3	711.3	711.3	711.3	711.3	711.3	711.3	711.3	711.3	711.3	711.3
2.5°	715.5	714.9	714.4	713.8	713.3	712.4	711.0	709.7	708.5	707.2	708.1
5°	713.4	712.7	712.1	711.3	710.6	709.6	708.2	706.9	705.5	704.1	705.5
7.5°	707.0	706.5	706.1	705.6	705.2	704.4	703.4	702.3	701.3	700.2	701.9
10°	702.1	701.6	701.1	700.6	700.2	699.6	698.9	698.3	697.6	696.9	698.7
12.5°	693.8	693.9	694.0	694.1	694.2	694.0	693.5	693.0	692.5	692.0	693.8
15°	680.4	680.9	681.4	681.8	682.3	682.5	682.5	682.5	682.5	682.5	684.5
17.5°	663.1	664.1	665.0	666.0	666.9	667.8	668.5	669.2	669.9	670.8	672.9
20°	651.6	652.7	653.8	655.0	656.1	657.1	658.0	659.0	659.9	660.9	663.4
22.5°	639.1	640.5	641.9	643.2	644.5	645.8	647.1	648.3	649.6	651.0	653.5
25°	618.5	620.2	621.8	623.4	625.0	626.8	628.8	631.0	633.0	635.0	637.8
27.5°	593.8	596.4	599.1	601.7	604.3	606.8	609.3	611.7	614.1	616.5	620.0
30°	577.3	580.3	583.3	586.2	589.3	592.2	595.2	598.1	601.2	604.1	607.7
32.5°	559.2	562.5	565.8	569.2	572.6	576.0	579.6	583.0	586.5	590.1	594.3
35°	533.0	536.8	540.8	544.6	548.6	552.7	557.0	561.4	565.7	570.1	575.1
37.5°	504.5	509.1	513.5	518.0	522.5	527.6	533.2	538.9	544.4	550.1	555.7
40°	485.5	490.6	495.6	500.7	505.7	511.3	517.6	523.7	529.9	536.0	542.0
42.5°	467.5	472.4	477.5	482.5	487.6	493.6	500.8	507.9	514.9	522.1	528.6
45°	437.1	443.3	449.5	455.7	461.8	469.0	477.0	485.0	493.0	501.0	508.2
47.5°	407.2	413.9	420.7	427.4	434.1	442.2	451.6	461.0	470.4	479.8	487.3
50°	386.6	393.7	400.8	407.9	415.0	423.7	434.0	444.3	454.6	464.9	472.7
52.5°	366.8	374.3	381.7	389.2	396.7	405.9	416.7	427.6	438.4	449.3	457.3
55°	335.1	343.3	351.5	359.8	368.0	378.1	390.0	401.9	413.8	425.8	434.0
57.5°	303.7	313.1	322.3	331.6	340.9	351.6	363.8	375.9	388.1	400.2	409.1
60°	281.4	291.2	301.1	311.0	320.8	332.3	345.4	358.4	371.4	384.6	393.2
62.5°	261.7	271.9	282.1	292.3	302.6	314.2	327.2	340.2	353.4	366.4	375.7
65°	228.8	240.0	251.4	262.6	273.8	286.1	299.6	313.2	326.7	340.2	349.6
67.5°	198.7	210.5	222.3	234.0	245.7	258.4	272.3	286.1	299.9	313.8	323.3
70°	177.3	189.2	201.2	213.1	225.0	238.0	252.3	266.4	280.6	294.9	304.7
72.5°	157.5	169.8	182.1	194.4	206.6	219.9	234.4	248.7	263.2	277.5	287.2
75°	126.8	139.7	152.5	165.3	178.1	191.9	206.5	221.2	235.8	250.5	260.3
77.5°	97.1	110.6	124.0	137.3	150.8	165.0	179.9	194.8	209.6	224.5	234.4
80°	77.4	91.3	105.2	119.3	133.2	147.6	162.6	177.4	192.3	207.2	216.8
82.5°	60.8	74.6	88.4	102.2	116.0	130.4	145.5	160.6	175.6	190.8	200.4
85°	37.2	51.3	65.5	79.7	93.9	108.4	123.0	137.6	152.4	167.0	176.6
87.5°	20.4	34.6	48.8	62.9	77.2	91.8	106.7	121.8	136.8	151.9	161.5
90°	11.4	27.3	43.2	59.1	75.0	91.3	107.9	124.4	141.0	157.5	167.9
92.5°	31.2	43.3	55.4	67.6	79.7	93.3	108.4	123.4	138.5	153.6	163.2
95°	78.1	80.9	83.8	86.7	89.6	98.8	114.2	129.6	145.0	160.5	170.4
97.5°	145.7	133.1	120.5	107.9	95.2	97.5	114.5	131.6	148.7	165.7	175.1
100°	197.2	173.0	148.9	124.6	100.4	96.7	113.6	130.5	147.4	164.3	174.7
102.5°	253.1	253.9	254.8	255.6	256.4	246.1	224.6	203.2	181.7	160.3	171.0
105°	331.5	345.3	359.1	372.9	386.7	367.0	313.8	260.5	207.3	154.1	164.8
107.5°	422.1	433.2	444.3	455.3	466.5	438.7	371.9	305.3	238.6	171.9	176.9
110°	479.7	489.3	498.9	508.5	518.1	494.0	436.3	378.6	320.8	263.2	246.6



TEST NUMBER: P331369-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	534.6	542.9	551.2	559.6	567.8	568.8	562.4	556.0	549.7	543.3	463.6
115°	621.4	627.9	634.6	641.2	647.7	659.1	675.4	691.7	707.9	724.2	620.7
117.5°	697.9	704.1	710.2	716.4	722.7	732.6	746.2	759.8	773.5	787.1	767.1
120°	754.6	759.0	763.6	768.0	772.5	781.5	795.0	808.4	821.9	835.4	844.7
122.5°	802.6	806.8	810.9	815.1	819.2	827.9	841.2	854.4	867.8	881.1	889.0
125°	874.8	878.0	881.0	884.1	887.3	894.7	906.6	918.5	930.3	942.2	950.1
127.5°	941.2	944.4	947.6	950.8	954.0	960.3	969.6	978.9	988.2	997.4	1005.5
130°	983.3	986.8	990.5	994.0	997.6	1003.1	1010.6	1018.0	1025.4	1032.9	1041.0
132.5°	1026.2	1029.3	1032.3	1035.2	1038.2	1043.0	1049.2	1055.6	1062.0	1068.3	1075.8
135°	1081.0	1084.8	1088.6	1092.5	1096.3	1100.3	1104.8	1109.2	1113.7	1118.1	1125.4
137.5°	1137.5	1140.1	1142.8	1145.4	1148.0	1151.0	1154.5	1157.9	1161.3	1164.8	1171.3
140°	1174.4	1176.1	1177.8	1179.4	1181.1	1183.5	1186.6	1189.6	1192.8	1195.8	1201.6
142.5°	1205.3	1206.8	1208.3	1209.8	1211.2	1213.6	1216.7	1219.7	1222.8	1226.0	1230.8
145°	1252.8	1252.5	1252.3	1252.1	1251.8	1253.7	1257.8	1261.8	1266.0	1270.0	1273.0
147.5°	1295.2	1294.2	1293.3	1292.4	1291.5	1293.0	1297.1	1301.0	1305.0	1309.1	1310.5
150°	1322.6	1320.9	1319.3	1317.6	1316.0	1317.0	1320.8	1324.6	1328.5	1332.2	1333.7
152.5°	1345.7	1343.9	1342.0	1340.2	1338.4	1339.2	1342.8	1346.5	1350.1	1353.7	1355.1
155°	1379.5	1377.4	1375.2	1373.0	1370.9	1371.3	1374.1	1377.0	1379.9	1382.7	1384.1
157.5°	1405.9	1404.1	1402.3	1400.5	1398.7	1398.8	1400.8	1402.7	1404.7	1406.7	1408.4
160°	1421.4	1420.0	1418.5	1417.0	1415.6	1415.6	1417.0	1418.5	1420.0	1421.4	1422.8
162.5°	1435.1	1433.7	1432.2	1430.8	1429.4	1429.3	1430.5	1431.8	1433.0	1434.2	1435.8
165°	1453.6	1452.1	1450.7	1449.3	1447.8	1447.4	1448.1	1449.0	1449.7	1450.4	1452.0
167.5°	1467.3	1465.9	1464.4	1463.0	1461.6	1461.2	1461.9	1462.5	1463.2	1463.9	1465.5
170°	1475.0	1473.6	1472.2	1470.8	1469.4	1468.8	1469.4	1469.8	1470.3	1470.8	1472.4
172.5°	1480.2	1478.7	1477.3	1475.9	1474.5	1474.0	1474.5	1474.9	1475.4	1475.9	1477.5
175°	1486.8	1485.2	1483.5	1481.9	1480.2	1479.6	1480.1	1480.6	1481.0	1481.5	1483.2
177.5°	1487.9	1486.6	1485.2	1483.9	1482.6	1482.0	1482.2	1482.4	1482.6	1482.8	1484.1
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6



TEST NUMBER: P331369-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	711.3	711.3	711.3	711.3	711.3	711.3	711.3	711.3
2.5°	709.0	709.9	710.8	711.1	710.7	710.4	710.0	709.7
5°	706.9	708.2	709.6	710.2	709.9	709.7	709.5	709.2
7.5°	703.5	705.2	706.8	707.5	707.3	707.0	706.8	706.6
10°	700.5	702.4	704.3	705.0	704.8	704.6	704.4	704.1
12.5°	695.6	697.4	699.3	700.0	699.8	699.6	699.4	699.1
15°	686.6	688.6	690.7	691.7	691.5	691.2	690.9	690.7
17.5°	675.0	677.2	679.3	680.4	680.4	680.4	680.4	680.4
20°	665.9	668.4	670.9	672.2	672.2	672.2	672.2	672.2
22.5°	656.0	658.5	661.0	662.5	662.8	663.2	663.6	663.9
25°	640.6	643.3	646.0	647.7	648.4	649.1	649.8	650.6
27.5°	623.5	626.9	630.5	632.4	632.9	633.4	633.9	634.4
30°	611.5	615.1	618.7	621.0	621.7	622.4	623.0	623.7
32.5°	598.5	602.8	606.9	609.7	611.0	612.2	613.4	614.6
35°	580.2	585.2	590.3	593.6	595.2	596.8	598.3	600.0
37.5°	561.3	566.8	572.5	576.1	577.8	579.5	581.2	582.9
40°	548.0	553.9	559.9	563.9	565.9	568.0	570.1	572.2
42.5°	535.0	541.6	548.1	552.4	554.4	556.5	558.6	560.6
45°	515.2	522.3	529.5	534.1	536.4	538.8	541.0	543.3
47.5°	494.6	502.1	509.5	514.4	516.9	519.5	522.0	524.5
50°	480.5	488.3	496.1	501.3	503.8	506.3	508.8	511.3
52.5°	465.2	473.2	481.2	486.6	489.2	491.9	494.6	497.4
55°	442.2	450.5	458.8	464.3	467.4	470.3	473.3	476.3
57.5°	418.0	426.9	435.8	441.7	444.7	447.8	450.8	453.8
60°	401.9	410.6	419.4	425.4	428.5	431.7	434.9	438.2
62.5°	384.9	394.2	403.4	409.6	412.5	415.6	418.6	421.6
65°	359.0	368.4	377.8	384.0	387.0	389.9	392.9	395.9
67.5°	332.8	342.2	351.7	358.1	361.1	364.3	367.4	370.5
70°	314.6	324.4	334.3	340.5	343.3	346.1	348.8	351.5
72.5°	296.9	306.5	316.2	322.7	326.0	329.3	332.5	335.9
75°	270.2	280.0	289.9	296.3	299.3	302.3	305.3	308.2
77.5°	244.2	254.0	263.8	270.2	273.5	276.7	279.8	283.1
80°	226.4	236.1	245.7	252.2	255.3	258.5	261.8	265.0
82.5°	210.0	219.5	229.2	235.5	238.5	241.6	244.6	247.6
85°	186.2	195.9	205.5	211.9	215.1	218.3	221.6	224.7
87.5°	171.1	180.7	190.3	196.6	199.5	202.6	205.6	208.6
90°	178.2	188.6	198.9	205.8	209.0	212.2	215.4	218.6
92.5°	172.8	182.4	192.0	198.2	201.4	204.4	207.4	210.5
95°	180.3	190.2	200.1	206.2	208.7	211.3	213.8	216.3
97.5°	184.6	194.0	203.5	209.6	212.7	215.6	218.6	221.7
100°	185.0	195.4	205.8	212.5	215.5	218.5	221.5	224.5
102.5°	181.8	192.6	203.3	210.4	213.5	216.7	219.8	223.1
105°	175.4	186.1	196.7	203.8	207.2	210.8	214.2	217.6
107.5°	182.0	186.9	192.0	196.2	199.8	203.2	206.6	210.2
110°	230.0	213.6	197.0	190.5	194.0	197.4	201.0	204.4



TEST NUMBER: P331369-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	384.0	304.3	224.6	186.3	189.7	192.9	196.2	199.4
115°	517.1	413.4	309.9	250.7	236.1	221.5	206.8	192.2
117.5°	747.2	727.2	707.3	670.2	616.2	562.1	508.0	453.8
120°	853.9	863.2	872.4	862.2	832.5	802.8	773.2	743.6
122.5°	897.0	904.9	912.9	914.8	910.7	906.6	902.5	898.4
125°	957.9	965.7	973.6	979.0	981.7	984.5	987.2	990.1
127.5°	1013.7	1021.8	1030.0	1035.0	1037.2	1039.4	1041.6	1043.7
130°	1049.1	1057.2	1065.4	1070.3	1071.8	1073.4	1075.0	1076.6
132.5°	1083.4	1091.0	1098.5	1103.1	1104.7	1106.3	1107.9	1109.4
135°	1132.6	1139.7	1146.9	1151.2	1152.6	1154.0	1155.3	1156.6
137.5°	1177.9	1184.5	1191.0	1194.7	1195.4	1196.1	1196.9	1197.6
140°	1207.5	1213.3	1219.1	1222.0	1222.2	1222.4	1222.6	1222.8
142.5°	1235.8	1240.6	1245.5	1248.0	1248.0	1248.0	1248.0	1248.0
145°	1276.1	1279.1	1282.1	1283.6	1283.6	1283.5	1283.5	1283.4
147.5°	1311.9	1313.3	1314.7	1315.2	1314.7	1314.3	1313.9	1313.4
150°	1335.1	1336.6	1338.0	1338.1	1336.9	1335.7	1334.5	1333.3
152.5°	1356.6	1358.1	1359.5	1359.4	1357.8	1356.2	1354.6	1353.1
155°	1385.5	1387.0	1388.5	1388.2	1386.2	1384.4	1382.5	1380.6
157.5°	1410.0	1411.6	1413.2	1413.1	1411.3	1409.4	1407.5	1405.6
160°	1424.2	1425.6	1427.0	1426.9	1425.3	1423.6	1422.0	1420.3
162.5°	1437.4	1439.1	1440.8	1440.5	1438.5	1436.4	1434.3	1432.3
165°	1453.7	1455.3	1457.0	1457.0	1455.3	1453.7	1452.0	1450.4
167.5°	1467.2	1468.8	1470.6	1470.3	1468.1	1466.0	1463.9	1461.7
170°	1474.1	1475.7	1477.4	1477.1	1475.0	1472.9	1470.8	1468.5
172.5°	1479.3	1480.9	1482.6	1482.4	1480.2	1478.0	1475.9	1473.7
175°	1484.8	1486.5	1488.1	1487.8	1485.4	1483.0	1480.7	1478.2
177.5°	1485.4	1486.7	1488.1	1487.9	1486.2	1484.5	1482.8	1481.1
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6

(END OF REPORT)