

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331349-840

Luminaire Tested: **SA2XXDIP-C675D725U840-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331349-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D725U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5578.6 lumens
Efficiency: N/A
Efficacy: 121.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331349-840
CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331349-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	91	83	77	73	84	78	72	68	67	63	60	57	54	51	47	45	44	39
3	83	74	67	61	77	69	63	57	59	55	51	50	47	44	42	40	38	34
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	35	31	29	26
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	30	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	21	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21658	21658	21658	21658
5°	24280	21797	19316	21797
10°	27824	21620	16718	21620
15°	30780	21224	14770	21224
20°	30311	20797	13464	20797
25°	27332	20232	12636	20232
30°	22585	19328	12033	19328
35°	16462	18382	11606	18382
40°	13148	17266	11367	17266
45°	11488	15972	11040	15972
50°	10798	14722	10826	14722
55°	9956	13453	10536	13453
60°	9122	12103	10091	12103
65°	8309	10892	9650	10892
70°	7544	9711	9007	9711
75°	6687	8390	7973	8390
80°	5755	6946	6425	6946
85°	5169	5169	3816	5169



TEST NUMBER: P331349-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.7	2.3
10°-20°	371.4	6.7
20°-30°	539.0	9.7
30°-40°	568.8	10.2
40°-50°	503.6	9.0
50°-60°	401.9	7.2
60°-70°	273.2	4.9
70°-80°	140.0	2.5
80°-90°	37.5	0.7
90°-100°	59.3	1.1
100°-110°	184.1	3.3
110°-120°	314.7	5.6
120°-130°	413.8	7.4
130°-140°	464.4	8.3
140°-150°	455.4	8.2
150°-160°	382.0	6.8
160°-170°	253.3	4.5
170°-180°	88.5	1.6
0°-30°	1038.1	18.6
0°-40°	1606.9	28.8
0°-60°	2512.4	45.0
0°-90°	2963.1	53.1
90°-120°	558.0	10.0
90°-150°	1891.7	33.9
90°-180°	2616.0	46.9
0°-180°	5578.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1341	1341	1341	1341	1341	
5°	1498	1345	1192	1345	1498	150
15°	1841	1270	884	1270	1841	508
25°	1534	1136	709	1136	1534	693
35°	835	933	589	933	835	543
45°	503	700	484	700	503	396
55°	354	478	374	478	354	317
65°	218	285	253	285	218	216
75°	107	134	128	134	107	115
85°	28	28	21	28	28	31
90°	27	1	27	1	27	13
95°	49	41	49	41	49	55
105°	175	170	175	170	175	184
115°	316	316	316	316	316	312
125°	461	459	461	459	461	411
135°	602	594	602	594	602	463
145°	729	721	729	721	729	455
155°	831	825	831	825	831	383
165°	898	898	898	898	898	253
175°	931	934	931	934	931	88
180°	935	935	935	935	935	



TEST NUMBER: P331349-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1403.2	1403.6	1404.5	1397.9	1397.0	1397.0	1391.3	1386.3	1380.6	1372.7	1373.5
5°	1498.1	1503.8	1505.8	1499.6	1490.4	1489.3	1480.6	1466.1	1452.7	1441.9	1434.2
7.5°	1611.3	1613.6	1608.5	1600.3	1593.5	1581.1	1564.8	1548.8	1526.4	1505.9	1490.7
10°	1697.1	1700.2	1691.4	1679.6	1669.8	1655.4	1631.6	1607.4	1578.0	1549.6	1526.9
12.5°	1762.2	1769.9	1758.7	1757.1	1740.3	1720.5	1692.2	1680.0	1638.6	1599.1	1574.8
15°	1841.4	1840.9	1842.0	1832.2	1819.8	1816.6	1786.8	1754.3	1696.1	1672.8	1632.6
17.5°	1818.6	1826.3	1830.0	1829.9	1829.6	1827.7	1818.1	1797.6	1768.4	1730.7	1684.3
20°	1764.1	1774.4	1775.9	1787.9	1794.5	1803.3	1806.9	1801.2	1783.2	1751.7	1711.5
22.5°	1680.0	1682.8	1687.7	1706.2	1720.7	1742.6	1754.1	1773.2	1766.3	1750.9	1717.3
25°	1534.2	1529.0	1547.1	1556.3	1589.8	1624.9	1650.2	1678.0	1702.7	1717.7	1707.9
27.5°	1359.1	1351.4	1378.4	1403.0	1430.3	1468.2	1507.6	1554.1	1592.8	1641.1	1657.7
30°	1211.4	1216.1	1241.9	1268.2	1309.4	1363.0	1407.3	1458.4	1513.6	1567.7	1605.3
32.5°	1052.3	1070.2	1086.4	1126.7	1163.0	1222.8	1287.8	1351.6	1420.4	1481.9	1540.1
35°	835.2	855.8	878.5	907.9	958.9	1018.1	1081.6	1167.6	1261.5	1345.5	1414.6
37.5°	703.0	699.6	712.7	733.9	775.3	823.0	896.1	981.2	1091.6	1190.3	1287.8
40°	623.8	621.7	631.0	650.6	682.1	717.1	781.0	855.8	958.4	1078.9	1195.0
42.5°	569.4	570.6	575.7	589.6	611.1	640.0	687.8	751.4	845.4	959.0	1083.6
45°	503.1	506.8	512.4	519.2	531.5	555.2	582.0	627.4	701.7	796.5	919.2
47.5°	455.6	455.7	461.4	467.3	474.6	488.0	509.9	538.3	590.7	667.9	773.4
50°	429.9	426.4	430.5	435.0	442.8	452.1	466.6	493.3	528.4	590.8	678.9
52.5°	398.6	398.7	402.4	404.1	411.1	420.3	433.5	452.1	483.8	532.6	605.1
55°	353.7	356.2	358.3	361.3	367.6	374.3	384.6	397.0	421.7	458.3	511.9
57.5°	311.3	312.1	314.3	320.1	324.1	330.2	340.0	351.2	367.4	394.5	434.7
60°	282.5	282.5	286.6	289.2	294.4	300.5	308.3	319.1	333.6	355.7	388.2
62.5°	256.1	255.7	257.3	261.6	265.5	271.2	279.0	288.2	301.7	321.4	348.2
65°	217.5	216.5	219.6	220.7	224.8	230.5	236.6	246.4	257.2	271.7	295.4
67.5°	180.5	181.7	183.3	185.3	187.5	193.5	197.6	204.6	213.7	225.7	241.8
70°	159.8	159.8	159.8	161.4	164.4	167.5	171.7	177.3	186.1	196.4	210.9
72.5°	136.7	138.4	140.0	139.1	143.0	144.8	149.8	153.0	161.4	167.9	180.8
75°	107.2	107.2	107.2	109.8	111.4	112.9	116.0	119.1	123.2	131.5	138.1
77.5°	80.0	79.8	80.3	80.9	82.6	84.4	85.3	88.2	92.0	95.7	101.5
80°	61.9	62.9	63.4	64.4	64.4	65.4	65.9	69.6	72.2	74.7	78.4
82.5°	47.9	48.1	48.2	48.4	48.8	49.4	50.7	51.9	52.8	54.9	57.8
85°	27.9	27.4	27.4	28.4	27.9	27.9	28.9	29.9	29.9	30.4	31.9
87.5°	16.1	16.1	16.5	16.0	16.0	16.4	16.5	16.2	16.6	17.1	16.8
90°	26.9	26.7	26.5	26.4	26.2	26.3	26.6	27.0	27.3	27.7	23.7
92.5°	25.5	25.5	25.5	25.4	25.4	25.3	25.3	25.2	25.1	25.1	24.2
95°	49.0	49.3	49.7	50.0	50.4	50.5	50.5	50.5	50.5	50.5	50.2
97.5°	84.7	84.8	84.8	84.9	84.9	84.9	84.9	84.9	84.9	84.9	84.2
100°	108.2	108.4	108.5	108.7	108.9	109.0	109.0	109.0	109.0	109.0	108.4
102.5°	134.6	134.8	135.0	135.2	135.3	135.4	135.2	135.1	134.9	134.8	134.1
105°	175.2	175.2	175.2	175.2	175.2	175.1	174.7	174.4	174.0	173.7	173.3
107.5°	213.5	214.3	215.1	215.9	216.7	217.0	216.8	216.7	216.6	216.4	216.4
110°	243.1	243.7	244.2	244.7	245.2	245.5	245.5	245.5	245.5	245.5	245.5



TEST NUMBER: P331349-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	271.6	272.0	272.3	272.7	273.1	273.5	273.9	274.3	274.8	275.2	275.3
115°	315.8	316.3	316.8	317.3	317.8	318.2	318.4	318.5	318.7	318.9	319.2
117.5°	357.9	358.4	358.9	359.5	360.0	360.4	360.9	361.3	361.7	362.1	363.1
120°	387.6	388.1	388.6	389.1	389.7	389.9	389.9	389.9	389.9	389.9	391.3
122.5°	416.7	417.0	417.4	417.8	418.2	418.6	419.0	419.4	419.8	420.2	421.2
125°	461.0	461.2	461.3	461.5	461.7	462.0	462.5	463.1	463.6	464.1	464.6
127.5°	501.4	502.0	502.5	503.1	503.6	504.2	504.8	505.5	506.1	506.8	507.4
130°	530.5	531.2	531.9	532.5	533.2	533.8	534.1	534.5	534.8	535.2	535.5
132.5°	558.3	558.8	559.4	559.9	560.5	561.2	561.9	562.7	563.5	564.2	564.1
135°	601.5	602.0	602.6	603.1	603.6	603.9	604.1	604.3	604.5	604.6	604.3
137.5°	640.7	641.4	642.1	642.8	643.5	643.9	644.0	644.2	644.3	644.4	644.0
140°	667.8	668.5	669.2	669.9	670.6	671.0	671.0	671.0	671.0	671.0	670.0
142.5°	692.5	693.2	693.8	694.5	695.2	695.5	695.4	695.2	695.1	695.0	694.4
145°	729.3	730.0	730.7	731.4	732.2	732.5	732.3	732.1	732.0	731.7	730.6
147.5°	762.3	763.1	763.7	764.4	765.1	765.2	764.8	764.4	764.0	763.7	763.0
150°	783.9	784.4	784.9	785.4	786.0	786.0	785.4	784.9	784.4	783.9	783.2
152.5°	804.1	804.7	805.4	806.1	806.7	806.7	806.1	805.4	804.7	804.1	803.1
155°	831.2	831.7	832.2	832.7	833.3	833.1	832.2	831.3	830.5	829.6	829.1
157.5°	854.5	855.4	856.3	857.1	857.9	857.8	856.6	855.4	854.1	852.9	852.6
160°	869.1	869.8	870.5	871.2	871.9	871.7	870.7	869.6	868.6	867.5	867.4
162.5°	881.7	882.5	883.4	884.2	885.0	884.9	883.7	882.5	881.3	880.1	880.0
165°	898.3	899.2	900.0	900.9	901.8	901.6	900.4	899.2	898.0	896.7	896.7
167.5°	911.9	912.8	913.7	914.6	915.5	915.3	914.1	912.9	911.7	910.4	910.5
170°	918.8	919.9	920.9	922.0	923.0	922.9	921.7	920.5	919.3	918.0	918.2
172.5°	924.5	925.5	926.6	927.7	928.7	928.6	927.4	926.1	924.9	923.7	923.9
175°	930.7	931.7	932.7	933.8	934.8	934.7	933.5	932.3	931.1	929.9	930.2
177.5°	933.5	934.3	935.1	936.0	936.9	936.9	936.0	935.1	934.3	933.5	933.7
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331349-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1376.4	1373.1	1371.1	1363.6	1357.1	1350.5	1348.4	1349.2	1340.2	1331.5	1327.8
5°	1430.1	1419.8	1410.0	1396.0	1379.6	1361.5	1352.2	1344.9	1327.0	1307.4	1296.1
7.5°	1478.1	1463.4	1444.5	1418.3	1394.3	1365.9	1347.9	1331.9	1305.5	1277.9	1260.9
10°	1507.4	1487.2	1463.0	1431.1	1401.7	1367.2	1342.9	1318.7	1287.8	1254.8	1234.2
12.5°	1532.6	1505.4	1481.6	1440.6	1405.8	1362.6	1333.8	1299.7	1267.2	1228.0	1207.8
15°	1592.5	1542.5	1497.0	1450.7	1407.9	1347.6	1315.7	1269.7	1226.9	1178.5	1155.3
17.5°	1638.7	1582.6	1511.1	1452.1	1402.2	1335.4	1288.5	1233.6	1183.0	1127.5	1096.0
20°	1665.2	1600.6	1523.9	1453.8	1393.9	1317.7	1266.7	1210.4	1151.1	1088.7	1054.7
22.5°	1680.8	1613.1	1537.1	1447.5	1377.5	1303.2	1239.0	1177.4	1117.3	1050.1	1014.3
25°	1685.8	1623.9	1543.5	1442.4	1356.9	1272.8	1195.5	1135.7	1063.0	1000.1	948.1
27.5°	1661.2	1616.9	1539.5	1432.7	1333.0	1234.8	1148.6	1080.9	1004.1	935.8	883.5
30°	1631.1	1605.3	1530.0	1422.8	1314.0	1208.4	1113.5	1036.7	960.4	891.3	837.7
32.5°	1584.5	1578.9	1512.8	1408.8	1293.8	1175.0	1076.8	999.2	914.6	846.8	795.7
35°	1493.0	1517.7	1475.9	1377.5	1255.8	1127.4	1021.3	932.6	845.0	780.0	732.1
37.5°	1370.3	1431.7	1420.8	1331.6	1204.5	1075.7	958.5	865.8	782.2	716.7	669.6
40°	1285.7	1364.0	1375.4	1296.6	1168.2	1035.7	911.4	819.2	737.7	677.9	630.5
42.5°	1195.0	1286.6	1317.7	1254.5	1128.5	993.6	869.4	773.8	693.2	635.0	593.0
45°	1042.9	1164.1	1220.2	1184.2	1062.5	924.3	796.5	699.5	626.3	571.7	539.3
47.5°	900.7	1033.1	1108.6	1095.9	989.0	852.1	725.8	632.8	561.5	517.9	488.8
50°	800.1	936.1	1027.4	1031.6	936.1	800.6	673.8	586.1	520.7	480.0	456.3
52.5°	712.7	842.5	942.1	963.9	877.2	747.0	627.2	540.0	482.3	444.8	423.6
55°	598.5	708.3	818.6	858.9	789.2	665.5	554.7	477.9	423.7	398.0	379.4
57.5°	497.6	589.2	691.1	735.5	692.6	586.6	482.7	416.1	372.1	349.5	335.3
60°	444.3	516.5	607.2	660.4	623.3	529.0	438.2	374.8	338.7	318.6	305.2
62.5°	394.9	458.8	535.5	584.1	563.9	474.9	393.6	337.7	306.5	287.6	278.0
65°	325.8	376.4	435.7	480.5	467.1	399.5	333.1	285.1	260.3	245.4	237.6
67.5°	268.3	304.8	345.9	385.2	374.4	326.5	273.2	235.8	217.3	204.5	199.9
70°	232.0	259.8	296.4	327.9	319.1	279.9	237.6	205.7	189.8	178.8	174.2
72.5°	197.3	220.3	248.1	273.9	267.9	235.4	200.2	176.0	163.7	153.7	149.9
75°	149.0	166.5	183.5	200.6	198.9	173.7	153.1	134.5	124.7	117.0	115.4
77.5°	110.0	119.8	131.4	141.5	138.7	124.2	108.1	97.5	90.2	85.0	84.2
80°	84.0	89.7	98.0	105.1	101.6	95.3	82.5	74.7	69.6	64.4	62.4
82.5°	60.9	66.7	71.6	75.4	72.7	67.0	59.0	53.7	50.6	47.2	46.3
85°	31.9	35.0	37.2	38.2	37.2	33.5	29.9	27.9	25.2	23.7	23.2
87.5°	16.4	15.6	14.8	15.0	13.4	12.9	10.9	9.2	9.2	9.3	8.9
90°	19.9	16.1	12.2	9.2	7.1	5.0	2.9	0.8	2.9	5.0	7.1
92.5°	23.2	22.3	21.4	20.2	18.7	17.2	15.6	14.0	15.6	17.2	18.7
95°	49.8	49.5	49.1	48.1	46.4	44.5	42.8	41.0	42.8	44.5	46.4
97.5°	83.6	82.9	82.3	81.2	79.6	78.1	76.5	75.0	76.5	78.1	79.6
100°	107.9	107.3	106.8	105.8	104.4	103.0	101.7	100.3	101.7	103.0	104.4
102.5°	133.5	132.8	132.2	131.3	130.2	129.1	127.8	126.7	127.8	129.1	130.2
105°	173.0	172.6	172.3	171.8	171.3	170.8	170.3	169.8	170.3	170.8	171.3
107.5°	216.4	216.4	216.4	216.0	215.3	214.5	213.8	213.0	213.8	214.5	215.3
110°	245.5	245.5	245.5	245.0	243.9	242.9	241.8	240.8	241.8	242.9	243.9



TEST NUMBER: P331349-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	275.5	275.6	275.7	275.3	274.2	273.2	272.2	271.0	272.2	273.2	274.2
115°	319.6	319.9	320.3	319.9	318.9	317.8	316.8	315.8	316.8	317.8	318.9
117.5°	364.2	365.1	366.1	365.9	364.5	363.0	361.6	360.2	361.6	363.0	364.5
120°	392.7	394.2	395.6	395.6	394.2	392.7	391.3	389.9	391.3	392.7	394.2
122.5°	422.2	423.2	424.1	423.8	422.1	420.5	418.8	417.1	418.8	420.5	422.1
125°	465.1	465.7	466.3	465.7	464.1	462.5	461.0	459.4	461.0	462.5	464.1
127.5°	508.1	508.7	509.3	508.6	506.6	504.6	502.6	500.6	502.6	504.6	506.6
130°	535.8	536.2	536.5	535.6	533.3	531.1	528.8	526.5	528.8	531.1	533.3
132.5°	564.1	564.0	563.9	563.0	561.1	559.3	557.4	555.5	557.4	559.3	561.1
135°	603.9	603.6	603.2	602.1	600.2	598.2	596.3	594.4	596.3	598.2	600.2
137.5°	643.5	643.1	642.6	641.6	640.1	638.4	636.8	635.3	636.8	638.4	640.1
140°	669.2	668.3	667.4	666.2	664.6	663.1	661.5	659.9	661.5	663.1	664.6
142.5°	693.8	693.2	692.6	691.5	689.9	688.3	686.7	685.2	686.7	688.3	689.9
145°	729.6	728.6	727.5	726.4	725.2	724.0	722.7	721.4	722.7	724.0	725.2
147.5°	762.2	761.5	760.8	759.7	758.2	756.8	755.3	753.9	755.3	756.8	758.2
150°	782.4	781.7	781.0	780.1	779.1	778.0	777.0	776.0	777.0	778.0	779.1
152.5°	802.3	801.5	800.6	799.7	798.7	797.6	796.6	795.5	796.6	797.6	798.7
155°	828.6	828.0	827.5	827.0	826.5	826.0	825.4	824.9	825.4	826.0	826.5
157.5°	852.3	852.0	851.7	851.4	851.0	850.7	850.3	850.0	850.3	850.7	851.0
160°	867.2	867.0	866.8	866.6	866.2	865.9	865.5	865.2	865.5	865.9	866.2
162.5°	879.8	879.6	879.4	879.3	879.2	879.2	879.1	879.0	879.1	879.2	879.2
165°	896.7	896.7	896.7	896.8	897.0	897.2	897.4	897.5	897.4	897.2	897.0
167.5°	910.5	910.6	910.6	910.9	911.4	911.9	912.4	912.9	912.4	911.9	911.4
170°	918.4	918.6	918.7	919.1	919.6	920.1	920.7	921.2	920.7	920.1	919.6
172.5°	924.0	924.2	924.4	924.7	925.2	925.8	926.3	926.9	926.3	925.8	925.2
175°	930.6	930.9	931.3	931.7	932.2	932.7	933.3	933.8	933.3	932.7	932.2
177.5°	934.0	934.3	934.6	934.9	935.3	935.8	936.2	936.6	936.2	935.8	935.3
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331349-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1323.6	1321.2	1312.5	1308.0	1300.5	1293.5	1289.0	1291.1	1292.7	1291.9	1290.6
5°	1285.7	1275.9	1260.9	1248.1	1238.8	1221.7	1214.6	1210.9	1207.9	1204.3	1200.6
7.5°	1240.5	1225.1	1203.7	1185.3	1167.9	1146.8	1134.8	1127.5	1120.1	1112.0	1104.8
10°	1208.4	1186.7	1164.1	1138.2	1117.6	1098.5	1081.6	1070.3	1060.0	1050.2	1042.9
12.5°	1174.6	1149.6	1121.6	1086.3	1063.6	1036.3	1033.7	1013.7	997.6	991.6	983.1
15°	1120.7	1085.7	1050.2	1008.4	990.3	965.5	950.1	934.6	920.7	910.9	908.4
17.5°	1059.6	1014.2	978.9	948.9	919.3	893.9	879.7	867.3	855.9	842.7	841.0
20°	1013.0	973.8	935.1	908.9	878.5	852.6	835.2	822.7	812.9	805.3	798.5
22.5°	968.9	925.9	890.6	861.8	831.8	811.0	797.2	785.3	777.1	768.5	762.2
25°	898.1	864.5	825.9	793.3	768.6	755.3	743.9	733.6	728.4	722.8	715.6
27.5°	836.1	798.8	762.7	737.5	715.8	703.9	695.8	688.8	684.0	680.6	676.6
30°	792.3	754.7	726.4	701.7	683.6	671.8	666.6	662.5	656.8	654.7	652.7
32.5°	750.3	716.4	692.2	670.7	653.5	645.7	641.0	637.3	632.9	630.8	626.6
35°	690.7	662.5	638.7	626.8	613.0	606.2	602.7	597.4	593.4	591.3	590.8
37.5°	634.8	610.2	594.6	579.4	573.5	569.4	564.4	560.9	559.7	559.4	558.9
40°	598.5	578.5	564.5	552.1	549.6	543.3	539.3	536.1	536.1	536.6	536.1
42.5°	565.5	547.4	535.2	524.5	521.5	517.8	513.6	513.4	514.3	516.0	514.3
45°	515.5	502.6	493.8	488.7	483.0	479.4	478.9	480.5	481.0	481.5	483.0
47.5°	469.5	461.0	453.0	447.4	444.8	444.2	443.6	446.4	448.8	449.7	452.1
50°	442.3	432.5	425.9	422.2	420.1	419.1	420.1	423.2	425.3	427.9	429.4
52.5°	411.8	404.9	400.2	397.5	396.7	397.3	397.5	401.0	404.2	405.2	406.0
55°	369.6	364.5	363.5	358.8	360.8	360.3	362.9	365.0	368.1	371.1	371.7
57.5°	327.6	323.5	320.6	321.0	321.6	324.0	326.1	329.7	333.1	336.3	336.6
60°	299.5	297.4	295.9	295.9	296.9	300.0	302.7	306.2	308.3	310.3	311.8
62.5°	274.0	271.9	270.3	271.1	273.9	275.7	278.7	280.6	282.7	284.8	285.5
65°	233.5	232.5	234.1	235.1	235.6	238.1	241.8	243.3	245.4	246.4	250.0
67.5°	196.3	196.5	196.3	197.7	200.8	201.4	204.8	208.3	208.7	210.8	213.1
70°	171.2	172.2	173.2	174.2	176.8	177.8	180.5	182.0	184.0	185.6	187.1
72.5°	148.0	148.2	149.3	149.1	151.3	153.5	155.7	157.2	159.3	161.3	162.8
75°	113.9	113.9	114.9	115.4	118.1	120.7	120.1	121.2	123.2	125.2	126.3
77.5°	83.2	82.1	83.2	83.7	84.5	86.7	87.2	88.6	90.9	90.2	91.4
80°	63.4	61.9	63.4	63.9	63.9	66.6	66.6	67.6	69.1	67.6	69.1
82.5°	45.2	44.5	45.6	45.7	46.6	46.7	47.6	47.8	49.3	48.6	49.3
85°	22.7	22.2	22.7	22.2	22.7	23.2	23.2	22.7	22.7	23.7	22.2
87.5°	8.9	9.0	9.4	10.2	10.5	10.9	10.4	10.3	10.3	9.4	9.4
90°	9.2	12.2	16.1	19.9	23.7	27.7	27.3	27.0	26.6	26.3	26.2
92.5°	20.2	21.4	22.3	23.2	24.2	25.1	25.1	25.2	25.3	25.3	25.4
95°	48.1	49.1	49.5	49.8	50.2	50.5	50.5	50.5	50.5	50.5	50.4
97.5°	81.2	82.3	82.9	83.6	84.2	84.9	84.9	84.9	84.9	84.9	84.9
100°	105.8	106.8	107.3	107.9	108.4	109.0	109.0	109.0	109.0	109.0	108.9
102.5°	131.3	132.2	132.8	133.5	134.1	134.8	134.9	135.1	135.2	135.4	135.3
105°	171.8	172.3	172.6	173.0	173.3	173.7	174.0	174.4	174.7	175.1	175.2
107.5°	216.0	216.4	216.4	216.4	216.4	216.4	216.6	216.7	216.8	217.0	216.7
110°	245.0	245.5	245.5	245.5	245.5	245.5	245.5	245.5	245.5	245.5	245.2



TEST NUMBER: P331349-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	275.3	275.7	275.6	275.5	275.3	275.2	274.8	274.3	273.9	273.5	273.1
115°	319.9	320.3	319.9	319.6	319.2	318.9	318.7	318.5	318.4	318.2	317.8
117.5°	365.9	366.1	365.1	364.2	363.1	362.1	361.7	361.3	360.9	360.4	360.0
120°	395.6	395.6	394.2	392.7	391.3	389.9	389.9	389.9	389.9	389.9	389.7
122.5°	423.8	424.1	423.2	422.2	421.2	420.2	419.8	419.4	419.0	418.6	418.2
125°	465.7	466.3	465.7	465.1	464.6	464.1	463.6	463.1	462.5	462.0	461.7
127.5°	508.6	509.3	508.7	508.1	507.4	506.8	506.1	505.5	504.8	504.2	503.6
130°	535.6	536.5	536.2	535.8	535.5	535.2	534.8	534.5	534.1	533.8	533.2
132.5°	563.0	563.9	564.0	564.1	564.1	564.2	563.5	562.7	561.9	561.2	560.5
135°	602.1	603.2	603.6	603.9	604.3	604.6	604.5	604.3	604.1	603.9	603.6
137.5°	641.6	642.6	643.1	643.5	644.0	644.4	644.3	644.2	644.0	643.9	643.5
140°	666.2	667.4	668.3	669.2	670.0	671.0	671.0	671.0	671.0	671.0	670.6
142.5°	691.5	692.6	693.2	693.8	694.4	695.0	695.1	695.2	695.4	695.5	695.2
145°	726.4	727.5	728.6	729.6	730.6	731.7	732.0	732.1	732.3	732.5	732.2
147.5°	759.7	760.8	761.5	762.2	763.0	763.7	764.0	764.4	764.8	765.2	765.1
150°	780.1	781.0	781.7	782.4	783.2	783.9	784.4	784.9	785.4	786.0	786.0
152.5°	799.7	800.6	801.5	802.3	803.1	804.1	804.7	805.4	806.1	806.7	806.7
155°	827.0	827.5	828.0	828.6	829.1	829.6	830.5	831.3	832.2	833.1	833.3
157.5°	851.4	851.7	852.0	852.3	852.6	852.9	854.1	855.4	856.6	857.8	857.9
160°	866.6	866.8	867.0	867.2	867.4	867.5	868.6	869.6	870.7	871.7	871.9
162.5°	879.3	879.4	879.6	879.8	880.0	880.1	881.3	882.5	883.7	884.9	885.0
165°	896.8	896.7	896.7	896.7	896.7	896.7	898.0	899.2	900.4	901.6	901.8
167.5°	910.9	910.6	910.6	910.5	910.5	910.4	911.7	912.9	914.1	915.3	915.5
170°	919.1	918.7	918.6	918.4	918.2	918.0	919.3	920.5	921.7	922.9	923.0
172.5°	924.7	924.4	924.2	924.0	923.9	923.7	924.9	926.1	927.4	928.6	928.7
175°	931.7	931.3	930.9	930.6	930.2	929.9	931.1	932.3	933.5	934.7	934.8
177.5°	934.9	934.6	934.3	934.0	933.7	933.5	934.3	935.1	936.0	936.9	936.9
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331349-840
 CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1286.6	1285.7	1285.7	1282.0	1285.7	1285.7	1286.6	1290.6	1291.9	1292.7	1291.1
5°	1193.5	1191.8	1189.3	1191.8	1189.3	1191.8	1193.5	1200.6	1204.3	1207.9	1210.9
7.5°	1101.4	1095.2	1094.3	1088.1	1094.3	1095.2	1101.4	1104.8	1112.0	1120.1	1127.5
10°	1034.1	1030.0	1029.5	1019.7	1029.5	1030.0	1034.1	1042.9	1050.2	1060.0	1070.3
12.5°	983.0	973.1	975.0	969.4	975.0	973.1	983.0	983.1	991.6	997.6	1013.7
15°	894.4	894.4	892.3	883.6	892.3	894.4	894.4	908.4	910.9	920.7	934.6
17.5°	830.8	829.8	824.9	827.3	824.9	829.8	830.8	841.0	842.7	855.9	867.3
20°	792.8	789.8	783.6	783.6	783.6	789.8	792.8	798.5	805.3	812.9	822.7
22.5°	757.0	756.8	750.2	752.2	750.2	756.8	757.0	762.2	768.5	777.1	785.3
25°	715.0	710.9	707.8	709.3	707.8	710.9	715.0	715.6	722.8	728.4	733.6
27.5°	675.2	673.0	672.8	668.5	672.8	673.0	675.2	676.6	680.6	684.0	688.8
30°	652.2	647.0	648.0	645.4	648.0	647.0	652.2	652.7	654.7	656.8	662.5
32.5°	625.7	623.9	622.9	620.7	622.9	623.9	625.7	626.6	630.8	632.9	637.3
35°	589.8	590.3	587.7	588.8	587.7	590.3	589.8	590.8	591.3	593.4	597.4
37.5°	558.4	560.0	558.8	559.1	558.8	560.0	558.4	558.9	559.4	559.7	560.9
40°	537.7	537.7	537.7	539.3	537.7	537.7	537.7	536.1	536.6	536.1	536.1
42.5°	517.9	517.1	516.2	516.1	516.2	517.1	517.9	514.3	516.0	514.3	513.4
45°	484.0	485.6	486.1	483.5	486.1	485.6	484.0	483.0	481.5	481.0	480.5
47.5°	453.4	453.6	453.4	455.8	453.4	453.6	453.4	452.1	449.7	448.8	446.4
50°	432.0	431.0	432.0	431.0	432.0	431.0	432.0	429.4	427.9	425.3	423.2
52.5°	409.3	409.5	408.9	408.7	408.9	409.5	409.3	406.0	405.2	404.2	401.0
55°	373.8	374.8	374.3	374.3	374.3	374.8	373.8	371.7	371.1	368.1	365.0
57.5°	337.0	337.9	338.6	336.3	338.6	337.9	337.0	336.6	336.3	333.1	329.7
60°	311.3	314.0	313.5	312.5	313.5	314.0	311.3	311.8	310.3	308.3	306.2
62.5°	287.9	288.8	288.7	288.5	288.7	288.8	287.9	285.5	284.8	282.7	280.6
65°	251.6	252.6	251.1	252.6	251.1	252.6	251.6	250.0	246.4	245.4	243.3
67.5°	212.5	212.8	214.0	214.7	214.0	212.8	212.5	213.1	210.8	208.7	208.3
70°	188.1	187.6	189.1	190.8	189.1	187.6	188.1	187.1	185.6	184.0	182.0
72.5°	162.6	163.7	163.2	164.3	163.2	163.7	162.6	162.8	161.3	159.3	157.2
75°	125.2	126.8	126.3	127.8	126.3	126.8	125.2	126.3	125.2	123.2	121.2
77.5°	90.5	90.7	90.5	91.4	90.5	90.7	90.5	91.4	90.2	90.9	88.6
80°	69.1	68.1	67.1	69.1	67.1	68.1	69.1	69.1	67.6	69.1	67.6
82.5°	48.1	48.7	47.7	47.7	47.7	48.7	48.1	49.3	48.6	49.3	47.8
85°	22.2	21.6	20.6	20.6	20.6	21.6	22.2	22.2	23.7	22.7	22.7
87.5°	9.4	9.0	9.1	8.7	9.1	9.0	9.4	9.4	9.4	10.3	10.3
90°	26.4	26.5	26.7	26.9	26.7	26.5	26.4	26.2	26.3	26.6	27.0
92.5°	25.4	25.5	25.5	25.5	25.5	25.5	25.4	25.4	25.3	25.3	25.2
95°	50.0	49.7	49.3	49.0	49.3	49.7	50.0	50.4	50.5	50.5	50.5
97.5°	84.9	84.8	84.8	84.7	84.8	84.8	84.9	84.9	84.9	84.9	84.9
100°	108.7	108.5	108.4	108.2	108.4	108.5	108.7	108.9	109.0	109.0	109.0
102.5°	135.2	135.0	134.8	134.6	134.8	135.0	135.2	135.3	135.4	135.2	135.1
105°	175.2	175.2	175.2	175.2	175.2	175.2	175.2	175.2	175.1	174.7	174.4
107.5°	215.9	215.1	214.3	213.5	214.3	215.1	215.9	216.7	217.0	216.8	216.7
110°	244.7	244.2	243.7	243.1	243.7	244.2	244.7	245.2	245.5	245.5	245.5



TEST NUMBER: P331349-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	272.7	272.3	272.0	271.6	272.0	272.3	272.7	273.1	273.5	273.9	274.3
115°	317.3	316.8	316.3	315.8	316.3	316.8	317.3	317.8	318.2	318.4	318.5
117.5°	359.5	358.9	358.4	357.9	358.4	358.9	359.5	360.0	360.4	360.9	361.3
120°	389.1	388.6	388.1	387.6	388.1	388.6	389.1	389.7	389.9	389.9	389.9
122.5°	417.8	417.4	417.0	416.7	417.0	417.4	417.8	418.2	418.6	419.0	419.4
125°	461.5	461.3	461.2	461.0	461.2	461.3	461.5	461.7	462.0	462.5	463.1
127.5°	503.1	502.5	502.0	501.4	502.0	502.5	503.1	503.6	504.2	504.8	505.5
130°	532.5	531.9	531.2	530.5	531.2	531.9	532.5	533.2	533.8	534.1	534.5
132.5°	559.9	559.4	558.8	558.3	558.8	559.4	559.9	560.5	561.2	561.9	562.7
135°	603.1	602.6	602.0	601.5	602.0	602.6	603.1	603.6	603.9	604.1	604.3
137.5°	642.8	642.1	641.4	640.7	641.4	642.1	642.8	643.5	643.9	644.0	644.2
140°	669.9	669.2	668.5	667.8	668.5	669.2	669.9	670.6	671.0	671.0	671.0
142.5°	694.5	693.8	693.2	692.5	693.2	693.8	694.5	695.2	695.5	695.4	695.2
145°	731.4	730.7	730.0	729.3	730.0	730.7	731.4	732.2	732.5	732.3	732.1
147.5°	764.4	763.7	763.1	762.3	763.1	763.7	764.4	765.1	765.2	764.8	764.4
150°	785.4	784.9	784.4	783.9	784.4	784.9	785.4	786.0	786.0	785.4	784.9
152.5°	806.1	805.4	804.7	804.1	804.7	805.4	806.1	806.7	806.7	806.1	805.4
155°	832.7	832.2	831.7	831.2	831.7	832.2	832.7	833.3	833.1	832.2	831.3
157.5°	857.1	856.3	855.4	854.5	855.4	856.3	857.1	857.9	857.8	856.6	855.4
160°	871.2	870.5	869.8	869.1	869.8	870.5	871.2	871.9	871.7	870.7	869.6
162.5°	884.2	883.4	882.5	881.7	882.5	883.4	884.2	885.0	884.9	883.7	882.5
165°	900.9	900.0	899.2	898.3	899.2	900.0	900.9	901.8	901.6	900.4	899.2
167.5°	914.6	913.7	912.8	911.9	912.8	913.7	914.6	915.5	915.3	914.1	912.9
170°	922.0	920.9	919.9	918.8	919.9	920.9	922.0	923.0	922.9	921.7	920.5
172.5°	927.7	926.6	925.5	924.5	925.5	926.6	927.7	928.7	928.6	927.4	926.1
175°	933.8	932.7	931.7	930.7	931.7	932.7	933.8	934.8	934.7	933.5	932.3
177.5°	936.0	935.1	934.3	933.5	934.3	935.1	936.0	936.9	936.9	936.0	935.1
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331349-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1289.0	1293.5	1300.5	1308.0	1312.5	1321.2	1323.6	1327.8	1331.5	1340.2	1349.2
5°	1214.6	1221.7	1238.8	1248.1	1260.9	1275.9	1285.7	1296.1	1307.4	1327.0	1344.9
7.5°	1134.8	1146.8	1167.9	1185.3	1203.7	1225.1	1240.5	1260.9	1277.9	1305.5	1331.9
10°	1081.6	1098.5	1117.6	1138.2	1164.1	1186.7	1208.4	1234.2	1254.8	1287.8	1318.7
12.5°	1033.7	1036.3	1063.6	1086.3	1121.6	1149.6	1174.6	1207.8	1228.0	1267.2	1299.7
15°	950.1	965.5	990.3	1008.4	1050.2	1085.7	1120.7	1155.3	1178.5	1226.9	1269.7
17.5°	879.7	893.9	919.3	948.9	978.9	1014.2	1059.6	1096.0	1127.5	1183.0	1233.6
20°	835.2	852.6	878.5	908.9	935.1	973.8	1013.0	1054.7	1088.7	1151.1	1210.4
22.5°	797.2	811.0	831.8	861.8	890.6	925.9	968.9	1014.3	1050.1	1117.3	1177.4
25°	743.9	755.3	768.6	793.3	825.9	864.5	898.1	948.1	1000.1	1063.0	1135.7
27.5°	695.8	703.9	715.8	737.5	762.7	798.8	836.1	883.5	935.8	1004.1	1080.9
30°	666.6	671.8	683.6	701.7	726.4	754.7	792.3	837.7	891.3	960.4	1036.7
32.5°	641.0	645.7	653.5	670.7	692.2	716.4	750.3	795.7	846.8	914.6	999.2
35°	602.7	606.2	613.0	626.8	638.7	662.5	690.7	732.1	780.0	845.0	932.6
37.5°	564.4	569.4	573.5	579.4	594.6	610.2	634.8	669.6	716.7	782.2	865.8
40°	539.3	543.3	549.6	552.1	564.5	578.5	598.5	630.5	677.9	737.7	819.2
42.5°	513.6	517.8	521.5	524.5	535.2	547.4	565.5	593.0	635.0	693.2	773.8
45°	478.9	479.4	483.0	488.7	493.8	502.6	515.5	539.3	571.7	626.3	699.5
47.5°	443.6	444.2	444.8	447.4	453.0	461.0	469.5	488.8	517.9	561.5	632.8
50°	420.1	419.1	420.1	422.2	425.9	432.5	442.3	456.3	480.0	520.7	586.1
52.5°	397.5	397.3	396.7	397.5	400.2	404.9	411.8	423.6	444.8	482.3	540.0
55°	362.9	360.3	360.8	358.8	363.5	364.5	369.6	379.4	398.0	423.7	477.9
57.5°	326.1	324.0	321.6	321.0	320.6	323.5	327.6	335.3	349.5	372.1	416.1
60°	302.7	300.0	296.9	295.9	295.9	297.4	299.5	305.2	318.6	338.7	374.8
62.5°	278.7	275.7	273.9	271.1	270.3	271.9	274.0	278.0	287.6	306.5	337.7
65°	241.8	238.1	235.6	235.1	234.1	232.5	233.5	237.6	245.4	260.3	285.1
67.5°	204.8	201.4	200.8	197.7	196.3	196.5	196.3	199.9	204.5	217.3	235.8
70°	180.5	177.8	176.8	174.2	173.2	172.2	171.2	174.2	178.8	189.8	205.7
72.5°	155.7	153.5	151.3	149.1	149.3	148.2	148.0	149.9	153.7	163.7	176.0
75°	120.1	120.7	118.1	115.4	114.9	113.9	113.9	115.4	117.0	124.7	134.5
77.5°	87.2	86.7	84.5	83.7	83.2	82.1	83.2	84.2	85.0	90.2	97.5
80°	66.6	66.6	63.9	63.9	63.4	61.9	63.4	62.4	64.4	69.6	74.7
82.5°	47.6	46.7	46.6	45.7	45.6	44.5	45.2	46.3	47.2	50.6	53.7
85°	23.2	23.2	22.7	22.2	22.7	22.2	22.7	23.2	23.7	25.2	27.9
87.5°	10.4	10.9	10.5	10.2	9.4	9.0	8.9	8.9	9.3	9.2	9.2
90°	27.3	27.7	23.7	19.9	16.1	12.2	9.2	7.1	5.0	2.9	0.8
92.5°	25.1	25.1	24.2	23.2	22.3	21.4	20.2	18.7	17.2	15.6	14.0
95°	50.5	50.5	50.2	49.8	49.5	49.1	48.1	46.4	44.5	42.8	41.0
97.5°	84.9	84.9	84.2	83.6	82.9	82.3	81.2	79.6	78.1	76.5	75.0
100°	109.0	109.0	108.4	107.9	107.3	106.8	105.8	104.4	103.0	101.7	100.3
102.5°	134.9	134.8	134.1	133.5	132.8	132.2	131.3	130.2	129.1	127.8	126.7
105°	174.0	173.7	173.3	173.0	172.6	172.3	171.8	171.3	170.8	170.3	169.8
107.5°	216.6	216.4	216.4	216.4	216.4	216.4	216.0	215.3	214.5	213.8	213.0
110°	245.5	245.5	245.5	245.5	245.5	245.5	245.0	243.9	242.9	241.8	240.8



TEST NUMBER: P331349-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	274.8	275.2	275.3	275.5	275.6	275.7	275.3	274.2	273.2	272.2	271.0
115°	318.7	318.9	319.2	319.6	319.9	320.3	319.9	318.9	317.8	316.8	315.8
117.5°	361.7	362.1	363.1	364.2	365.1	366.1	365.9	364.5	363.0	361.6	360.2
120°	389.9	389.9	391.3	392.7	394.2	395.6	395.6	394.2	392.7	391.3	389.9
122.5°	419.8	420.2	421.2	422.2	423.2	424.1	423.8	422.1	420.5	418.8	417.1
125°	463.6	464.1	464.6	465.1	465.7	466.3	465.7	464.1	462.5	461.0	459.4
127.5°	506.1	506.8	507.4	508.1	508.7	509.3	508.6	506.6	504.6	502.6	500.6
130°	534.8	535.2	535.5	535.8	536.2	536.5	535.6	533.3	531.1	528.8	526.5
132.5°	563.5	564.2	564.1	564.1	564.0	563.9	563.0	561.1	559.3	557.4	555.5
135°	604.5	604.6	604.3	603.9	603.6	603.2	602.1	600.2	598.2	596.3	594.4
137.5°	644.3	644.4	644.0	643.5	643.1	642.6	641.6	640.1	638.4	636.8	635.3
140°	671.0	671.0	670.0	669.2	668.3	667.4	666.2	664.6	663.1	661.5	659.9
142.5°	695.1	695.0	694.4	693.8	693.2	692.6	691.5	689.9	688.3	686.7	685.2
145°	732.0	731.7	730.6	729.6	728.6	727.5	726.4	725.2	724.0	722.7	721.4
147.5°	764.0	763.7	763.0	762.2	761.5	760.8	759.7	758.2	756.8	755.3	753.9
150°	784.4	783.9	783.2	782.4	781.7	781.0	780.1	779.1	778.0	777.0	776.0
152.5°	804.7	804.1	803.1	802.3	801.5	800.6	799.7	798.7	797.6	796.6	795.5
155°	830.5	829.6	829.1	828.6	828.0	827.5	827.0	826.5	826.0	825.4	824.9
157.5°	854.1	852.9	852.6	852.3	852.0	851.7	851.4	851.0	850.7	850.3	850.0
160°	868.6	867.5	867.4	867.2	867.0	866.8	866.6	866.2	865.9	865.5	865.2
162.5°	881.3	880.1	880.0	879.8	879.6	879.4	879.3	879.2	879.2	879.1	879.0
165°	898.0	896.7	896.7	896.7	896.7	896.7	896.8	897.0	897.2	897.4	897.5
167.5°	911.7	910.4	910.5	910.5	910.6	910.6	910.9	911.4	911.9	912.4	912.9
170°	919.3	918.0	918.2	918.4	918.6	918.7	919.1	919.6	920.1	920.7	921.2
172.5°	924.9	923.7	923.9	924.0	924.2	924.4	924.7	925.2	925.8	926.3	926.9
175°	931.1	929.9	930.2	930.6	930.9	931.3	931.7	932.2	932.7	933.3	933.8
177.5°	934.3	933.5	933.7	934.0	934.3	934.6	934.9	935.3	935.8	936.2	936.6
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331349-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1348.4	1350.5	1357.1	1363.6	1371.1	1373.1	1376.4	1373.5	1372.7	1380.6	1386.3
5°	1352.2	1361.5	1379.6	1396.0	1410.0	1419.8	1430.1	1434.2	1441.9	1452.7	1466.1
7.5°	1347.9	1365.9	1394.3	1418.3	1444.5	1463.4	1478.1	1490.7	1505.9	1526.4	1548.8
10°	1342.9	1367.2	1401.7	1431.1	1463.0	1487.2	1507.4	1526.9	1549.6	1578.0	1607.4
12.5°	1333.8	1362.6	1405.8	1440.6	1481.6	1505.4	1532.6	1574.8	1599.1	1638.6	1680.0
15°	1315.7	1347.6	1407.9	1450.7	1497.0	1542.5	1592.5	1632.6	1672.8	1696.1	1754.3
17.5°	1288.5	1335.4	1402.2	1452.1	1511.1	1582.6	1638.7	1684.3	1730.7	1768.4	1797.6
20°	1266.7	1317.7	1393.9	1453.8	1523.9	1600.6	1665.2	1711.5	1751.7	1783.2	1801.2
22.5°	1239.0	1303.2	1377.5	1447.5	1537.1	1613.1	1680.8	1717.3	1750.9	1766.3	1773.2
25°	1195.5	1272.8	1356.9	1442.4	1543.5	1623.9	1685.8	1707.9	1717.7	1702.7	1678.0
27.5°	1148.6	1234.8	1333.0	1432.7	1539.5	1616.9	1661.2	1657.7	1641.1	1592.8	1554.1
30°	1113.5	1208.4	1314.0	1422.8	1530.0	1605.3	1631.1	1605.3	1567.7	1513.6	1458.4
32.5°	1076.8	1175.0	1293.8	1408.8	1512.8	1578.9	1584.5	1540.1	1481.9	1420.4	1351.6
35°	1021.3	1127.4	1255.8	1377.5	1475.9	1517.7	1493.0	1414.6	1345.5	1261.5	1167.6
37.5°	958.5	1075.7	1204.5	1331.6	1420.8	1431.7	1370.3	1287.8	1190.3	1091.6	981.2
40°	911.4	1035.7	1168.2	1296.6	1375.4	1364.0	1285.7	1195.0	1078.9	958.4	855.8
42.5°	869.4	993.6	1128.5	1254.5	1317.7	1286.6	1195.0	1083.6	959.0	845.4	751.4
45°	796.5	924.3	1062.5	1184.2	1220.2	1164.1	1042.9	919.2	796.5	701.7	627.4
47.5°	725.8	852.1	989.0	1095.9	1108.6	1033.1	900.7	773.4	667.9	590.7	538.3
50°	673.8	800.6	936.1	1031.6	1027.4	936.1	800.1	678.9	590.8	528.4	493.3
52.5°	627.2	747.0	877.2	963.9	942.1	842.5	712.7	605.1	532.6	483.8	452.1
55°	554.7	665.5	789.2	858.9	818.6	708.3	598.5	511.9	458.3	421.7	397.0
57.5°	482.7	586.6	692.6	735.5	691.1	589.2	497.6	434.7	394.5	367.4	351.2
60°	438.2	529.0	623.3	660.4	607.2	516.5	444.3	388.2	355.7	333.6	319.1
62.5°	393.6	474.9	563.9	584.1	535.5	458.8	394.9	348.2	321.4	301.7	288.2
65°	333.1	399.5	467.1	480.5	435.7	376.4	325.8	295.4	271.7	257.2	246.4
67.5°	273.2	326.5	374.4	385.2	345.9	304.8	268.3	241.8	225.7	213.7	204.6
70°	237.6	279.9	319.1	327.9	296.4	259.8	232.0	210.9	196.4	186.1	177.3
72.5°	200.2	235.4	267.9	273.9	248.1	220.3	197.3	180.8	167.9	161.4	153.0
75°	153.1	173.7	198.9	200.6	183.5	166.5	149.0	138.1	131.5	123.2	119.1
77.5°	108.1	124.2	138.7	141.5	131.4	119.8	110.0	101.5	95.7	92.0	88.2
80°	82.5	95.3	101.6	105.1	98.0	89.7	84.0	78.4	74.7	72.2	69.6
82.5°	59.0	67.0	72.7	75.4	71.6	66.7	60.9	57.8	54.9	52.8	51.9
85°	29.9	33.5	37.2	38.2	37.2	35.0	31.9	31.9	30.4	29.9	29.9
87.5°	10.9	12.9	13.4	15.0	14.8	15.6	16.4	16.8	17.1	16.6	16.2
90°	2.9	5.0	7.1	9.2	12.2	16.1	19.9	23.7	27.7	27.3	27.0
92.5°	15.6	17.2	18.7	20.2	21.4	22.3	23.2	24.2	25.1	25.1	25.2
95°	42.8	44.5	46.4	48.1	49.1	49.5	49.8	50.2	50.5	50.5	50.5
97.5°	76.5	78.1	79.6	81.2	82.3	82.9	83.6	84.2	84.9	84.9	84.9
100°	101.7	103.0	104.4	105.8	106.8	107.3	107.9	108.4	109.0	109.0	109.0
102.5°	127.8	129.1	130.2	131.3	132.2	132.8	133.5	134.1	134.8	134.9	135.1
105°	170.3	170.8	171.3	171.8	172.3	172.6	173.0	173.3	173.7	174.0	174.4
107.5°	213.8	214.5	215.3	216.0	216.4	216.4	216.4	216.4	216.4	216.6	216.7
110°	241.8	242.9	243.9	245.0	245.5	245.5	245.5	245.5	245.5	245.5	245.5



TEST NUMBER: P331349-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	272.2	273.2	274.2	275.3	275.7	275.6	275.5	275.3	275.2	274.8	274.3
115°	316.8	317.8	318.9	319.9	320.3	319.9	319.6	319.2	318.9	318.7	318.5
117.5°	361.6	363.0	364.5	365.9	366.1	365.1	364.2	363.1	362.1	361.7	361.3
120°	391.3	392.7	394.2	395.6	395.6	394.2	392.7	391.3	389.9	389.9	389.9
122.5°	418.8	420.5	422.1	423.8	424.1	423.2	422.2	421.2	420.2	419.8	419.4
125°	461.0	462.5	464.1	465.7	466.3	465.7	465.1	464.6	464.1	463.6	463.1
127.5°	502.6	504.6	506.6	508.6	509.3	508.7	508.1	507.4	506.8	506.1	505.5
130°	528.8	531.1	533.3	535.6	536.5	536.2	535.8	535.5	535.2	534.8	534.5
132.5°	557.4	559.3	561.1	563.0	563.9	564.0	564.1	564.1	564.2	563.5	562.7
135°	596.3	598.2	600.2	602.1	603.2	603.6	603.9	604.3	604.6	604.5	604.3
137.5°	636.8	638.4	640.1	641.6	642.6	643.1	643.5	644.0	644.4	644.3	644.2
140°	661.5	663.1	664.6	666.2	667.4	668.3	669.2	670.0	671.0	671.0	671.0
142.5°	686.7	688.3	689.9	691.5	692.6	693.2	693.8	694.4	695.0	695.1	695.2
145°	722.7	724.0	725.2	726.4	727.5	728.6	729.6	730.6	731.7	732.0	732.1
147.5°	755.3	756.8	758.2	759.7	760.8	761.5	762.2	763.0	763.7	764.0	764.4
150°	777.0	778.0	779.1	780.1	781.0	781.7	782.4	783.2	783.9	784.4	784.9
152.5°	796.6	797.6	798.7	799.7	800.6	801.5	802.3	803.1	804.1	804.7	805.4
155°	825.4	826.0	826.5	827.0	827.5	828.0	828.6	829.1	829.6	830.5	831.3
157.5°	850.3	850.7	851.0	851.4	851.7	852.0	852.3	852.6	852.9	854.1	855.4
160°	865.5	865.9	866.2	866.6	866.8	867.0	867.2	867.4	867.5	868.6	869.6
162.5°	879.1	879.2	879.2	879.3	879.4	879.6	879.8	880.0	880.1	881.3	882.5
165°	897.4	897.2	897.0	896.8	896.7	896.7	896.7	896.7	896.7	898.0	899.2
167.5°	912.4	911.9	911.4	910.9	910.6	910.6	910.5	910.5	910.4	911.7	912.9
170°	920.7	920.1	919.6	919.1	918.7	918.6	918.4	918.2	918.0	919.3	920.5
172.5°	926.3	925.8	925.2	924.7	924.4	924.2	924.0	923.9	923.7	924.9	926.1
175°	933.3	932.7	932.2	931.7	931.3	930.9	930.6	930.2	929.9	931.1	932.3
177.5°	936.2	935.8	935.3	934.9	934.6	934.3	934.0	933.7	933.5	934.3	935.1
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331349-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1391.3	1397.0	1397.0	1397.9	1404.5	1403.6	1403.2
5°	1480.6	1489.3	1490.4	1499.6	1505.8	1503.8	1498.1
7.5°	1564.8	1581.1	1593.5	1600.3	1608.5	1613.6	1611.3
10°	1631.6	1655.4	1669.8	1679.6	1691.4	1700.2	1697.1
12.5°	1692.2	1720.5	1740.3	1757.1	1758.7	1769.9	1762.2
15°	1786.8	1816.6	1819.8	1832.2	1842.0	1840.9	1841.4
17.5°	1818.1	1827.7	1829.6	1829.9	1830.0	1826.3	1818.6
20°	1806.9	1803.3	1794.5	1787.9	1775.9	1774.4	1764.1
22.5°	1754.1	1742.6	1720.7	1706.2	1687.7	1682.8	1680.0
25°	1650.2	1624.9	1589.8	1556.3	1547.1	1529.0	1534.2
27.5°	1507.6	1468.2	1430.3	1403.0	1378.4	1351.4	1359.1
30°	1407.3	1363.0	1309.4	1268.2	1241.9	1216.1	1211.4
32.5°	1287.8	1222.8	1163.0	1126.7	1086.4	1070.2	1052.3
35°	1081.6	1018.1	958.9	907.9	878.5	855.8	835.2
37.5°	896.1	823.0	775.3	733.9	712.7	699.6	703.0
40°	781.0	717.1	682.1	650.6	631.0	621.7	623.8
42.5°	687.8	640.0	611.1	589.6	575.7	570.6	569.4
45°	582.0	555.2	531.5	519.2	512.4	506.8	503.1
47.5°	509.9	488.0	474.6	467.3	461.4	455.7	455.6
50°	466.6	452.1	442.8	435.0	430.5	426.4	429.9
52.5°	433.5	420.3	411.1	404.1	402.4	398.7	398.6
55°	384.6	374.3	367.6	361.3	358.3	356.2	353.7
57.5°	340.0	330.2	324.1	320.1	314.3	312.1	311.3
60°	308.3	300.5	294.4	289.2	286.6	282.5	282.5
62.5°	279.0	271.2	265.5	261.6	257.3	255.7	256.1
65°	236.6	230.5	224.8	220.7	219.6	216.5	217.5
67.5°	197.6	193.5	187.5	185.3	183.3	181.7	180.5
70°	171.7	167.5	164.4	161.4	159.8	159.8	159.8
72.5°	149.8	144.8	143.0	139.1	140.0	138.4	136.7
75°	116.0	112.9	111.4	109.8	107.2	107.2	107.2
77.5°	85.3	84.4	82.6	80.9	80.3	79.8	80.0
80°	65.9	65.4	64.4	64.4	63.4	62.9	61.9
82.5°	50.7	49.4	48.8	48.4	48.2	48.1	47.9
85°	28.9	27.9	27.9	28.4	27.4	27.4	27.9
87.5°	16.5	16.4	16.0	16.0	16.5	16.1	16.1
90°	26.6	26.3	26.2	26.4	26.5	26.7	26.9
92.5°	25.3	25.3	25.4	25.4	25.5	25.5	25.5
95°	50.5	50.5	50.4	50.0	49.7	49.3	49.0
97.5°	84.9	84.9	84.9	84.9	84.8	84.8	84.7
100°	109.0	109.0	108.9	108.7	108.5	108.4	108.2
102.5°	135.2	135.4	135.3	135.2	135.0	134.8	134.6
105°	174.7	175.1	175.2	175.2	175.2	175.2	175.2
107.5°	216.8	217.0	216.7	215.9	215.1	214.3	213.5
110°	245.5	245.5	245.2	244.7	244.2	243.7	243.1



TEST NUMBER: P331349-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	273.9	273.5	273.1	272.7	272.3	272.0	271.6
115°	318.4	318.2	317.8	317.3	316.8	316.3	315.8
117.5°	360.9	360.4	360.0	359.5	358.9	358.4	357.9
120°	389.9	389.9	389.7	389.1	388.6	388.1	387.6
122.5°	419.0	418.6	418.2	417.8	417.4	417.0	416.7
125°	462.5	462.0	461.7	461.5	461.3	461.2	461.0
127.5°	504.8	504.2	503.6	503.1	502.5	502.0	501.4
130°	534.1	533.8	533.2	532.5	531.9	531.2	530.5
132.5°	561.9	561.2	560.5	559.9	559.4	558.8	558.3
135°	604.1	603.9	603.6	603.1	602.6	602.0	601.5
137.5°	644.0	643.9	643.5	642.8	642.1	641.4	640.7
140°	671.0	671.0	670.6	669.9	669.2	668.5	667.8
142.5°	695.4	695.5	695.2	694.5	693.8	693.2	692.5
145°	732.3	732.5	732.2	731.4	730.7	730.0	729.3
147.5°	764.8	765.2	765.1	764.4	763.7	763.1	762.3
150°	785.4	786.0	786.0	785.4	784.9	784.4	783.9
152.5°	806.1	806.7	806.7	806.1	805.4	804.7	804.1
155°	832.2	833.1	833.3	832.7	832.2	831.7	831.2
157.5°	856.6	857.8	857.9	857.1	856.3	855.4	854.5
160°	870.7	871.7	871.9	871.2	870.5	869.8	869.1
162.5°	883.7	884.9	885.0	884.2	883.4	882.5	881.7
165°	900.4	901.6	901.8	900.9	900.0	899.2	898.3
167.5°	914.1	915.3	915.5	914.6	913.7	912.8	911.9
170°	921.7	922.9	923.0	922.0	920.9	919.9	918.8
172.5°	927.4	928.6	928.7	927.7	926.6	925.5	924.5
175°	933.5	934.7	934.8	933.8	932.7	931.7	930.7
177.5°	936.0	936.9	936.9	936.0	935.1	934.3	933.5
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3

(END OF REPORT)