

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331356-840

Luminaire Tested: **SA2XXDIP-C675D725U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331356-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D725U840-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5587.9 lumens
Efficiency: N/A
Efficacy: 121.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331356-840
CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331356-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	93	89	86	90	86	83	80	72	70	68	60	58	57	49	48	46	41
2	89	81	75	70	82	75	70	65	64	60	56	53	50	47	43	41	39	34
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33	29
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29	25
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25	22
6	63	51	42	37	58	47	40	35	40	34	30	34	29	26	28	25	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17312	17312	17312
5°	17378	17126	17227
10°	17274	16952	17038
15°	17060	16732	16715
20°	16756	16402	16385
25°	16456	15998	15998
30°	16067	15627	15491
35°	15707	15179	14954
40°	15253	14731	14450
45°	14805	14289	13935
50°	14320	13828	13335
55°	13813	13292	12797
60°	13249	12649	12184
65°	12642	12015	11461
70°	11877	11240	10707
75°	10805	10356	10100
80°	9586	9298	8815
85°	7836	7447	6688



TEST NUMBER: P331356-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.8	1.8
10°-20°	283.7	5.1
20°-30°	417.0	7.5
30°-40°	484.3	8.7
40°-50°	483.8	8.7
50°-60°	421.9	7.6
60°-70°	312.0	5.6
70°-80°	176.7	3.2
80°-90°	51.2	0.9
90°-100°	164.1	2.9
100°-110°	557.0	10.0
110°-120°	591.7	10.6
120°-130°	487.1	8.7
130°-140°	391.2	7.0
140°-150°	295.6	5.3
150°-160°	207.7	3.7
160°-170°	122.3	2.2
170°-180°	39.8	0.7
0°-30°	801.5	14.3
0°-40°	1285.8	23.0
0°-60°	2191.5	39.2
0°-90°	2731.4	48.9
90°-120°	1312.8	23.5
90°-150°	2486.7	44.5
90°-180°	2856.0	51.1
0°-180°	5587.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1072	1072	1072	1072	1072	
5°	1072	1068	1057	1064	1063	102
15°	1021	1014	1001	1005	1000	287
25°	924	915	898	900	898	425
35°	797	786	770	764	759	497
45°	648	641	626	615	610	500
55°	491	484	472	460	455	439
65°	331	324	314	305	300	327
75°	173	171	166	160	162	185
85°	42	41	40	37	36	48
90°	1	11	27	26	26	4
95°	28	68	309	117	90	29
105°	96	145	585	1046	890	102
115°	170	214	490	1010	1171	168
125°	237	280	470	818	950	210
135°	278	332	465	688	787	215
145°	317	365	463	574	628	199
155°	361	390	449	508	528	166
165°	393	405	430	456	463	111
175°	410	410	414	419	418	39
180°	410	410	410	410	410	



TEST NUMBER: P331356-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2
2.5°	1077.1	1076.2	1075.3	1074.4	1073.5	1072.0	1070.0	1067.9	1065.9	1063.9	1065.7
5°	1072.2	1071.3	1070.4	1069.4	1068.5	1066.8	1064.3	1061.8	1059.2	1056.7	1058.5
7.5°	1062.7	1061.3	1059.9	1058.4	1057.0	1055.0	1052.5	1049.9	1047.3	1044.7	1046.5
10°	1053.6	1052.0	1050.4	1048.7	1047.2	1045.0	1042.3	1039.6	1036.7	1034.0	1035.8
12.5°	1041.3	1039.9	1038.3	1036.9	1035.5	1033.5	1030.7	1027.9	1025.2	1022.5	1023.8
15°	1020.6	1019.3	1017.8	1016.5	1015.1	1012.9	1010.0	1006.9	1004.0	1001.0	1002.0
17.5°	994.2	992.8	991.5	990.1	988.8	986.5	983.5	980.5	977.4	974.4	975.5
20°	975.2	973.9	972.5	971.1	969.8	967.5	964.2	961.1	957.9	954.6	955.3
22.5°	956.2	954.3	952.4	950.5	948.6	946.1	943.1	940.1	937.1	934.0	934.1
25°	923.7	921.9	920.1	918.2	916.4	913.5	909.6	905.7	901.8	898.0	898.4
27.5°	886.6	884.9	883.3	881.6	880.0	877.7	874.5	871.5	868.4	865.4	864.6
30°	861.8	860.0	858.2	856.4	854.5	851.9	848.5	845.1	841.6	838.2	837.5
32.5°	835.5	833.9	832.5	831.0	829.6	827.1	823.4	819.8	816.2	812.5	811.3
35°	796.9	794.7	792.3	790.0	787.7	784.8	781.1	777.4	773.8	770.1	768.7
37.5°	753.4	751.3	749.3	747.3	745.4	742.5	738.8	735.2	731.5	727.8	726.1
40°	723.7	721.9	720.0	718.2	716.4	713.7	709.9	706.3	702.7	698.9	696.9
42.5°	694.9	693.0	691.2	689.3	687.5	684.8	681.1	677.4	673.8	670.1	667.8
45°	648.4	646.8	645.2	643.7	642.1	639.5	636.1	632.7	629.2	625.8	623.3
47.5°	602.3	600.8	599.3	597.7	596.2	593.7	590.1	586.5	583.0	579.4	576.7
50°	570.1	569.0	567.8	566.6	565.5	563.3	560.2	556.9	553.7	550.5	547.3
52.5°	538.8	537.2	535.7	534.2	532.7	530.5	527.5	524.4	521.4	518.4	515.7
55°	490.7	489.4	488.0	486.6	485.2	483.1	480.4	477.7	474.9	472.2	469.4
57.5°	442.4	441.4	440.3	439.2	438.1	436.1	433.0	430.0	427.0	423.9	421.2
60°	410.3	409.4	408.5	407.6	406.7	404.6	401.4	398.2	395.0	391.7	389.2
62.5°	379.0	377.5	376.1	374.6	373.1	371.1	368.7	366.2	363.8	361.2	358.9
65°	330.9	329.5	328.2	326.8	325.4	323.6	321.3	319.0	316.7	314.5	312.4
67.5°	282.1	280.9	279.8	278.7	277.6	276.1	274.0	272.0	269.9	267.8	266.2
70°	251.6	250.6	249.7	248.8	247.9	246.4	244.3	242.3	240.2	238.1	236.5
72.5°	220.3	219.2	218.3	217.4	216.5	215.4	214.1	212.8	211.5	210.1	208.5
75°	173.2	172.7	172.3	171.8	171.4	170.6	169.5	168.2	167.1	166.0	164.6
77.5°	131.2	130.4	129.6	128.8	128.1	127.4	126.9	126.4	126.0	125.5	124.9
80°	103.1	102.9	102.6	102.4	102.2	101.8	101.4	100.9	100.5	100.0	99.3
82.5°	76.7	76.6	76.6	76.5	76.5	76.3	76.0	75.8	75.5	75.2	74.4
85°	42.3	42.0	41.8	41.6	41.3	41.1	40.9	40.7	40.4	40.2	39.5
87.5°	15.0	15.1	15.3	15.3	15.2	15.3	15.8	16.6	17.2	16.9	16.2
90°	0.8	3.1	6.4	7.9	9.5	11.8	15.8	21.3	26.1	26.9	26.1
92.5°	9.6	13.9	19.6	23.0	28.4	35.9	53.7	78.8	101.2	102.6	86.6
95°	27.7	30.8	38.7	45.7	58.4	77.4	113.7	182.4	274.0	309.4	270.7
97.5°	45.0	49.3	57.7	68.4	82.9	104.3	150.0	245.7	397.9	528.3	554.2
100°	60.8	63.1	70.3	82.9	98.7	120.8	162.6	258.9	429.4	623.6	737.3
102.5°	75.3	77.1	84.1	96.7	113.2	135.3	174.0	259.5	417.5	626.8	805.5
105°	96.3	99.5	105.0	116.8	134.2	156.3	193.4	263.7	393.9	584.9	795.0
107.5°	119.1	121.6	126.9	137.8	155.0	177.3	213.3	274.6	382.2	540.1	725.6
110°	134.2	137.3	142.1	152.4	169.0	191.9	226.5	283.4	379.7	518.7	682.1



TEST NUMBER: P331356-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	148.0	151.3	156.6	166.2	182.2	205.7	239.2	292.9	380.3	504.7	651.8
115°	169.8	173.7	178.4	187.8	203.7	225.0	258.9	307.1	383.6	489.5	614.2
117.5°	192.2	195.3	200.1	208.4	223.6	245.7	277.1	322.2	389.3	482.0	590.5
120°	206.0	209.2	213.9	221.1	236.8	258.9	289.7	332.3	393.1	477.6	577.8
122.5°	219.3	221.9	226.5	234.3	250.0	272.9	301.7	341.2	397.6	475.0	567.1
125°	236.8	239.2	243.9	253.4	269.2	291.2	319.7	355.3	404.1	470.5	551.8
127.5°	250.7	253.9	260.5	270.9	286.1	308.8	336.5	368.3	411.0	467.8	537.6
130°	258.9	262.1	269.9	281.0	296.8	318.9	346.6	376.6	416.1	466.6	528.2
132.5°	266.5	270.3	278.8	290.5	306.9	329.0	355.4	384.8	421.1	466.0	520.6
135°	277.9	281.0	290.5	302.4	320.5	342.6	367.9	395.5	427.1	464.9	510.0
137.5°	288.6	292.4	301.8	314.5	332.5	353.0	378.0	403.7	432.4	464.8	502.5
140°	296.8	299.9	309.4	322.0	339.4	360.0	383.6	408.1	434.9	464.1	498.2
142.5°	305.0	307.6	316.4	329.0	345.8	365.1	388.1	411.9	436.9	464.1	493.7
145°	317.3	320.5	328.4	340.2	356.0	373.3	394.8	416.8	438.9	462.6	487.9
147.5°	330.6	333.0	340.5	351.4	364.6	380.0	400.1	419.5	439.6	459.8	481.9
150°	339.4	341.8	348.1	358.4	370.2	384.5	402.6	420.7	438.9	457.9	476.8
152.5°	348.3	349.4	355.7	364.7	375.9	388.9	405.2	421.4	437.7	454.7	472.4
155°	360.7	361.5	366.3	375.0	383.6	395.5	408.9	422.3	435.8	449.2	464.1
157.5°	371.2	371.9	375.8	383.3	390.3	400.2	411.6	422.3	432.1	443.5	456.5
160°	378.1	378.9	382.0	388.4	394.8	403.3	412.8	422.3	430.2	439.7	450.8
162.5°	385.1	384.6	387.8	392.8	398.5	405.3	413.5	421.7	428.4	436.6	445.7
165°	393.1	392.3	393.9	398.7	402.6	407.4	414.4	420.0	424.7	430.2	437.4
167.5°	399.8	398.8	400.2	403.2	406.1	409.1	414.2	418.9	421.1	424.7	429.1
170°	404.1	402.6	403.3	405.8	407.4	409.7	413.6	417.6	419.2	421.5	424.7
172.5°	406.7	405.8	405.3	407.7	408.6	410.3	413.0	415.7	416.7	417.8	420.3
175°	409.7	408.9	408.1	409.7	409.7	410.5	412.0	413.6	412.8	413.6	414.4
177.5°	411.1	409.9	409.2	410.5	410.5	410.5	411.1	412.4	411.1	410.5	411.1
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331356-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2
2.5°	1067.5	1069.4	1071.3	1072.0	1071.6	1071.3	1070.9	1070.6
5°	1060.4	1062.2	1064.0	1064.7	1064.3	1063.8	1063.4	1062.9
7.5°	1048.4	1050.3	1052.1	1052.7	1052.2	1051.8	1051.3	1050.8
10°	1037.6	1039.6	1041.4	1041.9	1041.3	1040.6	1039.9	1039.2
12.5°	1025.0	1026.3	1027.6	1027.9	1027.4	1027.0	1026.5	1026.0
15°	1002.9	1003.8	1004.7	1004.6	1003.4	1002.3	1001.2	1000.0
17.5°	976.5	977.5	978.7	978.7	977.5	976.4	975.3	974.2
20°	956.0	956.7	957.4	957.3	956.3	955.4	954.5	953.6
22.5°	934.3	934.4	934.5	934.3	933.8	933.2	932.7	932.2
25°	898.9	899.3	899.8	899.8	899.3	898.9	898.4	898.0
27.5°	863.9	863.3	862.6	861.7	860.6	859.5	858.4	857.3
30°	836.8	836.1	835.4	834.6	833.6	832.7	831.8	830.9
32.5°	810.1	808.9	807.6	806.6	805.7	804.8	803.8	802.8
35°	767.4	766.0	764.6	763.4	762.2	761.0	759.9	758.7
37.5°	724.5	722.8	721.0	719.6	718.5	717.4	716.4	715.3
40°	694.9	692.8	690.7	689.2	688.3	687.4	686.5	685.6
42.5°	665.6	663.4	661.2	659.3	658.0	656.8	655.5	654.2
45°	620.8	618.2	615.7	614.0	613.1	612.2	611.3	610.3
47.5°	574.1	571.4	568.8	566.7	565.4	564.1	562.8	561.5
50°	544.1	540.9	537.7	535.5	534.3	533.2	532.1	530.9
52.5°	513.0	510.4	507.8	505.6	504.1	502.6	501.1	499.6
55°	466.7	463.9	461.2	459.2	458.1	457.0	455.8	454.6
57.5°	418.5	415.8	413.1	411.3	410.4	409.6	408.7	407.8
60°	386.7	384.2	381.6	380.1	379.4	378.7	378.0	377.3
62.5°	356.6	354.3	351.9	350.3	349.4	348.5	347.7	346.8
65°	310.3	308.2	306.2	304.6	303.5	302.3	301.1	300.0
67.5°	264.6	263.1	261.5	260.1	259.2	258.3	257.4	256.5
70°	234.9	233.4	231.8	230.5	229.5	228.6	227.7	226.8
72.5°	206.9	205.3	203.7	202.5	201.8	201.1	200.4	199.5
75°	163.2	161.9	160.5	160.1	160.5	161.0	161.4	161.9
77.5°	124.2	123.5	122.8	122.2	121.5	120.9	120.3	119.6
80°	98.7	98.0	97.3	96.6	96.2	95.7	95.3	94.8
82.5°	73.5	72.6	71.8	71.3	71.2	71.1	71.0	70.9
85°	38.9	38.2	37.5	37.0	36.8	36.6	36.4	36.1
87.5°	15.5	14.6	14.4	14.2	14.0	13.8	13.6	13.4
90°	25.2	23.7	25.2	26.1	26.1	26.1	26.1	26.1
92.5°	68.9	59.1	52.4	47.6	46.9	44.3	45.0	43.7
95°	206.8	158.6	125.5	108.2	97.9	91.6	89.2	90.0
97.5°	482.6	394.9	309.4	252.5	214.7	195.3	183.8	177.1
100°	720.7	622.9	514.7	419.2	353.7	319.7	296.8	282.6
102.5°	876.8	854.6	775.5	674.3	603.1	545.1	516.5	497.4
105°	959.2	1048.3	1058.6	1032.6	983.6	934.6	900.7	889.7
107.5°	899.8	1034.1	1116.2	1154.5	1160.6	1157.9	1151.1	1136.4
110°	848.6	990.0	1091.0	1155.7	1189.6	1204.7	1211.7	1210.9



TEST NUMBER: P331356-840

CATALOG NUMBER: SA2XXDIP-C675D725U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	801.9	937.5	1045.5	1119.7	1166.9	1192.0	1205.5	1209.7
115°	744.4	866.0	969.4	1050.7	1106.7	1143.1	1163.6	1170.7
117.5°	701.1	807.9	901.7	978.0	1035.1	1073.5	1095.1	1101.1
120°	679.6	777.6	861.2	933.1	988.4	1025.4	1048.3	1056.2
122.5°	662.7	752.3	831.5	896.5	946.0	982.5	1002.9	1009.5
125°	637.8	719.1	788.6	847.8	893.6	923.6	943.3	949.7
127.5°	613.4	686.9	752.5	807.1	847.1	875.1	892.2	897.3
130°	597.5	665.5	727.8	779.9	818.6	845.5	861.2	867.6
132.5°	582.4	645.3	702.6	751.5	789.6	816.4	830.9	836.6
135°	561.3	613.4	665.5	709.6	743.7	769.7	783.9	787.1
137.5°	544.4	587.9	629.3	667.8	698.8	721.2	733.7	738.4
140°	533.6	571.6	607.8	642.6	667.8	688.3	700.2	705.0
142.5°	524.8	557.0	588.2	617.3	641.4	659.9	670.6	671.5
145°	512.3	538.4	562.9	585.7	604.7	618.1	626.0	628.3
147.5°	502.7	523.2	542.3	559.1	574.7	585.4	590.8	592.2
150°	495.7	513.1	529.7	543.9	555.7	565.2	570.0	570.8
152.5°	488.8	504.9	519.0	531.3	540.6	548.8	552.3	552.4
155°	479.2	491.8	503.6	512.3	521.0	526.5	529.7	528.2
157.5°	468.0	478.6	488.5	495.2	501.4	506.0	507.5	507.5
160°	461.0	469.7	478.4	483.9	489.5	493.4	494.1	494.1
162.5°	454.0	461.5	468.9	473.2	478.7	481.4	482.2	481.5
165°	443.6	449.2	454.7	457.9	461.0	464.1	464.1	463.4
167.5°	433.7	438.0	441.7	444.6	446.1	447.8	447.6	446.7
170°	428.7	431.0	434.1	435.8	436.6	438.9	438.1	436.6
172.5°	422.9	424.7	427.3	428.2	429.0	430.1	429.3	428.4
175°	416.8	417.6	418.4	419.2	419.2	420.0	419.2	417.6
177.5°	412.4	412.4	413.0	413.0	413.0	413.0	412.4	411.1
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5

(END OF REPORT)