

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331358-840

Luminaire Tested: **SA2XXDIP-C675D925U840-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331358-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D925U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6303.4 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331358-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331358-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26
5	69	58	50	44	63	53	47	41	46	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	28	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21658	21658	21658	21658
5°	24280	21797	19316	21797
10°	27824	21620	16718	21620
15°	30780	21224	14770	21224
20°	30311	20797	13464	20797
25°	27332	20232	12636	20232
30°	22585	19328	12033	19328
35°	16462	18382	11606	18382
40°	13148	17266	11367	17266
45°	11488	15972	11040	15972
50°	10798	14722	10826	14722
55°	9956	13453	10536	13453
60°	9122	12103	10091	12103
65°	8309	10892	9650	10892
70°	7544	9711	9007	9711
75°	6687	8390	7973	8390
80°	5755	6946	6425	6946
85°	5169	5169	3816	5169



TEST NUMBER: P331358-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.7	2.0
10°-20°	371.4	5.9
20°-30°	539.0	8.6
30°-40°	568.8	9.0
40°-50°	503.6	8.0
50°-60°	401.9	6.4
60°-70°	273.2	4.3
70°-80°	140.0	2.2
80°-90°	38.5	0.6
90°-100°	75.7	1.2
100°-110°	235.0	3.7
110°-120°	401.8	6.4
120°-130°	528.3	8.4
130°-140°	593.0	9.4
140°-150°	581.4	9.2
150°-160°	487.7	7.7
160°-170°	323.5	5.1
170°-180°	113.0	1.8
0°-30°	1038.1	16.5
0°-40°	1606.9	25.5
0°-60°	2512.4	39.9
0°-90°	2964.1	47.0
90°-120°	712.5	11.3
90°-150°	2415.2	38.3
90°-180°	3339.0	53.0
0°-180°	6303.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1341	1341	1341	1341	1341	
5°	1498	1345	1192	1345	1498	150
15°	1841	1270	884	1270	1841	508
25°	1534	1136	709	1136	1534	693
35°	835	933	589	933	835	543
45°	503	700	484	700	503	396
55°	354	478	374	478	354	317
65°	218	285	253	285	218	216
75°	107	134	128	134	107	115
85°	28	28	21	28	28	31
90°	34	1	34	1	34	16
95°	62	52	62	52	62	70
105°	224	217	224	217	224	235
115°	403	403	403	403	403	398
125°	588	586	588	586	588	525
135°	768	759	768	759	768	591
145°	931	921	931	921	931	582
155°	1061	1053	1061	1053	1061	488
165°	1147	1146	1147	1146	1147	323
175°	1188	1192	1188	1192	1188	113
180°	1194	1194	1194	1194	1194	



TEST NUMBER: P331358-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1403.2	1403.6	1404.5	1397.9	1397.0	1397.0	1391.3	1386.3	1380.6	1372.7	1373.5
5°	1498.1	1503.8	1505.8	1499.6	1490.4	1489.3	1480.6	1466.1	1452.7	1441.9	1434.2
7.5°	1611.3	1613.6	1608.5	1600.3	1593.5	1581.1	1564.8	1548.8	1526.4	1505.9	1490.7
10°	1697.1	1700.2	1691.4	1679.6	1669.8	1655.4	1631.6	1607.4	1578.0	1549.6	1526.9
12.5°	1762.2	1769.9	1758.7	1757.1	1740.3	1720.5	1692.2	1680.0	1638.6	1599.1	1574.8
15°	1841.4	1840.9	1842.0	1832.2	1819.8	1816.6	1786.8	1754.3	1696.1	1672.8	1632.6
17.5°	1818.6	1826.3	1830.0	1829.9	1829.6	1827.7	1818.1	1797.6	1768.4	1730.7	1684.3
20°	1764.1	1774.4	1775.9	1787.9	1794.5	1803.3	1806.9	1801.2	1783.2	1751.7	1711.5
22.5°	1680.0	1682.8	1687.7	1706.2	1720.7	1742.6	1754.1	1773.2	1766.3	1750.9	1717.3
25°	1534.2	1529.0	1547.1	1556.3	1589.8	1624.9	1650.2	1678.0	1702.7	1717.7	1707.9
27.5°	1359.1	1351.4	1378.4	1403.0	1430.3	1468.2	1507.6	1554.1	1592.8	1641.1	1657.7
30°	1211.4	1216.1	1241.9	1268.2	1309.4	1363.0	1407.3	1458.4	1513.6	1567.7	1605.3
32.5°	1052.3	1070.2	1086.4	1126.7	1163.0	1222.8	1287.8	1351.6	1420.4	1481.9	1540.1
35°	835.2	855.8	878.5	907.9	958.9	1018.1	1081.6	1167.6	1261.5	1345.5	1414.6
37.5°	703.0	699.6	712.7	733.9	775.3	823.0	896.1	981.2	1091.6	1190.3	1287.8
40°	623.8	621.7	631.0	650.6	682.1	717.1	781.0	855.8	958.4	1078.9	1195.0
42.5°	569.4	570.6	575.7	589.6	611.1	640.0	687.8	751.4	845.4	959.0	1083.6
45°	503.1	506.8	512.4	519.2	531.5	555.2	582.0	627.4	701.7	796.5	919.2
47.5°	455.6	455.7	461.4	467.3	474.6	488.0	509.9	538.3	590.7	667.9	773.4
50°	429.9	426.4	430.5	435.0	442.8	452.1	466.6	493.3	528.4	590.8	678.9
52.5°	398.6	398.7	402.4	404.1	411.1	420.3	433.5	452.1	483.8	532.6	605.1
55°	353.7	356.2	358.3	361.3	367.6	374.3	384.6	397.0	421.7	458.3	511.9
57.5°	311.3	312.1	314.3	320.1	324.1	330.2	340.0	351.2	367.4	394.5	434.7
60°	282.5	282.5	286.6	289.2	294.4	300.5	308.3	319.1	333.6	355.7	388.2
62.5°	256.1	255.7	257.3	261.6	265.5	271.2	279.0	288.2	301.7	321.4	348.2
65°	217.5	216.5	219.6	220.7	224.8	230.5	236.6	246.4	257.2	271.7	295.4
67.5°	180.5	181.7	183.3	185.3	187.5	193.5	197.6	204.6	213.7	225.7	241.8
70°	159.8	159.8	159.8	161.4	164.4	167.5	171.7	177.3	186.1	196.4	210.9
72.5°	136.7	138.4	140.0	139.1	143.0	144.8	149.8	153.0	161.4	167.9	180.8
75°	107.2	107.2	107.2	109.8	111.4	112.9	116.0	119.1	123.2	131.5	138.1
77.5°	80.0	79.8	80.3	80.9	82.6	84.4	85.3	88.2	92.0	95.7	101.5
80°	61.9	62.9	63.4	64.4	64.4	65.4	65.9	69.6	72.2	74.7	78.4
82.5°	47.9	48.1	48.2	48.4	48.8	49.4	50.7	51.9	52.8	54.9	57.8
85°	27.9	27.4	27.4	28.4	27.9	27.9	28.9	29.9	29.9	30.4	31.9
87.5°	17.6	17.6	17.9	17.5	17.4	17.9	17.9	17.6	18.1	18.6	18.1
90°	34.2	34.0	33.8	33.6	33.3	33.5	33.9	34.3	34.8	35.2	30.3
92.5°	32.6	32.6	32.5	32.5	32.5	32.4	32.3	32.2	32.1	32.0	30.9
95°	62.5	62.9	63.4	63.8	64.2	64.5	64.5	64.5	64.5	64.5	64.0
97.5°	108.3	108.3	108.4	108.4	108.5	108.5	108.5	108.5	108.5	108.5	107.6
100°	138.0	138.3	138.6	138.8	139.0	139.1	139.1	139.1	139.1	139.1	138.5
102.5°	172.0	172.2	172.4	172.6	172.8	172.9	172.7	172.5	172.3	172.2	171.3
105°	223.7	223.7	223.7	223.7	223.7	223.5	223.1	222.6	222.2	221.7	221.3
107.5°	272.5	273.6	274.6	275.6	276.6	277.0	276.9	276.7	276.5	276.3	276.3
110°	310.4	311.0	311.7	312.5	313.1	313.5	313.5	313.5	313.5	313.5	313.5



TEST NUMBER: P331358-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	346.7	347.2	347.7	348.2	348.6	349.2	349.7	350.2	350.8	351.3	351.5
115°	403.1	403.7	404.5	405.2	405.8	406.3	406.5	406.7	407.0	407.2	407.6
117.5°	457.0	457.6	458.3	459.0	459.6	460.2	460.8	461.3	461.8	462.4	463.6
120°	494.8	495.5	496.1	496.9	497.6	497.9	497.9	497.9	497.9	497.9	499.7
122.5°	531.9	532.4	532.9	533.4	533.9	534.4	534.9	535.4	536.0	536.5	537.9
125°	588.5	588.8	589.0	589.3	589.5	589.9	590.6	591.3	591.9	592.6	593.3
127.5°	640.2	640.9	641.6	642.3	643.0	643.8	644.6	645.4	646.2	647.0	647.8
130°	677.2	678.1	679.0	679.9	680.9	681.5	682.0	682.4	682.9	683.3	683.8
132.5°	712.8	713.5	714.2	714.9	715.6	716.4	717.4	718.4	719.4	720.3	720.2
135°	767.9	768.6	769.3	769.9	770.6	771.0	771.3	771.5	771.7	771.9	771.5
137.5°	817.9	818.8	819.7	820.6	821.5	822.0	822.2	822.4	822.6	822.7	822.2
140°	852.6	853.5	854.3	855.3	856.2	856.7	856.7	856.7	856.7	856.7	855.6
142.5°	884.0	884.9	885.9	886.8	887.7	888.0	887.8	887.7	887.5	887.3	886.5
145°	931.2	932.1	933.0	933.9	934.8	935.1	934.9	934.6	934.4	934.2	932.9
147.5°	973.3	974.2	975.0	975.9	976.7	976.9	976.4	975.9	975.4	974.9	974.0
150°	1000.8	1001.4	1002.1	1002.8	1003.4	1003.4	1002.8	1002.1	1001.4	1000.8	999.9
152.5°	1026.5	1027.4	1028.2	1029.1	1030.0	1030.0	1029.1	1028.2	1027.4	1026.5	1025.4
155°	1061.2	1061.9	1062.6	1063.2	1063.9	1063.7	1062.6	1061.5	1060.4	1059.1	1058.5
157.5°	1091.1	1092.1	1093.2	1094.3	1095.3	1095.1	1093.6	1092.1	1090.6	1089.0	1088.6
160°	1109.5	1110.4	1111.4	1112.3	1113.2	1113.0	1111.6	1110.2	1108.9	1107.5	1107.3
162.5°	1125.7	1126.8	1127.8	1128.9	1130.0	1129.7	1128.2	1126.7	1125.2	1123.7	1123.5
165°	1146.9	1148.0	1149.1	1150.2	1151.3	1151.1	1149.5	1148.0	1146.4	1144.9	1144.9
167.5°	1164.2	1165.4	1166.5	1167.7	1168.8	1168.6	1167.1	1165.5	1164.0	1162.4	1162.5
170°	1173.1	1174.4	1175.8	1177.1	1178.4	1178.3	1176.8	1175.2	1173.7	1172.0	1172.3
172.5°	1180.3	1181.6	1183.1	1184.4	1185.7	1185.6	1184.1	1182.5	1180.9	1179.3	1179.5
175°	1188.2	1189.5	1190.8	1192.2	1193.6	1193.5	1191.8	1190.3	1188.7	1187.2	1187.6
177.5°	1191.8	1192.9	1194.0	1195.1	1196.1	1196.1	1195.1	1194.0	1192.9	1191.8	1192.1
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331358-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1376.4	1373.1	1371.1	1363.6	1357.1	1350.5	1348.4	1349.2	1340.2	1331.5	1327.8
5°	1430.1	1419.8	1410.0	1396.0	1379.6	1361.5	1352.2	1344.9	1327.0	1307.4	1296.1
7.5°	1478.1	1463.4	1444.5	1418.3	1394.3	1365.9	1347.9	1331.9	1305.5	1277.9	1260.9
10°	1507.4	1487.2	1463.0	1431.1	1401.7	1367.2	1342.9	1318.7	1287.8	1254.8	1234.2
12.5°	1532.6	1505.4	1481.6	1440.6	1405.8	1362.6	1333.8	1299.7	1267.2	1228.0	1207.8
15°	1592.5	1542.5	1497.0	1450.7	1407.9	1347.6	1315.7	1269.7	1226.9	1178.5	1155.3
17.5°	1638.7	1582.6	1511.1	1452.1	1402.2	1335.4	1288.5	1233.6	1183.0	1127.5	1096.0
20°	1665.2	1600.6	1523.9	1453.8	1393.9	1317.7	1266.7	1210.4	1151.1	1088.7	1054.7
22.5°	1680.8	1613.1	1537.1	1447.5	1377.5	1303.2	1239.0	1177.4	1117.3	1050.1	1014.3
25°	1685.8	1623.9	1543.5	1442.4	1356.9	1272.8	1195.5	1135.7	1063.0	1000.1	948.1
27.5°	1661.2	1616.9	1539.5	1432.7	1333.0	1234.8	1148.6	1080.9	1004.1	935.8	883.5
30°	1631.1	1605.3	1530.0	1422.8	1314.0	1208.4	1113.5	1036.7	960.4	891.3	837.7
32.5°	1584.5	1578.9	1512.8	1408.8	1293.8	1175.0	1076.8	999.2	914.6	846.8	795.7
35°	1493.0	1517.7	1475.9	1377.5	1255.8	1127.4	1021.3	932.6	845.0	780.0	732.1
37.5°	1370.3	1431.7	1420.8	1331.6	1204.5	1075.7	958.5	865.8	782.2	716.7	669.6
40°	1285.7	1364.0	1375.4	1296.6	1168.2	1035.7	911.4	819.2	737.7	677.9	630.5
42.5°	1195.0	1286.6	1317.7	1254.5	1128.5	993.6	869.4	773.8	693.2	635.0	593.0
45°	1042.9	1164.1	1220.2	1184.2	1062.5	924.3	796.5	699.5	626.3	571.7	539.3
47.5°	900.7	1033.1	1108.6	1095.9	989.0	852.1	725.8	632.8	561.5	517.9	488.8
50°	800.1	936.1	1027.4	1031.6	936.1	800.6	673.8	586.1	520.7	480.0	456.3
52.5°	712.7	842.5	942.1	963.9	877.2	747.0	627.2	540.0	482.3	444.8	423.6
55°	598.5	708.3	818.6	858.9	789.2	665.5	554.7	477.9	423.7	398.0	379.4
57.5°	497.6	589.2	691.1	735.5	692.6	586.6	482.7	416.1	372.1	349.5	335.3
60°	444.3	516.5	607.2	660.4	623.3	529.0	438.2	374.8	338.7	318.6	305.2
62.5°	394.9	458.8	535.5	584.1	563.9	474.9	393.6	337.7	306.5	287.6	278.0
65°	325.8	376.4	435.7	480.5	467.1	399.5	333.1	285.1	260.3	245.4	237.6
67.5°	268.3	304.8	345.9	385.2	374.4	326.5	273.2	235.8	217.3	204.5	199.9
70°	232.0	259.8	296.4	327.9	319.1	279.9	237.6	205.7	189.8	178.8	174.2
72.5°	197.3	220.3	248.1	273.9	267.9	235.4	200.2	176.0	163.7	153.7	149.9
75°	149.0	166.5	183.5	200.6	198.9	173.7	153.1	134.5	124.7	117.0	115.4
77.5°	110.0	119.8	131.4	141.5	138.7	124.2	108.1	97.5	90.2	85.0	84.2
80°	84.0	89.7	98.0	105.1	101.6	95.3	82.5	74.7	69.6	64.4	62.4
82.5°	60.9	66.7	71.6	75.4	72.7	67.0	59.0	53.7	50.6	47.2	46.3
85°	31.9	35.0	37.2	38.2	37.2	33.5	29.9	27.9	25.2	23.7	23.2
87.5°	17.5	16.5	15.5	15.6	13.7	13.2	11.0	9.3	9.4	9.5	9.2
90°	25.4	20.5	15.6	11.7	9.1	6.4	3.7	1.0	3.7	6.4	9.1
92.5°	29.7	28.6	27.4	25.9	23.8	21.9	19.9	18.0	19.9	21.9	23.8
95°	63.6	63.1	62.7	61.4	59.1	56.9	54.6	52.4	54.6	56.9	59.1
97.5°	106.7	105.9	105.0	103.6	101.7	99.7	97.8	95.7	97.8	99.7	101.7
100°	137.7	137.0	136.4	135.1	133.4	131.6	129.8	127.9	129.8	131.6	133.4
102.5°	170.5	169.6	168.7	167.5	166.1	164.7	163.3	161.9	163.3	164.7	166.1
105°	220.9	220.4	219.9	219.3	218.7	218.0	217.3	216.7	217.3	218.0	218.7
107.5°	276.3	276.3	276.3	275.9	274.9	273.9	272.9	271.9	272.9	273.9	274.9
110°	313.5	313.5	313.5	312.8	311.4	310.0	308.7	307.4	308.7	310.0	311.4



TEST NUMBER: P331358-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	351.6	351.8	352.0	351.4	350.1	348.8	347.4	346.1	347.4	348.8	350.1
115°	408.1	408.5	408.9	408.5	407.2	405.8	404.5	403.1	404.5	405.8	407.2
117.5°	464.8	466.2	467.4	467.2	465.3	463.5	461.7	460.0	461.7	463.5	465.3
120°	501.4	503.2	505.0	505.0	503.2	501.4	499.7	497.9	499.7	501.4	503.2
122.5°	539.1	540.3	541.6	541.1	539.0	536.8	534.6	532.5	534.6	536.8	539.0
125°	593.9	594.6	595.3	594.6	592.6	590.6	588.5	586.5	588.5	590.6	592.6
127.5°	648.6	649.4	650.3	649.3	646.8	644.3	641.7	639.1	641.7	644.3	646.8
130°	684.2	684.6	685.1	683.9	681.0	678.0	675.1	672.2	675.1	678.0	681.0
132.5°	720.2	720.1	720.0	718.8	716.4	714.1	711.7	709.3	711.7	714.1	716.4
135°	771.0	770.6	770.2	768.7	766.3	763.8	761.3	758.9	761.3	763.8	766.3
137.5°	821.6	821.0	820.4	819.1	817.1	815.1	813.0	811.1	813.0	815.1	817.1
140°	854.3	853.2	852.1	850.6	848.6	846.6	844.6	842.5	844.6	846.6	848.6
142.5°	885.8	884.9	884.2	882.8	880.8	878.8	876.8	874.7	876.8	878.8	880.8
145°	931.5	930.2	928.9	927.4	925.8	924.2	922.7	921.1	922.7	924.2	925.8
147.5°	973.1	972.3	971.4	970.0	968.1	966.2	964.3	962.4	964.3	966.2	968.1
150°	999.0	998.0	997.1	996.0	994.7	993.3	992.0	990.7	992.0	993.3	994.7
152.5°	1024.4	1023.3	1022.3	1021.1	1019.7	1018.3	1017.0	1015.6	1017.0	1018.3	1019.7
155°	1057.8	1057.2	1056.5	1055.8	1055.2	1054.5	1053.8	1053.2	1053.8	1054.5	1055.2
157.5°	1088.2	1087.8	1087.4	1087.0	1086.5	1086.1	1085.6	1085.2	1085.6	1086.1	1086.5
160°	1107.1	1106.9	1106.7	1106.3	1105.9	1105.4	1105.0	1104.6	1105.0	1105.4	1105.9
162.5°	1123.3	1123.1	1122.8	1122.7	1122.6	1122.5	1122.4	1122.3	1122.4	1122.5	1122.6
165°	1144.9	1144.9	1144.9	1145.0	1145.2	1145.4	1145.7	1145.9	1145.7	1145.4	1145.2
167.5°	1162.5	1162.6	1162.6	1163.0	1163.6	1164.3	1165.0	1165.6	1165.0	1164.3	1163.6
170°	1172.6	1172.8	1173.0	1173.4	1174.1	1174.8	1175.4	1176.1	1175.4	1174.8	1174.1
172.5°	1179.7	1180.0	1180.2	1180.6	1181.3	1182.0	1182.7	1183.4	1182.7	1182.0	1181.3
175°	1188.1	1188.5	1189.0	1189.5	1190.2	1190.8	1191.5	1192.2	1191.5	1190.8	1190.2
177.5°	1192.5	1192.9	1193.3	1193.7	1194.3	1194.8	1195.3	1195.9	1195.3	1194.8	1194.3
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331358-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1323.6	1321.2	1312.5	1308.0	1300.5	1293.5	1289.0	1291.1	1292.7	1291.9	1290.6
5°	1285.7	1275.9	1260.9	1248.1	1238.8	1221.7	1214.6	1210.9	1207.9	1204.3	1200.6
7.5°	1240.5	1225.1	1203.7	1185.3	1167.9	1146.8	1134.8	1127.5	1120.1	1112.0	1104.8
10°	1208.4	1186.7	1164.1	1138.2	1117.6	1098.5	1081.6	1070.3	1060.0	1050.2	1042.9
12.5°	1174.6	1149.6	1121.6	1086.3	1063.6	1036.3	1033.7	1013.7	997.6	991.6	983.1
15°	1120.7	1085.7	1050.2	1008.4	990.3	965.5	950.1	934.6	920.7	910.9	908.4
17.5°	1059.6	1014.2	978.9	948.9	919.3	893.9	879.7	867.3	855.9	842.7	841.0
20°	1013.0	973.8	935.1	908.9	878.5	852.6	835.2	822.7	812.9	805.3	798.5
22.5°	968.9	925.9	890.6	861.8	831.8	811.0	797.2	785.3	777.1	768.5	762.2
25°	898.1	864.5	825.9	793.3	768.6	755.3	743.9	733.6	728.4	722.8	715.6
27.5°	836.1	798.8	762.7	737.5	715.8	703.9	695.8	688.8	684.0	680.6	676.6
30°	792.3	754.7	726.4	701.7	683.6	671.8	666.6	662.5	656.8	654.7	652.7
32.5°	750.3	716.4	692.2	670.7	653.5	645.7	641.0	637.3	632.9	630.8	626.6
35°	690.7	662.5	638.7	626.8	613.0	606.2	602.7	597.4	593.4	591.3	590.8
37.5°	634.8	610.2	594.6	579.4	573.5	569.4	564.4	560.9	559.7	559.4	558.9
40°	598.5	578.5	564.5	552.1	549.6	543.3	539.3	536.1	536.1	536.6	536.1
42.5°	565.5	547.4	535.2	524.5	521.5	517.8	513.6	513.4	514.3	516.0	514.3
45°	515.5	502.6	493.8	488.7	483.0	479.4	478.9	480.5	481.0	481.5	483.0
47.5°	469.5	461.0	453.0	447.4	444.8	444.2	443.6	446.4	448.8	449.7	452.1
50°	442.3	432.5	425.9	422.2	420.1	419.1	420.1	423.2	425.3	427.9	429.4
52.5°	411.8	404.9	400.2	397.5	396.7	397.3	397.5	401.0	404.2	405.2	406.0
55°	369.6	364.5	363.5	358.8	360.8	360.3	362.9	365.0	368.1	371.1	371.7
57.5°	327.6	323.5	320.6	321.0	321.6	324.0	326.1	329.7	333.1	336.3	336.6
60°	299.5	297.4	295.9	295.9	296.9	300.0	302.7	306.2	308.3	310.3	311.8
62.5°	274.0	271.9	270.3	271.1	273.9	275.7	278.7	280.6	282.7	284.8	285.5
65°	233.5	232.5	234.1	235.1	235.6	238.1	241.8	243.3	245.4	246.4	250.0
67.5°	196.3	196.5	196.3	197.7	200.8	201.4	204.8	208.3	208.7	210.8	213.1
70°	171.2	172.2	173.2	174.2	176.8	177.8	180.5	182.0	184.0	185.6	187.1
72.5°	148.0	148.2	149.3	149.1	151.3	153.5	155.7	157.2	159.3	161.3	162.8
75°	113.9	113.9	114.9	115.4	118.1	120.7	120.1	121.2	123.2	125.2	126.3
77.5°	83.2	82.1	83.2	83.7	84.5	86.7	87.2	88.6	90.9	90.2	91.4
80°	63.4	61.9	63.4	63.9	63.9	66.6	66.6	67.6	69.1	67.6	69.1
82.5°	45.2	44.5	45.6	45.7	46.6	46.7	47.6	47.8	49.3	48.6	49.3
85°	22.7	22.2	22.7	22.2	22.7	23.2	23.2	22.7	22.7	23.7	22.2
87.5°	9.4	9.7	10.3	11.3	11.8	12.4	11.9	11.8	11.7	10.8	10.8
90°	11.7	15.6	20.5	25.4	30.3	35.2	34.8	34.3	33.9	33.5	33.3
92.5°	25.9	27.4	28.6	29.7	30.9	32.0	32.1	32.2	32.3	32.4	32.5
95°	61.4	62.7	63.1	63.6	64.0	64.5	64.5	64.5	64.5	64.5	64.2
97.5°	103.6	105.0	105.9	106.7	107.6	108.5	108.5	108.5	108.5	108.5	108.5
100°	135.1	136.4	137.0	137.7	138.5	139.1	139.1	139.1	139.1	139.1	139.0
102.5°	167.5	168.7	169.6	170.5	171.3	172.2	172.3	172.5	172.7	172.9	172.8
105°	219.3	219.9	220.4	220.9	221.3	221.7	222.2	222.6	223.1	223.5	223.7
107.5°	275.9	276.3	276.3	276.3	276.3	276.3	276.5	276.7	276.9	277.0	276.6
110°	312.8	313.5	313.5	313.5	313.5	313.5	313.5	313.5	313.5	313.5	313.1



TEST NUMBER: P331358-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	351.4	352.0	351.8	351.6	351.5	351.3	350.8	350.2	349.7	349.2	348.6
115°	408.5	408.9	408.5	408.1	407.6	407.2	407.0	406.7	406.5	406.3	405.8
117.5°	467.2	467.4	466.2	464.8	463.6	462.4	461.8	461.3	460.8	460.2	459.6
120°	505.0	505.0	503.2	501.4	499.7	497.9	497.9	497.9	497.9	497.9	497.6
122.5°	541.1	541.6	540.3	539.1	537.9	536.5	536.0	535.4	534.9	534.4	533.9
125°	594.6	595.3	594.6	593.9	593.3	592.6	591.9	591.3	590.6	589.9	589.5
127.5°	649.3	650.3	649.4	648.6	647.8	647.0	646.2	645.4	644.6	643.8	643.0
130°	683.9	685.1	684.6	684.2	683.8	683.3	682.9	682.4	682.0	681.5	680.9
132.5°	718.8	720.0	720.1	720.2	720.2	720.3	719.4	718.4	717.4	716.4	715.6
135°	768.7	770.2	770.6	771.0	771.5	771.9	771.7	771.5	771.3	771.0	770.6
137.5°	819.1	820.4	821.0	821.6	822.2	822.7	822.6	822.4	822.2	822.0	821.5
140°	850.6	852.1	853.2	854.3	855.6	856.7	856.7	856.7	856.7	856.7	856.2
142.5°	882.8	884.2	884.9	885.8	886.5	887.3	887.5	887.7	887.8	888.0	887.7
145°	927.4	928.9	930.2	931.5	932.9	934.2	934.4	934.6	934.9	935.1	934.8
147.5°	970.0	971.4	972.3	973.1	974.0	974.9	975.4	975.9	976.4	976.9	976.7
150°	996.0	997.1	998.0	999.0	999.9	1000.8	1001.4	1002.1	1002.8	1003.4	1003.4
152.5°	1021.1	1022.3	1023.3	1024.4	1025.4	1026.5	1027.4	1028.2	1029.1	1030.0	1030.0
155°	1055.8	1056.5	1057.2	1057.8	1058.5	1059.1	1060.4	1061.5	1062.6	1063.7	1063.9
157.5°	1087.0	1087.4	1087.8	1088.2	1088.6	1089.0	1090.6	1092.1	1093.6	1095.1	1095.3
160°	1106.3	1106.7	1106.9	1107.1	1107.3	1107.5	1108.9	1110.2	1111.6	1113.0	1113.2
162.5°	1122.7	1122.8	1123.1	1123.3	1123.5	1123.7	1125.2	1126.7	1128.2	1129.7	1130.0
165°	1145.0	1144.9	1144.9	1144.9	1144.9	1144.9	1146.4	1148.0	1149.5	1151.1	1151.3
167.5°	1163.0	1162.6	1162.6	1162.5	1162.5	1162.4	1164.0	1165.5	1167.1	1168.6	1168.8
170°	1173.4	1173.0	1172.8	1172.6	1172.3	1172.0	1173.7	1175.2	1176.8	1178.3	1178.4
172.5°	1180.6	1180.2	1180.0	1179.7	1179.5	1179.3	1180.9	1182.5	1184.1	1185.6	1185.7
175°	1189.5	1189.0	1188.5	1188.1	1187.6	1187.2	1188.7	1190.3	1191.8	1193.5	1193.6
177.5°	1193.7	1193.3	1192.9	1192.5	1192.1	1191.8	1192.9	1194.0	1195.1	1196.1	1196.1
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331358-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1286.6	1285.7	1285.7	1282.0	1285.7	1285.7	1286.6	1290.6	1291.9	1292.7	1291.1
5°	1193.5	1191.8	1189.3	1191.8	1189.3	1191.8	1193.5	1200.6	1204.3	1207.9	1210.9
7.5°	1101.4	1095.2	1094.3	1088.1	1094.3	1095.2	1101.4	1104.8	1112.0	1120.1	1127.5
10°	1034.1	1030.0	1029.5	1019.7	1029.5	1030.0	1034.1	1042.9	1050.2	1060.0	1070.3
12.5°	983.0	973.1	975.0	969.4	975.0	973.1	983.0	983.1	991.6	997.6	1013.7
15°	894.4	894.4	892.3	883.6	892.3	894.4	894.4	908.4	910.9	920.7	934.6
17.5°	830.8	829.8	824.9	827.3	824.9	829.8	830.8	841.0	842.7	855.9	867.3
20°	792.8	789.8	783.6	783.6	783.6	789.8	792.8	798.5	805.3	812.9	822.7
22.5°	757.0	756.8	750.2	752.2	750.2	756.8	757.0	762.2	768.5	777.1	785.3
25°	715.0	710.9	707.8	709.3	707.8	710.9	715.0	715.6	722.8	728.4	733.6
27.5°	675.2	673.0	672.8	668.5	672.8	673.0	675.2	676.6	680.6	684.0	688.8
30°	652.2	647.0	648.0	645.4	648.0	647.0	652.2	652.7	654.7	656.8	662.5
32.5°	625.7	623.9	622.9	620.7	622.9	623.9	625.7	626.6	630.8	632.9	637.3
35°	589.8	590.3	587.7	588.8	587.7	590.3	589.8	590.8	591.3	593.4	597.4
37.5°	558.4	560.0	558.8	559.1	558.8	560.0	558.4	558.9	559.4	559.7	560.9
40°	537.7	537.7	537.7	539.3	537.7	537.7	537.7	536.1	536.6	536.1	536.1
42.5°	517.9	517.1	516.2	516.1	516.2	517.1	517.9	514.3	516.0	514.3	513.4
45°	484.0	485.6	486.1	483.5	486.1	485.6	484.0	483.0	481.5	481.0	480.5
47.5°	453.4	453.6	453.4	455.8	453.4	453.6	453.4	452.1	449.7	448.8	446.4
50°	432.0	431.0	432.0	431.0	432.0	431.0	432.0	429.4	427.9	425.3	423.2
52.5°	409.3	409.5	408.9	408.7	408.9	409.5	409.3	406.0	405.2	404.2	401.0
55°	373.8	374.8	374.3	374.3	374.3	374.8	373.8	371.7	371.1	368.1	365.0
57.5°	337.0	337.9	338.6	336.3	338.6	337.9	337.0	336.6	336.3	333.1	329.7
60°	311.3	314.0	313.5	312.5	313.5	314.0	311.3	311.8	310.3	308.3	306.2
62.5°	287.9	288.8	288.7	288.5	288.7	288.8	287.9	285.5	284.8	282.7	280.6
65°	251.6	252.6	251.1	252.6	251.1	252.6	251.6	250.0	246.4	245.4	243.3
67.5°	212.5	212.8	214.0	214.7	214.0	212.8	212.5	213.1	210.8	208.7	208.3
70°	188.1	187.6	189.1	190.8	189.1	187.6	188.1	187.1	185.6	184.0	182.0
72.5°	162.6	163.7	163.2	164.3	163.2	163.7	162.6	162.8	161.3	159.3	157.2
75°	125.2	126.8	126.3	127.8	126.3	126.8	125.2	126.3	125.2	123.2	121.2
77.5°	90.5	90.7	90.5	91.4	90.5	90.7	90.5	91.4	90.2	90.9	88.6
80°	69.1	68.1	67.1	69.1	67.1	68.1	69.1	69.1	67.6	69.1	67.6
82.5°	48.1	48.7	47.7	47.7	47.7	48.7	48.1	49.3	48.6	49.3	47.8
85°	22.2	21.6	20.6	20.6	20.6	21.6	22.2	22.2	23.7	22.7	22.7
87.5°	10.8	10.5	10.5	10.2	10.5	10.5	10.8	10.8	10.8	11.7	11.8
90°	33.6	33.8	34.0	34.2	34.0	33.8	33.6	33.3	33.5	33.9	34.3
92.5°	32.5	32.5	32.6	32.6	32.6	32.5	32.5	32.5	32.4	32.3	32.2
95°	63.8	63.4	62.9	62.5	62.9	63.4	63.8	64.2	64.5	64.5	64.5
97.5°	108.4	108.4	108.3	108.3	108.3	108.4	108.4	108.5	108.5	108.5	108.5
100°	138.8	138.6	138.3	138.0	138.3	138.6	138.8	139.0	139.1	139.1	139.1
102.5°	172.6	172.4	172.2	172.0	172.2	172.4	172.6	172.8	172.9	172.7	172.5
105°	223.7	223.7	223.7	223.7	223.7	223.7	223.7	223.7	223.5	223.1	222.6
107.5°	275.6	274.6	273.6	272.5	273.6	274.6	275.6	276.6	277.0	276.9	276.7
110°	312.5	311.7	311.0	310.4	311.0	311.7	312.5	313.1	313.5	313.5	313.5



TEST NUMBER: P331358-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	348.2	347.7	347.2	346.7	347.2	347.7	348.2	348.6	349.2	349.7	350.2
115°	405.2	404.5	403.7	403.1	403.7	404.5	405.2	405.8	406.3	406.5	406.7
117.5°	459.0	458.3	457.6	457.0	457.6	458.3	459.0	459.6	460.2	460.8	461.3
120°	496.9	496.1	495.5	494.8	495.5	496.1	496.9	497.6	497.9	497.9	497.9
122.5°	533.4	532.9	532.4	531.9	532.4	532.9	533.4	533.9	534.4	534.9	535.4
125°	589.3	589.0	588.8	588.5	588.8	589.0	589.3	589.5	589.9	590.6	591.3
127.5°	642.3	641.6	640.9	640.2	640.9	641.6	642.3	643.0	643.8	644.6	645.4
130°	679.9	679.0	678.1	677.2	678.1	679.0	679.9	680.9	681.5	682.0	682.4
132.5°	714.9	714.2	713.5	712.8	713.5	714.2	714.9	715.6	716.4	717.4	718.4
135°	769.9	769.3	768.6	767.9	768.6	769.3	769.9	770.6	771.0	771.3	771.5
137.5°	820.6	819.7	818.8	817.9	818.8	819.7	820.6	821.5	822.0	822.2	822.4
140°	855.3	854.3	853.5	852.6	853.5	854.3	855.3	856.2	856.7	856.7	856.7
142.5°	886.8	885.9	884.9	884.0	884.9	885.9	886.8	887.7	888.0	887.8	887.7
145°	933.9	933.0	932.1	931.2	932.1	933.0	933.9	934.8	935.1	934.9	934.6
147.5°	975.9	975.0	974.2	973.3	974.2	975.0	975.9	976.7	976.9	976.4	975.9
150°	1002.8	1002.1	1001.4	1000.8	1001.4	1002.1	1002.8	1003.4	1003.4	1002.8	1002.1
152.5°	1029.1	1028.2	1027.4	1026.5	1027.4	1028.2	1029.1	1030.0	1030.0	1029.1	1028.2
155°	1063.2	1062.6	1061.9	1061.2	1061.9	1062.6	1063.2	1063.9	1063.7	1062.6	1061.5
157.5°	1094.3	1093.2	1092.1	1091.1	1092.1	1093.2	1094.3	1095.3	1095.1	1093.6	1092.1
160°	1112.3	1111.4	1110.4	1109.5	1110.4	1111.4	1112.3	1113.2	1113.0	1111.6	1110.2
162.5°	1128.9	1127.8	1126.8	1125.7	1126.8	1127.8	1128.9	1130.0	1129.7	1128.2	1126.7
165°	1150.2	1149.1	1148.0	1146.9	1148.0	1149.1	1150.2	1151.3	1151.1	1149.5	1148.0
167.5°	1167.7	1166.5	1165.4	1164.2	1165.4	1166.5	1167.7	1168.8	1168.6	1167.1	1165.5
170°	1177.1	1175.8	1174.4	1173.1	1174.4	1175.8	1177.1	1178.4	1178.3	1176.8	1175.2
172.5°	1184.4	1183.1	1181.6	1180.3	1181.6	1183.1	1184.4	1185.7	1185.6	1184.1	1182.5
175°	1192.2	1190.8	1189.5	1188.2	1189.5	1190.8	1192.2	1193.6	1193.5	1191.8	1190.3
177.5°	1195.1	1194.0	1192.9	1191.8	1192.9	1194.0	1195.1	1196.1	1196.1	1195.1	1194.0
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331358-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1289.0	1293.5	1300.5	1308.0	1312.5	1321.2	1323.6	1327.8	1331.5	1340.2	1349.2
5°	1214.6	1221.7	1238.8	1248.1	1260.9	1275.9	1285.7	1296.1	1307.4	1327.0	1344.9
7.5°	1134.8	1146.8	1167.9	1185.3	1203.7	1225.1	1240.5	1260.9	1277.9	1305.5	1331.9
10°	1081.6	1098.5	1117.6	1138.2	1164.1	1186.7	1208.4	1234.2	1254.8	1287.8	1318.7
12.5°	1033.7	1036.3	1063.6	1086.3	1121.6	1149.6	1174.6	1207.8	1228.0	1267.2	1299.7
15°	950.1	965.5	990.3	1008.4	1050.2	1085.7	1120.7	1155.3	1178.5	1226.9	1269.7
17.5°	879.7	893.9	919.3	948.9	978.9	1014.2	1059.6	1096.0	1127.5	1183.0	1233.6
20°	835.2	852.6	878.5	908.9	935.1	973.8	1013.0	1054.7	1088.7	1151.1	1210.4
22.5°	797.2	811.0	831.8	861.8	890.6	925.9	968.9	1014.3	1050.1	1117.3	1177.4
25°	743.9	755.3	768.6	793.3	825.9	864.5	898.1	948.1	1000.1	1063.0	1135.7
27.5°	695.8	703.9	715.8	737.5	762.7	798.8	836.1	883.5	935.8	1004.1	1080.9
30°	666.6	671.8	683.6	701.7	726.4	754.7	792.3	837.7	891.3	960.4	1036.7
32.5°	641.0	645.7	653.5	670.7	692.2	716.4	750.3	795.7	846.8	914.6	999.2
35°	602.7	606.2	613.0	626.8	638.7	662.5	690.7	732.1	780.0	845.0	932.6
37.5°	564.4	569.4	573.5	579.4	594.6	610.2	634.8	669.6	716.7	782.2	865.8
40°	539.3	543.3	549.6	552.1	564.5	578.5	598.5	630.5	677.9	737.7	819.2
42.5°	513.6	517.8	521.5	524.5	535.2	547.4	565.5	593.0	635.0	693.2	773.8
45°	478.9	479.4	483.0	488.7	493.8	502.6	515.5	539.3	571.7	626.3	699.5
47.5°	443.6	444.2	444.8	447.4	453.0	461.0	469.5	488.8	517.9	561.5	632.8
50°	420.1	419.1	420.1	422.2	425.9	432.5	442.3	456.3	480.0	520.7	586.1
52.5°	397.5	397.3	396.7	397.5	400.2	404.9	411.8	423.6	444.8	482.3	540.0
55°	362.9	360.3	360.8	358.8	363.5	364.5	369.6	379.4	398.0	423.7	477.9
57.5°	326.1	324.0	321.6	321.0	320.6	323.5	327.6	335.3	349.5	372.1	416.1
60°	302.7	300.0	296.9	295.9	295.9	297.4	299.5	305.2	318.6	338.7	374.8
62.5°	278.7	275.7	273.9	271.1	270.3	271.9	274.0	278.0	287.6	306.5	337.7
65°	241.8	238.1	235.6	235.1	234.1	232.5	233.5	237.6	245.4	260.3	285.1
67.5°	204.8	201.4	200.8	197.7	196.3	196.5	196.3	199.9	204.5	217.3	235.8
70°	180.5	177.8	176.8	174.2	173.2	172.2	171.2	174.2	178.8	189.8	205.7
72.5°	155.7	153.5	151.3	149.1	149.3	148.2	148.0	149.9	153.7	163.7	176.0
75°	120.1	120.7	118.1	115.4	114.9	113.9	113.9	115.4	117.0	124.7	134.5
77.5°	87.2	86.7	84.5	83.7	83.2	82.1	83.2	84.2	85.0	90.2	97.5
80°	66.6	66.6	63.9	63.9	63.4	61.9	63.4	62.4	64.4	69.6	74.7
82.5°	47.6	46.7	46.6	45.7	45.6	44.5	45.2	46.3	47.2	50.6	53.7
85°	23.2	23.2	22.7	22.2	22.7	22.2	22.7	23.2	23.7	25.2	27.9
87.5°	11.9	12.4	11.8	11.3	10.3	9.7	9.4	9.2	9.5	9.4	9.3
90°	34.8	35.2	30.3	25.4	20.5	15.6	11.7	9.1	6.4	3.7	1.0
92.5°	32.1	32.0	30.9	29.7	28.6	27.4	25.9	23.8	21.9	19.9	18.0
95°	64.5	64.5	64.0	63.6	63.1	62.7	61.4	59.1	56.9	54.6	52.4
97.5°	108.5	108.5	107.6	106.7	105.9	105.0	103.6	101.7	99.7	97.8	95.7
100°	139.1	139.1	138.5	137.7	137.0	136.4	135.1	133.4	131.6	129.8	127.9
102.5°	172.3	172.2	171.3	170.5	169.6	168.7	167.5	166.1	164.7	163.3	161.9
105°	222.2	221.7	221.3	220.9	220.4	219.9	219.3	218.7	218.0	217.3	216.7
107.5°	276.5	276.3	276.3	276.3	276.3	276.3	275.9	274.9	273.9	272.9	271.9
110°	313.5	313.5	313.5	313.5	313.5	313.5	312.8	311.4	310.0	308.7	307.4



TEST NUMBER: P331358-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	350.8	351.3	351.5	351.6	351.8	352.0	351.4	350.1	348.8	347.4	346.1
115°	407.0	407.2	407.6	408.1	408.5	408.9	408.5	407.2	405.8	404.5	403.1
117.5°	461.8	462.4	463.6	464.8	466.2	467.4	467.2	465.3	463.5	461.7	460.0
120°	497.9	497.9	499.7	501.4	503.2	505.0	505.0	503.2	501.4	499.7	497.9
122.5°	536.0	536.5	537.9	539.1	540.3	541.6	541.1	539.0	536.8	534.6	532.5
125°	591.9	592.6	593.3	593.9	594.6	595.3	594.6	592.6	590.6	588.5	586.5
127.5°	646.2	647.0	647.8	648.6	649.4	650.3	649.3	646.8	644.3	641.7	639.1
130°	682.9	683.3	683.8	684.2	684.6	685.1	683.9	681.0	678.0	675.1	672.2
132.5°	719.4	720.3	720.2	720.2	720.1	720.0	718.8	716.4	714.1	711.7	709.3
135°	771.7	771.9	771.5	771.0	770.6	770.2	768.7	766.3	763.8	761.3	758.9
137.5°	822.6	822.7	822.2	821.6	821.0	820.4	819.1	817.1	815.1	813.0	811.1
140°	856.7	856.7	855.6	854.3	853.2	852.1	850.6	848.6	846.6	844.6	842.5
142.5°	887.5	887.3	886.5	885.8	884.9	884.2	882.8	880.8	878.8	876.8	874.7
145°	934.4	934.2	932.9	931.5	930.2	928.9	927.4	925.8	924.2	922.7	921.1
147.5°	975.4	974.9	974.0	973.1	972.3	971.4	970.0	968.1	966.2	964.3	962.4
150°	1001.4	1000.8	999.9	999.0	998.0	997.1	996.0	994.7	993.3	992.0	990.7
152.5°	1027.4	1026.5	1025.4	1024.4	1023.3	1022.3	1021.1	1019.7	1018.3	1017.0	1015.6
155°	1060.4	1059.1	1058.5	1057.8	1057.2	1056.5	1055.8	1055.2	1054.5	1053.8	1053.2
157.5°	1090.6	1089.0	1088.6	1088.2	1087.8	1087.4	1087.0	1086.5	1086.1	1085.6	1085.2
160°	1108.9	1107.5	1107.3	1107.1	1106.9	1106.7	1106.3	1105.9	1105.4	1105.0	1104.6
162.5°	1125.2	1123.7	1123.5	1123.3	1123.1	1122.8	1122.7	1122.6	1122.5	1122.4	1122.3
165°	1146.4	1144.9	1144.9	1144.9	1144.9	1144.9	1145.0	1145.2	1145.4	1145.7	1145.9
167.5°	1164.0	1162.4	1162.5	1162.5	1162.6	1162.6	1163.0	1163.6	1164.3	1165.0	1165.6
170°	1173.7	1172.0	1172.3	1172.6	1172.8	1173.0	1173.4	1174.1	1174.8	1175.4	1176.1
172.5°	1180.9	1179.3	1179.5	1179.7	1180.0	1180.2	1180.6	1181.3	1182.0	1182.7	1183.4
175°	1188.7	1187.2	1187.6	1188.1	1188.5	1189.0	1189.5	1190.2	1190.8	1191.5	1192.2
177.5°	1192.9	1191.8	1192.1	1192.5	1192.9	1193.3	1193.7	1194.3	1194.8	1195.3	1195.9
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331358-840
 CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1348.4	1350.5	1357.1	1363.6	1371.1	1373.1	1376.4	1373.5	1372.7	1380.6	1386.3
5°	1352.2	1361.5	1379.6	1396.0	1410.0	1419.8	1430.1	1434.2	1441.9	1452.7	1466.1
7.5°	1347.9	1365.9	1394.3	1418.3	1444.5	1463.4	1478.1	1490.7	1505.9	1526.4	1548.8
10°	1342.9	1367.2	1401.7	1431.1	1463.0	1487.2	1507.4	1526.9	1549.6	1578.0	1607.4
12.5°	1333.8	1362.6	1405.8	1440.6	1481.6	1505.4	1532.6	1574.8	1599.1	1638.6	1680.0
15°	1315.7	1347.6	1407.9	1450.7	1497.0	1542.5	1592.5	1632.6	1672.8	1696.1	1754.3
17.5°	1288.5	1335.4	1402.2	1452.1	1511.1	1582.6	1638.7	1684.3	1730.7	1768.4	1797.6
20°	1266.7	1317.7	1393.9	1453.8	1523.9	1600.6	1665.2	1711.5	1751.7	1783.2	1801.2
22.5°	1239.0	1303.2	1377.5	1447.5	1537.1	1613.1	1680.8	1717.3	1750.9	1766.3	1773.2
25°	1195.5	1272.8	1356.9	1442.4	1543.5	1623.9	1685.8	1707.9	1717.7	1702.7	1678.0
27.5°	1148.6	1234.8	1333.0	1432.7	1539.5	1616.9	1661.2	1657.7	1641.1	1592.8	1554.1
30°	1113.5	1208.4	1314.0	1422.8	1530.0	1605.3	1631.1	1605.3	1567.7	1513.6	1458.4
32.5°	1076.8	1175.0	1293.8	1408.8	1512.8	1578.9	1584.5	1540.1	1481.9	1420.4	1351.6
35°	1021.3	1127.4	1255.8	1377.5	1475.9	1517.7	1493.0	1414.6	1345.5	1261.5	1167.6
37.5°	958.5	1075.7	1204.5	1331.6	1420.8	1431.7	1370.3	1287.8	1190.3	1091.6	981.2
40°	911.4	1035.7	1168.2	1296.6	1375.4	1364.0	1285.7	1195.0	1078.9	958.4	855.8
42.5°	869.4	993.6	1128.5	1254.5	1317.7	1286.6	1195.0	1083.6	959.0	845.4	751.4
45°	796.5	924.3	1062.5	1184.2	1220.2	1164.1	1042.9	919.2	796.5	701.7	627.4
47.5°	725.8	852.1	989.0	1095.9	1108.6	1033.1	900.7	773.4	667.9	590.7	538.3
50°	673.8	800.6	936.1	1031.6	1027.4	936.1	800.1	678.9	590.8	528.4	493.3
52.5°	627.2	747.0	877.2	963.9	942.1	842.5	712.7	605.1	532.6	483.8	452.1
55°	554.7	665.5	789.2	858.9	818.6	708.3	598.5	511.9	458.3	421.7	397.0
57.5°	482.7	586.6	692.6	735.5	691.1	589.2	497.6	434.7	394.5	367.4	351.2
60°	438.2	529.0	623.3	660.4	607.2	516.5	444.3	388.2	355.7	333.6	319.1
62.5°	393.6	474.9	563.9	584.1	535.5	458.8	394.9	348.2	321.4	301.7	288.2
65°	333.1	399.5	467.1	480.5	435.7	376.4	325.8	295.4	271.7	257.2	246.4
67.5°	273.2	326.5	374.4	385.2	345.9	304.8	268.3	241.8	225.7	213.7	204.6
70°	237.6	279.9	319.1	327.9	296.4	259.8	232.0	210.9	196.4	186.1	177.3
72.5°	200.2	235.4	267.9	273.9	248.1	220.3	197.3	180.8	167.9	161.4	153.0
75°	153.1	173.7	198.9	200.6	183.5	166.5	149.0	138.1	131.5	123.2	119.1
77.5°	108.1	124.2	138.7	141.5	131.4	119.8	110.0	101.5	95.7	92.0	88.2
80°	82.5	95.3	101.6	105.1	98.0	89.7	84.0	78.4	74.7	72.2	69.6
82.5°	59.0	67.0	72.7	75.4	71.6	66.7	60.9	57.8	54.9	52.8	51.9
85°	29.9	33.5	37.2	38.2	37.2	35.0	31.9	31.9	30.4	29.9	29.9
87.5°	11.0	13.2	13.7	15.6	15.5	16.5	17.5	18.1	18.6	18.1	17.6
90°	3.7	6.4	9.1	11.7	15.6	20.5	25.4	30.3	35.2	34.8	34.3
92.5°	19.9	21.9	23.8	25.9	27.4	28.6	29.7	30.9	32.0	32.1	32.2
95°	54.6	56.9	59.1	61.4	62.7	63.1	63.6	64.0	64.5	64.5	64.5
97.5°	97.8	99.7	101.7	103.6	105.0	105.9	106.7	107.6	108.5	108.5	108.5
100°	129.8	131.6	133.4	135.1	136.4	137.0	137.7	138.5	139.1	139.1	139.1
102.5°	163.3	164.7	166.1	167.5	168.7	169.6	170.5	171.3	172.2	172.3	172.5
105°	217.3	218.0	218.7	219.3	219.9	220.4	220.9	221.3	221.7	222.2	222.6
107.5°	272.9	273.9	274.9	275.9	276.3	276.3	276.3	276.3	276.3	276.5	276.7
110°	308.7	310.0	311.4	312.8	313.5	313.5	313.5	313.5	313.5	313.5	313.5



TEST NUMBER: P331358-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	347.4	348.8	350.1	351.4	352.0	351.8	351.6	351.5	351.3	350.8	350.2
115°	404.5	405.8	407.2	408.5	408.9	408.5	408.1	407.6	407.2	407.0	406.7
117.5°	461.7	463.5	465.3	467.2	467.4	466.2	464.8	463.6	462.4	461.8	461.3
120°	499.7	501.4	503.2	505.0	505.0	503.2	501.4	499.7	497.9	497.9	497.9
122.5°	534.6	536.8	539.0	541.1	541.6	540.3	539.1	537.9	536.5	536.0	535.4
125°	588.5	590.6	592.6	594.6	595.3	594.6	593.9	593.3	592.6	591.9	591.3
127.5°	641.7	644.3	646.8	649.3	650.3	649.4	648.6	647.8	647.0	646.2	645.4
130°	675.1	678.0	681.0	683.9	685.1	684.6	684.2	683.8	683.3	682.9	682.4
132.5°	711.7	714.1	716.4	718.8	720.0	720.1	720.2	720.2	720.3	719.4	718.4
135°	761.3	763.8	766.3	768.7	770.2	770.6	771.0	771.5	771.9	771.7	771.5
137.5°	813.0	815.1	817.1	819.1	820.4	821.0	821.6	822.2	822.7	822.6	822.4
140°	844.6	846.6	848.6	850.6	852.1	853.2	854.3	855.6	856.7	856.7	856.7
142.5°	876.8	878.8	880.8	882.8	884.2	884.9	885.8	886.5	887.3	887.5	887.7
145°	922.7	924.2	925.8	927.4	928.9	930.2	931.5	932.9	934.2	934.4	934.6
147.5°	964.3	966.2	968.1	970.0	971.4	972.3	973.1	974.0	974.9	975.4	975.9
150°	992.0	993.3	994.7	996.0	997.1	998.0	999.0	999.9	1000.8	1001.4	1002.1
152.5°	1017.0	1018.3	1019.7	1021.1	1022.3	1023.3	1024.4	1025.4	1026.5	1027.4	1028.2
155°	1053.8	1054.5	1055.2	1055.8	1056.5	1057.2	1057.8	1058.5	1059.1	1060.4	1061.5
157.5°	1085.6	1086.1	1086.5	1087.0	1087.4	1087.8	1088.2	1088.6	1089.0	1090.6	1092.1
160°	1105.0	1105.4	1105.9	1106.3	1106.7	1106.9	1107.1	1107.3	1107.5	1108.9	1110.2
162.5°	1122.4	1122.5	1122.6	1122.7	1122.8	1123.1	1123.3	1123.5	1123.7	1125.2	1126.7
165°	1145.7	1145.4	1145.2	1145.0	1144.9	1144.9	1144.9	1144.9	1144.9	1146.4	1148.0
167.5°	1165.0	1164.3	1163.6	1163.0	1162.6	1162.6	1162.5	1162.5	1162.4	1164.0	1165.5
170°	1175.4	1174.8	1174.1	1173.4	1173.0	1172.8	1172.6	1172.3	1172.0	1173.7	1175.2
172.5°	1182.7	1182.0	1181.3	1180.6	1180.2	1180.0	1179.7	1179.5	1179.3	1180.9	1182.5
175°	1191.5	1190.8	1190.2	1189.5	1189.0	1188.5	1188.1	1187.6	1187.2	1188.7	1190.3
177.5°	1195.3	1194.8	1194.3	1193.7	1193.3	1192.9	1192.5	1192.1	1191.8	1192.9	1194.0
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331358-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1391.3	1397.0	1397.0	1397.9	1404.5	1403.6	1403.2
5°	1480.6	1489.3	1490.4	1499.6	1505.8	1503.8	1498.1
7.5°	1564.8	1581.1	1593.5	1600.3	1608.5	1613.6	1611.3
10°	1631.6	1655.4	1669.8	1679.6	1691.4	1700.2	1697.1
12.5°	1692.2	1720.5	1740.3	1757.1	1758.7	1769.9	1762.2
15°	1786.8	1816.6	1819.8	1832.2	1842.0	1840.9	1841.4
17.5°	1818.1	1827.7	1829.6	1829.9	1830.0	1826.3	1818.6
20°	1806.9	1803.3	1794.5	1787.9	1775.9	1774.4	1764.1
22.5°	1754.1	1742.6	1720.7	1706.2	1687.7	1682.8	1680.0
25°	1650.2	1624.9	1589.8	1556.3	1547.1	1529.0	1534.2
27.5°	1507.6	1468.2	1430.3	1403.0	1378.4	1351.4	1359.1
30°	1407.3	1363.0	1309.4	1268.2	1241.9	1216.1	1211.4
32.5°	1287.8	1222.8	1163.0	1126.7	1086.4	1070.2	1052.3
35°	1081.6	1018.1	958.9	907.9	878.5	855.8	835.2
37.5°	896.1	823.0	775.3	733.9	712.7	699.6	703.0
40°	781.0	717.1	682.1	650.6	631.0	621.7	623.8
42.5°	687.8	640.0	611.1	589.6	575.7	570.6	569.4
45°	582.0	555.2	531.5	519.2	512.4	506.8	503.1
47.5°	509.9	488.0	474.6	467.3	461.4	455.7	455.6
50°	466.6	452.1	442.8	435.0	430.5	426.4	429.9
52.5°	433.5	420.3	411.1	404.1	402.4	398.7	398.6
55°	384.6	374.3	367.6	361.3	358.3	356.2	353.7
57.5°	340.0	330.2	324.1	320.1	314.3	312.1	311.3
60°	308.3	300.5	294.4	289.2	286.6	282.5	282.5
62.5°	279.0	271.2	265.5	261.6	257.3	255.7	256.1
65°	236.6	230.5	224.8	220.7	219.6	216.5	217.5
67.5°	197.6	193.5	187.5	185.3	183.3	181.7	180.5
70°	171.7	167.5	164.4	161.4	159.8	159.8	159.8
72.5°	149.8	144.8	143.0	139.1	140.0	138.4	136.7
75°	116.0	112.9	111.4	109.8	107.2	107.2	107.2
77.5°	85.3	84.4	82.6	80.9	80.3	79.8	80.0
80°	65.9	65.4	64.4	64.4	63.4	62.9	61.9
82.5°	50.7	49.4	48.8	48.4	48.2	48.1	47.9
85°	28.9	27.9	27.9	28.4	27.4	27.4	27.9
87.5°	17.9	17.9	17.4	17.5	17.9	17.6	17.6
90°	33.9	33.5	33.3	33.6	33.8	34.0	34.2
92.5°	32.3	32.4	32.5	32.5	32.5	32.6	32.6
95°	64.5	64.5	64.2	63.8	63.4	62.9	62.5
97.5°	108.5	108.5	108.5	108.4	108.4	108.3	108.3
100°	139.1	139.1	139.0	138.8	138.6	138.3	138.0
102.5°	172.7	172.9	172.8	172.6	172.4	172.2	172.0
105°	223.1	223.5	223.7	223.7	223.7	223.7	223.7
107.5°	276.9	277.0	276.6	275.6	274.6	273.6	272.5
110°	313.5	313.5	313.1	312.5	311.7	311.0	310.4



TEST NUMBER: P331358-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	349.7	349.2	348.6	348.2	347.7	347.2	346.7
115°	406.5	406.3	405.8	405.2	404.5	403.7	403.1
117.5°	460.8	460.2	459.6	459.0	458.3	457.6	457.0
120°	497.9	497.9	497.6	496.9	496.1	495.5	494.8
122.5°	534.9	534.4	533.9	533.4	532.9	532.4	531.9
125°	590.6	589.9	589.5	589.3	589.0	588.8	588.5
127.5°	644.6	643.8	643.0	642.3	641.6	640.9	640.2
130°	682.0	681.5	680.9	679.9	679.0	678.1	677.2
132.5°	717.4	716.4	715.6	714.9	714.2	713.5	712.8
135°	771.3	771.0	770.6	769.9	769.3	768.6	767.9
137.5°	822.2	822.0	821.5	820.6	819.7	818.8	817.9
140°	856.7	856.7	856.2	855.3	854.3	853.5	852.6
142.5°	887.8	888.0	887.7	886.8	885.9	884.9	884.0
145°	934.9	935.1	934.8	933.9	933.0	932.1	931.2
147.5°	976.4	976.9	976.7	975.9	975.0	974.2	973.3
150°	1002.8	1003.4	1003.4	1002.8	1002.1	1001.4	1000.8
152.5°	1029.1	1030.0	1030.0	1029.1	1028.2	1027.4	1026.5
155°	1062.6	1063.7	1063.9	1063.2	1062.6	1061.9	1061.2
157.5°	1093.6	1095.1	1095.3	1094.3	1093.2	1092.1	1091.1
160°	1111.6	1113.0	1113.2	1112.3	1111.4	1110.4	1109.5
162.5°	1128.2	1129.7	1130.0	1128.9	1127.8	1126.8	1125.7
165°	1149.5	1151.1	1151.3	1150.2	1149.1	1148.0	1146.9
167.5°	1167.1	1168.6	1168.8	1167.7	1166.5	1165.4	1164.2
170°	1176.8	1178.3	1178.4	1177.1	1175.8	1174.4	1173.1
172.5°	1184.1	1185.6	1185.7	1184.4	1183.1	1181.6	1180.3
175°	1191.8	1193.5	1193.6	1192.2	1190.8	1189.5	1188.2
177.5°	1195.1	1196.1	1196.1	1195.1	1194.0	1192.9	1191.8
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3

(END OF REPORT)