

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332917-927

Luminaire Tested: **SA4XXRDIP-C575D1035U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332917-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C575D1035U927-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4699.6 lumens  
Efficiency: N/A  
Efficacy: 105.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332917-927

CATALOG NUMBER: SA4XXRDIP-C575D1035U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332917-927

CATALOG NUMBER: SA4XXRDIP-C575D1035U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40				
1	96	91	88	84	87	83	80	77	68	66	64	54	53	52	41	41	40	34				
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	37	35	34	29				
3	80	71	63	58	72	64	58	53	53	49	45	43	39	37	33	31	29	24				
4	73	62	55	49	66	57	51	45	47	42	38	38	34	32	29	27	25	21				
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	27	24	22	18				
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16				
7	57	45	37	32	52	41	35	30	35	29	26	28	24	21	22	19	17	15				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16	13				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	17	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6500	6500	6500
5°	6514	6434	6474
10°	6473	6357	6357
15°	6399	6224	6177
20°	6296	6048	5936
25°	6167	5842	5694
30°	6039	5626	5390
35°	5899	5401	5084
40°	5730	5145	4755
45°	5574	4891	4419
50°	5397	4598	4064
55°	5206	4294	3678
60°	4996	3961	3284
65°	4804	3543	2896
70°	4525	3085	2460
75°	4173	2558	1999
80°	3640	1948	1836
85°	3084	1769	1658



TEST NUMBER: P332917-927

CATALOG NUMBER: SA4XXRDIP-C575D1035U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	75.6	1.6
10°-20°	210.9	4.5
20°-30°	304.5	6.5
30°-40°	345.2	7.3
40°-50°	333.3	7.1
50°-60°	277.2	5.9
60°-70°	191.4	4.1
70°-80°	97.0	2.1
80°-90°	27.9	0.6
90°-100°	67.4	1.4
100°-110°	199.8	4.3
110°-120°	339.1	7.2
120°-130°	447.1	9.5
130°-140°	502.1	10.7
140°-150°	493.4	10.5
150°-160°	415.0	8.8
160°-170°	276.1	5.9
170°-180°	96.7	2.1
0°-30°	591.0	12.6
0°-40°	936.2	19.9
0°-60°	1546.7	32.9
0°-90°	1863.1	39.6
90°-120°	606.3	12.9
90°-150°	2048.8	43.6
90°-180°	2837.0	60.4
0°-180°	4699.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	805	805	805	805	805	
5°	804	801	794	800	799	76
15°	766	760	745	743	739	216
25°	692	680	656	646	639	319
35°	599	578	548	528	516	374
45°	488	465	428	399	387	376
55°	370	344	305	274	261	331
65°	252	224	186	160	152	248
75°	134	111	82	68	64	141
85°	33	22	19	18	18	38
90°	2	11	17	22	24	5
95°	48	54	60	62	62	53
105°	184	185	188	191	193	196
115°	345	345	343	342	342	340
125°	502	502	501	500	498	447
135°	648	652	652	651	648	501
145°	787	790	791	790	788	492
155°	901	901	901	903	901	415
165°	981	979	977	982	979	276
175°	1021	1017	1016	1021	1016	97
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P332917-927

CATALOG NUMBER: SA4XXRDIP-C575D1035U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1
2.5°	807.1	806.6	806.2	805.7	805.3	804.5	803.3	802.1	800.8	799.6	800.8
5°	803.8	803.3	802.7	802.2	801.7	800.6	798.9	797.3	795.6	794.0	795.4
7.5°	796.5	796.0	795.4	794.9	794.2	792.9	790.8	788.6	786.5	784.3	785.2
10°	789.6	789.0	788.3	787.6	787.0	785.4	782.9	780.4	777.9	775.5	776.0
12.5°	780.8	780.0	779.2	778.4	777.6	775.8	772.9	769.9	767.1	764.1	764.5
15°	765.6	764.4	763.2	761.9	760.7	758.4	754.9	751.5	748.1	744.7	744.4
17.5°	747.3	745.4	743.7	741.9	740.1	737.2	733.1	729.0	724.8	720.7	720.0
20°	732.9	731.2	729.4	727.6	725.8	722.6	718.0	713.3	708.6	704.0	702.9
22.5°	717.2	715.2	713.2	711.1	709.2	705.7	700.7	695.7	690.7	685.7	684.0
25°	692.3	689.8	687.3	684.8	682.4	678.3	672.7	667.1	661.5	655.9	653.6
27.5°	666.1	663.1	660.0	656.9	653.7	649.2	643.2	637.2	631.2	625.2	622.3
30°	647.8	644.4	641.0	637.6	634.2	629.2	622.8	616.4	609.9	603.5	600.1
32.5°	628.7	624.8	620.9	617.0	613.2	607.9	601.3	594.6	588.0	581.3	577.3
35°	598.6	594.2	589.8	585.4	581.1	575.4	568.5	561.7	554.8	548.0	543.4
37.5°	566.4	561.9	557.4	552.9	548.3	542.2	534.6	527.0	519.5	511.9	506.7
40°	543.7	539.2	534.6	530.1	525.6	519.4	511.7	503.8	496.1	488.2	482.4
42.5°	522.0	517.3	512.5	507.8	503.0	496.6	488.5	480.3	472.2	464.1	458.2
45°	488.2	483.2	478.1	473.0	467.9	461.3	453.0	444.9	436.7	428.4	421.7
47.5°	453.4	448.1	442.8	437.6	432.4	425.5	416.9	408.4	399.9	391.3	384.4
50°	429.7	424.3	419.0	413.6	408.3	401.2	392.4	383.7	374.9	366.1	359.3
52.5°	405.5	400.3	395.1	389.8	384.5	377.5	368.4	359.5	350.5	341.5	334.5
55°	369.9	364.4	358.9	353.4	347.9	340.7	331.8	323.0	314.0	305.1	298.0
57.5°	334.6	328.9	323.2	317.5	311.8	304.6	295.8	287.0	278.3	269.5	262.3
60°	309.4	304.0	298.5	293.0	287.6	280.4	271.6	262.8	254.1	245.3	238.2
62.5°	286.8	281.1	275.4	269.7	264.0	256.7	247.6	238.7	229.7	220.7	214.1
65°	251.5	245.7	239.7	233.9	227.9	220.6	211.8	203.1	194.3	185.5	179.7
67.5°	214.9	209.2	203.6	198.0	192.3	185.4	177.3	169.1	161.1	152.9	147.8
70°	191.7	185.9	180.2	174.4	168.7	161.9	154.1	146.3	138.5	130.7	126.2
72.5°	167.1	161.8	156.6	151.5	146.2	140.0	132.6	125.2	117.8	110.4	106.6
75°	133.8	128.7	123.7	118.6	113.5	107.7	101.3	94.8	88.4	82.0	78.8
77.5°	100.0	95.7	91.4	87.1	82.8	78.0	72.8	67.7	62.4	57.2	55.4
80°	78.3	74.3	70.3	66.4	62.4	58.4	54.3	50.1	46.0	41.9	41.5
82.5°	59.6	55.9	52.3	48.6	45.0	42.0	39.6	37.2	34.9	32.6	32.2
85°	33.3	30.6	27.8	25.0	22.3	20.8	20.4	20.0	19.5	19.1	18.9
87.5°	11.8	11.3	10.9	10.4	9.8	9.7	9.9	10.1	10.2	10.4	10.5
90°	2.4	4.3	6.3	8.2	10.1	11.8	13.2	14.6	16.0	17.4	18.5
92.5°	17.0	19.2	21.3	23.5	25.7	27.4	28.4	29.3	30.3	31.3	31.9
95°	47.5	49.0	50.6	52.2	53.8	55.1	56.4	57.7	58.9	60.1	60.6
97.5°	82.9	84.1	85.4	86.7	87.9	89.3	90.7	92.1	93.6	95.1	95.7
100°	110.7	111.4	112.1	112.8	113.5	114.6	116.2	117.8	119.4	121.0	121.4
102.5°	139.8	140.1	140.4	140.6	140.9	141.8	143.2	144.7	146.1	147.6	148.1
105°	184.3	184.4	184.6	184.7	185.0	185.4	186.1	186.8	187.5	188.2	188.7
107.5°	230.9	231.1	231.3	231.6	231.7	231.9	232.0	232.1	232.2	232.3	232.8
110°	262.5	262.8	263.2	263.6	264.0	264.0	263.8	263.6	263.5	263.3	262.9



TEST NUMBER: P332917-927

CATALOG NUMBER: SA4XXRDIP-C575D1035U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	295.4	295.5	295.6	295.6	295.7	295.6	295.2	294.9	294.6	294.3	294.2
115°	344.8	344.8	344.8	344.8	344.8	344.6	344.2	343.9	343.5	343.2	343.0
117.5°	391.3	391.4	391.5	391.7	391.8	391.7	391.5	391.3	391.0	390.8	390.1
120°	422.2	422.9	423.7	424.4	425.1	425.2	424.6	424.1	423.6	423.0	422.2
122.5°	454.5	454.8	455.0	455.3	455.6	455.7	455.4	455.1	454.9	454.6	454.1
125°	502.1	502.1	502.1	502.1	502.1	502.0	501.8	501.7	501.5	501.3	501.0
127.5°	545.3	545.8	546.3	546.8	547.4	547.5	547.2	546.9	546.7	546.4	546.1
130°	575.6	576.2	576.7	577.2	577.7	578.0	578.0	578.0	578.0	578.0	577.7
132.5°	606.7	607.0	607.4	607.8	608.2	608.3	608.2	608.0	607.8	607.8	607.4
135°	647.6	648.6	649.7	650.8	651.8	652.4	652.4	652.4	652.4	652.4	652.0
137.5°	692.2	692.7	693.2	693.6	694.2	694.5	694.8	695.1	695.4	695.7	695.2
140°	721.9	722.2	722.6	722.9	723.3	723.5	723.5	723.5	723.5	723.5	723.3
142.5°	749.1	749.5	749.8	750.2	750.5	750.6	750.5	750.4	750.2	750.0	750.0
145°	786.7	787.4	788.1	788.9	789.6	790.0	790.2	790.4	790.5	790.7	790.5
147.5°	824.1	824.9	825.8	826.6	827.4	827.8	827.7	827.5	827.4	827.3	827.1
150°	846.8	847.6	848.3	849.0	849.7	850.0	850.0	850.0	850.0	850.0	850.0
152.5°	868.4	868.8	869.2	869.7	870.1	870.3	870.4	870.6	870.8	870.8	871.3
155°	901.4	901.4	901.4	901.4	901.4	901.3	901.1	900.9	900.8	900.6	901.3
157.5°	929.2	928.9	928.6	928.3	928.0	927.8	927.7	927.7	927.7	927.6	928.2
160°	945.7	945.5	945.3	945.2	945.0	944.8	944.6	944.4	944.3	944.1	944.6
162.5°	960.8	960.4	960.0	959.5	959.0	958.7	958.5	958.4	958.2	958.0	958.9
165°	981.3	980.7	980.2	979.7	979.1	978.7	978.3	978.0	977.6	977.3	978.3
167.5°	997.0	996.2	995.5	994.7	994.0	993.6	993.6	993.7	993.7	993.8	994.8
170°	1005.8	1004.9	1004.0	1003.1	1002.3	1001.9	1002.1	1002.3	1002.4	1002.6	1003.7
172.5°	1012.1	1011.4	1010.7	1009.9	1009.2	1008.8	1008.8	1008.8	1008.9	1008.9	1010.1
175°	1020.8	1019.9	1019.1	1018.2	1017.3	1016.8	1016.6	1016.4	1016.2	1016.1	1017.3
177.5°	1023.7	1022.9	1022.2	1021.5	1020.8	1020.5	1020.5	1020.5	1020.5	1020.5	1021.4
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4



TEST NUMBER: P332917-927

CATALOG NUMBER: SA4XXRDIP-C575D1035U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1
2.5°	802.1	803.3	804.5	805.0	804.9	804.8	804.7	804.6
5°	796.7	798.1	799.5	800.0	799.7	799.5	799.2	798.9
7.5°	786.1	787.0	787.9	788.1	787.7	787.2	786.8	786.3
10°	776.6	777.1	777.7	777.7	777.1	776.6	776.0	775.5
12.5°	764.8	765.1	765.5	765.2	764.5	763.7	763.0	762.2
15°	744.1	743.9	743.5	743.0	742.0	741.0	740.1	739.1
17.5°	719.2	718.4	717.6	716.5	715.1	713.7	712.2	710.7
20°	701.8	700.7	699.6	698.2	696.4	694.6	692.8	691.0
22.5°	682.5	680.8	679.1	677.6	676.1	674.7	673.3	671.8
25°	651.3	648.9	646.6	644.8	643.3	642.0	640.6	639.2
27.5°	619.4	616.6	613.7	611.2	609.3	607.3	605.4	603.4
30°	596.7	593.2	589.8	587.0	584.8	582.6	580.4	578.2
32.5°	573.4	569.4	565.4	562.4	560.3	558.3	556.1	554.1
35°	538.7	534.0	529.4	525.9	523.4	520.9	518.4	515.9
37.5°	501.5	496.3	491.1	487.3	484.7	482.3	479.8	477.4
40°	476.7	471.0	465.2	461.1	458.6	456.1	453.7	451.2
42.5°	452.3	446.5	440.6	436.4	433.8	431.3	428.6	426.1
45°	415.0	408.3	401.6	397.0	394.5	392.1	389.6	387.1
47.5°	377.4	370.4	363.5	358.6	355.9	353.2	350.5	347.8
50°	352.4	345.6	338.7	334.1	331.4	328.8	326.2	323.6
52.5°	327.6	320.6	313.7	308.9	306.1	303.4	300.7	298.0
55°	290.9	283.8	276.6	271.8	269.2	266.6	264.0	261.3
57.5°	255.0	247.8	240.6	236.0	234.0	232.0	230.0	228.1
60°	231.1	223.9	216.8	212.2	210.0	207.8	205.7	203.4
62.5°	207.6	201.0	194.4	190.2	188.5	186.7	185.0	183.2
65°	173.8	167.9	162.0	158.2	156.6	155.0	153.3	151.6
67.5°	142.8	137.7	132.6	129.2	127.4	125.6	123.7	121.9
70°	121.7	117.2	112.6	109.6	108.3	106.9	105.5	104.2
72.5°	102.7	98.9	95.0	92.4	91.2	89.9	88.6	87.4
75°	75.7	72.6	69.4	67.4	66.5	65.8	65.0	64.1
77.5°	53.6	51.7	49.8	48.8	48.6	48.3	48.1	47.8
80°	41.1	40.7	40.2	40.0	39.8	39.7	39.6	39.5
82.5°	31.9	31.6	31.4	31.1	31.0	30.8	30.7	30.6
85°	18.5	18.3	18.0	17.9	17.9	17.9	17.9	17.9
87.5°	10.6	10.7	10.8	10.9	11.1	11.3	11.5	11.6
90°	19.5	20.6	21.6	22.3	22.7	23.1	23.4	23.7
92.5°	32.6	33.2	33.8	34.3	34.5	34.7	34.9	35.1
95°	61.2	61.7	62.2	62.5	62.5	62.5	62.5	62.5
97.5°	96.3	97.0	97.6	97.9	97.9	97.9	97.9	97.9
100°	121.7	122.0	122.4	122.6	122.6	122.6	122.6	122.6
102.5°	148.5	149.0	149.5	149.8	150.0	150.1	150.3	150.4
105°	189.3	189.8	190.3	190.8	191.3	191.9	192.4	192.9
107.5°	233.3	233.8	234.2	234.5	234.5	234.4	234.4	234.3
110°	262.6	262.2	261.9	262.0	262.5	263.0	263.6	264.1





TEST NUMBER: P332917-927

CATALOG NUMBER: SA4XXRDIP-C575D1035U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	294.1	294.1	294.1	294.1	294.1	294.2	294.4	294.5
115°	342.8	342.6	342.5	342.3	342.1	341.9	341.7	341.6
117.5°	389.6	389.0	388.4	387.9	387.5	387.2	386.8	386.5
120°	421.3	420.4	419.5	419.2	419.6	419.9	420.3	420.6
122.5°	453.4	452.9	452.3	451.6	451.0	450.4	449.7	449.1
125°	500.6	500.3	499.9	499.6	499.2	498.8	498.5	498.1
127.5°	545.7	545.3	544.9	544.6	544.4	544.1	543.8	543.5
130°	577.3	576.9	576.6	576.1	575.4	574.6	573.9	573.2
132.5°	607.0	606.7	606.3	606.0	605.7	605.5	605.1	604.9
135°	651.6	651.3	650.9	650.5	650.0	649.4	648.9	648.4
137.5°	694.7	694.3	693.9	693.6	693.8	693.9	694.0	694.1
140°	723.2	722.9	722.8	722.6	722.5	722.2	722.1	721.9
142.5°	750.0	750.0	750.0	749.9	749.9	749.8	749.8	749.7
145°	790.4	790.2	790.0	789.6	789.1	788.6	788.1	787.5
147.5°	827.0	826.8	826.6	826.5	826.3	826.2	826.0	825.9
150°	850.0	850.0	850.0	849.9	849.8	849.5	849.4	849.2
152.5°	871.7	872.1	872.6	872.6	872.1	871.6	871.2	870.7
155°	902.1	902.7	903.4	903.4	902.7	902.1	901.3	900.6
157.5°	928.7	929.2	929.8	929.7	929.2	928.5	928.0	927.3
160°	945.2	945.7	946.2	946.0	945.2	944.3	943.4	942.5
162.5°	959.9	960.8	961.8	961.9	961.0	960.1	959.3	958.3
165°	979.5	980.5	981.5	981.7	981.0	980.3	979.6	978.9
167.5°	995.9	997.0	998.0	998.0	996.9	995.8	994.7	993.6
170°	1004.7	1005.8	1006.9	1006.7	1005.5	1004.2	1003.1	1001.8
172.5°	1011.3	1012.5	1013.8	1013.7	1012.5	1011.2	1010.0	1008.8
175°	1018.5	1019.8	1021.0	1021.0	1019.8	1018.5	1017.3	1016.1
177.5°	1022.5	1023.4	1024.5	1024.4	1023.3	1022.1	1021.0	1019.9
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4

(END OF REPORT)