

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331383-840

Luminaire Tested: **SA2XXDIP-C865D330U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331383-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D330U840-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4838.4 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331383-840

CATALOG NUMBER: SA2XXDIP-C865D330U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331383-840

CATALOG NUMBER: SA2XXDIP-C865D330U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	96	96	96	87	87	87	78	78	78	73				
1	103	99	94	91	98	94	90	87	85	82	79	76	74	72	69	67	66	62				
2	94	86	80	74	89	82	76	71	74	70	66	67	63	60	60	58	55	52				
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	54	50	47	44				
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	41	38				
5	72	60	52	45	68	57	50	44	52	46	41	48	42	38	43	39	35	33				
6	67	54	46	39	63	52	44	38	47	41	36	43	38	34	39	35	31	29				
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25				
8	57	45	36	31	54	43	35	30	39	33	28	36	31	27	33	28	25	23				
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	23	21				
10	50	38	30	25	48	36	29	24	33	27	23	31	26	22	28	24	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22501	22501	22501
5°	22587	22261	22392
10°	22453	22035	22146
15°	22176	21750	21727
20°	21782	21321	21297
25°	21389	20794	20794
30°	20885	20310	20137
35°	20416	19730	19438
40°	19827	19150	18782
45°	19244	18573	18114
50°	18613	17975	17334
55°	17954	17275	16636
60°	17221	16443	15839
65°	16435	15614	14896
70°	15437	14611	13917
75°	14042	13456	13125
80°	12459	12087	11464
85°	10170	9689	8688



TEST NUMBER: P331383-840

CATALOG NUMBER: SA2XXDIP-C865D330U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.0	2.7
10°-20°	368.7	7.6
20°-30°	542.0	11.2
30°-40°	629.6	13.0
40°-50°	628.9	13.0
50°-60°	548.4	11.3
60°-70°	405.5	8.4
70°-80°	229.7	4.7
80°-90°	63.4	1.3
90°-100°	74.2	1.5
100°-110°	251.8	5.2
110°-120°	267.5	5.5
120°-130°	220.2	4.6
130°-140°	176.8	3.7
140°-150°	133.6	2.8
150°-160°	93.9	1.9
160°-170°	55.3	1.1
170°-180°	18.0	0.4
0°-30°	1041.8	21.5
0°-40°	1671.3	34.5
0°-60°	2848.6	58.9
0°-90°	3547.3	73.3
90°-120°	593.4	12.3
90°-150°	1124.0	23.2
90°-180°	1291.0	26.7
0°-180°	4838.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1394	1394	1394	1394	1394	
5°	1394	1388	1374	1384	1382	132
15°	1327	1318	1301	1306	1300	373
25°	1201	1189	1167	1170	1167	552
35°	1036	1022	1001	993	986	646
45°	843	833	813	799	793	650
55°	638	629	614	598	591	570
65°	430	422	409	397	390	425
75°	225	222	216	208	210	240
85°	55	54	52	48	47	63
90°	0	5	12	12	12	3
95°	12	31	140	53	41	13
105°	44	66	264	473	402	46
115°	77	97	221	457	529	76
125°	107	127	213	370	429	95
135°	126	150	210	311	356	97
145°	143	165	209	260	284	90
155°	163	176	203	230	239	75
165°	178	183	194	206	209	50
175°	185	185	187	189	189	18
180°	186	186	186	186	186	



TEST NUMBER: P331383-840

CATALOG NUMBER: SA2XXDIP-C865D330U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6
2.5°	1400.1	1398.9	1397.7	1396.5	1395.3	1393.4	1390.8	1388.2	1385.5	1382.9	1385.3
5°	1393.6	1392.4	1391.3	1390.1	1388.9	1386.6	1383.4	1380.1	1376.8	1373.5	1375.9
7.5°	1381.3	1379.5	1377.7	1375.7	1373.9	1371.3	1368.0	1364.6	1361.3	1358.0	1360.4
10°	1369.5	1367.5	1365.3	1363.2	1361.2	1358.4	1354.7	1351.2	1347.7	1344.0	1346.5
12.5°	1353.4	1351.6	1349.8	1347.9	1346.0	1343.3	1339.8	1336.2	1332.6	1329.1	1330.7
15°	1326.7	1324.8	1323.0	1321.3	1319.5	1316.7	1312.8	1308.9	1305.0	1301.2	1302.3
17.5°	1292.3	1290.5	1288.8	1287.0	1285.2	1282.3	1278.4	1274.4	1270.5	1266.6	1268.0
20°	1267.7	1265.9	1264.1	1262.3	1260.5	1257.6	1253.3	1249.2	1245.1	1240.9	1241.7
22.5°	1243.0	1240.5	1238.0	1235.5	1233.0	1229.8	1225.9	1221.9	1218.0	1214.1	1214.3
25°	1200.6	1198.3	1195.9	1193.6	1191.1	1187.4	1182.3	1177.3	1172.3	1167.2	1167.8
27.5°	1152.5	1150.3	1148.1	1146.0	1143.9	1140.7	1136.8	1132.8	1128.8	1124.8	1124.0
30°	1120.2	1117.9	1115.5	1113.2	1110.8	1107.3	1102.9	1098.4	1093.9	1089.4	1088.5
32.5°	1086.0	1084.1	1082.2	1080.3	1078.3	1075.0	1070.4	1065.6	1061.0	1056.2	1054.6
35°	1035.8	1032.9	1029.9	1026.9	1023.9	1020.1	1015.3	1010.6	1005.7	1001.0	999.3
37.5°	979.3	976.6	974.0	971.4	968.9	965.1	960.4	955.6	950.8	946.0	943.8
40°	940.7	938.4	935.9	933.5	931.2	927.6	922.8	918.1	913.3	908.6	905.8
42.5°	903.2	900.8	898.4	896.1	893.6	890.1	885.3	880.6	875.8	871.0	868.1
45°	842.8	840.8	838.7	836.7	834.6	831.2	826.8	822.3	817.9	813.4	810.1
47.5°	782.8	780.9	778.9	777.0	775.0	771.6	767.0	762.3	757.7	753.1	749.6
50°	741.0	739.5	738.1	736.6	735.1	732.3	728.1	723.9	719.7	715.6	711.4
52.5°	700.3	698.3	696.4	694.4	692.5	689.5	685.6	681.7	677.7	673.8	670.3
55°	637.8	636.1	634.3	632.5	630.7	628.0	624.5	620.9	617.3	613.7	610.2
57.5°	575.1	573.7	572.3	570.9	569.5	566.7	562.8	558.9	554.9	551.0	547.5
60°	533.3	532.1	531.0	529.8	528.6	525.9	521.7	517.6	513.4	509.2	505.9
62.5°	492.6	490.7	488.8	486.9	484.9	482.4	479.2	475.9	472.7	469.6	466.6
65°	430.2	428.4	426.6	424.7	423.0	420.6	417.7	414.7	411.7	408.7	406.1
67.5°	366.7	365.2	363.8	362.3	360.9	358.9	356.2	353.5	350.8	348.1	346.1
70°	327.0	325.8	324.6	323.4	322.2	320.2	317.6	314.9	312.3	309.5	307.5
72.5°	286.2	285.1	283.9	282.7	281.4	280.0	278.3	276.6	274.8	273.1	271.0
75°	225.1	224.5	223.9	223.4	222.8	221.7	220.3	218.7	217.2	215.7	214.0
77.5°	170.5	169.5	168.4	167.4	166.4	165.6	165.0	164.4	163.8	163.2	162.3
80°	134.0	133.7	133.4	133.1	132.8	132.4	131.8	131.2	130.6	130.0	129.1
82.5°	99.7	99.7	99.6	99.5	99.5	99.3	98.9	98.6	98.2	97.9	96.6
85°	54.9	54.6	54.3	54.0	53.7	53.4	53.1	52.8	52.5	52.3	51.4
87.5°	19.4	19.1	18.9	18.6	18.3	18.0	17.9	17.9	17.9	17.5	16.7
90°	0.4	1.4	2.8	3.5	4.2	5.4	7.2	9.6	11.8	12.1	11.8
92.5°	4.3	6.3	8.9	10.4	12.8	16.2	24.2	35.6	45.7	46.4	39.2
95°	12.5	13.9	17.5	20.7	26.4	34.9	51.4	82.4	123.8	139.9	122.4
97.5°	20.3	22.2	26.1	30.9	37.5	47.2	67.8	111.1	179.9	238.7	250.4
100°	27.5	28.6	31.7	37.5	44.6	54.6	73.5	117.0	194.1	281.9	333.3
102.5°	34.0	34.8	38.1	43.7	51.2	61.2	78.7	117.3	188.6	283.3	364.1
105°	43.5	44.9	47.5	52.8	60.7	70.7	87.5	119.2	178.0	264.4	359.3
107.5°	53.8	54.9	57.4	62.3	70.1	80.2	96.4	124.1	172.8	244.1	328.0
110°	60.7	62.1	64.2	68.9	76.3	86.7	102.4	128.1	171.7	234.4	308.3



TEST NUMBER: P331383-840

CATALOG NUMBER: SA2XXDIP-C865D330U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	67.0	68.4	70.8	75.1	82.3	93.0	108.2	132.4	171.9	228.1	294.6
115°	76.7	78.5	80.7	84.9	92.1	101.7	117.0	138.8	173.4	221.3	277.6
117.5°	86.8	88.3	90.4	94.2	101.1	111.1	125.2	145.6	176.0	217.8	266.9
120°	93.1	94.5	96.7	99.9	107.0	117.0	131.0	150.3	177.7	215.9	261.2
122.5°	99.2	100.3	102.4	105.9	113.0	123.3	136.3	154.2	179.7	214.7	256.3
125°	107.0	108.2	110.3	114.5	121.7	131.7	144.5	160.6	182.7	212.7	249.4
127.5°	113.3	114.7	117.8	122.5	129.3	139.6	152.1	166.5	185.7	211.5	243.0
130°	117.0	118.5	122.0	127.0	134.2	144.1	156.6	170.2	188.0	210.9	238.7
132.5°	120.5	122.2	126.0	131.3	138.8	148.8	160.7	173.9	190.4	210.6	235.3
135°	125.6	127.0	131.3	136.6	144.9	154.8	166.3	178.7	193.1	210.2	230.5
137.5°	130.5	132.2	136.4	142.2	150.3	159.6	170.9	182.5	195.5	210.1	227.1
140°	134.2	135.6	139.9	145.6	153.4	162.7	173.4	184.5	196.6	209.8	225.1
142.5°	137.8	139.1	143.0	148.8	156.3	165.0	175.4	186.2	197.4	209.8	223.2
145°	143.4	144.9	148.5	153.8	161.0	168.7	178.4	188.4	198.3	209.0	220.6
147.5°	149.5	150.5	153.9	158.9	164.8	171.8	180.9	189.7	198.6	207.8	217.8
150°	153.4	154.5	157.3	162.0	167.3	173.8	182.0	190.2	198.3	206.9	215.5
152.5°	157.4	157.9	160.8	164.8	170.0	175.7	183.1	190.5	197.8	205.5	213.5
155°	163.1	163.4	165.5	169.5	173.4	178.7	184.8	190.9	196.9	203.0	209.8
157.5°	167.7	168.1	169.9	173.3	176.4	180.9	186.0	190.9	195.3	200.5	206.3
160°	170.9	171.3	172.7	175.5	178.4	182.4	186.6	190.9	194.5	198.7	203.7
162.5°	174.1	173.8	175.3	177.5	180.2	183.2	186.9	190.6	193.6	197.3	201.5
165°	177.7	177.3	178.0	180.2	182.0	184.1	187.3	189.9	192.0	194.5	197.6
167.5°	180.7	180.3	180.9	182.3	183.6	184.9	187.2	189.3	190.4	192.0	194.0
170°	182.7	182.0	182.4	183.4	184.1	185.2	186.9	188.7	189.5	190.6	192.0
172.5°	183.8	183.4	183.2	184.3	184.7	185.5	186.7	187.9	188.3	188.8	190.0
175°	185.2	184.8	184.5	185.2	185.2	185.5	186.2	186.9	186.6	186.9	187.3
177.5°	185.8	185.2	185.0	185.5	185.5	185.5	185.8	186.4	185.8	185.5	185.8
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331383-840

CATALOG NUMBER: SA2XXDIP-C865D330U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6
2.5°	1387.7	1390.1	1392.4	1393.4	1392.9	1392.4	1392.0	1391.5
5°	1378.3	1380.7	1383.1	1383.9	1383.4	1382.8	1382.2	1381.6
7.5°	1362.7	1365.1	1367.6	1368.4	1367.8	1367.1	1366.4	1365.7
10°	1348.8	1351.2	1353.6	1354.3	1353.4	1352.5	1351.6	1350.8
12.5°	1332.4	1334.0	1335.7	1336.3	1335.5	1334.9	1334.2	1333.6
15°	1303.5	1304.7	1306.0	1305.8	1304.3	1302.8	1301.3	1299.8
17.5°	1269.3	1270.7	1272.1	1272.0	1270.6	1269.2	1267.8	1266.4
20°	1242.6	1243.5	1244.5	1244.3	1243.1	1241.9	1240.7	1239.5
22.5°	1214.5	1214.6	1214.8	1214.6	1213.8	1213.0	1212.3	1211.6
25°	1168.4	1168.9	1169.5	1169.5	1168.9	1168.4	1167.8	1167.2
27.5°	1123.1	1122.2	1121.3	1120.1	1118.6	1117.2	1115.8	1114.4
30°	1087.6	1086.8	1085.9	1084.8	1083.7	1082.5	1081.3	1080.1
32.5°	1053.0	1051.4	1049.8	1048.3	1047.2	1046.0	1044.8	1043.6
35°	997.4	995.6	993.9	992.2	990.8	989.3	987.7	986.2
37.5°	941.7	939.5	937.3	935.4	934.0	932.6	931.2	929.7
40°	903.2	900.5	897.9	895.9	894.7	893.5	892.3	891.1
42.5°	865.2	862.2	859.4	857.1	855.4	853.7	852.0	850.4
45°	806.9	803.5	800.3	798.1	796.9	795.7	794.5	793.3
47.5°	746.2	742.8	739.3	736.7	735.0	733.3	731.5	729.8
50°	707.2	703.1	698.9	696.1	694.6	693.1	691.7	690.1
52.5°	666.8	663.4	659.9	657.2	655.3	653.3	651.4	649.3
55°	606.6	603.0	599.5	596.9	595.4	593.9	592.5	591.0
57.5°	544.0	540.5	536.9	534.6	533.5	532.4	531.3	530.1
60°	502.7	499.4	496.1	494.0	493.1	492.2	491.3	490.5
62.5°	463.4	460.4	457.4	455.3	454.1	453.0	451.9	450.8
65°	403.3	400.7	398.0	395.9	394.5	392.9	391.4	389.9
67.5°	344.0	341.8	339.8	338.2	337.0	335.8	334.6	333.4
70°	305.4	303.3	301.2	299.5	298.4	297.2	296.0	294.8
72.5°	268.9	266.8	264.8	263.3	262.3	261.4	260.3	259.4
75°	212.2	210.4	208.6	208.0	208.6	209.2	209.7	210.4
77.5°	161.5	160.6	159.7	158.8	157.9	157.1	156.3	155.4
80°	128.2	127.3	126.4	125.6	125.0	124.5	123.9	123.3
82.5°	95.5	94.4	93.3	92.7	92.5	92.4	92.3	92.2
85°	50.5	49.6	48.7	48.1	47.8	47.5	47.2	46.9
87.5°	15.9	15.0	14.4	14.0	13.8	13.5	13.3	13.0
90°	11.4	10.7	11.4	11.8	11.8	11.8	11.8	11.8
92.5°	31.1	26.7	23.7	21.5	21.2	20.1	20.3	19.8
95°	93.5	71.7	56.8	48.9	44.2	41.4	40.3	40.7
97.5°	218.1	178.4	139.9	114.1	97.0	88.3	83.1	80.1
100°	325.8	281.6	232.7	189.5	159.9	144.5	134.2	127.7
102.5°	396.3	386.3	350.5	304.8	272.6	246.4	233.5	224.8
105°	433.5	473.8	478.5	466.8	444.5	422.4	407.1	402.1
107.5°	406.7	467.5	504.5	521.8	524.6	523.4	520.3	513.7
110°	383.5	447.5	493.1	522.4	537.8	544.5	547.8	547.3



TEST NUMBER: P331383-840

CATALOG NUMBER: SA2XXDIP-C865D330U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	362.4	423.7	472.5	506.1	527.5	538.8	544.8	546.7
115°	336.5	391.4	438.2	474.9	500.3	516.6	525.9	529.2
117.5°	316.9	365.2	407.6	442.0	467.9	485.2	494.9	497.7
120°	307.2	351.4	389.3	421.7	446.8	463.5	473.8	477.5
122.5°	299.5	340.0	375.9	405.2	427.6	444.1	453.3	456.3
125°	288.3	325.1	356.5	383.2	403.9	417.5	426.4	429.3
127.5°	277.2	310.5	340.1	364.8	382.8	395.6	403.2	405.6
130°	270.1	300.8	329.0	352.5	370.0	382.1	389.3	392.1
132.5°	263.3	291.6	317.6	339.7	356.9	369.0	375.6	378.2
135°	253.7	277.2	300.8	320.7	336.1	347.9	354.4	355.8
137.5°	246.1	265.8	284.5	301.8	315.9	326.0	331.6	333.8
140°	241.2	258.3	274.8	290.4	301.8	311.1	316.5	318.6
142.5°	237.2	251.8	265.9	279.0	289.8	298.3	303.1	303.5
145°	231.6	243.4	254.4	264.8	273.3	279.4	283.0	284.0
147.5°	227.2	236.5	245.1	252.7	259.7	264.6	267.0	267.7
150°	224.1	232.0	239.4	245.8	251.2	255.5	257.6	258.0
152.5°	221.0	228.2	234.6	240.1	244.4	248.0	249.6	249.7
155°	216.6	222.3	227.6	231.6	235.5	238.0	239.4	238.7
157.5°	211.6	216.3	220.8	223.9	226.6	228.7	229.3	229.3
160°	208.3	212.3	216.2	218.7	221.3	223.0	223.4	223.4
162.5°	205.2	208.6	212.0	213.9	216.4	217.6	217.9	217.6
165°	200.6	203.0	205.5	206.9	208.3	209.8	209.8	209.4
167.5°	196.0	197.9	199.7	201.0	201.6	202.4	202.3	201.9
170°	193.8	194.8	196.2	196.9	197.3	198.3	198.0	197.3
172.5°	191.2	192.0	193.1	193.5	193.9	194.4	194.0	193.6
175°	188.4	188.7	189.1	189.5	189.5	189.9	189.5	188.7
177.5°	186.4	186.4	186.7	186.7	186.7	186.7	186.4	185.8
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5

(END OF REPORT)