

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332899-927

Luminaire Tested: **SA4XXRDIP-C575D365U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332899-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C575D365U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2865.4 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332899-927
CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332899-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	101	97	93	90	95	92	88	85	81	78	76	71	69	68	62	61	60	55
2	93	85	79	74	87	80	75	70	71	67	64	63	60	57	55	53	51	47
3	85	75	68	62	79	71	65	59	63	58	54	56	52	49	49	46	44	40
4	78	67	59	53	73	63	56	51	56	51	46	50	46	42	44	41	38	35
5	72	60	52	46	67	57	49	44	51	45	40	45	40	37	40	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	27
7	61	49	41	35	58	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	45	37	31	54	42	35	30	38	32	28	34	29	26	31	27	24	21
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19
10	50	38	30	25	47	36	29	25	32	27	23	29	25	21	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6500	6500	6500
5°	6514	6434	6474
10°	6473	6357	6357
15°	6399	6224	6177
20°	6296	6048	5936
25°	6167	5842	5694
30°	6039	5626	5390
35°	5899	5401	5084
40°	5730	5145	4755
45°	5574	4891	4419
50°	5397	4598	4064
55°	5206	4294	3678
60°	4996	3961	3284
65°	4804	3543	2896
70°	4525	3085	2460
75°	4173	2558	1999
80°	3640	1948	1836
85°	3084	1769	1658



TEST NUMBER: P332899-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.6	2.6
10°-20°	210.9	7.4
20°-30°	304.5	10.6
30°-40°	345.2	12.0
40°-50°	333.3	11.6
50°-60°	277.2	9.7
60°-70°	191.4	6.7
70°-80°	97.0	3.4
80°-90°	26.0	0.9
90°-100°	23.9	0.8
100°-110°	70.7	2.5
110°-120°	120.0	4.2
120°-130°	158.3	5.5
130°-140°	177.8	6.2
140°-150°	174.7	6.1
150°-160°	146.9	5.1
160°-170°	97.7	3.4
170°-180°	34.2	1.2
0°-30°	591.0	20.6
0°-40°	936.2	32.7
0°-60°	1546.7	54.0
0°-90°	1861.1	65.0
90°-120°	214.6	7.5
90°-150°	725.3	25.3
90°-180°	1004.0	35.0
0°-180°	2865.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	805	805	805	805	805	
5°	804	801	794	800	799	76
15°	766	760	745	743	739	216
25°	692	680	656	646	639	319
35°	599	578	548	528	516	374
45°	488	465	428	399	387	376
55°	370	344	305	274	261	331
65°	252	224	186	160	152	248
75°	134	111	82	68	64	141
85°	33	22	19	18	18	37
90°	1	4	6	8	8	3
95°	17	19	21	22	22	19
105°	65	66	67	67	68	69
115°	122	122	122	121	121	120
125°	178	178	177	177	176	158
135°	229	231	231	230	230	177
145°	278	280	280	280	279	174
155°	319	319	319	320	319	147
165°	347	347	346	348	347	98
175°	361	360	360	362	360	34
180°	362	362	362	362	362	



TEST NUMBER: P332899-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1
2.5°	807.1	806.6	806.2	805.7	805.3	804.5	803.3	802.1	800.8	799.6	800.8
5°	803.8	803.3	802.7	802.2	801.7	800.6	798.9	797.3	795.6	794.0	795.4
7.5°	796.5	796.0	795.4	794.9	794.2	792.9	790.8	788.6	786.5	784.3	785.2
10°	789.6	789.0	788.3	787.6	787.0	785.4	782.9	780.4	777.9	775.5	776.0
12.5°	780.8	780.0	779.2	778.4	777.6	775.8	772.9	769.9	767.1	764.1	764.5
15°	765.6	764.4	763.2	761.9	760.7	758.4	754.9	751.5	748.1	744.7	744.4
17.5°	747.3	745.4	743.7	741.9	740.1	737.2	733.1	729.0	724.8	720.7	720.0
20°	732.9	731.2	729.4	727.6	725.8	722.6	718.0	713.3	708.6	704.0	702.9
22.5°	717.2	715.2	713.2	711.1	709.2	705.7	700.7	695.7	690.7	685.7	684.0
25°	692.3	689.8	687.3	684.8	682.4	678.3	672.7	667.1	661.5	655.9	653.6
27.5°	666.1	663.1	660.0	656.9	653.7	649.2	643.2	637.2	631.2	625.2	622.3
30°	647.8	644.4	641.0	637.6	634.2	629.2	622.8	616.4	609.9	603.5	600.1
32.5°	628.7	624.8	620.9	617.0	613.2	607.9	601.3	594.6	588.0	581.3	577.3
35°	598.6	594.2	589.8	585.4	581.1	575.4	568.5	561.7	554.8	548.0	543.4
37.5°	566.4	561.9	557.4	552.9	548.3	542.2	534.6	527.0	519.5	511.9	506.7
40°	543.7	539.2	534.6	530.1	525.6	519.4	511.7	503.8	496.1	488.2	482.4
42.5°	522.0	517.3	512.5	507.8	503.0	496.6	488.5	480.3	472.2	464.1	458.2
45°	488.2	483.2	478.1	473.0	467.9	461.3	453.0	444.9	436.7	428.4	421.7
47.5°	453.4	448.1	442.8	437.6	432.4	425.5	416.9	408.4	399.9	391.3	384.4
50°	429.7	424.3	419.0	413.6	408.3	401.2	392.4	383.7	374.9	366.1	359.3
52.5°	405.5	400.3	395.1	389.8	384.5	377.5	368.4	359.5	350.5	341.5	334.5
55°	369.9	364.4	358.9	353.4	347.9	340.7	331.8	323.0	314.0	305.1	298.0
57.5°	334.6	328.9	323.2	317.5	311.8	304.6	295.8	287.0	278.3	269.5	262.3
60°	309.4	304.0	298.5	293.0	287.6	280.4	271.6	262.8	254.1	245.3	238.2
62.5°	286.8	281.1	275.4	269.7	264.0	256.7	247.6	238.7	229.7	220.7	214.1
65°	251.5	245.7	239.7	233.9	227.9	220.6	211.8	203.1	194.3	185.5	179.7
67.5°	214.9	209.2	203.6	198.0	192.3	185.4	177.3	169.1	161.1	152.9	147.8
70°	191.7	185.9	180.2	174.4	168.7	161.9	154.1	146.3	138.5	130.7	126.2
72.5°	167.1	161.8	156.6	151.5	146.2	140.0	132.6	125.2	117.8	110.4	106.6
75°	133.8	128.7	123.7	118.6	113.5	107.7	101.3	94.8	88.4	82.0	78.8
77.5°	100.0	95.7	91.4	87.1	82.8	78.0	72.8	67.7	62.4	57.2	55.4
80°	78.3	74.3	70.3	66.4	62.4	58.4	54.3	50.1	46.0	41.9	41.5
82.5°	59.6	55.9	52.3	48.6	45.0	42.0	39.6	37.2	34.9	32.6	32.2
85°	33.3	30.6	27.8	25.0	22.3	20.8	20.4	20.0	19.5	19.1	18.9
87.5°	11.5	10.8	10.1	9.3	8.6	8.2	8.2	8.2	8.2	8.2	8.1
90°	0.9	1.5	2.2	2.9	3.6	4.2	4.7	5.1	5.6	6.2	6.5
92.5°	6.0	6.8	7.5	8.3	9.1	9.7	10.1	10.4	10.8	11.1	11.3
95°	16.8	17.3	17.9	18.5	19.0	19.6	20.0	20.4	20.8	21.3	21.5
97.5°	29.3	29.8	30.3	30.7	31.1	31.6	32.1	32.6	33.1	33.7	33.9
100°	39.2	39.5	39.7	39.9	40.2	40.6	41.1	41.7	42.3	42.9	42.9
102.5°	49.5	49.6	49.7	49.8	49.9	50.2	50.7	51.3	51.7	52.2	52.4
105°	65.2	65.3	65.4	65.4	65.4	65.6	65.9	66.1	66.4	66.6	66.8
107.5°	81.8	81.8	81.9	82.0	82.1	82.1	82.1	82.1	82.2	82.2	82.4
110°	92.9	93.1	93.2	93.3	93.4	93.5	93.4	93.3	93.2	93.2	93.1



TEST NUMBER: P332899-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	104.6	104.6	104.6	104.6	104.6	104.6	104.5	104.4	104.3	104.2	104.2
115°	122.1	122.1	122.1	122.1	122.1	122.0	121.8	121.8	121.6	121.5	121.4
117.5°	138.5	138.6	138.6	138.6	138.7	138.7	138.6	138.6	138.4	138.3	138.2
120°	149.5	149.7	150.0	150.2	150.5	150.5	150.4	150.1	150.0	149.8	149.5
122.5°	160.9	161.0	161.1	161.2	161.3	161.3	161.2	161.1	161.1	161.0	160.7
125°	177.8	177.8	177.8	177.8	177.8	177.7	177.7	177.6	177.5	177.4	177.4
127.5°	193.1	193.2	193.5	193.6	193.8	193.8	193.8	193.6	193.5	193.5	193.3
130°	203.8	204.0	204.1	204.4	204.5	204.6	204.6	204.6	204.6	204.6	204.5
132.5°	214.8	214.9	215.0	215.2	215.3	215.3	215.3	215.2	215.2	215.2	215.0
135°	229.3	229.7	230.0	230.4	230.8	230.9	230.9	230.9	230.9	230.9	230.8
137.5°	245.0	245.3	245.4	245.6	245.7	245.9	246.0	246.1	246.2	246.3	246.1
140°	255.6	255.7	255.8	256.0	256.1	256.1	256.1	256.1	256.1	256.1	256.1
142.5°	265.2	265.3	265.5	265.5	265.7	265.8	265.7	265.6	265.6	265.5	265.5
145°	278.5	278.8	279.0	279.2	279.6	279.7	279.7	279.8	279.9	280.0	279.9
147.5°	291.8	292.1	292.3	292.6	292.9	293.0	293.0	292.9	292.9	292.9	292.8
150°	299.8	300.1	300.3	300.6	300.8	301.0	301.0	301.0	301.0	301.0	301.0
152.5°	307.4	307.6	307.7	307.8	308.0	308.1	308.2	308.2	308.2	308.3	308.5
155°	319.1	319.1	319.1	319.1	319.1	319.1	319.0	318.9	318.9	318.9	319.1
157.5°	329.0	328.8	328.8	328.7	328.5	328.4	328.4	328.4	328.4	328.4	328.6
160°	334.8	334.7	334.7	334.6	334.5	334.5	334.5	334.4	334.3	334.2	334.5
162.5°	340.2	340.0	339.8	339.7	339.5	339.5	339.4	339.3	339.2	339.1	339.5
165°	347.4	347.2	347.1	346.8	346.7	346.5	346.3	346.3	346.1	346.0	346.3
167.5°	352.9	352.7	352.4	352.1	351.9	351.7	351.8	351.8	351.8	351.8	352.2
170°	356.1	355.8	355.5	355.1	354.8	354.7	354.7	354.8	354.9	355.0	355.3
172.5°	358.3	358.1	357.7	357.5	357.3	357.1	357.1	357.2	357.2	357.2	357.6
175°	361.4	361.1	360.8	360.4	360.1	360.0	359.9	359.8	359.8	359.7	360.1
177.5°	362.4	362.2	361.9	361.6	361.4	361.3	361.3	361.3	361.3	361.3	361.6
180°	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9



TEST NUMBER: P332899-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1
2.5°	802.1	803.3	804.5	805.0	804.9	804.8	804.7	804.6
5°	796.7	798.1	799.5	800.0	799.7	799.5	799.2	798.9
7.5°	786.1	787.0	787.9	788.1	787.7	787.2	786.8	786.3
10°	776.6	777.1	777.7	777.7	777.1	776.6	776.0	775.5
12.5°	764.8	765.1	765.5	765.2	764.5	763.7	763.0	762.2
15°	744.1	743.9	743.5	743.0	742.0	741.0	740.1	739.1
17.5°	719.2	718.4	717.6	716.5	715.1	713.7	712.2	710.7
20°	701.8	700.7	699.6	698.2	696.4	694.6	692.8	691.0
22.5°	682.5	680.8	679.1	677.6	676.1	674.7	673.3	671.8
25°	651.3	648.9	646.6	644.8	643.3	642.0	640.6	639.2
27.5°	619.4	616.6	613.7	611.2	609.3	607.3	605.4	603.4
30°	596.7	593.2	589.8	587.0	584.8	582.6	580.4	578.2
32.5°	573.4	569.4	565.4	562.4	560.3	558.3	556.1	554.1
35°	538.7	534.0	529.4	525.9	523.4	520.9	518.4	515.9
37.5°	501.5	496.3	491.1	487.3	484.7	482.3	479.8	477.4
40°	476.7	471.0	465.2	461.1	458.6	456.1	453.7	451.2
42.5°	452.3	446.5	440.6	436.4	433.8	431.3	428.6	426.1
45°	415.0	408.3	401.6	397.0	394.5	392.1	389.6	387.1
47.5°	377.4	370.4	363.5	358.6	355.9	353.2	350.5	347.8
50°	352.4	345.6	338.7	334.1	331.4	328.8	326.2	323.6
52.5°	327.6	320.6	313.7	308.9	306.1	303.4	300.7	298.0
55°	290.9	283.8	276.6	271.8	269.2	266.6	264.0	261.3
57.5°	255.0	247.8	240.6	236.0	234.0	232.0	230.0	228.1
60°	231.1	223.9	216.8	212.2	210.0	207.8	205.7	203.4
62.5°	207.6	201.0	194.4	190.2	188.5	186.7	185.0	183.2
65°	173.8	167.9	162.0	158.2	156.6	155.0	153.3	151.6
67.5°	142.8	137.7	132.6	129.2	127.4	125.6	123.7	121.9
70°	121.7	117.2	112.6	109.6	108.3	106.9	105.5	104.2
72.5°	102.7	98.9	95.0	92.4	91.2	89.9	88.6	87.4
75°	75.7	72.6	69.4	67.4	66.5	65.8	65.0	64.1
77.5°	53.6	51.7	49.8	48.8	48.6	48.3	48.1	47.8
80°	41.1	40.7	40.2	40.0	39.8	39.7	39.6	39.5
82.5°	31.9	31.6	31.4	31.1	31.0	30.8	30.7	30.6
85°	18.5	18.3	18.0	17.9	17.9	17.9	17.9	17.9
87.5°	8.1	8.0	8.0	8.1	8.2	8.3	8.5	8.6
90°	6.9	7.3	7.7	7.9	8.0	8.2	8.2	8.4
92.5°	11.6	11.7	12.0	12.1	12.2	12.3	12.4	12.4
95°	21.6	21.9	22.0	22.1	22.1	22.1	22.1	22.1
97.5°	34.1	34.3	34.5	34.6	34.6	34.6	34.6	34.6
100°	43.1	43.2	43.3	43.4	43.4	43.4	43.4	43.4
102.5°	52.6	52.8	52.9	53.1	53.1	53.2	53.2	53.2
105°	67.0	67.2	67.3	67.6	67.7	68.0	68.1	68.3
107.5°	82.6	82.8	82.9	83.0	83.0	83.0	83.0	82.9
110°	93.0	92.8	92.7	92.8	92.9	93.2	93.3	93.5



TEST NUMBER: P332899-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	104.2	104.1	104.1	104.1	104.2	104.2	104.2	104.3
115°	121.4	121.3	121.2	121.2	121.1	121.0	121.0	121.0
117.5°	137.9	137.7	137.5	137.4	137.2	137.0	137.0	136.8
120°	149.2	148.9	148.5	148.5	148.5	148.7	148.8	148.9
122.5°	160.6	160.3	160.1	159.9	159.7	159.5	159.2	159.0
125°	177.2	177.1	177.0	176.8	176.7	176.6	176.5	176.3
127.5°	193.2	193.1	192.9	192.8	192.7	192.7	192.5	192.4
130°	204.4	204.2	204.1	203.9	203.7	203.4	203.2	203.0
132.5°	214.9	214.8	214.7	214.5	214.4	214.4	214.3	214.1
135°	230.7	230.6	230.4	230.3	230.1	229.9	229.7	229.6
137.5°	246.0	245.8	245.7	245.6	245.6	245.7	245.7	245.7
140°	256.0	256.0	255.9	255.8	255.8	255.7	255.6	255.6
142.5°	265.5	265.5	265.5	265.5	265.5	265.5	265.5	265.5
145°	279.8	279.7	279.7	279.6	279.4	279.2	279.0	278.8
147.5°	292.8	292.7	292.6	292.6	292.6	292.5	292.4	292.4
150°	301.0	301.0	301.0	300.9	300.9	300.8	300.7	300.6
152.5°	308.6	308.8	309.0	308.9	308.7	308.6	308.4	308.2
155°	319.3	319.6	319.8	319.8	319.6	319.3	319.1	318.9
157.5°	328.8	329.0	329.2	329.2	328.9	328.8	328.5	328.3
160°	334.6	334.8	335.0	334.9	334.6	334.3	334.0	333.7
162.5°	339.8	340.2	340.5	340.5	340.2	339.9	339.6	339.3
165°	346.7	347.1	347.5	347.5	347.3	347.1	346.8	346.6
167.5°	352.6	352.9	353.3	353.3	352.9	352.5	352.1	351.7
170°	355.7	356.1	356.5	356.4	356.0	355.5	355.1	354.7
172.5°	358.1	358.5	358.9	358.9	358.5	358.0	357.6	357.1
175°	360.6	361.0	361.5	361.5	361.0	360.6	360.1	359.7
177.5°	361.9	362.3	362.7	362.7	362.3	361.9	361.5	361.1
180°	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9

(END OF REPORT)