

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332900-927

Luminaire Tested: **SA4XXRDIP-C575D365U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332900-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C575D365U927-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2897.3 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332900-927
CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332900-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	60	59	55
2	93	85	79	74	87	80	75	70	71	67	63	63	59	57	55	52	50	46
3	85	75	68	62	79	71	64	59	63	58	54	56	52	48	49	46	43	40
4	78	67	59	53	73	63	56	51	56	51	46	50	45	42	44	40	38	34
5	71	60	52	46	67	57	49	44	51	45	40	45	40	36	40	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	26
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6500	6500	6500
5°	6514	6434	6474
10°	6473	6357	6357
15°	6399	6224	6177
20°	6296	6048	5936
25°	6167	5842	5694
30°	6039	5626	5390
35°	5899	5401	5084
40°	5730	5145	4755
45°	5574	4891	4419
50°	5397	4598	4064
55°	5206	4294	3678
60°	4996	3961	3284
65°	4804	3543	2896
70°	4525	3085	2460
75°	4173	2558	1999
80°	3640	1948	1836
85°	3084	1769	1658



TEST NUMBER: P332900-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.6	2.6
10°-20°	210.9	7.3
20°-30°	304.5	10.5
30°-40°	345.2	11.9
40°-50°	333.3	11.5
50°-60°	277.2	9.6
60°-70°	191.4	6.6
70°-80°	97.0	3.3
80°-90°	25.7	0.9
90°-100°	102.9	3.6
100°-110°	214.2	7.4
110°-120°	191.9	6.6
120°-130°	161.4	5.6
130°-140°	134.6	4.6
140°-150°	102.8	3.5
150°-160°	72.3	2.5
160°-170°	42.5	1.5
170°-180°	13.8	0.5
0°-30°	591.0	20.4
0°-40°	936.2	32.3
0°-60°	1546.7	53.4
0°-90°	1860.8	64.2
90°-120°	509.0	17.6
90°-150°	907.8	31.3
90°-180°	1036.0	35.8
0°-180°	2897.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	805	805	805	805	805	
5°	804	801	794	800	799	76
15°	766	760	745	743	739	216
25°	692	680	656	646	639	319
35°	599	578	548	528	516	374
45°	488	465	428	399	387	376
55°	370	344	305	274	261	331
65°	252	224	186	160	152	248
75°	134	111	82	68	64	141
85°	33	22	19	18	18	37
90°	0	2	5	6	6	2
95°	9	29	228	113	68	10
105°	33	47	184	396	394	35
115°	58	72	164	315	378	57
125°	80	96	163	268	302	72
135°	96	114	162	238	270	74
145°	110	126	161	200	220	69
155°	125	135	156	177	184	58
165°	136	141	150	159	161	38
175°	142	142	144	146	145	13
180°	142	142	142	142	142	



TEST NUMBER: P332900-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1
2.5°	807.1	806.6	806.2	805.7	805.3	804.5	803.3	802.1	800.8	799.6	800.8
5°	803.8	803.3	802.7	802.2	801.7	800.6	798.9	797.3	795.6	794.0	795.4
7.5°	796.5	796.0	795.4	794.9	794.2	792.9	790.8	788.6	786.5	784.3	785.2
10°	789.6	789.0	788.3	787.6	787.0	785.4	782.9	780.4	777.9	775.5	776.0
12.5°	780.8	780.0	779.2	778.4	777.6	775.8	772.9	769.9	767.1	764.1	764.5
15°	765.6	764.4	763.2	761.9	760.7	758.4	754.9	751.5	748.1	744.7	744.4
17.5°	747.3	745.4	743.7	741.9	740.1	737.2	733.1	729.0	724.8	720.7	720.0
20°	732.9	731.2	729.4	727.6	725.8	722.6	718.0	713.3	708.6	704.0	702.9
22.5°	717.2	715.2	713.2	711.1	709.2	705.7	700.7	695.7	690.7	685.7	684.0
25°	692.3	689.8	687.3	684.8	682.4	678.3	672.7	667.1	661.5	655.9	653.6
27.5°	666.1	663.1	660.0	656.9	653.7	649.2	643.2	637.2	631.2	625.2	622.3
30°	647.8	644.4	641.0	637.6	634.2	629.2	622.8	616.4	609.9	603.5	600.1
32.5°	628.7	624.8	620.9	617.0	613.2	607.9	601.3	594.6	588.0	581.3	577.3
35°	598.6	594.2	589.8	585.4	581.1	575.4	568.5	561.7	554.8	548.0	543.4
37.5°	566.4	561.9	557.4	552.9	548.3	542.2	534.6	527.0	519.5	511.9	506.7
40°	543.7	539.2	534.6	530.1	525.6	519.4	511.7	503.8	496.1	488.2	482.4
42.5°	522.0	517.3	512.5	507.8	503.0	496.6	488.5	480.3	472.2	464.1	458.2
45°	488.2	483.2	478.1	473.0	467.9	461.3	453.0	444.9	436.7	428.4	421.7
47.5°	453.4	448.1	442.8	437.6	432.4	425.5	416.9	408.4	399.9	391.3	384.4
50°	429.7	424.3	419.0	413.6	408.3	401.2	392.4	383.7	374.9	366.1	359.3
52.5°	405.5	400.3	395.1	389.8	384.5	377.5	368.4	359.5	350.5	341.5	334.5
55°	369.9	364.4	358.9	353.4	347.9	340.7	331.8	323.0	314.0	305.1	298.0
57.5°	334.6	328.9	323.2	317.5	311.8	304.6	295.8	287.0	278.3	269.5	262.3
60°	309.4	304.0	298.5	293.0	287.6	280.4	271.6	262.8	254.1	245.3	238.2
62.5°	286.8	281.1	275.4	269.7	264.0	256.7	247.6	238.7	229.7	220.7	214.1
65°	251.5	245.7	239.7	233.9	227.9	220.6	211.8	203.1	194.3	185.5	179.7
67.5°	214.9	209.2	203.6	198.0	192.3	185.4	177.3	169.1	161.1	152.9	147.8
70°	191.7	185.9	180.2	174.4	168.7	161.9	154.1	146.3	138.5	130.7	126.2
72.5°	167.1	161.8	156.6	151.5	146.2	140.0	132.6	125.2	117.8	110.4	106.6
75°	133.8	128.7	123.7	118.6	113.5	107.7	101.3	94.8	88.4	82.0	78.8
77.5°	100.0	95.7	91.4	87.1	82.8	78.0	72.8	67.7	62.4	57.2	55.4
80°	78.3	74.3	70.3	66.4	62.4	58.4	54.3	50.1	46.0	41.9	41.5
82.5°	59.6	55.9	52.3	48.6	45.0	42.0	39.6	37.2	34.9	32.6	32.2
85°	33.3	30.6	27.8	25.0	22.3	20.8	20.4	20.0	19.5	19.1	18.9
87.5°	11.4	10.6	9.9	9.1	8.3	7.8	8.0	7.9	7.9	7.9	7.8
90°	0.3	0.9	1.7	2.0	2.2	2.2	3.9	3.9	4.5	5.1	4.8
92.5°	3.2	4.7	7.3	10.7	14.8	20.6	34.9	56.6	77.7	88.8	74.0
95°	9.3	10.1	12.9	16.6	23.2	35.0	59.3	105.3	172.2	228.1	234.6
97.5°	16.6	16.6	19.0	22.3	28.1	37.9	56.7	94.7	161.1	240.3	294.8
100°	21.3	21.3	23.2	26.6	31.9	40.9	57.4	89.0	146.2	225.1	296.8
102.5°	25.7	26.2	28.0	31.1	36.2	44.7	59.7	87.5	136.1	206.0	280.0
105°	32.8	33.6	35.0	38.3	43.4	51.5	65.0	88.2	127.4	183.6	249.5
107.5°	40.5	41.0	42.5	46.0	50.9	58.9	71.1	92.4	125.8	171.1	224.8
110°	45.6	46.2	47.6	50.9	56.0	63.5	75.9	95.5	126.3	166.8	212.5



TEST NUMBER: P332900-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	50.5	51.1	52.8	55.8	60.9	68.4	80.3	98.9	127.6	164.9	205.6
115°	57.7	58.5	60.4	63.3	68.6	76.1	87.4	104.2	130.2	163.8	199.1
117.5°	65.0	65.8	67.6	70.7	75.7	83.5	94.1	109.6	132.9	163.5	196.1
120°	70.0	70.6	72.5	75.6	80.3	88.2	98.9	113.4	135.0	163.5	194.6
122.5°	74.5	75.0	77.0	79.9	85.1	92.7	103.3	117.0	137.0	163.3	192.8
125°	80.3	81.4	83.2	86.3	91.6	99.4	109.5	122.3	140.0	163.0	189.8
127.5°	85.6	86.4	88.5	92.0	97.5	105.4	115.2	127.0	142.4	162.3	185.8
130°	88.5	89.6	91.8	96.0	101.3	109.5	119.0	129.9	144.2	162.1	183.4
132.5°	91.4	92.3	95.2	99.2	105.0	112.6	122.2	132.8	145.8	161.9	181.2
135°	95.5	96.6	99.4	104.2	110.0	117.3	126.5	136.7	148.1	161.5	177.8
137.5°	99.6	100.6	103.7	108.2	114.3	121.3	129.9	139.3	149.5	161.5	174.9
140°	102.5	103.3	106.4	111.1	117.0	123.7	132.1	141.1	150.6	161.3	173.3
142.5°	105.6	106.5	109.3	113.8	119.5	126.0	134.2	142.4	151.5	161.3	172.0
145°	110.0	110.9	113.7	117.6	122.9	129.0	136.3	143.9	152.0	160.7	169.7
147.5°	115.0	115.3	117.8	121.8	126.2	131.7	138.6	145.2	152.3	159.7	167.6
150°	118.1	118.4	120.6	124.1	128.3	133.6	139.7	145.8	152.3	159.0	166.0
152.5°	121.0	121.1	123.3	126.5	130.2	135.1	140.6	146.3	151.9	157.9	164.2
155°	125.2	125.4	127.1	129.9	133.0	137.2	142.0	146.7	151.2	156.2	161.5
157.5°	129.1	129.1	130.7	132.8	135.5	138.9	142.9	146.7	150.4	154.5	158.8
160°	131.6	131.6	132.7	134.7	136.9	140.0	143.4	146.7	149.8	153.1	156.8
162.5°	133.8	133.6	134.5	136.3	138.2	140.7	143.8	146.7	149.1	151.8	155.0
165°	136.3	136.3	136.9	138.3	139.7	141.4	143.9	146.2	147.8	149.8	152.0
167.5°	138.9	138.6	138.9	139.9	140.7	142.0	143.9	145.4	146.5	147.7	149.3
170°	140.0	139.7	140.0	140.9	141.4	142.2	143.6	145.0	145.6	146.4	147.6
172.5°	141.1	140.9	140.9	141.5	141.8	142.4	143.4	144.6	144.7	145.0	146.0
175°	142.2	142.0	142.0	142.2	142.5	142.5	143.1	143.9	143.6	143.6	144.2
177.5°	142.8	142.5	142.3	142.5	142.5	142.5	142.8	143.1	142.8	142.8	143.0
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332900-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1
2.5°	802.1	803.3	804.5	805.0	804.9	804.8	804.7	804.6
5°	796.7	798.1	799.5	800.0	799.7	799.5	799.2	798.9
7.5°	786.1	787.0	787.9	788.1	787.7	787.2	786.8	786.3
10°	776.6	777.1	777.7	777.7	777.1	776.6	776.0	775.5
12.5°	764.8	765.1	765.5	765.2	764.5	763.7	763.0	762.2
15°	744.1	743.9	743.5	743.0	742.0	741.0	740.1	739.1
17.5°	719.2	718.4	717.6	716.5	715.1	713.7	712.2	710.7
20°	701.8	700.7	699.6	698.2	696.4	694.6	692.8	691.0
22.5°	682.5	680.8	679.1	677.6	676.1	674.7	673.3	671.8
25°	651.3	648.9	646.6	644.8	643.3	642.0	640.6	639.2
27.5°	619.4	616.6	613.7	611.2	609.3	607.3	605.4	603.4
30°	596.7	593.2	589.8	587.0	584.8	582.6	580.4	578.2
32.5°	573.4	569.4	565.4	562.4	560.3	558.3	556.1	554.1
35°	538.7	534.0	529.4	525.9	523.4	520.9	518.4	515.9
37.5°	501.5	496.3	491.1	487.3	484.7	482.3	479.8	477.4
40°	476.7	471.0	465.2	461.1	458.6	456.1	453.7	451.2
42.5°	452.3	446.5	440.6	436.4	433.8	431.3	428.6	426.1
45°	415.0	408.3	401.6	397.0	394.5	392.1	389.6	387.1
47.5°	377.4	370.4	363.5	358.6	355.9	353.2	350.5	347.8
50°	352.4	345.6	338.7	334.1	331.4	328.8	326.2	323.6
52.5°	327.6	320.6	313.7	308.9	306.1	303.4	300.7	298.0
55°	290.9	283.8	276.6	271.8	269.2	266.6	264.0	261.3
57.5°	255.0	247.8	240.6	236.0	234.0	232.0	230.0	228.1
60°	231.1	223.9	216.8	212.2	210.0	207.8	205.7	203.4
62.5°	207.6	201.0	194.4	190.2	188.5	186.7	185.0	183.2
65°	173.8	167.9	162.0	158.2	156.6	155.0	153.3	151.6
67.5°	142.8	137.7	132.6	129.2	127.4	125.6	123.7	121.9
70°	121.7	117.2	112.6	109.6	108.3	106.9	105.5	104.2
72.5°	102.7	98.9	95.0	92.4	91.2	89.9	88.6	87.4
75°	75.7	72.6	69.4	67.4	66.5	65.8	65.0	64.1
77.5°	53.6	51.7	49.8	48.8	48.6	48.3	48.1	47.8
80°	41.1	40.7	40.2	40.0	39.8	39.7	39.6	39.5
82.5°	31.9	31.6	31.4	31.1	31.0	30.8	30.7	30.6
85°	18.5	18.3	18.0	17.9	17.9	17.9	17.9	17.9
87.5°	7.7	7.6	7.6	7.6	7.8	7.9	8.0	8.1
90°	5.1	5.3	5.6	5.6	5.9	6.2	5.9	5.9
92.5°	55.0	41.4	33.0	27.3	24.0	22.5	21.5	21.5
95°	207.5	164.1	126.5	99.4	85.6	77.0	71.9	68.3
97.5°	306.5	290.4	263.0	233.8	213.7	196.9	188.5	182.6
100°	337.6	343.3	329.5	308.8	284.5	267.4	259.0	256.7
102.5°	336.1	363.8	367.8	359.2	344.3	331.9	323.1	321.2
105°	313.5	362.0	389.8	401.2	401.8	399.5	395.6	394.0
107.5°	281.6	333.2	372.2	397.2	411.0	417.4	420.2	420.9
110°	262.4	310.8	351.4	382.1	402.0	413.8	418.8	421.4



TEST NUMBER: P332900-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	248.2	291.0	329.4	360.2	382.8	397.0	404.1	408.1
115°	234.1	268.5	301.3	328.1	350.2	367.0	376.0	378.3
117.5°	227.1	255.6	281.4	304.2	323.1	337.2	346.2	347.9
120°	223.9	250.0	272.4	292.3	308.2	320.6	327.9	331.0
122.5°	221.3	246.4	266.8	284.2	297.7	308.2	314.4	317.5
125°	216.7	240.7	260.1	275.5	286.7	294.9	300.2	301.8
127.5°	211.1	234.1	253.4	268.0	279.2	286.5	291.0	292.6
130°	206.6	228.8	247.8	262.6	274.1	281.1	285.6	287.2
132.5°	201.9	222.7	241.3	256.1	267.4	275.3	279.6	281.2
135°	195.4	213.7	230.7	244.7	255.9	263.7	268.2	269.9
137.5°	189.6	204.9	219.4	232.0	242.5	250.2	253.9	255.9
140°	186.2	199.3	211.9	223.7	233.5	239.6	243.6	245.8
142.5°	183.1	194.6	205.4	215.6	224.3	230.0	233.5	235.0
145°	178.6	188.1	196.5	204.4	211.4	216.1	219.0	220.3
147.5°	175.0	182.5	189.3	195.4	200.6	204.7	206.8	207.3
150°	172.8	179.2	184.8	189.8	194.3	198.0	199.6	199.9
152.5°	170.3	175.9	181.0	185.1	188.9	191.9	192.9	193.2
155°	166.6	171.0	175.2	178.6	181.4	183.6	184.5	184.5
157.5°	162.6	166.4	169.9	172.6	174.7	176.4	176.9	176.9
160°	160.2	163.2	166.3	168.6	170.2	171.9	172.2	172.2
162.5°	157.7	160.3	162.7	164.8	166.0	167.6	167.9	167.7
165°	154.2	156.0	157.9	159.3	160.4	161.5	161.3	161.0
167.5°	151.0	152.3	153.8	154.6	155.2	156.0	155.9	155.7
170°	148.9	149.8	150.9	151.8	152.3	152.6	152.3	152.3
172.5°	147.2	147.7	148.5	149.1	149.4	149.6	149.4	148.9
175°	144.7	145.0	145.6	145.6	145.6	146.2	145.6	145.0
177.5°	143.1	143.4	143.4	143.6	143.4	143.6	143.1	142.8
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5

(END OF REPORT)