

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331759-840

Luminaire Tested: **SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331759-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8200.5 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331759-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331759-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	94	90	87	90	86	83	81	73	70	68	60	58	57	48	47	46	41
2	90	83	77	72	82	76	72	67	65	61	58	54	51	49	43	42	40	36
3	82	73	67	61	76	68	62	57	58	53	50	48	45	42	39	37	35	31
4	76	66	58	52	70	61	54	49	52	47	43	43	40	37	36	33	31	27
5	70	59	51	46	64	55	48	43	47	42	38	39	36	33	33	30	28	24
6	65	53	45	40	59	49	43	38	42	37	33	36	32	29	30	27	25	22
7	60	48	41	35	55	45	38	34	39	34	30	33	29	26	28	25	22	20
8	56	44	37	32	51	41	35	30	36	30	27	30	26	24	26	23	20	18
9	52	40	33	28	48	38	31	27	33	28	24	28	24	21	24	21	19	17
10	49	37	30	26	45	35	29	25	30	25	22	26	22	20	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	35960	35960	35960	35960
5°	40161	36185	32083	36185
10°	44558	35931	27811	35931
15°	46748	35405	21912	35405
20°	40527	34625	18962	34625
25°	26580	33556	16930	33556
30°	17890	32261	15321	32261
35°	14491	30628	13819	30628
40°	12886	28854	12787	28854
45°	11663	26772	11415	26772
50°	10613	24707	10575	24707
55°	9979	22415	9847	22415
60°	8344	20315	8247	20315
65°	7037	18449	7981	18449
70°	6500	16475	7530	16475
75°	6089	14336	6949	14336
80°	5616	11799	6192	11799
85°	5169	9318	5446	9318



TEST NUMBER: P331759-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	211.1	2.6
10°-20°	588.3	7.2
20°-30°	758.1	9.2
30°-40°	720.4	8.8
40°-50°	617.1	7.5
50°-60°	470.0	5.7
60°-70°	297.1	3.6
70°-80°	148.4	1.8
80°-90°	42.3	0.5
90°-100°	49.5	0.6
100°-110°	181.5	2.2
110°-120°	485.1	5.9
120°-130°	800.8	9.8
130°-140°	851.6	10.4
140°-150°	791.6	9.7
150°-160°	636.4	7.8
160°-170°	410.1	5.0
170°-180°	141.2	1.7
0°-30°	1557.5	19.0
0°-40°	2277.9	27.8
0°-60°	3365.0	41.0
0°-90°	3852.7	47.0
90°-120°	716.1	8.7
90°-150°	3160.1	38.5
90°-180°	4348.0	53.0
0°-180°	8200.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2227	2227	2227	2227	2227	
5°	2478	2233	1980	2233	2478	245
15°	2797	2118	1311	2118	2797	754
25°	1492	1884	950	1884	1492	708
35°	735	1554	701	1554	735	470
45°	511	1172	500	1172	511	395
55°	354	796	350	796	354	311
65°	184	483	209	483	184	187
75°	98	230	111	230	98	103
85°	28	50	29	50	28	31
90°	29	1	29	1	29	14
95°	46	70	46	70	46	43
105°	82	326	82	326	82	85
115°	88	617	88	617	88	220
125°	918	873	918	873	918	794
135°	1115	1080	1115	1080	1115	860
145°	1272	1253	1272	1253	1272	796
155°	1381	1380	1381	1380	1381	637
165°	1450	1454	1450	1454	1450	409
175°	1478	1487	1478	1487	1478	141
180°	1484	1484	1484	1484	1484	



TEST NUMBER: P331759-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2317.5	2319.5	2321.3	2316.9	2316.9	2313.2	2305.2	2299.0	2281.7	2279.2	2279.2
5°	2477.9	2476.4	2479.4	2469.4	2455.5	2452.4	2437.7	2418.3	2398.2	2375.8	2371.2
7.5°	2637.4	2635.0	2628.8	2627.2	2616.5	2593.0	2569.4	2544.2	2510.7	2478.1	2461.6
10°	2717.8	2743.4	2727.8	2700.8	2706.2	2669.9	2650.5	2617.3	2589.4	2540.6	2529.8
12.5°	2797.0	2807.1	2802.2	2786.8	2779.9	2754.6	2728.5	2699.6	2648.2	2604.3	2566.3
15°	2796.7	2811.5	2815.3	2810.7	2814.6	2813.0	2799.0	2775.1	2730.2	2682.2	2640.4
17.5°	2590.3	2600.5	2625.9	2643.0	2664.7	2710.6	2733.1	2742.0	2735.3	2708.0	2678.5
20°	2358.7	2341.7	2412.9	2449.3	2480.2	2557.6	2624.1	2649.7	2690.7	2690.0	2682.2
22.5°	2030.6	2034.7	2102.1	2145.4	2235.7	2313.1	2388.9	2485.1	2564.5	2616.9	2647.6
25°	1492.0	1521.5	1588.7	1647.6	1748.2	1892.1	2022.9	2174.5	2317.7	2430.7	2538.3
27.5°	1120.5	1122.8	1176.1	1230.4	1290.2	1408.2	1572.8	1753.9	1958.0	2126.5	2320.2
30°	959.6	954.9	977.3	1010.7	1061.8	1153.1	1276.9	1454.9	1658.4	1912.2	2138.2
32.5°	845.7	846.0	862.8	887.5	929.9	991.5	1076.3	1220.8	1413.2	1662.7	1927.7
35°	735.2	734.4	746.8	764.6	782.3	821.8	879.9	955.7	1088.0	1321.0	1591.9
37.5°	655.9	659.3	665.4	676.5	696.2	718.1	753.0	803.9	898.2	1035.9	1263.5
40°	611.4	612.9	621.4	630.7	642.3	659.3	687.9	729.0	797.9	907.8	1074.1
42.5°	570.5	572.1	578.0	586.7	595.9	612.9	636.6	672.1	727.9	813.6	950.9
45°	510.8	510.8	516.1	520.1	530.1	545.5	564.9	594.3	633.0	696.5	787.8
47.5°	454.7	454.8	458.5	465.1	471.4	483.5	502.5	526.5	554.7	603.8	681.8
50°	422.5	423.3	425.7	431.0	434.9	445.8	460.5	481.3	510.8	548.7	613.7
52.5°	396.6	396.1	399.0	401.3	403.9	411.7	422.7	441.1	467.4	500.4	554.2
55°	354.5	351.3	356.0	359.8	362.1	365.3	371.4	383.0	405.5	433.3	473.6
57.5°	301.8	300.5	303.9	307.4	314.7	323.1	328.3	335.7	347.3	367.3	407.2
60°	258.4	258.4	265.4	267.7	276.3	287.1	297.9	304.2	315.8	328.9	358.3
62.5°	220.0	220.8	224.0	226.3	231.1	244.4	259.5	273.2	284.2	296.7	316.2
65°	184.2	185.7	185.7	187.2	190.4	193.5	199.7	210.5	229.8	247.6	262.4
67.5°	156.3	156.8	157.2	158.8	159.6	163.0	165.4	170.3	174.7	191.6	209.8
70°	137.7	140.1	139.3	140.9	141.6	143.2	146.2	148.6	155.5	159.5	170.3
72.5°	120.4	122.1	122.0	122.9	124.9	125.2	127.6	130.0	134.5	137.7	143.6
75°	97.6	96.7	97.6	99.1	99.9	100.6	100.6	103.7	106.0	109.1	113.0
77.5°	75.2	76.0	75.8	76.0	76.1	77.6	77.4	78.8	81.1	82.6	84.5
80°	60.4	61.1	60.4	61.1	61.9	62.7	61.9	62.7	65.0	66.6	66.6
82.5°	46.8	46.9	47.4	47.6	47.7	47.9	48.9	49.1	50.8	50.5	51.1
85°	27.9	27.1	27.1	27.1	27.9	28.7	27.9	27.9	28.7	28.7	28.7
87.5°	15.7	16.3	16.2	16.1	16.0	15.8	15.6	16.0	15.0	15.5	14.4
90°	29.0	28.5	28.1	27.6	27.1	26.3	25.0	23.8	22.6	21.5	19.6
92.5°	29.0	28.7	28.4	28.2	27.9	27.4	26.8	26.2	25.5	24.9	23.9
95°	46.2	46.4	46.7	46.9	47.2	46.7	45.4	44.2	43.0	41.9	40.2
97.5°	61.6	61.3	61.1	60.8	60.5	59.9	58.9	58.0	57.0	56.0	52.2
100°	71.9	71.5	71.0	70.5	70.0	68.9	67.0	65.0	63.1	61.2	57.2
102.5°	77.1	76.4	75.7	75.0	74.4	72.8	70.4	67.9	65.4	62.9	96.8
105°	81.6	80.6	79.7	78.8	77.8	75.9	73.3	70.7	68.1	65.4	130.6
107.5°	83.9	83.0	82.0	81.1	80.2	81.0	83.6	86.3	89.0	91.7	169.8
110°	84.8	83.8	82.9	81.9	81.0	92.4	116.3	140.2	164.0	187.8	256.8



TEST NUMBER: P331759-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	85.6	84.9	84.1	83.4	82.6	125.7	212.8	299.8	386.9	473.8	490.9
115°	88.1	105.2	122.4	139.6	156.7	220.6	331.0	441.4	551.9	662.4	656.4
117.5°	359.4	415.9	472.3	528.8	585.2	626.8	653.5	680.2	706.9	733.7	729.5
120°	654.9	687.0	719.2	751.4	783.7	798.4	795.5	792.6	789.7	786.9	782.6
122.5°	817.2	823.4	829.7	836.0	842.1	844.4	842.7	841.0	839.3	837.6	832.9
125°	917.9	917.2	916.5	915.7	915.0	913.8	912.1	910.5	908.8	907.2	902.6
127.5°	981.4	981.3	981.2	981.0	980.9	979.6	977.1	974.7	972.3	969.9	966.4
130°	1021.0	1021.2	1021.4	1021.7	1021.9	1020.7	1018.0	1015.4	1012.8	1010.2	1007.5
132.5°	1059.6	1059.9	1060.1	1060.3	1060.6	1059.6	1057.3	1055.0	1052.8	1050.6	1047.9
135°	1115.4	1115.9	1116.3	1116.8	1117.3	1116.3	1114.0	1111.6	1109.2	1106.8	1104.7
137.5°	1166.3	1167.1	1167.9	1168.7	1169.5	1168.7	1166.4	1164.1	1161.7	1159.4	1157.0
140°	1198.1	1199.2	1200.4	1201.6	1202.9	1202.3	1200.2	1198.1	1195.9	1193.8	1191.1
142.5°	1229.0	1230.2	1231.3	1232.5	1233.8	1233.3	1231.4	1229.4	1227.5	1225.6	1222.5
145°	1272.1	1273.3	1274.6	1275.8	1276.9	1276.7	1275.0	1273.3	1271.6	1270.0	1266.0
147.5°	1310.1	1311.1	1312.1	1313.1	1314.1	1314.0	1312.8	1311.5	1310.3	1309.1	1305.0
150°	1333.3	1334.5	1335.7	1336.9	1338.1	1338.0	1336.6	1335.1	1333.7	1332.2	1328.5
152.5°	1353.1	1354.6	1356.2	1357.8	1359.4	1359.5	1358.1	1356.6	1355.1	1353.7	1350.1
155°	1380.6	1382.5	1384.4	1386.2	1388.2	1388.5	1387.0	1385.5	1384.1	1382.7	1379.9
157.5°	1405.6	1407.5	1409.4	1411.3	1413.1	1413.2	1411.6	1410.0	1408.4	1406.7	1404.7
160°	1420.3	1422.0	1423.6	1425.3	1426.9	1427.0	1425.6	1424.2	1422.8	1421.4	1420.0
162.5°	1432.3	1434.3	1436.4	1438.5	1440.5	1440.8	1439.1	1437.4	1435.8	1434.2	1433.0
165°	1450.4	1452.0	1453.7	1455.3	1457.0	1457.0	1455.3	1453.7	1452.0	1450.4	1449.7
167.5°	1461.7	1463.9	1466.0	1468.1	1470.3	1470.6	1468.8	1467.2	1465.5	1463.9	1463.2
170°	1468.5	1470.8	1472.9	1475.0	1477.1	1477.4	1475.7	1474.1	1472.4	1470.8	1470.3
172.5°	1473.7	1475.9	1478.0	1480.2	1482.4	1482.6	1480.9	1479.3	1477.5	1475.9	1475.4
175°	1478.2	1480.7	1483.0	1485.4	1487.8	1488.1	1486.5	1484.8	1483.2	1481.5	1481.0
177.5°	1481.1	1482.8	1484.5	1486.2	1487.9	1488.1	1486.7	1485.4	1484.1	1482.8	1482.6
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6



TEST NUMBER: P331759-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2280.5	2275.4	2271.2	2260.0	2254.4	2242.0	2240.2	2239.6	2223.5	2208.0	2203.6
5°	2358.7	2346.3	2327.8	2306.1	2283.7	2260.5	2245.0	2232.6	2201.6	2172.2	2155.3
7.5°	2437.7	2411.1	2379.0	2338.0	2303.8	2265.4	2237.0	2211.4	2167.5	2125.4	2097.0
10°	2496.5	2453.2	2410.5	2354.1	2310.0	2266.6	2226.4	2191.6	2142.0	2086.4	2046.9
12.5°	2533.0	2485.4	2426.7	2371.5	2314.3	2259.3	2205.3	2160.6	2102.4	2044.9	1998.0
15°	2582.4	2531.3	2460.1	2381.2	2307.6	2235.7	2173.8	2118.1	2042.3	1973.4	1916.1
17.5°	2622.8	2552.5	2476.1	2384.8	2299.7	2208.2	2128.5	2057.3	1972.9	1889.8	1822.3
20°	2635.7	2566.2	2477.9	2386.6	2286.0	2178.5	2092.5	2015.2	1924.6	1834.0	1756.7
22.5°	2627.8	2573.5	2475.5	2366.2	2263.1	2150.6	2053.6	1963.8	1863.3	1770.9	1681.1
25°	2573.1	2554.6	2461.6	2342.5	2224.8	2094.1	1981.9	1883.6	1769.1	1670.0	1572.5
27.5°	2445.7	2485.8	2428.2	2301.3	2170.5	2030.3	1904.2	1792.3	1673.4	1562.0	1464.8
30°	2323.2	2415.2	2390.5	2272.8	2126.6	1988.8	1847.2	1730.4	1603.5	1488.9	1393.0
32.5°	2155.4	2307.5	2331.7	2233.2	2082.0	1930.7	1782.2	1666.0	1533.5	1412.8	1319.3
35°	1888.2	2115.8	2220.2	2157.6	2005.9	1842.6	1689.3	1553.9	1420.8	1301.6	1208.8
37.5°	1569.5	1879.5	2053.6	2058.0	1918.7	1749.0	1582.1	1447.6	1311.4	1194.4	1094.0
40°	1362.8	1698.6	1925.4	1975.7	1858.1	1674.7	1505.9	1369.0	1235.9	1121.4	1006.0
42.5°	1177.1	1511.7	1790.4	1877.8	1784.4	1602.3	1432.9	1289.7	1160.3	1052.0	934.2
45°	951.9	1244.4	1551.6	1707.9	1656.1	1487.3	1308.6	1172.5	1050.9	957.3	844.2
47.5°	802.9	1009.2	1306.5	1517.8	1516.9	1362.9	1187.1	1056.6	943.9	856.2	764.8
50°	718.1	897.7	1149.2	1389.1	1409.2	1280.0	1112.8	983.6	878.4	786.3	712.8
52.5°	642.0	789.9	1016.1	1246.1	1303.3	1191.4	1029.3	909.9	807.8	723.1	660.1
55°	542.5	657.0	828.8	1043.9	1130.6	1051.7	907.8	796.3	713.5	642.3	588.1
57.5°	458.9	544.8	682.7	855.9	956.8	907.2	788.4	697.9	627.0	562.6	519.9
60°	406.3	476.7	593.6	738.3	849.7	814.9	713.5	629.1	568.8	513.1	472.8
62.5°	356.8	417.3	517.5	634.9	737.0	722.7	639.9	569.1	516.1	465.4	431.3
65°	287.1	331.2	409.4	501.5	583.5	590.5	530.9	482.9	435.7	395.5	365.3
67.5°	228.6	257.4	312.5	390.0	451.5	473.4	437.1	400.4	362.9	331.8	305.7
70°	192.7	215.9	256.1	318.8	375.4	398.5	377.7	349.0	316.5	290.9	268.5
72.5°	156.1	178.7	208.4	254.5	302.9	328.0	320.7	300.1	273.8	252.6	231.4
75°	117.6	124.6	144.7	175.7	213.6	235.3	240.7	229.8	208.9	192.7	180.3
77.5°	86.9	91.2	100.8	117.0	141.8	161.1	169.1	167.7	153.4	143.9	132.3
80°	69.7	72.0	76.6	83.6	102.2	121.5	126.9	126.9	116.8	113.0	101.4
82.5°	52.9	54.6	57.5	61.3	70.0	86.8	92.9	94.1	87.8	82.6	73.5
85°	30.2	29.4	31.0	33.3	34.8	39.5	48.8	50.3	48.8	42.5	40.2
87.5°	14.0	14.3	13.9	12.8	12.9	13.0	15.6	18.2	16.3	14.8	14.1
90°	17.7	15.8	13.8	11.6	9.0	6.4	3.7	1.1	3.7	6.4	9.0
92.5°	23.0	22.0	21.1	20.7	21.0	21.2	21.4	21.7	21.4	21.2	21.0
95°	38.6	36.9	35.1	38.3	46.2	54.0	61.9	69.8	61.9	54.0	46.2
97.5°	48.3	44.4	40.6	49.8	71.9	94.1	116.3	138.5	116.3	94.1	71.9
100°	53.1	49.0	44.9	59.3	92.0	124.6	157.3	190.1	157.3	124.6	92.0
102.5°	130.8	164.7	198.6	219.0	225.9	232.9	239.7	246.7	239.7	232.9	225.9
105°	195.7	260.8	326.0	355.0	347.8	340.6	333.6	326.4	333.6	340.6	347.8
107.5°	247.9	326.0	404.1	440.3	434.4	428.7	422.9	417.2	422.9	428.7	434.4
110°	325.8	394.7	463.6	495.6	490.6	485.6	480.6	475.5	480.6	485.6	490.6



TEST NUMBER: P331759-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	508.0	524.9	542.0	548.3	543.8	539.4	535.0	530.6	535.0	539.4	543.8
115°	650.5	644.5	638.5	633.5	629.4	625.4	621.4	617.3	621.4	625.4	629.4
117.5°	725.5	721.3	717.2	713.0	708.4	703.9	699.3	694.8	699.3	703.9	708.4
120°	778.3	774.1	769.7	765.8	762.2	758.6	755.1	751.4	755.1	758.6	762.2
122.5°	828.2	823.5	818.9	814.7	810.9	807.1	803.3	799.6	803.3	807.1	810.9
125°	898.1	893.5	889.0	885.1	882.1	879.0	875.9	872.8	875.9	879.0	882.1
127.5°	963.0	959.7	956.2	952.9	949.5	946.0	942.6	939.2	942.6	946.0	949.5
130°	1004.9	1002.3	999.7	996.4	992.7	988.9	985.0	981.2	985.0	988.9	992.7
132.5°	1045.3	1042.7	1040.1	1037.1	1033.9	1030.7	1027.4	1024.1	1027.4	1030.7	1033.9
135°	1102.5	1100.3	1098.2	1095.2	1091.5	1087.6	1083.8	1079.9	1083.8	1087.6	1091.5
137.5°	1154.6	1152.2	1149.6	1147.1	1144.5	1141.8	1139.1	1136.4	1139.1	1141.8	1144.5
140°	1188.5	1185.9	1183.3	1181.0	1179.1	1177.2	1175.3	1173.4	1175.3	1177.2	1179.1
142.5°	1219.5	1216.5	1213.6	1211.1	1209.4	1207.7	1206.0	1204.3	1206.0	1207.7	1209.4
145°	1261.8	1257.8	1253.7	1251.8	1252.1	1252.3	1252.5	1252.8	1252.5	1252.3	1252.1
147.5°	1301.0	1297.1	1293.0	1291.5	1292.4	1293.3	1294.2	1295.2	1294.2	1293.3	1292.4
150°	1324.6	1320.8	1317.0	1316.0	1317.6	1319.3	1320.9	1322.6	1320.9	1319.3	1317.6
152.5°	1346.5	1342.8	1339.2	1338.4	1340.2	1342.0	1343.9	1345.7	1343.9	1342.0	1340.2
155°	1377.0	1374.1	1371.3	1370.9	1373.0	1375.2	1377.4	1379.5	1377.4	1375.2	1373.0
157.5°	1402.7	1400.8	1398.8	1398.7	1400.5	1402.3	1404.1	1405.9	1404.1	1402.3	1400.5
160°	1418.5	1417.0	1415.6	1415.6	1417.0	1418.5	1420.0	1421.4	1420.0	1418.5	1417.0
162.5°	1431.8	1430.5	1429.3	1429.4	1430.8	1432.2	1433.7	1435.1	1433.7	1432.2	1430.8
165°	1449.0	1448.1	1447.4	1447.8	1449.3	1450.7	1452.1	1453.6	1452.1	1450.7	1449.3
167.5°	1462.5	1461.9	1461.2	1461.6	1463.0	1464.4	1465.9	1467.3	1465.9	1464.4	1463.0
170°	1469.8	1469.4	1468.8	1469.4	1470.8	1472.2	1473.6	1475.0	1473.6	1472.2	1470.8
172.5°	1474.9	1474.5	1474.0	1474.5	1475.9	1477.3	1478.7	1480.2	1478.7	1477.3	1475.9
175°	1480.6	1480.1	1479.6	1480.2	1481.9	1483.5	1485.2	1486.8	1485.2	1483.5	1481.9
177.5°	1482.4	1482.2	1482.0	1482.6	1483.9	1485.2	1486.6	1487.9	1486.6	1485.2	1483.9
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6



TEST NUMBER: P331759-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2195.6	2191.3	2183.2	2170.8	2163.4	2150.4	2141.7	2146.7	2148.0	2146.7	2145.5
5°	2136.7	2120.4	2098.0	2076.3	2056.2	2034.5	2022.2	2016.7	2005.9	1999.6	1996.6
7.5°	2065.3	2037.3	2005.6	1967.8	1935.7	1902.2	1885.0	1876.4	1854.3	1842.3	1831.7
10°	2012.1	1967.9	1936.2	1886.7	1856.5	1812.4	1782.2	1783.0	1752.8	1735.8	1723.4
12.5°	1953.3	1904.8	1852.0	1807.5	1765.5	1730.1	1693.6	1679.0	1647.0	1630.5	1597.1
15°	1855.7	1799.3	1743.5	1683.1	1640.6	1585.7	1533.1	1468.8	1416.9	1372.1	1359.7
17.5°	1749.3	1679.3	1623.5	1552.6	1479.7	1387.3	1326.3	1289.0	1257.7	1234.1	1216.4
20°	1676.2	1605.0	1545.4	1438.7	1340.3	1277.7	1232.7	1204.2	1171.6	1146.1	1132.2
22.5°	1599.4	1525.1	1443.9	1324.7	1248.1	1197.8	1157.8	1124.9	1102.9	1083.0	1070.3
25°	1490.5	1409.2	1275.4	1193.3	1131.4	1078.7	1050.9	1030.8	1007.5	980.5	968.2
27.5°	1375.3	1246.1	1149.9	1088.9	1029.9	995.6	970.6	940.6	919.8	907.6	894.7
30°	1289.3	1160.0	1085.0	1018.4	976.6	938.7	909.3	892.3	872.1	851.2	842.7
32.5°	1193.3	1090.0	1018.1	962.7	920.3	888.0	864.7	837.2	822.6	809.8	791.9
35°	1074.1	995.9	930.2	885.3	845.1	818.8	791.6	775.4	749.1	738.3	731.3
37.5°	973.2	905.4	856.4	809.0	777.1	748.0	731.4	705.6	694.2	679.1	664.5
40°	916.3	849.7	802.5	763.8	728.2	706.5	685.6	664.8	647.7	640.8	623.0
42.5°	858.1	803.9	756.7	714.3	690.4	667.5	641.1	625.7	608.1	596.8	585.8
45°	777.7	729.7	689.5	654.7	628.3	604.4	587.3	561.8	551.8	529.4	520.1
47.5°	707.2	662.6	624.2	591.1	565.4	549.8	524.8	504.8	488.8	475.0	463.1
50°	657.0	619.9	582.7	553.3	530.1	507.7	482.1	472.0	447.3	440.3	433.3
52.5°	611.2	575.9	541.9	513.1	489.9	468.1	445.6	432.4	415.8	408.8	403.6
55°	547.1	513.1	480.6	455.0	431.8	409.4	395.5	379.2	371.4	366.1	359.8
57.5°	482.7	452.1	427.2	401.3	378.0	360.1	344.1	334.3	326.3	319.1	311.7
60°	441.9	412.4	390.0	366.1	342.0	327.3	315.0	303.4	294.1	283.3	280.1
62.5°	398.5	372.8	352.2	328.9	308.0	294.6	282.8	271.8	260.6	244.9	240.5
65°	338.9	318.8	297.2	277.8	259.2	246.1	229.0	216.7	212.1	210.5	209.7
67.5°	285.1	266.1	247.5	227.6	210.8	198.5	190.0	188.0	184.8	183.9	181.7
70°	249.2	231.4	212.8	194.2	178.0	175.7	172.6	169.5	165.6	164.1	162.5
72.5°	217.0	198.5	180.0	165.1	158.1	155.2	152.2	149.1	146.4	144.9	143.9
75°	166.4	149.4	136.9	131.6	127.6	125.3	120.7	118.4	116.8	114.5	113.7
77.5°	119.8	110.2	104.5	101.1	97.0	94.5	91.9	89.6	88.0	87.5	86.2
80°	91.3	86.6	82.8	78.2	76.6	73.5	72.7	70.4	71.2	68.9	68.9
82.5°	70.9	65.0	61.8	59.6	58.1	55.5	54.8	53.7	53.8	52.1	52.1
85°	36.4	34.8	33.3	31.7	31.7	29.4	30.2	29.4	29.4	27.9	27.1
87.5°	14.0	13.9	13.0	13.4	13.8	13.5	13.8	13.4	13.6	13.9	13.4
90°	11.6	13.8	15.8	17.7	19.6	21.5	22.6	23.8	25.0	26.3	27.1
92.5°	20.7	21.1	22.0	23.0	23.9	24.9	25.5	26.2	26.8	27.4	27.9
95°	38.3	35.1	36.9	38.6	40.2	41.9	43.0	44.2	45.4	46.7	47.2
97.5°	49.8	40.6	44.4	48.3	52.2	56.0	57.0	58.0	58.9	59.9	60.5
100°	59.3	44.9	49.0	53.1	57.2	61.2	63.1	65.0	67.0	68.9	70.0
102.5°	219.0	198.6	164.7	130.8	96.8	62.9	65.4	67.9	70.4	72.8	74.4
105°	355.0	326.0	260.8	195.7	130.6	65.4	68.1	70.7	73.3	75.9	77.8
107.5°	440.3	404.1	326.0	247.9	169.8	91.7	89.0	86.3	83.6	81.0	80.2
110°	495.6	463.6	394.7	325.8	256.8	187.8	164.0	140.2	116.3	92.4	81.0



TEST NUMBER: P331759-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	548.3	542.0	524.9	508.0	490.9	473.8	386.9	299.8	212.8	125.7	82.6
115°	633.5	638.5	644.5	650.5	656.4	662.4	551.9	441.4	331.0	220.6	156.7
117.5°	713.0	717.2	721.3	725.5	729.5	733.7	706.9	680.2	653.5	626.8	585.2
120°	765.8	769.7	774.1	778.3	782.6	786.9	789.7	792.6	795.5	798.4	783.7
122.5°	814.7	818.9	823.5	828.2	832.9	837.6	839.3	841.0	842.7	844.4	842.1
125°	885.1	889.0	893.5	898.1	902.6	907.2	908.8	910.5	912.1	913.8	915.0
127.5°	952.9	956.2	959.7	963.0	966.4	969.9	972.3	974.7	977.1	979.6	980.9
130°	996.4	999.7	1002.3	1004.9	1007.5	1010.2	1012.8	1015.4	1018.0	1020.7	1021.9
132.5°	1037.1	1040.1	1042.7	1045.3	1047.9	1050.6	1052.8	1055.0	1057.3	1059.6	1060.6
135°	1095.2	1098.2	1100.3	1102.5	1104.7	1106.8	1109.2	1111.6	1114.0	1116.3	1117.3
137.5°	1147.1	1149.6	1152.2	1154.6	1157.0	1159.4	1161.7	1164.1	1166.4	1168.7	1169.5
140°	1181.0	1183.3	1185.9	1188.5	1191.1	1193.8	1195.9	1198.1	1200.2	1202.3	1202.9
142.5°	1211.1	1213.6	1216.5	1219.5	1222.5	1225.6	1227.5	1229.4	1231.4	1233.3	1233.8
145°	1251.8	1253.7	1257.8	1261.8	1266.0	1270.0	1271.6	1273.3	1275.0	1276.7	1276.9
147.5°	1291.5	1293.0	1297.1	1301.0	1305.0	1309.1	1310.3	1311.5	1312.8	1314.0	1314.1
150°	1316.0	1317.0	1320.8	1324.6	1328.5	1332.2	1333.7	1335.1	1336.6	1338.0	1338.1
152.5°	1338.4	1339.2	1342.8	1346.5	1350.1	1353.7	1355.1	1356.6	1358.1	1359.5	1359.4
155°	1370.9	1371.3	1374.1	1377.0	1379.9	1382.7	1384.1	1385.5	1387.0	1388.5	1388.2
157.5°	1398.7	1398.8	1400.8	1402.7	1404.7	1406.7	1408.4	1410.0	1411.6	1413.2	1413.1
160°	1415.6	1415.6	1417.0	1418.5	1420.0	1421.4	1422.8	1424.2	1425.6	1427.0	1426.9
162.5°	1429.4	1429.3	1430.5	1431.8	1433.0	1434.2	1435.8	1437.4	1439.1	1440.8	1440.5
165°	1447.8	1447.4	1448.1	1449.0	1449.7	1450.4	1452.0	1453.7	1455.3	1457.0	1457.0
167.5°	1461.6	1461.2	1461.9	1462.5	1463.2	1463.9	1465.5	1467.2	1468.8	1470.6	1470.3
170°	1469.4	1468.8	1469.4	1469.8	1470.3	1470.8	1472.4	1474.1	1475.7	1477.4	1477.1
172.5°	1474.5	1474.0	1474.5	1474.9	1475.4	1475.9	1477.5	1479.3	1480.9	1482.6	1482.4
175°	1480.2	1479.6	1480.1	1480.6	1481.0	1481.5	1483.2	1484.8	1486.5	1488.1	1487.8
177.5°	1482.6	1482.0	1482.2	1482.4	1482.6	1482.8	1484.1	1485.4	1486.7	1488.1	1487.9
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6



TEST NUMBER: P331759-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2138.7	2139.9	2138.1	2139.3	2138.1	2139.9	2138.7	2145.5	2146.7	2148.0	2146.7
5°	1992.7	1983.4	1981.9	1979.5	1981.9	1983.4	1992.7	1996.6	1999.6	2005.9	2016.7
7.5°	1818.5	1817.1	1813.2	1807.8	1813.2	1817.1	1818.5	1831.7	1842.3	1854.3	1876.4
10°	1706.4	1702.5	1701.7	1696.3	1701.7	1702.5	1706.4	1723.4	1735.8	1752.8	1783.0
12.5°	1575.1	1550.2	1547.6	1534.1	1547.6	1550.2	1575.1	1597.1	1630.5	1647.0	1679.0
15°	1341.1	1336.5	1321.0	1310.9	1321.0	1336.5	1341.1	1359.7	1372.1	1416.9	1468.8
17.5°	1207.4	1192.2	1187.4	1185.3	1187.4	1192.2	1207.4	1216.4	1234.1	1257.7	1289.0
20°	1121.4	1107.4	1105.1	1103.6	1105.1	1107.4	1121.4	1132.2	1146.1	1171.6	1204.2
22.5°	1061.9	1047.3	1041.3	1036.6	1041.3	1047.3	1061.9	1070.3	1083.0	1102.9	1124.9
25°	960.4	954.9	951.9	950.3	951.9	954.9	960.4	968.2	980.5	1007.5	1030.8
27.5°	881.0	869.1	866.8	862.7	866.8	869.1	881.0	894.7	907.6	919.8	940.6
30°	835.8	831.9	826.5	821.8	826.5	831.9	835.8	842.7	851.2	872.1	892.3
32.5°	782.5	779.3	774.5	772.3	774.5	779.3	782.5	791.9	809.8	822.6	837.2
35°	723.6	712.8	708.1	701.1	708.1	712.8	723.6	731.3	738.3	749.1	775.4
37.5°	661.2	655.5	648.9	651.3	648.9	655.5	661.2	664.5	679.1	694.2	705.6
40°	612.9	609.0	607.5	606.7	607.5	609.0	612.9	623.0	640.8	647.7	664.8
42.5°	574.5	563.8	559.8	559.7	559.8	563.8	574.5	585.8	596.8	608.1	625.7
45°	516.1	506.1	499.2	499.9	499.2	506.1	516.1	520.1	529.4	551.8	561.8
47.5°	456.5	456.2	451.8	453.1	451.8	456.2	456.5	463.1	475.0	488.8	504.8
50°	428.0	423.3	420.2	421.0	420.2	423.3	428.0	433.3	440.3	447.3	472.0
52.5°	400.7	396.7	394.3	397.5	394.3	396.7	400.7	403.6	408.8	415.8	432.4
55°	356.0	351.3	350.5	349.8	350.5	351.3	356.0	359.8	366.1	371.4	379.2
57.5°	306.0	302.9	298.2	296.2	298.2	302.9	306.0	311.7	319.1	326.3	334.3
60°	270.0	263.9	256.1	255.4	256.1	263.9	270.0	280.1	283.3	294.1	303.4
62.5°	237.2	236.0	234.5	234.3	234.5	236.0	237.2	240.5	244.9	260.6	271.8
65°	208.1	207.4	208.1	208.9	208.1	207.4	208.1	209.7	210.5	212.1	216.7
67.5°	181.4	180.0	178.6	179.3	178.6	180.0	181.4	181.7	183.9	184.8	188.0
70°	161.0	160.2	159.5	159.5	159.5	160.2	161.0	162.5	164.1	165.6	169.5
72.5°	141.2	141.0	140.3	139.6	140.3	141.0	141.2	143.9	144.9	146.4	149.1
75°	113.0	111.4	111.4	111.4	111.4	111.4	113.0	113.7	114.5	116.8	118.4
77.5°	86.0	85.2	84.5	83.9	84.5	85.2	86.0	86.2	87.5	88.0	89.6
80°	68.1	67.4	66.6	66.6	66.6	67.4	68.1	68.9	68.9	71.2	70.4
82.5°	52.0	51.2	51.1	50.5	51.1	51.2	52.0	52.1	52.1	53.8	53.7
85°	27.9	28.7	27.9	29.4	27.9	28.7	27.9	27.1	27.9	29.4	29.4
87.5°	13.5	13.0	13.7	13.2	13.7	13.0	13.5	13.4	13.9	13.6	13.4
90°	27.6	28.1	28.5	29.0	28.5	28.1	27.6	27.1	26.3	25.0	23.8
92.5°	28.2	28.4	28.7	29.0	28.7	28.4	28.2	27.9	27.4	26.8	26.2
95°	46.9	46.7	46.4	46.2	46.4	46.7	46.9	47.2	46.7	45.4	44.2
97.5°	60.8	61.1	61.3	61.6	61.3	61.1	60.8	60.5	59.9	58.9	58.0
100°	70.5	71.0	71.5	71.9	71.5	71.0	70.5	70.0	68.9	67.0	65.0
102.5°	75.0	75.7	76.4	77.1	76.4	75.7	75.0	74.4	72.8	70.4	67.9
105°	78.8	79.7	80.6	81.6	80.6	79.7	78.8	77.8	75.9	73.3	70.7
107.5°	81.1	82.0	83.0	83.9	83.0	82.0	81.1	80.2	81.0	83.6	86.3
110°	81.9	82.9	83.8	84.8	83.8	82.9	81.9	81.0	92.4	116.3	140.2



TEST NUMBER: P331759-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	83.4	84.1	84.9	85.6	84.9	84.1	83.4	82.6	125.7	212.8	299.8
115°	139.6	122.4	105.2	88.1	105.2	122.4	139.6	156.7	220.6	331.0	441.4
117.5°	528.8	472.3	415.9	359.4	415.9	472.3	528.8	585.2	626.8	653.5	680.2
120°	751.4	719.2	687.0	654.9	687.0	719.2	751.4	783.7	798.4	795.5	792.6
122.5°	836.0	829.7	823.4	817.2	823.4	829.7	836.0	842.1	844.4	842.7	841.0
125°	915.7	916.5	917.2	917.9	917.2	916.5	915.7	915.0	913.8	912.1	910.5
127.5°	981.0	981.2	981.3	981.4	981.3	981.2	981.0	980.9	979.6	977.1	974.7
130°	1021.7	1021.4	1021.2	1021.0	1021.2	1021.4	1021.7	1021.9	1020.7	1018.0	1015.4
132.5°	1060.3	1060.1	1059.9	1059.6	1059.9	1060.1	1060.3	1060.6	1059.6	1057.3	1055.0
135°	1116.8	1116.3	1115.9	1115.4	1115.9	1116.3	1116.8	1117.3	1116.3	1114.0	1111.6
137.5°	1168.7	1167.9	1167.1	1166.3	1167.1	1167.9	1168.7	1169.5	1168.7	1166.4	1164.1
140°	1201.6	1200.4	1199.2	1198.1	1199.2	1200.4	1201.6	1202.9	1202.3	1200.2	1198.1
142.5°	1232.5	1231.3	1230.2	1229.0	1230.2	1231.3	1232.5	1233.8	1233.3	1231.4	1229.4
145°	1275.8	1274.6	1273.3	1272.1	1273.3	1274.6	1275.8	1276.9	1276.7	1275.0	1273.3
147.5°	1313.1	1312.1	1311.1	1310.1	1311.1	1312.1	1313.1	1314.1	1314.0	1312.8	1311.5
150°	1336.9	1335.7	1334.5	1333.3	1334.5	1335.7	1336.9	1338.1	1338.0	1336.6	1335.1
152.5°	1357.8	1356.2	1354.6	1353.1	1354.6	1356.2	1357.8	1359.4	1359.5	1358.1	1356.6
155°	1386.2	1384.4	1382.5	1380.6	1382.5	1384.4	1386.2	1388.2	1388.5	1387.0	1385.5
157.5°	1411.3	1409.4	1407.5	1405.6	1407.5	1409.4	1411.3	1413.1	1413.2	1411.6	1410.0
160°	1425.3	1423.6	1422.0	1420.3	1422.0	1423.6	1425.3	1426.9	1427.0	1425.6	1424.2
162.5°	1438.5	1436.4	1434.3	1432.3	1434.3	1436.4	1438.5	1440.5	1440.8	1439.1	1437.4
165°	1455.3	1453.7	1452.0	1450.4	1452.0	1453.7	1455.3	1457.0	1457.0	1455.3	1453.7
167.5°	1468.1	1466.0	1463.9	1461.7	1463.9	1466.0	1468.1	1470.3	1470.6	1468.8	1467.2
170°	1475.0	1472.9	1470.8	1468.5	1470.8	1472.9	1475.0	1477.1	1477.4	1475.7	1474.1
172.5°	1480.2	1478.0	1475.9	1473.7	1475.9	1478.0	1480.2	1482.4	1482.6	1480.9	1479.3
175°	1485.4	1483.0	1480.7	1478.2	1480.7	1483.0	1485.4	1487.8	1488.1	1486.5	1484.8
177.5°	1486.2	1484.5	1482.8	1481.1	1482.8	1484.5	1486.2	1487.9	1488.1	1486.7	1485.4
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6



TEST NUMBER: P331759-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2141.7	2150.4	2163.4	2170.8	2183.2	2191.3	2195.6	2203.6	2208.0	2223.5	2239.6
5°	2022.2	2034.5	2056.2	2076.3	2098.0	2120.4	2136.7	2155.3	2172.2	2201.6	2232.6
7.5°	1885.0	1902.2	1935.7	1967.8	2005.6	2037.3	2065.3	2097.0	2125.4	2167.5	2211.4
10°	1782.2	1812.4	1856.5	1886.7	1936.2	1967.9	2012.1	2046.9	2086.4	2142.0	2191.6
12.5°	1693.6	1730.1	1765.5	1807.5	1852.0	1904.8	1953.3	1998.0	2044.9	2102.4	2160.6
15°	1533.1	1585.7	1640.6	1683.1	1743.5	1799.3	1855.7	1916.1	1973.4	2042.3	2118.1
17.5°	1326.3	1387.3	1479.7	1552.6	1623.5	1679.3	1749.3	1822.3	1889.8	1972.9	2057.3
20°	1232.7	1277.7	1340.3	1438.7	1545.4	1605.0	1676.2	1756.7	1834.0	1924.6	2015.2
22.5°	1157.8	1197.8	1248.1	1324.7	1443.9	1525.1	1599.4	1681.1	1770.9	1863.3	1963.8
25°	1050.9	1078.7	1131.4	1193.3	1275.4	1409.2	1490.5	1572.5	1670.0	1769.1	1883.6
27.5°	970.6	995.6	1029.9	1088.9	1149.9	1246.1	1375.3	1464.8	1562.0	1673.4	1792.3
30°	909.3	938.7	976.6	1018.4	1085.0	1160.0	1289.3	1393.0	1488.9	1603.5	1730.4
32.5°	864.7	888.0	920.3	962.7	1018.1	1090.0	1193.3	1319.3	1412.8	1533.5	1666.0
35°	791.6	818.8	845.1	885.3	930.2	995.9	1074.1	1208.8	1301.6	1420.8	1553.9
37.5°	731.4	748.0	777.1	809.0	856.4	905.4	973.2	1094.0	1194.4	1311.4	1447.6
40°	685.6	706.5	728.2	763.8	802.5	849.7	916.3	1006.0	1121.4	1235.9	1369.0
42.5°	641.1	667.5	690.4	714.3	756.7	803.9	858.1	934.2	1052.0	1160.3	1289.7
45°	587.3	604.4	628.3	654.7	689.5	729.7	777.7	844.2	957.3	1050.9	1172.5
47.5°	524.8	549.8	565.4	591.1	624.2	662.6	707.2	764.8	856.2	943.9	1056.6
50°	482.1	507.7	530.1	553.3	582.7	619.9	657.0	712.8	786.3	878.4	983.6
52.5°	445.6	468.1	489.9	513.1	541.9	575.9	611.2	660.1	723.1	807.8	909.9
55°	395.5	409.4	431.8	455.0	480.6	513.1	547.1	588.1	642.3	713.5	796.3
57.5°	344.1	360.1	378.0	401.3	427.2	452.1	482.7	519.9	562.6	627.0	697.9
60°	315.0	327.3	342.0	366.1	390.0	412.4	441.9	472.8	513.1	568.8	629.1
62.5°	282.8	294.6	308.0	328.9	352.2	372.8	398.5	431.3	465.4	516.1	569.1
65°	229.0	246.1	259.2	277.8	297.2	318.8	338.9	365.3	395.5	435.7	482.9
67.5°	190.0	198.5	210.8	227.6	247.5	266.1	285.1	305.7	331.8	362.9	400.4
70°	172.6	175.7	178.0	194.2	212.8	231.4	249.2	268.5	290.9	316.5	349.0
72.5°	152.2	155.2	158.1	165.1	180.0	198.5	217.0	231.4	252.6	273.8	300.1
75°	120.7	125.3	127.6	131.6	136.9	149.4	166.4	180.3	192.7	208.9	229.8
77.5°	91.9	94.5	97.0	101.1	104.5	110.2	119.8	132.3	143.9	153.4	167.7
80°	72.7	73.5	76.6	78.2	82.8	86.6	91.3	101.4	113.0	116.8	126.9
82.5°	54.8	55.5	58.1	59.6	61.8	65.0	70.9	73.5	82.6	87.8	94.1
85°	30.2	29.4	31.7	31.7	33.3	34.8	36.4	40.2	42.5	48.8	50.3
87.5°	13.8	13.5	13.8	13.4	13.0	13.9	14.0	14.1	14.8	16.3	18.2
90°	22.6	21.5	19.6	17.7	15.8	13.8	11.6	9.0	6.4	3.7	1.1
92.5°	25.5	24.9	23.9	23.0	22.0	21.1	20.7	21.0	21.2	21.4	21.7
95°	43.0	41.9	40.2	38.6	36.9	35.1	38.3	46.2	54.0	61.9	69.8
97.5°	57.0	56.0	52.2	48.3	44.4	40.6	49.8	71.9	94.1	116.3	138.5
100°	63.1	61.2	57.2	53.1	49.0	44.9	59.3	92.0	124.6	157.3	190.1
102.5°	65.4	62.9	96.8	130.8	164.7	198.6	219.0	225.9	232.9	239.7	246.7
105°	68.1	65.4	130.6	195.7	260.8	326.0	355.0	347.8	340.6	333.6	326.4
107.5°	89.0	91.7	169.8	247.9	326.0	404.1	440.3	434.4	428.7	422.9	417.2
110°	164.0	187.8	256.8	325.8	394.7	463.6	495.6	490.6	485.6	480.6	475.5



TEST NUMBER: P331759-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	386.9	473.8	490.9	508.0	524.9	542.0	548.3	543.8	539.4	535.0	530.6
115°	551.9	662.4	656.4	650.5	644.5	638.5	633.5	629.4	625.4	621.4	617.3
117.5°	706.9	733.7	729.5	725.5	721.3	717.2	713.0	708.4	703.9	699.3	694.8
120°	789.7	786.9	782.6	778.3	774.1	769.7	765.8	762.2	758.6	755.1	751.4
122.5°	839.3	837.6	832.9	828.2	823.5	818.9	814.7	810.9	807.1	803.3	799.6
125°	908.8	907.2	902.6	898.1	893.5	889.0	885.1	882.1	879.0	875.9	872.8
127.5°	972.3	969.9	966.4	963.0	959.7	956.2	952.9	949.5	946.0	942.6	939.2
130°	1012.8	1010.2	1007.5	1004.9	1002.3	999.7	996.4	992.7	988.9	985.0	981.2
132.5°	1052.8	1050.6	1047.9	1045.3	1042.7	1040.1	1037.1	1033.9	1030.7	1027.4	1024.1
135°	1109.2	1106.8	1104.7	1102.5	1100.3	1098.2	1095.2	1091.5	1087.6	1083.8	1079.9
137.5°	1161.7	1159.4	1157.0	1154.6	1152.2	1149.6	1147.1	1144.5	1141.8	1139.1	1136.4
140°	1195.9	1193.8	1191.1	1188.5	1185.9	1183.3	1181.0	1179.1	1177.2	1175.3	1173.4
142.5°	1227.5	1225.6	1222.5	1219.5	1216.5	1213.6	1211.1	1209.4	1207.7	1206.0	1204.3
145°	1271.6	1270.0	1266.0	1261.8	1257.8	1253.7	1251.8	1252.1	1252.3	1252.5	1252.8
147.5°	1310.3	1309.1	1305.0	1301.0	1297.1	1293.0	1291.5	1292.4	1293.3	1294.2	1295.2
150°	1333.7	1332.2	1328.5	1324.6	1320.8	1317.0	1316.0	1317.6	1319.3	1320.9	1322.6
152.5°	1355.1	1353.7	1350.1	1346.5	1342.8	1339.2	1338.4	1340.2	1342.0	1343.9	1345.7
155°	1384.1	1382.7	1379.9	1377.0	1374.1	1371.3	1370.9	1373.0	1375.2	1377.4	1379.5
157.5°	1408.4	1406.7	1404.7	1402.7	1400.8	1398.8	1398.7	1400.5	1402.3	1404.1	1405.9
160°	1422.8	1421.4	1420.0	1418.5	1417.0	1415.6	1415.6	1417.0	1418.5	1420.0	1421.4
162.5°	1435.8	1434.2	1433.0	1431.8	1430.5	1429.3	1429.4	1430.8	1432.2	1433.7	1435.1
165°	1452.0	1450.4	1449.7	1449.0	1448.1	1447.4	1447.8	1449.3	1450.7	1452.1	1453.6
167.5°	1465.5	1463.9	1463.2	1462.5	1461.9	1461.2	1461.6	1463.0	1464.4	1465.9	1467.3
170°	1472.4	1470.8	1470.3	1469.8	1469.4	1468.8	1469.4	1470.8	1472.2	1473.6	1475.0
172.5°	1477.5	1475.9	1475.4	1474.9	1474.5	1474.0	1474.5	1475.9	1477.3	1478.7	1480.2
175°	1483.2	1481.5	1481.0	1480.6	1480.1	1479.6	1480.2	1481.9	1483.5	1485.2	1486.8
177.5°	1484.1	1482.8	1482.6	1482.4	1482.2	1482.0	1482.6	1483.9	1485.2	1486.6	1487.9
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6



TEST NUMBER: P331759-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2240.2	2242.0	2254.4	2260.0	2271.2	2275.4	2280.5	2279.2	2279.2	2281.7	2299.0
5°	2245.0	2260.5	2283.7	2306.1	2327.8	2346.3	2358.7	2371.2	2375.8	2398.2	2418.3
7.5°	2237.0	2265.4	2303.8	2338.0	2379.0	2411.1	2437.7	2461.6	2478.1	2510.7	2544.2
10°	2226.4	2266.6	2310.0	2354.1	2410.5	2453.2	2496.5	2529.8	2540.6	2589.4	2617.3
12.5°	2205.3	2259.3	2314.3	2371.5	2426.7	2485.4	2533.0	2566.3	2604.3	2648.2	2699.6
15°	2173.8	2235.7	2307.6	2381.2	2460.1	2531.3	2582.4	2640.4	2682.2	2730.2	2775.1
17.5°	2128.5	2208.2	2299.7	2384.8	2476.1	2552.5	2622.8	2678.5	2708.0	2735.3	2742.0
20°	2092.5	2178.5	2286.0	2386.6	2477.9	2566.2	2635.7	2682.2	2690.0	2690.7	2649.7
22.5°	2053.6	2150.6	2263.1	2366.2	2475.5	2573.5	2627.8	2647.6	2616.9	2564.5	2485.1
25°	1981.9	2094.1	2224.8	2342.5	2461.6	2554.6	2573.1	2538.3	2430.7	2317.7	2174.5
27.5°	1904.2	2030.3	2170.5	2301.3	2428.2	2485.8	2445.7	2320.2	2126.5	1958.0	1753.9
30°	1847.2	1988.8	2126.6	2272.8	2390.5	2415.2	2323.2	2138.2	1912.2	1658.4	1454.9
32.5°	1782.2	1930.7	2082.0	2233.2	2331.7	2307.5	2155.4	1927.7	1662.7	1413.2	1220.8
35°	1689.3	1842.6	2005.9	2157.6	2220.2	2115.8	1888.2	1591.9	1321.0	1088.0	955.7
37.5°	1582.1	1749.0	1918.7	2058.0	2053.6	1879.5	1569.5	1263.5	1035.9	898.2	803.9
40°	1505.9	1674.7	1858.1	1975.7	1925.4	1698.6	1362.8	1074.1	907.8	797.9	729.0
42.5°	1432.9	1602.3	1784.4	1877.8	1790.4	1511.7	1177.1	950.9	813.6	727.9	672.1
45°	1308.6	1487.3	1656.1	1707.9	1551.6	1244.4	951.9	787.8	696.5	633.0	594.3
47.5°	1187.1	1362.9	1516.9	1517.8	1306.5	1009.2	802.9	681.8	603.8	554.7	526.5
50°	1112.8	1280.0	1409.2	1389.1	1149.2	897.7	718.1	613.7	548.7	510.8	481.3
52.5°	1029.3	1191.4	1303.3	1246.1	1016.1	789.9	642.0	554.2	500.4	467.4	441.1
55°	907.8	1051.7	1130.6	1043.9	828.8	657.0	542.5	473.6	433.3	405.5	383.0
57.5°	788.4	907.2	956.8	855.9	682.7	544.8	458.9	407.2	367.3	347.3	335.7
60°	713.5	814.9	849.7	738.3	593.6	476.7	406.3	358.3	328.9	315.8	304.2
62.5°	639.9	722.7	737.0	634.9	517.5	417.3	356.8	316.2	296.7	284.2	273.2
65°	530.9	590.5	583.5	501.5	409.4	331.2	287.1	262.4	247.6	229.8	210.5
67.5°	437.1	473.4	451.5	390.0	312.5	257.4	228.6	209.8	191.6	174.7	170.3
70°	377.7	398.5	375.4	318.8	256.1	215.9	192.7	170.3	159.5	155.5	148.6
72.5°	320.7	328.0	302.9	254.5	208.4	178.7	156.1	143.6	137.7	134.5	130.0
75°	240.7	235.3	213.6	175.7	144.7	124.6	117.6	113.0	109.1	106.0	103.7
77.5°	169.1	161.1	141.8	117.0	100.8	91.2	86.9	84.5	82.6	81.1	78.8
80°	126.9	121.5	102.2	83.6	76.6	72.0	69.7	66.6	66.6	65.0	62.7
82.5°	92.9	86.8	70.0	61.3	57.5	54.6	52.9	51.1	50.5	50.8	49.1
85°	48.8	39.5	34.8	33.3	31.0	29.4	30.2	28.7	28.7	28.7	27.9
87.5°	15.6	13.0	12.9	12.8	13.9	14.3	14.0	14.4	15.5	15.0	16.0
90°	3.7	6.4	9.0	11.6	13.8	15.8	17.7	19.6	21.5	22.6	23.8
92.5°	21.4	21.2	21.0	20.7	21.1	22.0	23.0	23.9	24.9	25.5	26.2
95°	61.9	54.0	46.2	38.3	35.1	36.9	38.6	40.2	41.9	43.0	44.2
97.5°	116.3	94.1	71.9	49.8	40.6	44.4	48.3	52.2	56.0	57.0	58.0
100°	157.3	124.6	92.0	59.3	44.9	49.0	53.1	57.2	61.2	63.1	65.0
102.5°	239.7	232.9	225.9	219.0	198.6	164.7	130.8	96.8	62.9	65.4	67.9
105°	333.6	340.6	347.8	355.0	326.0	260.8	195.7	130.6	65.4	68.1	70.7
107.5°	422.9	428.7	434.4	440.3	404.1	326.0	247.9	169.8	91.7	89.0	86.3
110°	480.6	485.6	490.6	495.6	463.6	394.7	325.8	256.8	187.8	164.0	140.2



TEST NUMBER: P331759-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	535.0	539.4	543.8	548.3	542.0	524.9	508.0	490.9	473.8	386.9	299.8
115°	621.4	625.4	629.4	633.5	638.5	644.5	650.5	656.4	662.4	551.9	441.4
117.5°	699.3	703.9	708.4	713.0	717.2	721.3	725.5	729.5	733.7	706.9	680.2
120°	755.1	758.6	762.2	765.8	769.7	774.1	778.3	782.6	786.9	789.7	792.6
122.5°	803.3	807.1	810.9	814.7	818.9	823.5	828.2	832.9	837.6	839.3	841.0
125°	875.9	879.0	882.1	885.1	889.0	893.5	898.1	902.6	907.2	908.8	910.5
127.5°	942.6	946.0	949.5	952.9	956.2	959.7	963.0	966.4	969.9	972.3	974.7
130°	985.0	988.9	992.7	996.4	999.7	1002.3	1004.9	1007.5	1010.2	1012.8	1015.4
132.5°	1027.4	1030.7	1033.9	1037.1	1040.1	1042.7	1045.3	1047.9	1050.6	1052.8	1055.0
135°	1083.8	1087.6	1091.5	1095.2	1098.2	1100.3	1102.5	1104.7	1106.8	1109.2	1111.6
137.5°	1139.1	1141.8	1144.5	1147.1	1149.6	1152.2	1154.6	1157.0	1159.4	1161.7	1164.1
140°	1175.3	1177.2	1179.1	1181.0	1183.3	1185.9	1188.5	1191.1	1193.8	1195.9	1198.1
142.5°	1206.0	1207.7	1209.4	1211.1	1213.6	1216.5	1219.5	1222.5	1225.6	1227.5	1229.4
145°	1252.5	1252.3	1252.1	1251.8	1253.7	1257.8	1261.8	1266.0	1270.0	1271.6	1273.3
147.5°	1294.2	1293.3	1292.4	1291.5	1293.0	1297.1	1301.0	1305.0	1309.1	1310.3	1311.5
150°	1320.9	1319.3	1317.6	1316.0	1317.0	1320.8	1324.6	1328.5	1332.2	1333.7	1335.1
152.5°	1343.9	1342.0	1340.2	1338.4	1339.2	1342.8	1346.5	1350.1	1353.7	1355.1	1356.6
155°	1377.4	1375.2	1373.0	1370.9	1371.3	1374.1	1377.0	1379.9	1382.7	1384.1	1385.5
157.5°	1404.1	1402.3	1400.5	1398.7	1398.8	1400.8	1402.7	1404.7	1406.7	1408.4	1410.0
160°	1420.0	1418.5	1417.0	1415.6	1415.6	1417.0	1418.5	1420.0	1421.4	1422.8	1424.2
162.5°	1433.7	1432.2	1430.8	1429.4	1429.3	1430.5	1431.8	1433.0	1434.2	1435.8	1437.4
165°	1452.1	1450.7	1449.3	1447.8	1447.4	1448.1	1449.0	1449.7	1450.4	1452.0	1453.7
167.5°	1465.9	1464.4	1463.0	1461.6	1461.2	1461.9	1462.5	1463.2	1463.9	1465.5	1467.2
170°	1473.6	1472.2	1470.8	1469.4	1468.8	1469.4	1469.8	1470.3	1470.8	1472.4	1474.1
172.5°	1478.7	1477.3	1475.9	1474.5	1474.0	1474.5	1474.9	1475.4	1475.9	1477.5	1479.3
175°	1485.2	1483.5	1481.9	1480.2	1479.6	1480.1	1480.6	1481.0	1481.5	1483.2	1484.8
177.5°	1486.6	1485.2	1483.9	1482.6	1482.0	1482.2	1482.4	1482.6	1482.8	1484.1	1485.4
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6



TEST NUMBER: P331759-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2305.2	2313.2	2316.9	2316.9	2321.3	2319.5	2317.5
5°	2437.7	2452.4	2455.5	2469.4	2479.4	2476.4	2477.9
7.5°	2569.4	2593.0	2616.5	2627.2	2628.8	2635.0	2637.4
10°	2650.5	2669.9	2706.2	2700.8	2727.8	2743.4	2717.8
12.5°	2728.5	2754.6	2779.9	2786.8	2802.2	2807.1	2797.0
15°	2799.0	2813.0	2814.6	2810.7	2815.3	2811.5	2796.7
17.5°	2733.1	2710.6	2664.7	2643.0	2625.9	2600.5	2590.3
20°	2624.1	2557.6	2480.2	2449.3	2412.9	2341.7	2358.7
22.5°	2388.9	2313.1	2235.7	2145.4	2102.1	2034.7	2030.6
25°	2022.9	1892.1	1748.2	1647.6	1588.7	1521.5	1492.0
27.5°	1572.8	1408.2	1290.2	1230.4	1176.1	1122.8	1120.5
30°	1276.9	1153.1	1061.8	1010.7	977.3	954.9	959.6
32.5°	1076.3	991.5	929.9	887.5	862.8	846.0	845.7
35°	879.9	821.8	782.3	764.6	746.8	734.4	735.2
37.5°	753.0	718.1	696.2	676.5	665.4	659.3	655.9
40°	687.9	659.3	642.3	630.7	621.4	612.9	611.4
42.5°	636.6	612.9	595.9	586.7	578.0	572.1	570.5
45°	564.9	545.5	530.1	520.1	516.1	510.8	510.8
47.5°	502.5	483.5	471.4	465.1	458.5	454.8	454.7
50°	460.5	445.8	434.9	431.0	425.7	423.3	422.5
52.5°	422.7	411.7	403.9	401.3	399.0	396.1	396.6
55°	371.4	365.3	362.1	359.8	356.0	351.3	354.5
57.5°	328.3	323.1	314.7	307.4	303.9	300.5	301.8
60°	297.9	287.1	276.3	267.7	265.4	258.4	258.4
62.5°	259.5	244.4	231.1	226.3	224.0	220.8	220.0
65°	199.7	193.5	190.4	187.2	185.7	185.7	184.2
67.5°	165.4	163.0	159.6	158.8	157.2	156.8	156.3
70°	146.2	143.2	141.6	140.9	139.3	140.1	137.7
72.5°	127.6	125.2	124.9	122.9	122.0	122.1	120.4
75°	100.6	100.6	99.9	99.1	97.6	96.7	97.6
77.5°	77.4	77.6	76.1	76.0	75.8	76.0	75.2
80°	61.9	62.7	61.9	61.1	60.4	61.1	60.4
82.5°	48.9	47.9	47.7	47.6	47.4	46.9	46.8
85°	27.9	28.7	27.9	27.1	27.1	27.1	27.9
87.5°	15.6	15.8	16.0	16.1	16.2	16.3	15.7
90°	25.0	26.3	27.1	27.6	28.1	28.5	29.0
92.5°	26.8	27.4	27.9	28.2	28.4	28.7	29.0
95°	45.4	46.7	47.2	46.9	46.7	46.4	46.2
97.5°	58.9	59.9	60.5	60.8	61.1	61.3	61.6
100°	67.0	68.9	70.0	70.5	71.0	71.5	71.9
102.5°	70.4	72.8	74.4	75.0	75.7	76.4	77.1
105°	73.3	75.9	77.8	78.8	79.7	80.6	81.6
107.5°	83.6	81.0	80.2	81.1	82.0	83.0	83.9
110°	116.3	92.4	81.0	81.9	82.9	83.8	84.8



TEST NUMBER: P331759-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	212.8	125.7	82.6	83.4	84.1	84.9	85.6
115°	331.0	220.6	156.7	139.6	122.4	105.2	88.1
117.5°	653.5	626.8	585.2	528.8	472.3	415.9	359.4
120°	795.5	798.4	783.7	751.4	719.2	687.0	654.9
122.5°	842.7	844.4	842.1	836.0	829.7	823.4	817.2
125°	912.1	913.8	915.0	915.7	916.5	917.2	917.9
127.5°	977.1	979.6	980.9	981.0	981.2	981.3	981.4
130°	1018.0	1020.7	1021.9	1021.7	1021.4	1021.2	1021.0
132.5°	1057.3	1059.6	1060.6	1060.3	1060.1	1059.9	1059.6
135°	1114.0	1116.3	1117.3	1116.8	1116.3	1115.9	1115.4
137.5°	1166.4	1168.7	1169.5	1168.7	1167.9	1167.1	1166.3
140°	1200.2	1202.3	1202.9	1201.6	1200.4	1199.2	1198.1
142.5°	1231.4	1233.3	1233.8	1232.5	1231.3	1230.2	1229.0
145°	1275.0	1276.7	1276.9	1275.8	1274.6	1273.3	1272.1
147.5°	1312.8	1314.0	1314.1	1313.1	1312.1	1311.1	1310.1
150°	1336.6	1338.0	1338.1	1336.9	1335.7	1334.5	1333.3
152.5°	1358.1	1359.5	1359.4	1357.8	1356.2	1354.6	1353.1
155°	1387.0	1388.5	1388.2	1386.2	1384.4	1382.5	1380.6
157.5°	1411.6	1413.2	1413.1	1411.3	1409.4	1407.5	1405.6
160°	1425.6	1427.0	1426.9	1425.3	1423.6	1422.0	1420.3
162.5°	1439.1	1440.8	1440.5	1438.5	1436.4	1434.3	1432.3
165°	1455.3	1457.0	1457.0	1455.3	1453.7	1452.0	1450.4
167.5°	1468.8	1470.6	1470.3	1468.1	1466.0	1463.9	1461.7
170°	1475.7	1477.4	1477.1	1475.0	1472.9	1470.8	1468.5
172.5°	1480.9	1482.6	1482.4	1480.2	1478.0	1475.9	1473.7
175°	1486.5	1488.1	1487.8	1485.4	1483.0	1480.7	1478.2
177.5°	1486.7	1488.1	1487.9	1486.2	1484.5	1482.8	1481.1
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6

(END OF REPORT)