

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332929-927

Luminaire Tested: **SA4XXRDIP-C795D365U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332929-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C795D365U927-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3547.8 lumens  
Efficiency: N/A  
Efficacy: 101.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332929-927

CATALOG NUMBER: SA4XXRDIP-C795D365U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332929-927

CATALOG NUMBER: SA4XXRDIP-C795D365U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	76	76	76	72	
1	103	99	95	91	98	94	90	87	84	82	79	76	74	72	68	66	65	65	65	65	61	
2	94	87	81	75	89	82	77	72	74	70	66	67	64	61	60	58	55	55	55	55	52	
3	86	77	69	63	81	73	66	61	66	61	56	60	55	52	54	50	48	48	48	48	44	
4	79	68	60	54	75	65	58	52	59	53	48	53	49	45	48	44	41	41	41	41	38	
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	44	39	36	36	36	36	33	
6	67	55	47	41	64	53	45	39	48	42	37	44	38	34	40	35	32	32	32	32	30	
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	29	29	29	26	
8	58	45	38	32	55	44	36	31	40	34	29	37	31	28	33	29	26	26	26	26	24	
9	54	42	34	29	51	40	33	28	37	31	26	34	29	25	31	27	23	23	23	23	21	
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21	21	21	21	20	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8884	8884	8884
5°	8904	8795	8849
10°	8848	8689	8689
15°	8747	8507	8444
20°	8607	8267	8115
25°	8429	7986	7783
30°	8255	7690	7368
35°	8064	7383	6951
40°	7832	7032	6500
45°	7618	6687	6042
50°	7376	6286	5556
55°	7116	5871	5029
60°	6830	5414	4490
65°	6567	4846	3960
70°	6187	4216	3361
75°	5702	3497	2732
80°	4974	2664	2506
85°	4215	2418	2260



TEST NUMBER: P332929-927

CATALOG NUMBER: SA4XXRDIP-C795D365U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.4	2.9
10°-20°	288.3	8.1
20°-30°	416.3	11.7
30°-40°	471.8	13.3
40°-50°	455.6	12.8
50°-60°	378.9	10.7
60°-70°	261.6	7.4
70°-80°	132.6	3.7
80°-90°	35.1	1.0
90°-100°	23.9	0.7
100°-110°	70.7	2.0
110°-120°	120.0	3.4
120°-130°	158.3	4.5
130°-140°	177.8	5.0
140°-150°	174.7	4.9
150°-160°	146.9	4.1
160°-170°	97.7	2.8
170°-180°	34.2	1.0
0°-30°	807.9	22.8
0°-40°	1279.7	36.1
0°-60°	2114.3	59.6
0°-90°	2543.6	71.7
90°-120°	214.6	6.0
90°-150°	725.3	20.4
90°-180°	1004.0	28.3
0°-180°	3547.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1100	1100	1100	1100	1100	
5°	1099	1095	1085	1093	1092	104
15°	1047	1038	1018	1016	1010	295
25°	946	930	896	883	874	436
35°	818	790	749	721	705	511
45°	667	635	586	546	529	514
55°	506	471	417	375	357	452
65°	344	307	254	219	207	339
75°	183	151	112	93	88	193
85°	46	29	26	24	24	51
90°	1	4	6	8	8	3
95°	17	19	21	22	22	19
105°	65	66	67	67	68	69
115°	122	122	122	121	121	120
125°	178	178	177	177	176	158
135°	229	231	231	230	230	177
145°	278	280	280	280	279	174
155°	319	319	319	320	319	147
165°	347	347	346	348	347	98
175°	361	360	360	362	360	34
180°	362	362	362	362	362	



TEST NUMBER: P332929-927

CATALOG NUMBER: SA4XXRDIP-C795D365U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5
2.5°	1103.2	1102.6	1101.9	1101.4	1100.7	1099.6	1098.0	1096.4	1094.7	1093.1	1094.7
5°	1098.8	1098.0	1097.3	1096.5	1095.7	1094.3	1092.0	1089.8	1087.5	1085.3	1087.2
7.5°	1088.9	1088.1	1087.3	1086.5	1085.7	1083.9	1080.9	1078.0	1075.1	1072.1	1073.3
10°	1079.4	1078.5	1077.5	1076.6	1075.6	1073.5	1070.2	1066.8	1063.4	1060.0	1060.7
12.5°	1067.2	1066.2	1065.1	1064.0	1063.0	1060.4	1056.5	1052.4	1048.5	1044.5	1045.0
15°	1046.6	1044.9	1043.1	1041.5	1039.8	1036.6	1031.9	1027.2	1022.5	1017.9	1017.5
17.5°	1021.4	1019.0	1016.5	1014.2	1011.7	1007.7	1002.0	996.4	990.8	985.2	984.1
20°	1001.9	999.4	997.0	994.6	992.1	987.8	981.4	975.0	968.6	962.3	960.8
22.5°	980.3	977.6	974.9	972.1	969.4	964.6	957.7	950.9	944.1	937.3	935.1
25°	946.3	942.9	939.5	936.1	932.8	927.2	919.6	911.9	904.2	896.5	893.3
27.5°	910.5	906.3	902.1	897.9	893.6	887.4	879.2	871.0	862.8	854.6	850.6
30°	885.6	880.9	876.2	871.6	866.9	860.2	851.4	842.6	833.7	824.9	820.2
32.5°	859.3	854.1	848.7	843.4	838.2	831.0	821.9	812.8	803.7	794.6	789.2
35°	818.2	812.2	806.2	800.2	794.2	786.6	777.2	767.8	758.4	749.1	742.8
37.5°	774.2	768.0	761.8	755.7	749.5	741.2	730.9	720.5	710.1	699.7	692.6
40°	743.2	737.0	730.9	724.7	718.5	710.0	699.3	688.7	678.0	667.3	659.5
42.5°	713.5	707.0	700.6	694.1	687.6	678.8	667.7	656.6	645.5	634.3	626.3
45°	667.3	660.4	653.5	646.6	639.6	630.6	619.3	608.1	596.8	585.7	576.5
47.5°	619.6	612.5	605.4	598.2	591.0	581.6	570.0	558.3	546.6	534.9	525.4
50°	587.3	580.0	572.7	565.4	558.1	548.4	536.5	524.5	512.5	500.5	491.2
52.5°	554.3	547.2	540.0	532.8	525.7	515.9	503.7	491.4	479.1	466.8	457.3
55°	505.6	498.0	490.6	483.1	475.6	465.8	453.6	441.4	429.3	417.1	407.3
57.5°	457.4	449.6	441.8	434.0	426.2	416.3	404.3	392.4	380.4	368.4	358.5
60°	423.0	415.5	408.1	400.5	393.0	383.3	371.3	359.3	347.4	335.3	325.6
62.5°	392.0	384.2	376.4	368.6	360.8	350.8	338.5	326.2	313.9	301.7	292.6
65°	343.8	335.7	327.6	319.6	311.6	301.6	289.5	277.6	265.6	253.7	245.6
67.5°	293.7	286.1	278.3	270.6	262.8	253.5	242.3	231.2	220.1	209.0	202.0
70°	262.1	254.2	246.3	238.4	230.6	221.3	210.6	199.9	189.3	178.6	172.5
72.5°	228.4	221.3	214.1	207.0	199.9	191.3	181.3	171.1	161.1	151.0	145.7
75°	182.8	175.9	169.0	162.1	155.1	147.3	138.5	129.7	120.9	112.1	107.7
77.5°	136.7	130.8	124.9	119.1	113.1	106.6	99.6	92.4	85.3	78.2	75.7
80°	107.0	101.6	96.2	90.7	85.3	79.8	74.1	68.5	62.9	57.3	56.7
82.5°	81.4	76.4	71.5	66.5	61.5	57.4	54.2	50.9	47.7	44.5	44.0
85°	45.5	41.7	38.0	34.3	30.5	28.4	27.8	27.3	26.7	26.1	25.7
87.5°	15.7	14.6	13.5	12.5	11.4	10.9	10.9	10.8	10.7	10.7	10.6
90°	0.9	1.5	2.2	2.9	3.6	4.2	4.7	5.1	5.6	6.2	6.5
92.5°	6.0	6.8	7.5	8.3	9.1	9.7	10.1	10.4	10.8	11.1	11.3
95°	16.8	17.3	17.9	18.5	19.0	19.6	20.0	20.4	20.8	21.3	21.5
97.5°	29.3	29.8	30.3	30.7	31.1	31.6	32.1	32.6	33.1	33.7	33.9
100°	39.2	39.5	39.7	39.9	40.2	40.6	41.1	41.7	42.3	42.9	42.9
102.5°	49.5	49.6	49.7	49.8	49.9	50.2	50.7	51.3	51.7	52.2	52.4
105°	65.2	65.3	65.4	65.4	65.4	65.6	65.9	66.1	66.4	66.6	66.8
107.5°	81.8	81.8	81.9	82.0	82.1	82.1	82.1	82.1	82.2	82.2	82.4
110°	92.9	93.1	93.2	93.3	93.4	93.5	93.4	93.3	93.2	93.2	93.1



TEST NUMBER: P332929-927

CATALOG NUMBER: SA4XXRDIP-C795D365U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	104.6	104.6	104.6	104.6	104.6	104.6	104.5	104.4	104.3	104.2	104.2
115°	122.1	122.1	122.1	122.1	122.1	122.0	121.8	121.8	121.6	121.5	121.4
117.5°	138.5	138.6	138.6	138.6	138.7	138.7	138.6	138.6	138.4	138.3	138.2
120°	149.5	149.7	150.0	150.2	150.5	150.5	150.4	150.1	150.0	149.8	149.5
122.5°	160.9	161.0	161.1	161.2	161.3	161.3	161.2	161.1	161.1	161.0	160.7
125°	177.8	177.8	177.8	177.8	177.8	177.7	177.7	177.6	177.5	177.4	177.4
127.5°	193.1	193.2	193.5	193.6	193.8	193.8	193.8	193.6	193.5	193.5	193.3
130°	203.8	204.0	204.1	204.4	204.5	204.6	204.6	204.6	204.6	204.6	204.5
132.5°	214.8	214.9	215.0	215.2	215.3	215.3	215.3	215.2	215.2	215.2	215.0
135°	229.3	229.7	230.0	230.4	230.8	230.9	230.9	230.9	230.9	230.9	230.8
137.5°	245.0	245.3	245.4	245.6	245.7	245.9	246.0	246.1	246.2	246.3	246.1
140°	255.6	255.7	255.8	256.0	256.1	256.1	256.1	256.1	256.1	256.1	256.1
142.5°	265.2	265.3	265.5	265.5	265.7	265.8	265.7	265.6	265.6	265.5	265.5
145°	278.5	278.8	279.0	279.2	279.6	279.7	279.7	279.8	279.9	280.0	279.9
147.5°	291.8	292.1	292.3	292.6	292.9	293.0	293.0	292.9	292.9	292.9	292.8
150°	299.8	300.1	300.3	300.6	300.8	301.0	301.0	301.0	301.0	301.0	301.0
152.5°	307.4	307.6	307.7	307.8	308.0	308.1	308.2	308.2	308.2	308.3	308.5
155°	319.1	319.1	319.1	319.1	319.1	319.1	319.0	318.9	318.9	318.9	319.1
157.5°	329.0	328.8	328.8	328.7	328.5	328.4	328.4	328.4	328.4	328.4	328.6
160°	334.8	334.7	334.7	334.6	334.5	334.5	334.5	334.4	334.3	334.2	334.5
162.5°	340.2	340.0	339.8	339.7	339.5	339.5	339.4	339.3	339.2	339.1	339.5
165°	347.4	347.2	347.1	346.8	346.7	346.5	346.3	346.3	346.1	346.0	346.3
167.5°	352.9	352.7	352.4	352.1	351.9	351.7	351.8	351.8	351.8	351.8	352.2
170°	356.1	355.8	355.5	355.1	354.8	354.7	354.7	354.8	354.9	355.0	355.3
172.5°	358.3	358.1	357.7	357.5	357.3	357.1	357.1	357.2	357.2	357.2	357.6
175°	361.4	361.1	360.8	360.4	360.1	360.0	359.9	359.8	359.8	359.7	360.1
177.5°	362.4	362.2	361.9	361.6	361.4	361.3	361.3	361.3	361.3	361.3	361.6
180°	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9



TEST NUMBER: P332929-927

CATALOG NUMBER: SA4XXRDIP-C795D365U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5
2.5°	1096.4	1098.0	1099.6	1100.4	1100.3	1100.1	1099.9	1099.8
5°	1089.0	1090.9	1092.8	1093.5	1093.1	1092.8	1092.4	1092.0
7.5°	1074.5	1075.8	1077.0	1077.2	1076.7	1076.0	1075.5	1074.8
10°	1061.5	1062.2	1063.0	1063.0	1062.2	1061.5	1060.7	1060.0
12.5°	1045.4	1045.8	1046.3	1046.0	1045.0	1043.9	1042.8	1041.8
15°	1017.2	1016.8	1016.4	1015.6	1014.2	1012.9	1011.6	1010.3
17.5°	983.1	982.1	981.0	979.5	977.5	975.5	973.5	971.5
20°	959.3	957.7	956.2	954.3	951.9	949.4	947.0	944.6
22.5°	932.9	930.6	928.4	926.2	924.2	922.3	920.3	918.3
25°	890.2	887.0	883.8	881.3	879.4	877.6	875.7	873.8
27.5°	846.7	842.8	838.8	835.5	832.8	830.1	827.4	824.7
30°	815.6	810.9	806.2	802.3	799.4	796.4	793.4	790.4
32.5°	783.7	778.3	772.9	768.7	765.9	763.0	760.2	757.3
35°	736.3	730.0	723.7	718.7	715.4	712.0	708.6	705.3
37.5°	685.5	678.3	671.2	666.0	662.7	659.3	655.9	652.5
40°	651.6	643.7	635.9	630.3	626.9	623.5	620.2	616.8
42.5°	618.3	610.3	602.3	596.5	592.9	589.5	586.0	582.4
45°	567.3	558.1	548.9	542.6	539.2	535.9	532.5	529.2
47.5°	515.9	506.4	496.9	490.2	486.6	482.8	479.1	475.4
50°	481.8	472.5	463.0	456.6	453.0	449.5	445.9	442.4
52.5°	447.8	438.3	428.7	422.2	418.4	414.7	411.1	407.3
55°	397.6	387.9	378.2	371.5	368.0	364.4	360.8	357.3
57.5°	348.6	338.7	328.8	322.6	319.9	317.2	314.5	311.8
60°	315.9	306.2	296.4	290.0	287.1	284.1	281.1	278.1
62.5°	283.7	274.7	265.7	260.0	257.6	255.2	252.8	250.4
65°	237.5	229.5	221.4	216.3	214.0	211.8	209.5	207.3
67.5°	195.1	188.2	181.3	176.6	174.1	171.6	169.1	166.7
70°	166.3	160.1	153.9	149.9	148.1	146.2	144.3	142.4
72.5°	140.5	135.1	129.8	126.4	124.7	122.9	121.2	119.5
75°	103.5	99.2	94.8	92.1	91.0	89.9	88.7	87.6
77.5°	73.2	70.7	68.1	66.7	66.4	66.1	65.8	65.4
80°	56.2	55.6	55.1	54.7	54.5	54.3	54.1	53.9
82.5°	43.6	43.3	42.9	42.5	42.4	42.1	42.0	41.8
85°	25.3	25.0	24.6	24.4	24.4	24.4	24.4	24.4
87.5°	10.5	10.5	10.4	10.5	10.6	10.8	10.9	11.1
90°	6.9	7.3	7.7	7.9	8.0	8.2	8.2	8.4
92.5°	11.6	11.7	12.0	12.1	12.2	12.3	12.4	12.4
95°	21.6	21.9	22.0	22.1	22.1	22.1	22.1	22.1
97.5°	34.1	34.3	34.5	34.6	34.6	34.6	34.6	34.6
100°	43.1	43.2	43.3	43.4	43.4	43.4	43.4	43.4
102.5°	52.6	52.8	52.9	53.1	53.1	53.2	53.2	53.2
105°	67.0	67.2	67.3	67.6	67.7	68.0	68.1	68.3
107.5°	82.6	82.8	82.9	83.0	83.0	83.0	83.0	82.9
110°	93.0	92.8	92.7	92.8	92.9	93.2	93.3	93.5





TEST NUMBER: P332929-927

CATALOG NUMBER: SA4XXRDIP-C795D365U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	104.2	104.1	104.1	104.1	104.2	104.2	104.2	104.3
115°	121.4	121.3	121.2	121.2	121.1	121.0	121.0	121.0
117.5°	137.9	137.7	137.5	137.4	137.2	137.0	137.0	136.8
120°	149.2	148.9	148.5	148.5	148.5	148.7	148.8	148.9
122.5°	160.6	160.3	160.1	159.9	159.7	159.5	159.2	159.0
125°	177.2	177.1	177.0	176.8	176.7	176.6	176.5	176.3
127.5°	193.2	193.1	192.9	192.8	192.7	192.7	192.5	192.4
130°	204.4	204.2	204.1	203.9	203.7	203.4	203.2	203.0
132.5°	214.9	214.8	214.7	214.5	214.4	214.4	214.3	214.1
135°	230.7	230.6	230.4	230.3	230.1	229.9	229.7	229.6
137.5°	246.0	245.8	245.7	245.6	245.6	245.7	245.7	245.7
140°	256.0	256.0	255.9	255.8	255.8	255.7	255.6	255.6
142.5°	265.5	265.5	265.5	265.5	265.5	265.5	265.5	265.5
145°	279.8	279.7	279.7	279.6	279.4	279.2	279.0	278.8
147.5°	292.8	292.7	292.6	292.6	292.6	292.5	292.4	292.4
150°	301.0	301.0	301.0	300.9	300.9	300.8	300.7	300.6
152.5°	308.6	308.8	309.0	308.9	308.7	308.6	308.4	308.2
155°	319.3	319.6	319.8	319.8	319.6	319.3	319.1	318.9
157.5°	328.8	329.0	329.2	329.2	328.9	328.8	328.5	328.3
160°	334.6	334.8	335.0	334.9	334.6	334.3	334.0	333.7
162.5°	339.8	340.2	340.5	340.5	340.2	339.9	339.6	339.3
165°	346.7	347.1	347.5	347.5	347.3	347.1	346.8	346.6
167.5°	352.6	352.9	353.3	353.3	352.9	352.5	352.1	351.7
170°	355.7	356.1	356.5	356.4	356.0	355.5	355.1	354.7
172.5°	358.1	358.5	358.9	358.9	358.5	358.0	357.6	357.1
175°	360.6	361.0	361.5	361.5	361.0	360.6	360.1	359.7
177.5°	361.9	362.3	362.7	362.7	362.3	361.9	361.5	361.1
180°	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9

(END OF REPORT)