

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331739-840

Luminaire Tested: **SA2XXRDIP-C1005D330U840-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331739-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D330U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4701.3 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331739-840

CATALOG NUMBER: SA2XXRDIP-C1005D330U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331739-840

CATALOG NUMBER: SA2XXRDIP-C1005D330U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75
1	104	100	96	93	99	95	92	89	86	84	81	78	76	75	71	69	68	64
2	95	88	82	77	91	84	79	74	77	72	69	70	66	63	63	61	58	55
3	88	78	71	65	83	75	68	63	68	63	59	62	58	55	57	53	51	48
4	81	70	62	56	76	67	60	54	61	55	51	56	51	47	51	47	44	41
5	74	63	55	49	71	60	53	47	55	49	44	51	46	42	47	42	39	36
6	69	57	49	43	65	54	47	42	50	44	39	46	41	37	43	38	35	32
7	64	52	44	38	61	50	42	37	46	40	35	42	37	33	39	35	31	29
8	60	47	39	34	57	45	38	33	42	36	32	39	34	30	36	32	28	26
9	56	43	36	31	53	42	35	30	39	33	29	36	31	27	33	29	26	24
10	52	40	33	28	50	39	32	27	36	30	26	34	28	25	31	27	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27611	27611	27611
5°	27716	27266	27417
10°	27506	26820	26591
15°	27189	26024	25275
20°	26751	24890	23639
25°	26302	23599	22057
30°	25682	22275	20025
35°	25074	20834	18242
40°	24464	19344	16179
45°	23749	17671	14312
50°	23016	15978	12479
55°	22261	14159	10716
60°	21390	12245	8896
65°	20397	10288	8103
70°	19218	8478	7449
75°	17767	7723	6949
80°	15676	6908	6332
85°	12338	5446	5446



TEST NUMBER: P331739-840

CATALOG NUMBER: SA2XXRDIP-C1005D330U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.1	3.4
10°-20°	439.5	9.3
20°-30°	617.2	13.1
30°-40°	673.0	14.3
40°-50°	618.8	13.2
50°-60°	486.0	10.3
60°-70°	316.9	6.7
70°-80°	163.4	3.5
80°-90°	44.1	0.9
90°-100°	26.8	0.6
100°-110°	83.2	1.8
110°-120°	142.2	3.0
120°-130°	187.0	4.0
130°-140°	209.9	4.5
140°-150°	205.8	4.4
150°-160°	172.7	3.7
160°-170°	114.5	2.4
170°-180°	40.0	0.9
0°-30°	1216.8	25.9
0°-40°	1889.8	40.2
0°-60°	2994.7	63.7
0°-90°	3519.0	74.9
90°-120°	252.2	5.4
90°-150°	855.0	18.2
90°-180°	1182.0	25.1
0°-180°	4701.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1710	1710	1710	1710	1710	
5°	1710	1702	1682	1695	1692	162
15°	1627	1608	1557	1528	1512	458
25°	1476	1424	1325	1264	1238	679
35°	1272	1190	1057	963	926	796
45°	1040	933	774	668	627	803
55°	791	668	503	414	381	706
65°	534	408	269	219	212	529
75°	285	180	124	114	111	301
85°	67	36	29	29	29	78
90°	0	5	12	12	12	4
95°	19	22	23	23	22	21
105°	77	78	78	79	79	81
115°	143	145	144	144	143	141
125°	208	211	210	209	208	185
135°	269	272	273	273	272	207
145°	326	329	331	331	330	204
155°	373	374	375	377	376	172
165°	406	405	405	408	406	114
175°	422	421	420	422	421	40
180°	423	423	423	423	423	



TEST NUMBER: P331739-840

CATALOG NUMBER: SA2XXRDIP-C1005D330U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1
2.5°	1716.4	1715.0	1713.5	1712.2	1710.8	1708.6	1705.6	1702.6	1699.6	1696.6	1699.3
5°	1710.1	1708.4	1706.7	1705.0	1703.2	1700.2	1695.7	1691.2	1686.8	1682.3	1685.4
7.5°	1692.5	1690.4	1688.3	1686.1	1683.9	1680.3	1675.1	1669.8	1664.7	1659.4	1660.3
10°	1677.7	1675.3	1672.8	1670.4	1668.0	1663.3	1656.5	1649.6	1642.7	1635.9	1634.9
12.5°	1659.1	1656.1	1653.1	1650.2	1647.3	1641.3	1632.5	1623.8	1615.0	1606.2	1604.3
15°	1626.6	1622.8	1619.0	1615.2	1611.4	1603.7	1592.1	1580.3	1568.6	1556.9	1550.4
17.5°	1586.6	1580.8	1575.1	1569.3	1563.6	1553.2	1538.1	1523.2	1508.1	1493.2	1485.4
20°	1556.9	1550.0	1543.2	1536.3	1529.4	1517.4	1500.2	1483.0	1465.8	1448.6	1440.0
22.5°	1524.7	1517.0	1509.3	1501.7	1493.9	1480.4	1461.0	1441.6	1422.2	1402.8	1391.7
25°	1476.4	1465.4	1454.4	1443.4	1432.4	1415.6	1392.9	1370.2	1347.5	1324.7	1310.7
27.5°	1418.3	1406.3	1394.3	1382.4	1370.4	1351.6	1326.1	1300.4	1274.9	1249.3	1232.8
30°	1377.5	1364.3	1351.3	1338.2	1325.1	1304.8	1277.3	1249.8	1222.3	1194.8	1177.2
32.5°	1337.8	1322.5	1307.3	1292.0	1276.7	1255.1	1227.0	1198.9	1170.8	1142.8	1122.8
35°	1272.1	1254.7	1237.1	1219.5	1202.0	1178.1	1147.8	1117.6	1087.3	1057.0	1035.4
37.5°	1206.6	1187.3	1168.0	1148.7	1129.5	1103.8	1071.5	1039.3	1006.9	974.7	950.9
40°	1160.7	1140.1	1119.4	1098.8	1078.2	1051.2	1017.8	984.5	951.1	917.8	893.3
42.5°	1113.7	1092.0	1070.3	1048.4	1026.7	998.7	964.2	929.7	895.2	860.8	835.6
45°	1040.1	1016.9	993.9	970.9	947.9	918.3	882.1	846.1	809.9	773.9	749.4
47.5°	968.2	943.8	919.4	894.9	870.5	839.7	802.4	765.1	727.8	690.5	666.3
50°	916.3	891.8	867.4	842.9	818.5	787.4	749.6	711.8	673.9	636.1	612.4
52.5°	865.5	839.9	814.5	788.9	763.4	732.2	695.1	658.1	621.1	584.1	561.2
55°	790.8	764.1	737.2	710.3	683.6	651.6	614.4	577.2	540.2	503.0	482.3
57.5°	714.4	686.9	659.3	631.9	604.3	572.7	537.0	501.3	465.6	429.9	411.0
60°	662.4	634.9	607.3	579.9	552.3	520.9	485.4	450.0	414.5	379.2	361.6
62.5°	611.7	584.1	556.6	529.1	501.6	470.9	437.2	403.3	369.6	335.9	319.1
65°	533.9	506.0	478.3	450.4	422.5	393.1	362.1	331.2	300.2	269.3	257.6
67.5°	459.0	431.4	403.7	376.1	348.4	320.6	292.9	265.0	237.1	209.2	203.9
70°	407.1	380.2	353.4	326.6	299.7	274.5	250.7	227.0	203.3	179.6	176.1
72.5°	357.5	331.7	306.1	280.3	254.6	232.2	213.2	194.1	175.0	156.0	153.1
75°	284.8	260.6	236.6	212.6	188.4	170.6	158.9	147.2	135.5	123.8	121.4
77.5°	213.3	192.2	171.1	150.0	128.8	115.4	109.8	104.1	98.5	92.9	91.5
80°	168.6	151.2	133.6	116.0	98.6	88.1	84.6	81.2	77.8	74.3	72.9
82.5°	127.8	114.1	100.5	86.7	73.1	65.0	62.7	60.4	58.1	55.7	54.9
85°	66.6	59.3	52.1	44.8	37.7	33.5	32.5	31.5	30.4	29.4	29.4
87.5°	19.9	17.9	15.9	13.8	11.8	11.0	11.3	11.7	12.0	12.4	12.1
90°	0.4	1.3	2.2	3.2	4.1	5.6	7.3	9.0	10.7	12.5	12.3
92.5°	6.4	7.1	7.8	8.5	9.2	9.7	10.1	10.5	10.9	11.3	11.4
95°	18.6	19.4	20.1	20.9	21.7	22.2	22.3	22.5	22.7	22.8	22.8
97.5°	33.9	34.6	35.2	36.0	36.7	37.2	37.5	37.8	38.1	38.4	38.4
100°	45.3	45.9	46.6	47.3	47.9	48.3	48.5	48.8	49.0	49.3	49.3
102.5°	57.3	57.8	58.3	58.8	59.3	59.8	60.0	60.3	60.6	60.9	61.0
105°	76.7	77.0	77.2	77.5	77.7	77.9	78.1	78.2	78.4	78.5	78.7
107.5°	96.2	96.6	96.9	97.4	97.7	97.9	97.9	97.9	97.9	97.9	97.9
110°	108.9	109.3	109.8	110.3	110.7	111.0	111.0	111.0	111.0	111.0	111.0



TEST NUMBER: P331739-840

CATALOG NUMBER: SA2XXRDIP-C1005D330U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	122.5	123.0	123.5	123.9	124.4	124.6	124.5	124.5	124.4	124.4	124.2
115°	142.7	143.2	143.7	144.1	144.6	144.8	144.6	144.4	144.3	144.1	144.1
117.5°	162.8	163.5	164.1	164.7	165.4	165.5	165.0	164.6	164.1	163.7	163.5
120°	176.2	176.9	177.5	178.1	178.7	178.7	178.1	177.5	176.9	176.2	176.2
122.5°	188.5	189.2	190.1	190.8	191.6	191.8	191.3	190.9	190.4	190.0	189.8
125°	207.6	208.3	209.0	209.7	210.5	210.8	210.5	210.3	210.1	209.7	209.5
127.5°	226.3	227.2	228.1	228.9	229.8	230.1	229.9	229.6	229.3	229.0	228.7
130°	238.0	239.0	240.0	241.1	242.1	242.6	242.4	242.3	242.1	241.9	241.8
132.5°	251.2	252.0	252.8	253.6	254.5	254.9	254.9	255.0	255.0	255.0	254.7
135°	268.6	269.5	270.4	271.2	272.2	272.7	272.9	273.0	273.2	273.3	273.2
137.5°	287.1	287.8	288.5	289.3	290.0	290.4	290.6	290.8	291.0	291.2	291.2
140°	298.3	299.0	299.7	300.4	301.1	301.6	302.1	302.5	302.9	303.3	303.3
142.5°	309.7	310.4	311.1	311.8	312.6	313.1	313.3	313.6	313.9	314.1	314.2
145°	326.1	326.7	327.2	327.8	328.3	328.8	329.3	329.8	330.2	330.7	330.8
147.5°	340.7	341.4	342.0	342.7	343.4	343.9	344.2	344.6	344.9	345.2	345.4
150°	350.7	351.2	351.6	352.1	352.6	353.0	353.4	353.7	354.0	354.3	354.6
152.5°	359.6	360.0	360.5	361.0	361.4	361.9	362.2	362.6	363.0	363.5	363.8
155°	372.8	373.0	373.3	373.5	373.8	374.1	374.3	374.5	374.8	375.0	375.4
157.5°	384.2	384.4	384.5	384.7	384.9	385.0	385.2	385.3	385.4	385.6	386.1
160°	391.0	391.2	391.3	391.5	391.6	391.8	391.8	391.9	392.0	392.1	392.5
162.5°	397.3	397.4	397.4	397.4	397.5	397.5	397.6	397.7	397.8	397.8	398.4
165°	405.7	405.6	405.5	405.5	405.4	405.3	405.3	405.3	405.3	405.3	405.9
167.5°	412.6	412.4	412.2	411.9	411.7	411.6	411.5	411.5	411.5	411.5	412.0
170°	416.4	416.2	415.9	415.7	415.5	415.3	415.2	415.1	415.1	415.0	415.5
172.5°	418.9	418.7	418.5	418.2	418.0	417.8	417.8	417.7	417.6	417.5	418.1
175°	422.1	421.8	421.6	421.3	421.1	420.9	420.8	420.6	420.4	420.3	420.8
177.5°	423.3	423.1	422.9	422.8	422.6	422.4	422.3	422.2	422.0	421.9	422.3
180°	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8



TEST NUMBER: P331739-840

CATALOG NUMBER: SA2XXRDIP-C1005D330U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1
2.5°	1702.0	1704.8	1707.6	1708.6	1708.1	1707.6	1707.0	1706.5
5°	1688.5	1691.6	1694.7	1695.7	1694.7	1693.6	1692.6	1691.6
7.5°	1661.1	1662.0	1662.9	1662.5	1660.7	1658.9	1657.2	1655.4
10°	1633.8	1632.7	1631.7	1630.2	1628.1	1626.1	1624.0	1621.9
12.5°	1602.5	1600.5	1598.7	1596.1	1592.7	1589.2	1585.8	1582.4
15°	1543.9	1537.3	1530.8	1525.8	1522.4	1518.9	1515.5	1512.1
17.5°	1477.6	1469.9	1462.1	1455.2	1449.4	1443.4	1437.4	1431.6
20°	1431.4	1422.8	1414.2	1406.1	1398.6	1391.0	1383.4	1375.8
22.5°	1380.7	1369.6	1358.5	1350.1	1344.5	1338.9	1333.2	1327.6
25°	1296.6	1282.5	1268.4	1258.8	1253.5	1248.4	1243.2	1238.1
27.5°	1216.4	1199.9	1183.5	1171.1	1163.0	1154.8	1146.6	1138.4
30°	1159.7	1142.2	1124.6	1111.3	1102.0	1092.7	1083.4	1074.1
32.5°	1102.8	1082.8	1062.7	1048.3	1039.7	1030.9	1022.1	1013.4
35°	1013.7	992.1	970.4	955.7	948.2	940.6	933.0	925.5
37.5°	927.0	903.1	879.2	862.9	854.3	845.7	837.0	828.3
40°	868.9	844.4	820.1	803.4	794.5	785.5	776.6	767.6
42.5°	810.3	785.1	759.8	742.9	734.2	725.5	716.9	708.2
45°	725.0	700.5	676.1	659.8	651.6	643.3	635.0	626.8
47.5°	642.0	617.7	593.4	577.5	570.1	562.6	555.0	547.5
50°	588.7	564.9	541.2	525.6	518.5	511.2	504.0	496.8
52.5°	538.3	515.3	492.5	477.7	471.0	464.3	457.7	451.0
55°	461.7	441.1	420.4	406.9	400.3	393.7	387.3	380.7
57.5°	392.1	373.1	354.3	342.0	336.6	331.0	325.6	320.0
60°	344.1	326.6	309.0	297.5	292.0	286.5	280.9	275.5
62.5°	302.5	285.7	269.0	258.9	255.7	252.4	249.0	245.8
65°	245.9	234.2	222.5	216.1	215.1	214.1	213.1	212.1
67.5°	198.5	193.2	187.7	184.5	183.5	182.4	181.3	180.2
70°	172.7	169.3	165.8	163.4	162.0	160.6	159.3	157.8
72.5°	150.3	147.3	144.4	142.6	141.8	141.0	140.1	139.3
75°	119.0	116.6	114.2	112.8	112.5	112.1	111.8	111.4
77.5°	90.1	88.8	87.4	86.3	85.8	85.3	84.7	84.2
80°	71.5	70.2	68.8	68.1	68.1	68.1	68.1	68.1
82.5°	54.0	53.2	52.4	52.0	52.0	52.0	52.0	52.0
85°	29.4	29.4	29.4	29.4	29.4	29.4	29.4	29.4
87.5°	11.8	11.5	11.2	11.0	11.0	11.1	11.1	11.1
90°	12.2	12.0	11.8	11.8	11.9	12.0	12.0	12.1
92.5°	11.4	11.4	11.5	11.5	11.5	11.5	11.5	11.5
95°	22.8	22.8	22.8	22.7	22.6	22.4	22.3	22.1
97.5°	38.4	38.4	38.4	38.4	38.4	38.4	38.4	38.3
100°	49.3	49.3	49.3	49.2	49.1	49.1	49.0	48.9
102.5°	61.1	61.1	61.2	61.2	61.1	61.0	61.0	60.9
105°	78.8	79.0	79.2	79.2	79.2	79.2	79.2	79.2
107.5°	98.0	98.1	98.1	98.0	97.6	97.3	96.8	96.4
110°	111.0	111.0	111.0	110.9	110.6	110.4	110.2	109.9



TEST NUMBER: P331739-840

CATALOG NUMBER: SA2XXRDIP-C1005D330U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	124.0	123.8	123.6	123.4	123.3	123.1	122.9	122.7
115°	144.0	143.9	143.8	143.7	143.4	143.2	143.0	142.7
117.5°	163.3	163.1	162.9	162.7	162.5	162.3	162.0	161.8
120°	176.2	176.2	176.2	176.1	175.9	175.6	175.4	175.2
122.5°	189.6	189.3	189.1	189.0	188.8	188.6	188.4	188.3
125°	209.3	209.0	208.8	208.6	208.6	208.5	208.4	208.3
127.5°	228.5	228.2	227.9	227.6	227.4	227.1	226.9	226.6
130°	241.6	241.5	241.3	241.1	240.8	240.3	240.0	239.7
132.5°	254.3	254.0	253.7	253.4	253.1	252.9	252.6	252.4
135°	273.2	273.1	273.0	272.9	272.6	272.4	272.2	271.9
137.5°	291.1	291.0	291.0	290.8	290.5	290.2	289.9	289.5
140°	303.3	303.3	303.3	303.1	302.8	302.5	302.2	301.8
142.5°	314.3	314.3	314.4	314.3	314.0	313.6	313.3	313.0
145°	330.9	330.9	331.0	330.9	330.6	330.3	330.0	329.6
147.5°	345.5	345.7	345.9	345.8	345.5	345.2	344.9	344.6
150°	354.8	355.0	355.3	355.3	355.0	354.8	354.6	354.3
152.5°	364.1	364.4	364.7	364.7	364.4	364.1	363.8	363.5
155°	375.8	376.2	376.6	376.7	376.4	376.2	376.0	375.7
157.5°	386.6	387.2	387.7	387.8	387.4	387.0	386.7	386.3
160°	393.0	393.5	394.0	394.0	393.7	393.4	393.1	392.8
162.5°	398.9	399.4	400.0	400.0	399.7	399.3	398.9	398.5
165°	406.4	407.0	407.5	407.6	407.2	406.8	406.4	406.1
167.5°	412.6	413.1	413.7	413.8	413.4	412.9	412.5	412.1
170°	416.1	416.6	417.2	417.2	416.8	416.3	415.8	415.3
172.5°	418.6	419.2	419.7	419.8	419.3	418.8	418.4	417.9
175°	421.4	421.9	422.5	422.5	422.1	421.6	421.1	420.6
177.5°	422.7	423.0	423.4	423.4	423.0	422.7	422.3	421.9
180°	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8

(END OF REPORT)