

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332658-830

Luminaire Tested: **SA4XXDIP-C1020D1035U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332658-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1020D1035U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8068.5 lumens
Efficiency: N/A
Efficacy: 133.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332658-830
CATALOG NUMBER: SA4XXDIP-C1020D1035U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332658-830

CATALOG NUMBER: SA4XXDIP-C1020D1035U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52				
1	98	94	90	86	91	87	83	80	74	71	69	62	60	59	51	50	49	44				
2	89	82	76	70	82	76	71	66	65	61	57	54	51	49	45	43	41	36				
3	82	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35	31				
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	36	33	30	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23				
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20				
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	24	21	18	16				
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	22	19	17	14				
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13130	13130	13130
5°	13169	13011	13105
10°	13086	12904	12969
15°	12929	12721	12754
20°	12718	12494	12506
25°	12479	12235	12200
30°	12185	11929	11820
35°	11880	11610	11456
40°	11564	11248	11041
45°	11233	10891	10683
50°	10868	10574	10246
55°	10473	10162	9831
60°	10078	9700	9405
65°	9635	9259	8886
70°	9135	8674	8337
75°	8372	7966	7764
80°	7452	7146	6969
85°	6521	6280	6150



TEST NUMBER: P332658-830

CATALOG NUMBER: SA4XXDIP-C1020D1035U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.2	1.9
10°-20°	431.5	5.3
20°-30°	635.2	7.9
30°-40°	738.4	9.2
40°-50°	738.4	9.2
50°-60°	645.9	8.0
60°-70°	479.7	5.9
70°-80°	272.5	3.4
80°-90°	82.3	1.0
90°-100°	43.0	0.5
100°-110°	274.3	3.4
110°-120°	524.8	6.5
120°-130°	666.2	8.3
130°-140°	712.8	8.8
140°-150°	666.5	8.3
150°-160°	537.5	6.7
160°-170°	346.7	4.3
170°-180°	119.5	1.5
0°-30°	1219.8	15.1
0°-40°	1958.2	24.3
0°-60°	3342.6	41.4
0°-90°	4177.1	51.8
90°-120°	842.2	10.4
90°-150°	2887.7	35.8
90°-180°	3891.0	48.2
0°-180°	8068.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1626	1626	1626	1626	1626	
5°	1625	1619	1606	1619	1617	154
15°	1547	1541	1522	1529	1526	436
25°	1401	1391	1374	1374	1370	644
35°	1205	1196	1178	1169	1162	753
45°	984	974	954	940	936	758
55°	744	739	722	707	698	666
65°	504	497	485	472	465	499
75°	268	262	255	250	249	285
85°	70	70	68	68	66	77
90°	3	13	21	26	28	6
95°	52	22	21	26	27	67
105°	283	289	294	300	268	296
115°	529	531	531	532	532	520
125°	743	747	745	748	749	663
135°	922	921	925	927	929	710
145°	1063	1066	1066	1067	1069	664
155°	1166	1166	1164	1167	1165	537
165°	1230	1225	1225	1232	1224	347
175°	1258	1253	1253	1261	1250	120
180°	1258	1258	1258	1258	1258	



TEST NUMBER: P332658-830

CATALOG NUMBER: SA4XXDIP-C1020D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1630.5	1629.8	1629.1	1628.4	1627.8	1626.1	1623.5	1621.0	1618.4	1615.9	1618.3
5°	1625.0	1623.9	1622.8	1621.6	1620.4	1618.3	1615.0	1611.8	1608.7	1605.5	1608.7
7.5°	1610.0	1608.7	1607.6	1606.5	1605.3	1603.0	1599.4	1595.9	1592.3	1588.8	1591.4
10°	1596.4	1595.3	1594.0	1592.9	1591.8	1589.3	1585.5	1581.8	1578.0	1574.2	1576.5
12.5°	1578.7	1577.5	1576.3	1575.2	1574.0	1571.4	1567.4	1563.5	1559.4	1555.5	1558.0
15°	1546.9	1545.7	1544.5	1543.4	1542.2	1539.5	1535.1	1530.8	1526.4	1522.1	1523.8
17.5°	1508.5	1507.1	1505.6	1504.2	1502.8	1500.0	1495.8	1491.8	1487.6	1483.6	1484.6
20°	1480.4	1478.9	1477.5	1476.0	1474.6	1471.7	1467.4	1463.0	1458.7	1454.3	1455.2
22.5°	1450.2	1448.2	1446.3	1444.4	1442.6	1439.4	1435.0	1430.7	1426.3	1422.0	1423.6
25°	1400.9	1398.9	1396.8	1394.8	1392.8	1389.8	1385.7	1381.7	1377.6	1373.6	1373.9
27.5°	1344.6	1342.6	1340.4	1338.3	1336.2	1333.3	1329.6	1325.8	1322.0	1318.2	1317.6
30°	1307.1	1304.8	1302.4	1300.1	1297.8	1294.8	1291.0	1287.2	1283.5	1279.7	1278.6
32.5°	1267.4	1265.4	1263.3	1261.2	1259.1	1256.0	1252.1	1248.1	1244.1	1240.1	1238.7
35°	1205.4	1203.4	1201.4	1199.4	1197.3	1194.3	1190.2	1186.2	1182.1	1178.1	1176.0
37.5°	1140.0	1138.1	1136.3	1134.4	1132.6	1129.5	1125.1	1120.8	1116.4	1112.1	1109.9
40°	1097.3	1095.0	1092.6	1090.3	1088.0	1084.7	1080.3	1076.0	1071.7	1067.3	1064.4
42.5°	1051.4	1050.0	1048.6	1047.3	1045.8	1042.7	1037.9	1033.1	1028.3	1023.5	1020.1
45°	983.9	981.8	979.9	977.8	975.8	972.4	967.8	963.2	958.6	953.9	950.7
47.5°	913.2	911.9	910.5	909.1	907.7	904.8	900.6	896.3	892.0	887.7	884.1
50°	865.3	864.1	863.0	861.9	860.6	858.1	854.0	850.0	845.9	841.9	837.8
52.5°	818.4	817.0	815.6	814.3	812.8	810.0	805.7	801.4	797.1	792.9	789.3
55°	744.1	743.2	742.3	741.5	740.6	738.2	734.1	730.1	726.0	722.0	718.5
57.5°	673.3	672.2	671.3	670.2	669.3	666.8	662.8	658.8	654.8	650.8	647.5
60°	624.2	622.7	621.3	619.9	618.4	615.9	612.1	608.3	604.5	600.8	598.1
62.5°	576.3	575.0	573.8	572.6	571.4	568.8	564.8	560.8	556.8	552.8	550.4
65°	504.4	502.8	501.4	500.0	498.5	496.3	493.4	490.6	487.7	484.7	481.9
67.5°	431.9	430.6	429.2	427.9	426.5	424.5	421.7	419.0	416.1	413.4	410.6
70°	387.0	385.0	383.0	381.0	378.9	376.7	374.5	372.1	369.9	367.5	365.1
72.5°	339.1	337.1	335.1	333.0	331.0	329.0	327.2	325.4	323.5	321.6	319.8
75°	268.4	267.0	265.5	264.1	262.7	261.2	259.8	258.4	256.8	255.4	254.3
77.5°	201.0	200.3	199.6	199.1	198.4	197.5	196.1	194.9	193.6	192.4	192.0
80°	160.3	159.4	158.5	157.7	156.8	156.1	155.5	155.0	154.4	153.7	153.2
82.5°	120.6	120.3	119.9	119.4	119.0	118.8	118.7	118.6	118.5	118.3	118.0
85°	70.4	70.4	70.4	70.4	70.4	70.1	69.5	68.9	68.3	67.8	67.8
87.5°	27.7	27.9	28.1	28.4	28.6	28.7	28.8	28.9	29.0	29.1	29.4
90°	2.8	5.1	7.4	9.7	12.1	14.0	15.6	17.3	19.0	20.7	22.0
92.5°	11.9	12.0	12.1	12.3	12.3	13.3	14.9	16.6	18.3	20.0	21.2
95°	51.7	44.7	37.5	30.4	23.3	19.9	20.1	20.3	20.5	20.7	22.0
97.5°	109.9	114.3	118.8	123.2	127.6	118.2	94.8	71.5	48.2	24.9	25.0
100°	154.3	158.1	161.8	165.6	169.4	156.8	128.0	99.2	70.2	41.4	37.9
102.5°	204.0	206.8	209.5	212.3	215.0	214.5	210.8	207.0	203.2	199.4	161.1
105°	283.2	284.5	285.7	287.0	288.2	289.4	290.4	291.4	292.6	293.6	295.5
107.5°	356.8	357.4	358.1	358.6	359.3	360.3	361.7	363.2	364.6	366.0	366.9
110°	406.5	407.1	407.7	408.3	409.0	409.9	411.1	412.5	413.7	414.9	415.4



TEST NUMBER: P332658-830

CATALOG NUMBER: SA4XXDIP-C1020D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	454.7	455.8	456.9	458.1	459.2	460.1	460.6	461.2	461.8	462.3	462.3
115°	528.8	529.4	530.1	530.7	531.3	531.5	531.3	531.1	530.8	530.7	531.1
117.5°	595.6	596.4	597.3	598.1	599.0	599.6	600.0	600.5	601.0	601.4	601.3
120°	640.7	641.6	642.4	643.3	644.1	644.4	644.2	644.0	643.8	643.6	644.0
122.5°	682.9	683.4	683.9	684.4	684.9	685.3	685.6	685.9	686.2	686.5	686.7
125°	743.3	744.1	745.0	745.8	746.7	746.9	746.5	746.0	745.6	745.2	745.8
127.5°	800.5	800.7	801.0	801.2	801.3	801.9	803.0	803.9	804.8	805.8	805.7
130°	837.4	837.6	837.8	838.0	838.2	838.7	839.3	839.9	840.6	841.2	841.4
132.5°	871.3	871.7	872.0	872.4	872.8	873.4	874.2	875.0	875.7	876.6	876.8
135°	922.1	921.9	921.7	921.4	921.2	921.5	922.4	923.2	924.1	924.9	925.3
137.5°	967.0	967.1	967.2	967.3	967.4	967.9	968.8	969.8	970.6	971.6	972.0
140°	996.5	996.8	997.3	997.7	998.1	998.5	998.9	999.4	999.8	1000.2	1000.8
142.5°	1022.8	1023.5	1024.3	1025.0	1025.8	1026.2	1026.5	1026.8	1027.0	1027.3	1027.7
145°	1063.2	1063.8	1064.5	1065.1	1065.7	1066.0	1066.0	1066.0	1066.0	1066.0	1066.3
147.5°	1095.4	1096.6	1097.8	1098.9	1100.1	1100.6	1100.3	1100.1	1099.9	1099.8	1099.9
150°	1118.7	1119.6	1120.4	1121.2	1122.1	1122.4	1122.2	1122.0	1121.8	1121.5	1121.5
152.5°	1138.3	1139.0	1139.6	1140.3	1140.9	1141.1	1140.8	1140.4	1140.0	1139.6	1140.0
155°	1165.8	1166.0	1166.2	1166.4	1166.6	1166.4	1165.8	1165.2	1164.5	1163.9	1164.7
157.5°	1188.9	1188.8	1188.6	1188.5	1188.5	1188.0	1187.3	1186.6	1185.9	1185.2	1186.3
160°	1202.5	1201.8	1201.3	1200.6	1200.0	1199.6	1199.4	1199.1	1198.9	1198.7	1200.0
162.5°	1214.6	1213.7	1213.0	1212.1	1211.4	1210.9	1210.6	1210.4	1210.2	1210.0	1211.3
165°	1229.7	1228.7	1227.7	1226.6	1225.6	1225.0	1225.0	1225.0	1225.0	1225.0	1226.7
167.5°	1241.8	1240.8	1239.6	1238.6	1237.5	1236.9	1236.7	1236.6	1236.5	1236.3	1238.2
170°	1248.6	1247.4	1246.0	1244.8	1243.6	1243.0	1243.2	1243.5	1243.7	1243.9	1245.6
172.5°	1253.1	1251.9	1250.6	1249.3	1248.1	1247.5	1247.7	1248.0	1248.2	1248.4	1250.1
175°	1258.0	1256.8	1255.5	1254.2	1253.0	1252.5	1252.6	1252.9	1253.1	1253.3	1255.2
177.5°	1260.3	1259.0	1257.9	1256.8	1255.6	1255.2	1255.5	1255.8	1256.1	1256.5	1257.8
180°	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0



TEST NUMBER: P332658-830

CATALOG NUMBER: SA4XXDIP-C1020D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1620.5	1622.9	1625.2	1626.3	1626.0	1625.8	1625.5	1625.3
5°	1611.8	1615.0	1618.3	1619.6	1619.0	1618.3	1617.8	1617.2
7.5°	1593.9	1596.5	1599.0	1600.2	1599.8	1599.4	1599.0	1598.7
10°	1578.9	1581.2	1583.5	1584.3	1583.8	1583.2	1582.6	1582.1
12.5°	1560.6	1563.1	1565.7	1566.5	1565.8	1564.9	1564.1	1563.3
15°	1525.6	1527.3	1529.1	1529.5	1528.6	1527.8	1526.9	1526.0
17.5°	1485.7	1486.9	1487.9	1488.2	1487.6	1487.0	1486.5	1485.8
20°	1456.0	1457.0	1457.8	1457.9	1457.4	1456.8	1456.2	1455.7
22.5°	1425.1	1426.7	1428.2	1428.5	1427.5	1426.4	1425.4	1424.4
25°	1374.1	1374.4	1374.7	1374.2	1373.1	1372.0	1370.7	1369.6
27.5°	1316.9	1316.2	1315.5	1314.5	1313.0	1311.5	1310.0	1308.6
30°	1277.4	1276.2	1275.1	1273.8	1272.3	1270.8	1269.4	1268.0
32.5°	1237.3	1236.0	1234.5	1233.1	1231.6	1230.2	1228.8	1227.3
35°	1174.0	1172.0	1170.0	1168.2	1166.8	1165.4	1163.9	1162.4
37.5°	1107.7	1105.5	1103.3	1101.3	1099.4	1097.4	1095.5	1093.6
40°	1061.5	1058.6	1055.7	1053.6	1052.1	1050.7	1049.2	1047.7
42.5°	1016.8	1013.4	1010.0	1007.9	1006.9	1005.9	1004.9	1004.0
45°	947.5	944.3	941.1	939.1	938.3	937.5	936.5	935.7
47.5°	880.5	876.9	873.4	870.4	868.3	866.0	863.8	861.7
50°	833.8	829.7	825.7	822.7	821.0	819.3	817.6	815.8
52.5°	785.7	782.0	778.4	775.6	773.4	771.2	769.0	766.8
55°	715.0	711.5	708.0	705.5	703.7	702.0	700.2	698.5
57.5°	644.2	640.9	637.6	635.1	633.4	631.8	630.1	628.4
60°	595.6	593.0	590.3	588.3	586.8	585.4	584.0	582.5
62.5°	548.1	545.6	543.3	541.4	540.0	538.5	537.1	535.6
65°	479.0	476.1	473.2	471.0	469.6	468.2	466.7	465.2
67.5°	407.8	405.0	402.3	400.7	400.2	399.8	399.4	399.1
70°	362.9	360.5	358.3	356.7	355.8	354.9	354.0	353.2
72.5°	317.9	316.0	314.2	312.8	312.0	311.1	310.3	309.3
75°	253.1	251.9	250.8	250.1	249.8	249.5	249.2	248.9
77.5°	191.6	191.3	191.0	190.4	189.6	188.9	188.1	187.4
80°	152.6	152.0	151.5	151.0	150.7	150.4	150.1	149.9
82.5°	117.6	117.3	117.0	116.6	116.3	116.0	115.7	115.5
85°	67.8	67.8	67.8	67.6	67.3	67.0	66.7	66.4
87.5°	29.7	29.9	30.2	30.3	30.4	30.5	30.5	30.6
90°	23.2	24.5	25.7	26.6	27.0	27.4	27.8	28.2
92.5°	22.4	23.8	25.0	25.6	25.7	25.8	25.9	26.0
95°	23.2	24.5	25.7	26.5	26.7	26.9	27.1	27.2
97.5°	25.1	25.3	25.4	25.5	25.7	25.9	26.1	26.4
100°	34.3	30.7	27.1	25.5	25.7	25.9	26.1	26.4
102.5°	122.8	84.5	46.1	27.0	27.0	27.1	27.1	27.1
105°	297.4	299.2	301.0	298.3	290.8	283.2	275.7	268.2
107.5°	367.9	368.8	369.7	370.5	371.4	372.1	373.0	373.7
110°	415.8	416.2	416.6	417.2	417.7	418.4	419.1	419.6



TEST NUMBER: P332658-830

CATALOG NUMBER: SA4XXDIP-C1020D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	462.2	462.1	462.0	462.4	463.2	464.0	464.8	465.5
115°	531.5	532.0	532.3	532.5	532.5	532.5	532.5	532.5
117.5°	601.2	601.2	601.1	601.1	601.0	600.9	600.8	600.7
120°	644.4	644.8	645.3	645.3	644.8	644.4	644.0	643.6
122.5°	687.0	687.2	687.5	687.4	687.0	686.5	686.2	685.7
125°	746.5	747.1	747.7	748.1	748.4	748.6	748.8	748.9
127.5°	805.6	805.4	805.3	805.1	805.0	804.8	804.6	804.5
130°	841.6	841.8	842.0	842.2	842.2	842.2	842.2	842.2
132.5°	876.9	877.2	877.4	877.4	877.2	877.0	876.9	876.8
135°	925.8	926.1	926.6	927.0	927.5	927.8	928.2	928.7
137.5°	972.5	973.0	973.5	973.6	973.5	973.4	973.2	973.1
140°	1001.5	1002.1	1002.7	1003.1	1003.3	1003.5	1003.7	1004.0
142.5°	1028.2	1028.7	1029.2	1029.4	1029.4	1029.4	1029.5	1029.5
145°	1066.5	1066.7	1066.9	1067.2	1067.6	1068.0	1068.5	1068.8
147.5°	1100.0	1100.2	1100.4	1100.6	1100.8	1101.0	1101.3	1101.5
150°	1121.5	1121.5	1121.5	1121.6	1121.9	1122.1	1122.3	1122.5
152.5°	1140.3	1140.7	1140.9	1141.0	1140.9	1140.9	1140.7	1140.6
155°	1165.5	1166.4	1167.2	1167.3	1166.8	1166.1	1165.5	1164.9
157.5°	1187.3	1188.5	1189.5	1189.5	1188.5	1187.3	1186.3	1185.2
160°	1201.3	1202.5	1203.7	1203.7	1202.5	1201.3	1200.0	1198.7
162.5°	1212.5	1213.8	1215.0	1214.9	1213.5	1212.1	1210.7	1209.3
165°	1228.4	1230.1	1231.7	1231.6	1229.7	1227.9	1226.0	1224.1
167.5°	1240.0	1241.9	1243.7	1243.6	1241.5	1239.4	1237.3	1235.2
170°	1247.3	1248.9	1250.6	1250.4	1248.3	1246.2	1244.1	1242.0
172.5°	1251.8	1253.4	1255.1	1254.8	1252.5	1250.3	1248.0	1245.8
175°	1257.1	1259.0	1260.8	1260.5	1258.0	1255.5	1253.0	1250.5
177.5°	1259.1	1260.5	1261.9	1261.5	1259.5	1257.5	1255.5	1253.5
180°	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0

(END OF REPORT)